



OVR DIN Rail SPD

OVRT22L40150PTSU

UL 1449 3rd Edition



Electrical Characteristics

Protection mode		L-L / L-G
Number of poles / Type of current		2 / AC
Type / Test class		UL 1449 3rd Ed. - Type 4 for Type 2 apps IEC 61 643-1 2nd Ed - T2 / II
Nominal voltage (U_n) (L-G)	V	120 +/- 15%
Frequency	Hz	50-60
Maximum continuous operating voltage (U_c) (L-G)	V	175
Voltage protection level (U_{res}) - 3/5/10kA (L-G)	kV	0.6/0.7/0.8
Voltage Protection Rating (VPR - UL 3rd Ed.) (L-G)	kV	0.6
Nominal discharge current (I_n @ 8/20)	kA	20
Maximum discharge current (I_{max} @ 8/20)	kA	40
Follow current interrupt rating (I_n)	A	None
Response time	ns	<25
Operating current (I_o)	mA	<0.1
Short circuit withstand current (I_{sc})	kA	200
Integrated thermal disconnecter		Yes
State indicator		Yes
Safety reserve		No
Remote indicator		Yes
Disconnecter	Circuit breaker - B or C curve	A
	Class J fuse	A
		≤125
		≤100

Mechanical Characteristics

Wire range - solid wire	AWG	4-14
Wire range - stranded wire	AWG	6-14
Stripping length	in	0.5
Tightening torque	in-lbs	24.5
Degree of protection		NEMA 1

Remote Indicator

Type of contact		1 NO / 1 NC
Minimum load		12 VDC / 10 mA
Maximum load		250 VAC / 1 A
Connection cross section	AWG	16

Miscellaneous Characteristics

Operating temperature	F	-40° to 176°
Maximum altitude	ft	6562
Weight	lb	0.5
Color of housing / Fire resistance according to UL 94		Gray RAL 7035 / V-0
Reference standards		UL 1449 3rd Ed, IEC 61 643-1 2nd Ed

Replacement Cartridges

Phase		OVRT240150CU
Neutral		-

Contact Us

ABB Inc.

Low Voltage Control Products
16250 W. Glendale Drive
New Berlin, WI 53151
Phone: 888-385-1221
Fax: 800-726-1441

USA Technical Support & Customer Service:

888-385-1221, Option 4
7:30AM to 5:30PM, CST,
Monday - Friday
lvps.support@us.abb.com

Web: www.abb.us/lowvoltage