

# Stanilite®

## Platinum Spitfire® LED surface mount Nexus® non-maintained



### Range

Platinum range

### Product group


Spitfire LED



### Features

- Superior photometric classification
- LED technology 100,000 hours plus lamp life
- Dual LED
- Low power consumption and LED light source for reduced operation and maintenance costs
- Advanced charging technology combined with Lithium iron phosphate battery for long life and low maintenance
- Nexus monitored, wireless
- RF frequency range 920 - 925 MHz
- Surface mount
- Low maintenance - ideal for factories and warehouses
- Ambient operating temperature; 10°C to 40°C

Catalogue no.	Description
<b>Nexus products</b>	
SGSFBNRF2LEDP	Platinum Spitfire dual LED surface mount Nexus RF
<b>Spare parts</b>	
03-01310P	Battery LiFePO4 3.2V 3.2Ah



Dimensions			
	Length	Width	Height
	288mm	167mm	68mm
Weight			
	Model	Weight	
	Nexus RF	2.2kg	
Construction			
	Part	Construction	
	Lamp head	White polycarbonate	
	Surface mount box	White powder coated steel box	

<b>Light source</b>		
	<b>Model</b>	<b>Light source</b>
	Dual LED	3W

<b>Power consumption</b>		
	<b>Model</b>	<b>Power consumption</b>
	Nexus RF	1.0W

Note:

- Complies to IEC 60598-1:2014, IEC 60598-2-22:2014, IEC 60598-2-1:1979+A1:1987 and SS 563-2:2010