



Test Report				Date of issue: 20.11.2015																																																																																												
				Type: M3JM 355LKA 2																																																																																												
				Product Code: 3GJM351810-_DG																																																																																												
				Protection type: Ex d l Mb																																																																																												
				Cert. No.: LCIE 10 ATEX 3089 X / IECEx LCI 04.0008X																																																																																												
Rating:																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>V</th> <th>Hz</th> <th>kW</th> <th>r/min</th> <th>A</th> <th>cos φ</th> <th>Duty</th> </tr> </thead> <tbody> <tr> <td>3-Motor</td> <td>690</td> <td>Y 50</td> <td>500</td> <td>2982</td> <td>479</td> <td>0,9</td> <td>S1</td> </tr> <tr> <td>Insul.cl.F</td> <td>400</td> <td>D 50</td> <td>500</td> <td>2982</td> <td>827</td> <td>0,9</td> <td>S1</td> </tr> <tr> <td>IP66</td> <td>415</td> <td>D 50</td> <td>500</td> <td>2983</td> <td>796</td> <td>0,9</td> <td>S1</td> </tr> </tbody> </table>												V	Hz	kW	r/min	A	cos φ	Duty	3-Motor	690	Y 50	500	2982	479	0,9	S1	Insul.cl.F	400	D 50	500	2982	827	0,9	S1	IP66	415	D 50	500	2983	796	0,9	S1																																																						
	V	Hz	kW	r/min	A	cos φ	Duty																																																																																									
3-Motor	690	Y 50	500	2982	479	0,9	S1																																																																																									
Insul.cl.F	400	D 50	500	2982	827	0,9	S1																																																																																									
IP66	415	D 50	500	2983	796	0,9	S1																																																																																									
Cold resistance				Insulation resistance at 69 °C			Overload																																																																																									
Line Ambient: 23 °C				4700 MΩ 1000 V			Torque 160% 15s																																																																																									
U ₁ - V ₁ 0,00260 Ω																																																																																																
U ₁ - W ₁ 0,00261 Ω																																																																																																
V ₁ - W ₁ 0,00260 Ω																																																																																																
				High-voltage test winding 2400 V			60 s																																																																																									
<table border="1"> <thead> <tr> <th rowspan="2">Test</th> <th rowspan="2">Torque [Nm]</th> <th colspan="2">Line</th> <th colspan="2">Input</th> <th colspan="2">Output</th> <th rowspan="2">cos φ</th> <th rowspan="2">η [%]</th> </tr> <tr> <th>U[V]</th> <th>f[Hz]</th> <th>I[A]</th> <th>P1 [kW]</th> <th>P2 [kW]</th> <th>n[r/min]</th> </tr> </thead> <tbody> <tr> <td>No load test</td> <td></td> <td>400,2</td> <td>D 50</td> <td>181,0</td> <td>6,47</td> <td></td> <td>3000</td> <td>0,05</td> <td></td> </tr> <tr> <td>Locked rotor test</td> <td></td> <td>57,2</td> <td>D 50</td> <td>827,0</td> <td>21,0</td> <td></td> <td>0</td> <td>0,26</td> <td></td> </tr> <tr> <td>Thermal test (100% load)</td> <td>1601</td> <td>400,3</td> <td>D 50</td> <td>825,8</td> <td>515,9</td> <td>500,0</td> <td>2983</td> <td>0,90</td> <td>96,9</td> </tr> <tr> <td>Partial load points:</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>~75% load</td> <td>1198</td> <td>400,8</td> <td>D 50</td> <td>630,8</td> <td>386,7</td> <td>375,0</td> <td>2988</td> <td>0,89</td> <td>97,0</td> </tr> <tr> <td>~50% load</td> <td>804</td> <td>400,6</td> <td>D 50</td> <td>447,4</td> <td>258,8</td> <td>250,0</td> <td>2992</td> <td>0,84</td> <td>96,6</td> </tr> <tr> <td>~25% load</td> <td>401,5</td> <td>400,9</td> <td>D 50</td> <td>284,1</td> <td>132,1</td> <td>125,0</td> <td>2997</td> <td>0,67</td> <td>94,7</td> </tr> </tbody> </table>											Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]	U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]	No load test		400,2	D 50	181,0	6,47		3000	0,05		Locked rotor test		57,2	D 50	827,0	21,0		0	0,26		Thermal test (100% load)	1601	400,3	D 50	825,8	515,9	500,0	2983	0,90	96,9	Partial load points:										~75% load	1198	400,8	D 50	630,8	386,7	375,0	2988	0,89	97,0	~50% load	804	400,6	D 50	447,4	258,8	250,0	2992	0,84	96,6	~25% load	401,5	400,9	D 50	284,1	132,1	125,0	2997	0,67	94,7
Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]																																																																																							
		U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]																																																																																									
No load test		400,2	D 50	181,0	6,47		3000	0,05																																																																																								
Locked rotor test		57,2	D 50	827,0	21,0		0	0,26																																																																																								
Thermal test (100% load)	1601	400,3	D 50	825,8	515,9	500,0	2983	0,90	96,9																																																																																							
Partial load points:																																																																																																
~75% load	1198	400,8	D 50	630,8	386,7	375,0	2988	0,89	97,0																																																																																							
~50% load	804	400,6	D 50	447,4	258,8	250,0	2992	0,84	96,6																																																																																							
~25% load	401,5	400,9	D 50	284,1	132,1	125,0	2997	0,67	94,7																																																																																							
Temperature rise at rated load.																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>[°C]</th> <th>[K]</th> <th>Method</th> <th>Measurement method</th> </tr> </thead> <tbody> <tr> <td>Stator winding :</td> <td></td> <td>71</td> <td>1</td> <td>1 Resistance</td> </tr> <tr> <td>Frame :</td> <td></td> <td>32</td> <td>2</td> <td>2 Thermocouples</td> </tr> <tr> <td>Bearing D-end :</td> <td></td> <td>58</td> <td>2</td> <td>3 Thermometer</td> </tr> <tr> <td>Ambient Temperature :</td> <td>25</td> <td></td> <td>2</td> <td></td> </tr> </tbody> </table>												[°C]	[K]	Method	Measurement method	Stator winding :		71	1	1 Resistance	Frame :		32	2	2 Thermocouples	Bearing D-end :		58	2	3 Thermometer	Ambient Temperature :	25		2																																																														
	[°C]	[K]	Method	Measurement method																																																																																												
Stator winding :		71	1	1 Resistance																																																																																												
Frame :		32	2	2 Thermocouples																																																																																												
Bearing D-end :		58	2	3 Thermometer																																																																																												
Ambient Temperature :	25		2																																																																																													
<p>Starting current (I_S / I_N) : 8,48</p> <p>Locked rotor torque (T_L / T_N) : 3,05</p> <p>These tests have been carried out on motor no. 3GF10028994B, on date 2010-06-04, which is identical in electrical design with the above.</p> <p>Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.</p> <p>On behalf of customer</p> <p>On behalf of manufacturer</p> <p>Tested by ABB Oy, Motors and Generators, Vaasa, Finland</p> <p>Telephone +358 10 2211 Telefax +358 10 22 47372</p>																																																																																																

Computer print-out valid without signature.