



Ref. Certif. No.
SE-96557M2

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Contactor
Name and address of the applicant	ABB France 11 Rue d'Arsonval 69680 Chassieu France
Name and address of the manufacturer	Same as applicant
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	See page 2
Ratings and principal characteristics	Ue = 220V / 400V / 440V / 500V / 690V / 1000V, Ie = 25 - 130A See also page 2
Trademark (if any)	
Customer's Testing Facility (CTF) Stage used	-
Model / Type Ref.	AF*80-30-**-**, AF*96-30-**-**, AF*80-40-**-**, AF*80-22-**-**
Additional information (if necessary may also be reported on page 2)	See page 2
A sample of the product was tested and found to be in conformity with	IEC 60947-4-1:2018
As shown in the Test Report Ref. No. which forms part of this Certificate	2025257STO-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden



Signature:

Date: 27 September, 2021

Quan Li

Factories

ABB France
11 Rue d'Arsonval
69680 Chassieu
FRANCE

ABB Xinhui Low Voltage Switchgear Company Ltd
Jinguzhou Ind. Development Zone
Xinhui District, Jiangmen City
Guangdong CN-529100
CHINA

Additional information

Rated conditional short-circuit current, $I_q = 35\text{kA}$ (1000V) or 80kA (690V, 3-pole) or 100 kA (220-440 / 500V)

Rated insulation voltage, $U_i = 1000\text{V}$

Rated impulse withstand voltage, $U_{imp}=8\text{kV}$

Type	AC-1: 1000V	AC-1: 690V	AC-3: 220- 440V	AC-3: 500V	AC-3: 690V	AC-3: 1000V	AC-3e 220- 440V	AC-3e 500V	AC-3e 690V	AC-4: 220- 500V	AC-4: 690V	AC-8a: 400V
AF80-30 (I_e):	50	125	80	65	49	25	80	65	49	65*	40	105
AF96-30 (I_e):	60	130	105	80	57	30	105	80	57	76*	45	120
AF80-40 (I_e):	50	125	80	65	49	25	-	-	-	65	40	-
AF80-22 (I_e):	50	125	80	65	49	25	-	-	-	65	40	-

*Also includes reversing starter contactor

Additional information (if necessary)

Type key

AF S 80 - 30 - 11 - 13
1 2 3 4 5 6

- 1 = Main designation
AF Contactor AF Range
- 2 = Application
"blank": standard application
S: contactor for safety application
- 3 = Size of contactor
80, 96
- 4 = Number of main contacts
30 = 3 NO- and 0 NC-contacts
40 = 4 NO- and 0 NC-contacts
22 = 2 NO- and 2 NC-contacts
- 5 = Number of auxiliary contacts
00 = 0 NO- and 0 NC-contacts.
04 = 0 NO- and 4 NC-contacts. Mounted as 2nd stack, (only for AFS)
11 = 1 NO- and 1 NC-contacts. Side mounting
13 = 1 NO- and 3 NC-contacts. Mounted as 2nd stack, (only for AFS)
22 = 2 NO- and 2 NC-contacts. Mounted as 2nd stack
31 = 3 NO- and 1 NC-contacts. Mounted as 2nd stack, (only for AFS)
- 6 = Coil configuration
11 = 20-60VDC/24-60VAC
12 = 48-130VAC/VDC
13 = 100-250VAC/VDC
14 = 250-500VAC/VDC
41 = 24-60VAC

This certificate replaces CB certificate SE-96557M1, dated 02 July 2020.

A new certificate is issued due to adding additional tests and change the address of the applicant and factory.

Date: 27 September, 2021

Signature: *Qian Li*