




On-load tap-changer type UCGL./III, VUCGL./III, UCLL./III, UCDL./III, 21 tap positions, linear switching.
 Max. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 11,
 the preceding pos. was 10.

Lindningskopplare typ UCGL./III, VUCGL./III, UCLL./III, UCDL./III, 21 lägen, linjär koppling.
 Max. antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 11,
 föregående läge var 10.



Tap selector
Väljare

Pos. Läge	Tap selector and diverter switch connect	Väljaren och lastkopplaren förbinder
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	
7	7-V-x	
8	8-H-v	
9	9-V-x	
10	10-H-v	
11	11-V-x	
12	12-H-v	
13	13-V-x	
14	14-H-v	
15	15-V-x	
16	16-H-v	
17	17-V-x	
18	18-H-v	
19	19-V-x	
20	20-H-v	
21	21-V-x	

The tap-changer is shown in pos. 11,
 the preceding pos. was 10.
 The tap selector is seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 11,
 föregående läge var 10.
 Väljaren sedd uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
 tap-changer. Dashed lines show leads belonging
 to the cleats and leads.

Heldragna linjer visar ledare som ingår i
 lindningskopplaren. Streckade linjer visar
 ledare som tillhör anslutningsdonet.

Drawn by Form No.	Sheet	Year Week Cont		-		-		-		
	Design checked by	Rev Ind	Revision	Appd	Year	Week				
		Accepted by qual control		Accepted for prod by		Description (English)			DATA ORIGINAL	
		G.Andersson GA		T.Larsen		CONNECTION DIAGRAM			File name	
Design checked by	A.Hultberg M		Issued by Dept Year Week		Description (own language)			Lang		
	COM/FOK 07 49		5492 0367-17			KOPPLINGSSCHEMA			Sheet	
	ABB		Asea Brown Boveri					1		
								Revind Cont		
								-		

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB 19