

C160 Custom Configuration

1 Introduction

ABB can supply custom configurations for the C160 Process Controller on request.

Enter the required setting or place a check mark (✓) against the relevant parameters in the following tables and return this document to the Global Sales office at Stonehouse.

2 Basic Hardware and Configuration

2.1 Hardware Assignment and Input Type

Referring to Section 4.3.1 of the User Guide (IM/C160), enter the setting required for each of the following parameters:

Frequency		Relay 1	Relay 2	Relay 3	Logic Output Source	Analog Output Source	✓ Required Configuration
50 Hz	60 Hz						
<i>i</i>	<i>fl</i>	Alarm 1	Alarm 2	Alarm 3	Totalizer Count Pulse*	PV	
<i>2</i>	<i>b</i>	Alarm 1	Alarm 2	Alarm 3	Totalizer Wrap Pulse*	PV	
<i>3</i>	<i>c</i>	Totalizer Count Pulse*	Alarm 1	Alarm 2	Totalizer Wrap Pulse*	PV	
<i>4</i>	<i>d</i>	Totalizer Wrap Pulse*	Alarm 1	Alarm 2	Totalizer Count Pulse*	PV	
<i>5</i>	<i>E</i>	Alarm 1	Alarm 2	Alarm 3	Totalizer Count Pulse*	PV Average	
<i>U</i>		Custom	Custom	Custom	Custom	Custom	

* Pulse energizes assigned relay

Continued...

Input Type Configuration (✓ the input type required)

THC Type B	
THC Type E	
THC Type J	
THC Type K	
THC Type N	
THC Type R	
THC Type S	
THC Type T	
PT100 RTD	
0 to 20 mA	
4 to 20 mA	
0 to 5 V	
1 to 5 V	
0 to 50 mV	
4 to 20 mA (Square Root)	
Custom	

Engineering Display Range (enter the values required)

Engineering High	
Engineering Low	

Temperature Units (✓ the units required)

Degrees C	
Degrees F	
No Temperature Units	

Decimal Places (✓ the number of decimal places required)

0	
1	
2	
3	
4	

2.2 Alarms and Set Points

Referring to Section 4.3.2 of the User Guide (IM/C160), enter the setting required for each of the following parameters:

Alarm 1 Type (✓ the alarm type required)

None	
High Process	
Low Process	
High Latch	
Low Latch	

Alarm 1 Trip (enter the Alarm 1 trip point value)

Alarm 2 Type (✓ the alarm type required)

None	
High Process	
Low Process	
High Latch	
Low Latch	

Alarm 2 Trip (enter the Alarm 2 trip point value)

Alarm Hysteresis (enter the Alarm hysteresis value)

2.3 Totalizer Configuration

Referring to Section 4.3.3 of the User Guide (IM/C160), enter the setting required for each of the following parameters:

Totalizer Setup (✓ the mode required)

Count Up, Wrap Off	
Count Up, Wrap On	
Count Down, Wrap Off	
Count Down, Wrap On	

Totalizer Display Decimal Places

(✓ the number of decimal places required)

0	
1	
2	
3	
4	
5	

Display	Max./Min. Values Displayed	Average Value Displayed	Preset/Predetermined Values Displayed	✓ required configuration
0	No	No	No	
1	Yes	No	No	
2	Yes	Yes	No	
3	No	Yes	Yes	
4	No	No	Yes	
5	Yes	No	Yes	
6	Yes	Yes	Yes	

Display	Totalizer Stop/Go	Totalizer Reset	Max./Min./Average	✓ required configuration
0	No	No	No	
1	Yes	No	No	
2	No	Yes	No	
3	Yes	No	Yes	
4	No	Yes	Yes	
5	Yes	Yes	Yes	

2.4 Digital Input

Referring to Section 4.3.4 of the User Guide (IM/C160), enter the setting required for each of the following parameters:

Digital Input Functions (✓ the function required)

None	
Totalizer Reset	
Totalizer Stop/Go	
Average, Max./Min. Reset	
Front Panel Lockout	
Alarm Acknowledge	

Analog Input Filter (✓ the filter value required)

0 Seconds	
1 Second	
2 Seconds	
5 Seconds	
10 Seconds	
20 Seconds	
40 Seconds	
60 Seconds	

2.5 Ranges

Referring to Section 4.4 of the User Guide (IM/C160), enter the value required for each of the following parameters:

Retransmission High	
Retransmission Low	
Totalizer Count High	
Totalizer Count Low	
Totalizer Cutoff	

ABB has Sales & Customer Support expertise in over 100 countries worldwide

www.abb.com

The Company's policy is one of continuous product improvement and the right is reserved to modify the information contained herein without notice.

Printed in UK (01.09)

© ABB 2009



ABB Limited
Oldends Lane, Stonehouse
Gloucestershire
GL10 3TA
UK
Tel: +44 (0)1453 826661
Fax: +44 (0)1453 829671

ABB Inc.
125 E. County Line Road
Warminster
PA 18974
USA
Tel: +1 215 674 6000
Fax: +1 215 674 7183