


On-load tap-changer type UCGL./C, VUCGL./C, 5 tap positions, linear switching.
 Max. effective No. of turns in pos. 1.
 The tap-changer is delivered set in pos. 3, the preceding pos. was 2.

Lindningskopplare typ UCGL./C, VUCGL./C, 5 lägen, linjär koppling.
 Max antal effektiva varv i läge 1.
 Lindningskopplaren levereras inställd i läge 3, föregående läge var 2.

Pos. Läge	Tap selector and diverter switch connect	30
1	1-V-x	
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	



The tap-changer is shown in pos. 3, the preceding pos. was 2.
 The tap selector is seen from above.
 Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 3, föregående läge var 2.
 Väljaren sedd uppifrån.
 Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the tap-changer. Dashed lines show leads belonging to the cleats and leads.

Heldragna linjer visar ledare som ingår i lindningskopplaren. Streckade linjer visar ledare som tillhör anslutningsdonet.

We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.
 © ABB 19

Sheet	Cont									
	Year	Week								
Dept			1	VUCG Added.	SUKN	07	47			
	Rev Ind	Revision	Appd	Year	Week					
RevInd	Accepted by qual control		Accepted for prod by		Description (English)				DATAORIGINAL	
	R.Yngvesson				CONNECTION DIAGRAM					
Design checked by	Design checked by		Drawn by		Description (own language)				File name	
	B-O.Stenestam		L.Bergman		KOPPLINGSSHEMA				0373-1	
Lang	Drawing checked by		Issued by Dept		Year	Week			Sheet	
	M.Hedlund		COM/TKO		97	17			1	
RevInd	ABB		Asea Brown Boveri		5492 0373-1				Cont	
									-	