


We reserve all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden. © ABB '19

On-load tap-changer type (V)UCGL./F, (V)UCLL./F, UCCL./F,
6 tap positions, linear switching.
Min. effective No. of turns in pos. 1.
The tap-changer is delivered set in pos. 4,
the preceding pos. was 3.

Lindningskopplare typ (V)UCGL./F, (V)UCLL./F, UCCL./F,
6 lägen, linjär koppling.
Min antal effektiva varv i läge 1.
Lindningskopplaren levereras inställd i läge 4,
föregående läge var 3.

Pos. Läge	Tap selector and diverter switch connect	
1	1-V-x	30
2	2-H-v	
3	3-V-x	
4	4-H-v	
5	5-V-x	
6	6-H-v	



The tap-changer is shown in pos. 4,
the preceding pos. was 3.
The tap selector is seen from above.
Contact arm V is located above contact arm H.

Lindningskopplaren visad i läge 4,
föregående läge var 3.
Väljaren sedd uppifrån.
Kontaktarm V ligger över kontaktarm H.

Continuous lines show leads included in the
tap-changer. Dashed lines show leads belonging
to the cleats and leads.

Heldragna linjer visar ledare som ingår i
lindningskopplaren. Streckade linjer visar
ledare som tillhör anslutningsdonet.

Sheet	Year	Week	Cont
Rev Ind	Revision	Appd	Year Week
Accepted by qual control L.Oberg	Accepted for prod by M.Haggmar		Description (English) CONNECTION DIAGRAM
Design checked by H.Sundberg	Drawn by A.Wang		Description (own language) KOPPLINGSSHEMA
Drawing checked by N.Gustavsson	Issued by Dept CO/TK	Year 14	Week 02
ABB			
1ZSC004308-AAB			
Lang	Sheet		
	1		
Rev Ind	Cont		
	-		

DATAORIGINAL

File name

Lang

Sheet

1

Rev Ind

Cont

-