


M2AA 090
 (*) Except 090_LD

S = { $\varnothing 7$ – Special IM 2001/*11
 M6 – Special IM 2101/*11

Additional information:

VC005: Metal protective roof, vertical motor, shaft down / Doble protector de ventilador

VC219: Flange ring FT 100 / Aro brida FT 100 // VC220: Flange ring FF 100 / Aro brida FF 100

<p>Motor Dimension Print</p>	<p>Motor Type : M2AA 090 (*)</p>	<p>Document N°: 3GZE 500 090-921.005</p>
<p>Description : Motor foot and flange mounted special (2-pieces) IM2001/*11 or IM2101/*11 Motor con patas y brida (2 piezas) IM2001/*11 o IM2101/*11</p>		
<p>Unit : Discret Automation & Motion - Fábrica Motores Date : 2012-12-03</p>	<p>Issued by : ERM/ A. Caubera Approved by : ERM/ G. Blanes</p>	<p>Replaces : Replaced by :</p>
<p>Asea Brown Boveri, S.A.</p>	<p>Customer Reference :</p> 