



Test Report				Date of issue: 20.11.2015																																																																																												
				Type: M3JM 400LD 6																																																																																												
				Product Code: 3GJM403540-_DG																																																																																												
				Protection type: Ex d I Mb																																																																																												
				Cert. No.: LCIE 10 ATEX 3004 X / IECEx LCI 04.0032X																																																																																												
Rating:																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>V</th> <th>Hz</th> <th>kW</th> <th>r/min</th> <th>A</th> <th>cos φ</th> <th>Duty</th> <th colspan="3"></th> </tr> </thead> <tbody> <tr> <td>3-Motor</td> <td>690</td> <td>Y 50</td> <td>560</td> <td>993</td> <td>569</td> <td>0,85</td> <td>S1</td> <td colspan="3"></td> </tr> <tr> <td>Insul.cl.F</td> <td>400</td> <td>D 50</td> <td>560</td> <td>993</td> <td>984</td> <td>0,85</td> <td>S1</td> <td colspan="3"></td> </tr> <tr> <td>IP66</td> <td>415</td> <td>D 50</td> <td>560</td> <td>994</td> <td>960</td> <td>0,84</td> <td>S1</td> <td colspan="3"></td> </tr> </tbody> </table>												V	Hz	kW	r/min	A	cos φ	Duty				3-Motor	690	Y 50	560	993	569	0,85	S1				Insul.cl.F	400	D 50	560	993	984	0,85	S1				IP66	415	D 50	560	994	960	0,84	S1																																													
	V	Hz	kW	r/min	A	cos φ	Duty																																																																																									
3-Motor	690	Y 50	560	993	569	0,85	S1																																																																																									
Insul.cl.F	400	D 50	560	993	984	0,85	S1																																																																																									
IP66	415	D 50	560	994	960	0,84	S1																																																																																									
Resistance				Insulation resistance at 78 °C				Overload																																																																																								
Line				2770 MΩ 1000 V				Torque 160% 15s																																																																																								
Ambient: 19 °C U ₁ - V ₁ 0,00263 Ω U ₁ - W ₁ 0,00263 Ω V ₁ - W ₁ 0,00263 Ω				High-voltage test winding 2400 V				60 s																																																																																								
<table border="1"> <thead> <tr> <th rowspan="2">Test</th> <th rowspan="2">Torque [Nm]</th> <th colspan="2">Line</th> <th colspan="2">Input</th> <th colspan="2">Output</th> <th rowspan="2">cos φ</th> <th rowspan="2">η [%]</th> </tr> <tr> <th>U[V]</th> <th>f[Hz]</th> <th>I[A]</th> <th>P1 [kW]</th> <th>P2 [kW]</th> <th>n[r/min]</th> </tr> </thead> <tbody> <tr> <td>No load test</td> <td></td> <td>400,0</td> <td>D 50</td> <td>308,4</td> <td>7,27</td> <td></td> <td>1000</td> <td>0,03</td> <td></td> </tr> <tr> <td>Locked rotor test</td> <td></td> <td>71,0</td> <td>D 50</td> <td>980,2</td> <td>33,4</td> <td></td> <td>0</td> <td>0,28</td> <td></td> </tr> <tr> <td>Thermal test (100% load)</td> <td>5386</td> <td>400,8</td> <td>D 50</td> <td>984,2</td> <td>580,3</td> <td>560,0</td> <td>993</td> <td>0,85</td> <td>96,5</td> </tr> <tr> <td>Partial load points:</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>~75% load</td> <td>4044</td> <td>400,1</td> <td>D 50</td> <td>763,3</td> <td>434,5</td> <td>420,0</td> <td>995</td> <td>0,82</td> <td>96,7</td> </tr> <tr> <td>~50% load</td> <td>2698</td> <td>400,0</td> <td>D 50</td> <td>561,8</td> <td>290,5</td> <td>280,0</td> <td>997</td> <td>0,75</td> <td>96,4</td> </tr> <tr> <td>~25% load</td> <td>1348</td> <td>400,0</td> <td>D 50</td> <td>396,9</td> <td>148,1</td> <td>140,0</td> <td>999</td> <td>0,54</td> <td>94,5</td> </tr> </tbody> </table>											Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]	U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]	No load test		400,0	D 50	308,4	7,27		1000	0,03		Locked rotor test		71,0	D 50	980,2	33,4		0	0,28		Thermal test (100% load)	5386	400,8	D 50	984,2	580,3	560,0	993	0,85	96,5	Partial load points:										~75% load	4044	400,1	D 50	763,3	434,5	420,0	995	0,82	96,7	~50% load	2698	400,0	D 50	561,8	290,5	280,0	997	0,75	96,4	~25% load	1348	400,0	D 50	396,9	148,1	140,0	999	0,54	94,5
Test	Torque [Nm]	Line		Input		Output		cos φ	η [%]																																																																																							
		U[V]	f[Hz]	I[A]	P1 [kW]	P2 [kW]	n[r/min]																																																																																									
No load test		400,0	D 50	308,4	7,27		1000	0,03																																																																																								
Locked rotor test		71,0	D 50	980,2	33,4		0	0,28																																																																																								
Thermal test (100% load)	5386	400,8	D 50	984,2	580,3	560,0	993	0,85	96,5																																																																																							
Partial load points:																																																																																																
~75% load	4044	400,1	D 50	763,3	434,5	420,0	995	0,82	96,7																																																																																							
~50% load	2698	400,0	D 50	561,8	290,5	280,0	997	0,75	96,4																																																																																							
~25% load	1348	400,0	D 50	396,9	148,1	140,0	999	0,54	94,5																																																																																							
Temperature rise at rated load.																																																																																																
<table border="1"> <thead> <tr> <th></th> <th>[°C]</th> <th>[K]</th> <th>Method</th> <th>Measurement method</th> </tr> </thead> <tbody> <tr> <td>Stator winding :</td> <td></td> <td>83</td> <td>1</td> <td>1 Resistance</td> </tr> <tr> <td>Frame :</td> <td></td> <td>54</td> <td>2</td> <td>2 Thermocouples</td> </tr> <tr> <td>Bearing D-end :</td> <td></td> <td>55</td> <td>2</td> <td>3 Thermometer</td> </tr> <tr> <td>Ambient Temperature :</td> <td>25</td> <td></td> <td>2</td> <td></td> </tr> </tbody> </table>												[°C]	[K]	Method	Measurement method	Stator winding :		83	1	1 Resistance	Frame :		54	2	2 Thermocouples	Bearing D-end :		55	2	3 Thermometer	Ambient Temperature :	25		2																																																														
	[°C]	[K]	Method	Measurement method																																																																																												
Stator winding :		83	1	1 Resistance																																																																																												
Frame :		54	2	2 Thermocouples																																																																																												
Bearing D-end :		55	2	3 Thermometer																																																																																												
Ambient Temperature :	25		2																																																																																													
<p>Starting current (I_S / I_N) : 6,90</p> <p>Locked rotor torque (T_L / T_N) : 2,17</p> <p>These tests have been carried out on motor no. 3G1F1508257042B, on date 2015-03-30, which is identical in design with the above.</p> <p>Manufactured and tested in accordance with rules of IEC 60034-1 and IEC 60034-2-1. PLL determined from residual loss.</p> <p>On behalf of customer</p> <p>On behalf of manufacturer</p> <p>Tested by ABB Oy, Motors and Generators, Vaasa, Finland</p> <p>Telephone +358 10 2211 Telefax +358 10 22 47372</p>																																																																																																

Computer print-out valid without signature.