

Electrical installation solutions for buildings – Technical details

RCDs

Index

Functions and classification criteria for RCDs	2/2
Limitation of specific let-through energy I^2t	2/6
Peak current I_p	2/15
Coordination tables: F 200 RCCBs	2/24
Coordination tables: back-up DS201	2/27
Coordination tables : back-up DS301C	2/35
Coordination tables: back-up DS202CR	2/38
Coordination tables: back-up DS203NC	2/40
Coordination tables: back-up DSE201	2/43
Coordination tables: back-up DSE201 M	2/44
Coordination tables: selectivity DS202C	2/47
Coordination tables : selectivity DS301C	2/70
Coordination tables: selectivity DS203NC	2/75
Coordination tables: selectivity DS202CR	2/76
Coordination tables: selectivity DSE201	2/85
Coordination tables: selectivity DSE201 M	2/86
Coordination tables: residual current protection selectivity	2/91
Power loss, derating and performance in altitude	2/97
Tripping characteristic	2/102
Emergency stop using DDA 200 AE series	2/103
Unwanted tripping - AP-R solution (high immunity)	2/104
Unwanted tripping - F2C-ARH solution	2/106
Type B RCDs	2/114
Series connection of RCDs	2/117
Use of 4P RCCBs in 3-phase system without neutral pole	2/123
Operating voltage of test button	2/124
RD2 residual current relays	2/129
RD3 residual current relays	2/130
ELR front panel residual current relays	2/133
Toroidal transformers	2/134


RCDs technical details

Functions and classification criteria for RCDs

Overview of the RCCB types

The variety of residual current protective devices (RCDs) has increased continuously over the last few decades following technological development and the massive introduction of electronics in all areas of application.

In accordance with the possibility of recognizing the most varied forms of residual current and the relatively demanding device testing, the spectrum of RCD types today ranges from protecting pure AC consumers to high-frequency consumers. The level of protection is shifting more and more from the AC and A types to the F and B types.



RCDs technical details

Functions and classification criteria for RCDs

Functions and classification criteria for RCDs

A residual current operated circuit-breaker is an amperometric protection device which is tripped when the system leaks a significant current to earth.

This device continuously calculates the vector sum of the single-phase or three-phase system line currents and while the sum is equal to zero allows electricity to be supplied. This supply is rapidly interrupted if the sum exceeds a value preset according to the sensitivity of the device.

Residual current operated circuit-breakers can be classed according to four parameters:

- type of construction
- detectable wave form
- tripping sensitivity
- tripping time.

Depending on the type of construction, RCDs may be classed as:

- RCBOs (magnetothermic with overcurrent protection)
- RCCBs (without overcurrent protection releaser incorporated)
- RCD blocks.

RCBOs combine, in a single device, the residual current function and the overcurrent protection function typical of MCBs. RCBOs are tripped by both current leakage to earth and overloads and short-circuits and they are self-protecting up to a maximum short-circuit current value indicated on the label.

RCCBs are only sensitive to current leakage to earth. They must be used in series with an MCB or fuse which protects them from the potentially damaging thermal and dynamic stresses of any overcurrents.

These devices are used in systems already equipped with MCBs which preferably limit the specific energy passing through, also acting as the main disconnecting switches upstream of any derived MCBs (e.g.: domestic consumer unit). RCD blocks are residual current devices suitable for assembly with a standard MCB. IEC/EN 61009 app. G only allows assembly of RCBOs once on site, that is to say outside the factory, using adaptable RCD blocks and the appropriate MCBs. Any subsequent attempts to separate them must leave permanent visible damage. The residual current operated circuit-breaker obtained in this way maintains both the electrical characteristics of the MCB and those of the RCD block.

According to the wave form of the earth leakage currents they are sensitive to, the RCDs may be classed as:

- AC type (for alternating current only)
- A type (for alternating and/or pulsating current with DC components)
- F type (for alternating and/or pulsating current with DC components with detection of high frequency currents up to 1 kHz.)
- B type (for alternating and/or pulsating current with DC components and continuous fault current).

AC type RCDs are suitable for all systems where users have sinusoidal earth current.

They are not sensitive to impulsive leakage currents up to a peak of 250 A (8/20 wave form) such as those which may occur due to overlapping voltage impulses on the mains (e.g.: insertion of fluorescent bulbs, X-ray equipment, data processing systems and SCR controls).

A type RCDs are not sensitive to impulsive currents up to a peak of 250 A (8/20 wave form).

They are particularly suitable for protecting systems in which the user equipment has electronic devices for rectifying the current or phase cutting adjustment of a physical quantity (speed temperature, light intensity, etc.) supplied directly by the mains without the insertion of transformers and insulated in class I (class II is, by definition, free of faults to earth). These devices may generate a pulsating fault current with DC components which the A type RCD can recognise.

F type RCDs can detect sinusoidal AC currents as well as pulsating DC currents. In addition to this, they are also tested according to IEC/EN 62423 which foresees the application of a simulated multi-frequency residual current with appropriate coefficient associated to the each level of frequency up to 1kHz.

The intervention characteristic has a short-time delayed which prevents unwanted tripping in case pulsed leakage currents of up to ten milliseconds occur at activation of filters.

The RCDs Type F have a surge current withstand capacity of more than 3kA and can accept superimposed smooth DC residual currents of up to 10mA without affecting their standard functionality.

Main area of use are the circuits of single phase inverters regulating the speed of motors by supplying a variable frequency, from 10 to 1000 Hz.

RCDs technical details

Functions and classification criteria for RCDs

B type RCDs are recommended for use with drives and inverters for supplying motors for pumps, lifts, textile machines, machine tools, etc., since they recognise a continuous fault current with a low level ripple.

Type AC, A and B RCDs comply with IEC/EN 61008/61009, moreover type B is covered by IEC 62423 Ed. 1 and by IEC/EN 60755 for residual current operated protective devices.

According to tripping sensitivity ($I\Delta n$ value), RCDs may be divided into the following categories:

- low-sensitivity ($I\Delta n > 0.03 \text{ A}$), not suitable for protection against direct contacts; co-ordinated with the earth system according to the formula $I\Delta n < 50/R$, to provide protection against indirect contacts;
- high-sensitivity ($I\Delta n: 0.01...0.03 \text{ A}$), or "physiologically sensitive" for protection against indirect contacts, with simultaneous additional protection against direct contacts.
- against fire (up to 500 mA) according to IEC/EN 60364

Residual current sensitivity and environment

Household and special environments




$I\Delta n$
 $\leq 30 \text{ mA}$

High-sensitivity or physiologically sensitive RCDs

IEC/EN 60364 makes the use of these devices mandatory in all bathrooms, showers and private and public swimming pools and environments in which plugs and sockets may be installed without insulating or low safety voltage transformers.

Laboratories, service industry and small industry



$I\Delta n$
from 30 mA
to 500 mA

Low-sensitivity RCDs

Large service industry and industrial complex



$I\Delta n$
from 500 mA
to 1000 mA

According to their tripping time, RCDs can be classed as:

- instantaneous (or rapid or general)
- type S selective (or - incorrectly - delayed).

Selective RCDs (RCBOs - RCCBs or RCD-blocks) have a delayed tripping action and are installed upstream of other rapid residual current operated circuit-breakers to guarantee selectivity and limit the power out only to the portion of the system affected by a fault.

RCDs technical details

Functions and classification criteria for RCDs

The tripping time is not adjustable. It is set according to a predetermined time – current characteristic with an intrinsic delay for small currents, tending to disappear as the current grows. IEC/EN 61008 and 61009 establish the tripping times relative to the type of RCD and the $I\Delta n$.

Type AC	In [A]	$I\Delta$ [A]	Tripping times (s) x currents			
			$1 \times I\Delta$	$2 \times I\Delta$	$5 \times I\Delta$	500A
Generic	Any	Any	0.3	0.15	0.04	0.04
S (selective)	Any	>0.030	0.13-0.5	0.06-0.2	0.05-0.15	0.04-0.15


The indicated maximum tripping times are also valid for A type RCDs, but increasing the current values of factor 1.4 for RCDs with $I\Delta n > 0.01$ A and of factor 2 for RCDs with $I\Delta n \leq 0.01$ A.

The range of ABB RCDs also includes AP-R (anti-disturbance) devices which trip according to the limit times allowed by the Standards for instantaneous RCDs. This function is due

to the slight tripping delay (approx. 10 ms) relative to the standard instantaneous ones.

The graph shows the comparison of the qualitative tripping curves for:

- a 30 mA instantaneous RCD
- a 30 mA AP-R instantaneous RCD
- a 100 mA selective RCD (type S)



Note: this is a qualitative chart; it is referred only to industrial frequencies of 50-60 Hz.

RCDs technical details



Limitation of specific let-through energy I^2t

I^2t diagrams - Specific let-through energy value I^2t

The I^2t curves give the values of the specific let-through energy expressed in A^2s ($A=amps$; $s=seconds$) in relation to the perspective short-circuit current (I_{rms}) in kA.

DS 200-DS 200 M, characteristics B and C


230/400 V let-through energy



DS201 L - DS201 - DS201 T - DS201 M

characteristics B and C


230 V let-through energy



DS202CR - DS202CR M

characteristics B and C


230 V let-through energy




RCDs technical details

Limitation of specific let-through energy I^2t

Specific let-through energy I^2t DS201L - Characteristic C




Specific let-through energy I^2t DS201 - Characteristic B




RCDs technical details

Limitation of specific let-through energy I^2t

Specific let-through energy I^2t DS201 - Characteristic C




Specific let-through energy I^2t DS201 - Characteristic K




RCDs technical details

Limitation of specific let-through energy I^2t

Specific let-through energy I^2t DS201M - Characteristic B




Specific let-through energy I^2t DS201M - Characteristic C



RCDs technical details

Limitation of specific let-through energy I^2t


Specific let-through energy I^2t DS201M - Characteristic K




RCBO DS301C

Technical data

Specific let-through energy $I^2 t$ DS301C—Characteristic C



Specific let-through energy $I^2 t$ DS301C—Characteristic B




RCDs technical details

Limitation of specific let-through energy I^2t


DS203NC L, characteristic B

400 V let-through energy



DS203NC, characteristic B

400 V let-through energy




RCDs technical details

Limitation of specific let-through energy I^2t


DS203NC L, characteristic C

400 V let-through energy




DS203NC, characteristic C

400 V let-through energy



DS203NC, characteristic K

400 V let-through energy





RCDs technical details

Limitation of specific let-through energy I^2t



DSE201

230 V let-through energy



DSE201 M

230 V let-through energy




RCDs technical details

Peak current I_p

DS201 L - DS201 - DS201 T - DS201 M

characteristics B e C


230 V



DS202CR - DS202CR M

characteristics B and C


230 V




RCDs technical details

Peak current I_p

Ipeak DS201L - Characteristic C




Ipeak DS201 - Characteristic B




RCDs technical details

Peak current I_p

Ipeak DS201 - Characteristic C




Ipeak DS201 - Characteristic K




RCDs technical details

Peak current I_p

Ipeak DS201M - Characteristic B




Ipeak DS201M - Characteristic C



RCDs technical details

Peak current I_p


Ipeak DS201M - Characteristic K




RCBO DS301C

Technical data

Ipeak DS301C—Characteristic C




Ipeak DS301C—Characteristic B




RCDs technical details

Peak current I_p

DS203NC L, characteristic B




DS203NC, characteristic B




RCDs technical details

Peak current I_p

DS203NC L, characteristic C




DS203NC, characteristic C



RCDs technical details


Peak current I_p

DS203NC, characteristic K




DSE201

DSE201, characteristic B




DSE201, characteristic C




DSE201 M

DSE201M, characteristic B



DSE201M, characteristic C



RCDs technical details

Coordination tables: F 200 RCCBs

Coordination tables between Short Circuit Protection Devices (SCPD) and F 200 RCCBs

If you are using an RCCB you must verify that the Short Circuit Protection Device (SCPD) protects it from the effects of high current that arise under short-circuit conditions. The IEC/EN 61008 provides some tests to verify the behaviour of RCCB in short-circuit conditions. The tables

below provide the maximum withstanding short-circuit current expressed in eff. kA for which the RCCBs are protected thanks to the coordination with the SCPD installed upstream or downstream. The tests are performed with SCPD with a rated current (thermal protection) less than or equal to the rated current of the associated RCCB.

F 202

	Single-phases 230-240 V circuit					
	25 A	40 A	63 A	80 A	100 A	125 A
SN201L/S201L Na	4.5	4.5				
SN201/S201 Na	6	6				
SN201M/S201M Na	10	10				
S202L	10	10				
S202	20	20	20			
S202M	25	25	25			
S202P	40	25	25			
S300P	40	25	25			
S702	10	10	10	10	10	
S752	10	10	10			
S802N	36	36	36	36	36	36
S802S	50	50	50	50	50	50
Fuse 25 gG	100					
Fuse 40 gG	60	60				
Fuse 63 gG	20	20	20			
Fuse 100 gG	10	10	10	10	10	
Fuse 125 gG						10

F 202

	400-415 V circuits with isolated neutral (IT) under double faults					
	25 A	40 A	63 A	80 A	100 A	125 A
SN201N/SN201/SN201M	3	3				
S201L/S201L Na/S202L	4.5	4.5				
S201/S201 Na/S202	6	6	6			
S201M/S201M Na/S202M	10	10	10			
S201P/S201P Na/S202P	25	15	15			
S300P	25	15	15			
S801N/S802N	20	20	20	20	20	20
S801S/S802S	25	25	25	25	25	25

RCDs technical details

Coordination tables: F 200 RCCBs

F 204

	Three-phases circuits with neutral (y/D) 230-240 V/400-415 V*					
	25 A	40 A	63 A	80 A	100 A	125 A
SN201L/S201L/S201LNa*	4.5	4.5				
SN201/S201/S201Na*	6	6				
SN201M/S201M/S201MNa*	10	10				
S202L*	10	10				
S202*	20	20	20			
S202M*	25	25	25			
S202P*	40	25	25			
S300P	40	25	25			
S702	10	10	10	10	10	
S752	10	10	10			
S802N*	36	36	36	36	36	36
S802S*	50	50	50	50	50	50
Fuse 25 gG	100					
Fuse 40 gG	60	60				
Fuse 63 gG	20	20	20			
Fuse 100 gG	10	10	10	10	10	
Fuse 125 gG						10

* The switches are considered between phase and neutral (230/240V)

F 204

	Three-phases circuits with neutral (y/D) 230-240 V/400-415 V					
	25 A	40 A	63 A	80 A	100 A	125 A
S203L/S204L	4.5	4.5				
S203/S204	6	6	6			
S203M/S204M	10	10	10			
S203P/S204P	25	15	15			
S300P	25	15	15			
S702	10	10	10	10	10	
S752	10	10	10			
S803N/S804N	20	20	20	20	20	20
S803S/S804S	25	25	25	25	25	25
Fuse 25 gG	50					
Fuse 40 gG	30	30				
Fuse 63 gG	20	20	20			
Fuse 100 gG	10	10	10	10	10	
Fuse 125 gG						10

RCDs technical details

Coordination tables: F 200 RCCBs

F 204

	Three-phases circuits with neutral (y/D) 133-138V/230-240V					
	25 A	40 A	63 A	80 A	100 A	125 A
SN201L	10	10				
SN201	15	15				
S201M	20	20				
S203L/S204L	10	10				
S203/S204	20	20	20			
S203M/S204M	25	25	25			
S203P/S204P	40	25	25			
S300P	40	25	25			
S702	10	10	10	10	10	
S752	10	10	10			
S803N-S804N	36	36	36	36	36	36
S803S-S804S	50	50	50	50	50	50
Fuse 25 gG	100					
Fuse 40 gG	60	60				
Fuse 63 gG	20	20	20			
Fuse 100 gG	10	10	10	10	10	
Fuse 125 gG						10

RCDs technical details

Coordination tables: back-up DS201

Fuses - DS201 (2019) @ 230/240V

		Supply side		Fuses gG					
Load side	Char	Icu [kA]	In[A]	25	40	50	63	80	100
DS201 (2019) L	C	6	6...32	35	25	25	25	15	10
DS201 (2019)	B,C,K	10	1...40	35	25	25	25	15	10
DS201 (2019) M	B,C,K	15	4...40	35	25	25	25	15	15

MCCB Tmax XT @ 415V - DS201 (2019) @ 230/240V

		Supply side	XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4	XT2	XT4
		Version	B	C	N	N	N	S	S	S	S	H	H	H	L	L	V	V	
Load side	Char	Icu [kA]	18	25	36	36	36	50	50	50	50	70	70	70	120	120	150	150	
		In[A]	160	160	160	160	250	250	160	160	250	250	160	160	250	160	250	160	250
DS201 (2019) L	C	6	6...25	18	18	18	20	10	18	18	20	10	18	18	20	18	20	18	18
			32	10	10	10	10	10	10	18	10	10	10	18	10	18	10	10	10
			32,40	18	18	18	25	18	20	20	25	18	20	20	25	20	25	20	20
DS201 (2019)	B,C,K	10	1...25	18	18	18	25	18	20	20	25	18	20	20	25	20	25	20	20
			32,40	18	18	18	18	18	10	10	18	18	10	10	18	10	18	10	10
DS201 (2019) M	B,C,K	15	4...25	18	18	18	25	18	20	20	25	18	20	20	25	20	25	20	20
			32,40	18	18	18	18	18	15	15	18	18	15	15	18	15	18	15	15

MCCB Tmax T @ 415V - DS201 (2019)@230/240V

RCDs technical details

Coordination tables: back-up DS201

S200 -DS201 (2019) @ 230/240V

Load side	Char	Supply side	S200	S200M	S200P	S300P	S200P	S300P
		Version	B,C	B,C	B,C	B,C	B,C	B,C
		Icu [kA]	20	25	40	40	25	25
		In[A]	0,5..63	0,5...63	0,5...25	0,5...25	32...63	32...63
DS201 (2019) L	C	6	6...32	20	25	40	25	25
DS201 (2019)	B,C,K	10	1...40	20	25	40	25	25
DS201 (2019) M	B,C,K	15	4...40	20	25	40	25	25

DS201 (2019) - SN201 @ 230/240V

Load side	Char	Supply side	DS201 (2019)	DS201 (2019) M
		Version	B,C,K	B,C,K
		Icu [kA]	10	15
		In[A]	1..40	2..40
SN201 L	B,C	6	2...40	10
SN201	B,C,D	10	2...40	10

S800S - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800S
		Version	B,C,D,K
		Icu [kA]	50
	C	In[A]	25 32 40 50 63 80 100 125
		6	50 40 25 25 18 15 15 15
		10	50 40 25 25 18 15 15 15
		16	50 40 25 25 18 15 15 15
		20	40 25 25 18 15 15 15 15
		25	25 25 18 15 15 15 15 15
		32	25 18 15 15 15 15 15 15
	B,C,K	1	50 50 50 50 50 50 50 50
		2	50 50 50 50 50 50 50 50
		4	50 50 50 50 50 50 50 50
		6	50 50 50 50 50 50 50 50
		8	50 50 50 50 50 50 50 50
		10	50 50 50 50 50 50 50 50
		13	50 50 50 50 50 50 50 50
		16	50 50 50 50 50 50 50 50
		20	50 50 50 50 50 50 50 50
		25	50 50 50 50 50 50 50 50
	B,C,K	32	50 50 50 50 50 50 50 50
		40	50 50 50 50 50 50 50 50
		4	50 50 50 50 50 50 50 50
		6	50 50 50 50 50 50 50 50
		10	50 50 50 50 50 50 50 50
		13	50 50 50 50 50 50 50 50
		16	50 50 50 50 50 50 50 50
		20	50 50 50 50 50 50 50 50
	B,C,K	25	50 50 50 50 50 50
		32	50 50 50 50 50 50
		40	50 50 50 50 50 50

RCDs technical details

Coordination tables: back-up DS201

S800N - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800N							
			Version	B,C,D						
Icu [kA]	36	In[A]	25	32	40	50	63	80	100	125
DS201 (2019) L	C	6	6	36	36	25	25	18	15	15
			10	36	36	25	25	18	15	15
			16	36	36	25	25	18	15	15
			20		36	25	25	18	15	15
			25			25	25	18	15	15
			32				25	18	15	15
DS201 (2019)	B,C,K	10	1	36	36	36	36	36	36	36
			2	36	36	36	36	36	36	36
			4	36	36	36	36	36	36	36
			6	36	36	36	36	36	36	36
			8	36	36	36	36	36	36	36
			10	36	36	36	36	36	36	36
			13	36	36	36	36	36	36	36
			16	36	36	36	36	36	36	36
			20		36	36	36	36	36	36
			25			36	36	36	36	36
			32				36	36	36	36
			40					36	36	36
DS201 (2019) M	B,C,K	15	4	36	36	36	36	36	36	36
			6	36	36	36	36	36	36	36
			10	36	36	36	36	36	36	36
			13	36	36	36	36	36	36	36
			16	36	36	36	36	36	36	36
			20		50	36	36	36	36	36
			25			36	36	36	36	36
			32				36	36	36	36
			40					36	36	36

RCDs technical details

Coordination tables: back-up DS201

S800C - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800C								
			Version	B,C,D,K							
		Icu [kA]	25								
DS201 (2019) L	C	6	In[A]	25	32	40	50	63	80	100	125
			6	25	25	25	25	18	15	15	15
			10	25	25	25	25	18	15	15	15
			16	25	25	25	25	18	15	15	15
			20		25	25	25	18	15	15	15
			25			25	25	18	15	15	15
			32				25	18	15	15	15
DS201 (2019)	B,C,K	10	1	25	25	25	25	25	25	25	25
			2	25	25	25	25	25	25	25	25
			4	25	25	25	25	25	25	25	25
			6	25	25	25	25	25	25	25	25
			8	25	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25	25
			13	25	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25	25
			20		25	25	25	25	25	25	25
			25			25	25	25	25	25	25
			32				25	25	25	25	25
			40					25	25	25	25
DS201 (2019) M	B,C,K	15	4	25	25	25	25	25	25	25	25
			6	25	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25	25
			13	25	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25	25
			20		25	25	25	25	25	25	25
			25			25	25	25	25	25	25
			32				25	25	25	25	25
			40					25	25	25	25

RCDs technical details

Coordination tables: back-up DS201

S800B - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800B							
			Version	B,C,D,K						
Icu [kA]	16									
DS201 (2019) L	C	6	In[A]	32	40	50	63	80	100	125
			6	16	16	16	16	15	15	15
			10	16	16	16	16	15	15	15
			16	16	16	16	16	15	15	15
			20	16	16	16	16	15	15	15
			25		16	16	16	15	15	15
			32			16	16	15	15	15
							16	15	15	15
DS201 (2019)	B,C,K	10	1	16	16	16	16	16	16	16
			2	16	16	16	16	16	16	16
			4	16	16	16	16	16	16	16
			6	16	16	16	16	16	16	16
			8	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16
DS201 (2019) M	B,C,K	15	4	16	16	16	16	16	16	16
			6	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16

RCDs technical details

Coordination tables: back-up DS201

S800U - DS201 (2019) @ 230/240V

Load side	Char		Supply side	S800U								
			Version	K,Z								
			Icu [kA]	50								
			In[A]	25	30	40	50	60	70	80	90	100
DS201 (2019) L	C	6	6	50	50	50	50	50	50	50	50	
			10	50	50	50	50	50	50	50	50	
			16	50	50	50	50	50	50	50	50	
			20		50	50	50	50	50	50	50	
			25			50	50	50	50	50	50	
			32				50	50	50	50	50	
								50	50	50	50	
DS201 (2019)	B,C,K	10	1	50	50	50	50	50	50	50	50	
			2	50	50	50	50	50	50	50	50	
			4	50	50	50	50	50	50	50	50	
			6	50	50	50	50	50	50	50	50	
			8	50	50	50	50	50	50	50	50	
			10	50	50	50	50	50	50	50	50	
			13	50	50	50	50	50	50	50	50	
			16	50	50	50	50	50	50	50	50	
			20		50	50	50	50	50	50	50	
			25			50	50	50	50	50	50	
			32				50	50	50	50	50	
			40					50	50	50	50	
DS201 (2019) M	B,C,K	15	4	50	50	50	50	50	50	50	50	
			6	50	50	50	50	50	50	50	50	
			10	50	50	50	50	50	50	50	50	
			13	50	50	50	50	50	50	50	50	
			16	50	50	50	50	50	50	50	50	
			20		50	50	50	50	50	50	50	
			25			50	50	50	50	50	50	
			32				50	50	50	50	50	
			40					50	50	50	50	

RCDs technical details

Coordination tables: back-up DS201

S750 DR - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S750 DR									
			Version	Eselective; Kselective									
				25	In[A]	16	20	25	35	40	50	63	80
DS201 (2019) L	C	6	6		20	20	20	20	20	20	20	20	20
			10		20	20	20	20	20	20	20	20	20
			16			20	20	20	20	20	20	20	20
			20				20	20	20	20	20	20	20
			25					20	20	20	20	20	20
			32						20	20	20	20	20
			40							20	20	20	20
DS201 (2019)	B,C,K	10	1	20	20	20	20	20	20	20	20	20	20
			2	20	20	20	20	20	20	20	20	20	20
			4	20	20	20	20	20	20	20	20	20	20
			6	20	20	20	20	20	20	20	20	20	20
			8	20	20	20	20	20	20	20	20	20	20
			10	20	20	20	20	20	20	20	20	20	20
			13		20	20	20	20	20	20	20	20	20
			16			20	20	20	20	20	20	20	20
			20				20	20	20	20	20	20	20
			25					20	20	20	20	20	20
DS201 (2019) M	B,C,K	15	32						20	20	20	20	20
			40							20	20	20	20

RCDs technical details

Coordination tables: back-up DS201

S750 - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S750					
			Version	Eselective; Kselective				
			Icu [kA]	25				
DS201 (2019) L	C	6	In[A]	16	20	25	35	40
			6	20	20	20	20	20
			10	20	20	20	20	20
			16		20	20	20	20
			20			20	20	20
			25				20	20
			32					20
								20
								20
								20
DS201 (2019)	B,C,K	10	1	20	20	20	20	20
			2	20	20	20	20	20
			4	20	20	20	20	20
			6	20	20	20	20	20
			8	20	20	20	20	20
			10	20	20	20	20	20
			13		20	20	20	20
			16			20	20	20
			20				20	20
			25				20	20
			32					20
			40					20
DS201 (2019) M	B,C,K	15	4	20	20	20	20	20
			6	20	20	20	20	20
			10	20	20	20	20	20
			13		20	20	20	20
			16			20	20	20
			20				20	20
			25				20	20
			32					20
			40					20

RCBO DS301C

Coordination tables: back-up DS301C

Fuses - RCBOs DS301C @230/240 V

Load side	Char	Supply side										Fuses gG					
		25		40		50		63		80		100					
		Icu (kA)	In (A)	Icu (kA)	In (A)	Icu (kA)	In (A)	Icu (kA)	In (A)	Icu (kA)	In (A)	Icu (kA)	In (A)	Icu (kA)	In (A)	Icu (kA)	In (A)
RCBOs DS301C	B, C	6	6...20	10	10	10	10	10	10	10	10	10	10	10	10	10	10

MCCB Tmax XT @ 415 V - RCBOs DS301C @230/240 V

Load side	Char	Icu (kA)	In (A)	Supply side																
				XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4		
				Version	B	C	N	N	N	S	S	S	S	H	H	H	L	L	V	V
				Icu (kA)	18	25	36	36	36	50	50	50	50	70	70	70	120	120	150	150
RCBOs DS301C	B, C	6	6...20	16	20	23	23	10	16	23	23	10	16	23	23	16	23	16	23	16

S200 - RCBOs DS301C @230/240 V

Load side	Char	Icu (kA)	In (A)	Supply side		S200	S200M	S200P	S300P	S200P	S300P
				Version	B, C	B, C	B, C	B, C	B, C	B, C	B, C
				Icu (kA)	20	25	40	40	40	25	25
RCBOs DS301C	B, C	6	6...20	10	10	10	10	10	10	10	10

RCBOs DS301C @230/240 V - SN201 @ 230/240V

Load side	Char	Icu (kA)	In (A)	Supply side		SN201	SN201M
				Version	B, C, D	B, C	B, C
				Icu (kA)	10	10	10
RCBOs DS301C	B, C	6	6...20	10	10	10	10

S800S - RCBOs DS301C @230/240 V

Load side	Char	Icu (kA)	In (A)	Supply side		S800S					
				Version	B, C, D, K	B, C, D, K					
				Icu (kA)	35	35					
RCBOs DS301C	B, C	6	6	25	32	40	50	63	80	100	125
			10	30	25	18	18	18	15	15	15
			13	30	25	18	18	18	15	15	15
			16	30	25	18	18	18	15	15	15
			20		25	18	18	18	15	15	15

S800N - RCBOs DS301C @230/240 V

Load side	Char	Icu (kA)	In (A)	Supply side		S800N					
				Version	B, C, D	B, C, D					
				Icu (kA)	36	36					
RCBOs DS301C	B, C	6	6	25	32	40	50	63	80	100	125
			10	30	25	18	18	18	15	15	15
			13	30	25	18	18	18	15	15	15
			16	30	25	18	18	18	15	15	15
			20		25	18	18	18	15	15	15

RCBO DS301C

Coordination tables: back-up DS301C

S800C - RCBOs DS301C @230/240 V

			Supply side	S800C							
			Version	B, C, D, K							
			Icu (kA)	25							
Load side	Char	Icu (kA)	In (A)	25	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	25	25	18	18	18	15	15	15
			10	25	25	18	18	18	15	15	15
			13	25	25	18	18	18	15	15	15
			16	25	25	18	18	18	15	15	15
			20		25	18	18	18	15	15	15

S800B - RCBOs DS301C @230/240 V

			Supply side	S800B						
			Version	B, C, D, K						
			Icu (kA)	16						
Load side	Char	Icu (kA)	In (A)	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	15	15	15	15	15	15	15
			10	15	15	15	15	15	15	15
			13	15	15	15	15	15	15	15
			16	15	15	15	15	15	15	15
			20	15	15	15	15	15	15	15

S800U - RCBOs DS301C @230/240 V

			Supply side	S800 U								
			Version	K, Z								
			Icu (kA)	50								
Load side	Char	Icu (kA)	In (A)	25	30	40	50	60	70	80	90	100
RCBOs DS301C	B, C	6	6	50	50	40	40	40	30	30	25	25
			10	50	50	40	40	40	30	30	25	25
			13	50	50	40	40	40	30	30	25	25
			16		50	40	40	40	30	30	25	25
			20		50	40	40	40	30	30	25	25

RCBO DS301C

Coordination tables: back-up DS301C

S750 DR - RCBOs DS301C @230/240 V

Load side	Char	Icu (kA)	In (A)	Supply side		S750 DR					
				Version		Eselective, Kselective					
				Icu (kA)	25	16	20	25	32	40	50
RCBOs DS301C	B, C	6	6	25	25	25	25	22	22	22	22
			10	25	25	25	25	22	22	22	22
			13		25	25	25	22	22	22	22
			16			25	25	22	22	22	22
			20				25	22	22	22	22

S750 - RCBOs DS301C @230/240 V

Load side	Char	Icu (kA)	In (A)	Supply side		S750					
				Version		Eselective, Kselective					
				Icu (kA)	25	16	20	25	32	40	50
RCBOs DS301C	B, C	6	6	25	25	25	25	22	22	22	22
			10	25	25	25	25	22	22	22	22
			13		25	25	25	22	22	22	22
			16			25	25	22	22	22	22
			20				25	22	22	22	22

RCDs technical details

Coordination tables: back-up DS202CR

MCB/Fuses - DS202CR @ 230 V

		Supply s.	S200	S200M	S200P	S300P	S200P	S300P	25gG	40gG	50gG	63gG	80gG	100gG
Char.			B-C	B-C	B-C	B-C	B-C	B-C	B-C	B-C	B-C	B-C	B-C	B-C
Load s.	Icu [kA]	20	25	40	40	25	25	35	25	20	15	10	10	
		In [A]	0,5...63	0,5...63	0,5...25	0,5...25	32...63	32...63						
DS202CR	B,C	10	2...40	20	25	40	40	25	35	25	20	15	10	10
DS202CR M	B,C	10	2...40	20	25	40	40	25	35	25	20	15	10	10

S800 - DS202CR @230/400V

		Supply s.	S800S	S800N	S800C	S800B
Char.			B-C	B-C	B-C	B-C
Load s.	Icu [kA]	50	36	25	16	
		In [A]	80...125	80...125	80...125	80...125
DS202CR	B,C	10	2...40	50	36	25
DS202CR M	B,C	10	2...40	50	36	25

RCDs technical details

Coordination tables: back-up DS202CR

MCCB @ 415V - DS202CR @ 230 V

			Supply side	XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4	XT1	XT2	XT4
			Version	B	C	N	N	N	S	S	S	S	H	H	H	L	L	V			
Load side	Char.	Icu [kA]	In [A]	18	25	36	36	36	50	50	50	50	70	70	70	85	120	150			
DS202CR	B,C, D,K	10	2..25	18	18	18	25	18	20	20	25	18	20	20	25	20	25	20	20		
			32, 40				18		10	10	18		10	10	18	10	18	10	10		
DS202CR M	B,C	10	2..25	18	18	18	25	18	20	20	25	18	20	20	25	20	25	20	20		
			32, 40				18		10	10	18		10	10	18	10	18	10	10		

RCDs technical details

Coordination tables: back-up DS203NC

Fuses-DS203NC @ 400V

		Supply side		gL/gG						
Load side	Char	Icu [kA]	In[A]	25	40	63	80	100	125	160
DS203NC	L C	6	6...32	100	70	40	15	15	10	10
DS203NC	B,C,K	10	6...32	100	70	40	15	15	10	10

MCCB @ 415V - DS203NC @ 400V

		Supply side		XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3
		Char		B	C	N	N	N	N	S	S	S
Load side		Icu[KA]	In [A]	18	25	36	36	36	36	50	50	50
DS203NC	L C	6	6...25	16	16	16	20	10	10	16	20	10
			32	10	10	10	16	10	10	10	16	10
DS203NC	B,C,K	10	6...16	16	16	16	25	16	25	16	25	16
			20...25				25		16		25	
			32				16		16		16	

		Supply side		XT4	XT1	XT2	XT4	XT2	XT4	XT2	XT4
		Char		S	H	H	H	L	L	V	V
Load side		Icu[KA]	In [A]	50	70	70	70	120	120	150	150
DS203NC	L C	6	6...25	10	16	20	10	20	10	20	10
			32	10	10	16	10	16	10	16	10
DS203NC	B,C,K	10	6...16	25	16	25	25	25	25	25	25
			20...25	16		25	16	25	16	25	16
			32	16		16	16	16	16	16	16

MCCB @ 415V - DS203NC @ 400V

		Supply side		T1	T1	T1	T2	T3	T4	T2	T3	T4	T2	T4	T4		
		Char		B	C	N	N	N	N	S	S	S	H	H	L	L	V
Load side		Icu [kA]	In[A]	16	25	36	36	36	36	50	50	50	70	70	85	120	200
DS203NC	L C	6	6...25	16	16	16	20	10	10	20	10	10	20	10	20	10	10
			32	10	10	10	16	10	10	16	10	10	16	10	16	10	10
DS203NC	B,C,K	10	6...25	16	16	16	25	16	16	25	16	16	25	16	25	16	16
			32	16	16	16	16	16	16	16	16	16	16	16	16	16	16

S200 - DS203NC @ 400V

		Supply side		S200	S200M	S200P	S300P	S200P	S300P
		Char		B-C	B,C	B,C	B,C	B,C	B,C
Load side		Icu [kA]		20	25	40	40	25	25
			In[A]	0,5..63	0,5...63	0,5...25	0,5...25	32	32
DS203NC	L C	6	6...32	20	25	40	40	25	25
DS203NC	B,C,K	10	6...32	20	25	40	40	25	25

RCDs technical details

Coordination tables: back-up DS203NC

S800 - DS203NC @ 400V

		Supply side		S800N							
Load side	Char			B,C,D							
		Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DS203NC L	C	6	36								
			6...16	36	36	25	25	18	15	15	15
			20		36	25	25	18	15	15	15
			25			25	25	18	15	15	15
DS203NC	B,C,K	10	32				25	18	15	15	15
			6...16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25			36	36	36	36	36	36
			32				36	36	36	36	36

		Supply side		S800S							
Load side	Char			B,C,D,K							
		Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DS203NC L	C	6	6...16	50	40	25	25	18	15	15	15
			20		40	25	25	18	15	15	15
			25			25	25	18	15	15	15
			32				25	18	15	15	15
DS203NC	B,C,K	10	6...16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
							50	50	50	50	50

		Supply side		S800B							
Load side	Char			B,C,D,K							
		Icu [kA]	In[A]	25	32	40	50	63	80	100	125*
DS203NC L	C	6	6	-	16	16	16	16	15	15	15
			8	-	16	16	16	16	15	15	15
			10	-	16	16	16	16	15	15	15
			13	-	16	16	16	16	15	15	15
			16	-	16	16	16	16	15	15	15
			20	-	16	16	16	16	15	15	15
			25	-		16	16	16	15	15	15
			32	-			16	16	15	15	15
DS203NC	B,C,K	10	6	-	16	16	16	16	16	16	16
			8	-	16	16	16	16	16	16	16
			10	-	16	16	16	16	16	16	16
			13	-	16	16	16	16	16	16	16
			16	-	16	16	16	16	16	16	16
			20	-	16	16	16	16	16	16	16
			25	-		16	16	16	16	16	16
			32	-			16	16	16	16	16

*Only S800B B,C

RCDs technical details

Coordination tables: back-up DS203NC

		Supply side		S800C						
		Char		B,C,D,K						
Load side	Icu [kA]	25								
		In[A]	25	32	40	50	63	80	100	125
DS203NC L C	6	6	25	25	25	25	18	15	15	15
		8	25	25	25	25	18	15	15	15
		10	25	25	25	25	18	15	15	15
		13	25	25	25	25	18	15	15	15
		16	25	25	25	25	18	15	15	15
		20		25	25	25	18	15	15	15
		25			25	25	18	15	15	15
		32				25	18	15	15	15
DS203NC	B,C,K	10	6	25	25	25	25	25	25	25
			8	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25
			13	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25
			20		25	25	25	25	25	25
			25			25	25	25	25	25
			32				25	25	25	25

RCDs technical details

Coordination tables: back-up DSE201

Fuses - DSE201 @ 230/240 V

			Supply side	Fuse 25gG	Fuse 40gG	Fuse 50gG	Fuse 63gG	Fuse 80gG	Fuse 100gG	Fuse 125gG	Fuse 160gG	Fuse 200gG
Load side	Icu [kA]	Char.	In [A]	25	40	50	63	80	100	125	160	200
DSE201	6	B,C	up to 20	25	25	20	10	10	10	10	10	10
			25-32	-	25	20	10	7,5	7,5	7,5	7,5	7,5

MCCB @ 415 V - DSE201 @ 230/240 V

			Supply side	T1	T2	T3	T4
Load side	Icu [kA]	Char.	In [A]	160	160	250	250
DSE201	6	B,C	up to 20	10	10	10	10
			25-32	7,5	7,5	7,5	7,5

MCCB @ 415 V - DSE201 @ 230/240 V

			Supply side	XT1	XT2	XT3	XT4
Load side	Icu [kA]	Char.	In [A]	160	160	250	250
DSE201	6	B,C	up to 20	10	10	10	10
			25-32	7,5	7,5	7,5	7,5

RCDs technical details

Coordination tables: back-up DSE201 M

Fuses/S750DR - DSE201 M @ 230/240 V

		Supply side		Fuse gG	S750DR
Load side	Char.	Icu [kA]	In [A]	In [A]	In [A]
DSE201 M	B	15	6	63	100
			10, 16, 20	100	100
			25, 32	100	100
			40	125	100
		10	50	160	100
	C	15	6	40	100
			10, 16, 20	100	100
			25, 32	100	100
			40	125	100
		10	50	160	100

This table shows coordination between DSE201 M and the Supply side fuse maximum current value. Combination of the two protections allows the breaking capacity to be elevated up to that of the combined fuse.

i.e. Load side RCBO DSE201 M-C16, Supply side fuse with In up to 100 A (breaking capacity: 100 kA). RCBO protection up to 100 kA

RCDs technical details

Coordination tables: back-up DSE201 M

MCCB @ 415 V - DSE201 M @ 230/240 V

Supply side			XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4	XT2	XT4
			B	C	N	N	N	N	S	S	S	H	H	H	L	L	V	V	
Load side	Char.	Icu [kA]	In [A]	18	25	36	36	36	36	50	50	50	70	70	70	120	120	150	150
DSE201 M	B,C	15	6, 10 16...40	18	25	30	36	36	36	30	50	40 25	40 30	70 60	40 40	40 30	40 40	40 30	40 30
		10	50	18	25	30	36	16	36	30	36	16	40	30	40	40	30	40	30

MCCB @ 415 V - DSE201M @ 230/240 V

Supply side			T1	T1	T1	T2	T3	T4	T2	T3	T4	T2	T4	T2	T4	T2	T4	T4
			B	C	N	N	N	N	S	S	S	H	H	H	L	L	V	V
Load side	Char.	Icu [kA]	In [A]	16	25	36	36	36	36	50	50	70	70	70	85	120	200	
DSE201 M	B,C	15	6, 10 16...40	16	25	30	36	36	36	50	40 25	70 60	40 40	85 60	40 40	40 40	40 40	40 40
		10	50	16	25	30	36	16	36	36	16	40	40	40	40	40	40	

S800 - DSE201M @ 230/240 V

Supply side			S800U								
			K,Z								
			50								
Load side	Char.	Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DSE201 M	B,C	15	6...16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50
			40					50	50	50	50
			10	50					50	50	50

S800 - DSE201M @ 230/240 V

Supply side			S800S								
			B,C,D,K								
			50								
Load side	Char.	Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DSE201 M	B,C	15	6...16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50
			40					50	50	50	50
			10	50					50	50	50

RCDs technical details

Coordination tables: back-up DSE201 M

S800 - DSE201M @ 230/240 V

Load side	Char.	Icu [kA]	In[A]	S800N							
				Supply side				B,C,D			
								36			
Load side	Char.	Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DSE201 M	B,C	15	6...16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25			36	36	36	36	36	36
			32				36	36	36	36	36
			40					36	36	36	36
			10	50					36	36	36

S800 - DSE201M @ 230/240 V

Load side	Char.	Icu [kA]	In[A]	S800C							
				Supply side				B,C,D			
								25			
Load side	Char.	Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DSE201 M	B,C	15	6...16	25	25	25	25	25	25	25	25
			20		25	25	25	25	25	25	25
			25			25	25	25	25	25	25
			32				25	25	25	25	25
			40					25	25	25	25
			10	50					25	25	25

S800 - DSE201M @ 230/240 V

Load side	Char.	Icu [kA]	In[A]	S800B							
				Supply side				B,C,D,K			
								25			
Load side	Char.	Icu [kA]	In[A]	32	40	50	63	80	100	125	
DSE201 M	B,C	15	6...16	16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16	16
			25		16	16	16	16	16	16	16
			32			16	16	16	16	16	16
			40				16	16	16	16	16
			10	50				16	16	16	16

S200P - DSE201M @ 230/240 V

Load side	Char.	Icu [kA]	In[A]	S200P				S300P			
				Supply side				B,C			
								B,C			
Load side	Char.	Icu [kA]	In[A]	0.5....25				32....63			
DSE201 M	B,C	15	6...40	25				15			
			10	50				15			
									15		

S300P - DSE201M @ 230/240 V

Load side	Char.	Icu [kA]	In[A]	S300P				S300P			
				Supply side				B,C			
								B,C			
Load side	Char.	Icu [kA]	In[A]	0.5....25				32....63			
DSE201 M	B,C	15	6...40	25				15			
			10	50				15			
									15		

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax XT1 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side XT1											
			Version	B,C,N,S,H										
				Release TM	16	20	25	32	40	50	63	80	100	125
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T	T	T	T
			10		3	3	3	4,5	T	T	T	T	T	T
			16				3	4,5	5	T	T	T	T	T
			20					3	5	T	T	T	T	T
			25						5	T	T	T	T	T
			32							T	T	T	T	T
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T	T	T	T	T
			4	T	T	T	T	T	T	T	T	T	T	T
			6	6	6	6	6	6	T	T	T	T	T	T
			8		3	3	3	4,5	7,5	8,5	T	T	T	T
			10		3	3	3	4,5	7,5	8,5	T	T	T	T
			13			3	4,5	5	7,5	T	T	T	T	T
			16			3	4,5	5	7,5	T	T	T	T	T
			20				3	5	6	T	T	T	T	T
			25					5	6	T	T	T	T	T
DS201 (2019) M	B,C,K	15	32						6	7,5	T	T		
			40							7,5	T	T		

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax XT2 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	In[A]	Supply side XT2												EL				
				Version		TM														
				Release	TM	16	20	25	32	40	50	63	80	100	125	160	10	25	63	100
DS201 (2019) L	C	6	6		T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			10		3 ¹	3	3	3	4,5	T	T	T	T	T	T	T	T	T	T	T
			16			3 ¹	3	4,5	5	T	T	T	T	T	T	T	T	T	T	T
			20				3 ¹	3	5	T	T	T	T	T	T	T	T	T	T	T
			25					3 ¹	5	T	T	T	T	T	T	T	T	T	T	T
			32						3 ¹	T	T	T	T	T	T	T	T	T	T	T
DS201 (2019)	B,C,K	10	1		T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			2		T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			4		T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			6		T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			8		3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	T
			10		3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	T
			13			3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	T
			16				3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T
			20					3 ¹	3	5	6	T	T	T	T	T	T	T	T	T
			25						3 ¹	5	6	T	T	T	T	T	T	T	T	T
DS201 (2019) M	B,C,K	15	32						3 ¹	6	7,5	T	T	T	T	T	T	T	T	T
			40							6 ¹	7,5	T	T	T	T	T	T	T	T	T

¹ Value valid in case of Supply S. breaker only magnetic

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax XT3 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side XT3								
			Version	N,S	63	80	100	125	160	200	250
			Release	TM							
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	
			10	T	T	T	T	T	T	T	
			16	5	T	T	T	T	T	T	
			20	5	T	T	T	T	T	T	
			25	5	T	T	T	T	T	T	
			32		T	T	T	T	T	T	
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T	
			2	T	T	T	T	T	T	T	
			4	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	
			8	7,5	8,5	T	T	T	T	T	
			10	7,5	8,5	T	T	T	T	T	
			13	5	7,5	T	T	T	T	T	
			16	5	7,5	T	T	T	T	T	
			20	5	6	T	T	T	T	T	
			25	5	6	T	T	T	T	T	
			32		6	7,5	T	T	T	T	
			40		6 ¹	7,5	T	T	T	T	
DS201 (2019) M	B,C,K	15	4	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	
			10	7,5	8,5	T	T	T	T	T	
			13	5	7,5	T	T	T	T	T	
			16	5	7,5	T	T	T	T	T	
			20	5	6	T	T	T	T	T	
			25	5	6	T	T	T	T	T	
			32		6	7,5	T	T	T	T	
			40		6 ¹	7,5	T	T	T	T	

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax XT4 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	In [A]	Supply side XT4																EL						
				Version N,S,H,L,V																						
				Release TM																						
				16	20	25	32	40	50	63	80	100	125	160	200	225	250	40	63	100	160	250				
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10	3	3 ¹	3	3	3	4,5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	T	
			16		3 ¹	3	4,5	5	T	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	T	
			20		3 ¹		3	5	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	
			25			3 ¹	5	T	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	
			32			3 ¹		T	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			2	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			8	3	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	3	T	T	T	T	T	T	
			10	3	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	3	T	T	T	T	T	T	
			13		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	T	
			16		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	T	
			20		3 ¹		3	5	6	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	
			25			3 ¹	5	6	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	
DS201 (2019) M	B,C,K	15	32		3 ¹		6	7,5	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	T
			40			6 ¹	7,5	T	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	T
			4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10	3	3 ¹	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	
			13		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	T	
			16		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	T	
			20		3 ¹		3	5	6	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	
			25			3 ¹	5	6	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	
			32			3 ¹		6	7,5	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	
			40			6 ¹	7,5	T	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T	

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax T1 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side T1											
			Version B,C,N		Release TMD									
			In[A]	16	20	25	32	40	50	63	80	100	125	160
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T	T	T	T
			10		3	3	3	4,5	T	T	T	T	T	T
			16			3	4,5	5	T	T	T	T	T	T
			20				3	5	T	T	T	T	T	T
			25					5	T	T	T	T	T	T
			32						T	T	T	T	T	T
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T	T	T	T	T
			4	T	T	T	T	T	T	T	T	T	T	T
			6	6	6	6	6	6	T	T	T	T	T	T
			8		3	3	3	4,5	7,5	8,5	T	T	T	T
			10		3	3	3	4,5	7,5	8,5	T	T	T	T
			13			3	4,5	5	7,5	T	T	T	T	T
			16			3	4,5	5	7,5	T	T	T	T	T
			20				3	5	6	T	T	T	T	T
			25					5	6	T	T	T	T	T
			32						6	7,5	T	T	T	T
			40							7,5	T	T	T	T
DS201 (2019) M	B,C,K	15	4	T	T	T	T	T	T	T	T	T	T	T
			6	6	6	6	6	6	T	T	T	T	T	T
			10		3	3	3	4,5	7,5	8,5	T	T	T	T
			13			3	4,5	5	7,5	T	T	T	T	T
			16			3	4,5	5	7,5	T	T	T	T	T
			20				3	5	6	T	T	T	T	T
			25					5	6	T	T	T	T	T
			32						6	7,5	T	T	T	T
			40							7,5	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax T2 @ 415V - DS201 (2019) @ 230/240V

		Supply side		T2																	
		Version		N,S,H,L																	
		Release		TMD, MA												EL					
Load side	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160	10	25	63	100	160		
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
			10	3 ¹	3	3	3	4,5	T	T	T	T	T	T	T	T	T	T	T		
			16		3 ¹	3	4,5	5	T	T	T	T	T	T	T	T	T	T	T		
			20		3 ¹	3	3	5	T	T	T	T	T	T	T	T	T	T	T		
			25			3 ¹	5	T	T	T	T	T	T	T	T	T	T	T	T		
			32				3 ¹		T	T	T	T	T	T	T	T	T	T	T		
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			2	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			8	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	T	T	
			10	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	T	T	
			13		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	T	T	
			16		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	T	T	
			20		3 ¹	3	3	5	6	T	T	T	T	T	T	T	T	T	T	T	
			25			3 ¹	5	6	T	T	T	T	T	T	T	T	T	T	T	T	
			32				3 ¹		6	7,5	T	T	T	T	T	T	T	T	T	T	
			40					6 ¹	7,5	T	T					T	T				
DS201 (2019) M	B,C,K	15	4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	T	T	
			13		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	T	T	
			16		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	T	T	
			20		3 ¹	3	3	5	6	T	T	T	T	T	T	T	T	T	T	T	
			25			3 ¹	5	6	T	T	T	T	T	T	T	T	T	T	T	T	
			32				3 ¹		6	7,5	T	T	T	T	T	T	T	T	T	T	
			40					6 ¹	7,5	T	T					T	T				

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax T3 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side T3							
			Version	N,S						
				Release	TMD, MA					
			In[A]	63	80	100	125	160	200	250
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T
			16	5	T	T	T	T	T	T
			20	5	T	T	T	T	T	T
			25	5	T	T	T	T	T	T
			32		T	T	T	T	T	T
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T
			4	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T
			8	7,5	8,5	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T
			40		6 ¹	7,5	T	T	T	T
DS201 (2019) M	B,C,K	15	4	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T
			40		6 ¹	7,5	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS201

S800N / S800S (Char C) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800N / S800S							
			Version	C							
			36 / 50								
DS201 (2019) L	C	6	In[A]	25	32	40	50	63	80	100	125
			6			0.55	1.1	1.5	2.5	3.6	5.5
			10			0.45	1	1.3	1.9	2.8	4.2
			16				0.75	1.1	1.6	2.3	3.6
			20					0.9	1.4	1.9	3.3
			25						1.2	1.6	2.7
			32						1	1.5	2.5
			1	0.55	0.6	1.4	3.4	7.2	T	T	T
			2	0.43	0.55	1.2	3	6.6	T	T	T
			4		0.43	0.75	1.3	2.1	3.9	6.6	T
DS201 (2019)	B,C,K	10	6		0.55	1.1	1.5	2.5	3.6	5.5	
			8		0.5	1.25	1.4	2.2	3.2	5	
			10		0.45	1	1.3	1.9	2.8	4.2	
			13		0.38	0.83	1.2	1.75	2.6	3.9	
			16			0.75	1.1	1.6	2.3	3.6	
			20				0.9	1.4	1.9	3.3	
			25					1.2	1.6	2.7	
			32					1	1.5	2.5	
			40						1.4	2.1	
			4	0.43	0.75	1.3	2.1	3.9	6.6	T	
DS201 (2019) M	B,C,K	15	6		0.55	1.1	1.5	2.5	3.6	5.5	
			10		0.45	1	1.3	1.9	2.8	4.2	
			13		0.35	0.9	1.2	1.7	2.6	3.8	
			16			0.75	1.1	1.6	2.3	3.6	
			20				0.9	1.4	1.9	3.3	
			25					1.2	1.6	2.7	
			32					1	1.5	2.5	
			40						1.4	2.1	

RCDs technical details

Coordination tables: selectivity DS201

S800 N / S800S (Char D) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side		S800N / S800S						
			Version	D	36 / 50						
DS201 (2019) L	C	6	In[A]	25	32	40	50	63	80	100	125
			6	0.6	1.3	2	3.2	3.9	T	T	T
			10	0.5	1.2	1.65	2.6	3.1	T	T	T
			16		0.9	1.4	1.8	2.6	5	T	T
			20			1.3	1.6	2.2	4.2	5.4	T
			25				1.5	1.9	3.5	4.5	T
			32					1.8	2.8	4.2	5.5
			1	1.6	4.8	T	T	T	T	T	T
			2	1.3	4.1	T	T	T	T	T	T
			4	0.8	1.6	3	5.4	7.6	T	T	T
DS201 (2019)	B,C,K	10	6	0.6	1.3	2	3.2	3.9	8	T	T
			8	0.4	1.25	1.8	2.9	3.6	7	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13		1.1	1.55	2.2	2.8	5.9	7.2	9.6
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5
			4	0.8	1.6	3	5.4	7.6	T	T	T
DS201 (2019) M	B,C,K	15	6	0.6	1.3	2	3.2	3.9	8	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13			1.55	2.1	2.8	5.6	7.1	9.5
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5

RCDs technical details

Coordination tables: selectivity DS201

S800S (Char K) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800S							
			Version	K							
			36 / 50	In[A]	25	32	40	50	63	80	100
DS201 (2019) L	C	6	6		1.3	2	3.2	3.9	T	T	T
			10		1.2	1.65	2.6	3.1	T	T	T
			16		0.9	1.4	1.8	2.6	5	T	T
			20			1.3	1.6	2.2	4.2	5.4	T
			25				1.5	1.9	3.5	4.5	T
			32					1.8	2.8	4.2	5.5
			1	1.6	4.8	T	T	T	T	T	T
DS201 (2019)	B,C,K	10	2	1.3	4.1	T	T	T	T	T	T
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
			8	0.4	1.25	1.8	2.9	3.6	7	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13		1.1	1.55	2.2	2.8	5.9	7.2	9.6
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5
DS201 (2019) M	B,C,K	15	4		1.6	3	5.4	7.6	T	T	T
			6		1.3	2	3.2	3.9	8	T	T
			10		1.2	1.65	2.6	3.1	6.2	8.6	T
			13			1.55	2.1	2.8	5.6	7.1	9.5
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5

RCDs technical details

Coordination tables: selectivity DS201

S800C (Char B) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800C							
			Version	B							
			25	32	40	50	63	80	100	125	
DS201 (2019) L	C	6	I _n [A]	25							
			6			0.6	1.2	1.6	2.6	3.8	
			10			0.5	1.1	1.4	2	3	
			16				0.8	1.2	1.7	2.5	
			20					1	1.5	2.1	
			25						1.3	1.8	
			32						1.1	1.7	
			1	0.5	0.8	1.6	5	10	T	T	
			2	0.43	0.6	1.3	4	9	T	T	
			4		0.45	0.8	1.5	2.5	4	7.3	
DS201 (2019)	B,C,K	10	6		0.6	1.4	1.6	2.6	3.8		
			8		0.55	1.3	1.5	2.4	3.5		
			10		0.5	1.1	1.4	2	3		
			13			0.9	1.3	1.9	2.8		
			16			0.8	1.2	1.7	2.5		
			20				1	1.5	2.1		
			25					1.3	1.8		
			32					1.1	1.7		
			40						1.6		
			4	0.45	0.8	1.5	2.5	4	7.3		
DS201 (2019) M	B,C,K	15	6		0.6	1.2	1.6	2.6	3.8		
			10		0.5	1.1	1.4	2	3		
			13		0.95	1.3	1.7	2.8			
			16			0.8	1.2	1.7	2.5		
			20				1	1.5	2.1		
			25					1.3	1.8		
			32					1.1	1.7		
			40						1.6		

RCDs technical details

Coordination tables: selectivity DS201

S800C (Char C) - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800C								
		Version	C								
		Icu [kA]	25								
DS201 (2019) L	C	6	In[A]	25	32	40	50	63	80	100	125
			6			0.55	1.1	1.5	2.5	3.6	5.5
			10			0.45	1	1.3	1.9	2.8	4.2
			16				0.75	1.1	1.6	2.3	3.6
			20					0.9	1.4	1.9	3.3
			25						1.2	1.6	2.7
			32						1	1.5	2.5
			1	0.55	0.6	1.4	3.4	7.2	T	T	T
			2	0.43	0.55	1.2	3	6.6	T	T	T
			4		0.43	0.75	1.3	2.1	3.9	6.6	T
DS201 (2019)	B,C,K	10	6		0.55	1.1	1.5	2.5	3.6	5.5	
			8		0.5	1.25	1.4	2.2	3.2	5	
			10		0.45	1	1.3	1.9	2.8	4.2	
			13		0.38	0.83	1.2	1.75	2.6	3.9	
			16			0.75	1.1	1.6	2.3	3.6	
			20				0.9	1.4	1.9	3.3	
			25					1.2	1.6	2.7	
			32					1	1.5	2.5	
			40						1.4	2.1	
			4	0.43	0.75	1.3	2.1	3.9	6.6	T	
DS201 (2019) M	B,C,K	15	6		0.55	1.1	1.5	2.5	3.6	5.5	
			10		0.45	1	1.3	1.9	2.8	4.2	
			13		0.35	0.9	1.2	1.7	2.6	3.8	
			16		0.75	1.1	1.6	2.3	3.6		
			20			0.9	1.4	1.9	3.3		
			25				1.2	1.6	2.7		
			32				1	1.5	2.5		
			40					1.4	2.1		

RCDs technical details

Coordination tables: selectivity DS201

S800C (Char D) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800C							
			Version	D							
			25	In[A]	25	32	40	50	63	80	100
DS201 (2019) L	C	6	6		1.3	2	3.2	3.9	T	T	T
			10		1.2	1.65	2.6	3.1	T	T	T
			16		0.9	1.4	1.8	2.6	5	T	T
			20			1.3	1.6	2.2	4.2	5.4	T
			25				1.5	1.9	3.5	4.5	T
			32					1.8	2.8	4.2	5.5
			1	1.6	4.8	T	T	T	T	T	T
DS201 (2019)	B,C,K	10	2	1.3	4.1	T	T	T	T	T	T
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
			8	0.4	1.25	1.8	2.9	3.6	7	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13		1.1	1.55	2.2	2.8	5.9	7.2	9.6
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5
DS201 (2019) M	B,C,K	15	4		1.6	3	5.4	7.6	T	T	T
			6		1.3	2	3.2	3.9	8	T	T
			10		1.2	1.65	2.6	3.1	6.2	8.6	T
			13			1.55	2.1	2.8	5.6	7.1	9.5
			16			1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5

RCDs technical details

Coordination tables: selectivity DS201

S800C (Char K) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800C							
			Version	K							
			25	25	32	40	50	63	80	100	125
DS201 (2019) L	C	6	6		1.3	2	3.2	3.9	T	T	T
			10		1.2	1.65	2.6	3.1	T	T	T
			16		0.9	1.4	1.8	2.6	5	T	T
			20			1.3	1.6	2.2	4.2	5.4	T
			25				1.5	1.9	3.5	4.5	T
			32					1.8	2.8	4.2	5.5
			1	1.6	4.8	T	T	T	T	T	T
DS201 (2019)	B,C,K	10	2	1.3	4.1	T	T	T	T	T	T
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
			8	0.4	1.25	1.8	2.9	3.6	7	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13		1.1	1.55	2.2	2.8	5.9	7.2	9.6
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5
DS201 (2019) M	B,C,K	15	4		1.6	3	5.4	7.6	T	T	T
			6		1.3	2	3.2	3.9	8	T	T
			10		1.2	1.65	2.6	3.1	6.2	8.6	T
			13			1.55	2.1	2.8	5.6	7.1	9.5
			16			1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5

RCDs technical details

Coordination tables: selectivity DS201

S800B (Char C) - DS201 (2019) @ 230/240V

Load side	Char	Supply side		S800B						
		Version		C						
		Icu [kA]	16							
DS201 (2019) L	C	6	In[A]	32	40	50	63	80	100	125
			6		0.55	1.1	1.5	2.5	3.6	5.5
			10		0.45	1	1.3	1.9	2.8	4.2
			16			0.75	1.1	1.6	2.3	3.6
			20				0.9	1.4	1.9	3.3
			25					1.2	1.6	2.7
			32					1	1.5	2.5
			1	0.6	1.4	3.4	7.2	T	T	T
			2	0.55	1.2	3	6.6	T	T	T
			4	0.43	0.75	1.3	2.1	3.9	6.6	T
DS201 (2019)	B,C,K	10	6	0.55	1.1	1.5	2.5	3.6	5.5	
			8	0.5	1.25	1.4	2.2	3.2	5	
			10	0.45	1	1.3	1.9	2.8	4.2	
			13	0.38	0.82	1.2	1.75	2.6	3.9	
			16		0.75	1.1	1.6	2.3	3.6	
			20			0.9	1.4	1.9	3.3	
			25				1.2	1.6	2.7	
			32				1	1.5	2.5	
			40					1.4	2.1	
			4	0.43	0.75	1.3	2.1	3.9	6.6	T
DS201 (2019) M	B,C,K	15	6	0.55	1.1	1.5	2.5	3.6	5.5	
			10	0.45	1	1.3	1.9	2.8	4.2	
			13	0.35	0.9	1.2	1.7	2.6	3.8	
			16		0.75	1.1	1.6	2.3	3.6	
			20			0.9	1.4	1.9	3.3	
			25				1.2	1.6	2.7	
			32				1	1.5	2.5	
			40					1.4	2.1	

RCDs technical details

Coordination tables: selectivity DS201

S800B (Char D) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800B							
			Version	D							
			16	In[A]	32	40	50	63	80	100	125
DS201 (2019) L	C	6	6	1.3	3.2	3.2	3.9	T	T	T	
			10	1.2	1.65	2.6	3.1	T	T	T	
			16	0.9	1.4	1.8	2.6	5	T	T	
			20		1.3	1.6	2.2	4.2	5.4	T	
			25			1.5	1.9	3.5	4.5	T	
			32				1.8	2.8	4.2	5.5	
			1	4.8	T	T	T	T	T	T	
DS201 (2019)	B,C,K	10	2	4.1	T	T	T	T	T	T	
			4	1.6	3	5.4	7.6	T	T	T	
			6	1.3	2	3.2	3.9	8	T	T	
			8	1.25	1.8	2.9	3.6	7	T	T	
			10	1.2	1.65	2.6	3.1	6.2	8.6	T	
			13	1.1	1.55	2.2	2.8	5.9	7.2	9.6	
			16	0.9	1.4	1.9	2.6	5	6.3	8.8	
			20		1.3	1.8	2.2	4.2	5.4	7.6	
			25			1.7	1.9	3.5	4.5	6.6	
			32				1.8	2.8	4.2	5.5	
DS201 (2019) M	B,C,K	15	40				1.7	2.7	4	5	
			4	1.6	3	5.4	7.6	T	T	T	
			6	1.3	2	3.2	3.9	8	T	T	
			10	1.2	1.65	2.6	3.1	6.2	8.6	T	
			13		1.55	2.1	2.8	5.6	7.1	9.5	
			16		1.4	1.8	2.6	5	6.3	8.8	
			20		1.3	1.6	2.2	4.2	5.4	7.6	
			25			1.5	1.9	3.5	4.5	6.6	
			32				1.8	2.8	4.2	5.5	
			40				1.7	2.7	4	5	

RCDs technical details

Coordination tables: selectivity DS201

S800B (Char K) - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800B								
			Version		K						
			Icu [kA]	16	In[A]	32	40	50	63	80	100
DS201 (2019) L	C		6	6	1.3	3.2	3.2	3.9	T	T	T
				10	1.2	1.65	2.6	3.1	T	T	T
				16	0.9	1.4	1.8	2.6	5	T	T
				20		1.3	1.6	2.2	4.2	5.4	T
				25			1.5	1.9	3.5	4.5	T
				32				1.8	2.8	4.2	5.5
				1	4.8	T	T	T	T	T	T
DS201 (2019)	B,C,K		10	2	4.1	T	T	T	T	T	T
				4	1.6	3	5.4	7.6	T	T	T
				6	1.3	2	3.2	3.9	8	T	T
				8	1.25	1.8	2.9	3.6	7	T	T
				10	1.2	1.65	2.6	3.1	6.2	8.6	T
				13	1.1	1.55	2.2	2.8	5.9	7.2	9.6
				16	0.9	1.4	1.9	2.6	5	6.3	8.8
				20		1.3	1.8	2.2	4.2	5.4	7.6
				25			1.7	1.9	3.5	4.5	6.6
				32				1.8	2.8	4.2	5.5
DS201 (2019) M	B,C,K		15	40				1.7	2.7	4	5
				4	1.6	3	5.4	7.6	T	T	T
				6	1.3	2	3.2	3.9	8	T	T
				10	1.2	1.65	2.6	3.1	6.2	8.6	T
				13		1.55	2.1	2.8	5.6	7.1	9.5
				16		1.4	1.8	2.6	5	6.3	8.8
				20		1.3	1.6	2.2	4.2	5.4	7.6
				25			1.5	1.9	3.5	4.5	6.6
				32				1.8	2.8	4.2	5.5
				40				1.7	2.7	4	5

RCDs technical details

Coordination tables: selectivity DS201

S800U (Char K) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800U									
			Version	K									
		50		In[A]	25	30	40	50	60	70	80	90	100
DS201 (2019) L	C	6	6	I _n [A]	0.34	0.41	0.57	1.1	1.5	2	2.5	3.6	T
			10	I _n [A]	0.23	0.3	0.45	1	1.3	1.6	1.9	2.8	T
			16	I _n [A]	0.21	0.35	0.75	1.1	1.3	1.6	2.3	T	
			20	I _n [A]		0.22	0.6	0.9	1.1	1.4	1.9	5.4	
			25	I _n [A]					1	1.2	1.6	4.5	
			32	I _n [A]						1	1.5	4.2	
			1	I _n [A]	0.55	0.6	1.4	3.4	7.2	8	T	T	T
DS201 (2019)	B,C,K	10	2	I _n [A]	0.44	0.55	1.2	3	6.6	7	T	T	T
			4	I _n [A]	0.38	0.43	0.75	1.3	2.1	3	3.9	6.6	T
			6	I _n [A]	0.34	0.38	0.56	1.1	1.5	2	2.5	3.6	T
			8	I _n [A]	0.23	0.32	0.5	1.25	1.4	1.8	2.2	3.2	T
			10	I _n [A]	0.2	0.28	0.45	1	1.3	1.6	1.9	2.8	8.6
			13	I _n [A]	0.22	0.38	0.83	1.2	1.4	1.75	2.6	7.2	
			16	I _n [A]	0.19	0.35	0.75	1.1	1.3	1.6	2.3	6.3	
			20	I _n [A]		0.28	0.58	0.9	1.1	1.4	1.9	5.4	
			25	I _n [A]					1	1.2	1.6	4.5	
			32	I _n [A]						1.5	1.5	4.2	
			40	I _n [A]						1.4	1.4	4	
DS201 (2019) M	B,C,K	15	4	I _n [A]	0.38	0.43	0.75	1.3	2.1	3	3.9	6.6	T
			6	I _n [A]	0.34	0.38	0.55	1.1	1.5	2	2.5	3.6	T
			10	I _n [A]	0.2	0.28	0.45	1	1.3	1.6	1.9	2.8	8.6
			13	I _n [A]		0.35	0.9	1.2	1.4	1.7	2.6	7.1	
			16	I _n [A]	0.19	0.34	0.75	1.1	1.3	1.6	2.3	6.3	
			20	I _n [A]	0.29	0.57	0.9	1.1	1.4	1.9	5.4		
			25	I _n [A]		0.53	0.6	0.9	1.2	1.6	4.5		
			32	I _n [A]			0.5	0.7	1	1.5	4.2		
			40	I _n [A]			0.3	0.5	0.8	1.4	4		

RCDs technical details

Coordination tables: selectivity DS201

S750 DR - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S750 DR								
			Version	Eselective; Kselective								
			25	In[A]	16	20	25	35	40	50	63	80
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T	T	T
			16		T	T	T	T	T	T	T	T
			20			T	T	T	T	T	T	T
			25				T	T	T	T	T	T
			32					T	T	T	T	T
			1	T	T	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T	T	T
			4	T	T	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T	T	T
DS201 (2019)	B,C,K	10	8	T	T	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T	T	T
			13		T	T	T	T	T	T	T	T
			16			T	T	T	T	T	T	T
			20				T	T	T	T	T	T
			25					T	T	T	T	T
			32						T	T	T	T
			40							T	T	T
			4	T	T	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T	T	T
DS201 (2019) M	B,C,K	15	10	T	T	T	T	T	T	T	T	T
			13	T	T	T	T	T	T	T	T	T
			16		T	T	T	T	T	T	T	T
			20			T	T	T	T	T	T	T
			25				T	T	T	T	T	T
			32					T	T	T	T	T
			40						T	T	T	T

RCDs technical details

Coordination tables: selectivity DS201

S750 - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side S750							
			Version		Eselective; Kselective					
			25							
		In[A]	16	20	25	35	40	50	63	
DS201 (2019) L	C	6	6	T	T	T	T	T	T	
			10	T	T	T	T	T	T	
			16		T	T	T	T	T	
			20			T	T	T	T	
			25				T	T	T	
			32					T	T	
			1	T	T	T	T	T	T	
			2	T	T	T	T	T	T	
DS201 (2019)	B,C,K	10	4	T	T	T	T	T	T	
			6	T	T	T	T	T	T	
			8	T	T	T	T	T	T	
			10	T	T	T	T	T	T	
			13		T	T	T	T	T	
			16			T	T	T	T	
			20				T	T	T	
			25					T	T	
			32						T	
			40						T	
DS201 (2019) M	B,C,K	15	4	T	T	T	T	T	T	
			6	T	T	T	T	T	T	
			10	T	T	T	T	T	T	
			13		T	T	T	T	T	
			16			T	T	T	T	
			20				T	T	T	
			25					T	T	
			32						T	
			40						T	

RCDs technical details

Coordination tables: selectivity DS201

Fuses - DS201 (2019) @ 230/240V

Load side	Char	Supply side		Fuses gG							
		Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DS201 (2019) L	C	6	6	1	1.5	4	4.5	T	T	T	T
			10		1.2	3.5	4	T	T	T	T
			16		1	3	3.5	5	T	T	T
			20		1	3	3.5	5	T	T	T
			25		1	2	3	4.5	T	T	T
			32		1	2	3	4.5	5	T	T
DS201 (2019)	B,C,K	10	1	2.8	5.3	T	T	T	T	T	T
			2	2	4	5.8	T	T	T	T	T
			4	1.4	2.1	5.1	6.2		T	T	T
			6	1	1.5	4	4.5	7	T	T	T
			8		1.2	3.5	4	6	T	T	T
			10		1.2	3.5	4	6	T	T	T
			13		1	3	3.5	5	T	T	T
			16		1	3	3.5	5	T	T	T
			20		1	3	3.5	5	8	T	T
			25		1	2	3	4.5	6.5	T	T
			32		1	2	3	4.5	5	8	T
			40					3.7	4	6	8.7
DS201 (2019) M	B,C,K	15	4	1.1	1.6	4.2	T	T	T	T	T
			6	1	1.5	4	4.5	7	T	T	T
			10		1.2	3.5	4	6	10	10	T
			13		1.2	3.5	4	6	10	10	T
			16		1	3	3.5	5	10	10	T
			20		1	3	3.5	5	8	10	T
			25			2	3	4.5	6.5	10	T
			32				3	4.5	5	8	T
			40					3.4	3.8	5.5	8.2

RCBO DS301C

Coordination tables: selectivity DS301C

MCCB Tmax XT1 @ 415 V - RCBOs DS301C @230/240 V

			Supply side	XT1										
			Version	B, C, N, S, H										
			Release	TM										
Load side	Char	Icu (kA)	In (A)	16	20	25	32	40	50	63	80	100	125	160
RCBOs DS301C	B, C	6	6	3	3	3	3	3	3	3	3	3	3	3
			10			3	3	3	3	3	3	3	3	3
			13				3	3	3	3	3	3	3	3
			16					3	3	3	3	3	3	3
			20						3	3	3	3	3	3

MCCB Tmax XT2 @ 415 V - RCBOs DS301C @230/240 V

			Supply side	XT2															
			Version	N, S, H, L, V															
			Release	TM															EL
Load side	Char	Icu (kA)	In (A)	16	20	25	32	40	50	63	80	100	125	160	10	25	63	100	160
RCBOs DS301C	B, C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10		3	3	3	3	4.5	T	T	T	T	T		T	T	T	
			13			3	3	4.5	T	T	T	T	T	T		T	T	T	
			16			3	3	4.5	T	T	T	T	T	T		T	T	T	
			20			3	3	3	T	T	T	T	T	T		T	T	T	

MCCB Tmax XT3 @ 415 V - RCBOs DS301C @230/240 V

		Supply side		XT3						
		Version		N, S						
		Release		TM						
Load side	Char	Icu (kA)	In (A)	63	80	100	125	160	200	250
RCBOs DS301C	B, C	6	6	1.5	4.5	4.5	4.5	4.5	4.5	4.5
			10	1.5	4.5	4.5	4.5	4.5	4.5	4.5
			13	1.5	4.5	4.5	4.5	4.5	4.5	4.5
			16	1.5	4.5	4.5	4.5	4.5	4.5	4.5
			20	1.5	4.5	4.5	4.5	4.5	4.5	4.5

MCCB Tmax XT4 @ 415 V - RCBOs DS301C @230/240 V

RCBO DS301C

Coordination tables: selectivity DS301C

S800N / S800S (Char B) - RCBOs DS301C @230/240 V

			Supply side	S800N / S800S							
			Version	B							
			Release	36 / 50							
Load side	Char	Icu (kA)	In (A)	25	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6				0.2	0.2	0.5	0.5	0.5
			10				0.2	0.2	0.5	0.5	0.5
			13				0.2	0.5	0.5	0.5	0.5
			16				0.2	0.5	0.5	0.5	0.5
			20					0.5	0.5	0.5	0.5

S800N / S800S (Char C) - RCBOs DS301C @230/240 V

			Supply side	S800N / S800S							
			Version	C							
			Release	36 / 50							
Load side	Char	Icu (kA)	In (A)	25	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6			0.2	0.2	0.5	0.5	0.5	0.5
			10			0.2	0.2	0.5	0.5	0.5	0.5
			13			0.2	0.5	0.5	0.5	0.5	0.5
			16			0.2	0.5	0.5	0.5	0.5	0.5
			20				0.5	0.5	0.5	0.5	0.5

S800N / S800S (Char D) - RCBOs DS301C @230/240 V

			Supply side	S800N / S800S							
			Version	D							
			Release	36 / 50							
Load side	Char	Icu (kA)	In (A)	25	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	0.4	0.4	0.4	0.4	1	1	1	3
			10	0.4	0.4	0.4	0.4	1	1	1	3
			13		0.4	0.4	0.4	1	1	1	3
			16		0.4	0.4	0.4	1	1	1	3
			20		0.4	0.4	1	1	1	1	3

S800C (Char B) - RCBOs DS301C @230/240 V

			Supply side	S800C							
			Version	B							
			Release	25							
Load side	Char	Icu (kA)	In (A)	25	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6			0.2	0.4	0.5	0.5	1	
			10			0.2	0.4	0.5	0.5	1	
			13			0.2	0.2	0.5	0.5	1	
			16				0.2	0.5	0.5	1	
			20					0.5	0.5	1	

RCBO DS301C

Coordination tables: selectivity DS301C

S800C (Char C) - RCBOs DS301C @230/240 V

			Supply side	S800C							
			Version	C							
			Release	25							
Load side	Char	Icu (kA)	In (A)	25	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6		0.2	0.4	0.5	0.5	1	2	
			10		0.2	0.4	0.5	0.5	1	2	
			13		0.2	0.2	0.5	0.5	1	2	
			16			0.2	0.5	0.5	1	2	
			20				0.5	0.5	1	2	

S800C (Char D) - RCBOs DS301C @230/240 V

			Supply side	S800C							
			Version	D							
			Release	25							
Load side	Char	Icu (kA)	In (A)	25	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	0.4	0.4	0.6	0.6	1	1	1.5	3
			10	0.4	0.4	0.6	0.6	1	1	1.5	3
			13		0.2	0.6	0.6	1	1	1.5	3
			16		0.2	0.6	0.6	1	1	1.5	3
			20			0.6	0.6	1	1	1.5	3

S800C (Char K) - RCBOs DS301C @230/240 V

			Supply side	S800C							
			Version	K							
			Release	25							
Load side	Char	Icu (kA)	In (A)	25	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	0.4	0.4	0.6	0.6	1	1	1.5	3
			10	0.4	0.4	0.6	0.6	1	1	1.5	3
			13		0.2	0.6	0.6	1	1	1.5	3
			16		0.2	0.6	0.6	1	1	1.5	3
			20			0.6	0.6	1	1	1.5	3

S800S (Char K) - RCBOs DS301C @230/240 V

			Supply side	S800S							
			Version	K							
			Release	36 / 50							
Load side	Char	Icu (kA)	In (A)	25	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	0.2	0.4	0.6	0.6	1	2	2	2
			10	0.2	0.4	0.6	0.6	1	2	2	2
			13		0.4	0.6	0.6	1	2	2	2
			16		0.4	0.6	0.6	1	2	2	2
			20			0.6	0.6	1	2	2	2

RCBO DS301C

Coordination tables: selectivity DS301C

S800B (Char B) - RCBOs DS301C @230/240 V

Load side	Char	Icu (kA)	Supply side	S800B						
			Version	B						
			Release	16						
Load side	Char	Icu (kA)	In (A)	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	0.2	0.2	0.2	0.5	1	2	
			10	0.2	0.2	0.2	0.5	1	2	
			13	0.2	0.2	0.2	0.5	1	2	
			16	0.2	0.2	0.5	1	2		
			20	0.2	0.5		1	2		

S800B (Char C) - RCBOs DS301C @230/240 V

Load side	Char	Icu (kA)	Supply side	S800B						
			Version	C						
			Release	16						
Load side	Char	Icu (kA)	In (A)	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	0.2	0.2	0.2	0.5	1	2	
			10	0.2	0.2	0.2	0.5	1	2	
			13	0.2	0.2	0.2	0.5	1	2	
			16	0.2	0.2	0.5	1	2		
			20	0.2	0.5		1	2		

S800B (Char D) - RCBOs DS301C @230/240 V

Load side	Char	Icu (kA)	Supply side	S800B						
			Version	D						
			Release	16						
Load side	Char	Icu (kA)	In (A)	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	0.5	0.5	0.5	0.5	1.5	1.5	3
			10	0.5	0.5	0.5	0.5	1.5	1.5	3
			13	0.5	0.5	0.5	0.5	1.5	1.5	3
			16	0.5	0.5	0.5	0.5	1.5	1.5	3
			20	0.5	0.5	0.5	1.5	1.5	1.5	3

S800B (Char K) - RCBOs DS301C @230/240 V

Load side	Char	Icu (kA)	Supply side	S800B						
			Version	K						
			Release	16						
Load side	Char	Icu (kA)	In (A)	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	0.5	0.5	0.5	0.5	1.5	1.5	3
			10	0.5	0.5	0.5	0.5	1.5	1.5	3
			13	0.5	0.5	0.5	0.5	1.5	1.5	3
			16	0.5	0.5	0.5	0.5	1.5	1.5	3
			20	0.5	0.5	0.5	1.5	1.5	1.5	3

RCBO DS301C

Coordination tables: selectivity DS301C

S800U (Char K) - RCBOs DS301C @230/240 V

			Supply side	S800U								
			Version	K								
			Release	16								
Load side	Char	Icu (kA)	In (A)	25	30	40	50	60	70	80	90	100
RCBOs DS301C	B, C	6	6	0.4	0.4	0.6	0.6	0.6	0.6	1.5	1.5	1.5
			10	0.4	0.4	0.6	0.6	0.6	0.6	1.5	1.5	1.5
			13		0.2	0.6	0.6	0.6	0.6	1.5	1.5	1.5
			16		0.2	0.6	0.6	0.6	0.6	1.5	1.5	1.5
			20			0.6	0.6	0.6	0.6	1.5	1.5	1.5

S750 DR - RCBOs DS301C @230/240 V

			Supply side	S750 DR								
			Version	Eselective, Kselective								
			Release	25								
Load side	Char	Icu (kA)	In (A)	16	20	25	35	40	50	63	80	100
RCBOs DS301C	B, C	6	6	T	T	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T	T	T
			13		T	T	T	T	T	T	T	T
			16		T	T	T	T	T	T	T	T
			20			T	T	T	T	T	T	T

S750 - RCBOs DS301C @230/240 V

			Supply side	S750						
			Version	Eselective, Kselective						
			Release	25						
Load side	Char	Icu (kA)	In (A)	16	20	25	35	40	50	63
RCBOs DS301C	B, C	6	6	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T
			13		T	T	T	T	T	T
			16		T	T	T	T	T	T
			20			T	T	T	T	T

Fuses - RCBOs DS301C @230/240 V

			Supply side	Fuses gG							
Load side	Char	Icu (kA)	In (A)	25	32	40	50	63	80	100	125
RCBOs DS301C	B, C	6	6	1.5	1.5	1.5	3	T	T	T	T
			10		1.5	1.5	3	T	T	T	T
			13		1.5	1.5	3	4.5	T	T	T
			16		1.5	1.5	3	4.5	T	T	T
			20		1.5	1.5	3	4.5	T	T	T

RCDs technical details

Coordination tables: selectivity DS203NC

Fuses-DS203NC @ 400V

			Supply S.	Fuse gL/gG							
Load S.	Char	Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DS203NC L	C	6	6	1	1.5	4	4.5	T	T	T	T
			8		1.2	3.5	4	T	T	T	T
			10		1.2	3.5	4	T	T	T	T
			13		1	3	3.5	5	T	T	T
			16		1	3	3.5	5	T	T	T
			20		1	3	3.5	5	T	T	T
			25		1	2	3	4.5	T	T	T
			32		1	2	3	4.5	5	T	T
DS203NC	B,C,K	10	6	1	1.5	4	4.5	7	T	T	T
			8		1.2	3.5	4	6	T	T	T
			10		1.2	3.5	4	6	T	T	T
			13		1	3	3.5	5	T	T	T
			16		1	3	3.5	5	T	T	T
			20		1	3	3.5	5	8	T	T
			25		1	2	3	4.5	6.5	T	T
			32		1	2	3	4.5	5	8	T

MCCB @ 415V - DS203NC @ 400V

			Supply S.	XT2	XT1-XT2		XT1-XT2-XT3							XT3			
			Version	B,C,N, S, H, L,V													
Load S.	Char	Icu [kA]	Release	TM													
			In[A]	12.5	16	20	25	32	40	50	63	80	100	125	160	200	250
DS203NC L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			8		3	3	3	4,5	T	T	T	T	T	T	T	T	T
			10		3	3	3	4,5	T	T	T	T	T	T	T	T	T
			13				3	4,5	5	T	T	T	T	T	T	T	T
			16				3	4,5	5	T	T	T	T	T	T	T	T
			20					3	5	T	T	T	T	T	T	T	T
			25						5	T	T	T	T	T	T	T	T
			32							T	T	T	T	T	T	T	T
DS203NC	B, C, K	10	6	6	6	6	6	6	T	T	T	T	T	T	T	T	T
			8		3	3	3	4,5	7,5	8,5	8,5	T	T	T	T	T	T
			10		3	3	3	4,5	7,5	8,5	8,5	T	T	T	T	T	T
			13				3	4,5	5	7,5	7,5	T	T	T	T	T	T
			16				3	4,5	5	7,5	7,5	T	T	T	T	T	T
			20					3	5	6	6	T	T	T	T	T	T
			25						5	6	6	T	T	T	T	T	T
			32							6	6	7,5	T	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS202CR

MCCB@415V-DS202CR@230V

			Supply side		XT1					
			Version		B, C					
			Release		TM					
Load side	Char.	Icu [kA]	In [A]	40A	50A	63A	80A	100A	125A	160A
DS202CR	B,C	10	10	0.6	2	2	3	3	6	6
			13	0.6	2	2	3	3	6	6
			16	0.6	2	2	3	3	6	6
			20	0.6	2	2	3	3	6	6
			25	--	0.8	1	1	2	3	3
			32	--	--	1	1	2	3	3
			40	--	--	--	1	2	3	3
DS202CR M	B,C	10	10	0.6	2	2	3	3	6	6
			13	0.6	2	2	3	3	6	6
			16	0.6	2	2	3	3	6	6
			20	0.6	2	2	3	3	6	6
			25	--	0.8	1	1	2	3	3
			32	--	--	1	1	2	3	3
			40	--	--	--	1	2	3	3

			Supply side		XT1					
			Version		N					
			Release		TM					
Load side	Char.	Icu [kA]	In [A]	40A	50A	63A	80A	100A	125A	160A
DS202CR	B, C	10	10	1	2	2	3	3	6	6
			13	1	2	2	3	3	6	6
			16	1	2	2	3	3	6	6
			20	1	2	2	3	3	6	6
			25	1	1	1	1	2	3	3
			32	--	1	1	1	2	3	3
			40	--	--	--	1	2	3	3
DS202CR M	B, C	10	10	1	2	2	3	3	6	6
			13	1	2	2	3	3	6	6
			16	1	2	2	3	3	6	6
			20	1	2	2	3	3	6	6
			25	1	1	1	1	2	3	3
			32	--	1	1	1	2	3	3
			40	--	--	--	1	2	3	3

			Supply side		XT1					
			Version		S, H					
			Release		TM					
Load side	Char.	Icu[kA]	In[A]	40A	50A	63A	80A	100A	125A	160A
DS202CR	B, C	10	10	T	T	T	T	T	T	T
			13	T	T	T	T	T	T	T
			16	T	T	T	T	T	T	T
			20	3.5	T	T	T	T	T	T
			25	1.6	3.5	T	T	T	T	T
			32	--	--	T=10	T	T	T	T
			40	--	--	--	T	T	T	T
DS202CR M	B, C	10	10	T	T	T	T	T	T	T
			13	T	T	T	T	T	T	T
			16	T	T	T	T	T	T	T
			20	3.5	T	T	T	T	T	T
			25	1.6	3.5	T	T	T	T	T
			32	--	--	T=10	T	T	T	T
			40	--	--	--	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS202CR

			Supply S. XT2								
			Version	S, H, V							
Load S.	Char	Icu [kA]	Release	TM							
DS202CR	B, C	10	In[A]	63A	80A	100A	125A	160A	63A	125A	160A
			10	6	6	T	T	T	T	T	T
			13	6	6	T	T	T	T	T	T
			16	6	6	T	T	T	T	T	T
			20	6	6	T	T	T	T	T	T
			25	1.2	6	T	T	T	T	T	T
			32	1.2	3	T	T	T	T	T	T
DS202CR M	B, C	10	40	--	3	T	T	T	T	T	T
			10	6	6	T	T	T	T	T	T
			13	6	6	T	T	T	T	T	T
			16	6	6	T	T	T	T	T	T
			20	6	6	T	T	T	T	T	T
			25	1.2	6	T	T	T	T	T	T
			32	1.2	3	T	T	T	T	T	T
			40	--	3	T	T	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS202CR

			Supply S.	XT3						
			Version	N,S						
			Release	TM						
Load S.	Char	Icu [kA]	In[A]	63	80	100	125	160	200	250
DS202CR	B, C	10	6	T	T	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T
			40		6 ¹	7,5	T	T	T	T
DS202CR M	B, C	10	6	T	T	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T
			40		6 ¹	7,5	T	T	T	T

¹ Value valid in case of Supply S. breaker only magnetic

RCDs technical details

Coordination tables: selectivity DS202CR

RCDs technical details

Coordination tables: selectivity DS202CR

			Supply S. S800												
			Version	S800B			S800C			S800N			S800S		
			Release	16			25			36			50		
Load S.	Char	Icu [kA]	In[A]	80A	100A	125A									
DS202CR	B	10	6A	1,2	1,7	3,0	1,2	1,7	3,0	1,2	1,7	3,0	1,2	1,7	3,0
			10A	0,9	1,2	1,6	0,9	1,2	1,6	0,9	1,2	1,6	0,9	1,2	1,6
			16A	0,9	1,1	1,5	0,9	1,1	1,5	0,9	1,1	1,5	0,9	1,1	1,5
			20A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
			25A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
			32A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
			40A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
DS202CR	M	10	6A	1,2	1,7	3,0	1,2	1,7	3,0	1,2	1,7	3,0	1,2	1,7	3,0
			10A	0,9	1,2	1,6	0,9	1,2	1,6	0,9	1,2	1,6	0,9	1,2	1,6
			16A	0,9	1,1	1,5	0,9	1,1	1,5	0,9	1,1	1,5	0,9	1,1	1,5
			20A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
			25A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
			32A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
			40A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
DS202CR	C	10	6A	1,0	1,8	3,0	1,0	1,8	3,0	1,0	1,8	3,0	1,0	1,8	3,0
			10A	0,9	1,2	1,6	0,9	1,2	1,6	0,9	1,2	1,6	0,9	1,2	1,6
			16A	0,9	1,1	1,5	0,9	1,1	1,5	0,9	1,1	1,5	0,9	1,1	1,5
			20A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
			25A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
			32A		1,0	1,3		1,0	1,3		1,0	1,3		1,0	1,3
			40A		1,0	1,3		1,0	1,3		1,0	1,3		1,0	1,3
DS202CR	M	10	6A	1,0	1,8	3,0	1,0	1,8	3,0	1,0	1,8	3,0	1,0	1,8	3,0
			10A	0,9	1,2	1,6	0,9	1,2	1,6	0,9	1,2	1,6	0,9	1,2	1,6
			16A	0,9	1,1	1,5	0,9	1,1	1,5	0,9	1,1	1,5	0,9	1,1	1,5
			20A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
			25A		1,1	1,5		1,1	1,5		1,1	1,5		1,1	1,5
			32A		1,0	1,3		1,0	1,3		1,0	1,3		1,0	1,3
			40A		1,0	1,3		1,0	1,3		1,0	1,3		1,0	1,3

RCDs technical details

Coordination tables: selectivity DS203NC

			Supply S. XT4													
			Version B,C,N,S,H,L,V													
Load S.	Char	Icu [kA]	Release	TM												
			In[A]	20	25	32	40	50	63	80	100	125	160	200	225	250
DS203NC L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T
			8	3	3	3	4,5	T	T	T	T	T	T	T	T	T
			10	3	3	3	4,5	T	T	T	T	T	T	T	T	T
			13			3	4,5	5	T	T	T	T	T	T	T	T
			16			3	4,5	5	T	T	T	T	T	T	T	T
			20			3	5	T	T	T	T	T	T	T	T	T
			25				5	T	T	T	T	T	T	T	T	T
			32					T	T	T	T	T	T	T	T	T
DS203NC	B, C, K	10	6	6	6	6	T	T	T	T	T	T	T	T	T	T
			8	3	3	3	4,5	7,5	8,5	8,5	T	T	T	T	T	T
			10	3	3	3	4,5	7,5	8,5	8,5	T	T	T	T	T	T
			13			3	4,5	5	7,5	7,5	T	T	T	T	T	T
			16			3	4,5	5	7,5	7,5	T	T	T	T	T	T
			20			3	5	6	6	T	T	T	T	T	T	T
			25				5	6	6	T	T	T	T	T	T	T
			32					6	6	7,5	T	T	T	T	T	T

			Supply S. XT2								XT4					
			Version B,C,N,S,H,L,V													
Load S.	Char	Icu [kA]	Release	EL												
			In[A]	25	63	100	160	40	63			100, 160		250		
DS203NC L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T
			8	T	T	T	T	T	T	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T	T	T	T	T	T	T
			13	T	T	T	T	T	T	T	T	T	T	T	T	T
			16	T	T	T	T	T	T	T	T	T	T	T	T	T
			20	T	T	T	T	T	T	T	T	T	T	T	T	T
			25	T	T	T	T			T	T	T	T	T	T	T
			32	T	T	T	T			T	T	T	T	T	T	T
DS203NC	B, C, K	10	6	T	T	T	T	T	T	T	T	T	T	T	T	T
			8	T	T	T	T	T	T	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T	T	T	T	T	T	T
			13	T	T	T	T	T	T	T	T	T	T	T	T	T
			16	T	T	T	T	T	T	T	T	T	T	T	T	T
			20	T	T	T	T	T	T	T	T	T	T	T	T	T
			25	T	T	T	T			T	T	T	T	T	T	T
			32	T	T	T	T			T	T	T	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS203NC

MCCB @ 415V -DS203NC @ 400V

			Supply S.	T1												
			Version	B,C,N												
			Release	TM												
			Iu[A]	160												
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160		
DS203NC L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T
			8		3	3	3	4,5	T	T	T	T	T	T	T	T
			10		3	3	3	4,5	T	T	T	T	T	T	T	T
			13			3	4,5	5	T	T	T	T	T	T	T	T
			16				3	4,5	5	T	T	T	T	T	T	T
			20					3	5	T	T	T	T	T	T	T
			25						5	T	T	T	T	T	T	T
			32							T	T	T	T	T	T	T
DS203NC	B,C,K	10	6	6	6	6	6	6	T	T	T	T	T	T	T	T
			8		3	3	3	4,5	7,5	8,5	T	T	T	T	T	T
			10		3	3	3	4,5	7,5	8,5	T	T	T	T	T	T
			13			3	4,5	5	7,5	T	T	T	T	T	T	T
			16				3	4,5	5	T	T	T	T	T	T	T
			20					3	5	T	T	T	T	T	T	T
			25						5	T	T	T	T	T	T	T
			32							6	7,5	T	T	T	T	T

			Supply S.	T2														
			Version	N,S,H,L														
			Release	TM														
			Iu[A]	160														
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160	25	63	100	160
DS203NC L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			8		3	3	3	3	4,5	T	T	T	T	T	T	T	T	T
			10		3	3	3	3	4,5	T	T	T	T	T	T	T	T	T
			13			3	3	4,5	5	T	T	T	T	T	T	T	T	T
			16				3	4,5	5	T	T	T	T	T	T	T	T	T
			20					3	5	T	T	T	T	T	T	T	T	T
			25						3	T	T	T	T	T	T	T	T	T
			32							T	T	T	T	T	T	T	T	T
DS203NC	B,C,K	10	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			8		3	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T
			10		3	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T
			13			3	3	4,5	5	7,5	T	T	T	T	T	T	T	T
			16				3	4,5	5	7,5	T	T	T	T	T	T	T	T
			20					3	5	T	T	T	T	T	T	T	T	T
			25						3	T	T	T	T	T	T	T	T	T
			32							6	7,5	T	T	T	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS203NC

			Supply S.	T3						
			Version	N,S						
			Release	TM, M						
			Iu[A]	250						
Load S.	Char	Icu [kA]	In[A]	63	80	100	125	160	200	250
DS203NC L	C	6	6	T	T	T	T	T	T	T
			8	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T
			13	5	T	T	T	T	T	T
			16	5	T	T	T	T	T	T
			20	5	T	T	T	T	T	T
			25	5	T	T	T	T	T	T
			32		T	T	T	T	T	T
DS203NC L	B,C,K	10	6	T	T	T	T	T	T	T
			8	7,5	8,5	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T

S800-DS203NC @ 400V

			Supply S.	S800N-S					
			Char	B					
				Icu [kA]	36-50				
Load S.				In[A]	50	63	80	100	125
DS203NC L	C	6	6		0.6	1.2	1.6	2.6	3.8
			8		0.5	1.1	1.4	2	3
			10		0.5	1.1	1.4	2	3
			13			0.8	1.2	1.7	2.5
			16			0.8	1.2	1.7	2.5
			20				1	1.5	2.1
			25					1.3	1.8
			32					1.1	1.7
DS203NC	B,C,K	10	6		0.6	1.2	1.6	2.6	3.8
			8		0.5	1.1	1.4	2	3
			10		0.5	1.1	1.4	2	3
			13			0.8	1.2	1.7	2.5
			16			0.8	1.2	1.7	2.5
			20				1	1.5	2.1
			25					1.3	1.8
			32					1.1	1.7

RCDs technical details

Coordination tables: selectivity DS203NC

Load S.	Char	Supply S.	S800N-S						
			C						
			Icu [kA]	36-50					
Load S.	Char	Supply S.	In[A]	40	50	63	80	100	125
DS203NC L	C	6	6	0.55	1.1	1.5	2.5	3.6	5.5
			8	0.45	1	1.3	1.9	2.8	4.2
			10	0.45	1	1.3	1.9	2.8	4.2
			13		0.75	1.1	1.6	2.3	3.6
			16		0.75	1.1	1.6	2.3	3.6
			20			0.9	1.4	1.9	3.3
			25				1.2	1.6	2.7
			32				1	1.5	2.5
DS203NC	B,C,K	6	6	0.55	1.1	1.5	2.5	3.6	5.5
			8	0.45	1	1.3	1.9	2.8	4.2
			10	0.45	1	1.3	1.9	2.8	4.2
			13		0.75	1.1	1.6	2.3	3.6
			16		0.75	1.1	1.6	2.3	3.6
			20			0.9	1.4	1.9	3.3
			25				1.2	1.6	2.7
			32				1	1.5	2.5

Load S.	Char	Supply S.	S800 N-S								
			D								
			Icu [kA]	36-50							
Load S.	Char	Supply S.	In[A]	25	32	40	50	63	80	100	125
DS203NC L	C	6	6	0.6	1.3	2	3.2	3.9	T	T	T
			8	0.5	1.2	1.65	2.6	3.1	T	T	T
			10	0.5	1.2	1.65	2.6	3.1	T	T	T
			13		0.9	1.4	1.8	2.6	5	T	T
			16		0.9	1.4	1.8	2.6	5	T	T
			20			1.3	1.6	2.2	4.2	5.4	T
			25				1.5	1.9	3.5	4.5	T
			32					1.8	2.8	4.2	5.5
DS203NC	B,C,K	10	6	0.6	1.3	2	3.2	3.9	8	T	T
			8	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13		0.9	1.4	1.8	2.6	5	6.3	8.8
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5

RCDs technical details

Coordination tables: selectivity DSE201

Fuses- DSE201 @ 230/240 V

			Supply side	Fuse 25gG	Fuse 40gG	Fuse 50gG	Fuse 63gG	Fuse 80gG	Fuse 100gG	Fuse 125gG	Fuse 160gG	Fuse 200gG
Load side	Char.	Icu [kA]	In [A]	25	40	50	63	80	100	125	160	200
DSE201	B,C	6	up to 20	1	side	3,5	T	T	T	T	T	T
			25-32		2	3	4,5	T	T	T	T	T

MCCB @ 415 V - DSE201 @ 230/240 V

			Supply side	T1							T2				
Load side	Char.	Icu [kA]	In [A]	50	63	80	100	125	160	50	63	80	100	125	160
DSE201	B,C	6	up to 20	3	5	T	T	T	T	3	5	T	T	T	T
			25-32		T	T	T	T	T		T	T	T	T	T

MCCB @ 415 V - DSE201 @ 230/240 V

			Supply side	T3							T4						
Load side	Char.	Icu [kA]	In [A]	63	80	100	125	160	200	250	63	80	100	125	160	200	250
DSE201	B,C	6	up to 20	5	T	T	T	T	T	T	5	T	T	T	T	T	T
			25-32		T	T	T	T	T	T		T	T	T	T	T	T

MCCB @ 415 V - DSE201 @ 230/240 V

			Supply side	XT1							XT2					
Load side	Char.	Icu [kA]	In [A]	50	63	80	100	125	160	50	63	80	100	125	160	
DSE201	B,C	6	up to 20	3	5	T	T	T	T	3	5	T	T	T	T	T
			25-32		T	T	T	T	T		T	T	T	T	T	T

MCCB @ 415 V - DSE201 @ 230/240 V

			Supply side	XT3							XT4						
Load side	Char.	Icu [kA]	In [A]	63	80	100	125	160	200	250	63	80	100	125	160	200	250
DSE201	B,C	6	up to 20	5	T	T	T	T	T	T	5	T	T	T	T	T	T
			25-32		T	T	T	T	T	T		T	T	T	T	T	T

RCDs technical details

Coordination tables: selectivity DSE201 M

Fuses/S750DR - DSE201M @ 230/240V

Load side	Char.	Icu [kA]	In [A]	Supply side								Fuse gG				
				16	20	25	35	50	63	80	100	E/K	25	35	50	63
DSE201M	B,C	15	6	0.2	0.5	0.8	1.7	3.1	7	10	10					
			10	0.2	0.4	0.7	1.4	2.3	3.4	4.8	7.5					
			16				1.3	2	2.9	4.2	6					
			20					1.9	2.7	3.8	5.6					
			25					1.9	2.6	3.6	5.4					
			32						2.4	3.2	4.2					
			40							3.2	4.2					
			10	50							3.5					

Fuses/S750DR - DSE201M @ 230/240V

Load side	Char.	Icu [kA]	In[A]	Supply side								S750DR				
				16	20	25	35	40	50	63	80	E/K	25	35	50	63
DSE201M	B,C	15	6	15	15	15	15	15	15	15	10					
			10	15	15	15	15	15	15	15	10					
			16			15	15	15	15	15	10					
			20				15	15	15	15	10					
			25					15	15	15	10					
			32						15	15	10					
			40							15	10					
			10	50							8					

MCCB @ 415 V - DSE201M @ 230/240 V

Load side	Char.	Icu [kA]	Icn [A]	Supply side								XT1				
				16	20	25	32	40	50	63	80	E/K	25	35	50	63
				6	3	3	3	5	6	6	10	T	T	T	T	
				10		3	3	3	4.5	7.5	7.5	T	T	T	T	
				16			3	4.5	5	7.5		12.5	T	T		
DSE201M	B,C	15	20				3	5	6	10	T	T				
			25					5	6	10	10	10	T	T		
			32					3	6	7.5	10	10	T	T		
			40						7.5	10	T	T				
			10	50							T	T				

RCDs technical details

Coordination tables: selectivity DSE201 M

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side								XT2				XT3							
			Version				N,S,H,L,V								N,S							
			Release				TM								TM							
			Iu [kA]				160								250							
			Icu [A]				36,50,70,120,150								36,50							
Load side	Char.	Icu [kA]	Icn [A]	12.5	63	80	100	125	160	63	80	100	125	160	200	250						
DSE201M	B,C	15	6	3	10	T	T	T	T	10	T	T	T	T	T	T	T	T				
			10		7.5	7.5	T	T	T	7.5	7.5	T	T	T	T	T	T	T				
			16		5	7.5	12.5	T	T	5	7.5	12.5	T	T	T	T	T	T				
			20		5	6	10	T	T	5	6	10	T	T	T	T	T	T				
			25		5	6	10	T	T	5	6	10	10	T	T	T	T	T				
			32		3	6	7.5	10	T	3	6	7.5	10	T	T	T	T	T				
			40			7.5	10	T			7.5	10	T	T	T	T	T	T				
			10		50			T	T			10	10	T	T	T	T	T				

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side								XT4							
			Version				N,S,H,L,V											
			Release				TM											
			Iu [kA]				250											
			Icu [A]				36,50,70,120,150											
Load side	Char.	Icu [kA]	Icn [A]	20	25	32	40	50	63	80	100	125	160	200	225	250		
DSE201M	B,C	15	6	6	6	6	7.5	10	T	T	T	T	T	T	T	T	T	T
			10	3	3	4.5	5	6.5	7.5	9	T	T	T	T	T	T	T	T
			16		3	4.5	5	6.5	5	8	T	T	T	T	T	T	T	T
			20			5	5	5	7.5	T	T	T	T	T	T	T	T	T
			25				5	5	7.5	T	T	T	T	T	T	T	T	T
			32					5	6	T	T	T	T	T	T	T	T	T
			40						5	T	T	T	T	T	T	T	T	T
			10		50					5	T	T	T	T	T	T	T	T

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side								XT2				XT4							
			Version				N,S,H,L,V								N,S,H,L,V							
			Release				EL								EL							
			Iu [kA]				160								250							
			Icu [A]				36,50,70,120,150								36,50,70,120,150							
Load side	Char.	Icu [kA]	Icn [A]	10	25	63	100	160	40	63	100	160	200	250								
DSE201M	B,C	15	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T				
			10		T	T	T	T	T	T	T	T	T	T	T	T	T	T				
			16			T	T	T	T	T	T	T	T	T	T	T	T	T				
			20			T	T	T	T	T	T	T	T	T	T	T	T	T				
			25			T	T	T			T	T	T	T	T	T	T	T				
			32			T	T	T			T	T	T	T	T	T	T	T				
			40				T	T				T	T	T	T	T	T	T				
			10	50			T	T				T	T	T	T	T	T	T				

RCDs technical details

Coordination tables: selectivity DSE201 M

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side		T2						T1-T2				T1-T2-T3				T3					
			Version		B,C,N,S,H,L										B,C,N,S,H,L,V									
			Release		TM																			
Load side	Char.	Icu [kA]	In [A]		12.5	16	20	25	32	40	50	63	80	100	125	160	200	250						
DSE201M	B,C	15	6	5.5 ¹	5.5	5.5	5.5	5.5	5.5	5.5	10.5	T	T	T	T	T	T	T	T					
			10		3 ¹	3	3	3	4.5	7.5	8.5	T	T	T	T	T	T	T	T					
			16			3 ¹	3	4.5	5	7.5	12	T	T	T	T	T	T	T	T					
			20			3 ¹		3	5	6	10	T	T	T	T	T	T	T	T					
			25				3 ¹	5	6	10	T	T	T	T	T	T	T	T	T					
			32				3 ¹		6	7.5	12	T	T	T	T	T	T	T	T					
			40						5.5 ¹	7.5	12	T	T	T	T	T	T	T	T					
			10	50						3 ¹	5 ²	7.5	10.5	T	T	T	T	T	T					

¹⁾ Value valid only for T2 magnetic only supply side circuit-breaker

²⁾ Value valid only for T2-T3 magnetic only supply side circuit-breaker

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side		T4						T5					
			Version		B,C,N,S,H,L,V											
			Release		TM											
Load side	Char.	Icu [kA]	In [A]	20	25	32	50	80	100	125	160	200	250	320-500		
DSE201M	B,C	15	6	7.5	7.5 ³	7.5	7.5	T	T	T	T	T	T	T		
			10	5	5 ³	5	6.5	9	T	T	T	T	T	T		
			16		3 ³	5	6.5	8	T	T	T	T	T	T		
			20				5	7.5	T	T	T	T	T	T		
			25				5	7.5	T	T	T	T	T	T		
			32				5 ³	7.5	T	T	T	T	T	T		
			40					6.5	T	T	T	T	T	T		
			10	50				5 ³	T	T	T	T	T	T		

³⁾ Value valid only for T4 magnetic only supply side circuit-breaker

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side		T2			T4		T5		
			Version		B,C,N,S,H,L,V							
			Release		EL							
Load side	Char.	Icu [kA]	In [A]	25	63	100	160	100,160	250,320	320-630		
DSE201M	B,C	15	6	T	T	T	T	T	T	T		
			10	T	T	T	T	T	T	T		
			16		T	T	T	T	T	T		
			20		T	T	T	T	T	T		
			25		T	T	T	T	T	T		
			32		T	T	T	T	T	T		
			40			T	T	T	T	T		
		10	50			10.5	10.5	T	T	T		

RCDs technical details

Coordination tables: selectivity DSE201 M

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 S						
				B						
				50						
Load side	Char.	Icu [kA]	In [A]	40	50	63	80	100	125	
DSE201M	B,C	15	6	0.4	0.5	0.7	1	1.5	2.6	
			10		0.4	0.6	0.7	1	1.4	
			16				0.7	0.9	1.3	
			20					0.9	1.3	
			25					0.9	1.3	
			32				0.8	1.1		
			40				0.8	1.1		
			10	50					1	

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 S							
				C							
				50							
Load side	Char.	Icu [kA]	In [A]	25	32	40	50	63	80	100	125
DSE201M	B,C	15	6	0.4	0.5	0.7	0.9	1.4	2.4	4.8	
			10	0.3	0.4	0.5	0.7	0.9	1.3	2	
			16	0.3	0.4	0.5	0.7	0.9	1.3	1.9	
			20		0.4	0.5	0.7	0.9	1.2	1.8	
			25		0.4	0.5	0.7	0.9	1.2	1.8	
			32		0.5	0.6	0.8	1	1.4		
			40			0.6	0.8	1	1.4		
			10	50			0.7	0.9	1.3		

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 S							
				D							
				50							
Load side	Char.	Icu [kA]	In [A]	25	32	40	50	63	80	100	125
DSE201M	B,C	15	6	0.5	1	1.2	2	2.8	T *	T	T
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
			16		0.6	0.8	1.1	1.4	2.5	3.3	5.6
			20		0.8	1.1	1.3	2.3	3	4.7	
			25		0.8	1.1	1.3	2.3	3	4.7	
			32			0.9	1.1	1.9	2.4	3.7	
			40				1.1	1.9	2.4	3.7	
			10	50				1.5	1.9	2.3	

* 9.9 for C char

RCDs technical details

Coordination tables: selectivity DSE201 M

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 N					
				B					
				36					
Load side	Char.	Icu [kA]	In [A]	40	50	63	80	100	125
DSE201M	B,C	15	6	0.4	0.5	0.7	1	1.5	2.6
			10		0.4	0.6	0.7	1	1.4
			16				0.7	0.9	1.3
			20					0.9	1.3
			25					0.9	1.3
			32				0.8	1.1	
			40				0.8	1.1	
			10	50					1

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 N							
				C							
				36							
Load side	Char.	Icu [kA]	In [A]	25	32	40	50	63	80	100	125
DSE201M	B,C	15	6	0.4	0.5	0.7	0.9	1.4	2.4	4.8	
			10	0.3	0.4	0.5	0.7	0.9	1.3	2	
			16	0.3	0.4	0.5	0.7	0.9	1.3	1.9	
			20		0.4	0.5	0.7	0.9	1.2	1.8	
			25		0.4	0.5	0.7	0.9	1.2	1.8	
			32			0.5	0.6	0.8	1	1.4	
			40				0.6	0.8	1	1.4	
			10	50				0.7	0.9	1.3	

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 N							
				D							
				36							
Load side	Char.	Icu [kA]	In [A]	25	32	40	50	63	80	100	125
DSE201M	B,C	15	6	0.5	1	1.2	2	2.8	T	T	T
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
			16		0.6	0.8	1.1	1.4	2.5	3.3	5.6
			20			0.8	1.1	1.3	2.3	3	4.7
			25			0.8	1.1	1.3	2.3	3	4.7
			32				0.9	1.1	1.9	2.4	3.7
			40					1.1	1.9	2.4	3.7
			10	50					1.5	1.9	2.3

RCDs technical details

Coordination tables: residual current protection selectivity

Selectivity

RCDs raise similar issue to those surrounding the installation of MCBs, and in particular the need to reduce to a minimum the parts of the system out of order in the event of a fault. For RCBOs the problem of selectivity in the case of short-circuit currents may be handled with the same specific criteria as for MCBs.


However, for correct residual current protection, the more important aspects are linked to tripping times. Protection against contact voltages is only effective if the maximum times indicated on the safety curve are not exceeded.

If an electrical system has user devices with earth leakage currents which exceed the normal values (e.g.: presence of capacitor input filters inserted between the device phase and earth cables) or if the system consists of many user devices, it is good practice to install various RCDs, on the main branches, with an upstream main residual current or non-residual current device instead of a single main RCD.

Horizontal selectivity

The non-residual current main circuit-breaker provides “horizontal selectivity”, preventing an earth fault at any point on the circuit or small leakage from causing unwanted main circuit-breaker tripping, which would put the entire system out of order.

However, in this way, section k of the circuit between the main circuit-breaker and the RCDs remains without “active” protection. Using a main RCD to protect it would lead to problems with “vertical selectivity”, which require tripping of the various devices to be co-ordinated, so that service continuity and system safety are not compromised. In this case, selectivity may be amperometric (partial) or chronometric (total).



Vertical selectivity

Vertical selectivity may also be established for residual current tripping, bearing in mind that in working back from system peripheral branches to the main electrical panels the risk of unskilled persons coming into contact with dangerous parts is significantly reduced.

RCDs technical details


Coordination tables: residual current protection selectivity

Amperometric (partial) selectivity

Selectivity may be created by placing low-sensitivity RCDs upstream and higher-sensitivity RCDs downstream. An essential condition which must be satisfied in order to achieve selective co-ordination is that the $I\Delta$ value of the breaker upstream (main breaker) is more than double the $I\Delta$ value of the breaker downstream. The operative rule to obtain an amperometric (partial) selectivity is $I\Delta n$ of the

upstream breaker = $3 \times I\Delta n$ of the downstream breaker (e. g.: F 204, A type, 300 mA upstream; F 202, A type, 100 mA downstream).

In this case, selectivity is partial and only the downstream breaker trips for earth fault currents $I\Delta 2 < I\Delta m < 0.5 \times I\Delta 1$.




Chronometric (total) selectivity

To achieve total selectivity, delayed or selective RCDs must be installed.

The tripping times of the two devices connected in series must be co-ordinated so that the total interruption time t_2 of the downstream breaker is less than the upstream breaker's no-response limit time t_1 , for any current value. In this way, the downstream breaker completes its opening before the upstream one.

To completely guarantee total selectivity, the $I\Delta$ value of the upstream device must also be more than double that of the downstream device in accordance with IEC 64-8/563.3, comments. The operative rule to obtain an chronometric (total) selectivity is $I\Delta n$ of the upstream breaker = $3 \times I\Delta n$ of the downstream breaker (e. g.: F 204, S type, 300 mA upstream; F 202, A type, 100 mA downstream). For safety reasons, the delayed tripping times of the upstream breaker must always be below the safety curve.



Legend

- 1 Theoretical safety curve
- 2 RCD A tripping characteristic
- 3 No-response limit times
- 4 RCD B tripping characteristic

RCDs technical details

Coordination tables: residual current protection selectivity

Table of RCD selectivity

Upstream I _{Δn} [mA]	10	30	100	300	300	500	500	1000	1000
Downstream I _{Δn} [mA]	inst	inst	inst	inst	S	inst	S	inst	S
10	inst		▲	▲	▲	■	▲	■	▲
30	inst		▲	▲	■	▲	■	▲	■
100	inst		▲	■	▲	■	▲	■	
300	inst							▲	■
300	S							▲	▲
500	inst								
500	S								
1000	inst								
1000	S								

inst = instantaneous S = selective ▲ = amperometric (partial) selectivity ■ = chronometric (total) selectivity

Back-up F-ATI Test and F-ARI Test

The values has to be delivered from the LAb

2P	Rated current [A]	25	40	63	80	100
Single phase circuit with neutral 230-240 V	Fuse gG 25A	kA	10			
	Fuse gG 40A		10	10		
	Fuse gG 63A		10	10	10	
	Fuse gG 100A		10	10	10	
	S800 S		6	9	10	
	S800 N		6	9	10	
	S200		7	7	5	
	S200 M		7	7	5	
	S200 P		7	7	5	
	S300 P		7	7	5	

4P	Rated current [A]	25	40	63	80	100
Three phase circuit with neutral 400-415 V	Fuse gG 25A		10			
	Fuse gG 40A		10	10		
	Fuse gG 63A		10	10	10	
	Fuse gG 100A		10	10	10	10
	S800 S		10	10	10	10
	S800 N		10	10	10	10
	S200		10	10	10	10
	S200 M		10	10	10	10
	S200 P		10	10	10	10
	S300 P		10	10	10	10

RCDs technical details

Coordination tables: residual current protection selectivity

Back-up F-ATI Test 2 & 4 pole with Selective SMCB S750

Upstream technology		MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB
RCD System pro M compact	F-ATI 2 Test	Product Range		SMCB	SMCB	SMCB	SMCB	SMCB	SMCB	SMCB
		Series		S750	S750	S750	S750	S750DR	S750DR	S750DR
		Characteristics		E,K	E,K	E,K	E,K	E,K	E,K	E,K
		Icu	25	25	25	25	25	25	25	25
			In	25	35	40	50	63	35	40
		A	10	25	20				20	
		A	10	40	20	20			20	20
		A	10	63	20	20	20	20	20	20
		A	10	25	20			20		
		A	10	40	20	20		20	20	20
		A	10	63	20	20	20	20	20	20

Upstream technology		MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB
RCD System pro M compact	F-ATI 4 Test	Product Range		SMCB	SMCB	SMCB	SMCB	SMCB	SMCB	SMCB
		Series		S750	S750	S750	S750	S750DR	S750DR	S750DR
		Characteristics		E,K	E,K	E,K	E,K	E,K	E,K	E,K
		Icu	25	25	25	25	25	25	25	25
			In	25	35	40	50	63	35	40
		A	10	25	20			20		
		A	10	40	20	20		20	20	
		A	10	63	20	20	20	20	20	20
		A	10	25	20			20		
		A	10	40	20	20		20	20	
		A	10	63	20	20	20	20	20	20

RCDs technical details

Coordination tables: residual current protection selectivity

Back-up F-ATI Test 2 & 4 pole with MCB S800S, S800N

Upstream technology		MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB
RCD	System pro M compact	Product Range		S800	S800	S800	S800	S800	S800	S800
		Series		S800S	S800S	S800S	S800S	S800S	S800N	S800N
		Characteristics		B,C,D,K	B,C,D,K	B,C,D,K	B,C,D,K	B,C,D,K	B,C,D	B,C,D
		Icu	50	50	50	50	50	36	36	36
			In	25	32	40	50	25	32	40
		A	10	25	20			15		
		A	10	40	20	20		15	15	15
		A	10	63	20	20	20	15	15	15
		A	10	25	20			15		
		A	10	40	20	20		15	15	15
		A	10	63	20	20	20	15	15	15

Upstream technology		MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB
RCD	System pro M compact	Product Range		S800	S800	S800	S800	S800	S800	S800
		Series		S800S	S800S	S800S	S800S	S800S	S800N	S800N
		Characteristics		B,C,D,K	B,C,D,K	B,C,D,K	B,C,D,K	B,C,D,K	B,C,D	B,C,D
		Icu	50	50	50	50	50	36	36	36
			In	25	32	40	50	63	25	32
		A	10	25	20			15		
		A	10	40	20	20		15	15	15
		A	10	63	20	20	20	20	15	15
		A	10	25	20			15		
		A	10	40	20	20		15	15	15
		A	10	63	20	20	20	15	15	15

RCDs technical details

Coordination tables: residual current protection selectivity

Back-up F-ATI Test 2 & 4 pole with MCB S800S+S802S-SCL-SR

Upstream technology		MCB	MCB	MCB	MCB	MCB			
RCD	System pro M compact	Product Range		S800	S800	S800	S800	S800	
		Series		S800S+S802S-SCL-SR	S800S+S802S-SCL-SR	S800S+S802S-SCL-SR	S800S+S802S-SCL-SR	S800S+S802S-SCL-SR	
		Characteristics		B,C,D,K	B,C,D,K	B,C,D,K	B,C,D,K	B,C,D,K	
		Icu		100	100	100	100	100	
			In	25	32	40	50	63	
		A	10	25	50				
		A	10	40	50	50			
		A	10	63	50	50	50	50	
		A	10	25	50				
		A	10	40	50	50			
		A	10	63	50	50	50	50	

Upstream technology		MCB	MCB	MCB	MCB	MCB			
RCD	System pro M compact	Product Range		S800	S800	S800	S800	S800	
		Series		S800S+S803S-SCL-SR	S800S+S803S-SCL-SR	S800S+S803S-SCL-SR	S800S+S803S-SCL-SR	S800S+S803S-SCL-SR	
		Characteristics		B,C,D,K	B,C,D,K	B,C,D,K	B,C,D,K	B,C,D,K	
		Icu		50	50	50	50	50	
			In	25	32	40	50	63	
		A	10	25	50				
		A	10	40	50	50			
		A	10	63	50	50	50	50	
		A	10	25	50				
		A	10	40	50	50			
		A	10	63	50	50	50	50	

RCDs technical details

Power loss, derating and performance in altitude

Power loss and internal resistance of RCDs and RCBOs

RCCBs F200 series

Rated current	Power loss per pole W	
In [A]	[W]	
	2P	4P
16	1.5	-
25	1.0	1.3
40	2.4	3.2
63	3.2	4.4
80	4.5	5.3
100	6.5	8.2
125	-	7.5

RCCBs F200 Type B

Power Loss [W]	In [A]	Per Pole	Total
F202 B	16	0.26	0.82
	25	0.65	1.6
	40	1.65	3.6
	63	4.14	8.58
F204 B	25	0.74	3.42
	40	1.92	6.96 (9.26)*
	63	4.8	15.6 (17.9)*
	80	5	17.2
	125	11.2	35.8

* 500 mA

RCD-Blocks DDA200 series

Rated current	Power loss Wlb* ①	
Ib [A]	[W]	
	2P	3P,4P
25	2.0	3.0
40	3.2	4.8
63	5.0	7.6

* The power loss Wlb shown in the table refers to Ib. For use with circuit-breakers with lower rated current In the power loss W must be determined using the formula: W = (I / Ib) • Wlb

RCBOs DS 200, DS 200 M series

Rated current	Power loss W ①				
In [A]	[W]	Characteristic B-C	Characteristic K		
		2P	3P/4P	2P	3P/4P
6	4.1	6.2		3.9	5.9
10	2.9	4.4		2.9	4.2
13	5.2	7.7		3.1	4.5
16	4.5	6.6		4.9	7.2
20	6.4	9.3		6.8	9.9
25	8.5	12.4		7.9	11.5
32	10.9	15.7		10.7	15.4
40	15	21.6		14.4	20.7
50	11.4	18.4		10.7	17.4
63	17.4	28.2		18.2	29.4

① data available in the tables are referred to the Power Loss per device

RCD-Blocks DDA800

Rated current	Power loss Wlb* ①	
In [A]	[W]	
	2P	3P, 4P
63	9	13.5
100	7	10.5
125	-	16.6

* The power loss Wlb shown in the table refers to Ib. For use with circuit-breakers with lower rated current In the power loss W must be determined using the formula: W = (I / Ib) • Wlb

RCBOs DS201

DS201		
Rated current	Power loss ①	Internal resistance
In [A]	[W]	[mΩ]
1	1.4	1400.0
2	1.6	400.0
4	2.2	137.5
6	2.4	66.7
8	1.9	29.7
10	1.8	18.0
13	2.5	15.0
16	3.3	12.8
20	3.6	9.0
25	5.5	8.8
32	6.4	6.3
40	5.0	3.1

RCBOs DS202CR series

In	Power loss [W] ①	Internal resistance [mΩ]
6	3,0	84,4
10	3,3	32,8
13	3,8	22,5
15	3,9	16,4
16	4,2	16,4
20	5,0	12,6
25	6,2	9,9
32	7,6	7,4
40	8,9	5,6

RCBOs DS203NC series

In	Power loss [W] ①	Internal resistance [mΩ]
6A	7.5	207.3
8A	4.2	66.4
10A	5.6	55.9
13A	7.2	42.5
16A	10.0	39.3
20A	11.8	29.5
25A	10.3	16.4
32A	15.1	14.8

DS800 and DS800 N series ①

Rated current	Rated current		
in [A]	2P	3P	4P
125	25.7	45.7	55.1

RCDs technical details

Power loss, derating and performance in altitude

RCBO DS301C - Voltage Drop, power loss, internal resistance, own consumption

Characteristic B

In (A)	Voltage drop (V)	Powerloss (W)			Internal Resistance (mΩ)
		Average per pole	Phase pole	Neutral pole	
6 A	0.4	1.10	2.1	0.1	2.2
10 A	0.3	1.30	2.35	0.25	2.6
13 A	0.2	1.24	2.12	0.35	2.47
16 A	0.0	1.42	2.11	0.72	2.83
20 A	0.2	1.83	2.88	0.78	3.66

Characteristic C

6 A	0.3	0.78	1.47	0.09	1.56	43.3
10 A	0.2	0.75	1.25	0.25	1.5	15.0
13 A	0.2	1.13	1.95	0.3	2.25	13.3
16 A	0.2	1.24	1.84	0.65	2.48	9.7
20 A	0.2	1.70	2.6	0.8	3.4	8.5

RCBO DSE201 series

In [A]	Voltage drop [V]	Power loss [W]	Internal resistance [mΩ]
6	0.42	2.5	70
10	0.25	2.5	25
16	0.24	3.8	15
20	0.27	5.5	14
25	0.15	3.8	6.1
32	0.16	5.2	5
40	0.14	5.5	3.4
50	0.11	5.3	2.1

RCBO DSE201 M series

In [A]	Voltage drop [V]	Power loss [W]	Internal resistance [mΩ]
6	0.30	1.8	49
10	0.18	1.8	18
16	0.15	2.4	9.5
20	0.15	3.0	7.6
25	0.13	3.3	5.3
32	0.14	4.4	4.3
40	0.14	5.5	3.4
50	0.11	5.3	2.1

Derating of load capability of RCBOs DS 200 series, DS201, DS202CR, DS203NC, DSE201 and DSE201 M

For DS 200 see tables for S 200 MCBs in technical details MCBs and dedicated tables for DS201 and DS202CR, within the range of temperatures from -25 °C to +55 °C.

Performance in altitude of RCDs

ABB RCDs are able to operate at altitude higher than foreseen by the relevant standard IEC/ EN 61008 and IEC/ EN 61009 taking into account the corrective factor below detailed:

Elevation [m]	2000	3000	4000	5000	6000
Rated Current [A]	1.0 x In	0.96 x In	0.94 x In	0.92 x In	0.90 x In
Rated Voltage [V]	1.0 x Un	0.877 x Un	0.775 x Un	0.676 x Un	0.588 x Un

For altitude higher than 3.000 m the isolating characteristic is no longer available.

For DDA800 RCD Blocks according to IEC/EN 60947-2, up to 2000 meters above sea level, the rated characteristics remain unchanged.

With increasing altitude, the properties of the atmosphere change regarding composition, dielectricity, the cooling capacity and the pressure.

The characteristics of the DDA800 RCD Blocks therefore change: this can be measured for the most part using the change in significant parameters such as the maximum rated operational voltage and the rated current:

Elevation [m]	2000	3000	4000	5000
Rated operational voltage Ue [V]	690	600	540	470
Max rated current In [A]	1x In	0.96 x In	0.93 x In	0.9 x In

RCDs technical details

Power loss, derating and performance in altitude

Derating in temperature for DS301C series

Max operating current depending on the ambient temperature (daily average $\leq 35^{\circ}\text{C}$) of characteristics type B and C.

In	Temperature ($^{\circ}\text{C}$)											
	-25	-20	-10	0	10	20	30	40	50	55	60	70
6 A	8.3	7.8	7.3	7.0	6.7	6.3	6.0	6.0	5.9	5.8	5.7	5.7
10 A	13.8	13.5	12.7	12.1	11.0	10.4	10.0	9.5	9.2	9.0	8.9	8.8
13 A	17.8	17.1	16.5	15.8	14.8	13.9	13.0	12.4	12.2	12.0	11.9	11.8
16 A	20.6	19.9	19.0	18.4	17.7	16.6	16.0	15.4	15.0	14.8	14.6	14.5
20 A	25.8	24.8	23.5	22.9	21.9	20.8	20.0	19.4	18.7	18.2	18.0	17.9

Derating in temperature for DS203NC series

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type B, C, K. Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

B, C	Temperature ($^{\circ}\text{C}$)									
In	-25	-20	-10	0	10	20	30	40	55	70
6A	7.29	7.16	6.91	6.65	6.41	6.17	6.00	5.90	5.75	
8A	9.71	9.54	9.20	8.85	8.55	8.24	8.00	7.83	7.57	
10A	12.13	11.92	11.49	11.06	10.68	10.31	10.00	9.76	9.39	
13A	15.77	15.49	14.93	14.37	13.89	13.41	13.00	12.65	12.12	
16A	19.40	19.06	18.37	17.68	17.10	16.52	16.00	15.54	14.5	13.8
20A	23.66	23.32	22.63	21.94	21.26	20.57	20.00	19.53	18.84	
25A	29.00	28.65	27.96	27.27	26.46	25.65	25.00	24.53	23.83	
32A	38.67	38.13	37.04	35.96	34.48	33.00	32.00	31.47	29	27

K

K	Temperature ($^{\circ}\text{C}$)									
In	-25	-20	-10	0	10	20	30	40	55	70
6A	7.2	6.9	6.6	6.4	6.2	6.0	5.8	5.7	5.6	
8A	9.5	9.2	8.9	8.5	8.2	8.0	7.8	7.6	7.4	
10A	11.9	11.5	11.1	10.7	10.3	10.0	9.7	9.5	9.1	
13A	15.5	14.9	14.4	13.9	13.4	13.0	12.6	12.3	11.7	
16A	19.2	18.4	17.7	17.1	16.5	16.0	15.5	15.1	14.5	13.8
20A	23.3	22.6	21.9	21.3	20.6	20.0	19.4	19.0	18.3	
25A	28.8	28.1	27.3	26.5	25.6	25.0	24.4	23.9	23.2	
32A	38.4	37.2	35.8	34.5	33.0	32.0	31.0	30.5	29	27

Derating in temperature for DS201 series

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type B, C. Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

In	Temperature (A) ($^{\circ}\text{C}$)	-25	-20	-10	0	10	20	30	40	50	55	60	65	70
2A	3.9	3.6	3.2	2.9	2.7	2.4	2.0	1.8	1.7	1.6	1.5	1.4	1.3	
4A	6.1	5.8	5.4	5.0	4.7	4.4	4.0	3.6	3.4	3.2	3.1	3.0	2.8	
6A	8.7	8.4	7.7	7.3	7.0	6.4	6.0	5.5	5.3	5.1	4.9	4.7	4.6	
8A	10.8	10.3	9.5	9.0	8.7	8.3	8.0	7.4	7.1	7.0	6.8	6.6	6.5	
10A	13.5	13.0	12.1	11.5	11.0	10.6	10.0	9.4	9.0	8.8	8.6	8.4	8.3	
13A	16.0	15.6	14.9	14.5	14.0	13.4	13.0	12.4	11.7	11.4	11.2	11.0	10.8	
16A	18.9	18.6	18.1	17.5	17.0	16.4	16.0	15.3	14.8	14.5	14.3	14.1	14.0	
20A	24.0	23.5	22.7	22.0	21.4	20.7	20.0	19.1	18.5	18.3	18.0	17.8	17.7	
25A	27.9	27.5	27.1	26.6	26.0	25.3	25.0	24.3	23.6	23.4	23.2	23.0	22.8	
32A	36.8	36.2	35.4	34.8	34.0	32.9	32.0	31.3	30.5	30.0	29.7	29.5	29.4	
40A	44.8	44.6	44.0	43.2	42.1	41.0	40.0	39.0	38.1	37.9	37.6	37.4	37.2	

RCDs technical details

Power loss, derating and performance in altitude

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type K.
Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

In (A)	Temperature (°C)												
	-25	-20	-10	0	10	20	30	40	50	55	60	65	70
1A	2.2	2.2	1.7	1.5	1.3	1.0	0.7	0.6	0.6	0.5	0.5	0.4	0.4
2A	3.5	3.2	2.8	2.8	2.4	2.0	1.8	1.8	1.7	1.6	1.5	1.5	1.4
4A	5.7	5.3	4.9	4.8	4.4	4.0	3.6	3.4	3.3	3.0	2.9	2.8	2.8
6A	8.0	7.7	7.4	7.0	6.5	6.0	5.4	5.3	5.2	4.8	4.7	4.6	4.5
8A	10.0	9.5	9.0	8.7	8.2	8.0	7.4	7.1	7.0	6.7	6.6	6.5	6.4
10A	12.6	12.1	11.5	11.0	10.5	10.0	9.4	9.1	8.9	8.8	8.6	8.4	8.3
13A	15.4	14.9	14.4	14.1	13.4	13.0	12.5	11.8	11.4	11.2	11.0	10.8	10.7
16A	18.7	18.2	17.5	17.0	16.4	16.0	15.4	14.7	14.6	14.3	14.2	14.0	13.9
20A	23.1	22.7	22.1	21.3	20.7	20.0	19.1	18.5	18.2	18.1	17.9	17.8	17.7
25A	27.4	27.1	26.5	26.0	25.4	25.0	24.3	23.6	23.4	23.2	23.0	22.8	22.6
32A	36.1	35.4	34.9	34.0	32.8	32.0	31.2	30.5	29.9	29.7	29.5	29.4	29.3
40A	44.4	43.9	43.2	42.1	40.9	40.0	39.0	38.2	37.7	37.4	37.2	37.0	36.8

Derating in temperature for DS202CR series

Max. operating current depending on the ambient temperature of a circuit-breaker in load circuit of characteristics type B and C.
Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

B, C	Temperature (°C)							
In (A)	0	10	20	25	30	40	50	60
6	7,2	6,8	6,4	6,2	6,0	5,5	5,1	4,5
10	12,2	11,5	10,8	10,4	10,0	9,1	8,2	7,1
13	15,7	14,8	13,9	13,5	13,0	12,0	10,9	9,6
16	19,1	18,2	17,1	16,6	16,0	14,8	13,4	11,9
20	24,0	22,8	21,4	20,7	20,0	18,4	16,6	14,5
25	30,2	28,6	26,9	26,0	25,0	22,9	20,6	18,0
32	37,6	35,9	34,0	33,0	32,0	29,9	27,5	25,0
40	46,5	44,4	42,3	41,2	40,0	37,5	34,9	31,9

RCDs technical details

Power loss, derating and performance in altitude

Derating in temperature for DSE201 series

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type B. C.
Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

	Temperature ($^{\circ}\text{C}$)									
In	-25	-20	-10	0	10	20	30	40	50	55
6 A	8.1	8.0	7.8	7.4	6.9	6.5	6.0	5.9	5.8	5.7
10 A	13.8	13.5	13.0	12.3	11.6	10.8	10.0	9.9	9.7	9.7
16 A	19.7	19.5	19.1	18.5	17.6	16.6	16.0	15.8	15.5	15.4
20 A	23.7	23.5	23.2	22.7	21.6	20.5	20.0	19.7	19.4	19.2
25 A	30.2	29.2	29.2	28.4	27.0	25.7	25.0	24.6	24.1	23.9
32 A	39.4	37.7	37.7	36.4	34.7	33.0	32.0	31.4	30.7	30.4
40 A	50.3	47.9	47.9	45.6	43.6	41.5	40.0	39.0	38.4	38.1
50 A	61.1	59.2	59.2	57.1	54.4	51.7	50.0	48.8	48.0	47.9

Derating in temperature for DSE201 M series

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type B, C.
Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

	Temperature ($^{\circ}\text{C}$)									
In	-25	-20	-10	0	10	20	30	40	50	55
6 A	7.3	7.2	6.9	6.7	6.4	6.2	6.0	5.9	5.9	5.8
10 A	13.0	12.9	12.2	11.4	10.9	10.4	10.0	9.8	9.7	9.5
16 A	20.2	19.7	18.7	17.8	17.3	16.6	16.0	15.8	15.4	15.2
20 A	26.0	19.7	24.0	22.8	21.9	20.7	20.0	19.8	19.6	19.5
25 A	32.6	25.2	30.4	29.0	27.5	26.0	25.0	24.6	24.2	23.9
32 A	41.1	31.5	38.0	36.3	34.8	33.1	32.0	30.9	29.8	29.6
40 A	50.3	49.4	47.9	45.6	43.7	41.5	40.0	39.0	38.4	38.1
50 A	61.1	60.4	59.2	57.1	54.4	51.7	50.0	48.8	48.0	47.9

Derating in temperature for F200 B series

Max operating current depending on the ambient temperature of the residual current circuit breaker.

	Temperature ($^{\circ}\text{C}$)				
In	-25...50	55	60	65	70
16 A	16	16	16	16	16
25 A	25	25	25	25	25
40 A	40	40	40	40	32
63 A	63	55	48	40	32

RCDs technical details

Tripping characteristic

Tripping characteristics valid for all the RCBOs

Acc. to	Tripping characteristic and rated current	Thermal release ②		Tripping time	Electromagnetic release ①		Tripping time
		conventional non-tripping current	conventional tripping current		Currents:	hold current surges	
IEC/EN 60898-1	B	6 to 40 A	1.13 · I_n	> 1 h	3 · I_n	> 0.1 s	
			1.45 · I_n	< 1 h	5 · I_n	< 0.1 s	
IEC/EN 60947-2	C	2 to 40 A	1.13 · I_n	> 1 h	5 · I_n	> 0.1 s	
			1.45 · I_n	< 1 h	10 · I_n	< 0.1 s	
IEC/EN 60947-2	K	1 to 40 A	1.05 · I_n	> 1 h	10 · I_n	> 0.2 s	
			1.2 · I_n	< 1 h ③	14 · I_n	< 0.2 s	
			1.5 · I_n	< 2 min. ③			
			6.0 · I_n	> 2 s (T1)			

① The indicated electromagnetic tripping values apply to a frequency range of 16 2/3 ... 60 Hz. For different network frequencies or direct current the values change according to the multiplier in the table below.


② The thermal releases are calibrated to a nominal reference ambient temperature; for Z and K, the value is 20 °C, for B and C = 30 °C.

In the case of higher ambient temperatures, the current values fall by ca. 6 % for each 10 K temperature rise.

③ As from operating temperature (after $I_1 > 1$ h or, as applicable, 2 h).


Characteristic B

IEC/EN 61009-1




Characteristic C

IEC/EN 61009-1



Characteristic K

IEC-EN60947-2



④ thermal trip

⑤ electromagnetic trip

RCDs technical details

Emergency stop using DDA 200 AE series



RCD-blocks type AE

Emergency stop using DDA 200 AE series RCD-blocks

The AE series RCD-block combines the protection supplied by the RCBOs with a positive safety emergency stop function for remote tripping.

In the AE version, the DDA 200 AE series RCD-blocks are available.

Operating principle (patented)

Two additional primary circuits powered with the same voltage and equipped with the same resistance have been added to the transformer; under normal conditions the same current would flow through, but since they are wound by the same number of coils in opposite directions they cancel each other out and do not produce any flow.

One of these two windings acts as the remote control circuit: the emergency stop is obtained by interrupting the current flow in this circuit.

The positive safety is therefore obvious: an accidental breakage in the circuit is equivalent to operating an emergency control button.

Advantages


Compared with the devices which are normally used in emergency circuits, DDA 200 AE blocks have the following advantages:

- positive safety
- no unwanted tripping if there is a temporary reduction or interruption of the mains voltage
- efficient immediate operation even after long off-service periods of the installation

Use

Application of the DDA 200 AE blocks complies with the requirements of IEC 60364-8. They are therefore suitable, for example, for escalators, lifts, hoists, electrically operated gates, machine tools, car washes and conveyor belts.

No more than one DDA 200 AE can be controlled using the same control circuit. Each DDA 200 AE requires a dedicated control circuit.



RCDs technical details

Unwanted tripping - AP-R solution (high immunity)

Unwanted tripping

In the event of disturbance in the mains, the RCDs normally present in the system are tripped, breaking the circuit even in the absence of a true earth fault.

Disturbances of this kind are most often caused by:

- operation overvoltages caused by inserting or removing loads (opening or closing protection of control devices, starting and stopping motors, switching fluorescent lighting systems on and off, etc.)
- overvoltages of atmospheric origin, caused by direct or indirect discharges on the electrical line.

Under these circumstances, breaker tripping is unwanted, since it does not satisfy the need to avoid the risks due to direct and indirect contacts. On the contrary, the sudden and unjustified interruption of the power supply may result in very serious problems.

AP-R RCDs

The ABB range of AP-R anti-disturbance residual current circuit-breakers and blocks was designed to overcome the problem of unwanted tripping due to overvoltages of atmospheric or operation origin.

The electronic circuit in these devices can distinguish between temporary leakage caused by disturbances on the mains and permanent leakage due to actual faults, only breaking the circuit in the latter case.

AP-R residual current circuit-breakers and blocks have a slight delay into the tripping time, but this does not compromise the safety limits set by the Standards in force (release time at $2 I_{\Delta n}=150$ ms).

Guaranteeing conventional residual current protection, their installation in the electrical circuit therefore allows any unwanted tripping to be avoided in domestic and industrial systems in which service continuity is essential.


This delay makes the AP-R residual current devices especially suited for installations involving motor starters/variable speed drives, fluorescent lamps or IT/electronic equipment.

The use of multiple electronic reactors for the supply of fluorescent lamps instead generates permanent leakage currents and inrush currents that can cause nuisance tripping of a standard residual current circuit breaker. IT system loads and other electronic equipment (e.g. dimmers, computers, inverters) with capacitive input filters connected between the phases and ground can also generate permanent earth leakage currents whose sum may provoke the nuisance tripping of a standard residual current circuit breaker. For these situations, the AP-R breakers allow a greater number of devices to be connected to the installation.

Frequency converters include a rectifier section and an inverter section.


In case of fault within a single-phase frequency converter AP-R type RCDs provide complete protection, because an earth fault occurring downstream the inverter, produces an earth fault current with multi-frequency shape with high amount of harmonics.

While, in case of fault within a three-phase frequency converter, B type RCDs ensure complete protection because in case of insulation fault between the rectifier and the inverter or downstream the inverter we can have a smooth DC earth fault current.



RCDs technical details

Unwanted tripping - AP-R solution (high immunity)



Compared with standard type breakers, AP-R residual current breakers are therefore characterised, for any given sensibility, by:

- Higher residual trip current
- Tripping time delay
- Better resistance to overvoltages, harmonics and impulse disturbances.

Regulations

The tests set out in the IEC 61008 and IEC 61009 standards verify the resistance of residual current breakers to unwanted tripping provoked by operation overvoltages, using a ring wave impulse shape of 0.5 µs/100 kHz. All

residual current circuit-breakers are required to pass this test with a peak current value of 200 A.

For what concerns atmospheric overvoltages, the IEC 61008 and 61009 standards prescribe the 8/20 µs surge test with a 3000 A peak current, but limit the requirement to residual current devices classified as selective; no test is required for other types.

The ABB range of AP-R anti-nuisance tripping breakers and blocks pass the general 0.5 µs/100 kHz ring wave test and also withstand the 8/20 µs impulse test with the same peak current of 3000 A prescribed for selective devices.

	A or AC	AP-R	B	Selective
Resistance to unwanted tripping caused by network disturbances with wave shape (0.5 µs/100 kHz)	250	250	200	250
Resistance to nuisance tripping due to overvoltages (operational or atmospheric) peak (8/20 wave)	N.A.	3000	3000	5000

RCDs technical details


Unwanted tripping - F2C-ARH solution

The F2C-ARH is an auto-reclosing device particularly suited for household and similar uses. It doesn't require a separate low voltage power supply, and can be supplied by the associated RCCBs (2 pole RCCBs up to 63 A – 30 mA) at the 230 V a.c. rated voltage.

Another feature that makes the product ideal for home applications is an internal control unit that checks there are


no insulation faults in the system before allowing the RCCB to reclose.

This ensures that reclosing occurs only in case of unwanted tripping of the RCCB (i.e. overvoltages induced by electrical storms), thus assuring continuity of power supply also in these situations.



Situation of temporary over-voltage, for example caused by a lightning, that causes RCCB's untimely tripping.

When the RCCB operates in presence of an effective insulation fault, the auto-reclosing device doesn't allow its reclosing and guarantees the system insulation.



Situation of permanent earth fault that causes RCCB's tripping.

RCDs technical details

Type B RCDs

Type B RCDs

In industrial electrical applications it is more and more common to use devices where in the event of an earth fault current unidirectional direct currents or currents with a minimum residual ripple which flow through the PE conductor can emerge. These devices can be for example inverters, medical equipment (e.g. x-ray equipment and CAT), or UPS.

Type A RCDs sensitive to pulsating currents (in addition to sinusoidal currents detected by RCDs of type AC as well) cannot detect and break these earth fault direct currents or currents with a minimum level residual ripple. In case there are electrical appliances which generate this type of currents in the event of an earth fault the use of RCDs of type AC or type A would not be appropriate.

In addition to Type A RCDs, Type F RCDs with an intermediate characteristics are also tested according to IEC/EN 62423 which foresees the application of a simulated multi-frequency residual current with appropriate coefficient associated to the each level of frequency up to 1kHz. A single phase frequency converter, also named as inverter, is a commonly used electric drive which regulates the speed of an electric motor, operating on supply voltage and frequency.

During normal operation, the current generated by a single phase inverter in the downstream section is the result of the overlapping of mixed frequency components which varies from 10Hz (motor frequency), to 50Hz (rated frequency) and 1000Hz (switching frequency).

RCDs type F have been specifically designed for single phase inverters applications in order to meet the requirement to assure adequate protection level in case of an earth fault with such harmonic content, offering at the same time an increased resistance to nuisance tripping.

On the other side only RCD type B remain the only devices which are suitable to detect smooth DC components in the residual current caused by insulation faults in the DC section of a three phase frequency converter

Standard IEC 62423 specifies requirements and tests for type B RCDs (RCCBs and/or RCBOs) for household and similar uses. Requirements and tests given in this standard are in addition to the requirements of type A given in IEC 61008 (for RCCBs) or IEC 61009 (for RCBOs, including RCD-blocks). This means that RCDs of type B have to be compliant also to all the requirements of residual current devices of type A.

As already said, type B RCDs are not only sensitive to alternating and pulsating earth fault currents with DC components at a frequency of 50/60 Hz (type A), but they are also sensitive to:

- alternating currents up to a frequency of 1000 Hz;
- alternating and/or pulsating currents with DC components overlapping with a direct current;
- earth fault currents generated by a rectifier with two or more phases;
- direct earth fault currents without residual ripple

Type B RCDs must be marked with the following symbols highlighting the switches' capacity to detect every type of current:   .


RCDs technical details

Type B RCDs

Construction features

Type B RCDs consist of one section for the detection of alternating earth fault currents and unidirectional pulsating earth fault currents, which functions independently of the line voltage. For the detection of direct earth fault currents or currents with a minimum residual ripple, type B RCDs have a second electronic section, the functioning of which depends on the line voltage.

The structure of the product is illustrated in the following diagram.



S Release

M Protection device mechanism

E Electronics for the intervention with direct unidirectional earth fault currents

T Test device

Tr1 Residual current transformer for the detection of sinusoidal earth fault currents

Tr2 Residual current transformer for the detection of direct unidirectional currents.

The residual current transformer Tr1 monitors the presence of pulsating and alternating earth fault currents in the electronic installation while residual current transformer Tr2 measures the direct unidirectional currents. In the event of a fault the second transformer transmits the opening command to the release S via the (printed) circuit board E. In type B RCCBs, the section whose functioning depends on the line voltage is supplied by all three-phase conductors and the neutral, so that the functioning as type B is guaranteed even if there is a voltage only in two of the 4 power conductors. In addition, the supply of the electronic section is sized in such a way that the device can safely intervene even if there is a voltage drop of 70%.


In this way an intervention takes place when direct unidirectional earth fault currents emerge, even in the event of faults in the electric power supply grid, for example if there is no neutral conductor.

Direct or similar earth fault currents


An increasing amount of industrial equipment is supplied by circuits which in the event of a fault generate direct earth fault currents with a very low residual ripple, which can be even less than 10%. For example with direct current supplied motor drives for pumps, elevators, textile machines etc. it is becoming more common to use inverters with a three-phase rectifier bridge.

In the event of an earth fault current the wave of the earth fault is as indicated in the figure below.


Three-phase rectifier bridge




Three-phase wye rectifier



Phase currents



Earth fault current



RCDs technical details

Type B RCDs


F200 B RCCBs provide additional protection against direct contact and are the right choice to ensure maximum system safety thanks to early detection of fault currents with continuous waveforms or high frequencies.

Selection of RCDs. General rules


Type B RCDs are suitable for non-linear circuits that can generate leakages with high direct current ($> 6 \text{ mA}$) and/or high frequency components. Such components can be found in several industrial components and applications that embed or depend on electronics.

The main circuits that can be considered responsible for such leakages and the common applications where Type B could be demanded are:


Circuits containing single and three-phase rectifiers



Circuits containing rectifiers with high levelling capacity




Circuits containing rectifiers with active power factor correction




RCDs technical details

Type B RCDs

Circuits containing continuous voltage generators with no separation from a.c. network



Circuits containing continuous voltage generators



RCDs technical details

Type B RCDs

Immunity to nuisance tripping: advantages of Type B

RCCBs

RCDs Type B are advance-designed products that, on one hand, are able to protect from different kinds of faults, regardless of their waveform; on the other hand, they are immune to unwanted trippings.

In order to be such an effective device in terms of protection, every Type B RCD must withstand successfully all the tests provided by the Standards. In the testplan are foreseen several tripping waveforms that are considered to represent the best approximation to a real fault condition in case of non linear circuits.

Tripping waveforms for Type B RCDs

	Residual current form	Limit value of tripping current
Alternating		0,5...1,0 $I_{\Delta n}$
Unidirectional pulsating		0,35...1,4 $I_{\Delta n}$
Unidirectional pulsating with phase angle mode		Cut-off angle 90° from 0,25 to 1,4 $I_{\Delta n}$ Cut-off angle 135° from 0,11 to 1,4 $I_{\Delta n}$
Alternating sinusoidal residual current plus pulsating dc current, suddenly applied or smoothly increasing		Max. 1,4 $I_{\Delta n}$ + 0,4 $I_{\Delta n}$ d.c.
Unidirectional pulsating superimposed on direct		Max. 1,4 $I_{\Delta n}$ + 0,4 $I_{\Delta n}$ d.c.
Multi-frequency		From 0,5 to 1,4 $I_{\Delta n}$
Two-phase rectified		From 0,5 to 2,0 $I_{\Delta n}$
Three-phase rectified		
Direct without ripple		
Alternating up to 1 kHz		Current frequency 150 Hz from 0,5 to 2,4 $I_{\Delta n}$ Current frequency 400 Hz from 0,5 to 6 $I_{\Delta n}$ Current frequency 1000 Hz from 0,5 to 14 $I_{\Delta n}$



RCDs technical details

Type B RCDs

To prove their immunity to unwanted tripping, Type B residual current devices must successfully pass further severe tests such as:

- 8/20 μ s impulse up to 3000 A (s. fig. 1);
- 10 ms impulse up to 10 $I_{\Delta n}$ (s. fig. 2).

These tests emulate the conditions that an RCD must withstand in case of overvoltages or leakages due to EMC filters or electronic loads. Type B and devices can be considered suitable for all difficult applications, not only in terms of protection, but of operational continuity as well.



Tripping times


Type	Fault currents	Tripping time at		
	Alternating currents	$1 \times I_{\Delta n}$	$2 \times I_{\Delta n}$	$5 \times I_{\Delta n}$
	Pulsating DC currents	$1,4 \times I_{\Delta n}$	$2 \times 1,4 \times I_{\Delta n}$	$5 \times 1,4 \times I_{\Delta n}$
	Smooth DC currents	$2 \times I_{\Delta n}$	$2 \times 2 \times I_{\Delta n}$	$5 \times 2 \times I_{\Delta n}$
Standard or short-time delay		Max. 0,3 s	Max. 0,15 s	Max. 0,04 s
Selectiv S		0,13 - 0,5 s	0,06 - 0,2 s	0,05 - 0,15 s
				0,04 - 0,15 s

RCDs technical details


Type B RCDs

Variation of residual current tripping thresholds according to frequency

F200 B 30 mA




F200 B 300 mA



RCDs technical details

Type B RCDs

F200 B 500 mA




RCDs technical details


Type B RCDs

F200 B high ratings

F204 B 30 mA




F204 B 300 mA



RCDs technical details

Type B RCDs

F204 B 500 mA




RCDs connected in series

This new section is a summary of “Guide to the selection of RCDs connected in series”.

For more details and complete explanation please refer to the white paper with document ID 9AKK108467A1850.

In many installations, two or more RCDs are installed in series: one common upstream RCD protects the distribution circuit and one or more downstream RCDs protect the final circuits. We use the term “in series” for a connection as per figure below, as commonly intended in the installation practice. It remains understood that the

upstream RCD does not necessarily see the same leakage current seen by any one of the downstream RCDs (as the correct, formal definition of “series” would require), for it generally collects the sum of said leakage currents. We believe that this abuse of terminology be for the sake of simplicity and brevity.



First, the correct types for downstream RCD(s) must be selected, basing on load characteristics.

This implies that the installation must be properly designed, so that protecting RCDs operated within their intrinsic limits. Then, the upstream RCD must be selected accounting for the total DC earth fault expected at the upstream point of installation, when the loads are in faulty and in fault-free conditions.

The following conditions hold:

- If a type B RCD is installed downstream, then the maximum DC earth current let through by it (and reaching the upstream RCD) is $2 \times I_{\Delta n}$, because this is the tripping threshold of type B RCDs in case of DC residual current.
- If a type F RCD is installed downstream (and assuming that the installation had been properly designed, so that the type F RCD operated within its limits), then the maximum DC earth current expected through it (and reaching the upstream RCD) is 10 mA regardless of its $I_{\Delta n}$, because this is the maximum DC earth fault that type F RCDs may tolerate.
- If a type A RCD is installed downstream (and assuming that the installation had been properly designed, so that the type A RCD operated within its limits), then the

maximum DC earth current expected through it (and reaching the upstream RCD) is 6 mA regardless of its $I_{\Delta n}$, because this is the maximum DC earth fault that type A RCDs may tolerate.


- Type AC RCDs are not expected to operate in presence of DC earth currents and therefore (assuming that the installation had been properly designed so that they operated safely) they do not contribute to the DC earth leakage that reaches the upstream RCD.

In case of two or more RCDs of type A/F/B installed in parallel downstream, the maximum DC earth current through the general upstream RCD, in the worst case, is the sum of the earth currents through each of the downstream RCDs. This is clearly a pessimistic scenario: in a real situation, DC components stemming from different subcircuits may not be simultaneously present (e.g., EV charging stations not necessarily operating at the same time), or the DC earth current from several parallel loads may at least partially compensate each other. Anyway, over long periods of time the likelihood of particularly unfavorable conditions rises, and the installation must be conservatively designed so to be on the safe side.

RCDs connected in series

It is therefore essential to ensure that RCDs installed upstream of one or more RCDs of type A, F or B are not blinded by an excessive DC earth current through them. Particularly, the RCD installed upstream must always provide protection in the event of an AC fault in the system portion under its surveillance. Some supplied loads like, e.g., electric vehicle charging, are expected to cause a non-negligible DC earth current component, also in fault free conditions. If such DC earth current

component is large enough to impair the correct operation of the upstream RCD, the latter may fail to protect, e.g., a superimposed AC earth fault, as illustrated in Figure below. Typical example of installation where an upstream RCD of type AC/A/F (i.e., less-than-B) may be blinded by an excessive DC earth current let thought by a downstream RCD of type B. If not properly selected, the upstream RCD may not operate correctly, therefore failing to clear a superimposed AC fault.




For the sake of simplicity, only a two-level installation will be dealt with, considering a single RCD upstream and one or more RCDs downstream. The general, multi-level case, which may also present a different number of levels in different portions, can be addressed similarly, starting from the low-

est levels, then suitably selecting the RCDs of the levels immediately above, and then moving to the levels above until the top-most RCD. Anyway, two-level installations are way more common, the multi-level case being reserved to rare exceptions.

RCDs connected in series

The simplest solution: type B upstream



Alternative solution with ABB RCDs

In the following tables, selective RCDs (denoted by S) are also considered. Such RCDs are characterized by an intentional delay before tripping (non-actuating time), to guarantee that downstream RCDs trip before the upstream one, i.e., selectivity.


Time delayed industrial type ABB residual circuit breakers, including those with a separate toroid (MRCD), as per Annex B or Annex M of IEC 60947-2 [4], are equivalent to selective RCDs, and are thus included in relevant cases, if the non-actuating time is ≥ 0.06 s.

Important warning.


IEC 60364-5-53:2019/AMD1:2020 [1] is an international standard: in some countries, national standards may be more restrictive and, for instance, may not allow the second option. Therefore, installation engineers must always refer to applicable national rules for the correct selection of RCDs.

RCDs connected in series

Installations with type B RCDs downstream



Installations without type B RCDs downstream



RCDs connected in series

Selection of upstream RCD type, allowed when using B type ABB RCDs downstream

case	type	Downstream RCD					Upstream RCD		
		Poles	Rated Current	IΔn	Max q.ty	Type	Poles	Rated current	IΔn
1	B	2P and 4P	any	30 mA	1	F200 A type	4P	up to 63 A	100 mA
						F200 A type	2P	80-100 A	100 mA
						F200 A type	4P	80-100 A	100 mA
						DDA200 A type	3P/4P	up to 63 A	100 mA
						DS201 AP-R or F type	1P+N	up to 40 A	100 mA
2	B	2P and 4P	any	30 mA	2	F200 A type	2P	up to 63 A	300 mA
						F200 A type	4P	up to 63 A	300 mA
						F200 A type	2P	80-100 A	300 mA
						F200 A type	4P	80-100 A	300 mA
						DDA200 A type	2P	up to 63 A	300 mA
						DS201 A or AP-R or F type	1P+N	up to 40 A	300 mA
						F200 A type Selective	2P	up to 63 A	100 mA
						F200 A type Selective	4P	up to 63 A	100 mA
						F200 A type Selective	2P	80-100 A	100 mA
						F200 A type Selective	4P	80-100 A	100 mA
3	B	2P and 4P	any	30 mA	5	F200 A type Selective	2P	up to 63 A	300 mA
						F200 A type Selective	4P	up to 63 A	300 mA
						F200 A type Selective	2P	80-100 A	300 mA
						F200 A type Selective	4P	80-100 A	300 mA
						DDA200 A type Selective	2P	63 A	300 mA

Please refer to your national standards for any restrictions in series connection of B type RCDs downstream

RCDs connected in series

Selection of upstream RCD type, allowed when using without B type ABB RCDs downstream


case	type	Downstream RCD					Upstream RCD		
		Poles	Rated Current	IΔn	Max q.ty	Type	Poles	Rated current	IΔn
4	"A or (F + charger embedding RDC-DD, e.g., ABB Terra AC)"	2P and 4P	any	30 mA	10	F200 A type	4P	up to 63 A	100 mA
						F200 A type	2P	80-100 A	100 mA
						F200 A type	4P	80-100 A	100 mA
						DDA200 A type	3P/4P	up to 63 A	100 mA
						DS201 AP-R or F type	1P+N	up to 40 A	100 mA
5	"A or (F + charger embedding RDC-DD, e.g., ABB Terra AC)"	2P and 4P	any	30 mA	20	F200 A type	2P	up to 63 A	300 mA
						F200 A type	4P	up to 63 A	300 mA
						F200 A type	2P	80-100 A	300 mA
						F200 A type	4P	80-100 A	300 mA
						DDA200 A type	2P	up to 63 A	300 mA
						DS201 A or AP-R or F type	1P+N	up to 40 A	300 mA
						F200 A type Selective	2P	up to 63 A	100 mA
						F200 A type Selective	4P	up to 63 A	100 mA
						F200 A type Selective	2P	80-100 A	100 mA
						F200 A type Selective	4P	80-100 A	100 mA
						DDA200 A type Selective	2P	63 A	100 mA
						DDA200 A type Selective	3P/4P	63 A	100 mA
6	"A or (F + charger embedding RDC-DD, e.g., ABB Terra AC)"	2P and 4P	any	30 mA	50	F200 A type Selective	2P	up to 63 A	300 mA
						F200 A type Selective	4P	up to 63 A	300 mA
						F200 A type Selective	2P	80-100 A	300 mA
						F200 A type Selective	4P	80-100 A	300 mA
						DDA200 A type Selective	2P	63 A	300 mA

RCDs technical details

Use of 4P RCCBs in 3-phase system without neutral pole

Use of a 4P RCCB in a 3-phase circuit without neutral


The test button circuit of these RCCBs 4P F 200, regardless of the rating, is wired inside the device between terminal 5/6 and 7/8/N as indicated below, and has been sized for an operating voltage between 110V (170V for the 30mA version according to EN standard) and 254 V (110 and 277 V according to UL 1053).



In case of installation in a 3 phase circuit without neutral, if the concatenate voltage is between 110V (170V for the 30mA version according to EN standard) and 254 V (277 V according to UL 1053) for the correct working of the test button there are two possible solutions:

- 1) To connect the 3 phases to the terminals 3/4 5/6 7/8/N and the terminals 4/3 6/5 8/7/N (supply and load side respectively)
- 2) To connect the 3 phases normally (supply to terminals 1/2 3/4 5/6 and load to terminals 2/1 4/3 6/5) and to bridge terminal 1/2 and 7/8/N in order to bring to the terminal 7/8/N the potential of the first phase. In this way the test button is supplied with the phases' concatenate voltage.

If the circuit is supplied with a concatenate voltage higher than 254 V, as in the typical case of 3 phase net with concatenate voltage of 400 V - or 480 V according to UL 1053 - (and voltage between phase and neutral of 230 V or 277 V according to UL 1053), it is not possible to use these connections because the circuit of the test button will be supplied at 400 V and could be damaged by this voltage.



IΔn [A]	Rest [Ω]
0.03	2200*
0.03	3900
0.1	2200
0.3	2200
0.5	2200

* Only for IEC range and 125 A right-sided ratings


In order to allow the correct operation of the test button also in 3 phase nets at 400 V - 480 V according to UL 1053 - (concatenate voltage) it is necessary to connect normally the phases (supply to terminals 1/2 3/4 5/6 and load to terminals 2/1 4/3 6/5) and to bridge terminal 4/3 and 8/7/N by mean of an electric resistance as indicated above.

In this way the test button circuit is fed at 400 V - 480 V according to UL 1053 - but for example in an IEC compliant RCCB with $I\Delta n=0.03$ A there will be the Rest=3.3 kOhm resistance in series to the test circuit resistance. Rest will cause a voltage drop that leaves in the test circuit a voltage less than 254 V - 277 V according to UL 1053. Rest resistance must have a power loss higher than 4 W.

In the normal operation of the RCCB (test circuit opened) the Rest resistance is not fed so it does not cause any power loss.

The solution RCCBs with neutral pole on left side

The test button circuit of these RCCBs is wired inside the device between terminal 3/4 and 5/6 as indicated below, and it has been sized for an operating voltage between 195 V and 440 V - 480 V. In case of a three phase system without neutral with concatenate voltage between phases of 230 V or 400 V - 277 V or 480 V - it is enough to connect the 3 phases normally (supply to terminals 1/2 3/4 5/6 and load to terminals 2/1 4/3 6/5) without any bridge.




RCDs technical details

Operating voltage of test button

Operating voltage of test button

The operation of RCDs depends on the maximum and minimum operating voltage of the test button.





This symbol represents
the circuit of test button

Maximum and minimum operating voltage of DS201 test button

DS201
Ut = 110-264 V;
for 30mA: Ut = 170-264V

DS201 M 110V
Ut = 110-264V

DS301C
for 30mA; Ut = 170-264 V






Between the two terminals
there is a rated voltage of
110-264 V

Maximum and minimum operating voltage of DS 200 and DDA 200 test button

DDA 202 and DS 202
In = 25-40 A
Ut = 110 - 254 V;
for 30mA: Ut = 170-254V

DDA 203 and DS 203
In = 25-40 A
Ut = 195 - 440 V;
for 30mA: Ut = 300-440V




DDA 204 and DS 204
In = 25-40 A
Ut = 195 - 440 V;
for 30mA: Ut = 300-440V



DDA 202 and DS 202
In = 63 A
Ut = 110 - 254 V;
for 30mA: Ut = 170-254V

DDA 203 and DS 203
In = 63 A
Ut = 195 - 440 V;
for 30mA: Ut = 300-440V

DDA 204 and DS 204
In = 63 A
Ut = 195 - 440 V;
for 30mA: Ut = 300-440V



RCDs technical details


Operating voltage of test button

Maximum and minimum operating voltage of DDA 200, special version 110 V

DDA 202 110 V

In = 25-40-63 A


Ut = 110-254 V



DDA 203 110 V

In = 40 A


Ut = 110-254 V



DDA 203 110 V

In = 63 A


Ut = 110-254 V



DDA 204 110 V

In = 63 A


Ut = 110-254 V



Maximum and minimum operating voltage of the DS203NC

DS203NC

Ut= 195-440V (300-440V for 30 mA)



RCDs technical details

Operating voltage of test button


Maximum and minimum operating voltage of DDA 200, special version 400 V

DDA 202

In = 63 A

Ut = 400 V

1/2 3/4



2/1 4/3

Maximum and minimum operating voltage of DDA 200 B type test button


DDA 202 B

In = 63 A

Ut=195-254 V (170-254 V for

30 mA)

1/2 3/4



2/1 4/3


DDA 203 B

In = 63 A

Ut=310-440 V (300-440 V

for 30 mA)

1/2 3/4 5/6



2/1 4/3 6/5


DDA 204 B

In = 63 A

Ut=195-254 V (300-440 V

for 30 mA)

1/2 3/4 5/6 N



2/1 4/3 6/5 N


Maximum and minimum operating voltage of DDA 200 AE test button

DDA 202 AE

In = 63 A

Ut = 184-264 V

INPUT T 1/2 3/4




2/1 4/3 OUTPUT T

DDA 203 AE

In = 63 A

Ut = 310-440 V

INPUT T 1/2 3/4 5/6




2/1 4/3 6/5 OUTPUT T

DDA 204 AE

In = 63 A

Ut = 184-264 V

INPUT T 1/2 3/4 5/6 N



2/1 4/3 6/5 N OUTPUT T

RCDs technical details

Operating voltage of test button

Maximum and minimum operating voltage of F 200 test button


F 202

$I_n = \leq 100 A$

$U_t = 110 - 254 V$

for 30mA^①: $U_t = 170 - 254 V$

1/2 3/4



2/1 4/3


F 204 neutral on right

$I_n = \leq 100 A$

$U_t = 110 - 254 V$

for 30mA^①: $U_t = 170 - 254 V$

1/2 3/4 5/6 7/8/N




2/1 4/3 6/5 8/7/N

F 204 neutral on left

$I_n = \leq 100 A$

$U_t = 195-440V$; for 30mA: $U_t = 250-440V$

R	S	T	
7/8/N	1/2	3/4	5/6



8/7/N 2/1 4/3 6/5

For use in 3-phases circuit without neutral at 400 V it is possible to connect the three phases R, S and T like in the figure.


F 204 neutral on right

$I_n = 125 A$

$U_t = 185 - 440 V$

for 30mA^①: $U_t = 150 - 250 V$

1/2 3/4 5/6 7/8/N



2CSG404936F00202

① Only for versions with marking according to EN 61008-1;EN 61008-2-1


F 204 neutral on left

$I_n = 125 A$

$U_t = 185 - 440V$

for 30mA: $U_t = 250 - 440 V$

7/8/N 1/2 3/4 5/6




8/7/N 2/1 4/3 6/5

F202 110V

$I_n \leq 100 A$

$U_t = 110 - 254 V$

1/2 3/4




2/1 4/3

F 204 110V

$I_n \leq 100 A$

$U_t = 110 - 254 V$

1/2 3/4 5/6 7/8/N



2/1 4/3 6/5 8/7/N

RCDs technical details

Operating voltage of test button


Maximum and minimum operating voltage of DDA 800 and DS800 test button

DDA 802

DS802

$IN \leq 125 A$

$Ut = 195-690 V$



DDA 804

DS804

$IN \leq 125 A$


$Ut = 195-690 V$

DDA 803


DS803

$IN \leq 125 A$

$Ut = 195-690 V$



1/2 3/4 5/6 7/8



RCDs technical details

RD2 residual current relays

RD2 residual current monitors

They operate combined with appropriate toroidal transformers (in 9 different diameters).

The relay can command the tripping of the protection circuit-breaker release, thus opening the circuit.

According to the IEC 62020 Standard, these relays are "A Type". They are sensitive to leakage sinusoidal currents and to leakage pulsating currents with direct components. Thus they can be defined as "A type".



More technical characteristics

Calibration tolerances		- sensitivity	$75\% \pm 10\%$
		- time	$75\% \pm 10\%$
Power consumption	[W]	0.45 at 48 V AC/DC	
		1.2 at 110 V AC/DC	
		3.4 at 230 V AC	
		11 at 400 V AC	
Dielectric test voltage at ind. freq. for 1 min.	[kV]	2.5	
Max. peak current with 8/20 μ s wave	[A]	5000	
Installation position		any	
Protection degree		IP20	

RCDs technical details

RD3 residual current relays

RD3 electronic residual current relay

RD3 is a residual current device that in combination with a toroidal transformer is able to detect and evaluate earth fault current. If used in combination with a shunt-trip or undervoltage release, it can realize the opening of a circuit breaker ensuring earth leakage current protection.

RD3



RD3M




RD3P



Setting of residual operating current and trip time delay.

Using the rotary selectors on the front of the device, it is possible to adjust the residual operating current and the trip time delay.



Adjustment of residual operating current (Δn [A]) and trip time delay (Δt [s]).

Main features

Pre-alarm

Placing the dip-switch in the ON position enables the pre-alarm function: the output contact on terminals 7 8 9 will change state in the event of a residual current exceeding 60% I_{DA} .

Autoreset

Placing the dip-switch in the ON position enables the automatic Reset function: the Relay OUTPUT contacts revert to their original state once the fault condition ceases.

Fail-safe

Built into the device (positive safety). In case of absence of supply to the device RD3 the output contact on terminals 10 11 12 will change state as shown in the figures.

RD3



RD3M



RD3P



RCDs technical details

RD3 residual current relays

Indicators

RD3



RD3M



RD3P



Stand by



FAULT




Pre Alarm



FAULT



Fault




Absent connection with toroid




Fail-safe - RD3, RD3M, RD3P

Integrated in the device (positive safety). In case of power supply voltage failure of RD3 device, the output contacts numbered 10 11 12 will switch as shown below.




Contacts when the device is OFF




Pre-alarm - RD3P, RD3M

When the dip-switch is set to ON, the prealarm function is activated: the output contact marked by the 7 8 9 terminals will switch in case of a fault detected by the device exceeding 60% Δ .



Autoreset - RD3P

When the dip-switch is set to ON, the automatic Reset function is activated: the output device contact will return to stand-by when the fault condition has been resolved.




RCDs technical details

RD3 residual current relays

Test


To perform the relay test, press the button on the front. The relay can be reset via the front button or a remote button, as shown in the figure:

Test



On RD3P version, a no trip test can also be performed by simultaneously pressing the front test and reset buttons for 3 seconds. In this case, the output contacts will not switch, as shown in the figure below:

Test NO TRIP - RD3P



Associated circuit breakers (and relative releasers)

- Tmax range from T1 to T5, In up to 630 A, Ue up to 690 V, with UVR undervoltage release or SOR shunt opening release
- XT range from XT1 to XT4, In up to 250 A, Ue up to 690 V, with UVR undervoltage release or SOR shunt opening release
- pro M Compact S200 range with In up to 63 A, Ue up to 440 V, with S 2C-A shunt trip or S 2C-UA undervoltage release

Tripping time (RD3 output relay switching time), cumulative time (with associate circuit breakers), non-trip time limit:

RD3: tripping time, cumulative time, non intervention time

Time selection	IΔn		2 IΔn		5 IΔn		10 IΔn	
	tripping time	cumulative time with associate circuit breaker	tripping time	cumulative time with associate circuit breaker	tripping time	cumulative time with associate circuit breaker	tripping time	cumulative time with associate circuit breaker
Dt [s]	≤ [s]	≤ [s]	≤ [s]	≤ [s]	≤ [s]	≤ [s]	≤ [s]	≤ [s]
0	0.2	0.3	0.12	0.15	0.02	0.04	0.02	0.04
0.06	0.3	0.5	0.17	0.2	0.09	0.15	0.09	0.15
0.2	0.45	0.5	0.45	0.5	0.45	0.5	0.45	0.5
0.3	0.55	0.6	0.55	0.6	0.55	0.6	0.55	0.6
0.5	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
1	1.2	-	1.2	-	1.2	-	1.2	-
2	2.2	-	2.2	-	2.2	-	2.2	-
3	3.2	-	3.2	-	3.2	-	3.2	-
5	5.2	-	5.2	-	5.2	-	5.2	-
10	10.2	-	10.2	-	10.2	-	10.2	-

RCDs technical details

ELR front panel residual current relays

ELR: tripping time, cumulative time, non intervention time

Time selection Δt [s]	$I_{\Delta n}$		$2 I_{\Delta n}$		$5 I_{\Delta n}$		$10 I_{\Delta n}$	
	tripping time \leq [s]	cumulative time with associate circuit breaker \leq [s]	non-intervention time [s]	tripping time \leq [s]	cumulative time with associate circuit breaker \leq [s]	tripping time \leq [s]	cumulative time with associate circuit breaker \leq [s]	tripping time \leq [s]
0	0.04	0.3	-	0.025	0.15	0.02	0.04	0.02
0.06	0.1	0.5	0.06	0.08	0.2	0.08	0.15	0.08
0.2	0.16 +15%	-	0.2	0.15 +15%	-	0.15 +15%	-	0.15 +15%
0.3	0.3 +15%	-	0.3	0.3 +15%	-	0.3 +15%	-	0.3 +15%
0.5	0.5 +15%	-	0.5	0.5 +15%	-	0.5 +15%	-	0.5 +15%
1	1 +15%	-	1	1 +15%	-	1 +15%	-	1 +15%
2	2 +15%	-	2	2 +15%	-	2 +15%	-	2 +15%
3	3 +15%	-	3	3 +15%	-	3 +15%	-	3 +15%
5	5 +15%	-	5	5 +15%	-	5 +15%	-	5 +15%

RCDs technical details

Toroidal transformers

Toroidal transformers

The choice of toroidal transformers is made according to the useful diameter and the minimum value of the leakage current to be detected.

Technical features of the toroidal transformers

Type	Toroid useful diameter [mm]	Max rated current [A] ⁽¹⁾	Min measurable current [mA]	Maximum capacity [A]
TRM	29	65	30	160
TR1	35	75	30	250
TR2	60	85	30	400
TR3	80	160	100	800
TR4	110	250	100	1250
TR4/A	110	250	300	1250
TR160	160	400	300	2000
TR160/A	160	400	500	2000
TR5	210	630	300	3200
TR5/A	210	630	500	3200
TR6	300	630	500	5000
TR6/A	300	630	1000	5000

(1) Toroidal transformers selection for use with ELR/RD3 according to IEC/ EN 60947-2 Annex M in combination with MCBs S200 range and MCCBs Tmax range up to T5 (630 A) and XT range up to XT4 (250 A)

RCDs technical details

Toroidal transformers

Technical characteristics

	TRM	TR1	TR2	TR3	TR4	TR4A	TR160	TR160A	TR5	TR5A	TR6	TR6A
Core		closed	closed	closed	closed	open	closed	open	closed	open	closed	open
Available internal diameter	[mm]	29	35	60	80	110	110	160	160	210	210	300
Weight	[kg]	0.17	0.22	0.28	0.45	0.52	0.6	1.35	1.6	1.45	1.85	2.1
Minimum measurable current	[mA]	30	30	30	100	100	300	300	500	300	500	1000
Installation position		Any										
Operating temperature	[°C]	-10...+70										
Storage temperature	[°C]	-20...+80										
Transformation ratio		500/1										
Dielectric test voltage at industrial freq. for 1 min.	[kV]	2.5										
Max. insulating voltage	[V a.c.]	1000										
Max. thermal overload	[kA]	40/1 sec.										
Connections		Screw terminal boards, max. section 2.5 mm ²										
Protection degree		IP20										

Generality

They must be mounted with residual current monitors upstream the lines or loads to be protected; all active conductors (phases and neutral) of single-phase as well as of three-phases lines must pass through them.

In this way these devices perform the vector sum of line currents detecting the possible homopolar differential currents that leak to earth: their core of sheet iron has high magnetic properties that allow to detect even very low leakage currents.

The choice of a toroidal transformer depends on the conductor or on the bar to be used.

It is suggested to use the open versions in case of revamping or upgrading of an existing installation.

Installation

All active conductors can be introduced in the toroidal transformers without the need of respecting any specific sense of introduction (P1-P2 or P2-P1). The output signal

must be picked up from terminals 1 (S1) and 2 (S2) and connected to the residual current monitor, while terminals 3 and 4 must be connected to the test output of those relays of FPP range with this function. With RD2 they must remain disconnected. For this connection it is better to use twisted or shielded cables, possibly far from busbars. The minimum recommended section of connection cables should have a maximum resistance of 3 Ω; anyway consider a maximum length of connection of 20 m for 0.5 mm² and of 100 m for 2.5 mm².

For versions with openable core it is necessary to control that the contact surface of the two semi-cores is clean, that bolts are tight and that connection cables connections on both sides are intact.

Connection cables with metallic shielding or armor must be earthed downstream the toroidal transformer; if they run within the transformer they must be earthed in the opposite direction.