MT5000 Series Guided wave radar level transmitter

High accuracy level and interface detection for liquids, slurries and solids K-TEK Products



Features

- SIL 2/3 Certified IEC 61508*
- Graphic Display with Waveform Screen
- Widest Selection of Wetted Materials
- Radar Signal Travels Along the Waveguide –
 Eliminates False Echoes and Minimizes Signal Loss
- No Moving Parts
- Rigid, Flexible Cable & Coaxial Probes
- All Digital Electronics
- Loop Powered to 217ft Probe Length
- Total and/or Interface Level Measurement
- Field Replaceable / Upgradable Electronics Module
- * transmitters equipped with 4-20mA/HART module option only

Options

- FOUNDATION fieldbus output
- Glass viewing window
- 316 Stainless Steel enclosure
- Remote sensor

Accessories

- External chambers
- Stilling wells
- JDF200 loop indicator
- RI100 Repeat Indicator for 2 4-20mA Output Signals



Electronic transmitter:			
Resolution	+/- 0.063in. /1.6mm		
Repeatability	0.1 in. / 3 mm		
Ambient Temperature	-40 to 151ºF (-40 to 66	<u>⁰</u> C)	
	Coax Probe or in stilling well/chamber	+/- 3mm	
Measuring accuracy, level	Single cable or rod	+/-5mm to 15.24m (50.0ft)/ +/-25mm to 66m (217ft)	
Measuring accuracy, interface level and ULD mode	All probes	+/-1.0in / 25mm	
	13.5 to 36 Vdc - 4-20mA HART loop powered		
Supply voltage	9 to 32 Vdc - FOUNDA	TION fieldbus	
Output/Communications	4-20 mA HART	- SIL 2/3 Certified IEC 61508	
	FOUNDATION fieldbus	5	
		- ITK 5.1.0 Compliant	
		- 5 AI and 1 PID blocks	
		- 15.8 mA quiescent current draw	
		- LAS Capable	
Power consumption	4-20mA	at 36.0 Vdc - 3.6mA 0.13 watts; 21mA 0.76 watts	
		at 13.5 Vdc - 3.6mA 0.046 watts; 21mA 0.28 watts	
	HART mode (4.0mA)	at 36.0 Vdc 0.144 watts	
		at 13.5 Vdc 0.054 watts	
	FOUNDATION fieldbus	5 0.5 watts maximum	
	4-20mA	at 36.0 Vdc and 21mA, 1740 ohms* *maximum with HART communication is 700 ohms	
Maximum line resistance		at 13.5 Vdc and 21mA, 645 ohms	
	HART mode (4.0mA)	< 650 to 700 ohms	
	FOUNDATION fieldbus	s 43.6 ohms/km @ 20 C	
Reverse polarity protection	Diode in series with lo	ор	
Jpdate rate	2 outputs per second		
Damping	Field adjustable, range	e: 0.1 to 36 seconds	
Alarm output	NE43, Jumper selectat	ble upscale (21 mA) or downscale (3.6 mA)	
Humidity	0 to 100% RH, non-cor	ndensing	
Linearization	20 point linearization t	able available	
Graphic Display	Field Selectable Units in Feet, Inches, Millimeters, Centimeters, Meters or Percentage and Waveform Screens		
Enclosure	Dual compartment		
Enclosure material	Cast low copper alumi	num with polyester powder coat or 316 stainless steel	
Electrical connection	1/2" FNPT, M20 adapte	er and bus connectors available	
	IP66, NEMA 4X		

¹ see approval agency restrictions

Specifications

Sensor

	Standard	Options	
Material	316/L stainless steel	304/L, Hastelloy C-276, Hastelloy B3, Monel 400, Titanium, Inconel625, other materials on request	
Process temperature	-60 to 400ºF (-50 to 204ºC), see o-ring selection	up to 800ºF (427ºC) with options	
Process pressure	-14.5 to 1500psig @ 300ºF (103 bar @ 38ºC)	-14.5 to 5000 psig (0 to 344barg)	
Range	2 to 217 ft. / 0.6 to 66.14 m		
Process Connection	3/4" NPT Standard, other threaded and flang	ged options available	
Dielectric Constant	Minimum 1.4, 1.3 in ULD mode		
Process Viscosity	coax 500 cp, single probe 10,000 cp		



MT5100 INTERFACE GUIDELINES

In order to properly detect the level of interface between two liquids using the MT5100, the following rules must be adhered to:

- 1. One of the following probe and mounting configurations must be used:
 - a. Single rigid rod or flexible cable mounted in a stilling well, external chamber, or existing displacer.*
 - b. Coaxial probe mounted into tank, external chamber, or displacer
 - c. Single rigid rod or flexible cable in open vessel with recommended installation conditions.

*This is the preferred mounting configuration to reduce the chance of fouling.

- 2. Emulsion layers will affect the detection of an interface level. An emulsion layer may negate an interface level indication completely. The MT5100 will read an interface level in the presence of a 3 inch emulsion. Greater emulsion layers may be possible. Please consult factory.
- 3. The minimum upper fluid thickness must be 4 inches when emulsion is present, and 3 inches with a clean interface. Closer measurement may be possible with calibration adjustment.
- 4. The upper fluid dielectric constant must be greater than 1.4 and less than 5.
- 5. The interface level indication is a calculated value based partially upon the dielectric of the upper fluid. The upper fluid dielectric must remain constant for consistency / accuracy in the interface level indication.
- 6. The lower fluid dielectric constant must not be less than 15.
- 7. If the application is a flooded condition (sensor completely submerged in process), it must remain completely flooded.
- 8. In a non-flooded condition, the upper fluid must not be allowed to enter the upper unmeasurable zone. The upper unmeasurable zone is typically located within the mounting nozzle of the vessel.
- 9. If measuring interface in an external chamber, ensure that the fluid is allowed to equalize between the vessel and the chamber. Consult the factory or your local representative for assistance.
- 10. R and RW remote coupler configurations are not recommended for interface applications unless the remote coax is 5ft or less and the probe is a coaxial configuration or in a chamber or stilling well.

If the required interface application does not fall within the above mentioned parameters, please consult the factory for an alternate technology, such as an LMT Series magnetostrictive transmitter or a KM26 magnetic level gauge.

GUIDELINES FOR MEASURING with ULD MODE

When measuring low dielectric fluids and bulk solids, it is possible to use the end of probe shift as the target. Requirements for using the end of probe in Ultra Low Dielectric (ULD) mode.

- 1. The dielectric of the material must be between 1.3 and 3.0.
- 2. You must have a clear end of probe signal. This may require an additional disk on the end of probe in order to increase the reflection.
- 3. The probe type can be cable, rod, or coaxial.
- 4. Accuracy may be affected if dielectric value changes.
- 5. If the end of probe is lost in sludge, interface or emulsion, and the end of probe signal is lost, then ULD reading will not be possible.
- 6. ULD mode cannot be used where interface or emulsion layer are present.

PROCESS CONNECTION / WAVEGUIDE COUPLER

Base Code	Insulator	Process Connection	Seal Options	Maximum Pressure	Min Temp⁵	Max Temp⁵		mpati Probe	
							Rod	Cable	Coaxial
C1 ¹	Teflon	3/4" NPT	Viton FKM A,	1500 psi @ 100°F / 103 bar @ 38°C	-60ºF	400ºF	P01, P03,	P11	P51, P91 ⁷
C2 ¹	-	1.5" NPT	Kalrez 4079 EPDM,	600 psi @ 400°F / 41 bar @ 204°C	-50ºC	204ºC	P02, P43	P12, P33	
C3 ¹		2.5" NPT	Markez Z1319	50 psi / 13.4 bar			P43	P33, P33, P61	
C1H ¹	Teflon	3/4" NPT	Viton FKM A,	3000 psi @ 100 F / 207 bar @ 38 C	-60ºF	400ºF	P01, P03	P11,	P51, P91 ³
			Kalrez 4079	Ū.	-50ºC	204ºC			_
C2H1		1.5" NPT	EPDM, Markez Z1319	1200 psi @ 400 F / 83 bar @ 204 C			P02, P43	P12, P33,	
C8	Borosili- cate	1.5" NPT		5000 psi @ 100ºF / 344 bar @ 38ºC	-60ºF	800ºF		P11 ⁴	P71
(316/L SS and Hastelloy C only)	Glass		Fused Borosilicate Glass	1500 psi @ 800ºF / 103 bar @ 427ºC Not for Hot Water or Steam Service	-50ºC	427ºC			
C9 ²	Alumina Ceramic	1" NPT	Viton FKM A, Kalrez 4079 EPDM, Markez Z1319	2000 psi @ 635ºF / 138 bar @ 335ºC	-60ºF -50ºC	635ºF 335ºC		P11 ⁴	P81
CZ	Custom (C	Custom (Consult Factory)							

Notes: 1. Add the suffix "S" to the Base Code to include a hermetic seal (example: /C4SV). Hermetic seals are required on all IECEx approved equipment.

2. Hermetic seal is required. O-ring selection Markez 1319 is recommended for steam service.

3. The P91 probe has a 1" MNPT adjustable compression fitting equipped with Teflon ferrules as the standard process connection. The maximum process pressure utilizing the Teflon ferrules is 50 psi (3.4 bars).

4. Requires installation in a stilling well or external chamber.

5. Consult O-ring Table for o-ring temperature specifications.

O-Ring Seals*

Order Code	Description	Min. Temp	Max. Temp
v	Viton A (FKM)	-15ºF -26ºC	400ºF 204ºC
к	Kalrez 4079	-40ºF -40ºC	400ºF 204ºC
E	EPDM	-60ºF -50ºC	250ºF 125ºC
А	Markez Z1319	-14ºF -10ºC	572ºF 300ºC

*The information in this chart has been supplied by the o-ring manufacturers. Before permanent installation, test the equipment with the chemicals and under the specific conditions of your application.

If the required o-ring material is not listed above, please consult the factory.

Pressure / Temperature Curves¹



1. Coupler temperatures are based on o-ring temperature ratings. Please refer to the o-ring chart above for further information. 2. C9 coupler temperature rating is based on Markez Z1319 o-ring selection. The temperature is based on o-ring placement in side the coupler, thus allowing higher temperatures at the process connection.

Probe Types

Code	O.D	Notes	Max Length	Attachment Options
Rigid Rod				
P01	0.25in (6mm)		20ft (3.05m) ^{1, 3}	
P02	0.50in (13mm)		20ft (6.10m) ^{2, 3, 4}	D
P03	0.375in (9mm)		10ft (3.05m) ^{1, 3}	
P43	0.125in (3mm)	316 SS and HSC-270	50ft (15.24m)	W (included)
Flexible C	able			
P11	0.1875in (5mm)	2,000lb (907kg) maximum pull force		
P12	0.25in (6mm)	2,000lb (907kg) maximum pull force	force 100ft (30.5m) ³	
P61	0.31in (8mm)	10,000lb (4536kg) maximum pull force		
Triangle C	able			
P33	0.25in (6mm)	Minimum 4" flange connection required	100ft (30.5m)	WS6 (included)
Coaxial (c	lean liquids only)			
P51	0.875in (22mm)			
P71	1.315in (34mm)	316SS only	22ft(6.71m)	2020
P81	0.875in (22mm)	22ft (6.71m)		none
P91	1.00in (25mm)			
CUSTOM				
PZZ	Custom Probe, C	Consult Factory		

Notes: 1. 5ft (1.52m) maximum probe length when installed in a stilling well or EC chamber (minimum 2" diameter) without centering spacer(s).

2. 20ft (3.05m) maximum probe length when installed in a stilling well or EC chamber (minimum 3" diameter) without centering spacer(s).

3. Lengths greater than 7ft (2.13m) require cable spacers at 5ft (1.52m) maximum intervals when installed in a 2" or smaller stilling well or EC chamber. Lengths greater than 10ft (3.05m) require cable spacers at 10ft (3.05m) maximum intervals when installed in 2.5" - 3" stilling well or EC chamber.

4. Segmented probes available

Cable weights for cable probes

Order Code	O.D.	Weight Height (WH)	Weight	Minimum Stilling Well Size	Compatible Probes
W09	0.875 in. (22.2 mm)	4.0 in. (101.6 mm)	0.7 lbs (301 g)	1.0 in. Sch. 80	P11
W10	1.0 in. (25.4 mm)	6.0 in. (152.4 mm)	1.3 lbs (590 g)	1.5 in. Sch. 160	P11, P12
W13	1.25 in. (31.75 mm)	3.5 in. (88.90 mm)	0.8 lbs (317 g)	1.5 in. Sch. 80	P11, P12
W16	1.625 in. (41.3 mm)	2.0 in. (50.8 mm)	1.1 lbs (499 g)	2.0 in. Sch. 80	P11
W19	1.875 in. (47.6 mm)	2.0 in. (50.8 mm)	1.5 lbs (680 g)	2.0 in. Sch. 80	P12
W29	2.875 in. (73.3 mm)	1.0 in. (25.4 mm)	1.8 lbs (816 g)	3.0 in. Sch. 40	P11, P12
W61	1.5 in. (38.1 mm)	5.25 in. (133.35 mm)	2.2 lbs (998 g)	n/a	P61
WS6	2.0 in. (50.8 mm)	6.0 in. (152.4 mm) long	0.9 lbs / 408 g	n/a	P33

Centering disks for rod probes

Order Code	O.D.	Minimum Stilling Well Size	
D15 1.5 in. (38.1 mm)		1.5 in. sch. 40	
D20 2.0 in. (50.8 mm)		2 in. sch. 40	
D23	2.3 in. (58.7 mm)	2.5 in. sch. 40	
D28	2.8 in. (71.1 mm)	3 in. sch. 80	
D38	3.75 in. (95.3 mm)	4 in. sch. 80	

MT5000 Recommended Installation

NOTE: The following guidelines are very conservative. If you have an application that exceeds these limits consult factory for application recommendations.



1. SINGLE PROBE - FLAT PLATE

MINIMUM DIELECTRIC CONSTANT	L MAXIMUM PROBE LENGTH ²	L1 Unmeasurable ¹	L2 Unmeasurable ¹ (WH = Weight Height)
≤4	20 ft. / 6.1 m	6 in. / 15.2 cm	3 in. / 7.6 cm (Rod) WH + 3 in. / 7.6 cm (cable)
10	40 ft. / 12.2 m	3 in. / 7.6 cm	2 ¹ (Rod)
35	50 ft. / 152 m	3 ¹ in. / 7.6 cm	WH + 3" / 7.6 cm (cable)

1. Depending on installation, L1 & L2 unmeasurable lengths of 0 may be possible with use of linearization table and latching feature. For easiest startup use $L1_{min} \ge 3$ " or as listed if greater and $L2_{min} \ge 3$ " (rod) or WH + 3" (cable).

2. Maximum probe lengths are limited as indicated in Probe Type table.



2. SINGLE PROBE - FLAT PLATE WITH COUPLING³

MINIMUM	L	L1	L2
DIELECTRIC	MAXIMUM	Unmeasurable ¹	Unmeasurable ¹
CONSTANT	PROBE LENGTH ²		(WH = Weight Height)
< 4	20 ft. / 6.1 m	8 in. / 20.3 cm	3 in. / 7.6 cm (Rod)
54	2011. / 0.111	8 m. / 20.5 cm	WH + 3 in. / 7.5 cm (Cable)
10	40 ft. / 12.2 m	4 in. / 10.2 cm	
10			2 ¹ (Rod)
35	50 ft. / 15.2 m	3 in. / 7.6 cm	WH + 3 in. / 7.5 cm (Cable)

1. Depending on installation, L1 & L2 unmeasurable lengths of 0 may be possible with use of linearization table and latching feature. For easiest startup use $L1_{min} \ge 3$ " or as listed if greater and $L2_{min} \ge 3$ " (rod) or WH + 3" (cable).

2. Maximum probe lengths are limited as indicated in Probe Type table.

3. The coupling should not extend into the vessel more than 1 in. / 2.5 cm.



3A. SINGLE PROBE - NOZZLE & FLANGE ³

MINIMUM DIELECTRIC CONSTANT	L MAXIMUM PROBE LENGTH ²	L1 Unmeasurable ¹	L2 Unmeasurable ¹ (WH = Weight Height)
≤4	20 ft. / 6.1 m	H + 8 in. / 20.3 cm	3 in. / 7.6 cm (Rod) WH + 3 in. / 7.5 cm (Cable)
10	40 ft. / 12.2 m	H + 4 in. / 10.2 cm	2 ¹ (Rod)
35	50 ft. / 15.2 m	H + 2 ¹ in. / 5.1 ¹ cm	WH + 3 in. / 7.5 cm (Cable)

1. Depending on installation, L1 & L2 unmeasurable lengths of 0 may be possible with use of linearization table and latching feature. For easiest startup use $L1_{min} \ge 3$ " or as listed if greater and $L2_{min} \ge 3$ " (rod) or WH + 3" (cable).

2. Maximum probe lengths are limited as indicated in Probe Type table.

3. A one time startup adjustment is required to eliminate the effect of the nozzle. For details refer to the Blanking Parameter in the Commissioning section of the Installation & Operation Manual.

MT5000 Recommended Installation

NOTE: The following guidelines are very conservative. If you have an application that exceeds these limits consult factory for application recommendations.



[height of nozzle (H) less than width of nozzle (S)]					
MINIMUM DIELECTRIC CONSTANT	L MAXIMUM PROBE LENGTH ²	L1 Unmeasurable ¹	L2 Unmeasurable ¹ (WH = Weight Height)		
≤4	20 ft. / 6.1 m	H + 6 in. / 15.24 cm	3 in. / 7.6 cm (Rod) WH + 3 in. / 7.6 cm (Cable)		
10	40 ft. / 12.2 m	H + 3 in. / 7.6cm	2 ¹ (Rod)		
35	50 ft. / 15.2 m	H + 3 ¹ in. / 7.6 ¹ cm	WH + 3 in. / 7.6 cm (Cable)		

3B. SINGLE PROBE - NOZZLE & FLANGE³

- Depending on installation, L1 & L2 unmeasurable lengths of 0 may be possible 1. with use of linearization table and latching feature. For easiest startup use $L1_{min} \ge 3$ " or as listed if greater and $L2_{min} \ge 3$ " (rod) or WH + 3" (cable). Maximum probe lengths are limited as indicated in Probe Type table.
- 2.
- A one time startup adjustment is required to eliminate the effect of the nozzle. 3 For details refer to the Blanking Parameter in the Commissioning section of the Installation & Operation Manual.



4. SINGLE PROBE - PERMANENT STILLING WELL

MINIMUM DIELECTRIC CONSTANT	L MAXIMUM PROBE LENGTH ²	L1 Unmeasurable ¹	L2 Unmeasurable ¹ (WH = Weight Height)
≤ 1.7 ³	20 ft. / 6.1 m	8 in. / 20.3 cm	3 in. / 7.6 cm (Rod)
3	30 ft. / 9.1 m	6 in. / 15.2 cm	WH + 3 in. / 7.6 cm (Cable)
10	50 ft. / 15.2 m	3 in. / 7.6 cm	2 ¹ (Rod)
35	217 ft. / 66.1 m		WH + 3 in. / 7.6 cm (Cable)

- Depending on installation, L1 & L2 unmeasurable lengths of 0 may be possible 1. with use of linearization table and latching feature. For easiest startup use $L1_{min}$ \geq 3" or as listed if greater and L2_{min} \geq 3" (rod) or WH + 3" (cable).
- 2. Maximum probe lengths are limited as indicated in Probe Type table.
- Stilling well size will determine minimum dielectric constant. ULD mode can be 3. used for longer lengths up to 50 ft (15.2 m).



5. SINGLE PROBE - REMOVABLE STILLING WELL

MINIMUM DIELECTRIC CONSTANT	L MAXIMUM PROBE LENGTH ²	L1 Unmeasurable ¹	L2 Unmeasurable ¹ (WH = Weight Height)
≤ 1.7 ³	20 ft. / 6.1 m	8 in. / 20.3 cm	3 in. / 7.6 cm (Rod)
3	30 ft. / 9.1 m	6 in. / 15.2 cm	WH + 3 in. / 7.6 cm (Cable)
10	50 ft. / 15.2 m	3 in. / 7.6 cm	2 ¹ (Rod)
35	217 ft. / 66.1 m		WH + 3 in. / 7.6 cm (Cable)

1. Depending on installation, L1 & L2 unmeasurable lengths of 0 may be possible with use of linearization table and latching feature. For easiest startup use $L1_{min}$ \geq 3" or as listed if greater and L2_{min} \geq 3" (rod) or WH + 3" (cable).

- Maximum probe lengths are limited as indicated in Probe Type table. 2.
- Stilling well size will determine minimum dielectric constant. 3.

MT5000 Recommended Installation

NOTE: The following guidelines are very conservative. If you have an application that exceeds these limits consult factory for



6. SINGLE PR	5. SINGLE PROBE - EXTERNAL CHAMBER								
MINIMUM	L	L1	L2						
DIELECTRIC	MAXIMUM	Unmeasurable ¹	Unmeasurable ¹						
CONSTANT	PROBE LENGTH ²		(WH = Weight Height)						
≤ 1.7 ³	20 ft. / 6.1 m	9 in. / 22.86 cm							
3	30 ft. / 9.1 m	6 in. / 15.2 cm	3 in. / 7.6 cm (Rod)						
10	50 ft. / 15.2 m	3 in. / 7.5 cm	WH + 3 in. / 7.6 cm (Cable)						
35	217 ft. / 66.1 m								

Depending on installation, L1 & L2 unmeasurable lengths of 0 may be possible 1. with use of linearization table and latching feature. For easiest startup use $L1_{min}$ \geq 3" or as listed if greater and L2_{min} \geq 3" (rod) or WH + 3" (cable).

- 2. Maximum probe lengths are limited as indicated in Probe Type table.
- 3. Stilling well size will determine minimum dielectric constant. ULD mode can be used for longer lengths up to 50ft (15.2m).



MINIMUM DIELECTRIC CONSTANT	L MAXIMUM PROBE LENGTH ²	L1 Unmeasurable ¹	L2 Unmeasurable ¹
1.4		4 in. / 10.2 cm	
2.0	22 ft. / 6.7 m		2 in. / 5 cm

7. COAXIAL PROBE (rod inside of outer tube) clean liquids only]

4.0 Depending on installation, L1 & L2 unmeasurable lengths of 0 may be 1. possible with use of linearization table and latching feature. For easiest startup use $L1_{min} \ge 3$ " or as listed if greater and $L2_{min} \ge 3$ " (rod) or WH + 3" (cable).

2 in. / 5.1 cm

Maximum probe lengths are limited as indicated in Probe Type table. 2.

Typically used in low dielectric, clean liquids. 3.



Base Model for MT5000, MT5100 and MT5200 Transmitters

Base Model for MT5000, MT5100 and MT5200 Transmitters MT5000 Series Guide Wave Radar	MT5.	xxx	xxxx	xx	х	xx(x)
Device Type						
MT5000, Liquid Total Level Transmitter		000				
MT5100, Total Level and Interface Level Transmitter		100				
MT5200, Solids and Low Dielectric Liquid Total Level Transmitter		200				
Coupler Material						
None		•	Y			
316/L Stainless Steel (Standard)		:	S6*			
304/L Stainless Steel (Rigid Probe only)		:	54			
Hastelloy C-276		l	H1			
Hastelloy B3 (Rigid Probes only)			H3			
Monel		l	M4			
Titanium (Rigid Probes only)			Т2			
Inconel 625		l	N2			
Special			Z9			
Transmitter Configuration						
None				Y		
Local Transmitter (Standard)				L*		
Local Transmitter with Window Cover (Standard)				LW*		
Remote Mounted Electronics with Standard 5 ft Cable (Dielectric > 15)				R		
Remote Mounted Electronics with Window Cover and Standard 5 ft Cabl	e (Dielectric > 15)			RW		
Special				Z9		
Transmitter Housing None					Y	
Dual Compartment Aluminum Housing (Standard)					ч А*	
Dual Compartment 316 Stainless Steel Housing					s	
Special					Z	
Process Connection / Waveguide Coupler					2	
None						Y
0.75 in. NPT Process Connection Coupler Single / Coaxial Probe Teflon Ir	nsulator					C1*
0.75 in. NPT Process Connection Coupler Single / Coaxial Probe Teflon Ir	nsulator High Press	sure				C1H
1.50 in. NPT Process Connection Coupler Single / Coaxial Probe Teflon Ir	nsulator					C2*
1.50 in. NPT Process Connection Coupler Single / Coaxial Probe Teflon Ir	sulator High Press	sure				C2H
2.50 in. NPT Process Connection Coupler Single / Coaxial Probe Teflon Ir	nsulator					C3
1.50 in. NPT Process Connection HP/HT Coupler Single Probe/Coaxial Pr	obe Borosilicate G	lass Insu	lator			C8
1.0 in. NPT Process Connection HP/HT Coupler Single Probe/Coaxial Pro	be Alumina Ceram	ic Insula	tor			C9
Custom Coupler, consult factory						cz
* - Standard						

* - Standard

Base Model

MT5.xxx.xxxx.xx.x.xxx.)xxx(xxxxxx)
Process Seal Type	x(xxx)	
None	Y	
Viton FKM A O-Ring Process Seal -15 °F (-26 °C) Min Temp to 400 °F (204 °C) Max Temp Standard	V*	
Additional Hermetic Glass Feed-Through with Viton FKM A O-Ring Process Seal	SV^{1*}	
Kalrez 4079 O-Ring Process Seal -40 °F (-40 °C) Min Temp to 400 °F (204 °C) Max Temp	K*	
Additional Hermetic Glass Feed-Through with Kalrez 4079 O-Ring Process Seal	SK ¹ *	
EPDM O-Ring Process Seal -60 °F (-50 °C) Min Temp to 250 °F (125 °C) Max Temp	Е	
Additional Hermetic Glass Feed-Through with EPDM O-Ring Process Seal	SE ^{1*}	
Markez Z1319 O-Ring Process Seal -14 °F (-10 °C) Min Temp to 572 °F (300 °C) Max Temp	A*	
Additional Hermetic Glass Feed-Through with Markez Z1319 O-Ring Process Seal	SA ^{1*}	
Borosilicate process seal, C8 coupler only	B*	
Additional Hermetic Glass Feed-Through with Borosilicate Process Seal, C8 coupler only	SB ¹ *	
Special Process Seal	Z9	
Probe Type		-
None		Υ
Rod probes		
Single Rigid Rod Probe, 0.25 in. (6 mm) Outer Diameter, 20 ft (6.1 m) Max Standard Length		P01*
Single Rigid Rod Probe, 0.50 in. (13 mm) Outer Diameter, 20 ft (6.10 m) Max Standard Length		P02*
Single Rigid Rod Probe 0.375 in. (9 mm) Outer Diameter, 20 ft (6.1 m) Max Standard Length		P03*
Simi-Rigid Rod Probe 0.125 in. (3 mm) Outer Diameter 50 ft (15.24 m) Max Standard Length Includes W	/eight	P43
Cable probes Single Flexible Cable Probe 0.1875 in. (5 mm) Outer Diameter, 200 ft (61 m) Max Standard Length		P11*
Single Flexible Cable Probe 0.25 in. (6 mm) Outer Diameter, 200 ft (61 m) Max Standard Length		P12*
Triangle Cable Probe 0.25 in. (6 mm) Outer Diameter, 100 ft (30.5 m) Max Standard Length		P33
Single Flexible Cable Probe 0.31 in (8 mm) Outer Diameter, 200 ft (61 m) Max Standard Length		P61
Coaxial probes		
Coaxial Probe 0.875 in. (22 mm) Outer Diameter 22 ft (6.7.5 m) Max Standard Length		P51
Coaxial Probe 1.315 in. (34 mm) Outer Diameter 316SS only 22 ft (6.7.5 m) Max Standard Length		P71
Coaxial Probe 0.1875 in. (5 mm) Outer Diameter 316SS only 22 ft (6.7.5 m) Max Standard Length		P81
Coaxial Probe 1.00 in. (25 mm) Outer Diameter 22 ft (6.7.5m) Max Standard Length with compression	fitting	P91 ²

1. Hermetic seal required for E1 and E2 approvals

Custom Probe, consult factory

2. Maximum process pressure of 3.45 barg (50 psig)

* - Standard

PZZ

MT5000 Series Guide Wave Radar ordering information continued		
MT5.xxx.xxxx.xx.xx(x).x(xxx).	XXXX	xxxx xx
Probe end attachment		
None	Y	
Centering weights (cable probes only)		
0.875 in. (22.2 mm) O.D., 4.0 in. (101.6 mm) Weight Height, approx. 0.7 lbs (301 g)	W09*	
1.0 in. (25.4mm) O.D., 6.0 in. (152.4 mm) Weight Height, approx. 1.3 lbs (590 g)	W10*	
1.25 in. (31.75 mm) O.D., 3.5 in. (88.9 mm) Weight Height, approx. 0.8 lbs (317 g)	W13*	
1.625 in. (41.3mm) O.D., 2.0 in. (50.8 mm) Weight Height, approx. 1.1 lbs (499 g)	W16	
1.875 in. (47.6 mm) O.D., 2.0 in. (50.8 mm) Weight Height, approx. 1.5 lbs (680 g)	W19	
2.875 in. (73.3 mm) O.D., 1.0 in. (25.4 mm) Weight Height, approx. 1.8 lbs (816 g)	W29	
2.00 in. (50.8 mm) O.D., 6.0 in. (152.4 mm) Weight Height, approx. 2.2 lbs (998 g)	WS6	
1.5 in. (38.1 mm) O.D., 5.25 in. (133.35 mm) Weight Height, approx. 2.2 lbs (998 g)	W61	
Custom Centering Weight (consult factory)	W99	
Centering disks (rod probes only)		
1.50 in. (38.1 mm) O.D. approx 0.4375 in. (11 mm) Height 1.50 in. (38.1 mm) Min Stilling Well Size	D15	
2.0 in. (50.8 mm) O.D. approx 0.4375 in. (11 mm) Height 2.0 in. (50.8 mm) Min Stilling Well Size	D20	
2.3 in. (58.7 mm) O.D. approx 0.4375 in. (11 mm) Height 2.5 in. (63.5 mm) Min Stilling Well Size	D23	
2.8 in. (71.1 mm) O.D. approx 0.4375 in. (11 mm) Height 3.0 in. (76.2 mm) Min Stilling Well Size	D28	
3.75 in. (95.3 mm) O.D. approx 0.4375 in. (11 mm) Height 4.0 in. (101.6 mm) Min Stilling Well Size	D38	
3.75 in. (95.3 mm) O.D. approx 0.4375 in. (11 mm) Height 4.0 in. (101.6 mm) Min Stilling Well Size	D60	
Custom Centering Disk (consult factory)	D99	
Eyelets (cable probes only)		
Eyelet SS6 for 0.1875 in. (5 mm) O.D. Cable	E1	
Eyelet SS6 for 0.25 in. (6 mm) O.D. Cable	E2	
Special	Z9	
Probe Attachment Material		
None		Υ
316/L Stainless Steel, Standard		S6*
304/L Stainless Steel		S4
Hastelloy C-276		H1
Monel		M4
Inconel 600		N2
Special		Z9
Process Temperature Extension		
Process Temperature 32 °F (0 °C) to 250 °F (121 °C) Standard		Н
Temperature Extension, extends electronics additional 6 in. above process connection		H
Special		ZS

Base Model

MT5000 Series Guide Wave Radar ordering information continued				
MT5.xxx.xxx.xx.xx(x).x(xxx).xxxx.xxxx.xxx.	x(xxxx)	ххх	xxxx	ххх
Electronics Module	_			
None	Υ			
Total Level, Graphic Display, 4 20 mA Output, HART	M7A			
Total Level, Graphic Display, FOUNDATION fieldbus	M7AF			
Total and/or Interface Level, Graphic Display, 4 20 mA Output, HART	M7B			
Total and/or Interface Level, Graphic Display, FOUNDATION fieldbus	M7BF			
Special	Z9			
Agency Approvals		_		
General purpose		Y0		
IECEx Intrinsically safe		E1		
IECEx Flameproof		E2		
FM / CSA Intrinsically safe		N1		
FM / CSA Explosion proof Housing		N2		
Special		Z9		
Process Connection Type				
None			Y0	
Integral Thread, Standard Process Connection			P4*	
Welded Process Connection			P2	
Loose flange for use with NPT threads. Specify flange type, material, and rating			P3	
Special			Z9	
Process Connection Material				
None			,	Y
304/L Stainless Steel			:	S4
316/L Stainless Steel			9	S6*
Carbon Steel			(C1
Hastelloy C-276			I	H1
Alloy 20				A2
Monel 400			I	M4
Super Duplex Stainless Steel			I	D2
Special			2	Z9

Base Model MT5000 Series Guide Wave Radar ordering information continued	
MT5.xxx.xxxx.xx.xx(x).x(xxx).xxxx.xxxx.xxx	хххх
Flange or Plug Size // Rating / Type	
None	Y
3/4" MNPT Threaded (C1, C1H process couplers)	NTBN*
1.0" MNPT Threaded (C9 process coupler)	NTCN*
1.5" MNPT Threaded (C2, C2H and C8 process couplers)	NTEN*
2.5" MNPT Threaded (C3 process coupler)	NTGN
3/4" G thread, British Pipe Thread (BSPP), (C1, C1H process couplers)	GTBN
1.0" G thread, British Pipe Thread (BSPP), (C9 process coupler)	GTCN
1.5" G thread, British Pipe Thread (BSPP), (C2, C2H and C8 process couplers)	GTEN
2.5" G thread, British Pipe Thread (BSPP), (C3 process coupler)	GTGN
1 in. // ANSI / ASME Class 150 // Raised Face Flange	R11
1 in. // ANSI / ASME Class 300 // Raised Face Flange	R13
1 in. // ANSI / ASME Class 600 // Raised Face Flange	R16
1.5 in. // ANSI / ASME Class 150 // Raised Face Flange	R151
1.5 in. // ANSI / ASME Class 300 // Raised Face Flange	R153
1.5 in. // ANSI / ASME Class 600 // Raised Face Flange	R156
2 in. // ANSI / ASME Class 150 // Raised Face Flange	R21
2 in. // ANSI / ASME Class 300 // Raised Face Flange	R23
2 in. // ANSI / ASME Class 600 // Raised Face Flange	R26
2.5 in. // ANSI / ASME Class 150 // Raised Face Flange	R251
2.5 in. // ANSI / ASME Class 300 // Raised Face Flange	R253
2.5 in. // ANSI / ASME Class 600 // Raised Face Flange	R256
3 in. // ANSI / ASME Class 150 // Raised Face Flange	R31
3 in. // ANSI / ASME Class 300 // Raised Face Flange	R33
3 in. // ANSI / ASME Class 600 // Raised Face Flange	R36
4 in. // ANSI / ASME Class 150 // Raised Face Flange	R41
4 in. // ANSI / ASME Class 300 // Raised Face Flange	R43
4 in. // ANSI / ASME Class 600 // Raised Face Flange	R46
6 in. // ANSI / ASME Class 150 // Raised Face Flange	R61
6 in. // ANSI / ASME Class 300 // Raised Face Flange	R63
6 in. // ANSI / ASME Class 600 // Raised Face Flange	R66
DN 25 // PN 25 // Raised Face Flange	D2525
DN 25 // PN 40 // Raised Face Flange	D2540
DN 32 // PN 25 // Raised Face Flange	D3225

Note: DIN flanges are per EN1092-1

MT5000 Series Guide Wave Radar ordering information continued	
MT5.xxx.xxxx.xx.xx(x).x(xxx).xxxx.xxxx.xxx	xxxx
Flange or Plug Size // Rating / Type - Continued from previous page	
DN 32 // PN 40 // Raised Face Flange	D3240
DN 40 // PN 25 // Raised Face Flange	D4025
DN 40 // PN 40 // Raised Face Flange	D4040
DN 50 // PN 25 // Raised Face Flange	D5025
DN 50 // PN 40 // Raised Face Flange	D5040
DN 65 // PN 25 // Raised Face Flange	D6525
DN 65 // PN 40 // Raised Face Flange	D6540
DN 80 // PN 25 // Raised Face Flange	D8025
DN 80 // PN 40 // Raised Face Flange	D8040
DN 100 // PN 25 // Raised Face Flange	D10025
DN 100 // PN 40 // Raised Face Flange	D10040
DN 125 // PN 25 // Raised Face Flange	D12525
DN 125 // PN 40 // Raised Face Flange	D12540
DN 150 // PN 25 // Raised Face Flange	D15025
DN 150 // PN 40 // Raised Face Flange	D15040
1.0 in. // ANSI / ASME Class 3000 // NPT-m Hex Plug	P1
1.5 in. // ANSI / ASME Class 3000 // NPT-m Hex Plug	P15
2.0 in. // ANSI / ASME Class 3000 // NPT-m Hex Plug	P2
2.5 in. // ANSI / ASME Class 3000 // NPT-m Hex Plug	P25
3.0 in. // ANSI / ASME Class 3000 // NPT-m Hex Plug	P3
Any flange not listed above, consult factory	Z9

Note: DIN flanges are per EN1092-1

Option codes are on the following page.

Option codes follow the model code with a dash (-)

MT5000 Series guided wave radar tran	smitter additional option codes					
Additional options	MT5.xxx.xx(x).x(xx)x.xx.xxx(xx).x(x).xx(x)-	ххх	xxx	xxx	xxxx	xx
Additional Approvals or Certifications		_				
Furnished with CRN data package (inclu	udes tagging, MTR and hydro tests)	CRN				
Nuclear use, device to be used in a nucl	ear facility (application must be reviewed by ABB)	P4				
Special		CLZ				
Sensor options			_			
Electro-polish finish on wetted metal se	urfaces (not possible with cable or coax probe designs)		SEL			
240 grit polish on wetted metal surface	es (not possible with cable or coax probe designs)		SEP			
Add Teflon sleeve on probe for slip resi	stance only, not for corrosion resistance		SEN			
Add 1/4" purge or flush port (requires e	extended process coupler)		SEB			
Extended process coupler, specify dista	ance		SE1			
Segment probe into 10ft sections, spec	cific rod and coax probe selections		SE3			
Degreased (oil and grease free) for oxy	gen or chlorine service		P1			
Sensor special			SEZ			
Target float options						
Add 316L target float, minimum fluid sp	pecific gravity 0.6			FT1		
Special target float per application req	uirements			FZ9		
Remote electronics signal cable length	(For remote coupler only)					
1.5 m (approx. 5 ft)					SRW	
3 m (approx. 9.8 ft)					SRT	
5 m (approx. 16.4 ft)					SR1	
Custom coaxial remote length					SRZ	
Repeat Indicator (for two analog level	outputs)					
RI100 remote indicator (HART only), rec housing	quires additional 4-20 loop, same material as transmitter					AR

Option codes continue on the following page.

Option codes follow the model code with a dash (-)

MT5000 Series guided wave radar transmitter additional option codes							0
Additional options MT5.xxx.xx(x).x(xx)x.xxxx(xx).x(x).xx(x)-xxx.xxx.xxx.xxx.xxx.xxx.	ххх	xx	хххх	xx	ххх	хх	ххх
Add rod extension rod to probe (material and diameter determined by coupler selection)							
152.4 mm (6.0 in)	AR1						
304.8 mm (12.0 in.)	AR2						
457.2 mm (18 in.)	AR3						
Special	AR9						
Mounted Accessories							
Centering spacers as specified separately on order		AS					
Centering disk for cable weight (cable probes only, disk material same as weight)							
1.50 in. (38.1 mm) O.D.; 1.50 in. (38.1 mm) Min Stilling Well Size			WD1				
2.0 in. (50.8 mm) O.D.; 2.0 in. (50.8 mm) Min Stilling Well Size			WD2				
2.3 in. (58.7 mm) O.D.; 2.5 in. (63.5 mm) Min Stilling Well Size			WD3				
2.8 in. (71.1 mm) O.D.; 3.0 in. (76.2 mm) Min Stilling Well Size			WD4				
3.75 in. (95.3 mm) O.D.; 4.0 in. (101.6 mm) Min Stilling Well Size			WD5				
4.0 in. (101.6 mm) O.D.; 5.0 in. (125 mm) Min Stilling Well Size			WD6				
Custom disk for cable weight (consult factory)			WDZ				
Device Identification Plate							
Add stainless steel hang tag with custom tag no.				Τ1			
Add stainless steel hang tag, custom markings 4 lines, 22 characters per line				тs			
Other tagging special				ΤZ			
Electrical Connector Type							
Fieldbus 7/8 in. (without mating plug)					U1		
Fieldbus M12 x 1 (without mating plug)					U2		
M20 stainless steel adapter					U8		
M20 brass adaptor					U9		
Electrical Connector Special					UZ		
Surge Protector							
Surge / Transient protector						S1	
Special Other							
Transmitter Special Option							STT
Tower length extension special length - meter insulation capability							TEZ
Special paint or treatment on housing							ST⊦
Special paint or treatment on flange							STF

Additional requirements and order comments are continued on the following page.

All codes located behind the // are for additional requirements and order comments.

These codes will not be included on the device tag.

All codes located behind the // are for additional requirements and order comments.

These codes will not be included on the device tag.

MT5000 Series guided wave radar additional option codes			
Additional requirements and order comments	MT5x//	xx	xxx
Certificates			
Test report 2.2 acc. EN 10204		C1	
MTR 3.1, Material monitoring with inspection certificate 3.1 acc. EN	10204	C2	
MTR 3.2, Material monitoring with inspection certificate 3.2 acc. EN	10204	C3	
Declaration of compliance with the order 2.1 acc. EN 10204		C4	
Material monitoring NACE MR 0175, MR 0103 with inspection certific	cate 3.1 acc. EN 10204	CN	
Printed record of configured settings in transmitter		CG	
With hydrostatic test report		СН	
With PMI report on wetted metal materials		CJ	
Other certificates		CZ	
Drawings			_
Drawings for approval required prior to construction			GD1
Drawings for record required			GD2
Certified as built drawings required			GD3
Other drawings			GDZ

Additional requirements and order comments are continued on the following page.

All codes located behind the // are for additional requirements and order comments. These codes will not be included on the device tag.

Additional Requirements and coder comments	MT5x//xx.xx.xx.xx.	xx	xx	xx
Documentation Language (installation, operation and n	naintenance manual)			
German		M1		
Italian		M2		
Spanish		М3		
French		M4		
English		M5		
Russian		MB		
Others		MZ		
Calibration Type				
3-point calibration verification certificate, factory defau or customer specified points within measurable zone	lt 90, 50 and 10% of measurable zone,		R3	
5-point calibration verification certificate, factory defau or customer specified points within measurable zone	lt 90, 75, 50, 25 and 10% of measurable zone,		R5	
Custom Linearization or Strapping table entered (up to	20 pts).		RL	
Witnessed calibration with certificate			RW	
Special calibration			RZ	
Programming and Parameter Settings				_
Custom parameter settings				N6
Software Special				
Specified software version				
Custom software version				

Pro	ha		ath
FIU	De	Len	gui

Flobe Length	
Minimum 24 in.	in.
Minimum 609.6 mm	mm

Contact us

ABB Inc. Measurement & Analytics

3400. Rue Pierre-Ardouin Québec, Québec G1P 0B2 CANADA Office Phone: +1 418.877.2944 ext. 2109 Direct Line : +1 581.628.2109 E-mail: Radars@ca.abb.com

www.abb.com/level

ABB Measurement & Analytics

No. 5, Lane 369, Chuangye Road, Kangqiao Town, Pudong District Shanghai, 201319, P.R. China Tel: +86 10 64231407 Fax: +86 10 64371913

www.abb.com/level

Note

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents - in whole or in parts – is forbidden without prior written consent of ABB.

Copyright © 2020 ABB All rights reserved