



ADDENDUM – 2020

Electrical installation solutions for buildings – Technical details

Complementary volume to the catalogue
“Electrical installation solutions
for buildings”



- Detailed product specification and characteristics
- Operating curves, connection diagrams, application examples etc.

MINIATURE
CIRCUIT-BREAKERS

RESIDUAL CURRENT
DEVICES

ARC FAULT DETECTION
DEVICES

PROTECTION
AND SAFETY

COMMAND AND
SIGNALING

CONTROL AND
AUTOMATION

ENERGY EFFICIENCY

PLUG-IN SYSTEMS

LIGHT SWITCHES AND
SOCKET OUTLETS

ABB I-BUS® KNX

INTRUSION ALARM
SYSTEMS

CONSUMER UNITS

AUTOMATION BOARDS

JUNCTION BOXES

Electrical installation solutions for buildings

Technical details

1

2

3

5

6

7

8

9

10

11

14

17

19

20

21

Two volumes, one objective: to always find the best solution

From a single catalogue with two complementary volumes: streamline to simplify, analyse to choose.

The catalog Electrical installation solutions for buildings comes in two separate but integrated volumes: one dedicated to the description and easy selection of products code and one for professionals searching for in-depth details and specifications, installation examples and special technical solutions.



Electrical installation solutions for buildings
An indispensable tool for those who are looking for easy selection of a completely reliable range of products

The main catalogue summarizes all the technical-commercial characteristics of the products, allows one to navigate between the main characteristics, descriptions, specifications, accessories, product pictures, illustrations and information about the individual codes.

The catalogue is a helpful product guide, which makes easier the orientation in a very complex product range of ABB products for electrical installation in buildings.

Electrical installation solutions for buildings - Technical details
Technical details and information, application examples, installation solutions: the complete ABB know how at the service of professionals

The technical addendum dedicated to technical-applicative details provides professionals with a series of specialized information such as the operating curve, selectivity tables, connection diagrams, etc. The numbers of chapters in the technical addendum match with the same chapters in the main catalog.



Two volumes that reference each other, which are manageable and easily consultable, designed for those who wish to find the clearest solution in the least possible time.

MCBs
S 200 series B characteristic

S 200 B characteristic
Function: Protection and control of the circuits against overloads and short-circuits; protection for people and large length of cables in TN and IT systems.
Applications: residential, commercial and industrial.
Protection IEC/EN 60898-2, IEC/EN 60947-2
Short-circuit rating 6 kA

Number of poles	In A	Rated current	Bln	Order details	Price	Weight	Pack unit
1	6	464902	S201-B6	ZCDS200B000002	0.125	10	
1	6	464903	S201-B6	ZCDS200B000003	0.125	10	
1	10	464907	S201-B10	ZCDS200B000015	0.125	10	
1	13	465007	S201-B13	ZCDS200B000015	0.125	10	
1	16	579459	S201-B16	ZCDS200B000015	0.125	10	
1	20	717011	S201-B20	ZCDS200B000015	0.125	10	
1	25	465020	S201-B25	ZCDS200B000015	0.125	10	
1	32	465024	S201-B32	ZCDS200B000015	0.125	10	
1	40	465028	S201-B40	ZCDS200B000015	0.125	10	
1	50	550925	S201-B50	ZCDS200B000015	0.125	10	
1	63	550932	S201-B63	ZCDS200B000015	0.125	10	

Number of poles	In A	Rated current	Bln	Order details	Price	Weight	Pack unit
2	6	464910	S202-B6	ZCDS200B000005	0.250	5	
2	6	464900	S202-B6	ZCDS200B000005	0.250	5	
2	10	464905	S202-B10	ZCDS200B000005	0.250	5	
2	13	464909	S202-B13	ZCDS200B000005	0.250	5	
2	16	464905	S202-B16	ZCDS200B000005	0.250	5	
2	20	477051	S202-B20	ZCDS200B000005	0.250	5	
2	25	465023	S202-B25	ZCDS200B000005	0.250	5	
2	32	465027	S202-B32	ZCDS200B000005	0.250	5	
2	40	467407	S202-B40	ZCDS200B000005	0.250	5	
2	50	550926	S202-B50	ZCDS200B000005	0.250	5	
2	63	550956	S202-B63	ZCDS200B000005	0.250	5	

Number of poles	In A	Rated current	Bln	Order details	Price	Weight	Pack unit
3	6	464912	S203-B6	ZCDS200B000002	0.375	1	
3	6	464903	S203-B6	ZCDS200B000005	0.375	1	
3	10	464909	S203-B10	ZCDS200B000015	0.375	1	
3	13	464909	S203-B13	ZCDS200B000015	0.375	1	
3	16	464905	S203-B16	ZCDS200B000015	0.375	1	
3	20	717011	S203-B20	ZCDS200B000015	0.375	1	
3	25	465023	S203-B25	ZCDS200B000015	0.375	1	
3	32	465027	S203-B32	ZCDS200B000015	0.375	1	
3	40	467407	S203-B40	ZCDS200B000015	0.375	1	
3	50	550923	S203-B50	ZCDS200B000015	0.375	1	
3	63	550970	S203-B63	ZCDS200B000015	0.375	1	

* Use Solder Free Flame-type breakers 12 kW
** Use Solder Free Flame-type breakers 20 kW
*** Use Solder Free Flame-type breakers 32 kW

40967799 * Suitable for Flame-type breakers 12 kW
40967799 * Suitable for Flame-type breakers 20 kW
40967799 * Suitable for Flame-type breakers 32 kW

1/26 ELECTRICAL INSTALLATION SOLUTIONS FOR BUILDINGS 2CHC 000 000 000 0001

1/27 ELECTRICAL INSTALLATION SOLUTIONS FOR BUILDINGS 2CHC 000 000 000 0001

The volume
Electrical installation
solutions for buildings
can be downloaded here



TIP:

You can always find a detailed online information about the particular product item:

Just type down this URL address: <http://new.abb.com/products/2CDS274337R0158>



With disconnecting neutral NA

Number of poles	In A	Rated current	Bln	Order details	Price	Weight	Pack unit
1+NA	6	531507	S201-NA6	ZCD2S100B000005	0.250	5	
1+NA	10	531507	S201-NA10	ZCD2S100B000005	0.250	5	
1+NA	13	531503	S201-NA13	ZCD2S100B000005	0.250	5	
1+NA	16	531503	S201-NA16	ZCD2S100B000005	0.250	5	
1+NA	20	717027	S201-NA20	ZCD2S100B000005	0.250	5	
1+NA	25	531534	S201-NA25	ZCD2S100B000005	0.250	5	
1+NA	32	531534	S201-NA32	ZCD2S100B000005	0.250	5	
1+NA	40	531535	S201-NA40	ZCD2S100B000005	0.250	5	
1+NA	50	531518	S201-NA50	ZCD2S100B000005	0.250	5	
1+NA	63	530941	S201-NA63	ZCD2S100B000005	0.250	5	

Number of poles	In A	Rated current	Bln	Order details	Price	Weight	Pack unit
2+NA	6	531507	S202-NA6	ZCD2S100B000005	0.250	5	
2+NA	10	531507	S202-NA10	ZCD2S100B000005	0.250	5	
2+NA	13	531503	S202-NA13	ZCD2S100B000005	0.250	5	
2+NA	16	531503	S202-NA16	ZCD2S100B000005	0.250	5	
2+NA	20	717027	S202-NA20	ZCD2S100B000005	0.250	5	
2+NA	25	531534	S202-NA25	ZCD2S100B000005	0.250	5	
2+NA	32	531534	S202-NA32	ZCD2S100B000005	0.250	5	
2+NA	40	531535	S202-NA40	ZCD2S100B000005	0.250	5	
2+NA	50	531518	S202-NA50	ZCD2S100B000005	0.250	5	
2+NA	63	530972	S202-NA63	ZCD2S100B000005	0.250	5	

* Suitable for Flame-type breakers 12 kW
** Suitable for Flame-type breakers 20 kW
*** Suitable for Flame-type breakers 32 kW

Arguments developed
in the same logical
sequence

Same
reference
heading

MCBs technical details
Tripping characteristics

Characteristic B (IEC standard)
Characteristic C (IEC standard)
Characteristic D (IEC standard)
Characteristic E (IEC standard)
Characteristic K (IEC standard)

Graphs showing tripping characteristics for S 200 series MCBS models, comparing Characteristic B, C, D, E, and K across different current ranges (6A, 10A, 13A, 16A, 20A, 25A, 32A, 40A, 50A, 63A).

The volume
Electrical installation
solutions for buildings -
Technical details
can be downloaded here



Electrical installation solutions for buildings – Technical details

MCBs

Index

Definitions according to standards for miniature circuit breakers	1/2
Tripping characteristics	1/4
Limitation of specific let-through energy I^2t	1/16
Peak current I_p	1/35
SOC - Selected Optimized Coordination	1/46
Coordination tables: back-up	1/47
Coordination tables: selectivity	1/82
MCBs internal resistance, power loss and max. permissible earth-fault loop impedance	1/165
Performances at different ambient temperatures, altitudes and frequencies	1/172
Use of MCBs in direct current circuits	1/181
S 200 UDC series DC Applications	1/182
S 200 MUC series AC/DC Applications	1/184
S800 series DC applications	1/185
Use of MCBs in altitude and different network frequency	1/188
Instruction for use of S 200 S	1/189
Particular supply sources and loads	1/190
S800 range features	1/195
S800-SCL range features	1/198

MCBs technical details

Definitions according to standards for miniature circuit breakers

Rated insulation voltage (Ui) according IEC/EN 60664-1:

Root mean square (R.M.S.) withstand voltage value assigned by the manufacturer to the equipment or to a part of it, characterizing the specified (long-term) withstand capability of its insulation.

NOTE:

The rated insulation voltage is not necessarily equal to the rated voltage of the equipment which is primarily related to functional performance.

IEC/EN 60898-1

Miniature Circuit Breakers according IEC/EN 60898-1 are intended for the protection against overcurrents of wiring installations of buildings and similar applications; they are designed for use by uninstructed people and for not being maintained. This part of IEC/EN 60898 applies for a.c. air-break circuit-breakers for operation at 50 Hz or 60 Hz, having a rated voltage not exceeding 440 V (between phases), a rated current not exceeding 125 A and a rated short-circuit capacity not exceeding 25.000 A.

As far as possible, it is in line with the requirements contained in IEC/EN 60947-2.

Rated short-circuit capacity (Icn)

The rated short-circuit capacity of a circuit-breaker is the value of the ultimate short-circuit breaking capacity assigned to that circuit-breaker by the manufacturer. The sequence of operations shall be: O – t – CO.*

Service short-circuit capacity (Ics)

A circuit-breaker having a given rated short-circuit capacity has a corresponding fixed service short-circuit capacity (Ics). This is therefore generally not indicated.

Rated operational voltage (Un)

The rated voltage of a circuit-breaker is the value of voltage, assigned by the manufacturer, to which its performance (particularly the short-circuit performance) is referred. The same circuit-breaker may be assigned a number of rated voltages and associated rated short-circuit capacities.

2The voltage which appears across the terminals of a pole of a circuit-breaker after the breaking of the current.

The value of the power frequency recovery voltage shall be equal to 110% of the rated voltage of the circuit-breaker under test.

IEC/EN 60947-2

This part of the IEC/EN 60947 applies to circuit-breakers, the main contacts of which are intended to be connected to circuits, the rated voltage of which does not exceed 1.000 V a.c. or 1.500 V d.c..

It applies whatever the rated currents, the method of construction or the proposed applications of the circuit-breakers may be.

The circuit-breakers are designed for use by instructed people.

Rated ultimate short-circuit breaking capacity Icu

The rated ultimate short-circuit breaking capacity of a circuit-breaker is the value of ultimate short-circuit breaking capacity assigned to that circuit-breaker by the manufacturer for the corresponding rated operational voltage. It is expressed as the value of the prospective breaking current, in kA (r.m.s. value of the a.c. component in the case of a.c.).

The sequence of operations shall be: O – t – CO.*

Rated service short-circuit breaking capacity Ics

The rated service short-circuit breaking capacity of a circuit-breaker is the value of service short-circuit breaking capacity assigned to that circuit-breaker by the manufacturer for the corresponding rated operational voltage. It is expressed as a value of prospective breaking current, in kA, corresponding to one of the specified percentages of the rated ultimate short-circuit breaking capacity and rounded up to the nearest whole number. It may be expressed as a % of Icu (for example Ics = 25 % Icu).

The sequence of operations shall be: O – t – CO – t – CO.*

- * The following symbols are used for defining the sequence of operations:
 - O represents an opening operation.
 - CO represents a closing operation followed by an automatic opening.
 - t represents the time interval between two short-circuit operations.

MCBs technical details

Definitions according to standards for miniature circuit breakers

Rated operational voltage (Ue)

The rated operational voltage of an equipment is a value of voltage which, combined with a rated operational current, determines the application of the equipment and to which the relevant tests and the utilization categories are referred. For single-pole equipment it is generally stated as the voltage across the pole. For multi pole equipment it is generally stated as the voltage between phases.

An equipment may be assigned a number of combinations of rated operational voltage and associated making and breaking capacities for different duties and utilization categories.

Max. power frequency recovery voltage (Umax)

Voltage which appears across the terminals of a pole of a switching device after the breaking of the current.

For all breaking capacities and short-circuit breaking capacity tests, the value of the power-frequency recovery voltage shall be 105 % of the value of the rated operational voltage. This value shall be within the specified tolerance (voltage 0 / + 5%).

NOTE:

The value of 1.05 times the rated operational voltage for the power frequency recovery voltage, together with the test voltage tolerance resulting in a maximum voltage of 1.1 times the rated operational voltage, is deemed to cover the effects of variations of the system voltage under normal service conditions.

UL 489

The requirements of this standard cover molded-case circuit breakers, circuit breaker and ground-fault circuit-interrupters, fused circuit breakers, and accessory high-fault protectors.

These circuit breakers are specifically intended to provide service entrance, feeder, and branch circuit protection in accordance with the National Installation Codes in Annex B, Ref. No.1.

This standard also covers instantaneous-trip circuit breakers (circuit interrupters) specifically intended for use as part of a combination motor controller in accordance with the National Installation Codes in Annex B, Ref. No. 1.

UL489B

These requirements cover molded-case circuit breakers, molded-case switches, and circuit-breaker enclosures rated up to 1000 V dc, intended for use with photovoltaic (PV) systems and Article 690 of the National Electrical Code, ANSI/NFPA-70. These requirements are intended to be used in conjunction with the requirements in the Standard for Molded-Case Circuit Breakers, Molded-Case Switches and Circuit-Breaker Enclosures, UL 489.

UL 1077

These requirements apply to supplementary protectors intended for use as overcurrent, or over- or under-voltage protection within an appliance or other electrical equipment where branch circuit overcurrent protection is already provided, or is not required.

Compliance with this standard is acceptable for use as a component of an end product.

MCBs technical details

Tripping characteristics

Tripping characteristics S 200 / S 200 M / S 200 P / S 200 S / S 200 MUC / SN 201 L / SN 201 / SN 201 M

Acc. to	Tripping characteristic and rated current	Thermal release ②		Tripping time	Electromagnetic release ①		Tripping time
		Current: conventional non-tripping current	conventional tripping current		Currents: hold current surges	trip at least at	
IEC/EN 60898-1	B	6 to 63 A	1.13 · In	> 1 h	3 · In		> 0.1 s
			1.45 · In	< 1 h	5 · In		< 0.1 s
	C	0.5 to 63 A	1.13 · In	> 1 h	5 · In		> 0.1 s
			1.45 · In	< 1 h	10 · In		< 0.1 s
	D	0.5 to 63 A	1.13 · In	> 1 h	10 · In		> 0.1 s
			1.45 · In	< 1 h	20 · In		< 0.1 s
IEC/EN 60947-2	K	0.2 to 63 A	1.05 · In	> 1 h	10 · In		> 0.2 s
			1.2 · In	< 1 h ③	14 · In		< 0.2 s
			1.5 · In	< 2 min. ③			
			6.0 · In	> 2 s (T1)			
	Z	0.5 to 63 A	1.05 · In	> 1 h	2 · In		> 0.2 s
			1.2 · In	< 1 h ③	3 · In		< 0.2 s

① The indicated electromagnetic tripping values apply to a frequency range of 16 2/3 ... 60 Hz. For different network frequencies or direct current the values change according to the multiplier in the table below

② The thermal releases are calibrated to a nominal reference ambient temperature; for Z and K, the value is 20 °C, for B and C = 30 °C. In the case of higher ambient temperatures, the current values fall by ca. 6 % for each 10 K temperature rise.

③ As from operating temperature (after $I_1 > 1$ h or, as applicable, 2 h).

	AC	DC		
	100 Hz	200 Hz	400 Hz	
Multiplier	1.1	1.2	1.5	1.5

The thermal tripping performance is independent from the network frequency

Tripping characteristics SU200 M

Acc. to	Tripping characteristics	Rated current	Thermal release ①)		Tripping time	Electromagnetic release ②)		Tripping time
			Currents: conventional non-tripping current	conventional tripping current		Range of instantaneous tripping		
UL 489	C	0.5 to 63 A	In	I1	I2			
				1.03 · In	> 1 h	5 · In		> 0.2 s
	K	0.2 to 63 A		1.25 · In	< 1 h ③)		10 · In	< 0.2 s
				1.03 · In	> 1 h	10 · In		> 0.2 s
	Z	0.5 to 63 A		1.25 · In	< 1 h ③)		14 · In	< 0.2 s
				1.03 · In	> 1 h	2 · In		> 0.2 s
				1.25 · In	< 1 h ③)		3 · In	< 0.2 s

①) The thermal releases are calibrated to a nominal reference ambient temperature e.g. for UL 489 of 40°C.

In the case of higher ambient temperatures, the current values fall by approx. 4 % for each 10 K temperature rise.

②) The indicated tripping values of electromagnetic tripping devices apply to a frequency of 50/60 Hz. The thermal release operates independent of frequency.

③) As from operating temperature (after $I_1 > 1$ h)

MCBs technical details

Tripping characteristics

Tripping characteristics S200 80-100A

Acc. to	Tripping characteristics	Rated current	Thermal release ¹⁾			Electromagnetic release ²⁾		
			Currents:		Tripping time	Range of instantaneous tripping	Tripping time	
			conventional non-tripping current	conventional tripping current				
		In	I ₁	I ₂				
IEC/EN 60898-1	B	80 up to 100 A	1.13 · In		> 2 h	3 · In	0.1 ... 90 s	
				1.45 · In	< 2 h	5 · In	< 0.1 s	
	C	80 up to 100 A	1.13 · In		> 2 h	5 · In	0.1 ... 30 s	
				1.45 · In	< 2 h	10 · In	< 0.1 s	

¹⁾ The thermal releases are calibrated to a nominal reference ambient temperature; for B and C the reference value is 30 °C.

In the case of higher ambient temperatures, the current values fall by approx. 6 % for each 10 K temperature rise.

²⁾ The indicated tripping values of electromagnetic tripping devices apply to a frequency of 50/60 Hz. The thermal release operates independent of frequency.

Tripping characteristics S 700

Tripping characteristic	Rated current	Delayed overload tripping			Short-time delayed selective tripping		
		Conventional non-tripping current	Conventional tripping current	Tripping time	Delayed tripping	Short-time delayed tripping	Tripping time
		I _{nt}	I _t	t	I _{tv}	I _{tk}	t
E _{selective}	10 to 100 A	1.05 x In		≥ 2 h	5 x In		0.05 s < t < 5 s (In ≤ 32 A) 0.05 s < t < 10 s (In > 32 A)
			1.2 x In	< 2 h		6.25 x In	0.01 s < t < 0.3 s
K _{selective}	16 to 50 A	1.05 x In		≥ 2 h	10 x In		0.05 s < t < 5 s (In ≤ 32 A) 0.05 s < t < 10 s (In > 32 A)
			1.2 x In	< 2 h		14 x In	0.01 s < t < 0.3 s
	63 to 100 A	1.05 x In		≥ 2 h	8 x In		0.05 s < t < 10 s
			1.2 x In	< 2 h		12 x In	0.01 s < t < 0.3 s

Tripping characteristics S 750 DR

Tripping characteristic	Reference ambient temperature	Delayed overload tripping			Short-time delayed selective tripping		
		Conventional non-tripping current	Conventional tripping current	Tripping time	Delayed tripping	Short-time delayed tripping	Tripping time
		I _{nt}	I _t	t	I _{tv}	I _{tk}	t
E _{selective}	30 °C	1.05 x In		≥ 2 h	5 x In		0.05 s < t < 5 s (In ≤ 32 A) 0.05 s < t < 10 s (In > 32 A)
			1.2 x In	< 2 h		6.25 x In	0.01 s < t < 0.3 s
K _{selective}	20 °C	1.05 x In		≥ 2 h	8 x In		0.05 s < t < 10 s
			1.2 x In	< 2 h		12 x In	0.01 s < t < 0.3 s

¹⁾ Reference ambient temperature 30 °C (in the case of higher ambient temperatures, the current values are reduced by ca. 5 % per each 10 K)

MCBs technical details

Tripping characteristics

Tripping characteristic S800

Acc. to	Tripping characteristic and rated current	Thermal release ②		Tripping time	Electromagnetic release ①		Tripping time
		Current conventional non-tripping current	conventional tripping current		Current hold current	trip at least at surges	
IEC/EN 60898-1	B 10 to 80 A	1.13 · In		> 1 h	3 · In		> 0.1 s
			1.45 · In	< 1 h		5 · In	< 0.1 s
	C 10 to 80 A	1.13 · In		> 1 h	5 · In		> 0.1 s
			1.45 · In	< 1 h		10 · In	< 0.1 s
	D 10 to 80 A	1.13 · In		> 1 h	10 · In		> 0.1 s
			1.45 · In	< 1 h		20 · In	< 0.1 s
IEC/EN 60947-2	B 0.5 to 125 A	1.05 · In		> 1 h	3.2 · In		> 0.1 s
			1.3 · In	< 1 h		4.8 · In	< 0.1 s
	C 0.5 to 125 A	1.05 · In		> 1 h	6.4 · In		> 0.1 s
			1.3 · In	< 1 h		9.6 · In	< 0.1 s
	D 0.5 to 125 A	1.05 · In		> 1 h	10.4 · In		> 0.1 s
			1.3 · In	< 1 h		15.6 · In	< 0.1 s
	K 0.5 to 125 A	1.05 · In		> 1 h	10.4 · In		> 0.1 s
			1.2 · In	< 1 h		15.6 · In	< 0.1 s
	KM 20 to 80 A				10.4 · In		> 0.1 s
						15.6 · In	< 0.1 s
	UCB (DC only) 0.5 to 125 A	1.05 · In		> 1 h	4.8 · In		> 0.1 s
			1.3 · In	< 1 h		7.2 · In	< 0.1 s
UL489	UCK (DC only) 0.5 to 125 A	1.05 · In		> 1 h	8.8 · In		> 0.1 s
			1.2 · In	< 1 h		13.2 · In	< 0.1 s
	PV-SP (DC only) 5 to 125 A	1.05 · In		> 1 h	4.8 · In		> 0.1 s
			1.3 · In	< 1 h		6 · In	< 0.1 s
	Z 10 to 100 A	1 · In		> 1 h	3.2 · In		> 0.1 s
			1.35 · In	< 1 h		4.8 · In	< 0.1 s
	K 10 to 100 A	1 · In		> 1 h	10.4 · In		> 0.1 s
			1.35 · In	< 1 h		15.6 · In	< 0.1 s
	UCZ (DC only) 10 to 80 A	1 · In		> 1 h	8.8 · In		> 0.1 s
			1.35 · In	< 1 h		13.2 · In	< 0.1 s
UL489B	PV-S (DC only) 5 A	1.13 · In		> 1 h	4.8 · In		> 0.1 s
			1.3 · In	< 1 h		6 · In	< 0.1 s

① The indicated electromagnetic tripping values apply to a frequency of 50/60 Hz.

② The thermal release are calibrated to a nominal reference ambient temperature; for B, C, D, UCB and PVS it is 30 °C, for K, UCK it is 20 °C for Z, K and UCZ it is 25 °C, for PVS acc. to UL489B it is 50 °C.


MCBs technical details

Tripping characteristics

Tripping characteristics S200 / S200M / S200P


Characteristic B

IEC-EN60898




Characteristic C

IEC-EN60898



Characteristic D

IEC-EN60898




MCBs technical details

Tripping characteristics

Tripping characteristics S200 / S200M / S200P


Characteristic K

IEC-EN60947-2



Characteristic Z

IEC-EN60947-2




MCBs technical details


Tripping characteristics

Tripping characteristics S200S

Characteristic B



Characteristic C




MCBs technical details


Tripping characteristics

Tripping characteristics SU200 M


Characteristic C



Characteristic K



Characteristic Z




MCBs technical details

Tripping characteristics

Tripping characteristics S200 80-100A


Characteristic B

IEC-EN60898-1




Characteristic B

IEC-EN60947-2




Characteristic C

IEC-EN60898-1



Characteristic C

IEC-EN60947-2




MCBs technical details

Tripping characteristics


Characteristic K

S 200 UDC



Characteristic Z

S 200 UDC



① thermal trip


② electromagnetic trip

MCBs technical details

Tripping characteristics


Characteristic E_{selective}

S 700 - 10 ... 100 A




Characteristic K_{selective}

S 700 - 16 ... 50 A




Characteristic K_{selective}

S 700 - 63 ... 100 A



Characteristic E_{selective}, K_{selective}


S 750 DR - 16 ... 100 A



a thermal trip
b electromagnetic trip

MCBs technical details

Tripping characteristics



Example:

Non-tripping current (Electromagnetic release)

S 201-B16










$$\begin{aligned}
 I_{\text{non-tripping}} &= k \times \text{non-tripping current} & \text{B-Characteristic} &= 3 \times I_n \\
 I_{\text{non-tripping}} &= 4,2 \times 3 \times 16 & \text{C-Characteristic} &= 5 \times I_n \\
 I_{\text{non-tripping}} &= 201,6 \text{ A} & \text{D-Characteristic} &= 10 \times I_n \\
 & & \text{K-Characteristic} &= 10 \times I_n \\
 & & \text{Z-Characteristic} &= 2 \times I_n
 \end{aligned}$$

The S 201-B16 does not trip at an impulse of 600 es at a current up to 201,6 A.

MCBs technical details

Tripping characteristics

S800



MCBs technical details


Limitation of specific let-through energy I^2t

Limitation of specific let-through energy

Tripping of an installation circuit by circuit-breaker when there is a short-circuit requires a certain amount of time depending on the characteristics of the circuit-breaker and the entity of the short-circuit current. During this period of time, some or all of the short-circuit current flows into the installation; the parameter I^2t defines the "specific let-through energy", ie. the specific energy that the breaker allows through when there is a short-circuit current I_{cc} during the tripping time t .

In this way, we can determine the capacity of a circuit-breaker to limit, ie. break high currents up to the rated breaking power of the device, by reducing the peak value of the above-mentioned currents to a value which is considerably lower than the estimated current.

I_{rms} = perspective simmetrical short-circuit current



Non-current limiting circuit-breaker

Oscillogram of short-circuit breaks on two circuit-breakers:

1 = traditional non-current limiting circuit-breaker


2 = current limiting circuit-breaker

u_B = arc voltage (red)

u_M = rest voltage (blue)

This can be achieved using mechanisms which open very rapidly and have the following advantages:

- they limit the thermal and dynamic effects both on the circuit-breaker and on the protected circuit;
- they reduce the dimensions of the current-limiting circuit-breaker without reducing breaking capacity;
- they considerably reduce ionized gases and sparklers emitted during the short-circuit and therefore they avoid the danger of ignition and fires.



Current limiting circuit-breaker

Short-circuit current

red = effective short-circuit current squared

blue = estimated short-circuit current squared (shunted circuit-breaker)

i_{K_M} = maximum values of symmetrical component of short-circuit current squared


shaded in

red = specific let-through energy in two cases

Limiting of let-through energy

Main selective circuit breakers (SMCB) like S 700 and S 750 DR support downstream mcb's in clearing short-circuit

currents. They additionally reduce let-through energies without tripping. This increases the operational availability of the electrical supply and reduces drawbacks to the feeding grid and the installed equipment.



MCBs technical details

Limitation of specific let-through energy I^2t

Max. withstanding specific let-through energy of cables

Section mm ²	PVC	EPR	HEPR
50	33,062,500	39,062,500	51,122,500
35	16,200,625	19,140,625	25,050,025
25	8,265,625	9,765,625	12,780,625
16	3,385,600	4,000,000	5,234,944
10	1,322,500	1,562,500	2,044,900
6	476,100	562,500	736,164
4	211,600	250,000	327,184
2.5	82,656	97,656	127,806
1.5	29,756	35,156	46,010

The selection of the cables depends both from the breakers' specific let-through energy and from carrying capacity and voltage drop of the line.

Data of the previous table are referred to the following cables:

PVC	EPR	HEPR
FM9	H07RN-F	N07G9-K
FM9OZ1		FTG100M1
N07V-K		RG7OR
FROR		FG7OM1
		FG7OR

Designation

Cable's reference to the standards	harmonized national cable recognized by CENELEC	H A
Rated voltage Uo/U	100/100 ≤ Uo/U < 300/300 300/300 V 300/500 V 450/750 V 750/1000 V	01 03 05 07 1
Insulating materials and non-metallic sheath	ethylene-vinylacetate mineral polyvinyl chloride	G M V
Conductor's shape	flexible conductor of a cable for fixed installation	K

Some cables on the market are identified with different names according with the designation UNEL 35011.

MCBs technical details

Limitation of specific let-through energy I^2t



I^2t diagrams - Specific let-through energy value I^2t

The I^2t curves give the values of the specific let-through

energy expressed in A^2s ($A=amps$; $s=seconds$) in relation to the perspective short-circuit current (I_{rms}) in kA.



S 200-S 200 M-S 200 P, characteristics B and C

230/400 V let-through energy



S 200-S 200 M-S 200 P, characteristics D-K

230/400 V let-through energy




MCBs technical details

Limitation of specific let-through energy I^2t




S200MUC-B B-characteristic

1p: 220 V DC, 2 p: 440 V DC let-through energy



S200MUC-C C-characteristic

1p: 220 V DC, 2 p: 440 V DC let-through energy





MCBs technical details

Limitation of specific let-through energy I^2t

S200MUC-K K-characteristic

1p: 220 V DC, 2 p: 440 V DC let-through energy





MCBs technical details

Limitation of specific let-through energy I^2t

S200MUC-Z Z-characteristic

1p: 220 V DC, 2 p: 440 V DC let-through energy





MCBs technical details

Limitation of specific let-through energy I^2t


S 200-S 200 M-S 200 P, characteristic Z

230/400 V let-through energy



SN201 L-SN201-SN201 M, characteristics B

230 V let-through energy





MCBs technical details

Limitation of specific let-through energy I^2t

SN201 L-SN201-SN201 M, characteristics C

230 V let-through energy




MCBs technical details

Limitation of specific let-through energy I^2t


S 700 characteristic E_{selective}

let-through energy




S 700 characteristic E_{selective}

let-through peak current (I_{peak})




S 700 characteristic K_{selective}

let-through energy



S 700 characteristic K_{selective}

let-through peak current (I_{peak})





MCBs technical details

Limitation of specific let-through energy I^2t

S 750 DR characteristic $E_{\text{selective}}, K_{\text{selective}}$

diagram of let-through values

I^2t 16 ... 100 A





MCBs technical details

Limitation of specific let-through energy I^2t

S800 S characteristics B, C, D and K

230 V let-through energy



- ① Min. pre-arching I^2t , e.g. NH80 A gL/gG
- ② Max. let-through I^2t , e.g. S801S-C20



Selectivity with respect to the upstream fuse to the point of intersection of both curves 1 and 2, e.g.
S801S-C20 to NH80A gL/gG: Selectivity up to min. 5 kA.

MCBs technical details

Limitation of specific let-through energy I^2t

S800 S characteristics B, C, D and K

400 V let-through energy



- ① Min. pre-arching I^2t , e.g. NH80 A gL/gG
- ② Max. let-through I^2t , e.g. S803S-C20



Selectivity with respect to the upstream fuse to the point of intersection of both curves 1 and 2, e.g.
S801S-C20 to NH80A gL/gG: Selectivity up to min. 5 kA.

MCBs technical details

Limitation of specific let-through energy I^2t

S800 S characteristics B, C, D and K

440 V let-through energy





MCBs technical details

Limitation of specific let-through energy I^2t

S800 S characteristics B, C, D and K

690 V let-through energy





MCBs technical details

Limitation of specific let-through energy I^2t

S800 N characteristics B, C and D

230 V let-through energy



① Min. pre-arching I^2t , e.g. NH80 A gL/gG
 ② Max. let-through I^2t , e.g. S801N-C20



Selectivity with respect to the upstream fuse to the point of intersection of both curves 1 and 2, e.g.
 S801N-C20 to NH80A gL/gG: Selectivity up to min. 3.8 kA.

MCBs technical details

Limitation of specific let-through energy I^2t

S800 N characteristics B, C and D

400 V let-through energy



- ① Min. pre-arching I^2t , e.g. NH80 A gL/gG
- ② Max. let-through I^2t , e.g. S803N-C20



Selectivity with respect to the upstream fuse to the point of intersection of both curves 1 and 2, e.g.
S801N-C20 to NH80A gL/gG: Selectivity up to min. 3.8 kA.

MCBs technical details

Limitation of specific let-through energy I^2t

S800 C characteristics B, C, D and K

230 V let-through energy



① Min. pre-arching I^2t , e.g. NH80 A gL/gG
 ② Max. let-through I^2t , e.g. S801C-C20



Selectivity with respect to the upstream fuse to the point of intersection of both curves 1 and 2, e.g.
 S801C-C20 to NH80A gL/gG: Selectivity up to min. 3.8 kA

MCBs technical details

Limitation of specific let-through energy I^2t

S800 C characteristics B, C, D and K

400 V let-through energy



- ① Min. pre-arching I^2t , e.g. NH80 A gL/gG
- ② Max. let-through I^2t , e.g. S803C-C20


Selectivity with respect to the upstream fuse to the point of intersection of both curves 1 and 2, e.g.
S801C-C20 to NH80A gL/gG: Selectivity up to min. 3.8 kA

MCBs technical details

Limitation of specific let-through energy I^2t


S800B characteristics B, C, D and K

230/400 V let-through energy



S800 U characteristics Z and K

240 V let-through energy




MCBs technical details

Peak current I_p


Limitation curves - Peak current values

The I_p curves give the values of the peak current, expressed in kA, in relation to the perspective symmetrical short-circuit current (kA).

S 200-S 200 M-S 200 P, characteristics B-C; DS 200-DS 200 M, characteristics B-C




S 200-S 200 M-S 200 P, characteristics K-D



MCBs technical details


Peak current I_p

S 200-S 200 M-S 200 P, characteristic Z



SN 201 L, SN 201, SN 201 M, characteristic B

230 V




MCBs technical details

Peak current I_p


SN 201 L, SN 201, SN 201 M, characteristic C

230 V



SN 201, characteristic D



230 V



MCBs technical details

Peak current I_p

S 750 DR characteristics $E_{\text{selective}}$, $K_{\text{selective}}$





MCBs technical details

Peak current I_p

S 800 S characteristics B, C, D and K

230/400 V let-through current





MCBs technical details

Peak current I_p

S 800 S characteristics B, C, D and K

440 V let-through current





MCBs technical details

Peak current I_p

S 800 S characteristics B, C, D and K

690 V let-through current





MCBs technical details

Peak current I_p

S 800 N characteristics B, C and D

230/400 V let-through current





MCBs technical details

Peak current I_p

S 800 C characteristics B, C, D and K

230/400 V let-through current





MCBs technical details

Peak current I_p

S 800 B characteristics B, C, D and K

230/400 V let-through current





MCBs technical details

Peak current I_p

S 800 U characteristics Z and K

240 V let-through current



MCBs technical details

SOC - Selected Optimized Coordination

SOC - SELECTED OPTIMIZED COORDINATION

Power and productivity for a better world™ **ABB**

Motor protection Selectivity Back-up Other devices protection

SOC - Selected Optimized Coordination

Motor Protection Coordination tables for motor starting and protection.

Selectivity Selectivity coordination tables between short circuit protection devices.

Back-up Back-up coordination tables between short-circuit protection devices.

Other devices protection Coordination table for the protection of switch-disconnector and other devices by short circuit protection devices.

Provider information disclaimer © Copyright 2013 ABB | Cookies and privacy policy

ABB is constantly improving or developing new products. Coordination between these products is therefore constantly updated. Providing always the up-to-date version in an environmental-friendly way the World Wide Web is a perfect platform. Therefor ABB offers a new tool online, SOC – Selected Optimized Coordination.

SOC is a web tool for the selection of ABB products in these applications:

- Motor starting and protection
- Selectivity between protection devices
- Back-up protection
- Other devices protection

Please check out under:

http://applications.it.abb.com/SOC_SN

SOC - SELECTED OPTIMIZED COORDINATION

Power and productivity for a better world™ **ABB**

Motor protection Selectivity Back-up Switch disconnector

Coordination tables for motor protection

→ What's new on SOC

Aggiorna tabella

Motore Interruttore automatico scalatore (MCCB) **Contattore** Relè di sovraffusione **Motor efficiency class:** IE1 IE2 IE3

Circuito di protezione	Tensione nominale	Corrente di corto circuito [A]	Tipo di avviamento	Coordinamento	Relè di sovraffusione	Potenza nominale del motore [kW]/[HP]
Tutti	Tutti	Tutti	Tutti	Tutti	Indiretto	Overview
ACB	240Vac	3	DOL-IEC	IEC Type 1	TOL	0.80
Fuses	400Vac	5	DOL-IEC	IEC Type 2	TOL	0.80
MCCB	415Vac	12	UL-IEC	UL Type A	TOL	0.80
NMS	600Vac	12	UL-IEC	UL Type C	ULC	0.12
esvarat	esvarat	18	UL-IEC	UL Type D	ULC	0.18
esvarat	esvarat	18	UL-IEC	UL Type E	ULC	0.25
900vac	25	—	UL-IEC	UL Type F	ULC	0.37
500vac	22	—	UL-IEC	UL Type G	ULC	0.5
690V/347V	25	—	UL-IEC	UL Component	ULC	0.80

search Export PDF

18 elementi (0.26 secondi)

Mostra solo i nuovi prodotti ABB 20 Numeri di record da mostrare

Scorri mostrando le tabelle più vicine alla selezione e quelle vicine (Ricerca Intelligente sulle combinazioni)

MCCB, 400 Vac, 33 kA, DOL-NB, Coordinamento IEC Type 1, Relé di sovraccarico TOL, Motor efficiency class IE1 + IE2

Motore	Interruttore automatico scalatore (MCCB)	Contattore	Relè di sovraffusione	Corrente di carico massima [A] Tabelle		
Potenza nominale [kW]	Corrente nominale [A]	Type	Corrente di innesco iniziale [A]	Type	Intervallo di corrente di funzionamento [A]	Corrente di carico massima [A] Tabelle
0,25	0,63 XT25 160 MP 1	14,00 AFR	TF42-1	0,74 - 1,00	1,00 --	1,00 --
0,37	1,10 XT25 160 MP 2	28,00 AFR	TF42-1-3	1,00 - 1,30	1,30 --	1,30 --

MCCB, 400 Vac, 59 kA, DOL-NB, Coordinamento IEC Type 2, Relé di sovraccarico TOL, Motor efficiency class IE1 + IE2

Motore	Interruttore automatico scalatore (MCCB)	Contattore	Relè di sovraffusione	Corrente di carico massima [A] Tabelle		
Potenza nominale [kW]	Corrente nominale [A]	Type	Corrente di innesco iniziale [A]	Type	Intervallo di corrente di funzionamento [A]	Corrente di carico massima [A] Tabelle
0,25	0,63 XT25 160 MP 1	14,00 AFR	TF42-1	0,74 - 1,00	1,00 --	1,00 --
0,37	1,10 XT25 160 MP 2	28,00 AFR	TF42-1-3	1,00 - 1,30	1,30 --	1,30 --

MCCB, 400 Vac, 59 kA, DOL-NB, Coordinamento IEC Type 1, Relé di sovraccarico TOL, Motor efficiency class IE1 + IE2 + IE3

Motore	Interruttore automatico scalatore (MCCB)	Contattore	Relè di sovraffusione	Corrente di carico massima [A] Tabelle		
Potenza nominale [kW]	Corrente nominale [A]	Type	Corrente di innesco iniziale [A]	Type	Intervallo di corrente di funzionamento [A]	Corrente di carico massima [A] Tabelle
0,25	0,63 XT25 160 MP 1	14,00 AFR	TF42-1	0,74 - 1,00	1,00 --	1,00 --
0,37	1,10 XT25 160 MP 2	28,00 AFR	TF42-1-3	1,00 - 1,30	1,30 --	1,30 --

MCCB, 400 Vac, 33 kA, DOL-NB, Coordinamento IEC Type 2, Relé di sovraccarico TOL, Motor efficiency class IE1 + IE2 + IE3

Motore	Interruttore automatico scalatore (MCCB)	Contattore	Relè di sovraffusione	Corrente di carico massima [A] Tabelle		
Potenza nominale [kW]	Corrente nominale [A]	Type	Corrente di innesco iniziale [A]	Type	Intervallo di corrente di funzionamento [A]	Corrente di carico massima [A] Tabelle
0,25	0,63 XT25 160 MP 1	14,00 AFR	TF42-1	0,74 - 1,00	1,00 --	1,00 --
0,37	1,10 XT25 160 MP 2	28,00 AFR	TF42-1-3	1,00 - 1,30	1,30 --	1,30 --

In the on line configurator you can choose among many filters, it is possible to select more than one filter at the same time.

Results are shown in the bottom part of the page. If a search does not produce any result, "Smart Search" will show the closest tables matching the search criteria.

Click on “>>” on the rightmost part of each record, to view the whole coordination table, tables can be printed or saved as PDF files.

SOC - SELECTED OPTIMIZED COORDINATION

Power and productivity for a better world™ **ABB**

Motor protection Selectivity Back-up Switch disconnector

Coordination tables for motor protection

→ Relazione Info su IEC Motors

Indice

Nome tabella : MCCB - 400Vac - 35kA - C

Tipo di circuito di protezione : MCCB
Tensione nominale : 400Vac
Presone di innesco : 0,63-1,10-25-50-100-200-400-800-1600-3200-6400-12800-25600-51200-102400-204800-409600-819200-1638400-3276800-6553600-13107200-26214400-52428800-104857600-209715200-419430400-838860800-1677721600-3355443200-6710886400-13421772800-26843545600-53687091200-107374182400-214748364800-429496729600-858993459200-1717986918400-3435973836800-6871947673600-13743895347200-27487790694400-54975581388800-109951162777600-219902325555200-439804651110400-879609302220800-1759218604441600-3518437208883200-7036874417766400-14073748835532800-28147497671065600-56294995342131200-11258999068426400-22517998136852800-45035996273705600-90071992547411200-18014398509482400-36028797018964800-72057594037929600-144115188078459200-288230376156918400-576460752313836800-115292150462767200-230584300925534400-461168601851068800-922337203702137600-184467440740427200-368934881480854400-737869762961708800-1475739525923417600-2951479051846835200-5902958103693670400-1180591620738734800-2361183241477469600-4722366482954939200-9444732965909878400-18889465931819756800-37778931863639513600-75557863727278727200-151115727454574454400-302231454909148908800-604462909818297817600-1208925819636595635200-2417851639273191270400-4835703278546382540800-9671406557092765081600-19342813114185530163200-38685626228371060326400-77371252456742120652800-154742504913484241285600-309485009826968482571200-618970019653936965142400-1237940039307873930884800-2475880078615747861769600-4951760157231495723539200-9903520314462991447078400-19807040628925982894156800-39614081257851965788313600-79228162515703931576627200-158456325311407863553244800-316912650622815727106489600-633825301245631454212979200-126765060249126290842558400-253530120498252581685116800-507060240996505163370233600-101412048199301032674467200-202824096398602065348934400-405648192797204130697868800-811296385594408261395737600-1622592771188816522791475200-3245185542377632645582950400-6490371084755265291165900800-1298074216951053058233181600-2596148433902106116466363200-5192296867804212232932726400-10384593735608424465865452800-20769187471216848931730905600-41538374942433697863461811200-83076749884867395726923622400-166153499769734791453847244800-332306999539469582907694489600-664613999078939165815388979200-132922799815787833163077798400-265845599631575666326155596800-531691199263151332652311193600-1063382398526302665246223387200-2126764797052605330492446774400-4253529594105210660984893548800-8507059188210421321969787097600-17014118376420842643939574195200-3402823675284168528787914838400-6805647350568337057575829676800-1361129470113335411515165933600-2722258940226670823030331867200-5444517880453341646060663734400-10889035760906883292121327468800-21778071521813766584242654937600-43556143043627533168485309875200-87112286087255066336970619750400-17422457217451013267341323950800-34844914434902026534682657901600-69689828869804053069365315803200-139379657739608106138730631606400-278759315479216212277461263212800-557518630958432424554922524425600-111503726191686448909844548851200-223007452383372897819689097702400-446014904766745795639378195404800-892029809533491591278756387809600-1784059619066983182557131756193600-3568119238133966365114263512387200-7136238476267932730228527025774400-1427247695253586546045705405548800-2854495390507173092091410811097600-5708985781014346184182821622195200-1141797156202883236365642324438400-2283594312405766472731284648876800-4567188624811532945462569297753600-9134377249623065890925138595507200-18268754499246131781852677191014400-36537508998492263563705354382028800-73075017996984527127410708764057600-14615003599396855425482141732101600-29230007198793710850964283464203200-58460014397587421701928566928406400-11692002879517484340385133856812800-2338400575903496868077026771365600-4676801151806993736154053543331200-9353602303613987472308107086662400-18707204607227974946016214173324800-37414409214455949892032428346649600-74828818428911899784064856693299200-14965763685782379956812971338659200-29931527371564759913625942677318400-59863054743129519827259845354636800-11972610948625903965451969073327200-23945221897251807930903938146654400-47890443794503615925807876293308800-95780887589007231851615752586617600-191561775178014463703231505173335200-383123550356028927406463010346670400-766247100712057854812926020693340800-153249420142411570962585040138681600-30649884028482314192517008027763200-61299768056964628385034016055526400-122599536113929256770068032111052800-245199072227858513540136064222105600-490398144455717027080272128444211200-980796288911434054160544256888422400-1961592577822868108321088513776844800-3923185155645736216642177027553689600-784637031129147243328435405510737600-1569274062258294486656708811021475200-313854812451658897331341762204350400-627709624903317794662683524408700800-125541924980663558932541054881701600-251083849961327117865082109763403200-502167699922654235730164219526806400-1004335399445308471460328439053612800-2008670798890616942920656878107225600-4017341597781233885841313756214451200-8034683195562467771682627512428902400-16069366391124935543373150244857804800-32138732782249871086746300489715609600-64277465564499742173492600979431219200-128554931128999484346985201958862438400-257109862257998968693970403917728876800-514219724515997937387940807835457753600-102843944903199587477588161567091553200-20568788980639917495517632313410306400-41137577961279834991035264626820612800-82275155922559669982070529253641225600-164550311845119339964141058507282451200-329100623685238679928282117014564902400-65820124737047735985656423402912904800-131640249474095471971312846805828996800-263280498948190943942625693611657993600-526560997896381887885251387223315987200-105312199579276377577050277444663954400-21062439915855275515410055488933908800-42124879831710551030820110977877777600-84249759663421102061640221955755555200-16849951932684224120328044391151150400-33699803865368448240656088782230230400-67399607730736896481312177564460460800-13479921546147379296264355132892081600-26959843092294758592528710265784163200-53919686184589517185057420531568326400-107839372369179034370114841063132652800-21567874473835806874022968212626525600-43135748947671613748045936425253051200-8627149789534322749609187285050602400-17254299579068645499218374570101204800-34508599158137290998436749140202409600-6901719831627458199687349828040409600-13803439663154916399374981656080918400-27606879326309832798749833312161836800-55213758652619665597499666624323673600-11042751710523933119499833324867415200-22085503421047866238999666649734830400-44171006842095732477999333299469660800-88342013684191464955998666598939321600-17668402736838291911998333197878723200-35336805473676583823997666395757446400-70673610947353167647997333791514892800-14134722189470635295597333582753785600-28269444378941270591197333165507571200-56538888757882541182394666331015142400-11307777751576522364678933366203084800-22615555503153044729357866732406169600-45231111006306089458715733332813139200-90462222003153178917435466665626378400-180924440065306357834710933331256756800-361848880030653115669421866662535113600-723697760015306231338843733335067727200-144739552003064466267687466667535454400-289479104006128932535374933337567888800-578958208012257865067549866675135777600-115791641602505531035159973335071555200-23158328320500106620709954666703510400-46316656641000213241419909333707020800-92633313282000426482839818667414041600-18526662656400851316579637333485403200-37053325312800162653159274666910806400-7410665062560032

MCBs technical details


Coordination tables

Back-up protection

The tables given provide the value (in kA, referring to the breaking capacity according to the IEC 60947-2 Standard) for which the back-up protection among the combination of selected circuit-breakers is verified. The tables cover the possible combinations between ABB SACE Tmax series of moulded-case circuit-breakers and those between the above-mentioned circuit-breakers and the ABB series of modular circuit-breakers.

The values indicated in the tables refer to the voltage:

- V_n of 230/240 V AC for coordination with modular SN 201 circuit-breakers
- V_n of 400/415 V AC for all the other coordinations.



Note

The following tables give the breaking capacities at 415 V AC for circuit-breakers SACE Tmax.

Tmax @ 415 V AC

Version	Icu [kA]
B	16
C	25
N	36
S	50
H	70
L (T2)	85
L (T4, T5)	120
V	200

Caption

MCB = miniature circuit-breakers (SN 201, S 2, S 800)
MCCB = moulded-case circuit-breakers (Tmax)

For moulded-case or air circuit-breakers:

- TM = thermomagnetic release
 – TMD (Tmax)
 – TMA (Tmax)
- M = magnetic only release
 – MF (Tmax)
 – MA (Tmax)
- EL = electronic release
 – PR221DS - PR222DS (Tmax)

Selective protection

The tables given provide the value (in kA, referring to the breaking capacity according to the IEC 60947-2 Standard) for which the selective protection is verified among the combination of selected circuit-breakers. The tables cover the possible combinations between ABB SACE Tmax series of moulded-case circuit-breakers, and the ABB series of modular circuit-breakers. The values in the table represent the maximum value obtainable of discrimination between supply side circuit-breaker and load side circuit-breaker referring to the voltage:

- V_n of 230/240 V AC for the SN 201 circuit-breakers and V_n of 400/415 V AC for the supply side circuit-breakers in the coordination between MCB with the modular SN 201 circuit-breakers (see picture).
- V_n of 400/415 V AC for all the other coordinations.

For miniature circuit-breakers:

- B = trip characteristic ($I_m=3...5I_n$)
 C = trip characteristic ($I_m=5...10I_n$)
 D = trip characteristic ($I_m=10...20I_n$)
 K = trip characteristic ($I_m=10...14I_n$)
 Z = trip characteristic ($I_m=2...3I_n$)

For solutions not shown in these tables, please consult the website: <http://bol.it.abb.com> or contact ABB SACE

For solutions not shown in these tables referring to SMISSLINE or S800 please use: leaflet 2CCC451039L02xx

MCBs technical details

Coordination tables: back-up

MCB - MCB @240 V

			Supply s.	S200	S200M	S200P	S200P	25gG	40gG	50gG	63gG	80gG	100gG
Load s.			Char.	B-C	B-C	B-C	B-C						
				Icu [kA]	20	25	40	25					
SN201 L	B,C	6	2...40	20	25	40	25	35	25	20	15	10	10
SN201	B,C,D	10	2...40	20	25	40	25	35	25	20	15	10	10
SN201 M	B,C	10	2...40	20	25	40	25	35	25	20	15	10	10
S200	B,C, K,Z	20	0,5...63		25	40	25						
S200 M	B,C,D	25	0,5...63			40							
S200 P	B,C	40	0,5...25										
	D,K,Z	25	32...63										

MCCB @ 415 V - SN201 @ 230/240V

			Supply S.1	T1	T1	T1	T2	T3	T2	T3	T2	T2
			Version	B	C	N			S		H	L
Load S.	Char.	In [A]	Icu [kA]	16	25	36			50		70	85
SN201 L	B, C	2..25	6	16	16	16	20	10	20	10	20	20
		32, 40		10	10	10	16		16		16	16
SN201	B, C, D, K	2..25	10	16	16	16	25	16	25	16	25	25
		32, 40					16		16		16	16
SN201 M	B, C	2..25	10	16	16	16	25	16	25	16	25	25
		32, 40					16		16		16	16

¹ Supply side circuit-breaker 4P (load side circuit branched between one phase and the neutral)

MCBs technical details

Coordination tables: back-up

MCB - MCB @ 415 V

		Supply S.	S200	S200M	S200P	S280
Char.			B-C	B-C	B-C	B-C
Load S.	Icu [kA]	10	15	25	15	6
		In [A]	0.5..63	0.5..63	0.5..25	32..63
S200	B,C,K,Z	10	0.5..63	15	25	15
S200M	B,C	15	0.5..63		25	
S200P	B,C, D,K,Z	25	0.5..25			
		15	32..63			

S800S – SN201 @ 230/240 V

		Supply s.	S800S
Char.			B, C, D, K
Load s.	Icu [kA]	50	
		In [A]	25 32 40 50 63 80 100 125
SN201	B, D	10	6 50 50 50 50 50 50 50
			10 50 50 50 50 50 50 50
			16 50 50 50 50 50 50 50
			20 50 50 50 50 50 50 50
			25 50 50 50 50 50 50 50
			32 50 50 50 50 50 50 50
			40 50 50 50 50 50 50 50

S800S – SN201 @ 230/240 V

		Supply s.	S800S
Char.			B, C, D, K
Load s.	Icu [kA]	50	
		In [A]	25 32 40 50 63 80 100 125
SN201	C	10	2 50 50 50 50 50 50 50
			4 50 50 50 50 50 50 50
			6 50 50 50 50 50 50 50
			10 50 50 50 50 50 50 50
			16 50 50 50 50 50 50 50
			20 50 50 50 50 50 50 50
			25 50 50 50 50 50 50 50
			32 50 50 50 50 50 50 50

MCBs technical details

Coordination tables: back-up

S800S – SN201 L @ 230/240 V

		Supply s.	S800S								
		Char.	B, C, D, K								
Load s.	Char.	Icu [kA]	50								
			In [A]	25	32	40	50	63	80	100	125
SN201 L	B, C	6	2	50	40	25	25	18	15	15	15
			4	50	40	25	25	18	15	15	15
			6	50	40	25	25	18	15	15	15
			10	50	40	25	25	18	15	15	15
			16	50	40	25	25	18	15	15	15
			20		40	25	25	18	15	15	15
			25			25	25	18	15	15	15
			32				25	18	15	15	15
			40					18	15	15	15

S800S – SN201 M @ 230/240 V

		Upstream	S800S								
		Char.	B, C, D, K								
Load s.	Char.	Icu [kA]	50								
			In [A]	25	32	40	50	63	80	100	125
SN201 M	B	10	6	50	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50
			40					50	50	50	50

S800S - SN201 M @ 230/240 V

		Supply s.	S800S								
		Char.	B, C, D, K								
Load s.	Char.	Icu [kA]	50								
			In [A]	25	32	40	50	63	80	100	125
SN201 M	C	10	2	50	50	50	50	50	50	50	50
			4	50	50	50	50	50	50	50	50
			6	50	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50

MCBs technical details

Coordination tables: back-up

S800S – S200 @230/400V

		Supply s.		S800S						
		Char.		B, C, D, K						
Load s.		Icu [kA]		50						
		In [A]	25	32	40	50	63	80	100	125
S200	C	10	0.5...6	50	50	50	50	50	50	50
			8	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50
			13	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25			50	50	50	50	50
			32				50	50	50	50
			40					50	50	50
			50						50	50
			63						50	50

S800S – S200L @230/400V

		Supply s.		S800S							
		Char.		B, C, D, K							
		Icu [kA]		50							
			In [A]	25	32	40	50	63	80	100	125
S200L	C	6	6...8	50	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50	50
			13	50	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50
			40					50	50	50	50

MCBs technical details

Coordination tables: back-up

S800S – S200M @230/400V

		Supply s.		S800S						
		Char.		B, C, D, K						
Load s.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200M	B	15	6...16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25			50	50	50	50	50
			32				50	50	50	50
			40					50	50	50
			50						50	50
			63						50	50

		Supply s.		S800S						
		Char.		B, C, D, K						
Load s.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200M	C	15	0.5...16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25			50	50	50	50	50
			32				50	50	50	50
			40					50	50	50
			50						50	50
			63						50	50

S800S – S200P @230/400V

		Supply s.		S800S						
		Char.		B, C, D, K						
Load s.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200P	B	25	6...16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25			50	50	50	50	50
		15	32				50	50	50	50
			40					50	50	50
			50						50	50
			63						50	50

		Supply s.		S800S						
		Char.		B, C, D, K						
Load s.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200P	C	25	0.5...16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25			50	50	50	50	50
		15	32				50	50	50	50
			40					50	50	50
			50						50	50
			63						50	50

MCBs technical details

Coordination tables: back-up

S800S – S400E @230/400V

MCBs technical details

Coordination tables: back-up

S800S – S400M @230/400V

		Supply s.		S800S								
		Char.		B, C, D, K								
Load s.	Char.	Icu [kA]	Icn [kA]	50								
				In [A]	25	32	40	50	63	80	100	125
S400M S450M FS401M FS403M	B, D	4*...16 10	50	25	50	50	50	50	50	50	50	50
				20		50	50	50	50	50	50	50
				25			50	50	50	50	50	50
				32				50	50	50	50	50
				40					50	50	50	50
				50						50	50	50
				63							50	50

* for B characteristic only

		Supply s.		S800S								
		Char.		B, C, D, K								
Load s.	Char.	Icu [kA]	Icn [kA]	50								
				In [A]	25	32	40	50	63	80	100	125
S400M S450M	C, K	50 25 15	0.5...2 3...20 25 32 40 50 63	0.5...2	50	50	50	50	50	50	50	50
				25	50	50	50	50	50	50	50	50
				25			50	50	50	50	50	50
				32				50	50	50	50	50
				40					50	50	50	50
				50						50	50	50
				63							50	50

S800S – S400M @254/440V

		Supply s.		S800S								
		Char.		B, C, D, K								
Load s.	Char.	Icu [kA]	Icn [kA]	50								
				In [A]	25	32	40	50	63	80	100	125
S400M S450M	C, K	15 10 6	0.5...2 3...10 13 16 20 25 32 40 50 63	0.5...2	30	30	30	30	30	30	30	30
				10	30	30	30	30	30	30	30	30
				13	30	30	30	30	30	30	30	30
				16	30	30	30	30	30	30	30	30
				20	30	30	30	30	30	30	30	30
				25		30	30	30	30	30	30	30
				32			30	30	30	30	30	30
				40				30	30	30	30	30
				50					30	30	30	30
				63						30	30	30

MCBs technical details

Coordination tables: back-up

S800N – S200 @ 230/400V

		Supply s.	S800N								
Load s.	Char.			B, C, D							
		Icu [kA]	In [A]	25	32	40	50	63	80	100	125
S200	B	10	6	36	36	36	36	36	36	36	36
			10	36	36	36	36	36	36	36	36
			13	36	36	36	36	36	36	36	36
			16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25			36	36	36	36	36	36
			32				36	36	36	36	36
			40					36	36	36	36
			50						36	36	36
			63							36	36

		Supply s.	S800N								
Load s.	Char.			B, C, D							
		Icu [kA]	In [A]	25	32	40	50	63	80	100	125
S200	C	10	0.5...6	36	36	36	36	36	36	36	36
			8	36	36	36	36	36	36	36	36
			10	36	36	36	36	36	36	36	36
			13	36	36	36	36	36	36	36	36
			16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25			36	36	36	36	36	36
			32				36	36	36	36	36
			40					36	36	36	36
			50						36	36	36
			63							36	36

S800N – S200L @ 230/400V

		Supply s.	S800N								
Load s.	Char.			B, C, D							
		Icu [kA]	In [A]	25	32	40	50	63	80	100	125
S200L	C	6	6...8	36	36	36	36	36	36	36	36
			10	36	36	36	36	36	36	36	36
			13	36	36	36	36	36	36	36	36
			16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25			36	36	36	36	36	36
			32				36	36	36	36	36
			40					36	36	36	36

MCBs technical details

Coordination tables: back-up

S800N – S200M @ 230/400V

		Supply s.		S800N							
		Char.		B, C, D							
Load s.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S200M	B	15	6...16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25		36	36	36	36	36	36	36
			32			36	36	36	36	36	36
			40				36	36	36	36	36
			50					36	36	36	36
			63						36	36	36

		Supply s.		S800N							
		Char.		B, C, D							
Load s.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S200M	C	15	0.5...16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25		36	36	36	36	36	36	36
			32			36	36	36	36	36	36
			40				36	36	36	36	36
			50					36	36	36	36
			63						36	36	36

S800N – S200P @ 230/400V

		Supply s.		S800N							
		Char.		B, C, D							
Load s.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S200P	B	25	6...16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25		36	36	36	36	36	36	36
			15	32		36	36	36	36	36	36
			40			36	36	36	36	36	36
			50				36	36	36	36	36
			63					36	36	36	36

		Supply s.		S800N							
		Char.		B, C, D							
Load s.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S200P	C	25	0.5...16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25		36	36	36	36	36	36	36
			15	32		36	36	36	36	36	36
			40			36	36	36	36	36	36
			50				36	36	36	36	36
			63					36	36	36	36

MCBs technical details

Coordination tables: back-up

S800N – S400E @230/400V

MCBs technical details

Coordination tables: back-up

S800N – S400M @230/400V

		Supply s.	S800N							
		Char.	B, C, D							
Load s.	Char.	Icu [kA]	36							
		In [A]	25	32	40	50	63	80	100	125
S400M S450M FS401MB FS403MB	B, D	Icn [kA] 10	4*...16	36	36	36	36	36	36	36
			20		36	36	36	36	36	36
			25			36	36	36	36	36
			32				36	36	36	36
			40					36	36	36
			50						36	36
			63						36	36

* for B characteristic only

		Supply s.	S800N							
		Char.	B, C, D							
Load s.	Char.	Icu [kA]	36							
		In [A]	25	32	40	50	63	80	100	125
S400M S450M FS401MC FS403MC	C, K	Icn [kA] 10	0.5...2	36	36	36	36	36	36	36
			25	36	36	36	36	36	36	36
			15	25		36	36	36	36	36
			32			36	36	36	36	36
			40				36	36	36	36
			50					36	36	36
			63						36	36

S800N – S400M @254/440V

		Supply s.	S800N							
		Char.	B, C, D							
Load s.	Char.	Icu [kA]	20							
		In [A]	25	32	40	50	63	80	100	125
S400M S450M	C, K	Icn [kA] 15	0.5...2	20	20	20	20	20	20	20
			10	3...10	20	20	20	20	20	20
			6	13	20	20	20	20	20	20
			16	20	20	20	20	20	20	20
			20		20	20	20	20	20	20
			25			20	20	20	20	20
			32				20	20	20	20
			40					20	20	20
			50						20	20
			63						20	20

MCBs technical details

Coordination tables: back-up

S800N – SN201 @ 230/240 V

		Supply s.		S800N							
		Char.		B, C, D							
Load s.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
SN201	B, D	10	6	36	36	36	36	36	36	36	36
			10	36	36	36	36	36	36	36	36
			16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25			36	36	36	36	36	36
			32				36	36	36	36	36
			40					36	36	36	36

S800N – SN201 @ 230/240 V

		Supply s.		S800N							
		Char.		B, C, D							
Load s.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
SN201	C	10	2	36	36	36	36	36	36	36	36
			4	36	36	36	36	36	36	36	36
			6	36	36	36	36	36	36	36	36
			10	36	36	36	36	36	36	36	36
			16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25			36	36	36	36	36	36
			32				36	36	36	36	36
			40					36	36	36	36

S800N – SN201L @ 230/240 V

		Supply s.		S800N							
		Char.		B, C, D							
Load s.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
SN201 L	B, C	6	2	36	36	25	25	18	15	15	15
			4	36	36	25	25	18	15	15	15
			6	36	36	25	25	18	15	15	15
			10	36	36	25	25	18	15	15	15
			16	36	36	25	25	18	15	15	15
			20		36	25	25	18	15	15	15
			25			25	25	18	15	15	15
			32				25	18	15	15	15
			40					18	15	15	15

MCBs technical details

Coordination tables: back-up

S800N – SN201M @ 230/240 V

		Supply s.	S800N							
		Char.	B, C, D							
Load s.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
SN201 M	B	10	6	36	36	36	36	36	36	36
			10	36	36	36	36	36	36	36
			16	36	36	36	36	36	36	36
			20		36	36	36	36	36	36
			25			36	36	36	36	36
			32				36	36	36	36
			40					36	36	36

S800N – SN201M @ 230/240 V

		Supply s.	S800N							
		Char.	B, C, D							
Load s.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
SN201 M	C	10	2	36	36	36	36	36	36	36
			4	36	36	36	36	36	36	36
			6	36	36	36	36	36	36	36
			10	36	36	36	36	36	36	36
			16	36	36	36	36	36	36	36
			20		36	36	36	36	36	36
			25			36	36	36	36	36

S800C – S200 @ 230/400 V

		Supply s.	S800C							
		Char.	B, C, D							
Load s.	Icu [kA]	25								
		In [A]	25	32	40	50	63	80	100	125
S200	B	10	6	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25
			13	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25
			20		25	25	25	25	25	25
			25			25	25	25	25	25
			32				25	25	25	25
			40					25	25	25
			50						25	25
			63							25

MCBs technical details

Coordination tables: back-up

S800C – S200M @ 230/400V

	Supply s.		S800C							
	Char.		B, C, D							
Load s.		Icu [kA]	25							
		In [A]	25	32	40	50	63	80	100	125
S200M	C	15	0.5...16	25	25	25	25	25	25	25
			20		25	25	25	25	25	25
			25		25	25	25	25	25	25
			32			25	25	25	25	25
			40				25	25	25	25
			50					25	25	25
			63						25	25

MCBs technical details

Coordination tables: back-up

S800C – S200P @ 230/400V

		Supply s.	S800C							
		Char.	B, C, D							
Load s.	Char.	Icu [kA]	25							
		In [A]	25	32	40	50	63	80	100	125
S200P	B	25	6...16	25	25	25	25	25	25	25
			20		25	25	25	25	25	25
			25		25	25	25	25	25	25
		15	32			25	25	25	25	25
			40				25	25	25	25
			50					25	25	25
			63						25	25

		Supply s.	S800C							
		Char.	B, C, D							
Load s.	Char.	Icu [kA]	25							
		In [A]	25	32	40	50	63	80	100	125
S200P	C	25	0.5...16	25	25	25	25	25	25	25
			20		25	25	25	25	25	25
			25		25	25	25	25	25	25
		15	32			25	25	25	25	25
			40				25	25	25	25
			50					25	25	25
			63						25	25

S800C – SN201 @ 230/240 V

		Supply s.	S800C							
		Char.	B, C, D, K							
Load s.	Char.	Icu [kA]	25							
		In [A]	25	32	40	50	63	80	100	125
SN201	B, D	10	6	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25
			20		25	25	25	25	25	25
			25		25	25	25	25	25	25
			32			25	25	25	25	25
			40				25	25	25	25

MCBs technical details

Coordination tables: back-up

S800C – SN201 @ 230/240 V

		Supply s.	S800C								
		Char.	B, C, D, K								
Load.s.	Char.	Icu [kA]	25								
			In [A]	25	32	40	50	63	80	100	125
SN201	C	10	2	25	25	25	25	25	25	25	25
			4	25	25	25	25	25	25	25	25
			6	25	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25	25
			20		25	25	25	25	25	25	25
			25			25	25	25	25	25	25
			32				25	25	25	25	25
			40					25	25	25	25

S800C – SN201L @ 230/240 V

		Supply s.	S800C								
		Char.	B, C, D, K								
Load s.	Char.	Icu [kA]	25								
			In [A]	25	32	40	50	63	80	100	125
SN201L	B, C	6	2	25	25	25	25	18	15	15	15
			4	25	25	25	25	18	15	15	15
			6	25	25	25	25	18	15	15	15
			10	25	25	25	25	18	15	15	15
			16	25	25	25	25	18	15	15	15
			20		25	25	25	18	15	15	15
			25			25	25	18	15	15	15
			32				25	18	15	15	15
			40					18	15	15	15

S800C – SN201M @ 230/240 V

		Supply s.	S800C								
		Char.	B, C, D, K								
Load s.	Char.	Icu [kA]	25								
			In [A]	25	32	40	50	63	80	100	125
SN201M	B	10	6	25	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25	25
			20		25	25	25	25	25	25	25
			25			25	25	25	25	25	25
			32				25	25	25	25	25
			40					25	25	25	25

MCBs technical details

Coordination tables: back-up

S800C – SN201M @ 230/240 V

		Supply s.		S800C																
		Char.	B, C, D, K																	
Load s.	Icu [kA]		25																	
			In [A]	25	32	40	50	63	80	100	125									
SN201M	C	10	2	25	25	25	25	25	25	25	25									
			4	25	25	25	25	25	25	25	25									
			6	25	25	25	25	25	25	25	25									
			10	25	25	25	25	25	25	25	25									
			16	25	25	25	25	25	25	25	25									
			20		25	25	25	25	25	25	25									
			25			25	25	25	25	25	25									
			32				25	25	25	25	25									

S800C – S280 @ 230/400V

	Supply s.		S800C							
	Char.		B, C, D							
Load s.		Icu [kA]	25							
		In [A]	25	32	40	50	63	80	100	125
S280	B	10	6	25	25	25	25	25	25	25
		25	10	25	25	25	25	20	16	16
			13	25	25	25	25	20	16	16
			16	25	25	25	25	20	16	16
			20		25	25	25	20	16	16
			25			25	25	20	16	16
		15	32			25	25	20	16	16
			40				20	16	16	16
		10	50					16	16	16
			63						16	16

MCBs technical details

Coordination tables: back-up

S800C – S400E @ 230/400V

		Supply s.		S800C						
		Char.		B, C, D						
Load s.		Icu [kA]		25						
			In [A]	32	40	50	63	80	100	125
S400E	C	Icn [kA] 6	0.5...6	25	25	25	25	25	25	25
			8	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25
			13	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25
			20		25	25	25	25	25	25
			25		25	25	25	25	25	25
			32			25	25	25	25	25
			40				25	25	25	25
			50					25	25	25
			63						25	25

MCBs technical details

Coordination tables: back-up

S800C – S400M @ 230/400V

		Supply s.		S800C							
		Char.		B, C, D							
Load s.	Char.	Icu [kA]	25								
			In [A]	25	32	40	50	63	80	100	125
S400M S450M	B, D	Icn [kA] 10	4*...16	25	25	25	25	25	25	25	25
			20		25	25	25	25	25	25	25
			25			25	25	25	25	25	25
			32				25	25	25	25	25
			40					25	25	25	25
			50						25	25	25
			63							25	25

		Supply s.		S800C							
		Char.		B, C, D							
Load s.	Char.	Icu [kA]	25								
			In [A]	25	32	40	50	63	80	100	125
S400M S450M	C	Icn [kA] 25	3...20	25	25	25	25	25	25	25	25
			15	25		25	25	25	25	25	25
			32			25	25	25	25	25	25
			40				25	25	25	25	25
			50					25	25	25	25
			63						25	25	25

		Supply s.		S800C							
		Char.		B, C, D							
Load s.	Char.	Icu [kA]	25								
			In [A]	25	32	40	50	63	80	100	125
S400M S450M	K	Icn [kA] 25	3...20	25	25	25	25	25	25	25	25
			10	25		25	25	25	25	25	25
			32			25	25	25	25	25	25
			40				25	25	25	25	25
			50					25	25	25	25
			63						25	25	25

MCBs technical details

Coordination tables: back-up

S800B – S200 @ 230/400V

		Supply s.		S800B						
		Char.		B, C, D, K						
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125*
S200	B	10	6	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16
			50					16	16	16
			63					16	16	16

		Supply s.		S800B						
		Char.		B, C, D, K						
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125*
S200	C, D, K, Z	10	0.5...6	16	16	16	16	16	16	16
			8	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16
			50					16	16	16
			63					16	16	16

* only S800B-B,C
back-up values indicated in kA

MCBs technical details

Coordination tables: back-up

S800B – S400E @230/400V

Load s.	Char.	Supply s.	S800B								
			B, C, D, K								
			Icu [kA]	In [A]	32	40	50	63	80	100	125
S400E	B, C	6	6	16	16	16	16	16	16	16	16
			8	16	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16	16
			25		16	16	16	16	16	16	16
			32			16	16	16	16	16	16
			40				16	16	16	16	16
			50					16	16	16	16
			63						16	16	16

S800B – S400M @230/400V

Load s.	Char.	Supply s.	S800B								
			B, C, D, K								
			Icu [kA]	In [A]	32	40	50	63	80	100	125*
S400M	B, D	10	6**	16	16	16	16	16	16	16	16
			8**	16	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16	16
			25		16	16	16	16	16	16	16
			32			16	16	16	16	16	16
			40				16	16	16	16	16
			50					16	16	16	16
			63						16	16	16

* only S800B-B, C

** only S400M-B

MCBs technical details

Coordination tables: back-up

		Supply s.	S800B							
		Char.	B, C, D, K							
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125
S400M	C	10	2	16	16	16	16	16	16	16
			3	16	16	16	16	16	16	16
			4	16	16	16	16	16	16	16
			6	16	16	16	16	16	16	16
			8	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16
			50					16	16	16
			63					16	16	16

		Supply s.	S800B							
		Char.	B, C, D, K							
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125
S400M	K	10	0.5...6	16	16	16	16	16	16	16
			8	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16
			50					16	16	16
			63					16	16	16

MCBs technical details

Coordination tables: back-up

S800B – S200M @ 230/400V

		Supply s.		S800B						
		Char.		B, C, D, K						
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125*
S200M	B	15	6	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16
		10	50					16	16	16
			63					16	16	16

		Supply s.		S800B						
		Char.		B, C, D, K						
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125*
S200	C, D K, Z	15	0.5...6	16	16	16	16	16	16	16
			8	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16
		10	50					16	16	16
			63					16	16	16

* only S800B-B,C

S800B – SN201 @ 230/240 V

		Supply s.		S800B						
		Char.		B, C, D, K						
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125*
SN201	B, D	10	6	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16

MCBs technical details

Coordination tables: back-up

		Supply s.		S800B						
		Char.		B, C, D, K						
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125*
SN201	C	10	2	16	16	16	16	16	16	16
			4	16	16	16	16	16	16	16
			6	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16

		Supply s.		S800B						
		Char.		B, C, D, K						
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125*
SN201 L	B, C	6	2	16	16	16	16	15	15	15
			4	16	16	16	16	15	15	15
			6	16	16	16	16	15	15	15
			10	16	16	16	16	15	15	15
			16	16	16	16	16	15	15	15
			20	16	16	16	16	15	15	15
			25		16	16	16	15	15	15
			32			16	16	15	15	15
			40				16	15	15	15

		Supply s.		S800B						
		Char.		B, C, D, K						
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125*
SN201 M	B	10	6	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16

MCBs technical details

Coordination tables: back-up

		Supply s.		S800B						
		Char.		B, C, D, K						
Load s.		Icu [kA]	In [A]	32	40	50	63	80	100	125
SN201 M	C	10	2	16	16	16	16	16	16	16
			4	16	16	16	16	16	16	16
			6	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16
			25		16	16	16	16	16	16
			32			16	16	16	16	16
			40				16	16	16	16

* only S800B-B,C
back-up values indicated in kA

S800U – S200 @ 230/400V

		Supply s.		S800U						
		Char.		K, Z						
Load s.		Icu [kA]		50						
S200	B	10	6	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50
			13	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25			50	50	50	50	50
			32				50	50	50	50
			40					50	50	50
			50						50	50
			63							50

		Supply s.		S800U						
		Char.		K, Z						
Load s.		Icu [kA]		50						
S200	B	10	0.5...6	50	50	50	50	50	50	50
			8	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50
			13	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25			50	50	50	50	50
			32				50	50	50	50
			40					50	50	50
			50						50	50
			63							50

MCBs technical details

Coordination tables: back-up

S800U – S200M @ 230/400V

		Supply s.		S800U						
		Char.		K, Z						
Load s.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200M	B	15	6...16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25			50	50	50	50	50
			32				50	50	50	50
			40					50	50	50
			50						50	50
			63						50	50

		Supply s.		S800U						
		Char.		K, Z						
Load s.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200M	C	15	0.5...16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25			50	50	50	50	50
			32				50	50	50	50
			40					50	50	50
			50						50	50
			63						50	50

S800U – S200P @ 230/400V

		Supply s.		S800U						
		Char.		K, Z						
Load s.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200P	B	25	6...16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25			50	50	50	50	50
		15	32				50	50	50	50
			40					50	50	50
			50						50	50
			63						50	50

MCBs technical details

Coordination tables: back-up

		Supply s.	S800U							
		Char.	K, Z							
Load s.	Char.	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S200P	C	25	0.5...16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25		50	50	50	50	50	50
		15	32			50	50	50	50	50
			40			50	50	50	50	50
			50			50	50	50	50	50
			63				50	50	50	50

S800U – S400E @230/400V

		Supply s.	S800U							
		Char.	K, Z							
Load s.	Char.	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S400E	B	Icn [kA] 6	6	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50
			13	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25		50	50	50	50	50	50
			32			50	50	50	50	50
			40			50	50	50	50	50
			50				50	50	50	50
			63					50	50	50

		Supply s.	S800U							
		Char.	K, Z							
Load s.	Char.	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S400E	C	Icn [kA] 6	0.5...6	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50
			13	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50
			20		50	50	50	50	50	50
			25		50	50	50	50	50	50
			32			50	50	50	50	50
			40			50	50	50	50	50
			50				50	50	50	50
			63					50	50	50

MCBs technical details

Coordination tables: back-up

S800U – S400M @230/400V

		Supply s.		S800U							
		Char.		K, Z							
Load s.	Char.	Icu [kA]	50								
			In [A]	25	32	40	50	63	80	100	125
S400M S450M	B, D	Icn [kA] 10	4*...16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50
			40					50	50	50	50
			50						50	50	50
			63							50	50
		Supply s.		S800U							
		Char.		K, Z							
Load s.	Char.	Icu [kA]	50								
			In [A]	25	32	40	50	63	80	100	125
S400M S450M	C	25	3...20	50	50	50	50	50	50	50	50
			15	25		50	50	50	50	50	50
			32			50	50	50	50	50	50
			40				50	50	50	50	50
			50					50	50	50	50
			63						50	50	50
		Supply s.		S800U							
		Char.		K, Z							
Load s.	Char.	Icu [kA]	50								
			In [A]	25	32	40	50	63	80	100	125
S400M S450M	K	25	3...20	50	50	50	50	50	50	50	50
			10	25		50	50	50	50	50	50
			32			50	50	50	50	50	50
			40				50	50	50	50	50
			50					50	50	50	50
			63						50	50	50

MCBs technical details

Coordination tables: back-up

Class J fuse – S800U (1 pole) @240 V AC

	Supply s.	FUSE	
Char.	Icu [kA]		
Load s.	In [A]	max. 250	max. 250
S800U	K, Z	30	10...80
			10...100

Class J fuse – S800U (multipole) @240V AC

	Supply s.	FUSE		
Char.	Icu [kA]			
Load s.		In [A]	max. 250	max. 250
S800U	K, Z	50	10...80	50
			10...100	50

Sace Tmax – S800U (1 pole) @240V AC

Sace Tmax – S800U (multipole) @240V AC

MCBs technical details

Coordination tables: back-up

MCCB - MCB @ 415 V

Load S.	Char.	In [A]	Icu [kA]	Supply S.				T1	T1	T1	T2	T3	T4	T2	T3	T4	T2	T4	T2	T4	T4
				Version	B	C	N		S		H		L	L	V						
S200	B,C,K,Z	0.5..10	10	16	25	30	36	36	36	36	40	40	40	40	40	40	40	40	40	40	40
		13..63						16		16											
S200M	B,C	0.5..10	15	16	25	30	36	36	36	36	40	40	70	70	85	85	40	40	60	60	40
		13..63						25		25		25		60		60					
S200P	B,C, D,K,Z	0.5..10	25					30	36	36	36	50	40	40	70	40	85	40	40	40	40
		13..25						30	36	30	36	50	30	40	60	40	60	40	40	40	40
		32..63	15	16	25	30	36	25	36	50	25	40	60	40	60	40	60	40	40	40	40
S800N	B,C,D	10..125	36							50	50	50	70	70	85	85	120	200			
S800S	B,C,D,K	10..125	50										70	70	85	85	120	200			
S800C	B,C,D,K	10..125						36	36	36	36	50	50	50	70	70	85	120	200		

* only for D characteristic

MCCB - MCB @ 415 V

Load s.	Carat.	In [A]	Icu [kA]	Supply s.				XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT2	XT4	XT2	XT4
				Version	B	C	N		S		H		L	V									
S200	B,C,K,Z	0.5..10	10	18	25	30	36	36	36	36	40	40	30	40	40	40	30	40	30	40	30	30	
		13..63						20		20													
S200M	B,C,D,K,Z	0.5..10	15	18	25	30	36	36	36	36	40	40	30	50	40	40	30	50	30	50	30	50	
		13..63						25		25		25		50		50		50		50		50	
S200P	B,C,D,K,Z	0.5..10	25					30	36	36	36	30	50	40	40	30	60	40	60	30	60	30	
		13..25						30	36	30	36	30	50	30	40	30	50	40	50	30	50	30	
		32..63	15	18	25	30	36	25	36	30	50	25	40	30	50	40	50	30	50	30	50	30	
S800N	B,C,D	6..125	36						50	50	50	50	70	70	70	70	120	120	150	150			
S800S	B,C,D,K	6..125	50									70	70	70	70	120	120	150	150				
S800C	B,C,D,K	10..125						36	36	36	36	50	50	50	70	70	70	70	120	120	150	150	

Tmax - S800B @ 230/400 V

Load s.	Char.	In [A]	Icu [kA]	Supply s.				T1	T1	T1	T2	T3	T4	T2	T3	T4	T2	T4	T2	T4	T2	T4
				Version	B	C	N		S		H		L	V								
S800B	B,C	32..100	16		25	36	36	36	36	50	50	50	70	70	85	85	120	200				
	D,K	125*			25	36	36	36	36	50	50	50	70	70	85	85	120	200				

XT - S800B @ 230/400 V

Load s.	Char.	In [A]	Icu [kA]	Supply s.				XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT2	XT4
				Version	B	C	N		S		H		L	V									
S800B	B,C	32..100	16		18	25	36	36	36	50	50	50	70	70	120	120	150	150					
	D,K	125*			18	25	36	36	36	50	50	50	70	70	120	120	150	150					

MCBs technical details

Coordination tables: back-up

Breaking capacities

Definition: B and C acc. to IEC EN 60 898, Icn

K and Z acc. to IEC EN 60 947-2, Icu

Type Tripping characteristic Nominal current	AC				DC		Back up protection up to ultimate short-circuit capacity of short-circuit protective device.	
	1 phase		2/3 phases		1phase			
	133 V~	230 V~	230 V~ 133/230 V~	400 V~ 230/400 V~	60 V---	Fuse	Selective MCB	
A	kA/cosφ	kA/cosφ	kA/cosφ	kA/cosφ	kA/T ≤ ms	gG	S700	
S 200-B S 200 M-B	6					63 A	100 A	
	10 ... 20					100 A	100 A	
	25 ... 32	10/0,5	6/0,7 10/0,5 (S 200 M-B)	10/0,5	6/0,7 10/0,5 (S 200 M-B)	10/4,0	100 A	100 A
	40						125 A	100 A
	50 ... 63						160 A	100 A
S 200-C S 200 M-C	0,5 ... 2	100 kA					not required	
	3 ... 4						20 A	-
	6						40 A	100 A
	8						63 A	100 A
	10 ... 20	10/0,5	6/0,7 10/0,5 (S 200 M-C)	10/0,5	6/0,7 10/0,5 (S 200 M-C)	10/4,0	100 A	100 A
	25 ... 32						100 A	100 A
	40						125 A	100 A
S 200-K S 200 M-K	50 ... 63						160 A	100 A
	0,5 ... 2	100 kA					not required	
	3						20 A	-
	4						25 A	-
	6 ... 10						63 A	100 A
	16 ... 20	10/0,5	6/0,7 10/0,5 (S 200 M-K)	10/0,5	6/0,7 10/0,5 (S 200 M-K)	10/4,0	80 A	100 A
	25 ... 32						100 A	100 A
S 200-Z S 200 M-Z	40						125 A	100 A
	50 ... 63						160 A	100 A
	0,5 ... 2	100 kA					not required	
	3 ... 4						20 A	-
	6						35 A	100 A
	8						40 A	100 A
	10 ... 16	10/0,5	6/0,7 10/0,5 (S 200 M-Z)	10/0,5	6/0,7 10/0,5 (S 200 M-Z)	10/4,0	63 A	100 A
S 200-M S 200 M-M	20 ... 25						80 A	100 A
	32 ... 40						100 A	100 A
	50 ... 63						125 A	100 A

1. In symmetrically earthed DC networks 2 pole MCBs can be applied at up to 125 V DC (series connection). In this case the breaking capacity is one level higher compared to an equivalent 1 pole installation. Polarity does not have to be considered. Thus any connection mode is permitted.

2. Back up protection is only required when the prospective short circuit current exceeds the rated breaking capacity.

MCBs technical details

Coordination tables: back-up

Breaking capacities

Definition: B and C acc. to IEC EN 60 898, Icn

K and Z acc. to IEC EN 60 947-2, Icu

Type Tripping characteristic Nominal current	AC				DC	Back up protection up to ultimate short-circuit capacity of short-circuit protective device.	
	1 phase		2/3 phases		1phase	Fuse	Selective MCB
	133 V~	230 V~	230 V~ 133/230 V~	400 V~ 230/400 V~	60 V---	gG	S700
A	kA/cosj	kA/cosj	kA/cosj	kA/cosj	kA/T ≤ ms		
S 200 P-B	6				10/4,0	63 A	100 A
	10, 13	25/0,25	25/0,25	25/0,25	25/0,25	80 A	100 A
	16 ... 25					100 A	100 A
	32 ... 40					125 A	100 A
	50 ... 63	15/0,25	15/0,25	15/0,25	15/0,25	160 A	100 A
S 200 P-C	0,5 ... 2	100 kA				not required	
	3, 4					32 A	100 A
	6, 8					63 A	100 A
	10 ... 13	25/0,25	25/0,25	25/0,25	25/0,25	80 A	100 A
	16 ... 25					100 A	100 A
	32 ... 40					125 A	100 A
	50 ... 63	15/0,25	15/0,25	15/0,25	15/0,25	160 A	100 A
S 200 P-K, Z	0,5 ... 2	100 kA				not required	
	3					25 A	-
	4					35 A	-
	6					63 A	100 A
	8	25/0,25	25/0,25	25/0,25	25/0,25	80 A	100 A
	10 ... 20					100 A	100 A
	25					125 A	100 A
	32 ... 63	15/0,25	15/0,25	15/0,25	15/0,25	160 A	100 A

1. In symmetrically earthed DC networks 2 pole MCBs can be applied at up to 125 V DC (series connection). Polarity does not have to be considered. Thus any connection mode is permitted.

2. Back up protection is only required when the prospective short circuit current exceeds the rated breaking capacity.

MCBs technical details

Coordination tables: back-up

Fuse gG - MCB S 200, S 200 M

240 V	Supply s.	Fuse gG		S 700
Load s.	Characteristic	In [A]	In [A]	In [A]
S200 S200 M	B	6	63	100
		10...20	100	100
		25...32	100	100
		40	125	100
		50...63	160	100
S200 S200 M	C	3...4	20	—
		6	40	100
		8	63	100
		10...20	100	100
		25...32	100	100
		40	125	100
		50...63	160	100
		3	20	—
S200	K	4	25	—
		6...10	63	100
		16...20	80	100
		25...32	100	100
		40	125	100
		50...63	160	100
		3...4	20	—
		6	35	100
S200	Z	8	40	100
		10...16	63	100
		20...25	80	100
		32...40	100	100
		50...63	125	100

This table shows coordination between an MCB and the upstream fuse maximum current value. Combination of the two protections allows the breaking capacity to be elevated up to that of the combined fuse.

i.e. downstream MCB breaker S 201-C16, upstream fuse with In up to 100 A (breaking capacity: 100 kA). MCB breaker protection up to 100 kA.

MCBs technical details

Coordination tables: back-up

Fuse gG - MCB S 200 P

240 V		Supply s.		Fuse gG	S 700
Load s.	Characteristic	In [A]	In [A]	In [A]	
S200 P	B	6	63		100
		10, 13	80		100
		16...25	100		100
		32...40	125		100
		50...63	160		100
		3, 4	40		100
S200 P	C	6, 8	63		100
		10, 13	100		100
		16...25	100		100
		32...40	125		100
		50...63	160		100
		3	25		—
S200 P	K, Z	4	35		—
		6	63		100
		8	80		100
		10...20	100		100
		25	125		100
		32...63	160		100

This table shows coordination between an MCB and the upstream fuse maximum current value. Combination of the two protections allows the breaking capacity to be elevated up to that of the combined fuse.

I.e. downstream MCB breaker S 201-C16, upstream fuse with In up to 100 A (breaking capacity: 100 kA). MCB breaker protection up to 100 kA.

MCBs technical details

Coordination tables: selectivity

Selective protection

Selectivity between SN 201 and S 200 upstream and downstream modular circuit-breakers

In the case, selectivity is amperometric and so the selectivity

limit is given simply by the magnetic threshold of the upstream breaker, which is fixed. The selectivity value is obtained if a minimum ratio of 1.3 ($I_{n\text{ upstream}}/I_{n\text{ downstream}}$ > 1.3) is observed between the rated currents of the two breakers.

MCB - SN201 @ 230/240 V

		Supply S.2		S800 N-S							
Load S.1		Char.	B								
		Icu [kA]	36-50								
SN201 L	B, C	6	In [A]	25	32	40	50	63	80	100	125
			2		0.433	0.6	1.3	4	T	T	T
			4			0.45	0.8	1.5	2.5	4	T
			6				0.6	1.2	1.6	2.6	3.8
			10				0.5	1.1	1.4	2	3
			16					0.8	1.2	1.7	2.5
			20						1	1.5	2.1
			25							1.3	1.8
			32							1.1	1.7
			40								1.6
SN201	B, C, D	10	2		0.433	0.6	1.3	4	9	T	T
			4			0.45	0.8	1.5	2.5	4	7.3
			6				0.6	1.2	1.6	2.6	3.8
			10				0.5	1.1	1.4	2	3
			16					0.8	1.2	1.7	2.5
			20						1	1.5	2.1
			25							1.3	1.8
			32							1.1	1.7
			40								1.6
			2		0.433	0.6	1.3	4	9	T	T
SN201 M	B, C	10	4			0.45	0.8	1.5	2.5	4	7.3
			6				0.6	1.2	1.6	2.6	3.8
			10				0.5	1.1	1.4	2	3
			16					0.8	1.2	1.7	2.5
			20						1	1.5	2.1
			25							1.3	1.8
			32							1.1	1.7
			40								1.6

¹ Load side circuit-breaker 1P+N (230/240 V)

² For networks with 230/240 V AC \Rightarrow two-pole circuit-breaker (phase + neutral)

for networks at 400/415 V AC \Rightarrow four-pole circuit-breaker (load side circuit branched between one phase and the neutral)

³ Only for curve B

MCBs technical details

Coordination tables: selectivity

Example

Upstream circuit-breaker	S 200 P, curve D 50 A											
Downstream circuit-breaker	SN 201 L, curve B 10 A											
Selectivity limit	10 ln=500 A											

S800 N-S										S800 N-S										
C										D										
36-50										36-50										
25	32	40	50	63	80	100	125	25	32	40	50	63	80	100	125					
0.43	0.55	1.2	3	T	T	T	T	1.3	4.1	T	T	T	T	T	T	T	T	T	T	
	0.43	0.75	1.3	2.1	3.9	T	T	0.8	1.6	3	5.4	T	T	T	T	T	T	T	T	
		0.55	1.1	1.5	2.5	3.6	5.5	0.6	1.3	2	3.2	3.9	T	T	T	T	T	T	T	
		0.45	1	1.3	1.9	2.8	4.2	0.5	1.2	1.65	2.6	3.1	T	T	T	T	T	T	T	
			0.75	1.1	1.6	2.3	3.6		0.9	1.4	1.8	2.6	5	T	T					
				0.9	1.4	1.9	3.3			1.3	1.6	2.2	4.2	5.4	T					
					1.2	1.6	2.7				1.5	1.9	3.5	4.5	T					
						1	1.5	2.5				1.8	2.8	4.2	5.5					
							1.4	2.1				1.7	2.7	4	5					
0.43	0.55	1.2	3	6.6	T	T	T	1.3	4.1	T	T	T	T	T	T	T	T	T	T	
	0.43	0.75	1.3	2.1	3.9	6.6	T	0.8	1.6	3	5.4	7.6	T	T	T	T	T	T	T	
		0.55	1.1	1.5	2.5	3.6	5.5	0.6	1.3	2	3.2	3.9	8	T	T					
		0.45	1	1.3	1.9	2.8	4.2	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T					
			0.75	1.1	1.6	2.3	3.6		0.9	1.4	1.8	2.6	5	6.3	8.8					
				0.9	1.4	1.9	3.3			1.3	1.6	2.2	4.2	5.4	7.6					
					1.2	1.6	2.7				1.5	1.9	3.5	4.5	6.6					
						1	1.5	2.5				1.8	2.8	4.2	5.5					
							1.4	2.1				1.7	2.7	4	5					
0.43	0.55	1.2	3	6.6	T	T	T	1.3	4.1	T	T	T	T	T	T	T	T	T	T	
	0.43	0.75	1.3	2.1	3.9	6.6	T	0.8	1.6	3	5.4	7.6	T	T	T	T	T	T	T	
		0.55	1.1	1.5	2.5	3.6	5.5	0.6	1.3	2	3.2	3.9	8	T	T					
		0.45	1	1.3	1.9	2.8	4.2	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T					
			0.75	1.1	1.6	2.3	3.6		0.9	1.4	1.8	2.6	5	6.3	8.8					
				0.9	1.4	1.9	3.3			1.3	1.6	2.2	4.2	5.4	7.6					
					1.2	1.6	2.7				1.5	1.9	3.5	4.5	6.6					
						1	1.5	2.5				1.8	2.8	4.2	5.5					
							1.4	2.1				1.7	2.7	4	5					

MCBs technical details

Coordination tables: selectivity

Fuse - SN201 @ 230/240 V

	Im	Icu [kA]	In [A]	25	32	40	50	63	80	100	125
SN201 L	B-C	6	2	1.5	2.5	T	T	T	T	T	T
		6	4	1	2	4.5	T	T	T	T	T
		6	6	1	1.5	4	4.5	T	T	T	T
		6	10		1.2	3.5	4	T	T	T	T
		6	16		1	3	3.5	5	T	T	T
		6	20		1	3	3.5	5	T	T	T
		6	25		1	2	3	4.5	T	T	T
		6	32		1	2	3	4.5	5	T	T
		6	40			1.5	2.5	4	5	T	T
SN201	B-C-D	10	2	1.5	2.5	5	T	T	T	T	T
		10	4	1	2	4.5	5	T	T	T	T
		10	6	1	1.5	4	4.5	7	T	T	T
		10	10		1.2	3.5	4	6	T	T	T
		10	16		1	3	3.5	5	T	T	T
		10	20		1	3	3.5	5	8	T	T
		10	25		1	2	3	4.5	6.5	T	T
		10	32		1	2	3	4.5	5	8	T
		10	40			1.5	2.5	4	5	6.5	T
SN201 M	B-C	10	2	1.5	2.5	5	7	T	T	T	T
		10	4	1	2	4.5	5	8	T	T	T
		10	6	1	1.5	4	4.5	7	T	T	T
		10	10		1.2	3.5	4	6	T	T	T
		10	16		1	3	3.5	5	9	T	T
		10	20		1	3	3.5	5	8	T	T
		10	25		1	2	3	4.5	6.5	9	T
		10	32		1	2	3	4.5	5	8	T
		10	40			1.5	2.5	4	5	6.5	9

MCBs technical details

Coordination tables: selectivity

MCB S700 - SN201 @ 230/240 V

Im		E									
		Icu [kA]		25	25	25	25	25	25	25	25
		In [A]		20	25	35	40	50	63	80	100
SN201 L	B-C	6	2	T	T	T	T	T	T	T	T
		6	4	T	T	T	T	T	T	T	T
		6	6	T	T	T	T	T	T	T	T
		6	10	T	T	T	T	T	T	T	T
		6	16		T	T	T	T	T	T	T
		6	20			T	T	T	T	T	T
		6	25			T	T	T	T	T	T
		6	32					T	T	T	T
		6	40						T	T	T
SN201	B-C-D	10	2	T	T	T	T	T	T	T	T
		10	4	T	T	T	T	T	T	T	T
		10	6	T	T	T	T	T	T	T	T
		10	10	T	T	T	T	T	T	T	T
		10	16		T	T	T	T	T	T	T
		10	20			T	T	T	T	T	T
		10	25			T	T	T	T	T	T
		10	32					T	T	T	T
		10	40						T	T	T
SN201 M	B-C	10	2	T	T	T	T	T	T	T	T
		10	4	T	T	T	T	T	T	T	T
		10	6	T	T	T	T	T	T	T	T
		10	10	T	T	T	T	T	T	T	T
		10	16		T	T	T	T	T	T	T
		10	20			T	T	T	T	T	T
		10	25			T	T	T	T	T	T
		10	32					T	T	T	T
		10	40						T	T	T

MCBs technical details

Coordination tables: selectivity

MCCB @ 415 V - SN201 @ 230/240 V

			Supply S. T1															T2				
			Version B, C, N															N, S, H, L				
			Release TMD															TMD, MA				
			Iu [A] 160															160				
Load S.	Char.	Icu [kA]	In [A]	16	20	25	32	40	50	63	80	100	125	160 ²	160	16	20	25	32	40	50	
SN201 L	B, C	6	≤4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
	B, C		6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
	B, C		10		3	3	3	4.5	T	T	T	T	T	T			31	3	3	3	3	4.5
	B, C		16			3	4.5	5	T	T	T	T	T	T			31	3	3	4.5		
	B, C		20				3	5	T	T	T	T	T	T			31		3			
	B, C		25					5	T	T	T	T	T	T			31					
	B, C		32						T	T	T	T	T	T			31					
	B, C		40							T	T	T	T	T								
SN201	B, C, D, K	10	≤4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
	B, C, D, K		6	6	6	6	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T
	B, C, D, K		8		3	3	3	4.5	7.5	8.5	T	T	T	T			31	3	3	3	3	4.5
	B, C, D, K		10		3	3	3	4.5	7.5	8.5	T	T	T	T			31	3	3	3	3	4.5
	B, C, D, K		13			3	4.5	5	7.5	T	T	T	T	T			31	3	4.5			
	B, C, D, K		16				3	4.5	5	7.5	T	T	T	T			31	3	4.5			
	B, C, D, K		20					3	5	6	T	T	T	T			31		3			
	B, C, D, K		25						5	6	T	T	T	T			31					
	B, C, D, K		32							6	7.5	T	T	T			31					
	B, C, D, K		40								7.5	T	T	T								
SN201 M	B, C	10	≤4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
	B, C		6	6	6	6	6	6	12	T	T	T	T	T	T	T	T	T	T	T	T	T
	B, C		10		3	3	3	4.5	7.5	8.5	T	T	T	T	T		31	3	3	3	4.5	
	B, C		13			3	4.5	5	7.5	T	T	T	T	T			31	3	4.5			
	B, C		16				3	4.5	5	7.5	T	T	T	T	T		31	3	4.5			
	B, C		20					3	5	6	T	T	T	T	T		31		3			
	B, C		25						5	6	T	T	T	T	T		31					
	B, C		32							6	7.5	T	T	T	T		31					
	B, C		40								7.5	T	T	T	T							

Supply side circuit-breaker 4P (load side circuit branched between one phase and the neutral)

Load side circuit-breaker 1P+N (230/240 V)

1 Value valid for magnetic only supply side circuit-breaker

2 Neutral at 50%

MCBs technical details

Coordination tables: selectivity

MCBs technical details

Coordination tables: selectivity

MCCB XT1@415V - SN201 @230/240V

			Supply S.	XT1										
			Version	B,C,N,S,H										
			Release	TM										
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160
SN201 L	B,C	6	≤ 4	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	
			10			3	3	3	4,5	T	T	T	T	
			16				3	4,5	5	T	T	T	T	
			20					3	5	T	T	T	T	
			25						5	T	T	T	T	
			32							T	T	T	T	
			40							T	T	T	T	
SN201	B,C,D,K	10	≤ 4	T	T	T	T	T	T	T	T	T	T	
			6	6	6	6	6	6	T	T	T	T	T	
			8		3	3	3	4,5	7,5	8,5	T	T	T	
			10		3	3	3	4,5	7,5	8,5	T	T	T	
			13			3	4,5	5	7,5	T	T	T	T	
			16				3	4,5	5	7,5	T	T	T	
			20					3	5	6	T	T	T	
			25						5	6	T	T	T	
SN201 M	B,C	10	32							6	7,5	T	T	
			40								7,5	T	T	
			≤ 4	T	T	T	T	T	T	T	T	T	T	
			6	6	6	6	6	6	T	T	T	T	T	
			10		3	3	3	4,5	7,5	8,5	T	T	T	
			13			3	4,5	5	7,5	T	T	T	T	
			16				3	4,5	5	7,5	T	T	T	
			20					3	5	6	T	T	T	
			25						5	6	T	T	T	
			32							6	7,5	T	T	
			40								7,5	T	T	

MCBs technical details

Coordination tables: selectivity

MCCB XT2@415V - SN201 @230/240V

			Supply S.		XT2														
			Version		N,S,H,L,V														
			Release		TM														
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160	10	25	63	100	160
SN201 L	B,C	6	≤ 4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10		3 ①	3	3	3	4,5	T	T	T	T	T	T	T	T	T	
			16			3 ①	3	4,5	5	T	T	T	T	T	T	T	T	T	
			20			3 ①		3	5	T	T	T	T	T	T	T	T	T	
			25				3 ①	5	T	T	T	T	T	T	T	T	T	T	
			32				3 ①		T	T	T	T	T	T	T	T	T	T	
			40						T	T	T	T	T	T	T	T	T	T	
SN201	B,C,D,K	10	≤ 4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			8		3 ①	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	
			10		3 ①	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	
			13			3 ①	3	4,5	5	7,5	T	T	T	T	T	T	T	T	
			16			3 ①	3	4,5	5	7,5	T	T	T	T	T	T	T	T	
			20			3 ①		3	5	6	T	T	T	T	T	T	T	T	
			25				3 ①	5	6	T	T	T	T	T	T	T	T	T	
			32				3 ①		6	7,5	T	T	T	T	T	T	T	T	
			40						6 1	7,5	T	T	T	T	T	T	T	T	
SN201 M	B,C	10	≤ 4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10		3 ①	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	
			13			3 ①	3	4,5	5	7,5	T	T	T	T	T	T	T	T	
			16			3 ①	3	4,5	5	7,5	T	T	T	T	T	T	T	T	
			20			3 ①		3	5	6	T	T	T	T	T	T	T	T	
			25				3 ①	5	6	T	T	T	T	T	T	T	T	T	
			32				3 ①		6	7,5	T	T	T	T	T	T	T	T	
			40						6 1	7,5	T	T	T	T	T	T	T	T	

① Value valid in case of Supply S. breaker only magnetic

MCBs technical details

Coordination tables: selectivity

MCCB XT3@415V - SN201 @230/240V

		Supply S.		XT3						
		Version		N,S						
		Release		TM						
Load S.	Char	Icu [kA]	In[A]	63	80	100	125	160	200	250
SN201 L	B,C	6	≤ 4	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T
			16	5	T	T	T	T	T	T
			20	5	T	T	T	T	T	T
			25	5	T	T	T	T	T	T
			32		T	T	T	T	T	T
			40		T	T	T	T	T	T
			≤ 4	T	T	T	T	T	T	T
SN201	B,C,D,K	10	6	T	T	T	T	T	T	T
			8	7,5	8,5	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T
			40		6 ①	7,5	T	T	T	T
			≤ 4	T	T	T	T	T	T	T
SN201 M	B,C	10	6	T	T	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T
			40		6 ①	7,5	T	T	T	T
			≤ 4	T	T	T	T	T	T	T

① Value valid in case of Supply S. breaker only magnetic

Tmax T1 – S800S @400/415V

MCBs technical details

Coordination tables: selectivity

S800S - S200 @ 230/400 V

		E.	S800S							
		Char.	B							
L.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200	B	10	6		0.4	0.5	0.7	1	1.5	2.6
			10			0.4	0.6	0.7	1	1.4
			13				0.5	0.7	0.9	1.3
			16					0.7	0.9	1.3
			20						0.9	1.3
			25						0.9	1.3
			32						0.8	1.1
			40						0.8	1.1
			50						1	
			63							0.9

		E.	S800S							
		Char.	B							
L.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200	C	10	0.5	T	T	T	T	T	T	T
			1	3.3	T	T	T	T	T	T
			1.6	0.6	1.3	T	T	T	T	T
			2	0.4	0.7	1.3	T	T	T	T
			3		0.4	0.6	0.7	1.1	2.6	T
			4		0.4	0.6	0.7	1	1.7	3.1
			6			0.4	0.5	0.7	1	1.5
			8				0.4	0.6	0.7	1
			10				0.4	0.6	0.7	1
			13					0.5	0.7	0.9
			16						0.7	0.9
			20							0.9
			25							0.9
			32							0.8
			40							0.8
			50							1
			63							0.9

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S										
		Char. B										
L.	Icu [kA]	50										
		In [A]	25	32	40	50	63	80	100	125		
S200	D	10	0.5	T	T	T	T	T	T	T		
			1	0.8	4.5	T	T	T	T	T		
			1.6	0.5	1	2.3	T	T	T	T		
			2	0.3	0.5	0.7	2.3	T	T	T		
			3		0.4	0.5	0.7	1.2	2.5	T		
			4		0.4	0.4	0.7	1	1.7	T		
			6				0.6	0.8	1.2	2		
			8					0.7	0.9	1.3		
			10						0.9	1.3		
			13							1		
			16							1.5		
			20									
			25									
			32									
			40									
			50									
			63									
		E. S800S										
		Char. B										
S200	K	10	Icu [kA]	50								
			In [A]	25	32	40	50	63	80	100	125	
			0.5	T	T	T	T	T	T	T	T	
			1	0.8	5	T	T	T	T	T	T	
			1.6	0.5	1	2.1	T	T	T	T	T	
			2	0.3	0.5	0.7	2.1	T	T	T	T	
			3		0.4	0.5	0.7	1.2	2.5	T	T	
			4		0.4	0.4	0.7	1	1.7	3	T	
			6				0.6	0.8	1.2	2	3.6	
			8					0.7	0.9	1.3	2	
			10						0.9	1.3	2	
			13							1	1.5	
			16								1.5	
			20									
			25									
			32									
			40									
			50									
			63									

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S									
		Char. C									
L.	Char.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125	
S200	B	10	6		0.4	0.5	0.7	0.9	1.4	2.4	4.8
			10		0.3	0.4	0.5	0.7	0.9	1.3	2
			13		0.3	0.4	0.5	0.7	0.9	1.3	1.9
			16		0.3	0.4	0.5	0.7	0.9	1.3	1.9
			20		0.4	0.5	0.7	0.9	1.2	1.8	
			25		0.4	0.5	0.7	0.9	1.2	1.8	
			32			0.5	0.6	0.8	1	1.4	
			40				0.6	0.8	1	1.4	
			50					0.7	0.9	1.3	
			63						0.9	1.2	

		E. S800S								
		Char. C								
L.	Char.	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S200	C	10	0.5	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T
			1.6	0.6	T	T	T	T	T	T
			2	0.5	1	T	T	T	T	T
			3	0.3	0.5	0.7	1.2	2.1	T	T
			4	0.3	0.4	0.7	1	1.5	2.6	T
			6		0.4	0.5	0.7	0.9	1.4	2.4
			8		0.3	0.4	0.5	0.7	0.9	1.3
			10		0.3	0.4	0.5	0.7	0.9	2
			13		0.3	0.4	0.5	0.7	0.9	1.3
			16		0.3	0.4	0.5	0.7	0.9	1.3
			20			0.4	0.5	0.7	0.9	1.2
			25			0.4	0.5	0.7	0.9	1.2
			32				0.5	0.6	0.8	1
			40					0.6	0.8	1
			50						0.7	0.9
			63							0.9

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S									
		Char. C									
L.	Icu [kA]	50									
		In [A]	25	32	40	50	63	80	100	125	
S200	D	0.5	T	T	T	T	T	T	T	T	
		1	2.1	T	T	T	T	T	T	T	
		1.6	0.8	2.3	T	T	T	T	T	T	
		2	0.4	0.7	2.3	T	T	T	T	T	
		3	0.3	0.5	0.7	1.2	2.2	T	T	T	
		4	0.3	0.4	0.7	1	1.4	2.6	T	T	
		6		0.4	0.6	0.8	1.1	1.8	3.2	T	
		8			0.5	0.7	0.9	1.2	1.8	2.8	
		10				0.7	0.9	1.2	1.8	2.8	
		13					0.7	1	1.4	2	
		16						1	1.4	2	
		20							1	1.4	
		25								1.4	
		32									
		40									
		50									
		63									
		E. S800S									
		Char. C									
S200	K	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125	
		0.5	T	T	T	T	T	T	T	T	
		1	2.1	T	T	T	T	T	T	T	
		1.6	0.8	2.3	T	T	T	T	T	T	
		2	0.4	0.7	2.3	T	T	T	T	T	
		3	0.3	0.5	0.7	1.2	2.2	T	T	T	
		4	0.3	0.4	0.7	1	1.4	2.6	T	T	
		6		0.4	0.6	0.8	1.1	1.8	3.2	T	
		8			0.5	0.7	0.9	1.2	1.8	2.8	
		10				0.7	0.9	1.2	1.8	2.8	
		13					0.7	1	1.4	2	
		16						1	1.4	2	
		20							1	1.4	
		25								1.4	
		32									
		40									
		50									
		63									

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S								
		Char: D								
L.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200	B	10	6	0.5	1	1.2	2	2.8	T	T
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9
			13	0.4	0.6	0.8	1.1	1.4	2.5	3.3
			16		0.6	0.8	1.1	1.4	2.5	3.3
			20			0.8	1.1	1.3	2.3	3
			25			0.8	1.1	1.3	2.3	3
			32				0.9	1.1	1.9	2.4
			40					1.1	1.9	2.4
			50						1.5	1.9
			63							1.7

		E. S800S								
		Char: D								
L.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200	C	10	0.5	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T
			1.6	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T
			3	0.7	2.2	4.4	T	T	T	T
			4	0.7	1.3	2.2	4.4	T	T	T
			6	0.5	1	1.2	2	2.8	T	T
			8	0.4	0.6	0.8	1.1	1.4	2.8	3.9
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9
			13	0.4	0.6	0.8	1.1	1.4	2.5	3.3

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S									
		Char: D									
L.	Icu [kA]	50									
		In [A]	25	32	40	50	63	80	100	125	
S200	D	0.5	T	T	T	T	T	T	T	T	
		1	T	T	T	T	T	T	T	T	
		1.6	T	T	T	T	T	T	T	T	
		2	2.3	T	T	T	T	T	T	T	
		3	0.7	1.3	4.4	T	T	T	T	T	
		4	0.7	1	2.2	4.4	T	T	T	T	
		6	0.6	0.8	1.5	2.5	3.6	T	T	T	
		8	0.5	0.7	1.1	1.5	2	4	5.5	T	
		10	0.5	0.7	1.1	1.5	2	4	5.5	T	
		13		0.6	0.9	1.2	1.5	2.6	3.4	5.2	
		16			0.9	1.2	1.5	2.6	3.4	5.2	
		20				0.9	1.1	1.8	2.2	3.2	
		25					1.1	1.8	2.2	3.2	
		32						1.7	2	2.9	
		40							1.9	2.6	
		50								2.2	
		63									
		E. S800S									
		Char: D									
S200	K	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125	
		0.5	T	T	T	T	T	T	T	T	
		1	T	T	T	T	T	T	T	T	
		1.6	T	T	T	T	T	T	T	T	
		2	2.3	T	T	T	T	T	T	T	
		3	0.7	1.3	4.4	T	T	T	T	T	
		4	0.7	1	2.2	4.4	T	T	T	T	
		6	0.6	0.8	1.5	2.5	3.6	T	T	T	
		8	0.5	0.7	1.1	1.5	2	4	5.5	T	
		10	0.5	0.7	1.1	1.5	2	4	5.5	T	
		13		0.6	0.9	1.2	1.5	2.6	3.4	5.2	
		16			0.9	1.2	1.5	2.6	3.4	5.2	
		20				0.9	1.1	1.8	2.2	3.2	
		25					1.1	1.8	2.2	3.2	
		32						1.7	2	2.9	
		40							1.9	2.6	
		50								2.2	
		63									

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

S800S - S200 M @ 230/400 V

		E.	S800S							
		Char.	B							
L.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200M	B	15	6		0.4	0.5	0.7	1	1.5	2.6
			10			0.4	0.6	0.7	1	1.4
			13				0.5	0.7	0.9	1.3
			16					0.7	0.9	1.3
			20						0.9	1.3
			25						0.9	1.3
			32						0.8	1.1
			40						0.8	1.1
			50						1	
			63							0.9

		E.	S800S							
		Char.	B							
L.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200M	C	15	0.5	T	T	T	T	T	T	T
			1	3.3	T	T	T	T	T	T
			1.6	0.6	1.3	T	T	T	T	T
			2	0.4	0.7	1.3	T	T	T	T
			3		0.4	0.6	0.7	1.1	2.6	8.8
			4		0.4	0.6	0.7	1	1.7	3.1
			6			0.4	0.5	0.7	1	1.5
			8				0.4	0.6	0.7	1
			10				0.4	0.6	0.7	1
			13					0.5	0.7	0.9
			16						0.7	0.9
			20							0.9
			25							0.9
			32							0.8
			40							0.8
			50							1
			63							0.9

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S									
		Char. B									
L.	Icu [kA]	50									
		In [A]	25	32	40	50	63	80	100	125	
S200M	D	15	0.5	T	T	T	T	T	T	T	
			1	0.8	5	T	T	T	T	T	
			1.6	0.5	1	2.3	T	T	T	T	
			2	0.3	0.5	0.7	2.3	T	T	T	
			3		0.4	0.5	0.7	1.2	2.5	8.6	
			4		0.4	0.4	0.7	1	1.7	3	
			6				0.6	0.8	1.2	3.6	
			8					0.7	0.9	1.3	
			10						0.9	1.3	
			13							1	
			16							1.5	
			20								
			25								
			32								
			40								
			50								
			63								
		E. S800S									
		Char. B									
L.	Icu [kA]	50									
		In [A]	25	32	40	50	63	80	100	125	
S200M	K	15	0.5	T	T	T	T	T	T	T	
			1	0.8	5	T	T	T	T	T	
			1.6	0.5	1	2.3	T	T	T	T	
			2	0.3	0.5	0.7	2.3	T	T	T	
			3		0.4	0.5	0.7	1.2	2.5	8.6	
			4		0.4	0.4	0.7	1	1.7	3	
			6				0.6	0.8	1.2	3.6	
			8					0.7	0.9	1.3	
			10						0.9	1.3	
			13							1	
			16							1.5	
			20								
			25								
			32								
			40								
			50								
			63								

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S									
		Char. C									
L.	Char.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125	
S200M	B	15	6		0.4	0.5	0.7	0.9	1.4	2.4	4.8
			10		0.3	0.4	0.5	0.7	0.9	1.3	2
			13		0.3	0.4	0.5	0.7	0.9	1.3	1.9
			16		0.3	0.4	0.5	0.7	0.9	1.3	1.9
			20		0.4	0.5	0.7	0.9	1.2	1.8	
			25		0.4	0.5	0.7	0.9	1.2	1.8	
			32			0.5	0.6	0.8	1	1.4	
			40				0.6	0.8	1	1.4	
			50					0.7	0.9	1.3	
			63						0.9	1.2	

		E. S800S								
		Char. C								
L.	Char.	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S200M	C	15	0.5	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T
			1.6	0.6	T	T	T	T	T	T
			2	0.5	1	T	T	T	T	T
			3	0.3	0.5	0.7	1.2	2.1	6.4	T
			4	0.3	0.4	0.7	1	1.5	2.6	6.1
			6		0.4	0.5	0.7	0.9	1.4	4.8
			8		0.3	0.4	0.5	0.7	0.9	1.3
			10		0.3	0.4	0.5	0.7	0.9	2
			13		0.3	0.4	0.5	0.7	0.9	1.3
			16		0.3	0.4	0.5	0.7	0.9	1.9
			20			0.4	0.5	0.7	0.9	1.2
			25			0.4	0.5	0.7	0.9	1.8
			32				0.5	0.6	0.8	1
			40					0.6	0.8	1
			50						0.7	0.9
			63							1.2

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S									
		Char. C									
L.	Icu [kA]	50									
		In [A]	25	32	40	50	63	80	100	125	
S200M	D	15	0.5	T	T	T	T	T	T	T	
			1	2.1	T	T	T	T	T	T	
			1.6	0.8	2.3	T	T	T	T	T	
			2	0.4	0.7	2.3	T	T	T	T	
			3	0.3	0.5	0.7	1.2	2.2	6.4	T	
			4	0.3	0.4	0.7	1	1.4	2.6	6.2	
			6		0.4	0.6	0.8	1.1	1.8	3.2	
			8			0.5	0.7	0.9	1.2	1.8	
			10				0.7	0.9	1.2	1.8	
			13					0.7	1	1.4	
			16						1	1.4	
			20							1	
			25							1.4	
			32								
			40								
			50								
			63								
		E. S800S									
		Char. C									
L.	Icu [kA]	50									
		In [A]	25	32	40	50	63	80	100	125	
S200M	K	15	0.5	T	T	T	T	T	T	T	
			1	2.1	T	T	T	T	T	T	
			1.6	0.8	2.3	T	T	T	T	T	
			2	0.4	0.7	2.3	T	T	T	T	
			3	0.3	0.5	0.7	1.2	2.2	6.4	T	
			4	0.3	0.4	0.7	1	1.4	2.6	6.2	
			6		0.4	0.6	0.8	1.1	1.8	3.2	
			8			0.5	0.7	0.9	1.2	1.8	
			10				0.7	0.9	1.2	1.8	
			13					0.7	1	1.4	
			16						1	1.4	
			20							1	
			25							1.4	
			32								
			40								
			50								
			63								

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S								
		Char. D								
L.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200M	B	6	0.5	1	1.2	2	2.8	T	T	T
		10	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
		13	0.4	0.6	0.8	1.1	1.4	2.5	3.3	5.6
		16		0.6	0.8	1.1	1.4	2.5	3.3	5.6
		20			0.8	1.1	1.3	2.3	3	4.7
		25				1.1	1.3	2.3	3	4.7
		32					0.9	1.1	1.9	2.4
		40						1.1	1.9	2.4
		50							1.5	1.9
		63								2.3
									1.7	2.3

		E. S800S								
		Char. D								
L.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S200M	C	0.5	T	T	T	T	T	T	T	T
		1	T	T	T	T	T	T	T	T
		1.6	T	T	T	T	T	T	T	T
		2	T	T	T	T	T	T	T	T
		3	0.7	2.2	4.4	T	T	T	T	T
		4	0.7	1.3	2.2	4.4	7.7	T	T	T
		6	0.5	1	1.2	2	2.8	9.9	T	T
		8	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
		10	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
		13	0.4	0.6	0.8	1.1	1.4	2.5	3.3	5.6
		16		0.6	0.8	1.1	1.4	2.5	3.3	5.6
		20			0.8	1.1	1.3	2.3	3	4.7
		25				1.1	1.3	2.3	3	4.7
		32					0.9	1.1	1.9	2.4
		40						1.1	1.9	2.4
		50							1.5	1.9
		63							1.7	2.3

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S										
		Char. D										
L.	Icu [kA]	50										
		In [A]	25	32	40	50	63	80	100	125		
S200M	D	15	0.5	T	T	T	T	T	T	T		
			1	T	T	T	T	T	T	T		
			1.6	T	T	T	T	T	T	T		
			2	2.3	T	T	T	T	T	T		
			3	0.7	1.3	4.4	T	T	T	T		
			4	0.7	1	2.2	4.4	7.7	T	T		
			6	0.6	0.8	1.5	2.5	3.6	T	T		
			8	0.5	0.7	1.1	1.5	2	4	5.5		
			10	0.5	0.7	1.1	1.5	2	4	T		
			13		0.6	0.9	1.2	1.5	2.6	3.4		
			16			0.9	1.2	1.5	2.6	3.4		
			20				0.9	1.1	1.8	2.2		
			25					1.1	1.8	2.2		
			32						1.7	2		
			40							1.9		
			50							2.6		
			63							2.2		
		E. S800S										
		Char. D										
S200M	K	15	Icu [kA]	50								
			In [A]	25	32	40	50	63	80	100	125	
			0.5	T	T	T	T	T	T	T	T	
			1	T	T	T	T	T	T	T	T	
			1.6	T	T	T	T	T	T	T	T	
			2	2.3	T	T	T	T	T	T	T	
			3	0.7	1.3	4.4	T	T	T	T	T	
			4	0.7	1	2.2	4.4	7.7	T	T	T	
			6	0.6	0.8	1.5	2.5	3.6	T	T	T	
			8	0.5	0.7	1.1	1.5	2	4	5.5	T	
			10	0.5	0.7	1.1	1.5	2	4	5.5	T	
			13		0.6	0.9	1.2	1.5	2.6	3.4	5.2	
			16			0.9	1.2	1.5	2.6	3.4	5.2	
			20				0.9	1.1	1.8	2.2	3.2	
			25					1.1	1.8	2.2	3.2	
			32						1.7	2	2.9	
			40							1.9	2.6	
			50								2.2	
			63									

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

S800S - S200 P @ 230/400 V

		E.	S800S							
		Char.	B							
L.	S200P	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
B	25	6			0.4	0.5	0.7	1	1.5	2.6
		10				0.4	0.6	0.7	1	1.4
		13					0.5	0.7	0.9	1.3
		16						0.7	0.9	1.3
		20							0.9	1.3
		25							0.9	1.3
		32							0.8	1.1
		40							0.8	1.1
		50							1	
		63								0.9

		E.	S800S							
		Char.	B							
L.	S200P	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
C	25	0.5	T	T	T	T	T	T	T	T
		1	3.3	T	T	T	T	T	T	T
		1.6	0.6	1.3	T	T	T	T	T	T
		2	0.4	0.7	1.2	T	T	T	T	T
		3		0.4	0.6	0.7	1.1	2.6	8.8	T
		4		0.4	0.6	0.7	1	1.7	3.1	7
		6			0.4	0.5	0.7	1	1.5	2.6
		8				0.4	0.6	0.7	1	1.4
		10				0.4	0.6	0.7	1	1.4
		13					0.5	0.7	0.9	1.3
15	25	16						0.7	0.9	1.3
		20							0.9	1.3
		25							0.9	1.3
		32							0.8	1.1
		40							0.8	1.1
15	15	50							1	
		63								0.9

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S								
		Char. B								
L.	Char.	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S200P	K	0.2	T	T	T	T	T	T	T	T
		0.3	T	T	T	T	T	T	T	T
		0.5	T	T	T	T	T	T	T	T
		0.75	T	T	T	T	T	T	T	T
		1	0.8	5	T	T	T	T	T	T
		1.6	0.5	1	2.3	T	T	T	T	T
		2	0.3	0.5	0.7	2.1	T	T	T	T
		3		0.4	0.5	0.7	1.2	2.5	8.6	T
		4		0.4	0.4	0.7	1	1.7	3	7.7
		6				0.6	0.8	1.2	2	3.6
		8					0.7	0.9	1.3	2
		10						0.9	1.3	2
		13							1	1.5
		16								1.5
		20								
		25								
		32								
		40								
		50								
		63								

		E. S800S								
		Char. C								
L.	Char.	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S200P	B	6			0.4	0.5	0.7	1	1.5	2.6
		10				0.4	0.6	0.7	1	1.4
		13					0.5	0.7	0.9	1.3
		16						0.7	0.9	1.3
		20							0.9	1.3
		25							0.9	1.3
		32							0.8	1.1
		40							0.8	1.1
		50							1	
		63								0.9

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S								
		Char. C								
L.	I _{cu} [kA]	50								
		I _n [A]	25	32	40	50	63	80	100	125
S200P	C	0.5	T	T	T	T	T	T	T	T
		1	3.3	T	T	T	T	T	T	T
		1.6	0.6	1.3	T	T	T	T	T	T
		2	0.4	0.7	1.3	T	T	T	T	T
		3		0.4	0.6	0.7	1.1	2.6	8.8	T
		4		0.4	0.6	0.7	1	1.7	3.1	7
		25	6		0.4	0.5	0.7	1	1.5	2.6
			8			0.4	0.6	0.7	1	1.4
			10			0.4	0.6	0.7	1	1.4
			13				0.5	0.7	0.9	1.3
			16					0.7	0.9	1.3
			20						0.9	1.3
			25						0.9	1.3
			32						0.8	1.1
		15	40						0.8	1.1
			50						1	
			63							0.9

		E. S800S								
		Char. C								
L.	I _{cu} [kA]	50								
		I _n [A]	25	32	40	50	63	80	100	125
S200P	K	0.2	T	T	T	T	T	T	T	T
		0.3	T	T	T	T	T	T	T	T
		0.5	T	T	T	T	T	T	T	T
		0.75	T	T	T	T	T	T	T	T
		1	0.8	5	T	T	T	T	T	T
		1.6	0.5	1	2.3	T	T	T	T	T
		2	0.3	0.5	0.7	2.3	T	T	T	T
		25	3		0.4	0.5	0.7	1.2	2.5	8.6
			4		0.4	0.4	0.7	1	1.7	3
			6			0.6	0.8	1.2	2	3.6
			8				0.7	0.9	1.3	2
			10					0.9	1.3	2
			13						1	1.5
			16							1.5
			20							
			25							
			32							
		15	40							
			50							
			63							

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S								
		D								
L.	Char.	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S200P	B	25	6	0.5	1	1.2	2	2.8	9.9	21.3
		10	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
		13	0.4	0.6	0.8	1.1	1.4	2.5	3.3	5.6
		16		0.6	0.8	1.1	1.4	2.5	3.3	5.6
		20			0.8	1.1	1.3	2.3	3	4.7
		25				1.1	1.3	2.3	3	4.7
		32				0.9	1.1	1.9	2.4	3.7
		40					1.1	1.9	2.4	3.7
		50						1.5	1.9	2.3
		63							1.7	2.3

		E. S800S								
		D								
L.	Char.	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S200P	C	25	0.5	T	T	T	T	T	T	T
		1	T	T	T	T	T	T	T	T
		1.6	T	T	T	T	T	T	T	T
		2	T	T	T	T	T	T	T	T
		3	0.7	2.2	4.4	T	T	T	T	T
		4	0.7	1.3	2.2	4.4	7.7	T	T	T
		6	0.5	1	1.2	2	2.8	9.9	22	T
		8	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
		10	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
		13	0.4	0.6	0.8	1.1	1.4	2.5	3.3	5.6
		16		0.6	0.8	1.1	1.4	2.5	3.3	5.6
		20			0.8	1.1	1.3	2.3	3	4.7
		25				1.1	1.3	2.3	3	4.7
		32				0.9	1.1	1.9	2.4	3.7
		40					1.1	1.9	2.4	3.7
		50						1.5	1.9	2.3
		63							1.7	2.3

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800S								
		D								
L.	Char.	Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S200P K	25	0.2	T	T	T	T	T	T	T	T
		0.3	T	T	T	T	T	T	T	T
		0.5	T	T	T	T	T	T	T	T
		0.75	T	T	T	T	T	T	T	T
		1	T	T	T	T	T	T	T	T
		1.6	T	T	T	T	T	T	T	T
		2	2.3	T	T	T	T	T	T	T
		3	0.7	1.3	4.4	T	T	T	T	T
		4	0.7	1	2.2	4.4	7.7	T	T	T
		6	0.6	0.8	1.5	2.5	3.6	12	24.2	T
		8	0.5	0.7	1.1	1.5	2	4	5.5	9.9
		10	0.5	0.7	1.1	1.5	2	4	5.5	9.9
		13		0.6	0.9	1.2	1.5	2.6	3.4	5.2
		16			0.9	1.2	1.5	2.6	3.4	5.2
		20				0.9	1.1	1.8	2.2	3.2
		25						1.8	2.2	3.2
	15	32						1.7	2	2.9
		40							1.9	2.6
		50								2.2
		63								

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

S800S – S400E/S450E @230/400V

		Supply s.		S800S							
		Char.		B							
Load s.		Icu [kA]		50							
		In [A]		25	32	40	50	63	80	100	125
S400E	B, C	Icn [kA]	6			0.4	0.5	0.6	0.9	1.4	2.4
S450E		6	10			0.4	0.5	0.7	0.9	1.3	
FS401E			13				0.5	0.7	0.9	1.2	
FS451E			16					0.7	0.9	1.2	
FS403E			20					0.9	1.2		
FS453E			25					0.9	1.2		
			32					0.7	1		
			40					0.7	1		
			50						0.9		
			63						0.9		

		Supply s.		S800S							
		Char.		C							
Load s.		Icu [kA]		50							
			In [A]	25	32	40	50	63	80	100	125
S400E	B, C	Icn [kA] 6	6		0.4	0.5	0.6	0.9	1.3	2.2	4.4
S450E			10		0.3	0.4	0.5	0.6	0.8	1.2	1.8
FS401E			13		0.3	0.4	0.5	0.6	0.8	1.2	1.7
FS451E			16		0.3	0.4	0.5	0.6	0.8	1.2	1.7
FS403E			20		0.4	0.5	0.6	0.8	1.1	1.6	
FS453E			25		0.4	0.5	0.6	0.8	1.1	1.6	
			32			0.4	0.5	0.7	0.9	1.3	
			40				0.5	0.7	0.9	1.3	
			50					0.7	0.9	1.2	
			63						0.8	1.1	

Supply s.		S800S										
Char.		D, K										
Load s.		Icu [kA]	50									
		In [A]	25	32	40	50	63	80	100	125		
S400E	B, C	Icn [kA] 6	6	0.5	0.9	1.1	1.8	2.5	T	T	T	
S450E			10	0.4	0.5	0.8	1	1.3	2.5	3.5	T	
FS401E			13	0.4	0.5	0.8	1	1.3	2.3	3	5.1	
FS451E			16	0.5	0.8	1	1.3	2.3	3	5.1		
FS403E			20		0.7	1	1.2	2.1	2.7	4.3		
FS453E			25		0.7	1	1.2	2.1	2.7	4.3		
			32			0.9	1	1.7	2.2	3.4		
			40				1	1.7	2.2	3.4		
			50					1.4	1.7	2.1		
			63						1.6	2.1		

MCBs technical details

Coordination tables: selectivity

S800S – S400M @230/400V

	Supply s.		S800S							
	Char.		B							
Load s.		Icu [kA]	50							
		In [A]	25	32	40	50	63	80	100	125
S400M	B	Icn [kA]	6		0.4	0.5	0.6	0.9	1.4	2.4
S450M			10			0.4	0.5	0.7	0.9	1.3
FS401M			13				0.5	0.7	0.9	1.2
FS451M			16					0.7	0.9	1.2
FS403M			20					0.9	1.2	
FS453M			25					0.9	1.2	
			32					0.7	1	
			40					0.7	1	
			50						0.9	
			63							0.9

MCBs technical details

Coordination tables: selectivity

S800S – S400M @230/400V

MCBs technical details

Coordination tables: selectivity

MCBs technical details

Coordination tables: selectivity

S800S – S400M @230/400V

		Supply s.		S800S							
		Char.		D, K							
Load s.	Icu [kA]	50									
		In [A]	25	32	40	50	63	80	100	125	
S400M S450M FS401M FS451M FS403M FS453M	B	Icn [kA] 10	6	0.5	0.9	1.1	1.8	2.5	9	T	T
			10	0.4	0.5	0.8	1	1.3	2.5	3.5	6.7
			13	0.4	0.5	0.8	1	1.3	2.3	3	5.5
			16		0.5	0.8	1	1.3	2.3	3	5.1
			20			0.7	1	1.2	2.1	2.7	4.3
			25			0.7	1	1.2	2.1	2.7	4.3
			32				0.9	1	1.7	2.2	3.4
			40					1	1.7	2.2	3.4
			50						1.4	1.7	2.1
			63						1.6	2.1	

		Supply s.		S800S							
		Char.		D, K							
Load s.	Icu [kA]	50									
		In [A]	25	32	40	50	63	80	100	125	
S400M S450M FS401M FS451M FS403M FS453M	C	50	0.5	T	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T	T
			1.6	T	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T	T
		25	3	0.7	2	4	T	T	T	T	T
			4	0.6	1.2	2	4	7	T	T	T
			6	0.5	0.9	1.1	1.8	2.5	9	T	T
			8	0.4	0.5	0.8	1	1.3	2.5	3.5	6.7
			10	0.4	0.5	0.8	1	1.3	2.5	3.5	6.7
			13	0.4	0.5	0.8	1	1.3	2.3	3	2.1
			16		0.5	0.8	1	1.3	2.3	3	5.1
			20			0.7	1	1.2	2.1	2.7	4.3
		15	25			0.7	1	1.2	2.1	2.7	4.3
			32				0.9	1	1.7	2.2	3.4
			40					1	1.7	2.2	3.4
			50						1.4	1.7	2.1
			63						1.6	2.1	

MCBs technical details

Coordination tables: selectivity

		Supply s.		S800S						
		Char.		D, K						
Load s.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S400M S450M	D	Icn [kA] 10	6	0.5	0.8	1.4	2.3	3.3	T	T
			8	0.5	0.6	1	1.4	1.8	3.6	5
			10	0.5	0.6	1	1.4	1.8	3.6	5
			13		0.5	0.8	1.1	1.4	2.4	3.1
			16			0.8	1.1	1.4	2.4	3.1
			20				0.8	1	1.6	2
			25					1	1.6	2
			32						1.5	1.8
			40						1.7	2.4
			50							2
			63							

		Supply s.		S800S						
		Char.		D, K						
Load s.	Icu [kA]	50								
		In [A]	25	32	40	50	63	80	100	125
S400M S450M	K	50	0.5	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T
			1.6	T	T	T	T	T	T	T
			2	2.1	T	T	T	T	T	T
		25	3	0.7	1.2	4	T	T	T	T
			4	0.6	0.9	2	4	7	T	T
			6	0.5	0.8	1.4	2.3	3.3	T	T
			8	0.5	0.6	1	1.4	1.8	3.6	5
			10	0.5	0.6	1	1.4	1.8	3.6	5
			13		0.5	0.8	1.1	1.4	2.4	3.1
			16			0.8	1.1	1.4	2.4	3.1
			20				0.8	1	1.6	2
		10	25					1	1.6	2
			32						1.5	1.8
			40						1.7	2.4
			50							2
			63							

MCBs technical details

Coordination tables: selectivity

S800N - S200 @ 230/400 V

		E.	S800N							
		Char.	B							
L.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
S200	B	10	6		0.4	0.5	0.7	1	1.5	2.6
		10				0.4	0.6	0.7	1	1.4
		13					0.5	0.7	0.9	1.3
		16						0.7	0.9	1.3
		20							0.9	1.3
		25							0.9	1.3
		32							0.8	1.1
		40							0.8	1.1
		50							1	
		63								0.9

		E.	S800N							
		Char.	B							
L.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
S200	C	10	0.5	T	T	T	T	T	T	T
		1	3.3	T	T	T	T	T	T	T
		1.6	0.6	1.3	T	T	T	T	T	T
		2	0.4	0.7	1.2	T	T	T	T	T
		3		0.4	0.6	0.7	1.1	2.6	T	T
		4		0.4	0.6	0.7	1	1.7	3.1	T
		6			0.4	0.5	0.7	1	1.5	2.6
		8				0.4	0.6	0.7	1	1.4
		10				0.4	0.6	0.7	1	1.4
		13					0.5	0.7	0.9	1.3
		16						0.7	0.9	1.3
		20							0.9	1.3
		25							0.9	1.3
		32							0.8	1.1
		40							0.8	1.1
		50							1	
		63								0.9

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N									
		B									
L.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
S200 D	10	0.5	T	T	T	T	T	T	T	T	
		1	0.8	5	T	T	T	T	T	T	
		1.6	0.5	1	2.3	T	T	T	T	T	
		2	0.3	0.5	0.7	2.3	T	T	T	T	
		3		0.4	0.5	0.7	1.2	2.5	T	T	
		4		0.4	0.4	0.7	1	1.7	3	T	
		6				0.6	0.8	1.2	2	3.6	
		8					0.7	0.9	1.3	2	
		10						0.9	1.3	2	
		13							1	1.5	
		16								1.5	
		20									
		25									
		32									
		40									
		50									
		63									
		E. S800N									
		B									
L.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
S200 K	10	0.5	T	T	T	T	T	T	T	T	
		1	0.8	5	T	T	T	T	T	T	
		1.6	0.5	1	2.3	T	T	T	T	T	
		2	0.3	0.5	0.7	2.3	T	T	T	T	
		3		0.4	0.5	0.7	1.2	2.5	T	T	
		4		0.4	0.4	0.7	1	1.7	3	T	
		6				0.6	0.8	1.2	2	3.6	
		8					0.7	0.9	1.3	2	
		10						0.9	1.3	2	
		13							1	1.5	
		16								1.5	
		20									
		25									
		32									
		40									
		50									
		63									

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N									
		Char. C									
L.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
S200	B	10	6		0.4	0.5	0.7	0.9	1.4	2.4	4.8
			10		0.3	0.4	0.5	0.7	0.9	1.3	2
			13		0.3	0.4	0.5	0.7	0.9	1.3	1.9
			16		0.3	0.4	0.5	0.7	0.9	1.3	1.9
			20			0.4	0.5	0.7	0.9	1.2	1.8
			25			0.4	0.5	0.7	0.9	1.2	1.8
			32				0.5	0.6	0.8	1	1.4
			40					0.6	0.8	1	1.4
			50						0.7	0.9	1.3
			63							0.9	1.2

		E. S800N									
		Char. C									
L.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
S200	C	10	0.5	T	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T	T
			1.6	0.6	T	T	T	T	T	T	T
			2	0.5	1	T	T	T	T	T	T
			3	0.3	0.5	0.7	1.2	2.1	T	T	T
			4	0.3	0.4	0.7	1	1.5	2.6	T	T
			6		0.4	0.5	0.7	0.9	1.4	2.4	4.8
			8		0.3	0.4	0.5	0.7	0.9	1.3	2
			10		0.3	0.4	0.5	0.7	0.9	1.3	2
			13		0.3	0.4	0.5	0.7	0.9	1.3	1.9
			16		0.3	0.4	0.5	0.7	0.9	1.3	1.9
			20			0.4	0.5	0.7	0.9	1.2	1.8
			25			0.4	0.5	0.7	0.9	1.2	1.8
			32				0.5	0.6	0.8	1	1.4
			40					0.6	0.8	1	1.4
			50						0.7	0.9	1.3
			63							0.9	1.2

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N									
		C									
L.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
S200	D	10	0.5	T	T	T	T	T	T	T	T
			1	2.1	T	T	T	T	T	T	T
			1.6	0.8	2.3	T	T	T	T	T	T
			2	0.4	0.7	2.3	T	T	T	T	T
			3	0.3	0.5	0.7	1.2	2.2	T	T	T
			4	0.3	0.4	0.7	1	1.4	2.6	T	T
			6		0.4	0.6	0.8	1.1	1.8	3.2	T
			8			0.5	0.7	0.9	1.2	1.8	2.8
			10				0.7	0.9	1.2	1.8	2.8
			13					0.7	1	1.4	2
			16						1	1.4	2
			20							1	1.4
			25								1.4
			32								
			40								
			50								
			63								
		E. S800N									
		C									
S200	K	10	Icu [kA]	36							
				In [A]	25	32	40	50	63	80	100
			0.5	T	T	T	T	T	T	T	T
			1	2.1	T	T	T	T	T	T	T
			1.6	0.8	2.3	T	T	T	T	T	T
			2	0.4	0.7	2.3	T	T	T	T	T
			3	0.3	0.5	0.7	1.2	2.2	T	T	T
			4	0.3	0.4	0.7	1	1.4	2.6	T	T
			6		0.4	0.6	0.8	1.1	1.8	3.2	T
			8			0.5	0.7	0.9	1.2	1.8	2.8
			10				0.7	0.9	1.2	1.8	2.8
			13					0.7	1	1.4	2
			16						1	1.4	2
			20							1	1.4
			25								1.4
			32								
			40								
			50								
			63								

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N								
		Char.	D							
L.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
S200	B	10	6	0.5	1	1.2	2	2.8	T	T
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9
			13	0.4	0.6	0.8	1.1	1.4	2.5	3.3
			16		0.6	0.8	1.1	1.4	2.5	3.3
			20			0.8	1.1	1.3	2.3	3
			25				1.1	1.3	2.3	3
			32				0.9	1.1	1.9	2.4
			40					1.1	1.9	2.4
			50						1.5	1.9
			63							1.7
S200	C	10	0.5	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T
			1.6	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T
			3	0.7	2.2	4.4	T	T	T	T
			4	0.7	1.3	2.2	4.4	T	T	T
			6	0.5	1	1.2	2	2.8	T	T
			8	0.4	0.6	0.8	1.1	1.4	2.8	3.9
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9
			13	0.4	0.6	0.8	1.1	1.4	2.5	3.3
			16		0.6	0.8	1.1	1.4	2.5	3.3
			20			0.8	1.1	1.3	2.3	3
			25				1.1	1.3	2.3	3
			32				0.9	1.1	1.9	2.4
			40					1.1	1.9	2.4
			50						1.5	1.9
			63							1.7

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N									
		Char. D									
L.	Char.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125	
S200	D	0.5	T	T	T	T	T	T	T	T	
		1	T	T	T	T	T	T	T	T	
		1.6	T	T	T	T	T	T	T	T	
		2	2.3	T	T	T	T	T	T	T	
		3	0.7	1.3	4.4	T	T	T	T	T	
		4	0.7	1	2.2	4.4	T	T	T	T	
		6	0.6	0.8	1.5	2.5	3.6	T	T	T	
		8	0.5	0.7	1.1	1.5	2	4	5.5	T	
		10	0.5	0.7	1.1	1.5	2	4	5.5	T	
		13		0.6	0.9	1.2	1.5	2.6	3.4	5.2	
		16			0.9	1.2	1.5	2.6	3.4	5.2	
		20				0.9	1.1	1.8	2.2	3.2	
		25					1.1	1.8	2.2	3.2	
		32						1.7	2	2.9	
		40							1.9	2.6	
		50								2.2	
		63									
		E. S800N									
		Char. D									
S200	K	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125	
		0.5	T	T	T	T	T	T	T	T	
		1	T	T	T	T	T	T	T	T	
		1.6	T	T	T	T	T	T	T	T	
		2	2.3	T	T	T	T	T	T	T	
		3	0.7	1.3	4.4	T	T	T	T	T	
		4	0.7	1	2.2	4.4	T	T	T	T	
		6	0.6	0.8	1.5	2.5	3.6	T	T	T	
		8	0.5	0.7	1.1	1.5	2	4	5.5	T	
		10	0.5	0.7	1.1	1.5	2	4	5.5	T	
		13		0.6	0.9	1.2	1.5	2.6	3.4	5.2	
		16			0.9	1.2	1.5	2.6	3.4	5.2	
		20				0.9	1.1	1.8	2.2	3.2	
		25					1.1	1.8	2.2	3.2	
		32						1.7	2	2.9	
		40							1.9	2.6	
		50								2.2	
		63									

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

S800N - S200M @ 230/400 V

		E. S800N									
		Char. B									
L.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S200M	B	6			0.4	0.5	0.7	1	1.5	2.6	
		10				0.4	0.6	0.7	1	1.4	
		13					0.5	0.7	0.9	1.3	
		16						0.7	0.9	1.3	
		20							0.9	1.3	
		25							0.9	1.3	
		32							0.8	1.1	
		40							0.8	1.1	
		50							1		
		63								0.9	

		E. S800N									
		Char. B									
L.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S200M	C	0.5	T	T	T	T	T	T	T	T	
		1	3.3	T	T	T	T	T	T	T	
		1.6	0.6	1.3	T	T	T	T	T	T	
		2	0.4	0.7	1.3	T	T	T	T	T	
		3		0.4	0.6	0.7	1.1	2.6	8.8	T	
		4		0.4	0.6	0.7	1	1.7	3.1	7	
		6			0.4	0.5	0.7	1	1.5	2.6	
		8				0.4	0.6	0.7	1	1.4	
		10				0.4	0.6	0.7	1	1.4	
		13					0.5	0.7	0.9	1.3	
		16						0.7	0.9	1.3	
		20							0.9	1.3	
		25							0.9	1.3	
		32							0.8	1.1	
		40							0.8	1.1	
		50							1		
		63								0.9	

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N									
		Char. B									
L.	Char.	Icu [kA] 36									
		In [A]	25	32	40	50	63	80	100	125	
S200M	D	0.5	T	T	T	T	T	T	T	T	
		1	0.8	5	T	T	T	T	T	T	
		1.6	0.5	1	2.3	T	T	T	T	T	
		2	0.3	0.5	0.7	2.3	T	T	T	T	
		3		0.4	0.5	0.7	1.2	2.5	8.6	T	
		4		0.4	0.4	0.7	1	1.7	3	7.7	
		6				0.6	0.8	1.2	2	3.6	
		8					0.7	0.9	1.3	2	
		15	10					0.9	1.3	2	
		13							1	1.5	
		16								1.5	
		20									
		25									
		32									
		40									
		50									
		63									
		E. S800N									
		Char. B									
S200M	K	0.5	T	T	T	T	T	T	T	T	
		1	0.8	5	T	T	T	T	T	T	
		1.6	0.5	1	2.3	T	T	T	T	T	
		2	0.3	0.5	0.7	2.3	T	T	T	T	
		3		0.4	0.5	0.7	1.2	2.5	8.6	T	
		4		0.4	0.4	0.7	1	1.7	3	7.7	
		6				0.6	0.8	1.2	2	3.6	
		8					0.7	0.9	1.3	2	
		15	10					0.9	1.3	2	
		13							1	1.5	
		16								1.5	
		20									
		25									
		32									
		40									
		50									
		63									

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N								
		Char. C								
L.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
S200M	B	6		0.4	0.5	0.7	0.9	1.4	2.4	4.8
		10		0.3	0.4	0.5	0.7	0.9	1.3	2
		13		0.3	0.4	0.5	0.7	0.9	1.3	1.9
		16		0.3	0.4	0.5	0.7	0.9	1.3	1.9
		20			0.4	0.5	0.7	0.9	1.2	1.8
		25			0.4	0.5	0.7	0.9	1.2	1.8
		32				0.5	0.6	0.8	1	1.4
		40					0.6	0.8	1	1.4
		50						0.7	0.9	1.3
		63							0.9	1.2

		E. S800N								
		Char. C								
L.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
S200M	C	0.5	T	T	T	T	T	T	T	T
		1	T	T	T	T	T	T	T	T
		1.6	0.6	T	T	T	T	T	T	T
		2	0.5	1	T	T	T	T	T	T
		3	0.3	0.5	0.7	1.2	2.1	6.4	T	T
		4	0.3	0.4	0.7	1	1.5	2.6	6.1	T
		6		0.4	0.5	0.7	0.9	1.4	2.4	4.8
		8		0.3	0.4	0.5	0.7	0.9	1.3	2
		10		0.3	0.4	0.5	0.7	0.9	1.3	2
		13		0.3	0.4	0.5	0.7	0.9	1.3	1.9
		16		0.3	0.4	0.5	0.7	0.9	1.3	1.9
		20			0.4	0.5	0.7	0.9	1.2	1.8
		25			0.4	0.5	0.7	0.9	1.2	1.8
		32				0.5	0.6	0.8	1	1.4
		40					0.6	0.8	1	1.4
		50						0.7	0.9	1.3
		63							0.9	1.2

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N									
		Char. C									
L.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S200M	D	0.5	T	T	T	T	T	T	T	T	
		1	2.1	T	T	T	T	T	T	T	
		1.6	0.8	2.3	T	T	T	T	T	T	
		2	0.4	0.7	2.3	T	T	T	T	T	
		3	0.3	0.5	0.7	1.2	2.2	6.4	T	T	
		4	0.3	0.4	0.7	1	1.4	2.6	6.2	T	
		6		0.4	0.6	0.8	1.1	1.8	3.2	6.4	
		8			0.5	0.7	0.9	1.2	1.8	2.8	
		15	10			0.7	0.9	1.2	1.8	2.8	
		13				0.7	1	1.4	2		
		16					1	1.4	2		
		20						1	1.4		
		25							1	1.4	
		32									
		40									
		50									
		63									
		E. S800N									
Char.		C									
L.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S200M	K	0.5	T	T	T	T	T	T	T	T	
		1	2.1	T	T	T	T	T	T	T	
		1.6	0.8	2.3	T	T	T	T	T	T	
		2	0.4	0.7	2.3	T	T	T	T	T	
		3	0.3	0.5	0.7	1.2	2.2	6.4	T	T	
		4	0.3	0.4	0.7	1	1.4	2.6	6.2	T	
		6		0.4	0.6	0.8	1.1	1.8	3.2	6.4	
		8			0.5	0.7	0.9	1.2	1.8	2.8	
		15	10			0.7	0.9	1.2	1.8	2.8	
		13				0.7	1	1.4	2		
		16					1	1.4	2		
		20						1	1.4		
		25							1	1.4	
		32									
		40									
		50									
		63									

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N									
		D									
L.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
S200M	B	15	6	0.5	1	1.2	2	2.8	T	T	T
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
			13	0.4	0.6	0.8	1.1	1.4	2.5	3.3	5.6
			16		0.6	0.8	1.1	1.4	2.5	3.3	5.6
			20			0.8	1.1	1.3	2.3	3	4.7
			25				1.1	1.3	2.3	3	4.7
			32					0.9	1.1	1.9	2.4
			40						1.1	1.9	2.4
			50							1.5	1.9
			63								1.7

		E. S800N									
		D									
L.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
S200M	C	15	0.5	T	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T	T
			1.6	T	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T	T
			3	0.7	2.2	4.4	T	T	T	T	T
			4	0.7	1.3	2.2	4.4	7.7	T	T	T
			6	0.5	1	1.2	2	2.8	T	T	T
			8	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
			13	0.4	0.6	0.8	1.1	1.4	2.5	3.3	5.6

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N									
		D									
L.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
S200M	D	15	0.5	T	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T	T
			1.6	T	T	T	T	T	T	T	T
			2	2.3	T	T	T	T	T	T	T
			3	0.7	1.3	4.4	T	T	T	T	T
			4	0.7	1	2.2	4.4	7.7	T	T	T
			6	0.6	0.8	1.5	2.5	3.6	T	T	T
			8	0.5	0.7	1.1	1.5	2	4	5.5	T
			10	0.5	0.7	1.1	1.5	2	4	5.5	T
			13		0.6	0.9	1.2	1.5	2.6	3.4	5.2
			16			0.9	1.2	1.5	2.6	3.4	5.2
			20				0.9	1.1	1.8	2.2	3.2
			25					1.1	1.8	2.2	3.2
			32						1.7	2	2.9
			40							1.9	2.6
			50								2.2
			63								
S200M	K	15	0.5	T	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T	T
			1.6	T	T	T	T	T	T	T	T
			2	2.3	T	T	T	T	T	T	T
			3	0.7	1.3	4.4	T	T	T	T	T
			4	0.7	1	2.2	4.4	7.7	T	T	T
			6	0.6	0.8	1.5	2.5	3.6	T	T	T
			8	0.5	0.7	1.1	1.5	2	4	5.5	T
			10	0.5	0.7	1.1	1.5	2	4	5.5	T
			13		0.6	0.9	1.2	1.5	2.6	3.4	5.2
			16			0.9	1.2	1.5	2.6	3.4	5.2
			20				0.9	1.1	1.8	2.2	3.2
			25					1.1	1.8	2.2	3.2
			32						1.7	2	2.9
			40							1.9	2.6
			50								2.2
			63								

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

S800N - S200P @ 230/400 V

		E.	S800N							
		Char.	B							
L.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
S200P	C	0.5	T	T	T	T	T	T	T	T
		1	3.3	T	T	T	T	T	T	T
		1.6	0.6	1.3	T	T	T	T	T	T
		2	0.4	0.7	1.3	T	T	T	T	T
		3		0.4	0.6	0.7	1.1	2.6	8.8	T
		4		0.4	0.6	0.7	1	1.7	3.1	7
		25	6		0.4	0.5	0.7	1	1.5	2.6
		8				0.4	0.6	0.7	1	1.4
		10				0.4	0.6	0.7	1	1.4
		13					0.5	0.7	0.9	1.3
	P	16						0.7	0.9	1.3
		20							0.9	1.3
		25							0.9	1.3
		32							0.8	1.1
		40							0.8	1.1
	N	50								1
		63								0.9

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N								
		Char. B								
L.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
S200P K	25	0.2	T	T	T	T	T	T	T	T
		0.3	T	T	T	T	T	T	T	T
		0.5	T	T	T	T	T	T	T	T
		0.75	T	T	T	T	T	T	T	T
		1	0.8	5	T	T	T	T	T	T
		1.6	0.5	1	2.3	T	T	T	T	T
		2	0.3	0.5	0.7	2.1	T	T	T	T
		3		0.4	0.5	0.7	1.2	2.5	8.6	T
		4		0.4	0.4	0.7	1	1.7	3	7.7
		6				0.6	0.8	1.2	2	3.6
	15	8					0.7	0.9	1.3	2
		10						0.9	1.3	2
		13							1	1.5
		16								1.5
		20								
		25								
		32								
		40								
		50								
		63								

		E. S800N								
		Char. C								
L.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
S200P B	25	6			0.4	0.5	0.7	1	1.5	2.6
		10				0.4	0.6	0.7	1	1.4
		13					0.5	0.7	0.9	1.3
		16						0.7	0.9	1.3
		20							0.9	1.3
	15	25							0.9	1.3
		32							0.8	1.1
		40							0.8	1.1
		50							1	
		63								0.9

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N								
		Char. C								
L.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
S200P C	25	0.5	T	T	T	T	T	T	T	T
		1	3.3	T	T	T	T	T	T	T
		1.6	0.6	1.3	T	T	T	T	T	T
		2	0.4	0.7	1.3	T	T	T	T	T
		3		0.4	0.6	0.7	1.1	2.6	8.8	T
		4		0.4	0.6	0.7	1	1.7	3.1	7
		6			0.4	0.5	0.7	1	1.5	2.6
		8				0.4	0.6	0.7	1	1.4
		10				0.4	0.6	0.7	1	1.4
		13					0.5	0.7	0.9	1.3
	15	16						0.7	0.9	1.3
		20							0.9	1.3
		25							0.9	1.3
		32							0.8	1.1
		40							0.8	1.1
	15	50								1
		63								0.9

		E. S800N								
		Char. C								
L.	Icu [kA]	36								
		In [A]	25	32	40	50	63	80	100	125
S200P K	25	0.2	T	T	T	T	T	T	T	T
		0.3	T	T	T	T	T	T	T	T
		0.5	T	T	T	T	T	T	T	T
		0.75	T	T	T	T	T	T	T	T
		1	0.8	5	T	T	T	T	T	T
		1.6	0.5	1	2.3	T	T	T	T	T
		2	0.3	0.5	0.7	2.3	T	T	T	T
		3		0.4	0.5	0.7	1.2	2.5	8.6	T
		4		0.4	0.4	0.7	1	1.7	3	7.7
		6				0.6	0.8	1.2	2	3.6
	15	8					0.7	0.9	1.3	2
		10						0.9	1.3	2
		13							1	1.5
		16								1.5
		20								
	15	25								
		32								
		40								
		50								
		63								

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N									
		D									
L.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
S200P	B	25	6	0.5	1	1.2	2	2.8	9.9	21.3	T
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
			13	0.4	0.6	0.8	1.1	1.4	2.5	3.3	5.6
			16		0.6	0.8	1.1	1.4	2.5	3.3	5.6
			20			0.8	1.1	1.3	2.3	3	4.7
			25			0.8	1.1	1.3	2.3	3	4.7
	15	15	32				0.9	1.1	1.9	2.4	3.7
			40					1.1	1.9	2.4	3.7
			50						1.5	1.9	2.3
			63							1.7	2.3

		E. S800N									
		D									
L.	Char.	Icu [kA]	36								
			In [A]	25	32	40	50	63	80	100	125
S200P	C	25	0.5	T	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T	T
			1.6	T	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T	T
			3	0.7	2.2	4.4	T	T	T	T	T
			4	0.7	1.3	2.2	4.4	7.7	T	T	T
	15	15	6	0.5	1	1.2	2	2.8	9.9	22	T
			8	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9	7.4
			13	0.4	0.6	0.8	1.1	1.4	2.5	3.3	5.6
			16		0.6	0.8	1.1	1.4	2.5	3.3	5.6
			20			0.8	1.1	1.3	2.3	3	4.7
			25			0.8	1.1	1.3	2.3	3	4.7
			32				0.9	1.1	1.9	2.4	3.7
			40					1.1	1.9	2.4	3.7
			50						1.5	1.9	2.3
			63							1.7	2.3

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

		E. S800N								
		D								
L.	Char.	Icu [kA]	36							
		In [A]	25	32	40	50	63	80	100	125
S200P	K	25	0.2	T	T	T	T	T	T	T
			0.3	T	T	T	T	T	T	T
			0.5	T	T	T	T	T	T	T
			0.75	T	T	T	T	T	T	T
			1	T	T	T	T	T	T	T
			1.6	T	T	T	T	T	T	T
			2	2.3	T	T	T	T	T	T
			3	0.7	1.3	4.4	T	T	T	T
			4	0.7	1	2.2	4.4	7.7	T	T
			6	0.6	0.8	1.5	2.5	3.6	12	24.2
			8	0.5	0.7	1.1	1.5	2	4	5.5
			10	0.5	0.7	1.1	1.5	2	4	9.9
			13		0.6	0.9	1.2	1.5	2.6	3.4
			16			0.9	1.2	1.5	2.6	5.2
			20				0.9	1.1	1.8	2.2
			25					1.1	1.8	3.2
		15	32						1.7	2
			40							2.9
			50							1.9
			63							2.6
										2.2

E. = feed side

L. = load side

T = Total selectivity up to breaking capacity of the switch on load side

Selectivity limit values indicated in kA

MCBs technical details

Coordination tables: selectivity

S800N – S400E/S450E @230/400V

		Supply s.		S800N							
		Char.		B							
Load s.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S400E S450E FS401E FS451E	B, C Icn [kA] 6	6			0.4	0.5	0.6	0.9	1.4	2.4	
		10				0.4	0.5	0.7	0.9	1.3	
		13					0.5	0.7	0.9	1.2	
		16						0.7	0.9	1.2	
		20							0.9	1.2	
		25							0.9	1.2	
		32							0.7	1	
		40							0.7	1	
		50								0.9	
		63								0.9	

		Supply s.		S800N							
		Char.		C							
Load s.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S400E S450E FS401E FS451E	B, C Icn [kA] 6	6		0.4	0.5	0.6	0.9	1.3	2.2	4.4	
		10		0.3	0.4	0.5	0.6	0.8	1.2	1.8	
		13		0.3	0.4	0.5	0.6	0.8	1.2	1.7	
		16		0.3	0.4	0.5	0.6	0.8	1.2	1.7	
		20			0.4	0.5	0.6	0.8	1.1	1.6	
		25			0.4	0.5	0.6	0.8	1.1	1.6	
		32				0.4	0.5	0.7	0.9	1.3	
		40					0.5	0.7	0.9	1.3	
		50						0.7	0.9	1.2	
		63							0.8	1.1	

		Supply s.		S800N							
		Char.		D							
Load s.	Icu [kA]	36									
		In [A]	25	32	40	50	63	80	100	125	
S400E S450E FS401E FS451E FS403E FS453E	B, C Icn [kA] 6	6	0.5	0.9	1.1	1.8	2.5	T	T	T	
		10	0.4	0.5	0.8	1	1.3	2.5	3.5	T	
		13	0.4	0.5	0.8	1	1.3	2.3	3	5.1	
		16		0.5	0.8	1	1.3	2.3	3	5.1	
		20			0.7	1	1.2	2.1	2.7	4.3	
		25			0.7	1	1.2	2.1	2.7	4.3	
		32				0.9	1	1.7	2.2	3.4	
		40					1	1.7	2.2	3.4	
		50						1.4	1.7	2.1	
		63							1.6	2.1	

MCBs technical details

Coordination tables: selectivity

S800N – S400M @230/400V

MCBs technical details

Coordination tables: selectivity

MCBs technical details

Coordination tables: selectivity

S800N – S400M @230/400V

	Supply s.		S800S									
Load s.	Char.			C								
		Icu [kA]	50									
		In [A]	25	32	40	50	63	80	100	125		
S400M	C	50	0.5	T	T	T	T	T	T	T	T	
S450M			1	T	T	T	T	T	T	T	T	
FS401M			1.6	1	T	T	T	T	T	T	T	
FS451M			2	0	0.9	T	T	T	T	T	T	
FS403M		25	3	0	0.4	0.7	1.1	1.9	5.8	T	T	
FS453M			4	0	0.4	0.6	0.9	1.3	2.4	5.5	T	
			6		0.4	0.5	0.6	0.9	1.3	2.2	4.4	
			8		0.3	0.4	0.5	0.6	0.8	1.2	1.8	
			10		0.3	0.4	0.5	0.6	0.8	1.2	1.8	
			13		0.3	0.4	0.5	0.6	0.8	1.2	1.7	
			16		0.3	0.4	0.5	0.6	0.8	1.2	1.7	
			20		0.4	0.5	0.6	0.8	1.1	1.6		
	15	25			0.4	0.5	0.6	0.8	1.1	1.6		
		32				0.4	0.5	0.7	0.9	1.3		
		40					0.5	0.7	0.9	1.3		
		50						0.7	0.9	1.2		
		63							0.8	1.1		

MCBs technical details

Coordination tables: selectivity

MCBs technical details

Coordination tables: selectivity


S800N – S400M @230/400V

	Supply s.		S800N							
	Char.		D							
Load s.		Icu [kA]	36							
		In [A]	25	32	40	50	63	80	100	125
S400M	B	Icn [kA] 10	6	0.5	0.9	1.1	1.8	2.5	9	T
S450M			10	0.4	0.5	0.8	1	1.3	2.5	3.5
FS401M			13	0.4	0.5	0.8	1	1.3	2.3	5.5
FS451M			16		0.5	0.8	1	1.3	2.3	3
FS403M										5.1
FS453M			20			0.7	1	1.2	2.1	2.7
			25			0.7	1	1.2	2.1	4.3
			32				0.9	1	1.7	2.2
			40					1	1.7	3.4
			50						1.4	1.7
			63							2.1


MCBs technical details

Coordination tables: selectivity

Functional diagram of selective main circuit breakers S 700



Functional diagram of selective main circuit breakers S 750 (DR)



Back-up protection

Selective main circuit breakers of the S 700 and S 750 DR series are capable of switching off short-circuit currents of up to 25 kA automatically in networks with a rated voltage of 230/400 V. Back-up protection is necessary only when the prospective short-circuit current may exceed 25 kA prosp. at the installation point. Further information on back-up protection on request.



Short circuit discrimination

When ABB miniature circuit-breaker are used in combination with the S 700 or S 750 DR, higher short-circuit currents can be disconnected than are indicated as permissible rated switching capacity of device. Considering the values given in the table, the S 700 and S 750 DR operates selectively with respect to the combination with the final device. If other mcb's are used selectivity for 6 kA and 10 kA devices is available up to the rated switching capacity of the final device.

MCBs technical details

Coordination tables: selectivity

MCB




Load side	Supply side		S 700												fuse												
	Char.	Icu [kA]	E/K												gG												
			In [A]	16	20	25	35	40	50	63	80	100	16	20	25	35	50	63	80	100							
S 200	C	≤ 2	>15	>15	>15	>15	>15	>15	>15	>15	>15	>15	1	1.2	4	>15	>15	>15	>15	>15	>15						
		3	10	10	10	10	10	10	10	10	8	8	0.3	0.7	1.2	4.6	6	6	6	6							
		4	10	10	10	10	10	10	10	10	8	8	0.3	0.6	0.9	2.8	6	6	6	6							
	B, C	6	10	10	10	10	10	10	10	10	8	8	0.2	0.5	0.8	2	3.3	5.5	6	6							
		8	10	10	10	10	10	10	10	10	8	8	0.2	0.4	0.7	1.7	2.8	4.5	6	6							
	B, C	10	10	10	10	10	10	10	10	10	8	8	0.2	0.4	0.7	1.5	2.5	3.5	5	6							
		13	10	10	10	10	10	10	10	10	8	8			0.7	1.5	2.5	3.5	5	6							
		16		10	10	10	10	10	10	10	8	8			1.3	2	2.9	4.1	6								
		20			10	10	10	10	10	10	8	8				1.8	2.6	3.5	5								
		25				10	10	10	10	10	8	8				1.8	2.6	3.5	5								
		32					10	10	10	10	8	8					2.2	3	4								
		40						10	10	10	8	8							2.5	4							
		50/63									8	8								3.5							
	S 200 M	≤ 2	>15	>15	>15	>15	>15	>15	>15	>15	>15	>15	1	1.2	4	>15	>15	>15	>15	>15	>15						
		3	15	15	15	15	15	15	15	15	10	10	0.3	0.7	1.2	4.6	10	10	10	10	10	10					
		4	15	15	15	15	15	15	15	15	10	10	0.3	0.6	0.9	2.8	10	10	10	10	10	10					
		6	15	15	15	15	15	15	15	15	10	10	0.2	0.5	0.8	1.7	3.1	7	10	10	10	10					
		8	15	15	15	15	15	15	15	15	10	10	0.2	0.4	0.7	1.4	2.3	3.4	4.8	7.5							
		10	15	15	15	15	15	15	15	15	10	10	0.2	0.4	0.7	1.4	2.3	3.4	4.8	7.5							
		13	15	15	15	15	15	15	15	15	10	10			0.7	1.4	2.3	3.4	4.8	7.5							
		16		15	15	15	15	15	15	15	10	10			1.3	2	2.9	4.2	6								
		20			15	15	15	15	15	15	10	10				1.9	2.7	3.8	5.6								
		25				15	15	15	15	15	10	10				1.9	2.6	3.6	5.4								
		32					15	15	15	15	10	10					2.4	3.2	4.2								
		40						15	15	15	10	10						3.2	4.2								
		50/63									10	10							3.8								

Limited overload selectivity

MCBs technical details

Coordination tables: selectivity

MCB





Load side	Supply side		S 700												fuse											
	Char.	Icu [kA]	E/K												gG											
			In [A]	16	20	25	35	40	50	63	80	100	16	20	25	35	50	63	80	100						
S 200 S 200 M	K	6	≤ 2	>15	>15	>15	>15	>15	>15	>15	>15	>15	0.3	1.2	4	>15	>15	>15	>15	>15	>15					
			3	10	10	10	10	10	10	10	10	10	0.3	0.7	1.2	4.6	6	6	6	6						
			4	10	10	10	10	10	10	10	10	10	0.3	0.6	0.9	2.8	6	6	6	6						
			6	10	10	10	10	10	10	10	10	10			0.7	1.7	3	5.9	6	6						
			8	10	10	10	10	10	10	10	10	10			1.3	2.2	3.6	6	6	6						
			10	10	10	10	10	10	10	10	10	10				1.7	2.5	4	6							
			16		10	10	10	10	10	10	10	10					2.2	3.1	4.6							
			20			10	10	10	10	10	10	10						3.1	4.6							
			25				10	10	10	10	10	10							2.6	3.5						
			32					10	10	10	10	10							3.5							
			40						10	10	10	10								2	3	4				
			50/63							10	10									2.2	3.5					
S 200 S 200 M	Z	6	≤ 2	>15	>15	>15	>15	>15	>15	>15	>15	>15	0.5	2	>15	>15	>15	>15	>15	>15						
			3	10	10	10	10	10	10	10	10	10	10	0.3	0.7	1.8	6	6	6	6	6					
			4	10	10	10	10	10	10	10	10	10	10	0.3	0.6	1.3	7	6	6	6	6					
			6	10	10	10	10	10	10	10	10	10	10	0.2	0.5	0.9	2.7	6	6	6	6					
			8	10	10	10	10	10	10	10	10	10	10	0.2	0.5	0.6	1.7	3.8	6	6	6					
			10	10	10	10	10	10	10	10	10	10	10		0.4	0.6	1.3	2.4	4	6	6					
			16		10	10	10	10	10	10	10	10	10			0.5	1.1	1.7	3	4.5	6					
			20			10	10	10	10	10	10	10	10				0.9	1.5	2.3	3.5	5.2					
			25				10	10	10	10	10	10	10					1.4	2	3	4					
			32					10	10	10	10	10	10					1.4	2	3	4					
			40						10	10	10	10	10						2	3	4					
			50/63							10	10								2.2	3.5						

Limited overload selectivity

MCBs technical details

Coordination tables: selectivity

MCB



		Supply side		S 700										fuse									
Load side	Char.	E/K										gG											
		Icu [kA]	25	In [A]	16	20	25	35	40	50	63	80	100	16	20	25	35	50	63	80	100		
S 200 P	B	6	6	25	25	25	25	25	25	25	25	25	0.2	0.4	0.6	1.2	2.2	3.7	6	10			
			10	25	25	25	25	25	25	25	25	25	0.2	0.4	0.6	1.1	1.8	2.7	4	6			
			13	25	25	25	25	25	25	25	25	25				0.6	1	1.7	2.5	3.7	5.5		
			16		25	25	25	25	25	25	25	25				1	1.6	2.4	3.5	5.3			
			20			25	25	25	25	25	25	25				1	1.6	2.2	3.3	4.7			
			25				25	25	25	25	25	25						1.5	2	3	4		
			32					25	25	25	25	25						1.3	2	2.8	3.6		
			40						25	25	25	25							1.9	2.7	3.4		
			50/63							25	25	25								2.7	3.4		
													10	10									
S 200 P	C	6	≤ 2	>25	>25	>25	>25	>25	>25	>25	>25	>25	1	2	>25	>25	>25	>25	>25	>25	>25		
			3	25	25	25	25	25	25	25	25	25	0.3	0.8	1.5	6	10	10	10	10			
			4	25	25	25	25	25	25	25	25	25	0.3	0.6	1	3.3	6	10	10	10			
			6	25	25	25	25	25	25	25	25	25				0.6	1.3	3	5.5	10	10		
			8	25	25	25	25	25	25	25	25	25					1.1	2.9	3.5	6	10		
			10	25	25	25	25	25	25	25	25	25					1	1.7	2.5	4	6		
			13	25	25	25	25	25	25	25	25	25						1.8	2.2	3	5.5		
			16		25	25	25	25	25	25	25	25						1.6	2	3	5		
			20			25	25	25	25	25	25	25							1.6	2.8	3.6		
			25				25	25	25	25	25	25								2.4	3.5		
S 200 P	K	6	32				25	25	25	25	25	25									3.1		
			40					25	25	25	25	25											
			50/63						25	25	25	25					10	10					
			≤ 2	>15	>15	>15	>15	>15	>15	>15	>15	>15	0.3	1	>15	>15	>15	>15	>15	>15	>15		
			3	15	15	15	15	15	15	15	15	15	0.3	0.8	1.5	6	6	6	10	10			
			4	15	15	15	15	15	15	15	15	15	0.3	0.6	1	3.3	6	6	6	10			
			6	15	15	15	15	15	15	15	15	15				0.6	1.3	3	5.5	6	9.5		
			8	15	15	15	15	15	15	15	15	15					1.1	2.5	3.5	6	6		
			10	25	25	25	25	25	25	25	25	25					1	1.7	2.5	4	6		
			13	25	25	25	25	25	25	25	25	25						1.6	2.2	3	5.5		
			16		25	25	25	25	25	25	25	25						1.5	2	3	5		
			20			25	25	25	25	25	25	25							1.6	2.6	3.6		
			25				15	15	15	15	15	15								2.4	3.3		
			32				15	15	15	15	15	15								3.1			
			40					15	15	15	15	15											
			50/63						15	15	15	15					10	10					

Limited overload selectivity

MCBs technical details

Coordination tables: selectivity

MCB



Load side	Supply side		S 700												fuse														
	Char.	Icu [kA]	E/K												gG														
			In [A]	16	20	25	35	40	50	63	80	100	16	20	25	35	50	63	80	100									
S 200 P	Z	6	≤ 2	>15	>15	>15	>15	>15	>15	>15	>15	>15	0.3	1	>15	>15	>15	>15	>15	>15									
			3	15	15	15	15	15	15	15	15	15	0.3	0.6	1.8	10	10	10	10	10									
			4	15	15	15	15	15	15	15	15	15	0.3	0.6	0.6	1.3	6	10	10	10									
			6	15	15	15	15	15	15	15	15	15				0.8	2.6	6	10	10									
			8	15	15	15	15	15	15	15	15	15							1.7	3.4	7	10							
			10	25	25	25	25	25	25	25	25	25							1.3	2.2	3.7	6							
			16		25	25	25	25	25	25	25	25								1.7	2.8	4.1							
			20			25	25	25	25	25	25	25									2.1	3.1							
			25				15	15	15	15	15	15										2.6							
			32					15	15	15	15	15																	
			40						15	15	15	15																	
			50/63										10	10															

Limited overload selectivity

Limit of selectivity

For the coordination of MCB, S 700 and upstream fuses the following selectivity limits can be assumed:



Load side	Upstream		fuse 63 A gG												fuse 80 A gG															
	Char.	Supply side	S 700												S 700															
			Icu [kA]	25	25	35	40	50	63	80	100	35	40	50	63	80	100	35	40	50	63	80	100							
S 200	6	C	≤ 2	>15	>15	>15	>15								>15	>15	>15	>15	>15	>15	>15	>15	>15							
			3	10	10	10	10								10	10	10	10	10	10	10	10	8							
			4	10	10	10	10								10	10	10	10	10	10	10	10	8							
			6	10	10	10	10								10	10	10	10	10	10	10	10	8							
			8	7.5	7	7	6								10	10	10	10	10	10	10	10	8	8						
			10	7.5	7	7	6								10	10	10	10	10	10	10	10	8	6						
			13	6	6	6	6								10	10	9	9	9	7.5	7.5	6								
			16	6	6	6	6								10	10	9	9	9	7.5	7.5	6								
			20	6	6	5	5								9	8	8	8	8	6	6	6								
			25			4.5	4.5	4.5									7.5	7.5	6	6	6									
			32				4.5	4.5	4.5										6	6	6									
			40					4												6	6	6								
			50																			4.5								
			50/63																											

Values for < 6 A and 8 A are only valid for C characteristic.

MCBs technical details

Coordination tables: selectivity

Upstream		fuse 100 A gG							fuse M 125 A gG						
	Supply side	S 700						S 700							
Load side	Char.	E/K						E/K							
		Icu [kA]						25						25	
		In [A]	35	40	50	63	80	100	35	40	50	63	80	100	
S 200	C	≤ 2	>15	>15	>15	>15	>15	>15	>15	>15	>15	>15	>15	>15	>15
		3	10	10	10	10	8	8	10	10	10	10	8	8	
		4	10	10	10	10	8	8	10	10	10	10	8	8	
		6	10	10	10	10	8	8	10	10	10	10	8	8	
	B, C	8	10	10	10	10	8	8	10	10	10	10	8	8	
		10	10	10	10	10	8	8	10	10	10	10	8	8	
		13	10	10	10	10	8	8	10	10	10	10	8	8	
	B, C	16	10	10	10	10	8	8	10	10	10	10	8	8	
		20	10	10	10	10	8	8	10	10	10	10	8	8	
		25	10	10	10	8	8	8	10	10	10	10	8	8	
		32			10	10	8	7.5			10	10	8	8	
		40				10	8	7				10	8	8	
		50					7	6					8	8	
		63						5						8	

Upstream		fuse 63 A gG							fuse 80 A gG						
	Supply side	S 700						S 700							
Load side	Char.	E/K						E/K							
		Icu [kA]						25						25	
		In [A]	35	40	50	63	80	100	35	40	50	63	80	100	
S 200 M	C	≤ 2	>15	>15	>15	>15			>15	>15	>15	>15	>15	>15	>15
		3	15	15	15	15			15	15	15	15	15	10	
		4	15	15	15	15			15	15	15	15	15	10	
		6	15	15	15	15			15	15	15	15	15	10	
	B, C	8	7.5	7	7	6			12.5	10	10	10	10	6	
		10	7.5	7	7	6			12.5	10	10	10	10	6	
		13	6	6	5				10	10	9	7.5	6		
	B, C	16	6	6	5				10	10	9	7.5	6		
		20	6	6	5				9	8	8	6	6		
		25	4.5	4.5	4.5					7.5	7.5	6	6		
		32			4.5	4.5					6	6	6		
		40				4					6	6	6		
		50											4.5		
		63													

Values for < 6 A and 8 A are only valid for C characteristic.

MCBs technical details

Coordination tables: selectivity

Upstream		fuse 100 A gG							fuse M 125 A gG						
Load side	Supply side	S 700						S 700							
	Char.	E/K						E/K							
	Icu [kA]	25						25							
	In [A]	35	40	50	63	80	100	35	40	50	63	80	100		
S 200 M	C	≤ 2	>15	>15	>15	>15	>15	>15	>15	>15	>15	>15	>15	>15	>15
		3	15	15	15	10	10	15	15	15	15	10	10		
		4	15	15	15	10	10	15	15	15	15	10	10		
		6	15	15	15	10	10	15	15	15	15	10	10		
	B, C	8	15	15	15	10	10	15	15	15	15	10	10		
		10	15	15	15	10	10	15	15	15	15	10	10		
	B, C	13	15	12.5	12.5	10	10	15	15	15	15	10	10		
		16	15	12.5	12.5	10	10	15	15	15	15	10	10		
		20	12.5	10	12.5	10	10	15	15	15	15	10	10		
		25		10	10	10	9		15	15	15	10	10		
	B, C	32		10	10	10	7.5			15	15	10	10		
		40			10	9	7				15	10	10		
		50				7	6					10	10		
		63					5						10		

Upstream		fuse 63 A gG							fuse 80 A gG						
Load side	Supply side	S 700						S 700							
	Char.	E/K						E/K							
	Icu [kA]	25						25							
	In [A]	35	40	50	63	80	100	35	40	50	63	80	100		
S 200 P	C	≤ 2	>25	>25	>15	>15			>25	>25	>25	>25	>25		
		3	15	15	15	15			25	25	15	15	15		
		4	15	15	15	15			25	25	15	15	15		
		6	15	15	15	15			25	25	15	15	15		
	B, C	8	7.5	7	7	6			12.5	10	12.5	10	10		
		10	7.5	7	7	6			12.5	10	12.5	10	6		
	B, C	13	6	6	5				10	10	10	8	6		
		16	6	6	5				10	10	10	8	6		
		20	6	6	5	5			9	8	8	7	6		
		25		4.5	4.5	4.5				7.5	7.5	6	6		
	B, C	32			4.5	4.5				6	6	6			
		40				4					6	6			
		50										4.5			
		63													

Values for < 6 A and 8 A are only valid for C characteristic.

MCBs technical details

Coordination tables: selectivity

Upstream		fuse 100 A gG										fuse 125 A gG									
	Supply side	S 700										S 700									
Load side	Char.	E/K										E/K									
		Icu [kA]										25									
S 200 P	C	Icu [kA]	25	35	40	50	63	80	100	35	40	50	63	80	100	35	40	50	63	80	100
		Icu [kA]	25	≤ 2	>25	>25	>25	>25	>25	25	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	3	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
	B, C	Icu [kA]	25	4	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	6	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
	B, C	Icu [kA]	25	8	20	17	15	15	13	10	25	25	25	25	25	25	25	25	25	15	15
		Icu [kA]	25	10	20	17	15	15	13	10	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	13	19	17	15	12.5	10	10	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	16	19	17	15	12.5	10	10	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	20	17	17	15	10	10	10	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	25	15	15	10	10	9	9	25	25	25	25	25	25	25	25	20	20	20
		Icu [kA]	25	32				15	10	9							20	20	15	20	
		Icu [kA]	25	40					10	9	9								15	15	15
		Icu [kA]	25	50						7	7								10	10	
		Icu [kA]	25	63							6										10

Upstream		fuse 160 A gG										fuse 200 A gG									
	Supply side	S 700										S 700									
Load side	Char.	E/K										E/K									
		Icu [kA]										25									
S 200 P	C	Icu [kA]	25	≤ 2	>25	>25	>25	>25	>25	>25	>25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	3	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	4	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
	B, C	Icu [kA]	25	6	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	8	25	25	25	25	15	15	25	25	25	25	25	25	25	25	25	15	15
	B, C	Icu [kA]	25	10	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	13	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	16	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	20	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25	25
		Icu [kA]	25	32				25	25	25	25					25	25	25	25	25	25
		Icu [kA]	25	40				25	25	25	25						25	25	25	25	25
		Icu [kA]	25	50					15	10								25	25	10	
		Icu [kA]	25	63						10										10	

Values for < 6 A and 8 A are only valid for C characteristic.

MCBs technical details

Coordination tables: selectivity

Discrimination of S750 DR with respect to downstream MCB S200 / S400 compared to fuse protection

MCBs		S 750 DR												fuse												
final circuit:	Char.	E/K												gG												
		I_{cu} [kA]	25																							
			I_n [A]	16	20	25	32	40	50	63	80	100		16	20	25	35	40	50	63	80	100				
S200 S400E	B, C	10	≤ 2	10	10	10	10	10	10	10	10	10		0.3	0.7	1.2	4.6	5	10	10	10	10				
			3	10	10	10	10	10	10	10	10	10		0.3	0.7	1.2	4.6	5	10	10	10	10				
			4	10	10	10	10	10	10	10	10	10		0.3	0.6	0.9	2.8	3.5	6	10	10	10				
			6	10	10	10	10	10	10	10	10	10		0.2	0.5	0.8	2	2.5	3.3	5.5	10	10				
			8	10	10	10	10	10	10	10	10	10			0.7	1.5	2	2.5	3.5	5	6					
			10	10	10	10	10	10	10	10	10	10			0.7	1.5	2	2.5	3.5	5	6					
			13	10	10	10	10	10	10	10	10	10			0.7	1.5	2	2.5	3.5	5	6					
			16	10	10	10	10	10	10	10	10	10				1.3	1.4	2	2.9	4.1	6					
			20		10	10	10	10	10	10	10	10					0.7	1.8	2.6	3.5	5					
			25			10	10	10	10	10	10	10					0.7	1.8	2.6	3.5	5					
			32				10	10	10	10	10	10							2.2	3	4					
			40					10	10	10	10	10							2.2	3	4					
			50						10	10	10	10									3.5					
			63							10	10	10										3.5				

Limited overload selectivity

Discrimination of S750 DR with respect to downstream MCB S200 / S400 compared to fuse protection

MCBs		S 750 DR												fuse												
final circuit:	Char.	E/K												gG												
		I_{cu} [kA]	25																							
			I_n [A]	16	20	25	32	40	50	63	80	100		16	20	25	35	40	50	63	80	100				
S200 S400E	K	10	≤ 2	10	10	10	10	10	10	10	10	10		0.3	1.2	4	6	10	10	10	10	10				
			3	10	10	10	10	10	10	10	10	10		0.3	0.7	1.2	4.6	5	10	10	10	10				
			4	10	10	10	10	10	10	10	10	10		0.3	0.6	0.9	2.8	3.5	6	10	10	10				
			6	10	10	10	10	10	10	10	10	10			0.7	1.7	2.5	3	5.9	9	10					
			8	10	10	10	10	10	10	10	10	10			0.4	0.8	1	1.7	2.5	4	6					
			10	10	10	10	10	10	10	10	10	10			0.4	0.8	1	1.7	2.5	4	6					
			16	10	10	10	10	10	10	10	10	10				0.7	0.9	1.2	2.2	3.1	4.6					
			20		10	10	10	10	10	10	10	10					0.7	1.1	1.7	2.6	3.5					
			25			10	10	10	10	10	10	10					0.7	1.1	1.7	2.6	3.5					
			32				10	10	10	10	10	10							1.5	2.2	3.5					
			40					10	10	10	10	10							1.5	2.2	3.5					
			50						10	10	10	10									2.2					
			63							10	10	10										2.2				

Limited overload selectivity

MCBs technical details

Coordination tables: selectivity

Discrimination of S750 DR with respect to downstream MCB S200 / S400 compared to fuse protection

MCBs		S 750 DR												S 200 / S 400													
final circuit:	Char.	E/K												fuse													
		I_{cu} [kA]	25											gG													
			I_n [A]	16	20	25	32	40	50	63	80	100		16	20	25	35	40	50	63	80	100					
S200 S400E	Z	10	≤ 2	10	10	10	10	10	10	10	10	10		0.5	2	6	6	10	10	10	10	10	10	10	10		
		3	10	10	10	10	10	10	10	10	10	10		0.3	0.7	1.8	6	10	10	10	10	10	10	10	10		
		4	10	10	10	10	10	10	10	10	10	10		0.3	0.6	1.3	3.5	4	7	10	10	10	10	10	10		
		6	10	10	10	10	10	10	10	10	10	10		0.2	0.5	0.9	1.3	2.7	3.8	6	10	10	10	10	10		
		8	10	10	10	10	10	10	10	10	10	10		0.4	0.6	1.3	1.5	2.4	4	6	6	6	6	6	6		
		10	10	10	10	10	10	10	10	10	10	10		0.4	0.6	1.3	1.5	2.4	4	6	6	6	6	6	6		
		16	10	10	10	10	10	10	10	10	10	10		0.5	1.1	1.5	1.7	3	4.5	6							
		20		10	10	10	10	10	10	10	10	10			0.7	1.4	2	3	4.4								
		25			10	10	10	10	10	10	10	10				0.7	1.4	2	3	4							
		32				10	10	10	10	10	10	10								2	3	4					
		40					10	10	10	10	10	10								2	3	4					
		50						10	10	10	10	10										3					
		63							10	10	10	10											3				

Limited overload selectivity



MCBs technical details

Coordination tables: selectivity

Discrimination of S750 DR with respect to downstream MCB S200M / S400M compared to fuse protection

MCBs		S 750 DR												S 200 / S 400																	
final circuit:	Char.	E/K												fuse																	
		I_{cu} [kA]	25											gG																	
			I_n [A]	16	20	25	32	40	50	63	80	100		16	20	25	35	40	50	63	80	100									
S200M S400M	B, C	15	≤ 2	15	15	15	15	15	15	15	15	15		1	1.2	4	10	10	15	15	15	15	15	15	15						
			3	15	15	15	15	15	15	15	15	15	15	0.3	0.7	1.2	4.6	5	15	15	15	15	15	15	15						
			4	15	15	15	15	15	15	15	15	15	15	0.3	0.6	0.9	2.8	3.5	6	15	15	15	15	15	15	15					
			6	15	15	15	15	15	15	15	15	15	15	0.2	0.5	0.8	2	2.5	3.3	5.5	15	15	15	15	15	15	15				
			8	15	15	15	15	15	15	15	15	15	15		0.7	1.5	2	2.5	3.5	5	6										
			10	15	15	15	15	15	15	15	15	15	15		0.7	1.5	2	2.5	3.5	5	6										
			13	15	15	15	15	15	15	15	15	15	15		0.7	1.5	2	2.5	3.5	5	6										
			16	15	15	15	15	15	15	15	15	15	15			1.3	1.4	2	2.9	4.1	6										
			20		15	15	15	15	15	15	15	15	15			0.7	1.8	2.6	3.5	5											
			25			15	15	15	15	15	15	15	15			0.7	1.8	2.6	3.5	5											
			32				15	15	15	15	15	15	15						2.2	3	4										
			40					15	15	15	15	15	15						2.2	3	4										
			50						15	15	15	15	15									3.5									
			63							15	15	15	15									3.5									

Limited overload selectivity

Discrimination of S750 DR with respect to downstream MCB S200M / S400M compared to fuse protection

MCBs		S 750 DR												S 200 / S 400																										
final circuit:	Char.	E/K												fuse																										
		I_{cu} [kA]	25											gG																										
			I_n [A]	16	20	25	32	40	50	63	80	100		16	20	25	35	40	50	63	80	100																		
S200M S400M	K	15	≤ 2	15	15	15	15	15	15	15	15	15		0.3	1.2	4	10	10	15	15	15	15	15	15	15	15	15	15	15											
			3	15	15	15	15	15	15	15	15	15	15	0.3	0.7	1.2	4.6	5	15	15	15	15	15	15	15	15	15	15	15											
			4	15	15	15	15	15	15	15	15	15	15	0.3	0.6	0.9	2.8	3.5	6	15	15	15	15	15	15	15	15	15	15	15										
			6	15	15	15	15	15	15	15	15	15	15		0.7	1.7	2.5	3	5.9	9	15																			
			8	15	15	15	15	15	15	15	15	15	15		0.4	0.8	1	1.7	2.5	4	6																			
			10	15	15	15	15	15	15	15	15	15	15		0.4	0.8	1	1.7	2.5	4	6																			
			16	15	15	15	15	15	15	15	15	15	15			0.7	0.9	1.2	2.2	3.1	4.6																			
			20		15	15	15	15	15	15	15	15	15			0.7	1.1	1.7	2.6	3.5																				
			25			15	15	15	15	15	15	15	15			0.7	1.1	1.7	2.6	3.5																				
			32				15	15	15	15	15	15	15								1.5	2.2	3.5																	
			40					15	15	15	15	15	15								1.5	2.2	3.5																	
			50						15	15	15	15	15									2.2																		
			63							15	15	15	15									2.2																		

Limited overload selectivity

MCBs technical details

Coordination tables: selectivity

Discrimination of S750 DR with respect to downstream MCB S200M / S400M compared to fuse protection

MCBs		S 750 DR												S 200 / S 400											
final circuit:	Char.	E / K												fuse											
		I_{cu} [kA]	25											gG											
			I_n [A]	16	20	25	32	40	50	63	80	100		16	20	25	35	40	50	63	80	100			
S200M S400M	Z	15	≤ 2	15	15	15	15	15	15	15	15	15		0.5	2	10	10	15	15	15	15	15	15	15	15
		3	15	15	15	15	15	15	15	15	15	15		0.3	0.7	1.8	6	15	15	15	15	15	15	15	15
		4	15	15	15	15	15	15	15	15	15	15		0.3	0.6	1.3	3.5	4	7	15	15	15	15	15	15
		6	15	15	15	15	15	15	15	15	15	15		0.2	0.5	0.9	1.3	2.7	3.8	6	15	15	15	15	15
		8	15	15	15	15	15	15	15	15	15	15		0.4	0.6	1.3	1.5	2.4	4	6	6	6	6	6	6
		10	15	15	15	15	15	15	15	15	15	15		0.4	0.6	1.3	1.5	2.4	4	6	6	6	6	6	6
		16	15	15	15	15	15	15	15	15	15	15		0.5	1.1	1.5	1.7	3	4.5	6					
		20		15	15	15	15	15	15	15	15	15			0.7	1.4	2	3	4.4						
		25			15	15	15	15	15	15	15	15				0.7	1.4	2	3	4					
		32				15	15	15	15	15	15	15						2	3	4					
		40					15	15	15	15	15	15						2	3	4					
		50						15	15	15	15	15									3				
		63							15	15	15	15										3			

Limited overload selectivity



MCBs technical details

Coordination tables: selectivity

Discrimination of S750 DR with respect to downstream MCB S200P compared to fuse protection

MCBs		S 750 DR												fuse											
final circuit:	Char.	E/K												gG											
		I_{cu} [kA]	25											gG											
			I_n [A]	16	20	25	32	40	50	63	80	100		16	20	25	35	40	50	63	80	100			
S200P	B	25	6	25	25	25	25	25	25	25	25	25	25	0.2	0.4	0.6	1.3	2.5	3	5.5	12	25			
		10	25	25	25	25	25	25	25	25	25	25	25	0.6	1	1.5	1.8	2.5	3.7	5.5					
		13	25	25	25	25	25	25	25	25	25	25	25	0.6	1	1.5	1.8	2.5	3.7	5.5					
		16	25	25	25	25	25	25	25	25	25	25	25	1	1.4	1.6	2	3	5						
		20		25	25	25	25	25	25	25	25	25	25	0.7	1.5	2	3	4							
		25		25	25	25	25	25	25	25	25	25	25	0.7	1.5	2	3	4							
	15	32			15	15	15	15	15											1.9	2.7	3.5			
		40				15	15	15	15											1.9	2.7	3.5			
		50					15	15	15											2.7	3.4				
		63						15	15											2.7	3.4				

Limited overload selectivity

Discrimination of S750 DR with respect to downstream MCB S200P compared to fuse protection

MCBs		S 750 DR												fuse													
final circuit:	Char.	E/K												gG													
		I_{cu} [kA]	25											gG													
			I_n [A]	16	20	25	32	40	50	63	80	100		16	20	25	35	40	50	63	80	100					
S200P	C	10	≤2	25	25	25	25	25	25	25	25	25	25	0.3	0.8	1.5	6	10	25	25	25	25	25	25	25		
		3	25	25	25	25	25	25	25	25	25	25	25	0.3	0.8	1.5	6	10	25	25	25	25	25	25	25		
		4	25	25	25	25	25	25	25	25	25	25	25	0.3	0.6	1	3.3	4	6	25	25	25	25	25	25	25	
		6	25	25	25	25	25	25	25	25	25	25	25	0.2	0.4	0.6	1.3	2.5	3	5.5	12	25					
		8	25	25	25	25	25	25	25	25	25	25	25	0.6	1	1.5	1.8	2.5	3.7	5.5							
		10	25	25	25	25	25	25	25	25	25	25	25	0.6	1	1.5	1.8	2.5	3.7	5.5							
		13	25	25	25	25	25	25	25	25	25	25	25	0.6	1	1.5	1.8	2.5	3.7	5.5							
		16	25	25	25	25	25	25	25	25	25	25	25	1	1.4	1.6	2	3	5								
		20		25	25	25	25	25	25	25	25	25	25	0.7	1.5	2	3	4									
		25		25	25	25	25	25	25	25	25	25	25	0.7	1.5	2	3	4									
		15	32		15	15	15	15	15											1.9	2.7	3.5					
		40			15	15	15	15	15											1.9	2.7	3.5					
		50				15	15	15	15											2.7	3.4						
		63					15	15	15											2.7	3.4						

Limited overload selectivity

MCBs technical details

Coordination tables: selectivity

Discrimination of S750 DR with respect to downstream MCB S200P compared to fuse protection

MCBs		S 750 DR										fuse										
final circuit:	Char.	E / K										gG										
		I_{cu} [kA]	25										gG									
			I_n [A]	16	20	25	32	40	50	63	80	100	16	20	25	35	40	50	63	80	100	
S200P	K	25	≤ 2	25	25	25	25	25	25	25	25	25	0.3	0.8	1.5	6	7.5	25	25	25	25	25
			3	25	25	25	25	25	25	25	25	25	0.3	0.8	1.5	6	7.5	25	25	25	25	25
			4	25	25	25	25	25	25	25	25	25	0.3	0.6	1	3.3	3.5	6	25	25	25	25
			6	25	25	25	25	25	25	25	25	25	0.6	1.3	1.5	3	5.5	9	25	25	25	25
			8	25	25	25	25	25	25	25	25	25	0.4	0.8	1	1.6	2.2	3.2	5.5	25	25	25
			10	25	25	25	25	25	25	25	25	25	0.4	0.8	1	1.6	2.2	3.2	5.5	25	25	25
			13	25	25	25	25	25	25	25	25	25	0.4	0.8	1	1.6	2.2	3.2	5.5	25	25	25
			16	25	25	25	25	25	25	25	25	25	0.7	0.9	1.5	2	3	5	25	25	25	25
			20		25	25	25	25	25	25	25	25	0.7	1.1	1.7	2.5	3.5					
			25		25	25	25	25	25	25	25	25	0.7	1.1	1.7	2.5	3.5					
	15	32			15	15	15	15	15	15	15						1.5	2.2	3.1			
			40			15	15	15	15	15	15						1.5	2.2	3.1			
			50			15	15	15	15	15	15								2.2			
			63				15	15											2.2			

Limited overload selectivity

Discrimination of S750 DR with respect to downstream MCB S200P compared to fuse protection

MCBs		S 750 DR										fuse										
final circuit:	Char.	E / K										gG										
		I_{cu} [kA]	25										gG									
			I_n [A]	16	20	25	32	40	50	63	80	100	16	20	25	35	40	50	63	80	100	
S200P	Z	25	≤ 2	25	25	25	25	25	25	25	25	25	0.3	0.6	1.8	4	25	25	25	25	25	25
			3	25	25	25	25	25	25	25	25	25	0.3	0.6	1.8	4	25	25	25	25	25	25
			4	25	25	25	25	25	25	25	25	25	0.3	0.6	0.8	2.5	4	7	25	25	25	25
			6	25	25	25	25	25	25	25	25	25	0.6	1.3	2	2.8	6	25	25	25	25	25
			8	25	25	25	25	25	25	25	25	25	0.4	0.8	1.2	1.5	2.3	3.7	6	25	25	25
			10	25	25	25	25	25	25	25	25	25	0.4	0.8	1.2	1.5	2.3	3.7	6	25	25	25
			16	25	25	25	25	25	25	25	25	25	0.7	0.9	1.5	1.9	2.9	4.5				
			20		25	25	25	25	25	25	25	25	0.7	1.3	2	2.8	4.4					
			25		25	25	25	25	25	25	25	25	0.7	1.3	2	2.8	4.4					
	15	32			15	15	15	15	15	15	15						1.8	2.7	4			
			40			15	15	15	15	15	15						1.8	2.7	4			
			50			15	15	15	15	15	15								3			
			63				15	15											3			

Limited overload selectivity

MCBs technical details

Coordination tables: selectivity

Short-circuit discrimination (in kA) apply for combinations¹⁾: fuse gL / gG – S 750 DR – S 200 / S 400



		fuse: 63A gG				80A gG				100A gG				≥125A gG												
final circuit:	supply side:		S 750 DR																							
	Char.	I _{cu} [kA]	E/K																							
			25																							
S200 S400E	C	I _n [A]	35	40	50	63	35	40	50	63	35	40	50	63	35	40	50	63								
		≤2	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15								
		3	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10								
		4	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10								
		6	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10								
	B, C	8	7	6	6	5	10	10	10	8	10	10	10	10	10	10	10	10								
		10	7	6	6	5	10	10	10	8	10	10	10	10	10	10	10	10								
		13	6	6	6	5	9	8	8	7	10	10	10	10	10	10	10	10								
		16	6	6	6	5	9	8	8	7	10	10	10	10	10	10	10	10								
		20	5	5	4.5	4.5	6	7	7	6.5	10	10	10	10	10	10	10	10								
S200 S400E	B, C	25	4.5	4.5	4		7	6	6		10	10	10	10	10	10	10	10								
		32		4	3.5			6	5.5		9	9			10	10										
		40			3				5		8				10											
K. Z.	supply side:		S 750 DR																							
	Char.	I _{cu} [kA]	E/K																							
			25																							
	C	I _n [A]	35	40	50	63	35	40	50	63	35	40	50	63	35	40	50	63								
		≤2	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15								
		3	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10								
		4	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10								
		6	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10	10								
	B, C	8	7	6	6	5	10	10	10	8	10	10	10	10	10	10	10	10								
		10	7	6	6	5	10	10	10	8	10	10	10	10	10	10	10	10								
		13	6	6	6	5	9	8	8	7	10	10	10	10	10	10	10	10								
		16	6	6	6	5	9	8	8	7	10	10	10	10	10	10	10	10								
		20	5	5	4.5	4.5	8	7	7	6.5	10	10	10	10	10	10	10	10								
	K. Z.	25	4.5	4.5	4		7	6	6		10	10	10	10	10	10	10	10								
		32		4	3.5			6	5.5		9	9			10	10										
		40			3				5		8				10											

¹⁾ The selectivity limit current I_{sl} results from the let-through I²t-value of S 750 DR plus S 200 / S 400 and the pre-arcing (melting) I²t-value of a fuse acc. to IEC / EN 60269

MCBs technical details

Coordination tables: selectivity

Short-circuit discrimination (in kA) apply for combinations¹⁾: fuse gL/gG – S 750 DR – S 200/S 400



		fuse: 63A gG				80A gG				100A gG				$\geq 125A gG$													
final circuit:	Char.	supply side: S 750DR												E/K													
		I_{cu} [kA]	25												25												
			I_n [A]	35	40	50	63	35	40	50	63	35	40	50	63	35	40	50	63								
S200M S400M	C	≤ 2	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15								
		3	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15								
		4	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15								
		6	10	10	10	10	10	15	15	15	15	10	15	15	15	15	15	15	15								
		8	7	6	6	5	10	10	10	10	8	15	15	15	15	15	15	15	15								
		10	7	6	6	5	10	10	10	10	8	15	15	15	15	15	15	15	15								
		13	6	6	6	5	9	8	8	7	10	10	10	10	10	15	15	15	15								
		16	6	6	6	5	9	8	8	7	10	10	10	10	10	15	15	15	15								
		20	5	5	4.5	4.5	8	7	7	6.5	10	10	10	10	10	15	15	15	15								
		25		4.5	4.5	4		7	6	6	10	10	10	10		15	15	15	15								
S200M S400M	B, C	32			4	3.5			6	5.5			9	9			15	15	15	15							
		40					3			5			8				15	15	15	14							

		fuse: 63A gG				80A gG				100A gG				$\geq 125A gG$													
final circuit:	Char.	supply side: S 750DR												E/K													
		I_{cu} [kA]	25												25												
			I_n [A]	35	40	50	63	35	40	50	63	35	40	50	63	35	40	50	63								
S200M S400M	K, Z	≤ 2	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15								
		3	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15								
		4	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15	15								
		6	10	10	10	10	10	15	15	15	15	10	15	15	15	15	15	15	15								
		8	7	6	6	5	10	10	10	10	8	15	15	15	15	15	15	15	15								
		10	7	6	6	5	10	10	10	10	8	15	15	15	15	15	15	15	15								
		13	6	6	6	5	9	8	8	7	10	10	10	10	10	15	15	15	15								
		16	6	6	6	5	9	8	8	7	10	10	10	10	10	15	15	15	15								
		20	5	5	4.5	4.5	8	7	7	6.5	10	10	10	10	10	15	15	15	15								
		25		4.5	4.5	4		7	6	6	10	10	10	10		15	15	15	15								
S200M S400M	K, Z	32			4	3.5			6	5.5			9	9			15	15	15	14							
		40					3			5			8				15	15	15	14							

¹⁾ The selectivity limit current I_{sl} results from the let-through I^2t -value of S 750 DR plus S 200/S 400 and the pre-arcing (melting) I^2t -value of a fuse acc. to IEC / EN 60269

MCBs technical details

Coordination tables: selectivity

Short-circuit discrimination (in kA) apply for combinations¹⁾: fuse gL / gG – S 750 DR – S 200 / S 400



		fuse:	63A gG				80A gG				100A gG				$\geq 125A gG$													
final circuit:	Char.	supply side:	S 750DR												E/K													
		I _{cu} [kA]	25												25													
		I _n [A]	35	40	50	63	35	40	50	63	35	40	50	63	35	40	50	63	35	40								
S 200P	C	≤ 2	15	15	15	15	25	25	25	25	25	25	25	25	25	25	25	25	25	25								
		3	15	15	15	15	25	25	15	15	25	25	25	25	25	25	25	25	25	25								
		4	15	15	15	15	20	20	15	15	25	25	25	25	25	25	25	25	25	25								
		6	10	10	10	10	17	16	15	14	25	25	20	20	25	25	25	25	25	25								
		8	7	6	6	5	10	10	10	8	20	20	15	15	25	25	25	25	25	25								
		10	7	6	6	5	10	10	10	8	20	15	15	15	25	25	25	25	25	25								
		13	6	6	6	5	9	8	8	7	15	15	15	15	22	22	20	20	20	20								
		16	6	6	6	5	9	8	8	7	12	12	10	10	22	22	20	18	20	18								
		20	5	5	4.5	4.5	8	7	7	6.5	12	12	10	10	20	20	20	18	20	18								
		25		4.5	4.5	4		7	6	6	10	10	10	10	15	15	15	15	15	15								
S 200P	B, C	15	32		4	3.5			6	5.5			10	10			10	10	15	15								
		40			3				5				9				9		15									

		fuse:	63A gG				80A gG				100A gG				$\geq 125A gG$													
final circuit:	Char.	supply side:	S 750DR												E/K													
		I _{cu} [kA]	25												25													
		I _n [A]	35	40	50	63	35	40	50	63	35	40	50	63	35	40	50	63	35	40								
S 200P	K, Z	50	≤ 2	15	15	15	15	25	25	25	25	25	25	25	25	25	25	25	25	25								
		3	15	15	15	15	25	25	15	15	25	25	25	25	25	25	25	25	25	25								
		4	15	15	15	15	20	20	15	15	25	25	25	25	25	25	25	25	25	25								
		6	10	10	10	10	17	16	15	14	25	25	20	20	25	25	25	25	25	25								
		8	7	6	6	5	10	10	10	8	20	20	15	15	25	25	25	25	25	25								
		10	7	6	6	5	10	10	10	8	20	15	15	15	25	25	25	25	25	25								
		13	6	6	6	5	9	8	8	7	15	15	15	15	22	22	20	20	20	20								
		16	6	6	6	5	9	8	8	7	12	12	10	10	22	22	20	18	20	18								
		20	5	5	4.5	4.5	8	7	7	6.5	12	12	10	10	20	20	20	18	20	18								
		25		4.5	4.5	4		7	6	6	10	10	10	10	15	15	15	15	15	15								
S 200P	K, Z	15	32		4	3.5			6	5.5			10	10			10	10	15	15								
		40			3				5				9				9		15									

¹⁾ The selectivity limit current I_{s1} results from the let-through I²t-value of S 750 DR plus S 200 / S 400 and the pre-arcing (melting) I²t-value of a fuse acc. to IEC / EN 60269

Notes

MCBs technical details

Coordination tables: selectivity

MCCB - S2.. B @ 415 V

Char.	Icu [kA]	Release	TM	Supply S.	T2	T1 - T2		T1 - T2 - T3										
				In [A]	Version	B, C, N, S, H, L								B, C, N, S, H, L, V				
						12.5	16	20	25	32	40	50	63	80	100	125	160	
Load S. B	-	-	-	≤2														
	-	-	-	3														
	-	-	-	4														
	S200	S200M	S200P	6	5.5 ¹	5.5	5.5	5.5	5.5	5.5	5.5	10.5	T	T	T	T	T	
	S200	S200M	S200P	8		5.5	5.5	5.5	5.5	5.5	5.5	10.5	T	T	T	T	T	
	S200	S200M	S200P	10		3 ¹	3	3	3	4.5	7.5	8.5	17	T	T	T	T	
	S200	S200M	S200P	13		3 ¹		3	3	4.5	7.5	7.5	12	20	T	T	T	
	S200	S200M	S200P	16				3 ¹	3	4.5	5	7.5	12	20	T	T	T	
	S200	S200M	S200P	20				3 ¹		3	5	6	10	15	T	T	T	
	S200	S200M	S200P	25					3 ¹	5	6	10	15	T	T	T	T	
	S200	S200M-S200P	-	32					3 ¹		6	7.5	12	T	T	T	T	
	S200	S200M-S200P	-	40							5.5 ¹	7.5	12	T	T	T	T	
	S200	S200M-S200P	-	50							3 ¹	5 ²	7.5	10.5				
	S200	S200M-S200P	-	63								5 ²	6 ³	10.5				
	-	-	-	80														
	-	-	-	100														
	-	-	-	125														

1 Value valid only for T2 magnetic only supply side circuit-breaker

3 Value valid only for T3 magnetic only supply side circuit-breaker

2 Value valid only for T2-T3 magnetic only supply side circuit-breaker

4 Value valid only for T4 magnetic only supply side circuit-breaker

MCCB - S2.. C @ 415 V

Char.	Icu [kA]	Release	TM	Supply S.	T2	T1 - T2		T1 - T2 - T3										
				In [A]	Version	B, C, N, S, H, L								B, C, N, S, H, L, V				
						12.5	16	20	25	32	40	50	63	80	100	125	160	
Load S. C	S200	S200M	S200P	≤2	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	S200M	S200P	3	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	S200M	S200P	4	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	S200M	S200P	6	5.5 ¹	5.5	5.5	5.5	5.5	5.5	5.5	10.5	T	T	T	T	T	
	S200	S200M	S200P	8		5.5	5.5	5.5	5.5	5.5	5.5	10.5	T	T	T	T	T	
	S200	S200M	S200P	10		3 ¹	3	3	3	4.5	7.5	8.5	17	T	T	T	T	
	S200	S200M	S200P	13		3 ¹		3	3	4.5	7.5	7.5	12	20	T	T	T	
	S200	S200M	S200P	16			3 ¹	3	4.5	5	7.5	12	20	T	T	T	T	
	S200	S200M	S200P	20			3 ¹		3	5	6	10	15	T	T	T	T	
	S200	S200M	S200P	25					3 ¹	5	6	10	15	T	T	T	T	
	S200	S200M-S200P	-	32					3 ¹		6	7.5	12	T	T	T	T	
	S200	S200M-S200P	-	40							5.5 ¹	7.5	12	T	T	T	T	
	S200	S200M-S200P	-	50							3 ¹	5 ²	7.5	10.5				
	S200	S200M-S200P	-	63								5 ²	6 ³	10.5				

1 Value valid only for T2 magnetic only supply side circuit-breaker

3 Value valid only for T3 magnetic only supply side circuit-breaker

2 Value valid only for T2-T3 magnetic only supply side circuit-breaker

4 Value valid only for T4 magnetic only supply side circuit-breaker

5 Value valid only for T4 In 160 magnetic only supply side circuit-breaker

MCBs technical details

Coordination tables: selectivity

T3	T4	T5	T2	T4	T5															
TM										EL										
200	250	20	25	32	50	80	100	125	160	200	250	320÷500	10	25	63	100	160	100, 160	250, 320	320÷630
T	T	7.5	7.5 ⁴	7.5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
T	T	7.5	7.5 ⁴	7.5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
T	T	5	5 ⁴	5	6.5	9	T	T	T	T	T	T	T	T	T	T	T	T	T	
T	T		5 ⁴	5	6.5	8	T	T	T	T	T	T	T	T	T	T	T	T	T	
T	T		3 ⁴	5	6.5	8	T	T	T	T	T	T	T	T	T	T	T	T	T	
T	T			5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
T	T			5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
T	T			5 ⁴	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
T	T				6.5	T	T	T	T	T	T	T	T		T	T	T	T	T	
T	T				5 ⁴	T	T	T	T	T	T	T	T		10.5	10.5	T	T	T	
T	T					T ⁴	T ⁴	T	T	T	T	T	T		10.5	T	T	T	T	

T3	T4													T5	T2				T4			
TM										EL												
200	250	20	25	32	50	80	100	125	160	200	250	320÷500	10	25	63	100	160	100, 160	250, 320	320÷630		
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	7.5	7.5 ⁴	7.5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	7.5	7.5 ⁴	7.5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5	5 ⁴	5	6.5	9	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5 ⁴		5	6.5	8	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	3 ⁴		5	6.5	8	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5		7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5		7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5 ⁴		7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	6.5						T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5 ⁴						T	T	T	T	T	T	T	T	10.5	10.5	T	T	T		
T	T	T						T	T	T	T	T	T	T	T	10.5	T	T	T	T		

MCBs technical details

Coordination tables: selectivity

MCCB - S2.. D @ 415 V

				Supply S.	T2	T1 - T2		T1 - T2 - T3										
				Version	B, C, N, S, H, L						B, C, N, S, H, L, V							
Char.	Icu [kA]			Release	TM													
	10	15	25	In [A]	12.5	16	20	25	32	40	50	63	80	100	125	160		
Load S. D	S200	S200M	S200P	≤2	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	S200M	S200P	3	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	S200M	S200P	4	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	S200M	S200P	6	5.5 ¹	5.5	5.5	5.5	5.5	5.5	5.5	10.5	T	T	T	T	T	
	S200	S200M	S200P	8					5.5	5.5	5.5	10.5	12	T	T	T	T	
	S200	S200M	S200P	10				3 ¹	3	3	3	5	8.5	17	T	T	T	
	S200	-	S200P	13					2 ¹	2	2	3	5	8	13.5	T		
	S200	S200M	S200P	16					2 ¹	2	2	3	5	8	13.5	T		
	S200	S200M	S200P	20					2 ¹		2	3	4.5	6.5	11	T		
	S200	S200M	S200P	25						2 ¹	2.5	4	6	9.5	T			
	S200	S200M-S200P	-	32								4	6	9.5	T			
	S200	S200M-S200P	-	40								3 ¹	5	8	T			
	S200	S200M-S200P	-	50								2 ¹	3 ²	5	9.5			
	S200	S200M-S200P	-	63								3 ²	5 ³	9.5				

1 Value valid only for T2 magnetic only supply side circuit-breaker

3 Value valid only for T3 magnetic only supply side circuit-breaker

5 Value valid only for T4 In 160 magnetic only supply side circuit-breaker

2 Value valid only for T2-T3 magnetic only supply side circuit-breaker

4 Value valid only for T4 magnetic only supply side circuit-breaker

MCCB - S2.. K @ 415 V

				Supply S.	T2	T1 - T2		T1 - T2 - T3										
				Version	B, C, N, S, H, L						B, C, N, S, H, L, V							
Char.	Icu [kA]			Release	TM													
	10	15	25	In [A]	12.5	16	20	25	32	40	50	63	80	100	125	160		
Load S. K	S200	S200M	S200P	≤2	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	S200M	S200P	3	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	S200M	S200P	4	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	S200M	S200P	6	5.5 ¹	5.5	5.5	5.5	5.5	5.5	5.5	10.5	T	T	T	T	T	
	S200	S200M	S200P	8				5.5	5.5	5.5	5.5	10.5	12	T	T	T	T	
	S200	S200M	S200P	10				3 ¹	3	3	3	6	8.5	17	T	T	T	
	-	-	S200P	13					2 ¹	3	3	5	7.5	10	13.5	T		
	S200	S200M	S200P	16					2 ¹	3	3	4.5	7.5	10	13.5	T		
	S200	S200M	S200P	20					2 ¹		3	3.5	5.5	6.5	11	T		
	S200	S200M	S200P	25						2 ¹	3.5	5.5	6	9.5	T			
	S200	S200M-S200P	-	32								4.5	6	9.5	T			
	S200	S200M-S200P	-	40								3 ¹	5	8	T			
	S200	S200M-S200P	-	50								2 ¹	3 ²	6	9.5			
	S200	S200M-S200P	-	63								3 ²	5.5 ³	9.5				

1 Value valid only for T2 magnetic only supply side circuit-breaker

3 Value valid only for T3 magnetic only supply side circuit-breaker

5 Value valid only for T4 In 160 magnetic only supply side circuit-breaker

2 Value valid only for T2-T3 magnetic only supply side circuit-breaker

4 Value valid only for T4 magnetic only supply side circuit-breaker

MCBs technical details

Coordination tables: selectivity

T3	T4													T5	T2					T4				T5
TM												EL												
200	250	20	25	32	50	80	100	125	160	200	250	320÷500	10	25	63	100	160	100,160	250,320	320÷630				
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	7.5	7.5 ⁴	7.5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	7.5	7.5 ⁴	7.5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5	5 ⁴	5	5	9	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5 ⁴		4	5.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T			4	5.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T			4 ⁴	5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T			4 ⁴	4.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T			4.5 ⁴		T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T			4.5 ⁴		T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T					T	T	T	T	T	T	T	T	T	T	9.5	9.5	T	T	T	T	T		
T	T					T	T	T	T	T	T	T	T	T	T	9.5	T	T	T	T	T	T		

T3	T4													T5	T2				T4				
TM												EL											
200	250	20	25	32	50	80	100	125	160	200	250	320÷500	10	25	63	100	160	100, 160	250, 320	320÷630			
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	7.5	7.5 ⁴	7.5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	7.5	7.5 ⁴	7.5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5 ⁴		5	5	9	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5 ⁴		5	5	8	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5 ⁴		5	8	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T					5	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T					5 ⁴	6 ⁴	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T					5 ⁴	6 ⁴	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T							5.5 ⁴	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T							5 ⁴	T	T	T	T	T	T	T	9.5	9.5	T	T	T	T		
T	T								T	T	T	T	T	T	T	9.5	T	T	T	T			

MCBs technical details

Coordination tables: selectivity

MCCB - S2.. Z @ 415 V

		Supply S.	T2	T1 - T2		T1 - T2 - T3												
		Version	B, C, N, S, H, L	B, C, N, S, H, L, V														
Char.	Icu [kA]	Release	TM															
		10	15	25	In [A]	12.5	16	20	25	32	40	50	63	80	100	125	160	
Load S. Z	S200	-	S200P	≤2	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	-	S200P	3	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	-	S200P	4	T	T	T	T	T	T	T	T	T	T	T	T	T	
	S200	-	S200P	6	5.5 ¹	5.5	5.5	5.5	5.5	5.5	5.5	10.5	T	T	T	T	T	
	S200	-	S200P	8		5.5	5.5	5.5	5.5	5.5	5.5	10.5	T	T	T	T	T	
	S200	-	S200P	10		3 ¹	3	3	3	4.5	8	8.5	17	T	T			
	-	-	S200P	13		3 ¹		3	3	4.5	7.5	7.5	12	20	T			
	S200	-	S200P	16				3 ¹	3	4.5	5	7.5	12	20	T			
	S200	-	S200P	20					3 ¹		3	5	6	10	15	T		
	S200	-	S200P	25						3 ¹	5	6	10	15	T			
	S200	S200P	-	32							3 ¹	6	7.5	12	T			
	S200	S200P	-	40								5.5 ¹	7.5	12	T			
	S200	S200P	-	50								4 ¹	5 ²	7.5	10.5			
	S200	S200P	-	63								5 ²	6 ³	10.5				

1 Value valid only for T2 magnetic only supply side circuit-breaker

3 Value valid only for T3 magnetic only supply side circuit-breaker

2 Value valid only for T2-T3 magnetic only supply side circuit-breaker

4 Value valid only for T4 magnetic only supply side circuit-breaker

MCBs technical details

Coordination tables: selectivity

T3	T4													T5	T2				T4				
TM												EL											
200	250	20	25	32	50	80	100	125	160	200	250	320÷500	10	25	63	100	160	100, 160	250, 320	320÷630			
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	7.5	7.5 ⁴	7.5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	7.5	7.5 ⁴	7.5	7.5	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T	5	5 ⁴	5	6.5	9	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T		5 ⁴	5	6.5	8	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T		5 ⁴	4.5	6.5	8	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
T	T			5	6.5	T	T	T	T	T	T	T			T	T	T	T	T	T	T		
T	T			5	6.5	T	T	T	T	T	T	T			T	T	T	T	T	T	T		
T	T			5 ⁴	6.5	T	T	T	T	T	T	T			T	T	T	T	T	T	T		
T	T				5	T	T	T	T	T	T	T			T	T	T	T	T	T	T		
T	T					3.5 ⁴	T	T	T	T	T	T				10.5	10.5	T	T	T	T		
T	T						T	T	T	T	T	T				10.5	T	T	T	T	T		

MCCB - S800 @ 415 V

			Supply S.	T1	T1 - T3								T1	T3				
			Version	B, C, N, S, H, L, V														
			Release	TM														
Load S.	Char.	Icu [kA]	In [A]	16	20	25	32	40	50	63	80	100	125	160	160	200	250	
S800N	B C D	36	10		4.5	4.5	4.5	4.5	8	10	201	251	T	T	T	T		
			13		4.5	4.5	4.5	7.5	10	15	251	T	T	T	T	T	T	
			16			4.5	4.5	7.5	10	15	251	T	T	T	T	T	T	
			20				4.5	7.5	10	15	251	T	T	T	T	T	T	
			25					6	10	15	201	T	T	T	T	T	T	
			32						7.5	10	201	T	T	T	T	T	T	
			40							10	201	T	T	T	T	T	T	
			50								15	T	T	T	T	T	T	
			63								T	T	T	T	T	T	T	
			80								T		T	T	T	T	T	
S800S	B C D K	50	100								T			T		T	T	
			125											T			T	
			10		4.5	4.5	4.5	4.5	8	10	201	251	361	361	361	361	T	
			13		4.5	4.5	4.5	7.5	10	15	251	361	361	361	361	361	T	
			16			4.5	4.5	7.5	10	15	251	361	361	361	361	361	T	
			20				4.5	7.5	10	15	251	361	361	361	361	361	T	
			25					6	10	15	201	361	361	361	361	361	T	
			32						7.5	10	201	361	361	361	361	361	T	
			40							10	201	361	361	361	361	361	T	
			50								15	361	361	361	361	361	T	
			63									361	361	361	361	361	T	
			80									361	361	361	361	361	T	
			100									361					T	
			125														T	

¹ Select the lowest value between what is indicated and the breaking capacity of the supply side circuit-breaker

MCBs technical details

Coordination tables: selectivity

MCCB-S800 @ 415 V

			Supply S. T4										T4 - T5		
			Version	N, S, H, L, V										EL	
			Release	TM											
Load S.	Char.	Icu [kA]	In [A]	20	25	32	50	80	100	125	160	200÷250	100÷630		
S800N/S	B	36-50	10	6.5	6.5 ¹	6.5	6.5	11	T	T	T	T	T	T	
			13	6.5	5 ¹	6.5	6.5	11	T	T	T	T	T	T	
			16		5 ¹	6.5	6.5	11	T	T	T	T	T	T	
			20		4 ¹	6.5	6.5	11	T	T	T	T	T	T	
			25				6.5	11	T	T	T	T	T	T	
			32				6.5	8	T	T	T	T	T	T	
			40				5 ¹	6.5	T	T	T	T	T	T	
			50					5 ¹	7.5	T	T	T	T	T	
			63						5 ¹	7	T	T	T	T	
			80								T	T	T	T	
			100									T	T	T	
			125										T		
			10	6.5	6.5 ¹	6.5	6.5	11	T	T	T	T	T	T	
	C	36-50	13	6.5	5 ¹	6.5	6.5	11	T	T	T	T	T	T	
			16		5 ¹	6.5	6.5	11	T	T	T	T	T	T	
			20		4 ¹	6.5	6.5	11	T	T	T	T	T	T	
			25		4 ¹		6.5	11	T	T	T	T	T	T	
			32				6.5	8	T	T	T	T	T	T	
			40				5 ¹	6.5	T	T	T	T	T	T	
			50				4 ¹	5 ¹	7.5	T	T	T	T	T	
			63					4 ¹	6.5 ¹	7	T	T	T	T	
			80					4 ¹	5 ¹	6.5 ¹	6.5	T	T	T	
			100						4 ¹	5 ¹	5 ¹	6.5	T	T	
			125							4 ¹	4 ¹	5 ¹	T		
			10	6.5	6.5 ¹	6.5	6.5	11	T	T	T	T	T	T	
	D	36-50	13		5 ¹		6.5	11	T	T	T	T	T	T	
			16				6.5	11	T	T	T	T	T	T	
			20				6.5 ¹	11	T	T	T	T	T	T	
			25				6.5 ¹	11	T	T	T	T	T	T	
			32					8 ¹	T	T	T	T	T	T	
			40					6.5 ¹	T	T	T	T	T	T	
			50						7.5 ¹	T	T	T	T	T	
			63							7 ¹	T	T	T	T	
			80								5 ¹	T	T	T	
			100									5 ¹	T	T	
			125										T		
			10		6.5 ¹	6.5	6.5	11	T	T	T	T	T	T	
	K	36-50	13		5 ¹	5	6.5	11	T	T	T	T	T	T	
			16		5 ¹		6.5	11	T	T	T	T	T	T	
			20		4 ¹		6.5	11	T	T	T	T	T	T	
			25				6.5 ¹	11 ¹	T	T	T	T	T	T	
			32				5 ¹	8 ¹	T	T	T	T	T	T	
			40					6.5 ¹	T	T	T	T	T	T	
			50					5 ¹	7.5 ¹	T	T	T	T	T	
			63					4 ¹	6.5 ¹	7 ¹	T	T	T	T	
			80						5 ¹	6.5 ¹	7 ¹	T	T	T	
			100							5 ¹	6.5 ¹	7 ¹	T	T	
			125								5 ¹	6.5 ¹	T		

¹ Value valid only for magnetic only supply side circuit-breaker (with In = 50 A, please consider MA52 circuit-breakers)

² For T4 In = 100 A, value valid only for magnetic only supply side circuit-breaker

³ For T4 In = 160 A, value valid only for magnetic only supply side circuit-breaker

MCBs technical details

MCBs internal resistance, power loss and max. permissible earth-fault loop impedance

Internal resistance and power loss of the miniature circuit-breakers

Internal resistance per pole in mΩ, power loss per pole in W

Type	Rated current	Device series B, C, D *	
		mW	W
	I _n A		
SN201 L	2	520	2.1
SN201	4	147.5	2.4
SN201 M	6	64	2.3
	10	19	1.9
	16	14	3.6
	20	12	4.8
	25	7.1	4.4
	32	6.5	6.7
	40	4.7	7.5

* Total power loss

Type	Rated current	Device series							
		B, C ①		D		K		Z	
I _n A	mΩ	W	mΩ	W	mΩ	W	mΩ	W	
S 200 and S 200 M	0.5	5500	1.4	4300	1.1	4300	1.1	8100	2.4
	1	1440	1.4	1250	1.25	1250	1.25	2100	2.3
	1.6	630	1.6	600	1.5	600	1.5	1000	2.8
	2	460	1.8	410	1.65	410	1.65	619	2.5
	3	150	1.3	130	1.2	130	1.2	235	2.4
	4	110	1.8	105	1.7	105	1.7	149	2.4
	6	55	2.0	52	1.9	52	1.9	75	3.2
	8	23	1.5	24	1.5	24	1.5	27	2.0
	10	19	2.1	16	1.6	13.5	1.4	24	2.7
	13	14	2.3	14	2.2	13.5	1.4	-	-
	16	8.5	2.5	8.5	2.5	7.7	2.0	10.9	2.8
	20	6.25	2.5	6.1	2.3	6.7	2.7	6.0	2.4
	25	5.0	3.2	4.3	3.1	4.6	2.9	4.5	3.3
	32	3.6	3.7	3.5	3.6	3.5	3.6	3.5	3.6
	40	3.0	4.8	2.2	4.2	2.8	4.5	2.5	4.1
	50	1.3	3.25	1.25	2.9	1.25	3.1	1.5	4.1
	63	1.2	4.8	1.2	4.8	1.0	4.4	1.3	5.2

① Current intensities 0.5 – 4 apply exclusively to C-type trip characteristics.

MCBs technical details

MCBs internal resistance, power loss and max. permissible earth-fault loop impedance

Internal resistance and power loss of the miniature circuit-breakers

Internal resistance per pole in mΩ, power loss per pole in W

Type	Rated current	Device series		K	W	Z	W
		B, C, D ①	mΩ				
	I _n A	mΩ	W	mΩ	W	mΩ	W
S 200 P	0.2	–	–	42500	1.7	–	–
	0.3	–	–	20000	1.8	–	–
	0.5	5500	1.4	6340	1.6	10100	2.5
	0.75	–	–	2500	1.4	–	–
	1	1440	1.4	1400	1.4	2270	2.3
	1.6	630	1.6	625	1.6	1100	2.8
	2	460	1.8	460	1.8	619	2.5
	3	211	1.9	211	1.9	211	1.9
	4	150	2.4	163	2.6	163	2.6
	6	61	2.2	67	2.4	104	3.7
	8	45	2.9	45	2.9	55	3.5
	10	14	1.4	19	1.9	21	2.1
	13	13.3	2.3	–	–	–	–
	16	9.7	2.5	8.2	2.1	10.9	2.8
	20	7.3	2.9	7.3	2.9	7.3	2.9
	25	5.6	3.5	5.6	3.5	5.6	3.5
	32	4.1	4.2	4.1	4.2	4.1	4.2
	40	4.0	6.4	4.0	6.4	4.0	6.4
	50	1.2	3.0	1.2	3.0	1.8	4.4
	63	1.4	5.6	1.3	5.2	1.3	5.2

① Current intensities 0.5 – 4 apply exclusively to C-type trip characteristics.

MCBs technical details

MCBs internal resistance, power loss and max. permissible earth-fault loop impedance

Internal resistance and power loss per pole

Internal resistance in mΩ per pole in cold state, power loss in W per pole at rated current

Type	Tripping characteristics	Rated current A	R _i	P _{Vmax}
			mΩ	W
S 200 S	B, C	6	52.1	2.16
	C	8	22.9	1.65
	B, C	10	19.0	2.20
	B, C	13	13.7	2.62
	B, C	16	9.1	3.28
	B, C	20	6.2	3.14

SU200 M

Rated current I _n A	C, K characteristics		Z characteristics	
	Internal resistance per pole		Power loss	Internal resistance per pole
	R _i mΩ	P _v W	R _i mΩ	P _v W
0.2	42500	1.7	-	-
0.3	18889	1.7	-	-
0.5	5600	1.4	9000	2.3
0.75	2489	1.4	-	-
1	1400	1.4	2200	2.2
1.6	703	1.8	1000	2.6
2	450	1.8	650	2.6
3	178	1.6	250	2.3
4	113	1.8	140	2.2
5	50	1.3	100	2.5
6	56	2.0	70	2.5
8	23	1.5	28	1.8
10	21	2.1	21	2.1
13	14	2.3	17	2.9
15	11	2.4	13	2.9
16	9.8	2.5	10	2.6
20	6.3	2.5	6.5	2.6
25	5.1	3.2	5.1	3.2
30	3.9	3.5	3.9	3.5
32	3.6	3.7	3.6	3.7
35	3.3	4.1	3.3	4.1
40	2.8	4.5	2.8	4.5
50	1.8	4.5	1.8	4.5
60	1.4	4.9	1.4	4.9
63	1.4	5.4	1.4	5.4

MCBs technical details

MCBs internal resistance, power loss and max. permissible earth-fault loop impedance

S200 80-100A

Tripping characteristic	Rated current		Internal resistance R_i mΩ	Power loss	
	I_n	A		P_v	W
	B, C	80		0.9	8.1
	B, C	100	0.8		9.8

Type	Rated current	R_i	P_{vmax}	Type	R_i	P_{vmax}
	A	mΩ	W		mΩ	W
S 700-E	10	38.0	4.9	S 700-K		
	16	15.5	5.2		10.5	3.1
	20	12.5	6.5		7.5	3.8
	25	7.4	6.5		5.7	3.9
	32	5.3	7.2		4.7	7.8
	35	4.0	7.6		3.8	6.8
	40	4.0	8.0		3.0	10.0
	50	2.9	9.5		2.0	9.6
	63	2.0	9.9		1.3	10.1
	80	1.5	13.5		1.1	12.3

S 750DR E			S 750DR K	
Rated current I_n / A	Internal resistance ¹ R_i / mΩ	Power loss ² P_v / W	Internal resistance ¹ R_i / mΩ	Power loss ² P_v / W
16	15.3	4.1	14.5	3.9
20	11.3	5.4	10.7	5.1
25	8.7	5.9	8.3	5.5
35	4.5	6.3	4.3	6.2
40	3.4	6.1	3.2	5.8
50	2.9	7.6	2.8	7.2
63	2.1	8.7	2.1	8.7
80	1.6	10.5	1.6	10.5
100	1.3	12.0	1.3	12.0

¹in cold state ²at rated current

S800PV-SP, S800PV-SD and S800PV-M-H

Typical internal resistances and power losses at 25 °C ambient temperature (per pole)

Rated current I_n [A]	Internal resistance R_i [mΩ]			Power loss P_v [W]		
	PV-SP	PV-SD	PV-M-H	PV-SP	PV-SD	PV-M-H
10	15.2			1.5		
13	12.1			2.0		
16	12.1			3.1		
20	8.7			3.5		
25	6.8			4.3		
32	3.1	1.8	1.8	3.2	1.8	1.8
40	2.3			3.7		
50	1.7			4.3		
63	1.6	0.9	0.9	6.4	3.6	3.6
80	1.0			6.4		
100	0.8			8.0		
125	0.6	0.5	0.6	9.4	7.8	6.0

MCBs technical details

MCBs internal resistance, power loss and max. permissible earth-fault loop impedance

S800S - S800N - S800C - S800HV

Typical internal resistances and power losses at 25 °C ambient temperature (per pole)

Rated current I_n [A]	Internal resistance R_i [mΩ]	Power loss P_v [W]				
		B, C, D, K ①	KM ②	UCB, UCK ②	B, C, D, K	KM ②
0.5	8124.6	-		8124.6	2	-
1	1627.2	-		1627.2	1.6	-
1.6	1118.6	-		1118.6	2.9	-
2	556.6	-		556.6	2.2	-
2.5	399.3	-		399.3	2.5	-
3	270.3	-		270.3	2.4	-
4	126.4	-		126.4	2	-
5	57.9	-		57.9	1.5	-
6	51.7	-		51.7	1.8	-
8	27.2	-		27.2	1.7	-
10	15.2	-		15.2	1.5	-
13	12.1	-		12.1	2	-
16	12.1	-		12.1	3.1	-
20	8.7	2.7		8.7	3.5	1.1
25	6.8	3		6.8	4.3	1.9
32	3.1	1.7		3.1	3.2	1.7
40	2.3	1.6		2.3	3.7	2.6
50	1.7	1.1		1.7	4.3	2.8
63	1.6	1		1.6	6.4	4
80	1	0.75		1	6.4	5
100	0.8	-		0.8	8	-
125	0.6	-		0.6	9.4	-

① K Applicable only for S800S-S800C ② KM, UCB, UCK Applicable only for S800S

S800B

Typical internal resistances and power losses at 25 °C ambient temperature (per pole)

Rated current I_n [A]	Internal resistance R_i [mΩ]	Power loss P_v [W]		
		B, C	D, K	B, C
32	3.1		3.1	3.2
40	2.3		2.3	3.7
50	1.7		1.7	4.3
63	1.6		1.6	6.4
80	1.0		1.0	6.4
100	0.8		0.8	8.0
125	0.7	-		10.9

S800U - S800UP

Typical internal resistances and power losses at 25 °C ambient temperature (per pole)

Rated current I_n [A]	Internal resistance R_i [mW]	Power loss P_v [W]	
		K, Z	K, Z
10	15.2		1.5
15	12.1		2.7
20	8.7		3.5
25	6.8		4.2
30	3.1		2.8
40	2.3		3.7
50	1.7		4.3
60	1.6		5.8
70	1.0		4.9
80	1.0		6.4
90	0.8		6.5
100	0.8		8.3

MCBs technical details

MCBs internal resistance, power loss and max. permissible earth-fault loop impedance

S800S - S800N - S800C

Maximum permissible earth-fault loop impedance Z_s at U_o 230 V* to ensure compliance with the requirements of IEC 60364-4.

The instantaneous release of the MCB ensures an operating time of max. 0.1s (TN system). Determined according to IEC 60364-5-52 / VDE 0100-520 and DIN VDE 0100-520 sheet 2:2002 (source impedance 300 mW, c = 0.95 and conductor temperature 70 °C = factor 0.8). The internal resistance of the MCB is included. Values below 10 A are available upon request.

* U_o : rated voltage against earthed conductor; for U_o : AC 240 V multiply Z_s by 1.04, for U_o : AC 254 V multiply Z_s by 1.10, for U_o : AC 400 V multiply Z_s by 1.74

Rated current (A)	B	C max. Z_s (Ω)	D	K
10	4.8	2.4	1.5	1.5
13	3.7	1.8	1.1	1.1
16	3.0	1.5	0.9	0.9
20	2.4	1.2	0.7	0.7
25	1.9	1.0	0.6	0.6
32	1.5	0.7	0.5	0.5
40	1.2	0.6	0.4	0.4
50	1.0	0.5	0.3	0.3
63	0.8	0.4	0.2	0.2
80	0.6	0.3	0.2	0.2
100	0.5	0.2	0.1	0.1
125	0.4	0.2	0.1	0.1

MCBs technical details

MCBs internal resistance, power loss and max. permissible earth-fault loop impedance

Maximum permissible earth-fault loop impedance ZS at U0 = 230 V~ b to ensure compliance with the operation conditions pursuant to IEC 60364-4.

Operating time < 0.4 s; at 400 V~ < 0.2 s and at > 400 V~ < 0.1 s The instantaneous release of the MCB ensures an operating time of ≤ 0.1 s (TN system).

Determined according to DIN VDE 0100-520 sheet 2:2002-11 (source impedance = 300 mΩ, c = 0.95 and conductor temperature 70 °C = factor 0.8). The internal resistance of the MCB is already included.

S 200 and S 200 M

Rated current I _n A	B	C	D	K	Z
	max. ZS				
	q	q	q	q	q
0.5	–	46	33.0	33.0	153.3
1	–	23	16.5	16.5	76.7
1.6	–	14.4	10.3	10.3	47.9
2	–	11.5	8.2	8.2	38.3
3	–	7.7	5.5	5.5	25.6
4	–	5.8	4.1	4.1	19.2
6	7.7	3.8	2.7	2.7	12.8
8	–	2.8	2.1	2.1	9.5
10	4.6	2.2	1.6	1.6	7.7
13	3.5	1.7	1.2	1.2	–
16	2.9	1.4	1.0	1.0	4.8
20	2.3	1.2	0.8	0.8	3.8
25	1.8	0.9	0.7	0.7	3.1
32	1.4	0.7	0.5	0.5	2.4
40	1.1	0.6	0.4	0.4	1.9
50	0.9	0.5	0.3	0.3	1.5
63	0.7	0.4	0.3	0.3	1.2

b U0 = rated voltage against earthed conductor; for U0 = 240 V~ is ZS · 1.04; for U0 = 127 V~ is ZS · 0.55

MCBs technical details

Performances at different ambient temperatures, altitudes and frequencies

S 200 P

Rated current I_n A	B	C	D	K	Z
	max. ZS q				
0.2	–	–		39.5	–
0.3	–	–		34.8	–
0.5	–	46	27.4	26.5	143
0.75	–	–		19.4	–
1	–	23	15	15	74.4
1.6	–	14.4	9.6	9.6	47.9
2	–	11.5	7.8	7.8	38.3
3	–	7.7	11.8	5.3	25.3
4	–	5.8	8.8	3.9	19.1
6	7.6	3.8	5.9	2.6	12.7
8	–	2.8	5.7	2.0	9.5
10	4.6	2.3	3.5	1.6	7.6
13	3.5	1.7	2.7	1.3	–
16	2.9	1.4	2.2	1.0	4.7
20	2.3	1.1	1.7	0.8	3.8
25	1.8	0.9	1.4	0.6	3.0
32	1.4	0.7	1.1	0.5	2.4
40	1.1	0.6	0.9	0.4	1.9
50	0.9	0.5	0.7	0.3	1.5
63	0.7	0.4	0.6	0.25	1.1

b U0 = rated voltage against earthed conductor; for U0 = 240 V~ is ZS · 1.04; for U0 = 127 V~ is ZS · 0.55

Take into account the voltage drop:

e.g. in the case of a 1.5 mm² conductor, protected by a B 16 circuit-breaker, the maximum cable length is 82 m. If the voltage drop is below 3%, this would result in a maximum cable length (2-strand) of 17 m. For more details on this topic, get your own copy of the technical information leaflet "Maximum cable lengths".

Maximum cable lengths in the case of different voltages and cross sections on request.

MCBs technical details

Performances at different ambient temperatures, altitudes and frequencies

Derating of load capability of MCBs

Derating of MCBs load capability takes in consideration 2 factors: ambient temperature and influence of adjacent devices. The rules to obtain the effective value of I_n are the following:

1. Deviating ambient temperature:

The rated value of the current of a miniature circuit-breaker refers to a temperature of 20 °C for circuit-breakers with characteristics K and Z and 30 °C for characteristics B, C and D. The following tables contain the derating of load

capability of S 200/S 200 M/S 200 P/S 200 S MCBs*

with temperature from -40 °C to 70 °C for the curves B, C, D and K, Z.

Max. operating current depending on the ambient temperature of a circuit-breaker in load circuit of characteristics type B, C, D, K, Z.

Tripping characteristics	I_n A	Rated current T °C	Maximum operating current at ambient temperature									
			-40	-30	-20	-10	0	10	20	30	40	50
B, C, D	0,5	0.61	0.59	0.58	0.56	0.55	0.53	0.52	0.50	0.49	0.47	0.46
	1	1.21	1.18	1.15	1.12	1.09	1.06	1.03	1.00	0.97	0.94	0.91
	1,6	1.94	1.89	1.84	1.79	1.74	1.70	1.65	1.60	1.55	1.50	1.46
	2	2.42	2.36	2.30	2.24	2.18	2.12	2.06	2.00	1.94	1.88	1.82
	3	3.63	3.54	3.45	3.36	3.27	3.18	3.09	3.00	2.91	2.82	2.73
	4	4.84	4.72	4.60	4.48	4.36	4.24	4.12	4.00	3.88	3.76	3.64
	6	7.26	7.08	6.90	6.72	6.54	6.36	6.18	6.00	5.82	5.64	5.46
	8	9.68	9.44	9.20	8.96	8.72	8.48	8.24	8.00	7.76	7.52	7.28
	10	12.10	11.80	11.50	11.20	10.90	10.60	10.30	10.00	9.70	9.40	9.10
	13	15.70	15.30	15.00	14.60	14.20	13.80	13.40	13.00	12.60	12.20	11.80
	16	19.40	18.90	18.40	17.90	17.40	17.00	16.50	16.00	15.50	15.00	14.60
	20	24.20	23.60	23.00	22.40	21.80	21.20	20.60	20.00	19.40	18.80	18.20
	25	30.30	29.50	28.80	28.00	27.30	26.50	25.80	25.00	24.30	23.50	22.80
K, Z	32	38.70	37.80	36.80	35.80	34.90	33.90	33.00	32.00	31.00	30.10	29.10
	40	48.40	47.20	46.00	44.80	43.60	42.40	41.20	40.00	38.80	37.60	36.40
	50	60.50	59.00	57.50	56.00	54.50	53.00	51.50	50.00	48.50	47.00	45.50
	63	76.20	74.30	72.50	70.60	68.70	66.80	64.90	63.00	61.10	59.20	57.30
	0,5	0.59	0.58	0.56	0.55	0.53	0.52	0.50	0.49	0.47	0.46	0.45
	1	1.18	1.15	1.12	1.09	1.06	1.03	1.00	0.97	0.94	0.91	0.88
	1,6	1.89	1.84	1.79	1.74	1.7	1.65	1.60	1.55	1.50	1.46	1.42
	2	2.36	2.3	2.24	2.18	2.12	2.06	2.00	1.94	1.88	1.82	1.77
	3	3.54	3.45	3.36	3.27	3.18	3.09	3.00	2.91	2.82	2.73	2.65
	4	4.72	4.60	4.48	4.36	4.24	4.12	4.00	3.88	3.76	3.64	3.53
	6	7.08	6.90	6.72	6.54	6.36	6.18	6.00	5.82	5.64	5.46	5.30
	8	9.44	9.20	8.96	8.72	8.48	8.24	8.00	7.76	7.52	7.28	7.06
	10	11.80	11.50	11.20	10.90	10.60	10.30	10.00	9.70	9.40	9.10	8.83
	13	15.30	15.00	14.60	14.20	13.80	13.40	13.00	12.60	12.20	11.80	11.45
	16	18.90	18.40	17.90	17.40	17.00	16.50	16.00	15.50	15.00	14.60	14.16
	20	23.60	23.00	22.40	21.80	21.20	20.60	20.00	19.40	18.80	18.20	17.65
	25	29.50	28.80	28.00	27.30	26.50	25.80	25.00	24.30	23.50	22.80	22.12
	32	37.80	36.80	35.80	34.90	33.90	33.00	32.00	31.00	30.10	29.10	28.23
	40	47.20	46.00	44.80	43.60	42.40	41.20	40.00	38.80	37.60	36.40	35.31
	50	59.00	57.50	56.00	54.50	53.00	51.50	50.00	48.50	47.00	45.50	44.14
	63	74.30	72.50	70.60	68.70	66.80	64.90	63.00	61.10	59.20	57.30	55.58

MCBs technical details

Performances at different ambient temperatures, altitudes and frequencies

SU200 M - IEC/EN 60947-2

I_n (A)	Ambient temperature T (°C)											
	-40	-30	-20	-10	0	10	25	30	40	50	60	70
0.2 ¹⁾	0.26	0.25	0.24	0.23	0.22	0.22	0.21	0.20	0.19	0.19	0.18	0.17
0.3 ¹⁾	0.39	0.37	0.36	0.35	0.33	0.32	0.31	0.30	0.29	0.28	0.27	0.26
0.5	0.64	0.62	0.60	0.58	0.56	0.54	0.52	0.5	0.48	0.46	0.45	0.43
0.75 ¹⁾	0.97	0.93	0.90	0.87	0.84	0.81	0.78	0.75	0.72	0.70	0.67	0.65
1	1.29	1.24	1.20	1.16	1.12	1.08	1.04	1.00	0.96	0.93	0.89	0.86
1.6	2.06	1.99	1.92	1.85	1.78	1.72	1.66	1.6	1.54	1.48	1.43	1.38
2	2.58	2.49	2.40	2.31	2.23	2.15	2.07	2.00	1.93	1.85	1.79	1.72
3	3.87	3.73	3.60	3.47	3.35	3.23	3.11	3.00	2.89	2.78	2.68	2.58
4	5.16	4.97	4.80	4.63	4.46	4.30	4.15	4.00	3.85	3.71	3.57	3.44
5	6.45	6.22	6.00	5.78	5.58	5.38	5.19	5.00	4.82	4.64	4.47	4.30
6	7.74	7.46	7.20	6.94	6.69	6.45	6.22	6.00	5.78	5.56	5.36	5.16
8	10.32	9.95	9.59	9.25	8.92	8.60	8.30	8.00	7.70	7.42	7.14	6.88
10	12.90	12.44	11.99	11.56	11.15	10.75	10.37	10.00	9.63	9.27	8.93	8.60
13	16.76	16.17	15.59	15.03	14.50	13.98	13.48	13.00	12.52	12.06	11.61	11.18
15	19.34	18.65	17.99	17.35	16.73	16.13	15.56	15.00	14.45	13.91	13.40	12.90
16	20.63	19.90	19.19	18.50	17.84	17.21	16.59	16.00	15.41	14.84	14.29	13.76
20	25.79	24.87	23.98	23.13	22.30	21.51	20.74	20.00	19.26	18.55	17.86	17.20
25	32.24	31.09	29.98	28.91	27.88	26.88	25.93	25.00	24.08	23.18	22.33	21.50
30	38.69	37.31	35.98	34.69	33.45	32.26	31.11	30.00	28.89	27.82	26.79	25.80
32	41.27	39.79	38.37	37.01	35.69	34.41	33.18	32.00	30.82	29.68	28.58	27.52
35	45.14	43.53	41.97	40.47	39.03	37.64	36.30	35.00	33.71	32.46	31.26	30.10
40	51.58	49.74	47.97	46.26	44.61	43.01	41.48	40.00	38.52	37.09	35.72	34.40
50	64.48	62.18	59.96	57.82	55.76	53.77	51.85	50.00	48.15	46.37	44.65	43.00
60	77.38	74.61	71.95	69.39	66.91	64.52	62.22	60.00	57.78	55.64	53.58	51.60
63	81.24	78.35	75.55	72.85	70.25	67.75	65.33	63.00	61.00	58.00	56.00	54.00

1) Current ratings 0.2, 0.3 and 0.75 A available with K characteristic only

MCBs technical details

Performances at different ambient temperatures, altitudes and frequencies

SU200 M - UL 489

I _n (A)	Ambient temperature T (°C)											
	-40	-30	-20	-10	0	10	25	30	40	50	60	70
0.2 ¹⁾	0.27	0.26	0.25	0.24	0.23	0.22	0.22	0.21	0.20	0.19	0.19	0.18
0.3 ¹⁾	0.40	0.39	0.37	0.36	0.35	0.33	0.32	0.31	0.30	0.29	0.28	0.27
0.5	0.67	0.64	0.62	0.60	0.58	0.56	0.54	0.52	0.50	0.48	0.46	0.45
0.75 ¹⁾	1.00	0.97	0.93	0.90	0.87	0.84	0.81	0.78	0.75	0.72	0.70	0.67
1	1.34	1.29	1.24	1.20	1.16	1.12	1.08	1.04	1.00	0.96	0.93	0.89
1.6	2.14	2.06	1.99	1.92	1.85	1.78	1.72	1.66	1.6	1.54	1.48	1.43
2	2.67	2.58	2.49	2.40	2.31	2.23	2.15	2.07	2.00	1.93	1.85	1.79
3	4.01	3.87	3.73	3.60	3.47	3.35	3.23	3.11	3.00	2.89	2.78	2.68
4	5.35	5.16	4.97	4.80	4.63	4.46	4.30	4.15	4.00	3.85	3.71	3.57
5	6.69	6.45	6.22	6.00	5.78	5.58	5.38	5.19	5.00	4.82	4.64	4.47
6	8.02	7.74	7.46	7.20	6.94	6.69	6.45	6.22	6.00	5.78	5.56	5.36
8	10.70	10.32	9.95	9.59	9.25	8.92	8.60	8.30	8.00	7.70	7.42	7.14
10	13.37	12.90	12.44	11.99	11.56	11.15	10.75	10.37	10.00	9.63	9.27	8.93
13	17.38	16.76	16.17	15.59	15.03	14.50	13.98	13.48	13.00	12.52	12.06	11.61
15	20.06	19.34	18.65	17.99	17.35	16.73	16.13	15.56	15.00	14.45	13.91	13.40
16	21.40	20.63	19.90	19.19	18.50	17.84	17.21	16.59	16.00	15.41	14.84	14.29
20	26.75	25.79	24.87	23.98	23.13	22.30	21.51	20.74	20.00	19.26	18.55	17.86
25	33.43	32.24	31.09	29.98	28.91	27.88	26.88	25.93	25.00	24.08	23.18	22.33
30	40.12	38.69	37.31	35.98	34.69	33.45	32.26	31.11	30.00	28.89	27.82	26.79
32	42.79	41.27	39.79	38.37	37.01	35.69	34.41	33.18	32.00	30.82	29.68	28.58
35	46.81	45.14	43.53	41.97	40.47	39.03	37.64	36.30	35.00	33.71	32.46	31.26
40	53.49	51.58	49.74	47.97	46.26	44.61	43.01	41.48	40.00	38.52	37.09	35.72
50	66.87	64.48	62.18	59.96	57.82	55.76	53.77	51.85	50.00	48.15	46.37	44.65
60	80.24	77.38	74.61	71.95	69.39	66.91	64.52	62.22	60.00	57.78	55.64	53.58
63	84.25	81.24	78.35	75.55	72.85	70.25	67.75	65.33	63.00	60.67	58.42	56.26

1) Current ratings 0.2, 0.3 and 0.75 A available with K characteristic only

S200 80-100A

B and C	Ambient temperature T (°C)											
	-40	-30	-20	-10	0	10	25	30	40	50	60	70
80	96.8	94.4	92.0	89.6	87.2	84.8	82.4	80.0	77.6	75.2	72.8	70.4
100	121.0	118.0	115.0	112.0	109.0	106.0	103.0	100.0	97.0	94.0	91.0	88.0

SN201

B, C and D	Ambient temperature T (°C)										
	-25	-20	-10	0	10	20	30	40	50	55	
2	2.37	2.32	2.26	2.18	2.12	2.06	2.00	1.95	1.91	1.89	
4	4.74	4.60	4.53	4.37	4.24	4.12	4.00	3.90	3.85	3.79	
6	7.20	7.00	6.80	6.40	6.30	6.20	6.00	5.90	5.80	5.70	
10	11.80	11.60	11.30	10.90	10.60	10.30	10.00	9.80	9.70	9.50	
16	18.10	17.70	17.40	16.90	16.60	16.30	16.00	15.80	15.70	15.50	
20	23.70	23.20	22.60	21.80	21.20	20.60	20.00	19.60	19.10	18.90	
25	29.40	29.00	28.20	27.40	26.70	26.00	25.00	24.20	23.50	23.10	
32	38.70	38.10	37.20	36.20	34.60	33.00	32.00	31.30	30.50	30.00	
40	48.30	47.50	45.80	44.40	42.70	41.00	40.00	39.50	38.60	38.20	

MCBs technical details

Performances at different ambient temperatures, altitudes and frequencies

S 750 DR

$E_{\text{selective}}$	Maximum operating current at ambient temperature T (°C)							
Rated current I_n (A)	-20	-10	0	10	20	30	40	50
16	21.4	20.4	19.3	18.2	17.1	16.0	15.2	14.4
20	26.8	25.4	24.1	22.7	21.4	20.0	19.0	18.0
25	33.5	31.8	30.1	28.4	26.7	25.0	23.8	22.5
32	42.9	40.7	38.5	36.4	34.2	32.0	30.4	28.8
40	53.6	50.9	48.2	45.4	42.7	40.0	38.0	36.0
50	67.0	63.6	60.2	56.8	53.4	50.0	47.5	45.1
63	84.5	80.2	75.9	71.6	67.3	63.0	59.9	56.8
80	107.2	101.8	96.3	90.9	85.4	80.0	76.0	72.1
100	134.1	127.2	120.4	113.6	106.8	100.0	95.1	90.1

$K_{\text{selective}}$	Maximum operating current at ambient temperature T (°C)							
Rated current I_n (A)	-20	-10	0	10	20	30	40	50
16	21.4	20.4	19.3	18.2	17.1	16.0	15.2	14.4
20	26.8	25.4	24.1	22.7	21.4	20.0	19.0	18.0
25	33.5	31.8	30.1	28.4	26.7	25.0	23.8	22.5
32	42.9	40.7	38.5	36.4	34.2	32.0	30.4	28.8
40	53.6	50.9	48.2	45.4	42.7	40.0	38.0	36.0
50	67.0	63.6	60.2	56.8	53.4	50.0	47.5	45.1
63	84.5	80.2	75.9	71.6	67.3	63.0	59.9	56.8
80	107.2	101.8	96.3	90.9	85.4	80.0	76.0	72.1
100	134.1	127.2	120.4	113.6	106.8	100.0	95.1	90.1

DDA200 + S200, DS200 with B, C and D characteristics

Max. operating current depending on the ambient temperature of a circuit-breaker in load circuit.

B and C	Ambient temperature T (°C)									
I_n (A)	-25	-20	-10	0	10	20	30	40	50	55
0.5	0.64	0.62	0.60	0.58	0.55	0.53	0.50	0.47	0.44	0.43
1	1.27	1.25	1.20	1.15	1.11	1.05	1.00	0.94	0.88	0.85
1.6	2.04	2.00	1.92	1.85	1.77	1.69	1.60	1.51	1.41	1.36
2	2.54	2.49	2.40	2.31	2.21	2.11	2.00	1.89	1.76	1.70
3	3.80	3.70	3.60	3.50	3.30	3.20	3.00	2.80	2.60	2.50
4	5.10	5.00	4.80	4.60	4.40	4.20	4.00	3.80	3.50	3.40
6	7.60	7.50	7.20	6.90	6.60	6.30	6.00	5.70	5.30	5.10
8	10.15	10.00	9.60	9.20	8.80	8.40	8.00	7.50	7.10	6.80
10	12.70	12.50	12.00	11.50	11.10	10.50	10.00	9.40	8.80	8.50
13	16.50	16.20	15.60	15.00	14.40	13.70	13.00	12.30	11.50	11.10
16	20.40	20.00	19.20	18.50	17.70	16.90	16.00	15.10	14.10	13.60
20	25.40	24.90	24.00	23.10	22.10	21.10	20.00	18.90	17.60	17.00
25	31.80	31.20	30.00	28.90	27.60	26.40	25.00	23.60	22.00	21.20
32	40.60	39.90	38.50	37.00	35.40	33.70	32.00	30.20	28.20	27.20
40	50.80	49.90	48.10	46.20	44.20	42.20	40.00	37.70	35.30	34.00
50	63.50	62.40	60.10	57.70	55.30	52.70	50.00	47.10	44.10	42.50
63	80.00	78.60	75.70	72.70	69.60	66.40	63.00	59.40	55.60	53.50

MCBs technical details

Performances at different ambient temperatures,
altitudes and frequencies

DDA200 + S200, DS200 (K and Z characteristics)

Max. operating current depending on the ambient temperature of a circuit-breaker in load circuit.

K and Z	Ambient temperature T (°C)									
I _n (A)	-25	-20	-10	0	10	20	30	40	50	55
0,5	0.63	0.61	0.59	0.56	0.53	0.50	0.47	0.43	0.40	0.38
1	1.25	1.22	1.17	1.12	1.06	1.00	0.94	0.87	0.79	0.75
1,6	2.00	1.96	1.88	1.79	1.70	1.60	1.50	1.39	1.26	1.20
2	2.50	2.45	2.35	2.24	2.12	2.00	1.87	1.73	1.58	1.50
3	3.75	3.70	3.50	3.40	3.20	3.00	2.80	2.60	2.40	2.30
4	5.00	4.90	4.70	4.50	4.20	4.00	3.70	3.50	3.20	3.00
6	7.5	7.30	7.00	6.70	6.40	6.00	5.60	5.20	4.70	4.5
8	10.0	9.80	9.40	8.90	8.50	8.00	7.50	6.90	6.30	6.0
10	12.5	12.20	11.70	11.20	10.60	10.00	9.40	8.70	7.90	7.5
13	16.3	15.90	15.20	14.50	13.80	13.00	12.20	11.30	10.30	9.8
16	20.0	19.60	18.80	17.90	17.00	16.00	15.00	13.90	12.60	12.0
20	25.0	24.50	23.50	22.40	21.20	20.00	18.70	17.30	15.80	15.0
25	31.3	30.60	29.30	28.00	26.50	25.00	23.40	21.70	19.80	18.8
32	40.0	39.20	37.50	35.80	33.90	32.00	29.90	27.70	25.30	24.0
40	50.0	49.00	46.90	44.70	42.40	40.00	37.40	34.60	31.60	30.0
50	62.5	61.20	58.60	55.90	53.00	50.00	46.80	43.30	39.50	37.5
63	78.8	77.20	73.90	70.40	66.80	63.00	58.90	54.60	49.80	47.2

MCBs technical details

Performances at different ambient temperatures, altitudes and frequencies

Derating of load capacity of S800

The table refers to the product standard IEC 60947-2. These values are only valid if the mounting conditions are similar to the IEC 60947-2.

The rated value of the current of the S800 refers to a calibration temperature of 30°C for characteristics B, C and D.

For characteristics K and UCK it refers to 40°C and the UL-version (S800U) refers to calibration temperature od 25°C.

Max. operating current depending on the ambient temperature of S800 with characteristics B, C, D, UCB.

I _n [A]	B, C, D, UCB Ambient temperature T (°C)																				
	-25	-20	-15	-10	-5	0	5	10	15	20	25	30	35	40	45	50	55	60	65	70	75
	0.5	1	1.6	2	2.5	3	4	5	6	8	10	12	13	16	20	25	30	35	40	45	50
0.5	0.6	0.6	0.6	0.6	0.6	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.4	0.4	0.4	
1	1.2	1.2	1.2	1.1	1.1	1.1	1.1	1.1	1.0	1.0	1.0	1.0	1.0	1.0	0.9	0.9	0.9	0.9	0.9	0.9	
1.6	1.9	1.9	1.8	1.8	1.8	1.8	1.7	1.7	1.7	1.7	1.6	1.6	1.6	1.5	1.5	1.5	1.4	1.4	1.4	1.3	
2	2.4	2.3	2.3	2.3	2.2	2.2	2.2	2.1	2.1	2.1	2.0	2.0	2.0	1.9	1.9	1.8	1.8	1.7	1.7	1.7	
2.5	3.0	2.9	2.9	2.8	2.8	2.7	2.7	2.7	2.6	2.6	2.5	2.5	2.5	2.4	2.4	2.3	2.3	2.2	2.2	2.1	
3	3.6	3.5	3.5	3.4	3.4	3.3	3.2	3.2	3.1	3.1	3.0	3	2.9	2.9	2.8	2.8	2.7	2.7	2.6	2.6	
4	4.8	4.7	4.6	4.5	4.5	4.4	4.3	4.3	4.2	4.1	4.1	4	3.9	3.8	3.8	3.7	3.6	3.5	3.4	3.3	
5	6.0	5.9	5.8	5.7	5.6	5.5	5.4	5.3	5.2	5.2	5.1	5.0	4.9	4.8	4.7	4.6	4.5	4.4	4.3	4.2	
6	7.2	7.1	7.0	6.9	6.8	6.7	6.6	6.4	6.3	6.2	6.1	6.0	5.9	5.8	5.7	5.6	5.4	5.3	5.2	5.1	
8	9.6	9.5	9.3	9.2	9.0	8.9	8.7	8.6	8.4	8.3	8.1	8.0	7.9	7.7	7.6	7.4	7.3	7.1	7.0	6.8	
10	12.0	11.8	11.7	11.5	11.3	11.1	10.9	10.7	10.6	10.4	10.2	10.0	9.8	9.6	9.4	9.3	9.1	8.9	8.7	8.5	
13	15.6	15.4	15.1	14.9	14.7	14.4	14.2	14.0	13.7	13.5	13.2	13.0	12.8	12.5	12.3	12.0	11.8	11.6	11.3	11.1	
16	19.2	18.9	18.6	18.3	18.1	17.8	17.5	17.2	16.9	16.6	16.3	16.0	15.7	15.4	15.1	14.8	14.5	14.2	13.9	13.7	
20	24.0	23.7	23.3	22.9	22.6	22.2	21.8	21.5	21.1	20.7	20.4	20.0	19.6	19.3	18.9	18.5	18.2	17.8	17.4	17.1	
25	30.0	29.6	29.1	28.7	28.2	27.8	27.3	26.8	26.4	25.9	25.5	25.0	24.5	24.1	23.6	23.2	22.7	22.2	21.8	21.3	
32	38.5	37.9	37.3	36.7	36.1	35.5	34.9	34.3	33.8	33.2	32.6	32.0	31.4	30.8	30.2	29.7	29.1	28.5	27.9	27.3	
40	48.1	47.3	46.6	45.9	45.1	44.4	43.7	42.9	42.2	41.5	40.7	40.0	39.3	38.5	37.8	37.1	36.3	35.6	34.9	34.1	
50	60.1	59.2	58.3	57.3	56.4	55.5	54.6	53.7	52.8	51.8	50.9	50.0	49.1	48.2	47.2	46.3	45.4	44.5	43.6	42.7	
63	75.7	74.6	73.4	72.2	71.1	69.9	68.8	67.6	66.5	65.3	64.2	63.0	61.8	60.7	59.5	58.4	57.2	56.1	54.9	53.8	
80	96.1	94.7	93.2	91.7	90.3	88.8	87.3	85.9	84.4	82.9	81.5	80.0	78.5	77.1	75.6	74.1	72.7	71.2	69.7	68.3	
100	120.2	118.4	116.5	114.7	112.8	111.0	109.2	107.3	105.5	129.6	101.8	100.0	98.2	96.3	94.5	92.7	90.8	89.0	87.2	85.3	
125	150.2	147.9	145.6	143.4	141.1	138.8	136.5	134.2	131.9	129.6	127.3	125.0	122.7	120.4	118.1	115.8	113.5	111.2	108.9	106.7	

Max. operating current depending on the ambient temperature of S800 with characteristic K, UCK, PV-SP (from 5 A)

I _n [A]	K, UCK, PV-SP Ambient temperature (°C)																				
	-25	-20	-15	-10	-5	0	5	10	15	20	25	30	35	40	45	50	55	60	65	70	75
	0.5	1	1.6	2	2.5	3	4	5	6	8	10	12	13	16	20	25	30	35	40	45	50
0.5	0.6	1.2	2.0	2.4	3.1	3.7	4.9	5.7	6.7	7.21	7.10	6.99	6.88	6.77	6.66	6.55	6.44	6.33	6.22	6.11	6.00
1	1.2	1.2	1.2	1.2	1.1	1.1	1.1	1.1	1.1	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	0.9	0.9	0.9
1.6	2.0	1.9	1.9	1.9	1.8	1.8	1.8	1.8	1.7	1.7	1.7	1.7	1.6	1.6	1.5	1.5	1.5	1.4	1.4	1.4	1.4
2	2.5	2.4	2.4	2.3	2.3	2.3	2.2	2.2	2.2	2.1	2.1	2.1	2.0	2	2.0	1.9	1.9	1.8	1.8	1.8	1.7
2.5	3.1	3.0	2.9	2.9	2.8	2.8	2.7	2.7	2.7	2.6	2.6	2.5	2.5	2.4	2.4	2.3	2.3	2.2	2.2	2.2	2.2
3	3.7	3.6	3.5	3.5	3.4	3.4	3.3	3.2	3.2	3.1	3.1	3.0	3	2.9	2.9	2.8	2.8	2.7	2.7	2.6	2.6
4	4.9	4.8	4.8	4.7	4.6	4.5	4.5	4.4	4.3	4.3	4.2	4.1	4.1	4	3.9	3.8	3.8	3.7	3.6	3.5	3.5
5	6.1	6.0	5.9	5.8	5.7	5.6	5.5	5.4	5.3	5.2	5.1	5.0	4.9	4.8	4.7	4.6	4.5	4.4	4.3	4.3	4.3
6	7.43	7.32	7.21	7.10	6.99	6.88	6.77	6.66	6.55	6.44	6.33	6.22	6.11	6.00	5.89	5.78	5.67	5.56	5.45	5.34	5.23
8	9.91	9.76	9.61	9.47	9.32	9.17	9.03	8.88	8.73	8.59	8.44	8.29	8.15	8.00	7.85	7.71	7.56	7.41	7.27	7.12	6.97
10	12.4	12.2	12.0	11.8	11.7	11.5	11.3	11.1	10.9	10.7	10.6	10.4	10.2	10.0	9.8	9.6	9.4	9.3	9.1	8.9	8.7
13	16.1	15.9	15.6	15.4	15.1	14.9	14.7	14.4	14.2	14.0	13.7	13.5	13.2	13.0	12.8	12.5	12.3	12.0	11.8	11.6	11.3
16	19.8	19.5	19.2	18.9	18.6	18.3	18.1	17.8	17.5	17.2	16.9	16.6	16.3	16.0	15.7	15.4	15.1	14.8	14.5	14.2	13.9
20	24.8	24.4	24.0	23.7	23.3	22.9	22.6	22.2	21.8	21.5	21.1	20.7	20.4	20.0	19.6	19.3	18.9	18.5	18.2	17.8	17.4
25	31.0	30.5	30.0	29.6	29.1	28.7	28.2	27.8	27.3	26.8	26.4	25.9	25.5	25.0	24.5	24.1	23.6	23.2	22.7	22.2	21.8
32	39.6	39.0	38.5	37.9	37.3	36.7	36.1	35.5	34.9	34.3	33.8	33.2	32.6	32.0	31.4	30.8	30.2	29.7	29.1	28.5	27.9
40	49.5	48.8	48.1	47.3	46.6	45.9	45.1	44.4	43.7	42.9	42.2	41.5	40.7	40.0	39.3	38.5	37.8	37.1	36.3	35.6	34.9
50	61.9	61.0	60.1	59.2	58.3	57.3	56.4	55.5	54.6	53.7	52.8	51.8	50.9	50.0	49.1	48.2	47.2	46.3	45.4	44.5	43.6
63	78.0	76.9	75.7	74.6	73.4	72.2	71.1	69.9	68.8	67.6	66.5	65.3	64.2	63.0	61.8	60.7	59.5	58.4	57.2	56.1	54.9
80	99.1	97.6	96.1	94.7	93.2	91.7	90.3	88.8	87.3	85.9	84.4	82.9	81.5	80.0	78.5	77.1	75.6	74.1	72.7	71.2	69.7
100	123.9	122.0	120.2	118.4	116.5	114.7	112.8	111.0	109.2	107.3	105.5	103.7	101.8	100.0	98.2	96.3	94.5	92.7	90.8	89.0	87.2
125	154.8	152.5	150.2	147.9	145.6	143.4	141.1	138.8	136.5	134.2	131.9	129.6	127.3	125.0	122.7	120.4	118.1	115.8	113.5	111.2	108.9

MCBs technical details

Performances at different ambient temperatures, altitudes and frequencies

Max. operating current depending on the ambient temperature of S800U - S800UP

I _e (A)	-25	-20	-15	-10	-5	0	5	10	15	20	25	30	35	40	45	50	55	60	65	70	75
U-K, Z, UCZ	Ambient temperature T (°C)																				
10	11.8	11.7	11.5	11.3	11.1	10.9	10.7	10.6	10.4	10.2	10	9.8	9.6	9.4	9.2	9.0	8.9	8.7	8.5	8.3	8.2
15	17.9	17.6	17.3	17.0	16.7	16.4	16.1	15.8	15.5	15.3	15	14.7	14.4	14.1	13.8	13.6	13.3	13.0	12.8	12.5	12.3
20	23.7	23.3	22.9	22.6	22.2	21.8	21.5	21.1	20.7	20.4	20	19.6	19.2	18.8	18.4	18.1	17.7	17.4	17.0	16.7	16.3
25	29.6	29.1	28.7	28.2	27.8	27.3	26.8	26.4	25.9	25.5	25	24.5	24.0	23.5	23.1	22.6	22.1	21.7	21.3	20.8	20.4
30	35.9	35.2	34.6	34.0	33.4	32.8	32.2	31.6	31.1	30.5	30	29.4	28.8	28.2	27.7	27.1	26.6	26.0	25.5	25.0	24.5
40	47.3	46.6	45.9	45.1	44.5	43.7	42.9	42.2	41.5	40.7	40	39.2	38.4	37.6	36.9	36.2	35.4	34.7	34.0	33.3	32.7
50	59.2	58.3	57.3	56.4	55.5	54.6	53.7	52.8	51.8	50.9	50	49.0	48.0	47.1	46.1	45.2	44.3	43.4	42.5	41.7	40.9
60	71.7	70.5	69.2	68.0	66.8	65.6	64.4	63.3	62.2	61.1	60	58.8	57.6	56.5	55.3	54.2	53.2	52.1	51.0	50.0	49.0
70	83.7	82.2	80.7	79.3	77.9	76.5	75.2	73.8	72.5	71.3	70	68.6	67.2	65.9	64.6	63.3	62.0	60.8	59.6	58.4	57.2
80	94.7	93.2	91.7	90.3	88.8	87.3	85.9	84.4	82.9	81.5	80	78.4	76.8	75.3	73.8	72.3	70.9	69.5	68.1	66.7	65.4
90	107.6	105.7	103.8	102.0	100.2	98.4	96.7	94.9	93.3	91.6	90	88.2	86.4	84.7	83.0	81.4	79.7	78.1	76.6	75.0	73.5
100	118.4	116.5	114.7	112.8	111.0	109.2	107.3	105.5	103.7	101.8	100	98.0	96.0	94.1	92.2	90.4	88.6	86.8	85.1	83.4	81.7

Max. operating current depending on the ambient temperature of S804U - PVSP5, - PVS5


I _e (A)	-25	-20	-15	-10	-5	0	5	10	15	20	25	30	35	40	45	50	55	60	65	70
PVSP5, - PVS5	Ambient temperature T (°C)																			
5	6.5	6.4	6.3	6.2	6.1	6.0	5.9	5.8	5.7	5.6	5.5	5.4	5.3	5.2	5.1	5.0	4.9	4.8	4.7	4.6

Influence of mounting distances between the devices

Multiply the rated current referring to your max. occurrent temperature with the factor of "influence of mounting distances".

Example: 2 x S802B-B125 at T = 40 °C with distance

$$I_n = 120.4 \text{ A} \times 92.1\% = 110.9 \text{ A}$$



Further influencing factors, which can lead to a reduction of the maximum operating current, are:

- Shortening the cable lenght compared to IEC 60947-1/2
- Reducing the cable cross section compared to IEC 60947-1/2
- Accumulation of cables

MCBs technical details

Performances at different ambient temperatures, altitudes and frequencies

2. Multiply the rated current (equivalent) referring to the new temperature by another factor only in case of presence of several devices installed alongside each other; see table.

Example: S 202 C 16 with T=40 °C

Type of use	Values to use	Formula	Calculation	Result
Load at ambient temperature	I_n (amb. t°) -see tables-			$I_n = 15.5 \text{ A}$
Load at ambient temperature with 8 adj. devices	I_n (amb. t°) -see tables- Fm (0.77)	I_n (amb. t°)x0.77	15.5x0.77	$I_n = 11.94 \text{ A}$

S200, DS200, DDA200+S200 Influence of adjacent devices Correction factor Fm

No. of adjacent devices	Fm
1	1
2	0.95
3	0.9
4	0.86
5	0.82
6	0.795
7	0.78
8	0.77
9	0.76
>9	0.76

SN201 Influence of adjacent devices Correction factor Fm

No. of adjacent devices	Fm
1	1.00
2	0.99
3	0.97
4	0.96
5	0.94
6	0.93
7	0.92
8	0.91
9	0.90
> 9	0.90

SU200 M Influence of adjacent devices Correction factor Fm

No. of adjacent devices	Fm
1	1.00
2, 3	0.9
4, 5	0.8
> 6	0.75

DS201 and DS202C Influence of adjacent devices Correction factor Fm

No. of adjacent devices	Fm
1	1.00
2	0.95
3	0.91
4	0.88
5	0.87
6	0.86
7	0.85
> 7	0.85

S200 80-100A Influence of adjacent devices Correction factor Fm

No. of adjacent devices	Fm
1	1.00
2, 3	0.9
4, 5	0.8
> 6	0.75

MCBs technical details

Use of MCBs in direct current circuits


Use of S 200/S 200 M/S 200 P miniature circuit-breakers in direct current circuits 72 VDC/125 VDC

In DC systems up to 72 VDC or, as the case may be, series connection up to 125 VDC, customary S 200/S 200 M series MCBs can be used. Polarity does not need to be taken into


consideration, the outgoing circuit may be implemented from above or below the device.

For higher direct voltage up to 440 VDC devices of the S 280 UC series must be used.

Example for max. permissible voltages between conductors depending on the number of poles and type of connection.



Examples for different voltages between a conductor and earth where voltages between conductors are identical:



MCBs technical details

S 200 UDC series DC Applications

DC = Direct Current

S 200 UDC MCBS can be used in the one-pole version as 60 V DC (125 V DC up to 40 A), and in the 2-pole version with series connection of two poles up to 125 V DC (250 V DC up to 40 A).

S 200 UDC contains fitted permanent magnets, which assists in the forced extinguishing of the arc.

If voltages to earth exceeding 60 V DC may occur, 2-pole S 200 UDC is to be used for one-pole disconnection.


For DC incoming supply from above S 200 UDC... MCBS have, in the area of arc chutes, permanent magnets, it is therefore necessary to take into account the polarity during the installation process.

Doing so ensures that in the case of a short circuit the magnetic field of the permanent magnets corresponds with the electromagnetic field of the short-circuit current, therefore safely leading the short circuit into the arc chute. Incorrect polarities may cause damage to the MCB. This is why – in the case of top-fed devices – terminal 1 must be connected to (-) and terminal 3 (+).


Example for permissible voltages between the conductors depending on the number of poles and circuit layout:

voltage between conductors	U_n 60 V DC (125 V DC up to 40 A)	125 V DC (250 V DC up to 40 A)	125 V DC (250 V DC up to 40 A)	125 V DC (250 V DC up to 40 A)
voltage between conductor and earth	U_n 60 V DC (125 V DC up to 40 A)	60 V DC (125 V DC up to 40 A)	125 V DC (250 V DC up to 40 A)	60 V DC (125 V DC up to 40 A)
MCB	1-pole S 201 UDC	2-pole S 202 UDC	2-pole S 202 UDC	2-pole S 202 UDC

supply from below



supply from above





MCBs technical details

S 200 UDC series DC Applications

Examples for different voltage levels between conductor and earth in the case of identical voltage between conductors:

voltage between conductors	U_n	125 V– all-pole disconnection	125 V– 1-pole disconnection
voltage between conductor and earth	U_n	60 V– circuit symmetrically earthed	125 V– circuit unsymmetrically earthed
MCB		2-pole S 202 UDC	2-pole S 202 UDC



- ① in the circuit diagram, the negative pole is earthed.
- ② in the circuit diagram, the positive pole is earthed.

MCBs technical details

S 200 MUC series AC/DC Applications

UC = Universal Current = AC/DC

S 200 MUC MCBS can be used in the one-pole version as 220 V DC, and in the 2-pole or 4-pole version with series connection of two poles up to 440 V DC.

S 200 MUC contains fitted permanent magnets, which assists in the forced extinguishing of the arc.











If voltages to earth exceeding 220 V DC may occur, 2-pole S 200 MUC is to be used for one-pole disconnection, and four-pole S 200 MUC for all-pole disconnection.

For DC incoming supply from above S 200 MUC... MCBS have, in the area of arc chutes, permanent magnets,




it is therefore necessary to take into account the polarity during the installation process.

Doing so ensures that in the case of a short circuit the magnetic field of the permanent magnets corresponds with the electromagnetic field of the short-circuit current, therefore safely leading the short circuit into the arc chute. Incorrect polarities may cause damage to the MCB. This is why – in the case of top-fed devices – terminal 1 must be connected to (-) and terminal to 3 (+).

Example for permissible voltages between the conductors depending on the number of poles and circuit layout:

voltage between conductors	U _n	220 V-	440 V-	440 V-	440 V-	440 V- (voltage reversal)
voltage between conductor and earth	U _n	220 V-	220 V-	440 V-	220 V-	220 V-
MCB		1-pole	2-pole	2-pole	2-pole	4-pole
supply from below						
						
supply from above						
						

Examples for different voltage levels between conductor and earth in the case of identical voltage between conductors:

voltage between conductors	U _n	440 V– all-pole disconnection	440 V– 1-pole disconnection	440 V– all pole disconnection
voltage between conductor and earth	U _n	220 V– circuit symmetrically earthed	440 V– circuit unsymmetrically earthed	440 V– circuit unearthing or unsymmetrically earthed
MCB		2-pole	2-pole	4-pole
				

① in the circuit diagram, the negative pole is earthed. ② in the circuit diagram, the positive pole is earthed.

MCBs technical details

S800 series DC applications




S800S-UC: The first choice as DC high performance MCB

The S800S-UC DC high performance MCB is in a wide range of DC applications at home. Due to their high rated operational voltage of up to 1000 VDC the max. rated current of 125 A and the high breaking capacity of up to 50 kA, make these devices suitable for applications, e.g.:

- DC track
- Galvanic applications
- Photovoltaics

S800S, N, and C: Up to 125 VDC on each pole

The AC range is also an interesting choice for DC applications up to 125 VDC per pole.



S800S-UC

Graphic	Short-circuit between output terminals	Contact to ground between output terminals and - earth
A	250VDC	250VDC
B	500VDC	250VDC
C	500VDC	500VDC
D	250VDC	250VDC
E	750VDC	750VDC
F	500VDC	250VDC (double failure)
G	750 V DC / 1000 V DC	500VDC (double failure)

S800S, S800N, S800C

Graphic	Short-circuit between output terminals	Contact to ground between output terminals and - earth
A	125VDC	125VDC
B	250VDC	125VDC
C	250VDC	250VDC
D	125VDC	125VDC
E	375VDC	375VDC
F	250VDC	125VDC (double failure)
G	500VDC	125VDC (double failure)

MCBs technical details

S800 series DC applications



String protection with S800PV-SP

A large proportion of the costs for photovoltaic systems is tied up in the equipment for the DC generation. The S800PV-SP protects these investments in the event of a fault.

Convincing:	Suitable for up to 1500 VDC
Loadable:	String protection up to 125 A
	Reliable protection at high ambient temperatures
Tested:	Rated ultimate short-circuit breaking capacity I_{cu} of 5 kA in accordance with IEC 60947-2 and Annex P
Fast:	Reclosable for minimum standstill times
Safe:	Disconnector properties, switching under load
Flexible:	Extensive range of accessories for remote shutdown and fault signalling



System isolation with S800PV-SD

The use of a DC isolator can be implemented reliably and in the minimum of space. Either you can choose the pole-independent S800PV-SD. The S800PV-SD is available as 2-, 3- and 4-pole version up to 1500 V DC.

Convincing:	Suitable for up to 1500 VDC
Loadable:	System isolation up to 125 A
	No change in operating behaviour up to 60°C ambient temperature
	Reliable switching of ohmic loads including moderate overloads
Compact:	Minimum dimensions with maximum efficiency
Tested:	Short-time withstand current I_{cw} of 1.5 kA in accordance with IEC 60947-3
Safe:	Disconnector properties, switching under load




Maximum device voltages

Article	2-pole	3-pole	4-pole
S800PV-SP			
I_e 5 ... 125 A	800 VDC	1200 VDC	1500 VDC
S800PV-SD			
I_e 32, 63, 125 A	800 VDC	1200 VDC	1500 VDC


ABB recommends to fulfill national and/or international standards as e. g. IEC 61439-1 Low-voltage switchgear and controlgear assemblies

Exemplary circuit diagrams

Earthed network



Non-earthed network








MCBs technical details

S800 series DC applications



GFDI = Ground Fault Detector Interrupter

The S804U-PVS5 is for GFDI application (Ground-Fault Detector Interrupter) in photovoltaic systems, with rated current 5A and short-circuit current rating of 3kA. The breaker is tested acc. to UL489B for 1000 VDC.



Wire size
14AWG — 2 AWG C_u,
solid or stranded

Conductor Type
Single conductor per terminal – copper only, 75C
wire

Line / load an +/- polarities may be reversed

Circuit 1, 2, 3, 4, 5 : ungrounded supplies
Circuit 3 : grounded supplies

MCBs technical details

Use of MCBs in altitude and different network frequency

Performance in altitude of MCBs

Up to the height of 2000 m, MCBs do not undergo any alterations in their rated performances. Over this height the properties of the atmosphere change in terms of composition, dielectric capacity, cooling capacity and

pressure, therefore the performances of the MCBs undergo derating, which can basically be measured in terms of variations in significant parameters, such as the maximum operating voltage and the rated current.

Miniature circuit breaker

Altitude	[m]	2000	3000	4000	5000
Rated voltage U_n		U_n	$0.887 \times U_n$	$0.775 \times U_n$	$0.676 \times U_n$
Rated current I_n		I_n	$0.96 \times I_n$	$0.93 \times I_n$	$0.90 \times I_n$

The derating of the rated voltage is valid for AC and DC voltages.

Variation of tripping thresholds of MCBs according to network frequency

The circuit-breakers are calibrated for a current with a frequency range between 50 and 60 Hz.

	AC			DC
	100 Hz	200 Hz	400 Hz	
Multiplier	1.1	1.2	1.5	1.5

The thermal tripping performance is independent from the network frequency.

Example:

S 202 C10 supplied at 50-60 Hz, the electro-magnetic tripping current is: $50 A \leq I_m \leq 100 A$;


S 202 C10 supplied at 400 Hz, the electro-magnetic tripping current is: $75 A \leq I_m \leq 150 A$.

MCBs technical details

Instruction for use of S 200 S

Connection and disconnection of different types of cables on the load side


Type of cables and cross sections





TEST

IEC/EN60898-1
Annex J
(Table J.3)

Disconnection of cables



Connection of cables



- Connection of one cable per opening.
- Rigid and flexible cables with end sleeves may be directly connected.
- If flexible cables without end sleeves are to be connected, the terminal must be opened. Splicing of the wires must be avoided.
- The cable must be inserted into the terminal either as far as possible or in such a way that a sufficient connection is obvious.
- The tightness of the connection must be checked.

Processing instructions

The screwless terminal at the load side of the S 200 S is designed so that copper cables basically may be connected without further preparation. If end sleeves are used as splicing protection for flexible cables, the compression of the end sleeves must comply with the pull-out forces in accordance with standard IEC/EN 60898-1 table J.3.

Recommended tools for flexible cables with end sleeves

Crimp tool with trapezoid compression profile

The cables may only be removed after operating the terminal's opening mechanism.

- If one cable is removed, the correct position of the remaining cable must be checked.

Wire stripping length / size of end sleeves for all cables

Wire stripping length and end sleeve length 12 (+2) mm

Distribution boards with metal cover

The distance from a metallic cover to the "shoulder" of the miniature circuit breaker must be at least 6 mm on the load side due to the arrangement of the easily accessible measurement point.

MCBs technical details

Particular supply sources and loads

Lighting circuit protection

Selection of circuit-breakers for the protection of lighting circuit and calculation of their rated current

To select the correct circuit-breaker for use in the protection of lighting circuits you need to know the type of load based on which you will work out the breaker's rated current. The protection circuit utilization current can be calculated simply starting with the rated power and the lighting voltage, or it

may be supplied directly by the device manufacturer.

Considering the utilization current, it is important to select the version of the breaker with a rated current just above the value calculated, defining the cable cross-section accordingly. The tables below show the rated current values of the circuit-breakers to be used according to the type and power of the device connected.

Table 1 High pressure discharge lamps

230 V and 400 V AC three-phase with or without power factor correcting capacitors, star or delta connection

Mercury vapour fluorescent lamp	Pw [W]	<700	<1000	<2000
	I [A]	6	10	16
Mercury vapour metal halogen lamp	Pw [W]	<375	<1000	<2000
	I [A]	6	10	16
High pressure sodium discharge lamp	Pw [W]	<400		<1000
	I [A]	6		16

Table 2 Fluorescent lamps

230 VAC single-phase/three-phase with neutral (400 V), with star connection.

The tables indicate the rated current of the circuit-breakers according to the lamp power and type of power supply.

Example of calculation

- Starter dissipated power: 25% of lamp power
 - Reference temperature: 30 and 40 °C according to circuit-breaker
 - Power factor:
 - lamp without capacitors $\cos \phi=0.6$
 - lamp with capacitors $\cos \phi=0.86$

Method of calculation

- $IB = (PL * n^oL * KST * KC) / (Un * \cos \phi)$ where:
 - Un = rated voltage 230 V
 - $\cos \phi$ = power factor
 - PL = lamp power
 - n^oL = number of lamps per phase
 - KST = 1.25
 - KC = 1 for star connection and 1.732 for delta connection

Type of lamp	Tube diss. pwr. [W]	Number of lamps per phase													
Single without capacitors	18	4	9	14	29	49	78	98	122	157	196	245	309	392	490
	36	2	4	7	14	24	39	49	61	78	98	122	154	196	245
	58	1	3	4	9	15	24	30	38	48	60	76	95	121	152
Single with capacitors	18	7	14	21	42	70	112	140	175	225	281	351	443	562	703
	36	3	7	10	21	35	56	70	87	112	140	175	221	281	351
	58	2	4	6	13	21	34	43	54	69	87	109	137	174	218
Double with capacitors	2x18=36	3	7	10	21	35	56	70	87	112	140	175	221	281	351
	2x36=72	1	3	5	10	17	28	35	43	56	70	87	110	140	175
	2x58=116	1	2	3	6	10	17	21	27	34	43	54	68	87	109
I _n [A] - 2P and 4P circuit-breakers	1	2	3	6	10	16	20	25	32	40	50	63	80	100	

MCBs technical details

Particular supply sources and loads

Fluorescent lamps. 230 VAC three-phase – Delta connection

Type of lamp	Tube diss. pwr. [W]	Number of lamps per phase											
Single without capacitors	18	2	5	8	16	28	45	56	70	90	113	141	178
	36	1	2	4	8	14	22	28	35	45	56	70	89
	58	0	1	2	5	8	14	17	21	28	35	43	55
Single with capacitors	18	4	8	12	24	40	64	81	101	127	162	203	255
	36	2	4	6	12	20	32	40	50	64	81	101	127
	58	1	2	3	7	12	20	25	31	40	50	63	79
Double with capacitors	2x18=36	2	4	6	12	20	32	40	50	64	81	101	127
	2x36=72	1	2	3	6	10	16	20	25	32	40	50	63
	2x58=116	0	1	1	3	6	10	12	15	20	25	31	39
In [A] - 3P circuit-break.	1	2	3	6	10	16	20	25	32	40	50	63	80
													100

Transformer protection

Insertion current

When the LV/LV transformers are powered up, very strong currents occur, which must be considered when selecting the protective device. The peak value of the first current wave often reaches a value between 10 and 15 times the transformer's effective rated current.

For power ratings below 50 kVA, it may reach between 20 and 25 times the rated current. This transient current decreases very rapidly with a time constant T varying from several ms to 10, 20 ms.

Main protection on the primary side

The tables below are the result of a set of tests on co-ordination between circuit-breakers and BT/BT transformers. The transformers used in the tests are normalized. The table, referring to a primary supply voltage of 230 or 400 V and to single-phase and three-phase transformers, indicate which circuit-breaker should be used according to the transformer power rating. The transformers considered have the primary winding outside the secondary winding.

The circuit-breakers suggested allow:

- transformer protection in the event of maximum short-circuit;
- prevention of unwanted tripping when the primary winding is powered up using
 1. modular circuit-breakers with a high magnetic threshold, curve D or K
 2. circuit-breakers with magnetic only releaser;
 - guaranteed circuit-breaker electrical life.

Protection on the secondary side

Due to the transformer's high insertion current, the circuit-breaker on the primary winding may not guarantee thermal protection for the transformer and its feeder line on the primary side.

This is typical of modular circuit-breakers which must have a higher rated current than the transformers. In such cases, in the event of a single-phase short-circuit at the transformer's primary terminals (minimum Icc at end of line), check that the circuit-breaker's magnetic releaser is tripped. In the normal application in distribution panels, this condition is always satisfied provided that the length of the feeder lines is reduced.

The transformer can be provided with thermal protection by installing a circuit-breaker with a rated current less than or equal to that of the transformer secondary winding immediately downstream of the LV/LV transformer.

In lighting systems protection against overloads is not necessary if the number of light points is clearly defined (no overloads).

Moreover, the Standard in force for these systems recommends the omission of protection against overloads in circuits in which unwanted tripping may prove hazardous, e.g.: circuits which supply fire-fighting equipment.

MCBs technical details

Particular supply sources and loads

Single-phase transformer (primary voltage 230 V)-1P and 1P+N MCBs

P _n [kVA]	I _n [A]	u _{cc} (%)	Circuit-breaker on primary side (1) and (2)
0.1	0.4	13	S 2* D1 o K1
0.16	0.7	10.5	S 2* D2 o K2
0.25	1.1	9.5	S 2* D3 o K3
0.4	1.7	7.5	S 2* D4 o K4
0.63	2.7	7	S 2* D6 o K6
1	4.2	5.2	S 2* D10 o K10
1.6	6.8	4	S 2* D16 o K16
2	8.4	2.9	S 2* D16 o K16
2.5	10.5	3	S 2* D20 o K20
4	16.9	2.1	S 2* D40 o K40
5	21.1	4.5	S 2* D50 o K50
6.3	27	4.5	S 2* D63 o K63

Single-phase transformer (primary voltage 400 V)-2P MCBs

P _n [kVA]	I _n [A]	u _{cc} (%)	Circuit-breaker on primary side (1) and (2)
1	2.44	8	S 2* D6 o K6
1.6	3.9	8	S 2* D10 o K10
2.5	6.1	3	S 2* D16 o K16
4	9.8	2.1	S 2* D20 o K20
5	12.2	4.5	S 2* D32 o K32
6.3	15.4	4.5	S 2* D40 o K40
8	19.5	5	S 2* D50 o K50
10	24	5	S 2* D63 o K63
12.5	30	5	S 2* D63 o K63

Three-phase transformer (primary voltage 400 V)-3P, 3P+N and 4P MCBs

P _n [kVA]	I _n [A]	u _{cc} (%)	Circuit-breaker on primary side (1) and (2)
5	7	4.5	S 2* D20 o K20
6.3	8.8	4.5	S 2* D20 o K20
8	11.6	4.5	S 2* D32 o K32
10	14	5.5	S 2* D32 o K32
12.5	17.6	5.5	S 2* D40 o K40
16	23	5.5	S 2* D63 o K63
20	28	5.5	S 2* D63 o K63

S 2*.. = S 200, S 200 M, S 200 P

(1) With modular or magnetic only circuit-breakers, without thermal adjustment, thermal protection is required for the transformer's secondary winding.

(2) Breaking capacity selected according to estimated I_{cc} at the point where the breaker is installed.

MCBs technical details

Particular supply sources and loads

Double tampoprinting of S 200 P

The breaking capacity

For the modular circuit-breakers realized according to IEC/EN 60898 standard, the breaking capacity is expressed by the I_{cn} quantity, indicated in Ampere, contained within a rectangle on the front side of the device. The max value of rated short-circuit capacity (I_{cn}) considered by this standard is 25000 A.

Always according to IEC/EN 60898 standard, the ratio between the service short-circuit capacity (I_{cs}) and the rated short-circuit capacity (I_{cn}) – K factor – shall have to be conforming to the enclosed table.

I_{cn}	K
< 6000 A	1
> 6000 A	0.75(*)
< 10000 A	
>10000 A	0.5(**)

(*) I_{cs} minimum value: 6000 A (** I_{cs} minimum value: 7500 A

Limiting class

The Manufacturer of the circuit-breaker has the right to declare the energy limiting class of the device. According to IEC/EN 60898 standard, the Manufacturer classifies the circuit-breaker with a limiting class which ranges from 1 to

3 according to the I^2t values let though by the circuit-breaker for rated current up to 16 A and rated currents exceeding 16 A up to 32 A included, according to the table below.

Rated current up to 16 A:

Short-circuit rated capacity	Limited energy classes				
	1	2	3		
	I^2t max (A ² s)	I^2t max (A ² s)	I^2t max (A ² s)	B Type	C Type
(A)	B-C Type	B Type	C Type	B Type	C Type
3000	No limits	31000	37000	15000	18000
4500	are specified	60000	75000	25000	30000
6000		100000	120000	35000	42000
10000		240000	290000	70000	84000

Rated current exceeding 16 A up to 32 A included:

Short-circuit rated capacity	Limited energy classes				
	1	2	3		
	I^2t max (A ² s)	I^2t max (A ² s)	I^2t max (A ² s)	B Type	C Type
(A)	B-C Type	B Type	C Type	B Type	C Type
3000	No limits	40000	50000	18000	22000
4500	are specified	80000	100000	32000	39000
6000		130000	160000	45000	55000
10000		310000	370000	90000	110000

MCBs technical details


Particular supply sources and loads

For instance, a circuit-breaker with rated current 16 A, B characteristic, with short-circuit rated capacity equal to 6 kA belongs to class 3 if it lets through max 35000 A²s of specific energy.

The limiting class value (1, 2 or 3) is indicated on the front side of the device, within a square, in addition to the breaking capacity.

As regards the miniature circuit-breakers S200P series, two different breaking capacities are indicated on the front side of the device, contained in a rectangle.

The breaking capacity indicated above the operating toggle is the one of the device, according to IEC/EN 60898 standard, the breaking capacity indicated under the lever is regarding the limiting class which, according to the standard, can be expressed only for values up to 10000 A.



MCBs technical details

WT63

Motor starter combinations acc. to IEC/EN 60947-4-1

690 V AC, 35 kA, type 2, normal start-up

Motor		Short-circuit protection		Contactor		Overload protection		Wiring	
Rated output	Rated current	Current limiter	Manual motor starter	Tripping current	Type	Safety clearance	Type	Current setting range	WT63-MMS
[kW]	[A]			[A]		[mm]		[A]	[mm ²]
0.37	0.61	WT63-3 or WT63-3 HS	MS/MO 325-1.0	11.50	A9	15	TA 25 DU 1.0	0.63-1.0	max. 16
1.5	2.08		MS/MO 325-2.5	28.75	A12	15	TA 25 DU 2.4	1.7-2.4	max. 16
1.1	2.36		MS/MO 325-2.5	28.75	A12	15	TA 25 DU 3.1	2.3-3.1	max. 16
3	3.6		MS/MO 325-4.0	40.00	A12	15	TA 25 DU 4.0	2.8-4.0	max. 16
4	4.97		MS/MO 325-6.3	78.75	A26	15	TA 25 DU 6.5	4.5-6.5	max. 16
7.5	8.7		MS/MO 325-12.5	187.50	A26	15	TA 25 DU 11	7.5-11	max. 16

For further combinations please contact the manufacturer.

Application notes

- WT63 may only be used for motor starter combinations confirmed by the manufacturer
- Max. no. of motor groups to be protected by WT63: 5
- The wiring between WT63 and MMS has to be short-circuit proof
- WT63 has to be installed with fitted terminal covers (factory assembled)

- The max. total operating current of WT63 has to be limited to 63 A, the max. total start-up current shall not exceed 450 A

For more details see separate product brochure.

MCBs technical details

S800 range features



The S800S, -N, -C, -B and -HV high performance MCBs: safe innovation

The S800 high performance MCB limits energy and current in case of a short-circuit power cutt off. The specially designed double arcing chamber system, i.e. per pole are two arcing chambers, ensures excellent operating characteristics. The new S800B has only one arcing chamber. Additional exceptional features of the S800 series are:

Convincing:	Selectivity to upstream overcurrent protection devices due to a total switch-off time of only ≤ 2.5 ms.
Safe:	Excellent backup protection by limiting the energy to a value $\leq 100\,000\text{ A}^2\text{s}$ (125A/50kA). In case of short-circuit, there is a low load to the circuit and the location of the damage due to the high limitation of the let-through energy.
Loads:	Up to 125A rated current
Checked:	S series up to 50kA rated ultimate short-circuit breaking capacity I_{cu} N series up to 36kA rated ultimate short-circuit breaking capacity I_{cu} C series up to 25kA rated ultimate short-circuit breaking capacity I_{cu} B series up to 16kA rated ultimate short-circuit breaking capacity I_{cu} HV series up to 4kA rated ultimate short-circuit breaking capacity I_{cu}
Selectable:	Characteristics: S series: B, C, D, K, KM, UCB, UCK N series: B, C, D C series: B, C, D, K B series: B, C, D, K HV series: C, K
Compact:	Slight 27mm width per pole
Flexible:	Accessories installed by the customer.




S800UP, -U, -U-UCZ, -U-PVS: Highest safety now also ensured for UL applications

Convincing:	Covering of different voltage ranges (240VAC, 480Y/277 V AC, 600VDC, 1000VDC)
Safe:	Excellent backup protection due to limitation of energy.
Loads:	Up to 100A rated current
Checked:	K-, Z series up to 50kA breaking capacity UCZ series up to 10kA breaking capacity PVS series up to 3kA breaking capacity
Selectable:	Characteristics: K, Z, UCZ, PVS
Compact:	Smallest sizes.
Flexible:	Accessories installed by the customer.
Standards:	UL489, UL489B, IEC 60947-2

Short description

Two triggers detect overcurrents, effect the switching station and provide short-circuit protection.

1. The thermal trip for overload protection with time delay.
2. The electromagnetic fast-acting trip with concrete anchor for short-circuit protection.



(1) 1 sinus half-wave
50 Hz $\Delta T/2 = 10$ ms

$I_k \times \sqrt{2}$	peak value of the prospective short-circuit current
i_d	max. let-through current of the S800 high performance MCB
U_n	supply voltage
U_B	build up and collapse of the arc voltage
t_k	Turn-off time of S800 high performance MCB

MCBs technical details

S800 range features



Play it safe: display the operational state

The mechanical drive of the S800 high performance MCB is equipped with a trip-free release. It therefore switches independent of the actuating force or speed on the actuating lever.

The trip position display thereby always reliably displays the exact position of the moving contact. The trip position provides additional trip detection allowing you to easily find the reason for the cut-off. Because the switch lever moves to the middle position in case of thermal or magnetic tripping, the user sees at a glance that this is an error state and can then initiate suitable measures.

*Middle position of switch lever, see picture

Reliable: the disconnector properties

In OFF position (0 position), the S800 high performance MCB guarantees safe electrical isolation of the circuit compliant to IEC 60947-2.

Flexible: the installation


The S800 high performance MCB can be directly mounted onto any position on the DIN mounting rail without any impairment to its characteristics. Because the pole dimensions are identical for all rated currents, installation in switching systems is simplified.

The S800 can be installed in different ways:

- together with other breakers in the same DIN rail horizontally or vertically
- as an individual breaker in a single fixed compartment where the breaker is switched on/off with a rotary handle from the door, and the breaker is mounted on the wall of the panel
- as an individual breaker in a single withdrawable module, when requirements for high availability in the installation are a must

Cage and ring terminals

When ordering you can choose between cage terminals or ring terminal connectors. No matter which type you select, both connection options guarantee a high degree of reliability.



Doesn't let go: the replaceable terminal adapter*

The S800 standard equipment with interchangeable terminal adapter for wires, cables and rigid conductors guarantees a high level of flexibility and comfort. Fast and safe connection of the conductors is ensured by the "onboard terminal shutter" integrated into the body of the terminal, thereby preventing incorrect underclamping of the connections.

* Available for the S, N, C, U and PV series.

MCBs technical details

S800 range features



Extra safe: Fire protection acc. to NF F 16-101 and NF F 16-102 (prEN45545-2)

The S800 high performance MCB provides standard compliance to the requirements of Standard prEN45545-2 (Railway applications – Fire Protection on railway vehicles – Part 2: Requirements for fire behaviour of materials and components). This standard is based on the French standard NF F 16-101/ NF F 16-102 and makes new requirements of the fire behaviour of the materials used. The main focus of attention with relation to fire protection is on the following:

- Flame spread
- Rate of heat release
- Smoke development
- Toxicity

The S800 high performance automatic meets the following classification compliant to NF F 16-101 and NF F 16-102:

- I3F2
- I3 no permanent flame at 850°C
- F2 index of fume density and toxicity ≤40

More information regarding the use of S800 breakers in rolling stock applications is available in the Technical catalogue 'DIN-Rail components for rolling stock applications 2CDC002053D0204'

MCBs technical details

S800-SCL range features

Group protection

The main application of the S800S-SCL-SR is group protection. In comparison to other short-circuit limiter you need only one S800S-SCL-SR for several motor starters or high performance miniature circuit breakers. With the requirement that the rated current of the short-circuit limiter does not exceed the total sum of the rated S800S currents of all downstream motor starters or circuit breakers. Furthermore the sum of all load currents including inrush currents shall not exceed the maximum permissible load of the S800S-SCL-SR. Several downstream motor protection combinations or several high performance miniature circuit breakers can be protected with only one S800S-SCL-SR.

Single-line protection


For single-line protection it is recommended to use the standard short-circuit limiter S803S-SCL. It has a toggle and will trip in case of a failure.

Current continuity

In case of a failure by using the S800-SCL-SR as group protection only the defective device will trip; all other devices will keep doing their work. Therefore you will have a very low breakdown, because only one motor will stop and not all of them.

Maximum system availability is given.

Schematic examples for rated currents up to 100 A



MCBs technical details

S800-SCL range features

S803S-SCL

Short-circuit current limiter

The S803S used together with an S803S-SCL ensures reliable switch-off of short-circuit currents up to 100 kA, at an operating voltage of 440 VAC and over the entire rated current range of up to 125 A.

For applications at 690 VAC, the combination of S803S-SCL ensures reliable short-circuit protection up to 50 kA; here also, this is ensured over the entire rated current range up to 125 A, typical for the S800.

Example combinations	Rated operational voltage Ue	Ultimate short-circuit breaking capacity Icu	Service short-circuit breaking capacity Ics
S803S-SCL125 +	440 VAC	100 kA	100 kA
S803S-C125	690 VAC	50 kA	50 kA
S803S-SCL63 +	440 VAC	100 kA	100 kA
S803S-K63	690 VAC	50 kA	50 kA
S803S-SCL32 +	440 VAC	100 kA	100 kA
S803S-B16	690 VAC	50 kA	50 kA

S800-SCL-SR

Self-resetting short-circuit limiter

The S800-SCL-SR can be used together with S800S High Performance MCB or Manual Motor Starters. It limits the short-circuit current until the downstream means of protection trips. Its current continuity makes it as the ideal solution for group protection. All parallel branches remain operative.


Minimum cable length between S800-SCL-SR/S803S-SCL and downstream devices (Connection has to be shortcircuit proofed acc. to IEC 61439-1)

MS/M0325

MS/M0132

S800

S800-SCL-SR/ S803S-SCL	min. length X	min. cross section
32 A	80 mm	6 mm ²
63 A	80 mm	16 mm ²
100/125 A	250 mm	35 mm ²



MCBs technical details

S800-SCL range features

Approved combinations with high performance MCB S800

Downstream devices	Upstream devices			S803S-SCL Short-circuit limiter		
	S800S-SCL-SR/S803W-SCL-SR Self resetting short-circuit limiter			32	63	125
Rated current Ie [A]	32	63	100	32	63	125
S800S Characteristic B						
6	■					
8	■					
10	■	■	■	■		
13	■	■	■	■		
16	■	■	■	■		
20	■	■	■	■		
25	■	■	■	■		
32	■	■	■	■	■	
40		■	■		■	
50		■	■		■	
63		■	■		■	■
80		■				■
100		■				■
125						■
S800S Characteristic C						
6	■					
8	■					
10	■	■	■	■		
13	■	■	■	■		
16	■	■	■	■		
20	■	■	■	■		
25	■	■	■	■		
32		■	■	■	■	
40		■	■		■	
50		■	■		■	
63		■			■	■
80		■				■
100						■
125						■
S800S Characteristic D/K						
6	■					
8	■					
10	■	■	■	■		
13	■	■	■	■		
16	■	■	■	■		
20		■	■	■		
25		■	■	■		
32		■	■	■	■	
40		■	■		■	
50		■			■	
63					■	■
80						■
100						■
125						■

MCBs technical details

S800-SCL range features

Approved combinations with motor starter/S800S-KM

Downstream devices	Upstream devices					
	S800S-SCL-SR/S803W-SCL-SR Self resetting short-circuit limiter			S803S-SCL Short-circuit limiter		
Rated current I_e [A]	32	63	100	32	63	125
MS/MO325						
0.1–2.5	■	■	■			
4	■	■	■			
6.3	■	■	■			
9	■	■	■	■	■	■
12.5	■	■	■	■	■	■
16	■	■	■	■	■	■
20		■	■	■	■	■
25	■	■	■	■	■	■
MS/MO132						
0.1–2.5	■	■				
4	■	■				
6.3	■	■	■			
10	■	■	■	■	■	■
16	■	■	■	■	■	■
20		■	■	■	■	■
25	■	■	■	■	■	■
32	■	■	■	■	■	■
S800S-KM						
20		■	■	■		
25		■	■	■		
32		■	■	■	■	
40		■	■			
50			■			
63			■		■	■
80					■	

Approved combinations with S803HV-K

Downstream devices	Upstream devices S803HV-SCL-SR Self resetting short-circuit limiter		
Rated operational current I_e [A]	32	63	100
6	■		
8	■		
10	■	■	■
13	■	■	■
16		■	■
20		■	■
25		■	■
32		■	■
40		■	■
50			■
63			■
80			
100			
125			

* Motor starter combinations acc. to IEC 60947-4-1

MCBs technical details

S800-SCL range features

■ Applies for all voltages according to the table below

	S800S-SCL-SR	S803W-SCL-SR	S803S-SCL	S803HV-SCL-SR
Rated ultimate short-circuit breaking capacity				
$I_{cu} = I_{cs}$ according to IEC 60947-2				
(AC) 50/60 Hz 240/415V	kA	100	100	
(AC) 50/60 Hz 254/440V	kA	100	100	100
(AC) 50/60 Hz 277/480V	kA	65	65	
(AC) 50/60 Hz 289/500V	kA	65	65	
(AC) 50/60 Hz 346/600V	kA	65	65	
(AC) 50/60 Hz 400/690V	kA	50	50	50
(AC) 50/60 Hz 580/1000V	kA			$I_{cu} = 15 \text{ kA}$ $I_{cs} = 10 \text{ kA}$
Short-circuit rating according to UL 508, CSA 22.2				
(AC) 50/60 Hz 480V	kA	65		
(AC) 50/60 Hz 600V	kA	65		

MCBs technical details

S800-SCL range features

Internal resistance at 25 °C ambient temperature and nominal power losses

Rated operational current I_e [A]	Internal resistance R_i [mΩ]	Power losses P_{Vn} [W]
32	2.8	3.6
63	1.3	5.7
100	0.7	7.8


Influence of ambient temperature – single mounted devices

Rated operational current I_e [A]	10 °C	15 °C	20 °C	25 °C	30 °C	35 °C	40 °C	45 °C	50 °C	55 °C	60 °C	65 °C	70 °C
32	38.2	37.2	35.8	35.2	34.2	33.3	32	30.7	29.8	28.8	27.8	26.5	25.1
63	75.3	73.2	70.6	69.3	67.4	65.5	63	60.5	58.6	56.7	54.8	52.3	49.8
100	119.5	116.2	112	110	107	104	100	96	93	90	87	84	80

Installation requirements

The total sum of the rated currents of all downstream motor starters or circuit breakers shall not exceed the rated current of the S800-SCL-SR (valid also for HV version). Furthermore the sum of all load currents including inrush currents shall not exceed the maximum permissible load of the S800-SCL-SR (valid also for HV version).

Maximum load



Example:

If you have 8 manual motor starters with each 5A as rated operational current

$$\text{Sum: } 8 \times 5\text{A} = 40\text{A}$$

Then you have to use either the 63A or 100A S803-SCL-SR. In this example we use the 63A version.

We know that our maximum load is 245A. Thus we have to calculate if this maximum load can be handled with the 63A version and, if yes, for how many seconds.

$$245\text{A} / 63\text{A} = 3.89 \sim 4$$

So now you can check where the multiplier „4“ crosses the graph of the 63A version to know for how many seconds this load can be handled. In this example a load of 245 A can be handled for max. 50 seconds.

Please note: always use the S800-SCL-SR in the left area of this graphic, since it would be damaged otherwise.

Electrical installation solutions for buildings – Technical details

RCDs

Index

Functions and classification criteria for RCDs	2/2
Limitation of specific let-through energy I^2t	2/5
Peak current I_p	2/13
Coordination tables: F 200 RCCBs	2/21
Coordination tables: back-up DS202C	2/24
Coordination tables: back-up DS201	2/26
Coordination tables: back-up DS203NC	2/35
Coordination tables: back-up DSE201	2/38
Coordination tables: back-up DSE201 M	2/39
Coordination tables: selectivity DS202C	2/42
Coordination tables: selectivity DS201	2/48
Coordination tables: selectivity DS203NC	2/72
Coordination tables: selectivity DSE201	2/77
Coordination tables: selectivity DSE201 M	2/78
Coordination tables: residual current protection selectivity	2/83
Power loss, derating and performance in altitude	2/87
Tripping characteristic	2/92
Emergency stop using DDA 200 AE series	2/93
Unwanted tripping - AP-R solution (high immunity)	2/94
Unwanted tripping - F2C-ARH solution	2/96
Type B RCDs	2/97
Use of 4P RCCBs in 3-phase system without neutral pole	2/107
Operating voltage of test button	2/108
RD2 residual current relays	2/113
RD3 residual current relays	2/114
ELR front panel residual current relays	2/117
Toroidal transformers	2/117

RCDs technical details

Functions and classification criteria for RCDs

Functions and classification criteria for RCDs

A residual current operated circuit-breaker is an amperometric protection device which is tripped when the system leaks a significant current to earth.

This device continuously calculates the vector sum of the single-phase or three-phase system line currents and while the sum is equal to zero allows electricity to be supplied. This supply is rapidly interrupted if the sum exceeds a value preset according to the sensitivity of the device.

Residual current operated circuit-breakers can be classed according to four parameters:

- type of construction
- detectable wave form
- tripping sensitivity
- tripping time.

Depending on the type of construction, RCDs may be classed as:

- RCBOs (magnetothermic with overcurrent protection)
- RCCBs (without overcurrent protection releaser incorporated)
- RCD blocks.

RCBOs combine, in a single device, the residual current function and the overcurrent protection function typical of MCBs. RCBOs are tripped by both current leakage to earth and overloads and short-circuits and they are self-protecting up to a maximum short-circuit current value indicated on the label.

RCCBs are only sensitive to current leakage to earth. They must be used in series with an MCB or fuse which protects them from the potentially damaging thermal and dynamic stresses of any overcurrents.

These devices are used in systems already equipped with MCBs which preferably limit the specific energy passing through, also acting as the main disconnecting switches upstream of any derived MCBs (e.g.: domestic consumer unit).

RCD blocks are residual current devices suitable for assembly with a standard MCB. IEC/EN 61009 app. G only allows assembly of RCBOs once on site, that is to say outside the factory, using adaptable RCD blocks and the appropriate MCBs. Any subsequent attempts to separate them must leave permanent visible damage. The residual current operated circuit-breaker obtained in this way maintains both the electrical characteristics of the MCB and those of the RCD block.

According to the wave form of the earth leakage currents they are sensitive to, the RCDs may be classed as:

- AC type (for alternating current only)
- A type (for alternating and/or pulsating current with DC components)
- B type (for alternating and/or pulsating current with DC components and continuous fault current).

AC type RCDs are suitable for all systems where users have sinusoidal earth current.

They are not sensitive to impulsive leakage currents up to a peak of 250 A (8/20 wave form) such as those which may occur due to overlapping voltage impulses on the mains (e.g.: insertion of fluorescent bulbs, X-ray equipment, data processing systems and SCR controls).

A type RCDs are not sensitive to impulsive currents up to a peak of 250 A (8/20 wave form).

They are particularly suitable for protecting systems in which the user equipment has electronic devices for rectifying the current or phase cutting adjustment of a physical quantity (speed temperature, light intensity, etc.) supplied directly by the mains without the insertion of transformers and insulated in class I (class II is, by definition, free of faults to earth). These devices may generate a pulsating fault current with DC components which the A type RCD can recognise.

RCDs technical details

Functions and classification criteria for RCDs

B type RCDs are recommended for use with drives and inverters for supplying motors for pumps, lifts, textile machines, machine tools, etc., since they recognise a continuous fault current with a low level ripple.

Type AC, A and B RCDs comply with IEC/EN 61008/61009, moreover type B is covered by IEC 62423 Ed. 1 and by IEC/EN 60755 for residual current operated protective devices.

According to tripping sensitivity ($I_{\Delta n}$ value), RCDs may be divided into the following categories:

- low-sensitivity ($I_{\Delta n} > 0.03 \text{ A}$), not suitable for protection against direct contacts; co-ordinated with the earth system according to the formula $I_{\Delta n} < 50/R$, to provide protection against indirect contacts;
- high-sensitivity ($I_{\Delta n}: 0.01...0.03 \text{ A}$), or "physiologically sensitive" for protection against indirect contacts, with simultaneous additional protection against direct contacts.
- against fire (up to 500 mA) according to IEC/EN 60364

Residual current sensitivity and environment

Household and special environments



$I_{\Delta n}$
 $\leq 30 \text{ mA}$

High-sensitivity or physiologically sensitive RCDs

IEC/EN 60364 makes the use of these devices mandatory in all bathrooms, showers and private and public swimming pools and environments in which plugs and sockets may be installed without insulating or low safety voltage transformers.

Laboratories, service industry and small industry



$I_{\Delta n}$
from 30 mA
to 500 mA

Low-sensitivity RCDs

Large service industry and industrial complex



$I_{\Delta n}$
from 500 mA
to 1000 mA

According to their tripping time, RCDs can be classed as:

- instantaneous (or rapid or general)
- type S selective (or - incorrectly - delayed).

Selective RCDs (RCBOs - RCCBs or RCD-blocks) have a delayed tripping action and are installed upstream of other rapid residual current operated circuit-breakers to guarantee selectivity and limit the power out only to the portion of the system affected by a fault.

RCDs technical details

Functions and classification criteria for RCDs

The tripping time is not adjustable. It is set according to a predetermined time – current characteristic with an intrinsic delay for small currents, tending to disappear as the current grows. IEC/EN 61008 and 61009 establish the tripping times relative to the type of RCD and the $I\Delta n$.

Type AC	In [A]	$I\Delta$ [A]	Tripping times (s) x currents			
			1x $I\Delta$	2x $I\Delta$	5x $I\Delta$	500A
Generic	Any	Any	0.3	0.15	0.04	0.04
S (selective)	Any	>0.030	0.13-0.5	0.06-0.2	0.05-0.15	0.04-0.15


The indicated maximum tripping times are also valid for A type RCDs, but increasing the current values of factor 1.4 for RCDs with $I\Delta n > 0.01$ A and of factor 2 for RCDs with $I\Delta n \leq 0.01$ A.

The range of ABB RCDs also includes AP-R (anti-disturbance) devices which trip according to the limit times allowed by the Standards for instantaneous RCDs. This function is due

to the slight tripping delay (approx. 10 ms) relative to the standard instantaneous ones.

The graph shows the comparison of the qualitative tripping curves for:

- a 30 mA instantaneous RCD
- a 30 mA AP-R instantaneous RCD
- a 100 mA selective RCD (type S)



Note: this is a qualitative chart; it is referred only to industrial frequencies of 50-60 Hz.

RCDs technical details



Limitation of specific let-through energy I^2t

I^2t diagrams - Specific let-through energy value I^2t

The I^2t curves give the values of the specific let-through energy expressed in A^2s ($A=amps$; $s=seconds$) in relation to the perspective short-circuit current ($Irms$) in kA.

DS 200-DS 200 M, characteristics B and C


230/400 V let-through energy



DS201 L - DS201 - DS201 T - DS201 M

DS202C - DS202C M, characteristics B and C


230 V let-through energy




RCDs technical details

Limitation of specific let-through energy I^2t

Specific let-through energy I^2t DS201L - Characteristic C




Specific let-through energy I^2t DS201 - Characteristic B




RCDs technical details

Limitation of specific let-through energy I^2t

Specific let-through energy I^2t DS201 - Characteristic C




Specific let-through energy I^2t DS201 - Characteristic K




RCDs technical details

Limitation of specific let-through energy I^2t

Specific let-through energy I^2t DS201M - Characteristic B




Specific let-through energy I^2t DS201M - Characteristic C



RCDs technical details

Limitation of specific let-through energy I^2t

Specific let-through energy I^2t DS201M - Characteristic K




RCDs technical details

Limitation of specific let-through energy I^2t


DS203NC L, characteristic B

400 V let-through energy



DS203NC, characteristic B

400 V let-through energy




RCDs technical details

Limitation of specific let-through energy I^2t


DS203NC L, characteristic C

400 V let-through energy




DS203NC, characteristic C

400 V let-through energy



DS203NC, characteristic K

400 V let-through energy





RCDs technical details

Limitation of specific let-through energy I^2t



DSE201

230 V let-through energy



DSE201 M


230 V let-through energy



RCDs technical details

Peak current I_p


DS201 L - DS201 - DS201 T - DS201 M
DS202C - DS202C M characteristics B and C
230 V




RCDs technical details

Peak current I_p

Ipeak DS201L - Characteristic C




Ipeak DS201 - Characteristic B




RCDs technical details

Peak current I_p

Ipeak DS201 - Characteristic C




Ipeak DS201 - Characteristic K




RCDs technical details

Peak current I_p

Ipeak DS201M - Characteristic B




Ipeak DS201M - Characteristic C



RCDs technical details

Peak current I_p


Ipeak DS201M - Characteristic K




RCDs technical details

Peak current I_p

DS203NC L, characteristic B




DS203NC, characteristic B




RCDs technical details

Peak current I_p

DS203NC L, characteristic C




DS203NC, characteristic C



RCDs technical details


Peak current I_p

DS203NC, characteristic K




DSE201

DSE201, characteristic B




DSE201, characteristic C




DSE201 M

DSE201M, characteristic B



DSE201M, characteristic C



RCDs technical details

Coordination tables: F 200 RCCBs

Coordination tables between Short Circuit Protection Devices (SCPD) and F 200 RCCBs

If you are using an RCCB you must verify that the Short Circuit Protection Device (SCPD) protects it from the effects of high current that arise under short-circuit conditions. The IEC/EN 61008 provides some tests to verify the behaviour of RCCB in short-circuit conditions. The tables

below provide the maximum withstanding short-circuit current expressed in eff. kA for which the RCCBs are protected thanks to the coordination with the SCPD installed upstream or downstream. The tests are performed with SCPD with a rated current (thermal protection) less than or equal to the rated current of the associated RCCB.

F 202

	Single-phases 230-240 V circuit					
	25 A	40 A	63 A	80 A	100 A	125 A
SN201L/S201L Na	4.5	4.5				
SN201/S201 Na	6	6				
SN201M/S201M Na	10	10				
S202L	10	10				
S202	20	20	20			
S202M	25	25	25			
S202P	40	25	25			
S292	25	25	25	25	25	25
S702	10	10	10	10	10	
S752	10	10	10			
S802N	36	36	36	36	36	36
S802S	50	50	50	50	50	50
Fuse 25 gG	100					
Fuse 40 gG	60	60				
Fuse 63 gG	20	20	20			
Fuse 100 gG	10	10	10	10	10	
Fuse 125 gG						10

F 202

	400-415 V circuits with isolated neutral (IT) under double faults					
	25 A	40 A	63 A	80 A	100 A	125 A
SN201N/SN201/SN201M	3	3				
S201L/S201L Na/S202L	4.5	4.5				
S201/S201 Na/S202	6	6	6			
S201M/S201M Na/S202M	10	10	10			
S201P/S201P Na/S202P	25	15	15			
S291/S292	10	10	10	10	10	10
S801N/S802N	20	20	20	20	20	20
S801S/S802S	25	25	25	25	25	25

RCDs technical details

Coordination tables: F 200 RCCBs

F 204

	Three-phases circuits with neutral (y/D) 230-240 V/400-415 V*					
	25 A	40 A	63 A	80 A	100 A	125 A
SN201L/S201L/S201LN ^a *	4.5	4.5				
SN201/S201/S201Na*	6	6				
SN201M/S201M/S201MN ^a *	10	10				
S202L*	10	10				
S202*	20	20	20			
S202M*	25	25	25			
S202P*	40	25	25			
S292*	25	25	25	25	25	25
S702	10	10	10	10	10	
S752	10	10	10			
S802N*	36	36	36	36	36	36
S802S*	50	50	50	50	50	50
Fuse 25 gG	100					
Fuse 40 gG	60	60				
Fuse 63 gG	20	20	20			
Fuse 100 gG	10	10	10	10	10	
Fuse 125 gG						10

* The switches are considered between phase and neutral (230/240V)

F 204

	Three-phases circuits with neutral (y/D) 230-240 V/400-415 V					
	25 A	40 A	63 A	80 A	100 A	125 A
S203L/S204L	4.5	4.5				
S203/S204	6	6	6			
S203M/S204M	10	10	10			
S203P/S204P	25	15	15			
S293/S294	10	10	10	10	10	10
S702	10	10	10	10	10	
S752	10	10	10			
S803N/S804N	20	20	20	20	20	20
S803S/S804S	25	25	25	25	25	25
Fuse 25 gG	50					
Fuse 40 gG	30	30				
Fuse 63 gG	20	20	20			
Fuse 100 gG	10	10	10	10	10	
Fuse 125 gG						10

RCDs technical details

Coordination tables: F 200 RCCBs

F 204

	Three-phases circuits with neutral (y/D) 133-138V/230-240V					
	25 A	40 A	63 A	80 A	100 A	125 A
SN201L	10	10				
SN201	15	15				
S201M	20	20				
S203L/S204L	10	10				
S203/S204	20	20	20			
S203M/S204M	25	25	25			
S203P/S204P	40	25	25			
S293/S294	25	25	25	25	25	25
S702	10	10	10	10	10	
S752	10	10	10			
S803N-S804N	36	36	36	36	36	36
S803S-S804S	50	50	50	50	50	50
Fuse 25 gG	100					
Fuse 40 gG	60	60				
Fuse 63 gG	20	20	20			
Fuse 100 gG	10	10	10	10	10	
Fuse 125 gG						10

RCDs technical details

Coordination tables: back-up DS202C

MCB/Fuses - DS202C @ 230/240 V

		Supply S.	S200	S200M	S200P	S200P	25gG	40gG	50gG	63gG	80gG	100gG	
Char.		B-C	B-C	B-C	B-C								
		Icu [kA]	20	25	40	25							
Load s.		In [A]	0,5...63	0,5...63	0,5...25	32...63							
DS202C	B,C, D,K	10	2...40	20	25	40	25	35	25	20	15	10	10
DS202C M	B,C	10	2...40	20	25	40	25	35	25	20	15	10	10

MCCB @ 415 V - DS202C @ 230/240 V

			Supply S.1	T1	T1	T1	T2	T3	T2	T3	T2	T2
			Version	B	C	N		S		H		L
Load S.	Char.	Icu [kA]	In [A]	16	25	36		50		70		85
DS202C	B, C, D, K	10	2..25				25		25		25	25
			32, 40	16	16	16	16	16	16	16	16	16
DS202C M	B, C	10	2..25				25		25		25	25
			32, 40	16	16	16	16	16	16	16	16	16

¹ Supply side circuit-breaker 4P (load side circuit branched between one phase and the neutral)

RCDs technical details

Coordination tables: back-up DS202C

MCCB @ 415V - DS202C @ 230/240 V

			Supply side	XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4
			Version	B	C	N	N	N	S	S	S	S	H	H	H	L	L	V
Load side	Char.	Icu [kA]	In [A]	18	25	36	36	36	50	50	50	50	70	70	70	85	120	150
DS202C	B,C, D,K	10	2..25	18	18	18	25	18	20	20	25	18	20	20	25	20	25	20
			32, 40				18		10	10	18		10	10	18	10	18	10
DS202C M	B,C	10	2..25	18	18	18	25	18	20	20	25	18	20	20	25	20	25	20
			32, 40				18		10	10	18		10	10	18	10	18	10

RCDs technical details

Coordination tables: back-up DS201

Fuses - DS201 (2019) @ 230/240V

		Supply side		Fuses gG					
Load side	Char	Icu [kA]	In[A]	25	40	50	63	80	100
DS201 (2019) L	C	6	6...32	35	25	25	25	15	10
DS201 (2019)	B,C,K	10	1...40	35	25	25	25	15	10
DS201 (2019) M	B,C,K	15	4...40	35	25	25	25	15	15

MCCB Tmax XT @ 415V - DS201 (2019) @ 230/240V

		Supply side		XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4	XT2	XT4
		Version	B	C	N	N	N	N	S	S	S	S	H	H	H	L	L	V	V	
Load side	Char	Icu [kA]	18	25	36	36	36	36	50	50	50	50	70	70	70	120	120	150	150	
DS201 (2019) L	C	6	In[A]	160	160	160	160	250	250	160	160	250	250	160	160	250	160	250	160	250
			6...25	18	18	18	20	10	18	18	20	10	18	18	20	18	20	18	18	18
			32	10	10	10	10	10	10	10	18	10	10	10	18	10	18	10	10	10
DS201 (2019)	B,C,K	10	1...25	18	18	18	25	18	20	20	25	18	20	20	25	20	25	20	20	20
			32,40	18	18	18	18	18	10	10	18	18	10	10	18	10	18	10	10	10
DS201 (2019) M	B,C,K	15	4...25	18	18	18	25	18	20	20	25	18	20	20	25	20	25	20	20	20
			32,40	18	18	18	18	18	15	15	18	18	15	15	18	15	18	15	15	15

MCCB Tmax T @ 415V - DS201 (2019)@230/240V

RCDs technical details

Coordination tables: back-up DS201

S200 -DS201 (2019) @ 230/240V

Load side	Char	Supply side	S200	S200M	S200P	S200P
		Version	B,C	B,C	B,C	B,C
		Icu [kA]	20	25	40	25
DS201 (2019) L	C	In[A]	0,5..63	0,5..63	0,5...25	32...63
DS201 (2019)	B,C,K	6	6...32	20	40	25
DS201 (2019) M	B,C,K	10	1...40	20	40	25
		15	4...40	20	40	25

DS201 (2019) - SN201 @ 230/240V

Load side	Char	Supply side	DS201 (2019)	DS201 (2019) M
		Version	B,C,K	B,C,K
		Icu [kA]	10	15
SN201 L	B,C	In[A]	1..40	2..40
SN201	B,C,D	6	2...40	10
		10		15

S800S - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800S
		Version	B,C,D,K
		Icu [kA]	50
DS201 (2019) L	C	In[A]	25 32 40 50 63 80 100 125
		6	50 40 25 25 18 15 15 15
		10	50 40 25 25 18 15 15 15
		16	50 40 25 25 18 15 15 15
		20	40 25 25 18 15 15 15 15
		25	25 25 18 15 15 15 15 15
		32	25 18 15 15 15 15 15 15
DS201 (2019)	B,C,K	1	50 50 50 50 50 50 50 50
		2	50 50 50 50 50 50 50 50
		4	50 50 50 50 50 50 50 50
		6	50 50 50 50 50 50 50 50
		8	50 50 50 50 50 50 50 50
		10	50 50 50 50 50 50 50 50
		13	50 50 50 50 50 50 50 50
		16	50 50 50 50 50 50 50 50
		20	50 50 50 50 50 50 50 50
		25	50 50 50 50 50 50 50 50
DS201 (2019) M	B,C,K	32	50 50 50 50 50 50 50 50
		40	50 50 50 50 50 50 50 50
		4	50 50 50 50 50 50 50 50
		6	50 50 50 50 50 50 50 50
		10	50 50 50 50 50 50 50 50
		13	50 50 50 50 50 50 50 50
		16	50 50 50 50 50 50 50 50
		20	50 50 50 50 50 50 50 50
		25	50 50 50 50 50 50 50 50
		32	50 50 50 50 50 50 50 50
		40	50 50 50 50 50 50 50 50

RCDs technical details

Coordination tables: back-up DS201

S800N - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800N								
			Version	B,C,D							
Icu [kA]	36										
In[A]	25		32	40	50	63	80	100	125		
DS201 (2019) L	C	6	6	36	36	25	25	18	15	15	
			10	36	36	25	25	18	15	15	
			16	36	36	25	25	18	15	15	
			20		36	25	25	18	15	15	
			25			25	25	18	15	15	
			32				25	18	15	15	
DS201 (2019)	B,C,K	10	1	36	36	36	36	36	36	36	
			2	36	36	36	36	36	36	36	
			4	36	36	36	36	36	36	36	
			6	36	36	36	36	36	36	36	
			8	36	36	36	36	36	36	36	
			10	36	36	36	36	36	36	36	
			13	36	36	36	36	36	36	36	
			16	36	36	36	36	36	36	36	
			20		36	36	36	36	36	36	
			25			36	36	36	36	36	
			32				36	36	36	36	
			40					36	36	36	
DS201 (2019) M	B,C,K	15	4	36	36	36	36	36	36	36	
			6	36	36	36	36	36	36	36	
			10	36	36	36	36	36	36	36	
			13	36	36	36	36	36	36	36	
			16	36	36	36	36	36	36	36	
			20		50	36	36	36	36	36	
			25			36	36	36	36	36	
			32				36	36	36	36	
			40					36	36	36	

RCDs technical details

Coordination tables: back-up DS201

S800C - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800C							
			Version	B,C,D,K						
Icu [kA]	25									
		In[A]	25	32	40	50	63	80	100	125
DS201 (2019) L	C	6	6	25	25	25	18	15	15	15
			10	25	25	25	18	15	15	15
			16	25	25	25	18	15	15	15
			20		25	25	18	15	15	15
			25		25	25	18	15	15	15
			32			25	18	15	15	15
DS201 (2019)	B,C,K	10	1	25	25	25	25	25	25	25
			2	25	25	25	25	25	25	25
			4	25	25	25	25	25	25	25
			6	25	25	25	25	25	25	25
			8	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25
			13	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25
			20		25	25	25	25	25	25
			25		25	25	25	25	25	25
			32			25	25	25	25	25
			40				25	25	25	25
DS201 (2019) M	B,C,K	15	4	25	25	25	25	25	25	25
			6	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25
			13	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25
			20		25	25	25	25	25	25
			25			25	25	25	25	25
			32				25	25	25	25
			40					25	25	25

RCDs technical details

Coordination tables: back-up DS201

S800B - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side		S800B						
			Version	B,C,D,K	32	40	50	63	80	100	125
DS201 (2019) L	C	6	In[A]	32	16	16	16	16	15	15	15
			6	16	16	16	16	16	15	15	15
			10	16	16	16	16	16	15	15	15
			16	16	16	16	16	16	15	15	15
			20	16	16	16	16	16	15	15	15
			25		16	16	16	16	15	15	15
			32			16	16	16	15	15	15
			1	16	16	16	16	16	16	16	16
			2	16	16	16	16	16	16	16	16
DS201 (2019)	B,C,K	10	4	16	16	16	16	16	16	16	16
			6	16	16	16	16	16	16	16	16
			8	16	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16	16
			25		16	16	16	16	16	16	16
			32			16	16	16	16	16	16
			40				16	16	16	16	16
DS201 (2019) M	B,C,K	15	4	16	16	16	16	16	16	16	16
			6	16	16	16	16	16	16	16	16
			10	16	16	16	16	16	16	16	16
			13	16	16	16	16	16	16	16	16
			16	16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16	16
			25		16	16	16	16	16	16	16
			32			16	16	16	16	16	16
			40				16	16	16	16	16

RCDs technical details

Coordination tables: back-up DS201

S800U - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800U							
			Version	K,Z							
			50	In[A]	25	30	40	50	60	70	80
DS201 (2019) L	C	6	6	50	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50
								50	50	50	50
DS201 (2019)	B,C,K	10	1	50	50	50	50	50	50	50	50
			2	50	50	50	50	50	50	50	50
			4	50	50	50	50	50	50	50	50
			6	50	50	50	50	50	50	50	50
			8	50	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50	50
			13	50	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50
			40					50	50	50	50
DS201 (2019) M	B,C,K	15	4	50	50	50	50	50	50	50	50
			6	50	50	50	50	50	50	50	50
			10	50	50	50	50	50	50	50	50
			13	50	50	50	50	50	50	50	50
			16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50
			40					50	50	50	50

RCDs technical details

Coordination tables: back-up DS201

S700 - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S700	
			Version	Eselective; Kselective
		Icu [kA]	25	
DS201 (2019) L	C	6	In[A]	80 100
			6	20 20
			10	20 20
			16	20 20
			20	20 20
			25	20 20
			32	20 20
			1	20 20
DS201 (2019)	B,C,K	10	2	20 20
			4	20 20
			6	20 20
			8	20 20
			10	20 20
			13	20 20
			16	20 20
			20	20 20
			25	20 20
			32	20 20
			40	20 20
			4	20 20
DS201 (2019) M	B,C,K	15	6	20 20
			10	20 20
			13	20 20
			16	20 20
			20	20 20
			25	20 20
			32	20 20
			40	20 20

RCDs technical details

Coordination tables: back-up DS201

S750 DR - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S750 DR						
			Version	Eselective; Kselective					
Icu [kA]	25								
		In[A]	16	20	25	35	40	50	63
DS201 (2019) L	C	6	6	20	20	20	20	20	20
		10	10	20	20	20	20	20	20
		16			20	20	20	20	20
		20				20	20	20	20
		25					20	20	20
		32						20	20
		40							
DS201 (2019)	B,C,K	10	1	20	20	20	20	20	20
		2	20	20	20	20	20	20	20
		4	20	20	20	20	20	20	20
		6	20	20	20	20	20	20	20
		8	20	20	20	20	20	20	20
		10	20	20	20	20	20	20	20
		13		20	20	20	20	20	20
		16			20	20	20	20	20
		20				20	20	20	20
		25					20	20	20
		32						20	20
		40							20
DS201 (2019) M	B,C,K	15	4	20	20	20	20	20	20
		6	20	20	20	20	20	20	20
		10	20	20	20	20	20	20	20
		13		20	20	20	20	20	20
		16			20	20	20	20	20
		20				20	20	20	20
		25					20	20	20
		32						20	20
		40							20

RCDs technical details

Coordination tables: back-up DS201

S750 - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S750							
			Version	Eselective; Kselective						
				Icu [kA]	25					
DS201 (2019) L	C	6	In[A]	16	20	25	35	40	50	63
			6	20	20	20	20	20	20	20
			10	20	20	20	20	20	20	20
			16		20	20	20	20	20	20
			20			20	20	20	20	20
			25				20	20	20	20
			32					20	20	20
			1	20	20	20	20	20	20	20
			2	20	20	20	20	20	20	20
			4	20	20	20	20	20	20	20
DS201 (2019)	B,C,K	10	6	20	20	20	20	20	20	20
			8	20	20	20	20	20	20	20
			10	20	20	20	20	20	20	20
			13		20	20	20	20	20	20
			16			20	20	20	20	20
			20				20	20	20	20
			25					20	20	20
			32					20	20	20
			40						20	20
			4	20	20	20	20	20	20	20
DS201 (2019) M	B,C,K	15	6	20	20	20	20	20	20	20
			10	20	20	20	20	20	20	20
			13		20	20	20	20	20	20
			16			20	20	20	20	20
			20				20	20	20	20
			25					20	20	20
			32						20	20
			40							20

RCDs technical details

Coordination tables: back-up DS203NC

Fuses-DS203NC @ 400V

		Supply side		gL/gG						
Load side	Char	Icu [kA]	In[A]	25	40	63	80	100	125	160
DS203NC	L C	6	6...32	100	70	40	15	15	10	10
DS203NC	B,C,K	10	6...32	100	70	40	15	15	10	10

MCCB @ 415V - DS203NC @ 400V

		Supply side		XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3
Char		B	C	N	N	N	N	N	S	S	S	S
Load side		Icu[KA]	In [A]	18	25	36	36	36	50	50	50	50
DS203NC	L C	6	6...25	16	16	16	20	10	10	16	20	10
			32	10	10	10	16	10	10	10	16	10
DS203NC	B,C,K	10	6...16	16	16	16	25	16	25	16	25	16
			20...25				25		16		25	
			32				16		16		16	

		Supply side		XT4	XT1	XT2	XT4	XT2	XT4	XT2	XT4
Char		S	H	H	H	L	L	V	V	V	
Load side		Icu[KA]	In [A]	50	70	70	70	120	120	150	150
DS203NC	L C	6	6...25	10	16	20	10	20	10	20	10
			32	10	10	16	10	16	10	16	10
DS203NC	B,C,K	10	6...16	25	16	25	25	25	25	25	25
			20...25	16		25	16	25	16	25	16
			32	16		16	16	16	16	16	16

MCCB @ 415V - DS203NC @ 400V

		Supply side		T1	T1	T1	T2	T3	T4	T2	T3	T4	T2	T4	T2	T4	T4
Char		B	C	N	N	N	N	N	S	S	S	H	H	L	L	V	
Load side		Icu [kA]	In[A]	16	25	36	36	36	50	50	50	70	70	85	120	200	
DS203NC	L C	6	6...25	16	16	16	20	10	10	20	10	20	10	20	10	10	
			32	10	10	10	16	10	10	16	10	16	10	16	10	10	
DS203NC	B,C,K	10	6...25	16	16	16	25	16	16	25	16	16	25	16	16	16	
			32	16	16	16	16	16	16	16	16	16	16	16	16	16	

S200 - DS203NC @ 400V

		Supply side		S200		S200M		S200P		S200P	
Char		B-C	B-C	B,C	B,C	B,C	B,C	B,C	B,C	B,C	B,C
Load side		Icu [kA]		20		25		40		25	
			In[A]	0,5..63		0,5...63		0,5...25		32	
DS203NC	L C	6	6...32	20		25		40		25	
DS203NC	B,C,K	10	6...32	20		25		40		25	

RCDs technical details

Coordination tables: back-up DS203NC

S800 - DS203NC @ 400V

		Supply side		S800N							
Load side	Char			B,C,D							
		Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DS203NC L	C	6	36								
			6..16	36	36	25	25	18	15	15	15
			20		36	25	25	18	15	15	15
			25			25	25	18	15	15	15
DS203NC	B,C,K	10	32				25	18	15	15	15
			6..16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25			36	36	36	36	36	36
DS203NC	B,C,K	10	32				36	36	36	36	36

		Supply side		S800S							
Load side	Char			B,C,D,K							
		Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DS203NC L	C	6	50								
			6..16	50	40	25	25	18	15	15	15
			20		40	25	25	18	15	15	15
			25			25	25	18	15	15	15
DS203NC	B,C,K	10	32				25	18	15	15	15
			6..16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50

		Supply side		S800B							
Load side	Char			B,C,D,K							
		Icu [kA]	In[A]	25	32	40	50	63	80	100	125*
DS203NC L	C	6	6	-	16	16	16	16	15	15	15
			8	-	16	16	16	16	15	15	15
			10	-	16	16	16	16	15	15	15
			13	-	16	16	16	16	15	15	15
			16	-	16	16	16	16	15	15	15
			20	-	16	16	16	16	15	15	15
			25	-		16	16	16	15	15	15
			32	-			16	16	15	15	15
DS203NC	B,C,K	10	6	-	16	16	16	16	16	16	16
			8	-	16	16	16	16	16	16	16
			10	-	16	16	16	16	16	16	16
			13	-	16	16	16	16	16	16	16
			16	-	16	16	16	16	16	16	16
			20	-	16	16	16	16	16	16	16
			25	-		16	16	16	16	16	16
			32	-			16	16	16	16	16

*Only S800B B,C

RCDs technical details

Coordination tables: back-up DS203NC

		Supply side		S800C						
		Char		B,C,D,K						
Load side	Icu [kA]	25								
		In[A]	25	32	40	50	63	80	100	125
DS203NC L C	6	6	25	25	25	25	18	15	15	15
		8	25	25	25	25	18	15	15	15
		10	25	25	25	25	18	15	15	15
		13	25	25	25	25	18	15	15	15
		16	25	25	25	25	18	15	15	15
		20		25	25	25	18	15	15	15
		25			25	25	18	15	15	15
		32				25	18	15	15	15
DS203NC	B,C,K	10	6	25	25	25	25	25	25	25
			8	25	25	25	25	25	25	25
			10	25	25	25	25	25	25	25
			13	25	25	25	25	25	25	25
			16	25	25	25	25	25	25	25
			20		25	25	25	25	25	25
			25			25	25	25	25	25
			32				25	25	25	25

RCDs technical details

Coordination tables: back-up DSE201

Fuses - DSE201 @ 230/240 V

		Supply side	Fuse 25gG	Fuse 40gG	Fuse 50gG	Fuse 63gG	Fuse 80gG	Fuse 100gG	Fuse 125gG	Fuse 160gG	Fuse 200gG	
Load side	Icu [kA]	Char.	In [A]	25	40	50	63	80	100	125	160	200
DSE201	6	B,C	up to 20	25	25	20	10	10	10	10	10	10
			25-32	-	25	20	10	7,5	7,5	7,5	7,5	7,5

MCCB @ 415 V - DSE201 @ 230/240 V

		Supply side	T1	T2	T3	T4	
Load side	Icu [kA]	Char.	In [A]	160	160	250	250
DSE201	6	B,C	up to 20	10	10	10	10
			25-32	7,5	7,5	7,5	7,5

MCCB @ 415 V - DSE201 @ 230/240 V

		Supply side	XT1	XT2	XT3	XT4	
Load side	Icu [kA]	Char.	In [A]	160	160	250	250
DSE201	6	B,C	up to 20	10	10	10	10
			25-32	7,5	7,5	7,5	7,5

RCDs technical details

Coordination tables: back-up DSE201 M

Fuses/S700 - DSE201 M @ 230/240 V

		Supply side		Fuse gG	S700	S750DR
Load side	Char.	Icu [kA]	In [A]	In [A]	In [A]	In [A]
DSE201 M	B	15	6	63	100	63
			10, 16, 20	100	100	63
			25, 32	100	100	63
			40	125	100	63
		10	50	160	100	63
	C	15	6	40	100	63
			10, 16, 20	100	100	63
			25, 32	100	100	63
			40	125	100	63
		10	50	160	100	63

This table shows coordination between DSE201 M and the Supply side fuse maximum current value. Combination of the two protections allows the breaking capacity to be elevated up to that of the combined fuse.

i.e. Load side RCBO DSE201 M-C16, Supply side fuse with In up to 100 A (breaking capacity: 100 kA). RCBO protection up to 100 kA

RCDs technical details

Coordination tables: back-up DSE201 M

MCCB @ 415 V - DSE201 M @ 230/240 V

		Supply side		XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4	XT2	XT4
				B	C	N	N	N	N	S	S	S	S	H	H	H	L	L	V	V
Load side	Char.	Icu [kA]	In [A]	18	25	36	36	36	36	50	50	50	50	70	70	70	120	120	150	150
DSE201 M	B,C	15		6, 10		18	25	30	36	36	36	50	40	30	70	40	40	30	40	30
		16...40		16...40		25	36	30	50	25	40	30	25	60	40	40	40	30	40	30
		10		50		18	25	30	36	16	36	30	36	16	40	30	40	40	30	40

MCCB @ 415 V - DSE201M @ 230/240 V

		Supply side		T1	T1	T1	T2	T3	T4	T2	T3	T4	T2	T4	T2	T4	T4
				B	C	N	N	N	N	S	S	S	H	H	L	L	V
Load side	Char.	Icu [kA]	In [A]	16	25	36	36	36	36	50	50	50	70	70	85	120	200
DSE201 M	B,C	15	6, 10	16	25	30	36	36	36	50	40	40	70	40	85	40	40
			16...40					25	36	50	25	40	60	40	60	40	40
		10	50	16	25	30	36	16	36	36	16	40	40	40	40	40	40

S800 - DSE201M @ 230/240 V

		S800U									
		Supply side		K,Z							
				50							
Load side	Char.	Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DSE201 M	B,C	15	6...16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
		25			50	50	50	50	50	50	50
			32			50	50	50	50	50	50
		40				50	50	50	50	50	50
			10	50				50	50	50	50

S800 - DSE201M @ 230/240 V

		Supply side		S800S							
				B,C,D,K							
				50							
Load side	Char.	Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DSE201 M	B,C	15	6...16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50
			40					50	50	50	50
			10	50					50	50	50

RCDs technical details

Coordination tables: back-up DSE201 M

S800 - DSE201M @ 230/240 V

		S800N									
		Supply side									
		B,C,D									
Load side	Char.	Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DSE201 M	B,C	15	6...16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25			36	36	36	36	36	36
			32				36	36	36	36	36
			40					36	36	36	36
			10	50					36	36	36

S800 - DSE201M @ 230/240 V

		S800C									
		Supply side									
		B,C,D									
Load side	Char.	Icu [kA]	In[A]	25	32	40	50	63	80	100	125
DSE201 M	B,C	15	6...16	25	25	25	25	25	25	25	25
			20		25	25	25	25	25	25	25
			25			25	25	25	25	25	25
			32				25	25	25	25	25
			40					25	25	25	25
			10	50					25	25	25

S800 - DSE201M @ 230/240 V

		S800B									
		Supply side									
		B,C,D,K									
Load side	Char.	Icu [kA]	In[A]	32	40	50	63	80	100	125	
DSE201 M	B,C	15	6...16	16	16	16	16	16	16	16	16
			20	16	16	16	16	16	16	16	16
			25		16	16	16	16	16	16	16
			32			16	16	16	16	16	16
			40				16	16	16	16	16
			10	50				16	16	16	16

S200P - DSE201M @ 230/240 V

		S200P									
		Supply side									
		B,C									
Load side	Char.	Icu [kA]	In[A]	0.5....25					32....63		
DSE201 M	B,C	15	6...40	25					15		
			10	50					15		

RCDs technical details

Coordination tables: selectivity DS202C

MCCB @ 415 V - DS202C @ 230/240V

Load S.	Char.	Icu [kA]	In [A]	Supply S. T1															T2						
				Version B, C, N		N, S, H, L															TMD, MA				
				Release	TMD	TMD, MA															TMD, MA				
DS202C	10	B, C, D, K	≤4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
		B, C, D, K	6	6	6	6	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
		B, C, D, K	8		3	3	3	4.5	7.5	8.5	T	T	T	T	T	T	T	3 ¹	3	3	3	3	4.5		
		B, C, D, K	10		3	3	3	4.5	7.5	8.5	T	T	T	T	T	T	T	3 ¹	3	3	3	3	4.5		
		B, C, D, K	13			3	4.5	5	7.5	T	T	T	T	T	T	T	T	3 ¹	3	4.5					
		B, C, D, K	16			3	4.5	5	7.5	T	T	T	T	T	T	T	T	3 ¹	3	4.5					
		B, C, D, K	20				3	5	6	T	T	T	T	T	T	T	T	3 ¹	3						
		B, C, D, K	25					5	6	T	T	T	T	T	T	T	T	3 ¹							
		B, C, D, K	32						6	7.5	T	T	T	T	T	T	T	3 ¹							
		B, C, D, K	40							7.5	T	T	T	T	T	T	T								
DS202C M	10	B, C	≤4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
		B, C	6	6	6	6	6	6	12	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
		B, C	10		3	3	3	4.5	7.5	8.5	T	T	T	T	T	T	T	3 ¹	3	3	3	3	4.5		
		B, C	13			3	4.5	5	7.5	T	T	T	T	T	T	T	T	3 ¹	3	4.5					
		B, C	16			3	4.5	5	7.5	T	T	T	T	T	T	T	T	3 ¹	3	4.5					
		B, C	20				3	5	6	T	T	T	T	T	T	T	T	3 ¹	3						
		B, C	25					5	6	T	T	T	T	T	T	T	T	3 ¹							
		B, C	32						6	7.5	T	T	T	T	T	T	T	3 ¹							
		B, C	40							7.5	T	T	T	T	T	T	T								

Supply side circuit-breaker 4P (load side circuit branched between one phase and the neutral)

Load side circuit-breaker 1P+N (230/240 V)

1 Value valid for magnetic only supply side circuit-breaker

2 Neutral at 50%

RCDs technical details

Coordination tables: selectivity DS202C

T3																									
N, S													TMD, MA												
EL													TMD, MA												
63	80	100	125 ²	125	160 ²	160	10	25	63	100	160	63	80	100	125 ²	125	160 ²	160	200 ²	200	250 ²	250			
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
7.5	8.5	T	T	T	T	T	T	T	T	T	T	T	7.5	8.5	T	T	T	T	T	T	T	T	T	T	T
7.5	8.5	T	T	T	T	T	T	T	T	T	T	T	7.5	8.5	T	T	T	T	T	T	T	T	T	T	T
5	7.5	T	7.5	T	T	T	T	T	T	T	T	T	5	7.5	T	7.5	T	T	T	T	T	T	T	T	T
5	7.5	T	7.5	T	T	T	T	T	T	T	T	T	5	7.5	T	7.5	T	T	T	T	T	T	T	T	T
5	6	T	6	T	T	T	T	T	T	T	T	T	5	6	T	6	T	T	T	T	T	T	T	T	T
5	6	T	6	T	T	T	T	T	T	T	T	T	5	6	T	6	T	T	T	T	T	T	T	T	T
6	7.5	6	T	T	T	T	T	T	T	T	T	T	6	7.5	6	T	T	T	T	T	T	T	T	T	T
6 ¹	7.5	6	T	T	T	T	T	T	T	T	T	T	6 ¹	7.5	T	T	T	T	T	T	T	T	T	T	T
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
7.5	8.5	T	T	T	T	T	T	T	T	T	T	T	7.5	8.5	T	T	T	T	T	T	T	T	T	T	T
5	7.5	T	7.5	T	T	T	T	T	T	T	T	T	5	7.5	T	7.5	T	T	T	T	T	T	T	T	T
5	7.5	T	7.5	T	T	T	T	T	T	T	T	T	5	7.5	T	7.5	T	T	T	T	T	T	T	T	T
5	6	T	6	T	T	T	T	T	T	T	T	T	5	6	T	6	T	T	T	T	T	T	T	T	T
5	6	T	6	T	T	T	T	T	T	T	T	T	5	6	T	6	T	T	T	T	T	T	T	T	T
6	7.5	6	T	T	T	T	T	T	T	T	T	T	6	7.5	6	T	T	T	T	T	T	T	T	T	T
6 ¹	7.5	6	T	T	T	T	T	T	T	T	T	T	6 ¹	7.5	T	T	T	T	T	T	T	T	T	T	T

1 Value valid for magnetic only supply side circuit-breaker

2 Neutral at 50%

RCDs technical details

Coordination tables: selectivity DS202C

MCCB@415V - DS202C @230/240V

				Supply S.	XT1									
				Version	B,C,N,S,H									
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160
DS202C	B,C,D,K	10	≤ 4	T	T	T	T	T	T	T	T	T	T	T
			6	6	6	6	6	6	6	T	T	T	T	T
			8		3	3	3	4,5	7,5	8,5	T	T	T	T
			10		3	3	3	4,5	7,5	8,5	T	T	T	T
			13				3	4,5	5	7,5	T	T	T	T
			16				3	4,5	5	7,5	T	T	T	T
			20					3	5	6	T	T	T	T
			25						5	6	T	T	T	T
			32							6	7,5	T	T	T
			40								7,5	T	T	T
DS202C M	B,C	10	≤ 4	T	T	T	T	T	T	T	T	T	T	T
			6	6	6	6	6	6	6	T	T	T	T	T
			10		3	3	3	4,5	7,5	8,5	T	T	T	T
			13				3	4,5	5	7,5	T	T	T	T
			16				3	4,5	5	7,5	T	T	T	T
			20					3	5	6	T	T	T	T
			25						5	6	T	T	T	T
			32							6	7,5	T	T	T
			40								7,5	T	T	T

RCDs technical details

Coordination tables: selectivity DS202C

			Supply S. XT2																
			Version	N,S,H,L,V															
Load S.	Char	Icu [kA]	Release	TM															
			In[A]	16	20	25	32	40	50	63	80	100	125	160	10	25	63	100	160
DS202C	B,C,D,K	10	≤ 4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			8		3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	
			10		3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	
			13			3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	
			16				3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	
			20					3 ¹		3	5	6	T	T	T	T	T	T	
			25						3 ¹	5	6	T	T	T	T	T	T	T	
			32							3 ¹	6	7,5	T	T	T	T	T	T	
			40								6 ¹	7,5	T	T	T	T	T	T	
DS202C M	B,C	10	≤ 4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10		3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	
			13			3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	
			16				3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	
			20					3 ¹		3	5	6	T	T	T	T	T	T	
			25						3 ¹	5	6	T	T	T	T	T	T	T	
			32							3 ¹	6	7,5	T	T	T	T	T	T	
			40								6 ¹	7,5	T	T	T	T	T	T	

¹ Value valid in case of Supply S. breaker only magnetic

RCDs technical details

Coordination tables: selectivity DS202C

			Supply S.	XT3						
			Version	N,S						
			Release	TM						
Load S.	Char	Icu [kA]	In[A]	63	80	100	125	160	200	250
DS202C	B,C,D,K	10	≤ 4	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T
			8	7,5	8,5	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T
			40		6 ¹	7,5	T	T	T	T
DS202C M	B,C	10	≤ 4	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T
			40		6 ¹	7,5	T	T	T	T

¹ Value valid in case of Supply S. breaker only magnetic

RCDs technical details

Coordination tables: selectivity DS202C

			Supply XT4 S.																		
			Version N,S,H,L,V																		
			Release TM																		
Load S.	Char	Icu [kA]	In[A]	20	25	32	40	50	63	80	100	125	160	200	225	250	40	63	100	160	250
DS202C	B,C,D,K	10	≤ 4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			8	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	3	T	T	T	T
			10	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	3	T	T	T	T
			13		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	3	T	T	T	T	T
			16		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	3	T	T	T	T	T
			20		3 ¹		3	5	6	T	T	T	T	T	T		T	T	T	T	T
			25			3 ¹	5	6	T	T	T	T	T	T			T	T	T	T	T
			32				3 ¹		6	7,5	T	T	T	T	T			T	T	T	T
			40					6 ¹	7,5	T	T	T	T	T				T	T	T	T
DS202CM	B,C	10	≤ 4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			10	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	3	T	T	T	T
			13		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	3	T	T	T	T	T
			16		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	3	T	T	T	T	T
			20		3 ¹		3	5	6	T	T	T	T	T	T		T	T	T	T	T
			25			3 ¹	5	6	T	T	T	T	T	T	T		T	T	T	T	T
			32				3 ¹		6	7,5	T	T	T	T	T		T	T	T	T	T
			40					6 ¹	7,5	T	T	T	T	T	T		T	T	T	T	T

¹ Value valid in case of Supply S. breaker only magnetic

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax XT1 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	In[A]	Supply side XT1										
				Version	B,C,N,S,H									
					Release	TM								
Load side	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T	T	T	
			10		3	3	3	4,5	T	T	T	T	T	
			16			3	4,5	5	T	T	T	T	T	
			20				3	5	T	T	T	T	T	
			25					5	T	T	T	T	T	
			32						T	T	T	T	T	
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T	T	T	T	
			2	T	T	T	T	T	T	T	T	T	T	
			4	T	T	T	T	T	T	T	T	T	T	
			6	6	6	6	6	6	T	T	T	T	T	
			8		3	3	3	4,5	7,5	8,5	T	T	T	
			10		3	3	3	4,5	7,5	8,5	T	T	T	
			13			3	4,5	5	7,5	T	T	T	T	
			16			3	4,5	5	7,5	T	T	T	T	
			20				3	5	6	T	T	T	T	
			25					5	6	T	T	T	T	
			32						6	7,5	T	T		
			40							7,5	T	T		
DS201 (2019) M	B,C,K	15	4	T	T	T	T	T	T	T	T	T	T	
			6	6	6	6	6	6	T	T	T	T	T	
			10		3	3	3	4,5	7,5	8,5	T	T	T	
			13			3	4,5	5	7,5	T	T	T	T	
			16			3	4,5	5	7,5	T	T	T	T	
			20				3	5	6	T	T	T	T	
			25					5	6	T	T	T	T	
			32						6	7,5	T	T		
			40							7,5	T	T		

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax XT2 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	In[A]	Supply side XT2												EL			
				Version		N,S,H,L,V													
				Release	TM														
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10	3 ¹	3	3	3	4,5	T	T	T	T	T	T	T	T	T	T	
			16		3 ¹	3	4,5	5	T	T	T	T	T	T	T	T	T	T	
			20		3 ¹		3	5	T	T	T	T	T	T	T	T	T	T	
			25			3 ¹	5	T	T	T	T	T	T	T	T	T	T	T	
			32			3 ¹		T	T	T	T	T	T	T	T	T	T	T	
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			2	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			8	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	
			10	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	
			13		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	
			16		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	
			20		3 ¹		3	5	6	T	T	T	T	T	T	T	T	T	
			25			3 ¹	5	6	T	T	T	T	T	T	T	T	T	T	
DS201 (2019) M	B,C, K	15	32			3 ¹		6	7,5	T	T	T	T	T	T	T	T	T	
			40					6 ¹	7,5	T	T	T	T	T	T	T	T	T	

¹ Value valid in case of Supply S. breaker only magnetic

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax XT3 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	XT3						
				Version	N,S					
					Release	TM	63	80	100	125
DS201 (2019) L	C	6		6	T	T	T	T	T	T
				10	T	T	T	T	T	T
				16	5	T	T	T	T	T
				20	5	T	T	T	T	T
				25	5	T	T	T	T	T
				32		T	T	T	T	T
DS201 (2019)	B,C,K	10		1	T	T	T	T	T	T
				2	T	T	T	T	T	T
				4	T	T	T	T	T	T
				6	T	T	T	T	T	T
				8	7,5	8,5	T	T	T	T
				10	7,5	8,5	T	T	T	T
				13	5	7,5	T	T	T	T
				16	5	7,5	T	T	T	T
				20	5	6	T	T	T	T
				25	5	6	T	T	T	T
DS201 (2019) M	B,C,K	15		32	6	7,5	T	T	T	T
				40	6 ¹	7,5	T	T	T	T
				4	T	T	T	T	T	T
				6	T	T	T	T	T	T
				10	7,5	8,5	T	T	T	T
				13	5	7,5	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax XT4 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	In [A]	Supply side XT4																EL					
				Version N,S,H,L,V																					
				Release TM																					
				16	20	25	32	40	50	63	80	100	125	160	200	225	250	40	63	100	160	250			
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			10	3	3 ¹	3	3	3	4,5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	T
			16		3 ¹	3	4,5	5	T	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	T
			20		3 ¹		3	5	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T
			25			3 ¹	5	T	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T
			32			3 ¹		T	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			8	3	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	3	T	T	T	T	T	T
			10	3	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	3	T	T	T	T	T	T
			13		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	T
			16		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	T	T
			20		3 ¹		3	5	6	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T
			25			3 ¹	5	6	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T
DS201 (2019) M	B,C,K	15	32		3 ¹		6	7,5	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T
			40			6 ¹	7,5	T	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax T1 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side T1											
			Version B,C,N		Release TMD									
			In[A]	16	20	25	32	40	50	63	80	100	125	160
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T	T	T	T
			10		3	3	3	4,5	T	T	T	T	T	T
			16			3	4,5	5	T	T	T	T	T	T
			20				3	5	T	T	T	T	T	T
			25					5	T	T	T	T	T	T
			32						T	T	T	T	T	T
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T	T	T	T	T
			4	T	T	T	T	T	T	T	T	T	T	T
			6	6	6	6	6	6	T	T	T	T	T	T
			8		3	3	3	4,5	7,5	8,5	T	T	T	T
			10		3	3	3	4,5	7,5	8,5	T	T	T	T
			13			3	4,5	5	7,5	T	T	T	T	T
			16			3	4,5	5	7,5	T	T	T	T	T
			20				3	5	6	T	T	T	T	T
			25					5	6	T	T	T	T	T
			32						6	7,5	T	T	T	T
			40							7,5	T	T	T	T
DS201 (2019) M	B,C,K	15	4	T	T	T	T	T	T	T	T	T	T	T
			6	6	6	6	6	6	T	T	T	T	T	T
			10		3	3	3	4,5	7,5	8,5	T	T	T	T
			13			3	4,5	5	7,5	T	T	T	T	T
			16			3	4,5	5	7,5	T	T	T	T	T
			20				3	5	6	T	T	T	T	T
			25					5	6	T	T	T	T	T
			32						6	7,5	T	T	T	T
			40							7,5	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax T2 @ 415V - DS201 (2019) @ 230/240V

			Supply side T2		Version N,S,H,L																
Load side	Char	Icu [kA]	Release	TMD, MA												EL					
				In[A]	16	20	25	32	40	50	63	80	100	125	160	10	25	63	100	160	
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
			10	3 ¹	3	3	3	4,5	T	T	T	T	T	T	T	T	T	T	T		
			16		3 ¹	3	4,5	5	T	T	T	T	T	T	T	T	T	T	T		
			20		3 ¹	3	3	5	T	T	T	T	T	T	T	T	T	T	T		
			25			3 ¹	5	T	T	T	T	T	T	T	T	T	T	T	T		
			32			3 ¹		T	T	T	T	T	T	T	T	T	T	T	T		
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
			2	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
			4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
			8	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	T		
			10	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	T		
			13		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	T		
			16		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	T		
			20		3 ¹	3	3	5	6	T	T	T	T	T	T	T	T	T	T		
			25			3 ¹	5	6	T	T	T	T	T	T	T	T	T	T	T		
			32			3 ¹		6	7,5	T	T	T	T	T	T	T	T	T	T		
			40				6 ¹	7,5	T	T					T	T					
DS201 (2019) M	B,C,K	15	4	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
			6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
			10	3 ¹	3	3	3	4,5	7,5	8,5	T	T	T	T	T	T	T	T	T		
			13		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	T		
			16		3 ¹	3	4,5	5	7,5	T	T	T	T	T	T	T	T	T	T		
			20		3 ¹	3	3	5	6	T	T	T	T	T	T	T	T	T	T		
			25			3 ¹	5	6	T	T	T	T	T	T	T	T	T	T	T		
			32			3 ¹		6	7,5	T	T	T	T	T	T	T	T	T	T		
			40				6 ¹	7,5	T	T					T	T					

RCDs technical details

Coordination tables: selectivity DS201

MCCB Tmax T3 @ 415V - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side T3							
			Version	N,S						
				Release	TMD, MA					
			In[A]	63	80	100	125	160	200	250
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T
			16	5	T	T	T	T	T	T
			20	5	T	T	T	T	T	T
			25	5	T	T	T	T	T	T
			32		T	T	T	T	T	T
DS201 (2019)	B,C,K	10	1	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T
			4	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T
			8	7,5	8,5	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T
			40		6 ¹	7,5	T	T	T	T
DS201 (2019) M	B,C,K	15	4	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T
			40		6 ¹	7,5	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS201

S800N / S800S (Char B) - DS201 (2019) @ 230/240V

RCDs technical details

Coordination tables: selectivity DS201

S800N / S800S (Char C) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side		S800N / S800S					
			Version		C					
			36 / 50		25	32	40	50	63	80
DS201 (2019) L	C	6	In[A]		25	32	40	50	63	80
			6				0.55	1.1	1.5	2.5
			10				0.45	1	1.3	1.9
			16					0.75	1.1	1.6
			20						0.9	1.4
			25							1.2
			32							1
			1	0.55	0.6	1.4	3.4	7.2	T	T
			2	0.43	0.55	1.2	3	6.6	T	T
			4	0.43	0.75	1.3	2.1	3.9	6.6	T
DS201 (2019)	B,C,K	10	6	0.55	1.1	1.5	2.5	3.6	5.5	
			8	0.5	1.25	1.4	2.2	3.2	5	
			10	0.45	1	1.3	1.9	2.8	4.2	
			13	0.38	0.83	1.2	1.75	2.6	3.9	
			16	0.38	0.75	1.1	1.6	2.3	3.6	
			20	0.38	0.75	0.9	1.4	1.9	3.3	
			25	0.38	0.75	1.2	1.6	2.7		
			32	0.38	0.75	1	1.5	2.5		
			40	0.38	0.75	1	1.4	2.1		
			4	0.43	0.75	1.3	2.1	3.9	6.6	T
DS201 (2019) M	B,C,K	15	6	0.55	1.1	1.5	2.5	3.6	5.5	
			10	0.45	1	1.3	1.9	2.8	4.2	
			13	0.35	0.9	1.2	1.7	2.6	3.8	
			16	0.35	0.75	1.1	1.6	2.3	3.6	
			20	0.35	0.75	0.9	1.4	1.9	3.3	
			25	0.35	0.75	1.2	1.6	2.7		
			32	0.35	0.75	1	1.5	2.5		
			40	0.35	0.75	1	1.4	2.1		

RCDs technical details

Coordination tables: selectivity DS201

S800 N / S800S (Char D) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side S800N / S800S								
			Version D								
			36 / 50								
DS201 (2019) L	C	6	In[A]	25	32	40	50	63	80	100	125
			6	0.6	1.3	2	3.2	3.9	T	T	T
			10	0.5	1.2	1.65	2.6	3.1	T	T	T
			16		0.9	1.4	1.8	2.6	5	T	T
			20			1.3	1.6	2.2	4.2	5.4	T
			25				1.5	1.9	3.5	4.5	T
			32					1.8	2.8	4.2	5.5
DS201 (2019)	B,C,K	10	1	1.6	4.8	T	T	T	T	T	T
			2	1.3	4.1	T	T	T	T	T	T
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
			8	0.4	1.25	1.8	2.9	3.6	7	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13		1.1	1.55	2.2	2.8	5.9	7.2	9.6
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
DS201 (2019) M	B,C,K	15	32				1.8	2.8	4.2	5.5	
			40					1.7	2.7	4	5
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13			1.55	2.1	2.8	5.6	7.1	9.5
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
DS201 (2019) C	B,C,K	20	20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32				1.8	2.8	4.2	5.5	
			40				1.7	2.7	4	5	
			4	0.8	1.6	3	5.4	7.6	T	T	T
DS201 (2019) A	B,C,K	25	6	0.6	1.3	2	3.2	3.9	8	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13			1.55	2.1	2.8	5.6	7.1	9.5
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
DS201 (2019) B	B,C,K	32	25			1.5	1.9	3.5	4.5	6.6	
			32				1.8	2.8	4.2	5.5	
			40				1.7	2.7	4	5	
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
DS201 (2019) D	B,C,K	40	10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13			1.55	2.1	2.8	5.6	7.1	9.5
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
DS201 (2019) E	B,C,K	50	32			1.8	2.8	4.2	5.5		
			40				1.7	2.7	4	5	
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
DS201 (2019) F	B,C,K	63	13			1.55	2.1	2.8	5.6	7.1	9.5
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32				1.8	2.8	4.2	5.5	
DS201 (2019) G	B,C,K	80	40			1.7	2.7	4	5		
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13			1.55	2.1	2.8	5.6	7.1	9.5
DS201 (2019) H	B,C,K	100	16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32				1.8	2.8	4.2	5.5	
			40				1.7	2.7	4	5	
DS201 (2019) I	B,C,K	125	40								
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13			1.55	2.1	2.8	5.6	7.1	9.5

RCDs technical details

Coordination tables: selectivity DS201

S800S (Char K) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800S							
			Version	K							
			36 / 50	In[A]	25	32	40	50	63	80	100
DS201 (2019) L	C	6	6		1.3	2	3.2	3.9	T	T	T
			10		1.2	1.65	2.6	3.1	T	T	T
			16		0.9	1.4	1.8	2.6	5	T	T
			20			1.3	1.6	2.2	4.2	5.4	T
			25				1.5	1.9	3.5	4.5	T
			32					1.8	2.8	4.2	5.5
			1	1.6	4.8	T	T	T	T	T	T
			2	1.3	4.1	T	T	T	T	T	T
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
DS201 (2019)	B,C,K	10	8	0.4	1.25	1.8	2.9	3.6	7	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13		1.1	1.55	2.2	2.8	5.9	7.2	9.6
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5
			4		1.6	3	5.4	7.6	T	T	T
			6		1.3	2	3.2	3.9	8	T	T
DS201 (2019) M	B,C,K	15	10		1.2	1.65	2.6	3.1	6.2	8.6	T
			13		1.55	2.1	2.8	5.6	7.1	9.5	
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5

RCDs technical details

Coordination tables: selectivity DS201

S800C (Char B) - DS201 (2019) @ 230/240V

RCDs technical details

Coordination tables: selectivity DS201

S800C (Char C) - DS201 (2019) @ 230/240V

RCDs technical details

Coordination tables: selectivity DS201

S800C (Char D) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800C							
			Version	D							
			25	25	32	40	50	63	80	100	125
DS201 (2019) L	C	6	I	6	1.3	2	3.2	3.9	T	T	T
			10	1.2	1.65	2.6	3.1	T	T	T	T
			16	0.9	1.4	1.8	2.6	5	T	T	T
			20		1.3	1.6	2.2	4.2	5.4	T	
			25			1.5	1.9	3.5	4.5	T	
			32				1.8	2.8	4.2		5.5
			1	1.6	4.8	T	T	T	T	T	T
DS201 (2019)	B,C,K	10	2	1.3	4.1	T	T	T	T	T	T
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
			8	0.4	1.25	1.8	2.9	3.6	7	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13		1.1	1.55	2.2	2.8	5.9	7.2	9.6
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40						1.7	2.7	4
DS201 (2019) M	B,C,K	15	4		1.6	3	5.4	7.6	T	T	T
			6		1.3	2	3.2	3.9	8	T	T
			10		1.2	1.65	2.6	3.1	6.2	8.6	T
			13			1.55	2.1	2.8	5.6	7.1	9.5
			16			1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40						1.7	2.7	4

RCDs technical details

Coordination tables: selectivity DS201

S800C (Char K) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800C							
			Version	K							
			25	In[A]	25	32	40	50	63	80	100
DS201 (2019) L	C	6	6		1.3	2	3.2	3.9	T	T	T
			10		1.2	1.65	2.6	3.1	T	T	T
			16		0.9	1.4	1.8	2.6	5	T	T
			20			1.3	1.6	2.2	4.2	5.4	T
			25				1.5	1.9	3.5	4.5	T
			32					1.8	2.8	4.2	5.5
			1	1.6	4.8	T	T	T	T	T	T
			2	1.3	4.1	T	T	T	T	T	T
			4	0.8	1.6	3	5.4	7.6	T	T	T
			6	0.6	1.3	2	3.2	3.9	8	T	T
DS201 (2019)	B,C,K	10	8	0.4	1.25	1.8	2.9	3.6	7	T	T
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T
			13		1.1	1.55	2.2	2.8	5.9	7.2	9.6
			16		0.9	1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5
			4		1.6	3	5.4	7.6	T	T	T
			6		1.3	2	3.2	3.9	8	T	T
DS201 (2019) M	B,C,K	15	10		1.2	1.65	2.6	3.1	6.2	8.6	T
			13		1.55	2.1	2.8	5.6	7.1	9.5	
			16			1.4	1.8	2.6	5	6.3	8.8
			20			1.3	1.6	2.2	4.2	5.4	7.6
			25				1.5	1.9	3.5	4.5	6.6
			32					1.8	2.8	4.2	5.5
			40					1.7	2.7	4	5

RCDs technical details

Coordination tables: selectivity DS201

S800B (Char B) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800B				
			Version	B				
			16	32	40	50	63	80
DS201 (2019) L	C	6	6			0.6	1.2	1.6
			10			0.5	1.1	1.4
			16				0.8	1.2
			20					1
			25					1.3
			32					1.1
			1	0.5	0.8	1.6	5	10
			2	0.43	0.6	1.3	4	9
			4		0.45	0.8	1.5	2.5
			6			0.6	1.3	1.6
DS201 (2019)	B,C,K	10	8		0.55	1.1	1.5	2.4
			10		0.5	0.9	1.4	1.9
			13			0.9	1.3	1.7
			16				1.2	1.5
			20				1	1.3
			25					1.1
			32					1.8
			40					1.7
			4	0.45	0.8	1.5	2.5	4
			6		0.6	1.2	1.6	2.6
DS201 (2019) M	B,C,K	15	10		0.5	1.1	1.4	3
			13			0.95	1.3	1.7
			16			0.8	1.2	1.7
			20				1	1.5
			25					2.1
			32					1.3
			40					1.8
								1.1

RCDs technical details

Coordination tables: selectivity DS201

S800B (Char C) - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800B						
			Version	C					
Icu [kA]	16								
		In[A]	32	40	50	63	80	100	125
DS201 (2019) L	C	6	6		0.55	1.1	1.5	2.5	3.6
			10		0.45	1	1.3	1.9	2.8
			16			0.75	1.1	1.6	2.3
			20				0.9	1.4	1.9
			25					1.2	1.6
			32					1	1.5
				1	0.6	1.4	3.4	7.2	T
DS201 (2019)	B,C,K	10	2	0.55	1.2	3	6.6	T	T
			4	0.43	0.75	1.3	2.1	3.9	6.6
			6	0.55	1.1	1.5	2.5	3.6	5.5
			8	0.5	1.25	1.4	2.2	3.2	5
			10	0.45	1	1.3	1.9	2.8	4.2
			13	0.38	0.82	1.2	1.75	2.6	3.9
			16		0.75	1.1	1.6	2.3	3.6
			20			0.9	1.4	1.9	3.3
			25				1.2	1.6	2.7
			32				1	1.5	2.5
DS201 (2019) M	B,C,K	15	40					1.4	2.1
			4	0.43	0.75	1.3	2.1	3.9	6.6
			6	0.55	1.1	1.5	2.5	3.6	5.5
			10	0.45	1	1.3	1.9	2.8	4.2
			13	0.35	0.9	1.2	1.7	2.6	3.8
			16		0.75	1.1	1.6	2.3	3.6
			20			0.9	1.4	1.9	3.3
			25				1.2	1.6	2.7
			32				1	1.5	2.5
			40					1.4	2.1

RCDs technical details

Coordination tables: selectivity DS201

S800B (Char D) - DS201 (2019) @ 230/240V

Load side	Char	Supply side	S800B								
			Version		D						
			Icu [kA]	16	In[A]	32	40	50	63	80	100
DS201 (2019) L	C	6	6	1.3	3.2	3.2	3.9	T	T	T	
			10	1.2	1.65	2.6	3.1	T	T	T	
			16	0.9	1.4	1.8	2.6	5	T	T	
			20		1.3	1.6	2.2	4.2	5.4	T	
			25			1.5	1.9	3.5	4.5	T	
			32				1.8	2.8	4.2	5.5	
			1	4.8	T	T	T	T	T	T	
			2	4.1	T	T	T	T	T	T	
			4	1.6	3	5.4	7.6	T	T	T	
			6	1.3	2	3.2	3.9	8	T	T	
DS201 (2019)	B,C,K	10	8	1.25	1.8	2.9	3.6	7	T	T	
			10	1.2	1.65	2.6	3.1	6.2	8.6	T	
			13	1.1	1.55	2.2	2.8	5.9	7.2	9.6	
			16	0.9	1.4	1.9	2.6	5	6.3	8.8	
			20		1.3	1.8	2.2	4.2	5.4	7.6	
			25			1.7	1.9	3.5	4.5	6.6	
			32				1.8	2.8	4.2	5.5	
			40				1.7	2.7	4	5	
			4	1.6	3	5.4	7.6	T	T	T	
			6	1.3	2	3.2	3.9	8	T	T	
DS201 (2019) M	B,C,K	15	10	1.2	1.65	2.6	3.1	6.2	8.6	T	
			13		1.55	2.1	2.8	5.6	7.1	9.5	
			16		1.4	1.8	2.6	5	6.3	8.8	
			20		1.3	1.6	2.2	4.2	5.4	7.6	
			25			1.5	1.9	3.5	4.5	6.6	
			32				1.8	2.8	4.2	5.5	
			40				1.7	2.7	4	5	

RCDs technical details

Coordination tables: selectivity DS201

S800B (Char K) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800B							
			Version	K							
			16	In[A]	32	40	50	63	80	100	125
DS201 (2019) L	C	6	6	1.3	3.2	3.2	3.9	T	T	T	
			10	1.2	1.65	2.6	3.1	T	T	T	
			16	0.9	1.4	1.8	2.6	5	T	T	
			20		1.3	1.6	2.2	4.2	5.4	T	
			25			1.5	1.9	3.5	4.5	T	
			32				1.8	2.8	4.2	5.5	
			1	4.8	T	T	T	T	T	T	
			2	4.1	T	T	T	T	T	T	
			4	1.6	3	5.4	7.6	T	T	T	
			6	1.3	2	3.2	3.9	8	T	T	
DS201 (2019)	B,C,K	10	8	1.25	1.8	2.9	3.6	7	T	T	
			10	1.2	1.65	2.6	3.1	6.2	8.6	T	
			13	1.1	1.55	2.2	2.8	5.9	7.2	9.6	
			16	0.9	1.4	1.9	2.6	5	6.3	8.8	
			20		1.3	1.8	2.2	4.2	5.4	7.6	
			25			1.7	1.9	3.5	4.5	6.6	
			32				1.8	2.8	4.2	5.5	
			40				1.7	2.7	4	5	
			4	1.6	3	5.4	7.6	T	T	T	
			6	1.3	2	3.2	3.9	8	T	T	
DS201 (2019) M	B,C,K	15	10	1.2	1.65	2.6	3.1	6.2	8.6	T	
			13		1.55	2.1	2.8	5.6	7.1	9.5	
			16		1.4	1.8	2.6	5	6.3	8.8	
			20		1.3	1.6	2.2	4.2	5.4	7.6	
			25			1.5	1.9	3.5	4.5	6.6	
			32				1.8	2.8	4.2	5.5	
			40				1.7	2.7	4	5	

RCDs technical details

Coordination tables: selectivity DS201

S800U (Char K) - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S800U									
			Version	K									
		50		In[A]	25	30	40	50	60	70	80	90	100
DS201 (2019) L	C	6	6	I _n [A]	0.34	0.41	0.57	1.1	1.5	2	2.5	3.6	T
			10	I _n [A]	0.23	0.3	0.45	1	1.3	1.6	1.9	2.8	T
			16	I _n [A]	0.21	0.35	0.75	1.1	1.3	1.6	2.3	T	
			20	I _n [A]		0.22	0.6	0.9	1.1	1.4	1.9	5.4	
			25	I _n [A]					1	1.2	1.6	4.5	
			32	I _n [A]						1	1.5	4.2	
			1	I _n [A]	0.55	0.6	1.4	3.4	7.2	8	T	T	T
DS201 (2019)	B,C,K	10	2	I _n [A]	0.44	0.55	1.2	3	6.6	7	T	T	T
			4	I _n [A]	0.38	0.43	0.75	1.3	2.1	3	3.9	6.6	T
			6	I _n [A]	0.34	0.38	0.56	1.1	1.5	2	2.5	3.6	T
			8	I _n [A]	0.23	0.32	0.5	1.25	1.4	1.8	2.2	3.2	T
			10	I _n [A]	0.2	0.28	0.45	1	1.3	1.6	1.9	2.8	8.6
			13	I _n [A]	0.22	0.38	0.83	1.2	1.4	1.75	2.6	7.2	
			16	I _n [A]	0.19	0.35	0.75	1.1	1.3	1.6	2.3	6.3	
			20	I _n [A]		0.28	0.58	0.9	1.1	1.4	1.9	5.4	
			25	I _n [A]					1	1.2	1.6	4.5	
			32	I _n [A]						1.5	1.5	4.2	
			40	I _n [A]						1.4	1.4	4	
DS201 (2019) M	B,C,K	15	4	I _n [A]	0.38	0.43	0.75	1.3	2.1	3	3.9	6.6	T
			6	I _n [A]	0.34	0.38	0.55	1.1	1.5	2	2.5	3.6	T
			10	I _n [A]	0.2	0.28	0.45	1	1.3	1.6	1.9	2.8	8.6
			13	I _n [A]		0.35	0.9	1.2	1.4	1.7	2.6	7.1	
			16	I _n [A]	0.19	0.34	0.75	1.1	1.3	1.6	2.3	6.3	
			20	I _n [A]		0.29	0.57	0.9	1.1	1.4	1.9	5.4	
			25	I _n [A]			0.53	0.6	0.9	1.2	1.6	4.5	
			32	I _n [A]				0.5	0.7	1	1.5	4.2	
			40	I _n [A]				0.3	0.5	0.8	1.4	4	

RCDs technical details

Coordination tables: selectivity DS201

S700 - DS201 (2019) @ 230/240V

Load side	Char	Supply side S700	Version	Eselective; Kselective
			Icu [kA]	25
DS201 (2019) L	C		I _n [A]	80
			6	T
			10	T
			16	T
			20	T
			25	T
			32	T
			1	T
			2	T
			4	T
DS201 (2019)	B,C,K		I _n [A]	6
			8	T
			10	T
			13	T
			16	T
			20	T
			25	T
			32	T
			40	T
			1	T
DS201 (2019) M	B,C,K		I _n [A]	10
			13	T
			16	T
			20	T
			25	T
			32	T
			40	T
			1	T
			4	T
			6	T

RCDs technical details

Coordination tables: selectivity DS201

S750 DR - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side	S750 DR							
			Version	Eselective; Kselective							
			25	In[A]	16	20	25	35	40	50	63
DS201 (2019) L	C	6	6	T	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T	T
			16		T		T	T	T	T	T
			20				T	T	T	T	T
			25				T	T	T	T	T
			32					T	T		
			1	T	T	T	T	T	T	T	T
			2	T	T	T	T	T	T	T	T
			4	T	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T	T
DS201 (2019)	B,C,K	10	8	T	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T	T
			13		T	T	T	T	T	T	T
			16			T	T	T	T	T	T
			20				T	T	T	T	T
			25				T	T	T	T	T
			32					T	T		
			40						T		
			4	T	T	T	T	T	T	T	T
			6	T	T	T	T	T	T	T	T
DS201 (2019) M	B,C,K	15	10	T	T	T	T	T	T	T	T
			13		T	T	T	T	T	T	T
			16			T	T	T	T	T	T
			20				T	T	T	T	T
			25				T	T	T	T	T
			32					T	T		
			40						T		

RCDs technical details

Coordination tables: selectivity DS201

S750 - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	Supply side S750							
			Version		Eselective; Kselective					
			25							
		In[A]	16	20	25	35	40	50	63	
DS201 (2019) L	C	6	6	T	T	T	T	T	T	
			10	T	T	T	T	T	T	
			16		T	T	T	T	T	
			20			T	T	T	T	
			25				T	T	T	
			32					T	T	
			1	T	T	T	T	T	T	
			2	T	T	T	T	T	T	
			4	T	T	T	T	T	T	
			6	T	T	T	T	T	T	
DS201 (2019)	B,C,K	10	8	T	T	T	T	T	T	
			10	T	T	T	T	T	T	
			13		T	T	T	T	T	
			16			T	T	T	T	
			20				T	T	T	
			25					T	T	
			32						T	
			40							T
			4	T	T	T	T	T	T	
			6	T	T	T	T	T	T	
DS201 (2019) M	B,C,K	15	10	T	T	T	T	T	T	
			13		T	T	T	T	T	
			16			T	T	T	T	
			20				T	T	T	
			25					T	T	
			32						T	
			40							T

RCDs technical details

Coordination tables: selectivity DS201

Fuses - DS201 (2019) @ 230/240V

Load side	Char	Icu [kA]	In[A]	Fuses gG							
				25	32	40	50	63	80	100	125
DS201 (2019) L	C	6	6	1	1.5	4	4.5	T	T	T	T
			10		1.2	3.5	4	T	T	T	T
			16		1	3	3.5	5	T	T	T
			20		1	3	3.5	5	T	T	T
			25		1	2	3	4.5	T	T	T
			32		1	2	3	4.5	5	T	T
DS201 (2019)	B,C,K	10	1	2.8	5.3	T	T	T	T	T	T
			2	2	4	5.8	T	T	T	T	T
			4	1.4	2.1	5.1	6.2		T	T	T
			6	1	1.5	4	4.5	7	T	T	T
			8		1.2	3.5	4	6	T	T	T
			10		1.2	3.5	4	6	T	T	T
			13		1	3	3.5	5	T	T	T
			16		1	3	3.5	5	T	T	T
			20		1	3	3.5	5	8	T	T
			25		1	2	3	4.5	6.5	T	T
			32		1	2	3	4.5	5	8	T
			40					3.7	4	6	8.7
DS201 (2019) M	B,C,K	15	4	1.1	1.6	4.2	T	T	T	T	T
			6	1	1.5	4	4.5	7	T	T	T
			10		1.2	3.5	4	6	10	10	T
			13		1.2	3.5	4	6	10	10	T
			16		1	3	3.5	5	10	10	T
			20		1	3	3.5	5	8	10	T
			25			2	3	4.5	6.5	10	T
			32				3	4.5	5	8	T
			40					3.4	3.8	5.5	8.2

RCDs technical details

Coordination tables: selectivity DS203NC

Fuses-DS203NC @ 400V

Load S.	Char	Icu [kA]	In[A]	Supply S. Fuse gL/gG							
				25	32	40	50	63	80	100	125
DS203NC L	C	6	6	1	1.5	4	4.5	T	T	T	T
			8		1.2	3.5	4	T	T	T	T
			10		1.2	3.5	4	T	T	T	T
			13		1	3	3.5	5	T	T	T
			16		1	3	3.5	5	T	T	T
			20		1	3	3.5	5	T	T	T
			25		1	2	3	4.5	T	T	T
			32		1	2	3	4.5	5	T	T
DS203NC	B,C,K	10	6	1	1.5	4	4.5	7	T	T	T
			8		1.2	3.5	4	6	T	T	T
			10		1.2	3.5	4	6	T	T	T
			13		1	3	3.5	5	T	T	T
			16		1	3	3.5	5	T	T	T
			20		1	3	3.5	5	8	T	T
			25		1	2	3	4.5	6.5	T	T
			32		1	2	3	4.5	5	8	T

MCCB @ 415V - DS203NC @ 400V

Load S.	Char	Icu [kA]	Release	XT2 XT1-XT2								XT1-XT2-XT3				XT3	
				Version				B,C,N,S,H,L,V				XT1-XT2-XT3					
				In[A]	12.5	16	20	25	32	40	50	63	80	100	125	160	200
DS203NC L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			8		3	3	3	3	4,5	T	T	T	T	T	T	T	T
			10		3	3	3	4,5	T	T	T	T	T	T	T	T	T
			13			3	4,5	5	T	T	T	T	T	T	T	T	T
			16			3	4,5	5	T	T	T	T	T	T	T	T	T
			20				3	5	T	T	T	T	T	T	T	T	T
			25					5	T	T	T	T	T	T	T	T	T
			32						T	T	T	T	T	T	T	T	T
DS203NC	B, C, K	10	6	6	6	6	6	6	T	T	T	T	T	T	T	T	T
			8		3	3	3	4,5	7,5	8,5	8,5	T	T	T	T	T	T
			10		3	3	3	4,5	7,5	8,5	8,5	T	T	T	T	T	T
			13			3	4,5	5	7,5	7,5	T	T	T	T	T	T	T
			16			3	4,5	5	7,5	7,5	T	T	T	T	T	T	T
			20				3	5	6	6	T	T	T	T	T	T	T
			25					5	6	6	T	T	T	T	T	T	T
			32						6	6	7,5	T	T	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS203NC

			Supply S. XT4													
			Version B,C,N,S,H,L,V													
Load S.	Char	Icu [kA]	Release	TM												
			In[A]	20	25	32	40	50	63	80	100	125	160	200	225	250
DS203NC L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T
			8	3	3	3	4,5	T	T	T	T	T	T	T	T	T
			10	3	3	3	4,5	T	T	T	T	T	T	T	T	T
			13			3	4,5	5	T	T	T	T	T	T	T	T
			16			3	4,5	5	T	T	T	T	T	T	T	T
			20			3	5	T	T	T	T	T	T	T	T	T
			25				5	T	T	T	T	T	T	T	T	T
			32					T	T	T	T	T	T	T	T	T
DS203NC	B, C, K	10	6	6	6	6	6	T	T	T	T	T	T	T	T	T
			8	3	3	3	4,5	7,5	8,5	8,5	T	T	T	T	T	T
			10	3	3	3	4,5	7,5	8,5	8,5	T	T	T	T	T	T
			13			3	4,5	5	7,5	7,5	T	T	T	T	T	T
			16			3	4,5	5	7,5	7,5	T	T	T	T	T	T
			20			3	5	6	6	T	T	T	T	T	T	T
			25				5	6	6	T	T	T	T	T	T	T
			32					6	6	7,5	T	T	T	T	T	T

			Supply S. XT2								XT4					
			Version B,C,N,S,H,L,V													
Load S.	Char	Icu [kA]	Release	EL												
			In[A]	25	63	100	160	40	63			100, 160		250		
DS203NC L	C	6	6	T	T	T	T	T	T	T	T	T	T	T	T	T
			8	T	T	T	T	T	T	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T	T	T	T	T	T	T
			13	T	T	T	T	T	T	T	T	T	T	T	T	T
			16	T	T	T	T	T	T	T	T	T	T	T	T	T
			20	T	T	T	T	T	T	T	T	T	T	T	T	T
			25	T	T	T	T			T	T	T	T	T	T	T
			32	T	T	T	T			T	T	T	T	T	T	T
DS203NC	B, C, K	10	6	T	T	T	T	T	T	T	T	T	T	T	T	T
			8	T	T	T	T	T	T	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T	T	T	T	T	T	T
			13	T	T	T	T	T	T	T	T	T	T	T	T	T
			16	T	T	T	T	T	T	T	T	T	T	T	T	T
			20	T	T	T	T	T	T	T	T	T	T	T	T	T
			25	T	T	T	T			T	T	T	T	T	T	T
			32	T	T	T	T			T	T	T	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS203NC

MCCB @ 415V -DS203NC @ 400V

			Supply S.	T1										
			Version	B,C,N										
			Release	TM										
			Iu[A]	160										
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160
DS203NC L	C	6	6	T	T	T	T	T	T	T	T	T	T	T
		8		3	3	3	3	4,5	T	T	T	T	T	T
		10		3	3	3	3	4,5	T	T	T	T	T	T
		13				3	4,5	5	T	T	T	T	T	T
		16				3	4,5	5	T	T	T	T	T	T
		20					3	5	T	T	T	T	T	T
		25						5	T	T	T	T	T	T
		32							T	T	T	T	T	T
DS203NC	B,C,K	10	6	6	6	6	6	6	T	T	T	T	T	T
		8		3	3	3	3	4,5	7,5	8,5	T	T	T	T
		10		3	3	3	3	4,5	7,5	8,5	T	T	T	T
		13				3	4,5	5	7,5	T	T	T	T	T
		16				3	4,5	5	7,5	T	T	T	T	T
		20					3	5	6	T	T	T	T	T
		25						5	6	T	T	T	T	T
		32							6	7,5	T	T	T	T

			Supply S.	T2										
			Version	N,S,H,L										
			Release	TM										
			Iu[A]	160										
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160
DS203NC L	C	6	6	T	T	T	T	T	T	T	T	T	T	T
		8		3	3	3	3	4,5	T	T	T	T	T	T
		10		3	3	3	3	4,5	T	T	T	T	T	T
		13				3	3	4,5	5	T	T	T	T	T
		16				3	3	4,5	5	T	T	T	T	T
		20					3	5	T	T	T	T	T	T
		25						3	T	T	T	T	T	T
		32							3	T	T	T	T	T
DS203NC	B,C,K	10	6	T	T	T	T	T	T	T	T	T	T	T
		8		3	3	3	3	4,5	7,5	8,5	T	T	T	T
		10		3	3	3	3	4,5	7,5	8,5	T	T	T	T
		13				3	3	4,5	5	7,5	T	T	T	T
		16				3	3	4,5	5	7,5	T	T	T	T
		20					3	5	6	T	T	T	T	T
		25						3	T	T	T	T	T	T
		32							6	7,5	T	T	T	T

RCDs technical details

Coordination tables: selectivity DS203NC

			Supply S.	T3						
			Version	N,S						
			Release	TM, M						
			Iu[A]	250						
Load S.	Char	Icu [kA]	In[A]	63	80	100	125	160	200	250
DS203NC L	C	6	6	T	T	T	T	T	T	T
			8	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T
			13	5	T	T	T	T	T	T
			16	5	T	T	T	T	T	T
			20	5	T	T	T	T	T	T
			25	5	T	T	T	T	T	T
			32		T	T	T	T	T	T
DS203NC L	B,C,K	10	6	T	T	T	T	T	T	T
			8	7,5	8,5	T	T	T	T	T
			10	7,5	8,5	T	T	T	T	T
			13	5	7,5	T	T	T	T	T
			16	5	7,5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7,5	T	T	T	T

S800-DS203NC @ 400V

			Supply S.	S800N-S					
			Char	B					
				Icu [kA]	36-50				
Load S.				In[A]	50	63	80	100	125
DS203NC L	C	6	6		0.6	1.2	1.6	2.6	3.8
			8		0.5	1.1	1.4	2	3
			10		0.5	1.1	1.4	2	3
			13			0.8	1.2	1.7	2.5
			16			0.8	1.2	1.7	2.5
			20				1	1.5	2.1
			25					1.3	1.8
			32					1.1	1.7
DS203NC	B,C,K	10	6		0.6	1.2	1.6	2.6	3.8
			8		0.5	1.1	1.4	2	3
			10		0.5	1.1	1.4	2	3
			13			0.8	1.2	1.7	2.5
			16			0.8	1.2	1.7	2.5
			20				1	1.5	2.1
			25					1.3	1.8
			32					1.1	1.7

RCDs technical details

Coordination tables: selectivity DS203NC

Load S.	Char	Supply S.	S800N-S							
			C							
			Icu [kA]	36-50						
Load S.	Char	Supply S.		In[A]	40	50	63	80	100	125
DS203NC L	C	6	6	6	0.55	1.1	1.5	2.5	3.6	5.5
			8	0.45	1	1.3	1.9	2.8	4.2	
			10	0.45	1	1.3	1.9	2.8	4.2	
			13		0.75	1.1	1.6	2.3	3.6	
			16		0.75	1.1	1.6	2.3	3.6	
			20			0.9	1.4	1.9	3.3	
			25				1.2	1.6	2.7	
			32				1	1.5	2.5	
DS203NC	B,C,K	6	6	6	0.55	1.1	1.5	2.5	3.6	5.5
			8	0.45	1	1.3	1.9	2.8	4.2	
			10	0.45	1	1.3	1.9	2.8	4.2	
			13		0.75	1.1	1.6	2.3	3.6	
			16		0.75	1.1	1.6	2.3	3.6	
			20			0.9	1.4	1.9	3.3	
			25				1.2	1.6	2.7	
			32				1	1.5	2.5	

Load S.	Char	Supply S.	S800 N-S									
			D									
			Icu [kA]	36-50								
Load S.	Char	Supply S.		In[A]	25	32	40	50	63	80	100	125
DS203NC L	C	6	6	6	0.6	1.3	2	3.2	3.9	T	T	T
			8	0.5	1.2	1.65	2.6	3.1	T	T	T	
			10	0.5	1.2	1.65	2.6	3.1	T	T	T	
			13		0.9	1.4	1.8	2.6	5	T	T	
			16		0.9	1.4	1.8	2.6	5	T	T	
			20			1.3	1.6	2.2	4.2	5.4	T	
			25				1.5	1.9	3.5	4.5	T	
			32					1.8	2.8	4.2	5.5	
DS203NC	B,C,K	10	6	6	0.6	1.3	2	3.2	3.9	8	T	T
			8	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T	
			10	0.5	1.2	1.65	2.6	3.1	6.2	8.6	T	
			13		0.9	1.4	1.8	2.6	5	6.3	8.8	
			16		0.9	1.4	1.8	2.6	5	6.3	8.8	
			20			1.3	1.6	2.2	4.2	5.4	7.6	
			25				1.5	1.9	3.5	4.5	6.6	
			32					1.8	2.8	4.2	5.5	

RCDs technical details

Coordination tables: selectivity DSE201

Fuses- DSE201 @ 230/240 V

			Supply side	Fuse 25gG	Fuse 40gG	Fuse 50gG	Fuse 63gG	Fuse 80gG	Fuse 100gG	Fuse 125gG	Fuse 160gG	Fuse 200gG
Load side	Char.	Icu [kA]	In [A]	25	40	50	63	80	100	125	160	200
DSE201	B,C	6	up to 20	1	side	3,5	T	T	T	T	T	T
			25-32		2	3	4,5	T	T	T	T	T

MCCB @ 415 V - DSE201 @ 230/240 V

			Supply side	T1								T2				
Load side	Char.	Icu [kA]	In [A]	50	63	80	100	125	160	50	63	80	100	125	160	
DSE201	B,C	6	up to 20	3	5	T	T	T	T	3	5	T	T	T	T	T
			25-32		T	T	T	T	T		T	T	T	T	T	T

MCCB @ 415 V - DSE201 @ 230/240 V

			Supply side	T3								T4					
Load side	Char.	Icu [kA]	In [A]	63	80	100	125	160	200	250	63	80	100	125	160	200	250
DSE201	B,C	6	up to 20	5	T	T	T	T	T	T	5	T	T	T	T	T	T
			25-32		T	T	T	T	T	T	T	T	T	T	T	T	T

MCCB @ 415 V - DSE201 @ 230/240 V

			Supply side	XT1								XT2				
Load side	Char.	Icu [kA]	In [A]	50	63	80	100	125	160	50	63	80	100	125	160	
DSE201	B,C	6	up to 20	3	5	T	T	T	T	3	5	T	T	T	T	T
			25-32		T	T	T	T	T		T	T	T	T	T	T

MCCB @ 415 V - DSE201 @ 230/240 V

			Supply side	XT3								XT4					
Load side	Char.	Icu [kA]	In [A]	63	80	100	125	160	200	250	63	80	100	125	160	200	250
DSE201	B,C	6	up to 20	5	T	T	T	T	T	T	5	T	T	T	T	T	T
			25-32		T	T	T	T	T	T		T	T	T	T	T	T

RCDs technical details

Coordination tables: selectivity DSE201 M

Fuses/S700 - DSE201M @ 230/240V

Load side	Char.	Icu [kA]	In [A]	Supply side								Fuse gG			
				16	20	25	35	50	63	80	100				
DSE201M	B,C	15	6	0.2	0.5	0.8	1.7	3.1	7	10	10				
			10	0.2	0.4	0.7	1.4	2.3	3.4	4.8	7.5				
			16				1.3	2	2.9	4.2	6				
			20					1.9	2.7	3.8	5.6				
			25					1.9	2.6	3.6	5.4				
			32						2.4	3.2	4.2				
			40							3.2	4.2				
			10	50							3.5				

Fuses/S700 - DSE201M @ 230/240V

Load side	Char.	Icu [kA]	In[A]	Supply side								S700			
				16	20	25	35	40	50	63	80	25	E/K		
DSE201M	B,C	15	6	15	15	15	15	15	15	15	10	10			
			10	15	15	15	15	15	15	15	10	10			
			16			15	15	15	15	15	10	10			
			20				15	15	15	15	10	10			
			25					15	15	15	10	10			
			32						15	15	10	10			
			40							15	10	10			
			10	50							8	8			

MCCB @ 415 V - DSE201M @ 230/240 V

Load side	Char.	Icu [kA]	Icn [A]	Supply side								XT1			
				Version								B,C,N,S,H			
				Release								TM			
				Iu [kA]								160			
DSE201M	B,C	15	Icu [A]	Icu [A]											
				6	3	3	3	5	6	6	10	T	T	T	T
				10		3	3	3	4.5	7.5	7.5	T	T	T	T
				16			3	4.5	5	7.5	12.5	T	T		
				20				3	5	6	10	T	T		
				25					5	6	10	10	T		
				32					3	6	7.5	10	T		
				40							7.5	10	T		
				10	50							T	T		

RCDs technical details

Coordination tables: selectivity DSE201 M

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side								XT2					XT3				
			Version								N,S,H,L,V								N,S	
			Release								TM								TM	
			Iu [kA]								160								250	
			Icu [A]								36,50,70,120,150								36,50	
Load side	Char.	Icu [kA]	Icn [A]	12.5	63	80	100	125	160	63	80	100	125	160	200	250				
DSE201M	B,C	15	6	3	10	T	T	T	T	10	T	T	T	T	T	T	T	T	T	
			10		7.5	7.5	T	T	T	7.5	7.5	T	T	T	T	T	T	T	T	
			16		5	7.5	12.5	T	T	5	7.5	12.5	T	T	T	T	T	T	T	
			20		5	6	10	T	T	5	6	10	T	T	T	T	T	T	T	
			25		5	6	10	T	5	6	10	10	T	T	T	T	T	T	T	
			32		3	6	7.5	10	T	3	6	7.5	10	T	T	T	T	T	T	
			40			7.5	10	T			7.5	10	T	T	T	T	T	T	T	
			10	50				T	T			10	10	T	T	T	T	T	T	

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side								XT4									
			Version								N,S,H,L,V									
			Release								TM									
			Iu [kA]								250									
			Icu [A]								36,50,70,120,150									
Load side	Char.	Icu [kA]	Icn [A]	20	25	32	40	50	63	80	100	125	160	200	225	250				
DSE201M	B,C	15	6	6	6	6	6	7.5	10	T	T	T	T	T	T	T	T	T	T	
			10	3	3	4.5	5	6.5	7.5	9	T	T	T	T	T	T	T	T	T	
			16		3	4.5	5	6.5	5	8	T	T	T	T	T	T	T	T	T	
			20			5	5	5	7.5	T	T	T	T	T	T	T	T	T	T	
			25				5	5	7.5	T	T	T	T	T	T	T	T	T	T	
			32					5	6	T	T	T	T	T	T	T	T	T	T	
			40						5	T	T	T	T	T	T	T	T	T	T	
			10	50					5	T	T	T	T	T	T	T	T	T	T	

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side								XT2					XT4				
			Version								N,S,H,L,V									
			Release								EL									
			Iu [kA]								160								250	
			Icu [A]								36,50,70,120,150								36,50,70,120,150	
Load side	Char.	Icu [kA]	Icn [A]	10	25	63	100	160	40	63	100	160	200	250						
DSE201M	B,C	15	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10		T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			16			T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			20				T	T	T	T	T	T	T	T	T	T	T	T	T	
			25					T	T	T		T	T	T	T	T	T	T	T	
			32						T	T	T		T	T	T	T	T	T	T	
			40							T	T			T	T	T	T	T	T	
			10	50					T	T				T	T	T	T	T	T	

RCDs technical details

Coordination tables: selectivity DSE201 M

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side		T2		T1-T2				T1-T2-T3				T3					
			Version		B,C,N,S,H,L						B,C,N,S,H,L,V									
			Release		TM															
Load side	Char.	Icu [kA]	In [A]		12.5	16	20	25	32	40	50	63	80	100	125	160	200	250		
DSE201M	B,C	15	6	5.5 ¹	5.5	5.5	5.5	5.5	5.5	5.5	10.5	T	T	T	T	T	T			
			10		3 ¹	3	3	3	4.5	7.5	8.5	T	T	T	T	T	T			
			16			3 ¹	3	4.5	5	7.5	12	T	T	T	T	T	T			
			20				3 ¹		3	5	6	10	T	T	T	T	T			
			25					3 ¹	5	6	10	T	T	T	T	T	T			
			32						3 ¹		6	7.5	12	T	T	T	T			
			40								5.5 ¹	7.5	12	T	T	T	T			
			10	50							3 ¹	5 ²	7.5	10.5	T	T	T			

¹⁾ Value valid only for T2 magnetic only supply side circuit-breaker

²⁾) Value valid only for T2-T3 magnetic only supply side circuit-breaker

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side		T4					T5				
			Version		B,C,N,S,H,L,V									
			Release		TM									
Load side	Char.	Icu [kA]	In [A]	20	25	32	50	80	100	125	160	200	250	320-500
DSE201M	B,C	15	6	7.5	7.5 ³	7.5	7.5	T	T	T	T	T	T	
			10	5	5 ³	5	6.5	9	T	T	T	T	T	
			16		3 ³	5	6.5	8	T	T	T	T	T	
			20				5	7.5	T	T	T	T	T	
			25				5	7.5	T	T	T	T	T	
			32				5 ³	7.5	T	T	T	T	T	
			40				6.5	T	T	T	T	T	T	
			10	50			5 ³	T	T	T	T	T	T	

³⁾ Value valid only for T4 magnetic only supply side circuit-breaker

MCCB @ 415 V - DSE201M @ 230/240 V

			Supply side		T2		T4		T5		
			Version		B,C,N,S,H,L,V						
			Release		EL						
Load side	Char.	Icu [kA]	In [A]	25	63	100	160	100,160	250,320	320-630	
DSE201M	B,C	15	6	T	T	T	T	T	T	T	
			10	T	T	T	T	T	T	T	
			16		T	T	T	T	T	T	
			20		T	T	T	T	T	T	
			25		T	T	T	T	T	T	
			32		T	T	T	T	T	T	
			40			T	T	T	T	T	
			10	50		10.5	10.5	T	T	T	

RCDs technical details

Coordination tables: selectivity DSE201 M

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 S						
				B						
				40	50	63	80	100	125	50
DSE201M	B,C	15	6	0.4	0.5	0.7	1	1.5	2.6	
			10		0.4	0.6	0.7	1	1.4	
			16				0.7	0.9	1.3	
			20					0.9	1.3	
			25					0.9	1.3	
			32				0.8	1.1		
			40				0.8	1.1		
			10	50					1	

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 S						
				C						
				25	32	40	50	63	80	100
DSE201M	B,C	15	6		0.4	0.5	0.7	0.9	1.4	2.4
			10		0.3	0.4	0.5	0.7	0.9	1.3
			16		0.3	0.4	0.5	0.7	0.9	1.3
			20			0.4	0.5	0.7	0.9	1.2
			25			0.4	0.5	0.7	0.9	1.2
			32				0.5	0.6	0.8	1
			40					0.6	0.8	1
			10	50					0.7	0.9

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 S						
				D						
				25	32	40	50	63	80	100
DSE201M	B,C	15	6	0.5	1	1.2	2	2.8	T *	T
			10	0.4	0.6	0.8	1.1	1.4	2.8	3.9
			16		0.6	0.8	1.1	1.4	2.5	3.3
			20			0.8	1.1	1.3	2.3	3
			25			0.8	1.1	1.3	2.3	3
			32				0.9	1.1	1.9	2.4
			40					1.1	1.9	2.4
			10	50					1.5	1.9

* 9.9 for C char

RCDs technical details

Coordination tables: selectivity DSE201 M

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 N					
				Supply side			B		
				40	50	63	80	100	125
DSE201M	B,C	15	6	0.4	0.5	0.7	1	1.5	2.6
			10		0.4	0.6	0.7	1	1.4
			16				0.7	0.9	1.3
			20					0.9	1.3
			25					0.9	1.3
			32				0.8	1.1	
			40				0.8	1.1	
			10	50					1

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 N					
				Supply side			C		
				25	32	40	50	63	80
DSE201M	B,C	15	6		0.4	0.5	0.7	0.9	1.4
			10		0.3	0.4	0.5	0.7	0.9
			16		0.3	0.4	0.5	0.7	0.9
			20			0.4	0.5	0.7	0.9
			25			0.4	0.5	0.7	0.9
			32				0.5	0.6	0.8
			40					0.6	0.8
			10	50					0.7

S800 - DSE201M @230/240 V

Load side	Char.	Icu [kA]	In [A]	S800 N					
				Supply side			D		
				25	32	40	50	63	80
DSE201M	B,C	15	6	0.5	1	1.2	2	2.8	T
			10	0.4	0.6	0.8	1.1	1.4	2.8
			16		0.6	0.8	1.1	1.4	2.5
			20			0.8	1.1	1.3	2.3
			25			0.8	1.1	1.3	2.3
			32				0.9	1.1	1.9
			40					1.1	1.9
			10	50					1.5

RCDs technical details

Coordination tables: residual current protection selectivity

Selectivity

RCDs raise similar issue to those surrounding the installation of MCBs, and in particular the need to reduce to a minimum the parts of the system out of order in the event of a fault. For RCBOs the problem of selectivity in the case of short-circuit currents may be handled with the same specific criteria as for MCBs.


However, for correct residual current protection, the more important aspects are linked to tripping times. Protection against contact voltages is only effective if the maximum times indicated on the safety curve are not exceeded.

If an electrical system has user devices with earth leakage currents which exceed the normal values (e.g.: presence of capacitor input filters inserted between the device phase and earth cables) or if the system consists of many user devices, it is good practice to install various RCDs, on the main branches, with an upstream main residual current or non-residual current device instead of a single main RCD.

Horizontal selectivity

The non-residual current main circuit-breaker provides “horizontal selectivity”, preventing an earth fault at any point on the circuit or small leakage from causing unwanted main circuit-breaker tripping, which would put the entire system out of order.

However, in this way, section k of the circuit between the main circuit-breaker and the RCDs remains without “active” protection. Using a main RCD to protect it would lead to problems with “vertical selectivity”, which require tripping of the various devices to be co-ordinated, so that service continuity and system safety are not compromised. In this case, selectivity may be amperometric (partial) or chronometric (total).



Vertical selectivity

Vertical selectivity may also be established for residual current tripping, bearing in mind that in working back from system peripheral branches to the main electrical panels the risk of unskilled persons coming into contact with dangerous parts is significantly reduced.

RCDs technical details


Coordination tables: residual current protection selectivity

Amperometric (partial) selectivity

Selectivity may be created by placing low-sensitivity RCDs upstream and higher-sensitivity RCDs downstream. An essential condition which must be satisfied in order to achieve selective co-ordination is that the $I\Delta$ value of the breaker upstream (main breaker) is more than double the $I\Delta$ value of the breaker downstream. The operative rule to obtain an amperometric (partial) selectivity is $I\Delta_n$ of the

upstream breaker = $3 \times I\Delta_n$ of the downstream breaker (e. g.: F 204, A type, 300 mA upstream; F 202, A type, 100 mA downstream).

In this case, selectivity is partial and only the downstream breaker trips for earth fault currents $I\Delta_2 < I\Delta_m < 0.5 \times I\Delta_1$.




Chronometric (total) selectivity

To achieve total selectivity, delayed or selective RCDs must be installed.

The tripping times of the two devices connected in series must be co-ordinated so that the total interruption time t_2 of the downstream breaker is less than the upstream breaker's no-response limit time t_1 , for any current value. In this way, the downstream breaker completes its opening before the upstream one.

To completely guarantee total selectivity, the $I\Delta$ value of the upstream device must also be more than double that of the downstream device in accordance with IEC 64-8/563.3, comments. The operative rule to obtain an chronometric (total) selectivity is $I\Delta_n$ of the upstream breaker = $3 \times I\Delta_n$ of the downstream breaker (e. g.: F 204, S type, 300 mA upstream; F 202, A type, 100 mA downstream). For safety reasons, the delayed tripping times of the upstream breaker must always be below the safety curve.



Legend

- 1 Theoretical safety curve
- 2 RCD A tripping characteristic
- 3 No-response limit times
- 4 RCD B tripping characteristic

RCDs technical details

Coordination tables: residual current protection selectivity

Table of RCD selectivity

Upstream IΔn [mA]	10	30	100	300	300	500	500	1000	1000	
Downstream IΔn [mA]	inst	inst	inst	inst	S	inst	S	inst	S	
10	inst		▲	▲	▲	■	▲	■	▲	■
30	inst		▲	▲	■	▲	■	▲	■	
100	inst			▲	■	▲	■	▲	■	
300	inst							▲	■	
300	S							▲	▲	
500	inst									
500	S									
1000	inst									
1000	S									

inst = instantaneous S = selective ▲ = amperometric (partial) selectivity ■ = chronometric (total) selectivity

Back-up F-ATI Test and F-ARI Test

The values has to be delivered from the LAb

2P	Rated current [A]	25	40	63	80	100
Single phase circuit with neutral 230-240 V	Fuse gG 25A	kA	10			
	Fuse gG 40A		10	10		
	Fuse gG 63A		10	10	10	
	Fuse gG 100A		10	10	10	
	S800 S		6	9	10	
	S800 N		6	9	10	
	S200		7	7	5	
	S200 M		7	7	5	
	S200 P		7	7	5	
4P	Rated current [A]	25	40	63	80	100
Three phase circuit with neutral 400-415 V	Fuse gG 25A		10			
	Fuse gG 40A		10	10		
	Fuse gG 63A		10	10	10	
	Fuse gG 100A		10	10	10	10
	S800 S		10	10	10	10
	S800 N		10	10	10	10
	S200		10	10	10	10
	S200 M		10	10	10	10
	S200 P		10	10	10	10

RCDs technical details

Coordination tables: residual current protection selectivity

Back-up F-ATI Test 2 & 4 pole with Selective SMCB S750

Upstream technology		MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB
RCD	System pro M compact	Product Range		SMCB	SMCB	SMCB	SMCB	SMCB	SMCB	SMCB
		Series		S750	S750	S750	S750	S750DR	S750DR	S750DR
		Characteristics		E,K	E,K	E,K	E,K	E,K	E,K	E,K
		Icu		25	25	25	25	25	25	25
		In		25	35	40	50	63	35	40
		A	10	25	7				7	
		A	10	40	7	7	9		7	7
		A	10	63	7	7	9	9	7	9
		A	10	25	7				7	7
		A	10	40	7	7	9		7	9
		A	10	63	7	7	9	9	7	9

Upstream technology		MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB	MCB
RCD	System pro M compact	Product Range		SMCB	SMCB	SMCB	SMCB	SMCB	SMCB	SMCB
		Series		S750	S750	S750	S750	S750DR	S750DR	S750DR
		Characteristics		E,K	E,K	E,K	E,K	E,K	E,K	E,K
		Icu		25	25	25	25	25	25	25
		In		25	35	40	50	63	35	40
		A	10	25	10				10	
		A	10	40	10	10			10	10
		A	10	63	10	10	10	10	10	10
		A	10	25	10				10	
		A	10	40	10	10			10	10
		A	10	63	10	10	10	10	10	10

RCDs technical details

Power loss, derating and performance in altitude

Power loss and internal resistance of RCDs and RCBOs

RCCBs F200 series

Rated current In [A]	Power loss per pole W [W]	
	2P	4P
16	1.5	-
25	1.0	1.3
40	2.4	3.2
63	3.2	4.4
80	4.5	5.3
100	6.5	8.2
125	-	7.5

RCCBs F200 Type B

	In [A]	Per Pole	Total
F202 B	16	0.02	0.04
	25	0.27	0.54
	40	1.70	3.40
	63	4.22	8.44
F204 B	25	0.29	1.16
	40	1.81	7.23
	63	4.50	17.98
	80	3.5	14
	125	7.5	44.8

RCD-Blocks DDA200 series

Rated current Ib [A]	Power loss Wlb* ① [W]	
	2P	3P,4P
25	2.0	3.0
40	3.2	4.8
63	5.0	7.6

* The power loss W_{lb} shown in the table refers to Ib. For use with circuit-breakers with lower rated current In the power loss W must be determined using the formula: $W = (I/Ib) \cdot W_{lb}$

RCD-Blocks DDA800

Rated current In [A]	Power loss Wlb* ① [W]	
	2P	3P, 4P
63	9	13.5
100	7	10.5
125	-	16.6

* The power loss W_{lb} shown in the table refers to Ib. For use with circuit-breakers with lower rated current In the power loss W must be determined using the formula: $W = (I/Ib) \cdot W_{lb}$

RCBOs DS 200, DS 200 M series

Rated current In [A]	Power loss W ①				
	[W]	Characteristic B-C	Characteristic K	2P	3P/4P
6	4.1	6.2	3.9	5.9	
10	2.9	4.4	2.9	4.2	
13	5.2	7.7	3.1	4.5	
16	4.5	6.6	4.9	7.2	
20	6.4	9.3	6.8	9.9	
25	8.5	12.4	7.9	11.5	
32	10.9	15.7	10.7	15.4	
40	15	21.6	14.4	20.7	
50	11.4	18.4	10.7	17.4	
63	17.4	28.2	18.2	29.4	

RCBOs DS201, DS202C series

Rated current In [A]	DS201		DS202C	
	Power loss ① [W]	Internal resistance [mΩ]	Power loss ① [W]	Internal resistance [mΩ]
1	1.4	1400.0		
2	1.6	400.0		
4	2.2	137.5		
6	2.4	66.7	8.1	224.8
8	1.9	29.7		
10	1.8	18.0	4.1	40.6
13	2.5	15.0	3.5	21
16	3.3	12.8	5.4	21
20	3.6	9.0	6.6	16.6
25	5.5	8.8	5.5	8.8
32	6.4	6.3	8.2	8
40	5.0	3.1		

RCBOs DS203NC series

In	Power loss [W]	Internal resistance [mΩ]
6A	7.5	207.3
8A	4.2	66.4
10A	5.6	55.9
13A	7.2	42.5
16A	10.0	39.3
20A	11.8	29.5
25A	10.3	16.4
32A	15.1	14.8

DS800 and DS800 N series ①

Rated current in [A]	2P	3P	4P
125	25.7	45.7	55.1

① data available in the tables are referred to the Power Loss per device

RCDs technical details

Power loss, derating and performance in altitude

RCBO DSE201 series			
In [A]	Voltage drop [V]	Power loss [W]	Internal resistance [mΩ]
6	0.42	2.5	70
10	0.25	2.5	25
16	0.24	3.8	15
20	0.27	5.5	14
25	0.15	3.8	6.1
32	0.16	5.2	5
40	0.14	5.5	3.4
50	0.11	5.3	2.1

RCBO DSE201 M series			
In [A]	Voltage drop [V]	Power loss [W]	Internal resistance [mΩ]
6	0.30	1.8	49
10	0.18	1.8	18
16	0.15	2.4	9.5
20	0.15	3.0	7.6
25	0.13	3.3	5.3
32	0.14	4.4	4.3
40	0.14	5.5	3.4
50	0.11	5.3	2.1

Derating of load capability of RCBOs DS 200 series, DS201, DS202C, DS203NC, DSE201 and DSE201 M

For DS 200 see tables for S 200 MCBs in technical details MCBs and dedicated tables for DS201 and DS202C, within the range of temperatures from -25 °C to +55 °C.

Elevation [m]	2000	3000	4000	5000	6000
Rated Current [A]	1.0 x In	0.96 x In	0.94 x In	0.92 x In	0.90 x In
Rated Voltage [V]	1.0 x Un	0.877 x Un	0.775 x Un	0.676 x Un	0.588 x Un

For altitude higher than 3.000 m the isolating characteristic is no longer available.

For DDA800 RCD Blocks according to IEC/EN 60947-2, up to 2000 meters above sea level, the rated characteristics remain unchanged.

With increasing altitude, the properties of the atmosphere change regarding composition, dielectricity, the cooling capacity and the pressure.

Performance in altitude of RCDs

ABB RCDs are able to operate at altitude higher than foreseen by the relevant standard IEC/ EN 61008 and IEC/ EN 61009 taking into account the corrective factor below detailed:

The characteristics of the DDA800 RCD Blocks therefore change: this can be measured for the most part using the change in significant parameters such as the maximum rated operational voltage and the rated current:

Elevation [m]	2000	3000	4000	5000
Rated operational voltage Ue [V]	690	600	540	470
Max rated current In [A]	1x In	0.96 x In	0.93 x In	0.9 x In

Derating in temperature for DS203NC series

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type B, C, K. Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

B, C	Temperature (°C)	-25	-20	-10	0	10	20	30	40	55
In		-25	-20	-10	0	10	20	30	40	55
6A	7.29	7.16	6.91	6.65	6.41	6.17	6.00	5.90	5.75	
8A	9.71	9.54	9.20	8.85	8.55	8.24	8.00	7.83	7.57	
10A	12.13	11.92	11.49	11.06	10.68	10.31	10.00	9.76	9.39	
13A	15.77	15.49	14.93	14.37	13.89	13.41	13.00	12.65	12.12	
16A	19.40	19.06	18.37	17.68	17.10	16.52	16.00	15.54	14.85	
20A	23.66	23.32	22.63	21.94	21.26	20.57	20.00	19.53	18.84	
25A	29.00	28.65	27.96	27.27	26.46	25.65	25.00	24.53	23.83	
32A	38.67	38.13	37.04	35.96	34.48	33.00	32.00	31.47	30.67	

RCDs technical details

Power loss, derating and performance in altitude

K	Temperature (°C)									
In	-25	-20	-10	0	10	20	30	40	55	
6A	7.2	6.9	6.6	6.4	6.2	6.0	5.8	5.7	5.6	
8A	9.5	9.2	8.9	8.5	8.2	8.0	7.8	7.6	7.4	
10A	11.9	11.5	11.1	10.7	10.3	10.0	9.7	9.5	9.1	
13A	15.5	14.9	14.4	13.9	13.4	13.0	12.6	12.3	11.7	
16A	19.2	18.4	17.7	17.1	16.5	16.0	15.5	15.1	14.4	
20A	23.3	22.6	21.9	21.3	20.6	20.0	19.4	19.0	18.3	
25A	28.8	28.1	27.3	26.5	25.6	25.0	24.4	23.9	23.2	
32A	38.4	37.2	35.8	34.5	33.0	32.0	31.0	30.5	29.7	

Derating in temperature for DS201 series

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type B, C. Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

In (A)	Temperature (°C)												
	-25	-20	-10	0	10	20	30	40	50	55	60	65	70
2A	3.9	3.6	3.2	2.9	2.7	2.4	2.0	1.8	1.7	1.6	1.5	1.4	1.3
4A	6.1	5.8	5.4	5.0	4.7	4.4	4.0	3.6	3.4	3.2	3.1	3.0	2.8
6A	8.7	8.4	7.7	7.3	7.0	6.4	6.0	5.5	5.3	5.1	4.9	4.7	4.6
8A	10.8	10.3	9.5	9.0	8.7	8.3	8.0	7.4	7.1	7.0	6.8	6.6	6.5
10A	13.5	13.0	12.1	11.5	11.0	10.6	10.0	9.4	9.0	8.8	8.6	8.4	8.3
13A	16.0	15.6	14.9	14.5	14.0	13.4	13.0	12.4	11.7	11.4	11.2	11.0	10.8
16A	18.9	18.6	18.1	17.5	17.0	16.4	16.0	15.3	14.8	14.5	14.3	14.1	14.0
20A	24.0	23.5	22.7	22.0	21.4	20.7	20.0	19.1	18.5	18.3	18.0	17.8	17.7
25A	27.9	27.5	27.1	26.6	26.0	25.3	25.0	24.3	23.6	23.4	23.2	23.0	22.8
32A	36.8	36.2	35.4	34.8	34.0	32.9	32.0	31.3	30.5	30.0	29.7	29.5	29.4
40A	44.8	44.6	44.0	43.2	42.1	41.0	40.0	39.0	38.1	37.9	37.6	37.4	37.2

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type K. Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

In (A)	Temperature (°C)												
	-25	-20	-10	0	10	20	30	40	50	55	60	65	70
1A	2.2	2.2	1.7	1.5	1.3	1.0	0.7	0.6	0.6	0.5	0.5	0.4	0.4
2A	3.5	3.2	2.8	2.8	2.4	2.0	1.8	1.8	1.7	1.6	1.5	1.5	1.4
4A	5.7	5.3	4.9	4.8	4.4	4.0	3.6	3.4	3.3	3.0	2.9	2.8	2.8
6A	8.0	7.7	7.4	7.0	6.5	6.0	5.4	5.3	5.2	4.8	4.7	4.6	4.5
8A	10.0	9.5	9.0	8.7	8.2	8.0	7.4	7.1	7.0	6.7	6.6	6.5	6.4
10A	12.6	12.1	11.5	11.0	10.5	10.0	9.4	9.1	8.9	8.8	8.6	8.4	8.3
13A	15.4	14.9	14.4	14.1	13.4	13.0	12.5	11.8	11.4	11.2	11.0	10.8	10.7
16A	18.7	18.2	17.5	17.0	16.4	16.0	15.4	14.7	14.6	14.3	14.2	14.0	13.9
20A	23.1	22.7	22.1	21.3	20.7	20.0	19.1	18.5	18.2	18.1	17.9	17.8	17.7
25A	27.4	27.1	26.5	26.0	25.4	25.0	24.3	23.6	23.4	23.2	23.0	22.8	22.6
32A	36.1	35.4	34.9	34.0	32.8	32.0	31.2	30.5	29.9	29.7	29.5	29.4	29.3
40A	44.4	43.9	43.2	42.1	40.9	40.0	39.0	38.2	37.7	37.4	37.2	37.0	36.8

RCDs technical details

Power loss, derating and performance in altitude

Derating in temperature for DS202C series

Max. operating current depending on the ambient temperature of a circuit-breaker in load circuit of characteristics type B, C and K. Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

B, C	Temperature ($^{\circ}\text{C}$)									
In (A)	-25	-20	-10	0	10	20	30	40	50	55
2	2.6	2.5	2.4	2.3	2.2	2.1	2.0	1.9	1.8	1.7
4	4.9	4.8	4.6	4.5	4.3	4.2	4	3.8	3.7	3.6
6	7.95	7.8	7.4	7.1	6.7	6.4	6	5.6	5.3	5.1
8	10.3	10.1	9.7	9.3	8.8	8.4	8	7.6	7.2	6.95
10	11.8	11.6	11.3	11.0	10.7	10.3	10	9.7	9.3	9.15
13	15.65	15.4	14.9	14.4	14.0	13.5	13	12.5	12.0	11.8
16	18.65	18.4	17.9	17.4	17.0	16.5	16	15.5	15.0	14.8
20	23.1	22.8	22.2	21.7	21.1	20.6	20	19.4	18.9	18.6
25	30.8	30.3	29.2	28.2	27.1	26.1	25	23.9	22.9	22.35
32	39.3	38.6	37.3	36.0	34.7	33.3	32	30.7	29.3	28.65
40	50.7	49.7	47.8	45.8	43.9	41.9	40	38.1	36.1	35.15

K	Temperature ($^{\circ}\text{C}$)									
In (A)	-25	-20	-10	0	10	20	30	40	50	55
2	2.5	2.4	2.4	2.3	2.1	2	1.9	1.7	1.7	1.7
4	4.7	4.6	4.4	4.4	4.1	4	3.8	3.8	3.6	3.6
6	7.8	7.5	7.2	6.7	6.4	6	5.5	5.4	5.0	5.1
8	10.1	9.7	9.2	8.9	8.3	8	7.6	7.3	6.9	6.7
10	11.6	11.3	11.0	10.8	10.2	10	9.8	9.2	9.2	8.9
13	15.4	14.9	14.4	13.9	13.5	13	12.6	12.0	11.8	11.6
16	18.5	17.8	17.3	17.0	16.4	16	15.5	15.0	14.9	14.5
20	22.8	22.2	21.7	21.2	20.6	20	19.3	18.9	18.7	18.2
25	30.3	29.3	28.1	27.1	26.2	25	24.0	23.0	22.3	22.0
32	38.6	37.4	35.9	34.8	33.3	32	30.7	29.2	28.6	27.9
40	49.7	47.8	45.8	44.0	41.9	40	38.2	36.1	35.2	34.5

RCDs technical details

Power loss, derating and performance in altitude

Derating in temperature for DSE201 series

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type B. C.
Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

	Temperature ($^{\circ}\text{C}$)									
In	-25	-20	-10	0	10	20	30	40	50	55
6 A	8.1	8.0	7.8	7.4	6.9	6.5	6.0	5.9	5.8	5.7
10 A	13.8	13.5	13.0	12.3	11.6	10.8	10.0	9.9	9.7	9.7
16 A	19.7	19.5	19.1	18.5	17.6	16.6	16.0	15.8	15.5	15.4
20 A	23.7	23.5	23.2	22.7	21.6	20.5	20.0	19.7	19.4	19.2
25 A	30.2	29.2	29.2	28.4	27.0	25.7	25.0	24.6	24.1	23.9
32 A	39.4	37.7	37.7	36.4	34.7	33.0	32.0	31.4	30.7	30.4
40 A	50.3	47.9	47.9	45.6	43.6	41.5	40.0	39.0	38.4	38.1
50 A	61.1	59.2	59.2	57.1	54.4	51.7	50.0	48.8	48.0	47.9

Derating in temperature for DSE201 M series

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type B, C.
Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

	Temperature ($^{\circ}\text{C}$)									
In	-25	-20	-10	0	10	20	30	40	50	55
6 A	7.3	7.2	6.9	6.7	6.4	6.2	6.0	5.9	5.9	5.8
10 A	13.0	12.9	12.2	11.4	10.9	10.4	10.0	9.8	9.7	9.5
16 A	20.2	19.7	18.7	17.8	17.3	16.6	16.0	15.8	15.4	15.2
20 A	26.0	19.7	24.0	22.8	21.9	20.7	20.0	19.8	19.6	19.5
25 A	32.6	25.2	30.4	29.0	27.5	26.0	25.0	24.6	24.2	23.9
32 A	41.1	31.5	38.0	36.3	34.8	33.1	32.0	30.9	29.8	29.6
40 A	50.3	49.4	47.9	45.6	43.7	41.5	40.0	39.0	38.4	38.1
50 A	61.1	60.4	59.2	57.1	54.4	51.7	50.0	48.8	48.0	47.9

RCDs technical details

Tripping characteristic

Tripping characteristics valid for all the RCBOs

Acc. to	Tripping characteristic and rated current	Thermal release ②		Tripping time	Electromagnetic release ①		Tripping time
		Current: conventional non-tripping current	conventional tripping current		Currents: hold current surges	trip at least at	
IEC/EN 60898-1	B	6 to 40 A	1.13 · I_n	> 1 h	3 · I_n	> 0.1 s	
			1.45 · I_n	< 1 h	5 · I_n	< 0.1 s	
IEC/EN 60947-2	C	2 to 40 A	1.13 · I_n	> 1 h	5 · I_n	> 0.1 s	
			1.45 · I_n	< 1 h	10 · I_n	< 0.1 s	
IEC/EN 60947-2	K	1 to 40 A	1.05 · I_n	> 1 h	10 · I_n	> 0.2 s	
			1.2 · I_n	< 1 h ③	14 · I_n	< 0.2 s	
			1.5 · I_n	< 2 min. ③			
			6.0 · I_n	> 2 s (T1)			

① The indicated electromagnetic tripping values apply to a frequency range of 16 2/3 ... 60 Hz. For different network frequencies or direct current the values change according to the multiplier in the table below.


② The thermal releases are calibrated to a nominal reference ambient temperature; for Z and K, the value is 20 °C, for B and C = 30 °C.

In the case of higher ambient temperatures, the current values fall by ca. 6 % for each 10 K temperature rise.

③ As from operating temperature (after $I_1 > 1$ h or, as applicable, 2 h).


Characteristic B

IEC/EN 61009-1




Characteristic C

IEC/EN 61009-1



Characteristic K

IEC-EN60947-2



④ thermal trip

⑤ electromagnetic trip

RCDs technical details

Emergency stop using DDA 200 AE series



RCD-blocks type AE

Emergency stop using DDA 200 AE series RCD-blocks

The AE series RCD-block combines the protection supplied by the RCBOs with a positive safety emergency stop function for remote tripping.

In the AE version, the DDA 200 AE series RCD-blocks are available.

Operating principle (patented)

Two additional primary circuits powered with the same voltage and equipped with the same resistance have been added to the transformer; under normal conditions the same current would flow through, but since they are wound by the same number of coils in opposite directions they cancel each other out and do not produce any flow.

One of these two windings acts as the remote control circuit: the emergency stop is obtained by interrupting the current flow in this circuit.

The positive safety is therefore obvious: an accidental breakage in the circuit is equivalent to operating an emergency control button.

Advantages


Compared with the devices which are normally used in emergency circuits, DDA 200 AE blocks have the following advantages:

- positive safety
- no unwanted tripping if there is a temporary reduction or interruption of the mains voltage
- efficient immediate operation even after long off-service periods of the installation

Use

Application of the DDA 200 AE blocks complies with the requirements of IEC 60364-8. They are therefore suitable, for example, for escalators, lifts, hoists, electrically operated gates, machine tools, car washes and conveyor belts.

No more than one DDA 200 AE can be controlled using the same control circuit. Each DDA 200 AE requires a dedicated control circuit.



RCDs technical details

Unwanted tripping - AP-R solution (high immunity)

Unwanted tripping

In the event of disturbance in the mains, the RCDs normally present in the system are tripped, breaking the circuit even in the absence of a true earth fault.

Disturbances of this kind are most often caused by:

- operation overvoltages caused by inserting or removing loads (opening or closing protection of control devices, starting and stopping motors, switching fluorescent lighting systems on and off, etc.)
- overvoltages of atmospheric origin, caused by direct or indirect discharges on the electrical line.

Under these circumstances, breaker tripping is unwanted, since it does not satisfy the need to avoid the risks due to direct and indirect contacts. On the contrary, the sudden and unjustified interruption of the power supply may result in very serious problems.

AP-R RCDs

The ABB range of AP-R anti-disturbance residual current circuit-breakers and blocks was designed to overcome the problem of unwanted tripping due to overvoltages of atmospheric or operation origin.

The electronic circuit in these devices can distinguish between temporary leakage caused by disturbances on the mains and permanent leakage due to actual faults, only breaking the circuit in the latter case.

AP-R residual current circuit-breakers and blocks have a slight delay into the tripping time, but this does not compromise the safety limits set by the Standards in force (release time at $2 I_{\Delta n}=150$ ms).

Guaranteeing conventional residual current protection, their installation in the electrical circuit therefore allows any unwanted tripping to be avoided in domestic and industrial systems in which service continuity is essential.


This delay makes the AP-R residual current devices especially suited for installations involving motor starters/variable speed drives, fluorescent lamps or IT/electronic equipment.

The use of multiple electronic reactors for the supply of fluorescent lamps instead generates permanent leakage currents and inrush currents that can cause nuisance tripping of a standard residual current circuit breaker. IT system loads and other electronic equipment (e.g. dimmers, computers, inverters) with capacitive input filters connected between the phases and ground can also generate permanent earth leakage currents whose sum may provoke the nuisance tripping of a standard residual current circuit breaker. For these situations, the AP-R breakers allow a greater number of devices to be connected to the installation.

Frequency converters include a rectifier section and an inverter section.


In case of fault within a single-phase frequency converter AP-R type RCDs provide complete protection, because an earth fault occurring downstream the inverter, produces an earth fault current with multi-frequency shape with high amount of harmonics.

While, in case of fault within a three-phase frequency converter, B type RCDs ensure complete protection because in case of insulation fault between the rectifier and the inverter or downstream the inverter we can have a smooth DC earth fault current.



RCDs technical details

Unwanted tripping - AP-R solution (high immunity)



Compared with standard type breakers, AP-R residual current breakers are therefore characterised, for any given sensibility, by:

- Higher residual trip current
- Tripping time delay
- Better resistance to overvoltages, harmonics and impulse disturbances.

Regulations

The tests set out in the IEC 61008 and IEC 61009 standards verify the resistance of residual current breakers to unwanted tripping provoked by operation overvoltages, using a ring wave impulse shape of 0.5 µs/100 kHz. All

residual current circuit-breakers are required to pass this test with a peak current value of 200 A.

For what concerns atmospheric overvoltages, the IEC 61008 and 61009 standards prescribe the 8/20 µs surge test with a 3000 A peak current, but limit the requirement to residual current devices classified as selective; no test is required for other types.

The ABB range of AP-R anti-nuisance tripping breakers and blocks pass the general 0.5 µs/100 kHz ring wave test and also withstand the 8/20 µs impulse test with the same peak current of 3000 A prescribed for selective devices.

	A or AC	AP-R	B	Selective
Resistance to unwanted tripping caused by network disturbances with wave shape (0.5 µs/100 kHz)	250	250	200	250
Resistance to nuisance tripping due to overvoltages (operational or atmospheric) peak (8/20 wave)	250	3000	3000	5000

RCDs technical details


Unwanted tripping - F2C-ARH solution

The F2C-ARH is an auto-reclosing device particularly suited for household and similar uses. It doesn't require a separate low voltage power supply, and can be supplied by the associated RCCBs (2 pole RCCBs up to 63 A – 30 mA) at the 230 V a.c. rated voltage.

Another feature that makes the product ideal for home applications is an internal control unit that checks there are


no insulation faults in the system before allowing the RCCB to reclose.

This ensures that reclosing occurs only in case of unwanted tripping of the RCCB (i.e. overvoltages induced by electrical storms), thus assuring continuity of power supply also in these situations.



Situation of temporary over-voltage,
for example caused by a lightning,
that causes RCCB's untimely tripping.

When the RCCB operates in presence of an effective insulation fault, the auto-reclosing device doesn't allow its reclosing and guarantees the system insulation.



Situation of permanent earth fault
that causes RCCB's tripping.

RCDs technical details

Type B RCDs

Type B RCDs

In industrial electrical applications it is more and more common to use devices where in the event of an earth fault current unidirectional direct currents or currents with a minimum residual ripple which flow through the PE conductor can emerge. These devices can be for example inverters, medical equipment (e.g. x-ray equipment and CAT), or UPS.

Type A RCDs sensitive to pulsating currents (in addition to sinusoidal currents detected by RDCs of type AC as well) cannot detect and break these earth fault direct currents or currents with a minimum level residual ripple. In case there are electrical appliances which generate this type of currents in the event of an earth fault the use of RCDs of type AC or type A would not be appropriate.

In order to meet these new demands, type B RCDs have been designed (which are able to detect the same earth fault currents detected by type AC and type A RCDs). This type of RCD (type B) is not mentioned in the reference standards for RCDs (IEC 61008-1 and IEC 61009-1).

An international standard has been introduced in 2007 an it specifies additional requirements for B type RCDs.

This new standard, IEC 62423, can only be referred to together with IEC 61008-1 (for RCCBs) and IEC 61009-1 (for RCD-blocks and RCBOs), this means that B type RCDs have to be compliant to all the prescriptions of IEC 61008/9.

As already said, type B RCDs are not only sensitive to alternating and pulsating earth fault currents with DC components at a frequency of 50/60 Hz (type A), but they are also sensitive to:

- alternating currents up to a frequency of 1000 Hz;
- alternating and/or pulsating currents with DC components overlapping with a direct current;
- earth fault currents generated by a rectifier with two or more phases;
- direct earth fault currents without residual ripple

...independently of the polarity or whether the earth fault current appears suddenly or increases gradually.

Type B RCDs must be marked with the following symbols highlighting the switches' capacity to detect every type of current:   .


RCDs technical details

Type B RCDs

Construction features

Type B RCDs consist of one section for the detection of alternating earth fault currents and unidirectional pulsating earth fault currents, which functions independently of the line voltage. For the detection of direct earth fault currents or currents with a minimum residual ripple, type B RCDs have a second electronic section, the functioning of which depends on the line voltage.

The structure of the product is illustrated in the following diagram.



S Release

M Protection device mechanism

E Electronics for the intervention with direct unidirectional earth fault currents

T Test device

Tr1 Residual current transformer for the detection of sinusoidal earth fault currents

Tr2 Residual current transformer for the detection of direct unidirectional currents.

The residual current transformer Tr1 monitors the presence of pulsating and alternating earth fault currents in the electronic installation while residual current transformer Tr2 measures the direct unidirectional currents. In the event of a fault the second transformer transmits the opening command to the release S via the (printed) circuit board E. In type B RCCBs, the section whose functioning depends on the line voltage is supplied by all three-phase conductors and the neutral, so that the functioning as type B is guaranteed even if there is a voltage only in two of the 4 power conductors. In addition, the supply of the electronic section is sized in such a way that the device can safely intervene even if there is a voltage drop of 70%.


In this way an intervention takes place when direct unidirectional earth fault currents emerge, even in the event of faults in the electric power supply grid, for example if there is no neutral conductor.

Direct or similar earth fault currents


An increasing amount of industrial equipment is supplied by circuits which in the event of a fault generate direct earth fault currents with a very low residual ripple, which can be even less than 10%. For example with direct current supplied motor drives for pumps, elevators, textile machines etc. it is becoming more common to use inverters with a three-phase rectifier bridge.

In the event of an earth fault current the wave of the earth fault is as indicated in the figure below.


Three-phase rectifier bridge




Three-phase wye rectifier



Phase currents



Earth fault current



RCDs technical details

Type B RCDs


F200 B RCCBs provide additional protection against direct contact and are the right choice to ensure maximum system safety thanks to early detection of fault currents with continuous waveforms or high frequencies.

Selection of RCDs. General rules


Type B RCDs are suitable for non-linear circuits that can generate leakages with high direct current ($> 6 \text{ mA}$) and/or high frequency components. Such components can be found in several industrial components and applications that embed or depend on electronics.

The main circuits that can be considered responsible for such leakages and the common applications where Type B could be demanded are:


Circuits containing single and three-phase rectifiers



Circuits containing rectifiers with high levelling capacity




Circuits containing rectifiers with active power factor correction




RCDs technical details

Type B RCDs

Circuits containing continuous voltage generators with no separation from a.c. network



Circuits containing continuous voltage generators



RCDs technical details

Type B RCDs

Immunity to nuisance tripping: advantages of Type B RCCBs

RCDs Type B are advance-designed products that, on one hand, are able to protect from different kinds of faults, regardless of their waveform; on the other hand, they are immune to unwanted trippings.

In order to be such an effective device in terms of protection, every Type B RCD must withstand successfully all the tests provided by the Standards. In the testplan are foreseen several tripping waveforms that are considered to represent the best approximation to a real fault condition in case of non linear circuits.

Tripping waveforms for Type B RCDs

	Residual current form	Limit value of tripping current
Alternating		0,5...1,0 $I_{\Delta n}$
Unidirectional pulsating		0,35...1,4 $I_{\Delta n}$
Unidirectional pulsating with phase angle mode		Cut-off angle 90° from 0,25 to 1,4 $I_{\Delta n}$ Cut-off angle 135° from 0,11 to 1,4 $I_{\Delta n}$
Alternating sinusoidal residual current plus pulsating dc current, suddenly applied or smoothly increasing		Max. 1,4 $I_{\Delta n}$ + 0,4 $I_{\Delta n}$ d.c.
Unidirectional pulsating superimposed on direct		Max. 1,4 $I_{\Delta n}$ + 0,4 $I_{\Delta n}$ d.c.
Multi-frequency		From 0,5 to 1,4 $I_{\Delta n}$
Two-phase rectified		From 0,5 to 2,0 $I_{\Delta n}$
Three-phase rectified		
Direct without ripple		
Alternating up to 1 kHz		Current frequency 150 Hz from 0,5 to 2,4 $I_{\Delta n}$ Current frequency 400 Hz from 0,5 to 6 $I_{\Delta n}$ Current frequency 1000 Hz from 0,5 to 14 $I_{\Delta n}$



RCDs technical details

Type B RCDs

To prove their immunity to unwanted tripping, Type B residual current devices must successfully pass further severe tests such as:

- 8/20 μ s impulse up to 3000 A (s. fig. 1);
- 10 ms impulse up to 10 $I_{\Delta n}$ (s. fig. 2).

These tests emulate the conditions that an RCD must withstand in case of overvoltages or leakages due to EMC filters or electronic loads. Type B and devices can be considered suitable for all difficult applications, not only in terms of protection, but of operational continuity as well.




Tripping times				
Type	Fault currents	Tripping time at		
	Alternating currents	1 x $I_{\Delta n}$	2 x $I_{\Delta n}$	5 x $I_{\Delta n}$
	Pulsating DC currents	1,4 x $I_{\Delta n}$	2 x 1,4 x $I_{\Delta n}$	5 x 1,4 x $I_{\Delta n}$
	Smooth DC currents	2 x $I_{\Delta n}$	2 x 2 x $I_{\Delta n}$	5 x 2 x $I_{\Delta n}$
Standard or short-time delay		Max. 0,3 s	Max. 0,15 s	Max. 0,04 s
Selectiv S		0,13 - 0,5 s	0,06 - 0,2 s	0,05 - 0,15 s
				0,04 - 0,15 s

RCDs technical details


Type B RCDs

Variation of residual current tripping thresholds according to frequency

F200 B 30 mA




F200 B 300 mA



RCDs technical details

Type B RCDs

F200 B 500 mA




RCDs technical details


Type B RCDs

F200 B high ratings

F204 B 30 mA




F204 B 300 mA



RCDs technical details

Type B RCDs

F204 B 500 mA




RCDs technical details

Use of 4P RCCBs in 3-phase system without neutral pole

Use of a 4P RCCB in a 3-phase circuit without neutral


The test button circuit of these RCCBs 4P F 200, regardless of the rating, is wired inside the device between terminal 5/6 and 7/8/N as indicated below, and has been sized for an operating voltage between 110V (170V for the 30mA version according to EN standard) and 254 V (110 and 277 V according to UL 1053).



In case of installation in a 3 phase circuit without neutral, if the concatenate voltage is between 110V (170V for the 30mA version according to EN standard) and 254 V (277 V according to UL 1053) for the correct working of the test button there are two possible solutions:

- 1) To connect the 3 phases to the terminals 3/4 5/6 7/8/N and the terminals 4/3 6/5 8/7/N (supply and load side respectively)
- 2) To connect the 3 phases normally (supply to terminals 1/2 3/4 5/6 and load to terminals 2/1 4/3 6/5) and to bridge terminal 1/2 and 7/8/N in order to bring to the terminal 7/8/N the potential of the first phase. In this way the test button is supplied with the phases' concatenate voltage.

If the circuit is supplied with a concatenate voltage higher than 254 V, as in the typical case of 3 phase net with concatenate voltage of 400 V - or 480 V according to UL 1053 - (and voltage between phase and neutral of 230 V or 277 V according to UL 1053), it is not possible to use these connections because the circuit of the test button will be supplied at 400 V and could be damaged by this voltage.



$I_{\Delta n}$ [A]	Rest [Ω]
0.03	3300*
0.03	3900
0.1	1000
0.3	330
0.5	200

* Only for IEC range and 125 A right-sided ratings


In order to allow the correct operation of the test button also in 3 phase nets at 400 V - 480 V according to UL 1053 - (concatenate voltage) it is necessary to connect normally the phases (supply to terminals 1/2 3/4 5/6 and load to terminals 2/1 4/3 6/5) and to bridge terminal 4/3 and 8/7/N by mean of an electric resistance as indicated above.

In this way the test button circuit is fed at 400 V - 480 V according to UL 1053 - but for example in an IEC compliant RCCB with $I_{\Delta n}=0.03$ A there will be the Rest=3.3 kOhm resistance in series to the test circuit resistance. Rest will cause a voltage drop that leaves in the test circuit a voltage less than 254 V - 277 V according to UL 1053. Rest resistance must have a power loss higher than 4 W.

In the normal operation of the RCCB (test circuit opened) the Rest resistance is not fed so it does not cause any power loss.

The solution RCCBs with neutral pole on left side

The test button circuit of these RCCBs is wired inside the device between terminal 3/4 and 5/6 as indicated below, and it has been sized for an operating voltage between 195 V and 440 V - 480 V. In case of a three phase system without neutral with concatenate voltage between phases of 230 V or 400 V - 277 V or 480 V - it is enough to connect the 3 phases normally (supply to terminals 1/2 3/4 5/6 and load to terminals 2/1 4/3 6/5) without any bridge.




RCDs technical details

Operating voltage of test button

Operating voltage of test button


The operation of RCDs depends on the maximum and minimum operating voltage of the test button.



Maximum and minimum operating voltage of DS201 test button

DS201
Ut = 110-264 V;
for 30mA: Ut = 170-264V

DS201 M 110V
Ut = 110-264V






Maximum and minimum operating voltage of DS 200 and DDA 200 test button

DDA 202 and DS 202
In = 25-40 A
Ut = 110 - 254 V;
for 30mA: Ut = 170-254V

DDA 203 and DS 203
In = 25-40 A
Ut = 195 - 440 V;
for 30mA: Ut = 300-440V




DDA 204 and DS 204
In = 25-40 A
Ut = 195 - 440 V;
for 30mA: Ut = 300-440V



DDA 202 and DS 202
In = 63 A
Ut = 110 - 254 V;
for 30mA: Ut = 170-254V

DDA 203 and DS 203
In = 63 A
Ut = 195 - 440 V;
for 30mA: Ut = 300-440V

DDA 204 and DS 204
In = 63 A
Ut = 195 - 440 V;
for 30mA: Ut = 300-440V



RCDs technical details


Operating voltage of test button

Maximum and minimum operating voltage of DDA 200, special version 110 V

DDA 202 110 V

$I_n = 25-40-63 A$


$U_t = 110-254 V$



DDA 203 110 V

$I_n = 40 A$


$U_t = 110-254 V$



DDA 203 110 V

$I_n = 63 A$


$U_t = 110-254 V$



DDA 204 110 V

$I_n = 63 A$


$U_t = 110-254 V$



Maximum and minimum operating voltage of the DS203NC

DS203NC

$U_t = 195-440 V$ (300-440V for 30 mA)



RCDs technical details


Operating voltage of test button

Maximum and minimum operating voltage of DDA 200, special version 400 V

DDA 202

In = 63 A

Ut = 400 V




Maximum and minimum operating voltage of DDA 200 B type test button

DDA 202 B

In = 63 A

Ut=195-254 V (170-254 V for

30 mA)




DDA 203 B

In = 63 A

Ut=310-440 V (300-440 V

for 30 mA)




DDA 204 B

In = 63 A

Ut=195-254 V (300-440 V

for 30 mA)




Maximum and minimum operating voltage of DDA 200 AE test button

DDA 202 AE

In = 63 A


Ut = 184-264 V



DDA 203 AE

In = 63 A


Ut = 310-440 V



DDA 204 AE

In = 63 A

Ut = 184-264 V



RCDs technical details

Operating voltage of test button

Maximum and minimum operating voltage of F 200 test button


F 202

$I_n = \leq 100 A$

$U_t = 110 - 254 V$

for 30mA^①: $U_t = 170 - 254 V$

1/2 3/4



2/1 4/3


F 204 neutral on right

$I_n = \leq 100 A$

$U_t = 110 - 254 V$

for 30mA^①: $U_t = 170 - 254 V$

1/2 3/4 5/6 7/8/N




2/1 4/3 6/5 8/7/N

F 204 neutral on left

$I_n = \leq 100 A$

$U_t=195-440V$; for 30mA: $U_t = 250-440V$

R	S	T
7/8/N	1/2	3/4
5/6		



8/7/N 2/1 4/3 6/5

For use in 3-phases circuit without neutral at 400 V it is possible to connect the three phases R, S and T like in the figure.


F 204 neutral on right

$I_n = 125 A$

$U_t = 185 - 440 V$

for 30mA^①: $U_t = 150 - 250 V$

1/2 3/4 5/6 7/8/N



ZCSG40496F00202

① Only for versions with marking according to EN 61008-1;EN 61008-2-1


F 204 neutral on left

$I_n = 125 A$

$U_t=185 - 440V$

for 30mA: $U_t = 250 - 440 V$

7/8/N 1/2 3/4 5/6




8/7/N 2/1 4/3 6/5

F202 110V

$I_n \leq 100 A$

$U_t = 110 - 254 V$

1/2 3/4




2/1 4/3

F 204 110V

$I_n \leq 100 A$

$U_t = 110 - 254 V$

1/2 3/4 5/6 7/8/N



2/1 4/3 6/5 8/7/N

RCDs technical details

Operating voltage of test button


Maximum and minimum operating voltage of DDA 800 and DS800 test button

DDA 802

DS802

$IN \leq 125 A$

$Ut = 195-690 V$




DDA 803

DS803

$IN \leq 125 A$

$Ut = 195-690 V$




DDA 804

DS804

$IN \leq 125 A$

$Ut = 195-690 V$



RCDs technical details


RD2 residual current relays

RD2 residual current monitors

They operate combined with appropriate toroidal transformers (in 9 different diameters).

The relay can command the tripping of the protection circuit-breaker release, thus opening the circuit.

According to the IEC 62020 Standard, these relays are "A Type". They are sensitive to leakage sinusoidal currents and to leakage pulsating currents with direct components. Thus they can be defined as "A type".



More technical characteristics

Calibration tolerances		- sensitivity	$75\% \pm 10\%$
		- time	$75\% \pm 10\%$
Power consumption	[W]	0.45 at 48 V AC/DC	
		1.2 at 110 V AC/DC	
		3.4 at 230 V AC	
		11 at 400 V AC	
Dielectric test voltage at ind. freq. for 1 min.	[kV]	2.5	
Max. peak current with 8/20 µs wave	[A]	5000	
Installation position		any	
Protection degree		IP20	

RCDs technical details

RD3 residual current relays

RD3 electronic residual current relay

RD3 is a residual current device that in combination with a toroidal transformer is able to detect and evaluate earth fault current. If used in combination with a shunt-trip or undervoltage release, it can realize the opening of a circuit breaker ensuring earth leakage current protection.

RD3



RD3M




RD3P



Setting of residual operating current and trip time delay.

Using the rotary selectors on the front of the device, it is possible to adjust the residual operating current and the trip time delay.



Adjustment of residual operating current (Δn [A]) and trip time delay (Δt [s]).

Main features

Pre-alarm

Placing the dip-switch in the ON position enables the pre-alarm function: the output contact on terminals 7 8 9 will change state in the event of a residual current exceeding 60% ID .

Autoreset

Placing the dip-switch in the ON position enables the automatic Reset function: the Relay OUTPUT contacts revert to their original state once the fault condition ceases.

Fail-safe

Built into the device (positive safety). In case of absence of supply to the device RD3 the output contact on terminals 10 11 12 will change state as shown in the figures.

RD3



RD3M



RD3P



RCDs technical details

RD3 residual current relays

Indicators

RD3



RD3M





RD3P




Stand by




FAULT



Fault




Absent connection with toroid




Fail-safe - RD3, RD3M, RD3P

Integrated in the device (positive safety). In case of power supply voltage failure of RD3 device, the output contacts numbered 10 11 12 will switch as shown below.




Contacts when the device is OFF





Pre-alarm - RD3P, RD3M

When the dip-switch is set to ON, the prealarm function is activated: the output contact marked by the 7 8 9 terminals will switch in case of a fault detected by the device exceeding 60% Δ .



Autoreset - RD3P

When the dip-switch is set to ON, the automatic Reset function is activated: the output device contact will return to stand-by when the fault condition has been resolved.




RCDs technical details

RD3 residual current relays

Test


To perform the relay test, press the button on the front. The relay can be reset via the front button or a remote button, as shown in the figure:

Test



On RD3P version, a no trip test can also be performed by simultaneously pressing the front test and reset buttons for 3 seconds. In this case, the output contacts will not switch, as shown in the figure below:

Test NO TRIP - RD3P



Associated circuit breakers (and relative releasers)

- Tmax range from T1 to T5, In up to 630 A, Ue up to 690 V, with UVR undervoltage release or SOR shunt opening release
- XT range from XT1 to XT4, In up to 250 A, Ue up to 690 V, with UVR undervoltage release or SOR shunt opening release
- pro M Compact S200 range with In up to 63 A, Ue up to 440 V, with S 2C-A shunt trip or S 2C-UA undervoltage release

Tripping time (RD3 output relay switching time), cumulative time (with associate circuit breakers), non-trip time limit:

RD3: tripping time, cumulative time, non intervention time

Time selection	$I_{\Delta n}$		$2 I_{\Delta n}$		$5 I_{\Delta n}$		$10 I_{\Delta n}$	
	tripping time	cumulative time with associate circuit breaker	tripping time	cumulative time with associate circuit breaker	tripping time	cumulative time with associate circuit breaker	tripping time	cumulative time with associate circuit breaker
Dt [s]	\leq [s]	\leq [s]	\leq [s]	\leq [s]	\leq [s]	\leq [s]	\leq [s]	\leq [s]
0	0.2	0.3	0.12	0.15	0.02	0.04	0.02	0.04
0.06	0.3	0.5	0.17	0.2	0.09	0.15	0.09	0.15
0.2	0.45	0.5	0.45	0.5	0.45	0.5	0.45	0.5
0.3	0.55	0.6	0.55	0.6	0.55	0.6	0.55	0.6
0.5	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
1	1.2	-	1.2	-	1.2	-	1.2	-
2	2.2	-	2.2	-	2.2	-	2.2	-
3	3.2	-	3.2	-	3.2	-	3.2	-
5	5.2	-	5.2	-	5.2	-	5.2	-
10	10.2	-	10.2	-	10.2	-	10.2	-

RCDs technical details

ELR front panel residual current relays

ELR: tripping time, cumulative time, non intervention time

Time selection Δt [s]	$I_{\Delta n}$		$2 I_{\Delta n}$		$5 I_{\Delta n}$		$10 I_{\Delta n}$		
	tripping time \leq [s]	cumulative time with associate circuit breaker \leq [s]	non-intervention time [s]	tripping time \leq [s]	cumulative time with associate circuit breaker \leq [s]	tripping time \leq [s]	cumulative time with associate circuit breaker \leq [s]	tripping time \leq [s]	cumulative time with associate circuit breaker \leq [s]
	0	0.04	0.3	-	0.025	0.15	0.02	0.04	0.02
0.06	0.1	0.5	0.06	0.08	0.2	0.08	0.15	0.08	0.15
0.2	0.16 +15%	-	0.2	0.15 +15%	-	0.15 +15%	-	0.15 +15%	-
0.3	0.3 +15%	-	0.3	0.3 +15%	-	0.3 +15%	-	0.3 +15%	-
0.5	0.5 +15%	-	0.5	0.5 +15%	-	0.5 +15%	-	0.5 +15%	-
1	1 +15%	-	1	1 +15%	-	1 +15%	-	1 +15%	-
2	2 +15%	-	2	2 +15%	-	2 +15%	-	2 +15%	-
3	3 +15%	-	3	3 +15%	-	3 +15%	-	3 +15%	-
5	5 +15%	-	5	5 +15%	-	5 +15%	-	5 +15%	-

RCDs technical details

Toroidal transformers

Toroidal transformers

The choice of toroidal transformers is made according to the useful diameter and the minimum value of the leakage current to be detected.

Technical features of the toroidal transformers

Type	Toroid useful diameter [mm]	Max rated current [A] ⁽¹⁾	Min measurable current [mA]	Maximum capacity [A]
TRM	29	65	30	160
TR1	35	75	30	250
TR2	60	85	30	400
TR3	80	160	100	800
TR4	110	250	100	1250
TR4/A	110	250	300	1250
TR160	160	400	300	2000
TR160/A	160	400	500	2000
TR5	210	630	300	3200
TR5/A	210	630	500	3200
TR6	300	630	500	5000
TR6/A	300	630	1000	5000

(1) Toroidal transformers selection for use with ELR/RD3 according to IEC/ EN 60947-2 Annex M in combination with MCBs S200 range and MCCBs Tmax range up to T5 (630 A) and XT range up to XT4 (250 A)

RCDs technical details

Toroidal transformers

Technical characteristics

	TRM	TR1	TR2	TR3	TR4	TR4A	TR160	TR160A	TR5	TR5A	TR6	TR6A
Core		closed	closed	closed	closed	open	closed	open	closed	open	closed	open
Available internal diameter	[mm]	29	35	60	80	110	110	160	160	210	210	300
Weight	[kg]	0.17	0.22	0.28	0.45	0.52	0.6	1.35	1.6	1.45	1.85	2.1
Minimum measurable current	[mA]	30	30	30	100	100	300	300	500	300	500	1000
Installation position		Any										
Operating temperature	[°C]	-10...+70										
Storage temperature	[°C]	-20...+80										
Transformation ratio		500/1										
Dielectric test voltage at industrial freq. for 1 min.	[kV]	2.5										
Max. insulating voltage	[V a.c.]	1000										
Max. thermal overload	[kA]	40/1 sec.										
Connections		Screw terminal boards, max. section 2.5 mm ²										
Protection degree		IP20										

Generality

They must be mounted with residual current monitors upstream the lines or loads to be protected; all active conductors (phases and neutral) of single-phase as well as of three-phases lines must pass through them.

In this way these devices perform the vector sum of line currents detecting the possible homopolar differential currents that leak to earth: their core of sheet iron has high magnetic properties that allow to detect even very low leakage currents.

The choice of a toroidal transformer depends on the conductor or on the bar to be used.

It is suggested to use the open versions in case of revamping or upgrading of an existing installation.

Installation

All active conductors can be introduced in the toroidal transformers without the need of respecting any specific sense of introduction (P1-P2 or P2-P1). The output signal

must be picked up from terminals 1 (S1) and 2 (S2) and connected to the residual current monitor, while terminals 3 and 4 must be connected to the test output of those relays of FPP range with this function. With RD2 they must remain disconnected. For this connection it is better to use twisted or shielded cables, possibly far from busbars. The minimum recommended section of connection cables should have a maximum resistance of 3 Ω; anyway consider a maximum length of connection of 20 m for 0.5 mm² and of 100 m for 2.5 mm².

For versions with openable core it is necessary to control that the contact surface of the two semi-cores is clean, that bolts are tight and that connection cables connections on both sides are intact.

Connection cables with metallic shielding or armor must be earthed downstream the toroidal transformer; if they run within the transformer they must be earthed in the opposite direction.

Electrical installation solutions for buildings – Technical details

Arc Fault Detection Devices

Index

Functions and classification criteria for AFDD 3/2

S-ARC1

Power loss, derating and performance in altitude	3/4
Specific let-through energy I^2t S-ARC1 and S-ARC1 M	3/5
Ipeak S-ARC1 and S-ARC1 M	3/6
Coordination tables: S-ARC1, S-ARC1M back-up	3/7
Coordination tables: S-ARC1, S-ARC1M selectivity	3/9

DS-ARC1

Power loss, derating and performance in altitude	3/14
Specific let-through energy I^2t DS-ARC1 and DS-ARC1 M	3/15
Ipeak S-ARC1 and DS-ARC1 M	3/16
Coordination tables: DS-ARC1, DS-ARC1M back-up	3/17
Coordination tables: DS-ARC1, DS-ARC1M selectivity	3/19

AFDD technical details

Functions and classification criteria for AFDD

Functions and classification criteria for AFDD

An AFDD (Arc Fault Detection Device) according to the product standard "IEC 62606 - General requirements for Arc Fault Detection Devices" is a device intended to mitigate the effects of arcing faults by disconnecting the circuit when an arc fault is detected: this product standard is partially derived from the UL 1699 standard.

Three different type of products are described in IEC 62606 standard:


- **AFDD in series with protection device:**
AFDD as one single device, comprising an AFD unit and opening means and intended to be connected in series with a suitable short circuit protective device declared by the manufacturer complying with one or more of the following standards IEC 60898-1, IEC 61009-1 or IEC 60269 series.
- **Integrated solution:**
AFDD as one single device, comprising an AFD unit integrated in a protective device complying with one or more of the following standards IEC 60898-1, IEC 61008-1, IEC 61009-1 or IEC 62423.
- **AFDD + protection device assembled on site:**
AFDD according to Annex D, comprised of an AFD unit and a declared protective device, intended to be assembled on site.

Different levels of protection

RCDs are recognized efficient to reduce the risk of fire by detection of leakage current and arcing to ground as a consequence of tracking currents within an electrical installation. For this reason RCDs can detect only earth arc faults.

In case of parallel arc faults MCBs and fuses can trip only if their intervention time-current curves are compatible with the values of the current of the arc faults, thus the trip is not instantaneous.

AFDD can guarantee protection against all types of arc faults:




Earth arc fault

current is flowing from active conductor to the earth



Series arc fault

current is flowing within one conductor of the final circuit



Parallel arc fault

current is flowing between active conductors in parallel with the load of the circuit

Series arc faults are generally too weak to be detected by MCBs.


MCBs can not detect earth arc faults because the current values are in general rather low.

In order to ensure a complete protection against arc faults, it is required the installation of an AFDD.

AFDD technical details

Functions and classification criteria for AFDD


01 MCB



Protection against:

- Overcurrent (short circuits, overload)


01 S-ARC1 AFDD with integrated MCB



Protection against:

- Overcurrent (short circuits, overload)
- Series, parallel and earth arc faults


02 RCCB



Protection against:

- Earth fault currents
- Earth arc faults

02 DS-ARC1 AFDD with integrated RCBO




Protection against:

- Overcurrent (short circuits, overload)
- Earth fault currents
- Series, parallel and earth arc faults



Maximum Protection

03 RCBO



Protection against:

- Overcurrent (short circuits, overload)
- Earth fault currents
- Earth arc faults

AFDD technical details

Power loss, derating and performance in altitude

Voltage drop, Internal resistance, Power loss and own consumption for S-ARC1 series

In [A]	Voltage drop [mV]	Internal resistance [mΩ]	Power loss [W]	Own consumption [W]
6	380	63.3	2.3	0.5
10	203	20.3	2.0	0.5
13	166	12.8	2.2	0.5
16	175	10.9	2.8	0.5
20	182	9.1	3.6	0.5
25	141	5.6	3.5	0.5
32	150	4.7	4.8	0.5
40	155	3.9	6.2	0.5

Derating in temperature for S-ARC1 series

Max operating current depending on the ambient temperature of a circuit breaker in load circuit of characteristics type B and C.

Daily average ambient temperature is intended to be $\leq +35^{\circ}\text{C}$.

In (A)	Temperature ($^{\circ}\text{C}$)									
	-25	-20	0	10	20	25	30	40	50	55
6	7.2	6.8	6.4	6.3	6.1	6.0	6.0	6.0	5.8	5.8
10	12.2	11.9	10.8	10.7	10.5	10.2	10.0	10.0	9.8	9.6
13	15.6	15.2	14.2	13.8	13.4	13.2	13.0	12.9	12.7	12.6
16	19.5	18.9	17.9	17.3	16.7	16.3	16.0	15.8	15.5	15.4
20	24.4	24.0	22.4	21.6	21.0	20.4	20.0	19.8	19.5	19.4
25	29.5	28.9	28.0	27.0	26.2	25.5	25.0	24.6	24.2	24.0
32	36.5	35.9	35.0	33.9	33.0	32.3	32.0	31.1	30.4	30.0
40	47.0	46.4	43.0	42.1	41.1	40.4	40.0	38.9	38.0	37.1

Performance in altitude for S-ARC1 series

Elevation [m]	3000	4000	5000	6000
Rated Current [A]	$0,96 \times \text{In}$	$0,94 \times \text{In}$	$0,92 \times \text{In}$	$0,90 \times \text{In}$
Rated Voltage [V]	$0,877 \times \text{Un}$	$0,775 \times \text{Un}$	$0,676 \times \text{Un}$	$0,588 \times \text{Un}$





For altitude higher than 3.000 m the isolating characteristic is no longer available.

Influence of adjacent devices

Number of devices	Correction factor
1	1
3	0,92
5	0,88
7	0,85
9	0,84

AFDD technical details

Specific let-through energy I^2t S-ARC1 and S-ARC1 M



—
01 I^2t
S-ARC1 Tripping
Characteristics B





—
02 I^2t
S-ARC1 Tripping
Characteristics C

—
03 I^2t
S-ARC1 M Tripping
Characteristics B

—
04 I^2t
S-ARC1 M Tripping
Characteristics C

AFDD technical details

Ipeak S-ARC1 and S-ARC1 M



—
01 Ipeak
S-ARC1 Tripping
Characteristics B

—
02 Ipeak
S-ARC1 Tripping
Characteristics C

—
03 Ipeak
S-ARC1 M Tripping
Characteristics B

—
04 Ipeak
S-ARC1 M Tripping
Characteristics C

AFDD technical details

Coordination tables: S-ARC1, S-ARC1M back-up

Fuses - S-ARC1, S-ARC1 M@230/230/240V

Supply S.		gL/gG						
Load S.	Icu [kA]	In[A]	25	40	50	63	80	100
S-ARC1, S-ARC1 M B,C	7.5 and 10	6...40	35	25	20	15	10	10

MCCB@415V - S-ARC1, S-ARC1 M@230/240V

Upstream			XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4	XT2	XT4	
Char			B	C	N	N	N	N	S	S	S	S	H	H	H	L	L	V	V	
Down-stream	Icu [kA]	In[A]	18	25	36	36	36	36	50	50	50	50	70	70	70	120	120	150	150	
S-ARC1	B,C	7.5	6...25	16	16	16	20	10	10	16	20	10	10	16	20	10	20	10	20	10
			32, 40	10	10	10	16	10	10	10	16	10	10	10	16	10	16	10	16	10
S-ARC1M	B,C	10	6...16	16	16	16	25	16	25	16	25	16	25	16	25	25	25	25	25	25
			20, 25				25	16	25	16	25	16	25	16	25	16	25	16	25	16
			32, 40	16	16	16	16	16	10	16	16	16	10	16	16	10	16	10	16	10

MCCB @415V - S-ARC1 , S-ARC1 M@230/240V

S800S - S-ARC1, S-ARC1 M@ 230/240V

Supply S.		S800S									
Char		B,C,D,K									
Load S.	Icu [kA]	50									
S-ARC1	B,C	7.5	In[A]	25	32	40	50	63	80	100	125
			6...16	50	40	25	25	18	15	15	15
			20		40	25	25	18	15	15	15
			25			25	25	18	15	15	15
			32				25	18	15	15	15
			40					18	15	15	15
S-ARC1M	B,C	10	6...16	50	50	50	50	50	50	50	50
			20		50	50	50	50	50	50	50
			25			50	50	50	50	50	50
			32				50	50	50	50	50
			40					50	50	50	50

S800N - S-ARC1, S-ARC1 M@ 230/240V

Supply S.				S800N							
Char				B,C,D							
Load S.	Icu [kA]			36							
S-ARC1	B,C	7.5	In[A]	25	32	40	50	63	80	100	125
			6...16	36	36	25	25	18	15	15	15
			20		36	25	25	18	15	15	15
			25			25	25	18	15	15	15
			32				25	18	15	15	15
			40					18	15	15	15
S-ARC1M	B,C	10	6...16	36	36	36	36	36	36	36	36
			20		36	36	36	36	36	36	36
			25			36	36	36	36	36	36
			32				36	36	36	36	36
			40					36	36	36	36

AFDD technical details

Coordination tables: S-ARC1, S-ARC1 M back-up

S800C - S-ARC1, S-ARC1 M@ 230/240V

		Supply S.		S800C					
		Char		B,C,D,K					
Load S.		Icu [kA]		25					
S-ARC1	B,C	7.5	In[A]	25	32	40	50	63	80
			6...16	25	25	25	25	18	15
			20		25	25	25	18	15
			25		25	25	25	18	15
			32			25	18	15	15
			40				18	15	15
S-ARC1M	B,C	10	6...16	25	25	25	25	25	25
			20		25	25	25	25	25
			25		25	25	25	25	25
			32			25	25	25	25
			40				25	25	25

S800B - S-ARC1, S-ARC M@ 230/240V

		Supply S.		S800B					
		Char		B,C,D,K					
Load S.		Icu [kA]		25					
S-ARC1	B,C	7.5	In[A]	32	40	50	63	80	100
			6...20	16	16	16	16	15	15
			25		16	16	16	15	15
			32			16	16	15	15
			40				16	15	15
			6...20	16	16	16	16	16	16
S-ARC1M	B,C	10	25		16	16	16	16	16
			32			16	16	16	16
			40				16	16	16

*Only S800B B,C

S200 - S-ARC1, S-ARC1 M@230/240V

		Supply S.		S200	S200M	S200P	S200P
		Char		B-C	B,C	B,C	B,C
Load S.		Icu [kA]		20	25	40	25
S-ARC1, S-ARC1 M	B,C	7.5 and 10	In[A]	0.5..63	0.5...63	0.5...25	32
			6...20	20	25	40	25

DS201 - S-ARC1, S-ARC1 M @230/240V

		Supply S.		DS201	
		Char		B,C	
Load S.		In[A]		2...40	
S-ARC1, S-ARC1 M	B,C	6...40	Icu [kA]		10
			7.5 and 10		10

AFDD technical details

Coordination tables: S-ARC1, S-ARC1M selectivity

Fuse gL/gG- S-ARC1, S-ARC M @ 230/400V

Load S.	Char	Icu [kA]	Supply S. Fuse gL/gG								
			In[A]	25	32	40	50	63	80	100	125
S-ARC1	B,C	7.5	6	1	1.5	4	4.5	T	T	T	T
			10		1.2	3.5	4	T	T	T	T
			13		1	3	3.5	5	T	T	T
			16		1	3	3.5	5	T	T	T
			20		1	3	3.5	5	T	T	T
			25		1	2	3	4.5	T	T	T
			32		1	2	3	4.5	5	T	T
			40			1.5	2.5	4	5	6.5	T
S-ARC1M	B,C	10	6	1	1.5	4	4.5	7	T	T	T
			10		1.2	3.5	4	6	T	T	T
			13		1	3	3.5	5	T	T	T
			16		1	3	3.5	5	T	T	T
			20		1	3	3.5	5	8	T	T
			25		1	2	3	4.5	6.5	9	T
			32		1	2	3	4.5	5	8	T
			40			1.5	2.5	4	5	6.5	9

MCCB@415V - S-ARC1, S-ARC1 M @230/240V

Load S.	Char	Icu [kA]	Supply S.											
			XT1											
			Version	B,C,N,S,H										
Release	TM													
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160
S-ARC1	B,C	7.5	6	T	T	T	T	T	T	T	T	T	T	
			10		3	3	3	4.5	T	T	T	T	T	
			13				3	4.5	5	T	T	T	T	
			16				3	4.5	5	T	T	T	T	
			20				3	5	T	T	T	T	T	
			25					5	T	T	T	T	T	
			32						T	T	T	T	T	
			40						T	T	T	T	T	
S-ARC1M	B,C	10	6	6	6	6	6	6	T	T	T	T	T	
			10		3	3	3	4.5	7.5	8.5	T	T	T	
			13				3	4.5	5	7.5	T	T	T	
			16				3	4.5	5	7.5	T	T	T	
			20				3	5	6	T	T	T	T	
			25					5	6	T	T	T	T	
			32						6	7.5	T	T	T	
			40						7.5	T	T	T	T	

AFDD technical details

Coordination tables: S-ARC1, S-ARC1 M selectivity

MCCB@415V - S-ARC1, S-ARC1 M @230/240V

Load S.	Char	Icu [kA]	Supply S.												XT2					
			Version												N,S,H,L,V					
			Release												TM					
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160	10	25	63	100	160	
S-ARC1	B,C	7.5	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
			10		3 ¹	3	3	3	4.5	T	T	T	T	T	T	T	T	T		
			13			3 ¹	3	4.5	5	T	T	T	T	T		T	T	T		
			16			3 ¹	3	4.5	5	T	T	T	T	T		T	T	T		
			20				3 ¹	3	5	T	T	T	T	T		T	T	T		
			25					3.1	5	6	T	T	T	T		T	T	T		
			32					3.1		T	T	T	T	T		T	T	T		
			40							T	T	T	T	T		T	T			
S-ARC1M	B,C	10	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T		
			10		3 ¹	3	3	3	4.5	7.5	8.5	T	T	T	T	T	T	T		
			13			3 ¹	3	4.5	5	7.5	T	T	T	T		T	T	T		
			16			3 ¹	3	4.5	5	7.5	T	T	T	T		T	T	T		
			20				3 ¹	3	5	6	T	T	T	T		T	T	T		
			25					3.1	5	6	T	T	T	T		T	T	T		
			32					3.1		6	7.5	T	T	T		T	T	T		
			40						6	7.5	T	T	T	T		T	T			

¹ Value valid in case of Supply S. breaker only magnetic

MCCB@415V - S-ARC1, S-ARC1 M @230/240V

Load S.	Char	Icu [kA]	Supply S.												XT3					
			Version												N,S					
			Release												TM					
Load S.	Char	Icu [kA]	In[A]	63	80	100	125	160	200	250										
S-ARC1	B,C	7.5	6	T	T	T	T	T	T	T					T	T				
			10	T	T	T	T	T	T	T					T	T				
			13	5	T	T	T	T	T	T					T	T				
			16	5	T	T	T	T	T	T					T	T				
			20	5	T	T	T	T	T	T					T	T				
			25	5	6	T	T	T	T	T					T	T				
			32		6	7.5	T	T	T	T					T	T				
			40		6 ¹	7.5	T	T	T	T					T	T				
S-ARC1M	B,C	10	6	T	T	T	T	T	T	T					T	T				
			10	7.5	8.5	T	T	T	T	T					T	T				
			13	5	7.5	T	T	T	T	T					T	T				
			16	5	7.5	T	T	T	T	T					T	T				
			20	5	6	T	T	T	T	T					T	T				
			25	5	6	T	T	T	T	T					T	T				
			32		6	7.5	T	T	T	T					T	T				
			40		6 ¹	7.5	T	T	T	T					T	T				

¹ Value valid in case of Supply S. breaker only magnetic

AFDD technical details

Coordination tables: S-ARC1, S-ARC1 M selectivity

MCCB@415V - S-ARC1, S-ARC1 M @230/240V

			Supply S.												XT4								
			Version												N,S,H,L,V								
			Release												TM								EL
Load S.	Char	Icu [kA]	In[A]	20	25	32	40	50	63	80	100	125	160	200	225	250	40	63	100	160	250		
S-ARC1	B,C	7.5	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10	3 ¹	3	3	3	4.5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	
			13		3 ¹	3	4.5	5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	
			16		3 ¹	3	4.5	5	T	T	T	T	T	T	T	T	3	T	T	T	T	T	
			20		3 ¹		3	5	T	T	T	T	T	T	T	T		T	T	T	T	T	
			25				3 ¹	5	6	T	T	T	T	T	T	T		T	T	T	T	T	
			32				3 ¹		6	7.5	T	T	T	T	T	T		T	T	T	T	T	
			40					6	7.5	T	T	T	T	T	T	T		T	T	T	T	T	
S-ARC1 M	B,C	10	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10	3 ¹	3	3	3	4.5	7.5	8.5	T	T	T	T	T	T	3	T	T	T	T	T	
			13		3 ¹	3	4.5	5	7.5	T	T	T	T	T	T	T	3	T	T	T	T	T	
			16		3 ¹	3	4.5	5	7.5	T	T	T	T	T	T	T	3	T	T	T	T	T	
			20		3 ¹		3	5	6	T	T	T	T	T	T	T		T	T	T	T	T	
			25				3 ¹	5	6	T	T	T	T	T	T	T		T	T	T	T	T	
			32				3 ¹		6	7.5	T	T	T	T	T	T		T	T	T	T	T	
			40					6	7.5	T	T	T	T	T	T	T		T	T	T	T	T	

¹ Value valid in case of Supply S. breaker only magnetic

MCCB@415V - S-ARC1, S-ARC1 M @230/240V

			Supply S.												T1							
			Version												B,C,N							
			Release												TMD							
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160	160							
S-ARC1	B,C	7.5	6	T	T	T	T	T	T	T	T	T	T	T		T	T	T	T	T	T	T
			10			3	3	3	4.5	T	T	T	T	T		T	T	T	T	T	T	T
			13				3	4.5	5	T	T	T	T	T		T	T	T	T	T	T	T
			16					3	4.5	5	T	T	T	T		T	T	T	T	T	T	T
			20						3	5	T	T	T	T		T	T	T	T	T	T	T
			25							5	T	T	T	T		T	T	T	T	T	T	T
			32							T	T	T	T	T		T	T	T	T	T	T	T
			40								T	T	T	T		T	T	T	T	T	T	T
S-ARC1M	B,C	10	6	6	6	6	6	6	6	T	T	T	T	T		T	T	T	T	T	T	T
			10			3	3	3	4.5	7.5	8.5	T	T	T		T	T	T	T	T	T	T
			13				3	4.5	5	7.5	T	T	T	T		T	T	T	T	T	T	T
			16					3	4.5	5	T	T	T	T		T	T	T	T	T	T	T
			20						3	5	T	T	T	T		T	T	T	T	T	T	T
			25							5	T	T	T	T		T	T	T	T	T	T	T
			32								6	T	T	T		T	T	T	T	T	T	T
			40									7.5	T	T		T	T	T	T	T	T	T

AFDD technical details

Coordination tables: S-ARC1, S-ARC1 M selectivity

MCCB@415V - S-ARC1, S-ARC1 M @230/240V

			Supply S.		T2													
			Version		N,S,H,L													
			Release		TMD										EL			
			Iu[A]		160												160	
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160	25	63	100	160
S-ARC1	B,C	7.5	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			10		3	3	3	3	4.5	T	T	T	T	T	T	T	T	T
			13			3	3	4.5	5	T	T	T	T	T		T	T	T
			16			3	3	4.5	5	T	T	T	T	T		T	T	T
			20				3		3	5	T	T	T	T		T	T	T
			25					3	5	T	T	T	T	T		T	T	T
			32						3		T	T	T	T		T	T	T
			40							T	T	T	T	T		T	T	T
S-ARC1M	B,C	10	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			10		3	3	3	3	4.5	7.5	8.5	T	T	T	T	T	T	T
			13			3	3	4.5	5	7.5	T	T	T	T		T	T	T
			16			3	3	4.5	5	7.5	T	T	T	T		T	T	T
			20				3		3	5	6	T	T	T		T	T	T
			25					3	5	6	T	T	T	T		T	T	T
			32						3	6	T	T	T	T		T	T	T
			40							6	7.5	T	T	T		T	T	T

MCCB@415V - S-ARC1@230/240V

		Supply S.		T3						
		Version		N,S						
		Release		TMD, MA						
		Iu[A]		250						
Load S.	Char	Icu [kA]	In[A]	63	80	100	125	160	200	250
S-ARC1	B,C	7.5	6	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T
			13	5	T	T	T	T	T	T
			16	5	T	T	T	T	T	T
			20	5	T	T	T	T	T	T
			25	5	T	T	T	T	T	T
			32		T	T	T	T	T	T
			40		T	T	T	T	T	T
S-ARC1M	B,C	10	6	T	T	T	T	T	T	T
			10	7.5	8.5	T	T	T	T	T
			13	5	7.5	T	T	T	T	T
			16	5	7.5	T	T	T	T	T
			20	5	6	T	T	T	T	T
			25	5	6	T	T	T	T	T
			32		6	7.5	T	T	T	T
			40		6	7.5	T	T	T	T

S800N/S - S-ARC1 , S- ARC 1 M @230/240V

		Supply S.			S800N-S		
Char					B		
Load S.	Icu [kA]				36-50		
S-ARC1, S-ARC1M	B,C	7.5 and 10	In[A]	50	63	80	100
			6	0.6	1.2	1.6	2.6
			10	0.5	1.1	1.4	2
			13		0.8	1.2	1.7
			16		0.8	1.2	1.7
			20			1	1.5
			25				1.3
			32				1.1
			40				1.6

AFDD technical details

Coordination tables: S-ARC1, S-ARC1 M selectivity

S800N/S-S-ARC1, S-ARC1 M @230/240V

Load S.	Char	Icu [kA]	Supply S.		S800N-S			
			In[A]	40	50	63	80	100
S-ARC1, S-ARC1M	B,C	7.5 and 10	6	0.55	1.1	1.5	2.5	3.6
			10	0.45	1	1.3	1.9	2.8
			13		0.75	1.1	1.6	2.3
			16		0.75	1.1	1.6	2.3
			20			0.9	1.4	1.9
			25				1.2	1.6
			32				1	1.5
			40					1.4
								2.1

S800N/S-S-ARC1, S-ARC1 M @230/240V

Load S.	Char	Icu [kA]	Supply S.		S800 N-S			
			In[A]	25	32	40	50	63
S-ARC1	B,C	7.5	6	32	40	50	63	80
			10	1.3	2	3.2	3.9	T
			13	1.2	1.65	2.6	3.1	T
			16	0.9	1.4	1.8	2.6	T
			20	0.9	1.4	1.8	2.6	T
			25		1.3	1.6	2.2	4.2
			32			1.5	1.9	3.5
			40				1.8	2.8
								4.2
S-ARC1M	B,C	10	6	0.6	1.3	2	3.2	8
			10	0.5	1.2	1.65	2.6	6.2
			13		0.9	1.4	1.8	2.6
			16		0.9	1.4	1.8	2.6
			20			1.3	1.6	2.2
			25				1.5	1.9
			32					3.5
			40					4.5
								5.5

S700 - S-ARC1, S-ARC1 M @230/240V

Load S.	Char	Icu [kA]	Supply S.		S700			
			In[A]	20	25	35	40	50
S-ARC1, S-ARC1M	B,C	7.5 and 10	6	T	T	T	T	T
			10	T	T	T	T	T
			13		T	T	T	T
			16		T	T	T	T
			20		T	T	T	T
			25			T	T	T
			32				T	T
			40					T

AFDD technical details

Power loss, derating and performance in altitude DS-ARC1 and DS-ARC1 M

Derating

Influence of adjacent devices	Number of devices	1	3	5	7	9
	Correction factor	1	0.95	0.92	0.9	0.9


Derating in temperature	In [A]	Temperature [°C]										
		-25	-20	-10	0	10	20	25	30	40	50	55
Max operating current depending on the ambient temperature (daily average $\leq +35^{\circ}\text{C}$) of characteristics type B and C.	6	7.9	7.8	7.7	7.3	6.9	6.3	6.1	6.0	5.9	5.8	5.7
	10	13.3	13.1	12.8	12.3	11.5	10.6	10.3	10.0	9.9	9.8	9.8
	13	17.0	16.7	16.2	15.5	14.5	13.6	13.3	13.0	12.7	12.6	12.5
	16	19.6	19.2	18.5	18.0	17.2	16.7	16.4	16.0	15.9	15.7	15.6
	20	24.3	23.8	23.2	22.3	21.4	20.7	20.3	20.0	19.8	19.5	19.3

Voltage Drop. power loss. internal resistance. own consumption	In [A]	Voltage drop [mV]	Internal resistance [mΩ]	Power loss [W]	Own consumption [W]
		6	408	68	2.5
	10	183	18	1.8	0.5
	13	195	20	2.0	0.5
	16	194	12	3.1	0.5
	20	212	11	4.2	0.5

Performance in altitude	Elevation [m]	3000	4000	5000	6000
		Rated Current [A]	0.96 × In	0.94 × In	0.92 × In
	Rated Voltage [V]	0.877 × Un	0.775 × Un	0.676 × Un	0.588 × Un

AFDD technical details


Specific let-through energy I^2t DS-ARC1 and DS-ARC1 M




AFDD technical details

Ipeak DS-ARC1 and DS-ARC1 M

—
01 Ipeak
DS-ARC1,
Characteristic C




01




02

—
03 Ipeak
DS-ARC1
Characteristics B



03



04

AFDD technical details

Coordination tables: DS-ARC1, DS-ARC1 M back-up

Fuses - DS-ARC1, DS-ARC1 M@230/230/240V

		Supply S.		gL/gG							
Load S.		Icu [kA]	In[A]	25	40	50	63	80	100		
DS-ARC1, DS-ARC1 M	B,C	7.5 and 10	6...20	35	25	20	15	10	10		

MCCB@415V - DS-ARC1, DS-ARC1 M@230/240V

Upstream			XT1	XT1	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4	XT2	XT4	
Char			B	C	N	N	N	N	S	S	S	S	H	H	H	L	L	V	V	
Down-stream	Icu [kA]	In[A]	18	25	36	36	36	36	50	50	50	50	70	70	70	120	120	150	150	
DS-ARC1	B,C	7.5	6...20	16	16	16	20	10	10	16	20	10	10	16	20	10	20	10	20	10
DS-ARC1M	B,C	10	6...16				25	16	25	16	25	16	25	25	25	25	25	25	25	25
			20	16	16	25	16	16	25	16	25	16	16	25	16	25	16	25	16	

MCCB @415V - DS-ARC1 , DS-ARC1 M@230/240V

Supply S.			T1	T1	T1	T2	T3	T4	T2	T3	T4	T2	T4	T2	T4	T2	T4	T4	T4
Char			B	C	N	N	N	N	S	S	S	H	H	L	L	V	V		
Load S.	Icu [kA]	In[A]	16	25	36	36	36	36	50	50	50	50	70	70	70	85	120	200	
DS-ARC1	B,C	7.5	6...20	16	16	16	20	10	10	20	10	10	20	10	20	10	20	10	10
DS-ARC1M	B,C	10	6...20	16	16	25	16	25	25	16	16	25	16	25	16	25	16	25	16

S800S - DS-ARC1, DS-ARC1 M@ 230/240V

Supply S.			S800S								
Char			B,C,D,K								
Load S.	Icu [kA]		50								
DS-ARC1	B,C	7.5	In[A]	25	32	40	50	63	80	100	125
			6...16	50	40	25	25	18	15	15	15
			20	-	40	25	25	18	15	15	15
			6...16	50	50	50	50	50	50	50	50
DS-ARC1M	B,C	10	20	-	50	50	50	50	50	50	50

S800N - DS-ARC1, DS-ARC1 M@ 230/240V

Supply S.			S800N								
Char			B,C,D								
Load S.	Icu [kA]		36								
DS-ARC1	B,C	7.5	In[A]	25	32	40	50	63	80	100	125
			6...16	36	36	25	25	18	15	15	15
			20	-	36	25	25	18	15	15	15
			6...16	36	36	36	36	36	36	36	36
DS-ARC1M	B,C	10	20	-	36	36	36	36	36	36	36

AFDD technical details

Coordination tables: DS-ARC1, DS-ARC1 M back-up

S800C - DS-ARC1, DS-ARC1 M@ 230/240V

Supply S.			S800C								
Char			B,C,D,K								
Load S.	Icu [kA]		25								
DS-ARC1	B,C	7.5	In[A]	25	32	40	50	63	80	100	125
			6...16	25	25	25	25	18	15	15	15
			20	-	25	25	25	18	15	15	15
DS-ARC1M	B,C	10	6...16	25	25	25	25	25	25	25	25
			20	-	25	25	25	25	25	25	25

S800B - DS-ARC1, S-ARC M@ 230/240V

Supply S.			S800B							
Char			B,C,D,K							
Load S.	Icu [kA]		25							
DS-ARC1	B,C	7.5	In[A]	32	40	50	63	80	100	125*
			6...20	16	16	16	16	15	15	15
DS-ARC1M	B,C	10	6...20	16	16	16	16	16	16	16

*Only S800B B,C

S200 - DS-ARC1, DS-ARC1 M@230/240V

Supply S.		S200	S200M	S200P	S200P	
Char		B-C	B,C	B,C	B,C	
Load S.	Icu [kA]	20	25	40	25	
DS-ARC1	B,C	7.5 and 10	In[A] 0.5..63 6...20 20	0.5..63 25	0.5...25 40	32 25

DS201 - DS-ARC1, DS-ARC1 M @230/240V

Supply S.			DS201	
Char			B,C	
Load S.	In[A]		2...40	
DS-ARC1	B,C	6...20	Icu [kA]	10
			7.5 and 10	10

AFDD technical details

Coordination tables: DS-ARC1, DS-ARC1 M selectivity

Fuse gL/gG- DS-ARC1, S-ARC M @ 230/400V

Load S.	Char	Icu [kA]	Supply S. Fuse gL/gG									
			In[A]	25	32	40	50	63	80	100	125	
DS-ARC1	B,C	7.5	6	1	1.5	4	4.5	T	T	T	T	
			10		1.2	3.5	4	T	T	T	T	
			13		1	3	3.5	5	T	T	T	
			16		1	3	3.5	5	T	T	T	
			20		1	3	3.5	5	T	T	T	
DS-ARC1M	B,C	10	6	1	1.5	4	4.5	7	T	T	T	
			10		1.2	3.5	4	6	T	T	T	
			13		1	3	3.5	5	T	T	T	
			16		1	3	3.5	5	T	T	T	
			20		1	3	3.5	5	8	T	T	

MCCB@415V - DS-ARC1, DS-ARC1 M @230/240V

Load S.	Char	Icu [kA]	Supply S.										XT1			
			Version										B,C,N,S,H			
			Release										TM			
DS-ARC1	B.C	7.5	6	T	T	T	T	T	T	T	T	T	T	T	T	T
			10			3	3	3	4.5	T	T	T	T	T	T	T
			13					3	4.5	5	T	T	T	T	T	T
			16					3	4.5	5	T	T	T	T	T	T
			20					3	5	T	T	T	T	T	T	T
DS-ARC1M	B.C	10	6	6	6	6	6	6	6	T	T	T	T	T	T	T
			10			3	3	3	4.5	7.5	8.5	T	T	T	T	T
			13					3	4.5	5	7.5	T	T	T	T	T
			16					3	4.5	5	7.5	T	T	T	T	T
			20					3	5	6	T	T	T	T	T	T

MCCB@415V - DS-ARC1, DS-ARC1 M @230/240V

Load S.	Char	Icu [kA]	Supply S.										XT2			
			Version										N,S,H,L,V			
			Release										TM			
DS-ARC1	B.C	7.5	6	T	T	T	T	T	T	T	T	T	T	T	T	T
			10	3 ¹	3	3	3	4.5	T	T	T	T	T	T	T	T
			13		3 ¹	3	4.5	5	T	T	T	T	T	T	T	T
			16		3 ¹	3	4.5	5	T	T	T	T	T	T	T	T
			20		3 ¹	3	5	T	T	T	T	T	T	T	T	T
DS-ARC1M	B.C	10	6	T	T	T	T	T	T	T	T	T	T	T	T	T
			10	3 ¹	3	3	4.5	7.5	8.5	T	T	T	T	T	T	T
			13		3 ¹	3	4.5	5	7.5	T	T	T	T	T	T	T
			16		3 ¹	3	4.5	5	7.5	T	T	T	T	T	T	T
			20		3 ¹	3	5	6	T	T	T	T	T	T	T	T

¹ Value valid in case of Supply S. breaker only magnetic

AFDD technical details

Coordination tables: DS-ARC1, DS-ARC1 M selectivity

MCCB@415V - DS-ARC1, DS-ARC1 M @230/240V

				Supply S.		XT3					
				Version		N,S					
				Release		TM					
Load S.	Char	Icu [kA]	In[A]	63	80	100	125	160	200	250	
DS-ARC1	B.C	7.5	6	T	T	T	T	T	T	T	
			10	T	T	T	T	T	T	T	
			13	5	T	T	T	T	T	T	
			16	5	T	T	T	T	T	T	
			20	5	T	T	T	T	T	T	
DS-ARC1M	B.C	10	6	T	T	T	T	T	T	T	
			10	7.5	8.5	T	T	T	T	T	
			13	5	7.5	T	T	T	T	T	
			16	5	7.5	T	T	T	T	T	
			20	5	6	T	T	T	T	T	

MCCB@415V - DS-ARC1, DS-ARC1 M @230/240V

				Supply S.		XT4											
				Version		N,S,H,L,V											
				Release		TM											
Load S.	Char	Icu [kA]	In[A]	20	25	32	40	50	63	80	100	125	160	200	225	250	
DS-ARC1	B.C	7.5	6	T	T	T	T	T	T	T	T	T	T	T	T	T	
			10	3 ¹	3	3	3	4.5	T	T	T	T	T	T	3	T	T
			13		3 ¹	3	4.5	5	T	T	T	T	T	T	3	T	T
			16		3 ¹	3	4.5	5	T	T	T	T	T	T	3	T	T
			20		3 ¹	3	5	T	T	T	T	T	T	T	T	T	T
DS-ARC1M	B.C	10	6	T	T	T	T	T	T	T	T	T	T	T	T	T	T
			10	3 ¹	3	3	4.5	7.5	8.5	T	T	T	T	T	3	T	T
			13		3 ¹	3	4.5	5	7.5	T	T	T	T	T	3	T	T
			16		3 ¹	3	4.5	5	7.5	T	T	T	T	T	3	T	T
			20		3 ¹	3	5	6	T	T	T	T	T	T	T	T	T

¹ Value valid in case of Supply S. breaker only magnetic

AFDD technical details

Coordination tables: DS-ARC1, DS-ARC1 M selectivity

MCCB@415V - DS-ARC1, DS-ARC1 M @230/240V

			Supply S.											
			T1											
			Version B,C,N											
			Release TMD											
			Iu[A] 160											
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160
DS-ARC1	B,C	7.5	6	T	T	T	T	T	T	T	T	T	T	T
			10			3	3	3	4.5	T	T	T	T	T
			13					3	4.5	5	T	T	T	T
			16					3	4.5	5	T	T	T	T
			20					3	5	T	T	T	T	T
DS-ARC1M	B,C	10	6	6	6	6	6	6	T	T	T	T	T	T
			10			3	3	3	4.5	7.5	8.5	T	T	T
			13					3	4.5	5	7.5	T	T	T
			16					3	4.5	5	7.5	T	T	T
			20					3	5	6	T	T	T	T

MCCB@415V - DS-ARC1, DS-ARC1 M @230/240V

			Supply S.											
			T2											
			Version N,S,H,L											
			Release TMD											
			Iu[A] 160											
Load S.	Char	Icu [kA]	In[A]	16	20	25	32	40	50	63	80	100	125	160
DS-ARC1	B,C	7.5	6	T	T	T	T	T	T	T	T	T	T	T
			10		3	3	3	3	4.5	T	T	T	T	T
			13			3	3	4.5	5	T	T	T	T	T
			16			3	3	4.5	5	T	T	T	T	T
			20			3	3	5	T	T	T	T	T	T
DS-ARC1M	B,C	10	6	T	T	T	T	T	T	T	T	T	T	T
			10		3	3	3	3	4.5	7.5	8.5	T	T	T
			13			3	3	4.5	5	7.5	T	T	T	T
			16			3	3	4.5	5	7.5	T	T	T	T
			20			3	3	5	6	T	T	T	T	T

AFDD technical details

Coordination tables: DS-ARC1, DS-ARC1 M selectivity

MCCB@415V - DS-ARC1@230/240V

				Supply S.		T3				
				Version		N,S				
				Release		TMD, MA				
				Iu[A]		250				
Load S.	Char	Icu [kA]	In[A]	63	80	100	125	160	200	250
DS-ARC1	B,C	7.5	6	T	T	T	T	T	T	T
			10	T	T	T	T	T	T	T
			13	5	T	T	T	T	T	T
			16	5	T	T	T	T	T	T
			20	5	T	T	T	T	T	T
DS-ARC1 M	B,C	10	6	T	T	T	T	T	T	T
			10	7.5	8.5	T	T	T	T	T
			13	5	7.5	T	T	T	T	T
			16	5	7.5	T	T	T	T	T
			20	5	6	T	T	T	T	T

S800N/S - DS-ARC1 , S- ARC 1 M @230/240V

				Supply S.		S800N-S			
		Char				B			
Load S.		Icu [kA]		In[A]	50	63	80	100	125
DS-ARC1, DS-ARC1M	B,C	7.5 and 10	6	0.6	1.2	1.6	2.6	3.8	
			10	0.5	1.1	1.4	2	3	
			13		0.8	1.2	1.7	2.5	
			16		0.8	1.2	1.7	2.5	
			20			1	1.5	2.1	

S800N/S-DS-ARC1 , S-ARC 1 M @230/240V

				Supply S.		S800N-S			
		Char				C			
Load S.		Icu [kA]		In[A]	40	50	63	80	100
DS-ARC1, DS-ARC1M	B,C	7.5 and 10	6	0.55	1.1	1.5	2.5	3.6	5.5
			10	0.45	1	1.3	1.9	2.8	4.2
			13		0.75	1.1	1.6	2.3	3.6
			16		0.75	1.1	1.6	2.3	3.6
			20			0.9	1.4	1.9	3.3

S800N/S-DS-ARC1, DS-ARC1 M @230/240V

				Supply S.		S800 N-S			
		Char				D			
Load S.		Icu [kA]		In[A]	25	32	40	50	63
DS-ARC1	B,C	7.5	6	0.6	1.3	2	3.2	3.9	T
			10	0.5	1.2	1.65	2.6	3.1	T
			13		0.9	1.4	1.8	2.6	5
			16		0.9	1.4	1.8	2.6	5
			20			1.3	1.6	2.2	4.2
			6	0.6	1.3	2	3.2	3.9	8
DS-ARC1M	B,C	10	10	0.5	1.2	1.65	2.6	3.1	6.2
			13		0.9	1.4	1.8	2.6	5
			16		0.9	1.4	1.8	2.6	5
			20			1.3	1.6	2.2	4.2
			6	0.6	1.3	2	3.2	3.9	5.4
			10	0.5	1.2	1.65	2.6	3.1	8.6

Electrical installation solutions for buildings – Technical details

Protection and safety

Protection and safety technical details

OVR Surge Protective Devices	5/2
E 90 fuseholders	5/29
E 9F fuses	5/33
EPD 24-TB-101	5/54
SQZ3 phase and sequence relays	5/58
RH/RL maximum and minimum current/voltage relays	5/59
E 236 undervoltage monitoring relays	5/60
Insulation monitoring devices	5/61
Tl insulating transformers for medical locations	5/65
QSO switchboard for medical locations	5/66
Insulation monitoring devices	5/69

Protection and safety technical details

Overvoltage protection overview – IEC/EN standards

International safety standards establish a requirement for assessing protection against transient overvoltages (surges) as an integral part of satisfactory electrical system design. A summary is provided within IEC 60364 standard for electrical installations of buildings regarding the requirements of surge protective devices (SPDs)

IEC 60364 assesses the need to protect AC power circuits, although cross-references transient overvoltage or surge protection on other metallic services including data, signal and telecommunications lines, as defined by IEC/EN 62305 Standard for Lightning Protection.

It covers transient overvoltages of atmospheric origin (lightning) or as a result of electrical switching, through two sections:

- **Section 443** which defines the criteria for risk assessment to use SPDs, considering factors such as levels of consequential loss due to overvoltages and the equipment rated impulse voltage
- **Section 534** which outlines the parameters for selection and installation of SPDs as appropriate, to ensure satisfactory protection of the structure itself and its contents, its personnel and electronic systems and electrical equipment

Risk assessment

Section 443 establishes that SPD are required where the consequences caused by overvoltage leads to:

- (a) results in serious injury to, or loss of, human life, (e.g. hospitals, care homes, home dialysis equipment)
- (b) results in interruption of public services and/or damage to cultural heritage, (e.g. power stations, data centres, heritage status buildings like museums, castles)
- (c) results in interruption of commercial or industrial activity (e.g. banks, hotels, supermarkets, industrial plants, farms)
- (d) affects a large number of collocated individuals (e.g. offices, universities, schools, residential tower blocks)

For all other cases than above a simplified risk assessment to determine the Calculated Risk Level CRL shall be conducted.

Note that a comprehensive risk assessment method to (IEC/EN 62305-2) must be used for high risk installations such as nuclear or chemical sites where the consequences of transient overvoltages could lead to explosions, harmful chemical or radioactive emissions thus affecting the environment.

In all cases, IEC/ EN 62305 which would require installation of equipotential bonding SPDs where a structural lightning protection system (LPS) is installed, or there is a risk of a direct lightning stroke to a service line.

Selection & installation of SPDs

Section 534 provides guidance on the selection and installation of SPDs to limit transient overvoltages.

The selection of an SPD is dependent on its location within the installation, the equipment rated impulse voltage at this location, and the expected transient overvoltage energy that the SPD is required to limit. The largest transient overvoltages are expected at the service entrance, i.e. at the origin of the installation.

Additionally transient overvoltages can be anticipated at sensitive and critical equipment as a result of electrical switching within the installation. SPDs should therefore be installed as appropriate at main distribution board level, subdistribution board level to protect sensitive equipment, and locally to protect critical equipment.

Where multiple SPDs are installed on the same conductor, these should coordinate with each other to ensure protection levels are not compromised within the system.

Where SPDs are required they must tested in line with SPD product standards IEC/EN 61643 series. Power SPDs are classified to IEC/EN 61643-11 by Class /Type respectfully. High energy Class I/Type 1 tested SPDs (Type 1) must be installed at the service entrance where a structural LPS is installed or there is an overhead metallic service line at risk from a direct lightning stroke.

Class I tested/Type I SPDs however do not provide protection to electronic systems. Transient overvoltage SPDs (Class II tested/Type 2 and Class III tested/Type 3) are required downstream to protect sensitive and critical equipment. These SPDs protect against the transient overvoltages caused by indirect lightning (inductive or resistive coupling) and the electrical switching of large inductive loads.

Combined Class/Type SPDs are classified with more than one Class test/Type, e.g. Class I+II tested SPD to IEC or Type 2+3 to EN. Such SPDs can provide both lightning current with overvoltage protection in addition to protection between all conductor combinations (or modes of protection) within a single unit. Combined Type SPDs provide high surge current handling combined with better overvoltage protection levels (Up) a performance parameter of an SPD.

The most important characteristic for an SPD is its voltage protection level (Up) and not its energy withstand (e.g. I_{imp}). SPDs with lower voltage protection levels (or let-through voltage) offer much better protection to sensitive and critical electronic systems, including:

- Minimal equipment stress (i.e. keeping circuit degradation to a minimum)
- Reduced risk from additive inductive voltages on the SPDs connecting leads
- Reduced risk from downstream voltage oscillations

Protection and safety technical details

IEC/ EN 61643 SPD standard series focus

ABB SPDs meet the performance parameters defined in International & European SPD product standards:

- **IEC/EN 61643-11** Surge protective devices connected to low-voltage power systems - requirements and tests.
- **IEC/EN 61643-21** Surge protective devices connected to telecommunications and signalling networks - performance requirements and testing methods.

These parts of the IEC/EN 61643 standard apply for all SPDs providing protection against lightning (direct and indirect) and transient overvoltages.

IEC/EN 61643-11 covers AC mains protection, for 50/60 Hz AC power circuits and equipment rated up to 1000 VRMS AC and 1500 V DC.

IEC/EN 61643-21 covers telecommunications and signalling networks with nominal system voltages up to 1000 VRMS AC and 1500 V DC.

Within these parts to the standard is defined:

- The electrical requirements for SPDs, including voltage protection and current limiting levels, status indication and minimum test performance.
- The mechanical requirements for SPDs, to ensure an appropriate quality of connection, and mechanical stability when mounted.
- The safety performance of the SPD, including its mechanical strength and its ability to withstand heat, overstress and insulation resistance.

The standard establishes the importance of testing SPDs to determine their electrical, mechanical and safety performance.

Electrical tests include impulse durability, current limiting, and transmission tests. Mechanical and safety tests establish levels of protection against direct contact, water, impact, the SPD installed environment etc.

For voltage and current limiting performance, an SPD is tested according to its Type (or Class to IEC), which defines the level of lightning current or transient overvoltage it is expected to limit/divert away from sensitive equipment.

Tests include Class I impulse current (10/350 waveform), Class I & II nominal discharge current (8/20 waveform), Class I & II voltage impulse and Class III combination wave tests for SPDs installed on power lines, and Class D (high energy), C (fast rate of rise), and B (slow rate of rise) for those on data, signal and telecoms lines.

SPDs are tested with the connections or terminations following manufacturer's instructions, as per the expected SPD installation.

Measurements are taken at the connectors/terminals. Three samples of an SPD are tested and all must pass before approval is granted.

SPDs which have been tested to IEC/EN 61643 should be suitably labelled and marked, to include the relevant performance data for their application.

SPD application and installation standards Within IEC/EN 61643 there are two further standards which provide recommendations on the selection and installation of SPDs.

These are:

- IEC/EN 61643-12 Surge protective devices connected to low-voltage power systems - selection and application principles.
- IEC/EN 61643-22 Surge protective devices connected to telecommunications and signalling networks - selection and application principles.

These application standards should be used with IEC/EN 61643-11 and IEC/EN 61643-21 respectively. Each application standard provides information and guidance on:

- Risk assessment and evaluating the need for SPDs in low-voltage systems, with reference to IEC/EN 62305. Lightning Protection standard and IEC 60364 Electrical installations for buildings.
- Important characteristics of an SPD (e.g. voltage protection level) in conjunction with the protection needs of equipment (i.e. its rated impulse voltage or impulse immunity – voltage).
- Selection of SPDs considering the entire installation environment, including their classification, function and performance.
- Coordination of SPDs throughout the installation (for power and data lines) and between SPDs and RCDs or overcurrent protective devices.

Through following the guidance in these documents, appropriate specification of SPDs to meet the installation requirement can be achieved.

ABB also provide SPDs tested to UL standards - a summary of the differences in between IEC SPD test standards and UL SPD test standards terminology can be found on the following pages.

Protection and safety technical details

OVR Surge Protective Devices

Selection of surge protective devices

The IEC standard introduced the concept of lightning protection zones (LPZ) to help in selecting the correct surge protection. This concept ensure the gradual reduction by stages of the energies and overvoltage caused by lightning or switching operations. This logic of coordination in the protection is what we call the “stepping protection”.

External Zones:

- LPZ 0A Unprotected zone outside the building subject to direct lightning strikes and therefore may have to handle to the full lightning current and lightning electromagnetic field.
- LPZ 0B Zone protected against direct lightning strikes by external air terminal and where the threat is the full lightning electromagnetic field.

Internal Zones:

Zones inside the building which are protected against direct lightning flashes.




- LPZ 1 Zone subject to partial lightning or surge currents. Type I SPDs shall be installed at the boundary between LPZ OA and LPZ 1 to reduce the entrance of lightning currents through power lines.
- LPZ 2...n Zone where the surge current is limited by current sharing and where the surge energy is reduced by additional surge protection like SPDs. Type 2 SPDs are installed at the boundaries of each zone, i.e. LPZ 1 and LPZ 2, LPZ 2 and LPZ 3, etc.

Lightning protection zones description (IEC 62305-4):

It consists in dividing a building in several volumes: the protection zone. The objective is to ensure that the LPZ gives enough protection to the equipment inside this zone. To do so, SPDs are installed at the protection zone boundaries. Each time an SPD is installed, a new protection zone is created.

Current impulse:

The 10/350 and 8/20 impulse waves are used in the Class I and Class II SPDs tests. The first number gives the rising time of the current impulse to reach 90% of the peak level and the second number gives the time to half value in micro-seconds (μ s).




Protection and safety technical details

OVR Surge Protective Devices

Protection in common and/or differential mode

Common mode

Overvoltages in common mode concern all neutral point connections. They occur between the live conductors and earth (e.g. phase/earth or neutral/earth). The neutral conductor is a live cable, as well as the phase conductors. This overvoltage mode destroys not only earthed equipment (Class I), but also non-earthed equipment (Class II) with insufficient electrical insulation (a few kilovolts) located close to an earthed mass. Class II equipment that is not situated close to an earthed mass is theoretically protected from this type of attack.




Overvoltages in common mode

Differential mode

Overvoltages in differential mode circulate between the live phase/phase or phase/neutral conductors. They can cause considerable damage to any equipment connected to the electrical network, particularly “sensitive” equipment.

These overvoltages concern TT earthing systems. They also affect TN-S systems if there is a significant difference in length between the neutral cable and the protective cable (PE).




Overvoltages in differential mode


Different types of OVR configuration

Either Common mode or differential mode of protection are required depending on the system configuration (IT, TNC, TNS, TT). For that purpose, you can find different OVR configuration (single pole, 3L, 4L, 1N, 3N).

Common mode configurations (TNC networks)




OVR T1 25-255-7 x 3
Ref.: 2CTB815101R8700




OVR T2 3L 40-275s P QS
Ref.: 2CTB815704R1800

Common and differential mode configurations (TNS, TT networks)



OVR T1 25-255-7 x 3
+ OVR T1 25 N
Ref.: 2CTB815101R8700
+ 2CTB815101R9700



OVR T2 3N 40-275s P QS
Ref.: 2CTB815704R2000

Surge and lightning protection solutions

Coordination and wiring principles

The SPD installed at the line entrance of an installation may not ensure an effective protection to the whole system. As a matter of fact, the selection of the voltage protection level (U_p) of SPDs depends on many parameters: Type of equipment to be protected, the length of the connections to the SPDs, the length in between the SPDs and the equipment to be protected.

Coordination required if :

The protection level (U_p) of the SPDs is not low enough to protect the equipment.


If the distance in between the SPDs and the equipment is >10 m.

NOTE:

The first SPD is diverting most of the surge current to the ground, and the second SPD will ensure a good protection level to the equipment.

It is what we call the stepping protection.

Coordination between Type 1, Type 1+2, Type 2 (with and without Safety System) and Type 2+3 surge protective device



Surge and lightning protection solutions

Coordination and wiring principles

Type of Surge Protective Devices	Miniature circuit breaker maximum ratings * curve B or C				Fuses maximum ratings* (gG)				Moulded Case Circuit Breaker
	Prospective short circuit current at SPD location (Ip)				IP ≤ 7 kA	IP ≤ 50 kA	IP ≤ 100 kA	IP <= 50kA	
Type 1	IP ≤ 6 kA	IP ≤ 10 kA	IP ≤ 15 kA	IP ≤ 50 kA	IP ≤ 7 kA	IP ≤ 50 kA	IP ≤ 100 kA	IP <= 50kA	
OVR T1 25 kA non-pluggable Imax 25 kA; Uc 255, 440 V	-	-	-	-	125 A	125 A	-	-	
OVR T1 25 kA non-pluggable Imax = 25 kA/I _{fi} = 7 kA; Uc 255 V	-	-	-	-	125 A	-	-	-	
Type 1+2									
OVR T1+2 non-pluggable Imax 25 kA/I _{fi} = 15 kA; Uc 255 V	-	-	-	-	125 A	125 A (IP < 15 kA)	-	-	
OVR T1-T2 pluggable Safety Reserve QuickSafe® Imax 12.5 kA; Uc 275, 440V	-	-	-	-	160 A	160 A	160 A	XT4S 250A Ekip LSI (I≤3In)	
Type 2									
OVR T2 pluggable Safety Reserve QuickSafe® Imax 40 and 80 kA; Uc 275, 440 V	S 200 M - 63	S 200 M - 63	S 200 P - 63	S 800 S - 125	160 A fuse	160 A fuse	160 A fuse		
Type 2 pluggable QuickSafe® Imax 40 kA; Uc 275, 350, 440, 600 V	S 200 M - 63	S 200 M - 63	S 200 P - 63	S 800 S - 125	125 A fuse	125 A fuse	125 A fuse	@ Uc=275V, Tmax XT4S 250, Ekip LSI, I<3 In	
OVR T2 non-pluggable Imax 20 and 40 kA Uc 275 V	S 200 M - 50	S 200 M - 50	S 200 P - 50	S 800 S - 50	50 A fuse	50 A fuse	-	-	
OVR T2 pluggable Imax 15 kA Uc 75 V	S 200 M - 16	S 200 M -	-	-	16 A fuse	16 A fuse	-	-	
Type 2+3									
OVR T2-T3 pluggable QuickSafe® Imax 20 kA; Uc 275, 350, 440, 600 V	S 200 M - 63	S 200 M - 63	S 200 P - 63	S 800 S - 125	125 A fuse	125 A fuse	125 A fuse	@ Uc=275V, Tmax XT4S 250, Ekip LSI, I<3 In	

* Maximum ratings, must be in accordance with the installation to follow coordination rules with main or upstream short circuit protection(s).

Service entrance SPDs	PE connection cable size
Type 1	16 mm ²
Type 1+2	16 mm ²
Type 2	4 mm ²
Type 2+3	4 mm ²

Type 2 QuickSafe® Characteristics	Prospective short circuit current at SPD location (Ip)	Circuit breaker* (curve B or C)	Fuses* (gG)
Maximum rating			
In: 5, 20, 30 kA Uc: 275, 350, 440, 600 V	0.625 kA < Ip < 100 kA	S800S B or C - 125 A**	E90/125 125 A fuse (without Safety Reserve System) 160 A fuse (with Safety Reserve System)

*: The backup disconnection of the SPD shall always be coordinated with the circuit breakers used in the installation
**: up to Ip ≤ 50kA

Protection and safety technical details


OVR Surge Protective Devices

Selection tool: TNC-S network 230/400 V

Industry, commercial building


Configuration 1

$15 \text{ kA} \leq I_p \leq 50 \text{ kA}$










Configuration 2

$7 \text{ kA} \leq I_p \leq 15 \text{ kA}$



Configuration 3

$I_p \leq 7 \text{ kA}$



I_p : prospective short circuit current of the power supply.

* Must be according to the coordination rules with main or upstream short circuit protection(s).

Protection and safety technical details


OVR Surge Protective Devices

Selection tool: TT network 230/400 V

Industry, commercial building


Configuration 1

$15 \text{ kA} \leq I_p \leq 50 \text{ kA}$




Configuration 2

$7 \text{ kA} \leq I_p \leq 15 \text{ kA}$




Configuration 3


$I_p \leq 7 \text{ kA}$




> 10 meters cable




> 10 meters cable




> 10 meters cable



> 10 meters cable



> 10 meters cable



I_p : prospective short circuit current of the power supply

* Must be according to the coordination rules with main or upstream short circuit protection(s).

Protection and safety technical details


OVR Surge Protective Devices

Selection tool: IT network 230 V without neutral Commercial, residential

The IT system has all live parts at the source isolated from earth or one part connected to earth with a high impedance.


Configuration 1

$I_p \leq 50 \text{ kA}$




Configuration 2


$I_p \leq 100 \text{ kA}$



> 10 meters cable



> 10 meters cable



Protection and safety technical details

OVR Surge Protective Devices

Selection tool: TNC, TNS/TT networks 230/400 V Residential

With external conductive parts (external lightning protection air terminal, antenna...) or powered by aerial lines

YES



NO




Neighbour with external lightning protection system (or generally with earthed extraneous conductive parts), or proximity of high points


Configuration 1

With risk of direct lightning current (external protection, aerial lines...)

YES




NO




Configuration 2

With risk of indirect lightning current, transient surges


Distribution board TNC




Distribution board TNC



Distribution board TNS/TT



Distribution board TNS/TT



* Should be according to the coordination rules with installed main breakers

Protection and safety technical details

UL 1449 Ed4

The Underwriters Laboratories (UL) standard for surge protective devices (SPDs) has been the primary safety standard for surge protection since the first edition was published in 1985, the fourth edition became mandatory for AC SPDs in March 2016.

The objective of UL 1449 has always been to increase safety in terms of surge protection.

Change in the standard's name: From TVSS to SPDs

Prior to UL 1449 3rd Edition taking effect, the devices this standard covers were known as Transient Voltage Surge Suppressors (TVSS), operating on power circuits not exceeding 600 V. With the inception of the 3rd and 4th Edition, these devices are now known as Surge Protective Devices (SPDs), and may operate on power circuits not exceeding 1500 V DC.

This new designation moves the UL standard closer to the international designation and to IEC standards.

The different type designations of surge protective devices

The UL 1449 placed SPDs into five different Type categories based on installation location within an electrical system. While Type 1, Type 2 and Type 3 categories refer to different types of SPDs that can be installed at specific locations, Type 4 and Type 5 categories refer to components used in an SPDs configuration.

Type 1 – “Permanently connected SPDs intended for installation between the secondary of the service transformer and the line side of the service equipment overcurrent device.”

Type 2 – “Permanently connected SPDs intended for installation on the load side of the service equipment overcurrent device.”

Type 3 – “Point of utilization SPDs, installed at a minimum conductor length of 10 meters (30 feet) from the electrical service panel.”

Type 4 - Component assemblies – “Component assembly consisting of one or more Type 5 components together with a disconnect (integral or external) or a means of complying with the limited current tests.”

Type 1, 2, 3 - Component assemblies – “Consists of a Type 4 component assembly with internal or external short circuit protection.”

Type 5 – “Discrete component surge suppressors, such as MOVs that may be mounted on a PWB, connected by its leads or provided within an enclosure with mounting means and wiring terminations.”

The closer an SPD is installed to the equipment, the better the protection is. This is a push in the direction of providing stepped protection including external and internal surge protection.



The measured voltage protection level

The Measured Limiting Voltage (MLV) is the maximum magnitude of voltage measured at the application of a specific impulse wave shape.

When applying a certain surge current on the SPD the measured voltage at the device terminals is the so called “let-through voltage.”

In UL 1449 2nd Edition, the let-through voltage was referred to as Suppressed Voltage Rating (SVR) and was calculated with a 0.5 kA surge wave form at 6 kV. The new designation is Voltage Protection Rating (VPR) and is calculated with a 3 kA surge wave form at 6 kV.

All products have been certified according to the UL 1449 4th Edition.

The MLV will allow comparison of different types of SPDs with regards to the let-through voltage. However, it is important to note that the surge current used to measure the let-through voltage is six times higher in the 3rd and 4th Edition than in the 2nd Edition. This means that, comparing the obsolete SVR designation with the new VPR ratings will not be valid, as VPR ratings will of course be higher than SVR ratings.

Protection and safety technical details

UL 1449 Ed4

List of OVR T2 UL products according to their certification

Type acc. To UL 1449 Ed4

Range	Type	Order code	Type 4 CA	Type 1 CA
T2 U	OVR T2 15-150 P U	2CTB802341R0000	■	
	OVR T2 15-320 P U	2CTB802341R0400	■	
	OVR T2 40-150 P U	2CTB802341R2000	■	
	OVR T2 40-150 P TS U	2CTB802341R2100	■	
	OVR T2 40-320 P U	2CTB802341R2400	■	
	OVR T2 40-320 P TS U	2CTB802341R2500	■	
	OVR T2 40-440 P TS U	2CTB802341R2900	■	
	OVR T2 40-550 P TS U	2CTB802341R3300	■	
	OVR T2 40-660 P TS U	2CTB802341R3700	■	
	OVR T2 70 N P U	2CTB802341R8000	■	
	OVR T2 1N 15-150 P U	2CTB802342R0000	■	
	OVR T2 1N 15-320 P U	2CTB802342R0400	■	
	OVR T2 1N 40-150 P U	2CTB802342R2000	■	
	OVR T2 1N 40-150 P TS U	2CTB802342R2100	■	
	OVR T2 1N 40-320 P TS U	2CTB802342R2500	■	
	OVR T2 1N 40-440 P TS U	2CTB802342R2900	■	
	OVR T2 1N 40-550 P TS U	2CTB802342R3300	■	
	OVR T2 1N 40-660 P TS U	2CTB802342R3700	■	
	OVR T2 2L 15-150 P U	2CTB802343R0000	■	
	OVR T2 2L 15-320 P U	2CTB802343R0400	■	
	OVR T2 2L 40-150 P TS U	2CTB802343R2100	■	
	OVR T2 2L 40-320 P TS U	2CTB802343R2500	■	
	OVR T2 2N 15-150 P U	2CTB802344R0000	■	
	OVR T2 2N 15-320 P U	2CTB802344R0400	■	
	OVR T2 2N 40-150 P TS U	2CTB802344R2100	■	
	OVR T2 2N 40-320 P TS U	2CTB802344R2500	■	
	OVR T2 2N 40-440 P TS U	2CTB802344R2900	■	
	OVR T2 2N 40-550 P TS U	2CTB802344R3300	■	
	OVR T2 2N 40-660 P TS U	2CTB802344R3700	■	
	OVR T2 3L 15-150 P U	2CTB802345R0000	■	
	OVR T2 3L 15-320 P U	2CTB802345R0400	■	
	OVR T2 3L 40-150 P TS U	2CTB802345R2100	■	
	OVR T2 3L 40-320 P TS U	2CTB802345R2500	■	
	OVR T2 3L 40-440 P TS U	2CTB802345R2900	■	
	OVR T2 3L 40-550 P TS U	2CTB802345R3300	■	
	OVR T2 3N 15-150 P U	2CTB802346R0000	■	
	OVR T2 3N 15-320 P U	2CTB802346R0400	■	
	OVR T2 3N 40-150 P TS U	2CTB802346R2100	■	
	OVR T2 3N 40-320 P TS U	2CTB802346R2500	■	
	OVR T2 3N 40-440 P TS U	2CTB802346R2900	■	
	OVR T2 3N 40-550 P TS U	2CTB802346R3300	■	
	OVR T2 3N 40-660 P TS U	2CTB802346R3700	■	
	OVR T2 15-150 C U	2CTB802348R2500	■	
	OVR T2 15-320 C U	2CTB802348R2700	■	
	OVR T2 40-150 C U	2CTB802348R3500	■	
	OVR T2 40-320 C U	2CTB802348R3700	■	
	OVR T2 40-440 C U	2CTB802348R3900	■	
	OVR T2 40-550 C U	2CTB802348R4100	■	
	OVR T2 40-660 C U	2CTB802348R4300	■	
	OVR T2 70 N C U	2CTB802348R6500	■	

Protection and safety technical details

Products Standards, UL 1449 Ed4

Terminology of SPD electrical characteristics

SPD terminology

8/20 wave:

Current waveform which passes through equipment when subjected to an overvoltage (low energy).

Type 2 surge protective device (SPD)

Permanently connected SPDs intended for installation on the load side of the service equipment overcurrent device, including SPDs located at a branch panel. It has successfully passed testing to the standard with the 8/20 wave (class II test).

Metal oxide varistor (MOV)

A varistor is an electronic component with a "diode like" nonlinear current-voltage characteristic, used to protect circuits against excessive transient voltages. Most commonly composed of metal oxides.

Maximum continuous operating voltage (MCOV, U_c)

The maximum designated root mean square (rms) value of power frequency voltage that may be applied continuously between the terminals of the SPD.

Nominal discharge current (I_n)

Peak current value of an 8/20 waveform which the SPD is rated for based on the test program.

Maximum discharge current (I_{max})

Peak current value of an 8/20 waveform which can be safely discharged by the SPD, with an amplitude complying with the class II operating test sequence. $I_{max} > I_n$.

Short circuit current rating (SCCR)


Maximum symmetrical fault current, at rated voltage, that the SPD can withstand without sustaining damage that exceeds acceptable criteria or creates a hazardous operating condition.

Voltage protection rating (VPR)

The value of the VPR is determined as the nearest highest value, taken from Table 63.1 of ANSI/UL 1449 4th Edition, to the measured limiting voltage determined during the transient voltage surge suppression test using the combination wave generator at a setting of 6 kV, 3 kA.

Voltage protection level (Up or U_{res})

The voltage let through by the SPD while diverting surge current to ground must not exceed the voltage withstand value of the equipment connected downstream.



Notes:

Test wave 8/20 μ s according to IEEE # C62.62-200/UL 1449

The first number corresponds to the time from 10% to 90% of its peak value (8 μ s).


The second number corresponds to the time taken for the wave to descend to 50% of its peak value (20 μ s).

Protection and safety technical details


OVR surge protective devices – UL Version

General wiring diagrams


Delta




Single phase




Split phase



Delta



Wye




NOTE: Multiple pole SPDs shown. Wiring diagrams for reference only.

IEC and UL SPD test standards–terminology

IEC 61643-11 Terminology	Description	UL 1449 Terminology
I_{imp}	The maximum surge current rating for an SPD when subjected to a $10 \times 350\mu s$ wave shape	No equivalent
I_{max}	The maximum surge current rating for an SPD when subjected to an $8 \times 20\mu s$ wave shape	Single surge current rating
I_n	Nominal surge discharge current $8 \times 20\mu s$ wave shape	I_n
I_{SCCR}	Short Circuit Current Rating (withstand)	SCCR
U_p	Voltage Protection Level, let thru voltage level of the SPD when subjected to a test surge	VPR
U_c	Maximum Continuous Operational Voltage SPD can be exposed to without failure.	MCOV
U_n	Nominal Operational Voltage, or application voltage	Operational voltage


8 x 20μs wave shape

- Used for IEC Class II test (EN Type 2)
- I_{max} is the surge current value designation for IEC
- I_n is also tested using this wave shape
- U_L single surge current rating




10 x 350μs wave shape (IEC only)

- Used for IEC 61643-11/ Class I tested SPD or EN 61643-11 Type 1
- SPD must survive 5 impulses increasing in magnitude to max I_{imp}
- I_{imp} is then the surge current value designation if SPD passes
- There is no equivalent test in the U_L standard





UL Types vs IEC Class tested SPDs and Locations



Protection and safety technical details


OVR Surge Protective Devices

Dimensional drawings of OVR surge protective devices


OVR T1

Type	Width mm
OVR T1 25-255-7	17.8
OVR T1 3N 25-255-7	89
OVR T1 50 N	35.6
OVR T1 25-255	35.6
OVR T1 25-440	35.6
OVR T1 3L 25-255	106.8
OVR T1 3L 25-255 TS	124.6
OVR T1 1N 25-255	71.2
OVR T1 1N 25-255 TS	89
OVR T1 2L 25-255	71.2
OVR T1 2L 25-255 TS	89
OVR T1 3N 25-255	142.4
OVR T1 3N 25-255 TS	160.2
OVR T1 4L 25-255	142.4
OVR T1 4L 25-255 TS	160.2
OVR T1 25 N	17.8
OVR T1 100 N	35.6
OVR T1+2 25-255 TS	35.6
OVR T1+2 1N 25-255 TS	71.2
OVR T1+2 3L 25-255 TS	106.8
OVR T1+2 3N 25-255 TS	142.4
OVR T1+2 4L 25-255 TS	142.4


Main dimensions mm



OVR T1 25-255-7



OVR T1 3N 25-255-7



OVR T1 50 N
OVR T1 25-255
OVR T1 25-440
OVR T1 3L 25-255
OVR T1 3L 25-255 TS
OVR T1 1N 25-255
OVR T1 1N 25-255 TS
OVR T1 2L 25-255
OVR T1 2L 25-255 TS
OVR T1 3N 25-255
OVR T1 3N 25-255 TS
OVR T1 4L 25-255
OVR T1 4L 25-255 TS
OVR T1 25 N
OVR T1 100 N
OVR T1+2 25-255 TS
OVR T1+2 1N 25-255 TS
OVR T1+2 3L 25-255 TS
OVR T1+2 3N 25-255 TS
OVR T1+2 4L 25-255 TS

Protection and safety technical details


OVR Surge Protective Devices

Dimensional drawings of OVR surge protective devices


OVR T1-T2 25kA QS

Type	Width mm
OVR T1-T2 12.5-275s P TS QS	17.8
OVR T1-T2 12.5-275s P QS	17.8
OVR T1-T2 12.5-440s P TS QS	35.6
OVR T1-T2 12.5-440s P QS	35.6
OVR T1-T2 N 50-275s P QS	17.8
OVR T1-T2 N 50-440 P QS	17.8
OVR T1-T2 3L 12.5-275s P TS QS	53.4
OVR T1-T2 3L 12.5-275s P QS	53.4
OVR T1-T2 3L 12.5-440s P TS QS	106.8
OVR T1-T2 3L 12.5-440s P QS	106.8
OVR T1-T2 1N 12.5-275s P QS	35.6
OVR T1-T2 1N 12.5-275s P TS QS	35.6
OVR T1-T2 1N 12.5-440s P QS	53.4
OVR T1-T2 1N 12.5-440s P TS QS	53.4
OVR T1-T2 3N 12.5-275s P QS	71.2
OVR T1-T2 3N 12.5-275s P TS QS	71.2
OVR T1-T2 3N 12.5-440s P QS	124.6
OVR T1-T2 3N 12.5-440s P TS QS	124.6
OVR T1-T2 4L 12.5-275s P QS	71.2
OVR T1-T2 4L 12.5-275s P TS QS	71.2
OVR T1-T2 4L 12.5-440s P QS	142.4
OVR T1-T2 4L 12.5-440s P TS QS	142.4


Main dimensions mm




OVR T1-T2 12.5-275s P TS QS
OVR T1-T2 12.5-440s P TS QS
OVR T1-T2 N 50-275s P TS QS
OVR T1-T2 N 50-440s P TS QS




OVR T1-T2 12.5-275s P QS
OVR T1-T2 12.5-440s P QS




OVR T1-T2 3L 12.5-275s P TS QS
OVR T1-T2 3L 12.5-440s P TS QS



OVR T1-T2 3L 12.5-275s P QS



OVR T1-T2 1N 12.5-275s P QS
OVR T1-T2 1N 12.5-440s P QS
OVR T1-T2 3N 12.5-275s P QS
OVR T1-T2 3N 12.5-440s P QS
OVR T1-T2 4L 12.5-275s P QS
OVR T1-T2 4L 12.5-440s P QS



OVR T1-T2 1N 12.5-275s P TS QS
OVR T1-T2 1N 12.5-440s P TS QS
OVR T1-T2 3N 12.5-275s P TS QS
OVR T1-T2 3N 12.5-440s P TS QS
OVR T1-T2 4L 12.5-275s P TS QS
OVR T1-T2 4L 12.5-440s P TS QS

Protection and safety technical details


OVR Surge Protective Devices

Dimensional drawings of OVR surge protective devices


OVR T2 75V

Type	Width mm
OVR T2 20-75 P	17.8
OVR T2 20-75 P TS	17.8
OVR T2 2 20-75 P	35.6
OVR T2 2 20-75 P TS	35.6

Main dimensions mm




OVR T2 20-75 P
OVR T2 2 20-75 P



OVR T2 20-75 P TS
OVR T2 2 20-75 P TS

OVR T2 Single pole -Unpluggable

Type	Width mm
OVR T2 20-150	17.8
OVR T2 40-150	17.8
OVR T2 20-275	17.8
OVR T2 40-275	17.8



OVR T2 20-150
OVR T2 40-150
OVR T2 20-275
OVR T2 40-275

Protection and safety technical details


OVR Surge Protective Devices

Dimensional drawings of OVR surge protective devices


OVR T2 Pluggable

Type	Width mm
OVR T2 40-275 P QS	17.8
OVR T2 40-275 P TS QS	17.8
OVR T2 40-275s P QS	17.8
OVR T2 40-275s P TS QS	17.8
OVR T2 40-350 P QS	17.8
OVR T2 40-350 P TS QS	17.8
OVR T2 80-275s P QS	17.8
OVR T2 80-275s P TS QS	17.8
OVR T2 N 80-275 P QS	17.8
OVR T2 N 80-350 P QS	17.8
OVR T2 N 80-275s P QS	17.8
OVR T2 40-440 P QS	17.8
OVR T2 40-440 P TS QS	17.8
OVR T2 40-440s P QS	17.8
OVR T2 40-440s P TS QS	17.8
OVR T2 80-440s P QS	17.8
OVR T2 80-440s P TS QS	17.8
OVR T2 40-600 P TS QS	17.8
OVR T2 N 80-440 P QS	17.8
OVR T2 N 80-440s P QS	17.8


Main dimensions mm




OVR T2 40-275 P QS
OVR T2 40-350 P QS
OVR T2 N 80-275 P QS
OVR T2 N 80-350 P QS
OVR T2 N 80-275s P QS




OVR T2 40-275 P TS QS
OVR T2 40-350 P TS QS
OVR T2 80-275s P TS QS
OVR T2 80-275s P QS
OVR T2 N 80-440 P QS
OVR T2 40-440 P QS
OVR T2 40-440s P QS
OVR T2 40-440s P TS QS
OVR T2 80-440s P QS
OVR T2 80-440s P TS QS
OVR T2 40-600 P TS QS




OVR T2 40-275s P QS
OVR T2 80-275s P QS
OVR T2 40-440s P QS
OVR T2 40-440s P TS QS
OVR T2 80-440s P QS
OVR T2 80-440s P TS QS
OVR T2 40-600 P TS QS




OVR T2 40-275s P TS QS
OVR T2 40-350 P TS QS
OVR T2 80-275s P TS QS
OVR T2 80-275s P QS
OVR T2 N 80-440 P QS
OVR T2 40-440 P QS
OVR T2 40-440s P QS
OVR T2 40-440s P TS QS
OVR T2 80-440s P QS
OVR T2 80-440s P TS QS
OVR T2 40-600 P TS QS



OVR T2 40-440 P QS
OVR T2 40-440s P QS
OVR T2 80-440s P QS
OVR T2 80-440s P TS QS
OVR T2 40-600 P TS QS



OVR T2 40-440s P QS
OVR T2 40-440s P TS QS
OVR T2 80-440s P QS
OVR T2 80-440s P TS QS
OVR T2 40-600 P TS QS



OVR T2 40-440s P QS
OVR T2 40-440s P TS QS
OVR T2 80-440s P QS
OVR T2 80-440s P TS QS
OVR T2 40-600 P TS QS

Protection and safety technical details


OVR Surge Protective Devices

Dimensional drawings of OVR surge protective devices


OVR T2 Pluggable

Type	Width mm
OVR T2 3L 20-275	53.4
OVR T2 3L 40-275	53.4
OVR T2 3L 40-275 P QS	53.4
OVR T2 3L 40-275 P TS QS	53.4
OVR T2 3L 40-275s P QS	53.4
OVR T2 3L 40-275s P TS QS	53.4
OVR T2 3L 80-275s P QS	53.4
OVR T2 3L 80-275s P TS QS	53.4
OVR T2 3L 40-350 P QS	53.4
OVR T2 3L 40-350 P TS QS	53.4
OVR T2 3L 40-440 P QS	53.4
OVR T2 3L 40-440 P TS QS	53.4
OVR T2 3L 80-440s P QS	53.4
OVR T2 3L 80-440s P TS QS	53.4
OVR T2 3L 40-400/690 P	103.8
OVR T2 3L 40-400/690 P TS	106.8
OVR T2 3L 40-600 P TS QS	53.4


Main dimensions mm




OVR T2 3L 40-275 P QS
OVR T2 3L 40-350 P QS




OVR T2 3L 40-275 P TS QS
OVR T2 3L 40-350 P TS QS




OVR T2 3L 40-440 P QS




OVR T2 3L 40-440 P TS QS
OVR T2 3L 40-600 P TS QS




OVR T2 3L 80-440s P QS




OVR T2 3L 40-275s P QS
OVR T2 3L 80-275s P QS




OVR T2 3L 40-275s P TS QS
OVR T2 3L 80-275s P TS QS



OVR T2 3L 80-440s P TS QS



OVR T2 3L 40-400/690 P



OVR T2 3L 40-400/690 P TS

Protection and safety technical details





OVR Surge Protective Devices

Dimensional drawings of OVR surge protective devices


OVR T2 Pluggable

Type	Width mm
OVR T2 4L 40-275	71.2
OVR T2 4L 40-275 P QS	71.2
OVR T2 4L 40-275 P TS QS	71.2
OVR T2 4L 40-275s P QS	71.2
OVR T2 4L 40-275s P TS QS	71.2
OVR T2 4L 80-275s P QS	71.2
OVR T2 4L 80-275s P TS QS	71.2
OVR T2 4L 40-440 P QS	71.2
OVR T2 4L 40-440 P TS QS	71.2
OVR T2 4L 40-600 P TS QS	71.2
OVR T2 4L 80-440s P QS	71.2
OVR T2 4L 80-440s P TS QS	71.2




Main dimensions mm



OVR T2 4L 40-600 P TS QS
OVR T2 4L 80-275s P QS



OVR T2 4L 80-275s P TS QS



Protection and safety technical details


OVR Surge Protective Devices

Dimensional drawings of OVR surge protective devices


OVR T2 Pluggable

Type	Width mm
OVR T2 3N 40-275 P QS	71.2
OVR T2 3N 40-275 P TS QS	71.2
OVR T2 3N 40-275s P QS	71.2
OVR T2 3N 40-275s P TS QS	71.2
OVR T2 3N 80-275s P QS	71.2
OVR T2 3N 80-275s P TS QS	71.2
OVR T2 3N 40-350 P QS	71.2
OVR T2 3N 40-350 P TS QS	71.2
OVR T2 3N 40-440 P QS	71.2
OVR T2 3N 40-440 P TS QS	71.2
OVR T2 3N 40-440s P QS	71.2
OVR T2 3N 80-440s P QS	71.2
OVR T2 3N 80-440s P TS QS	71.2


Main dimensions mm




OVR T2 3N 40-275 P QS
OVR T2 3N 40-275s P QS
OVR T2 3N 80-275s P QS
OVR T2 3N 40-350 P QS
OVR T2 3N 40-440 P QS
OVR T2 3N 40-440s P QS



OVR T2 3N 40-275 P TS QS
OVR T2 3N 40-350 P TS QS
OVR T2 3N 40-440 P TS QS
OVR T2 3N 40-440s P TS QS



OVR T2 3N 40-275s P TS QS
OVR T2 3N 80-275s P TS QS
OVR T2 3N 80-440s P TS QS
OVR T2 3N 40-350s P TS QS
OVR T2 3N 40-440s P TS QS
OVR T2 3N 80-440s P TS QS



OVR T2 3N 40-275s P QS
OVR T2 3N 80-275s P QS
OVR T2 3N 80-440s P QS
OVR T2 3N 40-350s P QS
OVR T2 3N 40-440s P QS
OVR T2 3N 80-440s P QS

Protection and safety technical details


OVR Surge Protective Devices

Dimensional drawings of OVR surge protective devices


OVR T2-T3 Pluggable

Type	Width mm
OVR T2-T3 20-275 P QS	17.8
OVR T2-T3 20-275 P TS QS	17.8
OVR T2-T3 20-440 P QS	17.8
OVR T2-T3 20-440 P TS QS	17.8
OVR T2-T3 3L 20-275 P QS	53.4
OVR T2-T3 3L 20-275 P TS QS	53.4
OVR T2-T3 1N 20-275 P QS	35.6
OVR T2-T3 1N 20-275 P TS QS	35.6
OVR T2-T3 3N 20-275 P QS	71.2
OVR T2-T3 3N 20-275 P TS QS	71.2
OVR T2-T3 3N 20-440 P QS	71.2


Main dimensions mm




OVR T2-T3 20-275 P QS
OVR T2-T3 20-440 P QS




OVR T2-T3 20-275 P TS QS
OVR T2-T3 20-440 P TS QS




OVR T2-T3 3L 20-275 P QS




OVR T2-T3 3L 20-275 P TS QS




OVR T2-T3 1N 20-275 P QS



OVR T2-T3 1N 20-275 P TS QS



OVR T2-T3 3N 20-275 P QS
OVR T2-T3 3N 20-440 P QS



OVR T2-T3 3N 20-275 P TS QS

Protection and safety technical details


OVR Surge Protective Devices

Dimensional drawings of OVR surge protective devices


OVR T2 Autoprotected

Type	Width mm
OVR PLUS N1 20	35.6
OVR PLUS N1 40	35.6
OVR PLUS N3 20	106.8
OVR PLUS N3 40	106.8

Main dimensions mm



OVR PLUS N1 20
OVR PLUS N1 40




OVR PLUS N3 20
OVR PLUS N3 40

OVR T2-3 StreetLight application

Type	Width mm
OVR T2-T3 N1 15-275s SL	17.5

Main dimensions mm



OVR T2-T3 N1 15-275s SL


Protection and safety technical details

OVR Surge Protective Devices


Single pole

Type	Width mm
OVR T2 15-150 P U	17.8
OVR T2 15-320 P U	17.8
OVR T2 40-150 P U	17.8
OVR T2 40-150 P TS U	17.8
OVR T2 40-320 P U	17.8
OVR T2 40-320 P TS U	17.8
OVR T2 40-440 P TS U	17.8
OVR T2 40-550 P TS U	17.8
OVR T2 40-660 P TS U	17.8
OVR T2 70 N P U	17.8

Main dimensions mm



OVR T2 15-150 P U
OVR T2 15-320 P U
OVR T2 40-150 P U
OVR T2 40-320 P U
OVR T2 70 N P U




OVR T2 40-150 P TS U
OVR T2 40-320 P TS U
OVR T2 40-440 P TS U
OVR T2 40-550 P TS U
OVR T2 40-660 P TS U


Single phase networks

Type	Width mm
OVR T2 1N 15-150 P U	35.6
OVR T2 1N 15-320 P U	35.6
OVR T2 1N 40-150 P U	35.6
OVR T2 1N 40-150 P TS U	35.6
OVR T2 1N 40-320 P TS U	35.6
OVR T2 1N 40-440 P TS U	35.6
OVR T2 1N 40-550 P TS U	35.6
OVR T2 1N 40-660 P TS U	35.6

Main dimensions mm



OVR T2 1N 15-150 P U
OVR T2 1N 15-320 P U
OVR T2 1N 40-150 P U




OVR T2 1N 40-150 P TS U
OVR T2 1N 40-320 P TS U
OVR T2 1N 40-440 P TS U
OVR T2 1N 40-550 P TS U
OVR T2 1N 40-660 P TS U


Delta networks

Type	Width mm
OVR T2 3L 15-320 P U	53.4
OVR T2 3L 40-320 P TS U	53.4
OVR T2 3L 40-550 P TS U	53.4

Main dimensions mm



OVR T2 3L 15-320 P U



OVR T2 3L 40-320 P TS U
OVR T2 3L 40-550 P TS U


Protection and safety technical details

OVR Surge Protective Devices


Split phase networks

Type	Width mm
OVR T2 2L 15-150 P U	35.6
OVR T2 2L 15-320 P U	35.6
OVR T2 2L 40-150 P TS U	35.6
OVR T2 2L 40-320 P TS U	35.6
OVR T2 2N 15-150 P U	53.4
OVR T2 2N 15-320 P U	53.4
OVR T2 2N 40-150 P TS U	53.4
OVR T2 2N 40-320 P TS U	53.4
OVR T2 2N 40-440 P TS U	53.4
OVR T2 2N 40-550 P TS U	53.4
OVR T2 2N 40-660 P TS U	53.4

Main dimensions mm



OVR T2 2L 15-150 P U
OVR T2 2L 15-320 P U
OVR T2 2N 15-150 P U
OVR T2 2N 15-320 P U




OVR T2 2L 40-150 P TS U
OVR T2 2L 40-320 P TS U
OVR T2 2N 40-150 P TS U
OVR T2 2N 40-320 P TS U
OVR T2 2N 40-440 P TS U
OVR T2 2N 40-550 P TS U
OVR T2 2N 40-660 P TS U


Grounded Wye networks

Type	Width mm
OVR T2 3L 15-150 P U	53.4
OVR T2 3L 40-150 P TS U	53.4
OVR T2 3L 40-440 P TS U	53.4
OVR T2 3N 15-150 P U	71.2
OVR T2 3N 15-320 P U	71.2
OVR T2 3N 40-150 P TS U	71.2
OVR T2 3N 40-320 P TS U	71.2
OVR T2 3N 40-440 P TS U	71.2
OVR T2 3N 40-550 P TS U	71.2
OVR T2 3N 40-660 P TS U	71.2

Main dimensions mm



OVR T2 3L 15-150 P U
OVR T2 3N 15-150 P U
OVR T2 3N 15-320 P U



OVR T2 3L 40-150 P TS U
OVR T2 3L 40-440 P TS U
OVR T2 3N 40-150 P TS U
OVR T2 3N 40-320 P TS U
OVR T2 3N 40-440 P TS U
OVR T2 3N 40-550 P TS U
OVR T2 3N 40-660 P TS U

Protection and safety technical details

E 90 fuseholders

E 90 fuse-holders

IEC 60947-3: Switches, disconnectors, switch-disconnectors and fuse combination units

This standard sets out the requirements of devices for connect/disconnect and switching operations.

Disconnector:

The disconnector is a mechanical device that, in the open position, meets the requirements specified for the disconnect function by the international IEC 60947-3 standard. The opening of a disconnector guarantees that the downstream circuit is electrically isolated from the upstream circuit. This is a required condition before personnel can access the equipment on the network, for example to perform maintenance. The IEC 60364 standard prohibits carrying out maintenance on the installation if the circuits have not been disconnected.

Fuse disconnector:

This is the definition of a fuse carrier that performs a disconnect function. Not all fuse carriers are disconnectors: in order to be classified as such they must meet the requirements and pass the tests prescribed by the

IEC 60947-3 standard.

Fuse switch-disconnector:

This is the designation given by the IEC 60947-3 standard to a fuse disconnector that permits switching under load. Not all fuse disconnectors allow this type of operation: in order to be classified as a fuse switch-disconnector, a device must have utilization category AC-21B or higher.

Utilization categories:

Not all connect/disconnect devices have the same performance specifications: the permitted operations depend on a parameter which defines the specific conditions of use, called the utilization category.

It specifies:

- a. The type of network (a.c./d.c.)
- b. The permitted type of operation (under no load, for resistive loads, for highly inductive loads, ecc...)
- c. The frequency of use

The E90 fuse switch-disconnectors have utilization category AC-22B. The E 90 PV fuse disconnectors have utilization category DC-20B.

Type of current	Utilization category		Typical applications
	A	B	
Alternating current	AC-20A	AC-20B	Connecting and disconnecting under no load.
	AC-21A	AC-21B	Switching of resistive loads, including moderate overloads
	AC-22A	AC-22B	Switching of mixed, resistive and inductive loads, including moderate overloads
	AC-23A	AC-23B	Switching of motors or other highly inductive loads
Direct current	DC-20A	DC-20B	Connecting and disconnecting under no load.
	DC-21A	DC-21B	Switching of resistive loads including moderate overloads
	DC-22A	DC-22B	Switching of mixed, resistive and inductive loads, including moderate overloads (e.g. shunt motors)
	DC-23A	DC-23B	Switching of highly inductive loads (e.g. series connected motors)

What loads can be connected/disconnected by a product with utilization category AC-22B?

Utilization category AC-22B permits occasional switching of mixed, resistive and inductive loads, including moderate overloads, in alternating current circuits. Examples of mixed loads are: transformers, power-factor corrected motors, capacitor banks, discharge lamps, heating, etc..

What loads can be connected/disconnected by a product with utilization category AC-20B?

Utilization category AC-20B does not permit connecting or disconnecting under load. An additional load break device is required.

IEC 60269-1: Fuses with voltage rating not exceeding 1000 V for alternating current and 1500 V for direct current

This standard sets out the requirements for low voltage fuses, and consequently the requirements for the fuse carrier devices that hold them.

The standard has two separate sections with different requirements, depending on the type of person using the equipment.

IEC 60269-2: supplementary requirements for fuses for use by authorized persons, mainly for industrial applications.

IEC 60269-3: supplementary requirements for fuses for use by unskilled persons, mainly for household and similar applications.

Protection and safety technical details

E 90 fuseholders

Meaning	Suffix A	Frequent use
	Suffix B	Infrequent use

What is the difference between a fuse carrier conforming to the IEC 60947-3 standard and one conforming to the IEC 60269-2 standard?

These are two complementary standards: IEC 60269-2 sets out the characteristics of the fuses, which in turn also determine the general requirements for the fuse carriers. It is therefore the reference standard for overcurrent protection, but not for connecting/disconnecting and switching.

Is a fuse carrier conforming to IEC 60269-1 a disconnector?

A device conforming only to IEC 60269 has a "disconnect function" but is not classified as a disconnector under the more stringent IEC 60947-3 standard.

Why does the E 90 series have a lower direct current voltage rating under the IEC 60269-3 standard than under the IEC 60269-2 standard?

IEC 60269-2 sets out the requirements for industrial applications, and therefore the reference voltages are higher

than those for the residential and commercial applications covered by IEC 60269-3. In other words, the rated voltage of the fuse carrier depends on the type of installation in which it is used, and the regulations applicable to it.

Is it possible to create multi-pole configurations using an assembly kit?

Multi-pole units made up using an assembly kit to combine single pole units will no longer conform to the reference standards.

In case of installations with many poles side by side, or installations in particular climate conditions, what derating of the nominal values should be taken into account?

The following tables give the parameters for derating the nominal current as a function of the number of poles installed side by side or the temperature and relative humidity.

Installation of multiple poles side by side:

E 91/32		E 91hN/32		E90 50/125	
Poles	Maximum current	Poles	Maximum current	Poles	Maximum current
1...4	I _n	1 ...3	I _n	1...3	I _n
5...7	0.8 x I _n	4...9	0.7 x I _n	4...6	0.95 x I _n
more than 7	0.7 x I _n	more than 10	0.6 x I _n	more than 7	0.9 x I _n

Climate conditions:

E90/32		E90 50/125	
Maximum temperature	Maximum current	Maximum temperature	Maximum current
20° C	I _n	20° C	I _n
30° C	I _n x 0.95	30° C	I _n x 0.95
40° C	I _n x 0.9	40° C	I _n x 0.9


Protection and safety technical details

E 90 fuseholders

Protection and disconnection of 1000 V DC lines


String protection

To avoid equipments damage on DC lines and to ensure isolation of the PV system in case of maintenance, E90 PV disconnectors fuses can be installed downstream the inverter to protect each single string. The fuses must be selected according to the rated current of the line and to the maximum dissipated power.




Back-Up Download

When the Icc short circuit current, at the point of installation, is greater than 10 kA (for 1000V & 1500V) DC, the OVR PVs Surge Protective Devices require a back-up protection with a specific type gR fuse.



DC side of the inverter

For small size photovoltaic systems, E 90 PV fuse disconnectors can be used to protect the DC side of the inverter. The fuse should be chosen according to the rated current of the inverter.



Protection and safety technical details

E 90 fuseholders

Protection system selection

Maximum fuse rated current

		Fuseholder			
Rated voltage		E 90/20 8.5 x 31.5 mm	E 90/32 10.3 x 38 mm	E 90/50 14 x 51 mm	E 90/125 22 x 58 mm
400 V a.c.	gG	20 A	32 A	-	-
	aM	10 A	32 A	-	-
500 V a.c.	gG	-	25 A	50 A	100 A
	aM	-	20 A	50 A	125 A*
690 V a.c.	gG	-	10 A	25 A	80 A
	aM	-	-	25 A	80 A

* = to be used in combination with a device which guarantees protection against overload.

In the table above you will find indication about the highest rated current fuse that you can host inside a fuseholder, depending on the rated voltage of the circuit, the fuse size and the tripping curve characteristic.

ABB fuses and fuseholders comply with all regulatory requirements and sometimes they allow to install a fuse with rated current higher than the one set by the Standard IEC EN 60269-2-1.

Protection and safety technical details

E 9F fuses

E 9F fuses

Can fuses with rated current values higher than the one indicated in the table be used? For example, can a 10.3 x 38 mm 32 A gG fuse be used in a 10.3 x 38 mm E 90/32 fuse holder?

Yes, by following the manufacturer's instructions: you have to check that the power dissipated at the rated voltage value declared by the manufacturer for the size considered does not exceed the maximum dissipated power limit of the fuse holder. In this specific case, an E 9F10 GG32 fuse dissipates 3 W at 400 V rated voltage.

Since an E 90/32 series fuse holder for 10.3 x 38 mm fuses achieves 3 W thermal dissipation, the fuse in question can be used at 400 V rated voltage or less.

Can a 10.3 x 38 mm 32 A gG fuse be used in a 10.3 x 38 mm E 90/32 fuse holder with a rated voltage exceeding 400 V?
In the specific case of E 9F10 GG32, use of rated voltage exceeding 400 V fails to allow the equipment to comply with the maximum dissipated power limit.

Must the rated voltage always be derated if a fuse with a rated current exceeding the value in the table is used?
No, it depends on the technical specifications of the fuse. Derating is not required for E 9F 8 gG 20 fuses since they ensure (at 400 V AC) 2.30 W dissipated power, which is lower than the 2.5 W limit imposed by the standard.

Maximum dissipated power value for cylindrical fuses according to IEC EN 60269-2-1 (Art. 5-5)

Characteristic curve	Fuse	8.5 x 31.5	10.3 x 38	14 x 51	22 x 58
gG	2.5 W	3 W	5 W	9.5 W	
aM	0.9 W	1.2 W	3 W	7 W	

The table lists the maximum dissipated power values of the fuses, considering the size and the characteristic curve. The highlighted values correspond to the maximum dissipated power limit for fuse holders.

E9F gG

Power dissipation [W]

In [A]	Size	8.5x31.5	10.3x38	14x51	22x58
0.5	0.55 W	0.07 W			
1	0.35 W	0.45 W	0.6 W		
2	0.45 W	0.5 W	0.75 W	0.9 W	
4		0.85 W	1.1 W	1.25 W	
6	0.83 W	0.95 W	1.25 W	1.4 W	
8	1 W	1.15 W	1.45 W	1.6 W	
10	1.2 W	1.3 W	1.65 W	1.9 W	
12		1.4 W	1.8 W	2 W	
16	1.7 W	1.9 W	2.35 W	2.5 W	
20	2 W	2.4 W	2.75 W	3.4 W	
25	2.4 W	2.7 W	3.1 W	3.5 W	
32		2.8 W	3.6 W	3.7 W	
40			4 W	4.3 W	
50			4.8 W	5.3 W	
63				6.3 W	
80				7.4 W	
100				8.3 W	
125					11.3 W


It is important verify that the power dissipation by the fuse does not exceed the limit allowed by the fuse it is hosted. In **bold** are shown the maximum values of power dissipation according to IEC EN 60269-2-1.

Protection and safety technical details

E 9F fuses

Time current characteristic curves

E9F gG




Protection and safety technical details

E 9F fuses

Time current characteristic curves

E9F gG




Protection and safety technical details

E 9F fuses

Time current characteristic curves

E9F gG





Protection and safety technical details



E 9F fuses

Operating I²T characteristics

E9F 8 gG



E9F 10 gG




Protection and safety technical details



E 9F fuses

Operating I²T characteristics

E9F 10 gG



E9F 14 gG





Protection and safety technical details


E 9F fuses

Operating I²T characteristics

E9F 22 gG




E9F 22 gG



Protection and safety technical details

E 9F fuses

E9F gG Temperature increase



E9F aM

Power dissipation [W]

In [A]	Size			
	8.5x31.5	10.3x38	14x51	22x58
0.5		0.07 W	0.9 W	
1	0.09 W	0.1 W	0.13 W	0.2 W
2	0.15 W	0.14 W	0.18 W	0.25 W
4	0.26 W	0.28 W	0.28 W	0.35 W
6	0.35 W	0.38 W	0.42 W	0.45 W
8	0.47 W	0.55 W	0.55 W	0.6 W
10	0.55 W	0.62 W	0.65 W	0.75 W
12	0.7 W	0.82 W	0.75 W	0.85 W
16		0.87 W	1.05 W	1.15 W
20		1.05 W	1.3 W	1.35 W
25		1.2 W	1.55 W	1.7 W
32		1.8 W	2.05 W	2.2 W
40			2.65 W	2.7 W
45			2.85 W	
50			2.95 W	3.6 W
63				4.8 W
80				6.2 W
100				6.65 W
125				9.9 W


It is important verify that the power dissipation by the fuse does not exceed the limit allowed by the fuse it is hosted.
In **bold** are shown the maximum values of power dissipation according to IEC EN 60269-2-1.

Protection and safety technical details

E 9F fuses

Time current characteristic curves

E9F aM




Protection and safety technical details

E 9F fuses

Time current characteristic curves

E9F aM




Protection and safety technical details

E 9F fuses

Time current characteristic curves

E9F aM




RMS value of prospective current (A) +/- 8%

Protection and safety technical details


E 9F fuses

Operating I²T characteristics

E9F 8 aM



E9F 10 aM




Protection and safety technical details


E 9F fuses

Operating I²T characteristics


E9F 10 aM



E9F 10 aM



E9F 14 aM




Protection and safety technical details


E 9F fuses

Operating I²T characteristics

E9F 14 aM



E9F 14 aM




Protection and safety technical details


E 9F fuses

Operating I²T characteristics

E9F 22 aM



E9F 22 aM




Protection and safety technical details


E 9F fuses

Operating I²T characteristics

E9F 22 aM



E9F aM Temperature increase (testing in superior contact)



Protection and safety technical details


E 9F fuses

E9F gPV 1000 V DC 10.3 x 38 mm cylindrical fuses

Type	Rated current [A]	Dissipated power 0.7 In [W]	Dissipated power 0.8 In [W]	Dissipated power In [W]
E 9F1 PV	1	0.125	0.175	0.250
E 9F2 PV	2	0.160	0.250	0.320
E 9F3 PV	3	0.66	0.87	1.36
E 9F4 PV	4	0.69	0.8	1.25
E 9F5 PV	5	0.59	0.73	1.12
E 9F6 PV	6	0.42	0.67	1.05
E 9F7 PV	7	0.40	0.64	1.0
E 9F8 PV	8	0.77	0.88	1.48
E 9F10 PV	10	0.67	0.90	1.5
E 9F12 PV	12	0.72	1.0	1.8
E 9F15 PV	15	0.9	1.3	2.2
E 9F20 PV	20	1.1	1.5	2.8
E 9F25 PV	25	1.3	1.8	3.0
E 9F30 PV	30	1.5	1.9	3.7

The power dissipation of the fuse cannot exceed the maximum power dissipation accepted by the fuseholder


Derating in combination with ambient temperature



Protection and safety technical details

E 9F fuses


Time current characteristic curves



Protection and safety technical details

E 9F fuses

Time current characteristic curves




Protection and safety technical details

E 9F fuses

E9F gPV 1500 V DC 10 x 85 mm cylindrical fuses

Type	Rated current In [A]	Power dissipation at 0.7xIn [W]	Power dissipation at 0.8xIn [W]	Power dissipation at 1.0xIn [W]
E9F4 PV1500	4	0.84	1.16	1.97
E9F5 PV1500	5	0.84	1.16	1.97
E9F6 PV1500	6	0.97	1.37	2.42
E9F7 PV1500	7	0.97	1.37	2.43
E9F8 PV1500	8	1.04	1.50	2.60
E9F10 PV1500	10	1.23	1.77	3.09
E9F12 PV1500	12	1.15	1.70	2.89
E9F15 PV1500	15	1.39	1.91	3.48
E9F20 PV1500	20	1.71	2.47	4.28
E9F25 PV1500	25	2.13	3.08	5.35
E9F30 PV1500	30	2.56	3.61	6.40
E9F32 PV1500	32	2.56	3.61	6.40


Ampere rating vs. Ambient temperature



Protection and safety technical details

E 9F fuses

Time current characteristic curves



Protection and safety technical details

EPD 24-TB-101


EPD 24

Time/Current characteristic curve ($TU = 25^\circ\text{C}$)

The trip time is typically 3 s in the range between $1.1 \times IN$ and $1.8 \times IN$.

Electronic current limitation occurs at typically $1.8 \times IN$ which means that under all overload conditions (independent of the power supply and the resistance of the load circuit) the max. overload before disconnection will not exceed $1.8 \times IN$ times the current rating. Trip time is between 100 ms and 3 sec (depending on overload or at short circuit).

Without this current limitation a considerably higher overload current would flow in the event of an overload or short circuit.



¹⁾ Current limitation typically $1.8 \times I_N$ at $I_N = 0.5 \text{ A} \dots 6 \text{ A}$
 Current limitation typically $1.5 \times I_N$ at $I_N = 8 \text{ A}$ or 10 A
 Current limitation typically $1.3 \times I_N$ at $I_N = 12 \text{ A}$

Maximum cable lengths

EPD24 reliably trips from 0Ω up to max. circuit resistance R_{max} .

Calculation of R_{max}		
Selected rating IN (A)	3	6
Operating voltage US (V DC) (= 80 % of 24 V) 2)	19.2	19.2
Trip current $lab = 1.25 \times IN$ (A) (EPD24 trips after 3 s)	3.75	7.50
R_{max} (Ω) = $(UB/lab) - 0.050$	5.07	2.51

2) Voltage drop of EPD24 and tolerance of trip point (typically $1.1 \times IN = 1.05 \dots 1.35 \times IN$) have been taken into account

Protection and safety technical details

EPD 24-TB-101

Selection table for the incoming cable lengths with different cable cross-sections

Cable cross section A (mm ²)	0.14	0.25	0.34	0.5	0.75	1.00	1.50
Cable length L (m) (= single length)	cable resistance (Ω) = $(\rho_0 \times 2 \times L) / A 3)$						
5	1.27	0.71	0.52	0.36	0.24	0.18	0.12
10	2.54	1.42	1.05	0.71	0.47	0.36	0.24
15	3.81	2.14	1.57	1.07	0.71	0.53	0.36
20	5.09	2.85	2.09	1.42	0.95	0.71	0.47
25	6.36	3.56	2.62	1.78	1.19	0.89	0.59
30	7.63	4.27	3.14	2.14	1.42	1.07	0.71
35	8.90	4.98	3.66	2.49	1.66	1.25	0.83
40	10.17	5.70	4.19	2.85	1.90	1.42	0.95
45	11.44	6.41	4.71	3.20	2.14	1.60	1.07
50	12.71	7.12	5.24	3.56	2.37	1.78	1.19
75	19.07	10.68	7.85	5.34	3.56	2.67	1.78
100	25.34	14.24	10.47	7.12	4.75	3.56	2.37
125	31.79	17.80	13.09	8.90	5.93	4.45	2.97
150	38.14	21.36	15.71	10.68	7.12	5.34	3.56
175	44.50	24.92	18.32	12.46	8.31	6.23	4.15
200	50.86	28.48	20.94	14.24	9.49	7.12	4.75
225	57.21	32.04	23.56	16.02	10.68	8.01	5.34
250	63.57	35.60	26.18	17.80	11.87	8.90	5.93

3) Resistivity of copper $r_0 = 0.0178 (\Omega \times \text{mm}^2)/\text{m}$

Example 1: max. length for 1.5 mm² and 3 A: 214 m

Example 2: max. length for 1.5 mm² and 6 A: 106 m

Example 3: mixed wiring: (Control cabinet --- sensor/actuator level)

$R1 = 40 \text{ m}$ for 1.5 mm² and $R2 = 5 \text{ m}$ for 0.25 mm²:

$R1 = 0.95 \Omega$, $R2 = 0.71 \Omega$, total $(R1 + R2) = 1.66 \Omega$

Please note

The user should ensure that the cable cross sections of the relevant load circuit are suitable for the current rating of the EPD24 used.

Automatic start-up of machinery after shut down must be prevented (Machinery Directive 98/37/EG and EN 60204-1).

In the event of a short circuit or overload the load circuit will be disconnected electronically by the EPD24.

Protection and safety technical details

EPD 24-TB-101

Information on UL approvals/CSA approvals



UL1604

Operating Temperature Code T5

- This equipment is suitable for use in Class I, Division 2, Groups A, B, C and D or non-hazardous locations only

WARNING:

- Exposure to some chemicals may degrade the sealing properties of materials used in the following device: relay
Sealant Material:

Generic Name: Modified diglycidyl ether of bisphenol A

Supplier: Fine Polymers Corporation

Type: Epi Fine 4616L-160PK

Casing Material:

Generic Name: Liquid Crystal Polymer

Supplier: Sumitomo Chemical

Type: E4008, E4009, or E6008

RECOMMENDATION:

- Periodically inspect the device named above for any degradation of properties and replace if degradation is found

WARNING – EXPLOSION HAZARD:

- Do not disconnect equipment unless power has been removed or the area is known to be non-hazardous
- Substitution of any components may impair suitability for Class I, Division 2



UL2367

Non-hazardous use



UL 508

Non-hazardous use



CSA C22.2 No. 213 (Class I, Division 2)

CSA C22.2 No. 142

Class 2

Meets requirement for Class 2 current limitation
(EPD24 ... -0,5 A/1 A/2 A/3 A)


Protection and safety technical details

EPD 24-TB-101

The EPD24 features an integral power distribution system.

The following wiring modes are possible with various pluggable current and signal busbars:

- LINE+ (24 V DC)
 - 0 V
- Caution:** The electronic devices EPD24 require a 0 V connection
- Auxiliary contacts



Mounting procedure

Before wiring insert busbars into protector block. A maximum of 10 connection cycles are permissible using connecting busbars.

Recommendation

After 10 units the busbars should be interrupted and receive a new entry live.

Table of length for busbars

(Order code 2CDE605100R0500)										
No. of units	2	3	4	5	6	7	8	9	10	
Length of busbar (mm) ± 0.5 mm	22	34.5	47	59.5	72	84.5	97	109.5	122	

Protection and safety technical details

SQZ3 phase and sequence relays

Operating principle

Through an output relay with contact in safety switching, the SQZ3 phase and sequence presence devices for 400 V a.c. three-phase networks enable the phase and sequence presence management monitoring also the minimum voltage (adjustable up to 70% of V_n). In case of any defect, the device operates within a range from 2 to 20 seconds, with the opportunity to control the appropriate acoustic signals, motor controlling contactors or circuit breakers.





Application environments

The installation of the SQZ3 phase and sequence presence relays are particularly suitable for any environment and situation where it is necessary to control the three-phase network operation promptly signalling any defect.



Example of installation

As shown in the diagrams, one of the possible applications is the installation of the SQZ3 phase and sequence presence relays in a department store, where the escalator supply circuit has a phase variation determining the SQZ3 relay intervention on the ESB contactor and causing the motor block and the alarm lighting indication.



Protection and safety technical details


RH/RL maximum and minimum current/voltage relays

Maximum voltage relay (RHV) application example

Monitoring a load with the following ratings:

$I_n = 5 \text{ A}$ (standard rated operating current)
 $V_n = 230 \text{ V a.c.}$ (standard rated operating voltage)
 $V_{max} = 250 \text{ V a.c.}$ (RHV relay intervention voltage)

1. Connect as in the diagram (since $V_{max} = 250 \text{ V}$).




2. Set the "Voltage%" trimmer to 83.33%, since:

$$V\% = \frac{250 \text{ (} V_{max} \text{)}}{300 \text{ (} V_{set} \text{)}} \times 100 = 83.33\%$$

being terminal 7-11 wired.

3. Set the "hysteresis %" trimmer; choosing 5% gives a intervention range from 237.5 to 250 V ($250 - 5\% = 237.5 \text{ V}$).
The relay will switch at 250 V and return to its normal state at 237.5 V
4. Adjust the "delay" trimmer to select the desired relay intervention delay (1...30 sec).
During this delay the "Power ON" LED blinks; at the end of the delay the "Alarm" LED becomes steadily lit and the relay intervenes.





Protection and safety technical details

E 236 undervoltage monitoring relays

Function

E



Protection and safety technical details

Insulation monitoring devices

ISOLTESTER-DIG

ISOLTESTER-DIG is the insulation monitoring device specifically designed by ABB for group 2 medical locations. ISOLTESTER-DIG measures the insulation to earth in IT-M network and the thermal and electrical overload of the insulation transformer, in accordance with the international standards: EN 61557-1, EN 61557-8 and IEC 60364-7-710.

Functioning principle

Insulation resistance is measured by applying a direct current signal between insulated line and earth and determining the dispersion current generated. Effective measurement is granted thanks to a digital filter integrated in the device even if interferences and harmonic components occur.

Programming

Through its LCD display and four selection keys, the device offers easy programming possibilities by setting intervention thresholds without making any for the complete monitoring of all electrical parameters. ISOLTESTER-DIG tests the thermal and electrical overload of the medical insulation transformer, managing two temperature thresholds coming from both PT100 and PTC probes. By controlling temperature, the overload of the transformer can be monitored and the automatic circuit-breaker downstream of the secondary can be avoided. All faulty conditions are remotely controlled thanks to QSD-DIG 230/24 remote signalling panels, granting a proper prompt technical supervision.

Self-testing system

Error-Link Fail system checks device proper functioning and controls wiring presence and properness at the end of the terminal blocks: it prevents the possibility to operate in group 2 medical locations when the insulation monitoring device is disconnected.

For better integration and improved monitoring

Thanks to the RS485 serial port, the ISOLTESTER-DIG-RS is able to communicate with the supervision system via ModbusRTU in order to collect all the required information of the monitored IT-M system in a centralized place. It also improves the monitoring activity with the possibility of logging measurements (max. and min. values). Logs can then be sent to the centralized control system via the communication protocol.

For higher safety

Thanks to a codified signal, the new ISOLTESTER-DIG-PLUS IT networks insulation monitoring device grants absolute reliability of measurement in any operational condition, even if high network interferences occur. Furthermore it is fitted with a RS485 serial port through which it can be perfectly integrated with communication systems such as PLC/PC by using ModbusRTU protocol. The measurement of network maximum and minimum values enables a wider monitoring and an easier plant checking in case of any fault. Finally, the programmable output relay allows to manage any warning condition signalled in a dedicated way.

- **Quality:** the recognized standard in hospital insulation control
- **Flexibility:** adjustable intervention thresholds according to all the parameters monitored
- **Completeness:** all electrical and thermal parameters controlled by a single device
- **Integration:** alarms sent up to 4 medical locations attended by medical and healthy staff, thanks to remote signalling panels. Only for RS and PLUS versions, ability to interact with supervising systems through ModbusRTU protocol via RS485 serial port

Protection and safety technical details

Insulation monitoring devices

ISOLTESTER-DIG

Frontal operators functioning

Green LED, SET:

Tool programming status

Yellow LED, Alarm:

Parameter out of threshold

3 digit display

Red LED, Output Relay:

Auxiliary relay status

Red LED, R:

Insulation resistance (kΩ)

Red LED, Error/Link Fail:
Internal fault alarm, faulty wiring to the line to be controlled, PT100 temperature probe open or under short-circuit

Red LED, Z:

Insulation impedance and line capacity (only for ISOLTESTER-DIG-PLUS)

TEST | ENTER:

Device and remote signalling panels testing and SETUP settings confirmation

Red LED, T1:

Primary winding temperature control

RESET | SET:

Device programming access, alarm disconnection and memorized values cancellation

Red LED, T2:

Secondary winding temperature control



+/-:

Selection of the parameter to be displayed, settings adjustment and memorized maximum and minimum values display (only for ISOLTESTER-DIG-PLUS/RS)

Red LED, I:

Line current

Easy programming by four pushbuttons



Protection and safety technical details

Insulation monitoring devices

ISOLTESTER-DIG-PLUS

Wherever it is necessary to guarantee safety and operational continuity and prevent power supply interruptions, such as in hospitals and in other medical locations, insulation transformers and devices detecting and signalling any first fault to earth have to be used.




Operating theaters equipment can generate interference within the network



A traditional monitoring device can generate an unwanted alarm in operating theaters

Risks arising from the use of a traditional insulation monitor:



Impossibility to distinguish between interference and real fault

Carelessness of the medical staff

Unjustified intervention of specialized technical stuff

ISOLTESTER-DIG-PLUS is the device for insulation monitoring in IT-M networks. It ensures absolute reliability of measurement by means of a codified signal able to detect interferences generated by common equipment in operating theatres and avoid unwanted alarms signalling.



Despite network interferences...



ISOLTESTER-DIG-PLUS avoids unwanted alarms.

Advantages of ISOLTESTER-DIG-PLUS:



Monitoring reliability

Integration with supervision systems

Proper fault analysis

Complete control of network parameters


Protection and safety technical details

Insulation monitoring devices

QSD-DIG 230/24

TEST
Pushbutton

ABB



Green LED
device is working
properly

MUTE
Pushbutton


Red LED
overload alarm

Yellow LED
fault alarm

Protection and safety technical details

TI insulating transformers for medical locations

Wirings and serial number location



- ① Primary winding**
0-230: Primary
SCH: Metallic shield

- ② PE**

- ③ Secondary winding**
0-230: Secondary
SCH: Central socket

- ④ Probe 1**

- 1: to ISOLTESTER-DIG 28 terminal block
2: to ISOLTESTER-DIG 28 terminal block
3: to ISOLTESTER-DIG 30 terminal block

- ⑤ Probe 2**

- 4: to ISOLTESTER-DIG 25 terminal block
5: to ISOLTESTER-DIG 25 terminal block
6: to ISOLTESTER-DIG 27 terminal block



Serial number


printed on the label attached at the metallic base, to be provided when requesting testing certificate

Protection and safety technical details

QSO switchboard for medical locations

Operating diagrams

QSO S




Description	QSO 3S Classic	QSO 5S Classic	QSO 3S Premium	QSO 5S Premium
2P 40 A SD202/40 disconnector	2	2	2	2
2P 63 A SD202/63 disconnector			1	1
E 91hN/32 fuse-holder	2	2	3	3
E219-D green light indicator power supply presence	1	1	2	2
ISOLTESTER-DIG-RZ insulation monitoring device	1	1	1	1
6 kA 2P C10 S202 miniature circuit-breaker	2	2	2	2
6 kA 2P C16 S202 miniature circuit-breaker	5	5	5	5
6 kA 2P C25 S202 miniature circuit-breaker	1	1	1	1
25 kA 2P S752 DR-K25 miniature circuit-breaker	1	1	1	1
1N 10 A 0,03 A DS202 C C10 A30 residual current breaker with overcurrent protection			1	1
1N 16 A 0,03 A DS202 C C16 A30 residual current breaker with overcurrent protection			2	2
AMM damper set	4	4	4	4
CT PRO XT40 current transformer	1	1	1	1
Medical insulation transformer with 3000 VA 230/230 V TI 3-S probes	1		1	
Medical insulation transformer with 5000 VA 230/230 V TI 5-S probes			1	
10 x 38 gG 2A E 9F10 GG2 fuse	4	4	6	6

Protection and safety technical details

QSO switchboard for medical locations

QSO M




Description	QSO 3M Classic	QSO 5M Classic	QSO 7,5M Classic	QSO 3M Premium	QSO 5M Premium	QSO 7,5M Premium
2P 63 A SD202/63 disconnector	3	3	3	3	3	3
E 91hN/32 fuse-holder	3	3	3	4	4	4
E219-D green light indicator power supply presence	2	2	2	2	2	2
ISOLTESTER-DIG-RZ insulation monitoring device	1	1	1	1	1	1
24 V SELVTESTER-24 insulation monitoring device				1	1	1
OVR T2-T3 1N 20-275 P QS surge protective device				2	2	2
6 kA 2P C10 S202 miniature circuit-breaker	3	3	3	8	8	8
6 kA 2P C16 S202 miniature circuit-breaker	7	7	7	8	8	8
6 kA 2P C25 S202 miniature circuit-breaker				1	1	1
M1175-FL 2P+T 16 A schucko socket with indicator lamp and fuse	1	1	1	1	1	1
25 KA 2P S752 DR-K25 miniature circuit-breaker	1	1		1	1	
25 KA 2P S752 DR-K40 miniature circuit-breaker				1		1
1N 10 A 0,03 A DS202 C C10 A30 residual current breaker with overcurrent protection	1	1	1	1	1	1
1N 16 A 0,03 A DS202 C C16 A30 residual current breaker with overcurrent protection				2	2	2
AMM damper set	4	4	4	8	8	8
CT PRO XT40 current transformer	1	1	1	1	1	1
TM-S 1000/12-24 P. 230-400V S. 24V control and safety transformer				1	1	1
Medical insulating transformer with 3000 VA 230/230 V TI 3-S probes	1			1		
Medical insulating transformer with 5000 VA 230/230 V TI 5-S probes		1			1	
Medical insulating transformer with 7500 VA 230/230 V TI 7,5-S probes			1			1
10 x 38 gG 2A E 9F10 GG2 fuse	6	6	6	8	8	8

Protection and safety technical details

QSO switchboard for medical locations

QSO L




Description	QSO 10L Classic	QSO 7.5 L Premium	QSO 10 L Premium
2P 63 A SD202/63 disconnector	3	3	3
E 91hN/32 fuse-holder	3	4	4
E219-D green light indicator power supply presence	2	2	2
BE/S 4.20.2.1 4 channel binary input terminal			1
ISOLTESTER-DIG-RZ insulation monitoring device	1	1	1
24 V SELVTESTER-24 insulation monitoring device		1	1
10 A SA/S 4.10.1 4 channel output terminal			1
OVRS 1000/12-24 P			
S2-CS/H6R auxiliary contact 1 exchange			1
6 kA 2P C10 S202 miniature circuit-breaker	6	8	8
6 kA 2P C16 S202 miniature circuit-breaker	9	11	11
6 kA 2P C25 S202 miniature circuit-breaker		3	3
6 kA 2P C32 S202 miniature circuit-breaker		1	1
M1175-FL 2P+T 16 A schucko socket with indicator lamp and fuse	1	1	1
25 kA S752 DR-K40 miniature circuit-breaker		1	
25 kA S752 DR-K50 miniature circuit-breaker		1	
25 kA S752 DR-K50+S750DR-AUX miniature circuit-breaker			1
1N 10A 0,03A DS202 C C10 A30 residual current breaker with overcurrent protection	1	1	1
1N 16A 0,03A DS202 C C16 A30 residual current breaker with overcurrent protection	2	2	2
AMM damper set	4	8	8
CT PRO XT50 current transformer	1	1	1
TM-S 1000/12-24 P. 230-400 V S.24 V control and safety transformer		1	1
Medical insulating transformer with 7500 VA 230/230 V TI 7,5-S probes		1	
Medical insulating transformer with 10000 VA 230/230 V TI 10-S probes	1		1
10 x 38 gG 2A E 9F10 GG2 fuse	6	8	6

Protection and safety technical details

Insulation monitoring devices


Insulation monitoring devices ISL for industrial applications

ISL-A 24-48



MICROSWITCH SETTINGS


The front microswitches allow the insulation threshold level to be adjusted between 10 and 60 kΩ, as shown below:



Protection and safety technical details

Insulation monitoring devices

ISL-A 115 and ISL-A 230



MICROSWITCH SETTINGS

The front microswitches are used for adjusting the insulation threshold level, enabling the fail-safe function and configuring the reset mode for both the alarm and trip thresholds.

Microswitches A, B, C, D for programming the trip and alarm thresholds:

ALARM	TRIP
300 kΩ:	A=0, B=0, C=0, D=0
150 kΩ:	100 kΩ: A=0, B=0, C=0, D=0 60 kΩ: A=1, B=0, C=0, D=0
80 kΩ:	40 kΩ: A=1, B=1, C=0, D=0
50 kΩ:	20 kΩ: A=1, B=1, C=1, D=0
30 kΩ:	10 kΩ: A=1, B=1, C=1, D=1

Microswitch E for configuring the FAIL SAFE mode

E=0 fail safe mode disabled

E=1 fail safe mode enabled

Microswitch F for configuring the RESET mode


F=0 manual reset

F=1 automatic reset

Protection and safety technical details

Insulation monitoring devices


ISL-A 600




Protection and safety technical details

Insulation monitoring devices

ISL-C 230




ISL-C 440



MICROSWITCH SETTINGS




The front microswitches are used for adjusting the insulation threshold level between 10 and 150 kΩ, as shown below:



Protection and safety technical details

Insulation monitoring devices


ISL-C 600



Protection and safety technical details


Insulation monitoring devices

ISL-MOT 1000



MICROSWITCH SETTINGS

The front microswitches are used for adjusting the insulation threshold level between 0.1 and 10 MΩ. A total of 7 microswitches are used, divided into two groups as shown below:



Protection and safety technical details

Insulation monitoring devices

Operating principle

In IT electrical distribution systems that supply critical applications, where operational continuity is essential, ISL insulation monitoring devices assure continuous surveillance to promptly detect any insulation loss.

Application environments

All IT distribution systems in which operational continuity is a critical factor, and in particular:



- 24-28 V, 100-144 V and 220 V d.c. networks
- 24-48 V, 100-144 V and 380-415 V a.c. networks
- 20-700 V a.c./d.c. voltageless networks

Example of installation

ISL-MOT 1000 is suitable for preventive protection of voltageless circuits such as alarm and fire-fighting systems, pumps, etc.

ISL-MOT 1000 continually monitors the insulation level between the line and earth, to guarantee that the system will function correctly when needed.

The trip threshold is programmable, and insulation loss can be signalled via a change-over contact, which can also be used for switching loads.



Electrical installation solutions for buildings – Technical details

Command and signaling



Index

E 200 switches	6/2
E 463 switches	6/3
E 210 switches	6/4
Technical data – Pushbuttons and indicator lights	6/5
Sample applications – On-off switches and control switches	6/6
Sample applications – Change over switches and group switches	6/7
Sample applications – Push buttons	6/8
Sample applications – Multiple indicator lights	6/9
Installation contactors	6/12
E 290 latching relays	6/20
E 291 sequential latching relays	6/26
LED lamp latching relays	6/29
E 297 installation relays	6/31
E 260 latching relays	6/36
STD dimmers	6/37
Modular transformers	6/38
Control, isolating and safety transformers	6/39
CP-D power supplies and the CP-D redundancy units	6/48
Modular sockets	6/56


Command and signaling technical details

E 200 switches


E200 Short-circuit withstand capacity



Assembling of S2C-H 6R and E 200




E 200 DC switching capacity



Command and signaling technical details

E 463 switches


E463 / E480 Short-circuit withstand capacity




Command and signaling technical details

E 210 switches


DC switching capacity E211 16A



DC switching capacity E211 25A



DC switching capacity E211 32A



Ohmic load
 — Normally-open contact
 — Normally-closed contact

Load with time constant
 $t = 15\text{ms}$ (inductive load)
 — Normally-open contact
 — Normally-closed contact

Command and signaling technical details


Technical data – Pushbuttons and indicator lights

**Overview of general meanings of the colours of operator control parts
(excerpt from VDE 0199 or DIN EN 60073).**

Colour	Meaning	Explanation	Application examples
RED	Emergency	Action in hazardous situations or emergency	EMERGENCY STOP, STOP or OFF with EMERGENCY STOP pushbutton Initiating an emergency function
YELLOW	Abnormal	Action if an abnormal condition is present	Intervention required to suppress the abnormal condition, manual intervention to restart an interrupted automatic cycle
GREEN	Safety	Action in safe conditions or to prepare a normal condition	Activation
BLUE	Regulation	Status requiring action	Reset function
WHITE GREY BLACK	Non-specific	Functions start	Available for any functions except, except for emergency stop, e.g. ON/OFF; Stop/Start

Command and signaling technical details


Sample applications – On-off switches and control switches



Additional garden lighting

On-off switches E211-16-20 (2NO contacts) and indicator lights E219-D

- On-off control for additional garden light
- The green indicator light in the central distribution board shows whether the garden light is ON or OFF




Room ventilator with status display

Control switches E218-25-31 (3NO + 1NC contacts) and E219-D48; E219-C48

- On-off function control of a ventilator
- Integrated signal lamp 24 V for status detection is directly embedded at the ventilator
- The green and red indicator lights 12-48 V show the current operating position in the central distribution board

Command and signaling technical details


Sample applications – Change over switches and group switches



Flap gate control

Change over switches E213-16-001 with position I-II (1CO contact) and E219-G; E219-B

- Control of a manual flap gate position with central visualization
- The blue indicator light shows that the flap gate is open
- The white indicator light shines in closed state




Electrical room heater

Group switches E214-16-101 with position I-0-II (1CO contact) and E219-E; E219-G

- Changeover switching of manual control to time switch mode, e. g. for an additional heater
- The yellow indicator light shows that the control mode occurs manually
- The heater is set on automatic control when the blue E219-G shines

Command and signaling technical details

Sample applications – Push buttons





Room lighting (fluorescent-tubes)

Pushbuttons mit 1NO contact (impulse) with green LED

- Lighting system with latching relay (impulse switching relais)
- The green LED which is integrated in the pushbutton shines when the lighting group has the status ON

Command and signaling technical details


Sample applications – Multiple indicator lights




Network and phase control

Multiple indicator lights E219-3D (3x green LEDs)

- All LEDs shine → Net is working
- If one phase breaks down, the green LED turns off
→ Attention! Phase break down in the network



Signaling motor OFF



Signaling motor ON


Motor status display

Multiple indicator lights E219-2CD (1x green, 1x red LED)


- ABB three-phase contactor (remote controlled with 2 auxiliary contacts (1NO + 1NC))
- The current operating mode of the motor drive is visualized over auxiliary contacts.

Command and signaling technical details

Sample applications – Multiple indicator lights



Signaling motor OFF



Signaling motor ON


Motor status display

Multiple indicator lights E219-3CDE (1x green, 1x yellow, 1x red LED)

- ABB polyphase contact gate (remote control) with 2 auxiliary contacts (1NO + 1NC)
- The current operating mode of the motor drive is visualized over contactor auxiliary contacts
- The error indication occurs over the signalling contact of the motor protection relay

Command and signaling technical details

Sample applications – Multiple indicator lights



**Signaling motor interference
on basis of thermal overload**

Motor status display (off and interruption)

Multiple indicator lights E219-3CDE (1x green, 1x yellow, 1x red LED)

- A thermal activation is signalized by the use of motor protection relay contacts
- Motor off = green LED on; closed motor protection relay contact = yellow LED shows interference

Command and signaling technical details

Installation contactors

Technical data main circuit

Main circuit – Utilization characteristics according to IEC/EN

Contactor type		ESB16..N	ESB20..N/ EN20..N	ESB25..N/ EN25..N	ESB40..N/ EN40..N	ESB63..N	ESB100..N
Standards	IEC/EN 60947-1, IEC/EN 60947-4-1, IEC/EN 61095						
Rated operational voltage U_e		220 V DC 250 V AC	220 V DC 250 V AC	220 V DC 400 V AC	220 V DC 400 V AC	220 V DC 400 V AC	220 V DC 400 V AC
Rated frequency		DC, 50/60 Hz	DC, 50/60 Hz	DC, 50/60 Hz	DC, 50/60 Hz	DC, 50/60 Hz	DC, 50/60 Hz
AC-1/AC-7a utilization category for air temperature near the contactor $\leq 55^\circ\text{C}$							
Rated operational current I_e AC-1/AC-7a	NO NC	16 A 16 A	20 A 20 A	25 A 25 A	40 A 30 A	63 A 30 A	100 A -
Rated operational power AC-1	230 V 1 phase 400 V 3 phases	3.7 kW	4.6 kW	5.8 kW	9.2 kW	14.5 kW	23 kW
AC-3/AC-7b utilization category for air temperature close to contactor $\leq 55^\circ\text{C}$							
Rated operational current I_e AC-3/AC-7b	230 V 1 phase 400 V 3 phases	6 A -	9 A -	9 A 9 A	22 A 22 A	30 A 30 A	-
Rated operational power AC-3	230 V 1 phase 400 V 3 phases	0.9 kW	1.3 kW	1.3 kW	3.7 kW	5 kW	-
Rated making capacity AC-3 acc. to IEC 60947-4-1	$10 \times I_e$ /AC-3	$10 \times I_e$ /AC-3	$10 \times I_e$ /AC-3	$10 \times I_e$ /AC-3	$10 \times I_e$ /AC-3	$10 \times I_e$ /AC-3	-
Rated breaking capacity AC-3 acc. to IEC 60947-4-1	$8 \times I_e$ /AC-3	$8 \times I_e$ /AC-3	$8 \times I_e$ /AC-3	$8 \times I_e$ /AC-3	$8 \times I_e$ /AC-3	$8 \times I_e$ /AC-3	-
Short-circuit protective devices - gG type fuses, type 1 coordinated		20 A	20 A	35 A	63 A	80 A	125 A
Rated short-time withstand current I_{cw} at 40°C ambient temp. in free air, from a cold state	10 s	48 A	72 A	72 A	176 A	240 A	-
Minimum switching capacity		17 V/200 mA	17 V/200 mA	17 V/200 mA	17 V/200 mA	17 V/200 mA	17 V/200 mA
Power loss per pole		0.9 W	1.4 W	2 W	3 W	4.5 W	6 W
Maximum electrical switching frequency	AC-1/AC-7a AC-3/AC-7b	300 cycles/h 600 cycles/h	300 cycles/h 600 cycles/h	300 cycles/h 600 cycles/h	300 cycles/h 600 cycles/h	150 cycles/h -	
Electrical durability	AC-1/AC-7a AC-3/AC-7b	150,000 cycles	150,000 cycles	130,000 cycles	150,000 cycles	100,000 cycles	70,000 cycles
Mechanical durability		1,000,000 cycles					

Command and signaling technical details

Installation contactors

Technical data main circuit and control circuit

Main circuit – Utilization characteristics according to UL/CSA

Contactor type	ESB16..N	ESB20..N/ EN20..N	ESB25..N/ EN25..N	ESB40..N/ EN40..N	ESB63..N	ESB100..N
Standards	UL 60947-1, UL 60947-4-1					
General use rating	240 V	16 A	20 A	–	–	–
	480 V	–	–	25 A	40 A	63 A
Motor rating						–
Full load current	220 ... 240 V 1 phase	6.9 A	8 A	–	–	–
	220 ... 240 V 3 phases	–	–	9.6 A	22 A	28 A
	440 ... 480 V 3 phases	–	–	7.6 A	21 A	21 A
Horse power rating	220 ... 240 V 1 phase	0.8 hp	1 hp	–	–	–
	220 ... 240 V 3 phases	–	–	3 hp	7.5 hp	10 hp
	440 ... 480 V 3 phases	–	–	5 hp	15 hp	15 hp
Short-circuit protection for contactors without thermal O/L relay - Motor protection excluded						–
Fuse rating	20 A	20 A	25 A	40 A	75 A	125 A
Fuse type 480 V	K5	K5	K5	K5	K5	K5
Max. electrical switching frequency						–
for general use	300 cycles/h	300 cycles/h	300 cycles/h	300 cycles/h	300 cycles/h	150 cycles/h
for motor use	600 cycles/h	600 cycles/h	600 cycles/h	600 cycles/h	600 cycles/h	–

General technical data

Contactor type	ESB16..N	ESB20..N/ EN20..N	ESB25..N/ EN25..N	ESB40..N/ EN40..N	ESB63..N	ESB100..N
Rated insulation voltage U_i acc. to IEC 60947-4-1 and VDE 0110 (Gr. C)	400 V	400 V	500 V	500 V	500 V	500 V
Rated impulse withstand voltage U_{imp}		6 kV EN: 6 kV	ESB: 6 kV EN: 4 kV/6 kV with protection cover		6 kV	6 kV
Ambient air temperature range ⁽¹⁾	operation storage	-25 ... +55 °C -40 ... +80 °C	-25 ... +55 °C -40 ... +80 °C	-25 ... +55 °C -40 ... +80 °C	-25 ... +55 °C -40 ... +80 °C	-25 ... +55 °C -40 ... +80 °C
Maximum operating altitude permissible	2000 m	2000 m	2000 m	2000 m	2000 m	2000 m
Vibration (sinusoidal) according to IEC/EN 60068-2-6 (Fc)	1 g/3-150 Hz	1 g/3-150 Hz	1 g/3-150 Hz	1 g/3-150 Hz	1 g/3-150 Hz	
Shock (half-sine) according to IEC/EN 60947-1 Annex Q	Category E	Category E	Category E	Category E	Category E	Category E
Shock (half-sine) according to IEC/EN 60068-2-27 (Ea)	15g/11ms	15g/11ms	15g/11ms	15g/11ms	15g/11ms	15g/11ms

1) If several contactors are mounted adjacently and the duty time is longer than one hour, every second contactor needs a distance piece, Type ESB-DIS (1/2 module).
This is not necessary at an ambient temperature $\leq 40^{\circ}\text{C}$ or on Type ESB16..N, ESB/EN20..N and ESB100..N

Magnet system characteristics


Contactor type	ESB16..N	ESB20..N/ EN20..N	ESB25..N/ EN25..N	ESB40..N/ EN40..N	ESB63..N	ESB100..N	
Coil operating limits acc. to IEC/EN60947-4-1	0.85 ... 1.1 $\times U_c$ (at $\theta \leq 55^{\circ}\text{C}$)						
Rated frequency	DC, 50/60/400 Hz						
Frequency range	DC, 40 ... 450 Hz						
Coil consumption	pull-in 60 Hz DC holding 60 Hz DC	2.5 VA 2.5 VA 2.5 W 2.5 VA 2.5 VA 2.5 W	2.5 VA 2.5 VA 2.5 W 2.5 VA 2.5 VA 2.5 W	4 VA 4 VA 4 W 4 VA 4 VA 4 W	4.5 VA 4.5 VA 5 W 4.5 VA 4.5 VA 5 W	60 VA 60 VA 70 W 4.5 VA 4.5 VA 5 W	90 VA 90 VA 100 W 7.5 VA 7.5 VA 8.5 W

Command and signaling technical details

Installation contactors

Technical data main circuit and control circuit

Mounting characteristics and conditions for use

Contactor type	ESB16..N	ESB20..N/ EN20..N	ESB25..N/ EN25..N	ESB40..N/ EN40..N	ESB63..N	ESB100..N
Mounting position	Position 1 to 5	 Pos. 2 Pos. 4 Pos. 1 Pos. 3	 +30° -30° Pos. 1 ± 30° Pos. 5			
Mounting on DIN rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715					

Main circuit - Connecting characteristics

Contactor type	ESB16..N	ESB20..N/ EN20..N	ESB25..N/ EN25..N	ESB40..N/ EN40..N	ESB63..N	ESB100..N
Connecting capacity						
Rigid	1x 1 ... 10 mm ² 2x 1 ... 4 mm ²	1x 1 ... 10 mm ² 2x 1 ... 4 mm ²	1x 1.5 ... 10 mm ² 2x 1.5 ... 4 mm ²	1x 1.5 ... 25 mm ² 2x 1.5 ... 10 mm ²	1x 1.5 ... 25 mm ² 2x 1.5 ... 10 mm ²	1x 10 ... 50 mm ²
Flexible with ferrule	1x 1 ... 6 mm ² 2x 1 ... 2.5 mm ²	1x 1 ... 6 mm ² 2x 1 ... 2.5 mm ²	1x 1.5 ... 10 mm ² 2x 1.5 ... 2.5 mm ²	1x 1.5 ... 16 mm ² 2x 1.5 ... 10 mm ²	1x 1.5 ... 16 mm ² 2x 1.5 ... 10 mm ²	1x 10 ... 35 mm ²
Flexible with insulated ferrule	1x 1 ... 6 mm ² 2x 1 ... 1.5 mm ²	1x 1 ... 6 mm ² 2x 1 ... 1.5 mm ²	1x 1.5 ... 10 mm ² 2x 1.5 mm ²	1x 1.5 ... 16 mm ² 2x 1.5 ... 10 mm ²	1x 1.5 ... 16 mm ² 2x 1.5 ... 10 mm ²	1x 10 ... 35 mm ²
Flexible	1x 1 ... 6 mm ² 2x 1 ... 4 mm ²	1x 1 ... 6 mm ² 2x 1 ... 4 mm ²	1x 1.5 ... 10 mm ² 2x 1.5 ... 4 mm ²	1x 1.5 ... 16 mm ² 2x 1.5 ... 10 mm ²	1x 1.5 ... 16 mm ² 2x 1.5 ... 10 mm ²	1x 10 ... 35 mm ²
Stranded acc. to UL/CSA	14-8 AWG	14-8 AWG	16-8 AWG	16-4 AWG	16-4 AWG	8-0 AWG
Degree of protection	IP20	IP20	IP20	IP20	IP20	IP20
Wire stripping length	10 mm	10 mm	10 mm	13 mm	13 mm	15 mm
Tightening torque	1.2 N·m/ 11 lb.in	1.2 N·m/ 11 lb.in	1 N·m/ 9 lb.in	2.5 N·m/ 20 lb.in	2.5 N·m/ 20 lb.in	3 N·m/ 27 lb.in
Recommended screw driver	Pozidriv 1	Pozidriv 1	Pozidriv 1	Pozidriv 2	Pozidriv 2	Pozidriv 2

Control circuit - Connecting characteristics

Command and signaling technical details

Installation contactors
Technical data auxiliary circuit

Auxiliary circuit - Utilization characteristics according to IEC/EN

For ambient temperature $T_u = 40^\circ\text{C}$ if not stated otherwise.

Contactor type	EH04-xxN		
Standards	IEC/EN 60947-1, IEC/EN 60947-5-1		
Rated operational voltage U_e	500 V AC 250 V DC		
Rated frequency	DC, 50/60 Hz		
Rated operational current I_e AC-15	24 V	NO/NC	6 A/6 A
	120 V	NO/NC	6 A/6 A
	240 V	NO/NC	4 A/4 A
	415 V	NO/NC	3 A/3 A
	500 V	NO/NC	2 A/2 A
Rated operational current I_e DC-13	125 V	NO/NC	0.55 A/0.55 A
	250 V	NO/NC	0.27 A/0.27 A
Minimum switching capacity	17 V/5 mA		
Short-circuit protective devices	10 A, gG type fuse		
Mechanical durability	1,000,000 cycles		
Electrical durability	AC-15	240 V/4 A	100,000 cycles
	DC-13	125 V/0.55 A	100,000 cycles
Maximum electrical switching frequency	AC-15	360 cycles/h	
	DC-13	360 cycles/h	

General technical data

Contactor type	EH04-xxN		
Duty time	100%		
Rated impulse withstand voltage U_{imp} acc. to IEC/EN 60947-1	4 kV		
Rated insulation voltage U_i acc. to IEC/EN 60947-1	500 V		
Pollution category acc. to IEC/EN 60664	2		
Overvoltage category acc. to IEC/EN 60664	Up to III		
Maximum operating altitude permissible	2000 m		
Ambient air temperature range	Operation	Open	-25 °C ... +55 °C
	Storage		-40 °C ... +80 °C
Vibration (sinusoidal) acc. to IEC/EN 60068-2-6 (Fc)	5 g/3-150 Hz		
Shock (half-sine) acc. to IEC/EN 60947-1 Annex Q	Category E		
Shock (half-sine) acc. to IEC/EN 60068-2-27 (Ea)	15 g/11 ms		

Auxiliary circuit - Utilization characteristics according to UL/CSA

Contactor type	EH04-xxN		
Standards	UL 60947-1, UL 60947-4-1		
Max. operational voltage	600 V AC		
Pilot duty	A600		
Thermal continuous test current	10 A		
General use rating	600 V AC per pole		

Command and signaling technical details

Installation contactors
Technical data auxiliary circuit

Mounting characteristics and conditions for use

Contactor type	EH04-xxN		
Mounting position	Position 1	0°	Yes
	Position 2	180°	Yes
	Position 3	270°	Yes
	Position 4	90°	Yes
	Position 5	standing	Yes
	Position 6	upside down	Not allowed
Mounting on DIN rail	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715		

Auxiliary circuit - Connecting characteristics

Contactor type	EH04-xxN	
Connecting capacity		
 Rigid	1x 1 mm ² ... 4 mm ² 2x 1 mm ² ... 1.5 mm ²	
 Flexible with ferrule	1x 1 mm ² ... 1.5 mm ²	
 Flexible with insulated ferrule	-	
 Flexible	1x 1 mm ² ... 1x 2.5 mm ²	
Stranded acc. to UL/CSA	AWG 18.... AWG 12	
Degree of protection	IP20	
Wire stripping length (upper/lower)	17 mm ($\leq 1.5\text{mm}^2$ 7 mm) / 9 mm ($\leq 1.5\text{mm}^2$ 7 mm)	
Tightening torque	0.9 N·m/ 8 lb.in	
Recommended screw driver	Pozidriv 1	

Command and signaling technical details

Installation contactors

DC switching table installation contactors

Type	Rated operational voltage	Contact	DC-1/A 1-pole	DC-3/A 1-pole
ESB16-..N	24 V DC	NO	16	12
	48 V DC		12	6
	60 V DC		12	4
	110 V DC		4	1.2
	220 V DC		0.4	0.2
	24 V DC	NC	11	5
	48 V DC		6	2
	60 V DC		4	1.5
	110 V DC		1.2	0.4
	220 V DC		0.2	0.1
ESB20-..N	24 V DC	NO	20	15
	48 V DC		15	7
	60 V DC		15	5
	110 V DC		5	1.5
	220 V DC		0.5	0.2
	24 V DC	NC	14	6
	48 V DC		7	3
	60 V DC		4.5	2
	110 V DC		1.5	0.6
	220 V DC		0.2	0.1

Type	Rated operational voltage	Contact	DC-1/A 3 poles in series	DC-3/A 3 poles in series
ESB25-..N	24 V DC	NO	24	24
	48 V DC		24	24
	60 V DC		24	24
	110 V DC		24	16
	220 V DC		13	4
	24 V DC	NC	24	19
	48 V DC		22	9.4
	60 V DC		17.5	7.5
	110 V DC		9.5	4.1
	220 V DC		3.8	1.6
ESB40-..N	24 V DC	NO	40	40
	48 V DC		40	40
	60 V DC		40	34
	110 V DC		30	18
	220 V DC		15	4.5
ESB63-..N	24 V DC	NO	63	63
	48 V DC		63	47
	60 V DC		60	38
	110 V DC		33	21
	220 V DC		17	5
ESB100-..N	24 V DC	NO	100	100
	48 V DC		100	70
	60 V DC		80	45
	110 V DC		50	25
	220 V DC		35	7

Command and signaling technical details

Installation contactors

Lamp load table

Please note that switching lamps is a capacitor load application where high inrush current peaks could occur. These are influenced by the length and cross section of the wire as well as the type of power supply unit and specifications of the lamp brand. For example, long cables can increase the possible number of lamps per pole. The table shows the allowed max. current for one pole and considers already the startup current peaks.

The following selection table shows the current values and the maximum switchable capacitor load for compensated lamps. These two limits have to be considered in the selection of contactors.

	ESB16..N EN20..N	ESB20..N EN25..N	ESB25..N EN25..N	ESB40..N EN40..N	ESB63..N	ESB100..N
Permitted compensating capacity per phase Cmax [μ F]	45	75	100	350	500	650
Lamp types	Maximum load of the current paths during switching of electric lamps I_e [A]					
Incandescent and halogen lamps (230 V)	4	6	7	20	30	45
Mixing lamps without ballast	4	6	7	20	30	45
Fluorescent lamps with conventional ballast	single lamp uncompensated 14	18	22	36	56	90
	single lamp parallel compensated 2	3	3.5	10	15	22
	series compensation, duo circuit 14	18	22	36	56	90
Fluorescent lamps with electronic ballast or CFL	4	6	7	20	30	45
LED lamps	4	6	7	20	30	45
High pressure mercury-vapor lamps	single lamp without compensation 7	9	11	18	28	45
	single lamp with parallel compensation 2	3	3.5	10	15	22
Halogen metal-vapor lamps	single lamp without compensation 7	9	11	18	28	45
	single lamp with parallel compensation 2	3	3.5	10	15	22
High pressure sodium-vapor lamps	single lamp without compensation 7	9	11	18	28	45
	single lamp with parallel compensation 2	3	3.5	10	15	22
Low pressure sodium-vapor lamps	single lamp without compensation 7	9	11	18	28	45
	single lamp with parallel compensation 2	3	3.5	10	15	22

Example for lamp load calculation

Due to many varieties of lamps and ballasts we advice to take the current load as base for reference. The lamp table considers already the inrush peaks and other lamp parameters. Please see the following examples for a reliable project lamp calculation.

Fluorescent lamp with conventional ballast, uncompensated the lamp operating current $I = 1.5$ A, voltage $U = 230$ V

1 pole of ESB25..N can be loaded with max. 22 A,
see lamp table => $22\text{ A} / 1.5\text{ A} = 14.66 \Rightarrow 14$ lamps

1 pole of ESB20..N can be loaded with max. 18 A,
see lamp table => $18\text{ A} / 1.5\text{ A} = 12$ lamps

Please use the referring value in the table stated above and divide it with the current stated on the lamp. This will lead to the number of lamps which can be switched.


Example with picture: ESB25..N used for LED lamps:
 $7\text{ A} (= 7000\text{ mA}) / 85\text{ mA} = 82.23 \Rightarrow 82$ lamps



Command and signaling technical details

Installation contactors

Voltage code table



⁽¹⁾ 110 V - 120 V for ESB25..N/EN25..N

⁽²⁾ only coil 6 available with 230 V - 240 V for ESB25..N/EN25..N


⁽³⁾ only coil 7 available with 400 V - 415 V for ESB25..N

⁽⁴⁾ Coil 8 available for ESB40-40N and ESB63-40N only.

Command and signaling technical details

E290 latching relays

E290 Latching Relay




Safety information

If more than one Latching relay installed next to each other, it is recommended to use a intermediate piece (distance). This guarantees optimal heat dissipation by the main modules. The intermediate pieces (9 or 18mm wide) can be found in the order information as types ZLS725 or ZLS726 (the use depends on the application).


Command and signaling technical details

E290 latching relays


E290-16-10 + E299-11 — Latching Relay with Auxiliary Contact




Application at a normal light control via different push buttons (PB);
The snapped-on auxiliary contact (E299-11) displays the current switching state of the light control (ON/OFF).



E290-16-10 + E292-16-11 + E299-11 — Latching Relay with Auxiliary Contact




Latching Relay E290 with attached contact module E292-16-11 (additional main contact tracks) plus an auxiliary contact to externally display the switching state of the main contacts (ON/OFF).



E290-16-10 + 295-PS — Latching Relay with permanent signal module



This combination permits control of the E290 coil via a permanent signal (e.g. directly controlled by a timer or a twilight switch). When using this accessory, manual switching at the main unit is not possible.




Command and signaling technical details

E290 latching relays

E290-16-10 + E293/X — Latching Relay with Central Control Module




The function of a Central ON/OFF control is implemented by using the accessory E293/X. The E293/X Central ON/OFF module uses the same coil voltage potential as the main unit E290. The light control can be either on site via the local buttons, or by the Central ON/OFF button.



E290-16-10 + E294/230 — Latching Relay with Central Control Module




This is a second possibility to implement a Central ON/OFF control. When a E294/... accessory is snapped on, this Central ON/OFF device uses a different voltage source for coil control. The light control can be performed locally on site via the regular button. The Central ON/OFF button permits a general switching state change from a central location.



E296CP + E290-16-10 + E299-11 — Latching Relay with Auxiliary Contact plus Compensator




The compensator E296-CP is used every time a certain number of lit local buttons is exceeded.



Command and signaling technical details

E290 latching relays

E290-16-10 + E293/X + E295GM — Latching Relay with Central Control Module and Group Module



An example of a central ON/OFF control E290 with E293/X combined with Group Modules E295-GM; The Group Modules are integrated into the control to be structured into different light area groups. The on-site local buttons permit individual control of each Latching Relay. The Integration of the Group Modules into this control permits a distribution into two groups. Pushing the button „Group ON/OFF“ permits individual switching of each group. The general button „Central ALL ON/OFF“ can put the switching state of all E290 devices into the desired position (ON/OFF).

Command and signaling technical details

E290 latching relays

In an office building, supermarket or other large building complex, latching relays can be used to achieve a flexible, modern and reliable lighting control system for the whole site.

Application for an E290 Latching Relay:

Each time the impulse button is operated, an electrical pulse is applied to the latching relay that results in a change to the switching state. This state is held mechanically until the next pulse is received.


Switching sequence:

OFF – ON – OFF – ON

The main application for a latching relay is to simply switch various independent lighting areas on and off. Switching from „on“ to „off“ is carried out by means of a short impulse.

As the device coil of the latching relay is only excited by a pulse for a short time during switching, no additional holding energy is required. The contact position (on/off) is held by means of a mechanical interlock until the next pulse command is sent. In the event of a power failure, the current switch position will always be held. This technology considerably helps to reduce the temperature rise and current consumption of devices operated by magnetic coils, thus saving on unnecessary energy costs.

Example of use within a commercial building



Command and signaling technical details

E290 latching relays

Application for an E290 Latching Relay in conjunction with an E293/X or E294 Central On-Off Control Module:

The interior lighting controlled by means of various impulse buttons can also be operated from a central control point by snapping on a central on-off control module onto the left side of the E290 latching relay.

Switching sequence:

Local => OFF – ON


Central => OFF – ON

(the central command is the superordinate command)

The combination of a Main device plus central on-off control module can be used to switch multiple lights on and off at the same time without any dependence on the current switch position of the devices. The actual switch position of the various devices (on/off) can be indicated by snapping an auxiliary contact (attachable on the right side) to the control center.

Another possibility would be the combination of an E290 with an E294 central on-off control module for various control voltages. This combination enables for example the cooperation with a PLC (programmable logic controller). Any number of different logical activations in respect of latching relays can be recorded and visualised.

Example of use within an industrial warehouse




Command and signaling technical details

E291 sequential latching relays

Application using an E291S Sequential Latching Relay:

This independent special sequential latching relay switches the contact position in a preset fixed switching sequence.

Switching sequence:
OFF – A – AB – B – OFF



E291S latching relays with sequential contacts

Operating principle


The two contacts of the E291S latching relays switch independently their position (open/closed) at each impulse according to a preset sequence in the control circuit.

Application environments

The E291S latching relays are particularly indicated in environments and situations requiring the load sequential control through a single pushbutton circuit (offices, restaurants, etc.).

Example of installation

As shown in the diagrams, one of the possible applications is to mount the E291S latching relays inside the lighting system of an art gallery. The first pushbutton impulse will switch on the ceiling lights, the second triggers the wall lamps, the third switches off the ceiling lights and the fourth switches off the wall lamps.






Command and signaling technical details

E290 latching relays

LATCHING RELAYS



Information about lamp insertion between phase and neutral

Power [W]	Number of switchable lamps	
	E290 - 16 A	E290 - 32 A
Incandescent lamps (230 V AC)		
15	200	266
25	120	160
40	75	102
60	50	65
75	40	52
100	30	40
150	20	26
200	15	20
300	9	12
500	5	7
Fluorescent lamps without power factor capacitors		
	18	81
	36	44
	40	38
	58	29
	65	26
Fluorescent lamps with power factor capacitors		
	18	103
	36	63
	40	40
	58	41
	65	37
Fluorescent twin-lamps		
	2 x 18	82
	2 x 36	41
	2 x 40	35
	2 x 58	23
	2 x 65	22
Lamps with electronic reactor		
	18	83
	36	46
	58	31
	2 x 18	40
	2 x 36	23
	2 x 58	14

Power [W]	Number of switchable lamps	
	E290 - 16 A	E290 - 32 A
Low pressure sodium vapor lamps (SOX)		
	55	27
	90	16
	135	11
	180	8
	185	8
High pressure sodium vapor lamps (NAV)		
	70	15
	150	8
	250	4
	400	3
	1000	1
Metal halide and high pressure mercury vapor lamps (HQL)		
	50	30
	80	18
	125	12
	250	6
	400	3
	1000	1
230 V halogen lamps (HQI)		
	150	20
	250	12
	300	10
	400	7
	500	6
	1000	3
Very low voltage halogen lamps (12 or 24 V AC)		
	20	116
	50	46
	75	31
	100	24
	150	15
	200	12
	300	7

Command and signaling technical details

LED lamp latching relays

Application for (in W)	P [W] of the LED component	Number of LED components			
		Latching Relays (E290)		Installation Relays (E297)	
		16 A	32 A		
Switchable total power P (W) per contact path		200	250	200	
LED E27 glow lamp shape					
	40	5.5	36	45	
	40	6.0	33	42	
	40	7.0	29	36	
	60	9.0	22	28	
	60	9.5	21	26	
	60	10.0	20	25	
	75	11.5	17	22	
	75	13.0	15	19	
	100	15.0	13	17	
	100	18.0	11	14	
LED E14 Candle-shaped bulb					
	25	3.0	67	83	
	25	4.0	50	63	
	40	6.0	33	42	
	40	6.0	33	42	
27/E14 Drop-shaped bulb					
	25	3.0	67	83	
	25	4.0	50	63	
	40	6.0	33	42	
LED E27/E14 Reflectors					
	40	4.5	44	56	
	50	5.5	36	45	
	40	8.5	24	29	
	40	9.5	21	26	
	40	13.0	15	19	
LED Low-voltage reflectors					
	20	3.4	59	74	
	35	5.5	36	45	
	35	6.5	31	38	
	35	7.0	29	36	
	50	8.0	25	31	
LED High-voltage reflectors					
	35	3.5	57	71	
	35	4.0	50	63	
	50	4.5	44	56	
	50	5.0	40	50	
	50	5.4	37	46	

Command and signaling technical details

LED lamp latching relays

Application for (in W)	P [W] of the LED component	Number of LED components			Installation Relays (E297)	
		Latchung Relays (E290)		16 A		
		32 A	16 A			
Switchable total power P (W) per contact path		200	250	32 A	16 A	
LEDTube 0.6 m fluorescent lamp with electronic ballast						
	18	10.5	19	24	11	
	36	16.5	12	15	7	
	36	18.0	11	14	7	
	36	21.0	10	12	6	
LEDTube 1.2 m fluorescent lamp with electronic ballast						
	18	10.5	19	24	11	
	36	16.5	12	15	7	
	36	18.0	11	14	7	
	36	21.0	10	12	6	
	58	22.0	9	11	5	
	58	26.0	8	10	5	
LEDTube 1.52 m fluorescent lamp with electronic ballast						
	18	10.5	19	24	11	
	36	16.5	12	15	7	
	36	18.0	11	14	7	
	36	21.0	10	12	6	
	58	22.0	9	11	5	
	58	26.0	8	10	5	
LEDTube 1.5 m with conventional/low-loss ballast						
	58	20.0	10	13	6	
	58	23.0	9	11	5	
	58	25.0	8	10	5	
LEDTube 1.2m with conventional/low-loss ballast						
	36	16.0	13	16	8	
	36	18.0	11	14	7	
LEDTube 0.6m with conventional/low-loss ballast						
	18	8.0	25	31	15	
	18	9.0	22	28	13	

Command and signaling technical details

E290 latching relays

Use of lighted pushbuttons

Latching relays can be controlled through lighted pushbuttons, without any limitations in terms of connection of three-terminal types.

In two-terminals pushbuttons the current that flows through pushbutton lamps can trigger an unwanted activation; in order to avoid this there is the E296-CP compensation module, installed in parallel on the coil.

Number of E296-CP compensation modules	Number of connectable lighted pushbuttons	
	1P – 2P types	3P – 4P types
0	8	9
1	18	22
2	45	38


Command and signaling technical details

E297 installation relay

E297-16-20 + E298-16-11 — Installation Relay with Contact Module




Light control via an Installation Relay E297 with connected Contact Module E298-16-11 (additional main contacts) to externally signal the switching state of the main contacts (ON/OFF).




E297-16-10 + 299-11 — Installation Relay with Auxiliary Contact




Application with a normal light control via an ON/OFF switch. The current condition indication of the light control (ON/OFF) is implemented, e.g., in the distribution board, with the help of the auxiliary contact (E299-11).



E297-16-20 + E298-16-11 + 299-11 — Installation Relay with Contact Module and Auxiliary Contact




Combination of an installation relay E297 with an attached Contact Module E298-16-11 (additional main contacts) plus an Auxiliary Contact to clearly indicate the switching state of the main contacts (ON/OFF).



Command and signaling technical details

E297 installation relay

E297 Installation Relay



Safety information

If more than one Latching relay installed next to each other, it is recommended to use a intermediate piece (distance). This guarantees optimal heat dissipation by the main modules. The intermediate pieces (9 or 18mm wide) can be found in the order information as types ZLS725 or ZLS726 (the use depends on the application).

Command and signaling technical details

E297 installation relay

Because of the individual options for using the installation relays in building management systems, these devices can be used to realise a modern and reliable consumer control system.

Application for an E297 Installation Relay:


When current is applied to an installation relay, the relay coil attracts one of the main contacts and changes the contact position. The coil of an installation relay has to remain energised in order to hold the contact position. If the voltage is removed from the coil, the installation relay always returns to the off position.

Switching sequence:

OFF – ON

Main areas of application include exterior lighting for office buildings or supermarket car parks as well as other big installations. An extremely flexible and modern lighting control system can be created, using E297 installation relays. Activation can be carried out by means of a twilight switch or a timer but also by means of a simple on-off switch or another electrical control unit. Reliable switching of an exterior lighting system, for example, is realised by sending clear on and off control commands from an external control point. The magnetic coil has to be permanently energised in order for the installation relay to be held in the on position. The energy consumption of the installation relay is reduced to a minimum by the performance-optimised magnetic coil. The low switching noise also makes it suitable for professional use in closed inhabited areas.

Example of use within a commercial building










Command and signaling technical details

E297 installation relay

INSTALLATION RELAYS

Information about lamp insertion between phase and neutral

	Power [W]	Number of switchable lamps
Incandescent lamps (230 V AC)		
	15	120
	25	72
	40	45
	60	30
	75	24
	100	18
	150	12
	200	9
	300	6
	500	3
Fluorescent lamps without power factor capacitors		
	18	50
	36	25
	40	23
	58	16
	65	13
Fluorescent lamps with power factor capacitors		
	18	17
	36	13
	40	12
	58	8
	65	7
Fluorescent twin-lamps		
	2 x 18	50
	2 x 36	25
	2 x 40	23
	2 x 58	16
	2 x 65	13
Lamps with electronic reactor		
	1 x 18	38
	1 x 36	30
	1 x 58	17
	2 x 18	19
	2 x 36	15
	2 x 58	8

	Power [W]	Number of switchable lamps
Low pressure sodium vapor lamps (SOX)		
	55	6
	90	4
	135	3
	180	2
	185	2
High pressure sodium vapor lamps (NAV)		
	70	10
	150	5
	250	3
	400	2
	1000	-
Metal halide and high pressure mercury vapor lamps (HQL)		
	50	16
	80	10
	125	7
	250	3
	400	2
	1000	-
230 V halogen lamps (HQI)		
	150	12
	250	7
	300	6
	400	4
	500	3
	1000	2
Very low voltage halogen lamps (12 or 24 V AC)		
	20	72
	50	29
	75	20
	100	15
	150	10
	200	7
	300	5

Command and signaling technical details

E297 installation relay

Operating principle






The E297 installation relays are 16 A contactors specifically engineered for residential and commercial applications and are available in a wide range of contact layouts and coil voltages.

Application environments

The E297 installation relays are particularly indicated in residential and commercial buildings for lighting control.


Example of installation

As shown in the diagrams, one of the possible applications is to mount the E297-16-11 installation relay with a NO and a NC contact inside the electric system of a hospital ward. The first control sent through a switch to the command circuit of the relay will turn off the ceiling lights and turn on the corridor lamps, while the second command returns to the previous state.



Command and signaling technical details


E 260 latching relays




Command and signaling technical details

STD dimmers


Control power STD 50-3: 20-500 W/VA
 STD 50-4: 40-420 W/VA Influence of ambient temperature on the control power
 The certified rated power is indicated on the dimmer.
 Where higher ambient temperatures occur, reduce values
 as is specified in the diagram.
 At 50 °C /122°F ambient temperature, the permissible
 load drops to 57%.




Electronic potentiometer




Brightness control of fluorescent lamps
 with 1 - 10 V control input. Control of more than
 one memory touch controller STD-MTS via one push-
 button.





Dimmer STD 50-4 in two-way circuit, lv halogen
 lamps via electronic transformer



Brightness control of a fluorescent lamp
 with 1 - 10 V DC control input with
 memory touch controller STD-MTS with
 external pushbutton, e.g. E 225



Connected load / ambient temperature diagram



Command and signaling technical details

Modular transformers



Modular transformers

The range of System pro M compact modular transformers consists of a series of safety transformers for general use, TS-C with 12-24 V secondary and powers of 25, 40 and 63 VA, the TM range of bell transformers, with secondary voltages of 12-24 V and a maximum rated power of 10-15-30-40 VA, and the TS range of bell transformers, with secondary voltages of 8-12-24 V and a rated secondary power of 8-16-24 VA (some TS types are available with an integrated switch ON/OFF).

Modular safety transformers for general use TS-C, continuous functioning

Standard: IEC EN 61558-2-6

The TS-C safety transformer is an insulation transformer for supplying SELV circuits (with extremely low safety voltage) or PELV circuits (with extremely low protection voltage). In contrast to the bell transformers, TS-C transformers can be used to continuously supply low voltage loads and they have a reduced voltage drop value. Even after a short-circuit they maintain their temperature below the specified limits. In addition they are equipped with a thermal sensitive restoring device which automatically restores power when the transformer is sufficiently cooled down or the overload has been removed.



Fail proof bell transformers TM series

Standard: IEC EN 61558-2-8

Following a short-circuit or an overload use the products may not continue to operate, but they continue assuring separation between primary and secondary circuits, safeguarding the user and adjacent electric parts: the serie includes 8 models with 10, 15, 30 and 40 VA power and 4, 8, 12 and 24 V output voltages.

Non-inherently short-circuit proof bell transformers TS series

Standard: IEC EN 61558-2-8

Even after a short-circuit they maintain their temperature below the specified limits. In fact they are equipped with a thermal protection device which automatically restores power when the transformer is sufficiently cooled down or the overload has been removed. The TS series includes 10 models with 8, 16, 24 VA power and output voltages of 4, 6, 8 and 12 and 24 V AC.

The TS8/SW series is equipped with an ON-OFF switch on the front side that allows the control of the load connected to transformer's secondary circuit. It includes 5 models with 8 VA power and output voltages of 4, 6, 8 and 12 V.

Command and signaling technical details

Control, isolating and safety transformers

Control, isolating and safety transformers

The choice of supply voltage for a control circuit must take into account two factors: the safety of users, and the functional reliability of the circuits, which can be dependent on the voltage drop.

Control transformer

Reference standard: CEI EN 61558-2-2:

Transformer for supplying control circuits, for example commands, signaling, interlocks, etc.

Isolating transformer

Reference standard: CEI EN 61558-2-4:

Transformer in which the primary and secondary windings are electrically separated by a double or reinforced insulation, to protect the circuit supplied by the secondary against hazards due to accidental simultaneous contact with earth and live parts, or grounded parts that may become live in the event of an insulation fault.

Safety transformer

Reference standard: CEI EN 61558-2-6:

Isolation transformer for supplying safety extra low voltage circuits (<50 V on no load). Accidental contact with the secondary winding phases can be withstood without any danger.

Impregnation and tropicalization

ABB transformers are fully impregnated using a thermal class F resin. This treatment improves the characteristics of the insulating materials, making the transformers suitable for installation in harsh environments. It also augments heat exchanges, thereby lowering the transformer temperature, prevents moisture from penetrating the windings and core, and minimises vibrations and the resultant noise.

Insulation classes

The duration of the insulation in the products depends on many factors, and in cases where the insulating material electrically segregates live parts from accessible parts, any alteration in its characteristics may put the safety of the user at risk.

The standards prescribe maximum temperature limits for transformer windings as a function of the insulation class. ABB transformers are constructed using class B materials. The maximum permitted ambient temperature is specified on the transformer rating plate as well as on this catalog.

Insulation class	T MAX
A	100 °C
E	115 °C
B	120 °C
F	140 °C
H	165 °C

Command and signaling technical details

Control, isolating and safety transformers

Protection of transformers

Protection on primary

On the primary side, the transformer cannot generate any overload by itself. During power up, however, a very high inrush current (approx. 20 In) is generated. Protections

should therefore be calibrated in order to prevent their tripping during the transformer connection phase. The most suitable types of protection are:

- aM fuses
- S202 miniature circuit breakers, D characteristic.

Minimum protection on primary

Transformer power (VA)		230 V single phase	400 V single phase
50	aM fuse	0.5 A	0.315 A
	aM fuse	1 A	0.63 A
100	Breaker capacity	1.6 A	1 A
	Trip characteristic	D	D
160	aM fuse	1.6 A	1 A
	Breaker capacity	3 A	2 A
200	Trip characteristic	D	D
	aM fuse	2 A	1.25 A
250	Breaker capacity	3 A	2 A
	Trip characteristic	D	D
320	aM fuse	2.5 A	1.6 A
	Breaker capacity	4 A	3 A
400	Trip characteristic	D	D
	aM fuse	3.15 A	2 A
630	Breaker capacity	5 A	3 A
	Trip characteristic	D	D
1000	aM fuse	4 A	2.5 A
	Breaker capacity	8 A	5 A
1600	Trip characteristic	D	D
	aM fuse	6.3 A	4 A
2000	Breaker capacity	13 A	8 A
	Trip characteristic	D	D
2500	aM fuse	10 A	6 A
	Breaker capacity	20 A	13 A
	Trip characteristic	D	D
	aM fuse	16 A	10 A
	Breaker capacity	32 A	20 A
	Trip characteristic	D	D
	aM fuse	20 A	12 A
	Breaker capacity	40 A	25 A
	Trip characteristic	D	D
	aM fuse	25 A	16 A
	Breaker capacity	50 A	32 A
	Trip characteristic	D	D

Notes:

The protection specified in the table is the minimum "recommended" for protecting the supply line.
The breaking capacity of the primary miniature circuit breakers is a function of the supply line.

Protection on secondary

The secondary circuit must be protected against overload and short-circuit. Moreover, additional protection may need to be adopted depending on the distribution system type.

- Overload: The tripping current value of the protection used should be equal to or lower than the secondary current of the transformer.

- Short-circuit: Any short-circuit in the most distant point of the line should make the protection device trip in less than 5 seconds (IEC 60364). The protection of the transformer and the protection of the line may coincide when the transformer supplies power to a single line and a full compatibility has been ensured. The suitable secondary protection can be found on the selection tables.

Command and signaling technical details

Control, isolating and safety transformers

Transformer				Circuit Breaker for Transformer Protection		
Type	Rated Power (VA)	Input Voltage (V)	Nominal current (A)	Type	Ordering Code	Current setting (A)
TM-...50...	50	230	0.22	MS132-0.25T	1SAM340000R1002	0.22
TM-...100...	100	230	0.43	MS132-0.63T	1SAM340000R1004	0.43
TM-...160...	160	230	0.70	MS132-1.0T	1SAM340000R1005	0.70
TM-...200...	200	230	0.87	MS132-1.0T	1SAM340000R1005	0.87
TM-...250...	250	230	1.09	MS132-1.6T	1SAM340000R1006	1.09
TM-...320...	320	230	1.39	MS132-1.6T	1SAM340000R1006	1.39
TM-...400...	400	230	1.74	MS132-2.5T	1SAM340000R1007	1.74
TM-...630...	630	230	2.74	MS132-4.0T	1SAM340000R1008	2.74
TM-...1000...	1000	230	4.35	MS132-6.3T	1SAM340000R1009	4.35
TM-...1600...	1600	230	6.96	MS132-10T	1SAM340000R1010	6.96
TM-...2000...	2000	230	8.70	MS132-10T	1SAM340000R1010	8.70
TM-...2500...	2500	230	10.87	MS132-12T	1SAM340000R1012	10.87
TM-...50...	50	400	0.13	MS132-0.16T	1SAM340000R1011	0.13
TM-...100...	100	400	0.25	MS132-0.25T	1SAM340000R1002	0.25
TM-...160...	160	400	0.40	MS132-0.4T	1SAM340000R1003	0.40
TM-...200...	200	400	0.50	MS132-0.63T	1SAM340000R1004	0.50
TM-...250...	250	400	0.63	MS132-0.63T	1SAM340000R1004	0.63
TM-...320...	320	400	0.80	MS132-1.0T	1SAM340000R1005	0.80
TM-...400...	400	400	1.00	MS132-1.6T	1SAM340000R1006	1.00
TM-...630...	630	400	1.58	MS132-2.5T	1SAM340000R1007	1.60
TM-...1000...	1000	400	2.50	MS132-4.0T	1SAM340000R1008	2.50
TM-...1600...	1600	400	4.00	MS132-6.3T	1SAM340000R1009	4.00
TM-...2000...	2000	400	5.00	MS132-10T	1SAM340000R1010	6.30
TM-...2500...	2500	400	6.25	MS132-10T	1SAM340000R1010	6.30



Properties

Each type of transformer detailed in the table above can be supplied on the primary side with a line protected by the corresponding Manual Motor Starter.

The indicated devices are calibrated to prevent from tripping during the transformer connection phase.

Caution: the motor starter do not protect the transformer, for this scope another compulsory protection must be installed on the secondary side as detailed on the transformers datasheet.


Wiring diagram with motorstarter




Command and signaling technical details

Control, isolating and safety transformers

Power draw according to temperature and altitude



Power draw % according to temperature



Power draw % according to altitude

TM-I

Power VA	Cable section		Secondary 115-230 V	
	Primary		Min. mm ²	Min. mm ²
50	0,5		4	0,5
100	0,5		4	0,5
160	0,5		1,5	0,5
200	0,5		1,5	0,5
250	0,5		1,5	0,5
320	0,5		1,5	0,5
400	0,5		1,5	0,5
630	0,5		2,5	0,5
1000	0,5		2,5	0,5
1600	0,5		2,5	0,5
2000	0,5		2,5	0,5
2500	0,5		2,5	0,5

Command and signaling technical details

Control, isolating and safety transformers

TM-S

Power VA	Cable section		Secondary 12-24V		Secondary 24-48V	
	Primary	Min. mm ²	Min. mm ²	Min. mm ²	Min. mm ²	Min.
50	0,5	4	0,5	4	0,5	4
100	0,5	4	0,5	4	0,5	4
160	0,5	1,5	0,5	1,5	0,5	1,5
200	0,5	1,5	0,5	1,5	0,5	1,5
250	0,5	1,5	0,5	1,5	0,5	1,5
320	0,5	1,5	0,5	2,5	0,5	2,5
400	0,5	1,5	0,5	2,5	0,5	2,5
630	0,5	2,5	0,5	2,5	0,5	2,5
1000	0,5	2,5	4	10	-	-
1600	0,5	2,5	1,5	50	-	-
2000	0,5	2,5	1,5	50	-	-
2500	0,5	2,5	1,5	50	-	-

TM-C

Power VA	Cable section		Secondary 12-24V		Secondary 24-48V	
	Primary	Min. mm ²	Min. mm ²	Min. mm ²	Min. mm ²	Min.
50	0,5	4	0,5	4	0,5	4
100	0,5	4	0,5	4	0,5	4
160	0,5	1,5	0,5	1,5	0,5	1,5
200	0,5	1,5	0,5	1,5	0,5	1,5
250	0,5	1,5	0,5	1,5	0,5	1,5
320	0,5	1,5	0,5	1,5	0,5	2,5
400	0,5	1,5	0,5	1,5	0,5	2,5
630	0,5	2,5	0,5	2,5	0,5	2,5
1000	0,5	2,5	0,5	2,5	4	10
1600	0,5	2,5	0,5	2,5	1,5	50
2000	0,5	2,5	0,5	2,5	1,5	50
2500	0,5	2,5	0,5	2,5	1,5	50

Transformer leaks

Power (VA)	No-load loss (W)	Load loss (W)
50	4	8,5
100	6,5	14
160	9	21
200	9	22
250	12	25
320	13	30
400	15	32
630	23	45
1000	36	60
1600	50	75
2000	60	90
2500	65	105

Command and signaling technical details


Control, isolating and safety transformers

Short circuit voltage, no-load output voltage variations

Power (VA)	50	100	160	200	250	320	400	630	1000	1600	2000	2500
Vcc ① (%)	10.6	7.5	5.2	4.8	9.5	6.9	6	4	3.5	3	2.8	2.3
ΔV ② (%)	11	7.8	6	5.8	6.7	7	5.4	4.3	3.3	2.8	2	1.8


① Percent of rated supply voltage; ② Percent of rated output voltage

Inrush power trend



Admissible overload

If the transformer rated power is not drawn on a continuous basis, the transformer may be overloaded, according to the diagram below:



If a transformer is used with an intermittent duty cycle, it can be sized according to the formula:

$$P_{\text{transformer}} = P_{\text{intermittent}} * \sqrt{\frac{\text{operating time}}{\text{total cycle time (operating + pause time)}}}$$

with time expressed in minutes

Command and signaling technical details

Control, isolating and safety transformers

In control equipment, can I use the two secondary outputs of a single transformer to supply two different auxiliary circuits?

It is possible to simultaneously use both the secondary outputs of an ABB transformer to supply two circuits with different voltage ratings. The sum of the power draw from each circuit must not exceed the power rating of the transformer.

What type of transformer should be used to supply safety extra low voltage (SELV) circuits?

To construct a SELV circuit it is necessary to use a safety transformer compliant with the IEC EN 61558-2-6 standard, which guarantees both electrical separation of the systems by means of double insulation and the required extra low voltage (12-24 V \pm 5%).

Can the secondary windings of two or more ABB single-phase transformers be connected in parallel?

It is possible to connect in parallel up to a maximum of 3 ABB transformers of equal power, bearing in mind that the total power which can be drawn will be equal to 90% of the sum of the individual powers. Pay great attention to terminal connection and, if necessary, test the circuit first in series and then in parallel.

In a piece of equipment supplied at 24 V a.c., I need to supply a cooling fan with a voltage rating of 230 V a.c. Can I use

a transformer, supplying it from the secondary?

It is possible to supply the transformers on the secondary side, but due to the nature of their construction, the voltage output from the primary may vary by 10-30% relative to the rated voltage.

How can I quickly size the power of a transformer?




$$P = 0.8 (\Sigma P_m + \Sigma P_r + P_a)$$

ΣP_m = Sum of all continuous power consumptions of contactors

ΣP_r = Sum of all the resistive powers

P_a = Inrush power of the largest contactor

Use of two output voltages at the same time


Case A	Case B	Case C
 <p>Use of one output voltage: 24 V</p>	 <p>Use of one output voltage: in 12 V</p>	 <p>Use of two output voltages: Output 1: 24 V Output 2: 12 V</p>

Command and signaling technical details

Control, isolating and safety transformers

Wiring rules for case c:

- The combined power delivered of the two outputs must not exceed the rated power.
- The power delivered on the output with less voltage must be at most:
- $\text{lower voltageP} \leq 0,5 \times (\text{ratedP} - \text{higher voltageP})$
- The protection device for the secondary must be positioned at the point of the passing current of the two outputs and selected based on the higher voltage of the two loads:



The fuse must be selected based on the higher voltage of the load and positioned in the point where the current of the two loads passes.

Example:

Transformer with ratedP 250 VA
12-24 V
Fuse 10 A gG or S 202 C10 automatic circuit breaker.

Examples:

Transformer with a rated power of 250 VA and 12/24 V secondary voltage:

	Power on 24 V output	Power on 12 V output	Comment
Es.1	250 VA	-	Case A is: the full power is delivered on the 24 V output
Es.2	-	250 VA	Case B is: the full power is delivered on the 12 V output
Es.3	100 VA	75 VA	Case C is: The power is delivered on the two outputs.
			Rule 1: Total power \leq ratedP Total power \leq 250 VA OK
			Rule 2: $\text{lower voltageP} \leq 0,5 \times (\text{ratedP} - \text{higher voltageP})$ $\text{lower voltageP} \leq 0,5 \times (250 - 100)$ $\text{lower voltageP} \leq 75 \text{ VA}$ OK

Connecting the transformer with the central point of the secondary to ground

Connection of the central point of the secondary of the transformer to ground makes it possible to decrease the potential of the secondary circuit in respect to ground, while maintaining the same output voltage.

Command and signaling technical details


Control, isolating and safety transformers

Example:

with a transformer with 12/24 V output you can connect the central zero and deliver a voltage of -12 V / 0 V / +12 V. The voltage available to the secondary is always 24 V while the difference in potential in respect to the ground does not exceed 12 V, during normal operation.


Warning for grounding the central point for safety and insulating transformers:

If the lamination is grounded (with the Faston plug for example), the insulation properties of the safety and insulating transforms will be reduced: the insulation between the secondary and primary becomes one and not double/reinforced, thus decreasing the transformer properties.



Lamination not grounded

Connection 12-0-12 preserving double insulation



Lamination grounded

The insulation between the primary and secondary is reduced to that between the laminations and primary. Consequently, this assembly takes away the advantage of double insulation.

Command and signaling technical details

CP-D power supplies and the CP-D redundancy units

CP-D range – Technical data

Data at $T_a = 25^\circ\text{C}$, $U_{in} = 230\text{ V AC}$ and rated values, unless otherwise indicated

Type	CP-D 12/0.83	CP-D 12/2.1
Input circuit - supply circuit	L, N	
Rated input voltage U_{in}	100-240 V AC	
Input voltage range	90-264 V AC / 120-375 V DC	
Frequency range AC	47-63 Hz	
Typical input current / typical power consumption	at 115 V AC at 230 V AC	200 mA / 12.68 W 128.3 mA / 13.01 W
Inrush current	at 115 / 230 V AC	16 A / 32 A
Power failure buffering time		min. 30 ms
Internal input fuse		1 A slow-acting / 250 V AC
Power factor correction (PFC)		2 A slow-acting / 250 V AC
Indication of operational states		
Output voltage	DC ON: green LED DC LOW: red LED	: output voltage applied : output voltage too low
Output circuit	+, -	
Rated output voltage	12 V DC	
Tolerance of the output voltage	$\pm 1\%$	
Adjustment range of the output voltage	-	12-14 V DC
Rated output power	10 W	25 W
Rated output current I_r	$T_a \leq 60^\circ\text{C}$	0.83 A
Derating of the output current	$60^\circ\text{C} < T_a \leq 70^\circ\text{C}$	2.5 %/ $^\circ\text{C}$
Maximum deviation with	load change statical change of output voltage within the input voltage range	max. 1 % max. 1 %
Control time		< 1 ms
Starting time after applying the supply voltage	at I_r	1000 ms
Rise time	at rated load	typ. 1 ms
Residual ripple and switching peaks	BW = 20 MHz	50 mV
Parallel connection		yes, using CP-D RU
Series connection		yes, to increase voltage
Resistance to reverse feed		18 V / 1 s
Output circuit - No-load, overload and short-circuit behavior		
Characteristic curve of output	hiccup-mode	U/I characteristic curve
Short-circuit protection	continuous short-circuit stability	
Short-circuit behavior	continuation with output power limiting	
Current limiting at short circuit	typ. 1.4 A	typ. 5.9 A
Overload protection	output power limiting	
Oversupply protection	15-16.5 V DC	
No-load protection	continuous no-load stability	
Starting of capacitive loads	unlimited	
General data		
Efficiency	typ. 78 %	typ. 82 %
Duty cycle	100 %	
Dimensions	see "Dimensional drawings"	
Material of housing	plastic	
Mounting	DIN rail (IEC/EN 60715), snap-on mounting without any tool	
Mounting position	horizontal	
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)
Degree of protection	housing / terminals	IP20 / IP20
Protection class		II

Command and signaling technical details

CP-D power supplies and the CP-D redundancy units

CP-D range – Technical data

Data at $T_a = 25^\circ\text{C}$, $U_{in} = 230\text{ V AC}$ and rated values, unless otherwise indicated

Type	CP-D 12/0.83	CP-D 12/2.1	
Electrical connection - Input circuit / Output circuit			
Connecting capacity	fine-strand with wire end ferrule rigid	0.2-1.5 mm ² (24-16 AWG) 0.2-2.5 mm ² (26-12 AWG)	0.2-2.5 mm ² (24-14 AWG) 0.2-2.5 mm ² (24-12 AWG)
Stripping length		4-5 mm (0.16-0.2 in)	7 mm (0.28 in)
Tightening torque		0.6 Nm (5 lb.in)	0.7 Nm (6 lb.in)
Environmental data			
Ambient temperature range	operation rated load storage	-40...+70 °C (-40...+158 °F) -40...+60 °C (-40...+131 °F) -40...+85 °C (-40...+185 °F)	
Altitude during operation	IEC/EN 60068-2-13	max. 4850 m	
Damp heat (cyclic) (IEC/EN 60068-2-30)		4 x 24 cycles, 40 °C, 95 % RH	
Vibration (sinusoidal) (IEC/EN 60068-2-6)		50 m/s ² , 10 Hz - 2 kHz	
Shock (half-sine) (IEC/EN 60068-2-27)		40 m/s ² , 22 ms	
Isolation data			
Rated insulation voltage U_i	input circuit / output circuit	3 kV AC	
Pollution degree		2	
Overvoltage category		II	
Standards / Directives			
Standards		IEC/EN 60950-1	
Low Voltage Directive		2014/35/EU	
EMC Directive		2014/30/EU	
RoHS Directive		2011/65/EU	
Protective low voltage		SELV (IEC/EN 60950-1)	
Electromagnetic compatibility			
Interference immunity to		IEC/EN 61000-6-2	
electrostatic discharge	IEC/EN 61000-4-2	level 4 (4 kV / 8 kV)	level 4 (4 kV / 15 kV)
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)	
electrical fast transient/burst	IEC/EN 61000-4-4	level 4 (4 kV)	
surge	IEC/EN 61000-4-5	level 3 (2 kV L-L)	
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)	
Interference emission		IEC/EN 61000-6-3	
high-frequency radiated		class B	
high-frequency conducted		class B	

Command and signaling technical details

CP-D power supplies and the CP-D redundancy units

CP-D range – Technical data

Data at $T_a = 25^\circ\text{C}$, $U_{\text{in}} = 230\text{ V AC}$ and rated values, unless otherwise indicated

Type	CP-D 24/0.42	CP-D 24/1.3	CP-D 24/2.5	CP-D 24/4.2			
Input circuit - supply circuit	L, N						
Rated input voltage U_{in}	100-240 V AC						
Input voltage range	90-264 V AC / 120-375 V DC						
Frequency range AC	47-63 Hz						
Typical input current / typical power consumption	at 115 V AC at 230 V AC	184 mA / 11.62 W 120.6 mA / 12 W	600 mA / 37.92 W 344 mA / 38.16 W	1120 mA / 69.3 W 660 mA / 70.1 W	1800 mA / 117.3 W 900 mA / 114.4 W		
Inrush current	at 115 / 230 V AC	max. 16 A / 32 A	max. 25 A / 50 A	max. 30 A / 60 A			
Power failure buffering time		min. 30 ms		min. 60 ms			
Internal input fuse		1 A slow-acting / 250 V AC	2 A slow-acting / 250 V AC	3.15 A slow-acting / 250 V AC			
Power factor correction (PFC)	no						
Indication of operational states							
Output voltage	DC ON: green LED	█: output voltage applied					
	DC LOW: red LED	█: output voltage too low					
Output circuit	+, - ++, --						
Rated output voltage	24 V DC						
Tolerance of the output voltage	±1 %						
Adjustment range of the output voltage	-	24-28 V DC					
Rated output power	10 W	30 W	60 W	100 W			
Rated output current I_r	Ta m 60 °C: 0.42 A	Ta m 60 °C: 1.3 A	Ta m 55 °C: 2.5 A	Ta m 60 °C: 4.2 A			
Derating of the output current	60 °C < Ta m 70 °C: 2.5 %/°C	60 °C < Ta m 70 °C: 2.5 %/°C	55 °C < Ta m 70 °C: 2.5 %/°C	60 °C < Ta m 70 °C: 2.5 %/°C			
Maximum deviation with	load change statical change of output voltage within the input voltage range	max. 1 %					
Control time	< 1 ms						
Starting time after applying the supply voltage	at I_r	1000 ms					
Rise time	at rated load	typ. 1 ms					
Residual ripple and switching peaks	BW = 20 MHz	50 mV					
Parallel connection	yes, using CP-D RU						
Series connection	yes, to increase voltage						
Resistance to reverse feed	35 V / 1 s						
Output circuit - No-load, overload and short-circuit behavior							
Characteristic curve of output	hiccup-mode U/I characteristic curve						
Short-circuit protection	continuous short-circuit stability						
Short-circuit behavior	continuation with output power limiting						
Current limiting at short circuit	typ. 0.78 A	typ. 4.2 A	typ. 6.05 A	typ. 11.5 A			
Overload protection	output power limiting						
Oversupply protection	30-33 V DC						
No-load protection	continuous no-load stability						
Starting of capacitive loads	unlimited						
General data							
Efficiency	typ. 80 %	typ. 83 %	typ. 86 %	typ. 89 %			
Duty cycle	100 %						
Dimensions	see "Dimensional drawings"						
Material of housing	plastic						
Mounting	DIN rail (IEC/EN 60715), snap-on mounting without any tool						
Mounting position	horizontal						
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)					
Degree of protection	housing / terminals	IP20 / IP20					
Protection class	II						

Command and signaling technical details

CP-D power supplies and the CP-D redundancy units

CP-D range – Technical data

Data at $T_a = 25^\circ\text{C}$, $U_{in} = 230\text{ V AC}$ and rated values, unless otherwise indicated







Type		CP-D 24/0.42	CP-D 24/1.3	CP-D 24/2.5	CP-D 24/4.2				
Electrical connection - Input circuit / Output circuit									
Connecting capacity	fine-strand with wire end ferrule	0.2-1.5 mm ² (24-16 AWG)	0.2-2.5 mm ² (24-14 AWG)						
	rigid	0.2-2.5 mm ² (26-12 AWG)	0.2-2.5 mm ² (24-12 AWG)						
Stripping length	4-5 mm (0.16-0.2 in)		7 mm (0.28 in)						
Tightening torque	0.6 Nm (5 lb.in)		0.7 Nm (6 lb.in)						
Environmental data									
Ambient temperature range	operation	-40...+70 °C							
	rated load	-40...+60 °C		-40...+55 °C	-40...+60 °C				
	storage	-40...+85 °C							
Altitude during operation	IEC/EN 60068-2-13	max. 4850 m							
Damp heat (cyclic) (IEC/EN 60068-2-30)	4 x 24 cycles, 40 °C, 95 % RH								
Vibration (sinusoidal) (IEC/EN 60068-2-6)	50 m/s ² , 10 Hz - 2 kHz								
Shock (half-sine) (IEC/EN 60068-2-27)	40 m/s ² , 22 ms								
Isolation data									
Rated insulation voltage U_i	input circuit / output circuit	3 kV AC	4 kV AC	3 kV AC					
Pollution degree		2							
Overvoltage category		II							
Standards / Directives									
Standards	IEC/EN 60950-1								
Low Voltage Directive	2014/35/EU								
EMC Directive	2014/30/EU								
RoHS Directive	2011/65/EU								
Protective low voltage	SELV (IEC/EN 60950-1)								
Electromagnetic compatibility									
Interference immunity to	IEC/EN 61000-6-2								
electrostatic discharge	IEC/EN 61000-4-2	level 4 (4 kV / 8 kV)	level 4 (4 kV / 15 kV)	level 4 (4 kV / 8 kV)					
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)							
electrical fast transient/burst	IEC/EN 61000-4-4	level 4 (4 kV)							
surge	IEC/EN 61000-4-5	level 3 (2 kV L-L)							
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)							
Interference emission	IEC/EN 61000-6-3								
high-frequency radiated	class B								
high-frequency conducted	class B								

Command and signaling technical details



CP-D power supplies and the CP-D redundancy units

CP-D range – Technical diagrams

Characteristic curve of output at $T_a = 25^\circ\text{C}$



Characteristic curve of temperature at rated output voltage







Command and signaling technical details

CP-D power supplies and the CP-D redundancy units

CP-D range – Technical diagrams

Dimensional drawings

Dimensions in mm



Command and signaling technical details

CP-D power supplies and the CP-D redundancy units

CP-D redundancy unit – Technical diagrams

Type	CP-D RU	
Input circuit - Supply circuit	IN 1 + + -, IN 2 + + -	
Rated input voltage U_{in}	24 V DC	
Input voltage range	9-35 V DC	
Rated input current I_{in} per channel	5 A	
Maximum input current per channel	10 A for 300 s	
Transient overvoltage protection	no	
Output circuit	OUT + + +, ---	
Rated output voltage U_{out}	24 V DC	
Voltage drop	typ. 0.5 V	
Rated output current I_{out}	10 A	
Resistance to reverse feed	< 35 V	
General data		
MTBF	on request	
Duty cycle	100 %	
Dimensions	see "Dimensional drawings"	
Material of housing	plastic	
Mounting	DIN rail, snap-on mounting without any tool	
Mounting position	1, 7	
Minimum distance to other units	horizontal / vertical 25 mm (0.98 in) / 25 mm (0.98 in)	
Electrical connection - Input circuit / Output circuit		
Connecting capacity	fine-strand with (out)wire end ferrule rigid	0.2-2.5 mm ² (24-14 AWG) 0.2-2.5 mm ² (24-12 AWG)
Stripping length		7.0 mm (0.28 in)
Tightening torque		0.67 Nm (6 lb.in)
Environmental data		
Ambient temperature range	operation storage	-40...+70 °C -40...+85 °C
Relative humidity	RH at 40 °C	20-95 %, no condensation
Vibration (IEC/EN 60068-2-6)		mounting by rail: 10-500 Hz, 2 G, along X, Y, Z each axis, 60 min for each axis
Shock (IEC/EN 60068-2-27)		15 G, 11 ms, 3 axis, 6 faces, 3 times for each face
Standards / Directives		
Standards	IEC/EN 61204-3, IEC/EN 60950-1	
RoHS Directive	2011/65/EU	
Electromagnetic compatibility		
Interference immunity to	EN 55024	
electrostatic discharge	IEC/EN 61000-4-2	level 3, air discharge 8 kV, contact discharge 4 kV
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3, 10 V/m
electrical fast transient/burst	IEC/EN 61000-4-4	level 3, 2 kV / 5 kHz
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3, 10 V
Interference emission		EN 55022
high-frequency radiated	IEC/CISPR 22 / EN 55022	class B
high-frequency conducted	IEC/CISPR 22 / EN 55022	class B


Command and signaling technical details

CP-D power supplies and the CP-D redundancy units

CP-D redundancy unit – Technical diagrams

Dimensional drawings

Dimensions in mm



CP-D RU

Command and signaling technical details

Modular sockets

Modular sockets

This table gives an indication of the voltage, frequency and modular socket solutions in each country.

Country	Volt.	Freq.	Modular sockets							
	110-130 V	220-250 V	50 Hz	60 Hz	M1011	M1363	M1170	M1173	M1174	M1175
Afghanistan			■	■			■	■	■	■
Albania			■	■			■	■	■	■
Algeria	■	■	■				■	■	■	■
American Samoa	■	■	■	■			■	■	■	■
Andorra			■				■	■	■	■
Angola			■				■	■	■	■
Argentina			■	■			■	■	■	■
Armenia			■				■	■	■	■
Aruba	■	■	■	■			■	■	■	■
Australia			■				■	■	■	■
Austria			■				■	■	■	■
Azerbaijan			■				■	■	■	■
Azores			■				■	■	■	■
Bahrain			■		■		■	■	■	■
Balearic Islands			■				■	■	■	■
Bangladesh			■		■		■	■	■	■
Belarus			■		■		■	■	■	■
Belgium			■		■		■			
Belize	■	■	■	■	■					
Benin			■				■			
Bhutan			■		■		■	■	■	■
Bolivia	■	■	■		■		■	■	■	■
Bosnia & Herzegovina			■		■		■	■	■	■
Botswana			■		■		■	■	■	■
Brazil	■	■	■	■	■		■	■	■	■
Brunei			■		■					
Bulgaria			■		■		■	■	■	■
Burkina Faso			■		■		■	■	■	■
Burundi			■		■		■	■	■	■
Cambodia			■		■		■	■	■	■
Cameroon			■		■		■	■	■	■
Canary Islands			■		■		■	■	■	■
Cape Verde			■		■		■	■	■	■
Central African Republic			■		■		■	■	■	■
Chad			■		■		■	■	■	■
Channel Islands			■		■					
Chile			■		■		■	■	■	■
Comoros			■		■		■	■	■	■
Congo Dem.Rep. (Zaire)			■		■		■	■	■	■
Congo, People's Rep. of			■		■		■	■	■	■
Cook Islands			■							
Croatia			■		■		■	■	■	■
Cuba	■	■	■	■	■		■	■	■	■
Cyprus			■		■		■	■	■	■
Czech Republic			■		■		■			
Denmark			■		■		■	■	■	■
Djibouti			■		■		■	■	■	■
Dominica			■		■					

Main countries are highlighted

Please consider that installation rules may change in each country, and control the local regulations before installing.

Country	Volt.	Freq.	Modular sockets							
	110-130 V	220-250 V	50 Hz	60 Hz	M1011	M1363	M1170	M1173	M1174	M1175
East Timor			■	■			■	■	■	■
Egypt			■	■			■	■	■	■
Equatorial Guinea			■	■			■	■	■	■
Eritrea			■	■			■	■	■	■
Estonia			■	■			■	■	■	■
Ethiopia			■	■			■	■	■	■
Faeroe Islands			■	■			■	■	■	■
Falkland Islands			■	■			■		■	
Fiji			■	■			■	■	■	■
Finland			■	■			■	■	■	■
France			■	■			■	■	■	■
French Guyana			■				■	■	■	■
Gabon			■	■			■	■	■	■
Gambia			■	■			■		■	
Georgia			■	■			■	■	■	■
Germany			■	■			■	■	■	■
Ghana			■	■			■			
Gibraltar			■	■			■	■	■	■
Greece			■	■			■	■	■	■
Greenland			■	■			■	■	■	■
Grenada			■	■			■			
Guadeloupe			■	■			■	■	■	■
Guatemala			■	■			■			
Guinea			■	■			■	■	■	■
Guinea-Bissau			■	■			■	■	■	■
Guyana			■	■			■			
Hong Kong			■	■			■			
Hungary			■	■			■	■	■	■
Iceland			■	■			■	■	■	■
India			■	■			■	■	■	■
Indonesia			■	■			■			
Iran			■	■			■	■	■	■
Iraq			■	■			■	■	■	■
Ireland			■	■			■			
Isle of Man			■	■			■	■	■	■
Israel			■	■			■	■	■	■
Italy			■	■			■	■	■	■
Ivory Coast			■	■			■	■	■	■
Jordan			■	■			■	■	■	■
Kazakhstan			■	■			■	■	■	■
Kenya			■	■			■			
Kiribati			■	■			■			
Korea, North			■	■			■	■	■	■
Korea, South			■	■			■	■	■	■
Kuwait			■	■			■	■	■	■
Kyrgyzstan			■	■			■	■	■	■
Laos			■	■			■	■	■	■
Latvia			■	■			■	■	■	■

Command and signaling technical details

Modular sockets

Country	Volt.	Freq.	Modular sockets							
	110-130 V	220-250 V	50 Hz	60 Hz	M1011	M1163	M1170	M1173	M1174	M1175
Lebanon	■	■	■		■	■	■	■	■	
Lithuania	■	■	■		■	■	■	■	■	
Luxembourg	■	■	■		■	■	■	■	■	
Macau	■	■	■		■					
Macedonia	■	■	■		■	■	■	■	■	
Madagascar	■	■	■		■	■	■	■	■	
Madeira	■	■	■		■	■	■	■	■	
Malawi	■	■	■		■					
Malaysia	■	■	■		■					
Maldives	■	■	■		■	■	■	■	■	
Mali	■	■	■		■	■	■	■	■	
Malta	■	■	■		■					
Martinique	■	■	■		■	■	■	■	■	
Mauritania	■	■	■		■	■	■	■	■	
Mauritius	■	■	■		■	■	■	■	■	
Moldova	■	■	■		■	■	■	■	■	
Monaco	■	■	■		■	■	■	■	■	
Mongolia	■	■	■		■	■	■	■	■	
Montenegro	■	■	■		■	■	■	■	■	
Morocco	■	■	■		■	■	■	■	■	
Mozambique	■	■	■		■	■	■	■	■	
Myanmar (form. Burma)	■	■	■		■	■	■	■	■	
Nauru	■	■	■							
Nepal	■	■	■		■	■	■	■	■	
Netherlands	■	■	■		■	■	■	■	■	
Netherlands Antilles	■	■	■	■	■	■	■	■	■	
New Caledonia	■	■	■		■	■	■	■	■	
New Zealand	■	■	■							
Niger	■	■	■		■	■	■	■	■	
Nigeria	■	■	■		■					
Norway	■	■	■		■	■	■	■	■	
Oman	■	■	■		■					
Pakistan	■	■	■		■	■	■	■	■	
Papua New Guinea	■	■	■							
Paraguay	■	■	■		■	■	■	■	■	
Peru	■	■	■	■	■	■	■	■	■	
Philippines	■	■	■	■	■	■	■	■	■	
Poland	■	■	■		■	■	■	■	■	
Portugal	■	■	■		■	■	■	■	■	
Qatar	■	■	■		■					
Réunion Island	■	■	■							
Romania	■	■	■		■	■	■	■	■	

Fuse detail



Indicator light detail



Country	Volt.	Freq.	Modular sockets							
	110-130 V	220-250 V	50 Hz	60 Hz	M1011	M1163	M1170	M1173	M1174	M1175
Russian Federation	■	■			■	■	■	■	■	
Rwanda	■	■	■			■	■	■	■	
Samoa	■	■	■							
San Marino	■	■	■							
Saudi Arabia	■	■	■	■	■	■	■	■	■	
Senegal	■	■	■		■	■	■	■	■	
Serbia	■	■	■		■	■	■	■	■	
Seychelles	■	■	■							
Sierra Leone	■	■	■							
Singapore	■	■	■							
Slovakia	■	■	■							
Slovenia	■	■	■							
Somalia	■	■	■							
Spain	■	■	■		■	■	■	■	■	
Sri Lanka	■	■	■							
St. Kitts and Nevis	■	■	■			■	■	■	■	
St. Lucia	■	■	■							
St. Vincent	■	■	■							
Sudan	■	■	■							
Suriname	■	■	■							
Sweden	■	■	■							
Swiss	■	■	■			■	■	■	■	
Syria	■	■	■							
Tahiti	■	■	■				■	■	■	
Tajikistan	■	■	■							
Tanzania	■	■	■							
Thailand	■	■	■							
Togo	■	■	■							
Tonga	■	■	■							
Tunisia	■	■	■							
Turkey	■	■	■							
Turkmenistan	■	■	■							
Uganda	■	■	■							
Ukraine	■	■	■							
United Arab Emirates	■	■	■							
United Kingdom	■	■	■							
Uruguay	■	■	■							
Uzbekistan	■	■	■							
Vietnam	■	■	■							
Yemen, Rep. of	■	■	■							
Zambia	■	■	■							
Zimbabwe	■	■	■							

Command and signaling technical details

Modular sockets

M1175-FL modular socket with fuse

Operating principle

The modular sockets with fuse are ideal wherever continuity of service is essential. The embedded fuse protecting the phase prevents tripping of the main protection switch in the event of a malfunction of the device plugged into the socket.

Application environments




The modular sockets are suitable for all electrical distribution or automation panels, to allow connection of non modular equipment such as measuring and maintenance instruments etc.

Example of installation

As illustrated in the figures, a modular socket allows to supply non modular devices directly from the electrical panel.

If the connected device malfunctions, there is the risk that the entire electrical system will be put out of service due to tripping of an MCB.

This is prevented by blowing of the fuse incorporated into the socket, thus assuring continuity of service.



Electrical installation solutions for buildings – Technical details

Control and automation

Index


AG Timer electro-mechanical time switches	7/2
DBT Timer digital time switches	7/5
E 232 staircase lighting time-delay switches	7/11
E 234 CT-D electronic timers	7/12
TL Line twilight switches	7/21
LCR load shedding switch	7/24

Control and automation technical details


AG Timer electro-mechanical time switches

How to program AD1NO-15m - AD1NO-R-15m

Connection diagrams




Description




How to program AD1CO-15m - AD1CO-R-15m - AW1CO-R-120m

Connection diagrams




Description




How to program AD1CO-30m - AD1CO-R-30m - AW1CO-R-210m

Connection diagrams




Description




How to program AD1-R-15m-72

Connection diagrams



Description



- 1 - Selector switch
- 2 - Indicator
- 3 - Trippers for programming
- 4 - Trippers for programming
- 5 - Accessory for panel mounting
- 6 - Transparent protection cover
- 7 - Extractable terminal block
- 8 - Accessory for wall or DIN rail installation

Control and automation technical details

AG Timer electro-mechanical time switches

AG Timer with DIN rail mounting

Operating principle




The AG Timer electro-mechanical time switches enable to control the circuit opening/closing according to a daily or weekly program or to manually set permanent ON/OFF operation.

Application environments

The AG Timer electro-mechanical time switches are particularly indicated in any environment and situation where it is necessary to program system load operation according to a daily or weekly frequency (shop lighting system, public buildings, heating systems, irrigation systems, etc.).

Example of installation

As shown in the diagrams, one of the possible applications is to mount the AW1CO-R-120m electro-mechanical time switch inside the power supply circuit of a golf field. In this case the device programming enables the daily activation of the irrigation system at a preset time.



Control and automation technical details

AG Timer electro-mechanical time switches

AG Timer with panel/wall mounting

Operating principle



The AD1-R-15m-72 electro-mechanical switch enables to control the circuit opening/closing according to a daily program or to manually set permanent ON/OFF operation.

Application environments

The AD1-R-15m-72 electro-mechanical time switch is particularly indicated in any environment and situation where it is necessary to program system load operation according to a daily frequency (lighting system, heating systems, venting systems, etc.).

Example of installation

One of the possible applications is to use the AD1-R-15m-72 to command the heating activation at specific times during the day, allowing energy saving.



Control and automation technical details

DBT Timer digital time switches

Innovations

- DBT Timer range is equipped with impulse, cycle, random and holiday programs. They can have daily, weekly or annual mode.
- Holiday management with the possibility of programming them in various period throughout the year
- Menu programming with 4 simple keys
- Astronomical management allows automatical setting, for each day of the year, of sunrise and sunset times
- Minimum switching time is 1 second for pulse program
- Multilingual menu with 6 language choices



Bluetooth communication combined with the DBT Timer APP available for Android and iOs ensure smart configuration and quick visualization. This functionality also allows to transfer programs from one device to another simply using the Smartphone.




The DY DCF77 antenna that receives the DCF77 radio synchronisation signal transmitted by the atomic clock installed c/o Mainflingen, near Frankfort, increases digital clock precision.

The DY GPS antenna that receives time from the Global Positioning System, that offers a more accurate value than land transmissions in addition to the possibility of receiving the signal anywhere in the world.


Control and automation technical details

DBT Timer digital time switches


Display description



Access to device



Menu description



Description
1 General indications
2 Time indication
Channel 1 / Channel 2 status indication On/OFF
Active manual program
Blocked switchings
3 Active random switchings
Active cycle switchings
Active holiday program
Active pulse program
4 Day of the week (DAY) indication

Button	Function
Back arrow	Turn on the display Access the menu ESC (one level back)
C1	Decrease datum Previous menu Switching channel 1 Lock channel 1
C2	Increase datum Next menu Switching channel 2 Lock channel 2
Ok	Confirm selection
R	Hardware reset
C1 + Ok 3 sec	Random switching channel 1
C2 + Ok 3 sec	Random switching channel 2
← + C1 3 sec	Active cycle switching on channel 1
← + C2 3 sec	Active cycle switching on channel 2

Menu	Description
Settings	Allows to change: language, date, time, daylight saving time (DST), astronomical coordinates, minimum and maximum duration of the interval between two switchings with random program, ON and OFF duration of cycle switchings and PIN for keyboard lock
Program	Allows to create a new program, check created programs, change or delete a created program, copy all created programs of channel 1 on channel 2 and vice versa.
Bluetooth	Allows to enable or disable the Bluetooth interface and to change the password used to associate devices (smartphone)
Hour counter	Allows to display the hours of usage (relay on) of connected load(s).
Reset	Allows to restore the initial state of the device
Firmware menu	Shows the firmware installed in the device

Control and automation technical details

DBT Timer digital time switches

DY DCF77 antenna

Operating principle:


This antenna receives scheduled messages broadcasted from the Frankfurt on Main (Germany) based DCF77 emitter.

Thanks to this signal, the time switches are automatically setted to: hour, date and proper daylight saving time.

The broadcast power is 50 kW and the range is approximately 2500 kilometers from Frankfurt on Main.

The signal is sometimes received intermittently and not in all locations, especially in countries far enough from the DCF77 emitter.

For optimal signal reception the arrow marked side of the antenna must be rotated towards Frankfurt on Main.



DY GPS antenna


Operating principle:

The Global Positioning System provides an accurate location and time information for an unlimited number of people in all weather, day or night, anywhere in the world.

The synchronization received from GPS is far more precise regarding to terrestrial broadcast.

The GPS system relays upon time from satellite based atomic clocks, constantly controlled and corrected from a ground stations network.

The time is derived from different sources simultaneously, the digital time switches can automatically compensate for propagation delays and other problems by providing more precise values than terrestrial.



Control and automation technical details

DBT Timer digital time switches

Operating principle


The DW2 two-channel digital weekly time switch enables to open and close circuits according to a daily or weekly program, controlling single loads or group ones even when they require different time controls with a common time reference. In this example, the digital time switch DW2 allows the operation of heating as well as lighting systems of a church when services are performed; when no service is performed, the device only controls the heating system.

Application environments

The DW2 two-channel digital weekly time switch is particularly indicated in environments and situations requiring the management of multiple loads according to a time program flexible enough to include or exclude their application based on the day of the week (offices, schools, public areas, etc.).

Example of installation

As shown in the diagrams, one of the possible applications is to mount the DW2 two-channel digital weekly time switch inside the power supply circuit of a church, where in the days when no service is performed only the heating system is activated (programmed on one of the two channels) at a preset time, while on Sundays and when services are performed the lighting system is also switched on (through a program on the second channel). According to the controlled system power, the activation is performed by an ESB contactor.



Control and automation technical details

DBT Timer digital time switches



DWA2



Astronomical version – DWA

- Astronomical and time programming
- Impulse, cycle, random and holiday program
- Automatic summer and winter time change
- Up to 120 storables events
- Opportunity to correct the astronomical time up to ± 120 min
- Up to 400 pre-defined cities
- 1 or 2 changeover contacts
- latitude adjustment range from $+90^\circ$ North to -90° South.
- longitude adjustment range from 180° East to 180° West.
- Manual and permanent override, activated with one touch on the front of the device
- Clear display of contact status
- Unlosable hinged window
- The protection code PIN is used to prevent interference by unauthorised persons
- Android and iOS application for quick and ease programming
- Wiring diagram printed on the side of the product

Programming example

Ex: Rome

- Lo Longitude 12° EAST
- La Latitude 41° NORTH
- UDT +1 Universal Date Time = +1 hour



Control and automation technical details

DBT Timer digital time switches

Operating principle

The installation of an astronomical time switch in a system is a particularly useful addition for settings and situations in which light sources, or other environmental conditions, can cause changes in the brightness level and falsify the reading. In these cases, the DWA1 and DWA2 astronomical switches can control the lighting system according to the sunrise and sunset times of the geographic zone in which the system is installed.

Application environments



The installation of the DWA1 and DWA2 astronomical time switches is particularly suitable for applications in which the operation of a twilight switch with external probe can be falsified or compromised by external agents (such as environmental pollution, overexposure to light, vandalism, etc.).

Example of installation

Atmospheric pollution is one of the causes of a reduction in

the level of environmental light. Dust deposits on the external probe of a traditional twilight switch can compromise the operation of the device, preventing it from automatically switching off the controlled lighting system in the presence of external light.

As shown in the example, this problem can be solved by installing a DWA1 astronomical time switch that controls the lighting system according to the level of light calculated from the preset longitude and latitude parameters.




Control and automation technical details


E 232 staircase lighting time-delay switches

E 232E-230 Multi 10, 8/230 Multi 10

Functions: Staircase lighting time-delay switch



Function: Latching relay, Latching relay with returning time



E232E-230 Multi10 and E232E-8/230 Multi10

DIN 18015-2

provides that "that the automatic disconnection of lighting equipment fitted in staircases of apartment buildings must provide for warning signals, e.g. dimming, in order to avoid sudden unexpected darkness".

Operating principle

Activated by a pulse command through a pushbutton, the E 232 staircase light switch turns on the installation's lights for a time T1. In order to avoid an unexpected darkness, the Multi10 devices are equipped with a switch-off warning (double flash).

Application environments

Installation of the E 232 staircase lighting with switch-off warning functionality is ideal wherever the lighting must be timed and unexpected darkness must be avoided (staircases

and passageways in public places, cellars, garages, etc.).

Example of installation

One of possible applications of the E 232E-230 Multi 10 staircase switch is in the staircase lighting plant of a multistory building. Pushing the push-button, the timer of the E 232E-230 Multi 10 switch turns on the lights for a settable T1 time. At the end of the time the device gives a prewarning by blinking that the set time expires. The user can restart the timer again by pressing the button.



Control and automation technical details

E 234 CT-D electronic timers

Remarks

Legend

- Control supply voltage not applied / Output contact open
- Control supply voltage applied / Output contact closed
- A1-Y1/B1 Control input with voltage-related triggering

Terminal designations on the device and in the diagrams

The 1st c/o contact is always designated **15-17/18**.

The 2nd c/o contact is designated **25-27/28**.

The n/o contacts of the star-delta timers are designated with **17-18** and **17-28**.


Control supply voltage is always applied to terminals **A1-A2**.

ON-delay (Delay on make) CT-ERD, CT-MFD

This function requires continuous control supply voltage for timing.


Timing begins when control supply voltage is applied.

The green LED flashes during timing. When the selected time delay is complete, the output relay energizes and the flashing green LED turns steady. If control supply voltage is interrupted, the output relay de-energizes and the time delay is reset. Control input **A1-Y1/B1** of the CT-MFD is disabled when this function is selected.



OFF-delay with auxiliary voltage (Delay on break) CT-AHD, CT-MFD

This function requires continuous control supply voltage for timing. If control input **A1-Y1/B1** is closed, the output relay energizes immediately. If control input **A1-Y1/B1** is opened, the time delay starts. The green LED flashes during timing. When the selected time delay is complete, the output relay de-energizes and the flashing green LED turns steady. If control input **A1-Y1/B1** recloses before the time delay is complete, the time delay is reset and the output relay does not change state. Timing starts again when control input **A1-Y1/B1** re-opens. If control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.




Control and automation technical details

E 234 CT-D electronic timers

 **Impulse-ON
(Interval)**
CT-VWD, CT-MFD


This function requires continuous control supply voltage for timing. The output relay energizes immediately when control supply voltage is applied and de-energizes after the set pulse time is complete. The green LED flashes during timing. When the selected pulse time is complete, the flashing green LED turns steady. If control supply voltage is interrupted, the output relay de-energizes and the time delay is reset. Control input **A1-Y1/B1** of the CT-MFD is disabled when this function is selected.



 **Impulse-OFF with auxiliary voltage
(Trailing edge interval)**
CT-MFD


This function requires continuous control supply voltage for timing.

If control supply voltage is applied, opening control input **A1-Y1/B1** energizes the output relay immediately and starts timing. The green LED flashes during timing. When the selected pulse time is complete, the output relay de-energizes and the flashing green LED turns steady. Closing control input **A1-Y1/B1**, before the time delay is complete, de-energizes the output relay and resets the time delay. If control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.




 **Flasher, starting with the ON time
(Recycling equal times, ON first)**
CT-EBD, CT-MFD

Applying control supply voltage starts timing with symmetrical ON & OFF times. The cycle starts with an ON time first. The ON & OFF times are displayed by the flashing green LED, which flashes twice as fast during the OFF time. If control supply voltage is interrupted, the output relay de-energizes and the time delay is reset. Control input **A1-Y1/B1** of the CT-MFD is disabled when this function is selected.



 **Flasher, starting with the OFF time
(Recycling equal times, OFF first)**
CT-MFD

Applying control supply voltage starts timing with symmetrical ON & OFF times. The cycle starts with an OFF time first. The ON & OFF times are displayed by the flashing green LED, which flashes twice as fast during the OFF time. If control supply voltage is interrupted, the output relay de-energizes and the time delay is reset. Control input **A1-Y1/B1** of the CT-MFD is disabled when this function is selected.




Control and automation technical details

E 234 CT-D electronic timers

1. Pulse former (Single shot) CT-MFD

This function requires continuous control supply voltage for timing.


Closing control input **A1-Y1/B1** energizes the output relay immediately and starts timing. Operating the control contact switch **A1-Y1/B1** during the time delay has no effect. The green LED flashes during timing. When the selected ON time is complete, the output relay de-energizes and the flashing green LED turns steady. After the ON time is complete, it can be restarted by closing control input **A1-Y1/B1**. If control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.



2. Pulse generator, starting with the ON or OFF time (Recycling unequal times, ON or OFF first) CT-TGD

This function requires continuous control supply voltage for timing.

Applying control supply voltage, with open control input **A1-Y1/B1**, starts timing with an ON time first. Applying control supply voltage, with closed control input **A1-Y1/B1**, starts timing with an OFF time first. The ON & OFF times are displayed by the flashing green LED, which flashes twice as fast during the OFF time. The ON & OFF times are independently adjustable. If control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.




3. Star-delta change-over (Star-delta starting) CT-SDD, CT-SAD

This function requires continuous control supply voltage for timing.

Applying control supply voltage to terminals **A1-A2**, energizes the star contactor connected to terminals **17-18** and begins the set starting time t₁. The green LED flashes during timing. When the starting time is complete, the first output contact de-energizes the star contactor.

Now, the transition time t₂ starts. When the transition time is complete, the second output contact energizes the delta contactor connected to terminals **17-28**. The delta contactor remains energized as long as control supply voltage is applied to the unit.



Control and automation technical details

E 234 CT-D electronic timers – Technical data

Data at $T_a = 25^\circ\text{C}$ and rated values, unless otherwise indicated

	CT-D with 1 c/o contact	CT-D with 2 c/o contacts	CT-MFD.21
Input circuit - Supply circuit			
Rated control supply voltage U_s	24-240 V AC / 24-48 V DC	12-240 V AC/DC	
Rated control supply voltage U_s tolerance	-15...+10 %		
Rated frequency	DC or 50/60 Hz		
Frequency range AC	47-63 Hz		
Typical power consumption	max. 3.5 VA		
Power failure buffering time	min. 20 ms		
Release voltage	> 10 % of the minimum rated control supply voltage U_s		
Input circuit - Control circuit			
Control input, control function	A1-Y1/B1	start timing external	
Kind of triggering		voltage-related triggering	
Resistance to reverse polarity		yes	
Parallel load / polarized		yes / yes	
Maximum cable length to the control inputs		50 m - 100 pF/m	
Minimum control pulse length		20 ms	
Control voltage potential		see rated control supply voltage	
Current consumption of the control input		see data sheet	
Timing circuit			
Time ranges	7 time ranges 0.05 s - 100 h	1.) 0.05-1 s 2.) 0.5-10 s 3.) 5-100 s 4.) 0.5-10 min 5.) 5-100 min 6.) 0.5-10 h 7.) 5-100 h	
	4 time ranges 0.05 s - 10 min (CT-SDD, CT-SAD)	1.) 0.05-1 s 2.) 0.5-10 s 3.) 5-100 s 4.) 0.5-10 min	
Recovery time		< 50 ms	
Accuracy within the rated control supply voltage tolerance		$\Delta t < 0.005\% / V$	
Accuracy within the temperature range		$\Delta t < 0.06\% / ^\circ C$	
Repeat accuracy (constant parameters)		$\Delta t < \pm 0.5\%$	
Setting accuracy of time delay		$\pm 10\%$ of full-scale value	
Star-delta transition time	CT-SDD/ CT-SAD	fixed 50 ms / adjustable: 20 ms, 30 ms, 40 ms, 50 ms, 60 ms, 80 ms or 100 ms	
Star-delta transition time tolerance	CT-SDD / CT-SAD	$\pm 3\text{ ms}$	
Indication of operational states			
Control supply voltage / timing	U: green LED	: control supply voltage applied : timing	
Relay energized	R, R1, R2: yellow LED	: output relay energized	
Operating elements and controls			
Adjustment of the time range		front-face rotary switch, direct reading scales	
Fine adjustment of the time value		front-face potentiometer	
Preselection of the timing function at multifunction devices		front-face rotary switch, direct reading scales	
Adjustment of the transition time	CT-SAC	front-face potentiometer	
Output circuit			

Control and automation technical details

E 234 CT-D electronic timers – Technical data

		CT-D with 1 c/o contact	CT-D with 2 c/o contacts	CT-MFD.21					
Kind of output	15-16/18	Relay, 1 c/o contact	-						
	15-16/18; 25-26/28	-	Relay, 2 c/o contacts						
	17-18; 17-28		Relay, 2 n/o contacts (CT-SDC, CT-SAC)						
Contact material	AgNi alloy, Cd free								
Rated operational voltage U_e	250 V								
Minimum switching voltage / minimum switching current	12 V / 100 mA								
Maximum switching voltage / maximum switching current	250 V AC / 6 A	250 V AC / 5 A							
Rated operational current I_e	AC-12 (resistive) at 230 V	6 A	5 A						
	AC-15 (inductive) at 230 V	3 A	3 A	n/o: 3 A n/c: 0.75 A					
	DC-12 (resistive) at 24 V	6 A	5 A						
	DC-13 (inductive) at 24 V	2 A	2 A	1 A					
AC rating (UL 508)	utilization category (Control Circuit Rating Code)	B 300							
	max. rated operational voltage	300 V AC							
	maximum continuous thermal current at B300	5 A	n/o: 5 A						
	maximum continuous thermal current at C300	-	n/c: 2.5 A						
	max. making/breaking apparent power at B300	3600 VA / 360 VA	n/o: 3600/360 VA						
max. making/breaking apparent power at C300	-	n/c: 1800/180 VA							
Mechanical lifetime	30 x 10 ⁶ switching cycles								
Electrical lifetime	0.1 x 10 ⁶ switching cycles								
Max. fuse rating to achieve short-circuit protection	n/c contact	6 A fast-acting							
	n/o contact	10 A fast-acting	6 A fast-acting						
General data									
Mean time between failures (MTBF)	on request								
Duty time	100%								
Dimensions	see 'Dimensional drawings'								
Mounting	DIN rail (IEC/EN 60715), snap-mounting without any tool								
Mounting position	any								
Minimum distance to other units	horizontal / vertical	no / no							
Degree of protection	housing / terminals	IP50 / IP20							
Electrical connection									
Connecting capacity	fine-stranded with(out) wire and ferrule	2 x 0.5-1.5 mm ² (2 x 20-16 AWG) 1 x 0.5-2.5 mm ² (1 x 20-14 AWG)							
	rigid	2 x 0.5-1.5 mm ² (2 x 20-16 AWG) 1 x 0.5-4 mm ² (1 x 20-12 AWG)							
Stripping length	7 mm (0.28 in)								
Tightening torque	0.5-0.8 Nm (4.43-7.08 lb.in)								
Environmental data									
Ambient temperature range	operation / storage	-20 ... +60 °C / -40 ... +85 °C							
Climatic class	EC/EN 60068-2-30	3K3							
Relative humidity range	25-85%								
Vibration, sinusoidal	IEC/EN 60068-2-6	20 m/s ² ; 10 cycles, 10...150...10 Hz							
Shock (half-sine)	IEC/EN 60068-2-27	150 m/s ² , 11 ms							

Control and automation technical details


E 234 CT-D electronic timers – Technical data

	CT-D with 1 c/o contact	CT-D with 2 c/o contacts	CT-MFC.21
Isolation data			
Rated insulation voltage U_i	input circuit / output circuit output circuit 1 / output circuit 2	300 V not available	300 V 300 V
Rated impulse withstand voltage U_{imp}	between all isolated circuits	4 kV; 1.2/50 μ s	
Power-frequency withstand voltage test(test voltage)	between all isolated circuits	2.5 kV; 50 Hz; 60 s	
Basic insulation (IEC/EN 61140)	input circuit / output circuit	300 V	
Protective separation (IEC/EN 61140, EN 50178)	input circuit / output circuit	250 V	
Pollution degree		3	
Overshoot category		III	
Standards / Directives			
Standards		IEC/EN 61812-1	
Low Voltage Directive		2014/35/EU	
EMC Directive		2014/30/EU	
RoHS Directive		2011/65/EU	
Electromagnetic compatibility			
Interference immunity to		IEC/EN 61000-6-2	
electrostatic discharge	IEC/EN 61000-4-2	Level 3 (6 kV / 8 kV)	
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	Level 3 (10 V / m)	
electrical fast transient / burst	IEC/EN 61000-4-4	Level 3 (2 kV / 5 kHz)	
surge	IEC/EN 61000-4-5	Level 4 (2 kV L-L)	
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	Level 3 (10 V)	
Interference emission		IEC/EN 61000-6-3	
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B	
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B	

Control and automation technical details


E 234 CT-D electronic timers – Technical diagrams

Example of application - Star-delta changeover



2CDC25212BF0006

Control circuit diagram



2CDC252009F0002


Power circuit diagram

Control and automation technical details


E 234 CT-D electronic timers – Technical diagrams

Connection diagrams


CT-MFD.21




CT-MFD.12



CT-ERD.22



CT-ERD.12




A1-A2	Supply: 12-240 V AC/DC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
15-16/18	1st c/o contact


A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact


CT-AHD.22



CT-AHD.12



CT-VWD.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact


A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
15-16/18	1st c/o contact

A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact


CT-TGD.22




CT-TGD.12



CT-SDD.22



CT-SAD.22



A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
15-16/18	1st c/o contact

A1-A2	Supply: 24-48 V DC or 24-240 V AC
17-18	1st n/o contact (star contactor)
17-28	2nd n/o contact (delta contactor)

A1-A2	Supply: 24-48 V DC or 24-240 V AC
17-18	1st n/o contact (star contactor)
17-28	2nd n/o contact (delta contactor)


Control and automation technical details

E 234 CT-D electronic timers – Technical diagrams

Load limit curves


AC load (resistive)

CT-D.1x




DC load (resistive)


CT-D.1x




Derating factor F for inductive AC load




CT-D.2x



CT-D.2x




Contact lifetime




Wiring notes for devices with control input

A parallel load to the control input is possible




Dimensional drawings

CT-D devices with 1 c/o contact or 2 n/o contacts



CT-D devices with 2 c/o contacts



Dimensions in mm, inches

Control and automation technical details

TL Line twilight switches





Main features of DIN rail version - TL1

DIN-Rail version

- 2 indication leds: one for contact status and one for threshold
- Adjustable switching delay
- Preset with 10 LUX from factory
- Brightness range from 2 to 200 lux
- Screw-less version
- 1 module width





TL1 operating principle



Main features of pole version - TL1 Pole

- Innovative design for direct installation on a pole/wall
- Quick and easy to install, thanks to the simple wiring and ease of adjustment
- Laser etched connection diagram on the back of the product
- Integrated brightness sensor preset at 10 LUX from factory
- Adjustable threshold value from 2 to 200 LUX
- Switching delay of 25 sec. ±10% for ON and 35 sec. ±10% for OFF
- Unlosable screw terminals
- Protection degree IP54

TL1 Pole operating principle



Control and automation technical details

TL Line twilight switches

TL Line with DIN rail mounting – TL1

Operating principle

The diagram shows an example of the installation of the TL1 twilight switch in the lighting system of a commercial building. When the external light falls below a certain level (e.g. during the evening when the shop is closed), the device switches on the window lights and the shop sign. The lights can be switched off late evening to reduce power consumption thanks to the AD1NO-15m switch timer.




Application environments

The installation of the TL1 twilight switch with an AG Timer is particularly useful in settings and situations where energy saving is a prime concern (shops, office corridors and public passageways, car parks, parks, etc.).

Example of installation

As shown in the diagrams, one of the possible applications is the installation of a TL1 twilight switch in the lighting system of a commercial building.

When the external light falls below a certain level (e.g. when the shop is closed), the twilight switch switches on the window lights and the sign. The lights can be switched off late evening to reduce power consumption thanks to the AD1NO-15m switch timer which keeps the circuit open until the next morning. When the external light returns to above the threshold value, the twilight switch relay returns to the open position.



LIGHTING

Control and automation technical details

TL Line twilight switches

TL Line with pole/wall mounting – TL1 Pole

Operating principle

The diagram shows an example of the installation of the pole-mounted TL1 Pole twilight switch for motorway lighting systems. When the external light falls below a certain level, 10 lux for example, the device switches on the lights present in tunnels, service areas, near to junctions, etc. The lights are then switched off by the TL1 Pole in the morning when the 10 lux value is exceeded.




Application environments

The installation of the TL1 Pole twilight switch is particularly suitable for controlling public street lighting, thanks to the fact that they can be installed on poles, lamp standards, etc.

Example of installation

As shown in the diagrams, one of the possible applications is the installation of a TL1 Pole twilight switch in the motorway lighting system.

When the external light falls below a certain level (for example at sunset), the pole-mounted twilight switch switches on the lights to provide the correct lighting for the setting. At sunrise, the external brightness exceeds the threshold value and the twilight relay returns to the open position.



Control and automation technical details

LCR load shedding switch

Operating principle


LCR load shedding switches are used in case of exceeding of consumption threshold allowed in the system by switching off in sequence one or two loads, if necessary. At preset intervals and until current consumption is not below the reference level, the switch tries to reset the disconnected loads.

Application environments

The installation of the LCR load shedding switches is suitable for any environment and situation where it is necessary to control electric energy consumption within consumption limits allowed in the system.

Example of installation


As shown in the diagrams, one of the possible applications is the installation of the LCR load shedding switches in a printing office system, where the conditioning switch-on causes the exceeding of the energy consumption threshold defined with the supplying company by contract. The LCR load shedding switch preserves printing machines operation by switching off one or two primary loads automatically (i.e. night conditioning and lighting), where ON red leds indicate temporary OFF. After a preset interval, the switch checks that current consumption values fall within the limits again trying to reset the previously disconnected loads.



Control and automation technical details

LCR load shedding switch



Description



- 1 - Terminals for power supply and current measurement**
 - 2 - Relay terminals**
 - 3 - Red led: on indicates disconnected load**
 - 4 - Programming keys**
 - 5 - Backlit display (for 30 s from the pressure of one key)**
 - 6 - Measured power**
 - 7 - Active buzzer (Tbe)**
 - 8 - Disconnected load**
 - 9 - Setpoint is exceeded**
 - 10 - Icons for text guide keys function**
 -  (**PR**) Buzzer silencing
 -  (**OK**) Disconnected load rejection
 - 11 - Not disconnectable loads**
 - 12 - Disconnectable loads**

Connection via normally open contacts NO with $I_c \leq 16$ A and $I_a + I_b + I_c \leq 32$ A

Connection via normally closed contacts NC with $I_c \leq 16$ A and $I_a + I_b + I_c \leq 32$ A



Electrical installation solutions for buildings – Technical details

Energy efficiency

Index

Multimeters and network analyser	8/2
DMTME multimeters	8/5
ANR Network analyser	8/8
M2M Network analyser	8/9
EQ meters pulse outputs and digital inputs	8/10
Digital instruments	8/11
TMD temperature control units	8/13
Measurement current transformers with through primary	8/14

Energy efficiency technical details

Multimeters and network analyser

Communication networks with Modbus RTU protocol
Modbus is a serial communication protocol created for use with programmable logic controllers (PLC). It has become an industry standard and is the most widely used protocol for connecting industrial electronic devices.

Its principal benefits are:

- Ease of use
- Low resource requirements
- Openly published and royalty-free
- Allows communication between many devices connected to the same network

The Modbus support was created for controlling transfer on the line and pipeline monitoring. The system's flexibility and reliability make it suitable for a wide variety of processes and operations in nearly every industry.

Conventional I/O system

Plus

Field devices unaffected from wiring error caused by other devices
 thanks to independent wiring
 Devices are cheaper
 Well known technology

Minus


Higher installation complexity caused by:
 point to point wiring
 many terminal blocks, need additional rack space or more cabinets
 troubleshooting on complex wiring
 increased number of points of failure
 longer initial check and start up
 Expensive installation

Modbus determines how many MASTERS and SLAVES to recognise and connect together, how many senders and receivers are identified, how many messages are exchanged in an orderly manner and how many errors occur.
 Every peripheral that needs to communicate via Modbus is assigned a unique address.

Any one of them can then send a Modbus command, although generally (necessarily, in the case of serial) only one peripheral acts as a master.

A Modbus command contains the Modbus address of the peripheral it is intended for, and only that peripheral will act on the command, even though all the others receive it as well.

All Modbus commands incorporate control information to ensure that the received command is correct.




Modbus Network

Plus

Well known protocol, fully documented
 Many PLC, DCS and process systems are supporting this protocol
 Many facilities already use it
 Optimum choice when:
 Modbus network or devices are being used
 Modbus protocol is already used as a facility standard

Minus


Device operations require separate power
 Limited diagnostic capabilities (device applications)
 Limited use as a device bus



Energy efficiency technical details

Multimeters and network analyser

Application example



Energy efficiency technical details


Multimeters and network analyser

Connection among the devices


The protocol has one Master and up to 247 Slaves on a common line covering a maximum distance of 1200 metres. Only the Master initiates transactions. The transactions are of the request/reply type (addressed to a single Slave) or of the broadcast/reply type (addressed to all Slaves).

Modbus is often used for connecting a supervisory computer with a remote terminal unit (RTU) in supervisory control and data acquisition systems (SCADA). There are two versions of the protocol: one for serial ports (RS232 by default, but also RS485) and one for Ethernet. Modbus uses a compact hexadecimal data representation. The RTU format appends to commands/ data a cyclic redundancy checksum (CRC) field, while the ASCII format uses an LRU type (longitudinal redundancy check) checksum.

Unicast mode



Broadcast mode



Energy efficiency technical details

DMTME multimeters

DMTME multimeters

The DMTME series instruments are digital multimeters that measure the true rms value of the principal electrical quantities in 230/400 V a.c. networks, with the ability to store in memory the maximum/minimum/average measured values, and meter active and reactive energy. Four red LED displays provide a clear local readout of multiple measurements simultaneously. The DMTME multimeters perform the functions of a voltmeter, ammeter, power factor meter, wattmeter, varmeter, frequency meter, active and reactive energy meter in a single instrument, thus substantially reducing installation space requirements and wiring time.

The DMTME-I-485 version is additionally equipped with a pulse output and RS485 port for communicating the measured parameters via a Modbus network.

All versions come with a mini CD containing the instruction manuals, technical documentation, communication protocol and the DMTME-SW software.


The main innovations of the range are:

- Automatic recognition of the C.T. connection polarity, which simplifies installation of the instrument, making it error-proof.
- An hour counter for scheduled maintenance and an instrument life time display, to assist the installer with routine activities.
- Separate auxiliary 115/230 V a.c. power supply on all models, with extractable terminal blocks.

The DMTME-SW software can perform real-time acquisition of all the readings of a multimeter or network of DMTME multimeters, with the values displayed in a single on-screen window.

The measurements are shown in both numeric and "analog instrument" format. DMTME-SW also functions as a simple Modbus communication test instrument, allowing the installer to check the correct operation of the network prior to testing by the system integrator.

Configuration example of networked DMTME multimeters



Energy efficiency technical details

DMTME multimeters

Operating principle


Beyond the custom functions of electric measure, the DMTME-I-485 multimeter is equipped with two programmable relays used as output alarms. The setting of the alarm thresholds of all the network electrical parameters allows the customer to hold always under control its own system.

Application environments

The installation of DMTME-I-485 multimeter is adapt in all those cases in which the customer must hold under remote control its own system.

The use of the multimeter allows to set up system automation, to prevent malfunctions, due to overloads and undervoltages, to manage maintainance and to prevent overcoming of the contractual power, avoiding penal from the energy supplier.

The multimeter can carry out the same functions of the LSS1/2 load shedding switch, with the advantage of allowing installation in three-phase systems, instead of only single phase systems.




Example of installation

A possible application is the installation of DMTME-I-485 inside an electrical distribution switchboard of an industrial system.

It's possible to set up an alarm based on the total absorbed power from the system. When the power exceeds the set up threshold, the switching of the multimeter inner contact excites the coil of an auxiliary external relay.

The switching of the external relay, a ESB contactor or a E234 electronic timer, detaches a non primary load to lower the absorption levels of the entire system.

This application can be performed also by using M2M and ANR network analyser.



Energy efficiency technical details

DMTME multimeters

Operating principle

In addition to measuring the main electrical quantities, the DMTME-I-485-96 digital front panel multimeter has a serial port for implementing a communication network, and two digital outputs which can be configured as alarm outputs. Programmable alarm thresholds on all the electrical parameters of the network allow the user to continually monitor the entire installation.





Application environments

The DMTME-I-485-96 multimeter is ideal for those situations where users must remotely monitor their installation. The multimeter makes it possible to implement system automation, prevent malfunctions due to overloads and undervoltages, manage maintenance, and monitor the functioning of the installation.

Example of installation

The figures show an application example in which the DMTME-I-485-96 is installed in a motorway tunnel panel, with an alarm threshold programmed on the total power consumption of the row of lights. If one or more lamps burn out, the total power consumption drops and triggers an alarm. Remote acquisition of this data thus allows a maintenance technicians to be sent out only when effectively needed.

This application can be performed also by using M2M and ANR network analyser.



Energy efficiency technical details

ANR Network analyser

Operating principle

The ANR network analyser can perform a variety of functions. In this example the ANR is used as a data concentrator, acquiring incoming data from other measuring devices and energy meters, and as a load manager. The digital outputs in fact allow alarm thresholds to be programmed which, if breached, will trigger audible and visible alarm signals, or command the energising of a relay coil or switch to disconnect a particular load, thereby implementing effective automated management of energy consumption to comply with the maximum power draw permitted under the contract with the energy supplier.


Application environments

ANR is suitable for industrial and services sector applications which require implementing control of energy consumption, optimising service continuity and managing the quality of the network.

Example of installation

As illustrated in the figures, the ANR can be used to allocate power consumption among production cycles and track the share of energy costs in the total product cost. Through its digital inputs, the ANR is able to acquire the pulse signals output by various energy meters and thus keep track of their totals.

This application can be performed also by using M2M and DMTME network analyser.



Energy efficiency technical details

M2M Network analyser

Operating principle

Among its several functionalities, M2M performs bidirectional metering of energy and power on the 4 quadrants, allowing both production and consumption of energy to be monitored with a single device.

With the M2M analyser it is possible to keep the electrical consumption of all types of system under control, measuring them in real time both in economic and environmental impact terms, thanks to the immediate conversion of the energy balance into Euros and CO₂ kg.

Application environment



M2M bidirectional reading allows the amount of produced and consumed energy, saved money and avoided pollution to be displayed, optimal in systems generating energy from renewable sources. At the same time the possibility of keeping the quality of electrical parameters under control helps in achieving positive results on safety and operating costs.

Example of installation

A typical application where to use these M2M functionalities is a photovoltaic plant. By activating the GENERATION option, the energy counts will be carried out on 4 quadrants separating energy and absorbed power. Through the monitoring of network THD and Power factor, M2M can control harmonic distortion introduced in the system by non-linear loads such as inverter, computers, etc.

The integration of electrical consumption measurement in a supervision system can be done via the most advanced communication protocols (Modbus RTU, Modbus TCP/IP and Profibus DP) allowing 360° analysis of system performances.

This application can be performed also by using ANR network analyser.




Energy efficiency technical details

EQ meters pulse outputs and digital inputs

Using the input counters on an A or B series meter for read out of C series meters values


Now and then it can be useful to measure special loads like for example a boiler and an AC. These loads can be measured with C series meters which has their pulse outputs connected¹⁾ to one A or B series meter in Silver level or higher for functionality. In this way the measured values of the C series meters can be read over Modbus or M-Bus networks by read out of input counters on the general A or B series meter.



Water, Gas, heat and other meters

Similar connections can be used for reading water, gas or heat meters for example as long as they can generate pulses according to the specification of the inputs of the EQ meters. The most common pulse output is called S0 and it is common on all sorts of meters. Please note that the EQ meters do not provide the power for the pulses.

Wiring diagram for the 24 V DC installation








¹⁾Please be aware that the same inputs cannot be used for tariff shift if they are used for pulse counting. To shift four tariffs via input a minimum of two inputs is needed. Tariffs can be shifted via communication for meters above Silver level if it has RS-485 or M-Bus interface or internal clock if the meter is in Gold or platinum level.

Energy efficiency technical details

Digital instruments

Alarm activation logic



Device status	NO polarity (default)	NC polarity
Instrument not supplied		
Instrument supplied - no alarm		
Instrument supplied - alarm condition		

Digital measurement instruments with relays

Control of a load with the following characteristics:
 $I_n = 5 \text{ A}$ (rated normal operating current)
 $V_n = 230 \text{ V a.c.}$ (rated normal operating voltage)
 $V_{min} = 200 \text{ V a.c.}$ (RLV relay trip)

To scroll through the menu items press briefly (<3sec); to confirm press and hold (>3sec).


- 1 Connect as shown in the diagram ($V_{min} = 200 \text{ V}$).
- 2 Press and hold the key to enter the programming menu.
- 3 Scroll to the ACC menu item and confirm, then choose CC to select direct current operation, and confirm.
- 4 Set the full scale value to 300 V
- 5 Set the alarm threshold at 70 and confirm.
- 6 Adjust the Delay trimmer: scroll to the dLY menu item and confirm, then select the relay tripping delay (1...30 sec).
- 7 Program the alarm reset hysteresis (HySTeresis) at 10% of the threshold: scroll to the HSt menu item, confirm, and select the value 10. This results in a trip window between 200 and 220 V. The relay will be tripped at 200 V and return to normal operation at 220 V.
- 8 Set the alarm output polarity: scroll to the OUt menu item and confirm, then choose whether the contact opens or closes when an alarm is triggered (N.O. by default).




Energy efficiency technical details

Digital instruments

Voltmeters menu layout




Ammeters menu layout




Energy efficiency technical details

TMD temperature control units



- 1 Display for viewing temperature values and settings
- 2 ALARM LED for viewing alarm status of measuring channels
- 3 TRIP LED for viewing trip status (second-level alarm) of measuring channels
- 4 FAULT LED for indicating temperature control unit and sensor faults
- 5 HOLD LED for indicating whether manual reset function is enabled
- 6 FAN LED for indicating whether fan output is enabled
- 7 MAX T. pushbutton for selecting to view the max temperature level
- 8 ENTER/RESET pushbutton for confirming the programmed settings and for manually resetting any alarms that have been tripped
- 9 +/- pushbuttons for selecting the measuring channels and for adjusting the programming parameters
- 10 SET pushbutton with status LED for accessing and programming the device's settings



Energy efficiency technical details

Measurement current transformers with through primary

Power consumption of copper cables between the device and the transformer

For 5 A secondary

Cable section mm ²	Power (two-pole cable) VA VA					
	1 m	2 m	4 m	6 m	8 m	10 m
1.5	0.58	1.15	2.31	3.46	4.62	5.77
2.5	0.36	0.71	1.43	2.14	2.86	3.57
4	0.22	0.45	0.89	1.34	1.79	2.24
6	0.15	0.30	0.60	1.89	1.19	1.49
10	0.09	0.18	0.36	0.54	0.71	0.89

Maximum load (A) on copper bars according to DIN 43670 and 43671

Bar dimensions mm	Rated current (In) A		
	1 bar	2 bars	3 bars
20x5	325	560	
20x10	427	925	1180
30x5	379	672	896
30x10	573	1060	1480
40x5	482	836	1090
40x10	715	1290	1770
50x10	852	1510	2040
60x10	985	1720	2300
80x10	1240	2110	2790
100x10	1490	2480	3260


Rating	Ratio fault limit in %			
	0.05 In	0.2 In	In	1.2 In
0.5	±1	±0.75	±0.5	±0.5
1	±2	±1.5	±1	±1
3	From 0.5 In to 1.2 In = ± 3			

Rating	Angle fault limit in %			
	0.05 In	0.2 In	In	1.2 In
0.5	±1.8	±1.35	±0.9	±0.9
1	±3.6	±2.7	±1.8	±1.8
3	No prescriptions			

Accuracy rating

- 0.5 rating is required for power meters.
- 1 rating is required for unofficial power measures and power meters (measurements within the firm).
- 3 rating is required for relays and protection devices.

Error Curves



Electrical installation solutions for buildings – Technical details


SMISSLINE TP plug-in system

Index

Busbar system 125 A Overview	9/2
Busbar system 250 A Overview	9/4
Socket/additional socket/busbars	9/5
Incoming terminal block/Incoming terminal components	9/6
Power supply	9/8
Incoming Power Bar System 250 A and 400 A	9/9
Incoming UL 508 – Industrial Control Equipment	9/10
Busbar system accessories	9/11
Combi module: starting solutions in kit form	9/12
Definitions	9/13
Approvals according to IEC/EN 61439-6	
Busbar system 125 A	9/14
Technical data IEC and technical data UL508A	
Busbar system 125 A	9/15
Technical data according to IEC/EN 61439-6	
Power Bar System 250 A	9/16
Miniature circuit breaker Properties	9/18
S400M	9/19
S400UC	9/20
Trip characteristics	9/21
Internal resistances at rated voltage and power losses	9/23
Limitation of specific let-through energy I^2	9/24
Limitation curves – Peak current values I_p	9/25
Power supply: overload and short-circuit protection	9/26
Back-up and selectivity dates	9/27
Back-up protection with fuses, S800	9/28
Back-up protection with Tmax and XT	9/29
Influence of ambient temperature	9/30
Protection of circuits with fluorescent lamps	9/32
S400UC	9/33
F402, F404 Properties	9/34
F402, F404 Standard, short-time delayed and selective type	9/36
F402, F404 Technical data	9/38
FS401	9/40
FS403	9/42
Switch disconnector	9/45
Surge arrester OVR	9/46
Auxiliary switches and signal contacts	9/49
Accessory mounting	9/50
Auxiliary switches and signal contacts	9/51
Contact arrangements to auxiliary busbars	9/52

SMISSLINE TP technical details


Busbar system 125A Overview



- | | |
|--|----------------------|
| 1 Supply terminal | 10 Cover for socket |
| 2 Incoming terminal block with a max. current rating of 160 A 50 mm ² (2x25 mm ²) + 2x10 mm ² (LA, LB) | 11 Socket |
| 3 Cover for incoming terminal block | 12 End piece |
| 4 Supply cable | 13 Additional socket |
| 5 Residual current operated circuit breaker with overcurrent protection RCBO FS401 and FS403 | 14 Outgoing cable |
| 6 Residual-current circuit breaker F404 | |
| 7 Miniature circuit breaker S401 M | |
| 8 Signal contact | |
| 9 Plug contacts | |


SMISSLINE TP technical details

Busbar system 125A Overview



SMISSLINE TP technical details


Busbar system 250 A Overview



- | | |
|---|---|
| 1 6 and 8-module socket | 10 Busbar 250 A PE |
| 2 end piece on left and right | 11 Busbar 250 A N |
| 3 6 and 8 module additional socket | 12 Incoming block, supply 250 A, M8 bolt on maximum 150 mm² |
| 4 Busbar LA 40 A | 13 Incoming terminal component, supply 250 A, maximum 120 mm² |
| 5 Busbar LB 40 A | 14 Isolator |
| 6 Busbar 250 A N | 15 Spareway cover |
| 7 Busbar 250 AL1 or DC +,- | 16 Adapter for DIN rail components |
| 8 Busbar 250 A L2 or DC +,- | 17 Adapter for Motor starter MS116/132 |
| 9 Busbar 250 A L3 or DC +,- | 18 Combi module with a current rating of 32 A |

SMISSLINE TP technical details

Socket/additional socket/busbars



Socket bases ZLS906, ZLS908

The SMISSLINE socket system is a totally new kind of assembly and connection technology for the construction of distributions. Besides the classic method of snapping the devices onto 35-mm mounting rails, the new family of devices can be directly attached to the socket bases with integrated busbars. The time-consuming process of connecting up the supply is thereby no longer needed. In addition, in the event of rearrangement or expansion, the replacement of devices in existing systems is made significantly easier.



The socket sections and the wide range of accessories make it possible to plan with the capability for expansion and to construct distribution systems of any desired size in a short period of time.

6- and 8-module sockets are installed either by screwing them onto any flat surface or by snapping them onto a 35 mm DIN mounting rail. Lateral movement or detachment of the sockets again is possible before final fixing.

In order to determine the required socket length, the space necessary for

- the devices required
- the incoming terminal block and
- any reserve spaces needed must be determined.

Snap mounting

Pull down the slide with a screwdriver until it latches (socket can be moved).



Press on front of slid:

Fixed position
(Sockets fixed)

The key features

- System of any desired length (even number of poles)
- Integrated busbars
- Simple device change
- Long-term planning and problem free extension possible
- Significant time savings during assembly and connection



Busbars for the sockets and additional socket ZLS200

The busbars of size 10x3mm can be loaded with currents up to 100 A. They are plated for perfect contact with the devices plug-in contacts. The maximum available busbar length is 1979 mm. The same busbar type is used, regardless whether it is fitted in the socket (L1, L2, L3, N) or in the additional socket (N, PE). The busbars are inserted in to the socket from the front.



Auxiliary busbars for the socket ZLS202

The 5x2mm auxiliary busbars are intended for a common power supply of auxiliary switches and signal contacts. They are also plated and their max. delivery length is 1979 mm.

Like the main busbars, the auxiliary busbars are inserted in holders LA and LB from the front. Of course, only on auxiliary busbar can be fitted.

SMISSLINE TP technical details

Incoming terminal block/Incoming terminal components

General

The incoming terminal block is used to connect cables directly to the busbars. The terminals act directly on the busbars and therefore fix the incoming terminal block. Removable terminal tops permit the connection of continuous conductors (risers) while horizontal or vertical cable entry is also possible.

Instead of using the incoming terminal block, the power supply can also be realized via a device (e.g. residual current operated circuit breaker, miniature circuit breaker or switch disconnector).


Power supply left or right, maximum 125 A.

Max. 35 °C Ambient air temperature for 125 A continuously.



Power supply in centre, maximum 160 A.

A maximum of 125 A is permitted on either side. A total of 160 A must not be exceeded.



Incoming terminal blocks ZLS224, 225

A standard incoming terminal block whose cover provides protection against accidental contact. Construction height 50 mm. The base plate can be fitted with a maximum of 4 main terminals L1, L2, L3 and N for the busbars, and 2 auxiliary terminals LA and LB for the auxiliary busbars.



Incoming terminal blocks, low ZLS228, 229

Incoming terminal block with construction height of 36 mm.


SMISSLINE TP technical details

Incoming terminal block/Incoming terminal components



Incoming terminal blocks ZLS260 to 262

Compact terminal block with the construction width of 18 mm for 2 poles.
The maximum rated current is 63 A for L1, L2, L3N and 6 A for LA, LB.




Incoming maximum 63 A.



Incoming terminal component ZLS250 to 255

The incoming terminal component, with an installation width of 36 mm is available as a single-pole component for the line conductors L1, L2, L3 and as neutral. The terminals act directly on the busbars and thereby fix the incoming terminal component. The incoming terminal component, L1, L2, L3 and N can be combined to meet specific needs. A maximum cable cross-section of 95 mm² can be connected to the incoming terminal component.



Incoming terminal component, in centre, maximum 200 A.
But on each side not more than 125 A.




Incoming bolt-on solution M8 50 mm² up to 150 mm² or 4/0AWG for UL

This Incoming block can be used for side feed Incoming with 250A for IEC and UL applications. It is a bolt-on solution for a connection up to 150 mm². For a safe and strong connection to Incoming molded case circuit breaker upstream. Can only be used for the 250 A Power Bar System.


SMISSLINE TP technical details

Power supply




Indirect supply via residual current operated circuit breaker (RCCB) (or switch disconnector)

The supply cable is connected at the top of the RCCB. This supply variant gives the busbars and therefore all subsequent devices RCCB protection. If several RCCB groups are planned, the busbars should be separated and spaced using the dark grey busbar insulator ZLS938. Attention must then be paid to the regulations governing protection of the residual current circuit breaker by subsequent miniature circuit breakers. The supply can also be fed in through the switch disconnector.




Direct supply to residual current operated circuit breaker (or switch disconnector)

Instead of using the incoming terminal block, the power can also be supplied via a device. In this case, the supply cable is connected to the lower terminal of the device. The residual current operated circuit breaker or switch disconnector can be supplied with 63A regardless of its rated current, since the plug-in connection arrangement of the device is suitable for this amount of current. For current in excess of 63A, the incoming terminal block or the incoming terminal component should be used.



Supply of auxiliary busbars LA and LB

The two auxiliary busbars LA and LB can be supplied using the additional terminal ZLS 233 via a incoming terminal block. The maximum operating current of the auxiliary busbars is 40 A.



Incoming block for two auxiliary busbars LA, LB


The pluggable incoming block is especially for the two auxiliary busbars LA, LB. The maximum rated current is 6 A.

SMISSLINE TP technical details

Incoming Power Bar System 250A and 400A IEC


—
01 Power supply side
feed, maximum 250A.

—
02 Central feed
250A, 400A total.
The cables in the con-
nections must have
the same length.
Incoming terminal
blocks ZLP25X.



—
01

—
02




SMISSLINE TP technical details

Incoming UL 508 – Industrial Control Equipment

- 01, 02 Max. 250 A Incoming Power Bar System 250 A any side 600 V AC
- 03 Max. 250 A Incoming 125 A each side 600 VAC
- 04 Max. 125 A 600 VAC
- 05 Max. 125 A 600 VAC

CSA C22.2 No. 14 – Industrial Control Equipment File E222110


Rated voltage:	277 Y/480V, 480V, 347 Y/600V and 600V
Rated current:	ZLS200 bus bar 125A, ZLSP200 250A
Maximum current for supply:	250A




01



02



03



04



05

SMISSLINE TP technical details

Busbar system accessories



Socket end piece ZLS920

To prevent displacement of sockets and busbars (particulary when installed vertically) end pieces can be fitted at the start and finish of each row of sockets. These simultaneously ensure electrically protected covering of the busbar end faces and mechanical fixing of the sockets oh the mounting rail.



Intermediate piece ZLS725

The light grey intermediate piece matches the device profile and fills empty module spaces.




Busbar insulator ZLS938

The dark grey busbar insulator electrically isolates the separated busbar ends from each other (e.g. when using several RCD protected groups) and also identifies the isolation point from outside. It conforms with the device profile and its space requirement is 1 module.



Busbar cover ZLS100

If component modules or spare modules are not requiered, the busbar cover ensures electrically protected covering of the main and auxiliary busbars. The cover (4 modules) can be divided anywhere. The openings allow voltage measurements on the busbars without removing the cover.



Extension adapter ZLS101

The extension adapter, single or several side by side, can be plugged into the busbar cover via the built-in holding device. This enables conventional DIN devices with 45 mm cap size to be snapped onto the SMISSLINE socket. By plugging in several extension adapters one on top of the other, heights can be adjusted in multiples of 7 mm

SMISSLINE TP technical details

Combi module: starting solutions in kit form

Direct-On-Line Starters

- MS116
- + BEA16-4
- + AF09, AF12, AF16


- MS116 up to 16 A
- + BEA26-4
- + AF26, AF30, AF38

- MS116 > 16 A
- + BEA38-4
- + AF26, AF30, AF38

- MS132
- + BEA16-4
- + AF09, AF12, AF16


- MS132 up to 10 A
- + BEA26-4
- + AF26, AF30, AF38

- MS132 > 10 A
- + BEA38-4
- + AF26, AF30, AF38



Mounting possibilities on the combi module:

The following combinations of contactor, motor circuit breaker and connector are possible on the combi module.



Reversing Starters

- MS116
- + BEA16-4, BER16-4, VEM4
- + AF09, AF12, AF16


- MS116 up to 16 A
- + BEA26-4, BER38-4, VEM4
- + AF26, AF30, AF38

- MS116 > 16 A
- + BEA38-4, BER38-4, VEM4
- + AF26, AF30, AF38

- MS132
- + BEA16-4, BER16-4, VEM4
- + AF09, AF12, AF16

- MS132 up to 10 A
- + BEA26-4, BER38-4, VEM4
- + AF26, AF30, AF38

- MS132 > 10 A
- + BEA38-4, BER38-4, VEM4
- + AF26, AF30, AF38



SMISSLINE TP technical details

Definitions

Rated short-circuit breaking capacity I_{cn}

According to EN 60898-1

The maximum current which a switching device can switch off without damage at a rated operational voltage and rated operational frequency. It is specified as an effective value.

Rated ultimate short-circuit breaking capacity I_{cu}

According to EN 60947-2

Ultimate short-circuit breaking capacity that a circuit breaker can switch off without damage at a rated operational voltage and rated operational frequency. It is specified as an effective value.

Rated service short-circuit breaking capacity I_{cs}

According to EN 60947-2

Service short-circuit breaking capacity that a circuit breaker can switch off without damage at a rated operational voltage and rated operational frequency. It is specified as an effective value.

Rated insulation voltage U_i

The rated insulation voltage (U_i) is the voltage to which dielectric checks and creepage distances refer. The maximum rated operational voltage must not exceed its rated insulation voltage.

Rated impulse withstand voltage U_{imp}

Peak of a withstand voltage of a specified form and polarity with which the circuit can be loaded under specified test conditions without a breakdown and to which clearances relate. The rated impulse withstand voltage must be equal to or greater than the values of the withstand overvoltages (transient overvoltages) which occur in the system in which the device is used.

Rated short-time withstand current I_{cw}

The rated short-time withstand current is the effective value of the short-circuit current, as specified by the manufacturer for this circuit, that the circuit can conduct without damage. Unless otherwise specified, a time of 1 s shall apply.

Rated conditional short-circuit current I_{cc}

The rated conditional short-circuit current is the value of the prospective short-circuit current, as specified by the manufacturer, for a switching device combination that the latter can conduct during the total break time. The information about the specified short-circuit device must be given by the manufacturer.

Rated fused short-circuit current I_{cf}

The rated fused short-circuit current is the conditional rated short-circuit current if the short-circuit device is a fuse in accordance with IEC 60269 [IEV 441-17-21, modified].

Rated peak withstand current I_{pk}

The rated peak withstand current is the peak value of the withstand current of the circuit of a combination of switching devices, as specified by the manufacturer.

Back-up protection

Assignment of two overcurrent protective devices in series, where the protective device, generally but not necessarily on the supply side, effects the overcurrent protection with or without the assistance of the other protective device and prevents excessive stress on the latter [IEC 60947-1, definition 2.5.24].

Total selectivity

Overcurrent discrimination where, in the presence of two overcurrent protective devices in series, the protective device on the load side effects the protection without causing the other protective device to operate [IEC 60947-2, definition 2.17.2].

Partial selectivity

Overcurrent discrimination where, in the presence of two overcurrent protective devices in series, the protective device on the load side effects the protection up to a given level of overcurrent, without causing the other protective device to operate [IEC 60947-2, definition 2.17.3].

SMISSLINE TP technical details

Approvals according to IEC/EN 61439-6. Busbar system 125 A.

Busbar system touch proof:

Use only for wall mounted application (horizontal or vertical).

When installed correctly the requirements of EN/IEC 61439-2 are met.

Number of poles	max. 6 to 110 3p+N / 2 additional bars PE+N
Rated operational voltage (U_e)	690 V AC, 1000 V DC (400 V AC, 250 V DC when used for load-free snap on and off under power)
Rated insulation voltage (U_i)	690 V AC, 1000 V DC
IP Code	IP20B
Mounting position	horizontal or vertical, direct mounting or mounting on DIN rail acc. to EN 60715 35 mm
Pollution degree	3 (690 V AC) 2 (1000 V DC)
Rated impulse voltage (U_{imp})	8 kV (L1L2L3N)
Rated current of the assembly (I_nA)	Max. 125 A side feeding Max. 200 A (center feeding) Max. 250 A (Double feed side or center)
Auxiliary circuit	max. 40 A
Rated current of a circuit (I_{nc})	Main circuit: Max. 125 A
Rated current of Auxiliary circuit	40 A
Rated short-time withstand current (I_{cw})	10kA / 300ms
Auxiliary circuit	4 kA / 50ms
Rated peak withstand current (I_{pk})	Main circuit: 30 kA
Auxiliary circuit	6 kA
Rated frequency (f)	50/60Hz
Rated conditional short-circuit current (I_{cc})	100 kA (415 V, 50 kA)
Ambient air temperature	max. 60°C
Size of CU bars 3P+N+PE	3x10 mm (30 mm ²)
Size of CU auxiliary bars La Lb	2x5 mm (10 mm ²)

Rated conditional short-circuit current (I_{cc})	Incoming current of main busbars (L1, L2, L3, N)	Short circuit protection device (SCPD)	
		Fuse	MCCB
50 kA (690 V)	250A		ABB T_{max} 250A
	200A	NH1 gG 690V/200A	ABB T_{max} 250A
	160A	NH1 gG 690V/160A	ABB T_{max} 250A
	63A	NH00 gG 690V/63A	ABB Type S803S in combination with Type S803S-SCL63-SR
	Incoming current of auxiliary busbars (LA LB)		
50 kA (415 V)	40A	NH00 gG 690V/40A	ABB Type S800 with 240V/415V

Rated Voltage (U_e)	Rated conditional short-circuit current (I_{cc})	Incoming current of main busbars (L1, L2, L3, N)	Short circuit protection device (SCPD)	
415 V	100 kA	250 A	NH1 gG 690V/250A	ABB T_{max} T4/XT4 250 A
690 V	25 kA	250 A	NH1 gG 690V/250A	ABB T_{max} T4/XT4 250 A
	Incoming current of auxiliary busbars (La Lb)			
	25 kA	40 A	NH00 gG 415 V/40 A	ABB Type S800 with (240V/415V AC)

SMISSLINE TP technical details

Busbar system 125A

**SMISSLINE TP system for UL 508 – Industrial Control Equipment,
CSA C22.2 No. 14 – Industrial Control Equipment UL File E222110**

Technical data UL508 Industrial Control Equipment SMISSLINE TP busbar system

Rated Voltage: 600 VAC

Rated Current (End feed, left and right): 125 A left, 125 A right

Rated Current (Center Feed): 250 A max. if used with two feeder blocks.

Short Circuit Ratings: 50 kA, max. 480 VAC and 480 Y/277V and 240 VAC or 35 kA. max. 600 VAC and 600 Y/347V

Technical data UL508 Industrial Control Equipment (ZLS906, ZLS908, ZLS920, ZLS926, ZLS928)

	Busbar ZLS200	Feeder block ZLS924 ZLS25X	Combimodule ZLS840X, 842X	Universal- adpter ZLS97X	Terminals ZLS95XUL, 91XUL	Combi modul ZMS132X	Adapter motor strater ZMS93X
Maximum rated voltage	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC
Maximum rated current	125 A	150A	30 A	32 A, 63 A	32 A, 100 A, 150 A	32 A	32 A

Terminals for 125A SMISSLINE TP System

ZLS954UL - Terminal 150A (Neutral)

ZLS959UL - Terminal (PE)

ZLS913UL - Terminal 63A (Neutral)

ZLS918UL – Terminal 32A (Neutral)

ZLS919UL - Terminal (PE)

ZLS929UL - Terminal (PE)

Circuit breaker accessories UL489 universal adapter

970UL, 971UL, 972UL or 973UL	
Maximum nominal voltage	600 V
Maximum nominal current	25 A, 45 A

SMISSLINE TP technical details

Technical data according to IEC/EN 61439-6

Power Bar System 250 A

Busbar system touch proof:

Use only for wall mounted application (horizontal or vertical).

When installed correctly the requirements of EN/IEC 61439-2 are met.

Number of poles:	6 to 110 3p+N / 2 additional bars PE+N
Rated operational voltage (U_e):	690VAC, 1000VDC (400VAC, 250VDC when used for load-free snap on and off under power)
Rated insulation voltage (U) Main circuit:	690VAC, 1000VDC
Rated insulation voltage (U) Auxiliary circuit:	415VAC
IP Code:	IP20B
Mounting position:	horizontal or vertical, direct mounting or mounting on DIN rail acc. to EN 60715 35 mm
Pollution degree:	3 (690V a.c.) 2 (1000V d.c.)
Rated impulse voltage (U_{imp}):	8 kV Main circuit; 6 kV Auxiliary circuit
Rated current of the assembly (I_{nA}):	max. 250 A side feeding
Rated current of a circuit (I_{nc}):	Main circuit: Max. 100 A
Rated current of Auxiliary circuit:	40 A
Rated short-time withstand current (I_{cw}):	15kA/100 ms Main circuit 4 kA / 50 ms Auxiliary circuit
Rated peak withstand current Main circuit (I_{pk}):	Main circuit: 30 kA
Rated peak withstand current Auxiliary circuit (I_{pk}):	6 kA
Rated frequency (f):	50/60Hz
Rated conditional short-circuit current (I_{cc}):	see table below
Ambient air temperature:	max. 60°C
Size of CU bars 3P+N+PE:	3x25 mm (75 mm ²)
Size of CU auxiliary bars La Lb:	2x5 mm (10 mm ²)

Rated Voltage (U_e)	Rated conditional short-circuit current (I_{cc})	Incoming current of main busbars (L1, L2, L3, N)	Short circuit protection device (SCPD)	
415 V	100 kA	250 A	NH1 gG 690V/250A	Fuse ABB T_{max} T4/XT4 250 A
690 V	25 kA	250 A	NH1 gG 690V/250A	ABB T_{max} T4/XT4 250 A
Incoming current of auxiliary busbars (La Lb)				
25 kA			NH00 gG 415 V/40 A	

SMISSLINE TP technical details

Busbar system 250 A

Technical data data UL508; Approvals for US and CA: cULus

SMISSLINE TP system for UL 508 – Industrial Control Equipment,

CSA C22.2 No. 14 – Industrial Control Equipment UL File E222110

Technical data UL508 Industrial Control Equipment SMISSLINE TP busbar system

Rated Voltage: 600 V AC

Rated Current: 250 A

Short Circuit Ratings: 50 kA, max. 480 V AC, 480 Y/277 V and 240 V AC or 30 kA, max. 600 V AC and 600 Y/347 V

Technical data UL508 Industrial Control Equipment (ZLSP906, ZLSP908, ZLSP920)

	Busbar ZLSP200	Feeder ZLS934	Feeder block ZLS924, 95X	Combimodule ZLS840X, 842X	Universal- adapter ZLS97X	Terminals ZLS95XUL, 91XUL	Combi modul ZMS132X	Adapter motor strater ZMS93X
Maximum rated voltage	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC	600 V AC
Maximum rated current	250 A	250 A	150 A	30 A	32 A, 63 A	32 A, 100 A, 150 A	32 A	32 A

Circuit breaker accessories UL489 universal adapter

970UL, 971UL, 972UL or 973UL

Maximum nominal voltage

Maximum nominal current

SMISSLINE TP technical details

Miniature circuit breaker Properties



General Information

The SMISSLINE miniature circuit-breaker is an energy-restricting circuit-breaker that has high performance values and that is equally suitable for the industrial sector, for commercial use and for installation at home.

If a short-circuit occurs, it guarantees excellent selectivity conditions to upstream overcurrent circuit breakers while the load on equipment that is connected downstream is limited to a minimum amount.

The most important features

- High rated breaking capacity of 10 kA or 6 kA
- Optimum ease of installation and connection
- The pole conductors are protected against accidental contact
- Tripping characteristic on B, C, D, K, UCZ/UCC



Miniature circuit-breaker in accordance with standard EN 60898-1

This standard is for electrical installation material for household installations and for similar purposes. It regulates the use of miniature circuit-breakers by the layman up to a maximum of 125 A, a voltage of 440 VAC and up to a maximum of 25 kA.

Miniature circuit-breaker in accordance with standard EN60947-2

This standard is for low-voltage material used for industrial purposes. It regulates the use of circuit-breakers (and not miniature circuit-breakers) by qualified personnel up to a maximum voltage of 1000 VAC or 1500 VDC. This standard does not recognise any maximum values when it comes to current and breaking capacity. In practice, the standard is also applied to miniature circuit-breakers.



Brief description of tripping

The SMISSLINE miniature circuit breakers have a current-limiting operation.

They have two different releases acting on the mechanism.

1. Thermal release, operating with a time delay, for overload protection
2. Electro-magnetic release plunger operated for short-circuit protection.




They offer:

- high short-circuit breaking capacity
- high selectivity to the back-up fuse
- In the event of short-circuits, low electrodynamic and heating effects on the cable and the point of fault location due to the drastically limited let through energy $\int i^2 dt$.



Oscillogram of a short-circuit current interruption



$I_k \cdot \sqrt{2}$ = peak value of prospective short-circuit current
 i_d = Max. peak let through current of circuit breaker S 400
 U_n = Supply voltage
 U_B = Arc voltage of circuit breaker
 t_k = Total interruption time

SMISSLINE TP technical details

S400M

With a expert working the requirements of EN/IEC 61439-2 are as well covered

	S400E, S400M
General data	
Tripping characteristics	B,C,D,K
Standards	IEC/EN 60898-1 IEC/EN 60947-2
Poles	1P, 1P+NP, 2P, 3P, 3P+NP
Rated current I_n	0.5A...63A
Rated frequency f	50/60Hz
Rated insulation voltage U_i acc. to DIN EN 60664-1	440VAC
Rated impulse withstand voltage U_{imp} (1.2/50μs)	4kV
Overshoot category	III
Pollution degree	2
Data acc. to IEC/EN 60898-1	1P: 230/400VAC; 1P+N: 230VAC; 2...4P: 400VAC; 3P+N: 400VAC
Rated operational voltage U_e	
Min. operating voltage	12VAC-12VDC
Rated short-circuit capacity I_{cn}	10kA S400M
Energy limiting class	3
Reference Ambient Air Temperature for Overload Tripping	C, D: 30°C
Electrical and Mechanical Endurance	10 000 ops.
Data acc. to IEC/EN 60947-2	
Rated operational voltage U_e	1P: 240VAC; 1P+N: 240VAC; 2...4P: 415VAC; 3P+N: 415VAC
Min. operating voltage	12V AC-12V DC
Rated ultimate short-circuit capacity I_{cu}	25kA (0,5 up to 16A, 240/415V) 15kA (20 up to 63A, 240/415V) 15kA (0,5 up to 16A, 254/440V) 6kA (20 up to 63A, 254/440V)
Rated service short-circuit capacity I_{cs}	15kA (0,5 up to 16A, 240/415V) 7,5kA (20 up to 63A, 240/415V) 6kA (0,5 up to 16A, 254/440V) 3kA (20 up to 63A, 254/440V)
Reference Ambient Air Temperature for Overload Tripping B, C, D: 30°C K: 40°C	
Electrical and Mechanical Endurance	$I_n < 32A$: 20 000 operating cycles $I_n \geq 32A$: 10 000 operating cycles
Mechanical Data	
Housing	RAL 7035
Toggle	black
Classification acc. To NF F 126-101, NF F 16-102	acc. to I2/F3
Protection degree acc. to EN 60529	IP20, IP40 in enclosure with cover
Mechanical endurance	20 000 ops.
Shock resistance acc. to IEC/EN 60068-2-30	30g-3 shocks-11ms
Vibration resistance acc. to IEC/EN 60068-2-6	5g-20 cycles at 5...150...5 Hz with load 0.8 I_n
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	2 cycles with 55°C/90-96% and 25°C/95-100%
Ambient temperature	-25...+55°C
Storage temperature	-40...+70°C
Installation	
Standed Cross-section of conductors (top/bottom)	upper terminal section: 0,75-25 mm ² lower terminal section: 0,75-10 mm ²
Tightening torque	2.8Nm
Screwdriver	No. 2 Pozidrive
Mounting	plug in on bus bar system SMISSLINE
Mounting position	any
Supply	any
Dimensions and weight	
Pole dimensions (HxDxW)	91x18x82
Pole weight	110g


SMISSLINE TP technical details

Miniature circuit breaker S400UC

S400UC	
General data	
Tripping characteristics	UCC, UCZ
Standards	IEC/EN 60947-2
Poles	1P, 2P
Rated current I_n	0.5 A ... 63 A
Rated frequency f	50/60 Hz
Rated insulation voltage U_i acc. to DIN EN 60664-1	440 V AC
Rated impulse withstand voltage $U_{imp.}$ (1.2/50 μ s)	4 kV
Overshoot category	III
Pollution degree	2
Data acc. to IEC/EN 60947-2	
Rated operational voltage U_e	110 V d.c. (1pole) 220 V d.c. (poles 1; 2) 440 V d.c. (2pole) 230/400 V (poles 1;2)
Min. operating voltage	12 V AC–12 V DC
Rated ultimate short-circuit capacity I_{cu}	10 kA (0,5 up to 63 A, 220 V d.c. 1pole) 20 kA (0,5 up to 63 A, 110 V d.c. 1pole) 25 kA (0,5 up to 63 A, 220 V d.c. 2pole) 10 kA (0,5 up to 63 A, 440 V d.c. 2pole) 10 kA (0,5 up to 63 A, 230/400 V a.c.)
Rated service short-circuit capacity I_{cs}	10 kA (0,5 up to 63 A, 220 V d.c. 1pole) 10 kA (0,5 up to 63 A, 110 V d.c. 1pole) 20 kA (0,5 up to 63 A, 220 V d.c. 2pole) 10 kA (0,5 up to 63 A, 440 V d.c. 2pole) 6 kA (0,5 up to 63 A, 230/400 V a.c.)
Reference Ambient Air Temperature for Overload Tripping	30 °C
Electrical and Mechanical Endurance	$I_n < 32$ A: 20 000 operating cycles $I_n \geq 32$ A: 10 000 operating cycles
Mechanical Data	
Housing	RAL 7035
Toggle	black
Protection degree acc. to EN 60529	IP20*, IP40 in enclosure with cover
Mechanical endurance	20 000 ops.
Shock resistance acc. to IEC/EN 60068-2-30	30 g–3 Shocks–11 ms
Vibration resistance acc. to IEC/EN 60068-2-6	5 g–20 cycles at 5 ... 150 ... 5 Hz with load 0.8 I_n
Environmental conditions (damp heat) acc. to IEC/EN 60068-2-30	2 cycles with 55 °C/90–96 % and 25 °C/95–100 %
Ambient temperature	-25 ... +55 °C
Storage temperature	-40 ... +70 °C
Installation	
Standed Cross-section of conductors (top/bottom)	upper terminal section: 0,75–25 mm ² lower terminal section: 0,75–10 mm ²
Tightening torque	2.8 Nm
Screwdriver	No. 2 Pozidrive
Mounting	plug in on bus bar system SMISSLINE
Mounting position	any
Supply	any
Dimensions and weight	
Pole dimensions (HxDxW)	91x18x82
Pole weight	110 g

SMISSLINE TP technical details

Miniature circuit breaker Trip characteristics



Trip characteristics: B

Thermal trip


1.13...1.45 $\times I_n$

Electromagnetic trip

3...5 $\times I_n$ AC

4...7 $\times I_n$ DC

Calibration temperature 30°C



Trip characteristics: C

Thermal trip

1.13...1.45 $\times I_n$ acc. to EN60898-1

Thermal trip


1.05...1.3 $\times I_n$ acc. to EN60947-2

Electromagnetic trip

5...10 $\times I_n$ AC

7...14 $\times I_n$ DC

Calibration temperature 30°C



Trip characteristics: D

Thermal trip


1.13...1.45 $\times I_n$

Electromagnetic trip

10...20 $\times I_n$ AC

15...30 $\times I_n$ DC

Calibration temperature 30°C



Trip characteristics: K

Thermal trip


1.05...1.3 $\times I_n$

Electromagnetic trip

10...14 $\times I_n$ AC

14...20 $\times I_n$ DC

Calibration temperature 40°C



Trip characteristics: UC

Z

1.05...1.35 $\times I_n$

3...5 $\times I_n$ DC

2...3 $\times I_n$ AC

C

1.13...1.45 $\times I_n$

7...14 $\times I_n$ DC

5...10 $\times I_n$ AC

Calibration temperature 30°C

SMISSLINE TP technical details

Miniature circuit breaker Trip characteristics


Trip characteristics example of trip curve interpretation of B-characteristics

a Thermal trip characteristics:

Lower test current $I_1 = 1.13 \times I_n$ = defined as non-tripping current.
The circuit breaker withstands 1.13 times the rated current for at least 60 minutes.
Upper test current $I_2 = 1.45 \times I_n$ = defined as trip current.
The circuit breaker trips at 1.45 times the rated current within 60 minutes.

b Electro-magnetic trip characteristics AC:

The circuit breaker withstands 3 times the rated current for more than 0.1 sec. (in this example, up to around 2 sec.).
The circuit breaker trips in less than 0.1 sec. at 5 times the rated current.



Trip behaviour of different trip characteristics

Trip characteristics and current ratings	Thermal release Test currents:			Electromagnetic release Test currents:		
	lower test current I_1	upper test current I_2	Trip time	lower test current	upper test current	Trip time
B 4 to 63 A	$1.13 \times I_n$	$1.45 \times I_n$	> 1 h < 1 h	$3 \times I_n$	$5 \times I_n$	> 0.1 s < 0.1 s
C 0.5 to 63 A	$1.13 \times I_n$	$1.45 \times I_n$	> 1 h < 1 h	$5 \times I_n$	$10 \times I_n$	> 0.1 s < 0.1 s
D 6 to 63 A	$1.13 \times I_n$	$1.4 \times I_n$	> 1 h < 1 h	$10 \times I_n$	$20 \times I_n$	> 0.1 s < 0.1 s
K 0.5 to 63 A	$1.05 \times I_n$	$1.2 \times I_n$ $1.5 \times I_n$ $6.0 \times I_n$	> 2 h < 2 h < 2 min > 2 s	$8 \times I_n$	$12 \times I_n$	> 0.2 s < 0.2 s

Application characteristics: B

Miniature circuit breaker for circuits supplying loads generating no or only minor inrush currents (boilers, electric heaters, cookers).

Application characteristics: C

The 'standard' miniature circuit breaker for circuits supplying loads producing inrush currents particular to inductive loads (TV sets, fluorescent and discharge lamps) and for socket outlets.

Application characteristics: D

Miniature circuit breaker for circuits supplying loads producing very high inrush currents (transformers, capacitor banks).

Main circuit breaker for the back-up protection of downstream connected circuit breakers.

Application characteristics: K

Circuit breaker for equipment:
The characteristics of these types enable the close protection requirements for equipment to be met.

Application characteristics: UC

Device protection in DC systems of up to 250 V = with a time constant of <15 ms (emergency networks, electroplating, etc.).

SMISSLINE TP technical details

Miniature circuit breaker

Internal resistances at rated voltage and power losses

Internal resistances and power loss per pole (cold resistance at room temperature)

Rated current I _n A	S400 M				S400 M-UCZ				S400 M-UCC	
	B, C, D ¹		K		B, C, D ¹		K		B, C, D ¹	
	R _i Ω	P _v W	R _i Ω	P _v W	R _i Ω	P _v W	R _i Ω	P _v W	R _i Ω	P _v W
0.5	5.5	1.4	4.906	1.2	6.34	1.6	6.34	1.6	6.34	2.6
1	1.44	1.5	1.505	1.5	1.55	1.6	1.55	1.6	1.55	3.5
1.6	0.63	1.6	0.594	1.5	0.695	1.8	0.695	1.8	0.695	2.9
2	0.460	1.8	0.415	1.7	0.46	1.9	0.46	1.9	0.46	3.9
3	0.150	1.4	0.181	1.6	0.165	1.5	0.165	1.5	0.165	4.5
4	0.123	1.9	0.150	2.4	0.12	1.9	0.12	1.9	0.12	2.4
6	0.051	1.8	0.080	2.9	0.052	1.9	0.052	1.9	0.052	3.5
8	0.029	1.9	0.043	2.7	0.038	2.4	0.038	2.4	0.038	3.5
10	0.012	1.2	0.0165	1.7	0.0126	1.3	0.013	1.3	0.013	1.3
13	0.0112	1.9	0.0153	2.6	0.0101	1.7	0.010	1.7	0.010	2.2
16	0.0074	1.9	0.0095	2.4	0.0077	1.8	0.007	1.8	0.007	1.8
20	0.004	1.6	0.0073	2.9	0.0067	2.7	0.0067	2.7	0.0067	2.5
25	0.0032	2	0.0053	3.3	0.0046	2.9	0.005	2.9	0.005	3.1
32	0.0026	2.7	0.0034	3.4	0.0025	3.6	0.0025	3.6	0.0025	3.7
40	0.0026	4.2	0.0028	4.5	0.0028	4.5	0.003	4.5	0.003	4.8
50	0.0017	4.3	0.0021	5.3	0.0012	3.0	0.0012	3.0	0.0012	3.0
63	0.0014	5.6	0.0015	5.9	0.0007	2.8	0.0007	2.8	0.0007	3.6

¹ Currents 0.5–4 A only apply to C and K characteristics.

SMISSLINE TP technical details



Miniature circuit breaker

Limitation of specific let-through energy I^2t



I^2t diagrams - Specific let-through energy value I^2t

The I^2t curves give the values of the specific let-through energy expressed in A^2s ($A=amps$; $s=seconds$) in relation to the prospective short-circuit current (I_{rms}) in kA.

S400 characteristics B-C



S400 characteristics D-K



SMISSLINE TP technical details


MCBs technical details

Limitation curves – Peak current values I_p


Limitation curves – Peak current values

The I_p curves give the values of the peak current, expressed in kA, in relation to the perspective symmetrical short-circuit current (kA).

Characteristics B–C



Characteristics K–D



SMISSLINE TP technical details

Power supply: overload and short-circuit protection

Overload and short-circuit protection of the plug-in socket system

Protection of the busbar system without upstream overcurrent protection

An important factor for the protection of the busbar system (sockets, incoming terminal block, incoming terminal component, adapter, combi module or terminals) is the characteristic of the rated peak withstand current I_{pk} . The rated peak withstand current I_{pk} of the SMISSLINE busbar system is 17 kA.

Protection of the busbar system with upstream overcurrent protection

The rated short-circuit current I_{cf} of the SMISSLINE busbar system is 50 kA.

If, on the power supply side, a circuit breaker of the type Sace Tmax 200 A, a high performance circuit breaker S800 or a NH fuse is positioned upstream of the busbar system, then due to the short-circuit current limiting effect of this protection device, a larger prospective short-circuit current of up to 50 kA for the plug-in socket system is permissible.

Overload and short-circuit protection of devices on the busbar system

The rated short-circuit breaking capacity (or rated breaking capacity) of the protective devices, together with the maximum short-circuit current at the installation location of the devices on the busbar system, must be taken into consideration.

This is not only relevant for the SMISSLINE busbar system, but is also applicable to the distribution construction.

Miniature circuit breaker

If the prospective short-circuit current at the installation location of a miniature circuit breaker is not greater than its rated breaking capacity, no back-up protection via an upstream overcurrent protection device is necessary.

If the prospective short-circuit current at the installation location of a miniature circuit breaker is greater than its rated short-circuit breaking capacity, the current ratings of the upstream overcurrent protection device must not exceed the table values in the back-up tables (catalogue, page 2/20 onwards).

Residual-current circuit breaker

A back-up fuse with max. 100 A gL/gG or a high performance circuit breaker S800 100 A is required for short-circuit protection upstream or downstream (see Coordination table, page 2/42). A back-up fuse is not required up to the level of the internal short-circuit withstand rating. Thermal protection can be ensured by means of downstream miniature circuit breakers, but only if the rated currents do not exceed the value of the current rating of the residual-current circuit breaker in consideration of a utilisation factor.

Surge arrester OVR

An upstream overcurrent protection device with max. 160 A gL/gG is necessary for short-circuit protection (in the case of non-independent interruptions of the secondary current).

Back-up fuses for devices with a universal adapter

In principle, the same requirements apply as for directly plugged-in devices.

SMISSLINE TP technical details

Back-up and selectivity dates

SOC - Selected Optimized Coordination

See as well ABB on <https://applications.it.abb.com/SOC/>



SOC - SELECTED OPTIMIZED COORDINATION

ABB

 Motor protection	Selectivity	Back-up	Other devices protection
			

SOC - Selected Optimized Coordination

SMISSLINE TP technical details

Miniature circuit breaker

Back-up protection with fuses, S800

a) If the short-circuit current at the point of installation of the circuit breaker is not greater than the nominal breaking capacity of the MCB, an upstream fuse is not needed. If a fuse is fitted upstream for installation reasons, any nominal current may be selected for the fuse.

b) If the short-circuit current at the point of installation of the circuit breaker is greater than its nominal breaking capacity, the nominal currents of the upstream fuses must not exceed the values specified in the table (back-up protection of the circuit breaker).

Upstream: Fuse NH..gL/gG

L.	I_{cu} [kA]	NH gL/gG									
		I_n [A]	25	40	63	80	100	125	160	200	
S400M/S450M FS401M/FS451M FS403M/ FS453M	I_{cn} [kA] 10	all types	100	100	100	100	80	50	30	20	
S400E/S450E FS401E/FS451E FS403E/FS453E	I_{cn} [kA] 6	all types	100	100	70	40	25	15	10	-	

E. = Upstream

L. = Downstream

Selectivity limits are specified in kA

S800S – S400M (SMISSLINE) @ 230/400V

L.	Char.	I_{cu} [kA]	S800S								
			B, C, D, K								
S400M FS401M FS403M	B, D	10	I_n [A]	25	32	40	50	63	80	100	125
			4*...16	50	50	50	50	50	50	50	50
			20	50	50	50	50	50	50	50	50
			25	50	50	50	50	50	50	50	50
			32	50	50	50	50	50	50	50	50
			40	50	50	50	50	50	50	50	50
			50	50	50	50	50	50	50	50	50
			63	50	50	50	50	50	50	50	50

S. S800S

L.	Char.	I_{cu} [kA]	S800S								
			B, C, D, K								
S400M	C, K	15	I_n [A]	25	32	40	50	63	80	100	125
			50	0.5...2	50	50	50	50	50	50	50
			25	3...20	50	50	50	50	50	50	50
			25		50	50	50	50	50	50	50
			32		50	50	50	50	50	50	50
			40		50	50	50	50	50	50	50
			50		50	50	50	50	50	50	50
			63		50	50	50	50	50	50	50

S800N – S400M (SMISSLINE) @ 230/400V

L.	Char.	I_{cu} [kA]	S800N								
			B, C, D								
S400M FS401M FS403M	B, D	10	I_n [A]	25	32	40	50	63	80	100	125
			4*...16	36	36	36	36	36	36	36	36
			20	36	36	36	36	36	36	36	36
			25		36	36	36	36	36	36	36
			32		36	36	36	36	36	36	36
			40		36	36	36	36	36	36	36
			50		36	36	36	36	36	36	36
			63		36	36	36	36	36	36	36

S. S800 N

L.	Char.	I_{cu} [kA]	S800 N								
			B, C, D								
S400M	C, K	15	I_n [A]	25	32	40	50	63	80	100	125
			50	0.5...2	36	36	36	36	36	36	36
			25	3...20	36	36	36	36	36	36	36
			25		36	36	36	36	36	36	36
			32		36	36	36	36	36	36	36
			40		36	36	36	36	36	36	36
			50		36	36	36	36	36	36	36
			63		36	36	36	36	36	36	36

E. = Upstream

L. = Downstream

Selectivity limits are specified in kA

Consulting the back-up table

This table provides the value (in kA) for which the back-up protection is ensured between a given combination of circuit breakers. The table covers possible combinations between the S800 or SACE series Tmax and between SMISSLINE miniature circuit breakers 400M.

SMISSLINE TP technical details

Miniature circuit breaker


Back-up protection with Tmax and XT

Sace Tmax – S400 @ 230/400V

		Up-Stream	T1	T1	T1	T2	T3	T4	T2	T3	T4	T2	T4	T2	T4	T4
	Version	Version	B	C	N	N	N	N	S	S	S	H	H	L	V	
Downstream	I _n [A]	I _{cu} [kA]	16	25	36	36	36	36	50	50	50	70	70	85	120	200
S400E	6...10	6	16	25	30	36	36	36	40	40	40	30	40	40	40	40
FS401E/403E	B, C 13...63						16	16	36	16	16	16	16	16	16	16
S400M	0.5...10	10	16	25	30	36	36	36	40	40	40	50	40	50	40	40
FS401M/403M	C, K 13...63						25	36	40	25	40	50	40	50	40	40
S400M	6...10	10	16	25	30	36	36	36	40	40	40	50	40	50	40	40
FS401M/403M	B, D 13...63						25	36	40	25	40	50	40	50	40	40

Sace XT – S400 @ 230/400V

		Up-Stream	XT1	XT2	XT3	XT4	XT1	XT2	XT3	XT4	XT1	XT2	XT4	XT2	XT4	XT2	XT4
	Version	Version	B	C	N				S			H		L		V	
Downstream	I _n [A]	I _{cu} [kA]	18	25		36			50			70		120		150	
FS400E	6...10	6	18	25	30	36	36	36	40			40	30	40	40	30	
S400E	B, C 13...63					16	36	30	36	16	40	30	40	40	30	40	
S450E																	
FS400M	0.5...10	10	18	25	30	36	36	36	40			40	30	50	40	30	
S400M	C, K 13...63					25	36	30	50	25	40	30	50	50	30	50	
S450M																	
FS400M	6...10	10	18	25	30	36	36	36	40			40	30	50	40	30	
S400M	B, D 13...63					25	36	30	50	25	40	30	50	50	30	50	
S450M																	



Example 1: With a S800 nominal current 50A is a Back-up protection till a nominal current of 25A to a S400 given. The Back-up protection ist till 36kA.

Example 2: There is no Back-up protection between supply side and the load side given.

Back-up protection

The tables given provide the value (in kA, referring to the breaking capacity) for which the back-up protection among the combination of selected circuit breakers is verified. The tables cover the possible combinations between S800 and those between the above mentioned circuit breakers and the ABB series of modular circuit breakers S400.

The values indicated in the tables refer to the voltage:
– Vn of 230/400VAC

SMISSLINE TP technical details

Miniature circuit breaker

Influence of ambient temperature

Allowable current of miniature circuit breakers depending on ambient temperature and max. load current for row mounted miniature circuit breakers.

Practical procedure

Conditions often arise which allow for simple consideration of the ambient temperature and thermal influences of row mounted circuit breakers according to EN 60898 and EN 60947-2. The following procedure has proven to be effective:

1. Selection of circuit breaker according to the rated current of the equipment or the current carrying capacity of the cable depending on which of these is the lower value.
2. Consideration of thermal factors
 - for an ambient temperature of 40°C: $I_B \leq 0,9 \times I_n$
 - for thermal influence of row mounted circuit breakers subject to the same loads: $I_B \leq 0,75 \times I_n$
3. This results in the rated current of the circuit breaker to be selected for $I_n \leq 1,5$ times the relevant current according to point 1.

This procedure considers all thermal influence factors and results in an optimum choice of the rated current for the circuit breaker.

Example: Current carrying capacity required of the cable: 4 A. Selected rated current of circuit breaker taking thermal influence into consideration: $I_n \geq 1,5 \times 4 \text{ A} \geq 6 \text{ A}$.

Basis for the simplified procedure

1. Different ambient temperature


The thermal releases are set to a reference ambient temperature. For trip characteristic K, this is 40°C, for trip characteristics B, C and D, this is 30°C. At different ambient temperatures, the specified current values change by around 6% per 10°C difference in temperature.

For more accurate calculations and very high or very low ambient temperatures, the following tables apply:

2. Influence of row mounted devices at continuous load

If the circuit breakers are lined up close to one another and have equally high load levels, a correction factor must be taken. This influence can be reduced if fillers and/or spacers (9 mm wide) are used.

Influence of adjacent devices S400



Influence of adjacent devices

Correction factor Fm

No. of adjacent devices	correction factor
1	1
2	0.95
3	0.9
4	0.86
5	0.82
6	0.8
7	0.78
8	0.77
9	0.76
>9	0.76

SMISSLINE TP technical details

Miniature circuit breaker

Influence of ambient temperature

Max. operating currents depending on ambient temperature for S400 miniature circuit breakers of tip characteristics B, C, D, UC-C and UC-Z

I _n (A)	Ambient temperature T (°C)										
	0	10	15	20	25	30	35	40	45	50	55
0.5*	0.58	0.55	0.53	0.52	0.51	0.50	0.48	0.47	0.46	0.44	0.43
1.0*	1.15	1.09	1.07	1.04	1.02	1.0	0.97	0.94	0.91	0.89	0.86
1.6*	1.85	1.75	1.71	1.67	1.63	1.6	1.55	1.50	1.46	1.42	1.38
2.0*	2.31	2.19	2.13	2.08	2.03	2.0	1.93	1.88	1.83	1.77	1.72
3.0*	3.5	3.32	3.24	3.16	3.09	3.0	2.93	2.85	2.77	2.69	2.61
4.0*	4.6	4.37	4.27	4.17	4.07	4.0	3.86	3.76	3.66	3.56	3.45
6.0	6.9	6.59	6.44	6.29	6.14	6.0	5.83	5.68	5.53	5.37	5.22
8.0	9.2	8.84	8.63	8.42	8.22	8.0	7.81	7.6	7.39	7.19	6.98
10.0	11.5	10.9	10.7	10.4	10.2	10.0	9.65	9.39	9.14	8.88	8.63
13.0	15.0	14.4	14.0	13.7	13.3	13.0	12.7	12.3	12.0	11.6	11.3
16.0	18.5	17.6	17.2	16.8	16.4	16.0	15.6	15.2	14.7	14.3	13.9
20.0	23.1	22.1	21.6	21.0	20.5	20.0	19.5	19.0	18.5	18.0	17.5
25.0	28.9	27.5	26.9	26.3	25.6	25.0	24.3	23.7	23.0	22.4	21.8
32.0	37.0	35.3	34.5	33.7	32.8	32.0	31.2	30.4	29.5	28.7	27.9
40.0	46.2	44.1	43.0	42.0	41.0	40.0	39.0	37.9	36.9	35.9	34.9
50.0	57.7	55	53.7	52.4	51.1	50.0	48.6	47.3	46.0	44.7	43.4
63.0	72.7	69.3	67.7	66.1	64.5	63.0	61.3	59.7	58.1	56.4	54.8

* only applies to C

Max. operating currents depending on ambient temperature for S400 miniature circuit breakers of trip characteristic K

I _n (A)	Ambient temperature T (°C)										
	10	15	20	25	30	35	40	45	50	55	
0.5	0.54	0.52	0.51	0.50	0.49	0.47	0.5	0.45	0.43	0.42	
1.0	1.14	1.12	1.09	1.07	1.0	1.02	1.0	0.96	0.94	0.91	
1.6	1.85	1.81	1.77	1.73	1.7	1.65	1.6	1.56	1.52	1.48	
2.0	2.29	2.23	2.18	2.13	2.1	2.03	2.0	1.93	1.87	1.82	
3.0	3.48	3.40	3.32	3.25	3.2	3.09	3.0	2.93	2.85	2.77	
4.0	4.58	4.48	4.38	4.28	4.2	4.07	4.0	3.87	3.77	3.66	
6.0	6.91	6.76	6.61	6.46	6.3	6.15	6.0	5.85	5.69	5.54	
8.0	9.24	9.03	8.82	8.62	8.4	8.21	8.0	7.79	7.59	7.38	
10.0	11.5	11.2	11.0	10.7	10.5	10.2	10.0	9.69	9.43	9.18	
13.0	15.1	14.7	14.4	14.0	13.7	13.4	13.0	12.7	12.3	12.0	
16.0	18.4	18.0	17.6	17.2	16.8	16.4	16.0	15.6	15.2	14.8	
20.0	23.0	22.5	22.0	21.5	20.9	20.4	20.0	19.4	18.9	18.4	
25.0	28.9	28.3	27.6	27.0	26.3	25.7	25.0	24.4	23.8	23.1	
32.0	36.9	36.1	35.3	34.4	33.6	32.8	32.0	31.1	30.3	29.5	
40.0	46.2	45.1	44.1	43.1	42.1	41.1	40.0	39.0	38.0	37.0	
50.0	57.7	56.4	55.1	53.8	52.5	51.3	50.0	48.7	47.4	46.1	
63.0	72.5	70.9	69.3	67.7	66.1	64.5	63.0	61.3	59.6	58.0	

SMISSLINE TP technical details

Miniature circuit breaker

Protection of circuits with fluorescent lamps

Protection of circuits with fluorescent lamps

The following table gives the maximum permissible number of fluorescent lamps which can be protected by a single-pole circuit breaker of characteristic. The figure for multi-pole circuit breakers is reduced by 20%.

Rated current ballast	FL not compensated			FL compensated in parallel			FL with electronic		
	KVG 19/20 W	36/40 W	59/65 W	KVG 19/20 W	36/40 W	59/65 W	EVG ¹⁾ 19/20 W	36/40 W	59/65 W
13	35	30	19	41	41	27	21	21	10
16	43	37	24	51	51	33	26	26	12
20	53	46	30	64	64	41	33	33	15
25	66	58	37	82	82	53	42	42	19


¹⁾ EVG: Two-lamp version, lamps switched together, electronic ballast

KVG: Conventional ballast


Use of miniature circuit breakers S400 M for DC systems

A standard miniature circuit breaker type S400 M and S400 E can be used in a DC system by observing the following conditions: Single pole miniature circuit breaker max. 60VDC. 2-pole miniature circuit breaker with 2-poles in series max. 125VDC. The polarity needs not to be taken into account. Load connection can either be at the top or at the bottom of the MCB.

Example of permissible DC voltages depending on the number of poles and the circuit configuration in earthed DC systems:



Examples for different voltages between a conductor and earth where voltages between conductors are identical:



SMISSLINE TP technical details

Miniature circuit breaker
S400UC

UC = Universal Current = AC/DC

S400UC MCBs can be used in the one-pole version as 250V d.c., and in the 2-pole version with series connection of two poles up to 440V d.c..

For DC incoming supply from above

S400 UC... MCBs have, in the area of arc chutes, permanent magnets, it is therefore necessary to take into account the polarity during the installation process.

Doing so ensures that in the case of a short circuit the magnetic field of the permanent magnets corresponds with the electromagnetic field of the short-circuit current, therefore safely leading the short circuit into the arc chute. Incorrect polarities may cause damage to the MCB.


This is why – in the case of top-fed devices – terminal 1 must be connected to (-) and terminal 3 (+).

Example for permissible voltages between the conductors depending on the number of poles and circuit layout:

voltage U_N between conductors	250 V d.c.	440 V d.c.	440 V d.c.	440 V d.c.
--	------------	------------	------------	------------

voltage U_N between conductor and earth	250 V d.c.	250 V d.c.	440 V d.c.	250 V d.c.
--	------------	------------	------------	------------

supply



SMISSLINE TP technical details

Residual current operated circuit breaker F402, F404

Properties



General information about residual current operated circuit breakers

The residual current operated circuit breaker prevents personal injury and damage to property caused by electric current. Use of this circuit breaker is required in various national and international standards for electrical installations.

Modern residual current operated circuit breakers respond to small residual currents.

Interruption occurs in a fraction of a second even before a hazardous situation for people, animals and property can arise.

The principle of magnetic tripping independent of the supply voltage ensures perfect and safe operation even in the event of undervoltage and neutral interruptions.

The key features

- High short-circuit resistance 10 kA
- Sensitive for alternating and pulsating DC residual currents
- 2- and 4-pole types
- Nominal residual trip currents 10, 30, 100, 300 and 500 mA
- Snap-on auxiliary switches and signal contacts
- Nominal currents 25, 40, 63 A
- Double terminals

According to the wave form of the earth leakage currents they are sensitive to, the RCDs may be classed as:

- AC type (for alternating current only) AC are not in the Smissline portfolio
- A type (for alternating and/or pulsating current with DC components)
- B type (for alternating and/or pulsating current with DC components and continuous fault current).

Shape of the fault current	Correct RDC function alternating current Type AC	pulsating current sensitiv Type A
sinusoidal a.c. 	rampant 	slowly rising
pulsating d.c. 	rampant with or without overlapping DC components from 6 mA 	slowly rising

Selectivity

RCDs raise similar issue to those surrounding the installation of MCBs, and in particular the need to reduce to a minimum the parts of the system out of order in the event of a fault.

For RCBOs the problem of selectivity in the case of short-circuit currents may be handled with the same specific criteria as for MCBs.


However, for correct residual current protection, the more important aspects are linked to tripping times. Protection against contact voltages is only effective if the maximum times indicated on the safety curve are not exceeded.

SMISSLINE TP technical details


Residual current operated circuit breaker F402, F404

Properties

Partial selectivity



Total selectivity



Amperometric (partial) selectivity

Selectivity may be created by placing low-sensitivity RCDs upstream and higher-sensitivity RCDs downstream.

An essential condition which must be satisfied in order to achieve selective co-ordination is that the $I_{\Delta 1}$ value of the breaker upstream (main breaker) is more than double the $I_{\Delta 2}$ value of the breaker downstream. The operative rule to obtain an amperometric (partial) selectivity is $I_{\Delta n}$ of the upstream breaker = $3 \times I_{\Delta n}$ of the downstream breaker (e.g.: F404, 300 mA upstream; F402, 100 mA downstream).

In this case, selectivity is partial and only the downstream breaker trips for earth fault currents $I_{\Delta 2} < I_{\Delta m} < 0.5 \times I_{\Delta 1}$.

Chronometric (total) selectivity

To achieve total selectivity, delayed or selective RCDs must be installed.

The tripping times of the two devices connected in series must be co-ordinated so that the total interruption time t_2 of the downstream breaker is less than the upstream breaker's no-response limit time t_1 , for any current value. In this way, the downstream breaker completes its opening before the upstream one.

To completely guarantee total selectivity, the I_{Δ} value of the upstream device must also be more than double that of the downstream device in accordance with IEC 64-9/563.3, comments. The operative rule to obtain an amperometric (partial) selectivity is $I_{\Delta n}$ of the upstream breaker = $3 \times I_{\Delta n}$ of the downstream breaker (e.g.: F404, S type, 300 mA upstream). For safety reasons, the delayed tripping times of the upstream breaker must always be below the safety curve.

SMISSLINE TP technical details

Residual current operated circuit breaker F402, F404

Standard, short-time delayed and selective type

The use of multiple electronic reactors for the supply of fluorescent lamps instead generates permanent leakage currents and inrush currents that can provoke nuisance tripping of a standard residual current breaker.

IT system loads and other electronic equipment (e.g. dimmers, computers, inverters) with capacitive input filters connected between the phases and ground can also generate permanent earth leakage currents whose sum may provoke the nuisance tripping of a standard residual current breaker.

For these situations, the SHORT-TIME DELAY breakers allow a greater number of devices to be connected to the installation.

Soft-starters for motors are loads which can generate high-frequency capacitive currents (provoked by the harmonics) toward ground or fed into the network. Also in this case, the use of SHORT-TIME DELAY residual breakers reduces the sensibility to nuisance tripping.

Compared with standard type breakers, SHORT-TIME DELAY residual current breakers are therefore characterised, for any given sensibility, by:

- Higher residual trip current
- Tripping time delay
- Better resistance to overvoltages, harmonics and impulse disturbances.

Regulations

The tests set out in the IEC 61008 and IEC 61009 standards verify the resistance of residual current breakers to unwanted tripping provoked by operation overvoltages, using a ring wave impulse shape of $0.5\mu s/100\text{ kHz}$. All residual current circuit-breakers are required to pass this test with a peak current value of 200A.


For what concerns atmospheric overvoltages, the IEC 61008 and 61009 standards prescribe the $9/20\mu s$ surge test with a 3000A peak current, but limit the requirement to residual current devices classified as selective; no test is required for other types.

The ABB range of SHORT-TIME DELAY anti-nuisance tripping breakers and blocks pass the general $0.5\mu s/100\text{ kHz}$ ring wave test and also withstand the $9/20\mu s$ impulse test with the same peak current of 3000A prescribed for selective devices.

The F402 K and F404 K should therefore be used to prevent unwanted tripping.

Three different types of Residual current operated circuit breaker

- standard RCD 30 mA
- selective RCD 300 mA [S]
- short-time delay RCD 30 mA [K]



- The standard RCD 30 mA tripp after circa 22mA and a release time of $\leq 35\text{ ms}$.
- The selectiv RCD 300 mA tripp after circa 200mA and a release time of circa 180ms.
- The short-time delay RCD 30 mA tripp after circa 25mA and a release time of 100 ... 120 ms.

SMISSLINE TP technical details

Residual current operated circuit breaker F402, F404

Standard, short-time delayed and selective type

Unwanted tripping

In the event of disturbance in the mains, the RCDs normally present in the system are tripped, breaking the circuit even in the absence of a true earth fault.

Disturbances of this kind are most often caused by:

- operation overvoltages caused by inserting or removing loads (opening or closing protection of control devices, starting and stopping motors, switching fluorescent lighting systems on and off, etc.)
- overvoltages of atmospheric origin, caused by direct or indirect discharges on the electrical line.

Under these circumstances, breaker tripping is unwanted, since it does not satisfy the need to avoid the risks due to direct and indirect contacts. On the contrary, the sudden and unjustified interruption of the power supply may result in very serious problems.

SHORT-TIME DELAY RCDs

The ABB range of SHORT-TIME DELAY anti-disturbance residual current circuitbreakers and blocks was designed to overcome the problem of unwanted tripping due to overvoltages of atmospheric or operation origin.

The electronic circuit in these devices can distinguish between temporary leakage caused by disturbances on the mains and permanent leakage due to actual faults, only breaking the circuit in the latter case.

SHORT-TIME DELAY residual current circuit-breakers and blocks have a slight delay into the tripping time, but this does not compromise the safety limits set by the Standards in force (release time at $2 I_{\Delta n} = 150 \text{ ms}$).

Guaranteeing conventional residual current protection, their installation in the electrical circuit therefore allows any unwanted tripping to be avoided in domestic and industrial systems in which service continuity is essential.

This delay makes the SHORT-TIME DELAY residual current devices especially suited for installations involving motor starters/variable speed drives, fluorescent lamps or IT/electronic equipment.

Table of RDC selectivity

Downstream $I_{\Delta n}$ [mA]	Upstream $I_{\Delta n}$ [mA]	10	30	100	300	300	500	500
		inst	inst	inst	inst	S	inst	S
10			■	■	■	■	■	■
30	inst		■	■	■	■	■	■
100	inst			■	■			■
300	inst							
300	S							
500	inst							

inst = instantaneous S = selective ■ = amperometric (partial) selectivity ■ = chronometric (total) selectivity

SMISSLINE TP technical details

Residual current operated circuit breaker F402, F404

Technical data

	F402	F404
Rated voltage U_n :	230 V	230/400 V
Number of poles:	2	4
Rated frequency f_n :	50/60 Hz	50/60 Hz (for Type LF 16 ² / ₃ Hz)
Rated breaking capacity I_m :		1000 A
Total trip time (average value)		
- at $I_{\Delta n}$	$\leq 300 \text{ ms}$	$\leq 300 \text{ ms}$
- at $5 I_{\Delta n}$	$\leq 40 \text{ ms}$	$\leq 40 \text{ ms}$
Delay time at $5 I_{\Delta n}$:	-	-
Resistance to short circuits (kA):	in conjunction with an upstream fuse gL / gG 100 A or a high performance MCB S800, 100 A	10 kA 10 kA in conjunction with an upstream fuse gL / gG 100 A or a high performance MCB S800, 100 A
Connection	Double lift terminal touch finger-proof, suitable for connecting load side terminal	single-, multi- and fine-wire conductors of up to 25 mm ²
Degree of protection:	IP20 inside panel IP40	IP20 inside panel IP40
Endurance:	> 5000 operating cycles	> 5000 operating cycles
Resistance to climate acc. to:	EN 61008	EN 61008
Rated insulation voltage U_i	500 V	500 V
Rated impulse withstand voltage U_{imp}	4 kV	4 kV
Mounting position:	any	any
Ambient temperature:	-25°C ... +40°C	-25°C ... +55°C acc. to EN 61009
Vibration resistance:	5g 5 ... 150 ... 5 Hz	5g 5 ... 150 ... 5 Hz
Plastic parts: Contacts:	halogen-free cadmium-free	halogen-free cadmium-free

	F402...K	F404...K	F404...S
Rated voltage U_n :	230 V	230/400 V	230/400 V
Number of poles:	2	4	4
Rated frequency f_n :	45 ... 60 Hz	45 ... 60 Hz	45 ... 60 Hz
Resistance to surge current:	3 kA 9/20 μs	3 kA 9/20 μs	5 kA 9/20 μs
Total trip time (average value)	240 ms	120 ... 300 ms	150 ... 500 ms 40 ... 150 ms
- at $I_{\Delta n}$	$\leq 40 \text{ ms}$		
- at $5 I_{\Delta n}$			
Delay time at $5 I_{\Delta n}$:	10 ms	10 ms	90 ms
Resistance to short circuits (kA):	10 kA in conjunction with an upstream fuse gL / gG 100 A or a high performance MCB S800 100 A	10 kA	10 kA
Connection	Double lift terminal touch finger-proof, suitable for connecting load side terminal single-, multi- and fine-wire conductors of up to 25 mm ²		
Degree of protection:	IP20 in panel IP40	IP20 in panel IP40	IP20 in panel IP40
Endurance:	> 5000 operating cycles	> 5000 operating cycles	> 5000 operating cycles
Resistance to climate acc. to:	EN 61008	EN 61008	EN 61008
Mounting position:	any	any	any
Ambient temperature:	-25°C ... +40°C	-25°C ... +55°C	-25°C ... +40°C
Vibration resistance:	5g 5 ... 150 ... 5 Hz	5g 5 ... 150 ... 5 Hz	5g 5 ... 150 ... 5 Hz
Plastic parts: Contacts:	halogen-free cadmium-free	halogen-free cadmium-free	halogen-free cadmium-free

SMISSLINE TP technical details

Residual current operated circuit breaker F402, F404

Technical data

Coordination tables between Short Circuit Protection Devices (SCPD) and F404 RCCBs

If you are using an RCCB you must verify that the Short Circuit Protection Device (SCPD) protects it from the effects of high current that arise under short-circuit conditions. The IEC/EN 61008 provides some tests to verify the behaviour of RCCB in short-circuit conditions. The tables below provide the maximum withstanding short-circuit current expressed in eff. kA for which the RCCBs are protected thanks to the coordination with the SCPD with a rated current (thermal protection) less than or equal to the rated current of the associated RCCB.

	F404 25 A	F404 40 A	F404 63 A
gG fuse 25 A	100		
gG fuse 40 A	60	60	
gG fuse 63 A	20	20	20
gG fuse 100 A	10	10	10
S403M	10	10	10
S803N	20	20	20
S803S	25	25	25

Internal resistances and power losses of RCCBs and RCBOs

Internal resistances and power losses per pole (cold resistance at room temperature)

4-pole RCCB F404

2-pole RCCB F402

in A	R _i mΩ	P _v W	Type	R _i mΩ	P _v W
25	2.1	1.3	25 A/10 mA	8.8	5.5
40	2.0	3.2	25 A/30 mA	6.1	3.8
63	1.1	4.4	40 A/30 mA	5.8	9.3

SMISSLINE TP technical details

Residual current operated circuit breaker FS401



Residual current operated circuit breakers with overcurrent protection (RCBO)

The SMISSLINE residual current operated circuit breakers with overcurrent protection (RCBO) are ideal for protecting people and property in all new and existing distribution systems. The combination of standby current and cable protection in one single device greatly simplifies planning and offers cost benefits. Using a RCBO can e.g. satisfy the minimum level of protection required by regulations in an apartment or in a particular distribution system. Should a residual current arise, only the circuit directly affected is switched off while all other circuits remain in operation.

The short time-delayed residual current operated circuit breaker with overcurrent protection FS401 K is a version particularly suited to unfavourable distribution and load situations. Without limiting the personal protection function in any way, the electronic short time delay prevents nuisance tripping which may arise as a result of capacitive discharge currents.

	FS401	FS401K
Rated voltage U_n :	230 V~	230 V~
Upstream fuses and	For backup and selectivity, the details for the miniature circuit breakers S400 E	
Selectivity limits:	and S400 M Page 2/19 to 2/36	
Number of poles:	2-pole (1PN)	2-pole (1PN)
Rated frequency f_n :	50/60 Hz	50/60 Hz
Rated breaking capacity I_{cn} :	10 kA – 230 V~ (10–16 A nominal current) 6 kA – 230 V~ (20–32 A nominal current)	10 kA – 230 V~ (10–16 A nominal current) 6 kA – 230 V~ (20 A nominal current)
Current limitation class:	3	3
Total cut-off time (average value) acc. to		EN 61009-1 EN 61009-1
– at I_n	40 ms	240 ms
– at 5 $I_{\Delta n}$	25 ms	35 ms
Delay time at 5 $I_{\Delta n}$:	–	10 ms
Rated insulation voltage U_i	500 V	500 V
Rated impulse withstand voltage U_{imp}	4 kV	4 kV
Connection cross-sections	Opposing action stroke clamp on cylinder, touch finger-proof. Suitable for connecting Terminal at load end	single, multi- and fine-wire conductors of up to 25 mm ²
Degree of protection:	IP20 inside panel IP40	IP20 inside panel IP40
Endurance:	> 5000 operating cycles	> 5000 operating cycles
Resistance to climate, acc. to:	EN 61009	EN 61009
Mounting position:	any	any
Ambient temperature:	-25°C ... +40°C	-25°C ... +40°C
Vibration resistance:	5 g 5 ... 150 ... 5 Hz	5 g 5 ... 150 ... 5 Hz
Plastic parts:	halogen-free cadmium-free	halogen-free Contacts: cadmium-free

Please notice:

For the influence of the ambient temperature and the thermal influences of row mounted RCBO's it is necessary to calculate with the same correction factors like with MCB's.

SMISSLINE TP technical details

Residual current operated circuit breaker FS401
Internal resistances and power losses, Derating

Max. operating currents depending on ambient temperature for RCBO of tip characteristics B and C.

B,C	Ambient temperature T (°C)								Influence of adjacent devices	
	In (A)	-25	-20	-10	0	10	20	30	40	No. of adjacent devices
In (A)	-25	-20	-10	0	10	20	30	40	1	1
2	2.6	2.5	2.4	2.3	2.2	2.1	2	1.9	2	0.95
4	4.9	4.8	4.6	4.5	4.3	4.2	4	3.8	3	0.9
6	7.95	7.8	7.4	7.1	6.7	6.4	6	5.6	4	0.86
8	10.3	10.1	9.7	9.3	8.8	8.4	8	7.6	5	0.82
10	11.8	11.6	11.3	11	10.7	10.3	10	9.7	6	0.8
13	15.65	15.4	14.9	14.4	14	13.5	13	12.5	7	0.78
16	18.65	18.4	17.9	17.4	17	16.5	16	15.5	8	0.77
20	23.1	22.8	22.2	21.7	21.1	20.6	20	19.4	9	0.76
25	30.8	30.3	29.2	28.2	27.1	26.1	25	23.9	10	0.76
32	39.3	38.6	37.3	36	34.7	33.3	32	30.7		
40	50.7	49.7	47.8	45.8	43.9	41.9	40	38.1		

Internal resistances and power losses

Internal resistances and power losses per pole (cold resistance at room temperature)

Type	FS401 B		FS401 C	
	R _i mΩ	P _V [W]	Type	R _i mΩ
FS401M-B6	53.8	1.9	S401M-C6	50.3
FS401M-B10	20.5	2.1	FS401M-C10	18.2
FS401M-B13	14.7	2.5	FS401M-C13	12.7
FS401M-B16	10.7	2.7	FS401M-C16	10.4
FS401M-B20	7.4	3.0	FS401M-C20	7.7
FS401M-B25	6.3	4.0	FS401M-C25	7.6
FS401M-B32	5.5	5.7	FS401M-C32	5.5

SMISSLINE TP technical details

Residual current operated breaker RCBO FS403



4-pole RCBO from the ABB SMISSLINE protective devices range

The combination of circuit protection and a residual current protection in one device as 4-pole RCBO simplifies both – planning and installation. It enables you to provide perfect protection in one device. This protection consists of:

- Short circuit protection
- Overload protection
- Residual current protection
- Preventive fire protection

High rated short-circuit breaking capacity of 10 kA, conforming to EN 61009-1

The I_{cn} 10 kA short-circuit breaking capacity of the RCBO complies with standard EN 61009-1. This standard specifies testing and usage of RCBO's for household and similar uses. The devices can also be used by non-professionals.

Features and benefits of the new devices:

- Overall width of 72mm (4 modules)
- Rated sensitivity 30 mA
- Current rating 10 A to 32 A
- B and C tripping characteristics
- Easy Drive double deck terminals on the output side for connecting two conductors in one chamber. The two chambers can accommodate conductors with different cross sections.

	FS403
Rated voltage U_n :	240/415 V
Number of poles:	3PN
Rated frequency f_n :	50/60 Hz
Rated breaking capacity I_{cn} :	10 kA bzw. 6 kA
Current limitation class:	3
Total cut-off time (average time) acc. to IEC/EN 61009-1	EN61009
– at $I_{Δn}$	40 ms
– at $5I_{Δn}$	25 ms
Stated Cross-section of conductors (top/bottom)	Upper terminal part 0,75–35 mm ² Lower terminal part 0,75–10 mm ²
Tightening torque:	2.8 Nm
Degree of protection:	IP20
Endurance:	> 5000
Resistance to climate:	according to EN61009
Ambient temperature:	–25 °C ... +40 °C
Vibration resistance:	EN 61009-1
Plastic parts:	halogen free, according
contacts:	IEC 61-249-2-21 cadmium free
Approvals and standards:	EN/IEC 61009-1, SEV

Accessory:

Auxiliary- and signal contacts are to attach on to the left of the device through the customer.

SMISSLINE TP technical details

Residual current operated circuit breaker FS403

Internal resistances and power losses, Derating

Internal resistances and power losses

Internal resistances and power losses per pole (cold resistance at room temperature)

FS403

Typ	R _i mΩ	P _v W
6A B, C	50	3
10A B, C	17.6	2.69
13A B, C	11.9	2.96
16A B, C	9.8	3.52
20A B, C	7.3	3.94
25A B, C	4.8	5.19
32A B, C	3.6	6.38

Performances at different ambient temperatures

Max. operating current depending on the ambient temperature of a circuit-breaker in load circuit of characteristics type B, C

Influence of adjacent devices Correction factor Fm

B,C	Ambient temperature T (°C)								No. Of adjacent devices	correction factor
In (A)	-25	-20	-10	0	10	20	30	40	1	
6	7.95	7.8	7.4	7.1	6.7	6.4	6	5.6	4	0.86
10	11.8	11.6	11.3	11	10.7	10.3	10	9.7	6	0.8
13	15.65	15.4	14.9	14.4	14	13.5	13	12.5	7	0.78
16	18.65	18.4	17.9	17.4	17	16.5	16	15.5	8	0.77
20	23.1	22.8	22.2	21.7	21.1	20.6	20	19.4	9	0.76
25	30.8	30.3	29.2	28.2	27.1	26.1	25	23.9	10	0.76
32	39.3	38.6	37.3	36	34.7	33.3	32	30.7		

SMISSLINE TP technical details



RCBO FS401, FS403

Limitation of specific let-through energy I^2t , peak current I_p

I^2t diagrams - Specific let-through energy value I^2t

The I^2t curves give the values of the specific let-through energy expressed in A^2s (A =amps; s =seconds) in relation to the prospective short-circuit current (I_{rms}) in kA.


FS400M characteristics B-C



Limitation curves – Peak current values

The I_p curves give the values of the peak current, expressed in kA, in relation to the prospective symmetrical short-circuit current (kA).

FS400M Characteristics B-C



SMISSLINE TP technical details

Switch disconnector



General switch disconnector

When used in a smissline socket system, the switch disconnector can be used instead of the incoming terminal block for up to 63A. With the smissline IS404 switch disconnector, individual loads, groups of loads or entire system parts can be separated or connected to the input supply.

The key features of the switch disconnector

- Input supply switch
- On-Off function
- Clear indication of switching position
- Snap-on auxiliary switch available
- Uniform smissline design

Technical data for switch disconnector IS404

Rated voltage U_n :	230/400 V~
Rated current I_n :	63 A
Rated frequency f_n :	50 Hz
Number of poles:	4
Rated impulse withstand voltage:	6 kV
Connection cross-sections C_u :	At top, touch finger-proof. Suitable for connecting up single-, multi- and fine-wire conductors of up to 25 mm ²
Degree of protection:	IP40
Endurance, mechanical/electrical:	5000 operating cycles
Mounting position:	any
Ambient temperature:	-25 °C ... +40 °C
Specifications:	EN/IEC 60947-3
Approvals:	SEV
Weight (approx.):	250 g
Switching duty:	AC-22A
Plastic parts:	halogen-free
Contacts:	cadmium-free

SMISSLINE TP technical details

Surge arrester OVR




Description of product

The 'OVR' surge protector is a 4-pole type II surge arrester meeting the requirements of IEC 61643-11.

The OVR is used to protect low voltage distribution systems and devices from overvoltages (DIN VDE 100) caused by remote lightning strikes or switching operations.

Typical sites of use are main and sub-distribution for low voltage systems where the arrester is plugged in directly on to the SMISSLINE busbar system.



Display and maintenance

The protective elements (high-performance varistors) are monitored thermally. In the event of a defect, this monitor automatically disconnects the overloaded high-performance varistors from the power supply and the operating indication changes from green to red. This status is also indicated by the signalling contact. In such cases, the arrester should be replaced immediately because the downstream devices are no longer protected against overvoltages.

If the operating indication is neither green nor red, you should check whether the connections are correct. You must also check whether there is any supply voltage.

If the device is connected correctly, the operating display (LED) lights up green.

The surge arrester requires no maintenance. A regular visual check is recommended.

Warning: When taking insulation resistance measurements on the electrical system, the arrester should be disconnected from the power supply since otherwise the measurement may be affected by the arrester characteristics. The enclosed sticker with the corresponding note should be placed in a clear position on the distribution board.

Assembly

Site of installation and electrical connection

The 'OVR' surge arrester installed at the input supply of the system to be protected.

The OVR404 is plugged in directly on to the SMISSLINE busbar system.

Earth conductor rating

The OVR should be linked to ground potential using the shortest route possible.

The earth conductor supplied with the device can be used for this purpose. The connection must be as short as possible. The minimum cross-section is 6 mm².

Running cables

Protected and unprotected cables (also including the earth conductor) must not be routed directly parallel to one another. They should be separated such that surge interference from unprotected to protected cables cannot occur. Cables should cross one another at right angles.

SMISSLINE TP technical details




Surge arrester OVR

Coordination between surge arrester

In order to ensure a full and complete protection it is necessary to have coordination between different surge arrester types.




Configuration 1

$15 \text{ kA} \leq I_p \leq 50 \text{ kA}$



Configuration 2

$7 \text{ kA} \leq I_p \leq 15 \text{ kA}$




SMISSLINE TP technical details

Surge arrester OVR

Rated voltage U_n :	230/400 V AC
Max. Continuous voltage U_c :	275 V AC
Number of poles:	4 (TN-S system)
Power consumption at U_n :	1.2 W per device
Requirement class according to IEC 61643-1:	Type 2
Rated leakage surge current I_n (9/20 µs):	15 kA
Max. leakage surge current I_{smax} (9/20 µs):	30 kA
Protection level U_p at I_{sn} : U_p at $I_s = 5\text{ kV}$:	$\leq 1.5\text{ kV}$ $\leq 1\text{ kV}$
Max. leakage surge current I_{sg} (9/20 µs):	100 kA 4-pole
Response time t_a :	$\leq 25\text{ ms}$
Connection cross-sections PE / L1/L2/L3/N:	Opposing action stroke clamp on cylinder, touch finger-proof. Suitable for connecting up single-, multi- and fine-wire conductors up to 25 mm ²
Max. Back-up fuse:	160 A gL/gG / 25 kA
Short-circuit withstandability with max. Back-up fuse:	25 kA
Signal contact max. operating voltage: max. load current: 1 changeover contact:	250 V AC 2 A 11/12 normally closed contact, 11/14 normally open contact
Temperature range:	-25 ... +60 °C
Degree of protection:	IP 20
Plastic parts: Contacts:	halogen-free cadmium-free

Surge protection TN-S system



SMISSLINE TP technical details

Auxiliary switches and signal contacts



General

The auxiliary switches and signal contacts are snapped on to the left of the protective devices. On the miniature circuit breakers an optional mounting on the right is also possible. For auxiliary switches and signal contacts supplied via SMISSLINE auxiliary busbars LA or LB a version with integrated contacting pieces is available Conventional supply via the terminals of the auxiliary devices is possible.

Function

The auxiliary switch works in the same way as the main contacts. The signal contact only operates when the protective device trips.

This can be simulated with the white test button. Each time the signal contact is tripped, it must be reset to its starting position using the orange-coloured reset button.

Auxiliary switch and signal contacts have special contacts which ensure high switching reliability even in systems with low voltages or low currents (PLC, signal systems etc.).

Auxiliary switch contacts operate at the same time as the contacts of the protective device (activated manually or automatically).

Normally open contact | 13
NO (normally open) | 14 joint operation with protective device

Normally open contact | 21
NC (normally close) | 22 opposing operation with protective device



Signal contacts only operate when the protective device is tripped electrically as a result of a short-circuit, a fault current or overcurrent (undervoltage for MS325).

Normally open contact | 97
NO (normally open) | 98 closes during automatic trip

Normally closed contact | 05
NC (normally close) | 06 opens during automatic trip




Technical data for auxiliary switch and signal contact


	Signal contact SK400	Auxiliary switch HK400
Rated voltage U_n :	400 V	400 V
Rated impulse withstand voltage:	4 kV	4 kV
Rated current:		
– I_{th} :	6 A	6 A
– AC15	2 A/230 V / 1 A/400 V	2 A/230 V / 1 A/400 V
– DC13	0.55 A/125 V=	0.55 A/125 V=
– DC15	0.27 A/250 V=	0.27 A/250 V=
Minimum current/voltage:	10 mA 12 V=	10 mA 12 V= (to ensure reliable electrical operation)
Connection cross-sections:	2x1.5 mm ² strand with sleeve	2x1.5 mm ² strand with sleeve
Plastic parts:	Free of halogen und cadmium	Free of halogen und cadmium
Internal resistance R_i :	0.0065 Ω	0.0065 Ω
Power loss at rated current P_v :	0.24 W	0.24 W
Ambient temperature:	$T_{max.} +55^{\circ}\text{C}$ $T_{min.} -25^{\circ}\text{C}$	$T_{max.} +55^{\circ}\text{C}$ $T_{min.} -25^{\circ}\text{C}$
Tightening torque:	1 Nm	1 Nm

SMISSLINE TP technical details


Accessory mounting



Contact description signal contact



Contact description auxiliary switch




① If you use an auxiliary switch and a signal contact you must connect first the signal contact on the MS325

SMISSLINE TP technical details


Auxiliary switches and signal contacts

1. Wiring without auxiliary busbars LA, LB

Wiring of auxiliary switch and signal contact blocks without contact to the auxiliary busbars LA and LB.




2. Input contacts the auxiliary busbars LA, LB. Standard output wiring.




3. Collective alarm, signal contact contacts the auxiliary busbars LA, LB


A cost-effective collective alarm solution can be implemented without additional wiring by using this arrangement.



Contact description signal contact



Contact description auxillary contact



SMISSLINE TP technical details


Auxiliary switches and signal contacts

Contact arrangements to auxiliary busbars



Left/right mounting of auxiliary switch/signal contact for miniature circuit breaker Space-saving on the socket system

By mounting the auxiliary switches/signal contacts alternately on the left and right, the installation width on the SMISSLINE socket system can be reduced. A dummy housing is therefore not needed when just using auxiliary switches or signal contacts.



S400 miniature circuit breakers with auxiliary switches mounted on left and right:


25% space saving



S400 miniature circuit breakers with NT40163 9 mm on the right and S400 with auxiliary switch on the left:
20% space saving



Supply options for auxiliary busbars LA and LB



Supply option for auxiliary busbars using incoming terminal block.




Supply option for auxiliary busbars using incoming terminal block.


Positioning of contacting piece ZLS632 on auxiliary switch and signal contact

The small auxiliary switch/signal contact contacting piece can be simply and quickly changed from the position of the LA to the LB auxiliary busbar by reversing it by 180 degree.

HK/SK 1NO, 1NC



Signal or auxiliary contact Collective alarm



Electrical installation solutions for buildings – Technical details

Light switches and socket outlets


Index

carat®	11/2
Busch-dynasty®	11/3
pure stainless steel	11/4
solo®	11/5
Busch-axcent® / Busch-axcent® flat	11/6
future® linear	11/7
Sky Niessen	11/8
Zenit	11/40
Mylos	11/82
Chiara	11/114
Unno	11/160
Millenium	11/166
Concept bs	11/169
Kalo	11/172



Technical details

carat®



Frame dimensions




Rocker switch 1gang




Socket outlet 1gang




Cover frame 1gang




Cover frame 2gang



Cover frame 3gang




Cover frame 4gang





Cover frame 5gang

Technical details



Busch-dynasty®




Rocker switch 1gang




Socket outlet 1gang




Cover frame 1gang




Cover frame 2gang



Cover frame 3gang



Cover frame 4gang




Cover frame 5gang

Technical details

pure stainless steel


Frame dimensions





Technical details

solo®



Frame dimensions




Rocker switch 1gang




Socket outlet 1gang




Cover frame 1gang




Cover frame 2gang



Cover frame 3gang



Cover frame 4gang




Cover frame 5gang


Technical details

Busch-axcent® / Busch-axcent® flat

Frame dimensions




Rocker switch 1gang




axcent




flat




Socket outlet 1gang



axcent



flat



Cover frame 1gang

Cover frame 2gang

Cover frame 3gang


Cover frame 4gang

Cover frame 5gang

Technical details

future® linear

Frame dimensions




Technical details


Sky Niessen

Luxury insert


Switch with night guide light




Switches with night guide light




Switch 16A with night guide light




With night guide light




Two-pole switch 16 A with night guide light




Two-pole switch 16 A with control pilot




Two-pole switch with control pilot




Two-pole switch with night guide light




Switch with control pilot



Switches with control pilot



Button with night guide light



* The • indicates where the night guide lamp must be connected.


* The "pil" indicates where the control pilot lamp must be connected.

Technical details


Sky Niessen

Luxury insert


Button with control pilot functioning as night guide light




**Button with control pilot
Motor with time-delayed relay**




Double switch




Double button




Combination of button and switch




Two-pole card switch 10 A



Two-pole card switch 16 A



Card switch



Technical details

Sky Niessen

Luxury insert

Time-delayed connection card switch. 8114.5

Technical characteristics:

- Power supply: 127 V~ / 60 Hz
230 V~ / 50 Hz

Valid for the following types of loads:

- (a) Conventional incandescent lamps, halogen incandescent lamps at 230 V~ or 127 V~, low voltage halogen lamps with conventional transformer or electronic transformer and motors:
At 230 V~, 50 Hz, maximum power 3,000 W
At 127 V~, 60 Hz, maximum power 1,600 W
- (b) Fluorescent lamps:
At 230 V~, 50 Hz, maximum power 1,300 W
At 127 V~, 60 Hz, maximum power 700 W


Operation

This appliance detects whether a card is present in the card slot.


- (a) Whenever it detects the presence of a card, it connects the load. It will maintain the load connected for the time the card remains present.
- (b) When, after having inserted a card, this is removed, the device will delay the cut-out of the load, according to the programmed time.

Assembly

- 1.- Secure the mechanism (1) in the recessed box with the screws of the box.
- 2.- Fit the frame (2) onto the mechanism.
- 3.- Secure the support (3) with the screws to the mechanism.
- 4.- Position the cover (4) onto the support.




Connection diagram:



Programming the load disconnection times when the card is removed.

It is possible to select the disconnection times after the card is removed, through the rotating potentiometer for programming on the cover.



Step	Waiting time for disconnection
1.-	5 s.
2.-	10 s.
3.-	20 s.
4.-	30 s.
5.-	60 s.
6.-	90 s.

Switch-switch (code: 8153) / Push-button (8153.2) Two-position key

Diagram as switch/button 8153 / 8153.2





Diagram as switch




Position of the key	Active contacts
1	Common and 1
2	Common and 2

Technical details

Sky Niessen

Luxury insert

Button for blinds



8144 & 8144.1


Switch for blinds

8130.3

230 V~ / 50 Hz; ±10%
Nominal power: 2 x 700 W/VA


- Allows two operating modes:
- (BLINDS): Switch for blinds.
- (SLATS): Switch for Venetian blinds with slats.
- Time to raise/lower switchable blinds (30-300 s).
- (C): Centre of an installation of a blind switch.
- Range of ambient temperature: from 0 to +35°C.
- To adapt to the Wireless system, use the buttons with the connector.
Ref.: 8432.X (Fig. 2)
- For manual operation exclusively, use the buttons Ref.: 8430, 8230, 5530. (Fig.2)

Fig. 1



8130.3 with auxiliary buttons for blinds 8144.
Centralization of blinds for buttons 8430, 8230,
5530.

Fig. 2



Technical details

Sky Niessen

USB charger

8185

1.- Technical data:

Nom. input voltage: 100 - 240 V AC ± 10 %

Nom. input frequency: 50 - 60 Hz

Nom. input current:

8185 and N2285: 0,20Aca at max load

N2185: 0,12Aca at max load

Stand-by current: 230 V AC : <= 0,3 W

Nom. output voltage: 5 V DC +5 / -5 %

Output current:

8185 and N2285: 1500 mA at 5 V DC

N2185: 750 mA at 5 V DC

Operating temp.:

8185 and N2285: 0 °C + 35 °C

N2185: 0 °C + 45 °C

Energy efficiency:

8185 and N2285: >= 71%

N2185: >= 66%

2.- Electric safety data


Safety standard: EN60950-1

Safety standard: II - Low voltage

Separation (prim. sec.):

Converter with galvanic insulation

5.- Connection diagrams





3.- Mean charge times for devices with lithium ion polymer compound batteries (for 8185 or N2285):

- 80% of the charge <1 h 15

- 100% of the charge <2 h 05

4.- Example of application: 8185



USB charger 2A

8185.2 & 8185.3

1.- Technical data:

Nom. input voltage: 100 - 230 V AC ± 10 %

Nom. input frequency: 50 - 60 Hz

Nom. input current: <0,2A AC at max load

Stand-by current: <10 MW at 230 V AC, no load

Nom. output voltage: 5 V DC +5 / -5 %

Output current per outlet: 2000mA at 5V DC

Operating temp.:

0 °C to 45 °C, installing one USB charger N2185.2 or 8185.2.

0 °C to 30 °C, installing one charger 8185.3 or two N2185.2 together.

Energy efficiency: >= 79%

2.- Electrical connection diagram:

Fig. 1. Diagram 8185.2






Fig. 2. Diagram 8185.3




3.- Installation:

3.2.- Installation of USB charger with one outlet 8185.2



3.3.- Fig. 5. -Installation of USB charger with two outlets 8185.3




Technical details

Sky Niessen

TV / R outlets

Technical data

- Connection: Screw terminal and clamp. Coaxial cable 75 ohm.
- Shielded zamak and metal plate chassis.
- In conformity with EN 50083-1:1993, EN 50083-2:2001, EN 61000-6-1:2001, EN 61000-4-2:1995 ESD 15kV AD, 8kV CD, EN50083-4:1998
- Fits in a Ø60 mm box.




Important: the connection of the TV outlets in serial distribution must be carried out according to the figure on the left. The cable coming from the previous outlet is connected in the right terminal and the cable going to the next outlet in the left terminal.


Code	8150	8150.3	8150.7	8150.8
Installation		Final	Intermediate	
Connection			Screw terminal and clamp	
Output connectors	C1 C2		IEC male Ø 9.52 mm IEC female Ø 9.52 mm	
Frequency range	MHz	I/O C1 C2	5 - 862 5 - 862 87.5 - 108	13 - 862 13 - 862 13 - 862
Basic loss	dB ±TOL	FM DAB VHF	10,0 ±0,7 10,0 ±1,5 4,0 ±1,5	5 - 862 1,1 ±0,3 TV: 0,9 ±0,3
Through loss	dB ±TOL	UHF	3,0 ±0,5	25,0 ±1,5 8,0 ±0,7 8,0 ±0,7
Directivity	dB	FM TV	-	30,0 ±0,2 >12 >9
Isolation	dB	FM TV	>14 >14	>18 >16 >15
Return loss	dB	FM TV	>18 >10	>12 >18 >18

Note: reference 8150.3 compatible with CATV

MATV connection diagram Serial distribution up to 9 floors




MATV connection diagram Distribution with tap-off units



In this diagram all final outlets are the same.
References 8150 or 8150.3 can be used equally.

MATV connection diagram Serial distribution for more than 9 floors




Example: 10 floors. The floors are divided in 2 groups of 5 floors each. The outlets are distributed according to the criteria shown in the MATV connection diagram for serial distribution up to 9 floors. The diagram above can be used in buildings up to 18 floors. For buildings with more than 18 floors and up to 27 floors, 3 groups have to be created and so on.

Technical details

Sky Niessen

TV-R / SAT outlets


SMATV connection diagram




Note:

End of line impedance. If the distribution equipment requires outlets with end of line resistors, 8151.7/N2251.7 outlets must be used or add to 8151.3/N2251.3 outlets a termination resistor to close the line.

a) SMATV star connection diagram



b) SMATV star connection diagram



Note:


It is recommended to avoid installing more than 2 intermediate outlets per line.

Code	8151.3 N2251.3	8151.7 N2251.7	8151.8 N2251.8	8152.7
Installation		Final	Intermediate	Final
Connection		Screw terminal and clamp		
Output connectors	C1 C2 C3		IEC male Ø 9,52 mm IEC female Ø 9,52 mm	
Frequency range	MHz	E/S C1 C2 C3	5 - 2400 5 - 862 930 - 2400 -	5 - 2500 5 - 68 / 125 - 862 87,5 - 108 950 - 2500
Basic loss	dB ±TOL	FM TV SAT	0,2 ±0,1 1,0 ±0,5 1,2 ±0,6	3,7 ±0,3 4,0 ±0,5 5,0 ±1,2
Through loss	dB ±0,5	FM TV SAT	- -	2,5 ±0,5 2,5 ±0,7 3,0 ±1,0
Directivity	dB	FM TV SAT	-	>20,0 >12,0 >5,0
Isolation	dB	FM TV SAT	>45 >14 >14	>45 >30 >28
Selectivity	dB	FM TV-R SAT	- >15 >15	- >15 >15
Return loss	dB	VR FM TV SAT	>25 >25 >14 >10	>13 >13 >12 >9
DC path	V... mA Tono		24 max 500 max 22 KHz/DiSEqC	24 max 500 max 22 KHz/DiSEqC

Technical details

Sky Niessen

Telephone outlets



Connections for special services:

Special services are understood to be those which need the installation of a subscriber other than the normal one, either in terms of number of wires or connections in the telephone outlet, or in both cases at the same time.

These services may be:

Reversed Call (between a main telephone and another extension), Shared Line (two subscribers per terminal), Blocked Dialing by Fee Indicator, Supplementary bell (with and without capacitor), Call transfers, Connection for Fax., Connection for Modem, etc.

Connections:

The connection of each of the appliances to the telephone outlet (either to the PRC or private outlet) must be specified by the manufacturer of the appliance in question. However, Electro-mechanical supplementary bell are connected according to the following diagrams.

The references Niessen 8117.3, 2117.8 XX, 2117.8 XX, 2217.8 XX, 2217.8 XX, 2017.3 (terminal access bases, TAB) are supplied with an 8-contact connector that complies with the Standard ISO 8877, without terminating resistor.

Primary ISDN access: Used as elements, cable (in point-to-point configuration), the network termination equipment at primary speed (TR1p, component supplied and owned by the ISDN service provider). If using shielded cables, the connection to the termination equipment shall be fixed with a terminal block with connection to the shield of each pair. Both shield connections can be joined. Optionally an 8-contact connector can be used.

Technical details

Sky Niessen

Female RJ45 Connector Device


2018.6 & AM33322-AN

1.- Preparing the Cable

- 1.1.- Put the cable into the hole of cap.
 - 1.2.- Cut approximately 5 cm. off the jacket
 - 1.3.- Open approx. 10 cm of the jacket with a cutter cord or another tool.
 - 1.4.- Cut the jacket
 - 1.5.- Cut the mesh (if it has one) and the cord at the same level of the jacket.
-

2.- Preparing the Conductors

- 2.1.- Select the adequate wiring scheme (568A or 568B) and place the pairs in a straight line.
- 2.2.- Position each of the four pairs in the holes of the end piece.
- 2.3.- Set the cover to the module.




3.- Technical specifications

- Wiring sticker: T568A &T568B
- W/insertion force: 20N max. (IEC 60603-7-4)
- Retention strength: 7.7kg.
- Operating temperature: -10C° — 60C°
- In compliance with ANA/TIA/EIS 568 B-2 standard


RJ45 Cat. 5E female connector

2018.5


- 1.- Remove the back cap from the connector. Strip approx. 5cm off the jacket and discard the cable cutter cord.




- 2.- Remove the back cap from the connector. Strip approx. 5cm off the jacket and discard the cable cutter cord.




2a.- Wiring according to T568A:



2b.- Wiring according to T568B:



- 3.- Push the cables against the end of the slot and cut them flush to the connector. Use an IBDN 110, BIX, KRONE wiring tool, or a similar type 110 tool.




- 4.- Mount the connector cap.




Technical details

Sky Niessen


VDI connectors




8155.2
Pin Out:
1G — W/GND Left Audio
1B — White 3G — R/GND Right Audio
3R — red



8155.3
Pin Out:
1G — Y/GND Composite Video
1A — Yellow 2G — W/GND Left Audio
2B — White 3G — R/GND Right Audio
3R — Red




8155.4
Pin Out:
R — Red Left Audio
G — Ground Right Audio
L — White




8155.5
PIN PIN
1 — 1 R+ 5 — GND 5
6 — 6 R- 10 — SGND 10
2 — 2 G+ 11 — ID0 11
7 — 7 G- 12 — ID1 12
3 — 3 B+ 13 — HSYC 13
8 — 8 B- 14 — VSYC 14
4 — 4 ID2 15 — ID2 15
G — GND G — GND


G-1	1	TMDS Data2+
	2	TMDS Data2 Shield
	3	TMDS Data2-
G-2	4	TMDS Data1+
	5	TMDS Data1 Shield
	6	TMDS Data1-
G-3	7	TMDS Data0+
	8	TMDS Data0 Shield
	9	TMDS Data0-
G-4	10	TMDS Clock+
	11	TMDS Clock Shield
	12	TMDS Clock-
	13	CEC
	14	RESERVED (N.C. on device)
	15	SCL
	16	SDA
	17	DDC/CEC Ground
	18	+5V Power
	19	Hot Plug Detect
	GND	Ground



On Group included 3 wires



8155.8
Pin Out:
1 — VBUS
2 — D-
3 — D+
4 — Ground
G — Shielded



Note:

Using a strap for fixing the cable to the board it is recommended to avoid disconnections. For this the plates have two through-holes at its rear end.

Technical details

Sky Niessen

Rotatory dimmer

Reference	Types of lamps	Power	Switchable
	incandescent halogen transformer-electromechanical halogen transformer-electronic fluorescent lamp LED		
2260.2	😊	😊	😊
8160*	😊	😊	😊
8160.2	😊	😊	😊
8160.3	😊	😊	😊
8160.5	😊	😊	😊
8160.7	😊	😊	😊
8160.9	😊	😊	😊
8160.8	😊	😊	😊
8161.8	Auxiliary component, does not bear load. Up to 5 units connected.		😊 Regulated with ref. 8161.8

* Valid for small motors of 300 VA

Rotatory dimmer, RL, 20-500 W

8160



230 V~ / 50 Hz.

😊 20-500W

☰ 20-500VA

Motors up to 300 VA

- Mechanism valid for cover and button Ref: 5560, 8260.2, 8460.2 and 8560.2
- Protection against short circuit: T3, 15H
- Protection against overload: electronic
- Range of ambient temperature: from 0 to +35°C
- Triac regulator





* If you wish to fit a night guide light use the 8102.5

Note:

The nominal power depends on the ambient temperature. In addition, when calculating the nominal power note the transformer losses (20%).

Rotatory dimmer, LED, 2-100 W

8160.2



- Mechanism valid for cover and button Ref: 5560, 8260.2, 8460.2 and 8560.2

- Protection against overload: Electronic

- Range of ambient temperature: from 0 to +35°C

Note:

The nominal power depends on the ambient temperature. In addition, when calculating the nominal power note the transformer losses (20%).

	(1)	(2)	(3)
LEDi 230 V~	2 W / VA, 100 W / VA	A	20
LC	2 W / VA, 100 W / VA	A	20
LC	10 W / VA, 250 W / VA	A	-
LEDi 230 V~	2 W / VA, 100 W / VA	B	-
LC	2 W / VA, 100 W / VA	B	-
LC	10 W / VA, 250 W / VA	B	-
LEDi 230 V~	10 W, 250 W	B	-
LC	10 W, 250 W	B	-

A

B

Technical details

Sky Niessen

Rotatory dimmer, RL, 200-700 W

(Incan. + halog. electromagnetic transformer). 8160.3


230 V~ / 50 Hz.

200-1000W

200-1000VA

- Mechanism valid for cover and button Ref: 5560, 8260.2, 8460.2 and 8560.2
- Calibrated fuse T-6.3H Time-delayed
- Protection against short circuit: T 6.3 H
- Range of ambient temperature: 0 - +35°C


Fig. 1



Note:

The nominal power depends on the ambient temperature. In addition, when calculating the nominal power note the transformer losses (20%).

Fig. 2



* If you wish to fit a night guide light use the 8102.5

Rotatory dimmer, RL, 60-400 W

8160.5

230 V~ / 50 Hz.


60-400 W

60-400 VA

- 6A complementary circuit switch.
- Mechanism valid for cover and button of ref. 5560, 8260.2, 8460.2 and 8560.2
- Nominal current - switch: 6 A
- Stray current protection: EN 55014

- Minimum load: 60 VA
- Protection against short circuit: T3, 15H
- Maximum protection against short circuit: 10 A
- Range of ambient temperature: from 0 to +35°C


Fig. 1



Note:

The nominal power depends on the ambient temperature. In addition, when calculating the nominal power note the transformer losses (20%).

Fig. 2



Rotatory dimmer, RC, 40-420 W

8160.7

230 V~ / 50 Hz.


40-420 W

40-420 VA

- Mechanism valid for cover and button of ref. 5560, 8260.2, 8460.2 and 8560.2
- Types of loads: incandescent and/or halogen lamps at 230V and/or halogen with electronic transformer.

- Protection against short circuit: electronic
- Protection against overload: electronic
- Range of ambient temperature: 0 - +35°C


Fig. 1



Note:

The nominal power depends on the ambient temperature. In addition, when calculating the nominal power note the transformer losses.

Fig. 2



* If you wish to fit a night guide light use the 8102.5

Technical details

Sky Niessen

Rotatory dimmer, RLC, 60-420 W & Rotatory dimmer remote control

8160.8 & 8161.8

230 V~ / 50 Hz

60-420 W

60-420 VA

60-420 VA

- Mechanism valid for cover and button Ref: 5560,

8260.2, 8460.2 and 8560.2

- The principal mechanism (8160.8) may be connected to up to 5 auxiliary elements (8161.8) which also regulate the load.

- Range of ambient temperature: 0 to +35°C


- Maximum number of auxiliary elements with an 8160.8: 5 units

- Maximum length of cable 100 m.

- Range of ambient temperature: 0 to +35°C

- Mechanism valid for cover and button Ref: 5560, 8260.2, 8460.2

* The connection N is only necessary if a night guide light is used in the regulator.



Note:

The nominal power depends on the ambient temperature.

In addition, when calculating the nominal power note the losses of the conventional (20%) and electronic (5%) transformers.

Rotatory dimmer, 1-10Vdc

8160.9

230 V~ / 50 Hz.

700 VA

- Mechanism valid for cover and button of ref. 5560, 8260.2, 8460.2 and 8560.2


- Valid for fluorescent lights with dimmable electronic ballast.

- Power: 700 VA

- Control voltage: 0/1 - 10 V DC

- Ballast control max. current: 50 mA DC.

- The night guide light must not be installed with this regulator.



Technical details

Sky Niessen

Rotatory dimmer remote control

8130

230 V~ / 50 Hz; ±10%



60-450 W

60-450 VA

60-450 VA

- Two-wire connection.
- Enables two operating modes selected with the front potentiometer: Regulator and Switch Modes.

- Range of ambient temperature: from 0 to +35°C.
- For manual operation exclusively, use the buttons Ref.: 8530, 8430, 8230 and 5530. (Fig. 2).



* If you wish to fit a night guide light, use the 8104.5

Note:

The nominal power depends on the ambient temperature. In addition, when calculating the nominal power note the losses of the conventional (20%) and electronic (5%) transformer.

Universal push dimmer 40-450W

8160.1

Mains voltage: 127 V~ / 60 Hz

220 V~ / 50 Hz

Power: - at 220 V~ / 50 Hz: 40 - 450 W
40 - 400 VA

Its special characteristics enable convenient remote control using conventional buttons, deriving one conductor only, and thus simplifying the electrical installations as the traditional switched installations can be replaced.

Short press:

If the regulator was switched off, with a short press the maximum lighting is always connected. If the regulator is switched on, with a short press it is disconnected. A short press is understood to be between 50 ms and 400 ms.

Long press:

If the regulator was switched off, with a long press, it is connected from minimum lighting and continues the regulation until the button is released. If the regulator was switched off, with a long press, the regulation process starts from the point it was at and until the button is released. A long press is understood to be greater than 400 ms.


Protection against overcurrents: With calibrated fuse Code T-2A. It is supplied with a spare.

Protection against erroneous connections: With electronic device. From min. to max. 3.8 seconds.

Night guide display: With red LED. Operating temperature: 0 °C to 30 °C.

Suppression of interference according to Standards: UNE-20507 and UNE-21806, EN 55014 and EN 60555.

* If you want a night guide light, use the 8104.5



Rotatory DALI dimmer & Rotatory DALI dimmer with power supply

8161.4 & 8161.5

8161.5

Nominal voltage (through the DALI external power supply)	9,5 – 22,5 V --
Power consumption (depending on the color of the guide light)	7 – 15 mA
Connection for electronic protection	
Maximum number of DALI service units that can be connected (depending on the external power supply)	64
Service temperature	0 °C – +35 °C
Protection class	IP20
Maximum cable length in the system	300 m
Number of colors of the guide light	18 + disconnected

8161.4

Nominal voltage	230 V~ ±10 % ; 50/60 Hz
Power consumption	7 – 15 mA
Gap voltage. Output voltage	15,5 V --
Maximum usable current	75 mA
Connection for electronic protection	
Maximum number of DALI service units that can be connected	37
Service temperature	0 °C – +35 °C
Protection class	IP20
Maximum cable length in the system	300 m
Number of colors of the guide light	18 + disconnected

Technical details

Sky Niessen

Rotatory DALI dimmer & Rotatory DALI dimmer with power supply

8161.4 & 8161.5

Operation

1- Attenuation speed:




Fig. 1:





Fig. 2:

Slow rotation of the control element:
– Precision setting with up to 254 levels of luminosity.

Quick rotation of the control element:
– Large changes in luminosity to reach the desired setting rapidly.


2- Adjusting the basic luminosity:



To set the basic luminosity, turn the control element slowly.

1. Switch on the lighting.
2. Adjust the lighting.
3. Press the control element for 10 seconds.
– Once the configuration has been carried out, the load will blink once.

3- Deleting the basic luminosity:




To delete the basic luminosity, turn the control element slowly.

1. Turn off the lighting.
Press the control element for 10 seconds.
– Once the configuration has been carried out, the load will blink once.

4- Switching on with the memory function:

The DALI potentiometers always switch on the lighting with the last value of luminosity set (memory function). This function overwrites the manual setting of the luminosity connection.

5- Modifying the connection luminosity:



To adjust an established luminosity connection the following points must be executed:


1. Switch on the lighting.
2. Adjust the lighting.
3. Double click quickly on the control element.
– Once the configuration has been carried out, the load will blink twice.

The memory function overwrites the luminosity connection established (connection with the last luminosity value it had before the disconnection).

Note:

If the lighting is disconnected after pressing twice is because the interval between the first and second time the button was pressed too long.

6- Deleting the connection luminosity:



To delete an established luminosity connection the following points must be executed:

1. Switch on the lighting.
2. Double click quickly on the control element.
– Once the configuration has been carried out, the load will blink twice.
The memory function works again after deleting the luminosity connection established (connection with the last luminosity value it had before the disconnection).

7- Adjusting the colour of the guide light:




Fig. 7:

To change the color of the connection light, do the following:

1. Turn off the lighting (load).
2. Press the control element, hold it down and rotate it quickly three times from one side to the other.
3. Release the control element.
– The guide light blinks 3 times.
4. Turn the control element to choose the color of the LED.
5. Confirm the color selected by pressing the control element briefly.
– Once the configuration has been carried out, the guide light will blink 3 times.

8- Changing the Power On level (optional setting)



Fig. 8:

The modification of the Power On level (luminosity connection after a grid failure) achieves a standard luminosity or disconnects all the service equipment connected with the luminosity value it had before the power cut.

To modify the Power On level, do the following:

1. Turn off the lighting (load).
2. Press the control element, hold it down and rotate it quickly three times from one side to the other.
3. Release the control element.
– The guide light blinks 3 times.
4. Press the control element for 10 seconds.
– After the configuration has been carried out, the lighting (load) will blink once and the guide light will blink 3 times.

The DALI service units will now be connected now with the return of the grid voltage with the last luminosity value set.

9- Operation in various control stations

The DALI service units can be operated from various control stations. The luminosity is always taken from the last potentiometer used. This is valid for the rest of the configuration, such as the basic luminosity and the memory function.

The color of the guide light has to be selected individually for each DALI potentiometer in an installation.


Technical details

Sky Niessen


Rotary DALI dimmer & Rotatory DALI dimmer with power supply

8161.4 & 8161.5

Electric connection



No.	Function
1	DALI power supply
2	DALI service unit
3	8161.4



No.	Function
1	DALI service unit
2	8161.5

Note:

- If the potentiometer DALI 8161.4 is used in installations with a DALI power supply, terminals L and N cannot be occupied. The device is supplied directly with current from the bus.
- Up to 3 DALI 8161.4 and 5 DALI 8161.5 potentiometers can be operated in parallel. For this purpose, observe the power consumption permitted.
- When the DALI service units e.g., EVG are connected, observe the indications of the corresponding manufacturer.
- The DALI control line and the power supply line can be found in a shared NYM cable.
- Multi-phase service is permitted.

Technical details

Sky Niessen

Universal single relay time delayed switch

8130.1


230 V~ / 50 Hz; ±10%

💡 2300 W
⚡ 2300 VA
☒ 2300 VA
⎓ 2300 VA

- Enables two operating modes selected with the front potentiometer:


- Switch Mode and Time-delayed Mode (30-300 s).
- For all types of loads.
- Range of ambient temperature: from 0 to +35°C.
- For manual operation exclusively, use the buttons Ref.: 8530, 8430, 8230 and 5530. (Fig. 2).

Fig. 1



8130.1 with auxiliary button 8104.5

Fig. 2



* If you want to fit a night guide light, use the 8104.5.

Universal double relay time delayed switch

8130.2


230 V~ / 50 Hz; ±10%

💡 2 x 700 W
⚡ 2 x 700 VA
☒ 2 x 700 VA
⎓ 2 x 700 VA
Ⓜ 2 x 700 VA

- Enables two operating modes selected with the front potentiometer: Double switch mode and time-delayed disconnection


- mode of load 2, after the disconnection of load 1 (30-300 s).
- For all types of loads.
- Range of ambient temperature: from 0 to +35°C.
- For manual operation exclusively, use the buttons Ref.: 8530, 8430, 8230 and 5530. (Fig. 2) for time-delayed mode only.

Fig. 1




8130.2 with auxiliary buttons (8144.2, 8104.5) and two lamps.

Fig. 2



8130.2 with an auxiliary button (8104.5), a lamp and a motor. To control combinations of light and fans in bathrooms.

Fig. 3



* If you want to fit a night guide light, use the 8104.5

Technical details

Sky Niessen

Time delayed switch with relay

8162

- Power supply: 230 V~ / 50 Hz

- Maximum power:


1.000 W

1.000 VA for $\cos \phi = 0,6$

650 VA

The time-delayed switch is an electronic mechanism that automatically disconnects the component controlled, within an adjustable time interval. It is activated manually by pressing the button directly.

Activation by remote control is with conventional auxiliary buttons.



* If you want to fit a night guide light, use the 8104.5.

- Protection against overcurrents:

With calibrated fuse Code T5A.

It is supplied with a spare.

- Protection against erroneous connections:

With electronic device.

- Regulation time: From 10 s to 10 min.

- Night guide display: With red LED.

- Operating temperature: 0° to 40 °C.

- Suppression of interference according to Standards: UNE-20507 and UNE-21806, EN 55014 and EN 60555.

Time delayed switch with triac

8162.1

Technical data:

Power supply: 230V~ ±10% / 50Hz

Maximum power:

40-500W for

40-400VA for

40-100VA for

Protection against overcurrents: With calibrated fuse F-3, 15H.

It is supplied with a spare.

Protection against erroneous connections: with electronic device.

Regulation time: From 10 s to 10 min. (±10%).

Night guide display: With red LED.

Operating temperature: 0 to 40 °C.

Manufactured in accordance with the standards:

UNE-EN-60669-1 • UNE-EN-60669-2-1 • UNE-EN-60669-2-3

Operation:

The time-delayed switch is an electronic mechanism that automatically disconnects the component controlled, within an adjustable time interval. It is activated by pressing the button directly.

The desired margin of time for the disconnection of the device is regulated using the adjusting screw, indicated in Figure 1. The margin of time that can be set ranges between 10 seconds and 10 minutes (±10%).




fig.1




fig.2

Technical details

Sky Niessen

MOS-Fet switch for motion sensor

Switch 8141.3

Switch 8141.3

Nominal voltage: 230 V~ 50 Hz.

Minimum nominal power: 60 W/VA

Maximum nominal power: 420 W/VA

Permitted load: incandescent lamps, halogen lamps at 230 V and halogen lamps with conventional and electronic transformers. Protected against overloads and short circuit.

Operating temperature: From 0°C to 35°C.


Protection against short circuits with fuse Code M-4 A.

Note:

Do not use the mechanism 8141.3 with contactors; in these cases use the 8141.4.

An auxiliary button (8104) can be connected, if you wish to operate the load manually.


Switch 8141.3



Note: To use the 8141.3 in parallel, make sure the minimum load is increased by: no. of devices x 60 W

In these applications, the light sources must be outside the detection area to prevent the disconnection due to a Sensor Switch being interpreted as a thermal variation by the other Sensor Switch, causing an unwanted connection.

* If you want to fit a night guide light, use the 8104.5.



Relay switch for motion sensor


Switch 8141.4

Nominal voltage: 230 V~ / 50 Hz.

Maximum power: 700 W / VA



$3 \text{ A cos } \varphi = 0,5$

Permitted load:




All types of loads.

Operating temperature: From 0°C to 35°C



Area of detection



In these applications, the light sources must be outside the detection area to prevent the disconnection due to a Sensor Switch being interpreted as a thermal variation by the other Sensor Switch, causing an unwanted connection.


Technical details

Sky Niessen

Relay switch

8161

230 V~ / 50 Hz
For all types of loads
Power 2300 W/VA



Can be combined with the IR button, with the programmer 8165.3 and with the presence sensor 9511.


Relay switch for blinds

8161.2


Power 700W/VA
I nominal - 3A cos φ 0.5
Power consumption ≤ 1W
Max I per aux. input ≤ 3 mA




View of the whole unit



Individual control



Centralized control



The IR button 8439.XX and the programmer 8165.3 can control a group of blind motors by operating the auxiliary inputs ("1" and "2") of the blind control device. Using a two-pole switch for blinds, the group of blinds can be moved manually or the sensor can be activated for periods of absence.

The recessed device 8161.2 is used to control:

- Blinds with mobile slats.
- Rolling blinds.
- Awnings.
- Closures with motorised domes or vaults, etc.

In this instruction manual the term "blind" or "blinds" as synonyms of the applications mentioned in the above paragraph.

Mechanism that can be combined with the programmer 8165.3

Service modes

Normal service (N) = factory setting

Example of use: "normal" activation of the blind.

One short press activates the order of actuation that activates the blind to its final position (up or down). A long press (holding it down) activates a regulation command. The output will remain permanently connected throughout the setting using the control element/extension.

If the regulation lasts more than three minutes, the recessed application will be disconnected.

Regulation of slats (L)

Example of use: "normal" activation of the blind and regulation of slats in small stages. The short press is identical to that of normal service. The output is regulated in steps during adjustment using the control element/extension. After the eighth step or 2 seconds the adjustment ends.

Installation with auxiliary buttons

Device 8161 can be operated with auxiliary buttons. In these cases, the following aspects have to be taken into account:

- To avoid switching faults, the power supply lines of the motor and the auxiliary elements must not be in the same cable or next to each other (the minimum distance must be 5 cm).

The following auxiliary elements can be used:

- Conventional mechanical buttons with or without potential-free terminals.

* Attention:

If you want to fit a night guide light, use the 8104.5

To ensure proper operation, **separate the switching lines from the auxiliary activation lines (in different conduits)**.

"Central" (Z)

Example of use: a recessed control blind application is used as a central unit for other blinds. Each press (short or long) of this central unit is interpreted and converted into a 3-minute activation command. This ensures that all the subordinate blinds reach the final position.

Programming (P)

Example of use:

in the event of a command to lower, the blind must automatically be lowered and the slats regulated.

Technical details

Sky Niessen

Timer control element + Cover plate for timer control element

8165.31 + 8565.3

Loads that are usually automated/programmed:

- Porch lights
- Garden lights
- Lights in corridors in schools, universities, shops, etc.
- Blinds in a house
- Shop awnings
- Alarm activation
- Heating or air conditioning
- A small wake-up alarm (next to the bell)

For all these applications there are two construction types for the function:

- 8161+8165.31+8565.3: To function as a relay switch.
- 8161.2+8165.31+8565.3:

To function as a relay switch for blinds, awnings, etc. Enables slats to be regulated, all the blinds to be centralized from one point and awnings to be operated.

See diagrams of relay switches.

Service modes

The control element has three service modes that you can select freely.

- “**MANUAL**” (symbol)= The automatic connection intervals, and the luminosity and twilight functions (with the blinds) are not executed.

Exclusive control with the buttons or .

RAISE blind

Short press:

- The blind moves toward the final upper position.
- When pressed again, the blind stops.

Long press:

- The blind is raised while the button is being pressed.

LOWER blind

Short press:

- The blind moves toward the final lower position.

- When pressed again, the blind stops.

Long press:

- The blind is lowered while the button is being pressed.

- “**AUTOMATIC**” (symbol)= Automatic control according to the selected program: Astro, day-week, connection times.

Manual control with the buttons or is also possible.

- “**HOLIDAYS**” (symbol)= control as in automatic service. A random number generator moves the connection intervals up to 30 minutes each day to simulate the presence of a person in the home. Manual control with the buttons or is also possible.


Link for button with battery and wireless switch actuator

8531.X & 8130.4

1- Selecting the functioning of the button with battery

The battery transmitter must have

Switch operation mode
(mode 2) selected.



Types of connection

The control element can work with three different types of connection: “**daily clock newspaper**”, “**weekly clock**” or “**weekly clock with Astro device**”.

- **Daily clock**: When programming the connection times, the day of the week cannot be selected. Thus, the times you program are repeated every day.

- **Weekly clock**: When programming the connection times, the days of the week are available (1 for Monday up to 7 for Sunday.) Thus it can be programmed differently for each day of the week.

- **Weekly clock with Astro**: Together with the programming of the days of the week, it is possible to activate the Astro function with each connection time.

Indications on the display

1 Current weekday / info line.

2 Info line / date.



3 Operating mode.

4 Time / switching time.

5 Display on the blind insert: Arrows up down during movement time;
Display on the light insert:

OFF / light value in %;

Display on the relay insert: ON / OFF.




Button	Function	In setting mode	Adjusting values	Reset to factory setting
	Calling up menu level and switching to setting mode			Return to operating mode
	Blind UP/ Light ON (brighter)/ Electric load ON	Select menu item	Adjust values	In operating mode press all buttons of the rocker switch simultaneously for approx. 5 seconds.
	Blind DOWN/ Light OFF (darker)/ Electric load OFF			
	Switching operating modes, Switching times today, Displaying sensor values, Confirmation.	Select menu	Accept value	

2- Configuring the wireless receiver actuator

The wireless receiver actuator basically offers two operating modes:

- a) Switch mode: Potentiometer position “INT”
- b) Time-delayed switch mode: We can time the disconnection of the actuator to the desired time, 3 s, 1 min, 5 min, 15 min.
To select the actuator operating mode, turn the potentiometer so that it points to the corresponding position.



Technical details

Sky Niessen


Link for button with battery and wireless switch actuator

8531.X & 8130.4


2.1.- Configuring a link between transmitter and receiver channel of the wireless actuator.

Details are provided below on the association between a transmitter (wireless button, wireless touch control, wireless motion sensor, etc.), and the receiver channel of the wireless actuator.

Turn the potentiometer of the wireless actuator to the position "P". The LED of the configuration button will blink slowly in red.



2.2.- Press the configuration button; the LED of the configuration button will blink quickly in red.




At this moment the wireless actuator is waiting to accept a link with a transmitter channel. (wireless button, wireless touch control, wireless motion sensor, etc.).

2.3.- Linking with the transmitter channel:


- to link with the button with battery, press the lower part of the button briefly. The LED of the button will remain red for a few seconds and go off.
- to link with a touch control.
- wireless motion sensor.

2.4.- Place the transmitter and receiver in operation mode:

- Turn the potentiometer of the battery to position "3"



- Turn the potentiometer of the chip to position "F"




3 blinks in green

3 blinks in red


2.5.- To act on the load: Short and long presses turn on/off.

3- Deleting a link from the receiver channel of the wireless actuator

3.1.- Turn the potentiometer of the wireless actuator to the position "Rst 1", link erase mode.




3.2.- Press the configuration button for approximately 8-10 seconds; The LED of the configuration button will blink quickly in red.




3.3.- Turn the potentiometer of the wireless actuator to the position "Rst 2", link erase mode. If the link has been deleted successfully, the wireless actuator will leave configuration mode and the configuration button will blink in green 3 times.

3.4.- Press the configuration button for 4 seconds; The LED of the configuration button will blink quickly in red.

3.5.- If the link has been deleted successfully, the wireless actuator will leave configuration mode and the configuration button will blink in green 3 times.



If the link has not been deleted successfully, the wireless actuator will leave configuration mode and the configuration button will blink in red 3 times.



Similarly if after one minute there is no attempt to establish an association for the deleted link, the wireless actuator will leave configuration mode automatically.

Technical details


Sky Niessen

Link for button with battery and wireless dimming actuator

8531.X & 8130.5

1- Selecting the functioning of the button with battery


The battery transmitter must have regulation operation mode (mode 4) selected.



2- Configuring the wireless receiver actuator

The wireless receiver actuator basically offers two operating modes:


- a) Switch mode: Potentiometer position "INT"
 - b) Time-delayed switch mode: We can time the disconnection of the actuator to the desired time, 3 s, 1 min, 5 min, 15 min.
- To select the actuator operating mode, turn the potentiometer so that it points to the corresponding position.




2.1.- Configuring a link between transmitter and receiver channel of the wireless actuator.

Details are provided below on the association between a transmitter (wireless button, wireless touch control, wireless motion sensor, etc.), and the receiver channel of the wireless actuator.

Turn the potentiometer of the wireless actuator to the position "P". The LED of the configuration button will blink slowly in red.



2.2.- Press the configuration button; the LED of the configuration button will blink quickly in red.




At this moment the wireless actuator is waiting to accept a link with an transmitter channel. (wireless button, wireless touch control, wireless motion sensor, etc.).

2.3.- Linking with the transmitter channel:


- to link with the button with battery, press the lower part of the button briefly. The LED of the button will remain red for a few seconds and go off.
- to link with a touch control.
- wireless motion sensor.

2.4.- Place the transmitter and receiver in operation mode:

- Turn the potentiometer of the battery to position "3"



- Turn the potentiometer of the chip to position "F"




2.5.- To act on the load:


- Short press up, turn on
- Short press down, turn off
- Long press up, regulate upward
- Long press down, regulate downward

3- Deleting a link from the receiver channel of the wireless actuator

3.1.- Turn the potentiometer of the wireless actuator to the position "Rst 1", link erase mode.



3.2.- Press the configuration button for approximately 8-10 seconds; The LED of the configuration button will blink quickly in red.



3.3.- Press the configuration button for 4 seconds; The LED of the configuration button will blink quickly in red.

Technical details


Sky Niessen

Link for button with battery and wireless blind actuator

8531.X & 8130.7

1- Selecting the functioning of the button with battery


The battery transmitter must have blinds operation mode (mode 1) selected.



2- Configuring the wireless receiver actuator

The wireless receiver actuator basically offers two operating modes:


- a) Switch mode: Potentiometer position "INT"
 - b) Time-delayed switch mode: We can time the disconnection of the actuator to the desired time, 3 s, 1 min, 5 min, 15 min.
- To select the actuator operating mode, turn the potentiometer so that it points to the corresponding position.




2.1.- Configuration of a link between transmitter and receiver channel of the wireless actuator.

Details are provided below on the association between a transmitter (wireless button, wireless touch control, wireless motion sensor, etc.), and the receiver channel of the wireless actuator.

Turn the potentiometer of the wireless actuator to the position "P1". The LED of the configuration button will blink slowly in red.




2.2.- To link with the button with battery, press the upper part of the button briefly. The LED of the button will remain green for a few seconds and go off.



At this moment the wireless actuator is waiting to accept a link with an transmitter channel. (wireless button, wireless touch control, wireless motion sensor, etc.).

2.3.- Turn the potentiometer of the wireless actuator to the position "P2". The LED of the configuration button will blink slowly in red.

2.4.- To link with the button with battery, press the lower part of the button briefly. The LED of the button will remain green for a few seconds and go off.




2.5.- Place the transmitter and receiver in operation mode:


- Turn the potentiometer of the battery to position "3" (image of dial instructions)
- Turn the potentiometer of the chip to position "F" (image of chip) 2.5-To act on the load:
Short press: If the blind is moving, it will stop. And if the blind is stopped, it will be raised/lowered one step or the slats rotated.
Long press: Raises/lowers the blind for the programmed time, with the selector with the electronic mechanism.

3- Deleting a link from the receiver channel of the wireless actuator

3.1.- Turn the potentiometer of the wireless actuator to the position "Rst 1", link erase mode.



3.2.- Press the configuration button for approximately 8-10 seconds; The LED of the configuration button will blink quickly in red.



3.4.- Press the configuration button for 4 seconds; The LED of the configuration button will blink quickly in red.

Technical details


Sky Niessen

Wireless switch actuator

8130.4

230 V~ / 50 Hz
 2300 W / VA
 2300 W / VA
 2300 W / VA
 1000 VA

- Transmission frequency: 868 MHz.
- Allows two operating modes:
 - Switch and time-delayed from 3 s to 15 min.
 - One auxiliary input and one relay output.
 - It has a potentiometer to select the operating modes and for configuration.
 - Dimensions: 47 mm. x 48 mm. x 22 mm.




Wireless dimming actuator

8130.5

230 V~ / 50 Hz ±10%
 25-350 W / VA
 25-350 W / VA
 25-350 W / VA

- Transmission frequency: 868 MHz.
- Allows 4 operating modes:
 - Universal, type C loads, L loads and ESL loads.
 - An auxiliary input and adjustable output.
 - It has a potentiometer to select the operating modes and for configuration.
 - Dimensions: 47 mm x 48 mm x 30 mm
 - Suitable for most low consumption LED lamps with phase-cut dimmers.





Wireless blind actuator

8130.7

230 V~ / 50 Hz ±10%

- Allows two operating modes:
 - 2 independent relays:
 - 2 x 700 W/VA.
 - Nominal current 3AX.
- Use of contactors in installations with fluorescents is recommended.
- Blinds: - 700 W/VA
- 3AX




Wireless DIN-rail actuator

8130.6

230 V~ / 50 Hz
 2300 W / VA
 2300 W / VA
 2300 W / VA
 1000 VA

- Transmission frequency: 868 MHz.
- Allows two operating modes:
 - Switch and time-delayed from 3 s to 30 min.
- It has a potentiometer to select the operating modes and for configuration.




4 position rotatory switch

8154

4 positions and 4 circuits.

The connection must be made with "Faston" type terminals.



SEQUENCE OF CONNECTIONS				
POSITIONS	0	1	2	3
CIRCUITS	●	●	●	●
○ 1	●	●	●	●
○ 2	●	●	●	●
○ 3	●	●	●	●
○ 4	●	●	●	●

Technical details

Sky Niessen

Digital room thermostat

8140.5

Technical data:

Power supply: 230 V~ ± 10%, 50 Hz for ref. 8140.5
127 V~ ± 10%, 60 Hz for ref. 8840.5

Consumption: < 1 W

Usage temperature: From 0 °C to 50 °C.

- Accuracy of the measurement: ± 2 °C (± 1 °C with calibration)
- Resolution: 0.1 °C.

Control output: Voltage-free relay contacts (NO)

- Maximum load: 3 A cos φ = 0.5

Operating mode of the output relay:


- Hysteresis: 0.5 °C.
- Pulse width modulation: With a difference of ± 4 °C compared to the setpoint temperature, variable from 100% to 0% modulation.

This control makes it possible to control heating and cooling devices (not simultaneously) using its internal electronic thermostat.

The thermostat can be calibrated in situ.

- **Nocturnal operating mode “C”:**

Based on establishing a difference between day and night temperatures (from 0 °C to 5 °C) with the purpose of saving energy.



Floor thermostat

8140.9

1. Technical data

Voltage: 230V~ +/-10% 50-60Hz

Load power: 2 300 W

Load type: floor heating resistor.

Control temperature: +5 °C to +45 °C (Set point).

OFF state: at OFF position, the thermostat is off, so that it does not address the temperature measured by the floor temperature probe.

The relay output contact is open.

Temperature accuracy: 0,5 °C.

Hysteresis: 0,5 °C.

Floor temperature sensor: NTC, 10KΩ at 25 °C, -40°C to 80 °C.

Double isolated cable, 4m length.

LED light indication: red and green

Ambient temperature: -20 °C to 45 °C

2. Installation

In order to get the better temperature measurement performance possible at the floor thermostat installation, it is recommended:

- Install the thermostat higher than 1m height from the floor.
- Do not install the thermostat near other heat or cold sources.
- Keep the floor temperature sensor away from interference sources or power circuits.
- Check the floor temperature sensor is correctly connected.

3. Connection


Important: Disconnect the mains voltage power when installing.

Work on the 230 V supply system may only be performed by specialist staff! Disconnect main power supply prior to installation and/or disassembly!

Connection diagram:

For heating and cooling installations with non-potential-free input.

For heating and cooling installations WITH potential-free input.



• Winter mode “W”:

Selected when the unit controlled is a heating unit.

• Summer mode “S”:

Selected when the unit controlled is an air conditioning unit.

• Temperature regulation by hysteresis:

In this operating mode of the output, the unit to be controlled is working constantly until it reaches the setpoint temperature, at which point it is disconnected and will not be re-activated until the ambient temperature is more than 0.5 °C from the setpoint.

• Temperature regulation by pulse width:

With this configuration of the output type, the unit to be controlled is working constantly up to ± 4 °C of the setpoint temperature. From this moment, a cyclical series of switching the unit on/off (varying the ratio of time ON-OFF) until the setpoint temperature is reached. The use of pulse width regulation is especially recommended for electrical heating, heat pumps and electrothermic actuators.

Attention: To regulate between hysteresis and pulse width, the thermostat must not be on, in other words the “ON” must not be shown on the display.

In cases in which it is important to avoid a frequent change between switching on and off, for example in gas boilers, temperature regulation by hysteresis should be used, which is selected by default in the thermostat.

4. Operation


The temperature set point can be adjusted by the rotary knob on the front of the thermostat, from +5 °C to +45 °C.

LED light in the front, indicates the following:

- Red color: Temperature set point is higher than measured temperature at floor sensor.
Relay output contact is closed.
- Green color:
Temperature set point is lower than measured temperature at floor sensor.
Relay output contact is open.
- LED off:
Thermostat is OFF state (disconnected).
- Blinking red color: (a) The floor temperature sensor would not be connected or (b) the temperature read by the floor temperature sensor is below - 40°C. Relay output contact is closed.

5. Guarantee

This product is subject to the guarantee offered in the selling general terms of ABB in each country.



Technical details

Sky Niessen

LED signaling light

8180.1


230 V~ / 50 Hz.

- Suppression of interference according to standards UNE-21806 and EN-55014
- At a distance of 1 meter, it provides a light flux greater than 2 lumen. The indicators will light up provided they are connected to the grid voltage and this maintains its nominal voltage value. These electronic mechanisms do not have rechargeable batteries or auxiliary energy sources, for cases in which the grid voltage falls below the nominal value or 0 V.

The device is installed with a universal box for recessed mounting, with the same electrical connections shown in the figure. Disconnect the grid voltage while installing the device.

Connection of the Indicator light.

(Figure 11)



LED DND/MUR signaling light

8180.2


230 V~ / 50 Hz.

- Suppression of interference according to standards UNE-21806 and EN-55014
- At a distance of 1 metre, it provides a light flux greater than 2 lumen. The pass/wait indicator is a device that is connected to the grid voltage and is able to indicate with a green or red LED light, the wait or pass

Connection of pass/wait indicator.

(Figure 1)

Connection of the device





where it is located. Installed in conjunction with a conventional switch, it makes it possible to have an indicator to indicate free or restricted passage, as relevant at any time (Figure 1).

In addition it can be installed with a switch that has three possibilities, thus allowing standby status, signaling free passage, and restricted passage (Figure 2).

Connection of pass/wait indicator.

(Figure 2)

Connection of the device



Beacon LED light

8181.2

1.- Introduction

The standard marker light is an autonomous indication device, with a battery for accumulating electrical energy, which guarantees the correct indication lighting of the communication routes of buildings in the event there is a power cut or when this falls below 70% of its nominal value (230 V).

2.- Technical Specifications 230 V~ / 50 Hz.

- Alert indication: This can be selected with the selector.
 - a) lighting in blue or
 - b) lighting in white
- Emergency lighting: high luminosity white.
- Nickel-Metal Hydride (NI-MH) battery, which currently have the lowest environmental impact.
- Autonomy: 3 hours, of which 1 h at maximum lighting. 2 h at lower lighting.

Remote control: Allows any type of component standardized regarding voltages.

- Compliant with the following regulations:
 - RD 2816/1982 (BOE 6-11-92): General regulation of the police. Art. 15.2
 - RD 314/2006 (BOE 28-03-06) Technical Building Code Section SU4. Sec. 2.2 Position and characteristics of lights.
 - Sec. 2.3 Installation characteristics.
 - REBT 2002, ITC-BT-28, section 5-g.
 - UNE-EN60598-2-22
- Suppression of interference according to standards UNE-21806 and EN-55014.
- At a distance of 1 meter, it provides a light flux greater than 2 lumen.

Technical details

Sky Niessen


Beacon LED light

Autonomous LED marker light. 8181.2


3.- Installation

- Connect, fit and secure the marker lights to the box (square or circular with 60 mm between screws).
- For greater protection in public premises, the external part of the unit can be affixed with two screws, thus the external parts of the unit are secured more firmly, thus protecting against vandalism.


See assembly in Figures 1, 2 and 3:



- Separate the diffuser support from the cover to be able to secure it to the marker light with the screws.




- Once the beacon has been secured to the box, position the frame and secure the diffuser support to the marker light.



- Fit the cover and the trim onto the diffuser support.


(Figure 6)



4.- Connection

The device is installed with its universal box for recessed mounting, with the same electrical connections shown in the figure. Disconnect the grid voltage while installing the device.

(Figure 7)



Connection of the device

* The voltage of the remote controls may be 9, 13 or 24 Vdc.

Electronic bell

N2224.-XX

1. Technical data

Power Supply


- N2224.1: 127V~ ; 60Hz
- N2224: 230 V~ ; 50-60 Hz

2. Mounting and connection scheme

2.1. Connection

Important: Disconnect the mains when installing.

Connection with Niessen push buttons





3. Operation

The bell can be connected to 4 push buttons maximum, with a different melody for each one of them.

4. Warranty

This product is subject to the warranty offered in the general conditions of sale of ABB in each country.

Connection with conventional push buttons



Technical details

Sky Niessen

FM stereo receiver with alarm module

9368 & 9368.7

1. Technical data

Rated voltage:

- 9368: 230 V~; ±15%; 50-60 Hz
- 9368.7: 127 V~; ±15%; 50-60 Hz

Max. consumption: 100 mA

Stand-by consumption ref. 9368 and 9368.7 (*): 0.2 W.

Stand-by consumption ref. (9368 or 9368.7) + 9368.3 (*): 0.5 W.

(*) With the display illumination at minimum.

Maximum output power: 2+2 W; <1% distortion (16 W)


Speaker impedance: 16 W (2+2 W audio)

2. Wiring diagram:

(*) FM RECEPTION

The FM indoor antenna that incorporates the module 9368 or 9368.7, uses the electrical network to improve reception.

If the reception is not quite right, you can connect an external FM antenna (thin wire or coaxial wire) in the connectors enabled for it.



Auxiliary module

9368.3

1. Technical data

Power supply through AUX.: 9 V

Maximum consumption: 175 ~ 200 mA


Consumption stand-by: 0.4 W

Headphones impedance: 16 ~ 600 Ω (25 + 25 mW audio phones)


Bluetooth®: Bluetooth® v2.1 2.4GHz IEEE 802.15.1

Maximum reach from the module 9368.3 to user's Bluetooth® device: 10 m.

2. Wiring diagram:



3. Mounting:



3. Mounting:



FRONT VIEW

Technical details

Sky Niessen

Radio & Bluetooth multiroom module + Remote control module

9368.1 & 9368.2

1. Technical Data

Power supply:

230 V~ / 127 V~, ±15%; 50-60 Hz

Bluetooth®:

Bluetooth® v2.1 2.4GHz IEEE 802.15.1

Maximum reach from the ceiling module 9368.1 to user's Bluetooth® device: 10 m.

Maximum power consumption:

200 mA

Consumption stand-by:

0.3 W

Communication data:

ZigBee 2.4GHz IEEE 802.15.4

Antenna impedance:

75 Ω


Maximum power headphone output

6+6 W; <1% distortion (4 Ω)

Minimum impedance of headphones:
4 Ω (6+6 W audio)


2. Wiring diagram:

BUS MULTIROOM is only necessary if there is more than one room in the house and/or you want to connect the rooms in the house.



NOTE: Because these devices are radio frequency and to avoid interference, you should not install modules of the same reference or any other RF equipment that could interfere less than 1 m. away. It should be noted that any obstacle between the devices, can significantly reduce the distance range between them.

3. Mounting:



1. Mounting plate
2. Insert - 9368 / 9368.2
3. Frame
4. Cover plate - 8586


Technical details

Sky Niessen


Sound amplifier - Connection to multiroom module

9335.1 - 9368.1

Wiring diagram of 9368.1 module to 9335.1 sound amplifier



Wiring diagram for 9329.1 loudspeakers to 9335.1 sound amplifier




Technical details

Sky Niessen


Dimensions

Sky Niessen




Dimensions

Skymoon




Boxes for flush mounting


1099/1199



999



999.2




Technical details

Zenit

Switches

Optional: locator light


1-way switch




Switches

With indicator light


1-way switch with indicator light




2-way switch



2-way switch with indicator lamp




2-way switch - Intermediate switch - 2-way switch




Push-buttons

Optional: locator light

Push-buttons



1-way double pole switch




Technical details

Zenit


Push-buttons

With locator or indicator light


Push-button with indicator lamp



Push-button for buzzer / bell with locator lamp




Push-button for relay with locator lamp



Card switch

With locator light

Card switch



Card timer switch

With locator light

1- Technical Data

Power Supply: 127 V~ / 60 Hz
230 V~ / 50 Hz

Night orientation: By a red LED
Operating T°: 0° C +40° C

Maximum power:

127 V~ / 60 Hz:
1600 W, 1600 W, 1600 W, 1600 W, 700 W


230 V~ / 50 Hz:

3000 W, 3000 W, 3000 W, 3000 W, 1600 W, 1300 W

2.- Mounting and connection scheme

2.1.- Mounting


2.2.- Connection



Important: Disconnect the electrical power when installing.

3.- Operation


Time selector for disconnection: The load time disconnection, after removing the card, can be programmed by the user through the rotary programme selector on the device cover.



Option	Time until disconnection 50Hz	Time until disconnection 60Hz	Previous status	Current Status	Action
1.-	5 s.	4 s.			
2.-	10 s.	8 s.	No card	Card detected	Connects load
3.-	20 s.	16 s.			
4.-	30 s.	25 s.			
5.-	60 s.	50 s.	Card detected	No card	Disconnects the load at preset time
6.-	90 s.	75 s.			

Blind switch & push-button

Blind switch & push-button



Technical details

Zenit

Electronic blind switch

N2261.2

Technical data:

- Power Supply: 230V~ 50Hz / 127V~ 60Hz
- Maximum power:
 - 230V~ 50Hz blind motors: 2x 700VA persianas ($\cos \varphi = 0,5$)
 - 127V~ 60Hz blind motors: 2x 350VA persianas ($\cos \varphi = 0,5$)
- Room temperature for operation: 0°C to 40°C
- According to: UNE-21806 y EN-55014

Functional features:

The electronic blind switch includes 3 modes of operation (to be selected in the rotatory switch):

- P: standard blinds control. Optionally other N2244 inserts can be connected to the N2261.2 to control the blind from other locations.
- V: venetian type blinds control. Optionally other N2244 inserts can be connected to the N2261.2 to control the blind from other locations.
- C: centralization. One N2261.2 can control all the N2261.2 centrally.

Wiring diagram:

- Direct blind control with a N2261.2 (Fig. 1).
- Remote control of the N2261.2 electronic blind control by using a blind push-button N2244 (Fig. 2).
- Centralized control of all the blind from one point by using a electronic blind switch N2261.2 as master of the rest electronic blind switches N2261.2 (Fig. 3).

Fig. 1




Fig. 2





Fig. 3




Operation:

Blind operating mode.

Slats or Venetian blinds operating mode.

Centralized operating mode.


Pulsation	Action	Action	Action
Short pulsation ▲ < 300ms	It raises the blind (3 min.), which was previously stationary. It stops the blind, which was previously moving.	It raises the blind (3 min.) which was previously stationary. It stops the blind, which was previously moving.	It raises the blinds (of those inserted connected), which were previously stationary. It stops the blinds, which were previously moving.
Short pulsation ▼ > 300ms	It lowers the blind (3 min.), which was previously stationary. It stops the blind, which was previously moving.	It lowers the blind (3 min.), which was previously stationary. It stops the blind, which was previously moving.	It lowers the blinds (of those inserted connected), which were previously stationary. It stops the blinds, which were previously moving.
Long pulsation ▲ < 300ms	Raises the blind while the pulsation lasts, which was previously stationary. It stops the blind, which was previously moving.	The slats rotate upwards in a pulsed way while the pulsation lasts, if the blind was previously stationary. If the pulsation lasts longer, the blind will raise for as long as the pulsation lasts. It stops the blind, which was previously moving.	It raises the blinds (of those connected mechanisms), which were previously stationary. It stops the blinds, which were previously moving.
Long pulsation ▼ > 300ms	It lowers the blind while the pulsation lasts, if it was previously stationary. It stops the blind, which was previously moving.	The slats rotate downwards in a pulsed way while the pulsation lasts, if the blind was previously stationary. If the pulsation lasts longer, the blind will raise for as long as the pulsation lasts. It stops the blind, which was previously moving.	It lowers the blinds (of those connected mechanisms), which were previously stationary. It stops the blinds, which were previously moving.




Mounting:

Follow the steps below to install the mechanism:


1. Connect the device according to the connection schemes. Figure 1, 2 or 3.
2. Assemble the device on the flush mounting box.
3. Then, place the plate.



1.



2.




3.

Technical details




Zenit

Key switches

2-way / 3 positions



Example for a blind control:





Position of the key	Active contacts
0	Common and 1
1	Common and 10
2	Common and 4

Key switches & push-buttons


1 or 2-way / 2 positions

Diagram as switch / push button
8153, N2253 / 8153.2, N2253.2



Position of the key	Active contacts
1	Common and 1
2	Common and 2

Scheme as a switch



Technical details

Zenit

USB chargers

N2185, N2285 & N2185.2

1. Technical data:

Rated input voltage:
100 - 240 V AC ± 10 %

Rated input frequency:
50 - 60 Hz

Rated input current:
N2185.2: 0,20Aac@max load
N2285: 0,20Aac@max load
N2185: 0,12Aac@max load

Consumption in standby:
N2185.2: <10 mW@230 VAC
N2185 & N2285 : <= 0,3W@230 VAC

Rated output voltage:
5 V DC +5 / -5 %

Rated output current:
N2185.2: 2000 mA a 5 V DC
N2285: 1500 mA a 5 V DC
N2185: 750 mA a 5 V DC



Operating temperature:
N2185.2: 0°C to 45°C, when installing
a N2185.2, 0°C to 30°C, when two
N2185.2 chargers together
N2285: 0° C + 35° C
N2185: 0° C + 45° C

Energy efficiency:
N2185.2: > 79%
N2285: >= 71%
N2185: >= 66%

2. Electrical safety data:

4. Installation

N2185.2 & N2185



N2285



Safety standard:
EN60950-1 - Low Voltage Directive

Protection class:
II - Low voltage

Isolation (primary-secondary):
Transformer with galvanised isolation

EMC Directive:
EN 55022, EN 55024

3. Wiring diagram:



Technical details

Zenit

Circuit breaker 6/10/16A & RCD

N2234.1, N2234.2 & N2234.3

1.- Technical data:

Rated voltage:

120 - 230 Vac

Rated frequency:

50 - 60 Hz

Rated current (In):

N2234.1: 6 Aac

N2234.2: 10 Aac

N2234.3: 16 Aac

Breaking capacity:

N2234.1: 1,5 kA

N2234.2 & N2234.3: 3 kA

Residual current (sensitivity) - $I_{\Delta n}$:
10 mA

Magneto-thermic action:

C type (see diagram)

Number of poles:

Two-pole (1P + N) with 1 protected pole

2.- Standards:

EN 61009 / 1 / 1994

EN 61009 / 2 / 1 / 1994

IEC 1009 / 2 / 2 / 1991

IEC 1009 / 1 Amd 1 1995


Low Voltage Directive:

CEE 73/23 & 93/66 CEE

EMC Directive:


CEE89/336, 92/31 CEE & 93/68 EEC

3.- Wiring diagram:




4.- Installation

1. Fix the plastic support in the mounting plate.
2. Insert the mechanism in the mounting plate from the rear side.
3. Place the cover plate.



4.- Current-Time tripping diagram




Technical details

Zenit

TV / R outlets

Technical data

- Connection: Screw terminal and clamp. Coaxial cable 75 ohm.
- Shielded zamak and metal plate chassis.
- In conformity with EN 50083-1:1993, EN 50083-2:2001, EN 61000-6-1:2001, EN 61000-4-2:1995 ESD 15KV AD, 8KV CD, EN50083-4:1998
- Fits in a Ø60 mm box.




Important: the connection of the TV outlets in serial distribution must be carried out according to the figure on the left. The cable coming from the previous outlet is connected in the right terminal and the cable going to the next outlet in the left terminal.

Code	8150	8150.3	8150.7	8150.8
Installation		Final	Intermediate	
Connection		Screw terminal and clamp		
Output connectors	C1 C2	IEC male Ø 9.52 mm IEC female Ø 9.52 mm		
Frequency range	MHz	I/O C1 C2	5 - 862 5 - 862 5 - 862 87.5 - 108	13 - 862 13 - 862 13 - 862 13 - 862
Basic loss	dB ±TOL	FM DAB VHF UHF	10,0 ±0,7 10,0 ±1,5 4,0 ±1,5 3,0 ±0,5	1,1 ±0,3 R: 0,3 ±0,1 TV: 0,9 ±0,3 8,0 ±0,7
Through loss	dB ±TOL	FM VHF UHF	- -	25,0 ±1,5 30,0 ±0,2 11,0 ±1,0 10,5 ±1,0
Directivity	dB	FM TV	- -	>12 >9 >25 >13
Isolation	dB	FM TV	>14 >14	>18 >16 >15 >18
Return loss	dB	FM TV	>18 >10	>16 >18 >12 >15


Note: reference 8150.3 compatible with CATV

MATV connection diagram Distribution with tap-off units




In this diagram all final outlets are the same.
References 8150 or 8150.3 can be used equally.

MATV connection diagram Serial distribution up to 9 floors



MATV connection diagram Serial distribution for more than 9 floors




Example: 10 floors. The floors are divided in 2 groups of 5 floors each. The outlets are distributed according to the criteria shown in the MATV connection diagram for serial distribution up to 9 floors. The diagram above can be used in buildings up to 18 floors. For buildings with more than 18 floors and up to 27 floors, 3 groups have to be created and so on.

Technical details

Zenit

Tomas de TV-R / SAT


SMATV connection diagram




Note:

End of line impedance. If the distribution equipment requires outlets with end of line resistors, 8151.7/N2251.7 outlets must be used or add to 8151.3/N2251.3 outlets a termination resistor to close the line.

a) SMATV star connection diagram



a) SMATV star connection diagram



Note:

It is recommended to avoid installing more than 2 intermediate outlets per line.


Code	8151.3 N2251.3	8151.7 N2251.7	8151.8 N2251.8	8152.7
Installation		Final	Intermediate	Final
Connection		Screw terminal and clamp		
Output connectors	C1 C2 C3		IEC male Ø 9.52 mm IEC female Ø 9.52 mm F female	
Frequency range MHz	E/S C1 C2 C3	5 - 2400 5 - 862 930 - 2400 -	5 - 2400 5 - 2400 5 - 2400 -	5 - 2500 5 - 68 / 125 - 862 87,5 - 108 950 - 2500
Basic loss dB ±TOL	FM TV SAT	0,2 ±0,1 1,0 ±0,5 1,2 ±0,6	3,7 ±0,3 4,0 ±0,5 5,0 ±1,2	10,0 ±1,0 10,0 ±1,0 12,0 ±2,0
Through loss dB ±0,5	FM TV SAT		- - -	2,5 ±0,5 2,5 ±0,7 3,0 ±1,0
Directivity dB	FM TV SAT		- - -	>20.0 >12.0 >5.0
Isolation dB	FM TV SAT	>45 >14 >14	>20 >20 >14	>45 >30 >28
Selectivity dB	FM TV-R SAT	- >15 >15	- - -	>15 >15 >15
Return loss dB	VR FM TV SAT	>25 >25 >14 >10	>16 >16 >16 >9	>13 >13 >12 >12
DC path	V... mA Tono		24 max 500 max 22 KHz/DiSEqC	24 max 500 max 22 KHz/DiSEqC

Technical details

Zenit


N2250.X & N2252 covers for TV outlets

1. In some cases the TV outlets have too small holes for frame's clamps.




2. There are two options of mounting the cover plates: a) cut the clamps that are facing the small holes.

b) Cut all the clamps of the frame.




3. When the cover plate is screwed to the insert, the 4 parts that stick out from the cover, will fix the frame to the wall.




N2251.3 TV-R/SAT outlet single, N2251.7 TV-R/SAT outlet dead-end and N2251.8 TV-R/SAT outlet loop through


Mounting diagram



Cable to use



Cable to use



- Use coaxial cable with 75Ω impedance.


- Avoid small bending radius.

Technical details


Zenit

N2150.7 & N2250.7 - TV outlet dead-end


Connector characteristics



Cable to use



Warning



- TV output: 9,52 mm male.

- Use coaxial cable with 75Ω impedance.


- Avoid small bending radius.

Name	TV outlet dead-end		
Frequency range	MHz	TV	5 - 2400
Connection loss	dB	TV	1
Isolation	dB	TV	>16
Return loss	dB	TV	>7,6
Bypass DC current	V mA		34 (max.) 500 (max.) 22Khz / DiSEqC

Telephone outlets


6 contacts
N2117.6 / N2217.6

Additional bell
with capacitor




6 contacts
N2117.6 / N2217.6

Additional bell
without capacitor



8 contacts
2017.3



Technical details

Zenit

RJ45 Cat. 6 female connector

2018.6

1 Preparing the Cable	1.1 Cut approximately 5 cm. off the jacket.	1.2 Open approx. 10 cm. of the jacket with a cutter cord or another tool.	1.3 Cut the jacket.	1.4 Cut the mesh (if it has one and the cord at the same level of the jacket).
2 Preparing the Conductors	2.1 Select the adequate wiring scheme (568A or 568B) and place the pairs in a straight line.	2.2 Position each of the four pairs in the holes of the end piece.	2.3 Ensure the end piece is located as close as possible to the edge of the jacket.	
2.4 Place the pairs in the direction of the end piece slots.	2.5 Insert the end piece into the module.	2.6 Unbraid the pairs, position and insert the cable in the module slots. Place the solid colour cable in the first slot of the pair .		
3 Conductor Terminations	3.1 Place the tool perpendicular to the module and finish cutting the cables.	4 Placing the Cable		
5 Disassembling the module from the supporting piece	5.1 Push the front of the module in with your thumb releasing the hooks.	5.2 Pry upwards to release the upper hook.	5.3 Pry downwards to release the lower hook.	


Technical details

Zenit


RJ45 Cat. 5E female connector

2018.5


- 1 Remove the back cap from the connector. Strip approx. 5cm off the jacket and discard the cable cutter cord.




- 2 Bring the cable close to the connector, with the jacket at approx. 6 mm from the connector. Insert the cables into the corresponding slots as indicated by the cable colour-wiring configuration for T568A or T568 B (as shown in Figures 2A and 2B).




2a Wiring according to T568A:



2b Wiring according to T568B:



- 3 Push the cables against the end of the slot and cut them flush to the connector. Use an IBDN 110, BIX, KRONE wiring tool, or a similar type 110 tool.




4 Mount the connector cap.




Technical details

Zenit


VDI connectors




N2155.2
Pin Out:
1G — W/GND Left Audio
1B — White 1B — White
3G — R/GNB Right Audio
3R — red



N2155.4
Pin Out:
R — Red Left Audio
G — Ground Right Audio
L — White





N2155.3
Pin Out:
1G — Y/GND Composite Video
1A — Yellow 1A — Yellow
2G — W/GND Left Audio
2B — White 2B — White
3G — R/GND Right Audio
3R — Red





N2155.5
PIN PIN
1 — 1 R+ 5 — GND 5
6 — 6 R- 10 — SGND 10
2 — 2 G+ 11 — ID0 11
7 — 7 G- 12 — ID1 12
3 — 3 B+ 13 — HSYC 13
8 — 8 B- 14 — VSYC 14
4 — 4 ID2 15 — ID2 15
G — GND G — GND

G-1	1	TMDS Data2+
G-1	2	TMDS Data2 Shield
G-1	3	TMDS Data2-
G-2	4	TMDS Data1+
G-2	5	TMDS Data1 Shield
G-2	6	TMDS Data1-
G-3	7	TMDS Data0+
G-3	8	TMDS Data0 Shield
G-3	9	TMDS Data0-
G-4	10	TMDS Clock+
G-4	11	TMDS Clock Shield
G-4	12	TMDS Clock-
G-4	13	CEC
G-4	14	RESERVED (N.C. on device)
G-4	15	SCL
G-4	16	SDA
G-4	17	DDC/CEC Ground
G-4	18	+5V Power
G-4	19	Hot Plug Detect
GND		Ground



N2155.8
Pin Out:
1 — Vbus
2 — D-
3 — D+
4 — Ground
G — Shielded



Note:
Using a strap for fixing the cable to the board it is recommended to avoid disconnections. For this the plates have two through-holes at its rear end.

Technical details

Zenit

Resistive rotatory/push dimmer - N2260.2

1. Technical data

Electrical data:

- Power supply: 230 V~ ; 50 Hz
- Minimum power: 60 W / VA
- Maximum power:
500 W incandescent lamps.
500 VA halogen lamps with electronic transformer.
400 VA halogen lamps with ferromagnetic transformer.
- Room temperature for operation: 0 to 30 °C.

Features:

- Dimming control by means of a local push button (N2260.1 and N2260.2) and a dimmer switch (N2260.2).
- Control capability through auxiliary push buttons (N2X04.X).
- LED indicator pilot.

Detecting the type of load

- After wiring the device to the power supply, the dimmer assesses the type of the load connected.

Overload

- If the device overloads above the maximum rated power, or if the operating temperature exceeds the maximum, the regulator will automatically stop working as a safety measure.

Short Circuit

In case of short circuit, the device will stop working as a safety measure.

Note: Disconnect the device from the power supply if you are making changes to the load.

2. Assembly/Connection

2.1. Connection

Important: disconnect the power supply when installing.




Figure 1:
Basic wiring diagram




Figure 2:
Special wiring diagram

Wiring for direct control

The electrical wiring for these devices is performed according to the wiring diagram shown in Figure 1.

The terminal marked "L" shows the phase wire of the installation.

The terminal indicated with Δ represents the conductor wiring terminal returning from the load, which is also connected to the neutral conductor of the installation. See Figure 1.

The terminal marked "1" is used to exercise control from several points by means of conventional push buttons. See Figure 2.

If the device is installed individually, follow the instructions indicated in Figure 1.

Wiring for remote control option

The special characteristics of these dimmers enable the remote control using conventional auxiliary push buttons (N2X04.X), making it possible to control the turning on and off and dimming features from different points using only one electronic dimmer and any number of conventional push buttons as desired.

In case it is required to exercise control from several points, refer to the diagram below. Any number of auxiliary conventional push buttons may be used as needed.

The outputs of these push buttons are connected to terminal "1".

See Figure 2.

Note: pay special attention to the device input and output conductors, according to the previous description.

3. Mounting

To install the device follow these steps:

1. Connect the device based on the corresponding wiring scheme.
Figure 1 and Figure 2.
2. Mount the device on the wall box.
3. Then, position the plate.




Figure 3: Installation

4. Operation

The operation of the dimmer during the set up, disconnection or regulation is as follows:

Short pulsation

If the dimmer is off, upon receiving a short pulsation it will turn on using always the maximum level of light.

If the dimmer is on, upon receiving a short pulsation it will turn off. A short pulsation refers to any pulsation lasting between 50 ms and 400 ms.

Long pulsation

If the dimmer is off, upon receiving a long pulsation it will turn on using the minimum level of light. Then it will increase it until the pulsation stops, or until it reaches the maximum level of light.

If the dimmer is on, upon receiving a long pulsation the dimming direction will reverse: if the level of light has increased up to a certain point, it will diminish, and vice versa. Whenever the maximum (or minimum) level of light is reached during a long pulsation, the dimming will stop in the maximum (or minimum) level, even if pulsation continues.

A long pulsation refers to any pulsation lasting for more than 400 ms.

Turning the knob clock-wise:

- If the load is off, or in the maximum intensity level, it will not perform any action.
- If the load is in a specific dimming point, it will increase the load intensity.

Turning the knob anti-clockwise:

- If the load is off, it will not perform any action.
- If the load is in a specific dimming point, or in the maximum level, it will diminish the load intensity.

Once the load reaches the maximum or minimum intensity level, if we keep turning the knob anti-clockwise or clockwise, the load will continue in its maximum/minimum intensity level.

Technical details

Zenit

LED rotatory/push dimmer - 2M

N2260.3 & N2260.8

1. Technical data

Rated voltage / max. power:

- N2260.3: 230 V~ ±10%, 50 Hz / 250 W/VA
230 V~ ±10%, 60 Hz / 200 W/VA
- N2260.8: 127 V~ ±10%, 60 Hz / 140 W/VA
- Room temperature for operation: 0 to 35 °C.

Protection:

- Back-up fuse: Electronic
- Overload protection: Electronic


N2260.3 - Rated min./max. power (230 V~):

- LEDi: 2 W/VA / 100W/VA (max. 10 lamps).
- Dimmable energy saving lamps: 2 W/VA / 100W/VA (máx. 10 lamps).
- LV LEDi with transformer: 4 W/VA / 100W/VA (max. 10 lamps).
- Incandescent lamps: 10 W/VA / 250W/VA.
- Halogen lamps: 10 W/VA / 250W/VA.
- LV halogen lamps with transformer: 10 W/VA / 250W/VA.


N2260.8 - Rated min./max. power (127 V~):

- LEDi: 2 W/VA / 55W/VA (max. 10 lamps).
- Dimmable energy saving lamps: 2 W/VA / 55W/VA (máx. 10 lamps).
- LV LEDi with transformer: 4 W/VA / 55W/VA (max. 10 lamps).
- Incandescent lamps: 10 W/VA / 140W/VA.
- Halogen lamps: 10 W/VA / 140W/VA.
- LV halogen lamps with transformer: 10 W/VA / 140W/VA.

2. Wiring diagram



Standard operation




Operation in a two-way circuit

Warning:


Disconnect the mains power supply prior to installation and/or disassembly! Permit work on the 230V/127V supply system to be performed only by specialist staff.

3. Mounting



Turn the device in the correct installation position. The marks on the back side of the device, orients the correct top position.

4. Set-up



The minimum brightness of the dimmer can be set by adjusting the on the back side of the device.

5. Operation

The LED dimmer is a phase-angle dimmer and is used to switch and dim all lamps listed in "Types of load", especially LEDi loads (LED lamps with an integrated ballast). The LED dimmer serves as light controller in connection with rotary dimmer control elements.

Notes:

- 1) Use only L or LC transformers. Pure C transformers are not permitted. If transformers are used, the specifications of the respective manufacturers must be observed. In particular, observe the information regarding the minimum load.

Connection load for LEDi

- 2) Above a connection load of 25 W/VA, suitable measures must be taken to increase the connection load to a maximum of 100 W/VA (230 V supply) or 55 W/VA (127 V supply) when connecting LEDi according to IEC 61000-3-2, for example, through the use of harmonic wave filters.

- 3) Maximum number of LEDi lamps is 10.

Technical details

Zenit

LED/Universal rotatory dimmer - 1M

N2160.3 & N2160.8

1. Technical data

		max 1 1 1	N2160.3 N2160.3 AMDE0322	N2160.8 N2160.8	Mode
Leading Edge	I.	10	4 - 60 W	4 - 30 W	
	II.	10	4 - 60 W	4 - 30 W	T L
	III.	-	4 - 60 W	4 - 30 W	T L
	IV.	-	4 - 250 W	4 - 125 W	T L
	V.	-	4 - 250 W	4 - 125 W	T L
	VI.	-	4 - 250 W	4 - 125 W	T L
	VII.	-	4 - 250 W	4 - 125 W	T L

Types of load supported (see table 1)

Leading-edge dimmable loads:

- I. LED lamps at 230V/12V type L
- II. LED lamps at 12V with electronic transformer
- III. Halogen lamps at 12V with electronic transformer

Trailing-edge dimmable loads (recommended):


- IV. LED lamps at 230V/127V type C
- V. LED lamps at 12V with electronic transformer
- VI. Halogen lamps at 12V with electronic transformer

Traditional loads:

- VII. Incandescent and halogen lamps.

Technical data


Nominal input voltage	(see tables 1)
Nominal input frequency	50 / 60Hz
Operating temperature	-5°C... +35°C
Maximum power supported:	(see tables 1 and 2)
Load type selector	Yes
Off position	Yes
Possible extension for ON/OFF	No
Connection wires	2 o 3
Short-circuit & overload protection	Yes
Temperature protection	Yes
IP protection	IP20
Safety standard	IEC 60669-2-1



Performance

The dimmer's nominal power will decrease according to ambient temperature in line with the graph. If 2 regulators are installed adjacent, reduce max. power to 50%. If 3 adjacent regulators are installed, reduce max. power to 25%.

2. Wiring diagram



3. Connection

3 WIRES (recommended):


Figure '3a' shows an example of a 3-wire connection.

2 WIRES:

Figure '3b' shows an example of a 2-wire connection. This connection is subject to load compatibility, and correct functioning in all cases cannot be guaranteed (see note above). The minimum load installed must exceed 14W and it must be complemented with a 6596 compensation filter in parallel.

4. Set-up

1. Check the voltage is disconnected.
2. Configure the dimmer functioning mode using the adjustment dial, according to the type of load (see table 1).
3. Place the arrow at the bottom end (-) of the selector dial 'S'.
4. Connect all wires through the rear terminals.
5. Make sure that the wires are correctly installed and free of potential short-circuits.
6. Restore the general power supply.
7. Switch on the lamps by turning the dimmer switch.
8. Adjust the minimum threshold by placing the arrow of the selector dial 'S' at the lowest point at which the lamps emit light without flashing.
9. Insert the mechanism in the recess box.



Make sure that the proper functioning mode has been configured (L or T) according to the type of load. Otherwise, the dimmer and the lamp could be damaged.

Note

Given the heterogeneity of the lamps and manufacturers in the market, some LED lamps may not be compatible with the dimmer resulting in persistent flashing problems. To avoid these problems, we recommend using the lamps of recognised manufacturers, avoiding the mixture of models and types whenever this is possible.

Technical details

Zenit

Rotary dimmer 1-10 Vdc for fluorescent or LED drivers - N2260.9

1. Technical data

- **Power supply:**
230V 50-60Hz 700VA
127V 50-60Hz 350VA
 - **Load type:** Dimmable electronic ballast with 1-10V control input.

2. Assembly/Connection

2.1 Connection

Follow the steps below to install the mechanism:

1. Connect the device according to the connection schemes. Figure 2 and Figure 3.
 2. Assemble the device on the flush mounting box.
 3. Then, place the plate.




Figure 1: Installation

Important: Disconnect the power supply when installing.

2. Connection

The fluorescent lighting dimmer N2260.9 may be connected to dimmable electronic ballasts with a control input of 1-10 V as shown in Figure 2:




Figure 2: Basic connection

The maximum charge to be connected to the control terminals $+/-$ should not exceed 50 mA.

See technical specifications of the dimmable electronic ballast to be installed.

Electronic ballasts generate a very high instantaneous peak current at connection, therefore it is recommended not to connect more than 6 ballasts to the N2260.9 fluorescence regulator.

In installations where it is required to connect more than 6 electronic ballasts to the same regulator mechanism, it is recommended to use a contactor to protect the mechanism contacts. See Figure 3.




Figure 3: Connection using a contactor

3. Operation button turns in the clockwise direction

If the charge is disconnected, i.e. the rotatory button is completely turned counter-clockwise, when turning right the charge will turn on (a "click" will be heard) and the intensity level will increase as we turn the button in the clockwise direction.

If the charge is at a given point of regulation, the charge intensity will increase as we turn the button in that direction.

If we turn the button completely in the clockwise direction, this will stop in a limit, which will coincide with the maximum regulation intensity level.

Operation button turns in the counter-clockwise direction

Intensity level will reduce as we turn the button in the counter-clockwise direction.

If we turn the button completely in the counter-clockwise direction, a “click” will be heard and the button will stop in a limit, the charge will be disconnected.

WARNING: This product should only be used with the compatible loads defined in the compatibility table above.

Any installation outside the declared power range could cause damage to the product that could result in malfunction or even accidents.

Technical details

Zenit

1 Module dimmer - N2160.E

1. Technical Data

Voltage:

N2160: 127 V~ ; 60 Hz
N2160.1: 230 V~ ; 50-60 Hz

Power:

N2160: 50-500 W ☺
N2160.1: 50-700 W ☺

Operating temperature:

0 – 30° C





Table 1:
Power reduction (%) as a function of temperature (°C)

2. Assembly/Connection

2.1. Assembly


Important:

If the dimmer is installed next to another electronic device that can produce heat, the maximum power must be reduced in half. If it is installed between two electronic devices that can produce heat, the maximum power must be reduced to the fourth.



2.2. Connection

Important:
Disconnect the power supply when installing.



3. Operation

Do not exceed the maximum shown in Table 1, since the dimmer has a NON-resettable thermal fuse. If the fuse is triggered, the electronic dimmer is useless for further use. In case of exceeding the maximum load, the fuse could not trig but it may happen that the load will not turn off.

Push dimmer - N2260

1. Technical Data

Power supply:

127 V~ ; 60 Hz / 230 V~ ; 50 Hz

Minimum power:

40 W / VA

Maximum power:

For 230 V~ ; 50 Hz:

☺ 450 W incandescent lamps.

☒ 400 VA halogen lamps with transformers.

For 127 V~ ; 60 Hz:

☺ 250 W incandescent lamps.

☒ 250 VA halogen lamps with transformers.

Protection against overcurrent:

Using a calibrated fuse ref. T-2A.

Protection against faulty connections:

Using an electronic device.

Regulation time:

from minimum to 3.8 secs.

Nighttime indicator display:

LED.


Temperature for operation:

0 to 30 °C.

Interference suppression:

UNE-21806 and EN 55014 Standards.

3. Mounting:



- To connect the device, lift the switch (Fig. 3).
- Connect the dimmer based on the wiring scheme (Figs. 1 and 2).
- Mount the device on the wall box, and then position the plate.
- To change the fuse, lift the switch, pulling softly along its edge (Fig. 5) and remove the fuse holder (Fig. 6).

2. Wiring diagram:




Figure 1




Figure 2

The electrical wiring for these devices is performed according to the wiring diagram shown in Figure 1.

The incoming arrow indicates the phase/line wire of the installation and the outgoing arrow indicates the wiring towards the receptor/load according to Figure 1.

The terminal "1" is used to enable the remote control from several points using conventional pushbuttons, refer to the Figure 2.

If the device is to be installed individually, follow the instructions indicated in Figure 1.

This dimmer allows the remote control using conventional auxiliary pushbuttons, making it possible to control the turning on and off and dimming features from different points by means of only one electronic device and any number of conventional pushbuttons as desired. In case it is required to allow control from several points, refer to the Figure 2. Any number of auxiliary conventional pushbuttons may be used as needed. The outputs of these pushbuttons are connected to terminal "1". See Figure 2.

NOTE: Pay special attention to the device input and output conductors, according to the previous description.

Make sure to disconnect the power supply before manipulating the device.

4. Operation:

The operation of the regulator during set up, disconnection or regulation is as follows:

SHORT PULSATION:

If the regulator is off, upon receiving a short pulsation it will turn on using always the maximum level of light.

If the regulator is on, upon receiving a short pulsation it will turn off.

A short pulsation refers to any pulsation lasting between 50 ms and 400 ms.

LONG PULSATION:

If the regulator is off, upon receiving a long pulsation it will turn on using the minimum level of light; then it will increase it until the pulsation stops, or until it reaches the maximum level of light. If the regulator is on, upon receiving a long pulsation the regulation direction will reverse: if the level of light has increased up to a certain point, it will diminish, and vice versa. Whenever the maximum level of light is reached during a long pulsation, the regulation will stop in the maximum level, even if pulsation continues. However, when the minimum level is reached, it does not stop and it starts increasing. A long pulsation refers to any pulsation lasting for more than 400 ms.

Technical details

Zenit

Movement detector - N2241

1. Introduction

This motion detector device senses the movement of people in an area of 5m (maximum) and in a 110° angle.

Depending on the level of light detected by the light sensor and the motion detected in the covered area, the device determines if the load connected to it should be activated or not, thus lighting the area in which it is connected whenever someone passes.

While it is detecting movement, the device maintains the load activated. When it stops detecting motion it disconnects the loads in the preset time. The device enables remote control through conventional push buttons with the use of only one conductor and thus simplifying electrical installations with the possibility to substitute the traditional switched installations.

2. Technical Characteristics:

Power supply: 230 V~ ; 50 Hz
127 V~ ; 60 Hz

Maximum power:



Incandescent lamps: 1,800 W (230 V~ 50 Hz)
1,000 W (127 V~ 60 Hz)

Halogen lamps with electronic transformer, or halogen lamps with ferromagnetic transformer:
750 VA (230 V~ ; 50 Hz)
400 VA (127 V~ ; 60 Hz)

Fluorescent lamps or motors: 400 VA (230 V~ ; 50 Hz)
200 VA (127 V~ ; 60 Hz)

Voltage free relay output: 2 terminals:

- Control capability through auxiliary push buttons (N2X04.X).
- Timer adjustment: Between 10 sec. and 10 minutes.
- Adjustment of light set point level for detection.
- Room temperature for operation: -10° C to 40° C.
- Detection range of the IR motion sensor: Max. 5 metres in a 110° angle.



Cross section diagram showing the detection area

Horizontal view diagram showing the detection area

Front device description




Fig 2.- Front view of the device

1. Detection lens
2. Light sensor
3. Light set point selector
4. Timer selector
5. Operating mode selector (3 positions):
 - I – Always on
 - A – Automatic (central position)
 - 0 – Always off
6. Red LED, indicator of automatic operating mode. It does not light when operating in modes I and 0.

3. Wiring

Pre-installation recommendations

Install the device away from heat sources or draughts.

The sensitivity of this detection device depends on several factors such as temperature, ambient humidity, as well as speed and direction of people's movement.

Before installing the device, it is important to determine where to install it so that it adequately covers the desired detection area.

Basic wiring

The electrical wiring of these devices is performed according to the wiring diagram shown in Figure 3.

The terminal marked "L" shows the phase wire of the installation. The terminal marked "N" shows the neutral wire of the installation. The terminals marked represent the two terminals of the relay output (voltage free).




Figure 3: Basic wiring diagram

The terminal marked "aux" (control terminal) is used in case it is desired to control the device (optional) from different points through conventional push buttons (auxiliary pushbuttons). See wiring diagram in Figure 4. It is possible to use the device as a crepuscular switch if a switch is connected to the control terminal to a pushbutton.

Note: Pay special attention to the device input and output conductors, according to the previous description.

Make sure to disconnect the power supply before manipulating the device.




Figure 4: Special wiring diagram

Wiring of several devices in parallel

The detection area in a zone can be increased by installing more than one motion detector device.

To ensure that the detection of movement by any of the devices installed activates the load controlled by all of them, their outputs should be wired in parallel to the load. See wiring diagram in Figure 5.




Figure 5: Parallel wiring diagram

Selection of the light and time threshold

Once the device is wired and installed, based on the type of application, it is important to determine the light value below which the device should activate the load while in Automatic Mode, either by the detection of movement or by pressing the auxiliary pushbutton.

The light set point selector (see Figure 6) enables the selection of the light threshold below which the detector will activate the load.

- If the potentiometer is turned to the left (anti-clockwise), the device will activate the load whenever it detects movement, regardless of the light value, during either day or night.

- If, on the contrary, the potentiometer is turned to the right (clockwise), the device will activate the load when it detects movements under low light conditions, i.e. almost in the dark.

Technical details

Zenit

Movement detector - N2241



Figure 6: Exploded view of the selection potentiometers for the selection of light and time thresholds.

The load disconnection time is another important parameter that needs to be chosen. The set value will be based primarily on the type of application and the detector installed. The time can be chosen easily by turning the time selector potentiometer (see Figure 6).

4. Installation

To install the device follow these steps:

1. Connect the device based on the wiring scheme. Figures 3, 4 and 5.
2. Mount the device on the wall box.
3. Then, position the plate.





Figure 7: Installation for N2241

The load disconnection time is another important parameter that needs to be chosen. The set value will be based primarily on the type of application and the area in which the detector is installed. The time can be chosen easily by turning the time selector potentiometer (see Figure 6).

5. Operation

The motion detector device has 3 different operating modes that the user can select at any time using the selector located at the front of the device. The available operating modes are the following:

- I – Always on
- A – Automatic (central position)
- O – Always off



Operating Mode "I": Always On

How to select the operating mode "Always On"

- The operating selector is in position I: Always On
- The front red pilot is off

In this operating mode, the load is always activated, regardless of the light level or the movement detected within the covered area.

While in this mode, the device does not respond to the auxiliary push button that may be connected to the control terminal.

Operating Mode: Automatic (A). Motion detector.

How to select the operating mode "Automatic"

- The operating selector is in position A: Automatic.
- The device indicates it is in the Automatic operating mode by lighting the front red pilot.
- Optionally, the auxiliary push buttons wired to the control terminal can be used.

This operating mode enables the independent activation and deactivation of the load, based on the movement detected within the covered area and on whether the light level is above or below the set threshold.

When the device detects movement of people and the light level sensed is below the set point, then it activates the load. With the conditions described above and while the device detects movement, the load will be activated.

Once the device stops detecting movement, it will deactivate the load based on the time set for deactivation; in this way, the device will be on standby until it detects another movement within the covered area.

When one of the auxiliary push buttons that may be connected to the control terminal is pushed, the device will behave as if it had detected movement. It will activate the load whenever the light level in the covered area is below the set point and will deactivate the load if no movement is detected within the time set.

Operation as Crepuscular Switch

The device can be operated as a crepuscular switch, i.e. it can activate the load when the light level is below the set threshold, no matter if there are people moving in the area or not. In the same way, the device may deactivate the load when the light level goes above the selected threshold.

How to select the operating mode "Automatic" when the device works as a crepuscular switch.

- The operating selector is in position A: Automatic
- The device indicates it is in the Automatic operating mode by lighting the front red pilot.
- Instead of using auxiliary push buttons, wire a switch to the control terminal and then, wire the terminal to the phase wire. When the switch is closed, the device operates as a crepuscular switch.

This operating mode is a well defined application derived from the device Automatic operating mode. In this mode, the device operates as a crepuscular switch, so that when the front light sensor detects a decrease in the light level below the set threshold, the switch activates the load, regardless whether there is movement of people or not within the covered area.

Once the light in the room collected by the sensor exceeds the set light threshold, it disconnects the load.

Note 1: For the correct operation of the device as a crepuscular switch, the device should be kept away from the light source (load) it controls. In this way, the purpose is that the device's light sensor only collects the room light (not artificial) that will determine if the light loads automatically controlled by the device should be turned on or off.

Note 2: This operating mode automatically decides whether to connect or disconnect the loads, based solely on the light collected by the device's light sensor. Therefore, the operation of the device does not rely on or respond to the movement of people within the covered area, if the switch connected to the control terminal is closed to the phase wire.

Technical details

Zenit

Time delay switch

N2262.1

1. Technical data

- Rated Voltage: 230 V~ ; 50 Hz

- Maximum power:

40 - 500 W for incandescent lamps.

40 - 400 VA for halogens with conventional transformers.

40 - 100 VA for motors.

Protection against overcurrents:

Through calibrated fuse F-3,15H. It is supplied with a replacement.

Protection against faulty connections:

Through electronic device.



Time delay: from 10 sec. to 10 min. ($\pm 10\%$).

Night vision device: red LED.

Operating temperature: from 0 to 40 °C.

2. Wiring diagram:

The electric connection of these articles is carried out in conformity with the presentation of the following Figures. The «L» terminal indicates the connection with the installation phase wire, and the arrow exiting the device indicates the connection to the receptor.



NOTE:

Pay particular attention to the connection of exit/entry device conductors, as shown in the diagrams.

When manipulating the device, make sure it is disconnected from the power grid.

For the applications requiring the timing of an engine of less than 40VA power, for example a small air-extractor engine with 13VA in a bathroom, the connection will be possible if you connect another load to the latter, so as to make sure the addition of both power loads results in a power output which is greater than 40VA, the minimum load required for the correct operation of the device.

If an engine is connected to another load (a halogen or incandescent lamp), the maximum power load of the latter has to equal the maximum power output value of the engine.

3. Mounting:




Fig. 3

1. Connect the device according to the instructions cited in the subsection on connection systems. Do not manipulate the device when connected to the power grid.

2. Introduce the mechanism in the flush-mounting box holding it with the screws of the box (or with fixation claws, if the box is equipped with them).

3. Set the time delay.

4. Mount the frame.

5. When mounting the other series, insert the frame between the support and the body and screw the support to the body. Mount the key on the support.

6. The time delayed switch is ready to use.

4. Operation:

The time delayed switch is an electronic operation mechanism making the automatic disconnection of the controlled element, within an adjustable time interval.

The manual operation is carried out by pressing the key.

Setting the desired time margin for disconnecting the device, is carried out by using an adjusting screw, as indicated on Figure 4. The time range is adjustable from 10 seconds to 10 minutes ($\pm 10\%$).




Fig. 4

Technical details

Zenit

Rotatory thermostat with remote sensor

N2240.3

1. Technical data

Voltage: 230V~ +/-10% 50-60Hz

Load power: 2.300W.

Load type: floor heating resistor.

Control temperature: +5°C to +45°C (Set point).

OFF state: at OFF position, the thermostat is off, so that it does not address the temperature measured by the floor temperature probe. The relay output contact is open.

Temperature accuracy: 0,5°C.


Hysteresis: 0,5°C.

Floor temperature sensor: NTC, 10KΩ at 25°C, -40°C to 80°C. Double isolated cable, 4m length.

LED light indication: red and green

Ambient temperature: -20°C to 45°C

2. Wiring diagram:



In order to get the better temperature measurement performance possible at the floor thermostat installation, it is recommended:


- Install the thermostat higher than 1m height from the floor.
- Do not install the thermostat near other heat or cold sources.
- Keep the floor temperature sensor away from interference sources or power circuits.
- Check the floor temperature sensor is correctly connected.

Important: Disconnect the mains voltage power when installing.

Work on the 230 V supply system may only be performed by specialist staff!

Disconnect main power supply prior to installation and/or disassembly!

3. Mounting



4. Operation:

The temperature set point can be adjusted by the rotary knob on the front of the thermostat, from +5°C to +45°C.

LED light in the front, indicates the following:

- Red color: Temperature set point is higher than measured temperature at floor sensor. Relay output contact is closed.
- Green color: Temperature set point is lower than measured temperature at floor sensor. Relay output contact is open.
- LED off: Thermostat is OFF state (disconnected).
- Blinking red color: (a) The floor temperature sensor would not be connected or (b) the temperature read by the floor temperature sensor is below.
- 40°C. Relay output contact is closed.

Technical details

Zenit

Digital thermostat

8140.5 + N2240.5

1. Technical data

Voltage: 230 V~ ; 50 - 60 Hz

Power consumption: < 1W

Control temperature: +0°C to +50°C

Temperature accuracy: ±2°C (±1°C with calibration)

Resolution: 0,1°C


Control output: potential-free relay contacts (NA).

Maximum load: 3A cos φ = 0,5.


Hysteresis: 0,5°C

Pulse-width modulation: ±4°C difference with the set-point temperature, variable from 100% to 0% modulation.

2. Wiring diagram:




For heating or cooling installations
WITHOUT potential free input



For heating or cooling installations
WITH potential free input


**Important: Disconnect the mains voltage power when installing.
Work on the 230 V supply system may only be performed by
specialist staff!
Disconnect main power supply prior to installation and/or disassembly!**

3. Mounting



1. Mounting plate
2. Insert - 8140.5
3. Cover plate - N2240.5
4. Frame

4. Operation:



This command allows you to control heating and cooling devices (not simultaneously) from its internal electronic thermostat. Also, thanks to the night mode, allows to maintain a temperature differential (from 0°C to 5°C, also programmable) to save energy with just one keystroke.

Night operating mode C :

It is based on setting a temperature difference (in °C) between day and night, in order to save energy.

Winter mode ☀ :

To be selected when the equipment under control is a heating equipment.

Summer mode ☀ :

To be selected when the equipment under control is an air-conditioning equipment.

Temperature control by hysteresis:

Thermostat's default type of control. The use of hysteresis control is particularly suitable for gas boilers.

Pulse-width temperature control:

The use of pulse-width control is particularly recommended for electric heaters, heat pumps or electrothermal actuators.

ATTENTION:

To select between hysteresis and pulse-width, it is necessary that the thermostat is off mode, i.e. the "ON" is not displayed on the screen.

(1) TEMPERATURE DISPLAY

Displays the set-point temperature.

(2) PUSH BUTTON FOR CONFIRMATION OF SELECTED OPTIONS

Confirms the selected values.

(3) ON/OFF AND UP PUSH BUTTON

Turns the control on and off. The display will show "ON" if it is turned on and will turn off when it is off. It serves to increase the temperature displayed on screen.

(4) NIGHT AND DOWN KEY PUSH BUTTON

Selects between day and night modes. The display will show C in night mode and in day mode it will disappear. It serves to decrease the temperature displayed on screen.

(5) FUNCTIONS/CONFIGURATION SELECTOR

By pressing "we will adjust the set-point temperature" and, if we press successively, we will choose "winter/summer", "night temperature", "thermometer calibration" and "output relay action mode".

- **1 press on "MODE"** to adjust the set-point temperature.

While the set-point temperature and the symbol "°C" flash on the display, set the desired value with "▲ and ▼" and press "OK".

- **2 presses on "MODE"** to choose between winter and summer.

While the symbols ☀ / ☀ flash on the display, set the desired value with "▲ and ▼" and press "OK".

- **3 presses on "MODE"** to choose the night temperature differential.

While the night temperature differential and the symbol C flash on the display, set the de-sired value with "▲ and ▼" and press "OK".

- **4 presses on "MODE"** to calibrate the thermometer.

The temperature indicator flashes and with "▲ y ▼" we select the appropriate ambient temperature. It will be set by pressing "OK".

- **5 presses on "MODE"** to choose the "output relay action mode". The "STD" or "INC" will be illuminated on the display when pressing "▲ or ▼". We select the right one and we press "OK".

"STD" indicates the operating mode by hysteresis.

"INC" indicates the operating mode by pulse-width modulation.

In all the cases the setting is validated pressing "OK". Failure to do so, the control returns to the previous settings in 5 seconds without saving the new ones.

With the control turned off, it behaves as a thermometer, showing the current temperature.

ATTENTION:

In the first implementation it is advised to wait **8 hours** before calibration. After an off voltage, the control requires **30 minutes** before showing an accurate temperature.

Technical details

Zenit

Rotatory fan control

N2254.1

1. Technical data


Voltage: 127 V~ ; 60 Hz

Load power: 190 W


Load type: ceiling fan.

Operating temperature: +0°C to +40°C

2. Wiring diagram:



3. Mounting:



4. Operation:

Speed / Button position: 0 Disconnected.

I Maximum speed.

II Medium speed.

III Minimum speed.

Electronic doorbell

N2224 & N2224.1

1. Technical data

Voltage:


- N2224: 230 V~ ; 50-60 Hz

- N2224.1: 127V~ 60Hz


4 melodies available.

Acoustic power at 1 meter with cover plate: 72 dB.

2. Wiring diagram:




Connection with more than one push-button per melody.



3. Mounting

To install the device follow these steps:

1. Connect the device based on the corresponding wiring scheme.
2. Mount the device on the wall box.
3. Then, position the plate.



4. Operation:

The bell can be connected to 4 push buttons maximum, with a different melody for each one of them.

Important: Disconnect the mains voltage power when installing.
Work on the power supply system may only be performed by specialist staff!
Disconnect main power supply prior to installation and/or disassembly!

Technical details

Zenit

Buzzer

N2119 & N2219

1. Technical data


Rated voltage: 127-230 Vac / 50-60 Hz.

Rated power: 8 VA.

Adjustable tone.

Acoustic power at 1 meter with cover plate: 75 dB.

2. Wiring diagram:



LED signaling light

N2180 BL/RJ/VD, N2180.1 BL, N2280 BL & N2280.2 RJ/VD

1. Technical data

Rated voltage: 127-230 Vac / 50-60 Hz.

Lamp:

- N2180 BL/RJ/VD / N2180.1 BL / N2280 BL: white LED.
- N2280.2 RJ/VD: red and green LED.



Luminous flux:

- N2180 BL/RJ/VD / N2280 BL / N2280.2 RJ/VD: > 2 lumen at 1 meter.
- N2180.1: < 0,5 lumen at 0,3 meter.

Diffuser:


- N2180 BL / N2180.1 BL / N2280 BL / N2280.2 RJ/VD: white.
- N2180 RJ: red.
- N2180 VD: green.

2. Wiring diagram:



Important: Disconnect the mains voltage power when installing.
Work on the power supply system may only be performed by specialist staff!
Disconnect main power supply prior to installation and/or disassembly!

3. Mounting:



Technical details

Zenit

LED beacon light

N2281

1. Technical data

Rated voltage: 230V~, 50-60Hz (optional 127 Vac version available)

Alert signals: it can be selected by the selector:

- (a) - blue color light or
- (b) - high brightness white light

Autonomy: 2 hours; 1h at maximum illumination and 1h at lower illumination.

Remote control: supports any standard remote control over voltages.


Standard: UNE-EN60598-2-22 Interference suppression according to norms UNE-21806 y EN-55014.

Brightness: more than 2 lumens (lm) at 1 meter distance.


Battery Nickels-Metal Hydride (Ni-MH), with less environmental impact.

Note: Ni-MH batteries have an estimated life of 4 years. Beacon Pilots correct operation should be verified periodically. In the absence of voltage and previously to have been connected to voltage for more than 24 hours, the mechanism should provide a minimum of one hour beacon lighting, if not, replace the mechanism.

2. Wiring diagram:




3. Mounting:



Make Up Room / Do Not Disturb system

N2180.4, N2180.5 & N2244.5



4. Operation:

The stairs beacon pilot is an autonomous signaling device, equipped with an electric energy storage battery, which ensures the correct building pathways signaling lighting in the event of a power outage or when it drops below 70% of its nominal value (230V~).

Once connected to mains voltage the device can remain in the following operation situations:

- (1) Alert (signaling)
- (2) Operation (beacon)
- (3) Standby (remote control)

Alert (signaling)

The device remains on alert (signaling), provided that the value of the power supply exceeds 70% of the power supply nominal voltage (230V~ 50-60Hz).

Emergency operation

It comes into an emergency operating condition when the power supply voltage is less than 70% of rated voltage (230V~ +/-10%). The device is illuminated with high brightness white color.

Note: The time necessary to recharge the device batteries is 24 hours.

Standby (remote control)

Situation in which the device remains off, even when the power supply voltage is interrupted. This action is achieved by using a remote control connected to the equipment, as shown in figure "Device connection". This way you can select certain number of appliances, from the total installed drivers, to remain off in a power failure, thereby reserving the batteries charge in case of a possible need for further use if the power outage is prolonged.

This is achieved by acting on the remote control that generates a continuous control signal or low voltage pulses, which acts on the pilot/by placing it/them at standby or running again (beacon), as desired. When achieving this type of installation, make sure of the correct connection of the different drivers.

Select the color of the device signaling light in alert situation (signaling).

No need to disconnect the supply voltage of the device to select the alert light through the potentiometer. Although the remote control inputs were connected, these should not be active at the time of selecting the alert light through the potentiometer.

Important: Disconnect the mains voltage power when installing. Work on the power supply system may only be performed by specialist staff! Disconnect main power supply prior to installation and/or disassembly!

Technical details

Zenit

Zenit elastic claws

Mounting the claws on the metal mounting plate

The elastic claws are inserted into the metal support of the mechanisms. For this, there is a guide where at the end of the path the claws are clipped and are perfectly secured, making a block with the mounting plate.



Once the claws are assembled, place the screwdriver in the mounting plate to level it and mount it correctly in the box.




Fig. 3



The assembly is pressed into the housing.




Fig. 4

The claws, when interconnected with the inner part of the box, flex by introducing the whole set into the box.




Fig. 5

Once the support is carried to the top of the box, the claws press against the inner walls of the box holding the support so that it is fixed to be able to mount the mechanisms.

The system is effectively fixed without the need for any additional elements. It supports the stresses to which the elements inserted in the ring can be subjected, in their habitual use.
(insertion of plugs, rocker pressing, etc.)

Insertion of a 1-module mechanism in a mountin plate with elastic claws.
1- Insert the additional parts (elastic claw insert ref. N20718).
2- Insert the 1-module mechanism into the metal bracket.

Fig. 6



Removing the mounting plate and claws from the box


In order to be able to disassemble the entire set, simply insert a tool (screwdriver) and press on each of the claws until they are released from the mechanism support, they fall into the inside of the box and it is now possible to remove all the system. To reassemble it you have to restart the whole process explained before.



Fig. 7



Fig. 8



Technical details

Zenit

FM stereo receiver with alarm module - 9368

1. Technical data

Rated voltage:

- 9368: 230 V~; ±15%; 50-60 Hz
- 9368.7: 127 V~; ±15%; 50-60 Hz

Max. consumption: 100 mA

Stand-by consumption ref. 9368 and 9368.7 (*): 0.2 W.

Stand-by consumption ref. (9368 or 9368.7) + 9368.3 (*): 0.5 W.

(*) With the display illumination at minimum.

Maximum output power: 2+2 W; <1% distortion (16 W)


Speaker impedance: 16 W (2+2 W audio)

2. Wiring diagram:

(*) FM RECEPTION

The FM indoor antenna that incorporates the module 9368 or 9368.7, uses the electrical network to improve reception.

If the reception is not quite right, you can connect an external FM antenna (thin wire or coaxial wire) in the connectors enabled for it.



Auxiliary module – 9368.3

1. Technical data

Power supply through AUX.: 9 V

Maximum consumption: 175 ~ 200 mA


Consumption stand-by: 0.4 W

Headphones impedance: 16 ~ 600 Ω (25 + 25 mW audio phones)



Bluetooth®: Bluetooth® v2.1 2.4GHz IEEE 802.15.1

Maximum reach from the module 9368.3 to user's Bluetooth® device:
10 m.



2. Wiring diagram:



3. Mounting:



3. Mounting:



REAR VIEW

FRONT VIEW

Technical details

Zenit

Radio & Bluetooth multiroom module + Remote control module

9368.1 & 9368.2

1. Technical Data

Power supply:
230 V~ / 127 V~, ±15%; 50-60 Hz

Bluetooth®:
Bluetooth® v2.1 2.4GHz IEEE 802.15.1
Maximum reach from the ceiling module 9368.1 to user's Bluetooth® device: 10 m.

Maximum power consumption:
200 mA

Consumption stand-by:
0.3 W

Communication data:
ZigBee 2.4GHz IEEE 802.15.4


Antenna impedance:
75 Ω

Maximum power headphone output:
6+6 W; <1% distortion (4 Ω)

Minimum impedance of headphones:
4 Ω (6+6 W audio)


2. Wiring diagram:

BUS MULTIROOM is only necessary if there is more than one room in the house and/or you want to connect the rooms in the house.



NOTE: Because these devices are radio frequency and to avoid interference, you should not install modules of the same reference or any other RF equipment that could interfere less than 1 m. away. It should be noted that any obstacle between the devices, can significantly reduce the distance range between them.

3. Mounting:



1. Mounting plate
2. Insert - 9368 / 9368.7
3. Cover plate - N2268
4. Frame


Technical details

Zenit


Sound amplifier - Connection to multiroom module

9335.1 - 9368.1

Wiring diagram of 9368.1 module to 9335.1 sound amplifier



Wiring diagram for 9329.1 loudspeakers to 9335.1 sound amplifier



Technical details

Zenit

Bluetooth sound module with amplifier

9368.4

1. Technical Data

Power supply:

230 V~ / 127 V~, ±15%; 50-60 Hz

Bluetooth®:

Bluetooth® v2.1 2.4GHz IEEE 802.15.1

Maximum reach from the ceiling module 9368.1 to user's Bluetooth® device: 10 m.

3 audio inputs:

Bluetooth, AUX (front), TV (rear)

Maximum power consumption: 7W

Consumption stand-by: 0.2 W

Min input signal level AUX / TV: 500 mV RMS

Input impedance: 10 kOhm

Amplifier power:

2 + 2 W <1% distortion (16 Ω)

Speaker impedance:

8 - 16 Ohm


2. Connection

[A] Basic: input from jack connector (front) or via Bluetooth®.

Output: amplified signal via R-L terminals (rear).

[B] Complete: input from jack connector (front), via Bluetooth® or rear terminals (L-IN-RIN) to connect TV audio.

Output: amplified signal via R-L terminals (rear) to feed speakers (min. impedance: 8 - 16 Ohm) or external amplifier (ref. 9335.X) for higher power output.



Technical details

Zenit

Bluetooth sound module with amplifier

9368.4

3. Set-up

Make sure power supply is disconnected during setup. Connect all wires to rear terminals according to diagrams. Secure mechanism into flush-mounted box using the screws. Connect main power supply.

Note:

Avoid installing the module into encapsulated metal boxes to prevent Bluetooth® connectivity issues.

4. Control Elements

- [1] ON / OFF
- [2] Bluetooth® mode selection
- [3] Add a new Bluetooth® device
- [4] Volume +/-
- [5] Analog audio mode: rear terminals (TV) or front jack (AUX)

5. Status LED

Bluetooth®

Blue (still)	Connected to Bluetooth® device
Blue (flashing quickly)	<ul style="list-style-type: none"> • No stored devices • Ready to sync to new devices
Blue (flashing slowly)	Trying to sync with stored device

AUX / TV

Yellow	Connected to jack input (front)
Green	Connected to TV input (rear)

6. Bluetooth® mode

Note:

Activate the Bluetooth® connection in your mobile device to enable BT mode.

I. First time sync (new installation/reset)

1. Press [1] to switch ON the BT module
 - The quickly flashing blue LED will indicate that the BT module is ready to sync with new device. If blue LED is not flashing, press [2] to activate BT mode.
2. Connect your mobile device to the BT module
 - Browse your mobile device to the Bluetooth settings.
 - Depending on the device, a list of BT devices will be displayed automatically. Alternatively select „search for BT devices“ function.
 - Select „ABB-BTR-XXXX“ to sync devices.
3. Once the blue LED remains permanently ON, you may play music.
 - The BT module will play the audio stream from your mobile.

II. Selecting previously stored devices

1. Press [1] to switch ON the BT module
 - The BT module will try to connect to previously stored devices (LED flashing slowly). If the last used device cannot be found, the module will skip to the previous device in the history list.
 - When a device is found, the devices will connect automatically and the LED will remain still.
2. Once the blue LED remains permanently ON, you may play music.
 - The BT module will play the audio stream from your mobile.

III. Adding new devices

1. Press button [3] for at least 1 second
 - The blue LED will turn to quick flashing
2. Connect to the new device following chapter „I. First time sync (new installation/reset)“
 - The BT module can store up to 8 devices. Once the list is full any new device will overwrite the device from the list which has been used the least.

Note:


To empty the device list you may push button [3] for at least 6 seconds.

Bluetooth® mode remarks

- Depending on the model, the loudspeakers on the multimedia device for playing music have been deactivated while it is connected to the BT module.
- BT module volume is independent to that from the mobile /computer.
 - It is recommended to keep the volume high in the mobile / computer to improve the usability of the BT module.
- Automatic connection
 - Only previously connected devices can connect to the BT module automatically.

7. TV/AUX mode

1. Press [5] to siwtch to TV/AUX mode.
2. Press [5] again to toggle between front and rear audio signals
 - Front input (jack), yellow LED
 - Rear input (TV LIN-RIN), green LED



8. Troubleshooting



- The sound unit does not turn on.
 - Check if the sound unit is powered. A voltage between 115 and 230 V~ 50/60Hz must be applied to L and N terminals.
- The sound unit turns on, but there is no sound.
 - Check that the speakers are properly connected to L+ / L and R+ / R outputs. Verify the absence of shortcircuits and check that line impedance is above 11 Ohms. Make sure that a Bluetooth® device is connected, or a signal is present at TV or AUX inputs. Set volume level to maximum.
- The blue LED flashes slowly, but the unit does not connect to a previously paired device.
 - Check that your device has Bluetooth connectivity enabled. Press twice the ON/OFF key [1] to force a new search through the paired device list [2]. To force a pairing process, press [3] key.
- The unit is at TV or AUX mode, and there is no sound.
 - Verify that an analog signal with a level around 250-500mV is present at TV (rear terminals) or AUX (front 3.5 mm jack) inputs.

Technical details


Zenit

Surface and flush-mounted Centralizations


1. For the mounting of the surface and flush mounting boxes, please check the diagrams for the Workstations in the next page.




2. Both in the surface solution and in the flush solution, there are metal mounting plates where the mechanisms are inserted.



3. The mechanisms are inserted in the mounting plate by pressure.





4. Once inserted, proceed with the wiring.



5. The mounting plate is closed by clipping.

6. Once all the devices are wired and the mounting plates correctly placed, the frame is mounted by clipping it to the box.




Technical details


Zenit

Installation of the surface mounting boxes for Workstations – T1193, T1194, T1195

Installation of the box



Installation of mechanisms




Technical details




Zenit

Installation of the flush mounting boxes for Workstations - T1093, T1094


Installation in cement and brick walls




Installation in drywall / hollow partition



Linking the boxes in cement / brick walls




Linking the boxes in drywall / hollow partition




Technical details

Zenit

Installation of inserts in flush mounting Workstations



Installation of the foldable lid in the Workstations




Technical details






Zenit

Installation of the floor box


Installation of the frame T1373 and inserts T10XX





Installation in flush floor



Installation of frame bracket T1393.4




Installation in concrete floor T1393.9



Technical details

Zenit

Frames



Technical details

Zenit

Frames


Type	Article No.	A	B	C	D	E	G	P
Frames for square boxes (60mm screw distance)	N2171 1-gang (1M)	85	85	-	22,4	44,6	7,5	-
	N2171.1 1-gang (1M)	85	85	-	22,4	44,6	7,5	-
	N2271 1-gang (2M)	85	85	-	44,6	44,6	7,5	-
	* N2271 1-gang (2M)	90	90	-	44,6	44,6	8	-
	N2271.1 1-gang (2M)	85	85	-	44,6	44,6	7,5	-
	N2272 2-gang (2M)	156	85	-	44,6	44,6	7,5	71
	* N2272 2-gang (2M)	161	90	-	44,6	44,6	8	71
	N2272.1 2-gang (2M)	156	85	-	44,6	44,6	7,5	71
	N2273 3-gang (2M)	227	85	-	44,6	44,6	7,5	71
	* N2273 3-gang (3M)	232	90	-	44,6	44,6	8	71
	N2273.1 3-gang (2M)	227	85	-	44,6	44,6	7,5	71
	N2274 4-gang (2M)	298	85	-	44,6	44,6	7,5	71
	* N2274 4-gang (4M)	303	90	-	44,6	44,6	8	71
	N2274.1 4-gang (2M)	298	85	-	44,6	44,6	7,5	71
	N2275 5-gang (2M)	369	85	-	44,6	44,6	7,5	71
Frames for 3 module boxes (83,5mm screw distance)	N2370.1 Blank	122	90	-	-	-	7,5	-
	N2371.1 1-gang (1M)	122	90	-	22,4	44,6	7,5	-
	N2371.1V 1-gang V (1M)	122	90	-	44,6	22,4	7,5	-
	N2372.1 1-gang (2M)	122	90	-	44,6	44,6	7,5	-
	* N2372.1 1-gang (2M)	122	90	-	44,6	44,6	8	-
	N2372.2 2-gang (1+1M)	122	90	-	22,4	44,6	7,5	-
	N2373.1 1-gang (3M)	122	90	-	66,8	44,6	7,5	-
Frames for 4 module boxes (107mm screw distance)	* N2373.1 1-gang (3M)	122	90	-	66,8	44,6	8	-
	N2374.1 1-gang (4M)	139,2	85	-	89	44,6	7,5	-
	* N2374.1 1-gang (4M)	142	90	-	89	44,6	8	-
Frames for 7 modules boxes (100mm screw distance)	N2777.1 1-gang (7M)	196	85	-	155,6	44,6	7,5	-
Mounting grids	N2271.9 1-gang (2M)	74	74	22,2	44,6	47	-	-
	N2272.9 2-gang (2M)	145	70,8	22,2	44,6	44,6	-	71
	N2271.9G 1-gang (2M)	74	74	22,2	44,6	47	-	-
	N2273.9 3-gang (2M)	216	70,8	22,2	44,6	44,6	-	71
	N2371.9V 1-gang (2M)	102	74	22,2	44,6	44,6	-	-
	N2373.9 1-gang (3M)	102	74	22,2	66,8	44,6	-	-
	N2374.9 1-gang (4M)	124	74	22,2	92	44,6	-	-
	N2673.9 1-gang (3+3M)	102	122	22,2	66,8	44,6	-	-
	N2777.9 1-gang (7M)	194	79	22,2	158	44,6	-	-
	N2991.1 BL	62	68	47	44,6	44,6	8,5	-
Surface mounting boxes	8591 BL	86	86	44,2	58	58	-	-
	8592 BL	157	86	44,2	58	129	-	-
	8593 BL	228	86	44,2	58	200	-	-
	N2993 BL	117	85	44,2	56	87	-	-
	N2994 BL	139,2	85	44,2	56	110,2	-	-
Frames for profiles	N2671	32	68	46,5	22,4	44,6	8,5	-
DIN-rail mounting plate	N2671.2	32	126	46,5	22,4	44,6	8,5	-
	N2672	62	68	46,5	44,6	44,6	8,5	-
DIN-rail mounting plate	2692 BL	53,5	56	58,5	-	-	-	-

* Noble materials


Technical details

Zenit


IP55 flush-mounting boxes



IP55 surface mounting boxes



IP40 surface mounting boxes




Technical details

Zenit


Centralizations

Surface mounting box



Ref.	A	B	C	D	E
T1292	212	204	55	117	121
T1293	212	275	55	188	121
T1294	212	346	55	259	121


Flush-mounting box



Ref.	A	B	C	D	E
T1092.1	186	178	55	-	-
T1093.1	186	249	55	-	-
T1094.1	186	320	55	-	-


Workstations

Surface mounting box



Ref.	A	B	C	D	E
T1193	235	176	45	83	146
T1194	295	176	45	83	206
T1195	355	176	45	83	266


Flush-mounting box




Ref.	A	B	C	D	E
T1093	211	150	42	-	-
T1094	271	150	42	-	-

Floor boxes T1393 and T1393.1


Floor box



Metallic housing T1393.9



Adapter frame T1371.4




Note: all dimensions in mm.

Technical details


Zenit

Mounting boxes


1099/1199




999




999.2




499.3



1499.4




1499.7




Technical details


Mylos – Overall dimensions



Frames round



Frames square



Technical details

Mylos – Installation solutions

Composition method of switches and mounting grid



Installing and removing switches from the mounting grid



- Frontal installation of the switches on the support
- Modularity of switches: 22 mm

Installation on concrete boxes



No. modules	Screw distance	Recommended box
2 (with claws)	-	00 050
2 (with screws)	60 mm	00 050
3	83.5 mm	1SL006A00
4	108 mm	00 053
7	100 mm	1SL0064A00
4+4	108 mm	Vimar V71318

Note: for further information on ABB boxes for masonry walls please refer to the catalog **1SLC001001D0905** - Insulating Enclosures and Installation Materials (see page 5/66).

Installation on surface mounted boxes



No. modules	Wall box	Recommended box
2	42 096	Use 2M mounting grid and frame
3	41 823	Use 3M mounting grid and frame
3	41 822	Use 3M mounting grid and frame
4	41 830	Use 4M mounting grid and frame

Note: for further information on wall boxes and duct systems please refer to the catalog **1SLC800001D0201** - Plastic and Metal Duct Systems

Technical details

Mylos – Construction details


Conventional switches (screw terminals)



Specifications of screws and terminals

All the contact blocks with conventional terminals of the Mylos wiring accessories' range have open position captive screws with cross and slot head and clamping frame. PH2 impression.

Screwless switches (spring terminals)



Cleaning and maintenance of the Velvet finish

All switches and devices of the Mylos wiring accessories' range have a Velvet finish, also available for the frames, that gives a velvet effect to the touch.

If there is a build-up of dirt or dust, for cleaning you can simply use common liquid or cream detergents (non-abrasive) on a soft cloth.



In the case of dirt, the use of degreasers is also tolerated. We recommend the use of specific products for cleaning the plastic opaque parts/dashboard. The use of alcohol/bleach/harsh acids can damage the finish and the pad printing.



Technical details


Mylos – Illumination of switches and selection of LED lamps

Night-time location signalling




The 2CSY1632MY and 2CSY1633MY LEDs can be added to conventional switches (see page 2/4) for night-time location. The LED electrically connected in parallel with the ON operating mechanism: it is lit when the load is off (OFF command), and it turns off when the load is powered (ON command).


Location signalling (Always ON)



Load functional signalling




Switches with incorporated LED (see page 2/8) have preinstalled 250V~ LEDs and dedicated terminals for wiring. It is possible to implement any type of functional indication, also with LEDs at different voltages.



Wiring of double-pole switches 2CSY1006MC/S
for Always ON signalling.

The LED is built in.



Wiring of double-pole switches 2CSY1006FC/S
for load functional indication.

The LED is built in.

Since the double-pole switches with incorporated LED do not have dedicated terminals for wiring, they have different part codes depending on which type of functional indication needs to be implemented.

Technical details


Mylos – Illumination of switches and selection of LED lamps

Plug-in LED illumination.

Conventional switches are lit by plug-in LEDs.


There is no need for additional wiring because once the device is fixed in place, it is already ready to light up.

In this way it is possible to implement night-time location signalling in a very easy manner.



Incorporated LED illumination.

Switches with incorporated LEDs provide maximum freedom for wiring the signalling LED through the presence of dedicated terminals.



Technical details

Mylos – Control devices

Switches, two-way switches, intermediate switches, push switches

Area of application

Control (on and off) of ohmic-inductive loads:

- with filament and fluorescent lamps (corrected and uncorrected);
- dedicated circuits for powered equipment (aspirators, range hoods, shutters, blinds, fans, etc.) and controllable outlets.

To eliminate architectural barriers in creating installations, we recommend the use of illuminable switches (Article 4 of Italian Ministerial Decree no. 236 of 14.06.1989).

Technical specifications

Rated voltage	250V~
Rated current	10A (16A for pushbuttons)
Opening distance of the contacts	> 3 mm
Dielectric strength	> 2000V~


Reference standards

LV Directive, EN 60669-1.





Wiring diagrams

The diagrams provided below represent the most widely applied engineering solutions for creating lighting points and are to be considered exhaustive of the possible signalling solutions that can be implemented on switches.

Light control from one point





OR



Technical details




Mylos – Control devices

Light control from one point




Light control from two points

Circuit with two two-way switches



LED
2CSY1633MY
installed
at the front









LED
2CSY1633MY
installed
at the front

Technical details

Mylos – Control devices

Light control from two points

Circuit with push switches and relay






Technical details


Mylos – Control devices

Light control from three points


Circuit with two two-way switches + one intermediate switch



LED
2CSY1633MY
installed
at the front



LED
2CSY1633MY
installed
at the front




LED
2CSY1633MY
installed
at the front

Technical details



Mylos – Control devices

Light control from three points



Circuit with push switches and relay




Night-time location signalling



Load functional signalling



Location (always ON) signalling



Technical details

Mylos – Control devices


Relays

Description	Code
Single-pole latching relay, with 230V~ coil, output contact 10A	2CSY1012MC
	2CSY1012MS

Relay with latching operation for control and adjustment from multiple lamp points by means of single-pole push switches with NO (normally open) contact.

Wiring diagrams

2CSY1012MC - 2CSY1012MS



Technical specifications

Power supply voltage (coil)	230V - 50/60Hz
Output contact	10A (AC1) 7A (AC15)
2CSY1012MC - 2CSY1012MS	

Reference standards


EN 60669-1, EN 60669-2-2.

Description	Code
Monostable relay, with 230V~ coil, output contact 10A	2CSY1014MC
	2CSY1014MS

For the implementation of automation or separations between the control circuit and power circuit. It can be used as an auxiliary element for controlling particular loads.

Wiring diagrams

2CSY1014MC - 2CSY1014MS



Technical specifications


Power supply voltage (coil)	230V - 50/60Hz
Output contact	10A (AC1) 7A (AC15)
2CSY1014MC - 2CSY1014MS	

Reference standards

EN 60669-1, EN 60669-2-2, CEI EN 61810-1.

Examples of application

The flush-mounted relays of the Mylos wiring accessories' range can be used to implement a simple disabled bathroom calling system with a reset pushbutton:



Technical details


Mylos – Key covers

Customization of switches' key covers


Mylos series allows customization of the control switches thanks to a wide choice of available key covers. Replacing them is very simple: it does not require the use of special tools and can be done without removing the switch from the support. Customization of control switches is possible both for devices with a one module key and for those with a half-module key.

The range includes key covers with/without functional labels and with/without symbols.

Note: the screwless control devices on page 2/7 do not allow the replacement of key covers. Part codes 2CSY1011MC/S and 2CSY1018MC/S do not allow the replacement of key covers.



Standard key cover composition



Key cover composition on 2CSY1017MY



Key cover composition on 2CSY1027MY

Technical details

Mylos – Socket outlets

Socket outlets

Area of application

Powering of household appliances, lighting equipment etc.

Main features of Italian and German standard sockets

The cells of the sockets are segregated and protected when the plug is disconnected: the live parts are accessible only with the corresponding plug fully inserted.

Technical specifications

Rated voltage	250V~
Rated current	10A o 16A
Shuttered and elastic live cells	

Possibility of coupling Mylos socket outlets with the various types of plugs on the market

	EU 2,5 A	Italian 10 A	Italian 16 A	Schuko 16 A	US 15 A	US 15 A

Italian standard socket outlets with safety shutters, 250V

	P 11 2CSY1101MC 2CSY1101MS	■	■			
	P 17/11 2CSY1103MC 2CSY1103MS	■	■	■		

Italian/German standard socket outlets with safety shutters and side/central earth, 250V

	P 30 2CSY1108MC 2CSY1108MS	■	■		■	
	P 30/17 2CSY1109MC 2CSY1109MS	■	■	■	■	

American and Euro-American socket outlets, 127V

	US socket outlet 2CSY1145MC 2CSY1145MS			■	■	
	EU-US socket outlet 2CSK1146MC 2CSK1146MS	■			■	

Special socket outlets

	Shaver socket outlet ⁽¹⁾ 2CSY113MC 2CSY113MS	■			■	
--	---	---	--	--	---	--

UK 13 A UK/Indian 16 A French 16 A



British socket outlets, 250V

	UK socket outlet 13 A 2CSY1134MC 2CSY1134MS	■				
	UK socket outlet 16 A 2CSY1164MC 2CSY1164MS		■			

French socket outlets, 250V

	French socket outlet 2CSY1144MC 2CSY1144MS		■			
--	--	--	---	--	--	--

Reference standards

IEC 60884-1

Note: In general terms, no socket outlets of any standard for domestic use fall under the European low voltage directive, because there is no harmonized European standard for these types of socket outlets: in fact, each country has its own standard and therefore a single standard is impossible. For this reason the socket outlets do not bear the CE mark. All the socket outlets of the Mylos wiring accessories' range conforming to CEI 23-50 are however certified by IMQ as a further guarantee of their quality and compliance with standards.

⁽¹⁾ Shaver socket outlets, European/American standard with insulating transformer 230V~ - 50/60 Hz

Technical details

Mylos – Socket outlets

Socket outlets for dedicated lines

Plug sockets for dedicated lines allow outlet points to be differentiated according to their particular application, avoiding incorrect connection of unsupported appliances. Different coloured enclosures (red, orange, green) distinguish them from common socket outlets. There are as yet no standard regulations on the correspondence between the colour of the socket and the type of power supply. In order to distinguish the area of application, the following usage customs are adopted.

Red: continuous power supply with UPS (uninterruptible power supply) through an insulating transformer.


Orange: power supply protected by network-generator unit through an insulating transformer.

Green: safety power supply with network-generator unit.

Special sockets outlets

Description	Code
2P shaver socket outlet with insulating transformer, power supply 230~ 50/60 Hz, output voltage 125V~ (American standard 2P socket) or 230V~ (2P socket P11 type)	2CSY1113MC 2CSY1113MS

Components



The shaver socket incorporates an insulating transformer with a power rating of 20 VA, protected against overload and resistant to short-circuits.

Power supply is guaranteed by a pushbutton that is operated automatically whenever the plug is inserted in the socket.

The secondary circuit, to which the cells of the socket are connected, is isolated from the primary power supply circuit by double insulation:

additional protections (shutter devices) on the cells of the socket are therefore not necessary.

The socket is suitable for the insertion of Italian standard plugs of the P11 type (2P) and American standard plugs (2P). The shaver socket is protected against overload with a thermal interruption device without auto-reclosing.

After the protection is tripped, the cells of the socket are not energized. To reclose the circuit, the plug of the device that caused the overload must be disconnected, waiting a few minutes in order to allow the transformer to cool down.

Technical specifications

Power supply	230 V~ 50-60 Hz
Output voltage	230 V~ for 2.5 A P11(2P) plugs 120 V~ for 15 A 125 V~ 2P plugs American standard with non-polarized flat pins
Available power	20VA
Operation with auto-protected	temperature

Reference standards

EN 61558-2-5, EN 61000-3-2, EN 55014-1, EN 55014-2.

Technical details

Mylos – Socket outlets

Special sockets outlets


Description	Code
Flush-mounted USB charger 2.1A, with male type A connector, power supply 230~ 50/60Hz, output voltage 5V DC	2CSY1162MC
	2CSY1162MS

Components



The flush-mounted USB charger allows you supply and recharge the most common portable electronic devices. With the simple use of a USB cable with Type A male connector it is possible to power mobile phones, smartphones, tablets and cameras that support standard USB power supply (up to 2100mA), independently of the manufacturer.

Wiring diagrams



Caution!
The device absorbs up to 60mW in the absence of connected electronic devices. To exclude this absorption, it is recommended to use a Double-pole switch.


Operating method

Connect the USB cable with the type A male connector to the charger and the opposite end to the device to be powered. Type A, B, miniUSB and microUSB USB connectors can be used indifferently. The device is now being charged.

Caution: the device supplies power according to the USB data transmission protocol, with a maximum current of 650 mA at 5V. Some devices may require a higher power supply current. Look up the manual of the connected device to check its absorption specifications.

The charging time depends on the connected device and may vary compared with the original charger.

Examples of application



Technical specifications

2CSY1162MC, 2CSY1162MS	
Power	100-230 V ~ 50/60 Hz
Maximum load consumption	224 mA a 100 V ~ • 120 mA a 230 V ~
Output voltage	5 V
Maximum load output	2,1 A
Performance	More of 77% (Energy Star EPS v.2)
No load consumption	2,5 mA a 100 V ~ • 3,5 mA a 230 V ~
Degree of protection	IP20
Operating temperature	0° C/+45° C (internal usage)
Storage temperature	-20 +80°C
Class device	Class II □
Overvoltage category (EN 62109)	CAT III

Technical details


Mylos – Socket outlets

TV/SAT sockets

The TV/SAT coaxial sockets for the Mylos series offer a complete range of products for implementing the terminal part of modern antenna systems. Manufactured fully from die cast Zama, they include a pressure terminal with safety screw in order to guarantee proper grip of the cable.

Individual sockets are available with male IEC or female F bushing, and double demixed sockets with both connection possibilities. Various levels of attenuation are available, ensuring that solutions are available for every type of installation.

Components



Attenuation values of the TV/SAT coaxial sockets

Code	Bushing	Passing attenuation [dB]			Bridging attenuation [dB]			Inverse attenuation [dB]	Direct current transit
		5÷40 MHz	47÷862 MHz	950÷2402 MHz	5÷40 MHz	47÷862 MHz	950÷2400 MHz		
2CSY1118MC/S	Male IEC Terr.	-	-	-	0.5	0.5	0.5	-	YES
2CSY1132MC/S	Male IEC Terr.	≤2	≤2	≤3	≤7	≤7	≤8	≥35	NO
2CSY1136MC/S	Male IEC Terr.	≤2	≤2	≤2.5	≤10.5	≤10	≤11	≥35	NO
2CSY1137MC/S	Male IEC Terr.	≤1.5	≤1.5	≤2.5	≤14.5	≤14	≤14.5	≥35	NO
2CSY1140MC/S	F Female	-	-	-	≤0.5	≤0.5	0.5	-	YES




Attenuation values of double demixed TV/SAT coaxial sockets

Code	Bushing	Passing attenuation [dB]		Bridging attenuation [dB]		Inverse attenuation [dB]	Direct current transit
		TV	SAT	TV	SAT		
2CSY1133MC/S	Male IEC Terr. F female SAT	-	-	≤2	≤2	-	YES
2CSY1130MC/S	Male IEC Terr. F female SAT	≤3	≤4.5	≤10	≤11	≥35	YES
2CSY1131MC/S	Male IEC Terr. F female SAT	≤2	≤3	≤14	≤15	≥35	YES

Technical details

Mylos – Socket outlets


Wiring diagrams



Technical details

Mylos – Socket outlets

Instructions for installation



Technical specifications

Frequency range	from 5 to 2400 MHz
Coaxial cable diameter	from Ø 5 to Ø 7 mm
Return channel	from 5 to 40 MHz
Shielding	class A
Wiring system	with front panel
Unequal chrominance/ luminance delay	< 1 ns for all models
Relative humidity	max 93% (non-condensing)

Reference standards

EN 50083-1, EN 50083-2, EN 50083-4


Technical details

Mylos – Socket outlets

Network and telephone sockets

The range includes devices for the implementation of telephone and computer networks, RJ11 4-contact telephone connectors for telephones, telefax, modems and RJ12 6-contact telephone connectors for intercommunicating telephone installations. RJ45 category 5e and 6 connectors are also available. These devices allow computer equipment (computers, modems, printers, etc) to be connected in a network and connection of multimedia devices.

Components



Code	Connector type	No. contacts	Cable type	Shielded	Category	Speed
2CSY1121MC/S	RJ11	4	twin core	NO	3	up to 16 Mb/s
2CSY1122MC/S	RJ12	6	twin core	NO	3	up to 16 Mb/s
2CSY1124MC/S	RJ45	8	UTP	NO	5e	up to 100 Mb/s
2CSY1127MC/S	RJ45	8	UTP	NO	6	up to 10 Mb/s
2CSY1128MC/S	RJ45	8	FTP	YES	6	up to 10 Mb/s

FTP = cable shielded with aluminium tape

UTP = unshielded cable

Instructions for installation

Unshielded connectors:

- wire the connector making sure that the connection terminals match;
- operate the lever wiring device on the connector;
- latch the connector on the adapter and proceed with the installation on the frame.

Shielded connectors:


- wire the connector making sure that the connection terminals match;
- position the cover of the connector and squeeze with pliers to make sure the contacts are tight;
- apply the shielding, ensuring insulation of the connector;
- latch the connector on the adapter and proceed with the installation on the frame.

Keystone adapter 2CSY1135MC/S


The structured wiring systems for data transmission are distinguished by their flexibility of use, installation independent of location and the use of the terminal outputs. The suppliers of components for wiring, when dealing with installations of a certain complexity and size, must be in able to show certification of conformity of the installation, directly or through accredited installations.

ABB meets this requirement with the adapter of the Mylos wiring accessorie's range, which is compatible with various Keystone coupling connectors available on the market and enables integration between the Mylos wiring accessories range and data transmission components of systems with structured wiring.


- latch the connector on the adapter and proceed with the installation on the support.



Unshielded connectors



Shielded connectors




Keystone adapter 2CSY1135MC/S


Technical details

Mylos – Socket outlets

Wiring diagrams for RJ11 and RJ12 telephone connectors




Connection in series




Terminals 3 and 4 are connected via the internal contact to the telephone (closed with the receiver hung up). Lifting the receiver causes interruption of the downstream line (L1), guaranteeing secrecy of the conversation.

Connection in parallel






Each socket captures the line signal (there is no secrecy of conversation).



Note: extracting one of the plugs causes disconnection of sockets located downstream. In order to prevent this, you just need to insert a plug in the socket from which the telephone device was removed with a jumper between terminal 4 and 5.

Wiring diagrams for RJ45 data connectors

To obtain the EIA/TIA 568A or 568B configuration included below, follow the colour code shown on the terminal box.



Technical specifications

Connections With perforated insulation

Conductors non-butted, inserted in the appropriate blade slots

Reference standards

EN 50083-1, EN 50083-2, EN 50083-4, ISO 11801.

Technical details

Mylos – Protection devices

Fuse holder

Description	Code
Fuse holder, Ø5x20 / Ø6.3x32, 16A	2CSY1301MC
	2CSY1301MS


Components



Removable cover for removal of the fuse

Replacement of the fuse

After removing the removable cover with a screwdriver, proceed with replacement as in the drawing:



Replacement fuses

Fuses with dimension Ø5x20mm or Ø6.3x32 mm can be installed.

The use of the fuses on page 4/23 is recommended.


Technical details

Mylos – Protection devices

Surge protection device limiter

Description	Code
Surge protection device limiter 75J, 250V~	2CSY1302MC
	2CSY1302MS


Components



This device provides protection for power supply sockets for all types of household appliances and in particular for those containing electronic components (Hi-Fi, TV, computers, video recorders, programming mechanisms, cash registers etc.) from damage caused by over-voltages present in power supply networks.

Instructions for installation and operation

The protection device is housed in the removable front cover. To replace it, after disconnecting the voltage from the installation, extract the cover from the limiter and separate the SPD block from the plastic cover, levering it with a screwdriver. Replace it with spare part 2CSY1302MY.




Functions


When the red warning light is on, it indicates that the protection has tripped and needs to be replaced (the load remains energised but it is not protected).

Examples of application

Over-voltages in domestic networks can be caused both by atmospheric interference and by control, operation or programming of connected inductive loads (air conditioners, burner motors, water pumps, reactors of fluorescent or discharge lamps, washing machines, etc.).



Wiring diagram



Technical specifications

Residual current limiting	protection (line-to-neutral)
Rated voltage (Un)	120-230 V~ 50/60 Hz
Number of ports	1
Rated load current IL	16 A
Max steady current (Uc)	250 V~
Test class	III
Protection level (Up)	< 1.2 kV
Test voltage of combined wave generator Uoc	2.5 kV
Rated flashover current (In)	1 kA (8/20 ns) 20 times
Max flashover current (Imax)	2 kA (8/20 ns) once
Temperature range	-5 °C - +40 °C
Internal integrated protection	fuse

Reference standards

LV Directive, Standard EN 61643-11

Technical details

Mylos – Safety and comfort devices


Loads that can be controlled with the dimmer

Dimmer type	Loads	Fluorescent filament or halogen lamps 230V	Fluorescent lamps	Toroidal transformers	Electronic transformers	Electro-mechanical transformers	Drills	Air agitators
Dimmer code	Description							
2CSY1205MC	Electronic dimmer with rotary control	YES	NO	NO	NO	NO	NO	NO
2CSY1205MS								
2CSY1206MC	Electronic dimmer with button control	YES	NO	YES	NO	YES	NO	NO
2CSY1206MS								
2CSY1207MC	Electronic dimmer with rotary control and two-way switch	YES	NO	NO	NO	NO	NO	NO
2CSY1207MS								

Dimmer

Description	Code
Electronic dimmer with rotary control for resistive loads 100-500W 230V~ 50/60Hz	2CSY1205MC
	2CSY1205MS

Components



Electronic dimmer with rotary control for resistive loads 100-500W 230V~ 50/60Hz (visible in the dark).

Operation


The load can be controlled and adjusted by rotating the knob.

The light intensity of the location LED is attenuated as the brightness of the controlled lamps increases.


Wiring diagram

The connection can be made between phase and neutral or between phase and phase, always in series with the load.

Control with dimmer



Control with a switch and adjustment with a dimmer



Technical specifications

Rated voltage	230V - 50/60Hz	110V - 50/60Hz
Resistive load power	100 - 500W	50 - 250W
Inductive load power	100 - 500VA	50 - 250VA
Technology	TRIAC	TRIAC
Operating temperature	-5 °C ÷ +35 °C.	
Adjustable load	Filament and halogen lamps	

Reference standards

CEI 23-9 (EN 60669-1)

Technical details

Mylos – Safety and comfort devices
Flush-mounted pluggable emergency light



2CSY218762R1236
Supplied with their supports

Compliance with
the following
EU Directives:
2014/35/UE (Low Voltage)
2014/30/UE (EMC)
2011/65/EU (RoHS)

User manual

Read all instructions carefully

The 2-module pluggable blackout lamp is an electronic emergency lamp for flush-mounted boxes installation. It turns on to enlightening areas where it is installed if a blackout occurs. The lamp can be unplugged and used as a portable torch; once unplugged it turns on automatically until it is plugged again into its back shell.


Safety warnings

During installation and operation the following indications must be respected:

1. The product must be installed by qualified personnel in strict compliance with the connection diagrams.
2. Do not power the product if any part is damaged.
3. The product must be installed and commissioned in compliance with the regulations concerning electrical systems.
4. Do not use the product for purposes other than those indicated.
5. In case of fault do not repair the product.
6. The product can be used in overvoltage category III and pollution degree 2 environments.
7. An overcurrent protection device must be installed in the electrical system upstream of the product.
8. After installation, the inaccessibility to the connection terminals without special tools must be guaranteed.
9. Check that conductors are not live before accessing the connection terminals.


Technical features

Connection scheme



Power supply:	230 V AC (-10% ÷ +10%) 50/60 Hz
Absorption:	3 VA (0,2 W)
Backup batteries:	1 rechargeable NiMH battery (not replaceable) - 3.6V & 140mAh full recharge time: 48 hours
Autonomy in event of power failure:	2 hours approx
Light source:	Light intensity: 20 lumens Beam angle: 120°
Red LED:	for low battery or fault indication
Installation:	on 45mm height flush-mounted box (footprint: 2 modules)
Terminal block:	for 1.5 mm ² cables
Operating temperature:	0°C ÷ +50°C
Storage temperature:	-20°C ÷ +50°C
Operating humidity:	20÷90% non-condensing
Protection:	IP40
Insulation:	reinforced between accessible parts (front) and all other terminals


Dimensions




1. Move the selector from the storage position (0) to the operating position (1)
2. Plug the lamp into the back shell
3. Connect the power supply wires to the terminals
4. Plug the lamp + back shell

Lamp extraction

1. Press the lamp: an audible click will be heard to indicate that the sealing mechanism has released the lamp.
2. Pull the lamp out of the back shell



Assembly drawing in Mylos frame



Technical details

Mylos – Safety and comfort devices
Flush-mounted motion detector



2CSY279081R1626 white
2CSY226581R1626 black
Supplied with their supports

Compliance with the following EU Directives:
2014/35/UE (Low Voltage)
2014/30/UE (EMC)
2011/65/EU (RoHS)

User manual

Read all instructions carefully


The ABB's motion detector is a flush-mounted twilight motion detector that senses all the movements in its active field and triggers the lighting system for a predetermined period only if the brightness level is lower than a pre-set threshold. It performs type 1B actions and is intended for use in environments with overvoltage category III and pollution degree 2, according to EN 60669.

Safety warnings

During installation and operation the following indications must be respected:

1. The product must be installed by qualified personnel in strict compliance with the connection diagrams.
2. Do not power the product if any part is damaged.
3. The product must be installed and commissioned in compliance with the regulations concerning electrical systems.
4. In case of fault do not repair the product.
5. An overcurrent protection device must be installed in the electrical system upstream of the product.
6. After installation, the inaccessibility to the connection terminals without special tools must be guaranteed.
7. Check that conductors are not live before accessing the connection terminals.

Connection scheme




Connectable loads
- Incandescent 800 W
- Fluorescent (neon) 200 VA
- Low voltage halogen 500 VA
- Halogen 230 V~ 800 W
- Low consumption (CFL) 200 VA
- Led 200 VA

Technical features

Power supply:	230 V AC (-10% ÷ +10%) 50/60 Hz
Maximum absorption:	5 VA (1 W)
Output:	NO relay with breaking capacity of 5A/250V (on resistive load) with "zero crossing" technology
Tripping time:	5 seconds (test), 30 seconds ÷ 15 minutes
Tripping brightness:	5 ÷ 100 lux
Detection angle:	110° at 20°C
Detection field:	7 meters at 20°C
Installation:	on flush-mounted box with 45 mm height (dimensions: 1 module)
Terminal block:	for 1.5 mm² cables
Operating temperature:	0°C ÷ +35°C
Storage temperature:	-10°C ÷ +60°C
Operating humidity:	20÷90% non-condensing
Protection:	IP40 (on accessible parts)
Insulation:	reinforced between accessible parts (front) and all other terminals

Dimensions



Installation

To be installed in the flush-mounted box the motion detector requires 1 module footprint. High temperatures reduce the sensitivity of the sensor: avoid installation close to heat sources, air vents or devices

that can rapidly change their temperature. For installation, consider that the detector is more sensitive to movements cross the detection field than movements in the direction of the detector itself.

is reached, turn the brightness control dimmer (◎) clockwise until the relay triggers.

Operations

Detector test
The test verifies the correct operations of the IR sensor and relay. Turn the brightness control (◎) clockwise to the maximum range (100 lux) and the timing regulator (◎) anticlockwise to the minimum range (5 seconds). Check that the relay triggers when a movement is spotted inside the detection field.

Brightness adjustment
This regulation (◎) sets the lower brightness threshold for the relay to trigger if a movement is detected. Turn the brightness control (◎) anticlockwise to the minimum range: in this position the relay will remain inactive with daylight. Toward dusk, when the brightness threshold for relay activation

Note. The timing can be 5 seconds or between 30 seconds and 15 minutes. The minimum setting value of the regulator (◎) corresponds to 5 seconds; a minimum clockwise rotation brings the timing to 30 seconds. Continue to rotate the regulator clockwise to increase timing values up to a maximum of 15 minutes.

Technical details


Mylos – Safety and comfort devices
Flush-mounted emergency light



2CSY218902R1235
Supplied with their supports

Compliance with the
following EU Directives:
2014/35/UE (Low Voltage)
2014/30/UE (EMC)
2011/65/EU (RoHS)

Connection scheme



User manual

Read all instructions carefully

The 1-module anti-blackout lamp is a non-pluggable electronic emergency lamp for flush-mounted boxes installation. It turns on to enlightening areas where it is installed if a blackout occurs and guarantees a constant output for more than two hours thanks to its rechargeable battery.

Safety warnings


During installation and operation the following indications must be respected:

1. The product must be installed by qualified personnel in strict compliance with the connection diagrams.
2. Do not power the product if any part is damaged.
3. The product must be installed and commissioned in compliance with the regulations concerning electrical systems.
4. Do not use the product for purposes other than those indicated.
5. In case of fault do not repair the product.
6. The product can be used in overvoltage category III and pollution degree 2 environments.
7. An overcurrent protection device must be installed in the electrical system upstream of the product.
8. After installation, the inaccessibility to the connection terminals without special tools must be guaranteed.
9. Check that conductors are not live before accessing the connection terminals.

Technical features

Power supply:	230 V AC (-10% ÷ +10%) 50/60 Hz
Absorption:	2,5 VA (0,1 W)
Backup batteries:	1 rechargeable NiMH battery (not replaceable) - 3.6 V & 140 mAh full recharge time: 48 hours
Autonomy in event of power failure:	2 hours approx
Light source:	1 white LED Light intensity: 2400 mcd Beam angle: 120°
Red LED:	for low battery indication
Installation:	on 45mm height flush-mounted box (footprint: 1 module)
Terminal block:	for 1.5 mm ² cables
Operating temperature:	0°C ÷ +40°C
Storage temperature:	-20°C ÷ +40°C
Operating humidity:	20÷90% non-condensing
Protection:	IP40
Insulation:	reinforced between accessible parts (front) and all other terminals

Dimensions



Installation


The emergency lamp requires 1 module footprint to be installed in the flush-mounted box.

The emergency lamp is supplied with the battery installed (not removable) and charged. To prevent the battery from discharging during storage, a jumper on the back insulates the battery from the circuit. Before installing the lamp, move the jumper from "0" to "I" position.

Note: if the jumper interferes with the back of the flush-mounted box when plugging the lamp, cut the protruding part (as indicated).

Respect the connection diagram.

If the red LED on the front of the emergency light is on, the battery is low.




Technical details

Mylos – Safety and comfort devices

Dimmer

Description	Code
Electronic dimmer with pushbutton control for resistive and inductive loads 60-500W (60-500VA) 230V~ 50/60Hz	2CSY1206MC
	2CSY1206MS

Components



Electronic dimmer with pushbutton control for resistive and inductive loads 60-500W 60-500VA 230V~ -50/60Hz (visible in the dark).


Operation

- The load can be controlled and adjusted using a pushbutton. The light intensity of the location LED is attenuated as the brightness of the controlled lamps increases.
- The load can be turned on, adjusted and turned off using the pushbutton present on the dimmer or with normal non-luminous NO pushbuttons connected to the dimmer.
- Storage of the adjustment set when the load was switched off (apart from network outages).
 - Switch-on and switch-off of the load is gradual.
 - Pressing the pushbutton quickly causes the load to be switched on or off. Adjustment is obtained by keeping it pressed. To reverse the direction of adjustment, interrupt and then resume pressing the pushbutton.
 - If the pushbutton is pressed approximately between 0.3 s and 1 s, the dimmer will light up the controlled lamps, automatically and gradually, to their maximum brightness.


Wiring diagram

The connection can be made between phase and neutral or between phase and phase, always in series with the load.

Control and adjustment with a dimmer pushbutton



Control and adjustment with a dimmer pushbutton and NO button connected in parallel



Technical specifications

Rated voltage	230V - 50/60Hz	110V - 50/60Hz
Resistive load power	60 - 500W	30 - 250W
Inductive load power	60 - 500VA	30 - 250VA
Technology	TRIAC	TRIAC
Operating temperature	-5 °C ÷ +35 °C.	
Adjustable load	Filament and halogen lamps, ferromagnetic transformers for halogen lamps	

Reference standards

CEI 23-9 (EN 60669-1)


Technical details

Mylos – Safety and comfort devices

Dimmer

Description	Code
Electronic dimmer with rotary control and two-way switch for resistive loads 100-500W 230V~ 50/60Hz	2CSY1207MC
	2CSY1207MS

Components



Electronic dimmer with rotary control and two-way switch for resistive loads 100-500W 230V~ -50/60Hz (visible in the dark).


Operation

The load is controlled directly by means of a pressed two-way switch. Adjustment is performed by rotating the knob. The light intensity of the location LED is attenuated as the brightness of the controlled lamps increases. Once the desired lighting level has been set, pressing the knob will switch the light source off, while pressing it again will switch it back on at the set lighting level.


Wiring diagram

The connection can be made between phase and neutral or between phase and phase, always in series with the load.


Control and adjustment with a dimmer



Control with two-way switch and dimmer, adjustment with dimmer



Control with two-way switch, intermediate switch and dimmer, adjustment with dimmer



Technical specifications

Rated voltage	230V - 50/60Hz	110V - 50/60Hz
Resistive load power	100 - 500W	50 - 250W
Inductive load power	100 - 500VA	50 - 250VA
Technology	TRIAC	TRIAC
Operating temperature	-5 °C ÷ +35 °C.	
Adjustable load	Filament and halogen lamps	

Reference standards

CEI 23-9 (EN 60669-1)


Technical details

Mylos – Safety and comfort devices

Gas detectors

Description	Code
Natural gas electronic detector with acoustic and luminous signal, relay output, 1 NO/NC change-over contact 6A (AC1)/2A (AC15) - 250V~. Power supply 230V~ - 50Hz. Equipped with dedicated frame for installation on type 503 box.	2CSY1210MC
LPG gas presence electronic detector with acoustic and luminous signal, relay output, 1 NO/NC change-over contact 6A (AC1)/2A (AC15) - 250V~. Power supply 230V~ - 50Hz. Equipped with dedicated frame for installation on type 503 box.	2CSY1211MS


Components




The wiring accessories' natural gas (CH4) or LPG gas detectors, flush-mounted with 3 modules (503 box) contribute to guaranteeing the safety of civil environments where gas operated domestic appliances are installed, such as: boilers, cookers. The equipment consists of a fixed power supply module and removable sensor module, which must be replaced after 5 years of continuous use. This allows a saving on the purchase and installation costs, with a lower impact on the environment due to the extension of the life time of the power supply/relay module for a further 5 years.

Positioning of the detector

The installation of the gas detector does not exonerate users from observance of all current laws and standards in the country of installation regarding the specifications, installation and use gas powered equipment, the ventilation of rooms and the release of combustion products.



- Install the natural gas detector at a maximum of 30 cm from the ceiling
- Install the LPG detector at a maximum of 30 cm from the floor surface.
- Install the detectors between 1 m and 4 m from the gas appliances..
- Do not install the detectors outdoors or in places exposed to atmospheric agents
- Do not install the detectors close to: sinks, air intakes, heating and air conditioning devices, windows and ventilation devices; in addition, the detectors must not be installed in closed spaces, such as behind a curtain or inside a cabinet.



Illustrative example: installation with 3 gas detectors (natural gas) that command the solenoid valve for shutting off the gassupply.


Technical details

Mylos – Safety and comfort devices

IR receiver for remote control


Description	Code
IR receiver for remote control, 1-channel, 230V~	2CSY1217MC
	2CSY1217MS

Components



IR receiver with 1 channel. This device allows operating commands to be received that are generated by a dedicated remote control, sold separately (code 2CSE1217EL). The active signal bandwidth of the remote control is selected by a dip-switch on the receiver (1 receiver for every channel of the remote control).

Wiring diagram



* 6.3 x 32 mm - 6.3A - 500 V (quick)
P.I. ≥ 1500A


Technical specifications

Operating temperature	-5 ÷ + 45 °C
Protection class	indoors, dry
Max load	16A resistive
Place of use	indoors, dry

Reference standards

CEI 64-8

Examples of application



Technical details


Mylos – Safety and comfort devices

Universal badge switch


Description	Code
Universal badge switch with location light	2CSY1426MC
	2CSY1426MS

Vertical badge electronic switch, relay output 16 A 250 V~, power supply 230 V~ 50-60 Hz, modules. Supplied without ISO card (badge). The device is equipped with a courtesy LED for night-time localization.


Components



Operation



Wiring diagram



Technical specifications

Power supply	230 V~ ±10% 50-60 Hz
Output	relay with clean contact 10 A, 250 V~ cos φ 1
Typical absorption	230 V~ 50-60 Hz: 30 mA, con relè attivo
Operating temperature	-5 °C +45 °C

Reference standards

LV Directive; EMC Directive; Standard EN 60669-2-1

Technical details

Mylos – Frames

Mylos frames feature an under-plate that guarantees maximum adhesion to every type of surface and allows the application of finishing materials, while maintaining minimal protrusion from the wall.

The under-plate is black except for the Pure White finishes, where it is white in order to guarantee maximum integration with the wall.

In the 4+4 module frames, the separator is painted with a white or black velvet finish.



Under-plate that adheres to all surfaces



43 ÷ 8.2 mm



White under-plate for maximum integration with the wall



Reference standards

CEI 23-9 (EN 60669-1).

Customization



All the Mylos frames are provided with a internal chromium plated internal trim, except for frames with a Pure White finish (white velvet paintwork). On request, it is also possible to get frames with a trim painted in the following colours:



White velvet



Black velvet




Glossy gold

Minimum order batch: 200 pieces including various modularities.

For quotes and delivery times contact the local ABB salesman.

Frames customized with a logo/text string can be supplied on request. They are produced by means of monochromatic pad printing on the highlighted areas.



Position 2
Logo inside a rectangle
10 mm in height and 45 mm in length

Positions 1-3-4-5
Logo in square with 13 mm sides.

Customization possible with standard colours (black, Pantone Cool Gray 3 C, Pantone 5425 C) or with a colour specified by the customer.

Minimum order batch: 36 pieces including various modularities.

For quotes and delivery times contact the local ABB salesman.

Application

Discover all the combinations and possibilities for customization of the Mylos series with the new dedicated app!



Download the application
for iPhone (Italian only)

Technical details

Chiara – General information

Main technical data and reference standards for the devices in the range

Component	Reference standards	Basic electrical data*			Prolonged operation	Resistance to abnormal heat and fire	
		Test voltage withstand (V)	Insulation resistance (MW)	Breaking capacity or utilization category		No. changes of position	Termopressione con biglia (°C)
Operating mechanisms	CEI 23-9 (EN 60669-1)	2000 at 50Hz for 1 minute	> 5	1.25 In (200 changes of position)	40000 at In 250V~ cosφ = 0,6)	125	850
Socket outlets	CEI 23-5/CEI 23-50/CEI 23-16 (EN 60884-1)	2000 at 50Hz for 1 minute	> 5	1.25 In (100 changes of position)	10000 at In 250V~ cosφ = 0,8)	125	850
Latching relay	CEI 23-9/CEI 23-62 (EN 60669-1/EN 60669-2-2)	2000 at 50Hz for 1 minute	> 5	-	50000 a In 250V~ cosφ = 0,6)	125	850
Monostable relays	CEI 94-4/CEI-EN 61810-1 (EN 60669-1/EN 60669-2-2)	2000 at 50Hz for 1 minute	> 5	1.25 In (200 changes of position)	50000 at In 250V~ cosφ = 0,6)	125	850
Automatic MCBs	CEI 23-3 (EN 60898)	2000 at 50Hz for 1 minute	-	1.5...3kA	8000	125	850
Automatic RCDs	CEI 23-95	2000 at 50Hz for 1 minute	-	1.5...3kA	4000	125	850
Supports and frames	CEI 23-9 (EN 60669-1)	-	-	-	-	75	650

*For the rated voltages and currents see the specifications for the individual part codes.

Clamping capacity of the terminals

Flexible wires	Rigid wires
Min. 0.75 mm ²	Max. 2x4 mm ²


Cable traction resistance of terminals: > 50N

Adhesion of switches and device to the support: > 0.6J


Technical details

Chiara – General information

Composition method for devices and supports



Installing and removing switches from the support



- Frontal installation of the switches on the frame
- Modularity of the switches: 22 mm

Specifications of screws and terminals

- Captive screws with open position captive screws with cross and slot head and clamping plate.
- Double input protected terminals for one or two conductors (rigid or flexible).

Technical details

Chiara – Installation solutions


Installation on concrete walls



No. modules	Screw distance	Recommended box
2 (with claws)	-	00 050
2 (with screws)	60 mm	00 050
3	83.5 mm	1SL006A00
4	108 mm	00 053
7	100 mm	1SL0064A00

Note: For further information on ABB boxes for concrete walls please refer to the catalog 1SLC001001D0905 - Insulating Enclosures and Installation Materials.

Installation of plasterboard walls



No. modules	Screw distance	Recommended box
2 (with screws)	-	10801/10802/10807
2 (with claws)	60 mm	10801/10802/10807
3	83.5 mm	10804
4	108 mm	Ave 254CG, BTicino PS564N, Gewiss GW24245 Vimar V71604
7	100 mm	Bticino PS567N Gewiss 24246 Vimar V71606

Note: For further information on ABB boxes for plasterboard walls please refer to the catalog 1SLC001001D0905 - Insulating Enclosures and Installation Materials.

Technical details

Chiara – Installation solutions

Protected installation with IP40/55 wall-mounted enclosures



IP40 wall-mounted enclosure

IP55 wall-mounted enclosure

No. Modules	IP40 enclosure	IP55 enclosure
1 (on 2-module enclosure)	2CSK2140CH	2CSK2155CH
2	2CSK2240CH	2CSK2255CH
3	2CSK2340CH	2CSK2355CH
4	2CSK2440CH	2CSK2455CH

The watertight enclosures allow the direct assembly of devices without the aid of supports. The devices are inserted from the rear. See technical details. For further information on IP40/IP55 wall-mounted enclosures, please refer to the catalog 1SLC001001D0905 - Insulating Enclosures and Installation Materials.

Protected installation with watertight escutcheon plate



IP55 wall-mounted escutcheon plate

No. Modules	IP55 escutcheon plate
2 (on a square or round box with screws, center distance 60mm)	2CSK3255CH
3	2CSK3355CH

Note: The watertight escutcheon plates provide a self-supporting solution that allows direct assembly of devices without the aid of supports. The devices are inserted from the rear.

Technical details

Chiara – Installation solutions

Installation on raised floors with Undernet under-floor turrets



No. Modules	Dedicated adapter	Undernet tower
5 (max 20 contact blocks)	2CSK1625CH	10900 e 10901
6 (max 12 contact blocks)	2CSK1626CH	10902 e 10903

Note: The dedicated adapter provides a self-supporting solution that allows direct assembly of devices without the aid of supports. The devices are inserted from the rear. The use of finishing plates is not required.

For further information on Undernet under-floor turrets, please refer to the catalog 1SLC006001D0903 - Under-floor Distribution Systems.

Installation on surface mounted boxes



No. Modules	Wall box	Frame
2	42 096	Use a 2M self-supporting frame
3	41 823	Use a 3M self-supporting frame
3	41 822	Use a 3M self-supporting frame
4	41 830	Use a 4M self-supporting frame

Note: The self-supporting frames allow the direct assembly of devices without the aid of supports. The devices are inserted from the rear.

For further information on the wall boxes and duct systems, please refer to the catalog 1SLC800001D0905 - Plastic and Metal Duct Systems.

Technical details

Chiara – Installation solutions


Installation on Lusy table towers



No. Modules	Lusy tower	Frame
4	10 507	Use a 4M self-supporting frame

Note: The self-supporting frames allow the direct assembly of devices without the aid of supports. The devices are inserted from the rear.
For further information on the Lusy table towers, please refer to the catalog 1SLC006001D0903 - Under-floor Distribution Systems.

Installation on DIN rail adapter



No. Modules	Dedicated adapter
1	2CSK1608CH
2	2CSK1608CH
3	2CSK1608CH


Note: The DIN rail adapter allows devices to be assembled without the aid of supports. The devices are inserted from the front. See technical details.

Technical details

Chiara – Selection of lights

Control devices	Lamps
2CSK1001CH Single-pole switch, 16A - 250V~	
2CSK1002CH Double-pole switch, 16A - 250V~	
2CSK1004CH Single-pole switch, 16A - 250V~, 2 modules	
2CSK1003CH Single-pole two-way switch, 16A - 250V~	
2CSK1007CH Single-pole two-way switch, 16A - 250V~, 2 modules	
2CSK1010CH Intermediate switch, 16A - 250V~	
2CSK1008CH Intermediate switch, 16A - 250V~, 2 modules	
2CSK1005CH Single-pole push switch NO, 16A	
2CSK1016CH Single-pole push switch NC, 16A	
2CSK1020CH Single-pole push switch NO with cord pull, 16A with 2.25 m cord	LED lamp 2CSK1616CH White
2CSK1021CH Single-pole push switch NC with cord pull, 16A with 2.25 m cord	230V 0.4W
2CSK1022CH Single-pole push switch 1 NO and 1 NC, 16A, with ON	
2CSK1023CH Single-pole push switch 1 NO and 1 NC, 16A, with OFF symbol	
2CSK1024CH Single-pole push switch NO, 16A, with red diffuser	
2CSK1025CH Single-pole push switch NO, 16A, with green diffuser	
2CSK1026CH Single-pole push switch NO, 16A, with orange diffuser	
2CSK1027CH Single-pole push switch NO, 16A, with white diffuser	
2CSK1028CH Single-pole push switch NO, 16A, with BELL	
2CSK1029CH Single-pole push switch NO, 16A, with KEY	
2CSK1030CH Single-pole push switch NO, 16A, with STAIR LIGHT	
2CSK1031CH Single-pole push switch NO, 16A, with backlit label holder plate	
2CSK1032CH Single-pole push switch NO, 16A, with backlit label holder plate, 3 modules	

Signalling devices	Lamps
2CSK1310CH Warning light, ORANGE colour	LED lamp 2CSK1616CH White
2CSK1311CH Warning light, WHITE colour	230V
2CSK1312CH Warning light, RED colour	0.4W
2CSK1313CH Warning light, GREEN colour	



Technical details

Chiara – Control devices

Switches, two-way switches, intermediate switches and pushbuttons

Area of application

Control (on and off) of ohmic-inductive loads:

- with filament and fluorescent lamps (corrected and uncorrected);
- dedicated circuits for powered equipment (aspirators, range hoods, shutters, blinds, fans, etc..) and controllable outlets.

To eliminate architectural barriers in creating installations, we recommend the use of luminous controls (Article 4 of Italian Ministerial Decree no. 236 del 14.06.1989).

Technical specifications

Rated voltage	250V~
Rated current	10A (16A for pushbuttons)
Opening distance of the contacts	> 3 mm
Dielectric strength	> 2000V~

Reference standards

LV Directive EN 60669-1.

Customization of the control device keys

The illuminable keys of the Chiara wiring accessories' range are supplied with all most widely used functional symbols.

Wiring diagrams

The diagrams provided below are the most widely applied installation solutions in creating lighting points.

Backlighting of the control devices

Night-time location

Characteristics

- It allows the command key to be identified in the dark.
- We recommend the use of white, blue, green or red Chiara lamps.

Applications

- Bedrooms
- Corridors

Functional signalling

Characteristics

- This allows the command key to be identified and the ON/OFF status of a circuit to be signalled in the dark.

Applications

- General services of a building complex (entrance halls, stair lights, landings etc.)
- Public environments (cinemas, theatres etc.)

Signalling with symbols

Characteristics

- This allows the command key and its specific function to be identified in the dark.

Applications

- Warehouses, shops, offices
- Hotels
- Nursing homes, hospitals

With warning light

Characteristics

- Allows the ON/OFF status of an appliance or a lighting circuit, even at a distance.
- Visible from both a front and side position.


Applications

- Signalling the switching on of lighting points outside the environment in which the control device is installed


Technical details

Chiara – Control devices

Example of functional signalling




Warning light on when the switch is OFF (if the switch is in the ON state, the warning light is off while the load is ON).




The two warning lights switch on and off respectively when the load is in the OFF and ON state.

Example of remote signalling



Warning light placed in parallel to the load, of which indicates the ON/OFF state (it is on when the switch is ON).



Two warning lights placed in parallel with the load (they switch on and off with it).

Instructions for installation in systems with relays and illuminable push switches

The lamps must be connected in parallel.

Using single-pole latching relays 2CSK1012CH, it is possible to connect up to four fluorescent lamps: by adding a $0.94\mu F$ capacitor to the heads of the relay, up to twelve fluorescent lamps can be connected.

Using double-pole latching relays 2CSK1014CH, it is possible to connect two fluorescent lamps: by adding a $1.41\mu F$ capacitor to the heads of the relay, up to twelve fluorescent lamps can be connected.

Technical details

Chiara – Control devices

Relays

Relay with latching operation for control and adjustment from multiple lamp points by means of single-pole push switches with NO (normally open) contact.

Technical specifications


Power supply voltage (coil)	230V - 50/60Hz
Output contact	2CSK1012CH 1NO / 2CSK1014CH 2NO; 10A (AC1) / 7A (AC15) - 250V~

Reference standards


EN 60669-1, EN 60669-2-2.

Wiring diagrams

2CSK1012CH





2CSK1014CH



Examples of application

The flush-mounted relays of the Chiara wiring accessories' range can be used to implement numerous functions. The example illustrates a disabled bathroom calling system with cancellation via a key operated push switch:



Technical details

Chiara – Socket outlets

Plug sockets

Area of application

Powering of household appliances, lighting equipment etc.

Main features Italian and German standard sockets.

The cells of the sockets are segregated and protected when the plug is disconnected: the live parts are accessible only with the corresponding plug fully inserted.

Possibility of coupling Chiara sockets with the various types of plugs on the market

2P, 10A	2P, 2,5A	2P+T, 10A	2P, 16A	2P+T, 16A	Schuko 2P+T, 16A	American 2P, 15A

Plug sockets, 250V~, Italian standard with safety shutters

	P 11	■	■	■		
	2CSK1101CH					
	P 17			■	■	
	2CSK1102CH					
	P 17/11	■	■	■	■	■
	2CSK1103CH					

Plug sockets, 250V~, Italian/German standard with safety shutters and side/central earth

	P 30	■	■	■		■
	2CSK1108CH					
	P 30/17	■	■	■	■	■
	2CSK1109CH					

Interlocked socket outlets with automatic MCB

	P 17/11	■	■	■	■	■
	2CSK1324CH					
	P 30	■	■	■		■
	2CSK1325CH					

Special sockets

	Shaver socket ⁽¹⁾	■	■			■
	2CSK1113CH					

⁽¹⁾ Shaver socket, European/American standard with insulating transformer 230V~ - 50/60 Hz

Technical specifications

Rated voltage	250V~
Rated current	10A o 16A
Shuttered and elastic live cells	

Reference standards

CEI 23-5, CEI 23-50, CEI 23-16 (IEC 60884-1).

Note: In general terms, no plug sockets of any standard for domestic use fall under the European low voltage directive, because there is no harmonized European standard for these types of sockets: in fact, each country has its own standard and therefore a single standard is impossible. For this reason the plug sockets do not bear the CE mark. All the sockets of the Chiara wiring accessories' range conforming to CEI 23-50 are however certified by IMQ as a further guarantee of their quality and compliance with standards.

Technical details

Chiara – Socket outlets

Plug sockets for dedicated lines

Plug sockets for dedicated lines allow outlet points to be differentiated according to their particular application, avoiding incorrect connection of unsupported appliances. Different coloured enclosures (red, orange, green) distinguish them from common power sockets. There are as yet no standard regulations on the correspondence between the colour of the socket and the type of power supply. In order to distinguish the area of application, the following usage customs are adopted.

Red:

continuous power supply with UPS (uninterruptible power supply) through an insulating transformer.

Orange:

power supply protected by network-generator unit through an insulating transformer.


Green:

safety power supply with network/generator unit.

Special sockets

Description	Code
2P shaver socket with insulating transformer. Power supply 230V~ - 50/60Hz. Output voltage 125V~ (American standard 2P socket) or 230V~ (2P socket P11 type)	2CSK1113CH

Components



The shaver socket incorporates an insulating transformer with a power rating of 20 VA, protected against overload and resistant to short-circuits.

Power supply is guaranteed by a pushbutton that is operated automatically whenever the plug is inserted in the socket.

The secondary circuit, to which the cells of the socket are connected, is isolated from the primary power supply circuit by double insulation:

additional protections (shutter devices) on the cells of the socket are therefore superfluous.

The socket is suitable for the insertion Italian standard plugs of the P11 type (2P) and American standard plugs (2P). The shaver socket is protected against overload with a thermal interruption device without auto-reclosing. After the protection is tripped, the cells of the socket are not energized. To reclose the circuit, the plug of the device that caused the overload must be disconnected, waiting a few minutes in order to allow the transformer to cool down.

Technical specifications

Power supply	230 V~ 50-60 Hz
Output voltage	230 V~ for plugs P11(2P) 2,5 A 120 V~ for plugs 2P 15 A 125 V~ American standard with non-polarized flat pins
Available power	20VA
Operation with auto-protected	temperature

Reference standards

EN 61558-2-5, EN 61000-3-2, EN 55014-1, EN 55014-2.

Technical details

Chiara – Socket outlets


Description	Code
Flush-mounted USB charger 500-650mA, with male type A connector, power supply 230~ 50/60Hz, output voltage 5V DC	2CSK1160CH

Components



The flush-mounted USB charger allows you supply and recharge the most common portable electronic devices. Using only a USB cable with Type A male connector it is possible to power mobile phones, smartphones, tablets and cameras that support standard USB power supply (up to 650mA), independently of the manufacturer.

Wiring diagrams



Caution!
The device absorbs up to 60mW in the absence of connected electronic devices. To exclude this absorption, it is recommended to use a double-pole switch.


Operating method

Connect the USB cable with the type A male connector to the charger and the opposite end to the device to be powered. Type A, B, miniUSB and microUSB USB connectors can be used indifferently. The device is now being charged.

Caution: the device supplies power according to the USB data transmission protocol, with a maximum current of 650mA at 5V _____. Some devices may require a higher power supply current. Look up the manual of the connected device to check its absorption specifications.

The charging time depends on the connected device and may vary compared with the original charger.

Examples of application



Technical specifications

Power supply	125-250V - 50/60 Hz
Input current	5A 230V
Output current	500-650mA at 5V DC
Max absorption in standby	60mW
Operating temperature	-20 +50°C
Storage temperature	-20 +80°C
Protection class	IP20
Place of use	indoors, dry
The device is protected against short-circuits by an internal fuse (not replaceable).	

Technical details


Chiara – Socket outlets

Interlocked socket outlets

Description	Code
2P+E socket outlet, 16A - 250V~, interlocked with MCB, P17/11	2CSK1324CH
2P+E socket outlet, 16A - 250V~, interlocked with MCB, P30	2CSK1325CH
2P+E socket outlet, 16A - 250V~, with RCD 10mA, P17/11	2CSK1326CH

Components

Interlocked socket outlets with automatic MCB (PIA)



Interlocked socket outlets with automatic MCD (PID)



Interlocked socket outlets with automatic MCB (PIA)

These sockets are suitable for installation in the system terminations for protection of the load supplied from the outlet against dangers of short circuits and overloads..

Interlocked socket outlets with automatic RCD (PID).

These sockets are suitable for installation in the system terminations for protection of the load supplied from the outlet against dangers of short circuits and overloads, as well as protection of the user against contact voltages. The residual current function with sensitivity of 10 mA also acts in the presence of non-sinusoidal fault currents (alternating currents mixed with unidirectional pulsating currents).

In compliance with installation standards, they are particularly suitable for the protection of:

- terminal user devices in rooms where there is a greater risk of electrocution (bathrooms, showers, etc.)
- sockets that power class 1 users with electronic circuits
- sockets for portable user devices in domestic or similar environments (irons, drills, etc.).


Operation

The MCB or RCD interlocked with the socket energises the cells of the socket only after the plug has been inserted and automatically cuts off voltage to the socket before the plug is fully extracted.

Therefore the plug is always inserted and extracted without an electrical arc.

The lever of the circuit-breaker can be closed only after the plug is inserted; without the plug, the lever operates without effect and does not close the switch.




Current-time tripping diagrams for circuit-breakers of the Chiara range



Technical details

Chiara – Socket outlets

Wiring diagrams



2CSK1326CH

Technical specifications

Power supply voltage	230 V~ - 50 Hz
Residual current (sensitivity)	IΔn 10 mA
Operation dependent on the line voltage	they must be installed downstream of a general residual current circuit-breaker
Thermomagnetic tripping	with characteristic C
Double-pole isolation	with 1 protected pole
Breaking capacity	3000 A
Rated current corresponding to the standard of the socket	
Type A RCBO for alternating and unidirectional pulsating currents	
Front LED with green light indicates normal operation with the presence of network power supply and contact closed	

Reference standards:

Interlocked socket outlets with MCB:

LV Directive, Standard CEI 23-97.

Interlocked socket outlets with RCD:

LV Directive, Standard CEI 23-96.

Technical details


Chiara – Socket outlets

TV/SAT sockets

The TV/SAT coaxial sockets for the Chiara series offer a complete range of products for implementing the terminal part of modern antenna systems. Manufactured fully from die cast Zama, they include a pressure terminal with safety screw in order to guarantee proper grip of the cable.

Individual sockets are available with male IEC or female F bushing, and double demixed sockets with both connection possibilities. Various levels of attenuation are available, ensuring that solutions are available for every type of installation.

Components



Attenuation values of the TV/SAT coaxial sockets

Code	Bushing	Passing attenuation [dB]			Bridging attenuation [dB]			Inverse attenuation [dB]	Direct current transit
		5÷40 MHz	47÷862 MHz	950÷2402 MHz	5÷40 MHz	47÷862 MHz	950÷2400 MHz		
2CSK1117CH	Male IEC Terr.	-	-	-	0,5	0,5	0,5	-	NO
2CSK1118CH	Male IEC Terr.	-	-	-	0,5	0,5	0,5	-	YES
2CSK1132CH	Male IEC Terr.	≤2	≤2	≤3	≤7	≤7	≤8	≥35	NO
2CSK1136CH	Male IEC Terr.	≤2	≤2	≤2,5	≤10,5	≤10	≤11	≥35	NO
2CSK1137CH	Male IEC Terr.	≤1,5	≤1,5	≤2,5	≤14,5	≤14	≤14,5	≥35	NO
2CSK1138CH	Male IEC Terr.	≤1,5	≤1,5	≤2,5	≤18,5	≤18	≤18,5	≥35	NO
2CSK1119CH	Female SAT	-	-	-	≤0,5	≤0,5	0,5	-	YES


Attenuation values of double demixed TV/SAT coaxial sockets

Code	Bushing	Passing attenuation [dB]		Bridging attenuation [dB]		Inverse attenuation [dB]	Direct current transit
		TV	SAT	TV	SAT		
2CSK1133CH	Male IEC Terr. Female SAT	-	-	≤2	≤2	-	YES
2CSK1120CH	Male IEC Terr. Female SAT	≤4	≤5	≤6,5	≤7	≥35	YES
2CSK1132CH	Male IEC Terr. Female SAT	≤3	≤4,5	≤10	≤11	≥35	YES
2CSK1131CH	Male IEC Terr. Female SAT	≤2	≤3	≤14	≤15	≥35	YES
2CSK1139CH	Male IEC Terr. Female SAT	≤1	≤2	≤18	≤19	≥35	YES

Technical details

Chiara – Socket outlets

Instructions for installation



Technical specifications

Manufactured from die cast Zama.

Pressure terminal.

Available with bushing of type: male CEI, female F.


Reference standards

EN 50083-1, EN 50083-2, EN 50083-4

Technical details

Chiara – Socket outlets

Wiring diagrams



Technical details


Chiara – Socket outlets

Network and telephone sockets

The range includes devices for the implementation of telephone and computer networks, RJ11 4-contact telephone connectors for telephones, telefax, modems and RJ12 6-contact telephone connectors for intercommunicating telephone installations.

RJ45 category 5e and 6 connectors are also available. These devices allow computer equipment (computers, modems, printers, etc) to be connected in a network and connection of multimedia devices.

Components



Code	Connector type	No. contacts	Cable type	Shielded	Category	Speed
2CSK1121CH	RJ11	4	twin core	NO	3	up to 16 Mb/s
2CSK1122CH	RJ12	6	twin core	NO	3	up to 16 Mb/s
2CSK1124CH	RJ45	8	UTP	NO	5e	up to 100 Mb/s
2CSK1125CH	RJ45	8	FTP	YES	5e	up to 100 Mb/s
2CSK1127CH	RJ45	8	UTP	NO	6	up to 10 Mb/s
2CSK1128CH	RJ45	8	FTP	YES	6	up to 10 Mb/s

FTP = cable shielded with aluminium tape

UTP = unshielded cable

Instructions for installation

Unshielded connectors:

1. wire the connector making sure that the connection terminals match;
2. operate the lever wiring device on the connector;
3. latch the connector on the adapter and proceed with the installation on the frame.

Shielded connectors:




1. wire the connector making sure that the connection terminals match;
2. position the cover of the connector and squeeze with pliers to make sure the contacts are tight;
3. apply the shielding, ensuring insulation of the connector;
4. latch the connector on the adapter and proceed with the installation on the support.

Keystone adapter 2CSK1135CH:

the structured wiring systems for data transmission are distinguished by their flexibility of use, installation independent of location and the use of the terminal outputs. The suppliers of components for wiring, when dealing with installations of a certain complexity and size, must be in able to show certification of conformity of the installation, directly or through accredited installations.

ABB meets this requirement with the adapter of the Chiara wiring accessories' range, which is compatible with various Keystone coupling connectors available on the market and enables integration between the Chiara wiring accessories' range and data transmission components of systems with structured wiring.

1. latch the connector on the adapter and proceed with the installation on the frame.



Unshielded connectors


Shielded connectors

Keystone adapter 2CSK1135CH

Technical details


Chiara – Socket outlets

Wiring diagrams for RJ11 and RJ12 telephone connectors




For telephone use, 2 wires of the RJ11 and RJ12 connectors, use the central contacts 3-4

Connection in series




Terminals 3 and 4 are connected via the internal contact to the telephone (closed with the receiver hung up). Lifting the receiver causes interruption of the downstream line (L1), guaranteeing secrecy of the conversation.

Connection in parallel






Each socket captures the line signal (there is no secrecy of conversation).



Note: extracting one of the plugs causes disconnection of sockets located downstream. In order to prevent this, you just need to insert a plug in the socket from which the telephone device was removed with a jumper between terminal 4 and 5.

Wiring diagrams for RJ45 data connectors

To obtain the EIA/TIA 568A or 568B configuration included below, follow the colour code shown on the terminal box.



Technical specifications

Connections With perforated insulation

Conductors non-butted, inserted in the appropriate blade slots

Reference standards

EN 50083-1, EN 50083-2, EN 50083-4, ISO 11801.

Technical details

Chiara – Protection devices

Fuse holder

Description	Code
Fuse holder, Ø5x20 / Ø6.3x32, 16A	2CSK1301CH


Components



Removable cover for removal of the fuse

Replacement of the fuse

After removing the removable cover with a screwdriver, proceed with replacement as in the drawing:



Replacement fuses


Fuses with dimension Ø5x20mm or Ø6.3x32 mm can be installed.

Technical details

Chiara – Protection devices

Description	Code
Overvoltage limiter, 75J, 230V~	2CSK1315CH


Components



This device provides protection for power supply sockets for all types of household appliances and in particular for those containing electronic components (Hi-Fi, TV, computers, video recorders, programming mechanisms, cash registers etc.) from damage caused by over-voltages present in power supply networks.

Instructions for installation and operation

The protection device is housed in the removable front cover. To replace it, after disconnecting the voltage from the installation, extract the cover from the limiter and separate the SPD block from the plastic cover, levering it with a screwdriver. Replace it with spare part 2CSY1302MY.




Functions


When the red warning light is on, it indicates that the protection has tripped and needs to be replaced (the load remains energised but it is not protected).

Examples of application

Over-voltages in domestic networks can be caused both by atmospheric interference and by control, operation or programming of connected inductive loads (air conditioners, burner motors, water pumps, reactors of fluorescent or discharge lamps, washing machines, etc.).



Wiring diagram



Technical specifications

Residual current limiting	protection (line-to-neutral)
Rated voltage (U_n)	120-230 V~ 50/60 Hz
Number of ports	1
Rated load current I_L	16 A
Max steady current (I_o)	250 V~
Test class	III
Protection level (U_p)	< 1.2 kV
Test voltage of combined wave generator U_{oc}	2.5 kV
Rated flashover current (I_h)	1 kA (8/20 ns) 20 times
Max flashover current (I_{max})	2 kA (8/20 ns) once
Temperature range	-5 °C - +40 °C
Internal integrated protection	fuse

Reference standards

LV Directive, Standard EN 61643-11

Technical details

Chiara – Protection devices

Miniature circuit-breakers and Residual current circuit-breakers

Description	Code
Automatic MCB, 1P+N, C6, breaking capacity 1.5kA	2CSK1304CH
Automatic MCB, 1P+N, C10, breaking capacity 3kA	2CSK1305CH
Automatic MCB, 1P+N, C16, breaking capacity 3kA	2CSK1306CH
Automatic RCD, 1P+N, C6 - 10 mA, breaking capacity 1.5kA	2CSK1307CH
Automatic RCD, 1P+N, C10 - 10 mA, breaking capacity 3kA	2CSK1308CH
Automatic RCD, 1P+N, C16 - 10 mA, breaking capacity 3kA	2CSK1309CH
Automatic RCD, 1P+N, C6 - 30 mA, breaking capacity 1.5kA	2CSK1328CH
Automatic RCD, 1P+N, C10 - 30 mA, breaking capacity 3kA	2CSK1329CH
Automatic RCD, 1P+N, C16 - 30 mA, breaking capacity 3kA	2CSK1330CH

Components

Automatic RCD



Automatic MCB



Automatic MCBS and automatic RCDs provide protection against over-currents and earth fault currents of terminal circuits. Protection class with the device embedded in smooth vertical walls with the associated support, frame and blank covers, if required: IP41.

Instructions for installation and operation

Use in dry and dust-free locations.

- Temperature between -5 °C and +40 °C..
- Suitability for installation on the supply side of a socket or device for the protection against overloads and short circuits of the equipment and, at the same time, for protection of the users against contact voltages.

The sensitivity (operating residual current) of 10mA and the suitability for operation also in the presence of non-sinusoidal fault currents (alternating currents mixed with unidirectional pulsating currents) allow the protection devices of the Chiara range to be classified as "type A RCBOS" (identified by the symbol), particularly suitable for the protection of:

- terminal uses in rooms where there is a greater risk of electrocution (bathrooms, showers, kitchens etc.), as prescribed by the CEI standards;
- class I consumer power sockets with electronic circuits (computers and accessories, electronic scales, electronic typewriters, cash registers etc.). In domestic and service industry networks non-sinusoidal fault currents are often present because of the use of electronic boards in domestic appliances.

The electromagnetic part of the circuit breakers guarantees protection against overloads and short circuits; the residual current part of the devices, for current values of 10mA, guarantees protection of persons against the contact voltages.

- Closing the circuit: manually press the lever of the circuit breaker at the "I" symbol.
- Opening the circuit:
 - manually, by pressing the lever of the circuit breaker at the "0" symbol or the yellow test button (test);
 - automatically, due to thermal (overload), magnetic (short-circuit) or residual current (earth fault current) tripping.
- The device must not be used as a control breaker.
- To check that the circuit breaker is installed and behaving correctly, the yellow test button (test) must be pressed every month. If the device is correctly installed and powered, the circuit breaker trips; if it does not, you must immediately inform the installation technician because safety will be compromised. After the test, you need to press the main key near the "I" symbol in order to reset the circuit breaker.
- Thermomagnetic tripping with characteristic "C" (see the current-time tripping diagram provided below).
- Double-pole operation with one protected pole + N, type A for alternated fault currents and unidirectional pushbuttons.
- Operating residual current (sensitivity) $I_{\Delta n}$ 10mA; the circuit breaker must be connected according to the electrical diagram provided below.

Technical details

Chiara – Protection devices

Functions

- Green front LED for signalling normal operation: presence of line voltage and closed circuit.
- Internal temperature checking: the circuit breaker automatically operates the opening of the circuit as soon as the safety threshold is exceeded.
- Self-test function to check the electrical continuity of the internal residual current circuit (in the absence of continuity, the circuit breaker will open).
- Opening the circuit if voltages occur higher than the predefined threshold at the circuit breaker input (for example, in 380V~ three-phase systems the circuit breaker prevents an erroneous "line-to line" connections, instead of "line-to-neutral").


Characteristics

- Main lever operated control part: "I" symbol (closed circuit); "O" symbol (open circuit).
- Front LED for signalling the presence of line voltage and closed circuit.
- Yellow test button (test) for checking that the device is functioning properly.
- Terminals protected with captive screws for clamping two conductors up to 4 mm² each
- Construction of the thermo magnetic part as prescribed by Standards EN 60898 and IEC 60898.
- Construction of the residual current part according to Standards EN 61009 and IEC 61009.
- Power supply voltage: 120-230V~ ±10% 50-60Hz.


The supply line can be connected to either the upper or the lower terminals of the circuit breaker, which must be installed downstream of a general residual current circuit breaker (Standard CEI 64-8/5, paragraph 532.2.2).

The line voltage determines operation (Standard IEC 1009-1, paragraph 4.1.2).


Wiring diagram



Characteristic curves





Current-time tripping diagrams for circuit-breakers of the Chiara range



Technical details

Chiara – Protection devices

Examples of application



Technical specifications

Type of circuit breaker	MCB	RCD
Rated voltage	230V	230V
Rated frequency	50 ÷ 60Hz	50 ÷ 60Hz
Rated residual current	-	10mA or 30mA
Short-circuit breaking capacity	6A 1500A 10A 3000A 16A 3000A	6A 1500A 10A 3000A 16A 3000A
Correnti nominali	6 -10 -16A	6 -10 -16A
Number of poles	1P + N	1P + N
Tripping characteristic		
Overcurrent protection	Type C	Type C
Limitation class	3	3
Residual current protection	-	Class A

Reference standards

Thermomagnetic: EN 60898-1 - Differential: IEC 61009-1

Technical details


Chiara – Safety and comfort devices

Thermostats and time-programmed thermostats

Description	Code
Summer/winter electronic thermostat, relay output, 1 contact NO 8A (AC1)/2A (AC15) - Power supply 230V~ 50/60Hz	2CSK1202CH

Components

Current value of the AMBIENT TEMPERATURE in °C. While adjusting the value of the DESIRED TEMPERATURE, its value is displayed (flashing). About 5 seconds after the last time the keys were pressed, it returns to displaying the AMBIENT TEMPERATURE.



The electronic thermostats of the Chiara series are equipped with a summer/winter switch for heating and air conditioning systems.

Characteristics

- Display of the current ambient temperature
- Display of the comfort temperature
- Display of the night-time temperature set
- Possibility to increase or decrease of temperature in steps of 0.5°C
- Minimum configurable value that can be set 5°C (anti-freeze temperature) and maximum configurable value 30°C
- Display of the operating status of the thermostat by means of symbols
- Anti-freeze function set to 5°C

Instructions for installation and operation


For correct operation, the thermostat must be installed at a height of approximately 1.5 metres from the floor, on internal walls, protected from direct sunlight and from any thermal interference such as heaters, lamps, televisions or any object that generates heat.

This device for controlling heating or air conditioning systems, uses a special technique that allows greater stability of the ambient temperature to be achieved while guaranteeing better comfort.

Areas of application

The environmental thermostats can be used for both heating and conditioning systems to control burners, pumps, valves, and refrigeration compressors.

Wiring diagrams



Technical specifications

Power supply	230V~ ±15% - 50Hz
Consumption	< 0.5 W
Output	Clean contact of 8A resistive relay
Operating temperature	from 0°C to +50°C
Adjustment range	from +5°C to +30°C
Precision	±1°C
Area of use	heating and air conditioning
Type of adjustment	PI
Proportional band	2.5°C

Reference standards

EN60730-1, EN60730-2-9, EN61000-3-2, EN61000-3-3, EN55014-1, EN55014-2

Technical details

Chiara – Safety and comfort devices


Dimmer

Loads that can be controlled with the dimmer

Dimmer type	Loads	Fluorescent or halogen lamps 230V	Fluorescent lamps	Toroidal transformers	Electronic transformers	Electro-mechanical transformers	Drills	Air agitators
Dimmer code	Description							
2CSK1205CH	Electronic dimmer with rotary control	YES	NO	NO	NO	NO	NO	NO
2CSK1207CH	Electronic dimmer with button control	YES	NO	YES	NO	YES	NO	NO
2CSK1204CH	Electronic dimmer with rotary control and two-way switch	YES	NO	NO	NO	NO	NO	NO

Description	Code
Electronic dimmer with rotary control for resistive loads 100-500W, 230V~ - 50/60Hz	2CSK1205CH

Components



Electronic dimmer with rotary control for resistive loads 100-500W 230V~ 50/60Hz (visible in the dark).

Operation


The load can be controlled and adjusted by rotating the knob.

The light intensity of the location LED is attenuated as the brightness of the controlled lamps increases.


Wiring diagram

The connection can be made between phase and neutral or between phase and phase, always in series with the load.

Control with dimmer



Control with a switch and adjustment with a dimmer



Technical specifications

Rated voltage	230V - 50/60Hz	110V - 50/60Hz
Resistive load power	100 - 500W	50 - 250W
Inductive load power	100 - 500VA	50 - 250VA
Technology	TRIAC	TRIAC
Operating temperature	-5 °C ÷ +35 °C.	
Adjustable load	Filament and halogen lamps	

Reference standards


CEI 23-9 (EN 60669-1)

Technical details

Chiara – Safety and comfort devices

Description	Code
Electronic dimmer with pushbutton control for resistive and inductive loads 60-500W, (60-500VA) 230V~ - 50/60Hz	2CSK1207CH

Components



Electronic dimmer with pushbutton control for resistive and inductive loads 60-500W 60-500VA 230V~ -50/60Hz (visible in the dark).


Operation

- The load can be controlled and adjusted using a pushbutton. The light intensity of the location LED is attenuated as the brightness of the controlled lamps increases.
The load can be turned on, adjusted and turned off using the pushbutton present on the dimmer or with normal non-luminous NO pushbuttons connected to the dimmer.
- Storage of the adjustment set when the load was switched off (apart from network outages).
 - Switch-on and switch-off of the load is gradual.
 - Pressing the pushbutton quickly causes the load to be switched on or off. Adjustment is obtained by keeping it pressed. To reverse the direction of adjustment, interrupt and then resume pressing the pushbutton.
 - If the pushbutton is pressed approximately between 0.3 s and 1 s, the dimmer will light up the controlled lamps, automatically and gradually, to their maximum brightness.


Wiring diagram

The connection can be made between phase and neutral or between phase and phase, always in series with the load.

Control and adjustment with a dimmer pushbutton



Control and adjustment with a dimmer pushbutton and NO button connected in parallel



Technical specifications

Rated voltage	230V - 50/60Hz	110V - 50/60Hz
Resistive load power	60 - 500W	30 - 250W
Inductive load power	60 - 500VA	30 - 250VA
Technology	TRIAC	TRIAC
Operating temperature	-5 °C ÷ +35 °C.	
Adjustable load	Filament and halogen lamps, ferromagnetic transformers for halogen lamps	

Reference standards


CEI 23-9 (EN 60669-1)

Technical details

Chiara – Safety and comfort devices

Description	Code
Electronic dimmer with rotary control and with two-way switch for resistive loads 100-500W, 230V~ -50/60Hz	2CSK1204CH

Components



Electronic dimmer with rotary control and two-way switch for resistive loads 100-500W 230V~ -50/60Hz (visible in the dark).

Operation


The load is controlled directly by means of a pressed two-way switch. Adjustment is performed by rotating the knob. The light intensity of the location LED is attenuated as the brightness of the controlled lamps increases.

Once the desired lighting level has been set, pressing the knob will switch the light source off, while pressing it again will switch it back on at the set lighting level.


Wiring diagram

The connection can be made between phase and neutral or between phase and phase, always in series with the load.


Control and adjustment with a dimmer



Control with two-way switch and dimmer, adjustment with dimmer



Control with two-way switch, intermediate switch and dimmer, adjustment with dimmer



Technical specifications

Rated voltage	230V - 50/60Hz	110V - 50/60Hz
Resistive load power	100 - 500W	50 - 250W
Inductive load power	100 - 500VA	50 - 250VA
Technology	TRIAC	TRIAC
Operating temperature	-5 °C ÷ +35 °C.	
Adjustable load	Filament and halogen lamps	

Reference standards

CEI 23-9 (EN 60669-1)


Technical details

Chiara – Safety and comfort devices

Gas detectors

Description	Code
Electronic natural gas detector with acoustic and indicator signal, relay output, 1 NO/NC change-over contact 6A (AC1)/2A (AC15) - 250V~. Power supply 230V~ - 50Hz. Equipped with dedicated frame for installation on type 503 box	2CSK1210CH
Electronic LPG gas detector with acoustic and indicator signal, relay output, 1 NO/NC change-over contact 6A (AC1)/2A (AC15) - 250V~. Power supply 230V~ - 50Hz. Equipped with dedicated frame for installation on type 503 box	2CSK1211CH

Components




The wiring accessories natural gas (CH4) or LPG gas detectors, flush-mounted with 3 modules (503 box embedded in the wall) contribute to guarantee the safety of civil environments where gas operated domestic appliances are installed, such as: boilers, cookers.


The equipment consists of a fixed power supply module and removable sensor module, which must be replaced after 5 years of continuous use. This allows a saving on the purchase and installation costs, with a lower impact on the environment due to the extension of the life time of the power supply/relay module for a further 5 years.

Positioning of the detector

The installation of the gas detector does not exonerate users from observance of all current laws and standards in the country of installation regarding the specifications, installation and use gas powered equipment, the ventilation of rooms and the release of combustion products.



- Install the natural gas detector at a maximum of 30 cm from the ceiling
- Install the LPG detector at a maximum of 30 cm from the floor surface.
- Install the detectors between 1 m and 4 m from the gas appliances.
- Do not install the detectors outdoors or in places exposed to atmospheric agents
- Do not install the detectors close to: sinks, air intakes, heating and air conditioning devices, windows and ventilation devices; in addition, the detectors must not be installed in closed spaces, such as behind a curtain or inside a cabinet.



Illustrative example: installation with 3 gas detectors (natural gas) that command the solenoid valve for shutting off the gassupply.

Technical details

Chiara – Safety and comfort devices

Extraction of the probe module (for example: to replace it)


CAUTION: always deactivate the line voltage 230V~

1. Remove the frame.
2. Delicately insert the flat blade of a small screwdriver and use it as a lever to uncouple the sensor module.
3. Rotate the sensor module upwards in order to uncouple it completely.

Replacement probe modules:

2CSY1220MC: Natural Gas replacement probe module

2CSY1223MC: LPG Gas replacement probe module



Characteristics

- Devices equipped with a control circuit with microprocessor that performs self-diagnosis tasks to ensure the perfect efficiency of the sensor over time.
- Sensor equipped with a special selective filter in order to avoid alarms in response to the presence of gas vapours that are not meant to be detected, such as steam from cooking, vapours from cleaning fluids etc.
- Devices equipped with an operating time meter, in order to signal the necessary replacement of the sensor module after the firsts 5 years of use.
- Luminous (red LED) and acoustic alarm signal.
- TEST (to verify that the device is operating properly) and Reset system with a single pushbutton.
- The gas detectors are equipped with an output relay that can command a valve to shut off the distribution of gas.

Key to signals

Luminous LED	Acoustic BUZZER
off	off
flashing	intermittent
on, fixed	-

Reference standards

LVD CEI 216-8 - EMC EN 50270

Wiring diagrams


CAUTION: the power supply network must incorporate a device to guarantee omnipolar disconnection.

The detector must be powered by a voltage of 230V~ 50Hz with continuity in order to guarantee maximum safety and correct signalling of replacement within the declared time limits.


For the electrical connections, bring cables with a maximum cross-section of 2.5 mm² to the terminals of the detector.

The diagrams (illustrative examples) show the position of the relay contacts at rest (no alarm).

Connection with solenoid valve normally closed



Connection with solenoid valve normally open



Technical specifications

Power supply voltage	230 V~ +/- 10% 50 Hz
Solenoid valve command relay	1 potential-free change-over contact
Capacity of relay contacts (max)	6 (2) A 250 V ~
Protection class	IP40
Type of insulation	Class II
Area of application	Domestic - type A
Semiconductor sensor	Installed inside the probe module
Operating temperature limits	- 10 °C ÷ + 40 °C
Operating humidity	90% UR (maximum)
Types of gas detected	Natural Gas - with model for natural gas LPG - with model for LPG gas
Alarm tripping	10% LIE (Lower Explosiveness Limit) For both models
Acoustic alarm	85 dB at 1 m
Sensor warm-up time at switch-on	1 minute
Storage temperature limits	- 15 °C ÷ + 50 °C

Technical details


Chiara – Safety and comfort devices
Flush-mounted emergency light



2CSk218932R1235
Supplied with their supports

Compliance with the
following EU Directives:
2014/35/UE (Low Voltage)
2014/30/UE (EMC)
2011/65/EU (RoHS)

Connection scheme



User manual

Read all instructions carefully

The 1-module anti-blackout lamp is a non-pluggable electronic emergency lamp for flush-mounted boxes installation. It turns on to enlightening areas where it is installed if a blackout occurs and guarantees a constant output for more than two hours thanks to its rechargeable battery.

Safety warnings


During installation and operation the following indications must be respected:

1. The product must be installed by qualified personnel in strict compliance with the connection diagrams.
2. Do not power the product if any part is damaged.
3. The product must be installed and commissioned in compliance with the regulations concerning electrical systems.
4. Do not use the product for purposes other than those indicated.
5. In case of fault do not repair the product.
6. The product can be used in overvoltage category III and pollution degree 2 environments.
7. An overcurrent protection device must be installed in the electrical system upstream of the product.
8. After installation, the inaccessibility to the connection terminals without special tools must be guaranteed.
9. Check that conductors are not live before accessing the connection terminals.

Technical features

Power supply:	230 V AC (-10% ÷ +10%) 50/60 Hz
Absorption:	2,5 VA (0,1 W)
Backup batteries:	1 rechargeable NiMH battery (not replaceable) - 3.6 V & 140 mAh full recharge time: 48 hours
Autonomy in event of power failure:	2 hours approx
Light source:	1 white LED Light intensity: 2400 mcd Beam angle: 120°
Red LED:	for low battery indication
Installation:	on 45mm height flush-mounted box (footprint: 1 module)
Terminal block:	for 1.5 mm ² cables
Operating temperature:	0°C ÷ +40°C
Storage temperature:	-20°C ÷ +40°C
Operating humidity:	20÷90% non-condensing
Protection:	IP40
Insulation:	reinforced between accessible parts (front) and all other terminals

Dimensions



Installation


The emergency lamp requires 1 module footprint to be installed in the flush-mounted box.

The emergency lamp is supplied with the battery installed (not removable) and charged. To prevent the battery from discharging during storage, a jumper on the back insulates the battery from the circuit. Before installing the lamp, move the jumper from "0" to "I" position.

Note: if the jumper interferes with the back of the flush-mounted box when plugging the lamp, cut the protruding part (as indicated).

Respect the connection diagram.

If the red LED on the front of the emergency light is on, the battery is low.



Technical details

Chiara – Safety and comfort devices
Flush-mounted pluggable emergency light



2CSK218782R1236
Supplied with their supports

Compliance with
the following
EU Directives:
2014/35/UE (Low Voltage)
2014/30/UE (EMC)
2011/65/EU (RoHS)

User manual

Read all instructions carefully

The 2-module pluggable blackout lamp is an electronic emergency lamp for flush-mounted boxes installation. It turns on to enlightening areas where it is installed if a blackout occurs. The lamp can be unplugged and used as a portable torch; once unplugged it turns on automatically until it is plugged again into its back shell.


Safety warnings

During installation and operation the following indications must be respected:

1. The product must be installed by qualified personnel in strict compliance with the connection diagrams.
2. Do not power the product if any part is damaged.
3. The product must be installed and commissioned in compliance with the regulations concerning electrical systems.
4. Do not use the product for purposes other than those indicated.
5. In case of fault do not repair the product.
6. The product can be used in overvoltage category III and pollution degree 2 environments.
7. An overcurrent protection device must be installed in the electrical system upstream of the product.
8. After installation, the inaccessibility to the connection terminals without special tools must be guaranteed.
9. Check that conductors are not live before accessing the connection terminals.


Technical features

Connection scheme



Power supply:	230 V AC (-10% ÷ +10%) 50/60 Hz
Absorption:	3 VA (0,2 W)
Backup batteries:	1 rechargeable NiMH battery (not replaceable) - 3.6V & 140mAh full recharge time: 48 hours
Autonomy in event of power failure:	2 hours approx
Light source:	Light intensity: 20 lumens Beam angle: 120°
Red LED:	for low battery or fault indication
Installation:	on 45mm height flush-mounted box (footprint: 2 modules)
Terminal block:	for 1.5 mm ² cables
Operating temperature:	0°C ÷ +50°C
Storage temperature:	-20°C ÷ +50°C
Operating humidity:	20÷90% non-condensing
Protection:	IP40
Insulation:	reinforced between accessible parts (front) and all other terminals


Dimensions




1. Move the selector from the storage position (0) to the operating position (1)
2. Plug the lamp into the back shell
3. Connect the power supply wires to the terminals
4. Plug the lamp + back shell

Lamp extraction

1. Press the lamp: an audible click will be heard to indicate that the sealing mechanism has released the lamp.
2. Pull the lamp out of the back shell



Assembly drawing in Mylos frame




Technical details

Chiara – Safety and comfort devices

Description	Code
Removable anti-blackout light, 230V~. Charge reserve 4.5 h and recharge time 10-20h. To be combined with 230V~ plug sockets; particularly recommended for codes 2CSK1108CH and 2CSK1109CH.	2CSK1214CH

Components



The anti-blackout light is an automatic removable, rechargeable electronic lamp that can be inserted in any Schuko socket or Italian P11 standard 10A bivalent socket. Socket outlets particularly recommended for holding the lamp are the sockets of the Chiara wiring accessories' range 2CSK1108CH and 2CSK1109CH, that allow the body of the lamp to be embedded in the socket outlet, thus minimizing the external dimensions.

The device was designed to light up automatically in the event of a blackout (no voltage warning), or to be used as a portable lighting device, useful in order to guarantee visibility and facilitate maintenance operations and/or searching for faults in unlit environments.

Functions


A light source is activated automatically whenever the line voltage is missing (blackout) thanks to rechargeable backup batteries.

- Possibility to extract it from the socket and use it as a normal pocket torch with an on/off button on the front.
- Long autonomy, 4.5 hours of continuous operation.
- Small dimensions - protrusion from the Schuko profile (only 8 mm).

On the front part there are two LEDs (one red and one green) that indicate the state of the lamp when it is powered:

- Red LED on, recharging in progress. In the event of a blackout the lamp will remain off (battery saving condition, used in the case of prolonged absence).
- Green LED on, recharging in progress. In the event of a blackout the lamp will light up and will switch off automatically when the network is restored.

The pushbutton on the front part allows you to switch from one condition to another.



Technical specifications

Plug	2P 10A
Center distance of the pins	19 mm
Ø of the pins	4 mm
Power supply	230V~50-60 Hz
Recharge time	10-20 hours
Useful battery life	4.5 hours

Reference standards

EN 60598-1, EN 60598-2

Technical details

Chiara – Safety and comfort devices

Other devices



2CSK235321R1226
Supplied with their supports

Compliance with the following EU Directives:
2014/35/UE (Low Voltage)
2014/30/UE (EMC)
2011/65/EU (RoHS)

User manual

Read all instructions carefully


The ABB's motion detector is a flush-mounted twilight motion detector that senses all the movements in its active field and triggers the lighting system for a predetermined period only if the brightness level is lower than a pre-set threshold. It performs type 1B actions and is intended for use in environments with overvoltage category III and pollution degree 2, according to EN 60669.

Safety warnings

During installation and operation the following indications must be respected:

1. The product must be installed by qualified personnel in strict compliance with the connection diagrams.
2. Do not power the product if any part is damaged.
3. The product must be installed and commissioned in compliance with the regulations concerning electrical systems.
4. In case of fault do not repair the product.
5. An overcurrent protection device must be installed in the electrical system upstream of the product.
6. After installation, the inaccessibility to the connection terminals without special tools must be guaranteed.
7. Check that conductors are not live before accessing the connection terminals.

Connection scheme




Connectable loads
- Incandescent 800 W
- Fluorescent (neon) 200 VA
- Low voltage halogen 500 VA
- Halogen 230 V~ 800 W
- Low consumption (CFL) 200 VA
- Led 200 VA

Technical features

Power supply:	230 V AC (-10% ÷ +10%) 50/60 Hz
Maximum absorption:	5 VA (1 W)
Output:	NO relay with breaking capacity of 5A/250V (on resistive load) with "zero crossing" technology
Tripping time:	5 seconds (test), 30 seconds ÷ 15 minutes
Tripping brightness:	5 ÷ 100 lux
Detection angle:	110° at 20°C
Detection field:	7 meters at 20°C
Installation:	on flush-mounted box with 45 mm height (dimensions: 1 module)
Terminal block:	for 1.5 mm² cables
Operating temperature:	0°C ÷ +35°C
Storage temperature:	-10°C ÷ +60°C
Operating humidity:	20÷90% non-condensing
Protection:	IP40 (on accessible parts)
Insulation:	reinforced between accessible parts (front) and all other terminals

Dimensions



Installation

To be installed in the flush-mounted box the motion detector requires 1 module footprint. High temperatures reduce the sensitivity of the sensor: avoid installation close to heat sources, air vents or devices

that can rapidly change their temperature. For installation, consider that the detector is more sensitive to movements cross the detection field than movements in the direction of the detector itself.

is reached, turn the brightness control dimmer (◎) clockwise until the relay triggers.

Operations

Detector test
The test verifies the correct operations of the IR sensor and relay. Turn the brightness control (◎) clockwise to the maximum range (100 lux) and the timing regulator (◎) anticlockwise to the minimum range (5 seconds). Check that the relay triggers when a movement is spotted inside the detection field.

Brightness adjustment
This regulation (◎) sets the lower brightness threshold for the relay to trigger if a movement is detected. Turn the brightness control (◎) anticlockwise to the minimum range: in this position the relay will remain inactive with daylight. Toward dusk, when the brightness threshold for relay activation

Note. The timing can be 5 seconds or between 30 seconds and 15 minutes. The minimum setting value of the regulator (◎) corresponds to 5 seconds; a minimum clockwise rotation brings the timing to 30 seconds. Continue to rotate the regulator clockwise to increase timing values up to a maximum of 15 minutes.


Technical details

Chiara – Safety and comfort devices


Description	Code
Universal badge switch with location light	2CSK1426CH
Relay output with NO contact 10A (AC1).	
Power supply 230V~ 50/60Hz	

Vertical badge electronic switch, relay output 16 A 250 V~, power supply 230 V~ 50-60 Hz, modules. Supplied without ISO card (badge). The device is equipped with a courtesy LED for night-time location.


Components



Operation



Wiring diagram



Technical specifications

Power supply	230 V~ ±10% 50-60 Hz
Output	relay with clean contact 10 A 250 V~ cos φ 1
Typical absorption	230 V~ 50-60 Hz: 30 mA, with relay active
Operating temperature	-5 °C +45 °C


Reference standards

LV Directive; EMC Directive; Standard EN 60669-2-1

Technical details

Chiara – Wall-mounted enclosures

IP40 and IP55 wall-mounted enclosures



Area of application


The IP40 wall-mounted enclosures, pursuant to Standard CEI 64-8, extend the area of application of the devices of the Chiara series to environments such as boiler rooms, warehouses, mechanical workshop, basements etc., where protection class IP40 is prescribed, defined by Standard EN 60529 (CEI 70-1).

This is guaranteed through devices installed in the enclosures, if the installation is carried out according to the supported procedures, through the use of connections, cable grommets and pipe ducts.


For devices with an open front (e.g. socket outlets) the protection class is less than IP40 but never less than IP20.

IP55 watertight wall-mounted enclosures, on the other hand, allow the application of the equipment of the Chiara series in environments such as building sites, sports installations, marinas, industrial and agricultural establishments, gardens, camp sites etc. The protection class IP55, defined by the Standard EN 60529 (CEI 70-1), is guaranteed by devices installed in the enclosures, if the installation is carried out according to the supported procedures, through the use of the suitable accessories and with the cover closed.

Dimensions of IP40 and IP55 enclosures



IP40 enclosure	no. modules	H	A	L	P
2CSK2140CH	1	38	80	65	55
2CSK2240CH	2	38	80	65	55
2CSK2340CH	3	38	80	104	55
2CSK2440CH	4	38	80	130	55



IP55 enclosure	no. modules	H	A	L	P
2CSK2155CH	1	40,5	80	65	63
2CSK2255CH	2	40,5	80	65	63
2CSK2355CH	3	40,5	80	104	63
2CSK2455CH	4	40,5	80	130	63

Technical details

Chiara – Wall-mounted enclosures

Because of the maximum depth dimension H, the IP40 and IP55 wall-mounted enclosures of the Chiara series cannot house the following contact blocks:

Code	Description
2CSK1204CH	Electronic dimmer with rotary control and two-way switch for resistive loads 100-500W
2CSK1205CH	Electronic dimmer with rotary control for resistive loads 100-500W
2CSK1207CH	Electronic dimmer with pushbutton control for resistive and inductive loads
2CSK1317CH	Electro-mechanical bell, 12V, 5VA, sound intensity 80 dB
2CSK1318CH	Electro-mechanical bell, 230V, 8VA, sound intensity 80 dB
2CSK1321CH	Electro-mechanical buzzer, 12V, 5VA, sound intensity 70 dB
2CSK1322CH	Electro-mechanical buzzer, 230V, 8VA, sound intensity 70 dB
2CSK1304CH	Automatic MCB 1P+N, C6
2CSK1305CH	Automatic MCB 1P+N, C10
2CSK1306CH	Automatic MCB 1P+N, C16

Code	Description
2CSK1307CH	Automatic RCD 1P+N, C6 – 10 mA
2CSK1308CH	Automatic RCD 1P+N, C10 – 10 mA
2CSK1309CH	Automatic RCD 1P+N, C16 – 10 mA
2CSK1328CH	Automatic RCD 1P+N, C6 – 30 mA
2CSK1329CH	Automatic RCD 1P+N, C10 – 30 mA
2CSK1330CH	Automatic RCD 1P+N, C16 – 30 mA
2CSK1324CH	Interlocked socket with MCB (2P+E 16A 230V P17/11)
2CSK1325CH	Interlocked socket with MCB (2P+E 16A 230V)
2CSK1326CH	Interlocked socket with automatic RCD 10mA (2P+E 16A 230V P17/11)
2CSK1012CH	Single pole latching relay, 230V, 1 10A output contact
2CSK1014CH	4 sequence switch relay, 230V, 2 10A output contacts

The installation of similar devices in the form of a DIN rail in the distribution board is recommended where possible.


Technical details

Chiara – Other installation solutions

Support for DIN bar 1-2-3 modules

Description	Code
Support for DIN bar for 1-2-3 modules, customisable	2CSK1608CH

Components






Reference dimensions:

- 1 module version: 1,9 DIN modules
- 2 modules version: 3,4 DIN modules
- 3 modules version: 4,4 DIN modules

Instruction for installation

3 modules: snap assemble the two halves.
1 or 2 modules: using a cutter, cut along lines 1 or 2 respectively and assemble the two halves.



Technical details

Chiara – Frames

The frames of the Chiara series are made from technopolymer with natural/pastel colour shades or surface galvanic painting, and are characterised by their minimal protrusion from the wall, since they are not fitted with an under-plate.

Reference standards

CEI 23-9 (EN 60669-1).




Frame that adheres
to all surfaces

2 ÷ 8 mm

Customization

Frames customized with a logo/text string can be supplied on request. They are produced by means of monochromatic pad printing on the areas highlighted below.



Customization is possible with standard colours (black, Pantone cool gray 3C, Pantone 5425 C) or with a colour specified by the customer.

Minimum order batch: 36 pieces including various modularities.

For quotes and delivery times contact an ABB sales executive.

Technical details

Chiara – Coding, Order information



Coding criteria of the devices




- 0 Control devices
- 1 Socket outlets
- 2 Comfort devices
- 3 Protection devices and signalling devices
- 6 Components for installation, accessories and spare parts

Example: single-pole switch




Coding criteria of the frames



- 2 2-module frame
- 3 3-module frame
- 4 4-module frame
- 7 7-module frame

- | | |
|----|-------------------|
| 01 | white |
| 02 | sand |
| 03 | stone |
| 04 | volcano |
| 11 | pastel yellow |
| 12 | pastel orange |
| 13 | pastel green |
| 14 | pastel blue |
| 15 | glossy chromium |
| 16 | satin chromium |
| 17 | glossy metal |
| 18 | satin metal black |
| 51 | glossy bronze |
| 52 | satin bronze |
| 53 | glossy gold |
| 54 | satin gold |

Example: technopolymer frame, 3 modules, sand colour






Packaging

To enable automatic warehouse management using optical readers, the devices and frames of the Chiara wiring accessories' range are packaged in boxes that bear the EAN bar code and that protect the contents adequately against dust and shocks. For a better explanations of the installation methods, a specific instruction sheet is supplied. Individual packages are available for only for the codes with the lowest turnover.

Technical details

Chiara – Overall dimensions

Chiara code	Description	No. Modules	Depth mm
2CSK1001CH	Single-pole switch, 16A - 250V~	1	30
2CSK1002CH	Double-pole switch, 16A - 250V~	1	30
2CSK1003CH	Single-pole two-way switch, 16A - 250V~	1	30
2CSK1004CH	Single-pole switch, 16A - 250V~, 2 modules	2	30
2CSK1005CH	Single-pole push switch NO, 16A	1	30
2CSK1006CH	Double-pole switch, 16A - 250V~, with key control	1	25
2CSK1006CHU	Double-pole switch, 16A - 250V~, with universal key control	1	25
2CSK1007CH	Single-pole two-way switch, 16A - 250V~, 2 modules	2	30
2CSK1008CH	Intermediate switch, 16A - 250V~, 2 modules	2	30
2CSK1009CH	Double-pole push switch, NO, 16A - 250V~, with key control	1	25
2CSK1009CHU	Double-pole push switch, NO, 16A - 250V~, with universal key control	1	25
2CSK1010CH	Intermediate switch, 16A - 250V~	1	30
2CSK1011CH	Change-over switch, 10A - 250V~, 3 positions	1	31
2CSK1012CH	Single pole latching relay, 230V	1	31
2CSK1014CH	4 sequence switch relay, 230V, 2 10A output contacts	1	31
2CSK1016CH	Single-pole push switch NC, 16A	1	30
2CSK1017CH	Double single-pole push switch, NO+NO, 16A - 250V~	1	30
2CSK1018CH	Double single-pole push switch, NO+NO, 16A - 250V~, with interlock	1	30
2CSK1022CH	Single-pole push switch 1 NO and 1 NC, 16A, with ON	1	30
2CSK1023CH	Single-pole push switch 1 NO and 1 NC, 16A, with OFF symbol	1	30
2CSK1020CH	Single-pole push switch NC with cord pull, 16A	1	30
2CSK1021CH	Single-pole push switch NC with cord pull, 16A	1	30
2CSK1028CH	Single-pole push switch NO, 16A, with BELL	1	30
2CSK1029CH	Single-pole push switch NO, 16A, with KEY	1	30
2CSK1030CH	Single-pole push switch NO, 16A, with STAIR LIGHT	1	30
2CSK1024CH	Single-pole push switch NO, 16A, with red diffuser	1	30
2CSK1025CH	Single-pole push switch NO, 16A, with green diffuser	1	30
2CSK1026CH	Single-pole push switch NO, 16A, with orange diffuser	1	30
2CSK1027CH	Single-pole push switch NO, 16A, with white diffuser	1	30
2CSK1031CH	Single-pole pushbutton NO, 16A, with backlit label holder plate push switch	2	30
2CSK1032CH	Single-pole push switch NO, 16A, with backlit label holder plate, 3 modules	3	30
2CSK1101CH	2P+E socket outlet, 10A - 250V~, P11 type	1	22
2CSK1102CH	2P+E socket outlet, 16A - 250V~, P17 type	1	22
2CSK1103CH	2P+E socket outlet, 10/16A - 250V~, P17/P11 type	1	22
2CSK1104CH	2P+E socket outlets, 10/16A, red	1	22
2CSK1105CH	2P+E socket outlets, 10/16A, green	1	22
2CSK1106CH	2P+E socket outlets, 10/16A, orange	1	22
2CSK1108CH	2P+E socket outlet, 16A - 250V~, P30 type	2	31
2CSK1114CH	2P+E socket outlets, 16A - 250V~, P30 type, red	2	31
2CSK1115CH	2P+E socket outlets, 16A - 250V~, P30 type, green	2	31
2CSK1116CH	2P+E socket outlets, 16A - 250V~, P30 type, orange	2	31
2CSK1109CH	2P+E socket outlet, 16A - 250V~, P30/17 type	2	35
2CSK1110CH	2P+E socket outlets, 16A - 250V~, P30/17 type, red	2	35
2CSK1111CH	2P+E socket outlets, 16A - 250V~, P30/17 type, green	2	35
2CSK1112CH	2P+E socket outlets, 16A - 250V~, P30/17 type, orange	2	35
2CSK1113CH	2P shaver socket with insulating transformer	3	37.5



Technical details

Chiara – Overall dimensions

Chiara code	Description	No. Modules	Depth mm
2CSK1324CH	2P+E socket outlet, 16A - 250V~, interlocked with MCB, P17/11	2	37.5
2CSK1325CH	2P+E socket outlet, 16A - 250V~, interlocked with MCB, P30	3	37.5
2CSK1326CH	2P+E socket outlet, 16A - 250V~, with RCD 10mA, P17/11	3	37.5
2CSK1117CH	TV coaxial socket, direct, male IEC connector ø 9.5 mm, insulated type	1	21
2CSK1118CH	TV/SAT coaxial socket, direct, male IEC connector ø 9.5 mm, with feedthrough of direct current	1	21
2CSK1132CH	TV/SAT coaxial socket, feedthrough, male IEC connector ø 9.5 mm, attenuation 7dB	1	21
2CSK1136CH	TV/SAT coaxial socket, feedthrough, male IEC connector ø 9.5 mm, attenuation 10dB	1	21
2CSK1137CH	TV/SAT coaxial socket, feedthrough, male IEC connector ø 9.5 mm, attenuation 14dB	1	21
2CSK1138CH	TV/SAT coaxial socket, feedthrough, male IEC connector ø 9.5 mm, attenuation 18dB	1	21
2CSK1119CH	TV/SAT coaxial socket, direct, female F connector, with feedthrough of direct current	1	21
2CSK1133CH	Double demixed TV/SAT coaxial socket, direct, male IEC connector ø 9.5 mm and female F connector	1	21
2CSK1120CH	Double demixed TV/SAT coaxial socket, feedthrough, male IEC connector ø 9.5 mm and female F connector, attenuation 7dB	1	21
2CSK1130CH	Double demixed TV/SAT coaxial socket, feedthrough, male IEC connector ø 9.5 mm and female F connector, attenuation 10dB	1	21
2CSK1131CH	Double demixed TV/SAT coaxial socket, feedthrough, male IEC connector ø 9.5 mm and female F connector, attenuation 14dB	1	21
2CSK1139CH	Double demixed TV/SAT coaxial socket, feedthrough, male IEC connector ø 9.5 mm and female F connector, attenuation 18dB	1	21
2CSK1121CH	RJ11 telephone connector	1	21
2CSK1122CH	RJ12 telephone connector	1	21
2CSK1124CH	RJ45 connector, Cat. 5e, UTP (unshielded)	1	21
2CSK1125CH	RJ45 connector, Cat. 5e, FTP (shielded)	1	21
2CSK1127CH	RJ45 connector, Cat. 6, UTP (unshielded)	1	21
2CSK1128CH	RJ45 connector, Cat. 6, FTP (shielded)	1	21
2CSK1160CH	Flush-mounted USB charger 500-650mA	1	35
2CSK1210CH	Electronic natural gas detector	3	39
2CSK1211CH	Electronic LPG gas detector with acoustic and indicator signal	3	39
2CSK1301CH	Fuse holder, for fuses Ø5x20 / Ø6.3x32 mm, max. 16A	1	26
2CSK1303CH	LED light for emergency lighting or steplight	3	50
2CSK1304CH	Automatic MCB, 1P+N, C6, breaking capacity 1.5kA	1	36
2CSK1305CH	Automatic MCB, 1P+N, C10, breaking capacity 3kA	1	36
2CSK1306CH	Automatic MCB, 1P+N, C16, breaking capacity 3kA	1	36
2CSK1307CH	Automatic RCD, 1P+N, C6 - 10 mA, breaking capacity 1.5kA	2	36
2CSK1308CH	Automatic RCD, 1P+N, C10 - 10 mA, breaking capacity 3kA	2	36

Technical details

Chiara – Overall dimensions


Chiara code	Description	No. Modules	Depth mm
2CSK1309CH	Automatic RCD, 1P+N, C16 - 10 mA, breaking capacity 3kA	2	36
2CSK1315CH	Oversupply limiter, 75J, 230V~	1	26
2CSK1328CH	Automatic RCD, 1P+N, C6 - 30 mA, breaking capacity 1.5kA	2	36
2CSK1329CH	Automatic RCD, 1P+N, C10 - 30 mA, breaking capacity 3kA	2	36
2CSK1330CH	Automatic RCD, 1P+N, C16 - 30 mA, breaking capacity 3kA	2	36
2CSK1310CH	Warning light, ORANGE colour	1	20
2CSK1311CH	Warning light, WHITE colour	1	20
2CSK1312CH	Warning light, RED colour	1	20
2CSK1313CH	Warning light, GREEN colour	1	20
2CSK1317CH	Electro-mechanical bell, 12V	1	37
2CSK1318CH	Electro-mechanical bell, 230V,	1	37
2CSK1321CH	Electro-mechanical buzzer, 12V	1	37
2CSK1322CH	Electro-mechanical buzzer, 230V	1	37
2CSK1201CH	Summer/winter electronic time-programmed thermostat	3	38
2CSK1202CH	Summer/winter electronic thermostat	2	29.5
2CSK1205CH	Electronic dimmer with rotary control for resistive loads 100-500W	1	39
2CSK1204CH	Electronic dimmer with rotary control and two-way switch for resistive loads 100-500W	1	39
2CSK1207CH	Electronic dimmer with pushbutton control for resistive and inductive loads 60-500W	1	39
2CSK1426CH	Universal badge switch with location light	2	32

Technical details


Chiara – Overall dimensions

Frames


2 modules




3 modules



4 modules




7 modules




Self-supporting frames

2 modules




Screw distance: 60 mm

3 modules



Screw distance: 83.5 mm


4 modules



Screw distance: 108 mm


Supports

2 modules




Screw distance of the box: 60 mm

3 modules




Screw distance of the box: 83.5 mm

4 modules



Screw distance of the box: 108 mm

7 moduli




Screw distance of the box: 100 mm

Technical details

Chiara – Overall dimensions


Safety and comfort devices

Anti-blackout light




IP40 wall-mounted enclosures



2 modules



3 modules




4 modules




IP55 wall-mounted enclosures



2 modules






3 modules



4 modules



IP55 flush-mounted escutcheon plate




Technical details

Unno

Switches

Optional: locator light


1-way switch




Switches

With locator light


1-way switch with indicator light




2-way switch



2-way switch with indicator lamp




2-way switch - Intermediate switch - 2-way switch




Socket outlets


1-module socket outlets



1-way double pole switch



3-module duplex socket outlets



Technical details

Unno

USB chargers

N1185 & N1185.2

1. Technical data:

Rated input voltage:

100 - 240 V AC ± 10 %

Rated input frequency:

50 - 60 Hz

Rated input current:

N1185.2: 0,20Aac@max load

N1185: 0,12Aac@max load

Consumption in standby:

N1185.2: < 10 mW@230 VAC

N1185: <= 0,3W@230 VAC

Rated output voltage:

5 V DC +5 / -5 %

Rated output current:

N1185.2: 2000 mA a 5 V DC

N1185: 750 mA a 5 V DC

Operating temperature:

N1185.2: 0°C to 45°C, when installing

a N1185.2. 0°C to 30°C, when two

N1185.2 chargers together

N1185: 0° C + 45° C

Energy efficiency:

N1185.2: > 79%

N1185: >= 66%

2. Electrical safety data:

Safety standard:

EN60950-1 - Low Voltage Directive

Protection class:

II - Low voltage


Isolation (primary-secondary):

Transformer with galvanized isolation


EMC Directive:

EN 55022, EN 55024

3. Wiring diagram



4. Installation




Data outlets - RJ45 Cat. 5e UTP female connector


N1118.5

Telephone outlets


N1117




- 1 Remove the back cap from the connector. Strip approx. 5 cm off the jacket and discard the cable cutter cord.




- 2 Bring the cable close to the connector, with the jacket at approx. 6 mm from the connector. Insert the cables into the corresponding slots as indicated by the cable color-wiring configuration for T568A or T568 B (as shown in Figures 2A and 2B).




2a Wiring according to T568A:



- 3 Push the cables against the end of the slot and cut them flush to the connector. Use an IBDN 110, BIX, KRONE wiring tool, or a similar type 110 tool.



2b Wiring according to T568B:



- 4 Mount the connector cap.



Technical details

Unno

Data outlets - RJ45 Cat. 6 UTP female connector


N1118.6

1 Preparing the Cable	1.1 Cut approximately 5 cm. off the jacket.	1.2 Open approx. 10 cm. of the jacket with a cutter cord or another tool.	1.3 Cut the jacket.	1.4 Cut the mesh (if it has one and the cord at the same level of the jacket).
2 Preparing the Conductors	2.1 Select the adequate wiring scheme (568A or 568B) and place the pairs in a straight line.	1.2 Position each of the four pairs in the holes of the end piece.	2.3 Ensure the end piece is located as close as possible to the edge of the jacket.	
2.4 Place the pairs in the direction of the end piece slots.	2.5 Insert the end piece into the module.	2.6 Unbraid the pairs, position and insert the cable in the module slots. Place the solid color cable in the first slot of the pair.		
3 Conductor Terminations	3.1 Place the tool perpendicular to the module and finish cutting the cables.	4 Placing the Cable		
5 Disassembling the module from the supporting piece	5.1 Push the front of the module in with your thumb releasing the hooks.	5.2 Pry upwards to release the upper hook.	5.3 Pry downwards to release the lower hook.	


Technical details

Unno


VDI connectors




N2155.2
Pin Out:
1G — W/GND Left Audio
1B — White Right Audio
3G — R/GNB
3R — red



N2155.4
Pin Out:
R — Red Left Audio
G — Ground Right Audio
L — White





N2155.3
Pin Out:
1G — Y/GND Composite Video
1A — Yellow
2G — W/GND Left Audio
2B — White
3G — R/GNB Right Audio
3R — Red





N2155.5
PIN PIN
1 — 1 R+ 5 — GND 5
6 — 6 R- 10 — SGND 10
2 — 2 G+ 11 — ID0 11
7 — 7 G- 12 — ID1 12
3 — 3 B+ 13 — HSYC 13
8 — 8 B- 14 — VSYC 14
4 — 4 ID2 15 — ID2 15
G — GND G — GND

G-1	1	TMDS Data2+
	2	TMDS Data2 Shield
	3	TMDS Data2-
G-2	4	TMDS Data1+
	5	TMDS Data1 Shield
	6	TMDS Data1-
G-3	7	TMDS Data0+
	8	TMDS Data0 Shield
	9	TMDS Data0
G-4	10	TMDS Clock+
	11	TMDS Clock Shield
	12	TMDS Clock-
	13	CEC
	14	RESERVED (N.C. on device)
	15	SCL
	16	SDA
	17	DDC/CEC Ground
	18	+5V Power
	19	Hot Plug Detect
GND		Ground



N2155.8
Pin Out:
1 — Vbus
2 — D-
3 — D+
4 — Ground
G — Shielded



Note:
Using a strap for fixing the cable to the board it is recommended to avoid disconnections. For this the plates have two through-holes at its rear end.

Technical details

Unno

1 Module dimmer

N1160 & N1160.1

1. Technical Data

Voltage:

N1160: 127 V~ ; 60 Hz
N1160.1: 230 V~ ; 50-60 Hz

Power:

N1160: 50-500 W
N1160.1: 50-700 W

Operating temperature:

0 – 30° C





Table 1:
Power reduction (%) as a function of temperature (°C)

2. Assembly/Connection

2.1. Assembly


Important:

If the dimmer is installed next to another electronic device that can produce heat, the maximum power must be reduced in half. If it is installed between two electronic devices that can produce heat, the maximum power must be reduced to the fourth.



2.2. Connection

Important:
Disconnect the power supply when installing.



3. Operation

Do not exceed the maximum shown in Table 1, since the dimmer has a NON-resettable thermal fuse. If the fuse is triggered, the electronic dimmer is useless for further use. In case of exceeding the maximum load, the fuse could not trig but it may happen that the load will not turn off.

Buzzer

N1119


1. Technical data

Rated voltage: 127-230 Vac / 50-60 Hz.

Rated power: 8 VA.
Adjustable tone.

Acoustic power at 1 meter with cover plate: 75 dB.



2. Wiring diagram:



Technical details

Unno


Frames




Technical details

Millenium


Frame dimensions




Rocker switch frame 1 gang




Premium rocker frame 1 gang




Half/Double rocker & other functions frame 1 gang




Triple rocker & KNX sensor frame 1 gang




Shaver socket outlet frame




Triple rocker & KNX sensor frame 2 gang



Half/Double rocker & other functions frame 2 gang



Distance between fixing screws for 1 gang frames















Distance between fixing screws for 2 gang frames

Suitable for flush wall boxes of 35 mm minimum except shaver socket. Cooker unit and 45 DP switch.

Technical details

Millenium


Circuit connection diagrams




Technical details

Millenium


Circuit connection diagrams




Shaver socket outlet




Thermostat 2 pipes




Thermostat 4 pipes



Telephone outlet - RJ11



Computer outlet - RJ45



Telephone outlet - BT R11 / RJ12

TV & SAT technical specifications

TV

Frequency (Mhz)	Insertion Loss (dB)	Output return loss (dB)	Voltage resistance
5 ~ 550	< 2.5	> 16	
550 ~ 750	< 2.5	> 14	2 KV
750 ~ 1000	< 2.5	> 14	





SAT OUTLET

Frequency (Mhz)	Insertion Loss (dB)	Output return loss (dB)	Voltage resistance
5 ~ 550	< 0.5	> 18	
550 ~ 750	< 0.8	> 18	2 KV
750 ~ 1000	< 0.8	> 16	

Technical details

Concept bs


Circuit connection diagrams




Technical details

Concept bs


Circuit connection diagrams



Modular Jack Socket Outlet
(6 position / 4 contacts)



RJ45 JACK
(8 position / 8 contacts)



Master Telephone
Outlet

Wiring Colour Code		
Pin Number	Base Colour	Indication
1	Black	Earth
2	Red	L2
3	Green	L1
4	Yellow	Spine
5	-	-
6	-	-


Telephone Outlet - RJ11

Wiring Colour Code	
Pin Number	Base Colour / Stripe
1	EM-T568A White Colour
2	White / Green
3	Green
4	White / Orange
5	Blue
6	White / Blue
7	Orange
8	White / Brown


Computer outlet - RJ45

Wiring Colour Code	
Pin Number	Base Colour / Stripe
1	Green / White
2	Blue / White
3	Orange / White
4	White / Orange
5	White / Blue
6	White / Green


Telephone Outlet - BT




Touch type time delay switch




Sound and light control switch




Countdown time switch, 1 gang 1 way




Volume control switch




Emergency broadcast line




4 step rotary switch




Fan Controller




Emergency switch



Thermostat controller with display,
2 pipe system



Thermostat controller with display,
4 pipe system




1 gang BS single pole
floor socket outlet


Technical details

Concept bs

The usage of AC503 (adapter plate)




The usage of the multi-gang frame



Technical details

Kalo


Circuit connection diagrams




Technical details

Kalo


Circuit connection diagrams




2G 13 A switch socket DP




1G universal switch socket




1G TV outlet



1G SAT outlet




TV/FM splitter




1G telephone outlet

Wiring Color Code		
Pin Number	Base Color	Indication
1	—	Earth
2	Black	L2
3	Red	L1
4	Green	Spare
5	Yellow	—
6	—	—




1G data outlet


Wiring Color Code		
Pin Number	EIA-T568A Wire Colour	EIA-T568B Wire Colour
1	White/Green	White/Orange
2	Green	Orange
3	White/Orange	White/Green
4	Blue	Blue
5	White/Blue	White/Blue
6	Orange	Green
7	White/Brown	White/Brown
8	Brown	Brown




shaver socket




1G rotary dimmer



fan regulator



1G 1W push switch



fused connection unit

Electrical installation solutions for buildings – Technical details

ABB i-bus® KNX

Index

Illumination and Light Sensors – DALI	14/2
Heating and Cooling	14/5
Busch-priOn®	14/6
Energy measurement	14/8
Security and Surveillance	14/9

ABB i-bus® KNX

Illumination and Light Sensors – DALI

The ABB DALI Gateways are used to interface between DALI (Digital Addressable Lighting Interface) and KNX installations. Four Gateways are available:

The DALI Gateway Basic DG/S 1.64.1.1 (1-fold) and DG/S 2.64.1.1 (2-fold) and on the other hand the DALI Gateway Premium DG/S 1.64.5.1 (1-fold) and DG/S 2.64.5.1 (2-fold).


All incorporate the DALI power supply.

DALI Gateways DG/S 1.64.x.1

Flexibility by controlling light individually per device or in groups



The DALI Gateway (1-fold) Basic and Premium can install up to 64 DALI devices both via 16 flexible DALI (orange lined group) and KNX lighting groups (green dotted lined group), each with one or more DALI participants. Control and Monitoring via KNX. Control and status feedback can also be carried out via Broadcast. 16 independent Lighting scenes are available.



Both basic Gateways are equipped with emergency lighting function, support the DALI standard EN 62386-202 that specifies DALI emergency lighting (self-contained).

The two DALI Gateways Premium are additionally equipped with colour temperature Tc (tunable white) function and supports the DALI standard EN 62386-209.

DALI Gateways DG/S 2.64.x.1

Maximum flexibility combined with highest amount of DALI participants and groups, to meet all customer needs



The DALI Gateway (2-fold) Basic and Premium can install up to 2 x 64 DALI devices both via 2 x 16 flexible DALI (orange lined group) and KNX lighting groups (green dotted lined group), each with one or more DALI participants. Control and Monitoring via KNX. Control and status feedback can also be carried out via Broadcast. 2 x 16 independent Lighting scenes are available.




ABB i-bus® KNX


Illumination and Light Sensors – DALI

DALI Light Controller DLR/S 8.16.1M

Energy through constant lighting control



Control via 16 lighting groups. Up to 8 lighting groups can be controlled with 8 light sensors. Master-slave, staircase light and Scene mode round off the functions.



DALI Light Controller DLR/A 4.8.1.1

Decentralized Constant Lighting Control



The new DALI Light Controller DLR/A 4.8.1.1 is a surface mounting device for switching and dimming of 8 independent lighting groups. A maximum of 64 DALI devices can be connected. The device can be used for 4-fold constant lighting control in connection with 4 Light Sensors LF/U 2.1. Furthermore staircase lighting and master / slave functions are provided. Fault feedback messages, e.g. concerning ballast or lamp failures, can be programmed and activated via KNX. The compact surface-mounted housing allows the decentralized installation in the underfloor or in false ceilings – optimal for the use with Room Controller RC/A.

ABB i-bus® KNX

Illumination and Light Sensors – DALI

DALI Gateway DG/S 8.1

The proven technology



Lighting groups are formed via “rigid” hardware wiring.
Fast commissioning as no addressing is necessary.
No readdressing when a ballast is exchanged. 8 x 16 DALI devices.




ABB i-bus® KNX

Heating and Cooling

Influencing Variables on Room Climate

Influencing Variables on Room Temperature

Internal and external factors have an effect on the thermal conditions in a room or a building. As an external factor the solar radiation is important for the indoor temperature – particularly with regard to modern architecture with glass fronts. Besides this, the room temperature is strongly affected by the exchange of thermal energy through windows and walls as well as the loss of thermal energy through open doors and windows.

Depending on the intensity, all this interactions influence also the energy efficiency of a building and have therefore to be optimised.

Internal thermal inputs from lighting, devices or persons have also an influence on the room climate. By planning a heating, ventilation or air conditioning system all this internal and external factors have to be considered.

Influencing Variables on Air Quality

The indoor climate in living and working areas has a scientifically proven impact on health, job performance and well-being of people. A suitable indicator for determination of the room air quality is the CO₂ concentration. In addition the values for room temperature and air humidity must be controlled to meet the requirements for a comfortable room climate.

Studies have shown, that high CO₂ concentration in the air influences the well-being as well as the performance and learning ability of people. Besides the normal CO₂ concentration in the air, human respiration is an important factor increasing the CO₂ concentration in a room. Therefore it is important to measure the CO₂ concentration in rooms where many persons are present (schools, conference rooms, open-plan offices). Monitoring of thresholds enables fans to be switched via ABB i-bus KNX allowing automatic control of the CO₂ concentration and sufficient supply of fresh air.




ABB i-bus® KNX

Busch-priOn®

Operation – Planning aid for Busch-priOn®

End strips without function

studio white,
Article-No. 6348-24G-101-500

glass black,
Article-No. 6348-825-101-500

white glass,
Article-No. 6348-811-101-500


stainless steel,
Article-No. 6348-860-101-500

Support frame, bus coupler



Note:

This power adaptor can supply up to 15 power bus couplers with current.



FM actuators

End strip



Commissioning adaptor,
Article-No. 6149/21-500

End strips without function

studio white,
Article-No. 6349-24G-101-500

white glass,
Article-No. 6349-811-101-500

glass black,
Article-No. 6349-825-101-500

stainless steel,
Article-No. 6349-860-101-500

ABB i-bus® KNX

Busch-priOn®

End strip with IR proximity function

glass black,
Article-No.
6350-825-101-500

Single-line
display and room
thermostat,
Article-No.
6351/08-825

Control element,
1gang,
Article-No.
6340-825-101-500

Control element,
3gang, Article-No.
6342-825-101-500

Rotary control
element, 1gang,
Article-No.
6341-825-101-500

Busch-Watchdog,
180 FM,
Article-No.
6345-825-101-500

End strips with temperature sensor.

studio white,
Article-No. 6352-24G-101-500

white glass,
Article-No. 6352-811-101-500

glass black,
Article-No. 6352-825-101-500

stainless steel,
Article-No. 6352-860-101-500

Labelling symbols




Labelling inserts for blinds, lighting,
RTC and scene. The colours are repeated in the
Busch-Jaeger colour concept.

ABB i-bus® KNX

Energy measurement

ABB offers various solutions for decentral energy measurement on the basis of the KNX standard.


Version 1



Electronic energy meters make the current energy values available on the KNX bus system in conjunction with a KNX interface. The measured data can be intermediately stored, evaluated and visualized from here.




Version 2



The Energy Module can record the energy consumption for the individual devices. It is used particularly when upgrading existing KNX systems and wherever energy measurement is required without switch functions. It facilitates a detailed and transparent insight into the energy consumption of a building. The current meter values can be sent and evaluated.



Version 3




The Energy Actuator facilitates control of the connected consumer loads via the ABB i-bus® KNX. For each of the three switch channels, the individual consumption can be measured in the same way as for the Energy Module. For every channel, the proven functionality of the ABB i-bus® KNX Switch Actuators are available.



ABB i-bus® KNX

Security and Surveillance – The new KNX Security Panel



A complete product portfolio: One system – all interfaces

To fulfill the project requirements ABB provides the user besides the new panel and keypad a complete product portfolio for professional alarm technology as well as known solutions for all trades of KNX building automation.

The KNX Security Panel is for universal usage for all kinds of hazardous situations in buildings like intrusion, personal attack, smoke, gas- and water leakage.

ABB i-bus® KNX

Security and Surveillance – The new KNX Security Panel



KNX Security Panel without cover, integrated zone modules and batteries

- ↔ Ethernet connection for programming, diagnostics and operation via a standard webbrowser
 - ← Direct inputs for security sensors
 - ↔ Keypads
 - Internal, external or remote alarming
 - ↔ Security bus for security sensors, zone modules and setting devices
-
- ↔ KNX interface to display alarm states via displays of building automation and to control automatic building functions with support of security sensors.

The KNX Security Panel provides all needed system interfaces: An ethernet connection is used for programming, diagnostics and operation via a standard webbrowser as well as integration into the building network. The security sensors will be connected directly to the panel inputs or via the security bus, where the setting device for the system is also connected. Furthermore the panel provides interfaces for the also newly developed keypads and for internal, external or remote alarming. Finally the integrated KNX interface allows on the one hand to display alarm states via displays of building automation and on the other to control automatic building functions with support of security sensors.

Electrical installation solutions for buildings – Technical details

Intrusion Alarm Systems

Index

Alarm panels	17/2
Arming devices	17/4
Indoor sensors	17/5
Outdoor sensors	17/9
Technical detectors	17/13
Signalling devices	17/16
Accessories	17/17

Intrusion Alarm Systems

ABB-secure@home



ABB-secure@home central units

Description	GSM	ABB-free@home®	Color	Type	Order number	Pack unit
Central unit	•	•	Glass white	SAS-W1.1E	2CSY233921R0003	1
Central unit		•	Glass white	SAS-W2.1E	2CSY245181R0004	1
Central unit	•	•	Glass black	SAS-W1.1F	2CSY233541R0003	1
Central unit		•	Glass black	SAS-W2.1F	2CSY255461R0004	1
Central unit			White	SAS-W3.1E	2CSY234925R0005	1
Spare batteries						
Rechargeable battery pack, Ni-Mh, 6 V, 1.6 Ah				SBA-W1.1	2CSY255111R0801	1



System capability



Device type	Max. no. of devices	Max. no. of zones
Anti-intrusion	Indoor and outdoor volumetric passive infrared detectors Magnet reed contacts	64
Home safety	Flood detectors, optical smoke detectors, heat detectors	1 active 24 h
Signaling	Outdoor sirens	4
Control	Remote controls, security keypads	16
Others	Wireless repeaters, wired interface	4

Communication between central unit and devices is wireless based on a radio frequency signal that ensures the reliability and the security of the communication itself.



Bidirectional



Indoor



**Rechargeable
battery backup
up to 30 h**



**Direct 230 V
power supply**



Up to 7 zones



**Integrated indoor
siren up to 95 db
at 1 m**



**Capacitive touch
keypad**

Reliability

ABB-secure@home wireless communication operates at 868.3MHz. It is a frequency band regulated by European norms (ERCREC-70-3E) much less crowded than the traditional one of 434MHz, with a power of 25mW and considered as privileged. In addition the components are ETSI-RED (Radio Equipment Directive) 2014/53/EU compliant. The alarm system uses an ABB owner communication protocol, optimized to the best ratio distance over energy consumption and it is classified as long range wireless communication, since it supports an alarm system up to 300m in free field. The bidirectional transmission let know the status of each single component, because the sensor receives instructions from the central unit and sends back messages when the action is accomplished.

Security

ABB-secure@home counts on a digital encrypted communication with 128 bits and it is supplied with a 65k rolling code remote control which creates unique code each time a command is sent to prevent it from being maliciously copied and replicated. Moreover the bidirectional communication let the central unit know the state of each controlled device, as battery charge state, state of functioning and if any infringement has been done. The multiple access (CSMA) transmission system, avoid interferences, disturbances and signal collisions.

Intrusion Alarm Systems

ABB-secure@home

The central unit is able to manage up to seven security zones, set as anti-burglar type (armed/disarmed), one safety zone, set as technical alarm always-on, and one zone dedicated to system devices. Each zone of the anti-theft system can be activated in three different modes:

	User	System activation after a detection
Notification mode	Located inside the apartment, office, shop	Notification only (e.g., SMS)
Home mode		Internal warning only (e.g., indoor siren)
Away mode	Located outside	All possible notifications (external and indoor siren, SMS, actuations)



USB connection



PC connection

The central unit provides two USB ports:

- 1 USB type A for updating the central unit firmware via USB stick
- 1 USB type B port for connection via USB type B cable to a computer with maintenance software

Electrical specifications:

- Power supply: 230 VAC ± 10%, 50/60 Hz
- Max. current: 45 mA
- Backup battery: Ni-Mh rechargeable, 6 V, 1.600 mAh

Dimensions (LxHxD):

- Square shaped: 273 x 188 x 48 mm

Conditions of use:

- Environmental class: I (indoor)
- Operating temperature: -5 °C to +45 °C
- Relative humidity: 75% average, non-condensing, 90% peak
- Installation: wall-mounted

Communication technologies:

- Safety devices: bidirectional FM transmission at 868.3 MHz
- Range in free field: 300 m
- For GSM models only:
 - Dual band GSM/UMTS module 900 MHz/1.800 MHz
 - Internal antenna
- ABB-free@home® 2-wire bus

Other features:

- Backlit LCD display, 128 x 64 pixels
- Indoor siren: built-in piezo siren, 95 dB at 1 m
- Protection: anti-tamper, anti-removal

Intrusion Alarm Systems

ABB-secure@home



Preconfigured remote control

Description	Color	Type	Order number	Pack unit
Preconfigured remote control	Glass black	SAD-W1.1F	2CSY202821R0305	1
Preconfigured remote control	Black	SAD-W3.1F	2CSY295161R1058	1
Spare lithium button battery, 3 V (CR2032), normally available on the market				



Bidirectional



Battery
up to 5 years

- Power supply: 1 lithium battery type CR2032, 3 V, 220 mAh
- Battery life: 5 years
- Protection: IP32
- Operating temperature: -5 °C to +55 °C
- Relative humidity: max. 93 % (non-condensing)
- Environment: indoors, outdoors
- Range in free field: 200 m
- Local signals: 5 LEDs red/green/orange
- Dimensions (LxHxD): 40 x 78 x 10 mm



Remote control

Description	Color	Type	Order number	Pack unit
Remote control	Glass black	SAD-W2.1F	2CSY251641R0306	1
Remote control	Black	SAD-W4.1F	2CSY277102R0301	1
Spare lithium button battery, 3 V (CR2032), normally available on the market				



Bidirectional



Battery
up to 5 years

- Power supply: 1 lithium battery type CR2032, 3 V, 220 mAh
- Battery life: 5 years
- Protection: IP32
- Operating temperature: -5 °C to +55 °C
- Relative humidity: max. 93 % (non-condensing)
- Environment: indoors, outdoors
- Range in free field: 200 m
- Local signals: 5 LEDs red/green/orange
- Dimensions (LxHxD): 40 x 78 x 10 mm

Intrusion Alarm Systems

ABB-secure@home



Perimeter magnet reed contact detector

Description	Color	Type	Order number	Pack unit
Universal perimeter detector	White	SMC-W1.1A	2CSY255791R0104	1
Universal perimeter detector	Brown	SMC-W1.1D	2CSY255731R0104	1
Spare lithium battery 3 V, 1.4 Ah	-	SBA-W2.1	2CSY255331R0802	1

- Bidirectional**
- Indoor**
- Battery up to 5 years**

- Power supply: lithium battery 3 V, 1.4 Ah
- 30-day guaranteed operation from low battery signal
- Battery life: 5 years with average use of 10 opening/closing operations daily
- Protection degree: IP30
- Dimensions (LxHxD): detector 31 x 106 x 35 mm, magnet 8 x 56 x 10 mm
- Color: white or brown
- Operating temperature: -5 °C to +45 °C
- Relative humidity: max. 93 % (non-condensing)
- Usage environment: indoors (dry and sheltered places)
- Range in free field: 300 m
- Local signals: 1 calibration LED
- Installation: free
- Protection degree: dual tamper
- Performance level: complies with EN 50131-1 and EN 50131-2-6 Class I standards



Rolling door magnet reed contact

Description	Color	Type	Order number	Pack unit
Magnetic contact for overhead doors	-	SMC-W2.1	2CSY255341R0602	1

This device signals the opening of overhead or sliding doors. It needs to be connected to a perimeter magnet reed contact detector (type codes: SMC-W1.1A or SMC-W1.1D) or to a dual passive IR perimeter motion detector (type codes: SMD-W2.1A or SMD-W2.1D), and is equipped with a 1.2-meter connection cable for this purpose. It is made of aluminum with high resistance to the transit of heavy vehicles. The minimum fixing distance is 20 mm from ferrous materials and 25 mm from non-ferrous materials.

- Protection degree: IP66
- Dimensions (LxHxD): 140 x 15.5 x 42 mm (fixed part) 86 x 25 x 32 mm (moving part)
- Operating temperature: -25 °C to +70 °C

Intrusion Alarm Systems

ABB-secure@home



Roller shutter sensor

Description	Color	Type	Order number	Pack unit
Rope-operated contact for shutters, monitors the opening of windows and doors, complete, for screw-on or drilling	White	SLM-W1.1	2CSY255001R0603	1

The device detects the lifting of shutters through the movement of the retractable rope. It is made of thermoplastic material; the rope is 3.5 m long. It needs to be connected to a perimeter magnet reed contact detector (type codes: SMC-W1.1A or SMC-W1.1D).

- Protection degree: IP40
- Dimensions (LxHxD): 100 x 77 x 15 mm
- Weight: 280 g
- Operating temperature: -25 °C to +70 °C



Magnet reed contact for surface/flush mounting

Description	Color	Type	Order number	Pack unit
Projecting or flush-mounted magnetic contact	White	SMC-W3.1A	2CSY295241R0606	1
Projecting or flush-mounted magnetic contact	Brown	SMC-W3.1D	2CSY295201R0606	1

The device monitors the opening of windows and doors. Installation options:

- Wall-mounted, inserting with pressure the cylindrical parts into 8 mm diameter holes
- Flush-mounted, with the use of the plastic adapters included in the packaging

It needs to be connected to a perimeter magnet reed contact detector (type codes: SMC-W1.1A or SMC-W1.1D) or to a dual passive IR perimeter motion detector (type codes: SMD-W2.1A or SMD-W2.1D) and is equipped with a 1.2-meter connection cable for this purpose. It is made of aluminum with high resistance to the transit of heavy vehicles. The minimum fixing distance is 20 mm from ferrous materials and 25 mm from non-ferrous materials.

- Protection degree: IP66
- Dimensions (LxHxD): 45 x 16.5 x 15 mm
- Weight: 50 g
- Operating temperature: -25 °C to +70 °C



Shock inertial sensor

Description	Color	Type	Order number	Pack unit
Shock inertial sensor	White	SGB-W1.1A	2CSY255871R0604	1

This device detects a possible shock occurring on a door, window, or the surface on which it is installed. Equipped with a 2-meter connection cable, it must be connected to a perimeter magnet reed contact detector (type codes: SMC-W1.1A or SMC-W1.1D). Assembly: projecting on door/window/generic surfaces using screws or double-sided adhesive tape.

- Protection degree: IP54
- Dimensions (LxHxD): 33 x 32.7 x 23.7 mm
- Weight: 40 g
- Operating temperature: -25 °C to +70 °C

Intrusion Alarm Systems

ABB-secure@home



Dual passive IR perimeter motion detector

Description	Color	Type	Order number	Pack unit
Perimeter detector	White	SMD-W2.1A	2CSY235871R0103	1
Perimeter detector	Brown	SMD-W2.1D	2CSY200091R0103	1
Spare lithium battery 3 V, 1.4 Ah	-	SBA-W2.1	2CSY255331R0802	1

-  **Bidirectional**
-  **Indoor**
-  **Battery up to 4 years**

- Power supply: lithium battery 3 V, 1.4 Ah (included in the package)
- 30-day guaranteed operation from low battery signal
- Battery life: 4 years with average use of 10 daily operations
- Protection degree: IP34
- Dimensions (LxHxD): 220 x 38 x 32 mm
- Operating temperature: -20 °C to +55 °C
- Relative humidity: max. 93 % (non-condensing)
- Usage environment: indoors (dry and sheltered places)
- Range in free field: 300 m
- Local signals: 1 red LED
- Detecting element: 2 IR sensors with linear Fresnel lens; 1 external contact with anti-tamper (can be excluded), anti-masking (can be excluded)
- Installation: free
- Anti-tamper protection: anti-opening, anti-tear (optional)

Diagram of side coverage

Typical installation between window and blind.







Diagram of top coverage



Side installation for large openings with two opposing devices.



Intrusion Alarm Systems

ABB-secure@home



Indoor passive IR motion detector

Description	Color	Type	Order number	Pack unit
Indoor passive infrared detector	White	SMD-W1.1A	2CSY255701R0105	1
Spare lithium battery 3 V, 1.4 Ah	-	SBA-W2.1	2CSY255331R0802	1
Joint for mounting the IR wall detector	White	SIM-W2.1A	2CSY255101R0607	1



Bidirectional



Indoor




**Battery
up to 4 years**


- Power supply: lithium battery 3 V, 1.4 Ah (included in the package)
- Battery life: 4 years (operation guaranteed 30 days from low battery signal)
- Protection degree: IP30
- Operating temperature: -5 °C to +45 °C
- Relative humidity: max. 95% (non-condensing)
- Environment: indoors
- Range in free field: 300 m
- Detecting elements: 1 IR sensor with Fresnel lens
- Programming elements: 2 jumpers, one for testing, one for pulse counting
- Local signals: 1 LED
- Anti-tamper protection: lid opening tamper
- Dimensions (LxHxD): 70 x 114 x 128 mm

Long distance coverage

Top view




Side view




No reaction

Only upper IR beam is crossed




Wide coverage angle

Top view



Side view



No reaction

Only lower IR beam is crossed



Alarm

Both IR beams are crossed



Intrusion Alarm Systems

ABB-secure@home



Perimeter bidirectional dual passive IR motion detector

Description	Color	Type	Order number	Pack unit
Perimeter bidirectional dual passive IR motion detector	White	SMD-W4.1A	2CSY254971R0202	1
Lithium battery, 3 V, 1.4 Ah	-	SBA-W2.1	2CSY255331R0802	1

Bidirectional




- Power supply: lithium battery 3 V, 1.4 Ah (included in the package)
- Battery life: 4 years (operation guaranteed 30 days from low battery signal)
- Protection degree: IP55
- Environment: outdoors
- Range in free field: 300 m
- Detecting elements: no. 4 sensors

Outdoor


- Programming elements: a 3-way DIP switch
- 1 sensitivity switch
- Local signals: 2 LEDs
- Anti-tamper protection: cover opening
- Dimensions (LxHxD): 56 x 235 x 128 mm
- Operating temperature: -15 °C to +55 °C
- Relative humidity: max. 93 % (non-condensing)

Battery up to 3 years

Diagram of side coverage



No reaction
Only upper IR beam is crossed



No reaction
Only lower IR beam is crossed






Diagram of top coverage



Alarm
Both IR beams are crossed




Intrusion Alarm Systems

ABB-secure@home





Compact dual passive IR perimeter motion detector

Description	Color	Type	Order number	Pack unit
Compact dual passive IR perimeter motion detector	White	SMD-W5.1A	2CSY254981R0203	1
Lithium battery, 3 V, 1.4 Ah	-	SBA-W2.1	2CSY255331R0802	1

-  **Bidirectional**
-  **Outdoor**
-  **Battery up to 3 years**

- Power supply: lithium battery 3 V, 1.4 Ah (included in the package)
- Battery life: 4 years (operation guaranteed 30 days from low battery signal)
- Protection degree: IP55
- Dimensions (LxHxD): 35 x 155 x 85 mm
- Operating temperature: -15 °C to +55 °C
- Relative humidity: max. 93 % (non-condensing)
- Range in free field: 300 m
- Detecting element: 2 IR sensors
- Programming elements: 1 DIP switch (with 6 switches)
- Local signals: no. 1 LED
- Anti-tamper protection: cover opening

Diagram of side coverage



No reaction
Only upper IR beam is crossed





Diagram of top coverage



Can be rotated 95° to either side (5° steps)

No reaction
Only lower IR beam is crossed



Alarm
Both IR beams are crossed



Intrusion Alarm Systems

ABB-secure@home



Outdoor dual passive IR motion detector


Description	Color	Type	Order number	Pack unit
Outdoor dual passive IR motion detector	White	SMD-W3.1A	2CSY255211R0201	1
Lithium battery, 3 V, 1.4 Ah	-	SBA-W2.1	2CSY255331R0802	1

- Bidirectional
- Outdoor
- Battery up to 3 years


- Power supply: lithium battery 3 V, 1.4 Ah (included in the package)
- Battery life: 3 years (operation guaranteed 30 days from low battery signal)
- Protection degree: IP55
- Operating temperature: -15 °C to +55 °C
- Relative humidity: max. 93 % (non-condensing)
- Environment: outdoors
- Range in free field: 300 m
- Detecting element: no. 2 IR sensors
- Programming elements: no. 2 DIP switches (with 3 and 6 switches)
- Local signals: no. 1 LED
- Anti-tamper protection: cover opening
- Dimensions (LxHxD): 71 x 186 x 105 mm

Diagram of side coverage


Detector position 1 (12 m average coverage area)




Detector position 2 (8.5 m average coverage area)




Detector position 3 (6 m average coverage area)



Detector position 4 (3.5 m average coverage area)



Detector position 5 (2.5 m average coverage area)



No reaction

Only upper IR beam is crossed





Diagram of top coverage



No reaction

Only lower IR beam is crossed



Alarm

Both IR beams are crossed



Intrusion Alarm Systems

ABB-secure@home



Outdoor dual passive IR motion detector for height

Description	Color	Type	Order number	Pack unit
Outdoor dual passive IR motion detector for height	White	SMD-W6.1A	2CSY255311R0204	1
Lithium battery, 3 V, 1.4 Ah	-	SBA-W2.1	2CSY255331R0802	1

- Bidirectional
- Outdoor
- Battery up to 3 years

- Power supply: lithium battery 3 V, 1.4 Ah (included in the package)
- Battery life: 4 years (with 120 s active interdiction)
- Operation guaranteed 30 days from low battery signal
- Protection degree: IP55
- Operating temperature: -20 °C to +60 °C
- Relative humidity: max. 95% (non-condensing)
- Range in free field: 300 m
- Detecting element: 2 IR sensors
- Programming elements: 1 DIP switch (with 6 switches) – 2 sensitivity selectors
- Local signals: no. 1 LED
- Tamper protection
- Dimensions (LxHxD): detector with joint 99 x 205 x 266 mm coverage, detector without joint 92 x 198 x 148 mm

Diagram of side coverage







Diagram of top coverage



No reaction
Only upper IR beam is crossed



No reaction
Only lower IR beam is crossed



Alarm
Both IR beams are crossed



Intrusion Alarm Systems

ABB-secure@home



ABB-Secure@home wireless interface module for Busch-Smoke alarm detector

Description	Color	Type	Order number	Pack unit
Smoke/heat detector interface module	-	STD-W1.1	2CSY254961R0701	1

The device is required for interfacing the smoke detectors (order number: 2CKA006800A2721) or heat detectors (order number: 2CKA006800A2723) with the central unit.



Bidirectional

The module is equipped with an integrated lithium battery with a minimum life of ten years. The device features bidirectional communication with the central unit that supervises it with a programmable supervision interval (typically every 15 minutes). During installation/programming it is possible to change the supervision interval through the specific functions available on the central unit.



Indoor



**Battery
10 years**

- Power supply: lithium battery 3 V, not replaceable
- Battery life: 10 years
- Installation: inside a smoke detector, heat detector
- Communication technology: FM 868.3 MHz transmission
- Range in free field: 300 m

Intrusion Alarm Systems

ABB-secure@home



Smoke detector

Description	Color	Type	Order number	Pack unit
Optical smoke detector	White	6833/01-84-500	2CKA006800A2721	1




Bidirectional




Indoor



**Battery
10 years**



Coverage area (radius 7,5 m)



Maximum height (6 m)

- Power supply: lithium battery 3 V, not replaceable
- Battery life: 10 years
- Dimensions (diameter x D): 120 mm x 47.5 mm
- Local signals: alarm (LED and buzzer), low battery (LED)
- Installation: ceiling



Heat detector

Description	Color	Type	Order number	Pack unit
Heat detector	White	6835/01-84-500	2CKA006800A2723	1




Bidirectional




Indoor



**Battery
10 years**



Coverage area (radius 7,5 m)



Maximum height (6 m)

- Power supply: lithium battery 3 V, not replaceable
- Battery life: 10 years
- Dimensions (diameter x D): 120 x 55 mm
- Color: white
- Usage environment: indoors
- Local signals: acoustic horn, sound pressure 85 dB at 3 m
- 1 alarm LED – low battery
- Installation: ceiling

Intrusion Alarm Systems

ABB-secure@home



Water detector

Description	Color	Type	Order number	Pack unit
Flood detector	White	STD-W5.1A	2CSY255191R0705	1
Lithium battery, 3 V, 1.4 Ah	-	SBA-W2.1	2CSY255331R0802	1



Bidirectional



Indoor



**Battery
up to 3 years**

- Power supply: lithium battery 3 V, 1.4 Ah (included in the package)
- Battery life: 3 years, operation guaranteed 30 days from low battery signal
- Color: white
- Operating temperature: 0 °C to +55 °C

- Range in free field: 300 m
- Local signals: 1 alarm LED
- Dimensions:
interface module: 30 x 36 x 103 mm
flood probe: 40 x 44 x 23 mm
- Connection cable length: 5 m
- Installation: wall

Intrusion Alarm Systems

ABB-secure@home



Outdoor alarm sirens

Description	Color	Type	Order number	Pack unit
Outdoor siren	White	SSD-W1.1A	2CSY277631R0502	1
Outdoor siren	Anthracite	SSD-W1.1B	2CSY229751R0502	1
Outdoor siren	Silver	SSD-W1.1C	2CSY296961R0502	1
Outdoor siren	Silver	SSD-W2.1C	2CSY258212R0501	1
Battery pack, LR20, 7.5 V, 12 Ah	-	SBA-W3.1	2CSY254991R0803	1

- Power supply: no. 1 battery pack LR20 7.5 V (5 type "D" x 1.5 V batteries), 12 Ah
- Operation guaranteed 30 days from low battery signal
- Battery life: 3 years under normal use
- Protection degree: IP55
- Color: silver, flashing orange
- Operating temperature: -20 °C to +55 °C
- Relative humidity: max. 93 % (non-condensing)
- Range in free field: 300 m
- Local signals: 1 trumpet, 100 dBA sound pressure at 3 m, 1x 8-LED flash
- Installation: free
- Anti-tamper protection: anti-opening and anti-removal
- Performance level: complies with EN 50131-1 and EN 50131-4 standards
- Environmental class: III, safety degree: 2
- Dimensions (LxHxD): 210 x 330 x 155 mm



Bidirectional



Outdoor



**Battery
up to 3 years**

Intrusion Alarm Systems

ABB-secure@home



Wireless repeater

Description	Color	Type	Order number	Pack unit
Wireless repeater	-	SIM-W1.1	2CSY255201R0601	1
Lithium battery, 3 V, 1.4 Ah	-	SBA-W2.1	2CSY255331R0802	1

-  **Bidirectional**
-  **Indoor**
-  **Battery up to 3 years**

- Power supply: 4 3 V DC batteries (included) or external 5 V DC plug-in power supply (optional, not included)
- Battery life: 3 years without 220 V power supply with 4 batteries installed (capacity $1.4 \text{ Ah} \times 4 = 5.6 \text{ Ah}$)
- Protection: IP20
- Dimensions (LxHxD): 97 x 97 x 35 mm
- Color: white
- Operating temperature: -5°C to $+45^{\circ}\text{C}$
- Relative humidity: 93 % max. (non-condensing)
- Usage environment: indoors, in a dry, sheltered place
- Communication technology: FM 868,3 MHz transmission
- Range in free field: 300 m
- Programming elements: no. 1 button
- Signaling elements: none
- Installation: wall
- Tamper protection: anti-tamper and anti-burglary

Notes

Electrical installation solutions for buildings – Technical details

Consumer units

Index

UK600 Series	19/2
MISTRAL41F/41W	19/9
MISTRAL65/65H	19/20
basic E	19/27
Mini Europa40	19/32
IP 40 and IP 55 panel fronts	19/34

Consumer units technical details


UK600 Series

UK600 IP30 Flush & hollow wall mounting consumer units

Codes	UK61...	UK62...	UK63...	UK64...	UK66...
Number of Modules	12	24	36	48	60
Colour	RAL 9016 white				
Without door	YES	YES	YES	YES	YES
With opaque door	YES	YES	YES	YES	YES
With transparent door	NO	NO	NO	NO	NO
Double Insulation	YES	YES	YES	YES	YES
Resistance to Heat	GWT 850 °C				
Type of Material	Thermo-plastic, Sheet steel				
Shock Resistance	2 Joule (IK 07)				
Installation Temperature	-5 °C ÷ +40 °C				
Protection degree	IP 30				
Maximum current	63 A				
Max Dissipation Power	31 W	45 W	54 W	62 W	69 W
Cable Holding System by hollow wall mounting	YES	YES	YES	YES	YES
Designed for Input	push and stay design				
Extractable Frame	YES	YES	YES	YES	YES
Media Enclosures	NO	YES	YES	YES	YES

Consumer units technical details


UK600 Series



Type	Allowed power loss Pzul according to DIN 43671 (W)			Max. output capacity P de in accordance with DIN VDE 60670-24 (W)	Dimensions in mm			
	20KΔT	25KΔT	30KΔT		30KΔT	H1	H2	H3
UK61..	10.0	13.0	16.0	31.0		372	302	325
UK62..	11.5	15.0	19.0	45.0		497	427	450
UK63..	14.5	19.0	24.0	54.0		622	552	575
UK64..	16.5	21.5	27.0	62.0		747	677	700
UK66..				69.0		872	802	825

Consumer units technical details


UK600 Series – Media enclosure



Type	Allowed power loss Pzul according to DIN 43671 (W)			Max. output capacity P de in accordance with DIN VDE 60670-24 (W)	Dimensions in mm		
	20KΔT	25KΔT	30KΔT		H1	H2	H3
UK62..	11.5	15.0	19.0	100.0	497	427	450
UK63..	14.5	19.0	24.0	114.0	622	552	575
UK64..	16.5	21.5	27.0	133.0	747	677	700
UK65..				155.0	872	802	825
UK66..							

Consumer units technical details


UK600 Series – Combi enclosure



Type	Allowed power loss Pzul according to DIN 43671 (W)			Max. output capacity P de in accordance with DIN VDE 60670-24 (W)	Dimensions in mm	
	20kA	25kA	30kA		H1	H2
UK662CV				78.0	424	353
UK665CV				73.0	549	228
UK662CW				75.0	424	353
UK665CW				71.0	549	228

Consumer units technical details


UK600 Series – Trim frame and door



Dimensions in mm		
Type	H1	H2
BL610	302	372
BL620	497	427
BL630	622	552
BL640	747	677
BL650	872	802

Consumer units technical details


UK600 Series – Interchangeable design frame



Type	Dimensions in mm				Technical specifications LED panel			
	H1	H2	H3	H4	Type	U	P	Colour temperature
BL520D	507	457	427	469	UZD624	12V DC	9.60 W	4200 K
BL630D	632	582	552	594	UZD634	12V DC	13.20 W	4200 K
BL640D	757	707	677	719	UZD644	12V DC	15.60 W	4200 K
BL650D	882	832	802	844	UZD654	12V DC	19.60 W	4200 K

Consumer units technical details

UK600 Series



Dimensions in mm

Type	Niche dimensions brick wall H1	Wall cut out hollow wal H2
UK61...	355	328
UK62...	480	453
UK63...	605	578
UK64...	730	703
UK65...	855	828
UK66...		

Consumer units technical details

MISTRAL41F/41W

Table of resistance to chemical agents

	Cold water	Hot water	Sulphuric acid	Hydrochloric acid	Acetic acid	Petroleum	Benzine	Acetone	Ethyl alcohol	Ammonia	Dichloromethane	Diesel oil - Naptha	Mineral oil	Food oils	Tetrachloroethylene	Trichloroethylene	Ether	Ozone	Toluene	Methyl alcohol	Alcohol	Milk	Fruit juices	Fluorocarbons	Detergives	Detergents	Potassium nitrate	Hydrogen peroxide
MISTRAL41F – Flush-mounted	■	■	□	●	■	●	●	●	□	■	●	□	■	■	●	●	●	■	□	■	■	■	●	■	■	■	■	
MISTRAL41W – Wall-mounted	■	■	□	●	■	●	●	●	□	■	●	□	■	■	●	●	●	■	□	■	■	■	●	■	■	■	□	■

■ resistant □ partially resistant ● non resistant

Consumer units technical details

MISTRAL41F/41W

MISTRAL41F – Technical details

Codes	1SLM004101A1202	1SLM004101A1203	1SLM004101A1204	1SLM004101A1205		
	1SLM004100A1100	1SLM004100A1101	1SLM004100A1102	1SLM004100A1103	1SLM004100A1104	1SLM004100A1105
	1SLM004100A1200	1SLM004100A1201	1SLM004100A1202	1SLM004100A1203	1SLM004100A1204	1SLM004100A1205
Number of modules	4	6	8	12	18	24
Dimensions (W x H x D) in mm	152 x 202 x 105	192 x 202 x 105	232 x 250 x 108	320 x 250 x 108	430 x 250 x 108	320 x 435 x 108
Colour	RAL 9016 white					
Door type	Transparent / opaque					
Protection class	II <input checked="" type="checkbox"/>					
Fire resistance	GWT 650 °C					
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts	IK08	IK08	IK08	IK08	IK08	IK08
Reference standard	IEC 60670					
Installation temperature	-15°C / + 60 °C	15°C / + 60 °C				
Resistance to heat	BPT 70°C	BPT 70 °C				
IP rating	IP41	IP41	IP41	IP41	IP41	IP41
Max. dissipation power	11 W	14 W	18 W	22 W	27 W	41 W
Extractable frame	Yes	Yes	Yes	Yes	Yes	Yes
Maximum current	63A	63 A	63 A	63 A	125 A	63 A
DIN rail centre distance –	–	–	–	–	–	150 mm
Halogen free	Yes	Yes	Yes	Yes	Yes	Yes
Cable entry	Knockout	Knockout	Flange multi pre-cuts	Flange multi pre-cuts	Flange multi pre-cuts	Flange multi pre-cuts

Codes	1SLM004101A1206	1SLM004101A1207	1SLM004101A1208	1SLM004101A1209	1SLM004101A1210
	1SLM004100A1106	1SLM004100A1107	1SLM004100A1108	1SLM004100A1109	1SLM004100A1110
	1SLM004100A1206	1SLM004100A1207	1SLM004100A1208	1SLM004100A1209	1SLM004100A1210
Number of modules	36 (2 x 18)	36 (3 x 12)	48	54	72
Dimensions (W x H x D) in mm	430 x 435 x 108	320 x 600 x 108	320 x 735 x 108	430 x 600 x 128	430 x 735 x 128
Colour	RAL 9016 white				
Door type	Transparent / opaque				
Protection class	II <input checked="" type="checkbox"/>				
Fire resistance	GWT 650 °C				
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts	IK08	IK08	IK08	IK08	IK08
Reference standard	IEC 60670				
Installation temperature	-15°C / + 60 °C	15°C / + 60 °C	-15°C / + 60 °C	-15°C / + 60 °C	-15°C / + 60 °C
Resistance to heat	BPT 70 °C				
IP rating	IP41	IP41	IP41	IP41	IP41
Max. dissipation power	47 W	50 W	59 W	59 W	82 W
Extractable frame	Yes	Yes	Yes	Yes	Yes
Maximum current	125 A	100 A	100 A	125 A	125 A
DIN rail centre distance	150 mm				
Halogen free	Yes	Yes	Yes	Yes	Yes
Cable entry	Flange multi pre-cuts				

Note: the versions with box and frontal splitted have the same characteristics of standard product

Consumer units technical details

MISTRAL41F/41W

MISTRAL41F & Multimedia – Technical details

Codes	1SLM004100A1300	1SLM004100A1301	1SLM004100A1302	1SLM004100A1303	1SLM004100A1304	1SLM004100A1305
	1SLM004100A1400	1SLM004100A1401	1SLM004100A1402	1SLM004100A1403	1SLM004100A1404	1SLM004100A1405
	1SLM004100A6305					
Number of modules	4	6	8	12	18	24
Dimensions (W x H x D) in mm	152 x 202 x 105	192 x 202 x 105	232 x 250 x 108	320 x 250 x 108	430 x 250 x 108	320 x 435 x 108
Colour	RAL 9016 white					
Door type	Transparent / opaque					
Protection class	II □					
Fire resistance	GWT 850 °C					
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts	IK08	IK08	IK08	IK08	IK08	IK08
Reference standard	IEC 60670					
Installation temperature	-15°C / + 60 °C	15°C / + 60 °C				
Resistance to heat	BPT 70 °C					
IP rating	IP41	IP41	IP41	IP41	IP41	IP41
Max. dissipation power	11 W	14 W	18 W	22 W	27 W	41 W (Multimedia 61 W)
Extractable frame	Yes	Yes	Yes	Yes	Yes	Yes
Maximum current	63 A	63 A	63 A	63 A	125 A	63 A
DIN rail centre distance –	–	–	–	–	–	150 mm
Halogen free	Yes	Yes	Yes	Yes	Yes	Yes
Cable entry	Flange with knockouts					

Codes	1SLM004100A1306	1SLM004100A1307	1SLM004100A1308	1SLM004100A1309	1SLM004100A1310
	1SLM004100A1406	1SLM004100A1407	1SLM004100A1408	1SLM004100A1409	1SLM004100A1410
	1SLM004100A6307		1SLM004100A6309		
Number of modules	36 (2 x 18)	36 (3 x 12)	48	54	72
Dimensions (W x H x D) in mm	430 x 435 x 108	320 x 600 x 108	320 x 735 x 108	430 x 600 x 128	430 x 735 x 128
Colour	RAL 9016 white	RAL 9016 white	RAL 9016 white	RAL 9016 white	RAL 9016 white
Door type	Transparent / opaque	Transparent / opaque	Transparent / opaque	Transparent / opaque	Transparent / opaque
Protection class	II □	II □	II □	II □	II □
Fire resistance	GWT 850 °C	GWT 850 °C	GWT 850 °C	GWT 850 °C	GWT 850 °C
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts	IK08	IK08	IK08	IK08	IK08
Reference standard	IEC 60670	IEC 60670	IEC 60670	IEC 60670	IEC 60670
Installation temperature	-15°C / + 60 °C	15°C / + 60 °C	-15°C / + 60 °C	-15°C / + 60 °C	-15°C / + 60 °C
Resistance to heat	BPT 70 °C	BPT 70 °C	BPT 70 °C	BPT 70 °C	BPT 70 °C
IP rating	IP41	IP41	IP41	IP41	IP41
Max. dissipation power	47 W	50 W (Multimedia 63 W)	59 W	59 W (Multimedia 74 W)	82 W
Extractable frame	Yes	Yes	Yes	Yes	Yes
Maximum current	125 A	100 A	100 A	125 A	125 A
DIN rail centre distance	150 mm	150 mm	150 mm	150 mm	150 mm
Halogen free	Yes	Yes	Yes	Yes	Yes
Cable entry	Flange with knockouts	Flange with knockouts	Flange with knockouts	Flange with knockouts	Flange with knockouts

Note: the versions with box and frontal splitted have the same characteristics of standard product

Consumer units technical details

MISTRAL41F/41W

MISTRAL41W & Multimedia – Technical details

Codes	1SPE007717F0200	1SPE007717F0300	1SPE007717F0400	1SPE007717F0800	1SPE007717F0500
	1SPE007717F0210	1SPE007717F0310	1SPE007717F0410	1SPE007717F0810	1SPE007717F0510
	1SPE007717F0100	1SPE007717F0220	1SPE007717F0320	1SPE007717F0420	1SPE007717F0820
1SLM004100A7105					
Number of modules	2	4	8	12	18
Dimensions (W x H x D) in mm	68 x 210 x 93	96 x 210 x 93	202 x 257 x 120	292 x 257 x 120	382 x 257 x 120
Colour	RAL 9016 white	RAL 9016 white	RAL 9016 white	RAL 9016 white	RAL 9016 white
Door type	No door	No door / transparent / opaque			
Protection class	II □	II □	II □	II □	II □
Fire resistance	GWT 650°C	GWT 650 °C	GWT 650 °C	GWT 650 °C	GWT 650 °C
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts	IK08	IK08	IK08	IK08	IK08
Reference standard	IEC 60670	IEC 60670	IEC 60670	IEC 60670	IEC 60670
Installation temperature	-15 °C / + 60 °C	-15 °C / + 60 °C	-15 °C / + 60 °C	-15 °C / + 60 °C	-15 °C / + 60 °C
Resistance to heat	BPT 70°C	BPT 70 °C	BPT 70 °C	BPT 70 °C	BPT 70 °C
IP rating	IP41	IP41	IP41	IP41	IP41
Max. dissipation power	9,2W	9,3 W	17,7 W	23,8 W	29,8 W
					30,2 W (Multimedia 41 W)
Maximum current	63A	63 A	63 A	63 A	63 A
DIN rail centre distance –	–	–	–	–	125 mm
Halogen free	Yes	Yes	Yes	Yes	Yes
Cable entry	Smooth	Smooth	Smooth	Smooth	Smooth

Codes	1SPE007717F0900	1SPE007717F0600	1SPE007717F0700	1SPE007717F1000	1SPE007717F1100
	1SPE007717F0910	1SPE007717F0610	1SPE007717F0710	1SPE007717F1010	1SPE007717F1110
	1SPE007717F0920	1SPE007717F0620	1SPE007717F0720	1SPE007717F1020	1SPE007717F1120
1SLM004100A7107					1SLM004100A7109
Number of modules	36 (2 x 18)	36 (3 x 12)	48	54	72
Dimensions (W x H x D) in mm	382 x 382 x 120	292 x 507 x 120	292 x 656 x 120	382 x 507 x 120	382 x 656 x 120
Colour	RAL 9016 white				
Door type	No door / transparent / opaque				
Protection class	II □				
Fire resistance	GWT 650 °C				
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts	IK08	IK08	IK08	IK08	IK08
Reference standard	IEC 60670				
Installation temperature	-15 °C / + 60 °C	15 °C / + 60 °C	-15 °C / + 60 °C	-15 °C / + 60 °C	-15 °C / + 60 °C
Resistance to heat	BPT 70 °C				
IP rating	IP41	IP41	IP41	IP41	IP41
Max. dissipation power	37,5 W	36,8 W (Multimedia 48 W)	44,8 W	45,2 W (Multimedia 52 W)	54,4 W
Maximum current	63 A				
DIN rail centre distance	125 mm				
Halogen free	Yes	Yes	Yes	Yes	Yes
Cable entry	Smooth	Smooth	Smooth	Smooth	Smooth

Note: the versions with box and frontal splitted have the same characteristics of standard product

Consumer units technical details

MISTRAL41F/41W

MISTRAL41W – Technical details

Codes	1SPE007717F1500	1SPE007717F1600	1SPE007717F1700	1SPE007717F1800	1SPE007717F2200	1SPE007717F1900
Number of modules	2	4	8	12	18	24
Dimensions (W x H x D) in mm	68 x 210 x 93	96 x 210 x 93	202 x 257 x 120	292 x 257 x 120	382 x 257 x 120	292 x 382 x 120
Colour	RAL 9016 white	RAL 9016 white				
Door type	No door	No door				
Protection class	II □	II □				
Fire resistance	GWT 750 °C	GWT 750 °C				
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts	IK08	IK08	IK08	IK08	IK08	IK08
Reference standard	IEC 60670	IEC 60670				
Installation temperature	-15 °C / + 60 °C	15 °C / + 60 °C				
Resistance to heat	BPT 70 °C	BPT 70 °C				
IP rating	IP41	IP41	IP41	IP41	IP41	IP41
Max. dissipation power	9,2 W	9,3 W	17,7 W	23,8 W	29,8 W	30,2 W
Maximum current	63 A	63 A				
DIN rail centre distance	–	–	–	–	–	125 mm
Halogen free	No	No	No	No	No	No
Cable entry	Smooth	Smooth	Smooth	Smooth	Smooth	Smooth

Codes	1SPE007717F2300	1SPE007717F2000	1SPE007717F2100	1SPE007717F2400	1SPE007717F2500
Number of modules	36 (2 x 18)	36 (3 x 12)	48	54	72
Dimensions (W x H x D) in mm	382 x 382 x 120	292 x 507 x 120	292 x 656 x 120	382 x 507 x 120	382 x 656 x 120
Colour	RAL 9016 white	RAL 9016 white	RAL 9016 white	RAL 9016 white	RAL 9016 white
Door type	No door	No door	No door	No door	No door
Protection class	II □	II □	II □	II □	II □
Fire resistance	GWT 750 °C	GWT 750 °C	GWT 750 °C	GWT 750 °C	GWT 750 °C
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts	IK08	IK08	IK08	IK08	IK08
Reference standard	IEC 60670	IEC 60670	IEC 60670	IEC 60670	IEC 60670
Installation temperature	-15 °C / + 60 °C	15 °C / + 60 °C	-15 °C / + 60 °C	-15 °C / + 60 °C	-15 °C / + 60 °C
Resistance to heat	BPT 70 °C	BPT 70 °C	BPT 70 °C	BPT 70 °C	BPT 70 °C
IP rating	IP41	IP41	IP41	IP41	IP41
Max. dissipation power	37,5 W	36,8 W	44,8 W	45,2 W	54,4 W
Maximum current	63 A	63 A	63 A	63 A	63 A
DIN rail centre distance	125 mm	125 mm	125 mm	125 mm	125 mm
Halogen free	No	No	No	No	No
Cable entry	Smooth	Smooth	Smooth	Smooth	Smooth

Note: the versions with box and frontal splitted have the same characteristics of standard product


Consumer units technical details

MISTRAL41F/41W


Upper and lower knockouts and precuts

Cable entry


Modules (mm)	diam. 40	diam. 32	diam. 25	diam. 20	Flange
4	-	-	3	3	///
6	-	-	5	5	///
8	-	1	9	-	150 x 55
12	1	8	4	-	240 x 55
18	1	12	2	-	330 x 55




4 modules - top and bottom - concrete and hollow wall




6 modules - top and bottom - concrete and hollow wall




8 modules - top and bottom - hollow wall




8 modules - top and bottom - concrete wall




12 modules - top and bottom - hollow wall



12 modules - top and bottom - concrete wall



18 modules - top and bottom - hollow wall



18 modules - top and bottom - concrete wall


Consumer units technical details

MISTRAL41F/41W

Upper and lower knockouts


Box

Modules	diam. 32
4 M	4
6 M	4
8 M	4
12 M	4
18 M	4
24 M	8
36 M - 2F	8
36 M - 3F	12
48 M	16
54 M	12
72 M	16



Side


Modules	diam. 32
4 M	1
6 M	1
8 M	1
12 M	1
18 M	1
24 M	3
36 M - 2F	3
36 M - 3F	4
48 M	5
54 M	4
72 M	5



Consumer units technical details

MISTRAL41F/41W

Overall dimensions








Dimensions in mm

Consumer units technical details

MISTRAL41F/41W

Overall dimensions




Dimensions in mm

Consumer units technical details

MISTRAL41F/41W

Overall dimensions




Dimensions in mm


Consumer units technical details

MISTRAL41F/41W



Overall dimensions




36 modules




54 modules



48 modules



72 modules



Dimensions in mm

Consumer units technical details

MISTRAL65 / 65H

Table of resistance to chemical agents

	Cold water	Hot water	Sulphuric acid	Hydrochloric acid	Acetic acid	Petroleum	Benzine	Acetone	Ethyl alcohol	Ammonia	Dichloromethane	Diesel oil - Naptha	Mineral oil	Food oils	Tetrachloroethylene	Trichloroethylene	Ether	Ozone	Toluene	Methyl alcohol	Alcohol	Milk	Fruit juices	Fluorocarbons	Detergents	Detergents	Potassium nitrate	Hydrogen peroxide
MISTRAL65	■	■	▲	●	■	●	●	●	▲	■	●	▲	■	■	●	●	●	●	●	■	■	■	●	■	■	■	■	
MISTRAL65H MISTRAL65H switchboards	■	■	▲	●	■	●	●	●	▲	■	●	▲	■	■	●	●	●	■	●	■	■	■	●	■	■	■	▲	■


■ resistant ▲ partially resistant ● non resistant

Ingress protection rating IP65

6

First number:
Protection against the penetration of
solid bodies


No dust can penetrate



5

Second number:
Protection against the penetration of water

Water projected with a nozzle from all directions
must not cause damage



Shock resistance (IK) – MISTRAL65: IK09 and MISTRAL65H: IK10

Code IK	00	01	02	03	04	05	06	07	08	09	10
Shock energy (Joule)	not protected	0.15	0.2	0.35	0.5	0.7	1	2	5	10	20

Consumer units technical details

MISTRAL65 / 65H

MISTRAL65 – Technical details

Codes	1SL1103A00 1SL1203A00 1SL1101A00 1SL1201A00 1SL1100A00 1SL1200A00	1SL1104A00 1SL1204A00 1SLM006501A1103 1SLM006501A1203 1SLM006501A1104 1SLM006502A1104 1SLM006502A1203 1SLM006502A1204		
Number of modules	4	8	12	18
Dimensions (W x H x D) in mm	152 x 202 x 117	232 x 250 x 154	320 x 250 x 155	430 x 250 x 155
Color	RAL 7035 grey	RAL 7035 grey	RAL 7035 grey	RAL 7035 grey
Door type	Opaque / Transparent	Opaque / Transparent	Opaque / Transparent	Opaque / Transparent
Protection class	II □	II □	II □	II □
Fire resistance	GWT 650 °C	GWT 650 °C	GWT 650 °C	GWT 650 °C
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Reference standard	IEC 60670 & IEC 61439-3	IEC 60670 & IEC 61439-3	IEC 60670 & IEC 61439-3	IEC 60670 & IEC 61439-3
Resistance to mechanical impacts	IK09	IK09	IK09	IK09
Installation temperature	-25 °C / + 60 °C	-25 °C / + 60 °C	-25 °C / + 60 °C	-25 °C / + 60 °C
Resistance to heat	BPT 70 °C	BPT 70 °C	BPT 70 °C	BPT 70 °C
IP rating	IP65	IP65	IP65	IP65
Max. dissipation power	12W	20W	27W	32W
Maximum current	63A	63A	63A	125A
Extractable frame	no	no	no	yes
Additional module	no	no	yes	yes
Installation of MCCBs	no	yes	yes	yes
DIN rail centre distance	–	–	–	150 – 125 mm
Halogen free	yes	yes	yes	yes
Cable entry finish	Smooth	Smooth	Smooth	Smooth

Codes	1SL1105A00 1SL1205A00 1SLM006501A1105 1SLM006501A1205	1SL1106A00 1SL1206A00 1SLM006501A1106 1SLM006501A1206	1SL1107A00 1SL1207A00 1SLM006501A1107 1SLM006501A1207	1SL1108A00 1SL1208A00 1SLM006501A1108 1SLM006501A1208	1SL1109A00 1SL1209A00 1SLM006501A1109 1SLM006501A1209
Number of modules	36	36	48	54	72
Dimensions (W x H x D) in mm	430 x 435 x 155	320 x 600 x 155	320 x 735 x 155	430 x 600 x 155	430 x 735 x 155
Color	RAL 7035 grey				
Door type	Opaque / Transparent				
Protection class	II □				
Fire resistance	GWT 650 °C				
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts	IK09	IK09	IK09	IK09	IK09
Reference standard	IEC 60670 & IEC 61439-3				
Installation temperature	-25 °C / + 60 °C				
Resistance to heat	BPT 70 °C				
IP rating	IP65	IP65	IP65	IP65	IP65
Max. dissipation power	43 W	51 W	64 W	63 W	81 W
Maximum current	125 A				
Extractable frame	yes	yes	yes	yes	yes
Additional module	yes	yes	yes	yes	yes
Installation of MCCBs	yes	yes	yes	yes	yes
DIN rail centre distance	150 – 125 mm				
Halogen free	yes	yes	yes	yes	yes
Cable entry finish	Smooth	Smooth	Smooth	Smooth	Smooth

Consumer units technical details

MISTRAL65 / 65H

MISTRAL65H – Technical details

Codes	1SLM006500A2110	1SLM006500A2111	1SLM006500A2112	1SLM006500A2113	1SLM006500A2214
	1SLM006500A2210	1SLM006500A2211	1SLM006500A2212	1SLM006500A2213	1SLM006500A3114*
Number of modules	4	8	12	18	24
Dimensions (W x H x D) in mm	152 x 202 x 117	232 x 250 x 154	320 x 250 x 155	430 x 250 x 155	320 x 435 x 155
Color	RAL 7035 grey				
Door type	Opaque/Trasparent	Opaque/Trasparent	Opaque/Trasparent	Opaque/Trasparent	Opaque/Trasparent
Protection class	II □				
Fire resistance	GWT 750 °C				
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts			IK10**		
Reference standards	IEC 62208				
Installation temperature	-25 °C / + 60 °C				
Resistance to heat	BPT 70 °C				
IP rating	IP65	IP65	IP65	IP65	IP65
Max. dissipation power	12W	20W	27W	32W	34W
Maximum current	63A	63A	63A	125A	125A
Extractable frame	no	no	no	no	yes
Additional module	no	no	yes	yes	yes
Installation of MCCBs	no	yes	yes	yes	yes
DIN rail centre distance	–	–	–	–	150 – 125 mm
Halogen free	no	no	no	no	no
Cable entry finish	Smooth/Precut	Smooth/Precut	Smooth/Precut	Smooth/Precut	Smooth/Precut

Codes	1SLM006500A2115	1SLM006500A2116	1SLM006500A2118	1SLM006500A2119
	1SLM006500A2215	1SLM006500A2216	1SLM006500A2218	1SLM006500A2219
	1SLM006500A3115*	1SLM006500A3116*	1SLM006500A2217	1SLM006500A3118*
Number of modules	36	36	48	54
Dimensions (W x H x D) in mm	430 x 435 x 155	320 x 600 x 155	320 x 735 x 155	430 x 600 x 155
Color	RAL 7035 grey	RAL 7035 grey	RAL 7035 grey	RAL 7035 grey
Door type	Opaque/Trasparent	Opaque/Trasparent	Opaque/Trasparent	Opaque/Trasparent
Protection class	II □	II □	II □	II □
Fire resistance	GWT 750 °C	GWT 750 °C	GWT 750 °C	GWT 750 °C
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Resistance to mechanical impacts			IK10**	
Reference standards	IEC 62208	IEC 62208	IEC 62208	IEC 62208
Installation temperature	-25 °C / + 60 °C			
Resistance to heat	BPT 70 °C	BPT 70 °C	BPT 70 °C	BPT 70 °C
IP rating	IP65	IP65	IP65	IP65
Max. dissipation power	43 W	51 W	64 W	63 W
Maximum current	125 A	125 A	125 A	125 A
Extractable frame	yes	yes	yes	yes
Additional module	yes	yes	yes	yes
Installation of MCCBs	yes	yes	yes	yes
DIN rail centre distance	150 – 125 mm			
Halogen free	no	no	no	no
Cable entry finish	Smooth/Precut	Smooth/Precut	Smooth/Precut	Smooth/Precut

* For the switchboards, modules indicate size

** IK08 in the area of knockouts

Consumer units technical details

MISTRAL65 / 65H


Upper and lower knockouts

Cable glands


Modules		diam. 16	diam. 20	diam. 25
4	04 x 1	2	-	-
8	08 x 1	3	3	-
12	12 x 1	2	2	2
24	12 x 2	5	5	2
36	12 x 3	5	5	2
48	12 x 4	5	5	2
18	18 x 1	2	2	2
36	18 x 2	5	5	2
54	18 x 3	5	5	2
72	18 x 4	5	5	2

Holes


Modules		diam. 12	diam. 16	diam. 20	diam. 25	diam. 32
4	04 x 1	4	4	-	-	-
8	08 x 1	-	6	7	2	-
12	12 x 1	-	10	7	4	2
24	12 x 2	-	10	7	4	2
36	12 x 3	-	10	7	4	2
48	12 x 4	-	10	7	4	2
18	18 x 1	-	14	9	4	2
36	18 x 2	-	14	9	4	2
54	18 x 3	-	14	9	4	2
72	18 x 4	-	14	9	4	2




4 modules – top and bottom



8 modules – top and bottom



12 modules – top and bottom




18 modules – top and bottom

Consumer units technical details

MISTRAL65 / 65H

Overall dimensions









Dimensions in mm

Consumer units technical details

MISTRAL65 / 65H

Overall dimensions




Dimensions in mm

Consumer units technical details

MISTRAL65/65H

Fixing template



	A [mm]	B [mm]	C [mm]	D [mm]	E [mm]	F [mm]	G [mm]
4 PLE	-	113	173	-	140	163	223.5
8 PLE	90	194	254.5	180	-	212	272.5
12 PLE	170	282.5	343	180	-	212	272.5
18 PLE	280	392	452.5	125	175	212	272.5
24 PLE	170	282.5	343	310	360	397	457.5
36 PLE - 2 F	280	392	452.5	310	360	397	457.5
36 PLE - 3 F	170	282.5	343	475	525	562	622.5
48 PLE	170	282.5	343	610	660	697	757.5
54 PLE	280	392	452.5	475	525	562	622.5
72 PLE	280	392	452.5	610	660	697	757.5

Consumer units technical details

basic E – Flush-mounted

Technical details

basic E – Flush-mounted

Number of modules	2	4	6	8	12	16	24	36
Dimensions (WxHxD) in mm	120x180x102	155x180x102	190x180x102	230x180x102	300x220x102	230x315x102	300x335x102	300x450x102
Body / Cover Colour	White / White							
Body / Cover Material	Thermoplastic							
	Opaque white							
Door Colour	Transparent grey							
Door Material	Thermoplastic							
Fire Resistance								
Cover-Body, Terminal-Holder	650° C / 850° C							
Installation Temperature	-25 / +60	-25 / +60	-25 / +60	-25 / +60	-25 / +60	-25 / +60	-25 / +60	-25 / +60
Resistance to Heat Cover-Body, Terminal-Holder	650–70° C							
IP rating	IP40							
Max. dissipation power	10 W	14 W	16 W	20 W	27 W	31 W	33 W	40 W
Extractable DIN rail	Yes							
Halogen Free	Yes							
Cable entry	Knockout							
Protection class	II							
Resistance to mechanical impacts	IK08							
Maximum current	63 A							
Resistance to heat	BPT 70° C							
Terminal bars (Number of holes)	–	–	–	2x5	2x13	2x13	2x13	2x21

Number of cable entries for Flush-mounted

basic E Flush-mounted	Module	Top Number of Entries	Bottom Number of Entries	Right Number of Entries	Left Number of Entries	Hole diameter (mm)
	2	2	2	3	3	28
	4	2	2	3	3	28
	6	4	4	2	2	28
	8	4	4	2	2	28
	12	6	6	2	2	28
	16	4	4	2	2	28
	24	6	6	2	2	28
	36	6	6	6	6	28

Consumer units technical details

basic E – Wall-mounted

Technical details

basic E –
Wall-mounted

Number of modules	2	4	6	8	12	16	24	36
Dimensions (WxHxD) in mm	120x180x102	155x180x102	190x180x102	230x180x102	300x220x102	230x315x102	300x335x102	300x450x102
Body / Cover Colour	White / White							
Body / Cover Material	Thermoplastic							
	Opaque white							
Door Colour	Transparent grey							
Door Material	Thermoplastic							
Fire Resistance								
Cover-Body, Terminal-Holder	650° C / 850° C							
Installation Temperature	-25 / +60	-25 / +60	-25 / +60	-25 / +60	-25 / +60	-25 / +60	-25 / +60	-25 / +60
Resistance to Heat Cover-Body, Terminal-Holder	650–70° C							
IP rating	IP40							
Max. dissipation power	10 W	14 W	16 W	20 W	27 W	31 W	33 W	40 W
Extractable DIN rail	Yes							
Halogen Free	Yes							
Cable entry	Knockout							
Protection class	II							
Resistance to mechanical impacts	IK08							
Maximum current	63 A							
Resistance to heat	BPT 70° C							
Terminal bars (Number of holes)	–	–	–	2x5	2x13	2x13	2x13	2x21

Number of cable entries for Wall-mounted

basic E Wall-mounted	Module	Top Number of Entries	Bottom Number of Entries	Hole diameter (mm)
	2	1	1	24
	4	1	1	24
	6	2	2	24
	8	2	2	24
	12	3	3	24
	16	3	3	24
	24	3	3	24
	36	3	3	24




Consumer units technical details


basic E

Overall dimensions


2M Enclosure, dimensions (mm)




Front cover + door



Surface mounted




Surface mounted




Flush mounted


4M Enclosure, dimensions (mm)




Front cover + door



Surface mounted




Surface mounted




Flush mounted


6M Enclosure, dimensions (mm)




Front cover + door



Surface mounted



Surface mounted




Flush mounted

Consumer units technical details


basic E

Overall dimensions


8M Enclosure, dimensions (mm)



12M Enclosure, dimensions (mm)



16M Enclosure, dimensions (mm)




Consumer units technical details


basic E

Overall dimensions

24M Enclosure, dimensions (mm)




36M Enclosure, dimensions (mm)




Consumer units technical details

Mini Europa40


Front view



2 modules




4 modules




6 modules

Side view



2 modules




4-6 modules


Consumer units technical details

Mini Europa40


Drilling sheets



2 modules



4 modules




6 modules

Modules	code
2 modules	1SL2402A00 – 12 422
4 modules	1SL2404A00 – 12 424
6 modules	1SL2406A00 – 12 426


Consumer units technical details

IP 40 panel fronts


Front view



2 modules




3 modules




4 modules

Side view




2-3 modules




4 modules


Drilling sheets



2 modules



3 modules




4 modules

Modules	code
2 modules	12 362
3 modules	12 363
4 modules	12 364


Consumer units technical details

IP 55 panel fronts


Front view



4 modules




6 modules




10 modules

Side view




4-6-10 modules


Drilling sheets



4 modules



6 modules



10 modules

Modules	code
4 modules	12 658
6 modules	12 659
10 modules	12 660

Electrical installation solutions for buildings – Technical details

Automation boards

Index

Compliance with standards and technical characteristics – Gemini	20/2
IP degree of protection – Gemini	20/4
IK degree of resistance to impacts – Gemini	20/5
Double insulation and self-extinguishing tests – Gemini	20/6
Resistance to chemical agents – Gemini	20/7
Integration with ABB products – Gemini	20/8
Disposal instructions	20/9
Overall dimensions – Basic configuration	20/10
Overall dimensions – Components for automation applications	20/13
Overall dimensions – Components for distribution and mixed applications	20/14
Overall dimensions – Casse SR2	20/26
Overall dimensions – SRX enclosures	20/28

Automation boards - technical details

Compliance with standards and technical characteristics – Gemini

Reference Standards

Standard IEC 62208 ("Empty enclosures for low voltage switch-gear and control gear assemblies. General requirements"), that has implemented at an international level the Standard EN 50298, presently EN 62208, is the prescriptive reference for Gemini switchboards.

The object of Standard CEI EN 50298 is to formulate definitions, classifications, characteristics and test prescriptions for cases designed to be used as part of protection and operating equipment (switchboards) in compliance with the Standards of the EN 61439 series, that have a maximum rated voltage of 1000 V in alternating current for maximum frequencies of 1000 Hz or 1500 V in direct current and are suitable for general use in both internal and external applications.

The Standard applies to empty enclosures, before the user has installed protection and operating devices inside them. The Standard does not apply to enclosures with structural and functional characteristics that make them subject to other prescriptions (e.g. cases for domestic installations and the like). In this case Standards IEC 60670 – CEI 23-48 ("General requirements for enclosures for accessories for household and similar fixed electrical installations") and CEI 23-49 ("Enclosures for accessories for household and similar fixed electrical installations. Part 2: particular requirements for enclosures for protection devices and accessories dissipating a considerable power in normal use") apply. On the basis of the indications of the ABB SACE technical characteristics' table, the installer may have to certify compliance with Standards CEI 23-51 – EN 61439 – CEI 17-13-1 ("Part 1: standard equipment subject")

Automation boards - technical details

Compliance with standards and technical characteristics – Gemini

Gemini switchboards features table

Size	1	2	3	4	5	6
Gemini with transparent door	1SL0211A00	1SL0212A00	1SL0213A00	1SL0214A00	1SL0215A00	1SL0216A00
Gemini with opaque door	1SL0201A00	1SL0202A00	1SL0203A00	1SL0204A00	1SL0205A00	1SL0206A00
External dimensions WxHxD (mm)	335x400x210	460x550x260	460x700x260	590x700x260	590x855x360	840x1005x360
Internal dimensions WxHxD (mm)	250x300x180	375x450x230	375x600x230	500x600x230	500x750x330	750x900x330
IP degree	IP66	IP66	IP66	IP66	IP66	IP66
Double isolation	Sì	Sì	Sì	Sì	Sì	Sì
IK degree	10	10	10	10	10	10
GWT (°C)	750	750	750	750	750	750
Operating temperature	-25 °C ... +100 °C					
No. of DIN modules	24 (12x2)	54 (18x3)	72 (18x4)	96 (24x4)	120 (24x5)	216 (36x6)
No. of vertical modules (H=150 mm)	2	3	4	4	5	6
Material	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic	Thermoplastic
Color	Gray RAL7035					
Fast wiring system	Unifix L					
No. of locks	2	2	2	2	3	3
Rated frequency	50-60 Hz					
STANDARD CEI 23-51⁽¹⁾						
- Max. dispersible power ⁽²⁾	45 W	72 W	85 W	102 W	156 W	248 W
STANDARD CEI EN 61439						
Over-temperature (par. 8.2.1)⁽³⁾						
- Max. dispersible power with over-temperature of 25 °C	40 W	65 W	77 W	91 W	133 W	205 W
- Max. dispersible power with over-temperature of 30 °C	45 W	72 W	85 W	102 W	156 W	248 W
- Max. dispersible power with over-temperature of 35 °C	52 W	85 W	100 W	121 W	187 W	299 W
- Max. dispersible power with over-temperature of 40 °C	62 W	100 W	118 W	143 W	221 W	355 W
Impulse withstand (par. 8.2.2)						
- Rated service voltage ⁽⁴⁾	≤ 800 V					
- Rated impulse withstand voltage	8 kV					

⁽¹⁾ Limits of applicability of the standard CEI 23-51

The standard may be applied only when the wired switchboard meets all the following conditions:

- fixed installation with average ambient temperature up to 25 °C, occasionally up to 35 °C;
- alternate current with rated voltage up to 440 V;
- input rated current up to 125 A;

- assumed short circuit rated current up to 10 kA or liming current devices protection with limited current up to 15 kA at their rated breaking capacity.

⁽²⁾ Maximum dissipation power data was obtained following the indications of Standard CEI 23-49, with a temperature difference of Dt=30 °C.

⁽³⁾ Note to paragraph 8.2.1 of Standard CEI EN 61439-1

The table gives the thermal dissipation values of Gemini switchboards when they are wall-mounted. The dispersible power figures (in Watts) vary according to the overtemperature allowed in the accessible parts of the switchboard and must be compared with the total amount of power dissipated by all the components installed inside the switchboard taking into account the factor of contemporaneity.







⁽⁴⁾ Rated service voltage according to CEI EN 61439-1 1000V AC and 1500V DC

Automation boards - technical details

IP degree of protection – Gemini

As indicated in the following table, the IP degree of protection is expressed by two characteristic numbers depending on the behavior of the product to which it refers according to the prescriptions of CEI 70-1 and IEC 529 Standards.







First number: protection against the penetration of solid bodies

IP	
0	No protection
1	 Protection against the penetration of solid bodies with a diameter of over 50mm
2	 Protection against the penetration of solid bodies with a diameter of over 12mm or a length of over 80mm
3	 Protection against the penetration of solid bodies with a diameter or thickness of over 2,5mm
4	 Protection against the penetration of solid bodies with a diameter or thickness of over 1,0mm
5	 Protection against the penetration of dusts
6	 Total protection against the penetration of dusts

1st number defined by Standards CEI 70-1 – IEC 60529

With IP66 degree of protection, Gemini switchboards are totally protected against the penetration of dusts and sprays of seawater.

Second number: protection against the penetration of water











IP	
0	No protection
1	 Protection against the penetration of drops of water falling vertically
2	 Protection against the penetration of drops of water falling at an angle of up to 15° from vertical
3	 Protection against the penetration of drops of water falling at an angle of up to 60° from vertical
4	 Protection against the penetration of splashes of water from all directions
5	 Protection against the penetration of water sprayed by a hose from all directions
6	 Protection against the penetration of sea water
7	 Protection against the penetration of water during temporary immersion
8	Protection against the penetration of water during continual immersion

2nd number defined by Standards CEI 70-1 - IEC 60529.

Automation boards - technical details

IK degree of resistance to impacts – Gemini

The IK degree is expressed in Joules in compliance with Standard CEI EN 50102.

IK 0		No protection against impacts	IK 06		Resistance to impacts with impact energy up to 1,00 J
IK 01		Resistance to impacts with impact energy up to 0,150 J	IK 07		Resistance to impacts with impact energy up to 2,00 J
IK 02		Resistance to impacts with impact energy up to 0,200 J	IK 08		Resistance to impacts with impact energy up to 5,00 J
IK 03		Resistance to impacts with impact energy up to 0,350 J	IK 09		Resistance to impacts with impact energy up to 10,00 J
IK 04		Resistance to impacts with impact energy up to 0,500 J	IK 10		Resistance to impacts with impact energy up to 20,00 J
IK 05		Resistance to impacts with impact energy up to 0,700 J			

Automation boards - technical details

Double insulation and self-extinguishing tests – Gemini


Double insulation

Double insulation guarantees that Gemini is protected against indirect contacts on condition that the manufacturer's instructions are observed when carrying out mounting

and wiring operations on the switchboard and that the appropriate accessories are used (e.g. screw-cover caps).

Double insulation is indicated by the graphic symbol 

Self-extinguishing tests

Test text	Equipment required	Compliance with Standards	Purpose	Test results of the test	Test conditions		
					Heat source	Test period	Characteristic elements
Glow-wire test		IEC 695-2-1 CEI 50-11	To assess the danger of fire by simulating thermal stresses produced by heat sources or by ignition (e.g. glowing elements, resistances overloaded for short intervals)	If a flame is generated, it must go out within 30 seconds of removing the glow wire. The test is conducted at temperatures of: - 650 °C - 750 °C - 850 °C - 960 °C	Glow wire ø 4 mm	30 sec.	Assessment of the time it takes for the flame to go out

Automation boards - technical details

Resistance to chemical agents – Gemini

Resistance to chemical agents

The behavior of Gemini switchboards in the presence of chemical agents is indicated in the table with the symbols:

Cold water	■
Hot water	■
Sulfuric acid 50%	■
Hydrochloric acid 36%	■
Acetic acid 60%	■
Benzol	▲
Gasoline	▲
Acetone	■
Ethyl alcohol	■
Ammonia	■
Dichloromethane	▲
Diesel oil - naphtha	▲
Mineral oils and greases	■
Food oils and greases	■
Perchloroethylene	▲
Trichlorethane	▲
Ethylether	■
Toluene	▲
Methanol	■
Wine	■
Fruit juices	■
Laundry lye	■
Detergents	■

Caption:

- high resistance
- ▲ limited resistance

Automation boards - technical details

Integration with ABB products – Gemini

Installation of Tmax XT moulded-case circuit breakers

The table indicates the type of installation required for the different versions of Tmax XT moulded-case circuit breakers in Gemini switchboards.

Before carrying out wiring operations check compliance with Standards on the basis of the technical characteristics of the switchboard and circuit breaker (CEI EN 60439-1).

Size	Installation	XT1				XT2				XT3				XT4			
		3p	4p	3p D	4p D	3p	4p	3p D	4p D	3p	4p	3p D	4p D	3p	4p	3p D	4p D
1	D	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	O1	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	T	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
2	D	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	K1	■	■	■													
	K2		■	■	■					■	■	■	■				
	O1	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	O2	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	T	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
3	D	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	K1	■	■	■													
	K2	■	■	■	■					■	■	■	■				
	O1	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	O2	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	T	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
4	D	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	K1	■	■	■													
	K2	■	■	■	■					■	■	■	■				
	O1	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	O2	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	T	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
5	D	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	K1	■	■	■													
	K2	■	■	■	■					■	■	■	■				
	O1	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	O2	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	T	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
6	D	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	K1	■	■	■													
	K2	■	■	■	■					■	■	■	■				
	O1	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	O2	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	T	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■

Caption

- D, installation on DIN rail
- K1, installation with Tmax kit H = 150 (holes made)
- K2, installation with Tmax kit H = 300 (holes made)
- O1, installation on modular plate (1 module, H = 150 mm)
- O2, installation on modular plate (2 modules, H = 300 mm)
- T, installation on total base plate

Automation boards - technical details

Disposal instructions

Information about how to dispose of Gemini switchboards when they reach the end of their life

Instructions are given below about the procedures to adopt when disposing of Gemini switchboards at the end of their life cycle.


The text is drafted in the form of a table referring to Standard CEI 308-1 "Information table concerning the end of life of electric and electronic products and a compilation guide", 2002 -04, ed. 1, pamphlet number 308-1 6454.

Section I – Global product specification

Name	Type of product			External dimensions WxHxD (mm)
Size	With transparent door	With opaque door	Rated weight (kg)	
1	1SL0211A00	1SL0201A00	4,3	335x400x210
2	1SL0212A00	1SL0202A00	7,9	460x550x260
3	1SL0213A00	1SL0203A00	9,5	460x700x260
4	1SL0214A00	1SL0204A00	12,0	590x700x260
5	1SL0215A00	1SL0205A00	17,8	590x855x360
6	1SL0216A00	1SL0206A00	21,1	840x1005x360

Section II – Global product table


General code: CER 17 02 03 plastic (more than 95% of the product's weight)

Part (P1, P2 ecc.)/ Component number	Diagram	Quantity % over total weight	Material description	Symbol	Dangerousness (Yes/No)	CER code
P1/BOX		~ 80%	Polypropylene	No 	No	17 02 03
P2/ROOF			Polycarbonate	No 	No	17 02 03
P3/DOOR		~ 20%	Steel	No 	No	17 04 05
P4/ACCESSORIES		< 5%	Brass	-	No	17 04 01
P5/ACCESSORIES		< 5%	Polypropylene	-	No	17 02 03

Automation boards - technical details


Overall dimensions – Basic configuration

Front view




Size 1

1SL0201A00 - 1SL0211A00 - 1SL0221A00




Size 2

1SL0202A00 - 1SL0212A00 - 1SL0222A00




Size 3

1SL0203A00 - 1SL0213A00 - 1SL0223A00




Size 4

1SL0204A00 - 1SL0214A00 - 1SL0224A00



Size 5


1SL0205A00 - 1SL0215A00 - 1SL0225A00




Size 6

1SL0206A00 - 1SL0216A00 - 1SL0226A00


Top view




Size 1




Size 2




Size 3



Size 4



Size 5




Size 6

Automation boards - technical details

Overall dimensions – Basic configuration

Side view



Size 1

Size 2


Size 3

Size 4

Size 5

Size 6

Installation with plastic brackets



Size 5


Size 6

Bracket


Automation boards - technical details

Overall dimensions – Basic configuration

Installation with stainless steel brackets



External opaque and transparent doors




Size	w	h	Locks	d = lock distance
1	325	349	2	200
2	450	499	2	300
3	450	649	2	400
4	575	649	2	400
5	575	799	3	500
6	825	949	3	750

Automation boards - technical details


Overall dimensions – Components for automation applications

Base plate

Metal, drilled




Metal, blank and insulating



Size	w	h	Metal, blank and drilled		Insulating		f = base distance MIN.	MAX.	c = distance inner door MIN.	MAX.	Distance of the plate from the inner door
			s	s							
1	235	285	2	5	16,3	91	33,5	110	-	-	
2	360	435	2	5	36,4	140	33,5	139	152,4	152,4	
3	360	585	2	5	36,4	140	33,5	139	152,4	152,4	
4	485	585	2	5	36,4	140	33,5	139	152,4	152,4	
5	485	735	2	5	47	244	33,5	228	252,0	252,0	
6	735	885	2	5	47	244	33,5	228	252,0	252,0	

The distance of the plate from the base and inner door depends on the installation point selected for mounting the plate on the box.

Inner doors




Size	w	h	s	Inner door distance			x	y
				d = door	b = base			
1	250	300	3	63	128	245	295	
2	375	450	4	63	177	365	435	
3	375	600	4	63	177	215	435	
4	500	600	4	63	177	340	440	
5	500	750	4	63	277	340	590	
6	750	900	4	63	277	585	735	

Measurements are expressed in millimeters.


Automation boards - technical details

Overall dimensions – Components for distribution and mixed applications


Uprights




Size 1





Size 2




Size 3, 4



Size 5



Size 6




Upright	Duct			
	Size	W	w	h
1		132	18	46
2		152	27	46
3		152	27	46
4		152	27	46
5		152	36	46
6		152	55	46


Automation boards - technical details

Overall dimensions – Components for distribution and mixed applications

DIN rails




Size	A	d = distance between panel with holes/DIN rail					
		pos. 1	pos. 2	pos. 3	pos. 4	pos. 5	pos. 6
1	210	51	63,5	76	88,5	-	-
2	318	51	63,5	76	88,5	101	113,5
3	318	51	63,5	76	88,5	101	113,5
4	443	51	63,5	76	88,5	101	113,5
5	443	51	63,5	76	88,5	101	113,5
6	663	51	63,5	76	88,5	101	113,5





The distances of the DIN rail from the Panel depend on depth adjustment made through rail mountings.

Drilled panels

1 + 1/2 module



1 module




Drilled panel	1 mod.		1+1/2 mod.		Window		Panel distance		
	Size	w	H	w	H	h	module	d = door	b = base
1	250	150	-	-	46	46	12	44	145
2	375	150	375	225	46	46	18	44	197
3	375	150	375	225	46	46	18	44	197
4	500	150	500	225	46	46	24	44	197
5	500	150	500	225	46	46	24	44	297
6	750	150	750	225	46	36	44	44	297

Automation boards - technical details


Overall dimensions – Components for distribution and mixed applications

Blank panels



Blank panel 2 modules



Blank panel 1 module



Blank panel 1/2 module





Size	1/2 mod.		1 mod.		2 mod.		Panel distance	
	w	h	w	h	w	h	d = door	b = base
1	250	75	250	150	250	300	26,5	162
2	375	75	375	150	375	300	26,5	214
3	375	75	375	150	375	300	26,5	214
4	500	75	500	150	500	300	26,5	214
5	500	75	500	150	500	300	26,5	314
6	750	75	750	150	750	300	26,5	314

Automation boards - technical details



Overall dimensions – Components for distribution and mixed applications

Kit for Tmax

Kit H 150



Kit H 300



kit for Tmax H 150 (available for sizes 2-6)

Size	W	H	d	f	b
2	375	150	19	46	318
3	375	150	19	46	318
4	500	150	19	46	443
5	500	150	19	46	443
6	750	150	19	46	663

kit for Tmax H 300 (available for sizes 2-6)

Size	W	H	d	f	b
2	375	300	19	46	318
3	375	300	19	46	318
4	500	300	19	46	443
5	500	300	19	46	443
6	750	300	19	46	663


Automation boards - technical details

Overall dimensions – Components for distribution and mixed applications


Kit for Tmax XT

Kit H 150

Plate




Panel




Kit H 300

Plate



Panel



Kit for Tmax XT H 150 (available for sizes 2-6)

Size	W	H	d	f	b
2	375	150	10	46	318
3	375	150	10	46	318
4	500	150	10	46	443
5	500	150	10	46	443
6	750	150	10	46	663


Kit for Tmax XT H 300 (available for sizes 2-6)

Size	W	H	d	f	b
2	375	300	10	46	318
3	375	300	10	46	318
4	500	300	10	46	443
5	500	300	10	46	443
6	750	300	10	46	663

Automation boards - technical details


Overall dimensions – Components for distribution and mixed applications

Modular plates




1 module

2 modules



Drilled panel



Blank panel

Size	1 module		2 modules	
	w	h	w	h
1	210	130	-	-
2	318	130	318	280
3	318	130	318	280
4	443	130	443	280
5	443	130	443	280
6	663	130	663	280

D = distance blank panel/plate						
pos. 1	pos. 2	pos. 3	pos. 4	pos. 5	pos. 6	
71,5	84	96,5	109	-	-	
71,5	84	96,5	109	121,5	134	
71,5	84	96,5	109	121,5	134	
71,5	84	96,5	109	121,5	134	
71,5	84	96,5	109	121,5	134	
71,5	84	96,5	109	121,5	134	


d = distance drilled panel/plate						
pos. 1	pos. 2	pos. 3	pos. 4	pos. 5	pos. 6	
54,7	67,2	79,7	92,2	-	-	
54,7	67,2	79,7	92,2	104,7	117,2	
54,7	67,2	79,7	92,2	104,7	117,2	
54,7	67,2	79,7	92,2	104,7	117,2	
54,7	67,2	79,7	92,2	104,7	117,2	
54,7	67,2	79,7	92,2	104,7	117,2	

The distance of the panels from the modular plates depends on the depth at which the DIN rail is regulated by using fixing devices.

Automation boards - technical details


Overall dimensions – Components for distribution and mixed applications

Coupling kit



Size	B	H	X	Y
1	-	-	-	-
2	455	258	90	286
3	455	258	90	286
4	583	260	90	412
5	583	360	190	412
6	834	360	190	662

Bottom base H 30




Size	B	H	X	Y
1	-	-	-	-
2	458	260	91	316
3	458	260	91	316
4	583	260	91	440
5	590	366	164	400
6	840	366	164	640

Automation boards - technical details


Overall dimensions – Components for distribution and mixed applications

Fixed frame



Size	B	H	X	Y	Y1
1	-	-	-	-	-
2	415	240	130	305	205
3	415	240	130	305	205
4	540	240	130	430	330
5	584	330	210	480	280
6	834	330	210	730	530

Integral cover




Size	B	H
1	347	238
2	472	289
3	472	289
4	600	289
5	604	390
6	854	390

Automation boards - technical details


Overall dimensions – Components for distribution and mixed applications

Pedestal



Front view



Size 4, 5



Size 6




Size	B	H	s
4	592	254	28
5	592	254	28
6	846	254	28

Automation boards - technical details

Overall dimensions – Components for distribution and mixed applications

Side view




Size	B	Y	Y1
4	213	130	65
5	313	120	60
6	313	120	60

Automation boards - technical details

Overall dimensions – Components for distribution and mixed applications


Horizontal Gemini kit




Size	A	B	C	H	Y	D	E
3	56	715,6	523	288	51	692	696
4	56	715,6	523	288	51	692	696
5	60	870	660	388	151	844	848
6	60	1021	810	388	153	994	998

Wiring kit

Duct 25x60 mm



Duct 40x60 mm




Size	A
1	210
2	318
3	318
4	443
5	443
6	663


Automation boards - technical details

Overall dimensions – Components for distribution and mixed applications


Ventilation kit




Anti-condensation kit



Floor pedestal



Pole installation kit




Size	A	B	L
1	232	206	196
2	358	332	320
3	358	332	320
4	483	457	447
5	483	457	447
6	733	707	697

Note: minimum pole section = 150 mm

Automation boards - technical details

Overall dimensions – Casse SR2

Basic version



Code	A	B	C	D	E	F (*)	G	H	I	L
SRN3215K	303	203	147	82	133,5	151,5	163	337	237	263
SRN3315K	303	303	147	82	133,5	151,5	263	337	337	263
SRN3415K	303	403	147	82	133,5	151,5	363	337	437	263
SRN4315K	403	303	147	82	133,5	201,5	263	437	337	363
SRN4320K	403	303	197	132	183,5	201,5	263	437	337	363
SRN4420K	403	403	197	132	183,5	201,5	363	437	437	363
SRN4620K	403	603	197	132	183,5	201,5	563	437	637	363
SRN5320K	503	303	197	132	183,5	251,5	263	537	337	463
SRN5420K	503	403	197	132	183,5	251,5	363	537	437	463
SRN5425K	503	403	247	182	233,5	251,5	363	537	437	463
SRN6420K	603	403	197	132	183,5	100	363	637	437	563
SRN6425K	603	403	247	182	233,5	100	363	637	437	563
SRN6625K	603	603	247	182	233,5	100	563	637	637	563
SRN7520K	703	503	197	132	183,5	100	463	737	537	663
SRN7525K	703	503	247	182	233,5	100	463	737	537	663
SRN8625K	803	603	247	182	233,5	150	563	837	637	763
SRN8630K	803	603	297	232	283,5	150	563	837	637	763
SRN8830K	803	803	297	232	283,5	150	763	837	837	763


Measurements are expressed in millimeters.

Code	A	B	C	D	E	F (*)	G	H	I	L
SRN10625K	1003	603	247	182	233,5	150	563	1037	637	963
SRN10630K	1003	603	297	232	283,5	150	563	1037	637	963
SRN10830K	1003	803	297	232	283,5	150	763	1037	837	963
SRN12630K	1203	603	297	232	283,5	150	563	1237	637	1163
SRN12830K	1203	803	297	232	283,5	150	763	1237	837	1163
SRN5420VK	503	403	197	132	183,5	150	363	537	437	463
SRN5425VK	503	403	247	182	233,5	150	363	537	437	463
SRN6420VK	603	403	197	132	183,5	150	363	637	437	563
SRN6425VK	603	403	247	182	233,5	150	363	637	437	563
SRN7520VK	703	503	197	132	183,5	150	463	737	537	663
SRN7525VK	703	503	247	182	233,5	150	463	737	537	663
SRN8625VK	803	603	247	182	233,5	150	563	837	637	763
SRN8630VK	803	603	297	232	283,5	150	563	837	637	763
SRN10625VK	1003	603	247	182	233,5	150	563	1037	637	963
SRN10630VK	1003	603	297	232	283,5	150	563	1037	637	963
SRN10830VK	1003	803	297	232	283,5	150	763	1037	837	963
SRN12630VK	1203	603	297	232	283,5	150	563	1237	637	1163
SRN12830VK	1203	803	297	232	283,5	150	763	1237	837	1163


Automation boards - technical details

Overall dimensions – Casse SR2


Centre distances for wall fixing




Centre distances for plinth fixing



Internal counterdoors



Internal plates



Code	M	N
KC5040K *	456	360
KC6040K *	556	360
KC7050K *	656	460
KC8060K	756	560
KC1060K	956	560
KC1080K	956	760
KC1260K	1156	560
KC1280K	1156	760

* The counterdoors with H 500 mm, 600 mm and 700 mm, only have one hole in the centre for the lock




Code	O	P
PF3020	160	260
PF3030	260	260
PF3040 - PF4030	360	260
PF4040	360	360
PF5030	260	460
PF5040	360	460
PF6040 - PF4060	360	560
PF6060	560	560
PF7050	460	660
PF8060	560	760
PF8080	760	760
PF1060	560	960
PF1080	760	960
PF1260	560	1160
PF1280	760	1160

Measurements are expressed in millimeters.


Automation boards - technical details

Overall dimensions – SRX enclosures

Basic version



Modular panels and inner door



(*) Locks (F)
1 central for enclosures from h=303 to 503 mm
2 for enclosures from h=603 to 703 mm (F=100mm)
2 for enclosures from h=803 to 1203 mm (F=150mm)

(**) Copper plated nut on the rear
only for enclosures from h=1003 to 1203 mm

(***) Copper plated nut on door
1 for enclosures from h=303 to 503 mm
4 for enclosures from h=603 to 803 mm
6 for enclosures from h=1003 to 1203 mm


Code	A	B	C	D	E	F (*)	G	H	I	L
SRN3215X	303	203	147	82	133,5	151,5	163	337	237	263
SRN3415X	303	403	147	82	133,5	151,5	363	337	437	263
SRN4315X	403	303	147	82	133,5	201,5	263	437	337	363
SRN4320X	403	303	197	132	183,5	201,5	263	437	337	363
SRN4420X	403	403	197	132	183,5	201,5	363	437	437	363
SRN4620X	403	603	197	132	183,5	201,5	563	437	637	363
SRN5420X - SRN5420VX	503	403	197	132	183,5	251,5	363	537	437	463
SRN5520X	503	503	197	132	183,5	251,5	363	537	437	463
SRN6420X - SRN6420VX	603	403	197	132	183,5	100	363	637	437	563
SRN6620X	603	603	197	132	183,5	100	363	637	437	563
SRN6630X	603	603	297	232	283,5	100	363	637	437	563
SRN7525X - SRN7525VX	703	503	247	182	233,5	100	463	737	537	663
SRN8620X	803	603	197	132	183,5	150	363	637	437	563
SRN8625VX	803	603	247	182	233,5	150	563	837	637	763
SRN8630X	803	603	297	232	283,5	150	563	837	637	763
SRN8830X	803	803	297	232	283,5	150	763	837	837	763
SRN10830X - SRN10830VX	1003	803	297	232	283,5	150	763	1037	837	963
SRN12630X	1203	603	297	232	283,5	150	563	1237	637	1163
SRN12830X	1203	803	297	232	283,5	150	763	1237	837	1163

Measurements are expressed in millimeters.

Automation boards - technical details

Overall dimensions – SRX enclosures


Centre distances for wall-mounting



Centre distances for plinth fixing




Inner doors



Code	M	N
KC5040X*	456	360
KC6040X*	556	360
KC7050X*	656	460
KC8060X	756	560
KC1080X	956	760

* Inner doors with H 500mm, 600mm, 700mm only have one hole in the centre for the lock

Internal plates



Code	O	P
PF3020	160	260
PF3030	260	260
PF3040 - PF4030	360	260
PF4040	360	360
PF5030	260	460
PF5040	360	460
PF5050	460	460
PF6040 - PF4060	360	560
PF6060	560	560
PF7050	460	660
PF8060	560	760
PF8080	760	760
PF1060	560	960
PF1080	760	960
PF1260	560	1160
PF1280	760	1160

Measurements are expressed in millimeters.

Electrical installation solutions for buildings – Technical details

Junction boxes


Index

Livorno Series emergency consumer units	21/2
IP44, IP55 and IP65 Junction boxes	21/4
Europa65 junction boxes	21/7


Junction boxes - technical details

Livorno Series flush- and wall- mounting emergency consumer units


Front view




13 180 - 13 183




13 186




13 161 - 13 165




13 171 - 13 175




13 141 - 13 151

13 144
13 143


Side view




13 180




13 183




13 161 - 13 165



13 171 - 13 175




13 141 - 13 151

13 144
13 143


Junction boxes - technical details

Livorno Series flush- and wall- mounting emergency consumer units


Drilling sheets




13 180




13 183





13 161 – 13 165



13 171 – 13 175




13 141 – 13 151

13 144
13 143


Junction boxes - technical details

IP 44 and IP 55 junction boxes in thermoplastic material


Front view




00 800
1SL0900A00




00 802
1SL0901A00




00 808
1SL0902A00




00 810
1SL0903A00




00 820 - 00 850
1SL0820A00 - 1SL0850A00




00 816 - 00 821
00 846 - 00 851
1SL0816A00 - 1SL0821A00
1SL0846A00 - 1SL0851A00
1SL0916A00 - 1SL0921A00
1SL0946A00 - 1SL0951A00




00 822 - 00 872
1SL0822A00 - 1SL0852A00
1SL0872A00
1SL0922A00



1SL0830A00 - 1SL0824A00
1SL0874A00 - 1SL0854A00
1SL0860A00 - 1SL0880A00
1SL0924A00
1SL0954A00
1SL0960A00



1SL0826A00 - 1SL0832A00
1SL0876A00 - 1SL0856A00
1SL0862A00 - 1SL0884A00
1SL0926A00
1SL0956A00
1SL0962A00






1SL0828A00 - 1SL0834A00
1SL0858A00
1SL0864A00 - 1SL0884A00
1SL0928A00
1SL0958A00
1SL0964A00

Junction boxes - technical details

IP 44 and IP 55 junction boxes in thermoplastic material


Side view




Junction boxes - technical details

IP 44 and IP 55 junction boxes in thermoplastic material


Drilling sheets and internal dimensions




00 800 - 00 581
1SL0900A00
1SL0910A00




00 802
1SL0901A00




00 808
1SL0902A00




00 810
1SL0903A00




00 820 - 00 850
1SL0820A00
1SL0850A00




00 816 - 00 846
1SL0816A00
1SL0846A00
1SL0916A00
1SL0946A00




00 821 - 00 851
1SL0821A00
1SL0851A00
1SL0921A00
1SL0951A00




00 822 - 00 852 - 00 872
1SL0822A00 - 1SL0852A00 - 1SL0872A00
1SL0922A00 - 1SL0952A00



1SL0824A00 - 1SL0830A00
1SL0874A00 - 1SL0854A00
1SL0860A00 - 1SL0880A00
1SL0924A00
1SL0954A00
1SL0960A00



1SL0826A00 - 1SL0832A00
1SL0876A00 - 1SL0856A00
1SL0862A00 - 1SL0884A00
1SL0926A00
1SL0956A00
1SL0962A00




1SL0828A00 - 1SL0834A00
1SL0878A00 - 1SL0858A00
1SL0864A00 - 1SL0884A00
1SL0928A00
1SL0958A00
1SL0964A00


Junction boxes - technical details

IP 65 junction boxes in polycarbonate


Front view




12 804




12 808




12 812



12 814




12 816




12 818


Side view



12 804 - 12 808 - 12 812



12 814




12 816 - 12 818

Junction boxes - technical details

IP 65 junction boxes in polycarbonate

Drilling sheet





new.abb.com/low-voltage