



Relion® 620 series

# Feeder Protection and Control REF620 ANSI Modbus Point List Manual





Document ID: 1MAC509789-IB  
Issued: 10/26/2012  
Revision: A  
Product version: 2.0

© Copyright 2012 ABB. All rights reserved.

# Copyright

This document and parts thereof must not be reproduced or copied without written permission from ABB, and the contents thereof must not be imparted to a third party, nor used for any unauthorized purpose.

The software or hardware described in this document is furnished under a license and may be used, copied, or disclosed only in accordance with the terms of such license.

## Trademarks

ABB and Relion are registered trademarks of ABB Group. All other brand or product names mentioned in this document may be trademarks or registered trademarks of their respective holders.

## Warranty

Please inquire about the terms of warranty from your nearest ABB representative.

ABB Inc.  
Distribution Automation  
4300 Coral Ridge Drive  
Coral Springs, FL 33065, USA  
Toll-free: 1 (800) 523-2620  
Phone: +1 954-752-6700  
Fax: +1 954 345-5329  
<http://www.abb.com/substationautomation>

# Disclaimer

The data, examples and diagrams in this manual are included solely for the concept or product description and are not to be deemed as a statement of guaranteed properties. All persons responsible for applying the equipment addressed in this manual must satisfy themselves that each intended application is suitable and acceptable, including that any applicable safety or other operational requirements are complied with. In particular, any risks in applications where a system failure and/or product failure would create a risk for harm to property or persons (including but not limited to personal injuries or death) shall be the sole responsibility of the person or entity applying the equipment, and those so responsible are hereby requested to ensure that all measures are taken to exclude or mitigate such risks.

This document has been carefully checked by ABB but deviations cannot be completely ruled out. In case any errors are detected, the reader is kindly requested to notify the manufacturer. Other than under explicit contractual commitments, in no event shall ABB be responsible or liable for any loss or damage resulting from the use of this manual or the application of the equipment.

# Conformity

This product complies with the directive of the Council of the European Communities on the approximation of the laws of the Member States relating to electromagnetic compatibility (EMC Directive 2004/108/EC) and concerning electrical equipment for use within specified voltage limits (Low-voltage directive 2006/95/EC). This conformity is the result of tests conducted by ABB in accordance with the product standards EN 50263 and EN 60255-26 for the EMC directive, and with the product standards EN 60255-6 and EN 60255-27 for the low voltage directive. The IED is designed in accordance with the international standards of the IEC 60255 series and ANSI C37.90.

---

<b>Section 1</b>	<b>Introduction .....</b>	<b>3</b>
	This manual .....	3
	Intended audience .....	3
	Product documentation .....	4
	Product documentation set .....	4
	Document revision history .....	5
	Related documentation .....	5
	Symbols and conventions .....	5
	Safety indication symbols .....	5
	Manual conventions .....	6
	Functions, codes and symbols .....	6
<b>Section 2</b>	<b>Modbus data mappings .....</b>	<b>11</b>
	Overview .....	11
	Point list for REF620 v2.0 ANSI .....	11
<b>Section 3</b>	<b>Glossary .....</b>	<b>85</b>





## Section 1 Introduction

### 1.1 This manual

The point list manual describes the outlook and properties of the data points specific to the IED. The manual should be used in conjunction with the corresponding communication protocol manual.


### 1.2 Intended audience

This manual addresses the communication system engineer or system integrator responsible for pre-engineering and engineering for communication setup in a substation from an IED perspective.

The system engineer or system integrator must have a basic knowledge of communication in protection and control systems and thorough knowledge of the specific communication protocol.

## 1.3 Product documentation

### 1.3.1 Product documentation set



**Figure 1:** *The intended use of manuals in different lifecycles*

The engineering manual contains instructions on how to engineer the IEDs using the different tools in PCM600. The manual provides instructions on how to set up a PCM600 project and insert IEDs to the project structure. The manual also recommends a sequence for engineering of protection and control functions, LHMI functions as well as communication engineering for IEC 61850 and DNP3.

The installation manual contains instructions on how to install the IED. The manual provides procedures for mechanical and electrical installation. The chapters are organized in chronological order in which the IED should be installed.

The operation manual contains instructions on how to operate the IED once it has been commissioned. The manual provides instructions for monitoring, controlling and setting the IED. The manual also describes how to identify disturbances and how to view calculated and measured power grid data to determine the cause of a fault.

The application manual contains application descriptions and setting guidelines sorted per function. The manual can be used to find out when and for what purpose a typical protection function can be used. The manual can also be used when calculating settings.

The technical manual contains application and functionality descriptions and lists function blocks, logic diagrams, input and output signals, setting parameters and technical data

sorted per function. The manual can be used as a technical reference during the engineering phase, installation and commissioning phase, and during normal service.

The communication protocol manual describes a communication protocol supported by the IED. The manual concentrates on vendor-specific implementations. The point list manual describes the outlook and properties of the data points specific to the IED. The manual should be used in conjunction with the corresponding communication protocol manual.

## 1.3.2 Document revision history

Document revision/date	Product version	History
A/10/26/2012	2.0	First release



Download the latest documents from the ABB web site  
<http://www.abb.com/substationautomation>.

## 1.3.3 Related documentation

Name of the document	Document ID
Modbus Communication Protocol Manual	1MAC458836-IB

## 1.4 Symbols and conventions

### 1.4.1 Safety indication symbols



The caution icon indicates important information or warning related to the concept discussed in the text. It might indicate the presence of a hazard which could result in corruption of software or damage to equipment or property.



The information icon alerts the reader to important facts and conditions.






The tip icon indicates advice on, for example, how to design your project or how to use a certain function.

Although warning hazards are related to personal injury, it should be understood that operation of damaged equipment could, under certain operational conditions, result in degraded process performance leading to personal injury or death. Therefore, comply fully with all warning and caution notices.

## 1.4.2 Manual conventions

Conventions used in IED manuals. A particular convention may not be used in this manual.

- Abbreviations and acronyms in this manual are spelled out in the glossary. The glossary also contains definitions of important terms.
- Push button navigation in the LHMI menu structure is presented by using the push button icons, for example:  
To navigate between the options, use  and .
- HMI menu paths are presented in bold, for example:  
Select **Main menu > Settings**.
- LHMI messages are shown in Courier font, for example:  
To save the changes in non-volatile memory, select `Yes` and press .
- Parameter names are shown in italics, for example:  
The function can be enabled and disabled with the *Operation* setting.
- Parameter values are indicated with quotation marks, for example:  
The corresponding parameter values are "Enabled" and "Disabled".
- IED input/output messages and monitored data names are shown in Courier font, for example:  
When the function picks up, the `PICKUP` output is set to `TRUE`.
- Dimensions are provided both in inches and mm. If it is not specifically mentioned then the dimension is in mm.

## 1.4.3 Functions, codes and symbols

Table 1: Functions included in standard configurations

Function	IEC61850	ANSI/C37.2	IEC60617
<b>Protection</b>			
Three-phase non-directional overcurrent protection, low stage, instance 1	PHLPTOC1	51P	3I> (1)
Three-phase non-directional overcurrent protection, high stage, instance 1	PHHPTOC1	50P-1	3I>> (1)
Three-phase non-directional overcurrent protection, high stage, instance 2	PHHPTOC2	50P-2	3I>> (2)
Three-phase non-directional overcurrent protection, instantaneous stage, instance 1	PHIPTOC1	50P-3	3I>>> (1)
Three-phase non-directional long time overcurrent protection, low stage, instance 1	PHLTPTOC1	51LT	3I> (3)
Three-phase directional overcurrent protection, low stage, instance 1	DPHLPDOC1	67/51P	3I> -> (1)
Three-phase directional overcurrent protection, high stage, instance 1	DPHHPDOC1	67/50P-1	3I>> -> (1)
Three-phase directional overcurrent protection, high stage, instance 2	DPHHPDOC2	67/50P-2	3I>> -> (2)
Non-directional ground-fault protection, low stage, instance 1	EFLPTOC1	51G	Io> (1)
Non-directional ground-fault protection, low stage, instance 2	EFLPTOC2	51N-1	Io> (2)
Non-directional ground-fault protection, low stage, instance 4	EFLPTOC4	50SEF	Io> (4)
Non-directional ground-fault protection, high stage, instance 1	EFHPTOC1	50G-1	Io>> (1)
Non-directional ground-fault protection, high stage, instance 2	EFHPTOC2	50G-2	Io>> (2)
Non-directional ground-fault protection, high stage, instance 3	EFHPTOC3	50N-1	Io>> (3)
Non-directional ground-fault protection, high stage, instance 4	EFHPTOC4	50N-2	Io>> (4)

Function	IEC61850	ANSI/C37.2	IEC60617
Non-directional ground-fault protection, instantaneous stage, instance 1	EFIPTOC1	50G-3	Io>>> (1)
Non-directional ground-fault protection, instantaneous stage, instance 2	EFIPTOC2	50N-3	Io>>> (2)
Directional ground-fault protection, low stage, instance 1	DEFLPDEF1	67/51N	Io> -> (1)
Directional ground-fault protection, high stage, instance 1	DEFHPDEF1	67/50N-1	Io>> -> (1)
Directional ground-fault protection, high stage, instance 2	DEFHPDEF2	67/50N-2	Io>> -> (2)
Three phase directional power protection, instance 1	DPSRDIR1	32P-1	I1-> (1)
Ground directional power protection, instance 1	DNZSRDIR1	32N-1	I2 -, Io-> (1)
Phase distance protection, instance 1	PHDSTPDIS1	21P	Z<
Negative-sequence overcurrent protection, instance 1	NSPTOC1	46-1	I2> (1)
Negative-sequence overcurrent protection, instance 2	NSPTOC2	46-2	I2> (2)
Phase discontinuity protection	PDNSPTOC1	46PD	I2/I1>
Residual overvoltage protection, instance 1	ROVPTOV1	59G	Uo> (1)
Residual overvoltage protection, instance 2	ROVPTOV2	59N-1(1)	Uo> (2)
Residual overvoltage protection, instance 3	ROVPTOV3	59N-1(2)	Uo> (3)
Three-phase undervoltage protection, instance 1	PHPTUV1	27-1(1)	3U< (1)
Three-phase undervoltage protection, instance 2	PHPTUV2	27-2(1)	3U< (2)
Three-phase undervoltage protection, instance 3	PHPTUV3	27-1(2)	3U< (3)
Three-phase undervoltage protection, instance 4	PHPTUV4	27-2(2)	3U< (4)
Three-phase overvoltage protection, instance 1	PHPTOV1	59-1(1)	3U> (1)
Three-phase overvoltage protection, instance 2	PHPTOV2	59-2(1)	3U> (2)
Three-phase overvoltage protection, instance 3	PHPTOV3	59-1(2)	3U> (3)
Three-phase overvoltage protection, instance 4	PHPTOV4	59-2(2)	3U> (4)
Negative-sequence overvoltage protection, instance 1	NSPTOV1	47-1(1)	U2> (1)
Negative-sequence overvoltage protection, instance 2	NSPTOV2	47-2(1)	U2> (2)
Negative-sequence overvoltage protection, instance 3	NSPTOV3	47-1(2)	U2> (3)
Negative-sequence overvoltage protection, instance 4	NSPTOV4	47-2(2)	U2> (4)
Frequency protection, instance 1	FRPFRQ1	81-1	f>/f<,df/dt (1)
Frequency protection, instance 2	FRPFRQ2	81-2	f>/f<,df/dt (2)
Voltage per hertz protection, instance 1	OEPVPH1	24	U/f> (1)
Three-phase thermal protection for feeders, cables and distribution transformers, Instance 1	T1PTTR1	49F	3Ith>F (1)
Phase current sets summing function	CMSUM1	CSUM	CSUM
Three phase measurement switching	VMSWI1	VSWI	VSWI
Numerical stabilized low impedance restricted ground-fault protection	LREFPNDF1	87LOZREF	dIoLo>
Circuit breaker failure protection, instance 1	CCBRBRF1	50BF-1	3I>/Io>BF (1)
Circuit breaker failure protection, instance 2	CCBRBRF2	50BF-2	3I>/Io>BF (2)
Three-phase inrush detector, instance 1	INRPHAR1	INR	3I2f> (1)
Master trip, instance 1	TRPPTRC1	86/94-1	Master Trip (1)
Master trip, instance 2	TRPPTRC2	86/94-2	Master Trip (2)
Arc protection, instance 1	ARCSARC1	AFD-1	ARC (1)
Arc protection, instance 2	ARCSARC2	AFD-2	ARC (2)
Arc protection, instance 3	ARCSARC3	AFD-3	ARC (3)

Function	IEC61850	ANSI/C37.2	IEC60617
High impedance fault detection	PHIZ1	HIZ	PHIZ1
Load shedding and restoration, instance 1	LSHDPFRQ1	81LSH-1	UFLS/R (1)
Load shedding and restoration, instance 2	LSHDPFRQ2	81LSH-2	UFLS/R (2)
Loss of phase, instance 1	PHPTUC1	37-1	3I< (1)
<b>Control</b>			
Circuit-breaker control, instance 1	CBXCBR1	52-1	I <-> O CB (1)
Circuit-breaker control, instance 2	CBXCBR2	52-2	I <-> O CB (2)
Auto-reclosing, instance 1	DARREC1	79-1	O -> I(1)
Auto-reclosing, instance 2	DARREC2	79-2	O -> I(2)
Synchronism and energizing check, instance 1	SECRSYN1	25-1	SYNC(1)
Synchronism and energizing check, instance 2	SECRSYN2	25-2	SYNC(2)
Synchronism and energizing check, instance 3	SECRSYN3	25-3	SYNC(3)
<b>Condition Monitoring</b>			
Circuit-breaker condition monitoring, instance 1	SSCBR1	52CM-1	CBCM (1)
Circuit-breaker condition monitoring, instance 2	SSCBR2	52CM-2	CBCM (2)
Trip circuit supervision, instance 1	TCSSCBR1	TCM-1	TCS (1)
Trip circuit supervision, instance 2	TCSSCBR2	TCM-2	TCS (2)
Current circuit supervision	CCRDIF1	CCM	MCS 3I
Fuse failure supervision, instance 1	SEQRFUF1	60-1	FUSEF (1)
Fuse failure supervision, instance 2	SEQRFUF2	60-2	FUSEF (2)
Cable fault detection	RCFD1	CFD	CFD
<b>Measurement</b>			
Three-phase current measurement, instance 1	CMMXU1	IA, IB, IC	3I
Sequence current measurement, instance 1	CSMSQI1	I1, I2, I0	I1, I2, I0
Residual current measurement, instance 1	RESCMMXU1	IG	Io
Three-phase voltage measurement, instance 1	VMMXU1	VA, VB, VC	3U
Three-phase voltage measurement, instance 2	VMMXU2	VA, VB, VC (2)	3U(B)
Residual voltage measurement	RESVMMXU1	VG	Uo
Sequence voltage measurement, instance 1	VSMSQI1	V1, V2, V0	U1, U2, U0
Sequence voltage measurement, instance 2	VSMSQI2	V1, V2, V0 (2)	U1, U2, U0(B)
Single-phase power and energy measurement, instance 1	SPEMMXU1	SP, SE	SP, SE
Three-phase power and energy measurement, instance 1	PEMMXU1	P, E	P, E
Current total demand distortion, instance 1	CMHAI1	PQI-1	PQM3I
Voltage total harmonic distortion, instance 1	VMHAI1	PQVPH-1	PQM3U(1)
Voltage total harmonic distortion, instance 2	VMHAI2	PQVPH-2	PQM3U(2)
Voltage variation, instance 1	PHQVVR1	PQSS-1	PQ 3U<>(1)
Voltage unbalance, instance 1	VSQVUB1	PQVUB-1	PQMUBU(1)
Voltage unbalance, instance 2	VSQVUB2	PQVUB-2	PQMUBU(2)
Load profile	LDPMSTA1	LoadProf	LoadProf
Frequency measurement	FMMXU1	f	f
<b>Recorder</b>			

Function	IEC61850	ANSI/C37.2	IEC60617
Disturbance recorder	RDRE1	DFR	DR
Fault recorder	FLTMSTA1	FR	FR
Sequence event recorder	SER	SER	SER
Fault location	DRFLO	FLO	DRFLO
<b>Other Functions</b>			
Minimum pulse timer (2 pcs), instance 1	TPGAPC1	TP-1	TP (1)
Minimum pulse timer (2 pcs), instance 2	TPGAPC2	TP-2	TP (2)
Minimum pulse timer (2 pcs), instance 3	TPGAPC3	TP-3	TP (3)
Minimum pulse timer (2 pcs), instance 4	TPGAPC4	TP-4	TP (4)
Minimum pulse timer (2 pcs, second resolution), instance 1	TPSGAPC1	62CLD-1	TPS (1)
Minimum pulse timer (2 pcs, second resolution), instance 2	TPSGAPC2	62CLD-3	TPS (2)
Minimum pulse timer (2 pcs, minute resolution), instance 1	TPMGAPC1	62CLD-2	TPM (1)
Minimum pulse timer (2 pcs, minute resolution), instance 2	TPMGAPC2	62CLD-4	TPM (2)
Pulse timer (8 pcs), instance 1	PTGAPC1	PT-1	PT (1)
Pulse timer (8 pcs), instance 2	PTGAPC2	PT-2	PT (2)
Time delay off (8 pcs), instance 1	TOFGAPC1	TOF-1	TOF (1)
Time delay off (8 pcs), instance 2	TOFGAPC2	TOF-2	TOF (2)
Time delay off (8 pcs), instance 3	TOFGAPC3	TOF-3	TOF (3)
Time delay off (8 pcs), instance 4	TOFGAPC4	TOF-4	TOF (4)
Time delay on (8 pcs), instance 1	TONGAPC1	TON-1	TON (1)
Time delay on (8 pcs), instance 2	TONGAPC2	TON-2	TON (2)
Time delay on (8 pcs), instance 3	TONGAPC3	TON-3	TON (3)
Time delay on (8 pcs), instance 4	TONGAPC4	TON-4	TON (4)
Set reset (8 pcs), instance 1	SRGAPC1	SR-1	SR (1)
Set reset (8 pcs), instance 2	SRGAPC2	SR-2	SR (2)
Set reset (8 pcs), instance 3	SRGAPC3	SR-3	SR (3)
Set reset (8 pcs), instance 4	SRGAPC4	SR-4	SR (4)
Move (8 pcs), instance 1	MVGAPC1	MV-1	MV (1)
Move (8 pcs), instance 2	MVGAPC2	MV-2	MV (2)
Move (8 pcs), instance 3	MVGAPC3	MV-3	MV (3)
Move (8 pcs), instance 4	MVGAPC4	MV-4	MV (4)
Move (8 pcs), instance 5	MVGAPC5	MV-5	MV (5)
Move (8 pcs), instance 6	MVGAPC6	MV-6	MV (6)
Move (8 pcs), instance 7	MVGAPC7	MV-7	MV (7)
Move (8 pcs), instance 8	MVGAPC8	MV-8	MV (8)
Generic control points, instance 1	SPCGGIO1	CNTRL-1	SPC(1)
Generic control points, instance 2	SPCGGIO2	CNTRL-2	SPC(2)
Generic control points, instance 3	SPCGGIO3	CNTRL-3	SPC(3)
Remote Generic control points, instance 1	SPCRGGIO1	RCNTRL-1	SPCR(1)
Local Generic control points, instance 1	SPCLGGIO1	LCNTRL-1	SPCL(1)
Generic Up-Down Counters, instance 1	UDFCNT1	CTR-1	CTR(1)

Function	IEC61850	ANSI/C37.2	IEC60617
Generic Up-Down Counters, instance 2	UDFCNT2	CTR-2	CTR(2)
Generic Up-Down Counters, instance 3	UDFCNT3	CTR-3	CTR(3)
Generic Up-Down Counters, instance 4	UDFCNT4	CTR-4	CTR(4)
Generic Up-Down Counters, instance 5	UDFCNT5	CTR-5	CTR(5)
Generic Up-Down Counters, instance 6	UDFCNT6	CTR-6	CTR(6)
Generic Up-Down Counters, instance 7	UDFCNT7	CTR-7	CTR(7)
Generic Up-Down Counters, instance 8	UDFCNT8	CTR-8	CTR(8)
Generic Up-Down Counters, instance 9	UDFCNT9	CTR-9	CTR(9)
Generic Up-Down Counters, instance 10	UDFCNT10	CTR-10	CTR(10)
Generic Up-Down Counters, instance 11	UDFCNT11	CTR-11	CTR(11)
Generic Up-Down Counters, instance 12	UDFCNT12	CTR-12	CTR(12)
Programmable buttons (16 buttons), instance 1	FKEYGGIO1	FKEY	FKEY



## Section 2 Modbus data mappings

### 2.1 Overview

This document describes the Modbus data points and structures available in REF620 Ver. 2.0 ANSI IED.

#### Point list table columns

Coil Addr (0x)	Coil (0x) PLC address
Input Add (1x)	Input (1x) PLC address
Register (:Bit) Addr (4x)	Register PLC address, and bit within register
Dc	Data category
MCD	Momentary Change Detect
Type	Register type and value interpretation; signed or unsigned
Scale	Scale factor, default value is 1
Offset	Offset factor, default value is 0
Description	Data description
IEC61850 Data Attribute Name	IEDs internal IEC61850 signal name
Control Structure	Internal control structure identity
Control Register Addr	Register PLC Address, available for control operation
Control Bit Number	Control bit within control register for control operation
W	Writable Register

### 2.2 Point list for REF620 v2.0 ANSI

*Table 2: System Status Registers*

Coil Addr	4x Register Addr.	Dc	Type	Scale	OffSet	Description	IEC61850 Data Attribute Name
	9000	0	u16			System Status Register, 1	
	9001	0	u16			System Status Register, 2	
	9002	0	u16			System Status Register, 3	
	9003	0	u16			System Status Register, 4	
	9004	0	u16			System Status Register, 5	
	9005	0	u16			System Status Register, 6	
	9200	0	u16			Device Information	
		0	u16				

## Section 2 Modbus data mappings

Coil Addr	4x Register Addr.	Dc	Type	Scale	OffSet	Description	IEC61850 Data Attribute Name
		0	u16				

**Table 2.1** *Select Parameter Setting Group Registers*

Coil Addr	4x Register Addr.	W	Type	Scale	OffSet	Description	IEC61850 Data Attribute Name
	9006	x	u16			Parameter Setting Group in Use	

**Table 3:** *Time Stamp of Last Device Reset*

Coil Addr	4x Register Addr.	Dc	Type	Scale	OffSet	Description	IEC61850 Data Attribute Name
	9030	0	u16			Year(High Byte)/Month(Low Byte)	
	9031	0	u16			Day(High Byte)/Hour(Low Byte)	
	9032	0	u16			Min(High Byte)/Sec(Low Byte)	
	9033	0	u16			MilliSecond	
	9034	0	u16			Time Quality	
	9035	0	u16			Cause of Reset (1-Power Reset, 2-Watchdog Reset, 3-Warm Reset)	

**Table 4:** *Device Real-Time clock in local Time*

Coil Addr	4x Register Addr.	W	Type	Scale	OffSet	Description	IEC61850 Data Attribute Name
	9010	x	u16			Real-time struct - Control register (0..2)	
	9011	x	u16			Real-time struct - Year (2000-2999)	
	9012	x	u16			Real-time struct - Month (1..12)	
	9013	x	u16			Real-time struct - Day (1..31)	
	9014	x	u16			Real-time struct - Hour (0..23)	
	9015	x	u16			Real-time struct - Minute (0..59)	
	9016	x	u16			Real-time struct - Seconds (0..59)	
	9017	x	u16			Real-time struct - Milliseconds (0..999)	

**Table 5:** *Device Real-Time clock in UTC Time*

Coil Addr	4x Register Addr.	W	Type	Scale	OffSet	Description	IEC61850 Data Attribute Name
	9020	x	u16			Real-time struct - Control register (0..2)	
	9021	x	u16			Real-time struct - Year (2000-2999)	
	9022	x	u16			Real-time struct - Month (1..12)	
	9023	x	u16			Real-time struct - Day (1..31)	
	9024	x	u16			Real-time struct - Hour (0..23)	
	9025	x	u16			Real-time struct - Minute (0..59)	
	9026	x	u16			Real-time struct - Seconds (0..59)	
	9027	x	u16			Real-time struct - Milliseconds (0..999)	

**Table 6: Event Records**

Coil Addr	4x Register Addr.	W	Type	Scale	OffSet	Description	IEC61850 Data Attribute Name
	9040	x	u16			Number of Events to Read	
	9041	x	u16			Event Selection	
	9042		u16			Sequence Number	
	9043		u16			Number of Unread Records	
	9044		u16			Year(High Byte)/Month(Low Byte)	
	9045		u16			Day(High Byte)/Hour(Low Byte)	
	9046		u16			Min(High Byte)/Sec(Low Byte)	
	9047		u16			MilliSecond	
	9048		u16			Event Type	
	9049		u16			Data Object ID 1 <sup>1)</sup>	
	9050		u16			Data Object ID 2 <sup>1)</sup>	
	9051		u16			Event Data Value	
	9052		u16			Event Data Value	

1) See Decoding of Data Object ID1 and 1

### Decoding of Data Object ID1 and Data Object ID2

DataObject ID2 displays the coil address of the data object, of which the value change incurs the event. Its counterpart of the 4x Modbus address is DataObject ID2 divided by 16 plus 40000. Bit offset of 4x address is the remainder of DataObject ID2 divided by 16.

For Instance, Bit 2 in register of 40297 would appear in Data Object ID2 as 4754. The coil address is  $297 * 16 + 2 = 4754$ .

Data Object ID1 is reserved for the event caused by a 32bit value change. In this case, Data Object ID1 is non-zero and a 32 bit number is composed of Data Object ID1 as bits from 31 to 16 and Data Object ID2 as bits from 15 to 0.

**Table 7: Fault records**

Coil Addr	4x Register Addr.	W	Dc	Type	Scale	Description	IEC61850 Data Attribute Name
	8000	x		u16		Fault Record Selection	
	8001			u16		Sequence Number	
	8002			u16		Number of Unread Records	
	8003			u16		Year(High Byte)/Month(Low Byte)	
	8004			u16		Day(High Byte)/Hour(Low Byte)	
	8005			u16		Min(High Byte)/Sec(Low Byte)	
	8006			u16		MilliSecond	
	8007			u16		Time Quality	
	8008		100	u16		FLTMSTA1 Active setting group	LD0.FLTMSTA1.ActSG.stVal
	8009		100	u16	100	FLTMSTA1 Phase A current	LD0.FLTMSTA1.AmpsA.mag.f

## Section 2 Modbus data mappings

Coil Addr	4x Register Addr.	W	Dc	Type	Scale	Description	IEC61850 Data Attribute Name
	8010		100	u16	100	FLTMSTA1 phase A current (b)	LD0.FLTMSTA1.AmpsAb.mag.f
	8011		100	u16	100	FLTMSTA1 Phase A current (c)	LD0.FLTMSTA1.AmpsAc.mag.f
	8012		100	u16	100	FLTMSTA1 Phase B current	LD0.FLTMSTA1.AmpsB.mag.f
	8013		100	u16	100	FLTMSTA1 phase B current (b)	LD0.FLTMSTA1.AmpsBb.mag.f
	8014		100	u16	100	FLTMSTA1 Phase B current (c)	LD0.FLTMSTA1.AmpsBc.mag.f
	8015		100	u16	100	FLTMSTA1 Phase C current	LD0.FLTMSTA1.AmpsC.mag.f
	8016		100	u16	100	FLTMSTA1 phase C current (b)	LD0.FLTMSTA1.AmpsCb.mag.f
	8017		100	u16	100	FLTMSTA1 Phase C current (c)	LD0.FLTMSTA1.AmpsCc.mag.f
	8018		100	u16	100	FLTMSTA1 Residual current	LD0.FLTMSTA1.AmpsN.mag.f
	8019		100	u16	100	FLTMSTA1 Residual current (b)	LD0.FLTMSTA1.AmpsNb.mag.f
	8020		100	u16	100	FLTMSTA1 Residual current (c)	LD0.FLTMSTA1.AmpsNc.mag.f
	8021		100	u16	100	FLTMSTA1 Calculated residual current	LD0.FLTMSTA1.AmpsNCIc.mag.f
	8022		100	u16	100	FLTMSTA1 Calculated residual current (b)	LD0.FLTMSTA1.AmpsNCIcb.mag.f
	8023		100	u16	100	FLTMSTA1 Calculated residual current (c)	LD0.FLTMSTA1.AmpsNCIcc.mag.f
	8024		100	u16	100	FLTMSTA1 Negative sequence current	LD0.FLTMSTA1.AmpsNgSeq.mag.f
	8025		100	u16	100	FLTMSTA1 Negative sequence current (b)	LD0.FLTMSTA1.AmpsNgSeqb.mag.f
	8026		100	u16	100	FLTMSTA1 Negative sequence current (c)	LD0.FLTMSTA1.AmpsNgSeqc.mag.f
	8027		100	u16	100	FLTMSTA1 Positive sequence current	LD0.FLTMSTA1.AmpsPsSeq.mag.f
	8028		100	u16	100	FLTMSTA1 Positive sequence current (b)	LD0.FLTMSTA1.AmpsPsSeqb.mag.f
	8029		100	u16	100	FLTMSTA1 Positive sequence current (c)	LD0.FLTMSTA1.AmpsPsSeqc.mag.f
	8030		100	u32	100	FLTMSTA1 Breaker clear time	LD0.FLTMSTA1.CBClrTm.mag.f
	8031						
	8032		100	s32	100	FLTMSTA1 Conductance Yo	LD0.FLTMSTA1.CondN.mag.f
	8033						
	8034		100	u16	100	FLTMSTA1 Angle phase B to phase C voltage - phase A current	LD0.FLTMSTA1.DifAAngBC.mag.f
	8035		100	u16	100	FLTMSTA1 Angle phase B to phase C voltage - phase A current (b)	LD0.FLTMSTA1.DifAAngBCb.mag.f
	8036		100	u16	100	FLTMSTA1 Differential current phase A	LD0.FLTMSTA1.DifAmpsA.mag.f
	8037		100	u16	100	FLTMSTA1 Differential current phase B	LD0.FLTMSTA1.DifAmpsB.mag.f
	8038		100	u16	100	FLTMSTA1 Differential current phase C	LD0.FLTMSTA1.DifAmpsC.mag.f
	8039		100	u16	100	FLTMSTA1 Differential current residual	LD0.FLTMSTA1.DifAmpsN.mag.f
	8040		100	u16	100	FLTMSTA1 Angle phase C to phase A voltage - phase B current	LD0.FLTMSTA1.DifBAngCA.mag.f
	8041		100	u16	100	FLTMSTA1 Angle phase C to phase A voltage - phase B current (b)	LD0.FLTMSTA1.DifBAngCAb.mag.f
	8042		100	u16	100	FLTMSTA1 Angle phase A to phase B voltage - phase C current	LD0.FLTMSTA1.DifCAngAB.mag.f
	8043		100	u16	100	FLTMSTA1 Angle phase A to phase B voltage - phase C current (b)	LD0.FLTMSTA1.DifCAngABb.mag.f
	8044		100	u16	100	FLTMSTA1 Angle residual voltage - residual current	LD0.FLTMSTA1.DifNAngN.mag.f

Coil Addr	4x Register Addr.	W	Dc	Type	Scale	Description	IEC61850 Data Attribute Name
	8045		100	u16	100	FLTMSTA1 Angle residual voltage - residual current (b)	LD0.FLTMSTA1.DifNAngNb.mag.f
	8046		100	u32	100	FLTMSTA1 Distance to fault measured in pu	LD0.FLTMSTA1.FltDiskm.mag.f
	8047						
	8048		100	u32	100	FLTMSTA1 Fault resistance	LD0.FLTMSTA1.FltZ.cVal.mag.f
	8049						
	8050		100	s16	100		
	8051		100	u16	100	FLTMSTA1 Frequency	LD0.FLTMSTA1.Hz.mag.f
	8052		100	s16	100	FLTMSTA1 Frequency gradient	LD0.FLTMSTA1.HzS.mag.f
	8053		100	u16	100	FLTMSTA1 Maximum phase A current	LD0.FLTMSTA1.MaxAmpsA.mag.f
	8054		100	u16	100	FLTMSTA1 Maximum phase A current (b)	LD0.FLTMSTA1.MaxAmpsAb.mag.f
	8055		100	u16	100	FLTMSTA1 Maximum phase A current (c)	LD0.FLTMSTA1.MaxAmpsAc.mag.f
	8056		100	u16	100	FLTMSTA1 Maximum phase B current	LD0.FLTMSTA1.MaxAmpsB.mag.f
	8057		100	u16	100	FLTMSTA1 Maximum phase B current (b)	LD0.FLTMSTA1.MaxAmpsBb.mag.f
	8058		100	u16	100	FLTMSTA1 Maximum phase B current (c)	LD0.FLTMSTA1.MaxAmpsBc.mag.f
	8059		100	u16	100	FLTMSTA1 Maximum phase C current	LD0.FLTMSTA1.MaxAmpsC.mag.f
	8060		100	u16	100	FLTMSTA1 Maximum phase C current (b)	LD0.FLTMSTA1.MaxAmpsCb.mag.f
	8061		100	u16	100	FLTMSTA1 Maximum phase C current (c)	LD0.FLTMSTA1.MaxAmpsCc.mag.f
	8062		100	u16	100	FLTMSTA1 Maximum residual current	LD0.FLTMSTA1.MaxAmpsN.mag.f
	8063		100	u16	100	FLTMSTA1 Maximum residual current (b)	LD0.FLTMSTA1.MaxAmpsNb.mag.f
	8064		100	u16	100	FLTMSTA1 Maximum residual current (c)	LD0.FLTMSTA1.MaxAmpsNc.mag.f
	8065		100	u16	100	FLTMSTA1 calculated temperature of the protected object relative to the trip level	LD0.FLTMSTA1.MaxTmpRI.mag.f
	8066		100	u16	100	FLTMSTA1 Maximum phase A differential current	LD0.FLTMSTA1.MxDifACIcA.mag.f
	8067		100	u16	100	FLTMSTA1 Maximum phase B differential current	LD0.FLTMSTA1.MxDifACIcB.mag.f
	8068		100	u16	100	FLTMSTA1 Maximum phase C differential current	LD0.FLTMSTA1.MxDifACIcC.mag.f
	8069		100	u16	100	FLTMSTA1 Maximum phase A bias current	LD0.FLTMSTA1.MxRstACIcA.mag.f
	8070		100	u16	100	FLTMSTA1 Maximum phase B bias current	LD0.FLTMSTA1.MxRstACIcB.mag.f
	8071		100	u16	100	FLTMSTA1 Maximum phase C bias current	LD0.FLTMSTA1.MxRstACIcC.mag.f
	8072		100	u32		FLTMSTA1 Fault record number	LD0.FLTMSTA1.OpCnt.stVal
	8073						
	8074		100	u32	100	FLTMSTA1 Trip time	LD0.FLTMSTA1.OpTm.mag.f
	8075						
	8076		100	u16	100	FLTMSTA1 PDNSPTOC1 ratio I2/I1	LD0.FLTMSTA1.PDNS1MxRat.mag.f
	8077		100	s32	100	FLTMSTA1 Reactance of fault loop	LD0.FLTMSTA1.PPLoopReac.mag.f
	8078						
	8079		100	s32	100	FLTMSTA1 Resistance of fault loop	LD0.FLTMSTA1.PPLoopRis.mag.f
	8080						
	8081		100	u16		FLTMSTA1 Protection function	LD0.FLTMSTA1.ProFcn.stVal

## Section 2 Modbus data mappings

1MAC509789-IB A

Coil Addr	4x Register Addr.	W	Dc	Type	Scale	Description	IEC61850 Data Attribute Name
	8082		100	u16	100	FLTMSTA1 Bias current phase A	LD0.FLTMSTA1.RstAmpsA.mag.f
	8083		100	u16	100	FLTMSTA1 Bias current phase B	LD0.FLTMSTA1.RstAmpsB.mag.f
	8084		100	u16	100	FLTMSTA1 Bias current phase C	LD0.FLTMSTA1.RstAmpsC.mag.f
	8085		100	u16	100	FLTMSTA1 Bias current residual	LD0.FLTMSTA1.RstAmpsN.mag.f
	8086		100	u16		FLTMSTA1 Autoreclosing shot pointer value	LD0.FLTMSTA1.ShotPntr.stVal
	8087		100	u16	100	FLTMSTA1 Maximum pickup duration of all stages during the fault	LD0.FLTMSTA1.StrDur.mag.f
	8088		100	s32	100	FLTMSTA1 Susceptance Yo	LD0.FLTMSTA1.SusN.mag.f
	8089						
	8090		100	u16	100	FLTMSTA1 Negative sequence voltage	LD0.FLTMSTA1.VNgSeq.mag.f
	8091		100	u16	100	FLTMSTA1 Negative sequence voltage (b)	LD0.FLTMSTA1.VNgSeqb.mag.f
	8092		100	u16	100	FLTMSTA1 Phase A voltage	LD0.FLTMSTA1.VoltsA.mag.f
	8093		100	u16	100	FLTMSTA1 Phase A to phase B voltage	LD0.FLTMSTA1.VoltsAB.mag.f
	8094		100	u16	100	FLTMSTA1 Phase A voltage (b)	LD0.FLTMSTA1.VoltsAb.mag.f
	8095		100	u16	100	FLTMSTA1 Phase A to phase B voltage (b)	LD0.FLTMSTA1.VoltsABb.mag.f
	8096		100	u16	100	FLTMSTA1 Phase B voltage	LD0.FLTMSTA1.VoltsB.mag.f
	8097		100	u16	100	FLTMSTA1 Phase B voltage (b)	LD0.FLTMSTA1.VoltsBb.mag.f
	8098		100	u16	100	FLTMSTA1 Phase B to phase C voltage	LD0.FLTMSTA1.VoltsBC.mag.f
	8099		100	u16	100	FLTMSTA1 Phase B to phase C voltage (b)	LD0.FLTMSTA1.VoltsBCb.mag.f
	8100		100	u16	100	FLTMSTA1 Phase C voltage	LD0.FLTMSTA1.VoltsC.mag.f
	8101		100	u16	100	FLTMSTA1 Phase C to phase A voltage	LD0.FLTMSTA1.VoltsCA.mag.f
	8102		100	u16	100	FLTMSTA1 Phase C to phase A voltage (b)	LD0.FLTMSTA1.VoltsCAb.mag.f
	8103		100	u16	100	FLTMSTA1 Phase B voltage (b)	LD0.FLTMSTA1.VoltsCb.mag.f
	8104		100	u16	100	FLTMSTA1 Residual voltage	LD0.FLTMSTA1.VoltsN.mag.f
	8105		100	u16	100	FLTMSTA1 Residual voltage (b)	LD0.FLTMSTA1.VoltsNb.mag.f
	8106		100	u16	100	FLTMSTA1 Positive sequence voltage	LD0.FLTMSTA1.VPsSeq.mag.f
	8107		100	u16	100	FLTMSTA1 Positive sequence voltage (b)	LD0.FLTMSTA1.VPsSeqb.mag.f
	8108		100	u16	100	FLTMSTA1 Zero sequence voltage	LD0.FLTMSTA1.VZroSeq.mag.f
	8109		100	u16	100	FLTMSTA1 Zero sequence voltage (b)	LD0.FLTMSTA1.VZroSeqb.mag.f
	8110		100	u32	100	DRFLO1 Fault Distance	LD0.DRFLO1.FitDisKm.mag.f
	8111						
	8112		100	u16	100	DRFLO1 Fault Loop	LD0.DRFLO1.FitLoop.stVal
	8113		100	u32	100	DRFLO1 Loop Reactance	LD0.DRFLO1.FitLoopX.mag.f
	8114						
	8115		100	u32	100	DRFLO1 Fault Resistance	LD0.DRFLO1.FitZ.mag.f

Table 8: LED Status (LEDGGIO1)

Coil Addr (0x)	Input Addr (1x)	Register (:Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		3149	0		u16			Programmable LEDs Status of programmable LED 1	LD0.LEDGGIO1.ISCSO1.stVal
		3150	0		u16			Programmable LEDs Status of programmable LED 2	LD0.LEDGGIO1.ISCSO2.stVal
		3151	0		u16			Programmable LEDs Status of programmable LED 3	LD0.LEDGGIO1.ISCSO3.stVal
		3152	0		u16			Programmable LEDs Status of programmable LED 4	LD0.LEDGGIO1.ISCSO4.stVal
		3153	0		u16			Programmable LEDs Status of programmable LED 5	LD0.LEDGGIO1.ISCSO5.stVal
		3154	0		u16			Programmable LEDs Status of programmable LED 6	LD0.LEDGGIO1.ISCSO6.stVal
		3155	0		u16			Programmable LEDs Status of programmable LED 7	LD0.LEDGGIO1.ISCSO7.stVal
		3156	0		u16			Programmable LEDs Status of programmable LED 8	LD0.LEDGGIO1.ISCSO8.stVal
		3157	0		u16			Programmable LEDs Status of programmable LED 9	LD0.LEDGGIO1.ISCSO9.stVal
		3158	0		u16			Programmable LEDs Status of programmable LED 10	LD0.LEDGGIO1.ISCSO10.stVal
		3159	0		u16			Programmable LEDs Status of programmable LED 11	LD0.LEDGGIO1.ISCSO11.stVal

Table 9: LED Condition monitoring (LEDPTRC1)

Coil Addr	Input Addr (1x)	Register (:Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6148		384:4	0					Global conditioning Trip general	LD0.LEDPTRC1.Op.general
6149		384:5		Yes					
6150		384:6	0					Global conditioning Trip phsA	LD0.LEDPTRC1.Op.phsA
6151		384:7		Yes					
6152		384:8	0					Global conditioning Trip phsB	LD0.LEDPTRC1.Op.phsB
6153		384:9		Yes					
6154		384:10	0					Global conditioning Trip phsC	LD0.LEDPTRC1.Op.phsC
6155		384:11		Yes					

Table 10: General Device Information (LPHD1)

Coil Addr (0x)	Input Addr (1x)	Register (:Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		3077	6		s32			Physical device Number of composition changes	LD0.LPHD1.NumCmpChg.stVal
		3078	6						
		3079	0		u16			Physical device General state	LD0.LPHD1.PhyHealth.stVal
		3080	0		u16			Physical device IED warning	LD0.LPHD1.PhyHealth1.stVal
		3081	0		u16			Physical device IED internal fault	LD0.LPHD1.PhyHealth2.stVal

**Table 11: General Device Information (LLN0)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5182		323:14	0					Control LLN0 Local / Remote	CTRL.LLN0.Loc.stVal
5183		323:15		Yes					
6156		384:12	0					Protection LLN0 Settings change	LD0.LLN0.SetChg.stVal
6158		384:14	0					Protection LLN0 Settings reservation	LD0.LLN0.SetSeld.stVal
		3045	0		u16			Control LLN0 LR state monitoring for PCM	CTRL.LLN0.LocRem.stVal
		3076	6		u16			Protection LLN0 Phase rotation order	LD0.LLN0.PhRotSet.setVal

**Table 12: 51P : Three-phase non-directional overcurrent protection low stage instance 1 (PHLPTOC1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5996		374:12	0					51P Enable signal for current multiplier	LD0.PHLPTOC1.InEnaMult.stVal
5998		374:14	0					51P Trip	LD0.PHLPTOC1.Op.general
6000		375:0	0					51P Trip phsA	LD0.PHLPTOC1.Op.phsA
6002		375:2	0					51P Trip phsB	LD0.PHLPTOC1.Op.phsB
6004		375:4	0					51P Trip phsC	LD0.PHLPTOC1.Op.phsC

**Table 13: 50P-1 : Three-phase non-directional overcurrent protection high stage instance 1 (PHHPTOC1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5926		370:6	0					50P-1 Enable signal for current multiplier	LD0.PHHPTOC1.InEnaMult.stVal
5928		370:8	0					50P-1 Trip	LD0.PHHPTOC1.Op.general
5930		370:10	0					50P-1 Trip phsA	LD0.PHHPTOC1.Op.phsA
5932		370:12	0					50P-1 Trip phsB	LD0.PHHPTOC1.Op.phsB
5934		370:14	0					50P-1 Trip phsC	LD0.PHHPTOC1.Op.phsC

**Table 14: 50P-2 : Three-phase non-directional overcurrent protection high stage instance 2 (PHHPTOC2)**

Coil Addr (0x)	Input Addr (1x)	Register (:Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5936		371:0	0					50P-2 Enable signal for current multiplier	LD0.PHHPTOC2.InEnaMult.stVal
5938		371:2	0					50P-2 Trip	LD0.PHHPTOC2.Op.general
5940		371:4	0					50P-2 Trip phsA	LD0.PHHPTOC2.Op.phsA
5942		371:6	0					50P-2 Trip phsB	LD0.PHHPTOC2.Op.phsB
5944		371:8	0					50P-2 Trip phsC	LD0.PHHPTOC2.Op.phsC



**Table 15: 50P-3 : Three-phase non-directional overcurrent protection instantaneous stage instance 1 (PHIPTOC1)**

Coil Addr (0x)	Input Addr (1x)	Register (:Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5986		374:2	0					50P-3 Enable signal for current multiplier	LD0.PHIPTOC1.InEnaMult.stVal
5988		374:4	0					50P-3 Trip	LD0.PHIPTOC1.Op.general
5990		374:6	0					50P-3 Trip phsA	LD0.PHIPTOC1.Op.phsA
5992		374:8	0					50P-3 Trip phsB	LD0.PHIPTOC1.Op.phsB
5994		374:10	0					50P-3 Trip phsC	LD0.PHIPTOC1.Op.phsC

**Table 16: 51LT : Three-phase non-directional long time overcurrent protection lower stage instance 1 (PHLTPTOC1)**

Coil Addr (0x)	Input Addr (1x)	Register (:Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6026		376:10	0					51LT Enable signal for current multiplier	LD0.PHLTPTOC1.InEnaMult.stVal
6028		376:12	0					51LT Trip	LD0.PHLTPTOC1.Op.general
6030		376:14	0					51LT Trip phsA	LD0.PHLTPTOC1.Op.phsA
6032		377:0	0					51LT Trip phsB	LD0.PHLTPTOC1.Op.phsB
6034		377:2	0					51LT Trip phsC	LD0.PHLTPTOC1.Op.phsC

**Table 17: 67/51P : Three-phase directional overcurrent protection low stage instance 1 (DPHLPTOC1)**

Coil Addr (0x)	Input Addr (1x)	Register (:Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5850		365:10	0					67/51P Enable signal for current multiplier	LD0.DPHLPTOC1.InEnaMult.stVal
5852		365:12	0					67/51P Trip	LD0.DPHLPTOC1.Op.general
5854		365:14	0					67/51P Trip phsA	LD0.DPHLPTOC1.Op.phsA
5856		366:0	0					67/51P Trip phsB	LD0.DPHLPTOC1.Op.phsB
5858		366:2	0					67/51P Trip phsC	LD0.DPHLPTOC1.Op.phsC

**Table 18: 67/50P-1 : Three-phase directional overcurrent protection high stage instance 1 (DPHHPTOC1)**

Coil Addr (0x)	Input Addr (1x)	Register (:Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5830		364:6	0					67/50P-1 Enable signal for current multiplier	LD0.DPHHPTOC1.InEnaMult.stVal
5832		364:8	0					67/50P-1 Trip	LD0.DPHHPTOC1.Op.general
5834		364:10	0					67/50P-1 Trip phsA	LD0.DPHHPTOC1.Op.phsA
5836		364:12	0					67/50P-1 Trip phsB	LD0.DPHHPTOC1.Op.phsB
5838		364:14	0					67/50P-1 Trip phsC	LD0.DPHHPTOC1.Op.phsC

**Table 19: 67/50P-2 : Three-phase directional overcurrent protection high stage instance 2 (DPHHPTOC2)**

Coil Addr (0x)	Input Addr (1x)	Register (:Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5840		365:0	0					67/50P-2 Enable signal for current multiplier	LD0.DPHHPTOC2.InEnaMult.stVal
5842		365:2	0					67/50P-2 Trip	LD0.DPHHPTOC2.Op.general

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5844		365:4	0					67/50P-2 Trip phsA	LD0.DPHHPTOC2.Op.phsA
5846		365:6	0					67/50P-2 Trip phsB	LD0.DPHHPTOC2.Op.phsB
5848		365:8	0					67/50P-2 Trip phsC	LD0.DPHHPTOC2.Op.phsC

**Table 20:** 51G : Non-directional earth-fault protection low stage instance 1 (EFLPTOC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5898		368:10	0					51G Enable signal for current multiplier	LD0.EFLPTOC1.InEnaMult.stVal
5900		368:12	0					51G Trip	LD0.EFLPTOC1.Op.general

**Table 21:** 51N-1 : Non-directional earth-fault protection low stage instance 2 (EFLPTOC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5902		368:14	0					51N-1 Enable signal for current multiplier	LD0.EFLPTOC2.InEnaMult.stVal
5904		369:0	0					51N-1 Trip	LD0.EFLPTOC2.Op.general

**Table 22:** 51N-1 : Non-directional earth-fault protection low stage instance 4 (EFLPTOC4)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5910		369:6	0					50SEF Enable signal for current multiplier	LD0.EFLPTOC4.InEnaMult.stVal
5912		369:8	0					50SEF Trip	LD0.EFLPTOC4.Op.general

**Table 23:** 50G-1 : Non-directional earth-fault protection high stage instance 1 (EFHPTOC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5870		366:14	0					50G-1 Enable signal for current multiplier	LD0.EFHPTOC1.InEnaMult.stVal
5872		367:0	0					50G-1 Trip	LD0.EFHPTOC1.Op.general

**Table 24:** 50G-2 : Non-directional earth-fault protection high stage instance 2 (EFHPTOC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5874		367:2	0					50G-2 Enable signal for current multiplier	LD0.EFHPTOC2.InEnaMult.stVal
5876		367:4	0					50G-2 Trip	LD0.EFHPTOC2.Op.general

**Table 25:** 50N-1 : Non-directional earth-fault protection high stage instance 3 (EFHPTOC3)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5878		367:6	0					50N-1 Enable signal for current multiplier	LD0.EFHPTOC3.InEnaMult.stVal
5880		367:8	0					50N-1 Trip	LD0.EFHPTOC3.Op.general

**Table 26:** 50N-2 : Non-directional earth-fault protection high stage instance 4 (EFHPTOC4)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5882		367:10	0					50N-2 Enable signal for current multiplier	LD0.EFHPTOC4.InEnaMult.stVal
5884		367:12	0					50N-2 Trip	LD0.EFHPTOC4.Op.general

**Table 27:** 50G-3 : Non-directional earth-fault protection instantaneous stage instance 1 (EFIPTOC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5890		368:2	0					50G-3 Enable signal for current multiplier	LD0.EFIPTOC1.InEnaMult.stVal
5892		368:4	0					50G-3 Trip	LD0.EFIPTOC1.Op.general

**Table 28:** 50N-3 : Non-directional earth-fault protection instantaneous stage instance 2 (EFIPTOC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5894		368:6	0					50N-3 Enable signal for current multiplier	LD0.EFIPTOC2.InEnaMult.stVal
5896		368:8	0					50N-3 Trip	LD0.EFIPTOC2.Op.general

**Table 29:** 67/51N : Directional earth-fault protection low stage instance 1 (DEFLPTOC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5826		364:2	0					67/51N Enable signal for current multiplier	LD0.DEFLPTOC2.InEnaMult.stVal
5828		364:4	0					67/51N Trip	LD0.DEFLPTOC2.Op.general

**Table 30:** T67/51N : Directional earth-fault protection low stage instance 1 (DEFLLDIR2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6096		381:0	0					67/51N Relay characteristic angle control	LD0.DEFLRDIR2.InRcaCtl.stVal

**Table 31:** 67/50N-1 : Directional earth-fault protection high stage instance 1 (DEFHPTOC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5814		363:6	0					67/50N-1 Enable signal for current multiplier	LD0.DEFHPTOC1.InEnaMult.stVal
5816		363:8	0					67/50N-1 Trip	LD0.DEFHPTOC1.Op.general

**Table 32:** 67/50N-1 : Directional earth-fault protection high stage instance 1 (DEFHRDIR1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6090		380:10	0					67/50N-1 Relay characteristic angle control	LD0.DEFHRDIR1.InRcaCtl.stVal

## Section 2 Modbus data mappings

**Table 33: 67/50N-2 : Directional earth-fault protection high stage instance 2 (DEFHPTOC2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5818		363:10	0					67/50N-2 Enable signal for current multiplier	LD0.DEFHPTOC2.InEnaMult.stVal
5820		363:12	0					67/50N-2 Trip	LD0.DEFHPTOC2.Op.general

**Table 34: 67/50N-2 : Directional earth-fault protection high stage instance 2 (DEFHRDIR2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6092		380:12	0					67/50N-2 Relay characteristic angle control	LD0.DEFHRDIR2.InRcaCtl.stVal

**Table 35: 32P-1 : Three phase directional power protection instance 1 (DPSRDIR1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6106		381:10	0					32P-1 direction signal	LD0.DPSRDIR1.Dir.general
		3074	6		s16	100		32P-1 Angle between polarizing and operating quantity	LD0.DPSRDIR1.OpChrAng.mag.f

**Table 36: 21P : Phase distance protection instance 1 (PHDSTPDIS1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6346		396:10	0					21P Trip Z1	LD0.PHDSTPDIS1.Op.general

**Table 37: 21P : Phase distance protection instance 1 (PHDSTPDIS2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6348		396:12	0					21P Trip Z2	LD0.PHDSTPDIS2.Op.general

**Table 38: 21P : Phase distance protection instance 1 (PHDSTPDIS3)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6350		396:14	0					21P Trip Z3	LD0.PHDSTPDIS3.Op.general

**Table 39: 21P : Phase distance protection instance 1 (PHDSTPDIS4)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6352		397:0	0					21P Trip Z4	LD0.PHDSTPDIS4.Op.general

**Table 40: 21P : Phase distance protection instance 1 (PHDSTPDIS5)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6354		397:2	0					21P Trip Z5	LD0.PHDSTPDIS5.Op.general

**Table 41: 21P : Phase distance protection instance 1 (PHGFCDIS1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6356		397:4	0					21P Start signal for load discrimination logic	LD0.PHGFCDIS1.LodDsrDet.stVal

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6358		397:6	0					21P Pickup GFC	LD0.PHGFCPDIS1.Str.general

**Table 42:** 46-1 : Negative-sequence overcurrent protection instance 1 (NSPTOC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5914		369:10	0					46-1 Enable signal for current multiplier	LD0.NSPTOC1.InEnaMult.stVal
5916		369:12	0					46-1 Trip	LD0.NSPTOC1.Op.general

**Table 43:** 46-2 : Negative-sequence overcurrent protection instance 2 (NSPTOC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5918		369:14	0					46-2 Enable signal for current multiplier	LD0.NSPTOC2.InEnaMult.stVal
5920		370:0	0					46-2 Trip	LD0.NSPTOC2.Op.general

**Table 44:** 46PD : Phase discontinuity protection (PDNSPTOC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6046		377:14	0					46PD Trip	LD0.PDNSPTOC1.Op.general

**Table 45:** 59G : Residual overvoltage protection instance 1 (ROVPTOV1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6076		379:12	0					59G Trip	LD0.ROVPTOV1.Op.general

**Table 46:** 59N-1 (1) : Residual overvoltage protection instance 2 (ROVPTOV2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6078		379:14	0					59N-1(1) Trip	LD0.ROVPTOV2.Op.general

**Table 47:** 59N-1 (2) : Residual overvoltage protection instance 3 (ROVPTOV3)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6080		380:0	0					59N-1(2) Trip	LD0.ROVPTOV3.Op.general

**Table 48:** 27-1 (1) : Three-phase undervoltage protection instance 1 (PHPTUV1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6386		399:2	0					27-1(1) Trip	LD0.PHPTUV1.Op.general
6388		399:4	0					27-1(1) Trip phsA	LD0.PHPTUV1.Op.phsA
6390		399:6	0					27-1(1) Trip phsB	LD0.PHPTUV1.Op.phsB
6392		399:8	0					27-1(1) Trip phsC	LD0.PHPTUV1.Op.phsC

**Table 49:** 27-2 (1) : Three-phase undervoltage protection instance 2 (PHPTUV2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6394		399:10	0					27-2(1) Trip	LD0.PHPTUV2.Op.general

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6396		399:12	0					27-2(1) Trip phsA	LD0.PHPTUV2.Op.phsA
6398		399:14	0					27-2(1) Trip phsB	LD0.PHPTUV2.Op.phsB
6400		400:0	0					27-2(1) Trip phsC	LD0.PHPTUV2.Op.phsC

**Table 50:** 27-1 (2) : Three-phase undervoltage protection instance 3 (PHPTUV3)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6402		400:2	0					27-1(2) Trip	LD0.PHPTUV3.Op.general

**Table 51:** 27-2 (2) : Three-phase undervoltage protection instance 4 (PHPTUV4)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6404		400:4	0					27-2(2) Trip	LD0.PHPTUV4.Op.general

**Table 52:** 59-1 (1) : Three-phase overvoltage protection instance 1 (PHPTOV1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6050		378:2	0					59-1(1) Trip	LD0.PHPTOV1.Op.general
6052		378:4	0					59-1(1) Trip phsA	LD0.PHPTOV1.Op.phsA
6054		378:6	0					59-1(1) Trip phsB	LD0.PHPTOV1.Op.phsB
6056		378:8	0					59-1(1) Trip phsC	LD0.PHPTOV1.Op.phsC

**Table 53:** 59-2 (1) : Three-phase overvoltage protection instance 2 (PHPTOV2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6058		378:10	0					59-2(1) Trip	LD0.PHPTOV2.Op.general
6060		378:12	0					59-2(1) Trip phsA	LD0.PHPTOV2.Op.phsA
6062		378:14	0					59-2(1) Trip phsB	LD0.PHPTOV2.Op.phsB
6064		379:0	0					59-2(1) Trip phsC	LD0.PHPTOV2.Op.phsC

**Table 54:** 59-2 (2) : Three-phase overvoltage protection instance 3 (PHPTOV3)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6066		379:2	0					59-1(2) Trip	LD0.PHPTOV3.Op.general
6068		379:4	0					59-1(2) Trip phsA	LD0.PHPTOV3.Op.phsA
6070		379:6	0					59-1(2) Trip phsB	LD0.PHPTOV3.Op.phsB
6072		379:8	0					59-1(2) Trip phsC	LD0.PHPTOV3.Op.phsC

**Table 55:** 59-2 (2) : Three-phase overvoltage protection instance 4 (PHPTOV4)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6074		379:10	0					59-2(2) Trip	LD0.PHPTOV4.Op.general

**Table 56:** 47-1 (1) : Negative-sequence overvoltage protection instance 1 (NSPTOV1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6082		380:2	0					47-1(1) Trip	LD0.NSPTOV1.Op.general

**Table 57:** 47-2 (1) : Negative-sequence overvoltage protection instance 2 (NSPTOV2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6084		380:4	0					47-2(1) Trip	LD0.NSPTOV2.Op.general

**Table 58:** 47-1 (2) : Negative-sequence overvoltage protection instance 3 (NSPTOV3)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6086		380:6	0					47-1(2) Trip	LD0.NSPTOV3.Op.general

**Table 59:** 47-2 (2) : Negative-sequence overvoltage protection instance 4 (NSPTOV4)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6088		380:8	0					47-2(2) Trip	LD0.NSPTOV4.Op.general

**Table 60:** 81-1 : Frequency protection instance 1 (FRPTRC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6128		383:0	0					81-1 Trip	LD0.FRPTRC1.Op.general
		3139	6		u16	100		81-1 Pickup duration	LD0.FRPTRC1.StrDur.mag.f

**Table 61:** 81-1 : Frequency protection instance 1 (FRPTOF1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6120		382:8	0					81-1 Trip signal for overfrequency	LD0.FRPTOF1.Op.general
		3135	6		u16	100		81-1 Pickup duration	LD0.FRPTOF1.StrDur.mag.f

**Table 62:** 81-1 : Frequency protection instance 1 (FRPTUF1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6136		383:8	0					81-1 Trip signal for underfrequency	LD0.FRPTUF1.Op.general
		3143	6		u16	100		81-1 Pickup duration	LD0.FRPTUF1.StrDur.mag.f

**Table 63:** 81-1 : Frequency protection instance 1 (FRPFRC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6112		382:0	0					81-1 Trip signal for frequency gradient	LD0.FRPFRC1.Op.general
		3131	6		u16	100		81-1 Pickup duration	LD0.FRPFRC1.StrDur.mag.f

**Table 64:** 81-2 : Frequency protection instance 2 (FRPTRC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6130		383:2	0					81-2 Trip	LD0.FRPTRC2.Op.general

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		3140	6		u16	100		81-2 Pickup duration	LD0.FRPTRC2.StrDur.mag.f

**Table 65:** 81-2 : Frequency protection instance 2 (FRPTOF2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6122		382:10	0					81-2 Trip signal for overfrequency	LD0.FRPTOF2.Op.general
		3136	6		u16	100		81-2 Pickup duration	LD0.FRPTOF2.StrDur.mag.f

**Table 66:** 81-2 : Frequency protection instance 2 (FRPTUF2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6138		383:10	0					81-2 Trip signal for underfrequency	LD0.FRPTUF2.Op.general
		3144	6		u16	100		81-2 Pickup duration	LD0.FRPTUF2.StrDur.mag.f

**Table 67:** 81-2 : Frequency protection instance 2 (FRPFRC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6114		382:2	0					81-2 Trip signal for frequency gradient	LD0.FRPFRC2.Op.general
		3132	6		u16	100		81-2 Pickup duration	LD0.FRPFRC2.StrDur.mag.f

**Table 68:** 24 : Voltage per hertz protection instance 1 (OEPVPH1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6304		394:0	0					24 Signal to indicate machine is in cooling process	LD0.OEPVPH1.CoolAct.stVal
6306		394:2	0					24 Trip	LD0.OEPVPH1.Op.general
6308		394:4	0					24 Signal for blocking reconnection of an overheated machine	LD0.OEPVPH1.StrInh.stVal

**Table 69:** 49F : Three-phase thermal protection for feeders cables and distribution transformers (T1PTTR1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6672		417:0	0					49F Thermal Alarm	LD0.T1PTTR1.AlmThm.general
6674		417:2	0					49F Enable Current multiplier	LD0.T1PTTR1.InEnaMult.stVal
6676		417:4	0					49F Thermal overload indicator. To inhibit reclose.	LD0.T1PTTR1.InhRec.stVal
6678		417:6	0					49F Trip	LD0.T1PTTR1.Op.general
		2987	6		u16	100		49F The calculated temperature of the protected object	LD0.T1PTTR1.Tmp.mag.f
		2988	6		u16	100		49F The calculated temperature of the protected object relative to the trip level	LD0.T1PTTR1.TmpRI.mag.f
		2989	6		u16	100		49F The ambient temperature used in the calculation	LD0.T1PTTR1.TmpUsed.mag.f



**Table 70:** 37-1 : Loss of phase instance 1 (PHPTUC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6362		397:10	0					37-1 Trip	LD0.PHPTUC1.Op.general
6364		397:12	0					37-1 Trip phase A	LD0.PHPTUC1.Op.phsA
6366		397:14	0					37-1 Trip phase B	LD0.PHPTUC1.Op.phsB
6368		398:0	0					37-1 Trip phase C	LD0.PHPTUC1.Op.phsC

**Table 71:** VSWI : Three phase measurement switching (VMSWI1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5680		355:0	0					VSWI Selected voltage source is bus 1	LD0.VMSWI1.VSelStBus1.stVal
5682		355:2	0					VSWI Selected voltage source is bus 2	LD0.VMSWI1.VSelStBus2.stVal

**Table 72:** 87LOZREF : Numerical stabilized low impedance restricted earth-fault protection (LREFPDIF1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6164		385:4	0					87LOZREF 2nd harmonic block	LD0.LREFPDIF1.Blk2Hst.general
6166		385:6	0					87LOZREF Trip	LD0.LREFPDIF1.Op.general

**Table 73:** 50BF-1 : Circuit breaker failure protection instance 1 (CCBRBRF1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5314		332:2	0					50BF-1 CB faulty and unable to trip	LD0.CCBRBRF1.InCBFlt.stVal
5315		332:3		Yes					
5316		332:4	0					50BF-1 CB in closed position	LD0.CCBRBRF1.InPosCls.stVal
5317		332:5		Yes					
5318		332:6	0					50BF-1 CBFP pickup command	LD0.CCBRBRF1.InStr.stVal
5319		332:7		Yes					
5320		332:8	0					50BF-1 Backup trip	LD0.CCBRBRF1.OpEx.general
5321		332:9		Yes					
5322		332:10	0					50BF-1 Retrip	LD0.CCBRBRF1.OpIn.general
5323		332:11		Yes					
5324		332:12	0					50BF-1 Delayed CB failure alarm	LD0.CCBRBRF1.Str.general
5325		332:13		Yes					

**Table 74:** 50BF-2 : Circuit breaker failure protection instance 2 (CCBRBRF2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5326		332:14	0					50BF-2 CB faulty and unable to trip	LD0.CCBRBRF2.InCBFlt.stVal
5327		332:15		Yes					

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5328		333:0	0					50BF-2 CB in closed position	LD0.CCBRBRF2.InPosCls.stVal
5329		333:1		Yes					
5330		333:2	0					50BF-2 CBFP pickup command	LD0.CCBRBRF2.InStr.stVal
5331		333:3		Yes					
5332		333:4	0					50BF-2 Backup trip	LD0.CCBRBRF2.OpEx.general
5333		333:5		Yes					
5334		333:6	0					50BF-2 Retrip	LD0.CCBRBRF2.OpIn.general
5335		333:7		Yes					
5336		333:8	0					50BF-2 Delayed CB failure alarm	LD0.CCBRBRF2.Str.general
5337		333:9		Yes					

**Table 75: 86/94-1 : Master trip instance 1 (TRPPTRC1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7238		452:6	2					86/94-1 Circuit breaker lockout output (set until reset)	LD0.TRPPTRC1.ClsLO.stVal
7239		452:7		Yes					
7240		452:8	2					86/94-1 Input for resetting the circuit breaker lockout function	LD0.TRPPTRC1.LORs.stVal
7241		452:9		Yes					
7242		452:10	2					86/94-1 Trip	LD0.TRPPTRC1.Op.general
7243		452:11		Yes					
7244		452:12	2					86/94-1 General trip output signal	LD0.TRPPTRC1.Tr.general
7245		452:13		Yes					

**Table 76: 86/94-2 : Master trip instance 2 (TRPPTRC2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7246		452:14	2					86/94-2 Circuit breaker lockout output (set until reset)	LD0.TRPPTRC2.ClsLO.stVal
7248		453:0	2					86/94-2 Input for resetting the circuit breaker lockout function	LD0.TRPPTRC2.LORs.stVal
7250		453:2	2					86/94-2 Trip	LD0.TRPPTRC2.Op.general
7252		453:4	2					86/94-2 General trip output signal	LD0.TRPPTRC2.Tr.general

**Table 77: 86/94-3 : Master trip instance 3 (TRPPTRC3)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7254		453:6	2					86/94-3 Circuit breaker lockout output (set until reset)	LD0.TRPPTRC3.ClsLO.stVal

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7256		453:8	2					86/94-3 Input for resetting the circuit breaker lockout function	LD0.TRPPTRC3.LORs.stVal
7258		453:10	2					86/94-3 Trip	LD0.TRPPTRC3.Op.general
7260		453:12	0					86/94-3 General trip output signal	LD0.TRPPTRC3.Tr.general

**Table 78: AFD-1 : Arc protection instance 1 (ARCSARC11)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5606		350:6	0					AFD-1 Fault arc detected=light signal output	LD0.ARCSARC11.FADet.stVal
5608		350:8	0					AFD-1 Remote Fault arc detected	LD0.ARCSARC11.InRemFA.stVal

**Table 79: AFD-1 : Arc protection instance 1 (ARCPTRC11)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5594		349:10	0					AFD-1 Operation mode input	LD0.ARCPTRC11.InOpMod.stVal
5596		349:12	0					AFD-1 Trip	LD0.ARCPTRC11.Op.general

**Table 80: AFD-2 : Arc protection instance 2 (ARCSARC21)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5610		350:10	0					AFD-2 Fault arc detected=light signal output	LD0.ARCSARC21.FADet.stVal
5612		350:12	0					AFD-2 Remote Fault arc detected	LD0.ARCSARC21.InRemFA.stVal

**Table 81: AFD-2 Arc protection instance 2 (ARCPTRC21)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5598		349:14	0					AFD-2 Operation mode input	LD0.ARCPTRC21.InOpMod.stVal
5600		350:0	0					AFD-2 Trip	LD0.ARCPTRC21.Op.general

**Table 82: AFD-3 : Arc protection instance 3 (ARCSARC31)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5614		350:14	0					AFD-3 Fault arc detected=light signal output	LD0.ARCSARC31.FADet.stVal
5616		351:0	0					AFD-3 Remote Fault arc detected	LD0.ARCSARC31.InRemFA.stVal

**Table 83: AFD-3 : Arc protection instance 3 (ARCPTRC31)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5602		350:2	0					AFD-3 Operation mode input	LD0.ARCPTRC31.InOpMod.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5604		350:4	0					AFD-3 Trip	LD0.ARCPTRC31.Op.general

**Table 84:** HIZ : High impedance fault detection (PHIZ1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6360		397:8	0					HIZ Trip	LD0.PHIZ1.Op.general

**Table 85:** 81LSH-1 : Load shedding and restoration instance 1 (LSHDPTRC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6184		386:8	0					81LSH-1 Block restore	LD0.LSHDPTRC1.BlkRest.stVal
6186		386:10	0					81LSH-1 Manual restore signal	LD0.LSHDPTRC1.ManRest.stVal
6188		386:12	0					81LSH-1 Trip of load shedding	LD0.LSHDPTRC1.Op.general
6190		386:14	0					81LSH-1 Restore signal for load restoring purposes	LD0.LSHDPTRC1.RestLodOp.general
6192		387:0	0					81LSH-1 Restore frequency attained and restore timer started	LD0.LSHDPTRC1.RestLodStr.general
		3160	6		u16	100		81LSH-1 Pickup duration	LD0.LSHDPTRC1.StrDur.mag.f

**Table 86:** 81LSH-1 : Load shedding and restoration instance 1 (LSHDPTUF1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6264		391:8	0					81LSH-1 Trip signal for under frequency	LD0.LSHDPTUF1.Op.general

**Table 87:** 81LSH-1 : Load shedding and restoration instance 1 (LSHDPFRC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6168		385:8	0					81LSH-1 Trip signal for high df/dt	LD0.LSHDPFRC1.Op.general

**Table 88:** 81LSH-2 : Load shedding and restoration instance 2 (LSHDPTRC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6194		387:2	0					81LSH-2 Block restore	LD0.LSHDPTRC2.BlkRest.stVal
6196		387:4	0					81LSH-2 Manual restore signal	LD0.LSHDPTRC2.ManRest.stVal
6198		387:6	0					81LSH-2 Trip of load shedding	LD0.LSHDPTRC2.Op.general
6200		387:8	0					81LSH-2 Restore signal for load restoring purposes	LD0.LSHDPTRC2.RestLodOp.general
6202		387:10	0					81LSH-2 Restore frequency attained and restore timer started	LD0.LSHDPTRC2.RestLodStr.general
		3161	6		u16	100		81LSH-2 Pickup duration	LD0.LSHDPTRC2.StrDur.mag.f

**Table 89: 81LSH-2 : Load shedding and restoration instance 2 (LSHDPTUF2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6266		391:10	0					81LSH-2 Trip signal for under frequency	LD0.LSHDPTUF2.Op.general

**Table 90: 81LSH-2 : Load shedding and restoration instance 2 (LSHDPFRC2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6170		385:10	0					81LSH-2 Trip signal for high df/dt	LD0.LSHDPFRC2.Op.general

**Table 91: 52-1 : Circuit-breaker control instance 1 (CBCILO1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5104		319:0	0					52-1 Enables closing	CTRL.CBCILO1.EnaCls.stVal
5105		319:1		Yes					
5106		319:2	0					52-1 Enables opening	CTRL.CBCILO1.EnaOpn.stVal
5107		319:3		Yes					
5108		319:4	0					52-1 Discards ENA_OPEN and ENA_CLOSE interlocking when TRUE	CTRL.CBCILO1.ItlByPss.stVal
5109		319:5		Yes					

**Table 92: 52-1 : Circuit-breaker control instance 1 (CBCSWI1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5122		320:2	0					52-1 Closing is enabled based on the input status	CTRL.CBCSWI1.ClsEna.stVal
5123		320:3		Yes					
5124		320:4	0					52-1 Executes the command for close direction	CTRL.CBCSWI1.OpCls.general
5125		320:5		Yes					
5126		320:6	0					52-1 Opening is enabled based on the input status	CTRL.CBCSWI1.OpnEna.stVal
5127		320:7		Yes					
5128		320:8	0					52-1 Executes the command for open direction	CTRL.CBCSWI1.OpOpn.general
5129		320:9		Yes					
5130		320:10	0					52-1 Object selected	CTRL.CBCSWI1.Pos.stSeld
5131		320:11		Yes					
5132		320:12	0					52-1 Apparatus closed position	CTRL.CBCSWI1.PosCls.stVal
5133		320:13		Yes					
5134		320:14	0					52-1 Apparatus position is ok	CTRL.CBCSWI1.PosOk.stVal
5135		320:15		Yes					
5136		321:0	0					52-1 Apparatus open position	CTRL.CBCSWI1.PosOpn.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5137		321:1		Yes					
5184		324:0	0					52-1 Apparatus position indication - Open	CTRL.CBCSWI1.Pos.stVal
5185		324:1		Yes					
5186		324:2	0					52-1 Apparatus position indication - Close	CTRL.CBCSWI1.Pos.stVal
5187		324:3		Yes					
5188		324:4	0					52-1 Apparatus position indication - OK	CTRL.CBCSWI1.Pos.stVal
5189		324:5		Yes					

**Table 93: 52-1 : Circuit-breaker control instance 1 (CBXCBR1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5170		323:2	0					52-1 Blocks closing	CTRL.CBXCBR1.BlkCls.stVal
5171		323:3		Yes					
5172		323:4	0					52-1 Blocks opening	CTRL.CBXCBR1.BlkOpn.stVal
5173		323:5		Yes					

**Table 94: 52-2 : Circuit-breaker control instance 2 (CBCILO2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5110		319:6	0					52-2 Enables closing	CTRL.CBCILO2.EnaCls.stVal
5111		319:7		Yes					
5112		319:8	0					52-2 Enables opening	CTRL.CBCILO2.EnaOpn.stVal
5113		319:9		Yes					
5114		319:10	0					52-2 Discards ENA_OPEN and ENA_CLOSE interlocking when TRUE	CTRL.CBCILO2.ItlByPss.stVal
5115		319:11		Yes					

**Table 95: 52-2 : Circuit-breaker control instance 2 (CBCSWI2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5138		321:2	0					52-2 Closing is enabled based on the input status	CTRL.CBCSWI2.ClsEna.stVal
5139		321:3		Yes					
5140		321:4	0					52-2 Executes the command for close direction	CTRL.CBCSWI2.OpCls.general
5141		321:5		Yes					
5142		321:6	0					52-2 Opening is enabled based on the input status	CTRL.CBCSWI2.OpnEna.stVal
5143		321:7		Yes					
5144		321:8	0					52-2 Executes the command for open direction	CTRL.CBCSWI2.OpOpn.general
5145		321:9		Yes					
5146		321:10	0					52-2 Object selected	CTRL.CBCSWI2.Pos.stSeld

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5147		321:11		Yes					
5148		321:12	0					52-2 Apparatus closed position	CTRL.CBCSWI2.PosCls.stVal
5149		321:13		Yes					
5150		321:14	0					52-2 Apparatus position is ok	CTRL.CBCSWI2.PosOk.stVal
5151		321:15		Yes					
5152		322:0	0					52-2 Apparatus open position	CTRL.CBCSWI2.PosOprn.stVal
5153		322:1		Yes					
5190		324:6	0					52-2 Apparatus position indication- Open	CTRL.CBCSWI2.Pos.stVal
5191		324:7		Yes					

Table 96: 52-2 : Circuit-breaker control instance 2 (CBXCBR2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5174		323:6	0					52-2 Blocks closing	CTRL.CBXCBR2.BlkCls.stVal
5175		323:7		Yes					
5176		323:8	0					52-2 Blocks opening	CTRL.CBXCBR2.BlkOprn.stVal
5177		323:9		Yes					

Table 97: 79-1 : Auto-reclosing instance 1 (DARREC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5706		356:10	0					79-1 Autoreclosing allowed	LD0.DARREC1.AROn.stVal
5708		356:12	0					79-1 Blocks and resets reclaim time	LD0.DARREC1.InBlkRclTm.stVal
5710		356:14	0					79-1 Blocks and resets reclose time	LD0.DARREC1.InBlkRecTm.stVal
5712		357:0	0					79-1 Blocks and holds the reclose shot from the thermal overload	LD0.DARREC1.InBlkThm.stVal
5714		357:2	0					79-1 Circuit breaker position input	LD0.DARREC1.InCBPos.stVal
5716		357:4	0					79-1 Circuit breaker status signal	LD0.DARREC1.InCBRdy.stVal
5718		357:6	0					79-1 Delayed AR initialization / blocking signal 2	LD0.DARREC1.InDIIni2.stVal
5720		357:8	0					79-1 Delayed AR initialization / blocking signal 3	LD0.DARREC1.InDIIni3.stVal
5722		357:10	0					79-1 Delayed AR initialization / blocking signal 4	LD0.DARREC1.InDIIni4.stVal
5724		357:12	0					79-1 A zone sequence coordination signal	LD0.DARREC1.InIncrPntr.stVal
5726		357:14	0					79-1 Interrupts and inhibits reclosing sequence	LD0.DARREC1.InInhRec.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5728		358:0	0					79-1 AR initialization / blocking signal 1	LD0.DARREC1.InIni1.stVal
5730		358:2	0					79-1 AR initialization / blocking signal 2	LD0.DARREC1.InIni2.stVal
5732		358:4	0					79-1 AR initialization / blocking signal 3	LD0.DARREC1.InIni3.stVal
5734		358:6	0					79-1 AR initialization / blocking signal 4	LD0.DARREC1.InIni4.stVal
5736		358:8	0					79-1 AR initialization / blocking signal 5	LD0.DARREC1.InIni5.stVal
5738		358:10	0					79-1 AR initialization / blocking signal 6	LD0.DARREC1.InIni6.stVal
5740		358:12	0					79-1 Level sensitive signal for allowing (high) / not allowing (low) reclosing	LD0.DARREC1.InReClsOn.stVal
5742		358:14	0					79-1 Synchronizing check fulfilled	LD0.DARREC1.InSynChk.stVal
5744		359:0	0					79-1 Signal indicating that AR is locked out	LD0.DARREC1.LO.stVal
5746		359:2	0					79-1 Close (reclose) command for circuit breaker	LD0.DARREC1.Op.general
5748		359:4	0					79-1 Open command for circuit breaker	LD0.DARREC1.OpOpn.general
5750		359:6	0					79-1 Reclosing shot in progress activated during dead time	LD0.DARREC1.PrgRec.stVal
5752		359:8	0					79-1 A signal for coordination between the AR and the protection	LD0.DARREC1.ProCrd.stVal
5754		359:10	0					79-1 Indicates that the AR is ready for a new sequence	LD0.DARREC1.RdyRec.stVal
5756		359:12	0					79-1 Indicates an unsuccessful reclosing sequence	LD0.DARREC1.UnsRec.stVal
5758		359:14	0					79-1 Wait for master command	LD0.DARREC1.WtMstr.stVal
		3046	4		s16			79-1 AR status signal for IEC61850	LD0.DARREC1.AutoRecSt.stVal
		3047	4		s16			79-1 Frequent operation counter	LD0.DARREC1.FrqOpCnt.stVal
		3049	4		s16			79-1 Resetable operation counter shot 1	LD0.DARREC1.OpCnt1.stVal
		3051	4		s16			79-1 Resetable operation counter shot 2	LD0.DARREC1.OpCnt2.stVal
		3053	4		s16			79-1 Resetable operation counter shot 3	LD0.DARREC1.OpCnt3.stVal
		3055	4		s16			79-1 Resetable operation counter shot 4	LD0.DARREC1.OpCnt4.stVal
		3057	4		s16			79-1 Resetable operation counter shot 5	LD0.DARREC1.OpCnt5.stVal



Table 98: 79-2 : Auto-reclosing instance 2 (DARREC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5760		360:0	0					79-2 Autoreclosing allowed	LD0.DARREC2.AROn.stVal
5762		360:2	0					79-2 Blocks and resets reclaim time	LD0.DARREC2.InBlkRclTm.stVal
5764		360:4	0					79-2 Blocks and resets reclose time	LD0.DARREC2.InBlkRecTm.stVal
5766		360:6	0					79-2 Blocks and holds the reclose shot from the thermal overload	LD0.DARREC2.InBlkThm.stVal
5768		360:8	0					79-2 Circuit breaker position input	LD0.DARREC2.InCBPos.stVal
5770		360:10	0					79-2 Circuit breaker status signal	LD0.DARREC2.InCBRdy.stVal
5772		360:12	0					79-2 Delayed AR initialization / blocking signal 2	LD0.DARREC2.InDIIni2.stVal
5774		360:14	0					79-2 Delayed AR initialization / blocking signal 3	LD0.DARREC2.InDIIni3.stVal
5776		361:0	0					79-2 Delayed AR initialization / blocking signal 4	LD0.DARREC2.InDIIni4.stVal
5778		361:2	0					79-2 A zone sequence coordination signal	LD0.DARREC2.InIncrPntr.stVal
5780		361:4	0					79-2 Interrupts and inhibits reclosing sequence	LD0.DARREC2.InInhRec.stVal
5782		361:6	0					79-2 AR initialization / blocking signal 1	LD0.DARREC2.InIni1.stVal
5784		361:8	0					79-2 AR initialization / blocking signal 2	LD0.DARREC2.InIni2.stVal
5786		361:10	0					79-2 AR initialization / blocking signal 3	LD0.DARREC2.InIni3.stVal
5788		361:12	0					79-2 AR initialization / blocking signal 4	LD0.DARREC2.InIni4.stVal
5790		361:14	0					79-2 AR initialization / blocking signal 5	LD0.DARREC2.InIni5.stVal
5792		362:0	0					79-2 AR initialization / blocking signal 6	LD0.DARREC2.InIni6.stVal
5794		362:2	0					79-2 Level sensitive signal for allowing (high) / not allowing (low) reclosing	LD0.DARREC2.InReClsOn.stVal
5796		362:4	0					79-2 Synchronizing check fulfilled	LD0.DARREC2.InSynChk.stVal
5798		362:6	0					79-2 Signal indicating that AR is locked out	LD0.DARREC2.LO.stVal
5800		362:8	0					79-2 Close (reclose) command for circuit breaker	LD0.DARREC2.Op.general
5802		362:10	0					79-2 Open command for circuit breaker	LD0.DARREC2.OpOpn.general
5804		362:12	0					79-2 Reclosing shot in progress activated during dead time	LD0.DARREC2.PrgRec.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5806		362:14	0					79-2 A signal for coordination between the AR and the protection	LD0.DARREC2.ProCrd.stVal
5808		363:0	0					79-2 Indicates that the AR is ready for a new sequence	LD0.DARREC2.RdyRec.stVal
5810		363:2	0					79-2 Indicates an unsuccessful reclosing sequence	LD0.DARREC2.UnsRec.stVal
5812		363:4	0					79-2 Wait for master command	LD0.DARREC2.WtMstr.stVal
		3059	4		s16			79-2 AR status signal for IEC61850	LD0.DARREC2.AutoRecSt.stVal
		3060	0		s16			79-2 Frequent operation counter	LD0.DARREC2.FrqOpCnt.stVal
		3062	6		s16			79-2 Resetable operation counter shot 1	LD0.DARREC2.OpCnt1.stVal
		3064	6		s16			79-2 Resetable operation counter shot 2	LD0.DARREC2.OpCnt2.stVal
		3066	6		s16			79-2 Resetable operation counter shot 3	LD0.DARREC2.OpCnt3.stVal
		3068	6		s16			79-2 Resetable operation counter shot 4	LD0.DARREC2.OpCnt4.stVal
		3070	6		s16			79-2 Resetable operation counter shot 5	LD0.DARREC2.OpCnt5.stVal

**Table 99: 25-1 : Synchronism and energizing check instance 1 (SECRSYN1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6416		401:0	0					25-1 Phase angle difference out of limit for synchronizing	LD0.SECRSYN1.AngInd.stVal
6418		401:2	0					25-1 Request to bypass synchronism check and voltage check	LD0.SECRSYN1.ByPss.stVal
6420		401:4	0					25-1 Dead Line Dead Bus	LD0.SECRSYN1.DLDBInd.stVal
6422		401:6	0					25-1 Dead Line Live Bus	LD0.SECRSYN1.DLLBInd.stVal
6424		401:8	0					25-1 CB closing request failed	LD0.SECRSYN1.FailCmd.stVal
6426		401:10	0					25-1 CB closing failed	LD0.SECRSYN1.FailSyn.stVal
6428		401:12	0					25-1 Frequency difference out of limit for synchronizing	LD0.SECRSYN1.HzInd.stVal
6430		401:14	0					25-1 Live Line Dead Bus	LD0.SECRSYN1.LLDBInd.stVal
6432		402:0	0					25-1 Live Line Live Bus	LD0.SECRSYN1.LLLBInd.stVal
6434		402:2	0					25-1 Systems in synchronism	LD0.SECRSYN1.Rel.stVal
6436		402:4	0					25-1 Synchronizing in progress	LD0.SECRSYN1.SynPrg.stVal
6438		402:6	0					25-1 Voltage difference out of limit for synchronizing	LD0.SECRSYN1.VInd.stVal
		2940	6		u16	100		25-1 Calculated voltage phase angle difference	LD0.SECRSYN1.DifAngClc.mag.f
		2941	6		u16	100		25-1 Calculated voltage frequency difference	LD0.SECRSYN1.DifHzClc.mag.f

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2942	6		u16	100		25-1 Calculated voltage amplitude difference	LD0.SECRSYN1.DifVClc.mag.f

Table 100: 25-2 : Synchronism and energizing check instance 2 (SECRSYN2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6440		402:8	0					25-2 Phase angle difference out of limit for synchronizing	LD0.SECRSYN2.AngInd.stVal
6442		402:10	0					25-2 Request to bypass synchronism check and voltage check	LD0.SECRSYN2.ByPss.stVal
6444		402:12	0					25-2 Dead Line Dead Bus	LD0.SECRSYN2.DLDBInd.stVal
6446		402:14	0					25-2 Dead Line Live Bus	LD0.SECRSYN2.DLLBInd.stVal
6448		403:0	0					25-2 CB closing request failed	LD0.SECRSYN2.FailCmd.stVal
6450		403:2	0					25-2 CB closing failed	LD0.SECRSYN2.FailSyn.stVal
6452		403:4	0					25-2 Frequency difference out of limit for synchronizing	LD0.SECRSYN2.HzInd.stVal
6454		403:6	0					25-2 Live Line Dead Bus	LD0.SECRSYN2.LLDBInd.stVal
6456		403:8	0					25-2 Live Line Live Bus	LD0.SECRSYN2.LLLBInd.stVal
6458		403:10	0					25-2 Systems in synchronism	LD0.SECRSYN2.Rel.stVal
6460		403:12	0					25-2 Synchronizing in progress	LD0.SECRSYN2.SynPrg.stVal
6462		403:14	0					25-2 Voltage difference out of limit for synchronizing	LD0.SECRSYN2.VInd.stVal
		2943	0		u16	100		25-2 Calculated voltage phase angle difference	LD0.SECRSYN2.DifAngClc.mag.f
		2944	0		u16	100		25-2 Calculated voltage frequency difference	LD0.SECRSYN2.DifHzClc.mag.f
		2945	0		u16	100		25-2 Calculated voltage amplitude difference	LD0.SECRSYN2.DifVClc.mag.f

Table 101: 25-3 : Synchronism and energizing check instance 3 (SECRSYN3)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6464		404:0	0					25-3 Phase angle difference out of limit for synchronizing	LD0.SECRSYN3.AngInd.stVal
6466		404:2	0					25-3 Request to bypass synchronism check and voltage check	LD0.SECRSYN3.ByPss.stVal
6468		404:4	0					25-3 Dead Line Dead Bus	LD0.SECRSYN3.DLDBInd.stVal
6470		404:6	0					25-3 Dead Line Live Bus	LD0.SECRSYN3.DLLBInd.stVal
6472		404:8	0					25-3 CB closing request failed	LD0.SECRSYN3.FailCmd.stVal
6474		404:10	0					25-3 CB closing failed	LD0.SECRSYN3.FailSyn.stVal
6476		404:12	0					25-3 Frequency difference out of limit for synchronizing	LD0.SECRSYN3.HzInd.stVal
6478		404:14	0					25-3 Live Line Dead Bus	LD0.SECRSYN3.LLDBInd.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6480		405:0	0					25-3 Live Line Live Bus	LD0.SECRSYN3.LLLBInd.stVal
6482		405:2	0					25-3 Systems in synchronism	LD0.SECRSYN3.Rel.stVal
6484		405:4	0					25-3 Synchronizing in progress	LD0.SECRSYN3.SynPrg.stVal
6486		405:6	0					25-3 Voltage difference out of limit for synchronizing	LD0.SECRSYN3.VInd.stVal
		2946	0		u16	100		25-3 Calculated voltage phase angle difference	LD0.SECRSYN3.DifAngClc.mag.f
		2947	0		u16	100		25-3 Calculated voltage frequency difference	LD0.SECRSYN3.DifHzClc.mag.f
		2948	0		u16	100		25-3 Calculated voltage amplitude difference	LD0.SECRSYN3.DifVClc.mag.f

**Table 102: 52CM-1 : Circuit-breaker condition monitoring instance 1 (SSCBR1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5202		325:2	0					52CM-1 Accumulated currents power (lyt) exceeded alarm limit	LD0.SSCBR1.APwrAlm.stVal
5203		325:3		Yes					
5204		325:4	0					52CM-1 Accumulated currents power (lyt) exceeded lockout limit	LD0.SSCBR1.APwrLO.stVal
5205		325:5		Yes					
5206		325:6	0					52CM-1 Remaining life of CB exceeded alarm limit	LD0.SSCBR1.CBLifAlm.stVal
5207		325:7		Yes					
5208		325:8	0					52CM-1 CB close travel time exceeded set value	LD0.SSCBR1.ClsAlm.stVal
5209		325:9		Yes					
5210		325:10	0					52CM-1 Signal for closeposition of apparatus from I/O	LD0.SSCBR1.InPosCls.stVal
5211		325:11		Yes					
5212		325:12	0					52CM-1 Signal for open position of apparatus from I/O	LD0.SSCBR1.InPosOpn.stVal
5213		325:13		Yes					
5214		325:14	0					52CM-1 Binary pressure alarm input	LD0.SSCBR1.InPresAlm.stVal
5215		325:15		Yes					
5216		326:0	0					52CM-1 Binary pressure input for lockout indication	LD0.SSCBR1.InPresLO.stVal
5217		326:1		Yes					
5218		326:2	0					52CM-1 CB spring charged input	LD0.SSCBR1.InSprCha.stVal
5219		326:3		Yes					

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5220		326:4	0					52CM-1 CB spring charging started input	LD0.SSCBR1.InSprChStr.stVal
5221		326:5		Yes					
5222		326:6	0					52CM-1 CB 'not tripped for long time' alarm	LD0.SSCBR1.LonTmAlm.stVal
5223		326:7		Yes					
5224		326:8	0					52CM-1 CB open travel time exceeded set value	LD0.SSCBR1.OpnAlm.stVal
5225		326:9		Yes					
5226		326:10	0					52CM-1 Number of CB operations exceeds alarm limit	LD0.SSCBR1.OpNumAlm.stVal
5227		326:11		Yes					
5228		326:12	0					52CM-1 Number of CB operations exceeds lockout limit	LD0.SSCBR1.OpNumLO.stVal
5229		326:13		Yes					
5230		326:14	0					52CM-1 CB is in closed position	LD0.SSCBR1.PosCls.stVal
5231		326:15		Yes					
5232		327:0	0					52CM-1 CB is in invalid position (not positively open or closed)	LD0.SSCBR1.Poslvd.stVal
5233		327:1		Yes					
5234		327:2	0					52CM-1 CB is in open position	LD0.SSCBR1.PosOpn.stVal
5235		327:3		Yes					
5236		327:4	0					52CM-1 Pressure below alarm level	LD0.SSCBR1.PresAlm.stVal
5237		327:5		Yes					
5238		327:6	0					52CM-1 Pressure below lockout level	LD0.SSCBR1.PresLO.stVal
5239		327:7		Yes					
5240		327:8	0					52CM-1 Reset accumulation energy	LD0.SSCBR1.RsAccAPwr.stVal
5241		327:9		Yes					
5242		327:10	0					52CM-1 Reset input for CB remaining life and operation counter	LD0.SSCBR1.RsCBWear.stVal
5243		327:11		Yes					
5244		327:12	0					52CM-1 Reset input for the charging time of the CB spring	LD0.SSCBR1.RsSprChaTm.stVal
5245		327:13		Yes					
5246		327:14	0					52CM-1 Reset input for CB closing and opening travel times	LD0.SSCBR1.RsTrvTm.stVal
5247		327:15		Yes					

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5248		328:0	0					52CM-1 Spring charging time has crossed the set value	LD0.SSCBR1.SprChaAlm.stVal
5249		328:1		Yes					
		2949	5		s32	100		52CM-1 Accumulated currents power (I <sub>yt</sub> ) phase A	LD0.SSCBR1.AccAPwrPhA.mag.f
		2950	5						
		2951	5		s32	100		52CM-1 Accumulated currents power (I <sub>yt</sub> ) phase B	LD0.SSCBR1.AccAPwrPhB.mag.f
		2952	5						
		2953	5		s32	100		52CM-1 Accumulated currents power (I <sub>yt</sub> ) phase C	LD0.SSCBR1.AccAPwrPhC.mag.f
		2954	5						
		2955	4		s16			52CM-1 The number of days CB has been inactive	LD0.SSCBR1.InaTmdCnt.stVal
		2956	0		s16			52CM-1 CB Remaining life phase A	LD0.SSCBR1.RmnLifPhA.stVal
		2957	0		s16			52CM-1 CB Remaining life phase B	LD0.SSCBR1.RmnLifPhB.stVal
		2958	0		s16			52CM-1 CB Remaining life phase C	LD0.SSCBR1.RmnLifPhC.stVal
		2959	6		u16	100		52CM-1 Travel time of the CB during closing operation	LD0.SSCBR1.TmmsCls.mag.f
		2960	6		u16	100		52CM-1 Travel time of the CB during opening operation	LD0.SSCBR1.TmmsOpn.mag.f
		2961	6		u16	100		52CM-1 The charging time of the CB spring	LD0.SSCBR1.TmsSprCha.mag.f

**Table 103: 52CM-2 : Circuit-breaker condition monitoring instance 2 (SSCBR2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5250		328:2	0					52CM-2 Accumulated currents power (I <sub>yt</sub> ) exceeded alarm limit	LD0.SSCBR2.APwrAlm.stVal
5251		328:3		Yes					
5252		328:4	0					52CM-2 Accumulated currents power (I <sub>yt</sub> ) exceeded lockout limit	LD0.SSCBR2.APwrLO.stVal
5253		328:5		Yes					
5254		328:6	0					52CM-2 Remaining life of CB exceeded alarm limit	LD0.SSCBR2.CBLifAlm.stVal
5255		328:7		Yes					
5256		328:8	0					52CM-2 CB close travel time exceeded set value	LD0.SSCBR2.ClsAlm.stVal
5257		328:9		Yes					
5258		328:10	0					52CM-2 Signal for close position of apparatus from I/O	LD0.SSCBR2.InPosCls.stVal
5259		328:11		Yes					

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5260		328:12	0					52CM-2 Signal for open position of apparatus from I/O	LD0.SSCBR2.InPosOprn.stVal
5261		328:13		Yes					
5262		328:14	0					52CM-2 Binary pressure alarm input	LD0.SSCBR2.InPresAlm.stVal
5263		328:15		Yes					
5264		329:0	0					52CM-2 Binary pressure input for lockout indication	LD0.SSCBR2.InPresLO.stVal
5265		329:1		Yes					
5266		329:2	0					52CM-2 CB spring charged input	LD0.SSCBR2.InSprCha.stVal
5267		329:3		Yes					
5268		329:4	0					52CM-2 CB spring charging started input	LD0.SSCBR2.InSprChStr.stVal
5269		329:5		Yes					
5270		329:6	0					52CM-2 CB 'not tripped for long time' alarm	LD0.SSCBR2.LonTmAlm.stVal
5271		329:7		Yes					
5272		329:8	0					52CM-2 CB open travel time exceeded set value	LD0.SSCBR2.OprnAlm.stVal
5273		329:9		Yes					
5274		329:10	0					52CM-2 Number of CB operations exceeds alarm limit	LD0.SSCBR2.OpNumAlm.stVal
5275		329:11		Yes					
5276		329:12	0					52CM-2 Number of CB operations exceeds lockout limit	LD0.SSCBR2.OpNumLO.stVal
5277		329:13		Yes					
5278		329:14	0					52CM-2 CB is in closed position	LD0.SSCBR2.PosCls.stVal
5279		329:15		Yes					
5280		330:0	0					52CM-2 CB is in invalid position (not positively open or closed)	LD0.SSCBR2.Poslvd.stVal
5281		330:1		Yes					
5282		330:2	0					52CM-2 CB is in open position	LD0.SSCBR2.PosOprn.stVal
5283		330:3		Yes					
5284		330:4	0					52CM-2 Pressure below alarm level	LD0.SSCBR2.PresAlm.stVal
5285		330:5		Yes					
5286		330:6	0					52CM-2 Pressure below lockout level	LD0.SSCBR2.PresLO.stVal
5287		330:7		Yes					
5288		330:8	0					52CM-2 Reset accumulation energy	LD0.SSCBR2.RsAccAPwr.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5289		330:9		Yes					
5290		330:10	0					52CM-2 Reset input for CB remaining life and operation counter	LD0.SSCBR2.RsCBWear.stVal
5291		330:11		Yes					
5292		330:12	0					52CM-2 Reset input for the charging time of the CB spring	LD0.SSCBR2.RsSprChaTm.stVal
5293		330:13		Yes					
5294		330:14	0					52CM-2 Reset input for CB closing and opening travel times	LD0.SSCBR2.RsTrvTm.stVal
5295		330:15		Yes					
5296		331:0	0					52CM-2 Spring charging time has crossed the set value	LD0.SSCBR2.SprChaAlm.stVal
5297		331:1		Yes					
		2962	6		s32	100		52CM-2 Accumulated currents power (lyt) phase A	LD0.SSCBR2.AccAPwrPhA.mag.f
		2963	6						
		2964	6		s32	100		52CM-2 Accumulated currents power (lyt) phase B	LD0.SSCBR2.AccAPwrPhB.mag.f
		2965	6						
		2966	6		s32	100		52CM-2 Accumulated currents power (lyt) phase C	LD0.SSCBR2.AccAPwrPhC.mag.f
		2967	6						
		2968	6		s16			52CM-2 CB Remaining life phase A	LD0.SSCBR2.RmnLifPhA.stVal
		2969	6		s16			52CM-2 CB Remaining life phase B	LD0.SSCBR2.RmnLifPhB.stVal
		2970	6		s16			52CM-2 CB Remaining life phase C	LD0.SSCBR2.RmnLifPhC.stVal
		2971	6		u16	100		52CM-2 Travel time of the CB during closing operation	LD0.SSCBR2.TmmsCls.mag.f
		2972	6		u16	100		52CM-2 Travel time of the CB during opening operation	LD0.SSCBR2.TmmsOpn.mag.f
		2973	6		u16	100		52CM-2 The charging time of the CB spring	LD0.SSCBR2.TmsSprCha.mag.f

**Table 104: TCM-1 : Trip circuit supervision instance 1 (TCSSCBR1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5586		349:2	0					TCM-1 Alarm output	LD0.TCSSCBR1.CirAlm.stVal

**Table 105: TCM-2 : Trip circuit supervision instance 2 (TCSSCBR2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5588		349:4	0					TCM-2 Alarm output	LD0.TCSSCBR2.CirAlm.stVal



**Table 106: CCM : Current circuit supervision (CCRDIF1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5618		351:2	0					CCM Alarm output	LD0.CCRDIF1.Alm.stVal
5620		351:4	0					CCM Fail output	LD0.CCRDIF1.Op.general

**Table 107: 60-1 : Fuse failure supervision instance 1 (SEQRFUF1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6488		405:8	0					60-1 General pickup of function	LD0.SEQRFUF1.Str.general
6490		405:10	0					60-1 Three-phase pickup of function	LD0.SEQRFUF1.Str3Ph.general

**Table 108: 60-2 : Fuse failure supervision instance 2 (SEQRFUF2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6492		405:12	0					60-2 General pickup of function	LD0.SEQRFUF2.Str.general
6494		405:14	0					60-2 Three-phase pickup of function	LD0.SEQRFUF2.Str3Ph.general

**Table 109: CFD : Cable fault detection (RCFD1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6408		400:8	0					CFD Trip	LD0.RCFD1.Op.general
6410		400:10	0					CFD Trip phsA	LD0.RCFD1.Op.phsA
6412		400:12	0					CFD Trip phsB	LD0.RCFD1.Op.phsB
6414		400:14	0					CFD Trip phsC	LD0.RCFD1.Op.phsC

**Table 110: IA IB IC : Three-phase current measurement instance 1 (CMMXU1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5624		351:8	0					IA IB IC High alarm	LD0.CMMXU1.HiAlm.stVal
5626		351:10	0					IA IB IC High warning	LD0.CMMXU1.HiWrn.stVal
5628		351:12	0					IA IB IC Low alarm	LD0.CMMXU1.LoAlm.stVal
5630		351:14	0					IA IB IC Low warning	LD0.CMMXU1.LoWrn.stVal
		2000	6		s32	100		IA IB IC IA Amplitude magnitude of instantaneous value	LD0.CMMXU1.A.phsA.instCVal.mag.f
		2001	6						
		2002	6		s32	100		IA IB IC IB Amplitude magnitude of instantaneous value	LD0.CMMXU1.A.phsB.instCVal.mag.f
		2003	6						
		2004	6		s32	100		IA IB IC IC Amplitude magnitude of instantaneous value	LD0.CMMXU1.A.phsC.instCVal.mag.f
		2005	6						

**Table 111: IA IB IC : Three-phase current measurement instance 1 (CMSTA1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2018	5		s32	100		IA IB IC Demand value of IA current	LD0.CMSTA1.AvAmpsA.mag.f
		2019	5						
		2020	5		s32	100		IA IB IC Demand value of IB current	LD0.CMSTA1.AvAmpsB.mag.f
		2021	5						
		2022	5		s32	100		IA IB IC Demand value of IC current	LD0.CMSTA1.AvAmpsC.mag.f
		2023	5						
		2024	5		s32	100		IA IB IC Maximum demand for Phase A	LD0.CMSTA1.MaxAmpsA.mag.f
		2025	5						
		2026	5		s32	100		IA IB IC Maximum demand for Phase B	LD0.CMSTA1.MaxAmpsB.mag.f
		2027	5						
		2028	5		s32	100		IA IB IC Maximum demand for Phase C	LD0.CMSTA1.MaxAmpsC.mag.f
		2029	5						

**Table 112: I1 I2 I0 : Sequence current measurement instance 1 (CSMSQI1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2054	6		s32	100		I1 I2 I0 Positive sequence current amplitude instantaneous value	LD0.CSMSQI1.SeqA.c1.instCVal.mag.f
		2055	6						
		2056	6		s32	100		I1 I2 I0 Negative sequence current amplitude instantaneous value	LD0.CSMSQI1.SeqA.c2.instCVal.mag.f
		2057	6						
		2058	6		s32	100		I1 I2 I0 Zero sequence current amplitude instantaneous value	LD0.CSMSQI1.SeqA.c3.instCVal.mag.f
		2059	6						

**Table 113: IG : Residual current measurement instance 1 (RESCMMXU1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5648		353:0	0					IG High alarm	LD0.RESCMMXU1.HiAlm.stVal
5650		353:2	0					IG High warning	LD0.RESCMMXU1.HiWrn.stVal
		2072	6		s32	100		IG Ground current Amplitude magnitude of instantaneous value	LD0.RESCMMXU1.A.res.instCVal.mag.f
		2073							

Table 114: VA VB VC : Three-phase voltage measurement instance 1 (VMMXU1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5656		353:8	0					VA VB VC High alarm	LD0.VMMXU1.HiAlm.stVal
5658		353:10	0					VA VB VC High warning	LD0.VMMXU1.HiWrn.stVal
5660		353:12	0					VA VB VC Low alarm	LD0.VMMXU1.LoAlm.stVal
5662		353:14	0					VA VB VC Low warning	LD0.VMMXU1.LoWrn.stVal
		2244	6		u16	100		VA VB VC VA Amplitude magnitude of instantaneous value	LD0.VMMXU1.PhV.phsA.cVal.mag.f
		2245	6		u16	100		VA VB VC VB Amplitude magnitude of instantaneous value	LD0.VMMXU1.PhV.phsB.cVal.mag.f
		2246	6		u16	100		VA VB VC VC Amplitude magnitude of instantaneous value	LD0.VMMXU1.PhV.phsC.cVal.mag.f
		2247	6		u16	100		VA VB VC VAB Amplitude magnitude of instantaneous value	LD0.VMMXU1.PPV.phsAB.instCVal.mag.f
		2248	6		u16	100		VA VB VC VBC Amplitude magnitude of instantaneous value	LD0.VMMXU1.PPV.phsBC.instCVal.mag.f
		2249	6		u16	100		VA VB VC VCA Amplitude magnitude of instantaneous value	LD0.VMMXU1.PPV.phsCA.instCVal.mag.f

Table 115: VA VB VC (2) : Three-phase voltage measurement instance 2 (VMMXU2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5664		354:0	0					VA VB VC(2) High alarm	LD0.VMMXU2.HiAlm.stVal
5666		354:2	0					VA VB VC(2) High warning	LD0.VMMXU2.HiWrn.stVal
5668		354:4	0					VA VB VC(2) Low alarm	LD0.VMMXU2.LoAlm.stVal
5670		354:6	0					VA VB VC(2) Low warning	LD0.VMMXU2.LoWrn.stVal
		2250	6		u16	100		VA VB VC(2) VA Amplitude magnitude of instantaneous value	LD0.VMMXU2.PhV.phsA.cVal.mag.f
		2251	6		u16	100		VA VB VC(2) VB Amplitude magnitude of instantaneous value	LD0.VMMXU2.PhV.phsB.cVal.mag.f

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2252	6		u16	100		VA VB VC(2) VC Amplitude magnitude of instantaneous value	LD0.VMMXU2.PhV.phsC.cVal.mag.f
		2253	6		u16	100		VA VB VC(2) VAB Amplitude magnitude of instantaneous value	LD0.VMMXU2.PPV.phsAB.instCVal.mag.f
		2254	6		u16	100		VA VB VC(2) VBC Amplitude magnitude of instantaneous value	LD0.VMMXU2.PPV.phsBC.instCVal.mag.f
		2255	6		u16	100		VA VB VC(2) VCA Amplitude magnitude of instantaneous value	LD0.VMMXU2.PPV.phsCA.instCVal.mag.f

**Table 116: VG : Residual voltage measurement instance 1 (RESVMMXU1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5672		354:8	0					VG High alarm	LD0.RESVMMXU1.HiAlm.stVal
5674		354:10	0					VG High warning	LD0.RESVMMXU1.HiWrn.stVal
		2240	6		s32	100		VG Ground voltage Amplitude magnitude of instantaneous value	LD0.RESVMMXU1.PhV.res.instCVal.mag.f
		2241							

**Table 117: V1 V2 V0 : Sequence voltage measurement instance 1 (VSMSQI1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2256	6		u16	100		V1 V2 V0 Positive sequence voltage amplitude instantaneous value	LD0.VSMSQI1.SeqV.c1.instCVal.mag.f
		2257	6		u16	100		V1 V2 V0 Negative sequence voltage amplitude instantaneous value	LD0.VSMSQI1.SeqV.c2.instCVal.mag.f
		2258	6		u16	100		V1 V2 V0 Zero sequence voltage amplitude instantaneous value	LD0.VSMSQI1.SeqV.c3.instCVal.mag.f

**Table 118: V1 V2 V0 (2) : Sequence voltage measurement instance 2 (VSMSQI2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2259	6		u16	100		V1 V2 V0(2) Positive sequence voltage amplitude instantaneous value	LD0.VSMSQI2.SeqV.c1.instCVal.mag.f
		2260	6		u16	100		V1 V2 V0(2) Negative sequence voltage amplitude instantaneous value	LD0.VSMSQI2.SeqV.c2.instCVal.mag.f

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2261	6		u16	100		V1 V2 V0(2) Zero sequence voltage amplitude instantaneous value	LD0.VSMSQI2.SeqV.c3.instCVal.mag.f

Table 119: P E : Three-phase power and energy measurement instance 1 (PEMMXU1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2388	6		s16	100		P E Average Power factor	LD0.PEMMXU1.TotPF.instMag.f
		2389	6		s32	100		P E Total Apparent Power	LD0.PEMMXU1.TotVA.instMag.f
		2390	6						
		2391	6		s32	100		P E Total Reactive Power	LD0.PEMMXU1.TotVAr.instMag.f
		2392	6						
		2393	6		s32	100		P E Active power magnitude of instantaneous value	LD0.PEMMXU1.TotW.instMag.f
		2394	6						

Table 120: P E : Three-phase power and energy measurement instance 1 (PEMMTR1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6328		395:8	0					P E Reset of accumulated energy reading	LD0.PEMMTR1.SupDmdRs.stVal
		2380	6		u32			P E Accumulated forward reactive energy value	LD0.PEMMTR1.DmdVArh.actVal
		2381	6						
		2382	6		u32			P E Accumulated forward active energy value	LD0.PEMMTR1.DmdWh.actVal
		2383	6						
		2384	6		u32			P E Accumulated reverse reactive energy value	LD0.PEMMTR1.SupVArh.actVal
		2385	6						
		2386	6		u32			P E Accumulated reverse active energy value	LD0.PEMMTR1.SupWh.actVal
		2387	6						

Table 121: PQI-1 : Current total demand distortion instance 1 (CMHAI1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5622		351:6	0					PQI-1 Alarm signal for TDD	LD0.CMHAI1.Alm.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2173	0		s32	100		PQI-1 Demand value for TDD for phase A	LD0.CMHA11.DmdTddA.phsA.cVal.mag.f
		2174	0						
		2175	0		s32	100		PQI-1 Demand value for TDD for phase B	LD0.CMHA11.DmdTddA.phsB.cVal.mag.f
		2176	0						
		2177	0		s32	100		PQI-1 Demand value for TDD for phase C	LD0.CMHA11.DmdTddA.phsC.cVal.mag.f
		2178	0						
		2179	0		s32	100		PQI-1 Maximum demand TDD for phase A	LD0.CMHA11.MaxDmdTddA.phsA.cVal.mag.f
		2180	0						
		2181	0		s32	100		PQI-1 Maximum demand TDD for phase B	LD0.CMHA11.MaxDmdTddA.phsB.cVal.mag.f
		2182	0						
		2183	0		s32	100		PQI-1 Maximum demand TDD for phase C	LD0.CMHA11.MaxDmdTddA.phsC.cVal.mag.f
		2184	0						
		2185	0		s32	100		PQI-1 3 second mean value of TDD for phase A	LD0.CMHA11.TddA.phsA.cVal.mag.f
		2186	0						
		2187	0		s32	100		PQI-1 3 second mean value of TDD for phase B	LD0.CMHA11.TddA.phsB.cVal.mag.f
		2188	0						
		2189	0		s32	100		PQI-1 3 second mean value of TDD for phase C	LD0.CMHA11.TddA.phsC.cVal.mag.f
		2190	0						

Table 122: PQVPH-1 : Voltage total harmonic distortion instance 1 (VMHA11)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5652		353:4	0					PQVPH-1 Alarm signal for THD	LD0.VMHA11.Alm.stVal
		2311	0		u16	100		PQVPH-1 Demand value for THD for phase A	LD0.VMHA11.DmdThdPhV.phsA.cVal.mag.f
		2312	0		u16	100		PQVPH-1 Demand value for THD for phase B	LD0.VMHA11.DmdThdPhV.phsB.cVal.mag.f

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2313	0		u16	100		PQVPH-1 Demand value for THD for phase C	LD0.VMHA11.DmdThdPhV.phsC.cVal.mag.f
		2314	0		u16	100		PQVPH-1 Maximum demand THD for phase A	LD0.VMHA11.MaxDmdThdV.phsA.cVal.mag.f
		2315	0		u16	100		PQVPH-1 Maximum demand THD for phase B	LD0.VMHA11.MaxDmdThdV.phsB.cVal.mag.f
		2316	0		u16	100		PQVPH-1 Maximum demand THD for phase C	LD0.VMHA11.MaxDmdThdV.phsC.cVal.mag.f
		2317	0		u16	100		PQVPH-1 3 second mean value of THD for phase A	LD0.VMHA11.ThdPhV.phsA.cVal.mag.f
		2318	0		u16	100		PQVPH-1 3 second mean value of THD for phase B	LD0.VMHA11.ThdPhV.phsB.cVal.mag.f
		2319	0		u16	100		PQVPH-1 3 second mean value of THD for phase C	LD0.VMHA11.ThdPhV.phsC.cVal.mag.f

Table 123: PQVPH-2 : Voltage total harmonic distortion instance 2 (VMHA12)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5654		353:6	0					PQVPH-2 Alarm signal for THD	LD0.VMHA12.Alm.stVal
		2320	0		u16	100		PQVPH-2 Demand value for THD for phase A	LD0.VMHA12.DmdThdPhV.phsA.cVal.mag.f
		2321	0		u16	100		PQVPH-2 Demand value for THD for phase B	LD0.VMHA12.DmdThdPhV.phsB.cVal.mag.f
		2322	0		u16	100		PQVPH-2 Demand value for THD for phase C	LD0.VMHA12.DmdThdPhV.phsC.cVal.mag.f
		2323	0		u16	100		PQVPH-2 Maximum demand THD for phase A	LD0.VMHA12.MaxDmdThdV.phsA.cVal.mag.f
		2324	0		u16	100		PQVPH-2 Maximum demand THD for phase B	LD0.VMHA12.MaxDmdThdV.phsB.cVal.mag.f
		2325	0		u16	100		PQVPH-2 Maximum demand THD for phase C	LD0.VMHA12.MaxDmdThdV.phsC.cVal.mag.f

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2326	0		u16	100		PQVPH-2 3 second mean value of THD for phase A	LD0.VMHA12.ThdPhV.phsA.cVal.mag.f
		2327	0		u16	100		PQVPH-2 3 second mean value of THD for phase B	LD0.VMHA12.ThdPhV.phsB.cVal.mag.f
		2328	0		u16	100		PQVPH-2 3 second mean value of THD for phase C	LD0.VMHA12.ThdPhV.phsC.cVal.mag.f

**Table 124: PQSS-1 : Voltage variation instance 1 (PH1QVVR1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6332		395:12	0					PQSS-1 Voltage dip detected	LD0.PH1QVVR1.DipOp.stVal
6334		395:14	0					PQSS-1 Voltage dip active	LD0.PH1QVVR1.DipStr.stVal
6336		396:0	0					PQSS-1 Voltage interruption detected	LD0.PH1QVVR1.IntrOp.stVal
6338		396:2	0					PQSS-1 Voltage interruption active	LD0.PH1QVVR1.IntrStr.stVal
6340		396:4	0					PQSS-1 Voltage variation detected	LD0.PH1QVVR1.VarOp.stVal
6342		396:6	0					PQSS-1 Voltage swell detected	LD0.PH1QVVR1.SwlOp.stVal
6344		396:8	0					PQSS-1 Voltage swell active	LD0.PH1QVVR1.SwlStr.stVal
		2567	6		s32			PQSS-1 Instantaneous dip operation counter	LD0.PH1QVVR1.DipInstCnt.stVal
		2568	6						
		2569	6		s32			PQSS-1 Maximum duration dip operation counter	LD0.PH1QVVR1.DipMaxCnt.stVal
		2570	6						
		2571	6		s32			PQSS-1 Momentary dip operation counter	LD0.PH1QVVR1.DipMomCnt.stVal
		2572	6						
		2573	6		s32			PQSS-1 Temporary dip operation counter	LD0.PH1QVVR1.DipTmpCnt.stVal
		2574	6						
		2575	6		s32			PQSS-1 Maximum duration interruption operation counter	LD0.PH1QVVR1.IntrMaxCnt.stVal
		2576	6						
		2577	6		s32			PQSS-1 Momentary interruption operation counter	LD0.PH1QVVR1.IntrMomCnt.stVal
		2578	6						



Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2579	6		s32			PQSS-1 Sustained interruption operation counter	LD0.PH1QVVR1.IntrSstCnt.stVal
		2580	6						
		2581	6		s32			PQSS-1 Temporary interruption operation counter	LD0.PH1QVVR1.IntrTmpCnt.stVal
		2582	6						
		2583	6		s32			PQSS-1 Instantaneous swell operation counter	LD0.PH1QVVR1.SwlInstCnt.stVal
		2584	6						
		2585	6		s32			PQSS-1 Maximum duration swell operation counter	LD0.PH1QVVR1.SwlMaxCnt.stVal
		2586	6						
		2587	6		s32			PQSS-1 Momentary swell operation counter	LD0.PH1QVVR1.SwlMomCnt.stVal
		2588	6						
		2589	6		s32			PQSS-1 Temporary swell operation counter	LD0.PH1QVVR1.SwlTmpCnt.stVal
		2590	6						

Table 125: PQVUB-1 : Voltage unbalance instance 1 (VSQVUB1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5684		355:4	0					PQVUB-1 Alarm active when percentile unbalance exceeds the limit	LD0.VSQVUB1.HiPctVUnb.stVal
5686		355:6	0					PQVUB-1 Observation period is active	LD0.VSQVUB1.ObsPerAct.stVal
5688		355:8	0					PQVUB-1 Alarm active when 3 sec voltage unbalance exceeds the limit	LD0.VSQVUB1.VarStr.stVal

Table 126: PQVUB-2 : Voltage unbalance instance 2 (VSQVUB2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5690		355:10	0					PQVUB-2 Alarm active when percentile unbalance exceeds the limit	LD0.VSQVUB2.HiPctVUnb.stVal
5692		355:12	0					PQVUB-2 Observation period is active	LD0.VSQVUB2.ObsPerAct.stVal
5694		355:14	0					PQVUB-2 Alarm active when 3 sec voltage unbalance exceeds the limit	LD0.VSQVUB2.VarStr.stVal

**Table 127: LoadProf : Load profile instance 1 (LDPMSTA1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6144		384:0	0					LoadProf Recording memory alarm status	LD0.LDPMSTA1.MemAlm.stVal
6146		384:2	0					LoadProf Recording memory warning status	LD0.LDPMSTA1.MemWrn.stVal
		3147	6		s32			LoadProf How much recording memory is currently used	LD0.LDPMSTA1.MemUsed.stVal
		3148	6						

**Table 128: f : Frequency measurement instance 1 (FMMXU1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2378	6		u16	100		Frequency instantaneous value	LD0.FMMXU1.Hz.instMag.f

**Table 129: SP SE : Single-phase power and energy measurement instance 1 (SPEMMXU1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2426	6		s16	100		SP SE Power factor magnitude of reported value Phase A	LD0.SPEMMXU1.PF.phsA.cVal.mag.f
		2427	6		s16	100		SP SE Power factor magnitude of reported value Phase B	LD0.SPEMMXU1.PF.phsB.cVal.mag.f
		2428	6		s16	100		SP SE Power factor magnitude of reported value Phase C	LD0.SPEMMXU1.PF.phsC.cVal.mag.f
		2429	6		s32	100		SP SE Apparent power magnitude of reported value Phase A	LD0.SPEMMXU1.VA.phsA.cVal.mag.f
		2430	6						
		2431	6		s32	100		SP SE Apparent power magnitude of reported value Phase B	LD0.SPEMMXU1.VA.phsB.cVal.mag.f
		2432	6						
		2433	6		s32	100		SP SE Apparent power magnitude of reported value Phase C	LD0.SPEMMXU1.VA.phsC.cVal.mag.f
		2434	6						
		2435	6		s32	100		SP SE Reactive power magnitude of reported value Phase A	LD0.SPEMMXU1.VAr.phsA.cVal.mag.f
		2436	6						
		2437	6		s32	100		SP SE Reactive power magnitude of reported value Phase B	LD0.SPEMMXU1.VAr.phsB.cVal.mag.f
		2438	6						
		2439	6		s32	100		SP SE Reactive power magnitude of reported value Phase C	LD0.SPEMMXU1.VAr.phsC.cVal.mag.f

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2440	6						
		2441	6		s32	100		SP SE Active power magnitude of reported value Phase A	LD0.SPEMMXU1.W.phsA.cVal.mag.f
		2442	6						
		2443	6		s32	100		SP SE Active power magnitude of reported value Phase B	LD0.SPEMMXU1.W.phsB.cVal.mag.f
		2444	6						
		2445	6		s32	100		SP SE Active power magnitude of reported value Phase C	LD0.SPEMMXU1.W.phsC.cVal.mag.f
		2446	6						

**Table 130: SP SE : Single-phase power and energy measurement instance 1 (SPEMMTR1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6656		416.0	0					SP SE Reset of accumulated energy reading	LD0.SPEMMTR1.SupDmdRs.stVal
		2402	6		u32			SP SE Accumulated forward reactive energy value Phase A	LD0.SPEMMTR1.DmdVArhA.actVal
		2403	6						
		2404	6		u32			SP SE Accumulated forward reactive energy value Phase B	LD0.SPEMMTR1.DmdVArhB.actVal
		2405	6						
		2406	6		u32			SP SE Accumulated forward reactive energy value Phase C	LD0.SPEMMTR1.DmdVArhC.actVal
		2407	6						
		2408	6		u32			SP SE Accumulated forward active energy value Phase A	LD0.SPEMMTR1.DmdWhA.actVal
		2409	6						
		2410	6		u32			SP SE Accumulated forward active energy value Phase B	LD0.SPEMMTR1.DmdWhB.actVal
		2411	6						
		2412	6		u32			SP SE Accumulated forward active energy value Phase C	LD0.SPEMMTR1.DmdWhC.actVal
		2413	6						
		2414	6		u32			SP SE Accumulated reverse reactive energy value Phase A	LD0.SPEMMTR1.SupVArhA.actVal
		2415	6						
		2416	6		u32			SP SE Accumulated reverse reactive energy value Phase B	LD0.SPEMMTR1.SupVArhB.actVal

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2417	6						
		2418	6		u32			SP SE Accumulated reverse reactive energy value Phase C	LD0.SPEMMTR1.SupVArhC.actVal
		2419	6						
		2420	6		u32			SP SE Accumulated reverse active energy value Phase A	LD0.SPEMMTR1.SupWhA.actVal
		2421	6						
		2422	6		u32			SP SE Accumulated reverse active energy value Phase B	LD0.SPEMMTR1.SupWhB.actVal
		2423	6						
		2424	6		u32			SP SE Accumulated reverse active energy value Phase C	LD0.SPEMMTR1.SupWhC.actVal
		2425	6						

**Table 131: TP-1 : Minimum pulse timer (2 pcs) instance 1 (TPGAPC1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7198		449:14	0					TP-1 Output 2 status	LD0.TPGAPC1.Op.general
7200		450:0	0					TP-1 Output 1 status	LD0.TPGAPC1.Str.general

**Table 132: TP-2 : Minimum pulse timer (2 pcs) instance 2 (TPGAPC2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7202		450:2	0					TP-2 Output 2 status	LD0.TPGAPC2.Op.general
7204		450:4	0					TP-2 Output 1 status	LD0.TPGAPC2.Str.general

**Table 133: TP-3 : Minimum pulse timer (2 pcs) instance 3 (TPGAPC3)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7206		450:6	0					TP-3 Output 2 status	LD0.TPGAPC3.Op.general
7208		450:8	0					TP-3 Output 1 status	LD0.TPGAPC3.Str.general

**Table 134: TP-4 : Minimum pulse timer (2 pcs) instance 4 (TPGAPC4)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7210		450:10	0					TP-4 Output 2 status	LD0.TPGAPC4.Op.general
7212		450:12	0					TP-4 Output 1 status	LD0.TPGAPC4.Str.general

**Table 135: 62CLD-1 : Minimum pulse timer (2 pcs second resolution) instance 1 (TPSGAPC1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7222		451:6	0					62CLD-1 Output 2 status	LD0.TPSGAPC1.Op.general
7224		451:8	0					62CLD-1 Output 1 status	LD0.TPSGAPC1.Str.general

**Table 136: 62CLD-3 : Minimum pulse timer (2 pcs second resolution) instance 2 (TPSGAPC2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7226		451:10	0					62CLD-3 Output 2 status	LD0.TPSGAPC2.Op.general
7228		451:12	0					62CLD-3 Output 1 status	LD0.TPSGAPC2.Str.general

**Table 137: 62CLD-2 : Minimum pulse timer (2 pcs minute resolution) instance 1 (TPMGAPC1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7214		450:14	0					62CLD-2 Output 2 status	LD0.TPMGAPC1.Op.general
7216		451:0	0					62CLD-2 Output 1 status	LD0.TPMGAPC1.Str.general

**Table 138: 62CLD-4 : Minimum pulse timer (2 pcs minute resolution) instance 2 (TPMGAPC2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7218		451:2	0					62CLD-4 Output 2 status	LD0.TPMGAPC2.Op.general
7220		451:4	0					62CLD-4 Output 1 status	LD0.TPMGAPC2.Str.general

**Table 139: PT-1 : Pulse timer (8 pcs) instance 1 (PTGAPC1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6846		427:14	0					PT-1 Input 1 status	LD0.PTGAPC1.In1.stVal
6848		428:0	0					PT-1 Input 2 status	LD0.PTGAPC1.In2.stVal
6850		428:2	0					PT-1 Input 3 status	LD0.PTGAPC1.In3.stVal
6852		428:4	0					PT-1 Input 4 status	LD0.PTGAPC1.In4.stVal
6854		428:6	0					PT-1 Input 5 status	LD0.PTGAPC1.In5.stVal
6856		428:8	0					PT-1 Input 6 status	LD0.PTGAPC1.In6.stVal
6858		428:10	0					PT-1 Input 7 status	LD0.PTGAPC1.In7.stVal
6860		428:12	0					PT-1 Input 8 status	LD0.PTGAPC1.In8.stVal
6862		428:14	0					PT-1 Output 1 status	LD0.PTGAPC1.Q1.stVal
6864		429:0	0					PT-1 Output 2 status	LD0.PTGAPC1.Q2.stVal
6866		429:2	0					PT-1 Output 3 status	LD0.PTGAPC1.Q3.stVal
6868		429:4	0					PT-1 Output 4 status	LD0.PTGAPC1.Q4.stVal
6870		429:6	0					PT-1 Output 5 status	LD0.PTGAPC1.Q5.stVal
6872		429:8	0					PT-1 Output 6 status	LD0.PTGAPC1.Q6.stVal
6874		429:10	0					PT-1 Output 7 status	LD0.PTGAPC1.Q7.stVal
6876		429:12	0					PT-1 Output 8 status	LD0.PTGAPC1.Q8.stVal

**Table 140: PT-2 : Pulse timer (8 pcs) instance 2 (PTGAPC2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6878		429:14	0					PT-2 Input 1 status	LD0.PTGAPC2.In1.stVal
6880		430:0	0					PT-2 Input 2 status	LD0.PTGAPC2.In2.stVal
6882		430:2	0					PT-2 Input 3 status	LD0.PTGAPC2.In3.stVal
6884		430:4	0					PT-2 Input 4 status	LD0.PTGAPC2.In4.stVal
6886		430:6	0					PT-2 Input 5 status	LD0.PTGAPC2.In5.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6888		430:8	0					PT-2 Input 6 status	LD0.PTGAPC2.In6.stVal
6890		430:10	0					PT-2 Input 7 status	LD0.PTGAPC2.In7.stVal
6892		430:12	0					PT-2 Input 8 status	LD0.PTGAPC2.In8.stVal
6894		430:14	0					PT-2 Output 1 status	LD0.PTGAPC2.Q1.stVal
6896		431:0	0					PT-2 Output 2 status	LD0.PTGAPC2.Q2.stVal
6898		431:2	0					PT-2 Output 3 status	LD0.PTGAPC2.Q3.stVal
6900		431:4	0					PT-2 Output 4 status	LD0.PTGAPC2.Q4.stVal
6902		431:6	0					PT-2 Output 5 status	LD0.PTGAPC2.Q5.stVal
6904		431:8	0					PT-2 Output 6 status	LD0.PTGAPC2.Q6.stVal
6906		431:10	0					PT-2 Output 7 status	LD0.PTGAPC2.Q7.stVal
6908		431:12	0					PT-2 Output 8 status	LD0.PTGAPC2.Q8.stVal

**Table 141: TOF-1 : Time delay off (8 pcs) instance 1 (TOFGAPC1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7006		437:14	0					TOF-1 Input 1 status	LD0.TOFGAPC1.In1.stVal
7008		438:0	0					TOF-1 Input 2 status	LD0.TOFGAPC1.In2.stVal
7010		438:2	0					TOF-1 Input 3 status	LD0.TOFGAPC1.In3.stVal
7012		438:4	0					TOF-1 Input 4 status	LD0.TOFGAPC1.In4.stVal
7014		438:6	0					TOF-1 Input 5 status	LD0.TOFGAPC1.In5.stVal
7016		438:8	0					TOF-1 Input 6 status	LD0.TOFGAPC1.In6.stVal
7018		438:10	0					TOF-1 Input 7 status	LD0.TOFGAPC1.In7.stVal
7020		438:12	0					TOF-1 Input 8 status	LD0.TOFGAPC1.In8.stVal
7022		438:14	0					TOF-1 Output 1 status	LD0.TOFGAPC1.Q1.stVal
7024		439:0	0					TOF-1 Output 2 status	LD0.TOFGAPC1.Q2.stVal
7026		439:2	0					TOF-1 Output 3 status	LD0.TOFGAPC1.Q3.stVal
7028		439:4	0					TOF-1 Output 4 status	LD0.TOFGAPC1.Q4.stVal
7030		439:6	0					TOF-1 Output 5 status	LD0.TOFGAPC1.Q5.stVal
7032		439:8	0					TOF-1 Output 6 status	LD0.TOFGAPC1.Q6.stVal
7034		439:10	0					TOF-1 Output 7 status	LD0.TOFGAPC1.Q7.stVal
7036		439:12	0					TOF-1 Output 8 status	LD0.TOFGAPC1.Q8.stVal

**Table 142: TOF-2 : Time delay off (8 pcs) instance 2 (TOFGAPC2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7038		439:14	0					TOF-2 Input 1 status	LD0.TOFGAPC2.In1.stVal
7040		440:0	0					TOF-2 Input 2 status	LD0.TOFGAPC2.In2.stVal
7042		440:2	0					TOF-2 Input 3 status	LD0.TOFGAPC2.In3.stVal
7044		440:4	0					TOF-2 Input 4 status	LD0.TOFGAPC2.In4.stVal
7046		440:6	0					TOF-2 Input 5 status	LD0.TOFGAPC2.In5.stVal
7048		440:8	0					TOF-2 Input 6 status	LD0.TOFGAPC2.In6.stVal
7050		440:10	0					TOF-2 Input 7 status	LD0.TOFGAPC2.In7.stVal

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7052		440:12	0					TOF-2 Input 8 status	LD0.TOFGAPC2.In8.stVal
7054		440:14	0					TOF-2 Output 1 status	LD0.TOFGAPC2.Q1.stVal
7056		441:0	0					TOF-2 Output 2 status	LD0.TOFGAPC2.Q2.stVal
7058		441:2	0					TOF-2 Output 3 status	LD0.TOFGAPC2.Q3.stVal
7060		441:4	0					TOF-2 Output 4 status	LD0.TOFGAPC2.Q4.stVal
7062		441:6	0					TOF-2 Output 5 status	LD0.TOFGAPC2.Q5.stVal
7064		441:8	0					TOF-2 Output 6 status	LD0.TOFGAPC2.Q6.stVal
7066		441:10	0					TOF-2 Output 7 status	LD0.TOFGAPC2.Q7.stVal
7068		441:12	0					TOF-2 Output 8 status	LD0.TOFGAPC2.Q8.stVal

Table 143: TOF-3 : Time delay off (8 pcs) instance 3 (TOFGAPC3)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7070		441:14	0					TOF-3 Output 1 status	LD0.TOFGAPC3.Q1.stVal
7072		442:0	0					TOF-3 Output 2 status	LD0.TOFGAPC3.Q2.stVal
7074		442:2	0					TOF-3 Output 3 status	LD0.TOFGAPC3.Q3.stVal
7076		442:4	0					TOF-3 Output 4 status	LD0.TOFGAPC3.Q4.stVal
7078		442:6	0					TOF-3 Output 5 status	LD0.TOFGAPC3.Q5.stVal
7080		442:8	0					TOF-3 Output 6 status	LD0.TOFGAPC3.Q6.stVal
7082		442:10	0					TOF-3 Output 7 status	LD0.TOFGAPC3.Q7.stVal
7084		442:12	0					TOF-3 Output 8 status	LD0.TOFGAPC3.Q8.stVal

Table 144: TOF-4 : Time delay off (8 pcs) instance 4 (TOFGAPC4)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7086		442:14	0					TOF-4 Output 1 status	LD0.TOFGAPC4.Q1.stVal
7088		443:0	0					TOF-4 Output 2 status	LD0.TOFGAPC4.Q2.stVal
7090		443:2	0					TOF-4 Output 3 status	LD0.TOFGAPC4.Q3.stVal
7092		443:4	0					TOF-4 Output 4 status	LD0.TOFGAPC4.Q4.stVal
7094		443:6	0					TOF-4 Output 5 status	LD0.TOFGAPC4.Q5.stVal
7096		443:8	0					TOF-4 Output 6 status	LD0.TOFGAPC4.Q6.stVal
7098		443:10	0					TOF-4 Output 7 status	LD0.TOFGAPC4.Q7.stVal
7100		443:12	0					TOF-4 Output 8 status	LD0.TOFGAPC4.Q8.stVal

Table 145: TON -1 : Time delay on (8 pcs) instance 1 (TONGAPC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7102		443:14	0					TON -1 Input 1	LD0.TONGAPC1.In1.stVal
7104		444:0	0					TON -1 Input 2	LD0.TONGAPC1.In2.stVal
7106		444:2	0					TON -1 Input 3	LD0.TONGAPC1.In3.stVal
7108		444:4	0					TON -1 Input 4	LD0.TONGAPC1.In4.stVal
7110		444:6	0					TON -1 Input 5	LD0.TONGAPC1.In5.stVal
7112		444:8	0					TON -1 Input 6	LD0.TONGAPC1.In6.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7114		444:10	0					TON -1 Input 7	LD0.TONGAPC1.In7.stVal
7116		444:12	0					TON -1 Input 8	LD0.TONGAPC1.In8.stVal
7118		444:14	0					TON -1 Output 1	LD0.TONGAPC1.Q1.stVal
7120		445:0	0					TON -1 Output 2	LD0.TONGAPC1.Q2.stVal
7122		445:2	0					TON -1 Output 3	LD0.TONGAPC1.Q3.stVal
7124		445:4	0					TON -1 Output 4	LD0.TONGAPC1.Q4.stVal
7126		445:6	0					TON -1 Output 5	LD0.TONGAPC1.Q5.stVal
7128		445:8	0					TON -1 Output 6	LD0.TONGAPC1.Q6.stVal
7130		445:10	0					TON -1 Output 7	LD0.TONGAPC1.Q7.stVal
7132		445:12	0					TON -1 Output 8	LD0.TONGAPC1.Q8.stVal

**Table 146: TON -2 : Time delay on (8 pcs) instance 2 (TONGAPC2)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7102		443:14	0					TON -1 Input 1	LD0.TONGAPC1.In1.stVal
7134		445:14	0					TON -2 Input 1	LD0.TONGAPC2.In1.stVal
7136		446:0	0					TON -2 Input 2	LD0.TONGAPC2.In2.stVal
7138		446:2	0					TON -2 Input 3	LD0.TONGAPC2.In3.stVal
7140		446:4	0					TON -2 Input 4	LD0.TONGAPC2.In4.stVal
7142		446:6	0					TON -2 Input 5	LD0.TONGAPC2.In5.stVal
7144		446:8	0					TON -2 Input 6	LD0.TONGAPC2.In6.stVal
7146		446:10	0					TON -2 Input 7	LD0.TONGAPC2.In7.stVal
7148		446:12	0					TON -2 Input 8	LD0.TONGAPC2.In8.stVal
7150		446:14	0					TON -2 Output 1	LD0.TONGAPC2.Q1.stVal
7152		447:0	0					TON -2 Output 2	LD0.TONGAPC2.Q2.stVal
7154		447:2	0					TON -2 Output 3	LD0.TONGAPC2.Q3.stVal
7156		447:4	0					TON -2 Output 4	LD0.TONGAPC2.Q4.stVal
7158		447:6	0					TON -2 Output 5	LD0.TONGAPC2.Q5.stVal
7160		447:8	0					TON -2 Output 6	LD0.TONGAPC2.Q6.stVal
7162		447:10	0					TON -2 Output 7	LD0.TONGAPC2.Q7.stVal
7164		447:12	0					TON -2 Output 8	LD0.TONGAPC2.Q8.stVal

**Table 147: TON -3 : Time delay on (8 pcs) instance 3 (TONGAPC3)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7166		447:14	0					TON -3 Output 1	LD0.TONGAPC3.Q1.stVal
7168		448:0	0					TON -3 Output 2	LD0.TONGAPC3.Q2.stVal
7170		448:2	0					TON -3 Output 3	LD0.TONGAPC3.Q3.stVal
7172		448:4	0					TON -3 Output 4	LD0.TONGAPC3.Q4.stVal
7174		448:6	0					TON -3 Output 5	LD0.TONGAPC3.Q5.stVal
7176		448:8	0					TON -3 Output 6	LD0.TONGAPC3.Q6.stVal



Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7178		448:10	0					TON -3 Output 7	LD0.TONGAPC3.Q7.stVal
7180		448:12	0					TON -3 Output 8	LD0.TONGAPC3.Q8.stVal

Table 148: TON -4 : Time delay on (8 pcs) instance 4 (TONGAPC4)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7182		448:14	0					TON -4 Output 1	LD0.TONGAPC4.Q1.stVal
7184		449:0	0					TON -4 Output 2	LD0.TONGAPC4.Q2.stVal
7186		449:2	0					TON -4 Output 3	LD0.TONGAPC4.Q3.stVal
7188		449:4	0					TON -4 Output 4	LD0.TONGAPC4.Q4.stVal
7190		449:6	0					TON -4 Output 5	LD0.TONGAPC4.Q5.stVal
7192		449:8	0					TON -4 Output 6	LD0.TONGAPC4.Q6.stVal
7194		449:10	0					TON -4 Output 7	LD0.TONGAPC4.Q7.stVal
7196		449:12	0					TON -4 Output 8	LD0.TONGAPC4.Q8.stVal

Table 149: SR-1 : Set reset (8 pcs) instance 1 (SRGAPC1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6910		431:14	0					SR-1 Q1 status	LD0.SRGAPC1.Q1.stVal
6912		432:0	0					SR-1 Q2 status	LD0.SRGAPC1.Q2.stVal
6914		432:2	0					SR-1 Q3 status	LD0.SRGAPC1.Q3.stVal
6916		432:4	0					SR-1 Q4 status	LD0.SRGAPC1.Q4.stVal
6918		432:6	0					SR-1 Q5 status	LD0.SRGAPC1.Q5.stVal
6920		432:8	0					SR-1 Q6 status	LD0.SRGAPC1.Q6.stVal
6922		432:10	0					SR-1 Q7 status	LD0.SRGAPC1.Q7.stVal
6924		432:12	0					SR-1 Q8 status	LD0.SRGAPC1.Q8.stVal
6926		432:14	0					SR-1 Set Q1 output when set	LD0.SRGAPC1.Set1.stVal
6928		433:0	0					SR-1 Set Q2 output when set	LD0.SRGAPC1.Set2.stVal
6930		433:2	0					SR-1 Set Q3 output when set	LD0.SRGAPC1.Set3.stVal
6932		433:4	0					SR-1 Set Q4 output when set	LD0.SRGAPC1.Set4.stVal
6934		433:6	0					SR-1 Set Q5 output when set	LD0.SRGAPC1.Set5.stVal
6936		433:8	0					SR-1 Set Q6 output when set	LD0.SRGAPC1.Set6.stVal
6938		433:10	0					SR-1 Set Q7 output when set	LD0.SRGAPC1.Set7.stVal
6940		433:12	0					SR-1 Set Q8 output when set	LD0.SRGAPC1.Set8.stVal

Table 150: SR-2 : Set reset (8 pcs) instance 2 (SRGAPC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6942		433:14	0					SR-2 Q1 status	LD0.SRGAPC2.Q1.stVal
6944		434:0	0					SR-2 Q2 status	LD0.SRGAPC2.Q2.stVal
6946		434:2	0					SR-2 Q3 status	LD0.SRGAPC2.Q3.stVal
6948		434:4	0					SR-2 Q4 status	LD0.SRGAPC2.Q4.stVal
6950		434:6	0					SR-2 Q5 status	LD0.SRGAPC2.Q5.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6952		434:8	0					SR-2 Q6 status	LD0.SRGAPC2.Q6.stVal
6954		434:10	0					SR-2 Q7 status	LD0.SRGAPC2.Q7.stVal
6956		434:12	0					SR-2 Q8 status	LD0.SRGAPC2.Q8.stVal
6958		434:14	0					SR-2 Set Q1 output when set	LD0.SRGAPC2.Set1.stVal
6960		435:0	0					SR-2 Set Q2 output when set	LD0.SRGAPC2.Set2.stVal
6962		435:2	0					SR-2 Set Q3 output when set	LD0.SRGAPC2.Set3.stVal
6964		435:4	0					SR-2 Set Q4 output when set	LD0.SRGAPC2.Set4.stVal
6966		435:6	0					SR-2 Set Q5 output when set	LD0.SRGAPC2.Set5.stVal
6968		435:8	0					SR-2 Set Q6 output when set	LD0.SRGAPC2.Set6.stVal
6970		435:10	0					SR-2 Set Q7 output when set	LD0.SRGAPC2.Set7.stVal
6972		435:12	0					SR-2 Set Q8 output when set	LD0.SRGAPC2.Set8.stVal

**Table 151: SR-3 : Set reset (8 pcs) instance 3 (SRGAPC3)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6974		435:14	0					SR-3 Q1 status	LD0.SRGAPC3.Q1.stVal
6976		436:0	0					SR-3 Q2 status	LD0.SRGAPC3.Q2.stVal
6978		436:2	0					SR-3 Q3 status	LD0.SRGAPC3.Q3.stVal
6980		436:4	0					SR-3 Q4 status	LD0.SRGAPC3.Q4.stVal
6982		436:6	0					SR-3 Q5 status	LD0.SRGAPC3.Q5.stVal
6984		436:8	0					SR-3 Q6 status	LD0.SRGAPC3.Q6.stVal
6986		436:10	0					SR-3 Q7 status	LD0.SRGAPC3.Q7.stVal
6988		436:12	0					SR-3 Q8 status	LD0.SRGAPC3.Q8.stVal

**Table 152: SR-4 : Set reset (8 pcs) instance 4 (SRGAPC4)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6990		436:14	0					SR-4 Q1 status	LD0.SRGAPC4.Q1.stVal
6992		437:0	0					SR-4 Q2 status	LD0.SRGAPC4.Q2.stVal
6994		437:2	0					SR-4 Q3 status	LD0.SRGAPC4.Q3.stVal
6996		437:4	0					SR-4 Q4 status	LD0.SRGAPC4.Q4.stVal
6998		437:6	0					SR-4 Q5 status	LD0.SRGAPC4.Q5.stVal
7000		437:8	0					SR-4 Q6 status	LD0.SRGAPC4.Q6.stVal
7002		437:10	0					SR-4 Q7 status	LD0.SRGAPC4.Q7.stVal
7004		437:12	0					SR-4 Q8 status	LD0.SRGAPC4.Q8.stVal

**Table 153: MV-1 : Move (8 pcs) instance 1 (MVGAPC1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6718		419:14	0					MV-1 Q1 status	LD0.MVGAPC1.Q1.stVal
6720		420:0	0					MV-1 Q2 status	LD0.MVGAPC1.Q2.stVal
6722		420:2	0					MV-1 Q3 status	LD0.MVGAPC1.Q3.stVal
6724		420:4	0					MV-1 Q4 status	LD0.MVGAPC1.Q4.stVal

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6726		420:6	0					MV-1 Q5 status	LD0.MVGAPC1.Q5.stVal
6728		420:8	0					MV-1 Q6 status	LD0.MVGAPC1.Q6.stVal
6730		420:10	0					MV-1 Q7 status	LD0.MVGAPC1.Q7.stVal
6732		420:12	0					MV-1 Q8 status	LD0.MVGAPC1.Q8.stVal

Table 154: MV-2 : Move (8 pcs) instance 2 (MVGAPC2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6734		420:14	0					MV-2 Q1 status	LD0.MVGAPC2.Q1.stVal
6736		421:0	0					MV-2 Q2 status	LD0.MVGAPC2.Q2.stVal
6738		421:2	0					MV-2 Q3 status	LD0.MVGAPC2.Q3.stVal
6740		421:4	0					MV-2 Q4 status	LD0.MVGAPC2.Q4.stVal
6742		421:6	0					MV-2 Q5 status	LD0.MVGAPC2.Q5.stVal
6744		421:8	0					MV-2 Q6 status	LD0.MVGAPC2.Q6.stVal
6746		421:10	0					MV-2 Q7 status	LD0.MVGAPC2.Q7.stVal
6748		421:12	0					MV-2 Q8 status	LD0.MVGAPC2.Q8.stVal

Table 155: MV-3 : Move (8 pcs) instance 3 (MVGAPC3)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6750		421:14	0					MV-3 Q1 status	LD0.MVGAPC3.Q1.stVal
6752		422:0	0					MV-3 Q2 status	LD0.MVGAPC3.Q2.stVal
6754		422:2	0					MV-3 Q3 status	LD0.MVGAPC3.Q3.stVal
6756		422:4	0					MV-3 Q4 status	LD0.MVGAPC3.Q4.stVal
6758		422:6	0					MV-3 Q5 status	LD0.MVGAPC3.Q5.stVal
6760		422:8	0					MV-3 Q6 status	LD0.MVGAPC3.Q6.stVal
6762		422:10	0					MV-3 Q7 status	LD0.MVGAPC3.Q7.stVal
6764		422:12	0					MV-3 Q8 status	LD0.MVGAPC3.Q8.stVal

Table 156: MV-4 : Move (8 pcs) instance 4 (MVGAPC4)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6766		422:14	0					MV-4 Q1 status	LD0.MVGAPC4.Q1.stVal
6768		423:0	0					MV-4 Q2 status	LD0.MVGAPC4.Q2.stVal
6770		423:2	0					MV-4 Q3 status	LD0.MVGAPC4.Q3.stVal
6772		423:4	0					MV-4 Q4 status	LD0.MVGAPC4.Q4.stVal
6774		423:6	0					MV-4 Q5 status	LD0.MVGAPC4.Q5.stVal
6776		423:8	0					MV-4 Q6 status	LD0.MVGAPC4.Q6.stVal
6778		423:10	0					MV-4 Q7 status	LD0.MVGAPC4.Q7.stVal
6780		423:12	0					MV-4 Q8 status	LD0.MVGAPC4.Q8.stVal

## Section 2 Modbus data mappings

**Table 157: MV-5 : Move (8 pcs) instance 5 (MVGAPC5)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6782		423:14	0					MV-5 Q1 status	LD0.MVGAPC5.Q1.stVal
6784		424:0	0					MV-5 Q2 status	LD0.MVGAPC5.Q2.stVal
6786		424:2	0					MV-5 Q3 status	LD0.MVGAPC5.Q3.stVal
6788		424:4	0					MV-5 Q4 status	LD0.MVGAPC5.Q4.stVal
6790		424:6	0					MV-5 Q5 status	LD0.MVGAPC5.Q5.stVal
6792		424:8	0					MV-5 Q6 status	LD0.MVGAPC5.Q6.stVal
6794		424:10	0					MV-5 Q7 status	LD0.MVGAPC5.Q7.stVal
6796		424:12	0					MV-5 Q8 status	LD0.MVGAPC5.Q8.stVal

**Table 158: MV-6 : Move (8 pcs) instance 6 (MVGAPC6)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6798		424:14	0					MV-6 Q1 status	LD0.MVGAPC6.Q1.stVal
6800		425:0	0					MV-6 Q2 status	LD0.MVGAPC6.Q2.stVal
6802		425:2	0					MV-6 Q3 status	LD0.MVGAPC6.Q3.stVal
6804		425:4	0					MV-6 Q4 status	LD0.MVGAPC6.Q4.stVal
6806		425:6	0					MV-6 Q5 status	LD0.MVGAPC6.Q5.stVal
6808		425:8	0					MV-6 Q6 status	LD0.MVGAPC6.Q6.stVal
6810		425:10	0					MV-6 Q7 status	LD0.MVGAPC6.Q7.stVal
6812		425:12	0					MV-6 Q8 status	LD0.MVGAPC6.Q8.stVal

**Table 159: MV-7 : Move (8 pcs) instance 7 (MVGAPC7)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6814		425:14	0					MV-7 Q1 status	LD0.MVGAPC7.Q1.stVal
6816		426:0	0					MV-7 Q2 status	LD0.MVGAPC7.Q2.stVal
6818		426:2	0					MV-7 Q3 status	LD0.MVGAPC7.Q3.stVal
6820		426:4	0					MV-7 Q4 status	LD0.MVGAPC7.Q4.stVal
6822		426:6	0					MV-7 Q5 status	LD0.MVGAPC7.Q5.stVal
6824		426:8	0					MV-7 Q6 status	LD0.MVGAPC7.Q6.stVal
6826		426:10	0					MV-7 Q7 status	LD0.MVGAPC7.Q7.stVal
6828		426:12	0					MV-7 Q8 status	LD0.MVGAPC7.Q8.stVal

**Table 160: MV-8 : Move (8 pcs) instance 8 (MVGAPC8)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6830		426:14	0					MV-8 Q1 status	LD0.MVGAPC8.Q1.stVal
6832		427:0	0					MV-8 Q2 status	LD0.MVGAPC8.Q2.stVal
6834		427:2	0					MV-8 Q3 status	LD0.MVGAPC8.Q3.stVal
6836		427:4	0					MV-8 Q4 status	LD0.MVGAPC8.Q4.stVal
6838		427:6	0					MV-8 Q5 status	LD0.MVGAPC8.Q5.stVal
6840		427:8	0					MV-8 Q6 status	LD0.MVGAPC8.Q6.stVal

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6842		427:10	0					MV-8 Q7 status	LD0.MVGAPC8.Q7.stVal
6844		427:12	0					MV-8 Q8 status	LD0.MVGAPC8.Q8.stVal

Table 161: CNTRL-1 : Generic control points instance 1 (SPCGGIO1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6496		406:0	0					CNTRL-1 Output 1 status	LD0.SPCGGIO1.SPCSO1.stVal
6498		406:2	0					CNTRL-1 Output 2 status	LD0.SPCGGIO1.SPCSO2.stVal
6500		406:4	0					CNTRL-1 Output 3 status	LD0.SPCGGIO1.SPCSO3.stVal
6502		406:6	0					CNTRL-1 Output 4 status	LD0.SPCGGIO1.SPCSO4.stVal
6504		406:8	0					CNTRL-1 Output 5 status	LD0.SPCGGIO1.SPCSO5.stVal
6506		406:10	0					CNTRL-1 Output 6 status	LD0.SPCGGIO1.SPCSO6.stVal
6508		406:12	0					CNTRL-1 Output 7 status	LD0.SPCGGIO1.SPCSO7.stVal
6510		406:14	0					CNTRL-1 Output 8 status	LD0.SPCGGIO1.SPCSO8.stVal
6512		407:0	0					CNTRL-1 Output 9 status	LD0.SPCGGIO1.SPCSO9.stVal
6514		407:2	0					CNTRL-1 Output 10 status	LD0.SPCGGIO1.SPCSO10.stVal
6516		407:4	0					CNTRL-1 Output 11 status	LD0.SPCGGIO1.SPCSO11.stVal
6518		407:6	0					CNTRL-1 Output 12 status	LD0.SPCGGIO1.SPCSO12.stVal
6520		407:8	0					CNTRL-1 Output 13 status	LD0.SPCGGIO1.SPCSO13.stVal
6522		407:10	0					CNTRL-1 Output 14 status	LD0.SPCGGIO1.SPCSO14.stVal
6524		407:12	0					CNTRL-1 Output 15 status	LD0.SPCGGIO1.SPCSO15.stVal
6526		407:14	0					CNTRL-1 Output 16 status	LD0.SPCGGIO1.SPCSO16.stVal

Table 162: CNTRL-2 : Generic control points instance 2 (SPCGGIO2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6528		408:0	0					CNTRL-2 Output 1 status	LD0.SPCGGIO2.SPCSO1.stVal
6530		408:2	0					CNTRL-2 Output 2 status	LD0.SPCGGIO2.SPCSO2.stVal
6532		408:4	0					CNTRL-2 Output 3 status	LD0.SPCGGIO2.SPCSO3.stVal
6534		408:6	0					CNTRL-2 Output 4 status	LD0.SPCGGIO2.SPCSO4.stVal
6536		408:8	0					CNTRL-2 Output 5 status	LD0.SPCGGIO2.SPCSO5.stVal
6538		408:10	0					CNTRL-2 Output 6 status	LD0.SPCGGIO2.SPCSO6.stVal
6540		408:12	0					CNTRL-2 Output 7 status	LD0.SPCGGIO2.SPCSO7.stVal
6542		408:14	0					CNTRL-2 Output 8 status	LD0.SPCGGIO2.SPCSO8.stVal
6544		409:0	0					CNTRL-2 Output 9 status	LD0.SPCGGIO2.SPCSO9.stVal
6546		409:2	0					CNTRL-2 Output 10 status	LD0.SPCGGIO2.SPCSO10.stVal
6548		409:4	0					CNTRL-2 Output 11 status	LD0.SPCGGIO2.SPCSO11.stVal
6550		409:6	0					CNTRL-2 Output 12 status	LD0.SPCGGIO2.SPCSO12.stVal
6552		409:8	0					CNTRL-2 Output 13 status	LD0.SPCGGIO2.SPCSO13.stVal
6554		409:10	0					CNTRL-2 Output 14 status	LD0.SPCGGIO2.SPCSO14.stVal
6556		409:12	0					CNTRL-2 Output 15 status	LD0.SPCGGIO2.SPCSO15.stVal
6558		409:14	0					CNTRL-2 Output 16 status	LD0.SPCGGIO2.SPCSO16.stVal

**Table 163: CNTRL-3 : Generic control points instance 3 (SPCGGIO3)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6560		410:0	0					CNTRL-3 Output 1 status	LD0.SPCGGIO3.SPCSO1.stVal
6562		410:2	0					CNTRL-3 Output 2 status	LD0.SPCGGIO3.SPCSO2.stVal
6564		410:4	0					CNTRL-3 Output 3 status	LD0.SPCGGIO3.SPCSO3.stVal
6566		410:6	0					CNTRL-3 Output 4 status	LD0.SPCGGIO3.SPCSO4.stVal
6568		410:8	0					CNTRL-3 Output 5 status	LD0.SPCGGIO3.SPCSO5.stVal
6570		410:10	0					CNTRL-3 Output 6 status	LD0.SPCGGIO3.SPCSO6.stVal
6572		410:12	0					CNTRL-3 Output 7 status	LD0.SPCGGIO3.SPCSO7.stVal
6574		410:14	0					CNTRL-3 Output 8 status	LD0.SPCGGIO3.SPCSO8.stVal
6576		411:0	0					CNTRL-3 Output 9 status	LD0.SPCGGIO3.SPCSO9.stVal
6578		411:2	0					CNTRL-3 Output 10 status	LD0.SPCGGIO3.SPCSO10.stVal
6580		411:4	0					CNTRL-3 Output 11 status	LD0.SPCGGIO3.SPCSO11.stVal
6582		411:6	0					CNTRL-3 Output 12 status	LD0.SPCGGIO3.SPCSO12.stVal
6584		411:8	0					CNTRL-3 Output 13 status	LD0.SPCGGIO3.SPCSO13.stVal
6586		411:10	0					CNTRL-3 Output 14 status	LD0.SPCGGIO3.SPCSO14.stVal
6588		411:12	0					CNTRL-3 Output 15 status	LD0.SPCGGIO3.SPCSO15.stVal
6590		411:14	0					CNTRL-3 Output 16 status	LD0.SPCGGIO3.SPCSO16.stVal

**Table 164: RCNTRL-1 : Remote Generic control points instance 1 (SPCRGGIO1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6624		414:0	0					RCNTRL-1 Output 1 status	LD0.SPCRGGIO1.SPCSO1.stVal
6626		414:2	0					RCNTRL-1 Output 2 status	LD0.SPCRGGIO1.SPCSO2.stVal
6628		414:4	0					RCNTRL-1 Output 3 status	LD0.SPCRGGIO1.SPCSO3.stVal
6630		414:6	0					RCNTRL-1 Output 4 status	LD0.SPCRGGIO1.SPCSO4.stVal
6632		414:8	0					RCNTRL-1 Output 5 status	LD0.SPCRGGIO1.SPCSO5.stVal
6634		414:10	0					RCNTRL-1 Output 6 status	LD0.SPCRGGIO1.SPCSO6.stVal
6636		414:12	0					RCNTRL-1 Output 7 status	LD0.SPCRGGIO1.SPCSO7.stVal
6638		414:14	0					RCNTRL-1 Output 8 status	LD0.SPCRGGIO1.SPCSO8.stVal
6640		415:0	0					RCNTRL-1 Output 9 status	LD0.SPCRGGIO1.SPCSO9.stVal
6642		415:2	0					RCNTRL-1 Output 10 status	LD0.SPCRGGIO1.SPCSO10.stVal
6644		415:4	0					RCNTRL-1 Output 11 status	LD0.SPCRGGIO1.SPCSO11.stVal
6646		415:6	0					RCNTRL-1 Output 12 status	LD0.SPCRGGIO1.SPCSO12.stVal
6648		415:8	0					RCNTRL-1 Output 13 status	LD0.SPCRGGIO1.SPCSO13.stVal
6650		415:10	0					RCNTRL-1 Output 14 status	LD0.SPCRGGIO1.SPCSO14.stVal
6652		415:12	0					RCNTRL-1 Output 15 status	LD0.SPCRGGIO1.SPCSO15.stVal
6654		415:14	0					RCNTRL-1 Output 16 status	LD0.SPCRGGIO1.SPCSO16.stVal

**Table 165: LCNTRL-1 : Local Generic control points instance 1 (SPCLGGIO1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6592		412:0	0					LCNTRL-1 Output 1 status	LD0.SPCLGGIO1.SPCSO1.stVal

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6594		412:2	0					LCNTRL-1 Output 2 status	LD0.SPCLGGIO1.SPCSO2.stVal
6596		412:4	0					LCNTRL-1 Output 3 status	LD0.SPCLGGIO1.SPCSO3.stVal
6598		412:6	0					LCNTRL-1 Output 4 status	LD0.SPCLGGIO1.SPCSO4.stVal
6600		412:8	0					LCNTRL-1 Output 5 status	LD0.SPCLGGIO1.SPCSO5.stVal
6602		412:10	0					LCNTRL-1 Output 6 status	LD0.SPCLGGIO1.SPCSO6.stVal
6604		412:12	0					LCNTRL-1 Output 7 status	LD0.SPCLGGIO1.SPCSO7.stVal
6606		412:14	0					LCNTRL-1 Output 8 status	LD0.SPCLGGIO1.SPCSO8.stVal
6608		413:0	0					LCNTRL-1 Output 9 status	LD0.SPCLGGIO1.SPCSO9.stVal
6610		413:2	0					LCNTRL-1 Output 10 status	LD0.SPCLGGIO1.SPCSO10.stVal
6612		413:4	0					LCNTRL-1 Output 11 status	LD0.SPCLGGIO1.SPCSO11.stVal
6614		413:6	0					LCNTRL-1 Output 12 status	LD0.SPCLGGIO1.SPCSO12.stVal
6616		413:8	0					LCNTRL-1 Output 13 status	LD0.SPCLGGIO1.SPCSO13.stVal
6618		413:10	0					LCNTRL-1 Output 14 status	LD0.SPCLGGIO1.SPCSO14.stVal
6620		413:12	0					LCNTRL-1 Output 15 status	LD0.SPCLGGIO1.SPCSO15.stVal
6622		413:14	0					LCNTRL-1 Output 16 status	LD0.SPCLGGIO1.SPCSO16.stVal

Table 166: CTR-1 : Generic Up-Down Counters instance 1 (UDFCNT1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7262		453:14	0					CTR-1 Status of the down counting	LD0.UDFCNT1.DnCntSt.stVal
7264		454:0	0					CTR-1 Status of the up counting	LD0.UDFCNT1.UpCntSt.stVal

Table 167: CTR-2 : Generic Up-Down Counters instance 2 (UDFCNT2)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7266		454:2	0					CTR-2 Status of the down counting	LD0.UDFCNT2.DnCntSt.stVal
7268		454:4	0					CTR-2 Status of the up counting	LD0.UDFCNT2.UpCntSt.stVal

Table 168: CTR-3 : Generic Up-Down Counters instance 3 (UDFCNT3)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7270		454:6	0					CTR-3 Status of the down counting	LD0.UDFCNT3.DnCntSt.stVal
7272		454:8	0					CTR-3 Status of the up counting	LD0.UDFCNT3.UpCntSt.stVal

Table 169: CTR-4 : Generic Up-Down Counters instance 4 (UDFCNT4)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7274		454:10	0					CTR-4 Status of the down counting	LD0.UDFCNT4.DnCntSt.stVal
7276		454:12	0					CTR-4 Status of the up counting	LD0.UDFCNT4.UpCntSt.stVal

**Table 170: CTR-5 : Generic Up-Down Counters instance 5 (UDFCNT5)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7278		454:14	0					CTR-5 Status of the down counting	LD0.UDFCNT5.DnCntSt.stVal
7280		455:0	0					CTR-5 Status of the up counting	LD0.UDFCNT5.UpCntSt.stVal

**Table 171: CTR-6 : Generic Up-Down Counters instance 6 (UDFCNT6)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7282		455:2	0					CTR-6 Status of the down counting	LD0.UDFCNT6.DnCntSt.stVal
7284		455:4	0					CTR-6 Status of the up counting	LD0.UDFCNT6.UpCntSt.stVal

**Table 172: CTR-7 : Generic Up-Down Counters instance 7 (UDFCNT7)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7286		455:6	0					CTR-7 Status of the down counting	LD0.UDFCNT7.DnCntSt.stVal
7288		455:8	0					CTR-7 Status of the up counting	LD0.UDFCNT7.UpCntSt.stVal

**Table 173: CTR-8 : Generic Up-Down Counters instance 8 (UDFCNT8)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7290		455:10	0					CTR-8 Status of the down counting	LD0.UDFCNT8.DnCntSt.stVal
7292		455:12	0					CTR-8 Status of the up counting	LD0.UDFCNT8.UpCntSt.stVal

**Table 174: CTR-9 : Generic Up-Down Counters instance 9 (UDFCNT9)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7294		455:14	0					CTR-9 Status of the down counting	LD0.UDFCNT9.DnCntSt.stVal
7296		456:0	0					CTR-9 Status of the up counting	LD0.UDFCNT9.UpCntSt.stVal

**Table 175: CTR-10 : Generic Up-Down Counters instance 10 (UDFCNT10)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7298		456:2	0					CTR-10 Status of the down counting	LD0.UDFCNT10.DnCntSt.stVal
7300		456:4	0					CTR-10 Status of the up counting	LD0.UDFCNT10.UpCntSt.stVal

**Table 176: CTR-11 : Generic Up-Down Counters instance 11 (UDFCNT11)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7302		456:6	0					CTR-11 Status of the down counting	LD0.UDFCNT11.DnCntSt.stVal



Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7304		456:8	0					CTR-11 Status of the up counting	LD0.UDFCNT11.UpCntSt.stVal

Table 177: CTR-12 : Generic Up-Down Counters instance 12 (UDFCNT12)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
7306		456:10	0					CTR-12 Status of the down counting	LD0.UDFCNT12.DnCntSt.stVal
7308		456:12	0					CTR-12 Status of the up counting	LD0.UDFCNT12.UpCntSt.stVal

Table 178: FKEY : Programmable buttons(16 buttons) instance 1 (FKEYGGIO1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4476	279:12	0					FKEY KEY 1	LD0.FKEYGGIO1.Ind1.stVal
		279:13		Yes					
	4478	279:14	0					FKEY KEY 2	LD0.FKEYGGIO1.Ind2.stVal
		279:15		Yes					
	4480	280:0	0					FKEY KEY 3	LD0.FKEYGGIO1.Ind3.stVal
		280:1		Yes					
	4482	280:2	0					FKEY KEY 4	LD0.FKEYGGIO1.Ind4.stVal
		280:3		Yes					
	4484	280:4	0					FKEY KEY 5	LD0.FKEYGGIO1.Ind5.stVal
		280:5		Yes					
	4486	280:6	0					FKEY KEY 6	LD0.FKEYGGIO1.Ind6.stVal
		280:7		Yes					
	4488	280:8	0					FKEY KEY 7	LD0.FKEYGGIO1.Ind7.stVal
		280:9		Yes					
	4490	280:10	0					FKEY KEY 8	LD0.FKEYGGIO1.Ind8.stVal
		280:11		Yes					
	4492	280:12	0					FKEY KEY 9	LD0.FKEYGGIO1.Ind9.stVal
		280:13		Yes					
	4494	280:14	0					FKEY KEY 10	LD0.FKEYGGIO1.Ind10.stVal
		280:15		Yes					
	4496	281:0	0					FKEY KEY 11	LD0.FKEYGGIO1.Ind11.stVal
		281:1		Yes					
	4498	281:2	0					FKEY KEY 12	LD0.FKEYGGIO1.Ind12.stVal
		281:3		Yes					
	4500	281:4	0					FKEY KEY 13	LD0.FKEYGGIO1.Ind13.stVal
		281:5		Yes					
	4502	281:6	0					FKEY KEY 14	LD0.FKEYGGIO1.Ind14.stVal
		281:7		Yes					
	4504	281:8	0					FKEY KEY 15	LD0.FKEYGGIO1.Ind15.stVal

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		281:9		Yes					
	4506	281:10	0					FKEY KEY 16	LD0.FKEYGGIO1.lnd16.stVal
		281:11		Yes					
4752		297:0	0					FKEY LED 1	LD0.FKEYGGIO1.SPCSO1.stVal
4753		297:1		Yes					
4754		297:2	0					FKEY LED 2	LD0.FKEYGGIO1.SPCSO2.stVal
4755		297:3		Yes					
4756		297:4	0					FKEY LED 3	LD0.FKEYGGIO1.SPCSO3.stVal
4757		297:5		Yes					
4758		297:6	0					FKEY LED 4	LD0.FKEYGGIO1.SPCSO4.stVal
4759		297:7		Yes					
4760		297:8	0					FKEY LED 5	LD0.FKEYGGIO1.SPCSO5.stVal
4761		297:9		Yes					
4762		297:10	0					FKEY LED 6	LD0.FKEYGGIO1.SPCSO6.stVal
4763		297:11		Yes					
4764		297:12	0					FKEY LED 7	LD0.FKEYGGIO1.SPCSO7.stVal
4765		297:13		Yes					
4766		297:14	0					FKEY LED 8	LD0.FKEYGGIO1.SPCSO8.stVal
4767		297:15		Yes					
4768		298:0	0					FKEY LED 9	LD0.FKEYGGIO1.SPCSO9.stVal
4769		298:1		Yes					
4770		298:2	0					FKEY LED 10	LD0.FKEYGGIO1.SPCSO10.stVal
4771		298:3		Yes					
4772		298:4	0					FKEY LED 11	LD0.FKEYGGIO1.SPCSO11.stVal
4773		298:5		Yes					
4774		298:6	0					FKEY LED 12	LD0.FKEYGGIO1.SPCSO12.stVal
4775		298:7		Yes					
4776		298:8	0					FKEY LED 13	LD0.FKEYGGIO1.SPCSO13.stVal
4777		298:9		Yes					
4778		298:10	0					FKEY LED 14	LD0.FKEYGGIO1.SPCSO14.stVal
4779		298:11		Yes					
4780		298:12	0					FKEY LED 15	LD0.FKEYGGIO1.SPCSO15.stVal
4781		298:13		Yes					
4782		298:14	0					FKEY LED 16	LD0.FKEYGGIO1.SPCSO16.stVal
4783		298:15		Yes					

**Table 179: DFR : Disturbance recorder (RDRE1)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
5592		349:8	0					Disturbance recorder Recording made	DR.RDRE1.RcdMade.stVal

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
		2883	6		s32			Disturbance recorder Remaining amount of recordings that fit into the available recording memory when present settings are used	DR.RDRE1.EMaxNumRcd.stVal
		2884	6						
		2885	6		s32			Disturbance recorder Time remaining to the next periodic triggering	DR.RDRE1.EPerTRem.stVal
		2886	6						
		2887	0		s32			Disturbance recorder Number of recordings in the memory	DR.RDRE1.FitNum.stVal
		2888	0						
		2889	0		s32			Disturbance recorder How much recording memory is currently used	DR.RDRE1.MemUsed.stVal
		2890	0						

Table 180: FLO : Fault location (DRFLO1)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
6110		381:14	0					DRFLO1 Relay Trip	LD0.DRFLO1.Tr.general
		8110	100		u16	100		DRFLO1 Fault Distance	LD0.DRFLO1.FitDisKm.mag.f
		8112	100		u16			DRFLO1 Fault Loop	LD0.DRFLO1.FitLoop.stVal
		8113	100		u16	100		DRFLO1 Loop Reactance	LD0.DRFLO1.FitLoopX.mag.f
		8115	100		u16	100		DRFLO1 FaultResistance	LD0.DRFLO1.FitZ.mag.f

Table 181: XGGIO100 : PSM (X100) card (XGGIO100)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
4804		300:4	0					X100 (PSM) Connectors 6-7	LD0.XGGIO100.SPCSO1.stVal
4805		300:5		Yes					
4806		300:6	0					X100 (PSM) Connectors 8-9	LD0.XGGIO100.SPCSO2.stVal
4807		300:7		Yes					
4808		300:8	0					X100 (PSM) Connectors 10c-11nc-12no	LD0.XGGIO100.SPCSO3.stVal
4809		300:9		Yes					
4810		300:10	0					X100 (PSM) Connectors 13c-14no	LD0.XGGIO100.SPCSO4.stVal
4811		300:11		Yes					
4812		300:12	0					X100 (PSM) Connectors 15-17/18-19	LD0.XGGIO100.SPCSO5.stVal
4813		300:13		Yes					
4814		300:14	0					X100 (PSM) Connectors 20-22/23-24	LD0.XGGIO100.SPCSO6.stVal
4815		300:15		Yes					

# Section 2

## Modbus data mappings

**Table 182: XGGIO105 : BIO (X105) standard BO card (XGGIO105)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4392	274:8	0					X105 (BIO) Connectors 1-2	LD0.XGGIO105.Ind1.stVal
		274:9		Yes					
	4394	274:10	0					X105 (BIO) Connectors 3-4	LD0.XGGIO105.Ind2.stVal
		274:11		Yes					
	4396	274:12	0					X105 (BIO) Connectors 5-6c	LD0.XGGIO105.Ind3.stVal
		274:13		Yes					
	4398	274:14	0					X105 (BIO) Connectors 7-6c	LD0.XGGIO105.Ind4.stVal
		274:15		Yes					
	4400	275:0	0					X105 (BIO) Connectors 8-9c	LD0.XGGIO105.Ind5.stVal
		275:1		Yes					
	4402	275:2	0					X105 (BIO) Connectors 10-9c	LD0.XGGIO105.Ind6.stVal
		275:3		Yes					
	4404	275:4	0					X105 (BIO) Connectors 11-12c	LD0.XGGIO105.Ind7.stVal
		275:5		Yes					
	4406	275:6	2					X105 (BIO) Connectors 13-12c	LD0.XGGIO105.Ind8.stVal
		275:7		Yes					
4816		301:0	0					X105 (BIO) Connectors 14c-15no-16nc	LD0.XGGIO105.SPSCO1.stVal
4817		301:1		Yes					
4818		301:2	0					X105 (BIO) Connectors 17c-18no-19nc	LD0.XGGIO105.SPSCO2.stVal
4819		301:3		Yes					
4820		301:4	0					X105 (BIO) Connectors 20c-21no-22nc	LD0.XGGIO105.SPSCO3.stVal
4821		301:5		Yes					
4822		301:6	0					X105 (BIO) Connectors 23-24	LD0.XGGIO105.SPSCO4.stVal
4823		301:7		Yes					

**Table 183: XGGIO110 : BIO (X110) standard BO card (XGGIO110)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4408	275:8	0					X110 (BIO) Connectors 1-2	LD0.XGGIO110.Ind1.stVal
		275:9		Yes					
	4410	275:10	0					X110 (BIO) Connectors 3-4	LD0.XGGIO110.Ind2.stVal
		275:11		Yes					
	4412	275:12	0					X110 (BIO) Connectors 5-6c	LD0.XGGIO110.Ind3.stVal
		275:13		Yes					

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4414	275:14	0					X110 (BIO) Connectors 7-6c	LD0.XGGIO110.Ind4.stVal
		275:15		Yes					
	4416	276:0	0					X110 (BIO) Connectors 8-9c	LD0.XGGIO110.Ind5.stVal
		276:1		Yes					
	4418	276:2	0					X110 (BIO) Connectors 10-9c	LD0.XGGIO110.Ind6.stVal
		276:3		Yes					
	4420	276:4	0					X110 (BIO) Connectors 11-12c	LD0.XGGIO110.Ind7.stVal
		276:5		Yes					
	4422	276:6	0					X110 (BIO) Connectors 13-12c	LD0.XGGIO110.Ind8.stVal
		276:7		Yes					
4824		301:8	0					X110 (BIO) Connectors 14c-15no-16nc	LD0.XGGIO110.SPCSO1.stVal
4825		301:9		Yes					
4826		301:10	0					X110 (BIO) Connectors 17c-18no-19nc	LD0.XGGIO110.SPCSO2.stVal
4827		301:11		Yes					
4828		301:12	0					X110 (BIO) Connectors 20c-21no-22nc	LD0.XGGIO110.SPCSO3.stVal
4829		301:13		Yes					
4830		301:14	0					X110 (BIO) Connectors 23-24	LD0.XGGIO110.SPCSO4.stVal
4831		301:15		Yes					

Table 184: XBGGIO110 : BIO (X110) HSO card (XBGGIO110)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4360	272:8	0					X110 (BIO-H) Connectors 1-5c	LD0.XBGGIO110.Ind1.stVal
		272:9		Yes					
	4362	272:10	0					X110 (BIO-H) Connectors 2-5c	LD0.XBGGIO110.Ind2.stVal
		272:11		Yes					
	4364	272:12	0					X110 (BIO-H) Connectors 3-5c	LD0.XBGGIO110.Ind3.stVal
		272:13		Yes					
	4366	272:14	0					X110 (BIO-H) Connectors 4-5c	LD0.XBGGIO110.Ind4.stVal
		272:15		Yes					
	4368	273:0	0					X110 (BIO-H) Connectors 6-10c	LD0.XBGGIO110.Ind5.stVal
		273:1		Yes					

## Section 2 Modbus data mappings

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4370	273:2	0					X110 (BIO-H) Connectors 7-10c	LD0.XBGGIO110.Ind6.stVal
		273:3		Yes					
	4372	273:4	0					X110 (BIO-H) Connectors 8-10c	LD0.XBGGIO110.Ind7.stVal
		273:5		Yes					
	4374	273:6	0					X110 (BIO-H) Connectors 9-10c	LD0.XBGGIO110.Ind8.stVal
		273:7		Yes					
4790		299:6	0					X110 (BIO-H) Connectors 15no-16no	LD0.XBGGIO110.SPCSO1.stVal
4791		299:7		Yes					
4792		299:8	0					X110 (BIO-H) Connectors 19no-20no	LD0.XBGGIO110.SPCSO2.stVal
4793		299:9		Yes					
4794		299:10	0					X110 (BIO-H) Connectors 23no-24no	LD0.XBGGIO110.SPCSO3.stVal
4795		299:11		Yes					

**Table 185: XBGGIO115 : BIO (X115) standard BO card (XBGGIO115)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4376	273:8	0					X115 (BIO) Connectors 1-2	LD0.XBGGIO115.Ind1.stVal
		273:9		Yes					
	4378	273:10	0					X115 (BIO) Connectors 3-4	LD0.XBGGIO115.Ind2.stVal
		273:11		Yes					
	4380	273:12	0					X115 (BIO) Connectors 5-6c	LD0.XBGGIO115.Ind3.stVal
		273:13		Yes					
	4382	273:14	0					X115 (BIO) Connectors 7-6c	LD0.XBGGIO115.Ind4.stVal
		273:15		Yes					
	4384	274:0	0					X115 (BIO) Connectors 8-9c	LD0.XBGGIO115.Ind5.stVal
		274:1		Yes					
	4386	274:2	0					X115 (BIO) Connectors 10-9c	LD0.XBGGIO115.Ind6.stVal
		274:3		Yes					
	4388	274:4	0					X115 (BIO) Connectors 11-12c	LD0.XBGGIO115.Ind7.stVal
		274:5		Yes					
	4390	274:6	0					X115 (BIO) Connectors 13-12c	LD0.XBGGIO115.Ind8.stVal
		274:7		Yes					
4796		299:12	0					X115 (BIO) Connectors 14c-15no-16nc	LD0.XBGGIO115.SPCSO1.stVal

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
4797		299:13		Yes					
4798		299:14	0					X115 (BIO) Connectors 17c-18no-19nc	LD0.XHBGGIO115.SPCSO2.stVal
4799		299:15		Yes					
4800		300:0	0					X115 (BIO) Connectors 20c-21no-22nc	LD0.XHBGGIO115.SPCSO3.stVal
4801		300:1		Yes					
4802		300:2	0					X115 (BIO) Connectors 23-24	LD0.XHBGGIO115.SPCSO4.stVal
4803		300:3		Yes					

Table 186: XHBGGIO115 : BIO (X115) HSO card (XHBGGIO115)

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4460	278:12	0					X115 (BIO-H) Connectors 1-5c	LD0.XHBGGIO115.Ind1.stVal
		278:13		Yes					
	4462	278:14	0					X115 (BIO-H) Connectors 2-5c	LD0.XHBGGIO115.Ind2.stVal
		278:15		Yes					
	4464	279:0	0					X115 (BIO-H) Connectors 3-5c	LD0.XHBGGIO115.Ind3.stVal
		279:1		Yes					
	4466	279:2	0					X115 (BIO-H) Connectors 4-5c	LD0.XHBGGIO115.Ind4.stVal
		279:3		Yes					
	4468	279:4	0					X115 (BIO-H) Connectors 6-10c	LD0.XHBGGIO115.Ind5.stVal
		279:5		Yes					
	4470	279:6	0					X115 (BIO-H) Connectors 7-10c	LD0.XHBGGIO115.Ind6.stVal
		279:7		Yes					
	4472	279:8	0					X115 (BIO-H) Connectors 8-10c	LD0.XHBGGIO115.Ind7.stVal
		279:9		Yes					
	4474	279:10	0					X115 (BIO-H) Connectors 9-10c	LD0.XHBGGIO115.Ind8.stVal
		279:11		Yes					
4844		302:12	0					X115 (BIO-H) Connectors 15no-16no	LD0.XHBGGIO115.SPCSO1.stVal
4845		302:13		Yes					
4846		302:14	0					X115 (BIO-H) Connectors 19no-20no	LD0.XHBGGIO115.SPCSO2.stVal
4847		302:15		Yes					
4848		303:0	0					X115 (BIO-H) Connectors 23no-24no	LD0.XHBGGIO115.SPCSO3.stVal
4849		303:1		Yes					

Section 2  
Modbus data mappings

**Table 187: XGGIO120 : AIM (X120) 4CT+4BI (XGGIO120)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4424	276:8	0					X120 (AIM) Connectors 1-2c	LD0.XGGIO120.Ind1.stVal
		276:9		Yes					
	4426	276:10	0					X120 (AIM) Connectors 3-2c	LD0.XGGIO120.Ind2.stVal
		276:11		Yes					
	4428	276:12	0					X120 (AIM) Connectors 4-2c	LD0.XGGIO120.Ind3.stVal
		276:13		Yes					
	4430	276:14	0					X120 (AIM) Connectors 5-6	LD0.XGGIO120.Ind4.stVal
		276:15		Yes					

**Table 188: XGGIO120 : AIM (X120) 4CT+4BI with sensitive IO (XGGIO120)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4424	276:8	0					X120 (AIM) Connectors 1-2c	LD0.XGGIO120.Ind1.stVal
		276:9		Yes					
	4426	276:10	0					X120 (AIM) Connectors 3-2c	LD0.XGGIO120.Ind2.stVal
		276:11		Yes					
	4428	276:12	0					X120 (AIM) Connectors 4-2c	LD0.XGGIO120.Ind3.stVal
		276:13		Yes					
	4430	276:14	0					X120 (AIM) Connectors 5-6	LD0.XGGIO120.Ind4.stVal
		276:15		Yes					

**Table 189: XAGGIO130 : AIM (X130) 8VT (XAGGIO130)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4352	272:0	0					X130 (AIM) Connectors 1-2	LD0.XAGGIO130.Ind1.stVal
		272:1		Yes					
	4354	272:2	0					X130 (AIM) Connectors 3-4	LD0.XAGGIO130.Ind2.stVal
		272:3		Yes					
	4356	272:4	0					X130 (AIM) Connectors 5-6	LD0.XAGGIO130.Ind3.stVal
		272:5		Yes					
	4358	272:6	0					X130 (AIM) Connectors 7-8	LD0.XAGGIO130.Ind4.stVal
		272:7		Yes					

**Table 190: XGGIO130 : BIO (X130) card (XGGIO130)**

Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4432	277:0	0					X130 (BIO) Connectors 1-2c	LD0.XGGIO130.Ind1.stVal
		277:1		Yes					



Coil Addr (0x)	Input Addr (1x)	Register:(Bit) Addr (4x)	Dc	MCD	Type	Scale	Offset	Description	IEC61850 Data Attribute Name
	4434	277:2	0					X130 (BIO) Connectors 3-2c	LD0.XGGIO130.Ind2.stVal
		277:3		Yes					
	4436	277:4	0					X130 (BIO) Connectors 4-5c	LD0.XGGIO130.Ind3.stVal
		277:5		Yes					
	4438	277:6	0					X130 (BIO) Connectors 6-5c	LD0.XGGIO130.Ind4.stVal
		277:7		Yes					
	4440	277:8	0					X130 (BIO) Connectors 7-8c	LD0.XGGIO130.Ind5.stVal
		277:9		Yes					
	4442	277:10	0					X130 (BIO) Connectors 9-8c	LD0.XGGIO130.Ind6.stVal
		277:11		Yes					
4832		302:0	0					X130 (BIO) Connectors 10c-11no-12nc	LD0.XGGIO130.SPCSO1.stVal
4833		302:1		Yes					
4834		302:2	0					X130 (BIO) Connectors 13c-14no-15nc	LD0.XGGIO130.SPCSO2.stVal
4835		302:3		Yes					
4836		302:4	0					X130 (BIO) Connectors 16c-17no-18nc	LD0.XGGIO130.SPCSO3.stVal
4837		302:5		Yes					

Table 191: Control Structures

Control Structures	Control Register Addr	Control bit number	Description	IEC61850 Data Attribute Name
1	1000		Control Structure 1 Execute Register	
	1001		Control Structure 1 Password 1	
	1002		Control Structure 1 Password 2	
	1003	0	Protection LLN0 Clear indication LEDs and texts	LD0.LLN0.LEDRs1.Oper.ctlVal
	1003	1	Protection LLN0 Clear alarm LEDs	LD0.LLN0.LEDRs2.Oper.ctlVal
	1003	2	Protection LLN0 Reset all power quality data	LD0.LLN0.PQRs.Oper.ctlVal
	1003	3	52-1 Select Open Breaker 1	CTRL.CBCSWI1.Pos.Oper.ctlVal
	1003	4	52-1 Select Close Breaker 1	
	1003	5	52-1 Cancel Select Breaker 1	
	1003	6	52-1 Operate Select Breaker 1	
	1003	7	52-1 Direct Open Breaker 1	
	1003	8	52-1 Direct Close Breaker 1	
	1003	9	52-2 Select Open Breaker 2	CTRL.CBCSWI2.Pos.Oper.ctlVal

## Section 2 Modbus data mappings

Control Structures	Control Register Addr	Control bit number	Description	IEC61850 Data Attribute Name
	1003	10	52-2 Select Close Breaker 2	
	1003	11	52-2 Cancel Select Breaker 2	
	1003	12	52-2 Operate Select Breaker 2	
	1003	13	52-2 Direct Open Breaker 2	
	1003	14	52-2 Direct Close Breaker 2	
	1003	15	FLTMSTA1 Reset fault records	LD0.FLTMSTA1.RecRs.Oper.ctlVal
	1004		Control Structure 1 Confirmation Register	
2	1005		Control Structure 2 Execute Register	
	1006		Control Structure 2 Password 1	
	1007		Control Structure 2 Password 2	
	1008	0	Disturbance recorder Manual trigger for the disturbance recorder	DR.RDRE1.RcdTrg.Oper.ctlVal
	1008	1	Disturbance recorder Clear all DFR recordings in the memory	DR.RDRE1.MemClr.Oper.ctlVal
	1008	2	RESERVED	
	1008	3	RESERVED	
	1008	4	RESERVED	
	1008	5	RESERVED	
	1008	6	RESERVED	
	1008	7	RESERVED	
	1008	8	PQI-1 CMHA11 max.demands	LD0.CMHA11.RecRs.Oper.ctlVal
	1008	9	IA IB IC(1) CMMXU1 demands	LD0.CMSTA1.RecRs.Oper.ctlVal
	1008	10	IA IB IC(2) CMMXU2 demands	LD0.CMSTA2.RecRs.Oper.ctlVal
	1008	11	RESERVED	
	1008	12	PQSS-1 Recorded data reset	LD0.PH1QVVR1.RecRs.Oper.ctlVal
	1008	13	PQSS-1 Counters reset	LD0.PH1QVVR1.RsCnt.Oper.ctlVal
	1008	14	CFD CFD Reset	LD0.RCFD1.Rst.Oper.ctlVal
	1008	15	Physical device Reset of IED	LD0.LPHD1.RsDev.Oper.ctlVal
	1009		Control Structure 2 Confirmation Register	
3	1010		Control Structure 3 Execute Register	
	1011		Control Structure 3 Password 1	
	1012		Control Structure 3 Password 2	
	1013	0	79-1 79 all counters reset	LD0.DARREC1.RsCnt.Oper.ctlVal
	1013	1	79-1 79 reset to initial condition	LD0.DARREC1.RsRec.Oper.ctlVal
	1013	2	79-2 79-2 all counters reset	LD0.DARREC2.RsCnt.Oper.ctlVal
	1013	3	79-2 79-2 reset	LD0.DARREC2.RsRec.Oper.ctlVal
	1013	4	LoadProf Reset load profile record	LD0.LDPMSTA1.RecRs.Oper.ctlVal
	1013	5	RESERVED	
	1013	6	RESERVED	

Control Structures	Control Register Addr	Control bit number	Description	IEC61850 Data Attribute Name
	1013	7	RESERVED	
	1013	8	P E Reset of accumulated energy reading	LD0.PEMMTR1.SuDmdRs.Oper.ctlVal
	1013	9	RESERVED	
	1013	10	SP SE Reset of accumulated energy reading	LD0.SPEMMTR1.SuDmdRs.Oper.ctlVal
	1013	11	RESERVED	
	1013	12	PQVPH-1 CMHAI1 max.demands	LD0.VMHAI1.RecRs.Oper.ctlVal
	1013	13	PQVPH-2 CMHAI1 max.demands	LD0.VMHAI2.RecRs.Oper.ctlVal
	1013	14	49F Reset 49F temperature	LD0.T1PTTR1.RsTmp.Oper.ctlVal
	1013	15	RESERVED	
	1014		Control Structure 3 Confirmation Register	
4	1015		Control Structure 4 Execute Register	
	1016		Control Structure 4 Password 1	
	1017		Control Structure 4 Password 2	
	1018	0	CNTRL-1 Trig output 1 - SET	LD0.SPCGGIO1.SPCSO1.Oper.ctlVal
	1018	1	CNTRL-1 Trig output 1 - RESET	
	1018	2	CNTRL-1 Trig output 2 - SET	LD0.SPCGGIO1.SPCSO2.Oper.ctlVal
	1018	3	CNTRL-1 Trig output 2 - RESET	
	1018	4	CNTRL-1 Trig output 3 - SET	LD0.SPCGGIO1.SPCSO3.Oper.ctlVal
	1018	5	CNTRL-1 Trig output 3 - RESET	
	1018	6	CNTRL-1 Trig output 4 - SET	LD0.SPCGGIO1.SPCSO4.Oper.ctlVal
	1018	7	CNTRL-1 Trig output 4 - RESET	
	1018	8	CNTRL-1 Trig output 5 - SET	LD0.SPCGGIO1.SPCSO5.Oper.ctlVal
	1018	9	CNTRL-1 Trig output 5 - RESET	
	1018	10	CNTRL-1 Trig output 6 - SET	LD0.SPCGGIO1.SPCSO6.Oper.ctlVal
	1018	11	CNTRL-1 Trig output 6 - RESET	
	1018	12	CNTRL-1 Trig output 7 - SET	LD0.SPCGGIO1.SPCSO7.Oper.ctlVal
	1018	13	CNTRL-1 Trig output 7 - RESET	
	1018	14	CNTRL-1 Trig output 8 - SET	LD0.SPCGGIO1.SPCSO8.Oper.ctlVal
	1018	15	CNTRL-1 Trig output 8 - RESET	
	1019		Control Structure 4 Confirmation Register	
5	1020		Control Structure 5 Execute Register	
	1021		Control Structure 5 Password 1	
	1022		Control Structure 5 Password 2	
	1023	0	CNTRL-1 Trig output 9 - SET	LD0.SPCGGIO1.SPCSO9.Oper.ctlVal
	1023	1	CNTRL-1 Trig output 9 - RESET	
	1023	2	CNTRL-1 Trig output 10 - SET	LD0.SPCGGIO1.SPCSO10.Oper.ctlVal
	1023	3	CNTRL-1 Trig output 10 - RESET	
	1023	4	CNTRL-1 Trig output 11 - SET	LD0.SPCGGIO1.SPCSO11.Oper.ctlVal

## Section 2 Modbus data mappings

Control Structures	Control Register Addr	Control bit number	Description	IEC61850 Data Attribute Name
	1023	5	CNTRL-1 Trig output 11 - RESET	
	1023	6	CNTRL-1 Trig output 12 - SET	LD0.SPCGGIO1.SPCSO12.Oper.ctlVal
	1023	7	CNTRL-1 Trig output 12 - RESET	
	1023	8	CNTRL-1 Trig output 13 - SET	LD0.SPCGGIO1.SPCSO13.Oper.ctlVal
	1023	9	CNTRL-1 Trig output 13 - RESET	
	1023	10	CNTRL-1 Trig output 14 - SET	LD0.SPCGGIO1.SPCSO14.Oper.ctlVal
	1023	11	CNTRL-1 Trig output 14 - RESET	
	1023	12	CNTRL-1 Trig output 15 - SET	LD0.SPCGGIO1.SPCSO15.Oper.ctlVal
	1023	13	CNTRL-1 Trig output 15 - RESET	
	1023	14	CNTRL-1 Trig output 16 - SET	LD0.SPCGGIO1.SPCSO16.Oper.ctlVal
	1023	15	CNTRL-1 Trig output 16 - RESET	
	1024		Control Structure 5 Confirmation Register	
6	1025		Control Structure 6 Execute Register	
	1026		Control Structure 6 Password 1	
	1027		Control Structure 6 Password 2	
	1028	0	CNTRL-2 Trig output 1 - SET	LD0.SPCGGIO2.SPCSO1.Oper.ctlVal
	1028	1	CNTRL-2 Trig output 1 - RESET	
	1028	2	CNTRL-2 Trig output 2 - SET	LD0.SPCGGIO2.SPCSO2.Oper.ctlVal
	1028	3	CNTRL-2 Trig output 2 - RESET	
	1028	4	CNTRL-2 Trig output 3 - SET	LD0.SPCGGIO2.SPCSO3.Oper.ctlVal
	1028	5	CNTRL-2 Trig output 3 - RESET	
	1028	6	CNTRL-2 Trig output 4 - SET	LD0.SPCGGIO2.SPCSO4.Oper.ctlVal
	1028	7	CNTRL-2 Trig output 4 - RESET	
	1028	8	CNTRL-2 Trig output 5 - SET	LD0.SPCGGIO2.SPCSO5.Oper.ctlVal
	1028	9	CNTRL-2 Trig output 5 - RESET	
	1028	10	CNTRL-2 Trig output 6 - SET	LD0.SPCGGIO2.SPCSO6.Oper.ctlVal
	1028	11	CNTRL-2 Trig output 6 - RESET	
	1028	12	CNTRL-2 Trig output 7 - SET	LD0.SPCGGIO2.SPCSO7.Oper.ctlVal
	1028	13	CNTRL-2 Trig output 7 - RESET	
	1028	14	CNTRL-2 Trig output 8 - SET	LD0.SPCGGIO2.SPCSO8.Oper.ctlVal
	1028	15	CNTRL-2 Trig output 8 - RESET	
	1029		Control Structure 6 Confirmation Register	
7	1030		Control Structure 7 Execute Register	
	1031		Control Structure 7 Password 1	
	1032		Control Structure 7 Password 2	
	1033	0	CNTRL-2 Trig output 9 - SET	LD0.SPCGGIO2.SPCSO9.Oper.ctlVal
	1033	1	CNTRL-2 Trig output 9 - RESET	
	1033	2	CNTRL-2 Trig output 10 - SET	LD0.SPCGGIO2.SPCSO10.Oper.ctlVal

Control Structures	Control Register Addr	Control bit number	Description	IEC61850 Data Attribute Name
	1033	3	CNTRL-2 Trig output 10 - RESET	
	1033	4	CNTRL-2 Trig output 11 - SET	LD0.SPCGGIO2.SPCSO11.Oper.ctlVal
	1033	5	CNTRL-2 Trig output 11 - RESET	
	1033	6	CNTRL-2 Trig output 12 - SET	LD0.SPCGGIO2.SPCSO12.Oper.ctlVal
	1033	7	CNTRL-2 Trig output 12 - RESET	
	1033	8	CNTRL-2 Trig output 13 - SET	LD0.SPCGGIO2.SPCSO13.Oper.ctlVal
	1033	9	CNTRL-2 Trig output 13 - RESET	
	1033	10	CNTRL-2 Trig output 14 - SET	LD0.SPCGGIO2.SPCSO14.Oper.ctlVal
	1033	11	CNTRL-2 Trig output 14 - RESET	
	1033	12	CNTRL-2 Trig output 15 - SET	LD0.SPCGGIO2.SPCSO15.Oper.ctlVal
	1033	13	CNTRL-2 Trig output 15 - RESET	
	1033	14	CNTRL-2 Trig output 16 - SET	LD0.SPCGGIO2.SPCSO16.Oper.ctlVal
	1033	15	CNTRL-2 Trig output 16 - RESET	
	1034		Control Structure 7 Confirmation Register	
8	1035		Control Structure 8 Execute Register	
	1036		Control Structure 8 Password 1	
	1037		Control Structure 8 Password 2	
	1038	0	CNTRL-3 Trig output 1 - SET	LD0.SPCGGIO3.SPCSO1.Oper.ctlVal
	1038	1	CNTRL-3 Trig output 1 - RESET	
	1038	2	CNTRL-3 Trig output 2 - SET	LD0.SPCGGIO3.SPCSO2.Oper.ctlVal
	1038	3	CNTRL-3 Trig output 2 - RESET	
	1038	4	CNTRL-3 Trig output 3 - SET	LD0.SPCGGIO3.SPCSO3.Oper.ctlVal
	1038	5	CNTRL-3 Trig output 3 - RESET	
	1038	6	CNTRL-3 Trig output 4 - SET	LD0.SPCGGIO3.SPCSO4.Oper.ctlVal
	1038	7	CNTRL-3 Trig output 4 - RESET	
	1038	8	CNTRL-3 Trig output 5 - SET	LD0.SPCGGIO3.SPCSO5.Oper.ctlVal
	1038	9	CNTRL-3 Trig output 5 - RESET	
	1038	10	CNTRL-3 Trig output 6 - SET	LD0.SPCGGIO3.SPCSO6.Oper.ctlVal
	1038	11	CNTRL-3 Trig output 6 - RESET	
	1038	12	CNTRL-3 Trig output 7 - SET	LD0.SPCGGIO3.SPCSO7.Oper.ctlVal
	1038	13	CNTRL-3 Trig output 7 - RESET	
	1038	14	CNTRL-3 Trig output 8 - SET	LD0.SPCGGIO3.SPCSO8.Oper.ctlVal
	1038	15	CNTRL-3 Trig output 8 - RESET	
	1039		Control Structure 8 Confirmation Register	
9	1040		Control Structure 9 Execute Register	
	1041		Control Structure 9 Password 1	
	1042		Control Structure 9 Password 2	
	1043	0	CNTRL-3 Trig output 9 - SET	LD0.SPCGGIO3.SPCSO9.Oper.ctlVal

## Section 2 Modbus data mappings

Control Structures	Control Register Addr	Control bit number	Description	IEC61850 Data Attribute Name
	1043	1	CNTRL-3 Trig output 9 - RESET	
	1043	2	CNTRL-3 Trig output 10 - SET	LD0.SPCGGIO3.SPCSO10.Oper.ctlVal
	1043	3	CNTRL-3 Trig output 10 -RESET	
	1043	4	CNTRL-3 Trig output 11 - SET	LD0.SPCGGIO3.SPCSO11.Oper.ctlVal
	1043	5	CNTRL-3 Trig output 11 - RESET	
	1043	6	CNTRL-3 Trig output 12 - SET	LD0.SPCGGIO3.SPCSO12.Oper.ctlVal
	1043	7	CNTRL-3 Trig output 12 -RESET	
	1043	8	CNTRL-3 Trig output 13 - SET	LD0.SPCGGIO3.SPCSO13.Oper.ctlVal
	1043	9	CNTRL-3 Trig output 13 -RESET	
	1043	10	CNTRL-3 Trig output 14 - SET	LD0.SPCGGIO3.SPCSO14.Oper.ctlVal
	1043	11	CNTRL-3 Trig output 14 - RESET	
	1043	12	CNTRL-3 Trig output 15 - SET	LD0.SPCGGIO3.SPCSO15.Oper.ctlVal
	1043	13	CNTRL-3 Trig output 15 - RESET	
	1043	14	CNTRL-3 Trig output 16 - SET	LD0.SPCGGIO3.SPCSO16.Oper.ctlVal
	1043	15	CNTRL-3 Trig output 16 - RESET	
	1044		Control Structure 9 Confirmation Register	
10	1045		Control Structure 10 Execute Register	
	1046		Control Structure 10 Password 1	
	1047		Control Structure 10 Password 2	
	1048	0	RCNTRL-1 Output 1 - SET	LD0.SPCRGGIO1.SPCSO1.Oper.ctlVal
	1048	1	RCNTRL-1 Output 1 - RESET	
	1048	2	RCNTRL-1 Output 2 - SET	LD0.SPCRGGIO1.SPCSO2.Oper.ctlVal
	1048	3	RCNTRL-1 Output 2 - RESET	
	1048	4	RCNTRL-1 Output 3 - SET	LD0.SPCRGGIO1.SPCSO3.Oper.ctlVal
	1048	5	RCNTRL-1 Output 3 - RESET	
	1048	6	RCNTRL-1 Output 4 - SET	LD0.SPCRGGIO1.SPCSO4.Oper.ctlVal
	1048	7	RCNTRL-1 Output 4 - RESET	
	1048	8	RCNTRL-1 Output 5 - SET	LD0.SPCRGGIO1.SPCSO5.Oper.ctlVal
	1048	9	RCNTRL-1 Output 5 - RESET	
	1048	10	RCNTRL-1 Output 6 - SET	LD0.SPCRGGIO1.SPCSO6.Oper.ctlVal
	1048	11	RCNTRL-1 Output 6 - RESET	
	1048	12	RCNTRL-1 Output 7 - SET	LD0.SPCRGGIO1.SPCSO7.Oper.ctlVal
	1048	13	RCNTRL-1 Output 7 - RESET	
	1048	14	RCNTRL-1 Output 8 - SET	LD0.SPCRGGIO1.SPCSO8.Oper.ctlVal
	1048	15	RCNTRL-1 Output 8 - RESET	
	1049		Control Structure 10 Confirmation Register	
11	1050		Control Structure 11 Execute Register	
	1051		Control Structure 11 Password 1	

Control Structures	Control Register Addr	Control bit number	Description	IEC61850 Data Attribute Name
	1052		Control Structure 11 Password 2	
	1053	0	RCNTRL-1 Output 9 - SET	LD0.SPCRGGIO1.SPCSO9.Oper.ctlVal
	1053	1	RCNTRL-1 Output 9 - RESET	
	1053	2	RCNTRL-1 Output 10 - SET	LD0.SPCRGGIO1.SPCSO10.Oper.ctlVal
	1053	3	RCNTRL-1 Output 10 - RESET	
	1053	4	RCNTRL-1 Output 11 - SET	LD0.SPCRGGIO1.SPCSO11.Oper.ctlVal
	1053	5	RCNTRL-1 Output 11 - RESET	
	1053	6	RCNTRL-1 Output 12 - SET	LD0.SPCRGGIO1.SPCSO12.Oper.ctlVal
	1053	7	RCNTRL-1 Output 12 - RESET	
	1053	8	RCNTRL-1 Output 13 - SET	LD0.SPCRGGIO1.SPCSO13.Oper.ctlVal
	1053	9	RCNTRL-1 Output 13 - RESET	
	1053	10	RCNTRL-1 Output 14 - SET	LD0.SPCRGGIO1.SPCSO14.Oper.ctlVal
	1053	11	RCNTRL-1 Output 14 - RESET	
	1053	12	RCNTRL-1 Output 15 - SET	LD0.SPCRGGIO1.SPCSO15.Oper.ctlVal
	1053	13	RCNTRL-1 Output 15 - RESET	
	1053	14	RCNTRL-1 Output 16 -SET	LD0.SPCRGGIO1.SPCSO16.Oper.ctlVal
	1053	15	RCNTRL-1 Output 16 -RESET	
	1054		Control Structure 11 Confirmation Register	
12	1055		Control Structure 12 Execute Register	
	1056		Control Structure 12 Password 1	
	1057		Control Structure 12 Password 2	
	1058	0	SR-1 Resets Q1 output when set	LD0.SRGAPC1.Rs1.Oper.ctlVal
	1058	1	SR-1 Resets Q2 output when set	LD0.SRGAPC1.Rs2.Oper.ctlVal
	1058	2	SR-1 Resets Q3 output when set	LD0.SRGAPC1.Rs3.Oper.ctlVal
	1058	3	SR-1 Resets Q4 output when set	LD0.SRGAPC1.Rs4.Oper.ctlVal
	1058	4	SR-1 Resets Q5 output when set	LD0.SRGAPC1.Rs5.Oper.ctlVal
	1058	5	SR-1 Resets Q6 output when set	LD0.SRGAPC1.Rs6.Oper.ctlVal
	1058	6	SR-1 Resets Q7 output when set	LD0.SRGAPC1.Rs7.Oper.ctlVal
	1058	7	SR-1 Resets Q8 output when set	LD0.SRGAPC1.Rs8.Oper.ctlVal
	1058	8	SR-2 Resets Q1 output when set	LD0.SRGAPC2.Rs1.Oper.ctlVal
	1058	9	SR-2 Resets Q2 output when set	LD0.SRGAPC2.Rs2.Oper.ctlVal
	1058	10	SR-2 Resets Q3 output when set	LD0.SRGAPC2.Rs3.Oper.ctlVal
	1058	11	SR-2 Resets Q4 output when set	LD0.SRGAPC2.Rs4.Oper.ctlVal
	1058	12	SR-2 Resets Q5 output when set	LD0.SRGAPC2.Rs5.Oper.ctlVal
	1058	13	SR-2 Resets Q6 output when set	LD0.SRGAPC2.Rs6.Oper.ctlVal
	1058	14	SR-2 Resets Q7 output when set	LD0.SRGAPC2.Rs7.Oper.ctlVal
	1058	15	SR-2 Resets Q8 output when set	LD0.SRGAPC2.Rs8.Oper.ctlVal
	1059		Control Structure 12 Confirmation Register	

## Section 2 Modbus data mappings

Control Structures	Control Register Addr	Control bit number	Description	IEC61850 Data Attribute Name
13	1060		Control Structure 13 Execute Register	
	1061		Control Structure 13 Password 1	
	1062		Control Structure 13 Password 2	
	1063	0	SR-3 Resets Q1 output when set	LD0.SRGAPC3.Rs1.Oper.ctlVal
	1063	1	SR-3 Resets Q2 output when set	LD0.SRGAPC3.Rs2.Oper.ctlVal
	1063	2	SR-3 Resets Q3 output when set	LD0.SRGAPC3.Rs3.Oper.ctlVal
	1063	3	SR-3 Resets Q4 output when set	LD0.SRGAPC3.Rs4.Oper.ctlVal
	1063	4	SR-3 Resets Q5 output when set	LD0.SRGAPC3.Rs5.Oper.ctlVal
	1063	5	SR-3 Resets Q6 output when set	LD0.SRGAPC3.Rs6.Oper.ctlVal
	1063	6	SR-3 Resets Q7 output when set	LD0.SRGAPC3.Rs7.Oper.ctlVal
	1063	7	SR-3 Resets Q8 output when set	LD0.SRGAPC3.Rs8.Oper.ctlVal
	1063	8	SR-4 Resets Q1 output when set	LD0.SRGAPC4.Rs1.Oper.ctlVal
	1063	9	SR-4 Resets Q2 output when set	LD0.SRGAPC4.Rs2.Oper.ctlVal
	1063	10	SR-4 Resets Q3 output when set	LD0.SRGAPC4.Rs3.Oper.ctlVal
	1063	11	SR-4 Resets Q4 output when set	LD0.SRGAPC4.Rs4.Oper.ctlVal
	1063	12	SR-4 Resets Q5 output when set	LD0.SRGAPC4.Rs5.Oper.ctlVal
	1063	13	SR-4 Resets Q6 output when set	LD0.SRGAPC4.Rs6.Oper.ctlVal
	1063	14	SR-4 Resets Q7 output when set	LD0.SRGAPC4.Rs7.Oper.ctlVal
	1063	15	SR-4 Resets Q8 output when set	LD0.SRGAPC4.Rs8.Oper.ctlVal
1064		Control Structure 13 Confirmation Register		
14	1065		Control Structure 14 Execute Register	
	1066		Control Structure 14 Password 1	
	1067		Control Structure 14 Password 2	
	1068	0	52CM Resets accumulation energy	LD0.SSCBR1.RsAccAPwr.Oper.ctlVal
	1068	1	52CM Reset CB remaining life and operation counter	LD0.SSCBR1.RsCBWear.Oper.ctlVal
	1068	2	52CM Reset the charging time of the CB spring	LD0.SSCBR1.RsSprChaTm.Oper.ctlVal
	1068	3	52CM Reset CB closing and opening travel times	LD0.SSCBR1.RsTrvTm.Oper.ctlVal
	1068	4	52CM-2 Resets accumulation energy	LD0.SSCBR2.RsAccAPwr.Oper.ctlVal
	1068	5	52CM-2 Reset CB remaining life and operation counter	LD0.SSCBR2.RsCBWear.Oper.ctlVal
	1068	6	52CM-2 Reset the charging time of the CB spring	LD0.SSCBR2.RsSprChaTm.Oper.ctlVal
	1068	7	52CM-2 Reset CB closing and opening travel times	LD0.SSCBR2.RsTrvTm.Oper.ctlVal
	1068	8	RESERVED	
	1068	9	RESERVED	
	1068	10	RESERVED	
	1068	11	RESERVED	
	1068	12	86/94-1 Reset 86/94-1 lockout and latch	LD0.TRPPTRC1.LORs.Oper.ctlVal
	1068	13	86/94-1 Reset latched trip	LD0.TRPPTRC1.TrRs.Oper.ctlVal
	1068	14	86/94-2 Reset 86/94-2 lockout and latch	LD0.TRPPTRC2.LORs.Oper.ctlVal



Control Structures	Control Register Addr	Control bit number	Description	IEC61850 Data Attribute Name
	1068	15	RESERVED	
	1069		Control Structure 14 Confirmation Register	
15	1070		Control Structure 15 Execute Register	
	1071		Control Structure 15 Password 1	
	1072		Control Structure 15 Password 2	
	1073	0	86/94-2 Reset latched trip	LD0.TRPPTRC2.TrRs.Oper.ctlVal
	1073	1	86/94-3 Reset 86/94-3 lockout and latch	LD0.TRPPTRC3.LORs.Oper.ctlVal
	1073	2	86/94-3 Reset latched trip	LD0.TRPPTRC3.TrRs.Oper.ctlVal
	1073	3	CTR-1 Loads the counter to preset value	LD0.UDFCNT1.LodCnt.Oper.ctlVal
	1073	4	CTR-1 Resets counter value	LD0.UDFCNT1.RsCnt.Oper.ctlVal
	1073	5	CTR-2 Loads the counter to preset value	LD0.UDFCNT2.LodCnt.Oper.ctlVal
	1073	6	CTR-2 Resets counter value	LD0.UDFCNT2.RsCnt.Oper.ctlVal
	1073	7	CTR-3 Loads the counter to preset value	LD0.UDFCNT3.LodCnt.Oper.ctlVal
	1073	8	CTR-3 Resets counter value	LD0.UDFCNT3.RsCnt.Oper.ctlVal
	1073	9	CTR-4 Loads the counter to preset value	LD0.UDFCNT4.LodCnt.Oper.ctlVal
	1073	10	CTR-4 Resets counter value	LD0.UDFCNT4.RsCnt.Oper.ctlVal
	1073	11	CTR-5 Loads the counter to preset value	LD0.UDFCNT5.LodCnt.Oper.ctlVal
	1073	12	CTR-5 Resets counter value	LD0.UDFCNT5.RsCnt.Oper.ctlVal
	1073	13	CTR-6 Loads the counter to preset value	LD0.UDFCNT6.LodCnt.Oper.ctlVal
	1073	14	CTR-6 Resets counter value	LD0.UDFCNT6.RsCnt.Oper.ctlVal
	1073	15	CTR-7 Loads the counter to preset value	LD0.UDFCNT7.LodCnt.Oper.ctlVal
	1074		Control Structure 15 Confirmation Register	
16	1075		Control Structure 16 Execute Register	
	1076		Control Structure 16 Password 1	
	1077		Control Structure 16 Password 2	
	1078	0	CTR-7 Resets counter value	LD0.UDFCNT7.RsCnt.Oper.ctlVal
	1078	1	CTR-8 Loads the counter to preset value	LD0.UDFCNT8.LodCnt.Oper.ctlVal
	1078	2	CTR-8 Resets counter value	LD0.UDFCNT8.RsCnt.Oper.ctlVal
	1078	3	CTR-9 Loads the counter to preset value	LD0.UDFCNT9.LodCnt.Oper.ctlVal
	1078	4	CTR-9 Resets counter value	LD0.UDFCNT9.RsCnt.Oper.ctlVal
	1078	5	CTR-10 Loads the counter to preset value	LD0.UDFCNT10.LodCnt.Oper.ctlVal
	1078	6	CTR-10 Resets counter value	LD0.UDFCNT10.RsCnt.Oper.ctlVal
	1078	7	CTR-11 Loads the counter to preset value	LD0.UDFCNT11.LodCnt.Oper.ctlVal
	1078	8	CTR-11 Resets counter value	LD0.UDFCNT11.RsCnt.Oper.ctlVal
	1078	9	CTR-12 Loads the counter to preset value	LD0.UDFCNT12.LodCnt.Oper.ctlVal
	1078	10	CTR-12 Resets counter value	LD0.UDFCNT12.RsCnt.Oper.ctlVal
	1078	11	RESERVED	
	1078	12	RESERVED	

## Section 2 Modbus data mappings

---

Control Structures	Control Register Addr	Control bit number	Description	IEC61850 Data Attribute Name
	1078	13	RESERVED	
	1078	14	RESERVED	
	1078	15	RESERVED	
	1079		Control Structure 16 Confirmation Register	

---

## Section 3      Glossary

<b>AFL</b>	Application function block library
<b>ANSI</b>	American National Standards Institute
<b>AR</b>	Autoreclosing
<b>CB</b>	Circuit breaker
<b>CT</b>	Current transformer
<b>CTRL</b>	Control logical device
<b>DFR</b>	Digital fault recorder
<b>DNP3</b>	A distributed network protocol originally developed by Westronic. The DNP3 Users Group has the ownership of the protocol and assumes responsibility for its evolution.
<b>DR</b>	Disturbance recorder
<b>EMC</b>	Electromagnetic compatibility
<b>HMI</b>	Human-machine interface
<b>I/O</b>	Input/output
<b>ID</b>	Identifier or identification
<b>IEC 61850</b>	International standard for substation communication and modelling
<b>IED</b>	Intelligent electronic device
<b>LD0</b>	Logical device zero (0)
<b>LED</b>	Light-emitting diode
<b>LHMI</b>	Local human-machine interface
<b>LLN0</b>	Logical node zero (0)
<b>MCD</b>	Momentary change detect
<b>Modbus</b>	A serial communication protocol developed by the Modicon company in 1979. Originally used for communication in PLCs and RTU devices.
<b>MOM</b>	Momentary position
<b>PCM600</b>	Protection and Control IED Manager
<b>PLC</b>	Programmable logic controller
<b>SBO</b>	Select-before-operate

---

<b>stVal</b>	Status value
<b>SW</b>	Software
<b>UTC</b>	Coordinated universal time
<b>Val</b>	Value



# Contact us

**ABB Inc.**

**Distribution Automation**

4300 Coral Ridge Drive

Coral Springs, FL 33065, USA

Phone: +1 (800) 523-2620

Phone: +1 954-752-6700

Fax: +1 954 345-5329

[www.abb.com/substationautomation](http://www.abb.com/substationautomation)