



WEBINAR TRAINING , 10 SEP 2020

การออกแบบและเลือกใช้อุปกรณ์สับเปลี่ยนแหล่งจ่ายไฟอัตโนมัติ (ATS Solution by Breker and Switch)

Chindanai , Charnchanok (Product Marketing Team)



Agenda and The key takeaways

01 : Webinar



60 Minutes after this session start included Question



The key takeaways

- Standard of Automatic transfer switching equipment
- ATS Concept
- Common question
- ATS from ABB Switch Solution

About me

Product Marketing Team



Big

Chindanai Lertvirutchainun





5Y

Project and design engineer at ABB Low voltage system

5Y

Product Marketing at ABB Low voltage product

Main product take care



- Breaker for LV (SACE) : ACB ,MCCB
- Switch for LV (Stromberg) : SWD ,SWF ,Enclosed ,ATS



About me

Service Engineer Supervisor



Kor Charnchanok Thongprad



13Y Join in ABB Service team

ABB Electrification Products Certificate

- Level 3 Expert to service low voltage circuit breaker
- First line commissioning and service training Terra High Power Charger (HPC)
- ABB Ability EDCS
- Level 3 Expert in order to provide service on ;ABB's block contactors and softstarters



—

Standard

Standard

To design and select

Breaker type



IEC60947-2

Switch type





IEC60947-6-1

UL1008

ATS


- **ATS Concept**
- Common question
- Our solution
- About TruOne

ATS Concept



ATS Concept


1. Contactor
with relay monitoring



2. Breaker
with ATS Controller




3. Change-over switch
with Controller



ATS Concept

1. Contactor with relay monitoring




Point 😊

- Save cost
- Save space

Point ☹️

- No standard
- Transfer time
- Many cables
- Easy to mistake
- 2 Sources interrupt
-



ATS Concept

2. Breaker with ATS Controller




Point 😊

- Save cost .. ?
- Save space
- Protection completed
- Close transition addition

Point 😞

- Standard IEC60947-2
- Transfer time
- Many cables
- Easy to mistake
- 2 Sources interrupt
-



ATS Concept

3. Change-over switch with Controller




Point 😊

- Save space
- Transfer time guarantee
- Make sure 2 source s separate
- IEC60947-6 , UL1008 Standard
- Gen start ,stop ,exercise

Point ☹️

- Addition cost
- New technology
-



ATS


- ATS Concept
- **Common question**
- Our solution
- About TruOne

ATS Common question

1. Type


Open Transition

จ้งหาไป - กลับ ไฟหาย (Brake before make)




Close Transition

จ้งหาไปไฟหาย จ้งหากลับไฟไม่หาย (Make before Brake)



ATS with Bypass



ATS Common question

1. Type

แบบไหนดีกว่ากัน ?

- Open Transition
- Close Transition

???

ATS Common question

1. Type

ทำ Close Transition
ต้องระวังเรื่องอะไร ?

???

ATS Common question

1. Type

แล้วการใช้ Close Transition
ตอบโจทย์ทุกอย่างไหม ?

ทางแก้ไข ?

???


ATS Common question

1. Type

ทางแก้ไข ?

เพิ่ม UPS !!!

ติดต่อ น้องธีรภัท ได้ ขายอยู่




ATS Common question

2. Double throw switch

A **double-throw** switch has a contact that can be connected to either of two other contacts

หน้าสัมผัสปลายทางจะต่อแค่หนึ่งในสองของต้นทาง



Electronics specification and abbreviation	Expansion of abbreviation	Symbol
SPST	Single pole, single throw	
DPST	Double pole, single throw	
SPDT Form C ^[4]	Single pole, double throw	
DPDT	Double pole, double throw	

ABB Change-over เป็น Double throw ทุกๆตัว
ABB TruOne เป็น Double throw เหมือนกัน

ATS Common question

3. Utilization for ATS

Refer IEC standard (60947-3).

Switch, Switch disconnect ,Fuse connector type

AC-20	Connecting and disconnecting under no-load conditions	947-3
AC-21	Switching of resistive loads, including moderate loads	
AC-22	Switching of mixed resistive and inductive loads, including moderate overloads	
AC-23	Switching of motor loads or other highly inductive loads	

Refer IEC standard (60947-6).

Change-over switch ,ATS type

AC-31	Switching of resistive loads, including moderate loads	947-6
AC-32	Switching of mixed resistive and inductive loads, including moderate overloads	
AC-33	Switching of motor loads or other highly inductive loads	

ATS Common question

3. Utilization for ATS

Refer IEC standard

A Utilization categories

(Frequent Operation)

Table 9 – Number and duration of operating cycles for the electrical and mechanical operational performance tests for operation A utilization categories

Rated operational current I_e A	Duration of operating cycle min ^a	Number of operating cycles		
		Without current	With current	Total
$0 < I_e \leq 100$	1	–	6 000	6 000
$100 < I_e \leq 300$	1	–	6 000	6 000
$300 < I_e \leq 400$	1	–	4 000	4 000
$400 < I_e \leq 630$	1	1 000	2 000	3 000
$630 < I_e \leq 800$	1	1 000	2 000	3 000
$800 < I_e \leq 1\,600$	2	1 500	1 500	3 000
$1\,600 < I_e \leq 2\,500$	4	2 000	1 000	3 000
$2\,500 < I_e$	4	2 000	1 000	3 000

^a The duration of operating cycle may be reduced with the consent of the manufacturer.

B Utilization categories

(Infrequent Operation)

Table 10 – Number and duration of operating cycles for the electrical and mechanical operational performance tests for operation B utilization categories


Rated operational current I_e A	Duration of operating cycle min ^a	Number of operating cycles		
		Without current	With current	Total
$0 < I_e \leq 100$	1	4 500	1 500	6 000
$100 < I_e \leq 300$	1	5 000	1 000	6 000
$300 < I_e \leq 400$	1	3 000	1 000	4 000
$400 < I_e \leq 630$	1	2 000	1 000	3 000
$630 < I_e \leq 800$	1	2 500	500	3 000
$800 < I_e \leq 1\,600$	3	2 500	500	3 000
$1\,600 < I_e \leq 2\,500$	6	1 500	500	2 000
$2\,500 < I_e$	6	1 500	500	2 000

^a The duration of operating cycle may be reduced with the consent of the manufacturer.



ATS Common question

4. In-phase


Fast transfer **without In-Phase**



Different phase angle
Utility vs Gen



Fast transfer **with In-Phase**



ATS จะตรวจสอบความเหมาะสมก่อนสับเปลี่ยนแหล่งจ่าย

- มุมเฟสของแรงดัน และความถี่ที่เหมาะสมกัน
- ขนาดของแรงดัน และความถี่ที่เหมาะสมกัน

ATS Common question

5. ATS vs Auto Reclose



Auto Reclose or ATS จะเลือกออกแบบอย่างไร

Auto Reclose

ต้องการความสะดวกระยะเกิดไฟตกชั่วขณะ (ที่ยังอยู่ในขอบเขตเวลาที่ตั้งไว้) เพื่อสั่ง Breaker Close โดยไม่ต้องเดินมาที่หน้าตู้ไฟฟ้า

อุปกรณ์หลัก :

1. Breaker
2. Shunt closing
3. Under voltage release
4. Ready to close contact
5. Voltage measuring relay.



ATS (Breaker)

ต้องการควบคุมการสั่งการสับเปลี่ยนแหล่งจ่ายไฟ แบบอัตโนมัติ ระหว่าง 2 แหล่งจ่าย

อุปกรณ์หลัก :

1. Breaker x 2
2. ATS022
3. Interlock (Mechanical/Electrical)
4. Shunt closing
5. Shunt opening

ATS Common question


5. ATS vs Auto Reclose

ATS (Breaker) ตัวอย่างวงจร

Emax 2 ,E2.2 Fixed Horizontal

รายการที่	รหัสสินค้า	รายละเอียด	จำนวน
1	xxxxxxx	Breaker Emax2 รุ่น E2.2	2
2	2CDS271001R0064	S201M-C6	2
3	1SDA073725R1	Motor Charging Spring E2.2-E6.2 220-240V AC/DC	1
4	1SDA073687R1	Shunt Closing Release E1.2..E6.2 ,220-240V AC/DC	1
5	1SDA073674R1	Shunt Opening Release E1.2..E6.2 ,220-240V AC/DC	1
6	MIAF-E2.2-DT	Mechanical Interlock Type A Fixed E2.2	1
	1SDA073881R1	1 x Cable kit for interlock E1.2-E6.2 Horizontal	1
	1SDA073889R1	1 x Lever for mechanical interlock E2.2	2
	1SDA073895R1	2 x Type A - floor mounted E2.2-E6.2	2
7.1	1SCA116892R1001	ODPSE230C	1
7.2	AF09x2-VM4	Contactor set	1
	1SBL137001R1310	AF09-30-10-13 100-250V50/60HZ-DC Contactor	2
	1SBN030105T1000	VM4 Mechanical Interlock Unit	1
8	1SDA065524R1	ATS022 Controller	1

ราคารวมอุปกรณ์ (ไม่รวมราคาเบรกเกอร์)



ATS

- ATS Concept
- Common question
- **Our solution**
- About TruOne

Our ATS Solution

Product Type

	SWITCHES		CONTACTOR	CIRCUIT BREAKER	
					
	Compact ATS	TruONE ATS	AF contractors with relays	Emax 2 and Tmax XT with ATS021/ATS022	Embedded ATS
Current Range	From 40 to 125 A	From 200 to 1200 (UL) /1600(IEC) A	From 9 to 1650 A	From 16 to 6300 A	From 800 to 6300 A
Transfer Type	Delayed ¹⁾ : I-O-II	Open: I-II Delayed ¹⁾ : I-O-II In-phase monitor	Open: I-II Delayed ¹⁾ : I-O-II	Delayed ¹⁾ : I-O-II	Delayed ¹⁾ : I-O-II Closed: I-I+II-II Synchrocheck
Standard	IEC 60947-6-1 IEC 60947-3 GB/T14048.11	UL 1008 IEC 60947-6-1 GB/T14048.11	IEC/UL 60947-4-1 GB/T14048.4	UL1066, UL489 IEC 60947-2 GB14048.2	UL1066 IEC 60947-2 GB14048.2
AUTOMATIC TRANSFER SWITCH					

¹⁾ Delayed transition is also know as Open transition with stable OFF between positions I and II

Our ATS Solution

Enclosed Type



TruONE ATS
Enclosed



Zenith ZTX



Zenith ZTG



Zenith ZTS

Current Range

From 200 to 1600A

From 30 to 1200 A

From 40 to 3000 A

From 40 to 4000 A

Transfer Type

Delayed¹⁾: I-O-II
In-phase monitor

Open: I-II
In-phase monitor

Open: I-II
Delayed²⁾: I-O-II
In-phase monitor

Open: I-II
Delayed²⁾: I-O-II
Closed: I-I+II-II
Bypass withdrawable
In-phase monitor

Standard

IEC 60947-6-1

UL 1008

UL 1008
IEC 60947-6-1³⁾
GB/T14048.11³⁾

UL 1008
IEC 60947-6-1
GB/T14048.11

AUTOMATIC TRANSFER SWITCH

¹⁾ Zenith and TruONE are also known as power contactor based solutions in NEMA/UL market
²⁾ Delayed transition is also know as Open transition with stable OFF between positions I and II
³⁾ IEC 60947-6-1 and GB/T 14048.11 certification is available for the current range 1600...3000 A



Our ATS Portfolio (Focus on Switch)

IEC Standard																	
Series	40	60/ 63	80	100	125	160/200	250/315	400	500	630	800	1000	1250	1600	2000	2500	3200
ABB (Open) IEC (Delayed Transition)	Compact ATS (OTM_21D)					TruOne OXB_ Level2/Level3/Level4										OTM2000-3200+OMD300/800	



OTM...21D Types



OXB.... Types



OTM...+OMD Types

Our ATS Portfolio (Focus on Switch)

UL Standard																		
Series	40	60/ 63	80	100	125	160/200	250/315	400	500	630	800	1000	1200	1600	2000	2500	3200	4000
ABB (Open) UL Fast /InPhase transistion	TruOne OXA_Level3/Level4													ZTG/ZTS				



OXA.... Types



ZTG / ZTS
only loose part Types

Our ATS Portfolio (Focus on Switch)

UL Standard																		
Series	40	60/ 63	80	100	125	160/200	250/315	400	500	630	800	1000	1200	1600	2000	2500	3200	4000
ABB (Enclosed) UL Fast /InPhase transistion	30A..1200 ZTG with TruOne Inside													ZTG Traditional offer				



ZTG with TruOne inside



ZTG

Our ATS Portfolio (Focus on Switch)

UL Standard																		
Series	40	60/ 63	80	100	125	160/200	250/315	400	500	630	800	1000	1200	1600	2000	2500	3200	4000
ABB Enclosed Bypass & Closed	ZTS																	



ZTS

Our ATS Portfolio (Focus on Switch)

We're taking Zenith ATS performance to new heights.

**ZTG with
TruOne inside
30-1200A UL1008**



ZTG Series

General purpose commercial and industrial applications



ZTX Series

Residential and light commercial applications



ZTG Series

Standard (Open) or Delayed Transition – 1600 – 3000 A



ZTG Series

Service Entranced Rated

**ZTG with GE-
Zenith inside
>1200A UL1008
ZTS with GE-Zenith**



ZTS Series

Standard (Open), Delayed or Closed Transition



ZBTS

Bypass/Isolation



ZTE Series

Standard (Open), Delayed or Closed transition



ZBTE

Bypass/Isolation

ATS

- ATS Concept
- Common question
- Our solution
- **About TruOne**

TruOne

About it !!!



**Highlight
Feature**

**Standard
Feature**




TruOne

Standard Feature



Standard feature

- Open Transition (I – II)
- Delay Transition (I – 0 – II)



TruOne

Standard Feature



Standard

- IEC 60947-6
- UL 1008

Current range

- IEC : 200 – 1600A
- UL : 200 – 1200A

Standard feature

- Complete with controller and cable 1.5m
- Solenoid
- 3poles ,4poles
- Double throw
- Auto and Manual transfer
- LCD Display
- Voltage drop, pick-up setting range
- Frequency drop, pick-up setting range

TruOne

Highlight Feature



Highlight Feature



- Transfer time below **50ms**
- **In-phase** monitoring
- **Load shedding** function
- Programmable DI/DO
- Event log
- **Predictive maintenance** (Level 4 version)
- Harmonic measuring

Communication & Measuring




- Optional communication : Modbus ,Profibus ,Ethernet
- Optional **Cloud monitoring**
- Current ,Power ,VAR ,VA monitoring display (Level 4 version)

TruOne

Virtual HMI



<https://new.abb.com/low-voltage/launches/truone-ats/Virtual-HMI>



—

Q & Q

ABB on social media

Website: www.abb.co.th



Facebook: ABB Thailand



Line official: @askabb

