

# Thermal Mass Flowmeter FMT500-IG (Sensyflow iG)

for gas, smart

**Industrial<sup>IT</sup>**  
enabled™

- **Direct measurement of mass flow and gas temperature**
  - No additional pressure and temperature compensation required
- **Digital measured value processing with improved signal quality**
- **Wide measuring range up to 1:150 with high measuring accuracy**
  - Factory-calibrated, with (optional) DKD calibration certificate
- **Quick response time of less than 0.5 seconds**
- **Negligible pressure loss**
- **No moving parts, no wear, maintenance-free**
- **Defined, reproducible mounting position in the middle of the conduit**
  - Pipe components for DN25...DN200 (1"...8")
  - Weld-on adapters for larger diameters and square ducts
  - Reliable and convenient hot tap fittings
- **Compact device with back-lit display**
- **Remote version with separate wall housing**
- **Communication:**
  - PROFIBUS DPV1 or analog/HART signal
- **Diagnostic and alarm functions**
- **ATEX certificate up to Category 1 (Zone 0), including Categories 2 and 3 and Dust-Ex**



**HART**<sup>®</sup>  
FIELD COMMUNICATIONS PROTOCOL

**PROFI**<sup>®</sup>  
BUS

**Direct mass flow measurement**  
**Quick response time**  
**High accuracy**

**ABB**

## Description

FMT500-IG (Sensyflow iG) is a thermal flowmeter for gases. The measuring principle (hot-film anemometer) allows the direct determination of mass flow and gas temperature. Taking the standard density of the gases into consideration, the standard volume flow rate can be displayed without additional pressure and temperature compensation.

The compact version of the FMT500-IG (Sensyflow iG) metering system comprises a transducer with the complete evaluation electronics and a pipe component. In the remote version the transducer and the electronics wall housing are connected via a max. 25 m long cable. Depending on the version, the transducer provides the measuring signals either as PROFIBUS or as analog/HART signals. The unit is operated either remotely via PROFIBUS/HART communication or locally by using a magnetic pen.

The pipe component is available for nominal pipe sizes ranging from DN 25 to DN 200 and in various designs. It is also possible to install the transducer directly in square ducts or pipes with any diameter via a weld-on adapter.

## Measuring principle


For many years, thermal gas-mass flowmeters with analog design have been established as complete process measuring devices in the chemical industry. The digital FMT500-IG (Sensyflow iG) represents a logical step in the consequent development of this well-proven technology.

## Physics of measurement

Thermal flow metering procedures use different ways to evaluate the flow dependent cooling of a heated resistor as measuring signal. In a hotfilm anemometer with temperature difference control, the heated platinum resistor is maintained at a constant overtemperature in relation to an unheated platinum sensor inside the gas flow. The heating power required for maintaining the overtemperature depends directly on the flow rate and the material properties of the gas. With a known (and constant) gas composition the mass-flow can be determined by electronically evaluating the heater current/mass-flow curve without additional pressure and temperature compensation. When using the constant power method, the temperature difference is measured which results from a constant heating power and depends on the heat quantity dissipated by the gas mass flow as well. Together with the standard density of the gas this results directly in the standard volume flow. Considering the high measuring range dynamics of 1:150, an accuracy smaller than 1 % of the measuring value is achieved.

## The digital Sensyflow method

With the patented digital Sensyflow method there are now 4 signals available to the evaluation electronics. These include, besides the heating power, the temperatures of the fluid and the heated sensor, which can thus be used to compensate the temperature dependency on gas characteristics. By storing the gas data in the measuring system it is possible to calculate and perform an optimum adaptation at any operating time.



## Advantages of the digital concept

- By providing several primary and secondary signals these signals can be output in parallel via the fieldbus connection. This makes a gas temperature measurement unnecessary.
- Through the implementation of complete digital signal processing it is possible to adapt the sensor control and signal conditioning to the process. This means that it is possible to achieve optimum measuring dynamics at all times, even under changing operating conditions.
- The digital Sensyflow method is capable of providing a further enhanced measuring range.
- While controlling the heater power at the same time, the temperature measurement of the heating resistor sets a limit of this temperature. If errors occur in the system resulting in gas temperatures beyond the specification, the heating power is switched off and the device sends a substitute value with an additional warning signal. Both measures result in a significant prolongation of the service life for high-temperature operation and enhanced equipment safety for the user.
- The most significant application and cost advantage results from the diagnostic features of the digital Sensyflow. The functions provided allow for preventive maintenance of the measuring system and the equipment, as operating times, temperature peaks and loads in the system can be evaluated, stored, and reported. This leads to direct cost savings by preventing failures and equipment downtime.

## Typical applications

- Gas volume measurement in chemical industry and process technology
- Compressed air balancing
- Gas burner control systems
- Biogas and activation air measurement in sewage plants
- Gas measurement at air decomposers
- Hydrogen measurement in the process

## Overview of FMT500-IG measuring system

**FMT500-IG with display**  
(Compact version)



**FMT500-IG transducer and electronics unit**  
(Remote version)



**Pipe component 1 in wafer flange version**  
DN 40 to DN 200 / ANSI 1½" to 8"



**Pipe component 2 as partial measuring section**  
DN 25 to DN 50 / ANSI 1" to 2"



**Weld-on adapter**  
from DN 150

## Type overview

Type	FMT500-IG	FMT500-IG (Ex)
Application	Process engineering	
Explosion protection	Zone 2 / 22 optional	Certificate KEMA 03ATEX2100 ATEX II 1/2 G and II 2 D (Zone 0, 1, 21) FM/CSA Version under preparation
Components	– IG transducer as compact or remote version – Pipe component type 1 or 2 or weld-on adapter	
Nominal pipe sizes	– Pipe component type 1: wafer flange DN 40, 50, 80, 100, 150, 200 – ANSI 1½", 2", 3", 4", 6", 8" – Pipe component type 2: measuring section DN 25, 40, 50 – ANSI 1", 1½", 2" (Process connection: flanges according to DIN 2635 Form C, PN 40 resp. ANSI B 16.5 150lbs/300lbs – Weld-on adapter for square ducts and pipe diameters ≥150 mm	
Materials	1.4571, ceramic sensor (other materials on request)	
Measured gases	Gases and gas mixtures with known composition	

## Equipment and functions

- Graphic display, back-lit, 120 x 32 pixels (optional)
- Mass flow or standard volume flow measurement, digital or bargraph display indication (see p. 15 for available flow rate units)
- Totalizer function (adding counter) with Start/Stop, Reset and Preset function
- Gas temperature measurement
- 4 characteristic curves for different gases or pipe diameters (optional)
- Max./min. value storage of flow rate, gas and housing temperature
- Alarm and limit value functions
- Status and diagnostic signals
- Operating hour meter
- Simulation of measured values and status signals
- Password-protected input menus
- 4 display languages
- Local operation by using a magnetic pen
- FDT/DTM for parameter setting via SMART VISION or process control system (optional, HART-DTM under preparation)

## PROFIBUS communication, DPV1 version

- in acc. with PA profile 3.0, max. transmission rate 1.5 Mbaud, direct connection to an intrinsically safe PROFIBUS DP in the hazardous area is possible






## Signal inputs and outputs, analog/HART version

- HART communication via 4...20 mA analog signal
- Current output for flow rate value
- 2 open collector digital outputs, configurable as
  - frequency output for flow rate and gas temperature
  - pulse output for totalizer (adding counter)
  - contact output for limit values and alarms
- 2 digital inputs, configurable for/as
  - external change-over of characteristic curve
  - Totalizer start/stop or reset
  - frequency input for external signal transmitter
- 24 V DC output for input/output wiring or for transmitter supply (max. 100 mA, not for explosion-proof versions)


**Technical data**

Type	FMT500-IG	FMT500-IG (Ex)
Measuring ranges DN 25 DN 40 DN 50 DN 80 DN 100 DN 150 DN 200 up to 3000 mm (square ducts and larger diameters on request)	$q_{min}$ 0 (1.5) ... 0 (3) ... 0 (5) ... 0 (15) ... 0 (25) ... 0 (60) ... 0 (100) ... 0 (20,000) ... For air or nitrogen in kg/h (other gases on request)	$q_{max}$ 180 450 750 2,000 3,200 9,000 15,000 3,000,000 For air or nitrogen in kg/h (other gases on request)
		$q_{min}$ 0 (1.5) ... 0 (3) ... 0 (5) ... 0 (15) ... 0 (25) ... 0 (60) ... 0 (100) ... 0 (20,000) ... For air or nitrogen in kg/h (other gases on request)
	The above values are guide values for applications involving air under atmospheric conditions	
<b>Measured error</b> Air, nitrogen other gases	Under calibration conditions in the stated measuring range $\leq \pm 0.9\%$ of measured value $\pm 0.05\%$ of possible end value in this nominal size (s. meas. ranges) $\leq \pm 1.8\%$ of measured value $\pm 0.10\%$ of possible end value in this nominal size (s. meas. ranges) For special calibration on request	
<b>Repeatability error</b>	$< 0.2\%$ of measured value	
<b>Influence of medium temperature</b>	$< 0.05\%$ /K of measured value (depending on type of gas)	
<b>Influence of medium pressure</b>	typically $0.2\%/100$ kPa (/1 bar) of measured value (depending on type of gas)	
<b>Response time</b>	$T_{63} \leq 0.5$ s	$T_{63} = 2$ s
<b>Operating pressure</b>	$4 \times 10^6$ Pa (40 bar)	
<b>Operating temperature of medium (Transducer)</b>	Standard range: $-25...+150$ °C Extended range: $-25...+300$ °C	acc. to temperature classes of ATEX certificate max. $-20...+150$ °C
<b>Ambient temperature</b> <b>Evaluation electronics</b> <b>Without display</b> <b>With display</b>	$-25...+65$ °C $-25...+50$ °C	$-20...+50$ °C $-20...+50$ °C
	Other ambient temperatures on request	
<b>Storage temperature</b>	$-25...+85$ °C	
<b>Degree of protection</b>	IP 67 (IP 66 for remote transducer)	
<b>Recommended installation requirements</b>	According to DIN EN ISO 5167-1 Minimum inlet run $15 \times$ pipe diameter D, outlet run $5 \times$ pipe diameter D (see page 15)	
<b>Pressure loss</b> (logarithmic diagram)	$< 1.0$ kPa (10 mbar), typical value $0.1$ kPa (1 mbar)	
	<p style="text-align: center;">Z-18927</p>	
<b>Electrical power values</b>	Universal power supply unit: $110...230$ V AC/DC $\pm 10\%$ ( $f = 48...62$ Hz) Low-voltage power supply unit: $24$ V AC/DC $\pm 20\%$ ( $f = 48...62$ Hz)	
<b>Power dissipation</b>	20 VA, current consumption 800 mA, slow-blow fuse of at least 2 A required	
<b>Connections</b>	M20 x 1.5 or $\frac{1}{2}$ " NPT	
<b>Cable (remote version)</b>	Round signal cable with braided copper screen LIYCY $10 \times 0.5$ mm <sup>2</sup> Max. 25 m between transducer and electronics unit	
<b>Output signals</b>	EN 50170, acc. to PA profile 3.0	
PROFIBUS DPV1 version		
Analog/HART version		
Analog output	$0/4...20$ mA (+ 10 % overrange), load $< 600 \Omega$ electrically isolated	
Digital outputs	2 x passive optocoupler (approx. 100 mA) selectable as frequency, pulse, or contact output	
Digital inputs	2 x 24 V lin typ. 10 mA (low $< 2$ mA, high $> 10$ mA) frequency and contact input	
<b>Installation class</b>	Overvoltage category III, degree of pollution 2	

**Electrical connection of standard and Zone 2/22 versions**

<p><b>Connection area of compact version</b></p> <p>L / + Phase / + terminal N / - Neutral / - terminal PE Protective earthing</p> <p>Universal power supply unit 110...230 V AC/DC <math>\pm</math> 10 % or low-voltage power supply unit 24 V AC/DC <math>\pm</math> 20 %</p> <p>(Zone 2/22 version only with 24 V power supply unit)</p>	 <p>Power terminals</p> <p>PROFIBUS or analog/HART module</p>
<p><b>Connection area of remote version</b></p> <p>L / + Phase / + terminal N / - Neutral / - terminal PE Protective earthing</p> <p>Universal power supply unit 110...230 V AC/DC <math>\pm</math> 10 % or low-voltage power supply unit 24 V AC/DC <math>\pm</math> 20 %</p> <p>(Zone 2/22 version only with 24 V power supply)</p> <p>1:1 cable link from the terminal block in the remote housing to the sensor.</p>	 <p>Terminal cover</p> <p>Separator plate (HART version, only)</p> <p>Terminals for sensor cable connection</p> <p>Power terminals</p> <p>PROFIBUS or analog/HART module</p>
<p><b>Sensor connector housing</b></p> <p>Sensor PIN1...PIN10 Cable at least 9-wire Min. size 0.5 mm Max. cable length 25 m</p> <p>1:1 cable link on remote housing (PIN6 not used)</p>	 <p>Terminals for sensor cable connection</p>
<p><b>PROFIBUS module connection</b></p> <p>A PROFIBUS DPV1 in/out signal B PROFIBUS DPV1 in/out signal</p> <p><b>*) Annotation on terminating resistors:</b> The bus termination should only be activated by setting the respective jumpers if the device is the only bus station on this PROFIBUS branch.</p> <p><b>Note:</b> When disconnecting the PROFIBUS cable from the device, the entire PROFIBUS communication will be interrupted, due to the system properties. For details on an alternative solution see the version with DP M12 connector socket.</p>	 <p>Cable shield, capacitive, connected to PE</p> <p>PROFIBUS connector terminals A/B</p> <p>Jumper for PROFIBUS terminating resistor*)</p>
<p><b>Analog/HART module connection</b></p> <p>11 Cable shield 12 + I<sub>out</sub> analog output / HART 13 - I<sub>out</sub> analog output / HART 14 + 24 V DC for external power supply, max. 100 mA 15 GND 24 V (ground) 16 D<sub>out</sub> 1 17 D<sub>out</sub> 2 18 GND<sub>out</sub> (ground D<sub>out</sub> 1 + 2) 19 D<sub>in</sub> 1 20 D<sub>in</sub> 2 21 GND<sub>in</sub> (ground D<sub>in</sub> 1 + 2) 22 Cable shield</p>	

**Examples for connecting peripherals (analog/HART version)**



**PROFIBUS DPV1 version with DP M12 connector socket**


This version with PROFIBUS DP M12 connector socket allows disconnection of the device from the bus without interrupting PROFIBUS DP operation. Instead of the center cable gland an assembled and wired DP M12 connector socket is supplied.

For connection to the PROFIBUS DP line you need 1 T-piece, cable socket and plug (see accessories).

Protection type of the plug-in connections: IP 66


This device variant is only available for non-Ex compact versions.

Please refer to Data Sheet 10/63-6.44 EN (under preparation) for other versions of T-pieces and appropriate DP connector plugs.








**Pin assignment of the device**

- 1 + 5 V
- 2 PROFIBUS DPV1 line A (green)
- 3 GND
- 4 PROFIBUS DPV1 line B (red)
- 5 Cable shield / protective earth




DP M12 connector socket

**Electrical connection of ATEX versions for Category 1/2 G and 2 D (Zone 0/1/21)**

<p><b>Connection area of compact version</b></p> <p>L / + Phase/+ terminal N / - Neutral/- terminal PA Protective earthing</p> <p>Universal power supply unit 110...230 V AC/DC <math>\pm</math> 10 %, 20 VA 48...62 Hz or low-voltage power supply unit 24 V AC/DC <math>\pm</math> 20 %, 20 VA 48...62 Hz</p> <p>Explosion protection for power terminals: EEx e</p>	 <p>Terminal cover</p> <p>Power terminals</p> <p>PROFIBUS or analog/HART module</p>
<p><b>Connection area of remote version</b></p> <p>L / + Phase/+ terminal N / - Neutral/- terminal PE Protective earthing</p> <p>Universal power supply unit 110...230 V AC/DC <math>\pm</math> 10 %, 20 VA 48...62 Hz or low-voltage power supply unit 24 V AC/DC <math>\pm</math> 20 %, 0 VA 48...62 Hz</p> <p>1:1 cable link from the terminal block in the remote housing to the sensor.</p>	 <p>Terminal cover</p> <p>Separator plate (HART version, only)</p> <p>Power terminals</p> <p>Terminals for sensor cable connection</p> <p>PROFIBUS or analog/HART module</p>
<p><b>Sensor connector housing</b></p> <p>Explosion protection EEx ia Sensor PIN1...PIN10 Cable at least 9 wires Min. size 0.5 mm Max.cable length 25 m</p> <p>1:1 cable link on remote housing (PIN6 not used)</p>	 <p>Terminals for sensor cable connection</p>
<p><b>PROFIBUS module connection</b></p> <p>A PROFIBUS DPV1 in/out signal B PROFIBUS DPV1 in/out signal</p> <p>Type of explosion protection EEx ib</p> <p>May be connected to an intrinsically safe PROFIBUS DP, only.</p> <p>External bus termination in acc. with RS 485_IS specification.</p> <p>When connecting the fieldbus or signal cables observe the safety-related specifications in the KEMA 03ATEX2100 certificate.</p>	 <p>Cable shield connected to PA</p> <p>PROFIBUS connector terminals X2/X3 PIN A/B</p>
<p><b>Analog/HART module connection</b></p> <p>31 + I<sub>out</sub> analog output / HART 32 - I<sub>out</sub> analog output / HART 33 D<sub>out</sub> 1 34 GND<sub>out</sub> (ground D<sub>out</sub> 1) 35 D<sub>out</sub> 2 36 GND<sub>out</sub> (ground D<sub>out</sub> 2) 37 D<sub>in</sub> 1 38 GND<sub>in</sub> (ground D<sub>in</sub> 1) 39 D<sub>in</sub> 2 40 GND<sub>in</sub> (ground D<sub>in</sub> 2)</p> <p>Type of explosion protection EEx ib or EEx e</p> <p>When connecting the fieldbus or signal cables observe the safety-related specifications in the KEMA 03ATEX2100 certificate.</p>	



## Mounting in hazardous areas



Remote housing Zone 2/21	Remote sensor Housing Zone 1, sensor Zone 0	Compact version Housing Zone 1, sensor Zone 0
<p><b>Ex</b> II 3(1) G EEx nA [ia] [ib] IIC T4 II 2 D T 115 °C</p> <p>Ambient temperature: -20...+50 °C</p> <p>*) Optionally -40 °C for ambient temperature</p>	<p><b>Ex</b> II 1/2 G EEx ia IIC T4 II 2 D T 80 °C</p> <p>Housing and sensor Zone 1</p> <p><b>Ex</b> II 2 G EEx ia IIC T4...T1 II 2 D T 100 °C or 200 °C or 300 °C</p> <p>Ambient temperature: -20...+80 °C</p> <p>*) Optionally -40 °C for ambient temperature</p>	<p><b>Ex</b> II 1/2 G EEx de [ia] [ib] IIC T4 II 2 D T 115 °C</p> <p>Housing and sensor Zone 1</p> <p><b>Ex</b> II 2 G EEx de [ia] [ib] IIC T4...T1 II 2 D T 115 °C or 200 °C or 300 °C</p> <p>Ambient temperature: -20...+50 °C</p> <p>*) Optionally -40 °C for ambient temperature</p>

FMT500-IG (Sensyflow iG-Ex) compact version				
Gas	Surface temperature	Process temperature	Sensor	Electronics unit
T4	T 115 °C	-20...+ 80 °C	1G	2G, 2D
T4	T 115 °C	-20...+100 °C	2G	2G, 2D
T3	T 115 °C	-20...+100 °C	2G	2G, 2D
T2	T 200 °C <sup>1)</sup>	-20...+200 °C <sup>1)</sup>	2G	2G, 2D
T1	T 300 °C <sup>1)</sup>	-20...+300 °C <sup>1)</sup>	2G	2G, 2D
FMT500-IG (Sensyflow iG-Ex) remote housing				
Gas	Surface temperature			Electronics unit
T4	T115 °C			3G, 2D
FMT500-IG (Sensyflow iG-Ex) remote sensor				
Gas	Surface temperature	Process temperature	Sensor	Connection head
T4	T 80 °C	-20...+ 80 °C	1G	2G, 2D
T4	T 80 °C	-20...+100 °C	2G	2G, 2D
T3	T 100 °C	-20...+100 °C	2G	2G, 2D
T2	T 200 °C <sup>1)</sup>	-20...+200 °C <sup>1)</sup>	2G	2G, 2D
T1	T 300 °C <sup>1)</sup>	-20...+300 °C <sup>1)</sup>	2G	2G, 2D

<sup>1)</sup> Temperatures in accordance with ATEX temperature classes, max. process temperature for transducer -20...+150 °C

## Safety-related input and output specifications

### PROFIBUS DPV1 version

Output current circuit	U <sub>o</sub> = ± 3.72 V			
PROFIBUS DP	EEx ib IIC/IIB			
RS 485_IS interface	I <sub>o</sub>	P <sub>o</sub>	EEx ib IIC/IIB	
Terminals X2, X3	[mA]	[mW]	C' <sub>i</sub> [nF/km]	L'/R' <sub>i</sub> [μH/Ω]
PIN A/B	± 155	± 144.2	≤ 250	≤ 28.5
Minimum cable size 0.2 mm Max. input voltage U <sub>i</sub> : ± 4.20 V Max. input current I <sub>i</sub> : ± 2.66 A (Value for RS 485_IS interface in accordance with KEMA Ex certificate) Electrical isolation of the RS 485_IS PROFIBUS fieldbus signals A and B Cable shield is connected to PA				

### Analog/HART version

Output current circuit	Intrinsically safe EEx ib IIC/IIB				Not intrinsically safe U <sub>m</sub> = 60 V
Current output	U <sub>o</sub> = 17.2 V; U <sub>i</sub> = 30 V; I <sub>ij</sub> = 100 mA				U <sub>B</sub> = 30 V I <sub>B</sub> = 30 mA
Active	I <sub>o</sub>	P <sub>o</sub>	EEx ib IIC		
PIN 31 + 32	[mA]	[mW]	C <sub>i</sub> [nF]	L <sub>i</sub> [mH]	
	78.3	337	2.0	0.25	
Characteristic curve: linear Approved for connection to passive intrinsically safe current circuits, only PIN 32 is connected to PA					
Digital output	U <sub>i</sub> = 15 V I <sub>i</sub> = 30 mA P <sub>i</sub> = 115 mW		C <sub>i</sub> = 2.0 nF L <sub>i</sub> = 0.250 mH		U <sub>B</sub> = 30 V I <sub>B</sub> = 100 mA
Passive					
D <sub>out</sub> 1: PIN 33 + 34					
D <sub>out</sub> 2: PIN 35 + 36					
Digital input	U <sub>i</sub> = 30 V I <sub>i</sub> = 250 mA P <sub>i</sub> = 1.1 W		C <sub>i</sub> = 2.0 nF L <sub>i</sub> = 0.250 mH		U <sub>B</sub> = 30 V I <sub>B</sub> = 100 mA
Passive					
D <sub>in</sub> 1: PIN 37 + 38					
D <sub>in</sub> 2: PIN 39 + 40					

### Special requirements:

The output current circuits are designed such that they can be connected to either intrinsically safe or not intrinsically safe current circuits. However, intrinsically safe and not intrinsically safe circuits must **not** be mixed or combined.

The rated voltage of not intrinsically safe current circuits is U<sub>m</sub> = 60 V.

- Make sure that the cover of the power terminal box is always closed properly. When using the device with intrinsically safe output current circuits it is permissible to open the terminal box.

- It is recommended to use the enclosed cable glands for the output current circuits, according the type of explosion protection: intrinsically safe = blue; not intrinsically safe = black.
- The transducer and the transmitter housing must be connected to an equipotential bonding system. When using intrinsically safe current outputs proper equipotential bonding must be ensured along the current circuits.
- Make sure that the measuring pipe materials are resistant to possible corrosive substances in the measured medium.



#### Notice:

The values indicated here have been taken out of the approval certificate. Always observe the specifications and supplements in the ATEX certificate.

**Do not open the front cover of the housing in the hazardous area!**

**Always observe the safety specifications in the operating instruction for all device versions!**

## Communication

### HART

The HART protocol is used for digital communication between a process control system/PC, a hand-held terminal and a field instrument. All parameters related to the device or measuring point can be transferred from the transmitter to the process control system or PC. Also, the transmitter can be re-configured in this way.

Digital communication is realized by modulating an AC signal upon the analog output (4...20 mA). This signal does not affect the connected evaluation units.

DSV401 (SMART VISION) - a universal communication program for smart field instruments using the FDT/DTM technology - is the appropriate operation and configuration tool. Various communication methods allow for data exchange with the entire range of field instruments. This program is mainly designed for parameter display, configuration, diagnostics and data management of all smart field instruments meeting the communication requirements.

Basic features like the upper range value or some flow rate units can be configured by using the universal HART DTM. The full functionality will be available with the FMT500-IG HART DTM (under preparation).

### Transmission method


FSK modulation on the 4...20 mA current output (+ overrange) acc. to Bell 202 Standard. Max. signal amplitude 1.2 mA<sub>pp</sub>.

### Load

Min. 250 Ω, max. 600 Ω  
Max. cable length 1500 m AWG 24, twisted, shielded

### Baud rate

1200 bauds  
Indication of logical1: 1200 Hz  
Indication of logical 0: 2200 Hz



## PROFIBUS DPV1

Bus communication of the thermal gas mass flowmeter FMT500-IG (Sensyflow iG) with PROFIBUS interface is based on the "Profile For Process Control Devices" Version 3.0 (PA Profile 3.0) as of October 1999. PROFIBUS DP (RS 485 type transmission) is used for bus coupling. Acyclic PROFIBUS DPV1 services are supported.

### PROFIBUS interface parameters


- DPV1 communication without alarms
- Support of C1 and C2 masters
- Max. transmission rate: 1.5 Mbauds
- ID number: 0x05CA
- GSD file name: ABB\_05CA.GSD

The cables for PROFIBUS connection must meet the following requirements to comply with PROFIBUS Specification EN50170 Part 8-2:


Parameter	DP, line type A, shielded
Surge impedance in Ω	135...165 at a frequency of 3...20 MHz
Operating capacity	(pF/m) 30
Loop resistance (Ω/km)	≤ 110
Solid conductor	AWG 22/1
Flexible conductor	> 0.32 mm <sup>2</sup>

Parameter setting and configuration are possible by using the SMART VISION program and the PROFIBUS-DTM FMT500-IG, similar to analog/HART communication.

Direct connection to intrinsically safe PROFIBUS DP lines (see the illustration below) is permissible under the proviso that approved device models are used and the safety specifications and safety-related parameters in accordance with KEMA 03ATEX2100 are observed. The cable length and possible number of Ex bus nodes depend on the Ex barrier used.



**Dimensional drawings** (dimensions in mm)



**PN 40**

Nom. size		L2	h	D1	d1	d2	D4	L3	L4	L5
DN 25	B1 = 125	269	263	–	28.5	–	115	600	486	–
DN 40	B2 = 80			94	43.1	88	150	860	731	–
DN 50	B3 = Ø115			109	54.5	102	165	1000	837	–
DN 80	B4 = 58			144	82.5	138	–	–	–	–
DN 100	K1 = 150			170	107.1	162	–	–	–	–
DN 150	K3 = 206			226	159.3	218	–	–	–	450
DN 200	L1 = 188			293	206.5	285	–	–	–	
> 350	L6 = 310	431	425							
> 700	M1 = 208	781	775							
	M2 = 265									
	M3 = 139									

**ANSI 150 lb, Sch 40 S**

ANSI 1"	B1 = 125	269	263	–	26.6	–	108	560	454	–
ANSI 1½"	B2 = 80			85	40.9	73	127	864	741	–
ANSI 2"	B3 = Ø115			103	52.6	92	154	1003	846	–
ANSI 3"	B4 = 58			135	78.0	127	–	–	–	–
ANSI 4"	K1 = 150			173	102.4	157	–	–	–	–
ANSI 6"	K3 = 206			221	154.2	216	–	–	–	450
ANSI 8"	L1 = 188			278	202.7	270	–	–	–	
ANSI 8"	L6 = 310									
> ANSI 14"	M1 = 208	431	425							
> ANSI 14"	M2 = 265									
> ANSI 28"	M3 = 139	781	775							

**ANSI 300 lb, Sch 40 S**

ANSI 1"	B1 = 125	269	263	–	26.6	–	123.9	560	454	–
ANSI 1½"	B2 = 80			94	40.9	73	155.4	864	741	–
ANSI 2"	B3 = Ø115			110	52.6	92	165.1	1003	846	–
ANSI 3"	B4 = 58			148	78.0	127	–	–	–	–
ANSI 4"	K1 = 150			180	102.4	157	–	–	–	–
ANSI 6"	K3 = 206			249	154.2	216	–	–	–	450
ANSI 8"	L1 = 188			307	202.7	270	–	–	–	
ANSI 8"	L6 = 310									
> ANSI 14"	M1 = 208	431	425							
> ANSI 14"	M2 = 265									
> ANSI 28"	M3 = 139	781	775							

**Weld-on adapter for FMT500-IG (Sensyflow iG)**

(1) Centering pin on outlet run side

Sealing ring groove

Weld-on adapter (upon delivery)

Connection flange DN 25

h

L

min. 28 mm

Ø d

Ø D

← Direction of flow

Z-189341

450 mm

Ø 33,7

Z-189342

**Required accuracy of mounting**  
Centric mounting <math>\pm 2\text{ mm}</math>  
Twist <math>< \pm 2^\circ</math>

Length h of the transducer (in mm)	Min./max. outer pipe diameter (in mm)
263	100...350
425	> 350...700
775	> 700...1400*

\* This maximum pipe diameter specification is only valid when installing the sensor centrally in the pipe. For larger diameters or angular ducts a non-centric sensor position is assumed for calibration.

**Weld-on adapter with ball valve for FMT500-IG (Sensyflow iG)**

Sealing ring groove

Weld-on adapter (upon delivery)

Connection flange DN 25

h

L

min. 28 mm

Ø d

Ø D

← Direction of flow

Z-20233

(1) Centering pin on outlet run side  
(2) Ball valve DN 40  
D Pipe diameter (outside)

540 mm

Ø 33,7

**Required accuracy of mounting**  
Centric mounting <math>\pm 2\text{ mm}</math>  
Twist <math>\pm 2^\circ</math>


Length h of the transducer (in mm)	Min./max. outer pipe diameter (in mm)
263	100...150
425	> 150...500
775	> 500...1150*

\* This maximum pipe diameter specification is only valid when installing the sensor centrally in the pipe. For larger diameters or angular ducts a non-centric sensor position is assumed for calibration.

**Note:**


Prior to mounting the weld-on adapters must be shortened to length  $L = h - 1/2 D_{\text{outer}}$   
The distance h between the upper flange edge and the pipe center line must be within a tolerance of  $\pm 2\text{ mm}$ .  
The right angle to the pipe center line must be observed (max. tolerance  $\pm 2^\circ$ )  
The centering pin of the adapter must be aligned centrally with the pipe center line in flow direction (on outlet run side, downstream of the measuring point).

**Integrated hot tap fitting for FMT500-IG (compact and remote versions)**



The integrated hot tap fitting is used instead of the pipe component and weld-on adapter assembly described above if the sensor must be exchangeable during operation with virtually no gas escaping from the system.

It is recommended to use the hot tap fitting for measurements in main conduits (e.g. compressed air systems) or for measuring points which otherwise require rinsing prior to removing the sensor. As a rule, hot tap fittings should be preferred for all systems where, otherwise, the entire system or parts of it must be switched off to replace a sensor.










Maximum pressure/temperature values for the integrated hot tap fitting

**Handling:**

The transmitter in a compact or remote version is screwed to the hot tap fitting through the DN 25 flange. Then the cover is put on. The sensor is set from the exchange position to the measuring position by turning the spigot nut. The bottom edge of the spigot nut indicates the current sensor position (see Detail A, sensor is in exchange position). Only when the measuring position 50 - OPEN-MESSEN (lower stop of the spigot nut) is reached, the sensor is placed exactly in the center of the pipe and exact measurement is ensured.

**Recommended steadying lengths according to DIN EN ISO 5167-1**

	
	<p>Expansion X = 15</p>
	<p>Reducer X = 15</p>
	<p>90° elbow X = 20</p>
	<p>Two 90° elbows in one level X = 25</p>
	<p>Two 90° elbows in two levels X = 40</p>
	<p>Valve/slide X = 50</p>

To achieve the stated measuring accuracy, the steadying lengths seen above must be provided. For combinations of inlet run disturbances, e. g. valve and reducer, you must always consider the longer inlet run length. In confined spaces at the mounting location the outlet run length can be shortened to 3 x D. The reduction of the minimum inlet run length, however, will impact on the achievable accuracy.

High repeatability of the measuring value is still provided. Under certain circumstances, special calibration can be performed for insufficient steadying lengths. For this purpose and in individual cases, consult the DKD Calibration Department at Alzenau. For gases with extremely low density (hydrogen, helium) the steadying lengths must be doubled.

## Ordering information

		Catalog No.									
<b>Transducer FMT500-IG (Sensyflow iG, iG-Ex)</b>		<b>V14224-</b>									
<b>Versions</b>											
Standard	-25...+150 °C	1									
High-temperature version	-25...+300 °C	2									
ATEX version for Zone 2 / 22 <sup>1)</sup>	-25...+150 °C	3									
ATEX version for Zone 1 / 21	-20...+150 °C max. <sup>2)</sup>	4									
ATEX version for Zone 0 / 21	-20...+ 80 °C	5									
<b>Medium</b>											
Gases and gas mixtures, natural gas without DVGW certificate		A									
Oxygen with O <sub>2</sub> certificate		B									
DVGW certificate for natural gas		C									
H <sub>2</sub> , He (1.5 MPa max.; always with process gas calibration) <sup>3)</sup>		D									
<b>Sensor unit</b>											
Standard ceramic sensor		1									
<b>Material 1.4571</b>											
Mounting length	263 mm (DN 25... DN 350) <sup>4)</sup>	1									
Mounting length	425 mm (> DN 350...DN 700) <sup>4)</sup>	2									
Mounting length	775 mm (> DN 700) <sup>4)</sup>	3									
<b>Power supply</b>											
Universal power supply: 110...230 V AC/DC ± 10% (f = 48...62 Hz)		1									
Low-voltage power supply: 24 V AC/DC ± 20% (f = 48...62 Hz)		2									
<b>Designs</b>											
Compact design, without display, controlled via interface (under preparation)		0									
Compact design, controlled via magnetic pen and keypad		1									
Remote version w. display, controlled via magnetic pen and keypad (f. cables s. accessories) <sup>5)</sup>		2									
<b>Communication</b>											
Analog signal / HART						1					
PROFIBUS DPV1, direct connection of bus cable						2					
PROFIBUS DPV1, with DP M12 connector socket (for non-Ex compact versions, only)						3					
<b>Cable glands (enclosed)</b>											
Metric, M20 x 1.5						1					
½" NPT						2					
<b>Number of characteristics</b>											
1 characteristic								1			
2 characteristics								2			
3 characteristics								3			
4 characteristics								4			
<b>Calibration certificate</b>											
Factory certificate								0			
DKD certificate for calibration with air (in in-house calibration lab.)								1			
(DKD calibration office No. 05701, PTB-approved) (not for process gas calibration)											
<b>Material certificate</b>											
Without								0			
3.1 B certificate								1			
<b>Accessories</b>											
		Catalog No.									
<b>Special cable between transducer and evaluation unit</b>											
Ready-made, for remote version only											
Cable length 5 m		7962844									
Cable length 15 m		7962845									
Cable length 25 m		7962846									
PROFIBUS DP-T connector plug		7962847									
PROFIBUS DP socket, for customizing the bus cable		7962848									
PROFIBUS DP connector, for customizing the bus cable		7962849									
For T-pieces and DP connectors see data sheet 10/63-6.44 EN (t.b.p.)											
PROFIBUS DTM		9820088									
PROFIBUS PDM (Siemens)		on request									
HART DTM (under preparation)		on request									

<sup>1)</sup> only with low-voltage power supply

<sup>2)</sup> depending on temperature class T4...T1, for T4/T3 max. 100 °C, max. gas temperature 150 °C

<sup>3)</sup> process gas calibration for other gases / gas mixtures on request

<sup>4)</sup> nominal size ranges when using pipe components or weld-on adapters without ball valve

<sup>5)</sup> with ATEX versions: wall housing with operating electronics, can be mounted in Ex zone 2



**Ordering information**

	Catalog No.				Code		
<b>Pipe component design 1 for FMT500-IG (Sensyflow iG) wafer flange version</b>	<b>V14232-</b>						
<b>PN 40, material stainless steel 1.4571 (316Ti) Inner diameter (mm)</b>							
Nominal size DN 40 43.1	1	2	0				
Nominal size DN 50 54.5	1	3	0				
Nominal size DN 80 82.5	1	4	0				
Nominal size DN 100 107.1	1	5	0				
Nominal size DN 150 159.3	1	6	0				
Nominal size DN 200 206.5	1	7	0				
<b>ANSI 150 lb, Sch 40 S, material stainless steel 1.4571 (316Ti)</b>							
Nominal size ANSI 1 1/2" 40.9	2	B	0				
Nominal size ANSI 2" 52.6	2	C	0				
Nominal size ANSI 3" 78.0	2	D	0				
Nominal size ANSI 4" 102.4	2	E	0				
Nominal size ANSI 6" 154.2	2	F	0				
Nominal size ANSI 8" 202.7	2	G	0				
<b>ANSI 300 lb, Sch 40 S, material stainless steel 1.4571 (316Ti)</b>							
Nominal size ANSI 1 1/2" 40.9	3	B	0				
Nominal size ANSI 2" 52.6	3	C	0				
Nominal size ANSI 3" 78.0	3	D	0				
Nominal size ANSI 4" 102.4	3	E	0				
Nominal size ANSI 6" 154.2	3	F	0				
Nominal size ANSI 8" 202.7	3	G	0				
<b>Ball valve or hot tap fitting</b>							
without					0		
Pipe component with ball valve for pressureless applications, non gas-tight material stainless steel 1.4571 (316Ti)					1		
Pipe component with integrated hot tap fitting for nominal size DN 50 or DN 80 (ANSI 2"/3") and transducer of 263 mm, for pressure applications up to 16 bars and gas-tight applications, material stainless steel 1.4571 (316Ti), flanges PN 40					4		
Pipe component with integrated hot tap fitting for nominal size DN 100 or DN 150 (ANSI 4"/6") and transducer of 425 mm, for pressure applications up to 16 bars and gas-tight applications, material stainless steel 1.4571 (316Ti), flanges PN 40					5		
<b>Additional ordering information</b>							
					Code		
3.1 B Certificate, material certificate (only for pipe component)					30A		

**Ordering information**

	Catalog No.	Code		
<b>Pipe component design 2 for FMT500-IG (Sensyflow iG) partial measuring section</b>	<b>V14233-</b>			
<b>PN 40, material stainless steel 1.4571 (316Ti)</b> (flange shape C according to DIN 2635)				
Nominal size DN 25 <sup>1)</sup> Inner Ø 28.5	1	1	0	
Nominal size DN 40 43.1	1	2	0	
Nominal size DN 50 54.5	1	3	0	
<b>ANSI 150 lb, Sch 40 S, material stainless steel 1.4571 (316Ti)</b>				
Nominal size ANSI 1" <sup>1)</sup> Inner Ø 26.6	2	A	0	
Nominal size ANSI 1 1/2" 40.9	2	B	0	
Nominal size ANSI 2" 54.6	2	C	0	
<b>ANSI 300 lb, Sch 40 S, material stainless steel 1.4571 (316Ti)</b>				
Nominal size ANSI 1" <sup>1)</sup> Inner Ø 26.6	3	A	0	
Nominal size ANSI 1 1/2" 40.9	3	B	0	
Nominal size ANSI 2" 54.6	3	C	0	
<b>Additional ordering information</b>				
		Code		
3.1 B Certificate, material certificate (only for pipe component)		30A		
<b>Ordering information</b>				
	Catalog No.			
<b>Weld-on adapter PN 40 for FMT500-IG (Sensyflow iG)</b> recommended from DN 150				
<b>Material</b> stainless steel 1.4571 (316Ti) 1.0037	14237-7962500 14237-7962502			
<b>Weld-on adapter with ball valve/hot tap fitting for FMT500-IG (Sensyflow iG), material stainless steel 1.4571 (316Ti)</b> Weld-on adapter with ball valve for pressureless, non gas-tight applications.	14237-7962832			
Weld-on adapter with integrated hot tap fitting for nominal size DN 100 to DN 125/ANSI 4" to 5" and transducers of 425 mm, for pressure applic. up to 16 bars and gas-tight applic., material 1.4571	14237-7964131			
Weld-on adapter with integrated hot tap fitting for nominal size DN 150 to DN 300/ANSI 6" to 12" and transducers of 425 mm, for pressure applic. up to 16 bars and gas-tight applic., material 1.4571	14237-7964132			
<b>Special pipe component for transducer iG</b> on request Description:"....." "....."	14237-7962767			
3.1 B Certificate, material certificate (only for pipe component)	on request			

<sup>1)</sup> In order to achieve the specified measuring accuracy, the calibration of the transducer must be performed in the original pipe component DN 25/1". If the transducer needs to be re-calibrated, it must be submitted together with the same pipe component.

### Additional ordering information for calibration

	Characteristic 1	Characteristic 2	Characteristic 3	Characteristic 4
Code-No. <sup>1)</sup> Name of gas	511	521	531	541
Gas component 1 Vol %				
Gas component 2 Vol %				
Gas component 3 Vol %				
Gas component 4 Vol %				
Gas component 5 Vol %				
Gas component 6 Vol %				
Gas component 7 Vol %				
Gas component 8 Vol %				
Gas component 9 Vol %				
Gas component 10 Vol %				
Code-No. <sup>1)</sup> Operating temperature °C	512	522	532	542
Code-No. <sup>1)</sup> Operating pressure bar abs.	513	523	533	543
Code-No. <sup>1)</sup> Measuring range	514	524	534	544
Code-No. <sup>1)</sup> Unit <sup>2)</sup>	515	525	535	545
Code-No. <sup>1)</sup> Nominal size DN Nom. pressure PN Pipe inner Ø (mm)	518	528	538	548
Code-No. <sup>1)</sup> Standard conditions °C, mbar abs.	519	529	539	549
Display and menu language (delivered state)	<input type="checkbox"/> German <input type="checkbox"/> English <input type="checkbox"/> French <input type="checkbox"/> Portuguese			
Material of the connected pipes				

<sup>1)</sup> Add the 3-digit Code No to the Catalog No

<sup>2)</sup> Available flow rate units see table, standard: kg/h, Nm<sup>3</sup>/h

t/d	t/h	t/min	t/s
kg/d	kg/h	kg/min	kg/s
	g/h	g/min	g/s
lb/d	lb/h	lb/min	lb/s
Nm <sup>3</sup> /d	Nm <sup>3</sup> /h	Nm <sup>3</sup> /min	Nm <sup>3</sup> /s
NI/d	NI/h	NI/min	NI/s
SCFD	SCFH	SCFM	SCFS

**Design data**

**1. Measuring task**

**2. Measuring point parameters**

Gas type and composition (Vol %) <sup>1)</sup> .....		Flow rate units <sup>2)</sup> kg/h ..... <input type="checkbox"/> kg/min ..... <input type="checkbox"/> kg/s ..... <input type="checkbox"/> Nm <sup>3</sup> /h ..... <input type="checkbox"/> Nl/s ..... <input type="checkbox"/> Lb/h ..... <input type="checkbox"/> Lb/min ..... <input type="checkbox"/> SCFM ..... <input type="checkbox"/> SCFH ..... <input type="checkbox"/> SCFS ..... <input type="checkbox"/> Others ..... <input type="checkbox"/>	
Measuring range min..... normal ..... max.....			
Medium temperature (°C) min..... normal ..... max.....			
Operating pressure (bar abs.) min..... normal ..... max.....			
Pipe: nominal width DN ..... Nominal pressure PN .. Internal pipe Ø (mm) ..... Wall thickness (mm)			
Gas contains corrosive substances	no. .... <input type="checkbox"/> yes ..... <input type="checkbox"/>	which .....	Pipe material .....
Gas contains components that tend to condensate	no. .... <input type="checkbox"/> yes ..... <input type="checkbox"/>	which .....	Dew point (°C) .....
Medium contains solid particles	no. .... <input type="checkbox"/> yes ..... <input type="checkbox"/>	Particle size (µm) .....	Quantity (mg/m <sup>3</sup> ) <sup>2)</sup> .....
Measuring point	First equipment. .... <input type="checkbox"/> Exchange ..... <input type="checkbox"/>	Old device .....	

**3. Device parameters**

<b>Application</b> Without explosion protection ..... <input type="checkbox"/> With explosion protection for zone 2 ..... <input type="checkbox"/> With explosion protection for zone 1 ..... <input type="checkbox"/> With explosion protection for zone 0 ..... <input type="checkbox"/>	<b>Supply voltage</b> 110...230 V AC/DC ..... <input type="checkbox"/> 24 V AC/DC ..... <input type="checkbox"/>	<b>Outputs</b> Analog/HART + digital ..... <input type="checkbox"/> PROFIBUS DPV1 ..... <input type="checkbox"/>
<b>Design</b> Compact design ..... <input type="checkbox"/> Remote version (separate) ..... <input type="checkbox"/> with cable length 5/15/25 m	<b>Pipe components</b> Wafer flange ..... <input type="checkbox"/> Partial measuring section ..... <input type="checkbox"/> Weld-on adapter ..... <input type="checkbox"/> Integrated hot tap fitting ..... <input type="checkbox"/>	<b>Existing steadying runs<sup>3)</sup></b> Steadying run on the inlet side ..... x D Steadying run on the outlet side ..... x D

<sup>1)</sup> Specify gas mixtures, e.g. natural gas: CH<sub>4</sub> = 90 %; C<sub>2</sub>H<sub>6</sub> = 5 %; N<sub>2</sub> = 3 %; CO<sub>2</sub> = 2 %

<sup>2)</sup> Standard condition, e.g. referred to 0 °C/1013 mbar

<sup>3)</sup> See recommendations on page 15

The Industrial<sup>IT</sup> wordmark and all mentioned product names in the form XXXXX<sup>IT</sup> are registered or pending trademarks of ABB.

The Company's policy is one of continuous product improvement and the right is reserved to modify the information contained herein without notice.

ABB has Sales & Customer Support expertise in over 100 countries worldwide.

Printed in the Fed. Rep. of Germany (11.03)

[www.abb.com](http://www.abb.com)

© ABB 2003



**ABB Ltd.**  
Oldends Lane, Stonehouse  
Gloucestershire, GL10 3TA  
UK  
Tel: +44(0)1453 826661  
Fax: +44(0)1453 827856

**ABB Inc.**  
125 E. County Line Road  
Warminster, PA 18974  
USA  
Tel: +1 215 674 6000  
Fax: +1 215 674 7183

**ABB Inc.**  
3450 Harvester Road  
Burlington Ontario L7N 3W5  
Canada  
Tel: +1 905 681 0565  
Fax: +1 905 681 2810

**ABB Automation Products GmbH**  
Borsigstr. 2  
63755 Alzenau  
Germany  
Tel: +49 551 905-534  
Fax: +49 551 905-555  
CCC-support.deapr@de.abb.com