CATALOG

Electronic relays and controls

Offer overview and technical data



- Interface relays and optocouplers
- Time relays
- Primary switch mode power supplies
- Measuring and monitoring relays

ABB has the industry's most comprehensive range of time relays measuring and monitoring relays, interface relays and power supplies – helping you to source all critical components from a single global supplier.

Increase the reliability of process equipment with control devices that provide intelligent signals and smart adjustments that help you achieve maximum system availability.


Electronic relays and controls

Table of contents

4	Overview
13	Time relays
73	Measuring and monitoring relays
247	Primary switch mode power supplies
361	Interface relays and optocouplers
458	Index

Interface relays and optocouplers
A proven technology used worldwide

Relays are universally applicable and are utilized in a diverse array of applications. They are a significant element in contemporary industrial processes and are used in applications where galvanic isolation, signal separation, voltage coupling and signal amplification are required.




Optocouplers are predominantly used in applications where a high switching frequency is necessary. Furthermore, optocouplers do not contain any moving parts and are therefore bounce-free, immune to vibrations and possess a long electrical life. This wide selection of relays adheres to the highest global standards and satisfies the requirements for a diverse number of applications and needs.

ABB offers a complete range of interface relays and optocouplers for increased flexibility and choice. This portfolio includes pluggable relays for easy interchange-ability and optocouplers for an extended electrical life. The portfolio includes electromechanical relays and optocouplers - the electromechanical relays operate using an electromagnetic field, whereas optocouplers use light.

Billions

of relays operate and interface between control circuits and electrical loads



Time relays
Have the perfect timing- everywhere


Available in three different ranges to cover every application, the CT range time relays are used to provide reliable timing functions worldwide. In both industrial and building applications, the time relays of the CT range have proven their excellent functionality in daily use under the toughest conditions.

Choose ABB as the partner for all your low voltage timing control needs to leverage our wide variety of product options. From economic to high-end solutions – the range offers maximum value. Time relays are found everywhere, for example in air conditioning systems, heaters and fans in industrial and in residential buildings . On-delay, off-delay and a range of other functions cover all requirements.



Shock
and vibration resistant CT-S relays are perfect for use in rolling stock

- Control panels
- Pump controls
- Star-delta motor starting
- Movable equipment like cranes
- Machine tools
- Automatic doors
- Car park barriers
- Assembly machines
- HVAC
- Compressor controls
- Transportation
- Industrial refrigeration
- Packaging machines
- Backing ovens
- Water and wastewater
- Wind
- Industrial cleaning processes





Primary switch mode power supplies
Excellent reliability in harsh environments

Available in four different ranges to cover every application requirement, ABB's CP range power supplies are used to power valuable assets worldwide.

E-mobility

Emergency lighting

LED lighting

Communi-cation

Printing industry

Packaging industry

Food industry

Escalators

Elevators




Choose ABB as your power supply partner and leverage our wide variety of product options. From economic to high-end solutions, the CP range offers maximum value. Their excellent reliability in daily use is well proven even under the toughest of conditions.









Measuring and monitoring relays

Increase process availability and take action

The relays inform users about abnormal conditions and allow them to take necessary corrective actions before severe and costly failures can occur.




Measuring and monitoring relays monitor and detect operating conditions with regard to phase, current, voltage, frequency, temperature, liquid level or insulation faults. The relays inform users about abnormal conditions and allow them to take necessary corrective actions before severe and costly failures can occur.

ABB offers the broadest range of measuring and monitoring relays in the industry - so you can source your critical components from a global supplier. Increase the reliability of your process equipment with controllers that deliver intelligent signals and settings to ensure maximum availability. Ensure continuous operation, engineer time savings and benefit from ABB's global support for measuring and monitoring relays.









Electronic relays and controls websites
Your one-stop shop for product information

On our web site you will also find the products in this catalog together with the current life cycle status, data sheets, certificates and tools.

3D data


Life cycle information

Coordination tables (SOC)

E-configure

Certificates

new.abb.com/low-voltage/products/electronicrelays




Marketing material


More brochures, catalogs and other tools about electronic relays and control products in rail applications, explosive atmospheres, as well as information about applications, safety products and motor protection and control products are available online.

Online data sheets

For detailed product information, use the order code to access the online data sheets as in the following example:

new.abb.com/products/1SVR740110R3300








ABB Connect
Your digital assistant

Connect to your electrification solutions with your digital assistant, access the latest news, and create your own digital workspace; search **'ABB Connect'** on the Apple App Store, Google Play Store or Microsoft Store and download today.

Find the latest product details

Make your phone or tablet your workspace

Tap and stay connected to all the latest information

new.abb.com/low-voltage/service/abb-connect


ABB
E 234 CT-ERD
E 234 CT-MFD
CT-ERC
CT-MFC
CT-AHS
CT-MVS

Time relays
Table of contents

15	**Time relays for industrial applications**
21	CT-C range
33	CT-S range
51	**Time relays for building applications**
54	CT-D range
65	**Timing functions**


CT-ERC
CT-MFC
CT-AHS
CT-MVS
ABB
A1
15
25
Z2
Y1/B1
Range
Time
Function
T Range
U/T
R
Inst. Del. 2.c/o
18
16
A2
26
28
Y1

Time relays for industrial applications
Table of contents

16	**Offer overview**
17	**Type selection**
19	**Applications**
21	**CT-C range**
22	Benefits and advantages
23	Operating controls
24	Selection table
25	Ordering details
26	Technical data
30	Technical diagrams
33	**CT-S range**
34	Benefits and advantages
38	Selection table
39	Ordering details
42	Technical data
46	Technical diagrams

Time relays for industrial applications
Offer overview



CT-C: the compact range
The CT-C range combines lower cost with higher value and performance by offering essential functions in a space-saving 17.5 mm housing. The range offers a choice of 11 devices, including single and multifunctional types, with timing functions that range from 0.05 seconds to 100 hours. Equipped with a wide voltage range, the CT-C range is suitable for a huge variety of applications worldwide.



CT-S: the high-performance range
The advanced CT-S range is ABB´s universal range of electronic timers. It includes 22 single-function devices and 16 multifunction time relays, offering flexibility in operation with up to 13 functions. The devices feature seven or ten time ranges, adjustable from 0.05 seconds to 300 hours. Additionally, every device is available in two different connection technologies: familiar double-chamber cage connection terminals (screw terminals) and ABB's vibration-resistant Easy Connect technology (push-in terminals).

Time relays for industrial applications
Type selection

	multi-functional	single-functional	multi-functional	single-functional
Timing function	**CT-C**		**CT-S**	
ON-delay	CT-MFC, CT-MKC	CT-ERC	CT-MVS, CT-MFS, CT-MBS, CT-WBS	CT-ERS
OFF-delay	CT-MFC, CT-MKC, CT-ARC	CT-AHC	CT-MVS, CT-MFS, CT-MBS	CT-APS, CT-AHS, CT-ARS
ON- and OFF-delay			CT-MVS, CT-MXS, CT-MFS, CT-MBS	
Impulse-ON	CT-MFC, CT-MKC	CT-VWC	CT-MVS, CT-MFS, CT-MBS, CT-WBS	
Impulse-OFF	CT-MFC, CT-MKC, CT-ARC		CT-MVS, CT-MFS, CT-MBS	
Impulse-ON and OFF			CT-MXS	
Flasher starting with ON	CT-MFC, CT-MKC	CT-EBC	CT-MFS, CT-MBS, CT-WBS	
Flasher staring with OFF	CT-MFC, CT-MKC	CT-EBC	CT-MFS, CT-MBS, CT-WBS	
Flasher starting with ON or OFF			CT-MVS	
Pulse generator starting with ON or OFF		CT-TGC	CT-MXS	
Pulse former	CT-MFC, CT-MKC		CT-MVS, CT-MFS, CT-MBS	
Star-delta change-over		CT-SDC, CT-SAC		CT-SDS
Star-delta change-over with impulse			CT-MVS.2x, CT-MFS, CT-MBS	
+ further functions (depending on device)			CT-MVS, CT-MXS, CT-MFS, CT-MBS, CT-WBS	

A detailed explanation of the different timing functions can be found in the chapter “Timing functions”.


Synonyms


Used expression	Alternative expression(s)
1 c/o contact	SPDT
2 c/o contacts	DPDT
voltage-related	wet / non-floating
volt-free	dry / floating







OASIS of the SEAS








Time relays for industrial applications
Applications

ABB offers a wide selection of time relays – from economic to high-end – to suit every application for businesses worldwide. ABB time relays provide simple, reliable and economical control solutions in all types of panel. They are typically used in industrial applications and OEM equipment, providing time-delayed switching to start a motor, control a load or manage a process.



Remote control of time delays with a remote potentiometer.



Cyclic switching of machinery, for example the weekly startup of a fan to prevent them sticking or the flushing of pipes to keep them clear.




Lighting control, for example the delayed switching of multiple rows of lamps in production facilities or greenhouses.



Time controlled start up or shut down of machinery equipment, for example the delayed switch off of conveyor belts or the successive shut down of a plant.



Alarm triggering in case of fault detection, for example to allow the flashing of a lamp in industrial applications or rolling stock.



Star-delta motor starting to reduce starting current with changeover delay to prevent interphase short-circuits.

Have the perfect timing everywhere with ABB's time relays:

- Control panels
- Pump controls
- Star-delta motor starting
- Movable equipment e.g. cranes
- Machine tools
- Automatic doors
- Car park barriers
- Assembly machines
- HVAC
- Compressor controls
- Transportation
- Industrial refrigeration
- Packaging machines
- Backing ovens
- Water and wastewater
- Wind
- Industrial cleaning processes


CT-ERC
CT-SDC
CT-MFC
CT-TGC
ABB
A1
15
17
25
18
16
A2
Y1/B1
28
26
Range
Time
Function
Pulse on Time
Pulse off Time

CT-C range
Table of contents

12 Benefits and advantages

13 Operating controls

14 Selection table

15 Ordering details

16 Technical data

20 Technical diagrams

CT-C range
Benefits and advantages



The CT-C range combines lower cost with higher value and performance by offering essential functions in a 17.5 mm housing, freeing up room in any control cabinet. The range includes 11 devices, offering both single and multifunctional types, with a time range from 0.05 seconds to 100 hours. Equipped with wide voltage ranges, CT-C time relays allow for use across a huge variety of applications worldwide.

Space savings

With a width of just 17.5 mm, the CT-C range is 22% smaller than standard industrial housings for time relays. Its reduced overall footprint saves space in control cabinets. For more flexibility both 1 c/o and 2 c/o output versions are offered in the compact housing.


Cost effective solution

The CT-C range is an economical range that combines lower cost with higher value and performance. It suits basic applications where a time relay is needed, while offering improved functionality in each device.

Optimized logistics

By combining more functions into each device, the CT-C range makes it possible to reduce stock by up to 75% compared to other ranges. All devices in the CT-C range offer a wide supply voltage range as well as a wide time setting range from 0.05 seconds to 100 hours. This significantly reduces order code variance, making the range more compact with just 11 order codes covering every requirement.

CT-C range
Operating controls



Connection terminals
Wide terminal spacing makes wiring connections easier:
2 x 1.5 mm² (2 x 16 AWG) with wire end ferrules or 2 x 2.5 mm² (2 x 14 AWG) without ferrules.

Preselection of the time range

Direct reading scales
Direct setting of the time delay without any additional calculation provides accurate time delay adjustment.

Selection of the timing function

⊠	ON-delay
■	OFF-delay with aux. voltage
1⊓⊠	Impulse-ON
1⊓■	Impulse-OFF with aux. voltage
⊓⊠	Flasher starting with ON
⊓■	Flasher starting with OFF
1⊓	Pulse former

Width 17.5 mm
With a width of just 17.5mm, CT-C time relays are ideal for installations with limited space.

Control input to start timing

Fine adjustment of the time delay

LEDs for status indication
All actual operational states are displayed by front-facing LEDs, simplifying commissioning and troubleshooting.
- U - green LED:
  ⎍‾‾⎎ control supply voltage applied / ⎍⎎⎍⎎ timing
- R, R1, R2 - yellow LED:
  ⎍‾‾⎎
  output relay energized

CT-C range
Selection table

	Order number	1SVR508010R1300	1SVR508020R0000	1SVR508020R1100	1SVR508120R0000	1SVR508100R0000	1SVR508100R0100	1SVR508110R0000	1SVR508110R0100	1SVR508130R0000	1SVR508150R0000	1SVR508160R0000	1SVR508160R0100	1SVR508210R0100	1SVR508211R0100
	Type	CT-MKC.31	CT-MFC.12	CT-MFC.21	CT-ARC.12	CT-ERC.12	CT-ERC.22	CT-AHC.12	CT-AHC.22	CT-VWC.12	CT-EBC.12	CT-TGC.12	CT-TGC.22	CT-SAC.22	CT-SDC.22
Timing function															
ON-delay		■	■	■		■	■								
OFF-delay with aux. voltage		■	■	■				■	■						
OFF-delay w/o aux. voltage					■										
Impulse-ON	1	■	■	■						■					
Impulse-OFF with aux. voltage	1	■	■	■											
Impulse-OFF w/o aux. voltage	1				■										
Flasher starting with ON		■	■	■							■				
Flasher starting with OFF		■	■	■							■				
Pulse generator starting with ON or OFF												■	■		
Pulse former	1	■	■	■											
Star-delta change-over														■	■
Features															
Control input, voltage-related triggering		■	■	■				■	■			■	■		
Time range															
0.05 s - 100 h		■	■	■		■	■	■	■	■	■	2	2		
0.05 s - 10 min					■									■	■
Supply voltage															
12-240 V AC/DC		■		■											
24-48 V DC			■		■	■	■	■	■	■	■	■	■	■	■
24-240 V AC			■		■	■	■	■	■	■	■	■	■	■	■
Output															
Solid state		■													
c/o contact			1	2	1	1	2	1	2	1	1	1	2		
n/o contact														2	2

CT-C range
Ordering details



CT-MFC.12



CT-ERC.22

■ Control input with voltage-related triggering

\- No triggering

Description

The CT-C range combines lower cost with higher value and performance in a slim 17.5 mm-wide housing. All relays have a wide time setting range from 0.05 seconds up to 100 hours. Combined with a wide voltage range they are the perfect choice for applications worldwide.

Ordering details

Timing function	Rated control supply voltage	Time ranges	Control input	Output	Type	Order code	Weight (1 pc) kg (lb)
Multi[1]	12-240 V AC/DC	7 (0.05 s - 100 h)	■	Solid state	CT-MKC.31	1SVR508010R1300	0.060 (0.132)
Multi[1]	24-240 V AC 24-48 V DC		■	1 c/o	CT-MFC.12	1SVR508020R0000	0.060 (0.132)
Multi[1]	12-240 V AC/DC		■	2 c/o	CT-MFC.21	1SVR508020R1100	0.065 (0.143)
Dual[2]	24-48 V DC 24-240 V AC	7 (0.05 s - 10 min)	-	1 c/o	CT-ARC.12	1SVR508120R0000	0.060 (0.132)
ON-delay	24-240 V AC 24-48 V DC	7 (0.05 s - 100 h)	-	1 c/o	CT-ERC.12	1SVR508100R0000	0.060 (0.132)
			-	2 c/o	CT-ERC.22	1SVR508100R0100	0.065 (0.143)
OFF-delay			■	1 c/o	CT-AHC.12	1SVR508110R0000	0.060 (0.132)
			■	2 c/o	CT-AHC.22	1SVR508110R0100	0.065 (0.143)
Impulse-ON			-	1 c/o	CT-VWC.12	1SVR508130R0000	0.060 (0.132)
Flasher[3]			-		CT-EBC.12	1SVR508150R0000	0.060 (0.132)
Pulse generator		2×7 (0.05 s - 100 h)	■		CT-TGC.12[4]	1SVR508160R0000	0.060 (0.132)
			■	2 c/o	CT-TGC.22[4]	1SVR508160R0100	0.065 (0.143)
Star-delta change-over		4 (0.05 s - 10 min)	-	2 n/o	CT-SDC.22[5]	1SVR508211R0100	0.065 (0.143)
			-		CT-SAC.22[6]	1SVR508210R0100	

[1] Functions: ON-delay, OFF-delay with auxiliary voltage, Impulse-ON, Impulse-OFF with auxiliary voltage, Flasher starting with ON, Flasher starting with OFF, Pulse former
[2] OFF-delay without aux. voltage (True OFF-delay), True Impulse-OFF
[3] Flasher starting with ON, Flasher starting with OFF
[4] ON and OFF times adjustable independently: 2 x 7 time ranges 0.05 s - 100 h
[5] Transition time 50 ms fixed
[6] Transition time adjustable

CT-C range
Technical data

Data at T_a = 25 °C and rated values, unless otherwise indicated

		CT-C with 1 c/o contact	CT-C with 2 c/o contacts	CT-MFC.21 CT-MKC.31
Input circuit - Supply circuit				
Rated control supply voltage U_s		24-240 V AC / 24-48 V DC		12-240 V AC/DC
Rated control supply voltage U_s tolerance		-15...+10 %		
Rated frequency		DC or 50/60 Hz		
Frequency range AC		47-63 Hz		
Typical power consumption		max. 3.5 VA		
Power failure buffering time		min. 20 ms		
Release voltage		> 10 % of the minimum rated control supply voltage U_s		
Minimum energizing time		100 ms (CT-ARC)		
Formatting time[1)]		5 min (CT-ARC)		
Input circuit - Control circuit				
Control input, control function	A1-Y1/B1	start timing external		
Kind of triggering		voltage-related triggering		
Resistance to reverse polarity		yes		
Parallel load / polarized		yes / yes		
Maximum cable length to the control inputs		50 m - 100 pF/m		
Minimum control pulse length		20 ms		
Control voltage potential		see rated control supply voltage		
Timing circuit				
Time ranges	7 time ranges 0.05 s - 100 h	1.) 0.05-1 s 2.) 0.5-10 s 3.) 5-100 s 4.) 0.5-10 min 5.) 5-100 min 6.) 0.5-10 h 7.) 5-100 h		
	4 time ranges 0.05 s - 10 min (CT-SDC, CT-SAC, CT-ARC)	1.) 0.05-1 s 2.) 0.5-10 s 3.) 5-100 s 4.) 0.5-10 min		
Recovery time		< 50 ms		
Accuracy within the rated control supply voltage tolerance		Δt < 0.005 % / V		
Accuracy within the temperature range		Δt < 0.06 % / °C		
Repeat accuracy (constant parameters)		Δt < ± 0.5 %		
Setting accuracy of time delay		± 10% of full-scale value		
Star-delta transition time	CT-SDC / CT-SAC	fixed 50 ms / adjustable: 20 ms, 30 ms, 40 ms, 50 ms, 60 ms, 80 ms or 100 ms		
Star-delta transition time tolerance	CT-SDC / CT-SAC	±3 ms		
Indication of operational states				
Control supply voltage / timing	U: green LED	⎍: control supply voltage applied ⎍⎍⎍: timing		
Relay energized	R, R1, R2: yellow LED	⎍: output relay energized		
Operating elements and controls				
Adjustment of the time range		front-face rotary switch, direct reading scales		
Fine adjustment of the time value		front-face potentiometer		
Preselection of the timing function at multifunction devices		front-face rotary switch, direct reading scales		
Adjustment of the transition time	CT-SAC	front-face potentiometer		

[1)] Prior to first commissioning and after a six month stop of operation.

CT-C range
Technical data


			CT-C with 1 c/o contact	CT-C with 2 c/o contacts	CT-MFC.21 CT-MKC.31
Output circuit					
Kind of output		15-16/18	Relay, 1 c/o contact	-	
		15-16/18; 25-26/28	-	Relay, 2 c/o contacts	
		17-18		Solid state, 1 n/o contact (CT-MKC)	
		17-18; 17-28		Relay, 2 n/o contacts (CT-SDC, CT-SAC)	
Contact material			AgNi alloy, Cd free		
Rated operational voltage U_e			250 V		
Minimum switching voltage / minimum switching current			12 V / 100 mA, 5 V/ 1 mA (CT-MKC)		
Maximum switching voltage / maximum switching current			see load limit curves		250 V AC/ 1 A (resistive, CT-MKC)
Rated operational current I_e		AC-12 (resistive) at 230 V	4 A	4 A (CT-MKC: 1A)	
		AC-15 (inductive) at 230 V	3 A	3 A	n/o: 3 A n/c: 0.75 A (CT-MFC), 0.25 A (CT-MKC)
		DC-12 (resistive) at 24 V	4 A	4 A (CT-MKC: 1 A)	
		DC-13 (inductive) at 24 V	2 A (CT-ARC: 1.5 A)	2 A (CT-ARC: 1.5 A)	1 A
AC rating (UL 508) (except CT-MKC)	utilization category (Control Circuit Rating Code)		B 300		n/o: B 300 n/c: C 300
	max. rated operational voltage		300 V AC		
	maximum continuous thermal current at B300		5 A		n/o: 5 A
	maximum continuous thermal current at C300		-		n/c: 2.5 A
	max. making/breaking apparent power at B300		3600 VA / 360 VA		n/o: 3600/360 VA
	max. making/breaking apparent power at C300		-		n/c: 1800/180 VA
Rating (UL 60947-5-1) (CT-MKC)		utilization category	-		AC-15: 0.2 A / 230 V DC-13: 1 A / 24 V
		max. rated operational voltage	-		250 V
		max. continuous thermal curren	-		1 A
Mechanical lifetime			30 x 10^6 switching cycles		
Electrical lifetime			0.1 x 10^6 switching cycles		10 x 10^6 (CT-MKC)
Max. fuse rating to achieve short-circuit protection		n/c contact	6 A fast-acting		
		n/o contact	10 A fast-acting		6 A fast-acting (CT-MFC) 1 A FF (CT-MKC)
General data					
Mean time between failures (MTBF)			on request		
Duty cycle			100%		
Dimensions			see 'Dimensional drawings'		
Mounting			DIN rail (IEC/EN 60715), snap-mounting without any tool		
Mounting position			any		
Minimum distance to other units		horizontal / vertical	no (CT-ARC: 10 mm if switching current >2 A) / no		
Material of housing			UL 94 V-2		
Degree of protection		housing / terminals	IP50 / IP20		
Electrical connection					
Connecting capacity		fine-stranded with(out) wire and ferrule	2 x 0.5-1.5 mm² (2 x 20-16 AWG) 1 x 0.5-2.5 mm² (1 x 20-14 AWG)		
		rigid	2 x 0.5-1.5 mm² (2 x 20-16 AWG) 1 x 0.5-4 mm² (1 x 20-12 AWG)		
Stripping length			7 mm (0.28 in)		
Tightening torque			0.5-0.8 Nm (4.43-7.08 lb.in)		

CT-C range
Technical data


			CT-C with 1 c/o contact	CT-C with 2 c/o contacts	CT-MFC.21 CT-MKC.31
Environmental data					
Ambient temperature range		operation / storage	-20 ... +60 °C / -40 ... +85 °C		
Climatic class		EC/EN 60068-2-30	3K3		
Relative humidity range			25-85%		
Vibration, sinusoidal		IEC/EN 60068-2-6	20 m/s²; 10 cycles, 10...150...10 Hz		
Shock (half-sine)		IEC/EN 60068-2-27	150 m/s², 11 ms		
Isolation data					
Rated insulation voltage U_i	input circuit / output circuit		300 V		
	output circuit 1 / output circuit 2		not available	300 V	300 V
Rated impulse withstand voltage U_{imp}	between all isolated circuits		4 kV; 1.2/50 µs		
Power-frequency withstand voltage test (test voltage)	between all isolated circuits		2.5 kV; 50 Hz; 60 s		
Basic insulation (IEC/EN 61140)	input circuit / output circuit		300 V		
Protective separation (pollution degree 2 / overvoltage category II)	input circuit / output circuit		250 V		
Pollution degree			3		
Overvoltage category			III		
Standards / Directives					
Standards			IEC/EN 61812-1		
Low Voltage Directive			2014/35/EU		
EMC Directive			2014/30/EU		
RoHS Directive			2011/65/EU incl. 2015/863/EU		
Electromagnetic compatibility					
Interference immunity to			IEC/EN 61000-6-2		
electrostatic discharge		IEC/EN 61000-4-2	level 3 (6 kV / 8 kV)		
radiated, radio-frequency, electromagnetic field		IEC/EN 61000-4-3	level 3 (10 V / m)		
electrical fast transient / burst		IEC/EN 61000-4-4	level 3 (2 kV / 5 kHz)		
surge		IEC/EN 61000-4-5	level 4 (2 kV L-L)		
conducted disturbances, induced by radio-frequency fields		IEC/EN 61000-4-6	level 3 (10 V)		
Interference emission					
high-frequency radiated		IEC/CISPR 22, EN 55022	class B		
high-frequency conducted		IEC/CISPR 22, EN 55022	class B		

CT-C range
Technical diagrams

Example of application - Star-delta changeover




Control circuit diagram



Power circuit diagram


Connection diagrams

CT-MFC.21




A1-A2	Supply: 12-240 V AC/DC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-MFC.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact

✉ CT-ERC.22



A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

✉ CT-ERC.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact

CT-C range
Technical diagrams


Connection diagrams

CT-AHC.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-AHC.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact

CT-VWC.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact

CT-EBC.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact

CT-TGC.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-TGC.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact

CT-SDC.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
17-18	1st n/o contact (star contactor)
17-28	2nd n/o contact (delta contactor)

CT-SAC.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
17-18	1st n/o contact (star contactor)
17-28	2nd n/o contact (delta contactor)

CT-ARC.12



A1-A2	Supply: 12-240 V AC/DC
15-16/18	1st c/o contact

CT-MKC.31




A1-A2	Supply: 12-240 V AC/DC
15-16/18	1st c/o contact


CT-C range
Technical diagrams

Load limit curves


AC load (resistive)




DC load (resistive)



Derating factor F for inductive AC load




Contact lifetime




Wiring notes for devices with control input


A parallel load to the control input is possible



Dimensional drawings
in **mm** and inches



CT-C devices with 1 c/o contact or 2 n/o contacts



CT-C devices with 2 c/o contacts


A1
15
25
ABB
CT-ERS
T Range
Time
U/T
R
18
28
26
A1
15
25 21
Y1/B1
Z2
Z1
ABB
CT-MVS
Inst. Del. 2.c/o
T Range
Time
Function
U/T
R1
R2
18
28 24
26 22
A1
17
ABB
CT-SDS
T Range
Time
U/T
R1
R2
18
A1
15
25
Z2
ABB
CT-AHS
T Range
Time
U/T
R
18
28
26
Y1

CT-S range
Table of contents

24	Benefits and advantages
28	Selection table
29	Ordering details - multifunctional devices
30	Ordering details - singlefunctional devices
31	Ordering details - Accessories
32	Technical data
36	Technical diagrams

CT-S range
Benefits and advantages



The advanced CT-S range includes 22 single-function devices and 16 multifunction timers with up to 13 functions. The devices feature seven or ten time ranges, which are adjustable from 0.05 seconds to 300 hours. Every device is available in two different connection technologies: double-chamber cage connection terminals or ABB's vibration-resistant Push-in Technology.

Improve installation efficiency

The CT-S range allows simple tool free mounting and demounting on the DIN rail. Thanks to the easy connect and the double-chamber cage connection technology simplified wiring with or without wire end ferrules is no problem. Both allow simple and easy installation, even in case of different cable diameters.


Reliable in harsh conditions

The CT-S range's extended features make it especially suited for harsh environments. The housing material has the highest UL fire protection classification. All functions are available with Push-in terminals, making operations in environments with high vibrations possible without retightening. Additionally, the CT-S range offers devices with an extended temperature range, running operations in temperatures as low as -40 °C effortlessly. Specific types are tested according to the latest rail industry standards, making them a perfect solution for rolling stock and other rail applications

Global availability

Every device in the CT-S range is designed to provide a wide supply voltage range, making global differences irrelevant. Additionally, the CT-S range meets a broad range of standards and requirements. Together with ABB's global support and sales network, using CT-S gives customers the confidence of worldwide sourcing – no matter where they build, install or operate their equipment.

CT-S range
Operating controls



Control input
Starts and pauses timing.

Preselection of time range
Direct assignment of the pre-selected time range to the fine adjustment potentiometer scale by multicolor scales

Fine adjustment of the time delay

Selection of the timing function

Connection terminals
Screw or push-in connection available.

Remote potentiometer connection possible

2nd contact selectable as an instantaneous contact

LEDs for status indication
All actual operational states are displayed by front-face LEDs, thus simplifying commissioning and troubleshooting.

- U/T - green LED:
  ⎍⎺⎍ control supply voltage applied /
  ⎍⎍⎍⎺ timing
- R, R1, R2 - yellow LED:
  ⎍⎺⎍ Output relay energized

Integrated marker label
Integrated marker labels allow the product to be marked quickly and simply. No additional marker labels are required.


CT-S range
Benefits and advantages



2CDC253026F0011

—
01 Tool-free mounting of wires

Easy Connect Technology
Tool-free wiring and excellent vibration resistance. Easy Connect (Push-in terminals) provide connection of wires up to 2 x 0.5 - 1.5 mm² (2 x 20 -16 AWG), rigid or fine-strand with or without wire end ferrules. The extended type designators for products with push-in terminals are indicated by a **P** following the extended type designator e.g. CT-xxS.xx**P**.



2CDC253025F0011


—
02 Wiring of double-cage chamber connection terminals with screw driver

Double-chamber cage connection terminals
According to IEC/EN 60947-1 double-chamber cage connection terminals provide connection of wires up to 2 x 0.5-2.5 mm² (2 x 20-14 AWG) rigid or fine-strand, with or without wire end ferrules. Thanks to the technology, using different cable diameters in one terminal is easy and simple to install. Potential distribution does not require additional terminals. The extended type designators for products with double-chamber cage connection terminals (screw terminals) are indicated by an **S** following the extended type designator, e.g. CT-xxS.xx**S**.



CT-S range
Made for the most extreme conditions

Selected products of the CT-S range comply to the latest rail standards like EN50155. Designed for harsh environments, not only are standard screw type terminals offered – push-in terminals with excellent vibration resistance are also available. Perfect for use in rolling stock.



Conductor car

- In the event of the press switch not switching off the auxiliary release pumps of the breaking system, a delayed switch off is triggered by the time relays
- While switching between hold-on and start-up coil on the main switch, a time relay can prolong the pulse
- The reliable and safe functionality of the compressor is essential for trains

Passenger cars

- The control of air flow and interior lighting is controlled by time relays. A time interval can trigger a delayed start and finish for the air circulation as well as turning on or off the lights inside the cabin
- The advanced CT-S range of time relays from ABB is designed to fulfill all necessary requirements for rail applications



Electronic relays for railway solutions brochure

For more information about time relays in rolling stock applications visit:

new.abb.com/low-voltage/products/electronicrelays

or scan the QR code

CT-S range
Selection table

Order number and type
All devices are available either with push-in terminals (P-type) or double-chamber cage connection terminals (S-type).

Terminal	Type	Order number
Push-in	● = P	■ = 4
Screw	● = S	■ = 3

	Order number*	1SVR7■0020R0200	1SVR7■0020R3300	1SVR7■0021R2300	1SVR7■0020R3100	1SVR7■0030R3300	1SVR7■0010R0200	1SVR7■0010R3200	1SVR7■0040R3300	1SVR7■0100R0300	1SVR7■0100R3300	1SVR7■0100R3100	1SVR7■0180R0300	1SVR7■0180R3300	1SVR7■0180R3100	1SVR7■0110R3300	1SVR7■0120R3100	1SVR7■0120R3300	1SVR7■0210R3300	1SVR7■0211R2300
	Type*	CT-MVS.21●	CT-MVS.22●	CT-MVS.23●	CT-MVS.12●	CT-MXS.22●	CT-MFS.21●	CT-MBS.22●	CT-WBS.22●	CT-ERS.21●	CT-ERS.22●	CT-ERS.12●	CT-APS.21●	CT-APS.22●	CT-APS.12●	CT-AHS.22●	CT-ARS.11●	CT-ARS.21●	CT-SDS.22●	CT-SDS.23●
Timing function																				
ON-delay	⊠	■	■	■	■		■	■	■	■	■	■								
ON-delay, accumulative	⊠(+)	■	■	■	■		■													
OFF-delay w. aux. voltage	▬	■	■	■	■		■	■					■	■	■	■				
OFF-delay w. aux. voltage, accumulative	▬						■													
OFF-delay w/o aux. voltage	▬																■	■		
ON- and OFF-delay, symmetrical	⊠▬	■	■	■	■		■	■												
ON- and OFF-delay, symmetrical, accumulative	⊠▬						■													
ON- and OFF-delay, asymmetrical	⊠▬					■														
ON/OFF function	▭	■	■	■	■	■	■	■	■											
Impulse-ON	1⊓⊠	■	■	■	■		■	■	■											
Impulse-ON, accumulative	1⊓⊠						■													
Impulse-OFF w. aux. voltage	1⊓▬	■	■	■	■		■	■												
Impulse-OFF w. aux. voltage, accumulative	1⊓▬						■													
Impulse-ON and OFF	1⊓▩					■														
Fixed impulse with adjustable time delay	⊠1⊓								■											
Adjustable impulse with fixed time delay	⊠1⊓								■											
Flasher starting with ON	⊓⊠						■	■	■											
Flasher with reset, starting with ON	⊓⊠						■	■												
Flasher starting with OFF	⊓▬						■	■	■											
Flasher with reset, starting with OFF	⊓▬						■	■												
Flasher starting with ON or OFF	⊓▩	■	■	■	■															
Pulse generator starting with ON or OFF	▩⊓					■														
Single pulse generator	▩1⊓					■														
Pulse former	1⊓	■	■	■	■		■	■												
Star-delta change-over	⧋																		■	■
Star-delta change-over with impulse	⧋1⊓	■	■	■			■	■												
Features																				
Control input, voltage-related triggering		■	■	■	■	■							■	■	■					
Control input, volt-free triggering							2	1								■				
Remote potentiometer connection		■				2	■	■												
2nd c/o contact selectable as instantaneous contact		■					■	■												
Extended temperature range (-40...+60 °C)		■					■			■			■							
Time range																				
0.05 s - 10 min																	■	■	■	■
0.05 s - 300 h		■	■	■	■	2	■	■	■	■	■	■	■	■	■	■				
Supply voltage																				
24-48 V DC			■		■	■		■	■		■	■		■	■	■			■	
24-240 V AC			■		■	■		■	■		■	■		■	■	■			■	
24-240 V AC/DC		■					■			■			■				■	■		
380-440 V AC				■																■
Output																				
c/o contact		2	2	2	1	2	2	2	2	2	2	1	2	2	1	2	1	2		
n/o contact																			2	2

CT-S range

Ordering details - multifunctional devices



CT-MVS.21P



CT-MBS.22P

■ Control input with voltage-related triggering

☐ Control input with volt-free triggering

☐ / ☐ Two control inputs with volt-free triggering

\- No triggering

Description

The high-performance CT-S range is ideally suited for universal use and is available with two different connection technologies:

- Double-chamber cage connection terminals (Screw terminals)
- Easy Connect Technology (Push-in terminals)

Ordering details

Timing function [5]	Rated control supply voltage	Time ranges	Control input	Output	Type	Order code	Weight (1 pc) kg (lb)
Multi	24- 240 V AC/DC	10 (0.05 s - 300 h)	■	2 c/o	CT-MVS.21S [1) 2) 3)]	1SVR730020R0200	0.148 (0.326)
					CT-MVS.21P [1) 2) 3)]	1SVR740020R0200	0.136 (0.30)
	24-48 V DC, 24-240 V AC				CT-MVS.22S	1SVR730020R3300	0.142 (0.313)
					CT-MVS.22P	1SVR740020R3300	0.131 (0.289)
	380-440 V AC				CT-MVS.23S	1SVR730021R2300	0.144 (0.317)
					CT-MVS.23P	1SVR740021R2300	0.133 (0.293)
Multi	24-48 V DC, 24-240 V AC	10 (0.05 s - 300 h)	■	1 c/o	CT-MVS.12S	1SVR730020R3100	0.107 (0.236)
					CT-MVS.12P	1SVR740020R3100	0.102 (0.225)
Multi	24-48 V DC, 24-240 V AC	2×10 (0.05 s - 300 h)	■	2 c/o	CT- MXS.22S [4)]	1SVR730030R3300	0.142 (0.313)
					CT-MXS.22P [4)]	1SVR740030R3300	0.131 (0.289)
Multi	24- 240 V AC/DC	10 (0.05 s - 300 h)	☐ / ☐	2 c/o	CT-MFS.21S [1) 2) 3)]	1SVR730010R0200	0.145 (0.32)
					CT-MFS.21P [1) 2) 3)]	1SVR740010R0200	0.133 (0.293)
	24-48 V DC, 24-240 V AC	10 (0.05 s - 300 h)	☐	2 c/o	CT-MBS.22S [2) 3)]	1SVR730010R3200	0.14 (0.309)
					CT-MBS.22P [2) 3)]	1SVR740010R3200	0.129 (0.284)
Multi	24-48 V DC, 24-240 V AC	10 (0.05 s - 300 h)	-	2 c/o	CT-WBS.22S	1SVR730040R3300	0.123 (0.271)
					CT-WBS.22P	1SVR740040R3300	0.115 (0.254)

[1)] Extended temperature range -40 °C
[2)] Remote potentiometer connection
[3)] 2nd c/o contact selectable as instantaneous contact
[4)] 2 remote potentiometer connections
[5)] See selection table on previous page

S: Screw connection
P: Push-in / easy connect

CT-S range

Ordering details - singlefunctional devices



CT-ERS.21P



CT-AHS.22P



CT-SDS.23P

■ Control input with voltage-related triggering

□ Control input with volt-free triggering

□ / □ Two control inputs with volt-free triggering

\- No triggering

Ordering details

Timing function	Rated control supply voltage	Time ranges	Control input	Output	Type	Order code	Weight (1 pc) kg (lb)
ON-delay	24-240 V AC/ DC	10 (0.05 s - 300 h)	-	2 c/o	CT-ERS.21S[1)]	1SVR730100R0300	0.13 (0.287)
					CT-ERS.21P[1)]	1SVR740100R0300	0.121 (0.267)
	24-48 V DC, 24-240 V AC				CT-ERS.22S	1SVR730100R3300	0.121 (0.267)
					CT-ERS.22P	1SVR740100R3300	0.113 (0.249)
	24-48 V DC, 24-240 V AC		-	1 c/o	CT-ERS.12S	1SVR730100R3100	0.106 (0.234)
					CT-ERS.12P	1SVR740100R3100	0.101 (0.222)
OFF-delay	24-240 V AC/ DC	10 (0.05 s - 300 h)	■	2 c/o	CT-APS.21S[1)]	1SVR730180R0300	0.146 (0.322)
					CT-APS.21P[1)]	1SVR740180R0300	0.125 (0.276)
	24-48 V DC, 24-240 V AC				CT-APS.22S	1SVR730180R3300	0.138 (0.304)
					CT-APS.22P	1SVR740180R3300	0.127 (0.28)
			■	1 c/o	CT-APS.12S	1SVR730180R3100	0.109 (0.24)
					CT-APS.12P	1SVR740180R3100	0.103 (0.227)
	24-48 V DC, 24-240 V AC	10 (0.05 s - 300 h)	□	2 c/o	CT-AHS.22S	1SVR730110R3300	0.136 (0.30)
					CT-AHS.22P	1SVR740110R3300	0.125 (0.276)
OFF-delay[2)]	24-240 V AC/DC	7 (0.05 s - 10 min)	-	1 c/o	CT-ARS.11S	1SVR730120R3100	0.106 (0.234)
					CT-ARS.11P	1SVR740120R3100	0.10 (0.22)
			-	2 c/o	CT-ARS.21S	1SVR730120R3300	0.124 (0.273)
					CT-ARS.21P	1SVR740120R3300	0.115 (0.254)
Star-delta change-over[3)]	24-48 V DC, 24-240 V AC	7 (0.05 s - 10 min)	-	2 n/o	CT-SDS.22S	1SVR730210R3300	0.114 (0.251)
					CT-SDS.22P	1SVR740210R3300	0.108 (0.238)
	380-440 V AC				CT-SDS.23S	1SVR730211R2300	0.118 (0.26)
					CT-SDS.23P	1SVR740211R2300	0.112 (0.247)

[1)] Extended temperature range -40 °C
[2)] Without auxiliary voltage
[3)] 50 ms transition time

S: Screw connection
P: Push-in / easy connect

CT-S range

Ordering details - Accessories


1SFC 151 139V0001

MT-x50B

The CT-S range offers the possibility of using accessories such as a remote potentiometer to adjust the time delay or a sealable, transparent cover to protect against unauthorized changes of time and threshold values.

Remote potentiometer

50 kΩ ±20 % - 0.2 Ω, degree of protection IP66


Material	Diameter in mm	Type	Order code	Pack.-unit pieces	Weight 1 piece g / oz
Plastic, black	22.5	MT-150B	1SFA611410R1506	1	0.040
Plastic, chrome	22.5	MT-250B	1SFA611410R2506	1	0.040
Metal, chrome	22.5	MT-350B	1SFA611410R3506	1	0.048


2CDC 252 042 F0009

30 mm adapters

30 mm adapter for attaching the potentiometer 22 mm in 30 mm mounting hole


Material	Type	Order code	Pack.-unit pieces	Weight 1 piece g / oz
Plastic, black	KA1-8029	1SFA616920R8029	1	
Metal, chrome	KA1-8030	1SFA616920R8030	1	


2CDC 252 043 F0209

Marker label 29.6 x 44.5 mm

Marker label

Caption	Type	Order code	Pack.-unit pieces	Weight 1 piece g / oz
Symbol (see illustration)	SK 615 562-87	GJD6155620R0087	1	0.002
Scale 0 - 10	SK 615 562-88	GJD6155620R0088	1	0.002
Scale 0 - 30	MA16-1060	1SFA611940R1060	1	0.002



2CDC 252 044 F0209

Marker label with scale 0-10
48.5 x 44.5 mm

Accessories for CT-S

Description	Type	Order code	Pack.-unit pieces	Weight 1 piece g / oz
Adapter for screw mounting	ADP.01	1SVR430029R0100	1	0.018 (0.040)
Sealable transparent cover	COV.11	1SVR730005R0100	1	0.004 (0.009)
Marker label for devices w/o DIP switches	MAR.01	1SVR366017R0100	10	0.001 (0.002)
Marker label for devices with DIP switches	MAR.12	1SVR730006R0000	10	0.001 (0.002)


2CDC 255 006 S0011

Sealable transparent cover
for CT-S in new housing

CT-S range
Technical data

Data at T_a = 25 °C and rated values, unless otherwise indicated

			CT-S
Input circuit - Supply circuit			
Rated control supply voltage U_s		CT-xxx.x1	24-240 V AC/DC
		CT-xxx.x2	24-48 V DC, 24-240 V AC
		CT-xxx.x3	380-440 V AC
Rated control supply voltage U_s tolerance			-15...+10 %
Rated frequency			DC or 50/60 Hz
Frequency range AC			47-63 Hz
Typical power consumption			max. 16 VA
Power failure buffering time		24 V DC	min. 15 ms
		230/400 V AC	min. 20 ms
Release voltage			> 10 % of the minimum rated control supply voltage U_s
Minimum energizing time			100 ms (CT-ARS)
Formatting time [1]			5 min (CT-ARS)
Input circuit - Control circuit			
Kind of triggering		CT-MVS, CT-MXS, CT-APS	voltage-related triggering
Control input, Control function		A1-Y1/B1	start timing external
Parallel load / polarized			yes / no
Maximum cable length to the control input			50 m - 100 pF/m
Minimum control pulse length			20 ms
Control voltage potential			see rated control supply voltage
Current consumption of the control input		24 V DC	1.2 mA
		230 V AC	8 mA
		400 V AC	6 mA
Kind of triggering		CT-MFS, CT-MBS, CT-AHS	volt-free triggering
Control input, Control function		Y1-Z2	start timing external
		X1-Z2	pause timing / accumulative functions (CT-MFS)
Maximum switching current in the control circuit			1 mA
Maximum cable length to the control input			50 m - 100 pF/m
Minimum control pulse length			20 ms
No-load voltage at the control inputs			10-40 V DC
Remote potentiometer			
Remote potentiometer connections, resistance value		Z1-Z2	50 kΩ (CT-MFS, CT-MBS, CT-MVS.21, CT-MXS)
		Z3-Z2	50 kΩ (CT-MXS)
Maximum cable length to remote potentiometer			2 x 25 m, shielded with 100 pF/m
Shield connection			Z2
Timing circuit			
Time ranges	10 time ranges 0.05 s - 300 h		1.) 0.05-1 s 2.) 0.15-3 s 3.) 0.5-10 s 4.) 1.5-30 s 5.) 5-100 s 6.) 15-300 s 7.) 1.5-30 min 8.) 15-300 min 9.) 1.5-30 h 10.) 15-300 h
	7 time ranges 0.05 s - 10 min (CT-SDS, CT-ARS)		1.) 0.05-1 s 2.) 0.15-3 s 3.) 0.5-10 s 4.) 1.5-30 s 5.) 5-100 s 6.) 15-300 s 7.) 0.5-10 min
Recovery time		24-240 V AC/DC	< 50 ms
		24-48 V DC, 24-240 V AC	< 80 ms
		380-440 V AC	< 60 ms
Accuracy within the rated control supply voltage tolerance			Δt < 0.004 % / V
Accuracy within the temperature range			Δt < 0.03 % / °C
Repeat accuracy (constant parameters)			< ±0.2 %
Setting accuracy of time delay			±6 % of full-scale value
Star-delta transition time			fixed 50 ms (CT-SDS, CT-MBS, CT-MFS, CT-MVS.2x)
Star-delta transition time tolerance			±2 ms

[1] Prior to first commisioning and after a six-month stop in operation

CT-S range
Technical data

Indication of operational states			
Control supply voltage / timing		U/T: green LED	⎍: control supply voltage applied / ⎍⎍: timing
Control supply voltage		U: green LED	⎍: control supply voltage applied
Relay state		R, R1, R2: yellow LED	⎍: output relay energized
Output circuit			
Kind of output		15-16/18	relay, 1 c/o contact
		15-16/18; 25-26/28	relay, 2 c/o contacts
		15-16/18; 25(21)-26(22)/28(24)	relay, 2 c/o contacts, 2nd c/o contact selectable as inst. contact
		17-18; 17-28	relay, 2 n/o contacts (CT-SDS)
Contact material			Cd-free, on request
Rated operational voltage U_e		IEC/EN 60947-1	250 V
Minimum switching voltage / minimum switching current			12 V / 100 mA
Maximum switching voltage / maximum switching current			see load limit curves
Rated operational current I_e		AC-12 (resistive) at 230 V	4 A
		AC-15 (inductive) at 230 V	3 A
		DC-12 (resistive) at 24 V	4 A
		DC-13 (inductive) at 24 V	2 A (CT-ARS; 1.5 A)
AC rating (UL 508)		utilization category (Control Circuit Rating Code)	B 300
		max. rated operational voltage	300 V AC
		maximum continuous thermal current at B300	5 A
		max. making/breaking apparent power at B300	3600 VA / 360 VA
Mechanical lifetime			30 x 10^6 switching cycles
Electrical lifetime		at AC-12, 230 V, 4 A	0.1 x 10^6 switching cycles
Frequency of operation		with/without load	360/72000 h^{-1} CT-ARS: 1200/18000 h^{-1}
Max. fuse rating to achieve short-circuit protection		n/c contact	6 A fast-acting
		n/o contact	10 A fast-acting
General data			
MTBF			on request
Duty cycle			100%
Dimensions			see ‘Dimensional drawings’
Mounting			DIN rail (IEC/EN 60715), snap-on mounting without any tool
Mounting position			any
Minimum distance to other units		vertical / horizontal	not necessary / not necessary
Material of housing			UL 94 V-0
Degree of protection		housing / terminals	IP50 / IP20


Electrical connection				
			Screw connection technology	**Easy Connect Technology (Push-in)**
Connecting capacity		fine-strand with(out) wire end ferrule	1 x 0.5-2.5 mm^2 (1 x 18-14 AWG) 2 x 0.5-1.5 mm^2 (2 x 18-16 AWG)	2 x 0.5-1.5 mm^2 (2 x 18-16 AWG)
		rigid	1 x 0.5-4 mm^2 (1 x 20-12 AWG) 2 x 0.5-2.5 mm^2 (2 x 20-14 AWG)	2 x 0.5-1.5 mm^2 (2 x 20-16 AWG)
Stripping length			8 mm (0.32 in)	
Tightening torque			0.6-0.8 Nm (7.08 lb.in)	-

CT-S range
Technical data

Environmental data			
Ambient temperature ranges	operation / storage	-25...+60 °C / -40...+85 °C, -40...+60 °C / -40...+85 °C for CT-MVS.21, CT-MFS.21, CT-ERS.21, CT-APS.21	
Relative humidity range		25 % to 85 %	
Vibration, sinusoidal (IEC/EN 60068-2-6)	functioning	40 m/s², 10-58/60-150 Hz	
	resistance	60 m/s², 10-58/60-150 Hz, 20 cycles	
Vibration, seismic (IEC/EN 60068-3-3)	functioning	20 m/s²	
Shock, half-sine (IEC/EN 60068-2-27)	functioning	150 m/s², 11 ms, 3 shocks/direction	
	resistance	300 m/s² , 11 ms, 3 shocks/direction	
Isolation data		**CT-S with 1 c/o**	**CT-S with 2 c/o**
Rated insulation voltage U_i	input circuit / output circuit	500 V	
	output circuit 1 / output circuit 2	not available	300 V
Rated impulse withstand voltage U_{imp}	between all isolated circuits	4 kV; 1.2/50 µs except devices CT-xxx.23: input / output: 6 kV; 1.2/50 µs output 1 / output 2: 4 kV; 1.2/50 µs	
Power-frequency withstand voltage (test voltage)	between all isolated circuits	2.0 kV; 50 Hz; 60 s	
Basic insulation (IEC/EN 61140)	input circuit / output circuit	500 V	
Protective separation (IEC/EN 61140; EN 50178)	input circuit / output circuit	250 V	
Pollution degree		3	
Overvoltage category		III	
Standards / Directives			
Standards		IEC/EN 61812-1	
Low Voltage Directive		2014/35/EU	
EMC Directive		2014/30/EU	
RoHS Directive		2011/65/EU	
Electromagnetic compatibility			
Interference immunity to		IEC/EN 61000-6-2	
electrostatic discharge	IEC/EN 61000-4-2	Level 3, 6 kV / 8 kV	
radiated, radio-frequency electromagnetic field	IEC/EN 61000-4-3	Level 3, 10 V/m (1 GHz) 3 V/m (2 GHz) 1 V/m (2.7 GHz)	
electrical fast transient / burst	IEC/EN 61000-4-4	Level 3, 2 kV / 5 kHz	
surge	IEC/EN 61000-4-5	Level 4, 2 kV A1-A2	
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	Level 3, 10 V	
harmonics and interharmonics	IEC/EN 61000-4-13	Class 3	
Interference emission		IEC/EN 61000-6-3	
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B	
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B	

CT-S range
Technical diagrams

DIP switch configuration CT-MXS.22x



Pulse generator, starting with ON or OFF

Single pulse generator, starting with OFF

Asymmetrical ON- and OFF-delay


Impulse-ON and Impulse-OFF

No function


ON/OFF function

Default setting: all DIP switches in position OFF

Example of application - Star-delta changeover



Control circuit diagram




Power circuit diagram

CT-S range
Technical diagrams


Connection diagrams

CT-MVS.21




A1-A2	Supply: 24-240 V AC/DC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact
21-22/24	2nd c/o contact as instantaneous contact
Z1-Z2	Remote potentiometer connection

CT-MVS.22




A1-A2	Supply: 224-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-MVS.23




A1-A2	Supply: 380-440V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-MVS.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact

CT-MXS.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact
Z1-Z2	Remote potentiometer connection
Z3-Z2	Remote potentiometer connection

CT-MFS.21




A1-A2	Supply: 24-240 V AC/DC
15-16/18	1st c/o contact
25-26/28	2nd c/o contact
21-22/24	2nd c/o contact as instantaneous contact
Y1-Z2	Control input
X1-Z2	Control input
Z1-Z2	Remote potentiometer connection

CT-MBS.22



A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact
25-26/28	2nd c/o contact
21-22/24	2nd c/o contact as instantaneous contact
Y1-Z2	Control input
Z1-Z2	Remote potentiometer connection

CT-WBS.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-S range
Technical diagrams


Connection diagrams

CT-ERS.21




A1-A2	Supply: 24-240 V AC/DC
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-ERS.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-ERS.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact

CT-APS.21




A1-A2	Supply: 24-240 V AC/DC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-APS.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-APS.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact

CT-AHS.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
Y1-Z2	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-ARS.11




A1-A2	Supply: 24-240 V AC/DC
15-16/18	1st c/o contact

CT-ARS.21




A1-A2	Supply: 24-240 V AC/DC
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

⚠ CT-SDS.22



A1-A2	Supply: 24-48 V DC or 24-240 V AC
17-18	1st n/o contact
17-28	2nd n/o contact

⚠ CT-SDS.23




A1-A2	Supply: 380-440 V AC
17-18	1st n/o contact
17-28	2nd n/o contact


CT-S range
Technical diagrams

Load limit curves


AC load (resistive)




DC load (resistive)



Derating factor F for inductive AC load




Contact lifetime




Wiring notes

Control inputs (volt-free triggering)




Triggering of the control inputs (volt-free) with a proximity switch (3 wire)




CT-S range
Technical diagrams


Wiring notes

Control inputs (voltage-related triggering)






Remote potentiometer




The control input Y1/B1 is triggered with electric potential against A2. It is possible to use the control supply voltage from terminal A1 or any other voltage within the rated control supply voltage range.

Dimensional drawings


in **mm** and inches




Main device



ADP.01 adapter for screw mounting



COV.11 sealable transparent cover



MAR.01 marker label


ABB
E 234 CT-ERD
A1 15
18 16 A2
ABB
E 234 CT-SDD
A1 17
28 18 A2
ABB
E 234 CT-MFD
A1 15 25
18 16 Y1/B1
28 26 A2
ABB
E 234 CT-TGD
A1 15 25
18 16 Y1/B1
28 26 A2

Time relays for building applications
Table of contents

43 Applications

44 Benefits and advantages


46 Selection table


47 Ordering details

48 Technical data

52 Technical diagrams


















Time relays for building applications
Applications

The CT-D range is designed in a modular housing, making it well suited for building and residential applications. In just 12 order codes the CT-D range covers all the main timing functions needed for building automation, safely and reliably.

A typical application for timers is delayed switching. Switching several rows of lamps on and off in corridors, stairwells, staircases, etc, is a widespread application in which the excellent functionality of the CT-D timers is undisputed.

Air conditioning systems, heaters and fans can be found everywhere in buildings - just like the CT-D timers long used to switch them. On-delay, off-delay and a range of other functions cover all requirements.

Elevators, escalators, gates, compressors and doors - here too ABB timers ensure optimum and time-delayed opening as required. ABB´s CT-D timers cover most functions with just 12 order codes.



CT-D range
Benefits and advantages



The CT-D range is ideal for building applications and installation panels, due to its compact modular housing. For maximum flexibility in operation, nine single-function as well as two multifunction devices with seven timing functions are available. The devices offer four or seven time ranges from 0.05 seconds up to 100 hours. Their wide supply voltage range allows their use in applications worldwide.

Space savings

The CT-D range is ideal for installation panels thanks to its compact modular housing. The housing's design helps make the status and configuration more clearly visible. The CT-D range also offers a higher output current than standard industrial types. As well as the 1 c/o contacts, ABB offers devices with 2 c/o contacts for maximum flexibility.


Easy to install

Direct reading scales help make time setting quick and easy. A pre-selection for the time range together with an additional scale for fine adjustments help improve installation efficiency. For more flexibility, the delay time can even be changed when processes are running, making optimization to fit the application even simpler. All devices can be mounted and demounted tool-free.

Global availabilty

The CT-D range fulfills various global standards and approvals, supporting business worldwide. Additionally, all devices from the CT-D range have a wide supply voltage from 24-48 V DC and 24-240 V AC, making it ideal for the use in installation panels around the world.

CT-D range
Operating controls



Width 17.5 mm
With a width of just 17.5 mm, the CT-D range timers are ideally suited for installation in distribution panels.

Connection terminals
Wide terminal spacing makes connection of wires simpler: 2 x 1.5 mm² (2 x 16 AWG) with wire end ferrules or 2 x 2.5 mm² (2 x 14 AWG) without ferrules.

Preselection of the time range

Direct reading scales
Direct setting of the time delay without any additional calculation provides accurate time delay adjustment.

Selection of the timing function

- ON-delay
- OFF-delay with aux. voltage
- Impulse-ON
- Impulse-OFF with aux. voltage
- Flasher starting with ON
- Flasher starting with OFF
- Pulse former

Fine adjustment of the time delay

LEDs for status indication
All actual operational states are displayed by front-facing LEDs, thus simplifying commissioning and troubleshooting.

- U - green LED:
  control supply voltage applied /
  timing
- R, R1, R2 - yellow LED:
  output relay energized

CT-D range
Selection table

	Order number	1SVR500020R0000	1SVR500020R1100	1SVR500100R0000	1SVR500100R0100	1SVR500110R0000	1SVR500110R0100	1SVR500130R0000	1SVR500150R0000	1SVR500160R0000	1SVR500160R0100	1SVR500210R0100	1SVR500211R0100
	Type	CT-MFD.12	CT-MFD.21	CT-ERD.12	CT-ERD.22	CT-AHD.12	CT-AHD.22	CT-VWD.12	CT-EBD.12	CT-TGD.12	CT-TGD.22	CT-SAD.22	CT-SDD.22
Timing function													
ON-delay		■	■	■	■								
OFF-delay with aux. voltage		■	■			■	■						
Impulse-ON		■	■					■					
Impulse-OFF with aux. voltage		■	■										
Flasher starting with ON		■	■						■				
Flasher starting with OFF		■	■										
Pulse generator starting with ON or OFF										■	■		
Pulse former		■	■										
Star-delta change-over												■	■
Features													
Control input, voltage-related triggering		■	■			■	■			■	■		
Time range													
0.05 s - 100 h		■	■	■	■	■	■	■	■	2	2		
0.05 s - 10 min												■	■
Supply voltage													
12-240 V AC/DC			■										
24-48 V DC		■		■	■	■	■	■	■	■	■	■	■
24-240 V AC		■		■	■	■	■	■	■	■	■	■	■
Output													
c/o contact		1	2	1	2	1	2	1	1	1	2		
n/o contact												2	2

CT-D range
Ordering details



CT-MFD.12



CT-ERD.22

■ Control input with voltage-related triggering

\- No triggering

Description

The CT-D range with its modular design is a perfect solution for installation panels. For maximum flexibility in operation, 10 single-function as well as two multifunction devices with seven timing functions are available. The devices offer four or seven time ranges from 0.05 seconds up to 100 hours. Their wide input range allows their use in applications worldwide.

Ordering details

Timing function	Rated control supply voltage	Time ranges	Control input	Output	Type	Order code	Weight (1 pc) kg (lb)
Multi[1]	24-240 V AC 24-48 V DC	7 (0.05 s - 100 h)	■	1 c/o	CT-MFD.12	1SVR500020R0000	0.060 (0.132)
Multi[1]	12-240 V AC/DC	7 (0.05 s - 100 h)	■	2 c/o	CT-MFD.21	1SVR500020R1100	0.065 (0.143)
ON-delay	24-240 V AC 24-48 V DC	7 (0.05 s - 100 h)	-	1 c/o	CT-ERD.12	1SVR500100R0000	0.060 (0.132)
			-	2 c/o	CT-ERD.22	1SVR500100R0100	0.065 (0.143)
OFF-delay			■	1 c/o	CT-AHD.12	1SVR500110R0000	0.060 (0.132)
			■	2 c/o	CT-AHD.22	1SVR500110R0100	0.065 (0.143)
Impulse-ON			-	1 c/o	CT-VWD.12	1SVR500130R0000	0.060 (0.132)
Flasher starting with ON					CT-EBD.12	1SVR500150R0000	
Pulse generator		2×7 (0.05 s - 100 h)	■		CT-TGD.12[2]	1SVR500160R0000	0.060 (0.132)
			■	2 c/o	CT-TGD.22[2]	1SVR500160R0100	0.065 (0.143)
Star-delta change-over		4 (0.05 s - 10 min)	-	2 n/o	CT-SDD.22[3]	1SVR500211R0100	0.065 (0.143)
			-		CT-SAD.22[4]	1SVR500210R0100	

[1] Functions: ON-delay, OFF-delay with auxiliary voltage, Impulse-ON, Impulse-OFF with auxiliary voltage, Flasher starting with ON, Flasher starting with OFF, Pulse former
[2] ON and OFF times adjustable independently: 2 x 7 time ranges 0.05 s - 100 h
[3] Transition time 50 ms fixed
[4] Transition time adjustable

CT-D range
Technical data

Data at T_a = 25 °C and rated values, unless otherwise indicated

		CT-D with 1 c/o contact	CT-D with 2 c/o contacts	CT-MFD.21
Input circuit - Supply circuit				
Rated control supply voltage U_s		24-240 V AC / 24-48 V DC		12-240 V AC/DC
Rated control supply voltage U_S tolerance		-15...+10 %		
Rated frequency		DC or 50/60 Hz		
Frequency range AC		47-63 Hz		
Typical power consumption		max. 3.5 VA		
Power failure buffering time		min. 20 ms		
Release voltage		> 10 % of the minimum rated control supply voltage U_s		
Input circuit - Control circuit				
Control input, control function	A1-Y1/B1	start timing external		
Kind of triggering		voltage-related triggering		
Resistance to reverse polarity		yes		
Parallel load / polarized		yes / yes		
Maximum cable length to the control inputs		50 m - 100 pF/m		
Minimum control pulse length		20 ms		
Control voltage potential		see rated control supply voltage		
Current consumption of the control input		see data sheet		
Timing circuit				
Time ranges	7 time ranges 0.05 s - 100 h	1.) 0.05-1 s 2.) 0.5-10 s 3.) 5-100 s 4.) 0.5-10 min 5.) 5-100 min 6.) 0.5-10 h 7.) 5-100 h		
	4 time ranges 0.05 s - 10 min (CT-SDD, CT-SAD)	1.) 0.05-1 s 2.) 0.5-10 s 3.) 5-100 s 4.) 0.5-10 min		
Recovery time		< 50 ms		
Accuracy within the rated control supply voltage tolerance		Δt < 0.005 % / V		
Accuracy within the temperature range		Δt < 0.06 % / °C		
Repeat accuracy (constant parameters)		Δt < ± 0.5 %		
Setting accuracy of time delay		± 10% of full-scale value		
Star-delta transition time	CT-SDD/ CT-SAD	fixed 50 ms / adjustable: 20 ms, 30 ms, 40 ms, 50 ms, 60 ms, 80 ms or 100 ms		
Star-delta transition time tolerance	CT-SDD / CT-SAD	±3 ms		
Indication of operational states				
Control supply voltage / timing	U: green LED	⎍⎺⎺⎺⎺⎺⎾: control supply voltage applied ⎍⎍⎍⎍⎍⎾: timing		
Relay energized	R, R1, R2: yellow LED	⎍⎺⎺⎺⎺⎺⎾: output relay energized		
Operating elements and controls				
Adjustment of the time range		front-face rotary switch, direct reading scales		
Fine adjustment of the time value		front-face potentiometer		
Preselection of the timing function at multifunction devices		front-face rotary switch, direct reading scales		
Adjustment of the transition time	CT-SAC	front-face potentiometer		

CT-D range
Technical data


			CT-D with 1 c/o contact	CT-D with 2 c/o contacts	CT-MFD.21
Output circuit					
Kind of output		15-16/18	Relay, 1 c/o contact	-	
		15-16/18; 25-26/28	-	Relay, 2 c/o contacts	
		17-18; 17-28		Relay, 2 n/o contacts (CT-SDC, CT-SAC)	
Contact material			AgNi alloy, Cd free		
Rated operational voltage U_e			250 V		
Minimum switching voltage / minimum switching current			12 V / 100 mA		
Maximum switching voltage / maximum switching current			250 V AC / 6 A	250 V AC / 5 A	
Rated operational current I_e		AC-12 (resistive) at 230 V	6 A	5 A	
		AC-15 (inductive) at 230 V	3 A	3 A	n/o: 3 A n/c: 0.75 A
		DC-12 (resistive) at 24 V	6 A	5 A	
		DC-13 (inductive) at 24 V	2 A	2 A	1 A
AC rating (UL 508)	utilization category (Control Circuit Rating Code)		B 300		n/o: B 300 n/c: C 300
	max. rated operational voltage		300 V AC		
	maximum continuous thermal current at B300		5 A		n/o: 5 A
	maximum continuous thermal current at C300		-		n/c: 2.5 A
	max. making/breaking apparent power at B300		3600 VA / 360 VA		n/o: 3600/360 VA
	max. making/breaking apparent power at C300		-		n/c: 1800/180 VA
Mechanical lifetime			30 x 10^6 switching cycles		
Electrical lifetime			0.1 x 10^6 switching cycles		
Max. fuse rating to achieve short-circuit protection		n/c contact	6 A fast-acting		
		n/o contact	10 A fast-acting		6 A fast-acting
General data					
Mean time between failures (MTBF)			on request		
Duty cycle			100%		
Dimensions			see 'Dimensional drawings'		
Mounting			DIN rail (IEC/EN 60715), snap-mounting without any tool		
Mounting position			any		
Minimum distance to other units		horizontal / vertical	no / no		
Material of housing			UL 94 V-2		
Degree of protection		housing / terminals	IP50 / IP20		
Electrical connection					
Connecting capacity		fine-stranded with(out) wire and ferrule	2 x 0.5-1.5 mm^2 (2 x 20-16 AWG) 1 x 0.5-2.5 mm^2 (1 x 20-14 AWG)		
		rigid	2 x 0.5-1.5 mm^2 (2 x 20-16 AWG) 1 x 0.5-4 mm^2 (1 x 20-12 AWG)		
Stripping length			7 mm (0.28 in)		
Tightening torque			0.5-0.8 Nm (4.43-7.08 lb.in)		
Environmental data					
Ambient temperature range		operation / storage	-20 ... +60 °C / -40 ... +85 °C		
Climatic class		EC/EN 60068-2-30	3K3		
Relative humidity range			25-85%		
Vibration, sinusoidal		IEC/EN 60068-2-6	20 m/s^2; 10 cycles, 10...150...10 Hz		
Shock (half-sine)		IEC/EN 60068-2-27	150 m/s^2, 11 ms		

CT-D range
Technical data


		CT-D with 1 c/o contact	CT-D with 2 c/o contacts	CT-MFC.21
Isolation data				
Rated insulation voltage U_i	input circuit / output circuit	300 V		
	output circuit 1 / output circuit 2	not available	300 V	300 V
Rated impulse withstand voltage U_{imp}	between all isolated circuits	4 kV; 1.2/50 µs		
Power-frequency withstand voltage test(test voltage)	between all isolated circuits	2.5 kV; 50 Hz; 60 s		
Basic insulation (IEC/EN 61140)	input circuit / output circuit	300 V		
Protective separation (pollution degree 2 / overvoltage category II)	input circuit / output circuit	250 V		
Pollution degree		3		
Overvoltage category		III		
Standards / Directives				
Standards		IEC/EN 61812-1		
Low Voltage Directive		2014/35/EU		
EMC Directive		2014/30/EU		
RoHS Directive		2011/65/EU		
Electromagnetic compatibility				
Interference immunity to		IEC/EN 61000-6-2		
electrostatic discharge	IEC/EN 61000-4-2	Level 3 (6 kV / 8 kV)		
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	Level 3 (10 V / m)		
electrical fast transient / burst	IEC/EN 61000-4-4	Level 3 (2 kV / 5 kHz)		
surge	IEC/EN 61000-4-5	Level 4 (2 kV L-L)		
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	Level 3 (10 V)		
Interference emission		IEC/EN 61000-6-3		
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B		
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B		

CT-D range
Technical diagrams

Example of application - Star-delta changeover



Control circuit diagram




Power circuit diagram

CT-D range
Technical diagrams


Connection diagrams

CT-MFD.21




A1-A2	Supply: 12-240 V AC/DC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-MFD.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact

CT-ERD.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-ERD.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact

CT-AHD.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-AHD.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact

CT-VWD.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact

CT-EBD.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
15-16/18	1st c/o contact

CT-TGD.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact
25-26/28	2nd c/o contact

CT-TGD.12




A1-A2	Supply: 24-48 V DC or 24-240 V AC
A1-Y1/B1	Control input
15-16/18	1st c/o contact

CT-SDD.22



A1-A2	Supply: 24-48 V DC or 24-240 V AC
17-18	1st n/o contact (star contactor)
17-28	2nd n/o contact (delta contactor)

CT-SAD.22




A1-A2	Supply: 24-48 V DC or 24-240 V AC
17-18	1st n/o contact (star contactor)
17-28	2nd n/o contact (delta contactor)

CT-D range
Technical diagrams


Load limit curves

AC load (resistive)

CT-D.1x




CT-D.2x




DC load (resistive)


CT-D.1x




CT-D.2x



Derating factor F for inductive AC load




Contact lifetime




Wiring notes for devices with control input


A parallel load to the control input is possible



Dimensional drawings
in **mm** and inches



CT-D devices with 1 c/o contact
or 2 n/o contacts



CT-D devices with 2 c/o contacts


ABB
E 234 CT-ERD
E 234 CT-MFD
CT-ERC
CT-MFC
CT-AHS
CT-MVS

Timing functions

Timing functions
CT-C, CT-S, CT-D


On delay functions (Delay on make) ⊠

On-delay



This function requires a continuous control supply voltage for timing. Timing begins when a control supply voltage is applied. When the selected time delay is complete, the output relay energizes. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.


ON-delay accumulative



This function requires a continuous control supply voltage for timing. Timing begins when a control supply voltage is applied. When the selected time delay is complete, the output relay energizes. Timing can be paused by closing the control input.
The elapsed time t1 is stored and continues from this time value when the control input is re-opened. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.


OFF delay functions (Delay on break) ■

OFF-delay with auxiliary voltage



This function requires a continuous control supply voltage for timing. If the control input is closed, the output relay energizes immediately. If the control input is opened, the time delay starts. When the selected time delay is complete, the output relay de-energizes.
If control input re-closes before the time delay is complete, the time delay is reset and the output relay does not change state. Timing starts again when the control input re-opens.
If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.


OFF-delay without auxiliary voltage



The OFF-delay function without auxiliary voltage does not require a continuous control supply voltage for timing. Applying a control supply voltage energizes the output relay. If the control supply voltage is interrupted, the OFF-delay starts. When timing is complete, the output relay de-energizes.
If a control supply voltage is re-applied before the time delay is complete, the time delay is reset and the output relay remains energized. A control supply voltage must be applied for the minimum energizing time (200 ms), for correct operation.

Timing functions
CT-C, CT-S, CT-D

OFF-delay with auxiliary voltage, accumulative



This function requires a continuous control supply voltage for timing. If the control input is closed, the output relay energizes immediately. If the control input is opened, the time delay starts. When the selected time delay is complete, the output relay de-energizes. If the control input closes before the time delay is complete, the time delay is reset and the output relay does not change state. Timing starts again when the control input reopens.

Pause timing / Accumulative OFF-delay: Timing can be paused by closing control 1. The elapsed time t1 is stored and continues from this time value when control input 1 is re-opened. This can be repeated as often as required. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.

Impulse-ON functions 1⎍⎍⌧

Impulse-ON (interval)



This function requires a continuous control supply voltage for timing. The output relay energizes immediately when the control supply voltage is applied and de-energizes after the set pulse time is complete. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.

Impulse-ON, accumulative



This function requires a continuous control supply voltage for timing. The output relay energizes immediately when the control supply voltage is applied and de-energizes after the set pulse time is complete. If control input 1 is open, timing begins when a control supply voltage is applied. Or, if control a supply voltage is already applied, opening control input 1 starts timing. When the selected pulse time is complete, the output relay de-energizes. Closing control input 1, before the pulse time is complete, de-energizes the output relay and re-sets the pulse time.

Pause timing / Accumulative impulse-ON:
Timing can be paused by closing control input 2. The elapsed time t1 is stored and continues from this time value when control input 2 is re-opened. This can be repeated as often as required. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.

Timing functions
CT-C, CT-S, CT-D


Impulse-OFF functions 1⎍■

Impulse-OFF with auxiliary voltage




This function requires a continuous control supply voltage for timing. The output relay energizes immediately when the control input is de-energized and the output de-energizes after the set pulse time is complete. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.

Impulse-OFF without auxiliary voltage



This function does not require a continuous control supply voltage for timing.
If the control supply voltage is interrupted, the output relay energizes and the OFF time starts. When timing is complete, the output relay de-energizes. If a control supply voltage is re-applied before the time delay is complete, the time delay is reset and the output relay de-energizes. A control supply voltage must be applied for the minimum energizing time (200 ms), for proper operation.


Impulse-OFF with auxiliary voltage
(Trailing edge interval) accumulative



This function requires a continuous control supply voltage for timing. If a control supply voltage is applied, opening control input 1 energizes the output relay immediately and starts timing. When the selected pulse time is complete, the output relay de-energizes. Closing control input 1, before the pulse time is complete, de-energizes the output relay and resets the pulse time.
Pause timing / Accumulative impulse-OFF:
Timing can be paused by closing control input 2. The elapsed time t1 is stored and continues from this time value when control input 2 is re-opened. This can be repeated as often as required. If the control supply voltage is interrupted, the output relay de- energizes and the time delay is reset.

Impulse-ON and Impulse-OFF functions 1⎍⎍▩

Impulse-ON and impulse-OFF



This function requires a continuous control supply voltage for timing. If a control supply voltage is applied, closing the control input energizes the output relay immediately and starts the pulse time t1. When t1 is complete, the output relay de-energizes. Re-opening the control input energizes the output relay immediately and starts the pulse time t2. When t2 is complete, the output relay de-energizes. t1 and t2 are independently adjustable. If the control input changes state before the pulse time is complete, the output relay de-energizes and the pulse time is reset. If the control input changes state again, the interrupted pulse time restarts. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.

Timing functions
CT-C, CT-S, CT-D


Flasher starting with ON functions ⎍⌧

Flasher starting with ON



Applying a control supply voltage starts timing with symmetrical ON & OFF times. The cycle starts with an ON time first. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.

Flasher with reset starting with ON



Applying a control supply voltage starts timing with symmetrical ON & OFF times. The cycle starts with an ON time first. The time delay can be reset by closing the control input. Opening the control input starts the timer pulsing again with symmetrical ON & OFF times. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.


Flasher starting with OFF functions ⎍■

Flasher starting with OFF



Applying a control supply voltage starts timing with symmetrical ON & OFF times. The cycle starts with an OFF time first. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.


Flasher with reset starting with OFF



Applying a control supply voltage starts timing with symmetrical ON & OFF times. The cycle starts with an OFF time first. The time delay can be reset by closing the control input. Opening the control input starts the timer pulsing again with symmetrical ON & OFF times. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.

Flasher starting with ON or OFF functions ⎍⌧■

Flasher starting with ON or OFF




Applying a control supply voltage starts timing with symmetrical ON / OFF times. If the control input is open while supply voltage is connected the cycle starts with an ON time first. If the control input is closed while supply voltage is connected the cycle starts with an OFF time first.

Timing functions
CT-C, CT-S, CT-D

Pulse former


Puls former (single shot)



This function requires a continuous control supply voltage for timing. Closing the control input energizes the output relay immediately and starts timing. Operating the control input during the time delay has no effect. When the selected ON time is complete, the output relay de-energizes. After the ON time is complete, it can be restarted by closing the control input. If control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.

Single-pulse generator


Single-pulse generator, starting with OFF



This function requires a continuous control supply voltage for timing. Applying a control supply voltage while the control input is open energizes the output relay after the OFF time t1 is complete. When the following ON time t2 is complete, the output relay de-energizes. Alternatively, when a control supply voltage is already applied, the timing process can be started by opening control input. Closing the control input with a control supply voltage applied, de-energizes the output relay and re- sets the time delay. The ON & OFF times are independently adjustable.

Pulse generator


Starting with the ON or OFF time
(Recycling unequal times, ON or OFF first)



This function requires a continuous control supply voltage for timing. Applying a control supply voltage, with closed control input, starts timing with an OFF time first. Applying a control supply voltage, with open control input, starts timing with an ON time first. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.

Impulse with delay

Fixed impulse with adjustable time delay



This function requires a continuous control supply voltage for timing. The time delay t1 starts when a control supply voltage is applied. When t1 is complete, the output relay energizes for the fixed impulse time t2 of 500 ms.
If the control supply voltage is interrupted, the time delay is re- set. The output relay does not change state.

Adjustable impulse with fixed time delay




This function requires a continuous control supply voltage for timing. As soon as the control supply voltage is applied the output relay will close after 500 ms. When t2 is complete, the output relay energizes and the selected pulse time t1 starts. When t1 is complete, the output relay de-energizes. If the control supply voltage is interrupted, the pulse time is reset and the output relay de-energizes.

Timing functions
CT-C, CT-S, CT-D

ON- and OFF-delay


Symmetrical ON- and OFF-delay [1)]



This function requires a continuous control supply voltage for timing. Closing the control input starts the ON-delay time t1. When timing is complete, the output relay energizes. Opening the control input starts the OFF-delay time t2. When the OFF-delay t2 is complete, the output relay de-energizes. If the control input opens before the ON-delay (<t1) is complete, the time delay is reset and the output relay remains de-energized. If control input closes before the OFF-delay time (<t2) is complete, the time delay is reset and the output relay remains energized.


1) Variant with 2nd control input for pause timing is available too.

Asymmetrical ON- and OFF-delay



This function requires a continuous control supply voltage for timing. Closing the control input starts the ON-delay t1. When timing is complete, the output relay energizes. Opening the control input starts the OFF-delay t2. When the OFF-delay is complete, the output relay de-energizes. The ON-delay and OFF-delay are independently adjustable. If the control input opens before the ON-delay is complete (<t1), the time delay is reset and the output relay remains de-energized. If the control input closes before the OFF-delay is complete (<t2), the time delay is reset and the output relay remains energized. If the control supply voltage is interrupted, the output relay de-energizes and the time delay is reset.

Star-Delta changeover



This function requires a continuous control supply voltage for timing. Applying a control supply voltage, energizes the star contactor connected to output 1 and begins the set starting time t1. When the starting time is complete, the first output contact de-energizes the star contactor. When the transition time t2 is complete, the second output contact energizes the delta contactor. The delta contactor remains energized as long as the control supply voltage is applied. t2 is fixed to 50 ms or in some variants adjustable.

Further functions

ON/OFF function



This function is used for test purposes during commissioning and troubleshooting.
If the selected maximum value of the time range is smaller than 300 hours (front-face potentiometer “Time sector” ≠ 300 h), applying a control supply voltage energizes the output relay immediately. Interrupting the control supply voltage, de-energizes the output relay.
If the selected maximum value of the time range is 300 hours (front- face potentiometer “Time sector” = 300 h) and a control supply voltage is applied the output relay does not energize.


CM-UFD
CM-PFE
CM-PAS
CM-MPN
CM-PSS
ESC
OK
U/T
F
Rx/Tx
A1 A2
Y1 Y2 Y3 Y0
L1 L2 L3 N

Measuring and monitoring relays
Table of contents

74 Benefits and advantages

76 Offer overview

79 Applications

81 Single-phase monitoring relays

105 Three-phase monitoring relays

137 Grid feeding monitoring relays

151 Insulation monitoring relays

181 Thermistor motor protection relays

203 Temperature monitoring relays


219 Liquid level monitoring relays

241 Accessories

Measuring and monitoring relays
Benefits and advantages




Higher utility class
The plastic housing material used meets the requirements for the highest flammability class. (UL94 V-0 rated)



Snap-on housing
Tool-free DIN rail installation and deinstallation of the relay.



Sealable transparent cover
Protection against unauthorized changes of time and threshold values.




Measuring and monitoring relays
Benefits and advantages



Easy Connect technology
- Tool-free wiring and excellent vibration resistance.
- Push-in terminals provide connection of wires up to 2 x 0.5 - 1.5 mm² (2 x 20 -16 AWG), rigid or fine-strand with or without wire end ferrules.
- Excellent vibration resistance – the right solution for harsh environments.



Double-chamber cage connection terminals
Double-chamber cage connection terminals provide connection of wires up to 2 x 0.5-2.5 mm² (2 x 20-14 AWG) rigid or fine-strand, with or without wire end ferrules.




LEDs for status indication
All actual operational states are displayed by front-face LEDs, simplifying commissioning and troubleshooting.



Integrated marker label
Integrated marker labels allow the product to be marked quickly and simply. No additional marker labels are required.


Measuring and monitoring relays
Offer overview

Measuring and monitoring relays monitor and detect operating conditions with regard to phase, current, voltage, frequency, temperature, liquid level or insulation faults. The relays inform users about abnormal conditions and allow them to take necessary corrective actions before severe and costly failures can occur. Depending on the product model, measuring and monitoring relays are categorized into seven product families.




Single-phase current monitoring relays
- Monitoring of motor current consumption
- Monitoring of lighting installations and heating circuits
- Monitoring of transportation equipment overload
- Monitoring of locking devices, electromechanical brake gear and locked rotors

Single-phase voltage monitoring relays
- Speed monitoring of DC motors
- Monitoring of battery voltages and other supply networks




Three-phase monitoring relays
- Voltage monitoring of mobile three-phase equipment
- Protection of personnel and installations against phase reversal
- Monitoring of the supply voltage of machines and installations
- Protection of equipment against damage caused by unstable supply voltage
- Switching to emergency or auxiliary supply
- Protection of motors against damage caused by unbalanced phase voltages and phase loss
- Suitable for HVAC applications




Grid feeding monitoring relays

The CM-UFD.M* range monitors all voltage and frequency parameters in a grid and ensures the safe feeding of decentrally produced electrical energy into the grid.
- Monitoring of the voltage with up to 2 thresholds for over- and undervoltage
- Monitoring of the frequency with up to 2 thresholds for over- and under-frequency
- ROCOF (rate of change of frequency) and vector shift detection
- In compliance with several local standards


Measuring and monitoring relays
Offer overview



Insulation monitoring relays
- Monitoring of electrically isolated supply mains for insulation resistance failure
- Detection of initial faults
- Protection against earth faults




Temperature monitoring relays
Acquisition, messaging and regulation of temperatures of solid, liquid and gaseous media in processes and machines
- Motor and system protection
- Control panel temperature monitoring
- Frost monitoring
- Temperature limits for process variables, e.g. in the packing or electroplating industry
- Control of systems and machines like heating, air-conditioning and ventilation systems, solar collectors, heat pumps or hot water supply systems
- Bearing, gear oil and coolant monitoring



Thermistor motor protection
CM-MSE and CM-MSS provide full protection of motors with integrated PTC resistor sensors.

Protection of motors against thermal overload, e. g. caused by insufficient cooling, heavy load starting conditions, undersized motors, etc.



Liquid level monitoring relays
- Protection of pumps against dry running
- Protection against container overflow
- Control of liquid levels
- Detection of leaks
- Control of mixing ratios

Measuring and monitoring relays
Offer overview



CM-N range: Multifunctional range
- 45 mm wide housing
- Output contacts: 2 c/o (SPDT) contacts
- Continuous voltage range (24-240 V AC/DC) or single-supply
- Setting and operation via front-face operating controls
- Adjustment of threshold values and switching hysteresis via direct reading scale
- Adjustable time delays
- Integrated and snap-fitted front-face marker label
- Sealable transparent cover (accessory)



CM-S range: Universal and multifunctional range
- Only 22.5 mm wide housing
- Output contacts: 1 or 2 c/o (SPDT) contacts
- One supply voltage range or supplied by measuring circuit
- Setting and operation via front-face operating controls
- Adjustment of threshold values and switching hysteresis via direct reading scale
- Integrated and snap-fitted front-face marker
- Snap-on housing: The relays can be placed on a DIN rail tool-free - just snap it on or remove it tool-free
- Sealable transparent cover (accessory)



CM-E range: Economy range
- Only 22.5 mm wide housing
- Output contacts: 1 c/o contact or 1 n/o contact
- One supply voltage range
- One monitoring function
- Cost-efficient solution for OEM applications
- Preset monitoring ranges

Measuring and monitoring relays
Applications


ABB offers a wide selection of measuring and monitoring relays to suit a wide range of applications for businesses worldwide. Excellent vibration resistance with the Easy Connect terminal technology and railway certifications for selected products ensure the operability, even in harsh environments.


Automation panels
- Textile industry - measuring and monitoring of motor voltage and current overload of, for example, looms.
- Packaging industry - measuring and monitoring of motor voltage and current overload of, for example, conveyor belts.

Infrastructure
- Water and wastewater applications - monitoring the liquid level of water tanks and wastewater recycling plants.
- Lifts - status monitoring of the three phase mains of, for example, construction lifts, passenger lifts and escalators.
- Hoisting applications - construction cranes, harbor cranes.
- Railway.

Renewable energy
- Solar - monitoring of the insulation resistance and the frequency and voltage of the public grid to keep electrical grids stable and meet local requirements.
- Wind - temperature, current and voltage supervision of automation panels and electrical motors.

Buildings
- Lifts - status monitoring of the three phase mains of, for example, construction lifts, passenger lifts and escalators.
- HVAC - monitoring of grid parameters, control and protection of loads.










A1
11 15
C
B
ABB
CM-ESS
Hyst. %
U V
Range
U
R
U/T
14 18
B1 0.3-1.5 A
B2 1-5 A
B3 3-15 A
CM-SRS
Hyst. %
I A
I
R
U/T
14 18
A1
11 15
21 25
B
ABB
CM-EFS
>U V
<U V
Tv s
Range
U
R
U/T
14 18
12 16
24 28
C

Single-phase monitoring relays
Table of contents

82 **Benefits and advantages**

84 **Operating controls**

86 **Single-phase current monitoring relays**

86 Selection table

87 Ordering details

88 **Single-phase voltage monitoring relays**

88 Selection table

89 Ordering details

90 **Technical data**

96 **Technical diagrams**

98 **Function diagrams**

Single-phase monitoring relays
Benefits and advantages



For the monitoring of currents and voltages in single-phase AC/DC systems, ABB's CM-range contains a wide selection of powerful and compact devices, all in an only 22.5 mm wide housing. This product range includes current and voltage monitoring relays for over- and undercurrent and voltage protection – from 3 mA to 15 A, and from 3 V to 600 V.

Continuous operation

Read the status of the relay at a glance: clear visualization of the device status via LEDs. Easy to adjust with rotary wheels and variants with push-in terminals make a quick and easy installation and setting possible.

Reliable in harsh conditions

All relays work reliably in environments with low temperatures down to -25 °C. Additionally, the housing fulfills the UL 94 V-0 flammability standard requirements. Together with the vibration resistant push-in terminals, the relay is not only reliable, no matter the environment temperature, but is also durable to shock and vibration. Save time as retightening is no longer needed, and enhance the reliability and safety of the equipment.

Easy installation

Like all devices from the measuring and monitoring portfolio, the single-phase monitoring relays are easily configurable via front facing potentiometers. Easy threshold configuration without calculation is accomplished by direct reading scales. For further configuration options, additional settings can be made via dip-switches, offering the flexibility to configure, for example, the working principle of the relays and the output configuration. The device can be set up before installation in the application and easy adjustments during the process are possible.

Single-phase monitoring relays
Benefits and advantages

Characteristics current and voltage monitoring relays[1)]

- Monitoring of DC and AC currents: 3 mA to 15 A
- Monitoring of DC and AC voltages from 3-600 V
- TRMS measuring principle
- One device includes 3 current measuring ranges
- One device includes 4 voltage measuring ranges: 3-30 V; 6-60 V; 30-300 V; 60-600 V
- Over- and undercurrent monitoring
- Over- and undervoltage monitoring
- ON or OFF-delay configurable
- Open- or closed-circuit principle configurable
- Threshold values for >U and/or <U adjustable
- Latching function configurable
- Thresholds for >I and/or <I adjustable
- Fixed hysteresis of 5 %
- Start-up delay T_v adjustable 0; 0.1-30 s
- Tripping delay T_v adjustable 0; 0.1-30 s
- 1 x 2 c/o contacts (common signal) or 2 x 1 c/o contact (separate signals for >I and <I) configurable
- 1 x 2 c/o contacts (common signal) or 2 x 1 c/o contact (separate signals for >U and <U) configurable
- 22.5 mm width
- 3 LEDs for the indication of operational states
- Various approvals and marks

[1)] depending on device

Applications

- Protection of electronic or electromechanical devices against over- and under voltage or over- and under current
- DC motor speed control
- Battery monitoring
- Monitoring of AC or DC supplies
- Monitoring of heating or lighting circuits

Current monitoring, single-phase
The ABB current monitoring relays CM-SRS.xx reliably monitor the occurrence of currents that exceed or fall below the selected threshold value. The functions overcurrent or undercurrent monitoring can be preselected. Single- and multifunction devices for the monitoring of direct or alternating currents from 3 mA to 15 A are available.


Current window monitoring (I_{min}, I_{max})
The window monitoring relay CM-SFS.2x is available if the application requires the simultaneous monitoring of over- and undercurrents.

Voltage monitoring, single-phase
The ABB voltage monitoring relays CM-SRS.xx are used to monitor direct and alternating voltages within a range of 3-600 V. Over- or undervoltage detection can be preselected.

Voltage window monitoring (U_{min}, U_{max})
For the simultaneous detection of over- and undervoltages, the window monitoring relay CM-EFS.2 can be used.

Single-phase monitoring relays
Operating controls

Current monitoring relays



Adjustment of the threshold value >I for overcurrent

Adjustment of the tripping delay T_V

DIP switches
- ON-delay
- OFF-delay
- Closed-circuit principle
- Open-circuit principle
- Latching function activated
- Latching function not activated
- 2x1 c/o (SPDT) contact
- 1x2 c/o (SPDT) contacts

Adjustment of the threshold value <I for undercurrent

Indication of operational states
I: red LED – over- / under-current
R: yellow LED – relay status
U/T: green LED – control supply voltage/timing

Adjustment of the start-up delay T_S


Single-phase monitoring relays
Operating controls

Voltage monitoring relays

Adjustment of the threshold value >U for overvoltage

Adjustment of the tripping delay T_v

DIP switches
- ON-delay
- OFF-delay
- Closed-circuit principle
- Open-circuit principle
- Latching function activated
- Latching function not activated
- 2x1 c/o (SPDT) contact
- 1x2 c/o (SPDT) contacts



Adjustment of the threshold value <U for undervoltage

Indication of operational states
U: red LED – over- / under-voltage
R: yellow LED – relay status
U/T: green LED – control supply voltage/timing

Adjustment of the measuring range

Single-phase current monitoring relays

Selection table

	Order number	1SVR730840R0200	1SVR740840R0200	1SVR730841R0200	1SVR740841R0200	1SVR730841R1200	1SVR740841R1200	1SVR730840R0300	1SVR730841R0300	1SVR730841R1300	1SVR730840R0400	1SVR740840R0400	1SVR730841R0400	1SVR740841R0400	1SVR730841R1400	1SVR740841R1400	1SVR730840R0500	1SVR730841R0500	1SVR730841R1500	1SVR730840R0600	1SVR740840R0600	1SVR730840R0700	1SVR730760R0400	1SVR740760R0400	1SVR730760R0500
	Type	CM-SRS.11S	CM-SRS.11P	CM-SRS.11S	CM-SRS.11P	CM-SRS.11S	CM-SRS.11P	CM-SRS.12S	CM-SRS.12S	CM-SRS.12S	CM-SRS.21S	CM-SRS.21P	CM-SRS.21S	CM-SRS.21P	CM-SRS.21S	CM-SRS.21P	CM-SRS.22S	CM-SRS.22S	CM-SRS.22S	CM-SRS.M1S	CM-SRS.M1P	CM-SRS.M2S	CM-SFS.21S	CM-SFS.21P	CM-SFS.22S
Rated control supply voltage U_s																									
24 - 240 V AC/DC		■	■					■			■	■					■			■	■	■	■	■	■
110 - 130 V AC				■	■				■				■	■				■							
220 - 240 V AC						■	■			■					■	■			■						
Measuring ranges AC/DC																									
3 - 30 mA		■	■	■	■	■	■				■	■	■	■	■	■				■	■		■	■	
10 - 100 mA		■	■	■	■	■	■				■	■	■	■	■	■				■	■		■	■	
0.1 - 1 A		■	■	■	■	■	■				■	■	■	■	■	■				■	■		■	■	
0.3 - 1.5 A								■	■	■							■	■	■			■			■
1 - 5 A								■	■	■							■	■	■			■			■
3 - 15 A								■	■	■							■	■	■			■			■
Monitoring function																									
Over- or undercurrent		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■			
Window current monitoring																							■	■	■
Latching																				sel	sel	sel	sel	sel	sel
Open-circuit or closed-circuit principle																				sel	sel	sel	sel	sel	sel
Timing functions for tripping delay																									
ON-delay, 0.1 - 30 s											adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj			
ON- or OFF-delay, 0.1 - 30 s																							sel	sel	sel
Output																									
c/o contact		1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
Connection type																									
Push-in terminals			■		■		■					■		■		■					■			■	
Double-chamber cage connection terminals		■		■		■		■	■	■	■		■		■		■	■	■	■		■	■		■

adj: adjustable
sel: selectable

Single-phase current monitoring relays
Ordering details


2CDC 251 054 V0011

CM-SRS.22S


2CDC 251 056 V0011

CM-SFS.22P

Description

The CM range current monitoring relays protect single-phase mains (DC or AC) from over- and undercurrent from 3 mA to 15 A.

Ordering details

Description	Type	Order code	Weight (1 pc) kg (lb)
See selection table	CM-SRS.11S	1SVR730840R0200	0.145 (0.320)
		1SVR730841R0200	0.161 (0.355)
		1SVR730841R1200	0.161 (0.355)
	CM-SRS.11P	1SVR740840R0200	0.137 (0.302)
		1SVR740841R0200	0.153 (0.337)
		1SVR740841R1200	0.153 (0.337)
	CM-SRS.12S	1SVR730840R0300	0.137 (0.302)
		1SVR730841R0300	0.168 (0.370)
		1SVR730841R1300	0.168 (0.370)
	CM-SRS.21S	1SVR730840R0400	0.152 (0.335)
		1SVR730841R0400	0.179 (0.395)
		1SVR730841R1400	0.179 (0.395)
	CM-SRS.21P	1SVR740840R0400	0.141 (0.311)
		1SVR740841R0400	0.168 (0.370)
		1SVR740841R1400	0.168 (0.370)
	CM-SRS.22S	1SVR730840R0500	0.144 (0.399)
		1SVR730841R0500	0.181 (0.399)
		1SVR730841R1500	0.181 (0.399)
	CM-SRS.M1S	1SVR730840R0600	0.153 (0.337)
	CM-SRS.M1P	1SVR740840R0600	0.142 (0.313)
	CM-SRS.M2S	1SVR730840R0700	0.155 (0.342)
	CM-SFS.21S	1SVR730760R0400	0.150 (0.331)
	CM-SFS.21P	1SVR740760R0400	0.139 (0.306)
	CM-SFS.22S	1SVR730760R0500	0.158 (0.348)

S: screw connection
P: push-in connection

Single-phase voltage monitoring relays

Selection table

	Order number	1SVR730830R0300	1SVR740830R0300	1SVR730831R0300	1SVR740831R0300	1SVR730831R1300	1SVR740831R1300	1SVR730830R0400	1SVR740830R0400	1SVR730831R0400	1SVR740831R0400	1SVR730831R1400	1SVR740831R1400	1SVR730830R0500	1SVR740830R0500	1SVR730750R0400	1SVR740750R0400
	Type	CM-ESS.1S	CM-ESS.1P	CM-ESS.1S	CM-ESS.1P	CM-ESS.1S	CM-ESS.1P	CM-ESS.2S	CM-ESS.2P	CM-ESS.2S	CM-ESS.2P	CM-ESS.2S	CM-ESS.2P	CM-ESS.MS	CM-ESS.MP	CM-EFS.2S	CM-EFS.2P
Rated control supply voltage U_s																	
24 - 240 V AC/DC		■	■					■	■					■	■	■	■
110 - 130 V AC				■	■					■	■						
220 - 240 V AC						■	■					■	■				
Measuring ranges AC/DC																	
3 - 30 V		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
6 - 60 V		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
30 - 300 V		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
60 - 600 V		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Monitoring function																	
Over- or undervoltage		■	■	■	■	■	■	■	■	■	■	■	■	■	■		
Windows voltage monitoring																■	■
Latching														sel	sel	sel	sel
Open-circuit or closed-circuit principle														sel	sel	sel	sel
Timing functions for tripping delay																	
ON-delay, 0.1 - 30 s								adj	adj	adj	adj	adj	adj	adj	adj		
ON- or OFF-delay, 0.1 - 30 s																sel	sel
Output																	
c/o contact		1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2
Connection type																	
Push-in terminals			■		■		■		■		■		■		■		■
Double-chamber cage connection terminals		■		■		■		■		■		■		■		■	

adj: adjustable
sel: selectable

Single-phase voltage monitoring relays
Ordering details



CM-ESS.MP



CM-EFS.2

Description

The CM range voltage monitoring relays provide reliable monitoring of voltages, as well as the detection of phase loss in single-phase mains.

Ordering details

Description	Type	Order code	Weight (1 pc) kg (lb)
See selection table	CM-ESS.1S	1SVR730830R0300	0.135 (0.298)
		1SVR730831R0300	0.164 (0.362)
		1SVR730831R1300	0.164 (0.362)
	CM-ESS.1P	1SVR740830R0300	0.126 (0.278)
		1SVR740831R0300	0.155 (0.342)
		1SVR740831R1300	0.155 (0.342)
	CM-ESS.2S	1SVR730830R0400	0.153 (0.337)
		1SVR730831R0400	0.181 (0.399)
		1SVR730831R1400	0.181 (0.399)
	CM-ESS.2P	1SVR740830R0400	0.142 (0.313)
		1SVR740831R0400	0.170 (0.375)
		1SVR740831R1400	0.170 (0.375)
	CM-ESS.MS	1SVR730830R0500	0.154 (0.340)
	CM-ESS.MP	1SVR740830R0500	0.143 (0.320)
	CM-EFS.2S	1SVR730750R0400	0.157 (0.346)
	CM-EFS.2P	1SVR740750R0400	0.146 (0.322)

S: screw connection
P: push-in connection

Single-phase current monitoring relays
Technical data

Type		**CM-SRS.1**	**CM-SRS.2**	**CM-SRS.M**	**CM-SFS.2**
Input circuit - Supply circuit		**A1-A2**			
Rated control supply voltage U_s	A1-A2	110-130 V AC			
	A1-A2	220-240 V AC			
	A1-A2	24-240 V AC/DC			
Rated control supply voltage U_s tolerance		-15...+10 %			
Rated frequency	AC versions	50/60 Hz			
	AC/DC versions	50/60 Hz or DC			
Current / power consumption		see data sheets			
Power failure buffering time		20 ms			
Transient overvoltage protection		Varistors			
Input circuit - Measuring circuit		**B1/B2/B3-C**			
Monitoring function		over- or undercurrent monitoring configurable			over- and under-current monitoring
Measuring method		True RMS measuring principle			
Measuring inputs		**CM-SxS.x1**		**CM-SxS.x2**	
	Terminal connection	B1-C	B2-C	B3-C	B1-C	B2-C	B3-C
	Measuring ranges AC/DC	3-30 mA	10-100 mA	0.1-1 A	0.3-1.5 A	1-5 A	3-15 A[1)]
	Input resistance	3.3 Ω	1 Ω	0.1 Ω	0.05 Ω	0.01 Ω	0.0025 Ω
	Pulse overload capacity t< 1 s	500 mA	1 A	10 A	15 A	50 A	100 A
	Continuous capacity	50 mA	150 mA	1.5 A	2 A	7 A	17 A
Threshold value(s)		adjustable within the indicated measuring range			
Setting accuracy of threshold value		10 % of full-scale value			
Hysteresis related to the threshold value		3-30 % adjustable			5 % fixed
Measuring signal frequency range		DC / 15 Hz - 2 kHz			
Rated measuring signal frequency range		DC / 50-60 Hz			
Maximum response time		AC: 80 ms / DC: 120 ms			
Accuracy within the control supply voltage tolerance		$\Delta U \leq 0.5$ %			
Accuracy within the temperature range		$\Delta U \leq 0.06$ % / °C			
Timing circuit					
Start-up delay T_s		none		0 or 0.1-30 s adjustable	
Tripping delay T_v		none	0 or 0.1-30 s adjustable		
Repeat accuracy (constant parameters)		±0.07 % of full scale			
Accuracy within the control supply voltage tolerance		-	Δt ≤ 0.5 %		
Accuracy within the temperature range		-	Δt ≤ 0.06 % / °C		
Indication of operational states					
Control supply voltage	U/T: green LED	⎍⎺⎺⎺⎺⎺⎍: control supply voltage applied, ⎍⎍⎍⎍⎍⎺⎺⎺⎺⎺

Single-phase current monitoring relays

Technical data

Type		CM-SRS.1	CM-SRS.2	CM-SRS.M	CM-SFS.2
Output circuits		**11(15)-12(16)/14(18), 21(25)-22(26)/24(28) - Relays**			
Kind of output		1 c/o contact	2 c/o contacts		1x2 c/o contacts or 2x1 c/o contact configurable
Operating principle		open-circuit principle [2]		open- or closed-circuit principle configurable [2]	
Contact material		AgNi			
Minimum switching voltage / minimum switching current		24 V / 10 mA			
Maximum switching voltage / maximum switching current		250 V AC / 4 A AC			
Rated operational voltage U_e and rated operational current I_e	AC-12 (resistive) at 230 V	4 A			
	AC-15 (inductive) at 230 V	3 A			
	DC-12 (resistive) at 24 V	4 A			
	DC-13 (inductive) at 24 V	2 A			
AC rating (UL 508)	Utilization category (Control Circuit Rating Code)	B 300			
	max. rated operational voltage	300 V AC			
	max. continuous thermal current at B 300	5 A			
	max. making/breaking apparent power (Make/Break) at B 300	3600/360 VA			
Mechanical lifetime		$30x10^6$ switching cycles			
Electrical lifetime (AC-12, 230 V, 4 A)		$0.1x10^6$ switching cycles			
Max. fuse rating to achieve short-circuit protection	n/c contact	6 A fast-acting	10 A fast-acting		6 A fast-acting
	n/o contact	10 A fast-acting			

[1] In case of measured currents > 10 A, lateral spacing has to be min. 10 mm

[2] Open-circuit principle: output relay energizes if the measured value exceeds ⊣/ / falls below ⊣\ the adjusted threshold value
Closed-circuit principle: output relay de-energizes if measured value exceeds ⊣/ / falls below ⊣\ the adjusted threshold value

Single-phase current monitoring relays
Technical data

Type		CM-SRS.1	CM-SRS.2	CM-SRS.M	CM-SFS.2
General data					
MTBF		on request			
Duty cycle		100%			
Dimensions		see dimensional drawings			
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool			
Mounting position		any			
Minimum distance to other units		10 mm (0.39 in) at measured current > 10 A			
Material of housing		UL 94 V-0			
Degree of protection	housing / terminals	IP50 / IP20			
Electrical connection					
Connecting capacity		**Screw connection technology**		**Easy Connect Technology (Push-in)**	
	fine-strand with(out) wire end ferrule	1 x 0.5-2.5 mm² (1 x 20-14 AWG) 2 x 0.5-1.5 mm² (2 x 20-16 AWG)		2 x 0.5-1.5 mm² (2 x 20-16 AWG)	
	rigid	1 x 0.5-4 mm² (1 x 20-12 AWG) 2 x 0.5-2.5 mm² (2 x 20-14 AWG)		2 x 0.5-1.5 mm² (2 x 20-16 AWG)	
Stripping length		8 mm (0.32 in)			
Tightening torque		0.6-0.8 Nm (7.08 lb.in)		-	
Environmental data					
Ambient temperature range	operation / storage	-20...+60 °C / -40...+85 °C			
Damp heat (IEC 60068-2-30)		55 °C, 6 cycles			
Vibration (sinusoidal)		class 2			
Shock		class 2			
Isolation data					
Rated insulation voltage	supply / measuring circuit / output	600 V			
	supply / output 1/2	250 V			
Rated impulse withstand voltage U_{imp}	supply /measuring circuit / output	6 kV 1.2/50 µs			
	supply / output 1/2	4 kV 1.2/50 µs			
Pollution degree		3			
Overvoltage category		III			
Standards / Directives					
Standards		IEC/EN 60255-27, IEC/EN 60947-5-1, EN 50178			
Low Voltage Directive		2014/35/EU			
EMC Directive		2014/30/EU			
RoHS Directive		2011/65/EU			
Electromagnetic compatibility					
Interference immunity to		IEC/EN 61000-6-2			
electrostatic discharge	IEC/EN 61000-4-2	level 3			
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3			
electrical fast transient / burst	IEC/EN 61000-4-4	level 3			
surge	IEC/EN 61000-4-5	level 3			
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3			
Interference emission		IEC/EN 61000-6-3			
high-frequency radiated	IEC/CISPR 22; EN 55022	Class B			
high-frequency conducted	IEC/CISPR 22; EN 55022	Class B			

Single-phase voltage monitoring relays
Technical data

Type		**CM-ESS.1**	**CM-ESS.2**	**CM-ESS.M**	**CM-EFS.2**
Input circuit - Supply circuit		**A1-A2**			
Rated control supply voltage U_s	A1-A2	110-130 V AC			
	A1-A2	220-240 V AC			
	A1-A2	24-240 V AC/DC			
Rated control supply voltage U_s tolerance		-15...+10 %			
Rated frequency	AC versions	50/60 Hz			
	AC/DC versions	50/60 Hz or DC			
Current / power consumption		see data sheet			
Power failure buffering time		20 ms			
Transient overvoltage protection		varistors			
Input circuit - Measuring circuit		**B-C**			
Monitoring function		over- or undervoltage monitoring configurable			over- and under voltage monitoring configurable
Measuring method		True RMS measuring principle			
Measuring inputs		**CM-ExS**			
	Terminal connection	B-C	B-C	B-C	B-C
	Measuring range AC/DC	3-30 V	6-60 V	30-300 V	60-600 V
	Input resistance	600 kΩ	600 kΩ	600 kΩ	600 kΩ
	Pulse overload capacity t < 1 s	800 V	800 V	800 V	800 V
	Continuous capacity	660 V	660 V	660 V	660 V
Threshold value(s)		adjustable within the indicated measuring range			
Tolerance of the adjusted threshold value		10 % of full-scale value			
Hysteresis related to the threshold value		3-30 % adjustable			5 % fixed
Measuring signal frequency range		DC / 15 Hz - 2 kHz			
Rated measuring signal frequency range		DC / 50-60 Hz			
Maximum response time		AC: 80 ms / DC: 120 ms			
Accuracy within the control supply voltage tolerance		ΔU ≤ 0.5 %			
Accuracy within the temperature range		ΔU ≤ 0.06 % / °C			
Transient overvoltage protection		Varistors			
Timing circuit					
Delay time T_V		none	0 or 0.1-30 s adjustable		
Repeat accuracy (constant parameters)		±0.07 % of full scale value			
Accuracy within the control supply voltage tolerance		-	Δt ≤ 0.5 %		
Accuracy within the temperature range		-	Δt ≤ 0.06 % / °C		
Indication of operational states					
Control supply voltage	U/T: green LED	⎍‾‾‾‾⎍: control supply voltage applied ⎍⎍⎍⎍⎍: tripping delay T_V active			
Measured value	U: red LED	⎍‾‾‾‾⎍: overvoltage, ⎍⎍⎍⎍⎍: undervoltage			
Relay status	R: yellow LED	⎍‾‾‾‾⎍: relay energized, no latching function ⎍⎍⎍⎍⎍: relay energized, active latching function ⎍⎍⎍⎍⎍: relay de-energized, active latching function			

Single-phase voltage monitoring relays
Technical data

Type		CM-ESS.1	CM-ESS.2	CM-ESS.M	CM-EFS.2
Output circuits					
Kind of output		1 c/o contact	2 c/o contacts		1x2 c/o contacts or 2x1 c/o contact configurable
Operating principle		open-circuit principle[1)]		open- or closed-circuit principle configurable[1)]	
Contact material		AgNi			
Minimum switching voltage / minimum switching current		24 V / 10 mA			
Maximum switching voltage / maximum switching current		250 V AC / 4 A AC			
Rated operational voltage U_e and rated operational current I_e	AC-12 (resistive) at 230 V	4 A			
	AC-15 (inductive) at 230 V	3 A			
	DC-12 (resistive) at 24 V	4 A			
	DC-13 (inductive) at 24 V	2 A			
AC rating (UL 508)	Utilization category (Control Circuit Rating Code)	B 300			
	max. rated operational voltage	300 V AC			
	max. continuous thermal current at B 300	5 A			
	max. making/breaking apparent power (Make/Break) at B 300	3600/360 VA			
Mechanical lifetime		$30x10^6$ switching cycles			
Electrical lifetime	AC-12, 230 V, 4 A	$0.1x10^6$ switching cycles			
Max. fuse rating to achieve short-circuit protection	n/c contact	6 A fast-acting	10 A fast-acting		6 A fast-acting
	n/o contact	10 A fast-acting			

Single-phase voltage monitoring relays

Technical data


Type		CM-ESS.1	CM-ESS.2	CM-ESS.M	CM-EFS.2
General data					
MTBF		on request			
Duty cycle		100%			
Dimensions		see dimensional drawings			
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool			
Mounting position		any			
Minimum distance to other units	vertical / horizontal	not necessary / not necessary			
Material of housing		UL 94 V-0			
Degree of protection	housing / terminals	IP50 / IP20			
Environmental data					
Ambient temperature ranges	operation	-20...+60 °C			
	storage	-40...+85 °C			
Damp heat, cyclic (IEC/EN 60068-2-30)		55 °C, 6 cycle			
Vibration, sinusoidal		class 2			
Shock		class 2			
Electrical connection					
Wire size		**Screw connection technology**		**Easy Connect Technology (Push-in)**	
	fine-strand with(out) wire end ferrule	1 x 0.5-2.5 mm² (1 x 18-14 AWG) 2 x 0.5-1.5 mm² (2 x 18-16 AWG)		2 x 0.5-1.5 mm² (2 x 18-16 AWG)	
	rigid	1 x 0.5-4 mm² (1 x 20-12 AWG) 2 x 0.5-2.5 mm² (2 x 20-14 AWG)		2 x 0.5-1.5 mm² (2 x 20-16 AWG)	
Stripping length		8 mm (0.32 in)			
Tightening torque		0.6-0.8 Nm (7.08 lb.in)		-	
Isolation data					
Rated insulation voltage	supply / measuring circuit / output	600 V			
	supply / output 1/2	250 V			
Rated impulse withstand voltage U_{imp}	supply / measuring circuit / output	6 kV 1.2/50 µs			
	supply / output 1/2	4 kV 1.2/50 µs			
Pollution degree		3			
Overvoltage category		III			
Standards / Directives					
Product standard		IEC/EN 60255-27, IEC/EN 60947-5-1, EN 50178			
Low Voltage Directive		2014/35/EU			
EMC Directive		2014/30/EU			
RoHS Directive		2011/65/EU			
Electromagnetic compatibility					
Interference immunity to		IEC/EN 61000-6-2			
electrostatic discharge	IEC/EN 61000-4-2	level 3			
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3			
electrical fast transient / burst	IEC/EN 61000-4-4	level 3			
surge	IEC/EN 61000-4-5	level 3			
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3			
Interference emission		IEC/EN 61000-6-3			
high-frequency radiated	IEC/CISPR 22; EN 55022	class B			
high-frequency conducted	IEC/CISPR 22; EN 55022	class B			


1) Open-circuit principle: output relay energizes if the measured value exceeds ⧸ / falls below ⧹ the adjusted threshold value
Closed-circuit principle: output relay de-energizes if measured value exceeds ⧸ / falls below ⧹ the adjusted threshold value

Single-phase current monitoring relays
Technical diagrams

Connection diagram


CM-SRS.1x, CM-SRS.2x






A1-A2	Control supply voltage
B1-C	Measuring range 1: 3-30 mA or 0.3-1.5 A
B2-C	Measuring range 2: 10-100 mA or 1-5 A
B3-C	Measuring range 3: 0.1-1 A or 3-15 A
11_{15}-12_{16}/14_{18} 21_{25}-22_{26}/24_{28}	Output contacts - open-circuit principle

CM-SRS.Mx




A1-A2	Control supply voltage
B1-C	Measuring range 1: 3-30 mA or 0.3-1.5 A
B2-C	Measuring range 2: 10-100 mA or 1-5 A
B3-C	Measuring range 3: 0.1-1 A or 3-15 A
11_{15}-12_{16}/14_{18} 21_{25}-22_{26}/24_{28}	Output contacts - open- or closed circuit principle

CM-SFS.2x



A1-A2	Control supply voltage
B1-C	Measuring range 1: 3-30 mA or 0.3-1.5 A
B2-C	Measuring range 2: 10-100 mA or 1-5 A
B3-C	Measuring range 3: 0.1-1 A or 3-15 A
11_{15}-12_{16}/14_{18} 21_{25}-22_{26}/24_{28}	Output contacts - open- or closed circuit principle


CM-SRS.2x



A1-A2	Control supply voltage
B1-C	Measuring range 1: 3-30 mA or 0.3-1.5 A
B2-C	Measuring range 2: 10-100 mA or 1-5 A
B3-C	Measuring range 3: 0.1-1 A or 3-15 A
11_{15}-12_{16}/14_{18} 21_{25}-22_{26}/24_{28}	Output contacts - open- or closed circuit principle

DIP switch functions


CM-SRS.1x, CM-SRS.2x



1	ON	Undercurrent monitoring
	OFF	Overcurrent monitoring

OFF = Default


CM-SRS.Mx



1	ON	Undercurrent monitoring
	OFF	Overcurrent monitoring
2	ON	Closed-circuit principle
	OFF	Open-circuit principle
3	ON	Latching function activated
	OFF	Latching function not activated

OFF = Default


CM-SFS.2x



1	ON	OFF-delay
	OFF	ON-delay
2	ON	Closed-circuit principle
	OFF	Open-circuit principle
3	ON	Latching function activated
	OFF	Latching function not activated
4	ON	2x1 c/o contact
	OFF	1x2 c/o contacts

OFF = Default

CM-SRS.2x




1	ON	Undercurrent monitoring
	OFF	Overcurrent monitoring
2	ON	Closed-circuit principle
	OFF	Open-circuit principle
3	ON	Latching function activated
	OFF	Latching function not activated


OFF = Default

Single-phase voltage monitoring relays
Technical diagrams

Connection diagram


CM-ESS.1, CM-ESS.2






A1-A2	Control supply voltage
B-C	Measuring ranges AC/DC: 3-30 V; 6-60 V; 30-300 V; 60-600 V
11_{15}-12_{16}/14_{18} 21_{25}-22_{26}/24_{28}	Output contacts - open-circuit principle

CM-EFS.2



A1-A2	Control supply voltage
B-C	Measuring ranges AC/DC: 3-30 V; 6-60 V; 30-300 V; 60-600 V
11_{15}-12_{16}/14_{18} 21_{25}-22_{26}/24_{28}	Output contacts - open- or closed circuit principle


CM-ESS.M



A1-A2	Control supply voltage
B-C	Measuring ranges AC/DC: 3-30 V; 6-60 V 30-300 V; 60-600 V
11_{15}-12_{16}/14_{18} 21_{25}-22_{26}/24_{28}	Output contacts - open- or closed circuit principle


DIP switch functions

CM-ESS.1, CM-ESS.2




1	ON	Undervoltage monitoring
	OFF	Overvoltage monitoring
OFF = Default		

CM-EFS.2



1	ON	ON-delay
	OFF	OFF-delay
2	ON	Closed-circuit principle
	OFF	Open-circuit principle
3	ON	Latching function activated
	OFF	Latching function not activated
4	ON	2x1 c/o contact
	OFF	1x2 c/o contacts
OFF = Default		

CM-ESS.M



1	ON	Undervoltage monitoring
	OFF	Overvoltage monitoring
2	ON	Closed-circuit principle
	OFF	Open-circuit principle
3	ON	Latching function activated
	OFF	Latching function not activated
OFF = Default		


Single-phase monitoring relays
Function diagrams

CM-SRS.1x and CM-SRS.2x


If the measured value exceeds resp. drops below the adjusted threshold value, the output relay(s) energize(s): on the CM-SRS.1x - immediately, on the CM-SRS.2x - after the set tripping delay T_V. If the measured value exceeds resp. drops below the threshold value plus resp. minus the adjusted hysteresis, the output relay(s) de-energize(s). The hysteresis is adjustable within a range of 3-30 % of the threshold value.

CM-SRS.1x

Overcurrent monitoring




Undercurrent monitoring




CM-SRS.2x

Overcurrent monitoring



Undercurrent monitoring



Further function diagrams see data sheet.

Single-phase monitoring relays


Function diagrams

CM-SRS.Mx


If the measured value exceeds resp. drops below the adjusted threshold value before the set start-up delay T_S is complete, the output relays do not change their actual state. If the measured value exceeds resp. drops below the adjusted threshold value when T_S is complete, the tripping delay T_V starts. If T_V is complete and the measured value is still exceeding resp. below the threshold value plus resp. minus the set hysteresis, the output relays energize / de-energize.

If the measured value exceeds resp. drops below the threshold value minus resp. plus the set hysteresis and the latching function is not activated, the output relays de-energize / energize. With activated latching function the output relays remain energized and de-energize only when the supply voltage is interrupted / the output relays remain de-energized and energize only when the supply voltage is switched off and then again switched on = Reset.
The hysteresis is adjustable within a range of 3-30 % of the threshold value.


Overcurrent monitoring with latching




Overcurrent monitoring without latching



Undercurrent monitoring with latching




Undercurrent monitoring without latching



Further function diagrams see data sheet.


Single-phase monitoring relays
Function diagrams

CM-SFS.2x
Current window monitoring 1x2 c/o contact 1x2 c/o
ON-delayed ⊠ without latching ▭



ON-delayed ⊠ current window monitoring with parallel switching c/o contacts 1x2 c/o:
If the measured value exceeds resp. drops below the adjusted threshold value before the set start-up delay T_S is complete, the output relays do not change their actual state.
If the measured value exceeds resp. drops below the adjusted threshold value when T_S is complete, the tripping delay T_V starts when ⊠ is configured. If T_V is complete and the measured value is still exceeding resp. below the threshold value minus resp. plus the fixed hysteresis (5%), the output relays energize open /de-energize closed.
If the measured value exceeds resp. drops below the threshold value plus resp. minus the hysteresis and the latching function is not activated ▭, the output relays de-energize open / energize closed. With activated latching function ⊠ the output relays remain energized open and de-energize only when the supply voltage is interrupted / the output relays remain de-energized closed and energize only when the supply voltage is switched off and then again switched on = Reset.

Current window monitoring 1x2 c/o contact 1x2 c/o
OFF-delayed ■ without latching ⊠



OFF-delayed ■ current window monitoring with parallel switching c/o contacts 1x2 c/o:
If the measured value exceeds resp. drops below the adjusted threshold value when the set start-up delay T_S is complete, the output relays energize open / de-energize closed, when ■ is configured, and remain in this position during the set tripping delay T_V. If the measured value exceeds resp. drops below the threshold value plus resp. minus the fixed hysteresis (5%) and the latching function is not activated ⊠, the tripping delay T_V starts. After completion of T_V, the output relays de-energize open / energize closed, provided that the latching function is not activated ⊠. With activated latching function ▭ the output relays remain energized open and de-energize only when the supply voltage is interrupted / the output relays remain de-energized closed and energize only when the supply voltage is switched off and then again switched on = Reset. When 2x1 c/o is adjusted on the device, the functionality is equivalent to the one described above. In this case, instead of both output relays, only one output relay each will be switched.
">I" = 11_{15}-12_{16}/14_{18} ; "<I" = 21_{25}-22_{26}/24_{28}

Further function diagrams see data sheet.


Single-phase monitoring relays
Function diagrams

CM-ESS.1x and CM-ESS.2x


Depending on the configuration, the voltage monitoring relays CM-ESS.1 and CM-ESS.2 can be used for over- or under-voltage monitoring in single-phase AC and/or DC systems. The voltage to be monitored (measured value) is applied to terminals B-C. The devices work according to the open-circuit principle. If the measured value exceeds resp. drops below the adjusted threshold value, the output relay(s) energize(s): on the CM-ESS.1 - immediately, on the CM-ESS.2 - after the set tripping delay T_V. If the measured value exceeds resp. drops below the threshold value plus resp. minus the adjusted hysteresis, the output relay(s) de-energize(s). The hysteresis is adjustable within a range of 3-30 % of the threshold value.

CM-ESS.1x

Overvoltage monitoring




Undervoltage monitoring




CM-ESS.2x

Overvoltage monitoring



Undervoltage monitoring




Further function diagrams see data sheet.

Single-phase monitoring relays
Function diagrams


CM-ESS.Mx

If the measured value exceeds resp. drops below the adjusted threshold value, the tripping delay T_V starts. If T_V is complete and the measured value is still exceeding resp. below the threshold value plus resp. minus the set hysteresis, the output relays energize / de-energize.
If the measured value exceeds resp. drops below the threshold value plus resp. minus the set hysteresis and the latching function is not activated, the output relays de-energize / energize. With activated latching function the output relays remain energized and de-energize only when the supply voltage is interrupted / the output relays remain de-energized and energize only when the supply voltage is switched off and then again switched on = Reset. The hysteresis is adjustable within a range of 3-30 % of the threshold value.


Overvoltage monitoring without latching




Overvoltage monitoring with latching



Undervoltage monitoring without latching



Undervoltage monitoring without latching




Further function diagrams see data sheet.


Single-phase monitoring relays
Function diagrams

CM-EFS.2x

Voltage window monitoring 1x2 c/o contact 1x2 c/o
ON-delayed ⊠ without latching ⊠



Voltage window monitoring 1x2 c/o contact 1x2 c/o
OFF-delayed ■ without latching ⊠



ON-delayed ⊠ voltage window monitoring with parallel switching c/o contacts 1x2 c/o:
If the measured value exceeds resp. drops below the adjusted threshold value, the tripping delay T_V starts, when ⊠ is configured. If T_V is complete and the measured value is still exceeding resp. below the threshold value minus resp. plus the fixed hysteresis (5%), the output relays energize open / de-energize closed.
If the measured value exceeds resp. drops below the threshold value plus resp. minus the hysteresis and the latching function is not activated ⊠, the output relays de-energize open / energize closed. With activated latching function ⊠ the output relays remain energized open and de-energize only when the supply voltage is interrupted / the output relays remain de-energized closed and energize only when the supply voltage is switched off and then again switched on = Reset.

OFF-delayed ■ voltage window monitoring with parallel switching c/o contacts 1x2 c/o:
If the measured value exceeds resp. drops below the adjusted threshold value, the output relays energize open / de-energize closed, when ■ is configured, and remain in this position during the set tripping delay T_V.

If the measured value exceeds resp. drops below the threshold value plus resp. minus the fixed hysteresis (5%) and the latching function is not activated ⊠, the tripping delay T_V starts.

After completion of T_V, the output relays de-energize open / energize closed, provided that the latching function is not activated ⊠. With activated latching function ⊠ the output relays remain energized open and de-energize only when the supply voltage is interrupted / the output relays remain de-energized closed and energize only when the supply voltage is switched off and then again switched on = Reset. When 2x1 c/o is adjusted on the device, the functionality is equivalent to the one described above. In this case, instead of both output relays, only one output relay each will be switched.
">U" = 11_{15}-12_{16}/14_{18} ; "<U" = 21_{25}-22_{26}/24_{28}

Further function diagrams see data sheet.


L1 L2 L3
ABB
CM-PFE
CM-PAS
CM-MPN
CM-PSS
Asym. %
Time s
R/T
F1
F2
Function
12 11 14
26 25 28
16

Three-phase monitoring relays
Table of contents

106 Benefits and advantages
109 Function
110 Operating controls
112 Selection table - singlefunctional
113 Ordering details - singlefunctional
114 Selection table - multifunctional
115 Ordering details - multifunctional
116 Technical data
127 Technical diagrams
129 Function diagrams

Three-phase monitoring relays
Benefits and advantages



For the monitoring of voltages in a three-phase system or network, ABB's CM range contains a wide selection of powerful and compact devices. This product range includes voltage monitoring relays for phase sequence, phase loss, unbalance and monitoring of over- and under voltage from 160 V to 820 V.



Continuous operation

Read the status of the relay at a glance: clear visualization of the device status via LEDs. Easy to adjust with rotary wheels and variants with push-in terminals make a quick and easy installation and setting possible.



Reliable in harsh conditions

All relays work reliably in environments with low temperatures down to -25°C. Additionally, the housing fulfills the UL 94 V-0 flammability standard requirements. Together with the vibration resistant push-in terminals, the relay is not only reliable no matter the environment temperature but is also durable to shock and vibration. Save time as retightening is no longer needed and enhance the reliability and safety not only for the equipment.



Easy installation

Like all devices from the measuring and monitoring portfolio, the three-phase monitoring relays are easily configurable via front facing potentiometers. Easy threshold configuration without calculation is accomplished by direct reading scales. For further configuration options, additional settings can be made via dip-switches, offering the flexibility to configure, for example, the working principle of the relays and the output configuration. The device can be set up before installation in the application and easy adjustments during the process are possible.

Three-phase monitoring relays
Benefits and advantages

Characteristics

- True RMS (TRMS) measuring principle
- Device for the use in mains with a frequency of 45-440 Hz and where harmonics are to be expected[1)]
- Adjustable phase unbalance threshold value
- Adjustable ON-delay/OFF-delay time
- Powered by the measuring circuit
- 1 n/o contact, 1 or 2 c/o contacts
- LEDs for the indication of operational states
- Multifunctional and singlefunctional devices
- Phase failure detection
- Phase sequence monitoring
- Over- and undervoltage monitoring (fixed or adjustable)
- Wide-range operating voltage guarantees world-wide operation
- Various approvals and marks

[1)] devices CM-MPS.23 and CM-MPS.43


Applications

- Control for connection of moving equipment (e.g. air conditioning compressors, refrigerated trucks and containers, and cranes)
- Control against reverse motor operation (lifting, handling, elevators, escalators, etc.)
- Control of sensitive three-phase supplies
- Overheating of the motor due to asymmetrical voltage
- Protection of a plant against destruction due to overvoltage
- Direction of rotation of the drive









—

Three-phase monitoring relays have many functions to protect various applications

Three-phase monitoring relays
Function

Phase unbalance monitoring
If the supply by the three-phase system is unbalanced due to an uneven distribution of the load, the motor will convert a part of the energy into reactive power. This energy gets lost unexploited; also the motor is exposed to higher thermal stress. Other thermal protection devices fail to detect continuing unbalances, which can lead to damage or destruction of the motor. The CM range three-phase monitors with phase unbalance monitoring can reliably detect this critical situation.


Phase sequence
Changing the phase sequence during operation or a wrong phase sequence prior to startup causes a change of the rotational direction of the connected device. Generators, pumps or fans rotate in the wrong direction and the installation is no longer working properly. In particular, for moveable equipment, such as construction machinery, phase sequence detection prior to the startup process is highly reasonable.

Phase loss
In case of phase loss, undefined stats of the installation are likely to occur; e.g. the startup process of motors is disturbed. All three-phase monitors of the ABB CM range detect a phase loss as soon as the voltage of one phase drops below 60 % of its nominal value.

Voltage monitoring
All electric devices can be damaged when operated continuously in a network with out-of-range voltages. For example, safe starting is not ensured in case of undervoltage. Also, the switching state of a contactor is not clearly defined when operated in a "forbidden" voltage range. This can lead to undefined states of the installation and cause damage or destruction of valuable parts.


Selectable phase sequence monitoring
The phase sequence monitoring can be switched off by means of a rotary switch or a DIP switch. This enables monitoring of three-phase mains where phase sequence is not relevant for the application, for example in case of motors with forward and reverse rotation, heating applications, etc.

Automatic phase sequence correction
The automatic phase sequence correction is activated by means of a DIP switch. With activated phase sequence correction, it is ensured that for any non-fixed or portable equipment, e.g. construction machinery, the correct phase sequence is always applied to the input terminals of the load. For details regarding the wiring, please see function description / diagrams.



Three-phase monitoring relays
Operating controls

S-range housing



Adjustment of the threshold value >U for overvoltage

Adjustment of the threshold value Asymetry for phase unbalance

DIP switches
- ON-delay
- OFF-delay
- Phase sequence monitoring deactivated
- Phase sequence monitoring activated
- Phase sequence correction activated
- Phase sequence correction deactivated
- 2x1 c/o (SPDT) contact
- 1x2 c/o (SPDT) contacts


Adjustment of the threshold value <U for undervoltage

Indication of operational states
R/T: red LED – Relay status / timing
F1: yellow LED – Fault message
F2: yellow LED – Fault message

Adjustment of the tripping delay T

Three-phase monitoring relays
Operating controls

N-range housing



Adjustment of the threshold value Asymmetry for phase unbalance

Adjustment of the threshold value >U for overvoltage

Adjustment of the threshold value <U for undervoltage

Indication of operational states
R/T: red LED – Relay status / timing
F1: yellow LED – Fault message
F2: yellow LED – Fault message

Adjustment of the tripping delay T

DIP switches
- ON-delay
- OFF-delay
- Phase sequence monitoring deactivated
- Phase sequence monitoring activated
- Phase sequence correction activated
- Phase sequence correction deactivated
- 2x1 c/o (SPDT) contact
- 1x2 c/o (SPDT) contacts

Three-phase monitoring relays

Selection table - singlefunctional

	Order number	1SVR550881R9400	1SVR550882R9500	1SVR550870R9400	1SVR550871R9500	1SVR550824R9100	1SVR550826R9100	1SVR730824R9300	1SVR740824R9300	1SVR730784R2300	1SVR740784R2300	1SVR730784R3300	1SVR740784R3300	1SVR730794R1300	1SVR740794R1300	1SVR730794R3300	1SVR740794R3300	1SVR730794R2300	1SVR740794R2300	1SVR730774R1300	1SVR740774R1300	1SVR730774R3300	1SVR740774R3300
	Type	CM-PBE	CM-PBE	CM-PVE	CM-PVE	CM-PFE	CM-PFE.2	CM-PFS.S	CM-PFS.P	CM-PSS.31S	CM-PSS.31P	CM-PSS.41S	CM-PSS.41P	CM-PVS.31S	CM-PVS.31P	CM-PVS.41S	CM-PVS.41P	CM-PVS.81S	CM-PVS.81P	CM-PAS.31S	CM-PAS.31P	CM-PAS.41S	CM-PAS.41P
Rated control supply voltage U_s																							
Phase to phase																							
160-300 V AC														■	■					■	■		
200-400 V AC																		■	■				
200-500 V AC						■	■	■															
208-440 V AC					■																		
300-500 V AC																■	■					■	■
320-460 V AC			■	■																			
380 V AC									■	■													
380-440 V AC	■	■																					
400 V AC											■	■											
Phase to neutral																							
185-265 V AC			■																				
220-240 V AC	■																						
Rated frequency																							
50/60 Hz	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Suitable for monitoring																							
Single-phase mains	■		■																				
Three-phase mains	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Monitoring function																							
Phase failure	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Phase sequence					■	■	■	■	sel	sel	sel	sel	sel	sel	sel	sel	sel	sel	■	■	■	■	■
Overvoltage			■	■					■	■	■	■	■	■	■	■	■	■					
Undervoltage			■	■					■	■	■	■	■	■	■	■	■	■					
Unbalance																			■	■	■	■	■
Neutral[1)]	■		■																				
Thresholds																							
adjustable (adj) or fixed (fix)	fix	fix	fix	fix	fix	fix	fix	fix	fix	fix	fix	fix	fix	fix	adj	adj	adj	adj	adj	adj	adj	adj	adj
Timing functions for tripping delay																							
ON delay							fix	fix											sel	sel	sel	sel	
On and OFF delay	fix	fix	fix	fix	fix	fix			adj	adj	adj	adj	adj	adj	adj	adj	adj	adj					
Connection type																							
Push-in terminals										■		■		■		■		■		■		■	
Double-chamber cage connection terminals									■		■		■		■		■		■		■		■

(1) The external conductor voltage towards the neutral conductor is measured.

adj: adjustable
sel: selectable
fix: fixed

Three-phase monitoring relays

Ordering details - singlefunctional



CM-PBE



CM-PSS.41P



CM-PAS.31P

Description

The three-phase monitoring relays are designed for use in three-phase mains for monitoring the phase parameters like phase sequence, phase failure, over- and undervoltage, as well as phase unbalance.

Ordering details

Characteristics	Type	Order code	Weight (1 pc) kg (lb)
See selection table	CM-PBE	1SVR550881R9400	0.08 (0.17)
	CM-PBE	1SVR550882R9500	0.08 (0.17)
	CM-PVE	1SVR550870R9400	0.08 (0.17)
	CM-PVE	1SVR550871R9500	0.08 (0.17)
	CM-PFE	1SVR550824R9100	0.08 (0.17)
	CM-PFE.2	1SVR550826R9100	0.067 (0.147)

Characteristics	Type	Order code	Weight (1 pc) kg (lb)
See selection table	CM-PFS.S	1SVR730824R9300	0.127 (0.280)
	CM-PFS.P	1SVR740824R9300	0.119 (0.262)
	CM-PSS.31S	1SVR730784R2300	0.132 (0.291)
	CM-PSS.31P	1SVR740784R2300	0.123 (0.271)
	CM-PSS.41S	1SVR730784R3300	0.132 (0.291)
	CM-PSS.41P	1SVR740784R3300	0.123 (0.271)
	CM-PVS.31S	1SVR730794R1300	0.141 (0.311)
	CM-PVS.31P	1SVR740794R1300	0.132 (0.291)
	CM-PVS.41S	1SVR730794R3300	0.139 (0.306)
	CM-PVS.41P	1SVR740794R3300	0.131 (0.289)
	CM-PVS.81S	1SVR730794R2300	0.136 (0.300)
	CM-PVS.81P	1SVR740794R2300	0.128 (0.282)
	CM-PAS.31S	1SVR730774R1300	0.133 (0.293)
	CM-PAS.31P	1SVR740774R1300	0.124 (0.273)
	CM-PAS.41S	1SVR730774R3300	0.132 (0.291)
	CM-PAS.41P	1SVR740774R3300	0.123 (0.271)

S: screw connection
P: push-in connection

Three-phase monitoring relays

Selection table - multifunctional

	Order number	1SVR730885R1300	1SVR740885R1300	1SVR730885R3300	1SVR740885R3300	1SVR730884R1300	1SVR740884R1300	1SVR730884R3300	1SVR740884R3300	1SVR730885R4300	1SVR740885R4300	1SVR730884R4300	1SVR740884R4300	1SVR750487R8300	1SVR760487R8300	1SVR750488R8300	1SVR760488R8300	1SVR750489R8300	1SVR760489R8300
	Type	CM-MPS.11S	CM-MPS.11P	CM-MPS.21S	CM-MPS.21P	CM-MPS.31S	CM-MPS.31P	CM-MPS.41S	CM-MPS.41P	CM-MPS.23S	CM-MPS.23P	CM-MPS.43S	CM-MPS.43P	CM-MPN.52S	CM-MPN.52P	CM-MPN.62S	CM-MPN.62P	CM-MPN.72S	CM-MPN.72P
Rated control supply voltage U_s																			
Phase to phase																			
160-300 V AC						■	■												
300-500 V AC								■	■			■	■						
350-580 V AC														■	■				
450-720 V AC																■	■		
530-820 V AC																		■	■
Phase to neutral																			
90-170 V AC		■	■																
180-280 V AC				■	■					■	■								
Rated frequency																			
50/60 Hz		■	■	■	■	■	■	■	■					■	■	■	■	■	■
50/60/400 Hz										■	■	■	■						
Suitable for monitoring																			
Mains with harmonic content										■	■	■	■						
Single-phase mains		■	■	■	■					■	■								
Three-phase mains		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Monitoring function																			
Phase failure		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Phase sequence		sel	sel	sel	sel	sel	sel	sel	sel	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj
Automatic phase sequence correction										adj	adj	adj	adj	adj	adj	adj	adj	adj	adj
Overvoltage		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Undervoltage		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Unbalance		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Interrupted neutral monitoring [1]		■	■	■	■					■	■								
Thresholds																			
Adjustable (adj)		adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj
Timing functions for tripping delay																			
On- or OFF delay		adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj	adj
Connection type																			
Push-in terminals			■		■		■		■		■		■		■		■		■
Double-chamber cage connection terminals		■		■		■		■		■		■		■		■		■	

1) The relay detects by means of a phase unbalance the interruption of the neutral conductor. The external conductor voltage towards the neutral conductor is measured too.

adj: adjustable
sel: selectable

Three-phase monitoring relays

Ordering details - multifunctional



CM-MPS.23P



CM-MPN.52P

Description

The three-phase monitoring relays are designed for use in three-phase mains for monitoring the phase parameters, such as phase sequence, phase failure, over- and undervoltage, as well as phase unbalance.

—

Ordering details

Characteristics	Type	Order code	Weight (1 pc) kg (lb)
See selection table	CM-MPS.11S	1SVR730885R1300	0.148 (0.326)
	CM-MPS.11P	1SVR740885R1300	0.137 (0.302)
	CM-MPS.21S	1SVR730885R3300	0.146 (0.322)
	CM-MPS.21P	1SVR740885R3300	0.135 (0.298)
	CM-MPS.31S	1SVR730884R1300	0.142 (0.313)
	CM-MPS.31P	1SVR740884R1300	0.133 (0.293)
	CM-MPS.41S	1SVR730884R3300	0.140 (0.309)
	CM-MPS.41P	1SVR740884R3300	0.132 (0.291)
	CM-MPS.23S	1SVR730885R4300	0.149 (0.328)
	CM-MPS.23P	1SVR740885R4300	0.138 (0.304)
	CM-MPS.43S	1SVR730884R4300	0.148 (0.327)
	CM-MPS.43P	1SVR740884R4300	0.137 (0.302)
	CM-MPN.52S	1SVR750487R8300	0.230 (0.507)
	CM-MPN.52P	1SVR760487R8300	0.226 (0.498)
	CM-MPN.62S	1SVR750488R8300	0.229 (0.505)
	CM-MPN.62P	1SVR760488R8300	0.225 (0.496)
	CM-MPN.72S	1SVR750489R8300	0.224 (0.494)
	CM-MPN.72P	1SVR760489R8300	0.220 (0.485)

S: screw connection
P: push-in connection

Three-phase monitoring relays
Technical data

Type		**CM-PBE**[1)]	**CM-PBE**	**CM-PVE**[1)]	**CM-PVE**	**CM-PFE**	**CM-PFE.2**	**CM-PFS**
Input circuit - supply circuit		**L1-L2-L3-N**	**L1-L2-L3**	**L1-L2-L3-N**	**L1-L2-L3**			
Rated control supply voltage U_S = measuring voltage		3x380-440 V AC, 220-240 V AC	3x380-440 V AC	3x320-460 V AC, 185-265 V AC	3x320-460 V AC	3x208-440 V AC	3x200-500 V AC	
Power consumption							13 mA / 9 VA	approx. 15 VA
Rated control supply voltage U_S tolerance		-15...+15 %		-15...+10 %				
Rated frequency		50/60 Hz		50/60 Hz (-10...+10 %)		50/60 Hz		
Duty time		100 %						
Input circuit - measuring circuit		**L1-L2-L3-N**	**L1-L2-L3**	**L1-L2-L3-N**	**L1-L2-L3**			
Monitoring functions	phase failure	■	■	■	■	■	■	■
	phase sequence	-	-	-	-	■	■	■
	over- / undervoltage	-	-	■	■	-	-	-
	neutral	■	-	■	-	-	-	-
Measuring ranges		3x380-440 V AC, 220-240 V AC	3x380-440 V AC	3x320-460 V AC, 185-265 V AC	3x320-460 V AC	3x208-440 V AC	3x200-500 V AC	
Thresholds	U_{min}	0.6 x U_N		fixed 185 V / 320 V	fixed 320 V	0.6 x U_N		
	U_{max}	-		fixed 265 V / 460 V	fixed 460 V	-		
Hysteresis related to the threshold value		fixed 5 % (release value = 0.65 x U_N)		fixed 5 %		-		
Measuring voltage frequency		50/60 Hz (-10 %...+10 %)				50/60 Hz		
Response time		40 ms		80 ms		500 ms		
Accuracy within the temperature range		-		$\Delta U \leq 0.06$ % / °C				
Timing circuit								
Start-up delay t_s		fixed 500 ms (±20 %)				fixed 500 ms		
Tripping t_v		fixed 150 ms (±20 %)		at over-/ undervoltage fixed 500 ms (±20 %)		fixed 500 ms		-
Indication of operational states								
Relay status	R: yellow LED	⎍ output relay energized						
Fault message	F: red LED	Only CM-PFS: ⎍ phase failure / ⎍ phase sequence error						

Three-phase monitoring relays

Technical data

Type		CM-PBE[1]	CM-PBE	CM-PVE[1]	CM-PVE	CM-PFE	CM-PFE.2	CM-PFS
Output circuits		**13-14**				**11-12/14**		**11_{15}-12_{16} / 14_{18}, 21_{25}-22_{26} / 24_{28}**
Kind of output		1 n/o contact				1 c/o contact		2 c/o contacts
Operating principle		closed-circuit principle[2]						
Minimum switching voltage / Minimum switching current		24 V / 10 mA						
Maximum switching voltage / maximum switching voltage		see data sheets						
Rated operational voltage U_e and rated operational current I_e	AC-12 (resistive) 230 V	4 A						
	AC-15 (inductive) 230 V	3 A						
	DC-12 (resistive) 24 V	4 A						
	DC-13 (inductive) 24 V	2 A						
AC rating (UL 508)	Utilization category (Control Circuit Rating Code)	B 300 pilot duty, general purpose 250 V, 4 A, cos phi 0.75						
	max. rated operational voltage	300 V AC						
	max. continuous thermal current at B 300	5 A						
	max. making/breaking apparent power at B 300	3600/360 VA						
Mechanical lifetime		30 x 10^6 switching cycles						
Electrical lifetime (AC-12, 230 V, 4 A)		0.1 x 10^6 switching cycles						
Max. fuse rating to achieve short-circuit protection	n/c contact	10 A fast-acting				6 A fast-acting		
	n/o contact	10 A fast-acting						
Conventional thermal current I_{th}						4 A		

1) Device with neutral monitoring: The external conductor voltage towards the neutral conductor is measured.
2) Closed-circuit principle: Output relay is de-energized if the measured value exceeds/drops below the adjusted threshold.

Three-phase monitoring relays
Technical data

Type		CM-PBE[1)]	CM-PBE	CM-PVE[1)]	CM-PVE	CM-PFE	CM-PFE.2	CM-PFS
General data								
Duty cycle		100 %						
Dimensions		see dimensional drawings						
Mounting		DIN rail (IEC/EN 60715)						
Mounting position		any						
Minimum distance to other unites	horizontal	not necesarry				≥ 10 mm if ambient temperature > 50 °C and rated operational currents > 2 A		≥ 10 mm in case of continuous measuring voltage > 440 V
Degree of protection	housing / terminals	IP50 / IP20						
Electrical connection								
Connecting capacity	fine-strand with wire end ferrule	2 x 0.75-1.5 mm² (2 x 18-16 AWG)						Same as CM-PSS.31
	fine-strand without wire end ferrule	2 x 1-1.5 mm² (2 x 18-16 AWG)						
	rigid	2 x 0.75-1.5 mm² (2 x 18-16 AWG)						
Stripping length		10 mm (0.39 in)						Same as CM-PSS.31
Tightening torque		0.6-0.8 Nm						
Environmental data								
Ambient temperature range	operation / storage	-20..+60 °C / -40...+85 °C						
Climatic class		-				3K3		
Damp heat	IEC/EN 60068-2-30	40 °C, 93 % RH, 4 days				-		
Damp heat, cyclic	IEC/EN 60068-2-30					6 x 24 h cycle, 55 °C, 95 % RH		
Vibration withstand	IEC/EN 60068-2-6	10-57 Hz: 0.075 mm; 57-150 Hz: 1 g				-		
Vibration, sinusoidal		-				class 2		
Shock		-				class 2		
Isolation data								
Rated insulation voltage U_i	between input, measuring and output circuits	400 V				-		
	input circuit / output circuit	-				600 V		
	output circuit 1 / output circuit 2	-						300 V
Rated impulse withstand voltage U_{imp}	between input, measuring and output circuits	4 kV / 1.2 -50 µs				-		
	input circuit / output circuit	-				6 kV		
	output circuit 1 / output circuit 2	-						4 kV
Basic insulation	supply circuit / output circuit	-						600 V AC
Pollution degree		3						
Overvoltage category		III						
Standards / Directives								
Standards		IEC/EN 60947-5-1, EN 50178				IEC/EN 60255-27, IEC/EN 60947-5-1, EN 50178		
Low Voltage Directive		2014/35/EU						
EMC Directive		2014/30/EU						
RoHS Directive		2011/65/EU						

Three-phase monitoring relays

Technical data

Type		CM-PBE[1]	CM-PBE	CM-PVE[1]	CM-PVE	CM-PFE	CM-PFE.2	CM-PFS
Electromagnetic compatibility								
Interference immunity to		IEC/EN 61000-6-2						
electrostatic discharge	IEC/EN 61000-4-2	level 3 - 6 kV/ 8 kV						
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 - 10 V/m						level 3 - 10 V/m (1 GHz) 3 V/m (2 GHz) 1 V/m (2.7 GHz)
electrical fast transient / burst	IEC/EN 61000-4-4	level 3 - 2 kV / 5 kHz						
surge	IEC/EN 61000-4-5	level 4 - 2 kV L-L						
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 - 10 V						
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	-						class 3
harmonics and interharmonics	IEC/EN 61000-4-13	-						class 3
Interference emission		IEC/EN 61000-6-3						
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B						
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B						

(1) Device with neutral monitoring: The external conductor voltage towards the neutral conductor is measured.

Three-phase monitoring relays
Technical data

Type		**CM-PSS.31**	**CM-PSS.41**	**CM-PVS.31**	**CM-PVS.41**	**CM-PVS.81**	**CM-PAS.31**	**CM-PAS.41**
Input circuit = Measuring circuit		**L1, L2, L3**						
Rated control supply voltage U_S = measuring voltage		3x380 V AC	3x400 V AC	3x160-300 V AC	3x300-500 V AC	3x200-400 V AC	3x160-300 V AC	3x300-500 V AC
Rated control supply voltage U_S tolerance		-15...+10 %						
Rated frequency		50/60 Hz						
Frequency range		45-65 Hz						
Typical current / power consumption		25 mA / 18 VA (380 V AC)	25 mA / 18 VA (400 V AC)	25 mA / 10 VA (230 V AC)	25 mA / 18 VA (400 V AC)	19 mA / 10 VA (300 V AC)	25 mA / 10 VA (230 V AC)	25 mA /18 VA (400 V AC)
Measuring circuit		**L1, L2, L3**						
Monitoring functions	Phase failure	■	■	■	■	■	■	■
	Phase sequence	can be switched off					■	■
	Automatic phase sequence correction	-	-	-	-	-	-	-
	Over- / undervoltage	■	■	■	■	■	-	-
	Phase unbalance	-	-	-	-	-	■	■
	Neutral	-	-	-	-	-	-	-
Measuring range	Overvoltage	3x418 V AC	3x440 V AC	3x220-300 V AC	3x420-500 V AC	3x300-400 V AC	-	-
	Undervoltage	3x342 V AC	3x360 V AC	3x160-230 V AC	3x300-380 V AC	3x210-300 V AC	-	-
	Phase unbalance	-	-	-	-	-	2-25 % of average of phase voltages	
Thresholds	Overvoltage	fixed		adjustable within measuring range			-	-
	Undervoltage	fixed		adjustable within measuring range			-	-
	Phase unbalance (switch-off value)	-	-	-	-	-	adjust. within measuring range	
Tolerance of the adjusted threshold value		6 % of full-scale value						
Hysteresis related to the threshold value	Over- / undervoltage	fixed 5 %					-	
	Phase unbalance	-	-	-	-	-	fixed 20 %	
Maximum measuring cycle time		100 ms						
Accuracy within the temperature range		ΔU ≤ 0.06 % / °C						
Measuring method		true RMS						
Timing circuit								
Start-up delay t_S		fixed 200 ms						
Tripping delay t_V		ON- or OFF-delay 0; 0.1-30 s adjustable					ON- delay 0; 0.1-30 s adjustable	
Repeat accuracy (constant parameters)		-	-	-	-	< ± 0.2 %	-	-
Accuracy within the rated control supply voltage tolerance		Δt ≤ 0.5 %						
Accuracy within the temperature range		Δt ≤ 0.06 % / °C						
Indication of operational states								
				1 yellow LED, 2 red LEDs				
		details see function description / -diagrams		details see operating mode and function description / -diagrams			details see function description / -diagrams	
Output circuits		**15-16/18, 25-26/28**						
Kind of output		relay, 2 x 1 c/o contact						
Operating principle		closed-circuit principle[1)]						
Contact material		AgNi alloy, Cd free						
Minimum switching power		24 V / 10 mA						
Maximum switching voltage		see "Load limit curves"						

1) Closed-circuit principle: Output relay(s) de-energize(s) if measured value exceeds or falls below the adjusted threshold value

Three-phase monitoring relays

Technical data

Type		CM-PSS.31	CM-PSS.41	CM-PVS.31	CM-PVS.41	CM-PVS.81	CM-PAS.31	CM-PAS.41
Rated operational voltage U_e and rated operational current I_e	AC-12 (resistive) 230 V	4 A						
	AC-15 (inductive) 230 V	3 A						
	DC-12 (resistive) 24 V	4 A						
	DC-13 (inductive) 24 V	2 A						
AC rating (UL 508)	Utilization category (Control Circuit Rating Code)	B 300						
	max. rated operational voltage	300 V AC						
	max. continuous thermal current at B 300	5 A						
	max. making/breaking apparent power at B 300	3600/360 VA						
Mechanical lifetime		30 x 10^6 switching cycles						
Electrical lifetime (AC-12, 230 V, 4 A)		0.1 x 10^6 switching cycles						
Max. fuse rating to achieve short-circuit protection	n/c contact	6 A fast-acting						
	n/o contact	10 A fast-acting						
General data								
MTBF		on request						
Duty cycle		100%						
Dimensions		see dimensional drawings						
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool						
Mounting position		any						
Minimum distance to other units	horizontal	10 mm (0.39 in) in case of continuous measuring voltages						
		> 400 V	> 400 V	> 220 V	> 400 V	-	> 220 V	> 400 V
Material of housing		UL 94 V-0						
Degree of protection	housing / terminals	IP50 / IP20						
Electrical connection								
Wire size		**Screw connection technology**				**Easy Connect Technology (Push-in)**		
	fine-strand with(out) wire end ferrule	1 x 0.5-2.5 mm² (1 x 18-14 AWG) 2 x 0.5-1.5 mm² (2 x 18-16 AWG)				2 x 0.5-1.5 mm² (2 x 18-16 AWG)		
	rigid	1 x 0.5-4 mm² (1 x 20-12 AWG) 2 x 0.5-2.5 mm² (2 x 20-14 AWG)				2 x 0.5-1.5 mm² (2 x 20-16 AWG)		
Stripping length		8 mm (0.32 in)						
Tightening torque		0.6-0.8 Nm (7.08 lb.in)				-		
Environmental data								
Ambient temperature ranges	operation / storage	-25...+60 °C / -40...+85 °C						
Damp heat, cyclic (IEC 60068-2-30)		6 x 24 h cycle, 55 °C, 95 % RH						
Climatic class		3K3						
Vibration (sinusoidal)		class 2						
Shock		class 2						
Isolation data								
Rated insulation voltage U_i	input circuit / output circuit	600 V						
	output circuit 1 / output circuit 2	300 V						
Rated impulse withstand voltage U_{imp}	input circuit	6 kV; 1.2/50 µs						
	output circuit	4 kV; 1.2/50 µs						
Basic insulation	input circuit / output circuit	600 V						
Protective separation	input circuit / output circuit	-						
Pollution degree		3						
Overvoltage category		III						

Three-phase monitoring relays
Technical data

Type		CM-PSS.31	CM-PSS.41	CM-PVS.31	CM-PVS.41	CM-PVS.81	CM-PAS.31	CM-PAS.41
Standards / Directives								
Standards		IEC/EN 60255-27, IEC/EN 60947-5-1, EN 50178						
Low Voltage Directive		2014/35/EU						
EMC directive		2014/30/EU						
RoHS directive		2011/65/EU						
Electromagnetic compatibility								
Interference immunity to		EN 61000-6-1						
electrostatic discharge	IEC/EN 61000-4-2	Level 3 (6 kV / 8 kV)						
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	Level 3 (10 V/m)						
electrical fast transient / burst	IEC/EN 61000-4-4	Level 3 (2 kV / 2 kHz)						
surge	IEC/EN 61000-4-5	Level 4 (2 kV L-L)						
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	Level 3 (10 V)						
Interference emission		IEC/EN 61000-6-3						
high-frequency radiated	IEC/CISPR 22, EN 55022	class B						
high-frequency conducted	IEC/CISPR 22, EN 55022	class B						

Three-phase monitoring relays

Technical data

Type			**CM-MPS.11**	**CM-MPS.21**	**CM-MPS.31**	**CM-MPS.41**
Input circuit = Measuring circuit			**L1, L2, L3, N**		**L1, L2, L3**	
Rated control supply voltage U_S = measuring voltage			3x90-170 V AC	3x180-280 V AC	3x160-300 V AC	3x300-500 V AC
Rated control supply voltage U_S tolerance			-15...+10 %			
Rated frequency			50/60 Hz			
Frequency range			45-65 Hz			
Typical current / power consumption			25 mA / 10 VA (115 V AC)	25 mA / 18 VA (230 V AC)	25 mA / 10 VA (230 V AC)	25 mA / 18 VA (400 V AC)
Measuring circuit			**L1, L2, L3, N**		**L1, L2, L3**	
Monitoring functions		Phase failure	■	■	■	■
		Phase sequence	can be switched off			
		Automatic phase sequence correction	-	-	-	-
		Over- / undervoltage	■	■	■	■
		Phase unbalance	■	■	■	■
		Interrupted neutral	■	■	-	-
Measuring range		Overvoltage	3x120-170 V AC	3x240-280 V AC	3x220-300 V AC	3x420-500 V AC
		Undervoltage	3x90-130 V AC	3x180-220 V AC	3x160-230 V AC	3x300-380 V AC
		Phase unbalance	2-25 % of average of phase voltages			
Thresholds		Overvoltage	adjustable within measuring range			
		Undervoltage	adjustable within measuring range			
		Phase unbalance (switch-off value)	adjustable within measuring range			
Tolerance of the adjusted threshold value			6 % of full-scale value			
Hysteresis related to the threshold value		Over- / undervoltage	fixed 5 %			
		Phase unbalance	fixed 20 %			
Accuracy within the temperature range			ΔU ≤ 0.06 % / °C			
Measuring method			True RMS			
Timing circuit						
Start-up delay t_S			fixed 200 ms			
Tripping delay t_V			ON- or OFF-delay 0; 0.1-30 s adjustable			
Accuracy within the rated control supply voltage tolerance			Δt ≤ 0.5 %			
Accuracy within the temperature range			Δt ≤ 0.06 % / °C			
Indication of operational states			Details see function description / -diagrams			
Output circuits			**15-16/18, 25-26/28**			
Kind of output			relay, 1 x 2 c/o contacts			
Operating principle			closed-circuit principle[1)]			
Contact material			AgNi alloy, Cd free			
Minimum switching power			24 V / 10 mA			
Maximum switching voltage			see load limit curves			
Rated operational voltage U_e and rated operational current I_e		AC-12 (resistive) 230 V	4 A			
		AC-15 (inductive) 230 V	3 A			
		DC-12 (resistive) 24 V	4 A			
		DC-13 (inductive) 24 V	2 A			
AC rating (UL 508)		Utilization category (Control Circuit Rating Code)	B 300			
		max. rated operational voltage	300 V AC			
		max. continuous thermal current at B 300	5 A			
		max. making/breaking apparent power at B 300	3600/360 VA			
Mechanical lifetime			30 x 10^6 switching cycles			
Electrical lifetime (AC-12, 230 V, 4 A)			0.1 x 10^6 switching cycles			
Max. fuse rating to achieve short-circuit protection		n/c contact	6 A fast-acting			
		n/o contact	10 A fast-acting			

1) Closed-circuit principle: Output relay(s) de-energize(s) if measured value exceeds or falls below the adjusted threshold value

Three-phase monitoring relays

Technical data

Type			CM-MPS.11	CM-MPS.21	CM-MPS.31	CM-MPS.41
General data						
MTBF			on request			
Duty time			100 %			
Dimensions			see dimension drawings			
Mounting			DIN rail (IEC/EN 60715), snap-on mounting without any tool			
Mounting position			any			
Minimum distance to other units		horizontal	10 mm (0.39 in) in case of continuous measuring voltages > 120 V	> 240 V	> 220 V	> 400 V
Material of housing			UL 94 V-0			
Degree of protection		housing / terminals	IP50 / IP20			
Electrical connection						
Wire size			Screw connection technology		Easy Connect Technology (Push-in)	
		fine-strand with(out) wire end ferrule	1 x 0.5-2.5 mm² (1 x 18-14 AWG) 2 x 0.5-1.5 mm² (2 x 18-16 AWG)		2 x 0.5-1.5 mm² (2 x 18-16 AWG)	
		rigid	1 x 0.5-4 mm² (1 x 20-12 AWG) 2 x 0.5-2.5 mm² (2 x 20-14 AWG)		2 x 0.5-1.5 mm² (2 x 20-16 AWG)	
Stripping length			8 mm (0.32 in)			
Tightening torque			0.6-0.8 Nm (7.08 lb.in)		-	
Environmental data						
Ambient temperature ranges		operation / storage	-25...+60 °C / -40...+85 °C			
Damp heat, cyclic			6 x 24 h cycle, 55 °C, 65 % RH			
Climatic class			3K3			
Vibration			class 2			
Shock			class 2			
Isolation data						
Rated insulation voltage U_i		input circuit / output circuit	600 V			
		output circuit 1 / output circuit 2	300 V			
Rated impulse withstand voltage U_{imp}		input circuit	6 kV; 1.2/50 µs			
		output circuit	4 kV; 1.2/50 µs			
Test voltage between all isolated circuits (routine test)			2.5 kV, 50 Hz, 1 s			
Basic insulation		input circuit / output circuit	600 V			
Protective separation (IEC/EN 61140, EN 50178)		input circuit / output circuit	yes		-	
Pollution degree			3			
Overvoltage category			III			
Standards / Directives						
Standards			IEC/EN 60255-2, IEC/EN 60947-5-1, EN 50178			
Low Voltage Directive			2014/35/EU			
EMC directive			2014/30/EU			
RoHS directive			2011/65/EU			
Electromagnetic compatibility						
Interference immunity to			IEC/EN 61000-6-2			
	electrostatic discharge	IEC/EN 61000-4-2	level 3 (6 kV / 8 kV)			
	radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)			
	electrical fast transient / burst	IEC/EN 61000-4-4	level 3 (2 kV / 2 kHz)			
	surge	IEC/EN 61000-4-5	level 4 (2 kV L-N)		Level 4 (2 kV L-L)	
	conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)			
	harmonics and interharmonics	IEC/EN 61000-4-13	class 3			
Interference emission			EN 61000-6-3, EN 61000-6-4			
	high-frequency radiated	IEC/CISPR 22, EN 55022	class B			
	high-frequency conducted	IEC/CISPR 22, EN 55022	class B			

Three-phase monitoring relays

Technical data

Type		**CM-MPS.23**	**CM-MPS.43**	**CM-MPN.52**	**CM-MPN.62**	**CM-MPN.72**
Input circuit = Measuring circuit		**L1, L2, L3, N**	**L1, L2, L3**			
Rated control supply voltage U_S = measuring voltage		3x180-280 V AC	3x300-500 V AC	3x350-580 V AC	3x450-720 V AC	3x530-820 V AC
Rated control supply voltage U_S tolerance		-15...+10 %				
Rated frequency		50/60/400 Hz		50/60 Hz		
Frequency range		45-440 Hz		45-65 Hz		
Typical current / power consumption		5 mA / 4 VA (230 V AC)	5 mA / 4 VA (400 V AC)	29 mA / 41 VA (480 V AC)	29 mA / 52 VA (600 V AC)	29 mA / 59 VA (690 V AC)
Measuring circuit		**L1, L2, L3, N**	**L1, L2, L3**			
Monitoring functions	Phase failure	■	■	■	■	■
	Phase sequence	can be switched off				
	Automatic phase sequence correction	configurable				
	Over- / undervoltage	■	■	■	■	■
	Phase unbalance	■	■	■	■	■
	Interrupted neutral	■	-	-	-	-
Measuring range	Overvoltage	3x240-280 V AC	3x420-500 V AC	3x480-580 V AC	3x600-720 V AC	3x690-820 V AC
	Undervoltage	3x180-220 V AC	3x300-380 V AC	3x350-460 V AC	3x450-570 V AC	3x530-660 V AC
	Phase unbalance	2-25 % of average of phase voltages				
Thresholds	Overvoltage	adjustable within measuring range				
	Undervoltage	adjustable within measuring range				
	Phase unbalance (switch-off value)	adjustable within measuring range				
Tolerance of the adjusted thrshold value		6 % of full-scale value				
Hysteresis related to the threshold value	Over- / undervoltage	fixed 5 %				
	Phase unbalance	fixed 20 %				
Maximum measuring cycle time		100 ms				
Accuracy within the temperature range		ΔU ≤ 0.06 % / °C				
Measuring method		True RMS				
Timing circuit						
Start-up delay t_S and t_{S2}		fixed 200 ms				
Start-up delay t_{S1}		fixed 250 ms				
Tripping delay t_V		ON- or OFF-delay 0; 0.1-30 s adjustable				
Accuracy within the rated control supply voltage tolerance		Δt ≤ 0.5 %				
Accuracy within the temperature range		Δt ≤ 0.06 % / °C				
Indication of operational states		Details see function description / -diagrams				
Output circuits		**15-16/18, 25-26/28**				
Kind of output		relay, 2 x 1 or 1 x 2 c/o contacts configurable				
Operating principle		closed-circuit principle[1)]				
Contact material		AgNi alloy, Cd free				
Minimum switching power		24 V / 10 mA				
Maximum switching voltage		see load limit curves				
Rated operational voltage U_e and rated operational current I_e	AC-12 (resistive) 230 V	4 A				
	AC-15 (inductive) 230 V	3 A				
	DC-12 (resistive) 24 V	4 A				
	DC-13 (inductive) 24 V	2 A				
AC rating (UL 508)	Utilization category (Control Circuit Rating Code)	B 300				
	max. rated operational voltage	300 V AC				
	max. continuous thermal current at B 300	5 A				
	max. making/breaking apparent power at B 300	3600/360 VA				
Mechanical lifetime		30 x 10^6 switching cycles				
Electrical lifetime (AC-12, 230 V, 4 A)		0.1 x 10^6 switching cycles				
Max. fuse rating to achieve short-circuit protection	n/c contact	6 A fast-acting		10 A fast-acting		
	n/o contact	10 A fast-acting				

1) Closed-circuit principle: Output relay(s) de-energize(s) if measured value exceeds or falls below the adjusted threshold value

Three-phase monitoring relays
Technical data


Type			CM-MPS.23	CM-MPS.43	CM-MPN.52	CM-MPN.62	CM-MPN.72
General data							
MTBF			on request				
Duty time			100 %				
Dimensions			see dimensional drawings				
Mounting			DIN rail (IEC/EN 60715), snap-on mounting without any tool				
Mounting position			any				
Minimum distance to other units		horizontal	10 mm (0.39 in)		not necessary		
Material of housing			UL 94 V-0				
Degree of protection		housing / terminals	IP50 / IP20				
Electrical connection							
Wire size			**Screw connection technology**		**Easy Connect Technology (Push-in)**		
	fine-strand with(out) wire end ferrule		1 x 0.5-2.5 mm² (1 x 18-14 AWG) 2 x 0.5-1.5 mm² (2 x 20-16 AWG)		2 x 0.5-1.5 mm² (2 x 18-16 AWG)		
	rigid		1 x 0.5-4 mm² (1 x 20-12 AWG) 2 x 0.5-2.5 mm² (2 x 20-14 AWG)		2 x 0.5-1.5 mm² (2 x 20-16 AWG)		
Stripping length			8 mm (0.32 in)				
Tightening torque			0.6-0.8 Nm (7.08 lb.in)			-	
Environmental data							
Ambient temperature ranges		operation / storage	-25...+60 °C / -40...+85 °C				
Damp heat, cyclic (IEC 60068-2-30)			6 x 24 h cycles, 55 °C, 95 % RH				
Climatic category			3K3				
Vibration (sinusoidal) (IEC/EN 60255-21-1)			class 2				
Shock (IEC/EN 60255-21-2)			class 2				
Isolation data							
Rated insulation voltage U_i		input circuit / output circuit	600 V		1000 V		
		output circuit 1 / 2	300 V				
Rated impulse withstand voltage U_{imp}		input circuit	6 kV; 1.2/50 µs		8 kV; 1.2/50 µs		
		output circuit	4 kV; 1.2/50 µs				
Basic insulation	input circuit / output circuit		600 V		1000 V		
Protective separation (IEC/EN 61140, EN 50148)		input circuit / output circuit	-				
Pollution degree			3				
Overvoltage category			III				
Standards / Directives							
Standards			IEC/EN 60255-27, IEC/EN 60947-5-1, EN 50178				
Low Voltage Directive			2014/35/EU				
EMC Directive			2014/30/EU				
RoHS Directive			2011/65/EU				
Electromagnetic compatibility							
Interference immunity to			IEC/EN 61000-6-2				
electrostatic discharge		IEC/EN 61000-4-2	level 3 (6 kV / 8 kV)				
radiated, radio-frequency, electromagnetic field		IEC/EN 61000-4-3	level 3 (10 V/m)				
electrical fast transient / burst		IEC/EN 61000-4-4	level 3 (2 kV / 2 kHz)				
surge		IEC/EN 61000-4-5	level 4 (2 kV L-N)	Level 4 (2 kV L-L)			
conducted disturbances, induced by radio-frequency fields		IEC/EN 61000-4-6	level 3 (10 V)				
harmonics and interharmonics		IEC/EN 61000-4-13	class 3				
Interference emission			IEC/EN 61000-6-3				
high-frequency radiated		IEC/CISPR 22, EN 55022	class B				
high-frequency conducted		IEC/CISPR 22, EN 55022	class B				

Three-phase monitoring relays
Technical diagrams


Connection diagrams

CM-PBE, CM-PVE

with neutral




without neutral




L1, L2, L3, (N)	Control supply voltage = Measuring voltage
13-14	Output contact - closed-circuit principle

CM-PFE




L1, L2, L3	Control supply voltage = Measuring voltage
11-12/14	Output contact - closed-circuit principle

CM-PVS.x1, CM-PSS.x1, CM-PAS.x1




L1, L2, L3	Control supply voltage = Measuring voltage
15-16/18 25-26/28	Output contact - closed-circuit principle

CM-PFS




L1, L2, L3	Control supply voltage = Measuring voltage
11_{15}-12_{16} /14_{18} 21_{25}-22_{26}/24_{28}	Output contact - closed-circuit principle

CM-MPS.11, CM-MPS.21, CM-MPS.23




L1, L2, L3, (N)	Control supply voltage = Measuring voltage
15-16/18 25-26/28	Output contact - closed-circuit principle

CM-MPS.31, CM-MPS.41, CM-MPS.43



L1, L2, L3, (N)	Control supply voltage = Measuring voltage
15-16/18 25-26/28	Output contact - closed-circuit principle

CM-MPN.x2



L1, L2, L3	Control supply voltage = Measuring voltage
15-16/18 25-26/28	Output contact - closed-circuit principle

Three-phase monitoring relays
Technical diagrams

Rotary switch "Function"

CM-PVS


	ON-delay with phase sequence monitoring
	OFF-delay with phase sequence monitoring
	ON-delay without phase sequence monitoring
	OFF-delay without phase sequence monitoring

CM-PSS

	ON-delay with phase sequence monitoring
	OFF-delay with phase sequence monitoring
	ON-delay without phase sequence monitoring
	OFF-delay without phase sequence monitoring

DIP switch functions


CM-MPS.x3 and CM-MPN.x2



1	**Timing function**	
	ON	ON-delayed
	OFF	OFF-delayed
2	**Phase sequence monitoring**	
	ON	deactivated
	OFF	activated
3	**Operating principle of output**	
	ON	2x1 c/o contact
	OFF	1x2 c/o contact
4	**Phase sequence correction**	
	ON	activated
	OFF	deactivated

Output relay R1 is responsive to overvoltage, output relay R2 is responsive to undervoltage. In case of other faults, both output relays react synchronously.


CM-MPS.x1



1	**Timing function**	
	ON	ON-delayed
	OFF	OFF-delayed
2	**Phase sequence monitoring**	
	ON	deactivated
	OFF	activated


Three-phase monitoring relays
Function diagrams

CM-PBE




Phase failure detection
If all phases (and the neutral) are present, the output relay energizes after the start-up delay t_s is complete. If a phase failure occurs, the tripping delay t_v starts. When timing is complete, the output relay de-energizes. As soon as the voltage returns to the tolerance range, timing of t_s starts. When timing is complete, the output relay re-energizes automatically. The yellow LED glows when the output relay is energized.

CM-PVE




Phase failure, under- / overvoltage detection
If all phases (and the neutral) are present with correct voltage, the output relay energizes after the start-up delay t_s is complete. If the voltage exceeds or falls below the fixed threshold value or if a phase failure occurs, the tripping delay t_v starts. When timing is complete, the output relay de-energizes. As soon as the voltage returns to the tolerance range, timing of t_s starts. When timing is complete, the output relay re-energizes automatically. The yellow LED glows when the output relay is energized.

CM-PFE, CM-PFE.2



Phase failure detection, phase sequence monitoring
If all phases are present with the correct phase sequence, the output relay energizes after the start-up delay t_s is complete. If a phase failure or a phase sequence error occurs, the tripping delay t_v starts. When timing is complete, the output relay de-energizes. The yellow LED glows when the output relay is energized.
In case of motors which continue running with only two phases, the CM-PFE detects phase failure if the reverse fed voltage is less than 60 % of the originally applied voltage.

CM-PFS




Phase failure detection, phase sequence monitoring
If all phases are present with the correct phase sequence, the output relay energizes after the start-up delay t_s is complete. If a phase failure or a phase sequence error occurs, the output relay de-energizes instantaneous. The yellow LED glows when the output relay is energized.
In case of motors which continue running with only two phases, the CM-PFS detects phase failure if the reverse fed voltage is less than 60 % of the originally applied voltage.

ATTENTION
If several CM-PFS units are placed side by side and the control supply voltage is higher than 415 V, spacing of at least 10 mm has to be kept between the individual units.

Three-phase monitoring relays
Function diagrams

CM-PSS.xx, CM-PVS.xx, CM.PAS.xx, CM-MPS.xx, CM-MPN.xx




t_s = start-up delay fixed 200 ms

Phase sequence monitoring and phase failure detection
Applying control supply voltage begins the fixed start-up delay t_s. When t_s is complete and all phases are present with correct voltage, the output relays energize and the yellow LED R/T glows.

Phase sequence monitoring
If phase sequence monitoring is activated, the output relays de-energize as soon as a phase sequence error occurs. The fault is displayed by alternated flashing of the LEDs F1 and F2. The output relays re-energize automatically as soon as the phase sequence is correct again.

Phase failure detection
The output relays de-energize instantaneous if a phase failure occurs. The fault is indicated by lighting of LED F1 and flashing of LED F2. The output relays re-energize automatically as soon as the voltage returns to the tolerance range.

CM-MPS.11, CM-MPS.21, CM-MPS.23




Displacement of the star point

Interrupted neutral monitoring
The interruption of the neutral in the main to be monitored is detected by means of phase unbalance evaluation.
Determined by the system, in case of unloaded neutral (i.e. symmetrical load between all three phases) it may happen that an interruption of the neutral will not be detected.
If the star point is displaced an asymmetrical load in the three-phase main, an interrupted neutral will be detected.

Three-phase monitoring relays
Function diagrams


CM-MPS.x3, CM-MPN.x2




Automatic phase sequence correction
This function can be selected only if phase sequence monitoring is activated and operating mode 2x1 c/o (SPDT) contact is selected.

Applying control supply voltage begins the fixed start-up delay t_{S1}. When t_{S1} is complete and all phases are present with correct voltage, output relay R1 energizes. Output relay R2 energizes when the fixed start-up delay t_{S2} is complete and all phases are present with the correct phase sequence. Output relay R2 remains de-energized if the phase sequence is incorrect.


If the voltage to be monitored exceeds or falls below the set threshold values for phase unbalance, over- or undervoltage or if a phase failure occurs, output relay R1 de-energizes and the LEDs F1 and F2 indicate the fault.
Output relay R2 is responsive only to a false phase sequence. In conjunction with a reversing contactor combination, this enables an automatic correction of the rotation direction.
See circuit diagrams on the right.



Control circuit diagram
(K1 = CM-MPS.23)



Control circuit diagram
(K1 = CM-MPS.43 or CM-MPN.xx)




Power circuit diagram

Three-phase monitoring relays
Function diagrams


CM-PSS.xx (1), CM-PVS.xx (2), CM-MPS.xx (2), CM-MPN.xx (2)

ON-delay ⊠, 1x2 c/o contacts 1x2 c/o



t_S = start-up delay fixed 200 ms
t_V = adjustable tripping delay

OFF-delay ■, 1x2 c/o contacts 1x2 c/o



t_S = start-up delay fixed 200 ms
t_V = adjustable tripping delay

Over- and undervoltage monitoring 1x2 c/o

Applying control supply voltage begins the fixed start-up delay t_S. When t_S is complete and all phases are present with correct voltage and with the correct phase sequence, the output relays energize and the yellow LED R/T glows.

Type of tripping delay = ON-delay

If the voltage to be monitored exceeds or falls below the fixed (1) or set (2) threshold value, the output relays de-energize after the set tripping delay t_V is complete. The LED R/T flashes during timing and turns off as soon as the output relays de-energize.
The output relays re-energize automatically as soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 % and the LED R/T glows.


Type of tripping delay = OFF-delay

If the voltage to be monitored exceeds or falls below the fixed (1) or set (2) threshold value, the output relays de-energize instantaneously and the LED R/T turns off.
As soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 %, the output relays re-energize automatically after the set tripping delay t_V is complete. The LED R/T flashes during timing and turns steady when timing is complete.

Three-phase monitoring relays
Function diagrams


CM-MPS.x3, CM-MPN.x2

ON-delay ⊠, 2x1 c/o contact 2x1 c/o



t_s = start-up delay fixed 200 ms
t_v = adjustable tripping delay

OFF-delay ■, 2x1 c/o contact 2x1 c/o



t_s = start-up delay fixed 200 ms
t_v = adjustable tripping delay

Over- and undervoltage monitoring 2x1 c/o

Applying control supply voltage begins the fixed start-up delay t_s. When t_s is complete and all phases are present with correct voltage and with the correct phase sequence, the output relays energize. The yellow LED R/T glows as long as at least one output relay is energized.

Type of tripping delay = ON-delay

If the voltage to be monitored exceeds or falls below the set threshold value, output relay R1 (overvoltage) or output relay R2 (undervoltage) de-energizes after the set tripping delay t_v is complete. The LED R/T flashes during timing.
The corresponding output relay re-energizes automatically as soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 %.


Type of tripping delay = OFF-delay

If the voltage to be monitored exceeds or falls below the set threshold value, output relay R1 (overvoltage) or output relay R2 (undervoltage) de-energizes instantaneously.
As soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 5 %, the corresponding output relay re-energizes automatically after the set tripping delay t_v is complete. The LED R/T flashes during timing.

Three-phase monitoring relays
Function diagrams


CM-PAS.xx, CM-MPS.xx, CM-MPN.xx

ON-delay ⊠



t_s = start-up delay fixed 200 ms
t_v = adjustable tripping delay

OFF-delay ■



t_s = start-up delay fixed 200 ms
t_v = adjustable tripping delay

Phase unbalance monitoring
Applying control supply voltage begins the fixed start-up delay t_s. When t_s is complete and all phases are present with correct voltage and with the correct phase sequence, the output relays energize and the yellow LED R/T glows.

Type of tripping delay = ON-delay
If the voltage to be monitored exceeds or falls below the set phase unbalance threshold value, the output relays de-energize after the set tripping delay t_v is complete. The LED R/T flashes during timing and turns off as soon as the output relays de-energize.
The output relays re-energize automatically as soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 20 % and the LED R/T glows.

Type of tripping delay = OFF-delay
If the voltage to be monitored exceeds or falls below the set phase unbalance threshold value, the output relays de-energize instantaneously and the LED R/T turns off.
As soon as the voltage returns to the tolerance range, taking into account a fixed hysteresis of 20 %, the output relays re-energize automatically after the set tripping delay t_v is complete. The LED R/T flashes during timing and turns steady when timing is complete.

Three-phase monitoring relays
Function diagrams

CM-PSS.xx, CM-PSV.xx, CM-PAS.xx, CM-MPS.xx, CM-MPN.xx

LED functions

Function	R/T: yellow LED	F1: red LED	F2: red LED
Control supply voltage applied, output relay energized	⎍	-	-
Tripping delay t_v active	⎍⎍	-	-
Phase failure	-	⎍	⎍⎍
Phase sequence	-	⎍⎍ alternating	
Overvoltage	-	⎍	-
Undervoltage	-	-	⎍
Phase unbalance	-	⎍	⎍
Interruption of the neutral	-	⎍	⎍⎍
Adjustment error	⎍⎍	⎍⎍	⎍⎍

Possible wrong adjustments of the front-facing operating controls

Overlapping of the threshold values:

- An overlapping of the threshold values is given if the threshold value for overvoltage is set to a smaller value than the threshold value for undervoltage.
- DIP switch 3 = OFF
- DIP switch 4 = ON: Automatic phase sequence correction is activated and selected operating mode is 1x2 c/o contacts
- DIP switch 2 and 4 = ON: Phase sequence detection is deactivated and the automatic phase sequence correction is activated

Type of tripping delay

The type of tripping delay ⊠ / ■ can be adjusted via a rotary (CM-PxS.xx) or a DIP switch (CM-MPx.xx).

Switch position ON-delay ⊠:
In case of a fault, the de-energizing of the output relays and the respective fault message are suppressed for the adjusted tripping delay t_v.

Switch position OFF-delay ■:
In case of a fault, the output relays de-energize instantaneously and a fault message is displayed and stored for the length of the adjusted tripping delay t_v. Thereby, also momentary undervoltage conditions are recognized.


A1
A2
Y1
Y2
Y3
Y0
L1
L2
L3
N
CM-UFD
ABB
ESC
U/T
F
Rx/Tx
OK
14
11
12
24
21
22
34
31
32
18
15
16
28
25
26
38
35
36
A
B
C

Grid feeding monitoring relays
Table of contents

138 Benefits and advantages

143 Operating controls

144 Selection table

145 Ordering details

146 Technical data

147 Technical diagrams

Grid feeding monitoring relays
Benefits and advantages



ABB's grid feeding monitoring relays detect unusual events in the public power grid and keeps it stable by automatically disconnecting and reconnecting the renewable power plant. The CM-UFD displays all relevant measuring data and events and can communicate them via a build-in communication interface. The cloud-based service Ability™ EDCS enables customers to monitor the conditions in real-time, send the values into the cloud and access the diagnostics remotely.

Optimum interface

Reduce downtime by up to 70%
Operate the device via LCD or remotely with the Modbus RTU. Users are informed immediately in case of an event in the public grid. Redundant microcontrollers ensure reliable measuring values and tripping.

Global availability

Cut installation time by up to 60%
There's no need to learn every possible adjustment and its effects on your system – ABB's trained staff supports your business and answers your technical questions promptly.


Easy installation

Commission & configure up to 60% faster
Simple instructions, presets for local grid feeding standards, and ABB's intuitive menu structure make installation quicker. Commissioning and troubleshooting errors are prevented.

Grid feeding monitoring relays
Benefits and advantages

ABB's CM-UFD range are multi-functional grid feeding monitoring relays, installed between the renewable energy system and the public grid. The innovative relays guarantee grid stability and prevent blackouts. If the public grid's voltage or frequency moves out of the permitted ranges, the device uses a decoupling unit (e.g. contactor or breaker Tmax XT) to separate the renewable energy system from the public grid. As soon as the grid is stable again, the system is automatically reconnected.

The CM-UFD range provides different monitoring functions in accordance with several local grid feeding standards to detect over-/undervoltage and over-/underfrequency.



Advantages

- Highly accurate measurement and setting
- Modbus RTU communication interface and ABB Ability™ EDCS connectivity
- Functional safety - single fault tolerances
- Clear multiline, backlit LCD
- Intuitive and user-friendly menu
- Event storage
- Pre-settings meet several local standards
- Type-tested to a number of local grid feeding standards by TÜV Süd

Functionality

The device measures the ten-minute average value, voltage increases and decreases, as well as any changes in grid frequency. The rate of change of frequency (ROCOF) and vector shift monitoring to detect a loss of mains event can be easily configured.

ABB ABILITY™ EDCS


Monitor your renewable energy plant remotely with ABB´s smart ABB Ability™ EDCS cloud platform.



Grid feeding monitoring relays
Benefits and advantages

The cloud-based service Ability™ EDCS enables customers to monitor the condition of CM-UFD.M*M in real-time and access the diagnostics remotely. This functionality is very important when operating in the field of critical power. Parametrize with ABB Ekip Connect and access data no matter where you are.

—
Example architecture



The grid feeding monitoring relays can be connected to the cloud directly by using Ekip Com Hub module. Another option is to connect via Modbus RTU when there is some other device equipped with the Ekip Com Hub like the Emax 2 air-circuit breaker.

In addition to the Ekip Connect 3 software, the following hardware is required:
- Ekip UP (min. firmware 2.23)
- Ekip Com Hub (min. firmware 1.18)
- Ekip Com Modbus RTU (min. firmware 2.28)
- Ekip Supply
- Ekip T&P cable
- CM-UFD.M*M (min. firmware 1.0.1)

For further information regarding integration into ABB Ability™ EDCS, please use the application note "2CDC112280M0101 CM-UFD.M*M integration into ABB Ability™ EDCS".

Grid feeding monitoring relays
Benefits and advantages


A reliable solution that takes country-specific requirements into account: the range is already pre-set to local requirements, making installation quick and simple. The devices can also be set manually with the display and used all over the world.

Pre-set devices
In accordance with a number of local standards, the CM-UFD relays can be used in all low voltage plants and in medium voltage plants.


Type-tested
To ensure reliability and compliance, the range is type-tested to local standards by the third party authority TÜV Süd.

—
Countries with a dedicated local standard (in red)

—
Countries referring to an existing local standard or using a product with reference to another dedicated standard (in grey)



Grid feeding monitoring relays
Operating controls



Grid feeding monitoring relays
Selection table

	Order number	1SVR560731R3700	1SVR560730R3401	1SVR560731R3701	1SVR560730R3402	1SVR560731R3702	1SVR560731R3703
	Type	CM-UFD.M22M	CM-UFD.M31	CM-UFD.M31M	CM-UFD.M33	CM-UFD.M33M	CM-UFD.M34M
Rated control supply voltage U_s							
24-240 V AC/DC		■	■	■	■	■	■
Standard							
CEI 0-21		■					
VDE AR-N 4105, VDE AR-N 4110			■	■			
ENA G98, G99					■	■	
DRRG standard of DEWA							■
Rated frequency							
DC or 50 Hz		■	■	■			
DC or 50/60 Hz					■	■	■
Modbus RTU		■		■		■	■
Suitable for monitoring							
Single-phase mains		■	■	■	■	■	■
Three-phase mains		■	■	■	■	■	■
Monitoring function							
Over-/undervoltage		■	■	■	■	■	■
Over-/underfrequency		■	■	■	■	■	■
ROCOF (rate of change of frequency)		■	■	■	■	■	■
10 minutes average value		■	■	■	■	■	■
Vector shift			■	■	■	■	■
Thresholds		adj	adj	adj	adj	adj	adj

Grid feeding monitoring relays
Ordering details



CM-UFD.M*M


Description

The grid feeding monitoring relays CM-UFD.M*M are designed to monitor the voltage and the frequency of the public low voltage or medium voltage grid. Whenever the measured values are not within the range of the adjusted threshold values, the CM-UFD.M*M causes tripping of the section switch (consisting of 1 or 2 switching devices according to the applicable standard). This tripping disconnects the power generation, such as photovoltaic systems, wind turbines, block-type thermal power stations from the grid.

Ordering details

Description	Type	Order code	Weight (1 pc) kg (lb)
See selection table	CM-UFD.M22M	1SVR560731R3700	0.312 (0.688)
	CM-UFD.M31	1SVR560730R3401	0.304 (0.670)
	CM-UFD.M31M	1SVR560731R3701	0.312 (0.688)
	CM-UFD.M33	1SVR560730R3402	0.304 (0.670)
	CM-UFD.M33M	1SVR560731R3702	0.312 (0.688)
	CM-UFD.M34M	1SVR560731R3703	0.312 (0.688)

Grid feeding monitoring relays
Technical data


DATA SHEET

Grid feeding monitoring according to CEI 0-21

CM-UFD.M22M with Modbus RTU

Characteristics

Ordering details

Data sheets

For every product of the CM-UFD range, a technical data sheet is available.

- Operating control and mode
- Operating principles
- Modbus RTU functionality where available
- Electrical connection
- Configuration and settings
- Menu structure
- Display and failure messages
- Connection and wiring
- Technical data
- Technical diagrams
- CAS system files

Ordering data and data sheet numbers


Description	Type	Order code	Data sheet number
	CM-UFD.M22M	1SVR560731R3700	2CDC112258D0201
	CM-UFD.M31	1SVR560730R3401	2CDC112208D0201
	CM-UFD.M31M	1SVR560731R3701	2CDC112270D0201
	CM-UFD.M33	1SVR560730R3402	2CDC112210D0201
	CM-UFD.M33M	1SVR560731R3702	2CDC112271D0201
	CM-UFD.M34M	1SVR560731R3703	2CDC112272D0201

For further information regarding integration into ABB Ability™ EDCS, please use the application note "2CDC112280M0101 CM-UFD.M*M integration into ABB Ability™ EDCS".


Grid feeding monitoring relays

Technical diagrams

Example of a single-phase application



Example of a three-phase application




Legend


1. Control supply voltage for CM-UFD.M*M
2. Public grid
3. Protection fuse for the CM-UFD.M*M
4. Protection fuse for the measuring circuit of the CM-UFD.M*M (optional)
5. Short-circuit protection
6. Undervoltage release
7. Control input for feedback function
8. Switching device of the section switch
9. Switching device of the generator and/or inverter
10. Generator and/or inverter
11. Primary switch mode power supply unit CP-E (230 V AC / 24 V DC) for the buffer module CP-B
12. Ultra-capacitor based buffer module CP-B (24 V DC in/out)
13. Wire protection fuse for the output of the buffer module CP-B

Grid feeding monitoring relays
Technical diagrams


Load limits curves




AC load (resistive)



DC load (resistive)




Derating factor F at inductive AC load



Contact lifetime

Dimensional drawings
in **mm** and inches




A1
11
KE
S1
S2
S3
ABB
CM-IWS
Test / Reset
R.1-value kΩ
R.2-value kΩ
U
F
R
R=R.1+R.2
L+
L-
14
A1
11
S1
S2
S3
ABB
CM-IWS
Test / Reset
R.1-value kΩ
R.2-value kΩ
U
F
R
R=R.1+R.2
L
A1
11
21
S1
S2
S3
ABB
CM-IWN
Test / Reset
R1.1-value kΩ
R2.1-value kΩ
Rx=Rx.1+Rx.2
R1.2-value kΩ
R2.2-value kΩ
U
F
R
12
14
L+
VS
V1+
V1-
VL+
VL-
ABB
CM-IVN
mains connection
VE
VS
L+
V1+
L-
V1-
CM-IVN
CM-IWN
L+
V1+
L-
V1-

Insulation monitoring relays for unearthed supply systems
Table of contents

152 Benefits and advantages

156 Applications

157 Operating controls

160 Selection table

161 Ordering details

162 Technical data

169 Technical diagrams

Insulation monitoring relays
Benefits and advantages



The insulation monitoring relays of the CM-IWx range guarantee a continuous insulation monitoring of an IT system. The devices recognize insulation faults as they develop and warn immediately if the value has fallen below the minimum set threshold. This ensures a reliable operation of the system and prevents operational interruption caused by a second, more severe, insulation fault which may lead to a short circuit tripping the main circuit breaker.



Continuous operation

Keep the system online and reduce downtime with early pre-warnings which enable time for maintenance planning. Monitor voltage free networks for early fault detection. Due to variants with rail and ship approval, the devices have a wide range of applications.



Safety and protection

Safe and reliable detection of insulation faults according to the latest standards is what ABB's insulation monitoring relays deliver. The portfolio extends from standard to more challenging applications and can prevent fire due to fast and reliable earth fault detection. Built-in self-diagnosis and interrupted wire detection further ensure safety.



Easy installation

Read the status of the relay at a glance: clear visualization of the device status via LEDs.
Easy to adjust with rotary wheels and variants with push-in terminals make a quick and easy installation and setting possible.

Insulation monitoring relays
Benefits and advantages

Overview
The CM-IWx product family offers a convincing solution for monitoring ungrounded AC, AC/DC and DC networks according to EN/IEC 61557-8. An IT network is supplied either by an isolating transformer or a voltage source, such as a battery or generator. In these systems, no active conductor is directly connected to earth potential.

The high reliability of an IT system is guaranteed thanks to continuous insulation monitoring. The insulation monitoring device recognizes insulation faults (at least one conductor has a galvanic connection to earth potential) as they develop and immediately reports if the insulation resistance has fallen below a given threshold. Therefore, maintenance activities can be scheduled and executed while the plant keeps running.

Main benefits
- Increase plant availability and avoid costly unplanned stops of a plant / machine by quickly detecting faults first
- Prevents fires due to detection of a creeping deterioration of the insulation resistance
- The adjustment of the setting values is simple and done in a user-friendly way with rotary switches on the front of the device
- Device status is displayed with LEDs that are easy to read and understand
- Devices for standard and more challenging applications are available
- Variants with rail and ship approvals are available



Insulation monitoring relays
Benefits and advantages

CM-IWS.1 – for unearthed pure AC systems



The CM-IWS.1 serves to monitor insulation resistance in accordance with IEC 61557-8 in unearthed IT AC systems, IT AC systems with galvanically connected DC circuits, or unearthed IT DC systems with a voltage up to 250 V AC and 300 V DC. It can be configured to the requirements of the applications and therefore has multi-functional uses. The device is available with two different terminal versions. You can choose between the proven screw connection technology (double-chamber cage connection terminals) and the completely tool-free Easy Connect Technology (push-in terminals).

- For monitoring the insulation resistance of unearthed IT systems up to U_n = 250 V AC and 300 V DC
- Test function
- According to IEC/EN 61557-8
- Rated control supply voltage 24-240 V AC/DC
- Prognostic measuring principle with superimposed square wave signal
- One measuring range 1-100 kΩ
- 1 c/o (SPDT) contact, closed-circuit principle
- Precise adjustment by front-face operating controls in 1 kΩ steps
- Interrupted wire detection
- Fault storage / latching configurable by control input
- Screw connection or Easy Connect Technology available
- Housing material for highest fire protection classification UL 94 V-0
- Tool-free mounting on DIN rail as well as demounting
- 22.5 mm width
- 3 LEDs for status indication

CM-IWS.2 – for unearthed AC, DC or mixed AC/DC systems



The CM-IWS.2 serves to monitor insulation resistance in accordance with IEC 61557-8 in unearthed IT AC systems with a voltage up to 400 V AC. The CM-IWS.2 can be configured to the requirements of the applications and therefore has multi-functional uses. The device is available with two different terminal versions. You can choose between the proven screw connection technology (double-chamber cage connection terminals) and the completely tool-free Easy Connect Technology (push-in terminals).

- For monitoring the insulation resistance of unearthed IT systems up to U_n = 400 V AC
- Test function
- According to IEC/EN 61557-8
- Rated control supply voltage 24–240 V AC/DC
- Measuring principle with superimposed DC voltage
- One measuring range 1-100 kΩ
- Fault storage / latching configurable by control input
- Precise adjustment by front-face operating controls in 1 kΩ steps
- Screw connection or Easy Connect Technology available
- Housing material for highest fire protection classification UL 94 V-0
- Tool-free mounting on DIN rail as well as demounting
- 1 c/o (SPDT) contact, closed-circuit principle
- 22.5 mm width
- 3 LEDs for status indication

Insulation monitoring relays
Benefits and advantages

CM-IWN.1 – for unearthed AC, DC or mixed AC/DC systems



The CM-IWN.1 serves to monitor insulation resistance in accordance with IEC 61557-8 in unearthed IT AC systems, IT AC systems with galvanically connected DC circuits, or unearthed IT DC systems with a voltage up to 400 V AC and 600 V DC. The measuring range can be extended up to 690 V AC and 1000 V DC by using the coupling unit CM-IVN. It can be configured to the requirements of the applications and therefore has multi-functional uses. The CM-IWN.1 is available with two different terminal versions. You can choose between the proven screw connection technology (double chamber cage connection terminals) and the completely tool-free Easy Connect Technology (push-in terminals).

- For monitoring the insulation resistance of unearthed IT systems up to U_n= 400 V AC and 600 V DC, expansion to 690 V AC and 1000 V DC with CM-IVN
- Test function
- According to IEC/EN 61557-8
- Rated control supply voltage 24-240 V AC/DC
- Prognostic measuring principle with superimposed square wave signal
- Two measuring ranges 1-100 kΩ and 2-200 kΩ
- Precise adjustment of the measuring value in 1 or 2 kW steps
- One (1 x 2 c/o) or two (2 x 1 c/o) threshold values Ran1/ R1 (warning) and Ran2/R2 (pre-warning) configurable(1)
- Precise adjustment of the threshold values in 1 kΩ steps (R1) and 2 kΩ steps (R2)
- Interrupted wire detection configurable
- Non-volatile fault storage configurable
- Open- or closed-circuit principle configurable
- Screw connection or Easy Connect Technology available
- Housing material for highest fire protection classification UL 94 V-0
- Tool-free mounting on DIN rail as well as demounting
- 45 mm width
- 3 LEDs for status indication

CM-IWM.10 and CM-IWM.11 – for unearthed AC, DC or mixed AC/DC systems with up to 1500 V measurement voltage




The insulation monitors CM-IWM.10 and CM-IWM.11 provide the best and up-to-date insulation monitoring of modern IT systems in an optimum and state of-the-art way fulfilling the relevant standards. The devices can be used in the most flexible way for AC, DC and AC/DC systems even with large leakage capacity to earth (PE). The adjustment of the setting values is simple and done in a user-friendly way on two rotary switches on the front of the device. Via LEDs the measured value, device parameters and device status are indicated easy to read.

- Insulation monitoring according to IEC/EN 61557-8
- Detection of symmetric and asymmetric insulation faults
- 1 c/o contact each for pre-warning and warning
- Measuring circuits can be disconnected via control terminals, e.g. for mains couplings
- Pre-warning threshold setting range: 20 kΩ ... 2 MΩ
- Warning threshold setting range: 1 kΩ ... 250 kΩ
- Open- or closed-circuit principle configurable
- Setting the maximum earth leakage capacitance to shorten the response time
- Simple, clearly arranged adjustment of the device with screwdriver
- LED chain to indicate the current insulation resistance
- Display of active measuring circuits
- Automatic and manual device self-test
- Alarm storage selectable
- External test and reset push button can be connected
- 90 mm width


Insulation monitoring relays
Applications

The CM-IWS.x and CM-IWN.x series provide excellent insulation monitoring for general purpose supply networks, such as:
- Non-earthed AC, DC, AC/DC networks
- UPS systems
- Battery networks
- Hybrid and battery-powered vehicles
- Railway applications



Earth fault / insulation resistance monitoring of a 4-wire IT AC system with CM-IWS.2

CM-IWM.x can be additionally used in special applications, such as:
- Industrial networks with frequency inverters or direct current drives
- Photovoltaic systems with high system leakage capacitance
- Networks with system voltages up to 1500 V DC or 1100 V AC without requiring a coupling unit
- Installation on the AC or DC side of an inverter
- Networks which require measuring circuit deactivation in case two or more un-earthed networks are coupled




*) G-HM connected: Measuring circuit is off

Example of a DC application with CM-IWM.11

Note:
Only one insulation monitor must be connected and active in a network at the same time.

Insulation monitoring relays
Operating controls

CM-IWM



Front-facing rotary switches
to adjust threshold values

Test and reset button


Indication of operational state and measured ground fault resistance

Insulation monitoring relays
Operating controls

CM-IWS

Test and reset button

Configuration and setting
Front-face rotary switches for threshold value adjustment:
- R.1 for R1 tens figures: 0, 10, 20, 30, 40, 50, 60, 70, 80, 90 kΩ in ten kΩ steps
- R.2 for R1 units figures: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10 kΩ in one kΩ steps




Indication of operational states
U: green LED - control supply voltage
F: red LED - fault message
R: yellow LED - relay status

Marker label for devices without DIP switches

Insulation monitoring relays
Operating controls

CM-IWN



Front-face rotary switches to adjust the threshold value:

- R1.1 for R1 tens figure: 0, 10, 20, 30, 40, 50, 60, 70, 80, 90 kΩ in ten kΩ steps
- R1.2 for R1 units figure: 1, 2, 3, 4, 5, 6, 7, 8, 9, 10 kΩ in one kΩ steps
- R2.1 for R2 tens figure: 0, 20, 40, 60, 80, 100, 120, 140, 160, 180 kΩ in twenty kΩ steps
- R2.2 for R2 units figure: 2, 4, 6, 8, 10, 12, 14, 16, 18, 20 kΩ in two kΩ steps

Test and reset button

Indication of operational states
U: green LED – control supply voltage
F1: red LED – fault message
F2: yellow LED – relay status

DIP switches
(see DIP switch functions)

Insulation monitoring relays

Selection table

	Order number	1SVR730670R0200	1SVR740670R0200	1SVR730660R0100	1SVR740660R0100	1SVR750660R0200	1SVR760660R0200	1SVR470670R1000	1SVR470670R1100
	Type	CM-IWS.2S	CM-IWS.2P	CM-IWS.1S	CM-IWS.1P	CM-IWN.1S	CM-IWN.1P	CM-IWM.10	CM-IWM.11
Rated control supply voltage U_s									
24 - 240 V AC/DC		■	■	■	■	■	■		
24 V DC								■	■
Measuring voltages									
250 V AC (L-PE)				■	■				
400 V AC (L-PE)		■	■			■	■		
690 V AC (L-PE)						■ (1)	■ (1)	■ (2)	
1000 V AC (L-PE)									■ (3)
300 V DC (L-PE)				■	■				
600 V DC (L-PE)						■	■		
690 V DC (L-PE)								■ (2)	
1000 V DC (L-PE)						■ (1)	■ (1)		■ (3)
Measuring range									
1 - 100 kΩ		■	■	■	■	■	■		
2 - 200 kΩ						■	■		
2 - 250 kΩ								■	■
System leakage capacitance, max.									
10 µF		■	■	■	■				
20 µF						■	■		
1000 µF								■	
3000 µF									■
Output									
1 c/o		■	■	■	■				
1 x 2 c/o or 2 x 1 c/o						■	■		
2 c/o								■	■
Operating principle									
Open-circuit principle		■	■	■	■			■	■
Open- or closed-circuit principle adjustable						■	■		
Test									
Front-face button or control input		■	■	■	■	■	■	■	■
Reset									
Front-face button or control input		■	■	■	■	■	■	■	■
Fault storage / latching configurable		■	■	■	■	■	■		
Non volatile storage configurable		■	■	■	■	■	■		
Interrupted wire detection						■	■	■	■
Threshold values configurable		1	1	1	1	2	2	2	2
Control input (measuring input deactivation)									■
Connection type									
Push-in terminals			■		■		■		
Double-chamber cage connection terminals		■		■		■			
Screw terminals								■	■

1) With coupling unit CM-IVN screw version CM-IVN.S: 1SVR750669R9400
push-in version CM-IVN.P: 1SVR760669R9400

2) Allowed voltage range of the supervised network: 0-760 V AC / 0-1000 V

3) Allowed voltage range of the supervised network: 0-1100 V AC / 0-1500 V DC

Insulation monitoring relays

Ordering details



CM-IWS.1



CM-IWS.2



CM-IWN.1



CM-IVN

Description

The CM-IWx serves to monitor insulation resistance in accordance with IEC 61557-8 in unearthed IT AC systems, IT AC systems with galvanically connected DC circuits, or IT DC systems. The devices are able to monitor control circuits (single-phase) and main circuits (3-phase).

The CM-IWM.x provides the best and up-to-date insulation monitoring of modern IT supply systems in an optimum and state of-the-art way according to IEC 61558-8 including annex C. The device can be used in the most flexible way for AC, DC and AC/DC systems, even with a large leakage capacity to earth (PE) and under adverse conditions.

Ordering details

Type	Rated control supply voltage	Nominal voltage U_n of the distribution system to be monitored	System leakage capacitance, max.	Adjustment range of the specified response value R_{an} (threshold)	Type	Order code	Weight (1 pc) kg (lb)
CM-IWS.x	24-240 V AC/DC	0-250 V AC / 0-300 V DC	10 µF	1-100 kΩ	CM-IWS.1S	1SVR730660R0100	0.148 (0.326)
					CM-IWS.1P	1SVR740660R0100	0.137 (0.302)
		0-400 V AC			CM-IWS.2S	1SVR730670R0200	0.141 (0.311)
					CM-IWS.2P	1SVR740670R0200	0.130 (0.287)
CM-IWN.x		0-400 V AC / 0-600 V DC	20 µF	1-100 kΩ 2-200 kΩ	CM-IWN.1S	1SVR750660R0200	0.241 (0.531)
					CM-IWN.1P	1SVR760660R0200	0.217 (0.478)
CM-IWM.x	24 V DC	0-690 V AC/DC [1]	1000 µF	1-250 kΩ 20 kΩ-2 MΩ	CM-IWM.10	1SVR470670R1000	0.500 (1.1)
		0-1000 V AC/DC [2]	3000 µF		CM-IWM.11	1SVR470670R1100	

1) Allowed voltage range of the supervised network: 0-760 V AC / 0-1000 V DC
2) Allowed voltage range of the supervised network: 0-1100 V AC / 0-1500 V DC

Coupling unit

Rated control supply voltage = measuring voltage	Nominal voltage U_n of the distribution system to be monitored	Type	Order code	Weight (1 pc) kg (lb)
Passive device, no control supply voltage needed	0-690 V AC / 0-1000 V DC	CM-IVN.S	1SVR750669R9400	0.179 (0.395)
		CM-IVN.P	1SVR760669R9400	0.165 (0.364)

S: screw connection
P: push-in connection

Insulation monitoring relays

Technical data - CM-IWx

Data at T_a = 25 °C and rated values, unless otherwise indicated

			CM-IWS.2	CM-IWS.1	CM-IWN.1
Input circuit - Supply circuit			**A1 - A2**		
Rated control supply voltage U_s			24-240 V AC/DC		
Rated control supply voltage tolerance			-15...+10 %		
Typical current / power consumption		24 V DC	30 mA / 0.7 VA	35 mA / 0.9 VA	55 mA / 1.3 VA
		115 V AC	12 mA / 1.4 VA	17 mA / 2.0 VA	20 mA / 2.3 VA
		230 V AC	12 mA / 2.8 VA	14 mA / 3.2 VA	15 mA / 3.5 VA
Rated frequency f_s			DC or 15-400 Hz		
Frequency range AC			13.5-440 Hz		
Power failure buffering time		min.	20 ms		
Start-up time t_s, fixed			min. 10 s	max. 15 s	min. 15 s
Input circuit - Measuring circuit			**L, ⏚**	**L+, L-, ⏚, KE**	**L+, L-, ⏚, KE**
Monitoring function			insulation resistance monitoring of IT systems		
Measuring principle			superimposed DC voltage	prognostic measuring principle with superimposed square wave signal	
Nominal voltage U_n of the distribution system to be monitored			0-400 V AC	0-250 V AC / 0-300 V DC	0-400 V AC / 0-600 V DC
Voltage range of the distribution system to be monitored			0-460 V AC (tolerance +15 %)	0-287.5 V AC / 0-345 V DC (tolerance +15 %)	0-460 V AC / 0-690 V DC (tolerance +15 %)
Rated frequency f_N of the distribution system to be monitored			50-60 Hz	DC or 15-400 Hz	DC or 15-400 Hz
System leakage capacitance C_e		max.	10 µF		20 µF
Tolerance of the rated frequency f_N			45-65 Hz	13.5-440 Hz	13.5-440 Hz
Extraneous DC voltage U_{fg} (when connected to an AC system)		max.	none	290 V DC	460 V DC
Number of possible response / threshold values			1		2
Adjustment range of the specified response value R_{an} (threshold)		min.-max.	1-100 Ω		–
		min.-max. R1	–		1-100 kΩ
		min.-max. R2	–		2-200 kΩ (activated / de-activated by DIP-switch)
Adjustment resolution			1 kΩ		
		R1	1 kΩ		1 kΩ
		R2	–		2 kΩ
Tolerance of the adjusted threshold value / Relative percentage uncertainty A at -5...+45 °C U_n = 0-115 % U_s = 85-110 %, f_N, f_s, C_e = 1µF		at 1-10 kΩ R_F (yellow marked scale)	≥ 15 %, max. ±0.5 kΩ		≥ 15 %, max. ± 1 kh, with CM-IVN ± 1.5 kh
		at 10-100 kΩ R_F	±6 %		–
		at 1-15 kΩ R_F	–		± 1 kh, with CM-IVN ± 1.5 kh
		at 15-200 kΩ R_F	–		±8 %
Hysteresis related to the threshold value			25 %; min. 2 kΩ		
Internal impedance Z_i		at 50 Hz	135 kΩ	100 kΩ	155 kΩ
Internal DC resistance R_i			185 kΩ	115 kΩ	185 kΩ
Measuring voltage U_m			15 V	22 V	24 V
Tolerance of measuring voltage U_m			+10 %		
Measuring current I_m		max.	0.1 mA	0.3 mA	0.15 mA
Response time t_{an}					
	pure AC system	0.5 x R_{an} and C_e = 1 µF	max. 10 s		
	DC system or AC system with connected rectifiers		–	max. 15 s	
Repeat accuracy (constant parameters)			< 0.1 % of full scale		
Accuracy of R_a (measured value) within the rated control supply voltage tolerance			< 0.05 % of full scale		
Accuracy of R_a (measured value) within the operation temperature range		at 1-10 kΩ R_F	5 Ω / K		
		at 10-100 kΩ R_F	0.05 % / K		–
		at 10-200 kΩ R_F	–		0.05 % / K
Transient overvoltage protection (⏚ - terminal)			Z-diode	avalanche diode	

Insulation monitoring relays

Technical data - CM-IWx

		CM-IWS.2	CM-IWS.1	CM-IWN.1
Input circuit - Control circuits		**S1 - S2 - S3**		
Control inputs - volt free	S1-S3	remote test		
	S2-S3	remote reset		
Maximum switching current in the control circuit		1 mA		
Maximum cable length to the control inputs		50 m - 100 pF/m [164 ft - 30.5 pF/ft]		
Minimum control pulse length		150 ms		
No-load voltage at the control input		≤ 24 V ± 5 %	≤ 24 V DC	
Indication of operational states				
Control supply voltage		LED U (green)		
Fault message		LED F (red)		
Relay status		LED R (yellow)		
Output circuits				
Kind of output		relay, 1 c/o (SPDT) contact		2 x 1 or 1 x 2 c/o (SPDT) contacts configurable
Operating principle		closed-circuit principle[1)]		open- or closed circuit principle configurable[1)]
Contact material		AgNi alloy, Cd free		
Min. switching voltage / Min. switching current		24 V / 10 mA		
Max. switching voltage / Max. switching current		see data sheet		
Rated operational voltage U_e and rated operational current I_e	AC-12 (resistive) at 230 V	4 A		
	AC-15 (inductive) at 230 V	3 A		
	DC-12 (resistive) at 24 V	4 A		
	DC-13 (inductive) at 24 V	2 A		
AC rating (UL 508)	Utilization category (Control Circuit Rating Code)	B 300, pilot duty general purpose 250 V, 4 A, cos ϕ 0.75		
	max. rated operational voltage	250 V AC		
	max. continuous thermal current at B 300	4 A		
	max. making/breaking apparent power at B 300	3600/360 VA		
Mechanical lifetime		30 x 10^6 switching cycles		
Electrical lifetime (AC-12, 230 V, 4 A)		0.1 x 10^6 switching cycles		
Max. fuse rating to achieve short-circuit protection	n/c contact	6 A fast-acting		
	n/o contact	10 A fast-acting		
Conventional thermal current I_{th}		4 A		
General data				
Duty cycle		100 %		
Dimensions		see dimensional drawings		
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool		
Mounting position		any		
Minimum distance to other units	vertical	not necessary		
	horizontal	10 mm (0.39 in) at U_n > 240 V	not necessary	10 mm (0.39 in) at U_n > 400 V
Material of housing		UL 94 V-0		
Degree of protection	housing / terminal	IP50 / IP20		

Electrical connection			
		Screw connection technology	**Easy Connect Technology (Push-in)**
Wire size	fine-strand with(out) wire end ferrule	1 x 0.5-2.5 mm² (1 x 18-14 AWG) 2 x 0.5-1.5 mm² (2 x 18-16 AWG)	2 x 0.5-1.5 mm² (2 x 18-16 AWG)
	rigid	1 x 0.5-4 mm² (1 x 20-12 AWG) 2 x 0.5-2.5 mm² (2 x 20-14 AWG)	2 x 0.5-1.5 mm² (2 x 20-16 AWG)
Stripping length		8 mm (0.32 in)	
Tightening torque		0.6-0.8 Nm (5.31-7.08 lb.in)	

[1)] Closed-circuit principle: Output relay(s) de-energize(s) if a fault is occurring
Open-circuit principle: Output relay(s) energize(s) if a fault is occurring

Insulation monitoring relays

Technical data - CM-IWx

		CM-IWS.2	CM-IWS.1	CM-IWN.1
Environmental data				
Ambient temperature ranges	operation / storage / transport	-25...+60 °C/-40...+85 °C/-40...+85 °C		
Climatic class	IEC/EN 60721-3-3	3K5 (no condensation, no ice formation)		
Damp heat, cyclic	IEC/EN 60068-2-30	6 x 24 h cycle, 55 °C, 95 % RH		
Vibration, sinusoidal		25 Hz: 2.5 g		
Isolation data				
Rated impulse withstand voltage U_{imp}	supply / measuring circuit	6 kV		
	supply / output circuit	6 kV		
	measuring / output circuit	6 kV		
	output 1 / output circuit 2			4 kV
Rated insulation voltage U_i	supply / measuring circuit	400 V	300 V	600 V
	supply / output circuit	300 V		
	supply / measuring circuit	400 V	300 V	600 V
	output 1 / output circuit 2	-	-	300 V
Basis insulation	supply / measuring circuit	400 V AC / 300 V DC	250 V AC / 300 V DC	400 V AC / 600 V DC
	supply / output circuit	250 V AC / 300 V DC		
	measuring / output circuit	400 V AC / 300 V DC	250 V AC / 300 V DC	400 V AC / 600 V DC
	output 1 / output 2	250 V AC / 300 V DC		
Protective separation (IEC/EN 61140)	supply / output circuit	250 V AC / 250 V DC		
	supply / measuring circuit	250 V AC / 250 V DC		
	measuring / output circuit	250 V AC / 250 V DC		
Pollution degree		3		
Overvoltage category		III		
Standards / Directives				
Standards		IEC/EN 60947-5-1, IEC/EN 61557-1, IEC/EN 61557-8		
Low Voltage Directive		2014/35/EU		
EMC Directive		2014/30/EU		
RoHS Directive		2011/65/EU		
Electromagnetic compatibility				
Interference immunity to		IEC/EN 61000-6-2, IEC/EN 61326-2-4		
electrostatic discharge	IEC/EN 61000-4-2	level 3, 6 kV / 8 kV		
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3, 10 V/m (1 GHz) / 3 V/m (2 GHz) / 1 V/m (2.7 GHz)		
electrical fast transient/burst	IEC/EN 61000-4-4	level 3, 2 kV / 5 kHz		
surge	IEC/EN 61000-4-5	level 3, installation class 3, supply circuit and measuring circuit 1 kV L-L, 2 kV L-earth		
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3, 10 V		
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	class 3		
harmonics and interharmonics	IEC/EN 61000-4-13	class 3		
Interference emissions		IEC/EN 61000-6-3		
high-frequency radiated	IEC/CISPR 22, EN 55022	class B		
high-frequency conducted	IEC/CISPR 22, EN 55022	class B		

Insulation monitoring relays

Technical data - CM-IVN

		CM-IVN
Input circuit - Measuring circuit		**VL+, VL-, V⏚**
Function		expansion of the nominal voltage range of the insulation monitoring relay CM-IWN to 690 V AC or 1000 V DC, max. length of connection cable 40 cm
Measuring principle		see CM-IWN
Nominal voltage U_n of the distribution system to be monitored		0-690 V AC / 0-1000 V DC
Voltage range of the distribution system to be monitored		0-793.5 V AC / 0-1150 V DC (tolerance +15 %)
Rated frequency f_N of the distribution system to be monitored		DC or 15-400 Hz
Tolerance of the rated frequency f_N		13.5-440 Hz
System leakage capacitance C_e	max.	identical to that of the insulation monitoring relay used
Extraneous DC voltage U_{fg} (when connected to an AC system)	max.	793.5 V DC
Tolerance of the adjusted threshold value / Relative percentage uncertainty A at -5...+ 45 °C, U_n = 0-115 %, U_s = 85-110 %, f_N, f_s, C_e = 1 µF	at 1-15 kΩ R_F	±1.5 kΩ
	at 15-200 kΩ R_F	±8 %
Internal impedance Z_i	at 50 Hz	195 kΩ
Internal DC resistance R_i		200 kΩ
Measuring voltage U_m		24 V
Tolerance of measuring voltage U_m		+10 %
Measuring current I_m		0.15 mA
General data		
MTBF		on request
Duty cycle		100 %
Dimensions		see dimensional drawings
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool
Mounting position		any
Minimum distance to other units	vertical	not necessary
	horizontal	10 mm (0.39 in) at U_n > 600 V
Degree of protection		IP50 / IP20
Electrical connection		
Wire size	fine-strand with(out) wire end ferrule	2 x 0.75-2.5 mm² (2 x 18-14 AWG)
	rigid	2 x 0.5-4 mm² (2 x 20-12 AWG)
Stripping length		7 mm (0.28 In)
Tightening torque		0.6-0.8 Nm (5.31-7.08 lb.In)
Max. length of connection cable to CM-IWN		40 cm
Environmental data		
Ambient temperature ranges	operation / storage / transport	-25...+60 °C / -40...+85 °C / -40...+85 °C
Climatic category	IEC/EN 60721-3-3	3K5 (no condensation, no ice formation)
Damp heat, cyclic	IEC/EN 60068-2-30	6 x 24 h cycle, 55 °C, 95 % RH
Vibration, sinusoidal	IEC/EN 60255-21-1	Class 2
Shock, half-sine	IEC/EN 60255-21-2	Class 2
Isolation data		
Rated impulse withstand voltage U_{imp}	input circuit / PE	8 kV
Rated insulation voltage U_i	input circuit / PE	1000 V
Pollution degree		3
Overvoltage category		III
Standards / Directives		
Standards		IEC/EN 60947-5-1, IEC/EN 61557-1, IEC/EN 61557-8
Low Voltage Directive		2014/35/EU
EMC Directive		2014/30/EU
RoHS Directive		2011/65/EU

Insulation monitoring relays

Technical data - CM-IVN

		CM-IVN
Electromagnetic compatibility		
Interference immunity to		IEC/EN 61000-6-2, IEC/EN 61326-2-4
electrostatic discharge	IEC/EN 61000-4-2	level 3, 6 kV / 8 kV
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3, 10 V/m (1 GHz) / 3 V/m (2 GHz) / 1 V/m (2.7 GHz)
electrical fast transient/burst	IEC/EN 61000-4-4	level 3, 2 kV / 5 kHz
surge	IEC/EN 61000-4-5	level 3, installation class 3, supply circuit and measuring circuit 1 kV L-L, 2 kV L-earth
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3, 10 V
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	level 3
harmonics and interharmonics	IEC/EN 61000-4-13	level 3
Interference emission		IEC/EN 61000-6-3
high-frequency radiated	IEC/CISPR 22, EN 50022	class B
high-frequency conducted	IEC/CISPR 22, EN 50022	class B

Insulation monitoring relays

Technical data - CM-IWM

		CM-IWM.10	CM-IWM.11
Input circuit			
Rated control supply voltage U_S		24 V DC	
Voltage range		20-30 V DC	
Typical power consumption		max. 5 W	
Measuring circuit		L(+) / L(-) to PE / KE	
Nominal voltage U_N		0-690 V AC/DC	0-1000 V AC/DC
Allowed voltage range of the supervised network		0-760 V AC / 0-1000 V DC	0-1100 V AC / 0-1500 V DC
Frequency range		DC or 16-1000 Hz	DC or 16-1000 Hz
Max. system leakage capacitance C_e		1000 µF	3000 µF
Internal resistance (AC/DC)		> 280 kΩ	
Measuring voltage		approx. ± 95 V	
Max. measured current (R_E = 0)		< 0.35 mA	
Response values R_E each adjustable via rotary switches			
	pre-warning ("VW")	warning ("AL")	
	20 kΩ	1 kΩ	
	30 kΩ	3 kΩ	
	50 kΩ	10 kΩ	
	70 kΩ	20 kΩ	
	100 kΩ	30 kΩ	
	150 kΩ	50 kΩ	
	250 kΩ	70 kΩ	
	500 kΩ	100 kΩ	
	1000 kΩ	150 kΩ	
	2000 kΩ	250 kΩ	
Response inaccuracy	IEC/EN 61557-8	± 15 % + 1.5 kΩ	
Response value hysteresis	at range 10 kΩ ... 700 kΩ	approx. 25 %	
	out of range:	approx. 40 % + 0.5 kΩ	
ON delay	at C_E = 1 µF R_E of ∞ to 0.5 * response value	< 10 s	
Control input		between T, R and G	between HM, T, R and G
Current flow		approx. 3 mA	
No-load voltage to ground		approx. 12 V	
Permissible wire length		< 50 m	
Min. activation time		0.5 s	
Output			
Contacts		2 x 1 c/o contacts for VW and AL	
Thermal current I_{th}		4 A	
Switching capacity to AC-15	n/o contact	3 A / AC 230 V acc. to IEC/EN 60947-5-1	
	n/c contact	1 A / AC 230 V acc. to IEC/EN 60947-5-1	
Electrical life	at 8 A, AC 250 V	1 x 10^4 switching cycles	
Short circuit strength max. fuse rating		4 A gL acc. to IEC/EN 60947-5-1	
Mechanical life		10 x 10^6 switching cycles	

Insulation monitoring relays

Technical data - CM-IWM

		CM-IWM.10	CM-IWM.11
General Data			
Operating mode		continuous operation	
Temperature range	operation	- 25 ... + 60 °C	- 25 ... + 60 °C (device mounted away from heat generation components) -25 ... +45 °C (device mounted without distance to other devices)
	storage	- 40 ... + 70 °C	
Relative air humidity		93 % at 40 °C	
Atmospheric pressure		860-1600 mbar (86-106 kPa)	
Altitude	IEC/EN 60664-1	< 4000 m	
Clearance and creepage distances			
Rated impulse voltage / pollution degree		IEC/EN 60664-1	
Measuring ciruit L(+) / L(-) to	auxiliary voltage DC and relay contacts VW, AL	8 kV / 2	
	auxiliary voltage DC to relay contacts VW, AL	8 kV / 2	
	relay contacts VW to relay contact AL	4 kV / 2	
Insulation test voltage, routine test		AC 5 kV; 1 s AC 2.5 kV; 1 s	
Technical data			
EMC			
Electrostatic discharge (ESD)	IEC/EN 61000-4-2	8 kV (air)	
HF irradiation	IEC/EN 61000-4-3	80 MHz-2.7 GHz: 10 V/m	
Fast transients	IEC/EN 61000-4-4	4 kV	
Surge voltages	IEC/EN 61000-4-5	between A1 - A2: 1 kV L(+) - L(-): 2 kV A1, A2 - PE: 4 kV L(+), L(-) - PE: 4 kV control line: 0.5 kV control line and earth: 1 kV	
HF-wire guided	IEC/EN 61000-4-6	10 V	
Interference suppression	EN 55011	limit value class A when connected to a low voltage public system (Class B, EN 55011) radio interference can be generated. To avoid this, appropriate measures have to be taken	
Degree of protection			
Housing	IEC/EN 60529	IP 40	
Terminals	IEC/EN 60529	IP 20	
Housing		thermpolastic with V0 behaviour according to UL subject 94	
Vibration resistance	IEC/EN 60068-2-6	10-55 Hz: 0.35 mm 2-13.2 Hz: ± 1 mm 13.2-100 Hz: ± 7 g	
Shock resistance	IEC/EN 60068-2-27	10 g / 11 ms, 3 pulses	
Climate resistance	IEC/EN 60068-1	25 / 060 / 04	
Terminal designation		EN 50005	
Connecting capacity		1 x 4 mm^2 solid	
		1 x 2.5 mm^2 stranded ferruled (isolated)	
		2 x 1.5 mm^2 stranded ferruled (isolated) DIN 46228-1/-2/-3-4	
		2 x 2.5 mm^2 stranded ferruled (isolated) DIN 46228-1/-2/-3	
Stripping length		8 mm	
Tightening torque		0.8 Nm	
Wire fixing		plus-minus terminal scews M3.5 terminal with wire protection	
Mounting	IEC/EN 60715	DIN rail	
Dimensions	width x height x depth	90 x 90 x 121 mm	

Insulation monitoring relays

Technical diagrams

LEDs, status information and fault messages

CM-IWN.x

Operational state	LED U (green)	LED F (red)	LED R (yellow)
Start-up		OFF	OFF
No fault		OFF	(1)
Prewarning			
Insulation fault (below threshold value)			(1)
KE/⏚ wire interruption			(1)
L+/L- wire interruption during system start-up / test function	 /		(1)
System leakage capacitance too high / invalid measurement result			(1)
Internal system fault	(1)		(1)
Setting fault (2)			
Test function		OFF	(1)
No fault after fault storage (3)		(4)	

CM-IWS.x

Operational state	LED U (green)	LED F (red)	LED R (yellow)
Start-up		OFF	OFF
No fault		OFF	
Insulation fault (below threshold value)			OFF
Invalid measuring result			OFF
KE/⏚ wire interruption (only CM-IWS. (1)			OFF
CM-IWS.1: System leakage capacitance too high / invalid measurement result			OFF
CM-IWS.2: Invalid measurement result			OFF
Internal system fault	OFF		OFF
Test function		OFF	OFF
No fault after fault storage (3)		(4)	

(1) Depending on the configuration.
(2) Possible faulty setting: The threshold value for final switch-off is set at a higher value than the threshold value for prewarning
(3) The device has triggered after an insulation fault. The fault has been stored and the insulation resistance has returned to a higher value than the threshold value plus hysteresis.
(4) Depending on the fault

CM-IWM.x


LED status	LED	Status
PWR: green LED		Control supply voltage applied
ERR: red LED		Internal device error
		Connection error L+/L-
		Connection error PE/KE
Active: green LED		Measuring phase with positive polarity
		Measuring phase with negative polarity
LED chain: yellow LED		8 LEDs indicate the current insulating resistance (≤ 10 kΩ ... ≥ 2 MΩ)
VW +: yellow LED		R_E lower than prewarning value to + potential
VW -: yellow LED		R_E lower than prewarning value to - potential
VW + and VW -: yellow LED		AC fault / symmetric fault
AL +: red LED		R_E lower than warning value to + potential
AL -: red LED		R_E lower than warning value to - potential
AL + and AL -: red LED		AC fault / symmetric fault

Insulation monitoring relays

Technical diagrams


Connection diagrams

CM-IWS.2




A1-A2	Control supply voltage
S1-S3	Remote test
S2-S3	Remote reset
L	Measuring circuit/input, system connection
⏚	Measuring circuit/input, earth connections
11-12/14	Output relay, closed-circuit principle

CM-IWS.1




A1-A2	Control supply voltage
S1-S3	Remote test
S2-S3	Remote reset
L+, L–	Measuring circuit/input, system connection
⏚, KE	Measuring circuit/input, earth connections
1-12/14	Output relay, closed-circuit principle

CM-IWN.1



A1-A2	Control supply voltage
S1-S3	Remote test
S2-S3	Remote reset
L+, L–	Measuring circuit/input, system connection
⏚, KE	Measuring circuit/input, earth connections
VS, V1+, V1	Connections for the coupling unit (if used)
11-12/14	Output relay 1, open- or closed-circuit principle
21-22/24	Output relay 2, open- or closed-circuit principle

CM-IVN




VE	Connection to CM-IWN.x - ⏚
VS	Connection to CM-IWN.x - VS
L+	Connection to CM-IWN.x - L+
V1+	Connection to CM-IWN.x - V1+
L-	Connection to CM-IWN.x - L-
V1-	Connection to CM-IWN.x - V1-
VL+ VL-	Measuring circuit / Measuring input, Connection to the system
V⏚	Measuring circuit / Measuring input, Connection to earth

Insulation monitoring relays

Technical diagrams


Connection diagrams

CM-IWM.10



Terminal designation	Signal designation
A1+, A2	Control supply voltage
L(+), L(-)	Connection for measuring ciruit
KE, PE	Connection for protective conductor
G, R	Control input (manual/auto reset) • G/R not jumpered: manual reset • G/R jumpered: auto reset
G, T	Control input (External test input) connection for an external device test pushbutton
11-12/14	Output relay 1 (warning)
21-22/24	Output relay 2 (prewarning)

CM-IWM.11




Terminal designation	Signal designation
A1+, A2	Control supply voltage
L(+), L(-)	Connection for measuring ciruit
KE, PE	Connection for protective conductor
G, R	Control input (manual/auto reset) • G/R not jumpered: manual reset • G/R jumpered: auto reset
G, T	Control input (External test input) connection for an external device test pushbutton
G, HM	Control input (measuring circuit deactivation) • G/HM not jumpered: measuring circuit activated • G/HM jumpered: measuring circuit deactivated
11-12/14	Output relay 1 (warning)
21-22/24	Output relay 2 (prewarning)

Insulation monitoring relays

Technical diagrams

DIP switches

CM-IWN.1



2CDC 252 050 F0b09

	ON	OFF (default)
DIP switch 1 Operating principle of the output relays	Closed-circuit principle If closed-circuit principle is selected, the output relays de-energize in case a fault is occurring. In non-fault state the relays are energized.	Open-circuit principle If open-circuit principle is selected, the output relays energize in case a fault is occurring. In non-fault state the relays are de-energized.
DIP switch 2 Non-volatile fault storage	Fault storage activated (latching) If the fault storage function is activated, the output relays remain in tripped position until a reset is done either by the front-face button or by the remote reset connection S2-S3. This function is non-volatile.	Fault storage de-activated (non latching) If the fault storage function is de-activated, the output relays switch back to their original position as soon as the insulation fault no longer exists.
DIP switch 3 Interrupted wire detection	Interrupted wire detection activated With this configuration, the CM-IWN.1 monitoring relays the wires connected to ⏚ and KE for interruptions.	Interrupted wire detection de-activated With this configuration the interrupted wire detection is de-activated.
DIP switch 4 2 x 1 c/o, 1 x 2 c/o	2 x 1 c/o (SPDT) contact If operating principle 2 x 1 c/o contact is selected, the output relay R1 (11-12/14) reacts to threshold value R1 (final switch-off) and the output relay R2 (21-22/24) reacts to threshold value R2 (prewarning)	1 x 2 c/o (SPDT) contacts If operating principle 1 x 2 c/o contacts is selected, both output relays R1 (11-12/14) and R2 (21-22/24) react synchronously to threshold value R1. Settings of the threshold value R2 have no effect on the operation.


Insulation monitoring relays

Technical diagrams


Wiring diagrams

CM-IWS.1


Always connect L+ and L- to different conductors. L+ and L- can be connected to any of the conductors.
$U_n \leq 250$ V AC; 300 V DC




2-wire AC system




2-wire DC system



3-wire AC system



3-wire DC system




4-wire AC system

Insulation monitoring relays
Technical diagrams

Wiring diagrams


CM-IWS.2

L can be connected to any of the conductors.
$U_n \leq 400$ V AC




2CDC252083F0009, 2CDC252082F0009

2-wire AC system



2CDC252090F0009, 2CDC252089F0009

3-wire AC system



2CDC5209 7F0009, 2CDC252096F0009

4-wire AC system


Insulation monitoring relays

Technical diagrams


Wiring diagrams

CM-IWN.1


Always connect L+ and L- to different conductors. L+ and L- can be connected to any of the conductors.
$U_n \leq 400$ V AC; 600 V DC (For monitoring of systems with higher voltages, use coupling unit CM-IVN.)




2-wire AC system




2-wire DC system



3-wire AC system



3-wire DC system




4-wire AC system

Insulation monitoring relays


Technical diagrams

Wiring diagrams

CM-IWM.10




Example of a AC application




Example of a DC application

CM-IWM.11



Example of a AC application



Example of a DC application


Insulation monitoring relays

Technical diagrams

Dimensional drawings


in **mm** and inches

CM-IWS.x




CM-IWS.x


Accessories



ADP.01 - Adapter for screw mounting



MAR.01 - Marker label for devices without DIP switches



COV.11 - Sealable transparent cover


Insulation monitoring relays

Technical diagrams

Dimensional drawings


in **mm** and inches

CM-IWN.x




CM-IWN.x


Accessories



ADP.02 - Adapter for screw mounting



MAR.12 - Marker label for devices with DIP switches



COV.12 - Sealable transparent cover


A1
11
21
T2
T1
ABB
CM-MSS
Reset
Test / Reset
U
F
R
24
22
S1
1T1
1T2/2T2
2T1

Thermistor motor protection relays
Table of contents

182 Benefits and advantages
183 Applications
184 Features
186 Offer overview
188 Operating controls
189 Selection table
190 Ordering details
193 Technical data
199 Technical diagrams

Thermistor motor protection relays
Benefits and advantages



The thermistor motor protection relays of the CM-MSx range protect motors with PTC sensors against high temperature. These sensors are incorporated in the motor windings, thus measuring the motor heat directly.

Continuous operation

By using thermistor motor protection relays from ABB, the down and commissioning time can be reduced. The relay is continuously monitoring the sensor circuit to detect short-circuit or interrupted i.e. wire faults, thus contributing to maintenance and time saving in case of faults. In addition, the clear error messages of the front LEDs makes it possible to distinguish between the various fault causes.

Reliable in harsh conditions


Direct motor protection through temperature monitoring of the motor winding offers 100 % motor protection, even under the most difficult ambient conditions. The ABB thermistor motor protection relays give you access to worldwide markets and are approved by local and international standards for many applications such as industry, renewable energies, the marine sector and dangerous and explosive environments. To prove that, the CM-MSS thermistor motor protection relays are certified according to ATEX Ex II (2) G and D for environments with explosive gas or dust loads.

Easy installation

Due to the compliance with the latest standards, there is no need to make any adjustments on the device. All relays come with two different connection possibilities - screw or push-in - to make any adjustments on the installation a breeze. Thanks to direct measurement of the motor temperature, dimensioning of the thermistor motor protection relay, considering the size of the motor, is not necessary.

Thermistor motor protection relays
Applications

Direct temperature monitoring
Generally, motor damage caused by overload or overheating situations can be prevented in different ways. Compared to the indirect temperature measuring which monitors the motor current, the temperature inside the motor can be measured by direct temperature measuring. This enables direct control and evaluation of different operating conditions:
Therefore, the consequences from overheating, such as abrasion as well as electrical failures, can be prevented. The direct measuring principle is carried out by a combination of the thermistor motor protection relay and three PTC sensors which are installed directly in the motor by the manufacturer. Those 3 PTC sensors are placed directly at the thermal hotspots, the motor windings.



Motor protection using current- and temperature-dependent protective devices
IEC 60204 stipulates that motors must be protected from overheating at a rating of 0.5 kW and higher. The protection can be provided or executed by overload protection, overtemperature protection or current limiting. For motors with frequent starting and braking, and in environments where cooling may be impaired (e.g. by dust), it is recommended to use the overtemperature protection option in the form of a protective device coordinated with this mode of operation.

On rotor-critical motors, overtemperature detection in the stator windings can lead to delayed and hence inadequate protection. In this case, the standards stipulate additional protection, e.g. by means of an overload relay. This combination of thermistor motor protection and an overload relay is recommended for full motor protection in case of frequent starting and braking of motors, irregular intermittent duty or excessive switching frequency.

Operating mode
The thermistor motor protection relays are used to monitor the temperature of motors or generators equipped with PTC sensors type A according to the latest product standard IEC 60947-8. The sensors are built-in into the motor windings, measuring the motor heating. In case of an increase of the temperature in the motor, the resistance of the PTC sensors increases as well. If the motor heats-up excessively (>2.83 kΩ), the output relay(s) de-energize(s) and the corresponding LED displays the overtemperature. A short circuit and an interrupted wire within the sensor circuit can also be detected. A reset is only possible after cooling down of the motor (<1.1 kΩ) or after a wire interruption, or a short circuit within the sensor circuit has been removed. A reset after tripping can be done manually with the Test / Reset button, externally with a push button between S1 and 1T2/2T2, or automatically by jumpering S1-1T2/2T2.

Thermistor motor protection relays
Features

Test function
The test function is only possible when there is no fault. By pressing the front-face combined Test / Reset button, a system test routine is executed. If the function „Remote Test / Reset“ (DIP switch 4) is activated, the system test routine is also possible via control input S1-T2 (S1-1T2/2T2*).
After starting the test routine, the output relays de-energize. They remain de-energized until the Test / Reset button is pressed again or control input S1-T2 (S1-1T2/2T2*) is closed (remote reset).


Short-circuit detection
If a short circuit is detected between the two lines of a sensor circuit, the output relay(s) de-energize(s) and the LEDs will display the specific error code.

Dynamic interrupted wire detection
During the operation, the device is permanently monitoring the measuring circuit. If the resistance in the measuring circuit rises, the device distinguishes if there is an overtemperature or an interrupted wire.

Fault storage , reset function
The fault storage is designed as non-volatile (remanent). This means that after switch-off and return of the control supply voltage the device returns to the state it was prior to the switch-off. If there was no fault prior to the interruption of the control supply voltage, the device restarts automatically after re-applying control supply voltage.
If there was a fault prior to the interruption, reset can be reset manually by the Test / Reset button or externally by remote reset between S1-T2 (S1-1T2/2T2*). With deactivated fault storage, reset can be made manually by the Test / Reset button, automatically by jumpering S1-T2 (S1-1T2/2T2*) or externally by remote reset between S1-T2 (S1-1T2/2T2*). Depending on the configuration of DIP switch 1, there are several possibilities to reset the device as shown in the picture.

DIP switch 1		
S1 1T2/2T2	1.) Front 2.) Remote 3.) A1-A2	1.) Front 2.) Remote
S1 1T2/2T2	1.) Front 2.) A1-A2	1.) Front
S1 1T2/2T2	1.) Auto-Reset	

*CM-MSS.51



Thermistor motor protection relays
Features

Single and accumulative evaluation

Single evaluation 2x1 c/o

If a fault occurs in the measuring circuit 1, output relay 1 (11-12/14) de-energizes. If a fault occurs in the measuring circuit 2, output relay 2 (21-22/24) de-energizes.

Accumulative evaluation 1x2 c/o

In case of a fault in one of the two measuring circuits, both output relays de-energize synchronously.

Bimetallic switches

In some applications, bimetallic switches - such as Klixon - are used as sensors instead of PTC temperature sensors. Bimetallic switches are temperature and current dependent, normally closed contacts, and are available for different temperature ranges. Since bimetallic switches have almost no resistance below their opening temperature, short-circuit detection is not possible when bimetallic switches are used.


ATEX certification

Suitably selected and adjusted devices are necessary for the safe operation of explosion-protected motors. Only the sensor line is conducted into the explosive atmosphere. The motor protection relay itself must be installed outside the potentially explosive atmospheres.

Marking:

II (2) G
II (2) D

CM-MSS functionality video






Thermistor motor protection relays
Offer overview



CM-MSE
- Auto reset
- Connection of several sensors (max. 6 sensors connected in series)
- Monitoring of bimetals
- 1 n/o contact
- Excellent cost / performance ratio




CM-MSS [1)]
- Different types of contacts available
  - 1 x 2 c/o (SPDT) contacts
  - 2 x 1 c/o (SPDT) contact
  - 1 n/o and 1 n/c contact
- 1 or 2 measuring circuits
- Different types of reset functions
  - Automatic
  - Manual
  - Remote
- Rated control supply voltages
  - 24 V AC/DC
  - 24-240 V AC/DC
  - 110-130 V AC, 220-240 V AC
- Various approvals and marks

[1)] Depending on device the characteristics vary, for detailed overview see "Selection table" on page 189.


ABB
ABB

Thermistor motor protection relays
Operating controls



Test / Reset button
Test - only possible if/when the relay doesn't show any fault.
Reset - only possible if measured value < switch-on resistance

Indication of operational states with LEDs
U: green LED - Status indication of control supply voltage
⌐¬ Control supply voltage applied
F: red LED - Fault message
R: yellow LED - Status indication of the output relay

For detailed status and failure analysis, please see "LEDs, status information and fault messages".

Marker label / DIP switches (depending on device) e.g.

2x1 c/o Single evaluation 2 x 1 c/o (SPDT) contact
1x2 c/o Accumulative evaluation 1 x 2 c/o (SPDT) contacts
Short-circuit detection de-activated
Short-circuit detection activated
Non-volatile fault storage activated
Non-volatile fault storage de-activated
Remote Reset
Remote Test/Reset

Thermistor motor protection relays
Selection table

	Order code	1SVR550805R9300	1SVR550800R9300	1SVR550801R9300	1SVR740720R1400	1SVR730720R1400	1SVR740700R0100	1SVR730700R0100	1SVR740700R2100	1SVR730700R2100	1SVR740722R1400	1SVR730722R1400	1SVR740700R0200	1SVR730700R0200	1SVR740700R2200	1SVR730700R2200	1SVR740712R1400	1SVR730712R1400	1SVR740712R0200	1SVR730712R0200	1SVR740712R2200	1SVR730712R2200	1SVR740712R1200	1SVR730712R1200	1SVR740712R1300	1SVR730712R1300
	Type	CM-MSE	CM-MSE	CM-MSE	CM-MSS.11P	CM-MSS.11S	CM-MSS.12P	CM-MSS.12S	CM-MSS.13P	CM-MSS.13S	CM-MSS.21P	CM-MSS.21S	CM-MSS.22P	CM-MSS.22S	CM-MSS.23P	CM-MSS.23S	CM-MSS.31P	CM-MSS.31S	CM-MSS.32P	CM-MSS.32S	CM-MSS.33P	CM-MSS.33S	CM-MSS.41P	CM-MSS.41S	CM-MSS.51P	CM-MSS.51S
Characteristics																										
ATEX approval					■	■					■	■					■	■	■	■	■	■	■	■	■	■
Number of sensor circuits		1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	1	2	2
Single or accumulative evaluation																									■	■
Number of LEDs					3	3	2	2	2	2	3	3	2	2	2	2	3	3	3	3	3	3	3	3	3	3
Contacts																										
1 c/o (SPDT) contact							■	■	■	■																
2 c/o (SPDT) contacts													■	■	■	■			■	■	■	■	■	■		
1 n/o		■	■	■																						
1 n/c and 1 n/o					■	■					■	■					■	■								
2 x 1 c/o or 1 x 2 c/o contacts, configurable																									■	■
Reset																										
Manual													■	■	■	■	■	■	■	■	■	■	■	■	■	■
Remote													■	■	■	■	■	■	■	■	■	■	■	■	■	■
Auto		■	■	■	■	■	■	■	■	■	■	■	■ (1)	■ (1)	■ (1)	■ (1)	■ (1)	■ (1)	■ (1)	■ (1)	■ (1)	■ (1)	■ (1)	■ (1)	■ (2)	■ (2)
Test button																	■	■	■	■	■	■	■	■	■	■
Functions																										
Short-circuit detection											■	■					■	■	■	■	■	■				
Short-circuit detection, configurable																							■	■	■	■
Dynamic interrupted wire detection					■	■					■	■					■	■	■	■	■	■	■	■	■	■
Non-volatile fault storage					■	■					■	■					■	■								
Non-volatile fault storage, configurable																							■	■	■	■
Rated control supply voltage U_s																										
24 V AC		■																								
110-130 V AC			■																							
220-240 V AC				■																						
24-240 V AC/DC					■	■					■	■					■	■					■	■	■	■
24 V AC/DC							■	■					■	■					■	■						
110-130 V AC, 220-240 V AC									■	■					■	■					■	■				
Connection type																										
Push-in terminals					■		■		■		■		■		■		■		■		■		■		■	
Double-chamber cage connection terminals						■		■		■		■		■		■		■		■		■		■		■
Screw		■	■	■																						

1) For automatic reset, connect terminals S1 to T2.
2) For automatic reset, connect Terminals S1 to 1T2/2T2.

Thermistor motor protection relays
Ordering details


2CDC 251 004 V0014

CM-MSS.12S


2CDC 251 013 V0014

CM-MSS.41S


2CDC 251 014 V0014

CM-MSS.51S

Description

The thermistor motor protection relay CM-MSS monitors the winding temperature and thus protects the motor from overheating, overload and insufficient cooling in accordance to the product standard IEC/EN 60947-8.

Ordering details

CM-MSx

Characteristics	Type	Order code	Weight (1 pc) kg (lb)
See selection table	CM-MSE	1SVR550805R9300	0.11 (0.24)
	CM-MSE	1SVR550800R9300	0.11 (0.24)
	CM-MSE	1SVR550801R9300	0.11 (0.24)
	CM-MSS.11P	1SVR740720R1400	0.119 (0.263)
	CM-MSS.11S	1SVR730720R1400	0.127 (0.280)
	CM-MSS.12P	1SVR740700R0100	0.105 (0.231)
	CM-MSS.12S	1SVR730700R0100	0.113 (0.249)
	CM-MSS.13P	1SVR740700R2100	0.147 (0.324)
	CM-MSS.13S	1SVR730700R2100	0.155 (0.342)
	CM-MSS.21P	1SVR740722R1400	0.118 (0.260)
	CM-MSS.21S	1SVR730722R1400	0.126 (0.278)
	CM-MSS.22P	1SVR740700R0200	0.121 (0.267)
	CM-MSS.22S	1SVR730700R0200	0.132 (0.291)
	CM-MSS.23P	1SVR740700R2200	0.163 (0.359)
	CM-MSS.23S	1SVR730700R2200	0.174 (0.384)
	CM-MSS.31P	1SVR740712R1400	0.120 (0.265)
	CM-MSS.31S	1SVR730712R1400	0.128 (0.282)
	CM-MSS.32P	1SVR740712R0200	0.120 (0.265)
	CM-MSS.32S	1SVR730712R0200	0.130 (0.287)
	CM-MSS.33P	1SVR740712R2200	0.162 (0.357)
	CM-MSS.33S	1SVR730712R2200	0.172 (0.379)
	CM-MSS.41P	1SVR740712R1200	0.130 (0.287)
	CM-MSS.41S	1SVR730712R1200	0.141 (0.311)
	CM-MSS.51P	1SVR740712R1300	0.135 (0.298)
	CM-MSS.51S	1SVR730712R1300	0.145 (0.320)

S: screw connection
P: push-in connection


Thermistor motor protection relays

Ordering details - PTC temperature sensors C011



1SVC 110 000 F0531

Temperature sensor example



Temperature sensor characteristics

Description

The PTC temperature sensors (temperature-dependent with positive temperature coefficient) are selected by the manufacturer of the motor depending on:

- the motor insulation class according to IEC/EN 60034-11,
- the special characteristics of the motor, such as the conductor cross-section of the windings, the permissible overload factor, etc.
- special conditions prescribed by the user, such as the permissible ambient temperature, risks resulting from locked rotor, extent of permitted overload, etc.

One temperature sensor must be embedded in each phase winding. For instance, in case of three-phase squirrel cage motors, three sensors are embedded in the stator windings. For pole-changing motors with one winding (Dahlander connection), three sensors are also required. Pole-changing motors with two windings, however, require six sensors. If an additional warning is required before the motor is switched off, separate sensors for a correspondingly lower temperature must be embedded in the winding. They have to be connected to a second control unit.

The sensors are suitable for embedding in motor windings with rated operating voltages of up to 600 V AC. Conductor length: 500 mm per sensor. A 14 V varistor can be connected in parallel to protect the sensors from overvoltage. Due to their characteristics, the thermistor motor protection relays can also be used with PTC temperature sensors of other manufacturers which comply with DIN 44 081 and DIN 44 082.

Ordering details

CM-MSS accessories

Rated response temperature T_{NF}	Color coding	Type	Order code	Weight (1 pc) kg (lb)
70 °C	white-brown	C011-70[1)]	GHC0110003R0001	0.02 (0.044)
80 °C	white-white	C011-80[1)]	GHC0110003R0002	0.02 (0.044)
90 °C	green-green	C011-90[1)]	GHC0110003R0003	0.02 (0.044)
100 °C	red-red	C011-100[1)]	GHC0110003R0004	0.02 (0.044)
110 °C	brown-brown	C011-110[1)]	GHC0110003R0005	0.02 (0.044)
120 °C	gray-gray	C011-120[1)]	GHC0110003R0006	0.02 (0.044)
130 °C	blue-blue	C011-130[1)]	GHC0110003R0007	0.02 (0.044)
140 °C	white-blue	C011-140[1)]	GHC0110003R0011	0.02 (0.044)
150 °C	black-black	C011-150[1)]	GHC0110003R0008	0.02 (0.044)
160 °C	blue-red	C011-160[1)]	GHC0110003R0009	0.02 (0.044)
170 °C	white-green	C011-170[1)]	GHC0110003R0010	0.02 (0.044)
150 °C	black-black	C011-3-150[2)]	GHC0110033R0008	0.05 (0.11)

1) Temperature sensor C011, standard version acc. to DIN 44081
2) Triple temperature sensor C011-3

Thermistor motor protection relays

Technical data - PTC temperature sensors C011

Characteristic data	Sensor type C011
Cold-state resistance	50 -100 Ω at 25 °C
Warm-state resistance ± 5 up to 6 K of rated response temperature T_{NF}	10 000 Ω
Thermal time constant, sensor open[1)]	< 5 s
Permitted ambient temperature	+180 °C

Rated response temperature ± tolerance $T_{NF} \pm \Delta T_{NF}$	PTC resistance R from -20 °C to T_{NF} - 20 K	PTC resistance R[2)] at PTC temperatures of:		
		T_{NF} - iT_{NF} (UPTC ≤ 2.5 V)	T_{NF} + iT_{NF} (UPTC ≤ 2.5 V)	T_{NF} + 15 K (UPTC ≤ 7.5 V)
70 ±5 °C	≤ 100 Ω	≤ 570 Ω	≥ 570 Ω	-
80 ±5 °C				
90 ±5 °C		≤ 550 Ω	≥ 1330 Ω	≥ 4000 Ω
100 ±5 °C				
110 ±5 °C				
120 ±5 °C				
130 ±5 °C				
140 ±5 °C				
150 ±5 °C				
160 ±5 °C				
170 ±7 °C		≤ 570 Ω	≥ 570 Ω	-

1) Not embedded in windings.
2) For triple temperature sensor take values x 3.

Thermistor motor protection relays

Technical data - CM-MSS

Data at T_a = 25 °C and rated values, unless otherwise indicated

Type			CM-MSS.x1	CM-MSS.x2	CM-MSS.x3
Supply circuit - Input circuit					
Rated control supply voltage U_s		A1-A2	24-240 V AC/DC	24 V AC/DC	220-240 V AC
		A2-A3	-	-	110-130 V AC
Rated control supply voltage U_s tolerance			-15...+10 %		
Rated frequency			15-400 Hz	50-60 Hz	
Electrical insulation between supply circuit and measuring circuit			yes	no	yes
Power failure buffering time			20 ms		
Supply circuit - Measuring circuit / Sensor circuit					
Number of circuits			1 (CM-MSS.51: 2)		
Sensor type			PTC type A (DIN/EN 44081, DIN/EN 44082)		
Max. total resistance of sensors connected in series, cold state			< 750 Ω		
Overtemperature monitoring	switch-off resistance (relay de-energizes)		2.83 kΩ ± 1% (CM-MSS.12 /.13 /.22 /.23: 2.7 kΩ ± 5%)		
	switch-on resistance (relay energizes)		1.1 kΩ ± 1% (CM-MSS.12 /.13 /.22 /.23: 1.2 kΩ ± 5%)		
Maximum voltage in sensor circuit		1.33 kW	2.5 V		
		4 kW	3.7 V		
		∞ kW	5.5 V		
Maximum current in sensor circuit			3.7 mA		
Maximum sensor cable length			2 x 100 m at 0.75 mm², 2 x 400 m at 2.5 mm²		
Accuracy within the rated control supply voltage tolerance			0.50 % (CM-MSS.12 /.13 /.22 /.23: 5 %)		
Accuracy within the temperature range			0.01 %/K (CM-MSS.12 /.13 /.22 /.23: 0.5 %/K)		
Repeat accuracy (constant parameters)			on request		
Reaction time of the safety function			< 100 ms		
Hardware fault tolerance (HFT)			0		
Control circuit					
Control function			see "Selection table CM-MSx range"		
Maximum no-load voltage			5.5 V		
Max. current			0.6 mA (CM-MSS.12 /.13 /.22 /.23: 1.2 mA)		
Maximum cable length			2 x 100 m at 0.75 mm², 2 x 400 m at 2.5 mm²		
Indication of operational states					
Control supply voltage		U	LED green		
Relay status		R	LED yellow		
Fault message		F	LED red		
Output circuit					
Kind of output			see "Selection table CM-MSx range"		
Operating principle			closed-circuit principle		
Contact material			AgNi alloy, Cd free		
Rated operational voltage U_e (IEC/EN 60947-1)			250 V AC		
Minimum switching voltage / Minimum switching current			24 V / 10 mA		
Maximum switching voltage / Maximum switching current			see data sheet		
Rated operating current I_e (IEC/EN 60947-5-1)		AC-12 (resistive) at 230 V	4 A		
		AC-15 (inductive) at 230 V	3 A		
		DC-12 (resistive) at 24 V	4 A		
		DC-13 (inductive) at 24 V	2 A		
AC Rating (UL 508)		utilization category (Control Circuit Rating Code)	B 300		
		maximum rated operational voltage	300 V AC		
		maximum continuous thermal current at B 300	5 A		
		maximum making/breaking apparent power at B 300	3600/360 VA		
		general purpose rating	250 V AC - 4 A		
Mechanical lifetime			30 x 10^6 switching cycles		
Electrical lifetime		at AC12, 230 V AC, 4 A	0.1 x 10^6 switching cycles		
Maximum fuse rating to achieve short-circuit protection		n/c contact	10 A fast-acting (CM-MSS.12, CM-MSS.13, CM-MSS.51: 6 A)		
		n/o contact	10 A fast-acting		

Thermistor motor protection relays

Technical data - CM-MSS

Type		CM-MSS.x1	CM-MSS.x2	CM-MSS.x3
General data				
MTBF		on request		
Duty time		100 %		
Dimensions		see "Dimensional drawings"		
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool		
Mounting position		any		
Minimum distance to other units	vertical / horizontal	10 mm (0.394 in) if switching current > 2 A		
Material of housing		UL 94 V-0		
Degree of protection	housing	IP50		
	terminals	IP20		
Electrical connection		**Screw connection technology**		**Easy Connect Technology (push-in)**
Connection capacity	fine-strand with(out) wire end ferrule	1 x 0.5-2.5 mm² (1 x 18-14 AWG) 2 x 0.5-1.5 mm² (2 x 18-16 AWG)		2 x 0.5-1.5 mm² (2 x 18-16 AWG)
	rigid	1 x 0.5-4 mm² (1 x 20-12 AWG) 2 x 0.5-2.5 mm² (2 x 20-14 AWG)		2 x 0.5-1.5 mm² (2 x 20-16 AWG)
Stripping length		8 mm (0.32 in)		
Tightening torque		0.6-0.8 Nm (7.08 lb.in)		-
Environmental data				
Ambient temperature ranges	operation	-25...+60 °C (-13...+140 °F)		
	storage	-40...+85 °C (-40...+185 °F)		
Damp heat, cyclic (IEC/EN 60068-2-30)		6 x 24 h cycle, 55 °C, 95 % RH		
Climatic class (IEC/EN 60721-3-3)		3K5 (no condensation, no ice formation)		
Vibration, sinusoidal		5-13.2 Hz: ±1 mm; 13.2-100 Hz: 0.7 g		
Shock		Class 2		
Isolation data				
Rated insulation voltage U_i	Supply circuit / Measuring circuit[1)]	300 V AC (CM-MSS.x2: n/a)		
	Supply circuit / Output circuits	300 V AC		
	Measuring circuit (1) / Output circuits	300 V AC		
	Output circuit 1 / Output circuit 2	300 V AC		
Rated impulse withstand voltage U_{imp}	Supply circuit / Measuring circuit[1)]	4 kV (CM-MSS.x2: n/a)		
	Supply circuit / Output circuits	4 kV		
	Measuring circuit (1) / Output circuits	4 kV		
	Output circuit 1 / Output circuit 2	4 kV		
Basic insulation	Supply circuit / Measuring circuit[1)]	600 V AC (CM-MSS.x2: n/a)		
	Supply circuit / Output circuits	600 V AC		
	Measuring circuit (1) / Output circuits	600 V AC		
	Output circuit 1 / Output circuit 2	300 V AC		
Protective separation (IEC/EN 61140, EN 50178)	Supply circuit / Measuring circuit[1)]	yes, up to 300 V		
	Supply circuit / Output circuits	yes (CM-MSS.x2: n/a)		
	Measuring circuit (1) / Output circuits	yes		
	Output circuit 1 / Output circuit 2	no		
Pollution degree (IEC/EN 60664-1)		3		
Overvoltage category (IEC/EN 60664-1)		III		

[1)] Potential of measuring circuit = Potential of control circuit

Standards	
Product standard	EN 60947-5-1, EN 60947-8
Low Voltage Directive	2014/35/EU
EMC directive	2014/30/EU
ATEX directive	2014/34/EU (only ATEX variants, see "Selection table CM-MSx range")
RoHS directive	2011/65/EU

Thermistor motor protection relays

Technical data - CM-MSS

Type		CM-MSS.x1	CM-MSS.x2	CM-MSS.x3
Electromagnetic compatibility				
Interference immunity to		IEC/EN 61000-6-2, IEC/EN 60947-8		
electrostatic discharge	IEC/EN 61000-4-2	Level 3, 6 kV contact discharge, 8 kV air discharge		
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	Level 3, 10 V/m (1 GHz), 3 V/m (2 GHz), 1 V/m (2.7 GHz)		
electrical fast transient / burst	IEC/EN 61000-4-4	Level 3, 2 kV / 5 kHz		
surge	IEC/EN 61000-4-5	Level 3, Installation class 3, supply circuit and measuring circuit 1 kV L-L, 2 kV L-N		
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	Level 3, 0.15-80 MHz, 10 V, 80 % AM (1kHz)		
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	Class 3		
harmonics and interharmonics	IEC/EN 61000-4-13	Class 3		
Additional interference immunity according to product standard IEC/EN 60255-1 (reference on IEC/EN 60255-26)				
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	10 V/m (80 MHz - 3 GHz)		
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	10 V at stated frequencies		
damped oscillatory waves	IEC/EN 61000-4-18	Signal lines, symmetric coupling: 1 kV peak voltage Power supply, asymmetric coupling: 2.5 kV peak voltage		
Interference emissions		IEC/EN 61000-6-3		
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B		
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B		
high-frequency radiated	Germanischer Lloyd	increased requirements in the emergency call frequency band		

Thermistor motor protection relays

Technical data - CM-MSE

Data at T_a = 25 °C and rated values, unless otherwise indicated

Type			CM-MSE
Supply circuit - Input circuit			
Rated control supply voltage U_s power consumption		1SVR550805R9300	24 V AC approx. 1.5 A
		1SVR550800R9300	110-130 V AC approx. 1.5 A
		1SVR550801R9300	220-240 V AC approx. 1.5 A
Rated control supply voltage U_s tolerance			-15...+10 %
Rated frequency			50-60 Hz
Measuring circuit			
Monitoring function		T1-T2	temperature monitoring by means of PTC sensors
Number of sensor circuits			1
Sensor circuit			
Sensor type			PTC type A (DIN/EN 44081, DIN/EN 44082)
Max. total resistance of sensors connected in series, cold state			≤1.0 kΩ
Overtemperature monitoring		switch-off resistance (relay de-energizes)	2.0-3.0 kΩ
		switch-on resistance (relay energizes)	1.2-1.65 kΩ
Maximum voltage in sensor circuit		4 kΩ	5 V
		∞ kΩ	15 V
Maximum current in sensor circuit			2 mA
Maximum sensor cable length			2 x 100 m at 0.75 mm², 2 x 400 m at 2.5 mm²
Reaction time			<100 ms
Output circuit			
Kind of output		13-14	1 n/o contact
Operational principle			closed-circuit principle (output relay de-energizes if the measured value exceeds/drops below the adjusted threshold)
Maximum switching voltage			250 V
Rated operating voltage U_e and rated operating current I_e		AC-12 (resistive) at 230 V	4 A
		AC-15 (inductive) at 230 V	3 A
		DC-12 (resistive) at 24 V	4 A
		DC-13 (inductive) at 24 V	2 A
AC Rating (UL 508)	utilization category (Control Circuit Rating Code)		B 300
	maximum rated operational voltage		300 V AC
	maximum continuous thermal current at B 300		5 A
	maximum making/breaking apparent power at B 300		3600/360 VA
	general purpose rating		250 V AC - 4 A
Mechanical lifetime			30 x 10^6 switching cycles
Electrical lifetime		at AC12, 230 V AC, 4 A	0.1 x 10^6 switching cycles
Maximum fuse rating to achieve short-circuit protection		n/c contact	10 A fast-acting
		n/o contact	10 A fast-acting
General data			
Dimensions			see "dimensional drawings"
Duty cycle			100 %
Mounting			DIN rail (IEC/EN 60715)
Mounting position			any
Degree of protection		housing / terminals	IP50 / IP20
Electrical connection			
Connecting capacity		fine strand with wire end ferrule	2 x 1.5 mm² (2 x 16 AWG)
		fine strand without wire end ferrule	2 x 0.75-1.5 mm² (2 x 18-16 AWG)
		rigid	2 x 1-1.5 mm² (2 x 18-16 AWG)
Stripping length			2 x 0.75-1.5 mm² (2 x 18-16 AWG)
Tightening torque			0.6-0.8 Nm (5.31-7.08 lb.in)
Environmental data			
Ambient temperature ranges		Operation	-20..+60 °C
		Storage	-40...+85 °C
Damp heat		IEC/EN 60068-2-30	40 °C, 93 % RH, 4 days
Vibration withstand		IEC/EN 60062-2-6	10-57 Hz: 0.075 mm; 57-150 Hz: 1 g

Thermistor motor protection relays

Technical data - CM-MSE

Type		CM-MSE
Isolation data		
Rated insulation voltage U_i	supply, measuring / output circuit	250 V
Rated impulse withstand voltage U_{imp}	between all isolated circuits	4 kV / 1.2 - 50 µs
Pollution degree		3
Overvoltage category		III
Standards / Directives		
Standards		IEC/EN 60947-5-1, IEC/EN 60947-8
Low Voltage Directive		2014/35/EU
EMC Directive		2014/30/EU
RoHS Directive		2011/65/EU
Electromagnetic compatibility		
Interference immunity to		IEC/EN 61000-6-2, IEC/EN 60947-8
electrostatic discharge	IEC/EN 61000-4-2	Level 3, 6 kV contact discharge, 8 kV air discharge
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	Level 3, 10 V/m (1 GHz), 3 V/m (2 GHz), 1 V/m (2.7 GHz)
electrical fast transient /burst	IEC/EN 61000-4-4	Level 3, 2 kV / 5 kHz
surge	IEC/EN 61000-4-5	Level 3, installation class 3, supply circuit and measuring circuit 1 kV L-L, 2 kV L-N
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	Level 3, 0.15-80 MHz, 10 V, 80 % AM (1kHz)
Interference emission		IEC/EN 61000-6-3
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B

Thermistor motor protection relays
Technical data

LEDs, status information and fault messages

CM-MSS

Operational state	U: green LED	F: red LED	R: yellow LED
Absence of control supply voltage	OFF	OFF	OFF
Internal fault[2)]	OFF	⎍⎍⎽	⎍⎍⎽
Internal fault[2)]	⎍⎍⎍⎽	⎍⎍⎍⎽	⎍⎍⎍⎽
Control supply voltage not within the tolerance range	⎍⎍⎍⎽	⎍‾‾‾⎽	OFF
Short circuit	⎍‾‾‾⎽	⎍⎍⎍⎽	OFF
Interrupted wire	⎍‾‾‾⎽	⎍⎍⎍⎍⎽	OFF
Measuring circuit 2: Overtemperature	⎍‾‾‾⎽	⎍⎍⎽	OFF
Measuring circuit 1: Overtemperature	⎍‾‾‾⎽	⎍‾‾‾⎽	OFF
Fault rectified but not confirmed	⎍‾‾‾⎽	- [1)]	⎍⎍⎍⎽
Test function	⎍⎍⎍⎽	OFF	OFF
Change of configuration not confirmed	⎍‾‾‾⎽	OFF	⎍⎍⎍⎽
No fault	⎍‾‾‾⎽	OFF	⎍‾‾‾⎽


1) Depending on the fault with the highest priority
2) Restart the device. If after restart the same fault is indicated, replace the device.

Thermistor motor protection relays

Technical diagrams


Connection diagrams

CM-MSS.11x, CM-MSS.21x




A1 – A2	Control supply voltage
13 – 14	n/o contact
21 – 22	n/c contact
T1 – T2	Measuring circuit

CM-MSS.12x




A1 – A2	Control supply voltage
11 – 12/14	c/o contact
T1 – T2	Measuring circuit

CM-MSS.13x




A1 – A2	Control supply voltage 220-240 V AC
A2 – A3	Control supply voltage 110-130 V AC
11 – 12/14	c/o contact
T1 – T2	Measuring circuit

CM-MSS.31x




A1 – A2	Control supply voltage
13 – 14	n/o contact
21 – 22	n/c contact
S1 – T2	Automatic reset (jumpered)
T1 – T2	Measuring circuit

CM-MSS.22x, CM-MSS.32x, CM-MSS.41x




A1 – A2	Control supply voltage 24 V AC/DC
11 – 12/14	1st c/o (SPDT) contact
21 – 22/24	2nd c/o (SPDT) contact
S1 – T2	Automatic reset (jumpered)
T1 – T2	Measuring circuit

CM-MSS.23x, CM-MSS.33x




A1 – A2	Control supply voltage 220-240 V AC
A2 – A3	Control supply voltage 110-130 V AC
11 – 12/14	1st c/o (SPDT) contact
21 – 22/24	2nd c/o (SPDT) contact
S1 – T2	Automatic reset (jumpered)
T1 – T2	Measuring circuit

CM-MSS.51x



A1 – A2	Control supply voltage 220-240 V AC
11 – 12/14	1st c/o (SPDT) contact
21 – 22/24	2nd c/o (SPDT) contact
S1 – 1T2/2T2	Automatic reset (jumpered)
1T1 – 1T2/2T2	Measuring circuit 1
2T1 – 1T2/2T2	Measuring circuit 2

CM-MSE




A1 – A2	Control supply voltage 24 V AC
T1-T2	Sensor circuit
13-14	Output contact - Closed circuit principle

Thermistor motor protection relays


Technical diagrams

Circuit diagrams


CM-MSS.11x, CM-MSS.21x




CM-MSS.12x




CM-MSS.13x




CM-MSS.22x




CM-MSS.23x




CM-MSS.31x




CM-MSS.32x, CM-MSS.41x




CM-MSS.33x



CM-MSS.51x



CM-MSE




A1
11
21
T3
T2
T1
ABB
CM-TCS
Hyst. %
(91)
91 °C
Hyst. %
(92)
92 °C
U
9
R
14
24
22

Temperature monitoring relays
Table of contents

204 Benefits and advantages
205 Applications
207 Operating controls
208 Selection table
209 Ordering details
210 Configuration and setup
212 Technical data
215 Technical diagrams
216 Function diagrams

Temperature monitoring relays
Benefits and advantages



The temperature monitoring relays of the CM-TCS range are able to measure temperatures of solids, liquids and gaseous media using PT100 sensors. Over-temperature and undertemperature monitoring, as well as open- or closed-circuit principle is configurable for all devices. As soon as the temperature falls below or exceeds the set threshold value, the output relays change their positions and the front-face LED‘s display the current status.

Continuous operation

By using temperature monitoring relays, both the downtime and the commissioning time can be reduced. The relay is continuously monitoring the sensor circuit to detect short-circuit or interrupted wire faults. The high accuracy of the measuring input leads to a fast detection of exceeding threshold values. In case of fault, maintenance effort is reduced and time saved.

Reliable in harsh conditions

All relays work reliably in environments with low temperatures down to -40 °C. Additionally, the housing fulfills the UL 94 V-0 flammability standard requirements. Together with the vibration resistant push-in terminals, the relay is not only reliable no matter the environment temperature but is also durable to shock and vibration. Save time as retightening is no longer needed and enhance the reliability and safety not only for the equipment.

Easy installation

Like all devices from the measuring and monitoring portfolio, the CM-TCS relays are easily configurable via front facing potentiometers. Easy threshold configuration without calculation is accomplished by direct reading scales. For further configuration options, additional settings can be made via dip-switches, offering the flexibility to configure, for example, the working principle of the relays and the output configuration. The device can be set up before installation in the application and easy adjustments during the process are possible.

Temperature monitoring relays
Applications

The temperature monitoring relays CM-TCS monitor overtemperature, undertemperature, or temperatures between two threshold values (window monitoring) with a PT100 sensor.

As soon as the temperature falls below or exceeds the threshold value, the output relays change their positions according to the configured functionality.

The current status is displayed by front-faced LEDs. Regardless of the selected configuration, the device is monitoring its measuring circuit for interrupted wires or short-circuits.











ABB
Thermo
SCIENTIFIC
LYNX 6000








Temperature monitoring relays
Operating controls

Push-in and screw terminals

Measuring input:
PT100

Adjustment of the threshold value
- 50 ... + 50 °C
0 ... + 100 °C
0 ... + 200 °C



Adjustment of the hysteresis for threshold value 2 - 20 %


Indication of operational states
U: green LED – status indication of control supply voltage
ϑ: red LED – fault message, state of measuring input
R: yellow LED – status indication of the output relays

DIP switch functions / marker label
- Overtemperature monitoring
- Undertemperature monitoring
- Temperature window monitoring activated
- Temperature window monitoring de-activated
- Closed-circuit principle
- Open-circuit principle
- 2 x 1 c/o (SPDT) contact
- 1 x 2 c/o (SPDT) contacts

Temperature monitoring relays

Selection table

	Order number	1SVR 730 740 R9100	1SVR 740 740 R9100	1SVR 730 740 R0100	1SVR 740 740 R0100	1SVR 730 740 R9200	1SVR 740 740 R9200	1SVR 730 740 R0200	1SVR 740 740 R0200	1SVR 730 740 R9300	1SVR 740 740 R9300	1SVR 730 740 R0300	1SVR 740 740 R0300
	Type	CM-TCS.21S	CM-TCS.21P	CM-TCS.11S	CM-TCS.11P	CM-TCS.22S	CM-TCS.22P	CM-TCS.12S	CM-TCS.12P	CM-TCS.23S	CM-TCS.23P	CM-TCS.13S	CM-TCS.13P
Rated control supply voltage U_s													
24 V AC/DC		■	■			■	■			■	■		
24-240 V AC/DC				■	■			■	■			■	■
Sensor circuits (2 or 3 wire)													
Number of temperature sensors		1	1	1	1	1	1	1	1	1	1	1	1
Number of thresholds		2	2	2	2	2	2	2	2	2	2	2	2
Measuring temperature range													
-50...+50 °C		■	■	■	■								
0...+100 °C						■	■	■	■				
0...+200 °C										■	■	■	■
Monitoring function													
Overtemperature		■	■	■	■	■	■	■	■	■	■	■	■
Undertemperature		■	■	■	■	■	■	■	■	■	■	■	■
Window temperature		■	■	■	■	■	■	■	■	■	■	■	■
Operating principle													
open or closed-circuit principle		■	■	■	■	■	■	■	■	■	■	■	■
Output contacts													
c/o		2	2	2	2	2	2	2	2	2	2	2	2



Temperature monitoring relays
Ordering details



CM-TCS

Description CM-TCS


The temperature monitoring relays CM-TCS are able to measure temperatures of solids, liquids and gaseous media using PT100 sensors. Overtemperature and undertemperature monitoring, as well as open- or closed-circuit principle, is configurable for all devices. As soon as the temperature falls below or exceeds the set threshold value, the output relays change their positions according to the configured functionality and the front-face LEDs display the current status.

Ordering details

Temperature monitoring relays CM-TCS

Rated control supply voltage	Measuring range	Temperature sensors	Type	Order code	Weight (1 pc) kg (lb)
24-240 V AC/DC	-50...+50 °C	PT100	CM-TCS.11S	1SVR730740R0100	0.151 (0.333)
			CM-TCS.11P	1SVR740740R0100	0.140 (0.309)
	0...+100 °C		CM-TCS.12S	1SVR730740R0200	0.151 (0.333)
			CM-TCS.12P	1SVR740740R0200	0.140 (0.309)
	0...+200 °C		CM-TCS.13S	1SVR730740R0300	0.151 (0.333)
			CM-TCS.13P	1SVR740740R0300	0.140 (0.309)
24 V AC/DC	-50...+50 °C		CM-TCS.21S	1SVR730740R9100	0.138 (0.304)
			CM-TCS.21P	1SVR740740R9100	0.127 (0.280)
	0...+100 °C		CM-TCS.22S	1SVR730740R9200	0.138 (0.304)
			CM-TCS.22P	1SVR740740R9200	0.127 (0.280)
	0...+200 °C		CM-TCS.23S	1SVR730740R9300	0.138 (0.304)
			CM-TCS.23P	1SVR740740R9300	0.127 (0.280)


S: screw connection
P: push-in connection



Temperature monitoring relays

Configuration and setup

DIP switches




	ON	OFF (default)
DIP switch 1 Monitoring principle	Overtemperature monitoring If overtemperature monitoring is selected, the CM-TCS recognizes temperatures above the selected threshold and trips the output relay according to the selected operating principle.	Undertemperature monitoring If undertemperature monitoring is selected, the CM-TCS recognizes temperatures below the selected threshold and trips the output relay according to the selected operating principle.
DIP switch 2 Temperature window monitoring	Temperature window monitoring activated If temperature window monitoring is selected, the CM-TCS monitors over- and undertemperature. If temperature window monitoring is activated, DIP switch 1 is disabled.	Temperature window monitoring de-activated Temperature window monitoring is de-selected.
DIP switch 3 Operating principle of the output relays	Closed-circuit principle If closed-circuit principle is selected, the output relays are energized. They de-energize if a fault is occurring.	Open-circuit principle If open-circuit principle is selected, the output relays are deenergized. They energize if a fault is occurring.
DIP switch 4 2 x 1 c/o contact, 1 x 2 c/o contacts	2 x 1 c/o (SPDT) contact If operating principle 2 x 1 c/o contact is selected, the output relay R1 (11-12/14) reacts to threshold value $\vartheta 1$ and the output relay R2 (21-22/24) reacts to threshold value $\vartheta 2$.	1 x 2 c/o (SPDT) contacts If operating principle 1 x 2 c/o contacts is selected, both output relays R1 (11-12/14) and R2 (21-22/24) react synchronously to one threshold value. Overtemperature monitoring: Settings of the threshold value $\vartheta 2$ have no effect on the operation. Undertemperature monitoring: Settings of the threshold values $\vartheta 2$ have no effect on the operation.


Temperature monitoring relays
Configuration and setup

Connection of resistance thermometer sensors

2-wire measurement
When using 2-wire temperature sensors, the sensor resistance and the wire resistance are added together. The resulting systematic errors must be taken into account when adjusting the tripping device. A jumper must be connected between the terminals T2 and T3.
The following table can be used for PT100 sensors to determine the temperature errors caused by the line length. When using resistance sensors with two-wire connection a bridge must be inserted between terminals T2 and T3.



3-wire measurement
To minimize the influence of the wire resistance, a three-wire connection is usually used. By means of the additional wire, two measuring circuits are created. One of these two circuits is used for reference. This way, the tripping device can calculate and take into account the wire resistance automatically.



Temperature error
(depending on the line length and conductor cross section for PT100 sensors at an ambient temperature of 20 °C, in K)

Line length in m	Wire size mm²			
	0.50	**0.75**	**1**	**1.5**
0	0.0	0.0	0.0	0.0
10	1.8	1.2	0.9	0.6
25	4.5	3.0	2.3	1.5
50	9.0	6.0	4.5	3.0
75	13.6	9.0	6.8	4.5
100	18.1	12.1	9.0	6.0
200	36.3	24.2	18.1	12.1
500	91.6	60.8	45.5	30.2

Error caused by the line
The error resulting from the line resistance amounts to approx. 2.5 Kelvin/Ohm. If the resistance of the line is not known and it is not possible to measure it, the error caused by the line can be estimated using the following table.

Temperature monitoring relays
Technical data

Type		**CM-TCS.11/12/13**	**CM-TCS.21/22/23**
Input circuit			
Rated control supply voltage U_s	A1-A2	24-240 V AC/DC	24 V AC/DC
Rated control supply voltage U_s tolerance		-15...+10 %	
Typical current / power / consumption	24 V DC	33 mA / 0.8 VA	18 mA / 0.45 VA
	115 V AC	12.5 mA / 1.5 VA	n/a
	230 V AC	13 mA / 2.9 VA	n/a
Rated frequency	AC	15-400 Hz	50/60 Hz
Frequency range	AC	13.5-440 Hz	45-65 Hz
Power failure buffering time	min.	20 ms	
Measuring circuit		**T1, T2, T3**	
Sensor type		PT100	
Connection of the sensor	2-wire	yes, jumper between T2-T3	
	3-wire	yes, use terminal T1, T2, T3	
Monitoring function		overtemperature, undertemperature or window monitoring	
Threshold values adjustable within the measuring range	CM-TCS.x1	-50...+50 °C	
	CM-TCS.x2	0...+100 °C	
	CM-TCS.x3	0...+200 °C	
Number of possible thresholds		2	
Tolerance of the adjusted threshold value		typ. ±5 % of the range end value	
Hysteresis related to the threshold value		2-20 % of threshold value, min. 1 °C	
Measuring principle		continuous current	
Typical current in the sensor circuit		0.8 mA	
Maximum current in sensor circuit		0.9 mA	
Interrupted wire detection		yes, indicated via LED status	
Short-circuit detection		yes, indicated via LED status	
Accuracy within the rated control supply voltage tolerance		< 0.2 °C / or < 0.01 %/K	
Accuracy within the temperature range		< 0.2 °C / or < 0.01 %/K	
Repeat accuracy (constant parameters)		< 0.2 % of full scale	
Maximum measuring cycle		320 ms	
Output circuit			
Kind of output		2 x 1 or 1 x 2 c/o (SPDT) contacts configurable	
Operating principle		open- or closed-circuit principle configurable (1)	
Contact material		AgNi alloy, Cd free	
Minimum switching voltage / Minimum switching current		24 V / 10 mA	
Maximum switching voltage / Maximum switching current		see 'Load limit curves'	
Rated operational voltage U_e and rated operational current I_e	AC-12 (resistive) 230 V	4 A	
	AC-15 (inductive 230 V	3 A	
	DC-12 (resistive) 24 V	4 A	
	DC-13 (inductive) 24 V	2 A	
AC Rating (UL508)	utilization category	B 300 pilot duty; general purpose 250 V, 4 A, cos φ 0.75	
	maximum rated operational voltage	250 V AC	
	maximum continuous thermal current at B 300	4 A	
	maximum making/breaking apparent power at B 300	3600/360 VA	
Mechanical lifetime		30 x 10^6 switching cycles	
Electrical lifetime (AC-12, 230 V, 4 A)		0.1 x 10^6 switching cycles	
Maximum fuse rating to achieve short-circuit protection	n/c contact	6 A fast-acting	
	n/o contact	10 A fast-acting	
Conventional thermal current I_{th}		4 A	

(1) Closed-circuit principle: Output relay(s) de-energize(s) if measured value exceeds or falls below the adjusted threshold value

Temperature monitoring relays

Technical data

Type			CM-TCS.11/12/13	CM-TCS.21/22/23
General data				
Dimensions			see "dimensional drawings"	
Mounting			DIN rail (IEC/EN 60715), snap-on mounting without any tool	
Mounting position			any	
Degree of protection		enclosure / terminals	IP50 / IP20	
Ambient temperature range		operation	-40...+60 °C	
		storage /transport	-40...+85 °C	
Electrical connection				
Wire size			**Screw connection technology**	**Easy Connect Technology (Push-in)**
	fine-strand without wire end ferrule	A1, A2, 11, 12, 14, 21, 22, 24	1 x 0.5-2.5 mm² (1 x 20-14 AWG) 2 x 0.5-1.5 mm² (2 x 20-16 AWG)	2 x 0.5-1.5 mm² (2 x 20-16 AWG) connection with lever
		T1, T2, T3	1 x 0.2-2.5 mm² (1 x 24-14 AWG) 2 x 0.2-1.5 mm² (2 x 24-16 AWG)	2 x 0.2-1.5 mm² (2 x 24-16 AWG) connection with lever
	fine-strand with wire end ferrule	A1, A2, 11, 12, 14, 21, 22, 24	1 x 0.5-2.5 mm² (1 x 20-14 AWG) 2 x 0.5-1.5 mm² (2 x 20-16 AWG)	2 x 0.5-1.5 mm² (2 x 20-16 AWG) connection: push-in
		T1, T2, T3	1 x 0.2-2.5 mm² (1 x 24-14 AWG) 2 x 0.2-1.5 mm² (2 x 24-16 AWG)	2 x 0.2-1.5 mm² (2 x 24-16 AWG) insulated ferrule (DIN 46228-4-E): connection: push-in ferrule (DIN 46228-1-A): < 0.5 mm², connection with lever ≥ 0.5 mm², connection: push-in
	rigid	A1, A2, 11, 12, 14, 21, 22, 24	1 x 0.5-4 mm² (1 x 20-12 AWG) 2 x 0.5-2.5 mm² (2 x 20-14 AWG)	2 x 0.5-1.5 mm² (2 x 20-16 AWG) connection: push-in
		T1, T2, T3	1 x 0.2-4 mm² (1 x 24-12 AWG) 2 x 0.2-2.5 mm² (2 x 24-14 AWG)	2 x 0.2-1.5 mm² (2 x 24-16 AWG) < 0.5 mm², connection with lever ≥ 0.5 mm², connection: push-in
Stripping length			8 mm (0.32 In)	
Tightening torque		< 0.5 mm²	0.5 Nm (4.43 lb.In)	-
		≥ 0.5 mm²	0.6 - 0.8 Nm (5.31 - 7.08 lb.In)	-
Standards / Directives				
Standards			IEC/EN 60255-27, IEC/EN 60947-5-1	
Low Voltage Directive			2014/35/EU	
EMC Directive			2014/30/EU	
RoHS Directive			2011/65/EU	
Environmental data				
Ambient temperature ranges		operation/storage/ transport	-40...+60 °C/-40...+85 °C/-40...+85 °C	
Climatic class		IEC/EN 60721-3-3	3K5 (no condensation, no ice formation)	
Damp heat, cyclic		IEC/EN 600068-2-30	6 x 24 h cycle, 55 °C, 95 % RH	
Vibration, sinusoidal			Class 2	
Shock			Class 2	
Isolation data				
Rated impulse withstand voltage U_{imp}		supply circuit / measuring circuit	4 kV	-
		supply circuit / output circuits	4 kV	
		measuring circuit / output circuits	4 kV	
		output circuit 1 / output circuit 2	4 kV	
Rated insulation voltage U_i		supply circuit / measuring circuit	300 V	-
		supply circuit / output circuits	300 V	
		measuring circuit / output circuits	300 V	
		output circuit 1 / output circuit 2	300 V	


Temperature monitoring relays
Technical data

Type		**CM_TCS.11/12/13**	**CM-TCS.21/22/23**
Basis insulation	supply circuit / measuring circuit	250 V AC / 300 V DC	-
	supply circuit / output circuits	250 V AC / 300 V DC	
	measuring circuit / output circuits	250 V AC / 300 V DC	
	output circuit 1 / output circuit 2	250 V AC / 300 V DC	
Protective separation (IEC/EN 61140, EN 50178)	supply circuit / measuring circuit	250 V AC / 250 V DC	-
	supply circuit / output circuits	250 V AC / 300 V DC	250 V AC / 250 V DC
	measuring circuit / output circuits	250 V AC / 300 V DC	250 V AC / 250 V DC
Pollution degree		3	
Overvoltatge category		III	
Electromagnetic compatibility			
Interference immunity to		IEC/EN 61000-6-2	
electrostatic discharge	IEC/EN 61000-4-2	Level 3, 6 kV / 8 kV	
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	Level 3, 10 V/m (1 GHz) / 3 V/m (2 GHz) / 1 V/m (2.7 GHz)	
electrical fast transient/burst	IEC/EN 61000-4-4	Level 3, 2 KV / 5 kHz	
surge	IEC/EN 61000-4-5	Level 3, installation class 3, supply circuit and measuring circuit 1 kV L-L, 2 kV L-earth	
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	Level 3, 10 V	
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	Class 3	
harmonics and interharmonics	IEC/EN 61000-4-13	Class 3	
Interference emission		IEC/EN 61000-6-3	
high-frequency radiated	IEC/CISPR 22, EN 55022	Class B	
high-frequency conducted	IEC/CISPR 22, EN 55022	Class B	

Temperature monitoring relays

Technical diagrams


Connection diagram



A1 – A2	Control supply voltage
11 – 12/14	Output relay R1
21 – 22/24	Output relay R2
T1, T2, T3	Measuring input, connection PT100

Dimensional drawing


in **mm** and inches



CM-TCS.xxx


Electrical isolation

CM-TCS.2x




Electrical isolation

CM-TCS.1x



Protective separation
acc. to IEC/EN 61140; EN 50178


Temperature monitoring relays
Function diagrams



Overtemperature monitoring, 1 x 2 c/o contacts 1x2 c/o
With this configuration, settings via $\vartheta 2$ have no influence on the operating function ($\vartheta 2$ disabled).


Open-circuit principle:
If the measured value is correct, the output relays remain de-energized when control supply voltage is applied. If the measured value exceeds the adjusted threshold value $\vartheta 1$, the output relays energize. If the measured value drops again below the adjusted threshold value $\vartheta 1$ minus the adjusted hysteresis, the output relays de-energize.

Closed-circuit principle:
The behavior is inverse to the one with open-circuit principle.



Overtemperature monitoring, 2 x 1 c/o contact 2x1 c/o
Open-circuit principle:
If the measured value is correct, the output relays remain de-energized when control supply voltage is applied. If the measured value exceeds the adjusted threshold value $\vartheta 2$, output relay R2 (prewarning) energizes. If the measured value exceeds the adjusted threshold value $\vartheta 1$, output relay R1 (final switch-off) energizes.
If the measured value drops again below the adjusted threshold value $\vartheta 1$ minus the adjusted hysteresis, output relay R1 (final switch-off) de-energizes. If the measured value drops below the adjusted threshold value $\vartheta 2$ minus the adjusted hysteresis, output relay R2 (prewarning) de-energizes.

Closed-circuit principle:
The behavior is inverse to the one with open-circuit principle.




Undertemperature monitoring, 1 x 2 c/o contacts 1x2 c/o
With this configuration, settings via $\vartheta 1$ have no influence on the operating function ($\vartheta 1$ disabled).

Open-circuit principle:
If the measured value is correct, the output relays remain de-energized when control supply voltage is applied. If the measured value drops below the adjusted threshold value $\vartheta 2$, the output relays energize. If the measured value exceeds again the adjusted threshold value $\vartheta 2$ plus the adjusted hysteresis, the output relays de-energize.


Closed-circuit principle:
The behavior is inverse to the one with open-circuit principle.

Temperature monitoring relays
Function diagrams




Undertemperature monitoring, 2 x 1 c/o contact 2x1 c/o
Open-circuit principle:
If the measured value is correct, the output relays remain de-energized when control supply voltage is applied. If the measured value drops below the adjusted threshold value $\vartheta 1$, output relay R1 (prewarning) energizes. If the measured value drops below the adjusted threshold value $\vartheta 2$, output relay R2 (final switch-off) energizes.
If the measured value exceeds again the adjusted threshold value $\vartheta 2$ plus the adjusted hysteresis, output relay R2 (final switch-off) de-energizes. If the measured value exceeds the adjusted threshold value $\vartheta 1$ plus the adjusted hysteresis, output relay R1 (prewarning) de-energizes.

Closed-circuit principle:
The behavior is inverse to the one with open-circuit principle.



Temperature window monitoring, 1 x 2 c/o contacts 1x2 c/o
Open-circuit principle:
If the measured value is correct, the output relays remain de-energized when control supply voltage is applied. If the measured value exceeds the adjusted threshold value $\vartheta 1$ or drops below the adjusted threshold value $\vartheta 2$, the output relays energize. If the measured value drops again below the adjusted threshold value $\vartheta 1$ minus the adjusted hysteresis or exceeds again the adjusted threshold value $\vartheta 2$ plus the adjusted hysteresis, the output relays de-energize.

Closed-circuit principle:
The behavior is inverse to the one with open-circuit principle.



Temperature window monitoring, 2 x 1 c/o contact 2x1 c/o
Open-circuit principle:
If the measured value is correct, the output relays remain de-energized when control supply voltage is applied.
If the measured value exceeds the adjusted threshold value $\vartheta 1$ or drops below the adjusted threshold value $\vartheta 2$, output relay R1 (> $\vartheta 1$) or R2 (< $\vartheta 2$) respectively energizes.
If the measured value drops again below the adjusted threshold value $\vartheta 1$ minus the adjusted hysteresis or exceeds again the adjusted threshold value $\vartheta 2$ plus the adjusted hysteresis, output relay R1 (>$\vartheta 1$) or R2 (<$\vartheta 2$) respectively de-energizes.

Closed-circuit principle:
The behavior is inverse to the one with open-circuit principle.


A1
11
C
MAX
MIN
ABB
CM-ENS
Sens. kΩ
U
R
MIN/
MAX
A1
11
C
MAX
MIN
ABB
CM-ENS
Function
Sens. range Ω
Sens. Ω
U
R
MIN/
MAX
A1
11 15
C
MAX
MIN
ABB
CM-ENS
Time
Function
Sens. range Ω
Sens. Ω
U/T
R
MIN/
MAX
24 28
21 25
22 26
14

Liquid level monitoring relays
Table of contents

220 Benefits and advantages

222 Applications

226 Operating controls

228 Selection table

229 Ordering details

230 Technical data

236 Function diagrams

237 Technical diagrams

Liquid level monitoring relays
Benefits and advantages



ABB's liquid level monitoring relays are the ideal solution to regulate and control liquid levels and ratios of mixtures of conductive fluids. The assortment includes single- or multifunctional devices which can be used for overflow protection, dry-running protection of pumps, filling and draining applications as well as max. and min. level alarming.

Global availability

The liquid level monitoring relays are designed to provide a wide supply voltage range, making global differences irrelevant. Additionally, the CM-ENS range meets a broad range of standards and requirements. Together with ABB's global support and sales network, using CM-ENS gives customers the confidence of worldwide sourcing – no matter where they build, install or operate their equipment.

Reliable in harsh conditions

High immunity against electromagnetic disturbances is ensured due to advanced measuring technology. Additionally, the housing fulfills the UL 94 V-0 flammability standard requirements. Together with the vibration resistant push-in terminals, the relay is not only reliable no matter the environment temperature but is also durable to shock and vibration. Save time as re-tightening is no longer needed and enhance the reliability and safety not only for the equipment.

Improve installation efficiency

Like all devices from the measuring and monitoring portfolio, the CM-ENS relays are easily configurable via front facing potentiometers. Easy threshold configuration without calculation is accomplished by direct reading scales. The device can be set up before installation in the application and easy adjustments during the process are possible.

Liquid level monitoring relays
Benefits and advantages



Operating principle

Liquid level control relays CM-ENS are designed to monitor levels of conductive liquids and media and is used, for example, for liquid level control in pump systems. The measuring principle is based on the resistance change sensed by single-pole electrodes. To avoid electrolytic phenomena, an AC current runs across the probes.
A selector switch on the front panel allows selection of the required function and the sensitivity range.



Suitability

Suitable for		Not suitable for	
spring water	acids, bases	chemically pure water	ethylene glycol
drinking water	liquid fertilizers	fuel	concentrated alcohol
sea water	milk, beer, coffee	oils	paraffin
sewage	non-concentrated alcohol	explosive areas (liquid gas)	lacquers



Characteristics

CM-ENS.1x
- Control of one or two liquid levels (min/max)
- Fill or drain function
- Adjustable response sensitivity 5-100 kΩ

CM-ENS.2x
- Control of one or two liquid levels (min/max)
- Fill (UP) or Drain (DOWN), adjustable via front-face potentiometer
- Adjustable response sensitivity 0.1-1000 kΩ

CM-ENS.31
- Control of one or two liquid levels (min/max)
- Fill (UP) or Drain (DOWN), adjustable via front-face potentiometer
- Adjustable response sensitivity 0.1-1000 kΩ
- Selectable ON- or OFF-delay
- 2 c/o (SPDT) contacts

All CM-ENS devices
- Devices with wide rated control supply voltage 24-240 V AC/DC
- Cascadable
- High EMC immunity
- 3 LEDs for the indication of operational states
- Screw connection technology or Easy Connect Technology
- Housing material for highest fire protection classification UL 94 V-0
- Tool-free mounting and demounting on DIN rail
- 22.5 mm (0.89 in) width

Liquid level monitoring relays
Applications

Liquid level monitoring relays work in conjunction with, for example, suspension electrodes, and can be used either for direct liquid level control or also for cascading devices, as well as operation modes with several electrodes, or control of two liquid levels are possible.



Suspension electrode







Liquid level monitoring relays
Applications

Cascading of several devices


With the CM-ENS it is possible to use two devices in one tank. This enables the possibility to realize a pre-warning with additional electrodes. In this way, two additional alarm outputs for exceeding or dropping below the normal level can be implemented in addition to the filling levels MAX and MIN. In addition, a reserve pump can be connected to the additional device.




Filling with alarm empty



Filling with reserve pump



Draining with alarm full




Draining with reserve pump

Operating mode with three electrodes

The CM-ENS measures the electrical resistance of the liquid between two immersion electrodes and a reference electrode.

For CM-ENS.1x only: If the relay is connected to the rated control supply voltage, the output relay changes its switching state as soon as the liquid level reaches the MAX-electrode, while the minimum sensor is submerged. The relay returns to the original state as soon as the minimum sensor is no longer in contact with the monitored medium.


For CM-ENS.2x and CM-ENS.31 only: The function fill (^) or drain (v) can be selected via a front-face potentiometer. If the fill function is selected, the output relay is energized until the MAX-electrode becomes wet. Then it is de-energized and not re-energized until the MIN-electrode becomes dry. If the drain function is selected, the output relay energizes as soon as the MAX-electrode becomes wet. It remains energized until the liquid level has dropped below the MIN-electrode.



Operation mode with three electrodes

Operation mode with two electrodes

If only one level should be controlled, only the MAX-electrode shall be connected at the CM-ENS.




Operation mode with two electrodes

Liquid level monitoring relays
Applications

Control of two liquid levels via liquid level monitoring relay CM-ENS

In combination with suspension electrodes CM-HC or CM-HCT (suitable for drinking water).







Liquid level monitoring relays
Applications

Overflow protection via liquid level monitoring relay CM-ENS


In combination with the compact support CM-KH-3 and 3 bar electrodes CM-SE.





Liquid level monitoring relays
Operating controls

CM-ENS.1x




Adjustment of the response sensitivity

Marker label

Indication of operational states with LEDs
U: green LED - Status indication of control supply voltage
⎍⎺⎺⎺⎺⎺⎍ control supply voltage applied
R: yellow LED - Status indication of the output relays
⎍⎺⎺⎺⎺⎺⎍ energized
MIN/MAX: yellow LED - Status indication of the electrodes
⎍⎺⎺⎺⎺⎺⎍ MIN and MAX wet
⎍⎺⎍⎺⎍⎺⎺⎺⎍ MIN wet

CM-ENS.2x



Adjustment of the function
↑ Fill
↓ Drain

Adjustment of the response sensitivity range

Adjustment of the response sensitivity

Marker label

Indication of operational states with LEDs
U: green LED - Status indication of control supply voltage
⎍⎺⎺⎺⎺⎺⎍ control supply voltage applied
R: yellow LED - Status indication of the output relays
⎍⎺⎺⎺⎺⎺⎍ energized
MIN/MAX: yellow LED - Status indication of the electrodes
⎍⎺⎺⎺⎺⎺⎍ MIN and MAX wet
⎍⎺⎍⎺⎍⎺⎺⎺⎍ MIN wet

Liquid level monitoring relays
Operating controls

CM-ENS.31


Adjustment of the time delay

Adjustment of the function
- ON-delayed Fill
- ON-delayed Drain
- OFF-delayed Fill
- OFF-delayed Drain

Adjustment of the response sensitivity range

Adjustment of the response sensitivity

Marker label



Indication of operational states with LEDS

U: green LED - Status indication of control supply voltage
- control supply voltage applied
- time delay is running

R: yellow LED - Status indication of the output relays
- energized

MIN/MAX: yellow LED - Status indication of the electrodes
- MIN and MAX wet
- MIN wet

Liquid level monitoring relays
Selection table

	Order code	1SVR 550 855 R9500	1SVR 550 850 R9500	1SVR 550 851 R9500	1SVR 550 855 R9400	1SVR 550 850 R9400	1SVR 550 851 R9400	1SVR 730 850 R0100	1SVR 740 850 R0100	1SVR 730 850 R2100	1SVR 740 850 R2100	1SVR 730 850 R0200	1SVR 740 850 R0200	1SVR 730 850 R2200	1SVR 740 850 R2200	1SVR 730 850 R0300	1SVR 740 850 R0300
	Type	CM-ENE MIN	CM-ENE MIN	CM-ENE MIN	CM-ENE MAX	CM-ENE MAX	CM-ENE MAX	CM-ENS.11S	CM-ENS.11P	CM-ENS.13S	CM-ENS.13P	CM-ENS.21S	CM-ENS.21P	CM-ENS.23S	CM-ENS.23P	CM-ENS.31S	CM-ENS.31P
Rated control supply voltage Us																	
24-240 V AC/DC								■	■			■	■			■	■
24 V AC		■			■												
110-130 V AC			■			■				■	■			■	■		
220-240 V AC				■			■			■	■			■	■		
Sensor circuit																	
Number of electrodes (including ground reference)		2	2	2	2	2	2	3	3	3	3	3	3	3	3	3	3
Response sensitivity range																	
0-100 kOhm		■	■	■	■	■	■										
5-100 kOhm								adj	adj	adj	adj						
0.1-1000 kOhm												adj	adj	adj	adj	adj	adj
Monitoring function																	
Dry running protection		■	■	■				■	■	■	■	■	■	■	■	■	■
Overflow protection					■	■	■	■	■	■	■	■	■	■	■	■	■
Liquid level control					■	■	■	■	■	■	■	■	■	■	■	■	■
Operating principle																	
Open-circuit principle		■	■	■				■	■	■	■						
Closed-circuit principle					■	■	■										
Open- or closed-circuit principle												sel	sel	sel	sel	sel	sel
Adjustable ON-/OFF-delay																	
0.1-10 s																■	■
Output contacts																	
n/o		1	1	1	1	1	1										
c/o (SPDT)								1	1	1	1	1	1	1	1	2	2
Connection type																	
Push-in terminals									■		■		■		■		■
Double-chamber cage connection terminals								■		■		■		■		■	
Screw		■	■	■	■	■	■										

adj: adjustable
sel: selectable

Liquid level monitoring relays
Ordering details



CM-ENE MIN



CM-ENS.3x

Description

The liquid level monitoring relays CM-ENS and CM-ENE monitors and controls the liquid level and ratios of mixtures of conductive fluids. It is used for filling and draining applications, to protect pumps against dry-running, to protect tanks against overflow, and for signalization of the status of the monitored liquid level.

Ordering details

Characteristics	Type	Order code	Weight (1 pc) kg (lb)
See selection table	CM-ENE MIN	1SVR550855R9500	0.15 (0.33)
		1SVR550850R9500	0.15 (0.33)
		1SVR550851R9500	0.15 (0.33)
	CM-ENE MAX	1SVR550855R9400	0.15 (0.33)
		1SVR550850R9400	0.15 (0.33)
		1SVR550851R9400	0.15 (0.33)
	CM-ENS.11S	1SVR730850R0100	0.124 (0.273)
	CM-ENS.11P	1SVR730850R2100	0.117 (0.258)
	CM-ENS.13S	1SVR740850R0100	0.153 (0.337)
	CM-ENS.13P	1SVR740850R2100	0.145 (0.320)
	CM-ENS.21S	1SVR730850R0200	0.125 (0.276)
	CM-ENS.21P	1SVR740850R0200	0.117 (0.258)
	CM-ENS.23S	1SVR730850R2200	0.154 (0.340)
	CM-ENS.23P	1SVR740850R2200	0.147 (0.324)
	CM-ENS.31S	1SVR730850R0300	0.143 (0.315)
	CM-ENS.31P	1SVR740850R0300	0.134 (0.295)

Liquid level monitoring relays

Technical data

Type		**CM-ENE MIN**	**CM-ENE MAX**
Supply circuit			
Rated control supply voltage U_S - power consumption	A1-A2	24 V AC, approx. 1.5 VA	
	A1-A2	110-130 V AC, approx. 1.2 VA	
	A1-A2	220-240 V AC, approx. 1.4 VA	
Rated control supply voltage U_S tolerance		-15...+15 %	
Rated frequency		50-60 Hz	
Measuring circuit		**MIN-C, MAX-C**	
Monitoring function		dry-running protection	overflow protection
Response sensitivity		0-100 kΩ, not adjustable	
Maximum electrode voltage		30 V AC	
Maximum electrode current		1.5 mA	
Electrode supply line	max. cable capacity	3 nF	
	max. cable length	30 m	
Timing circuit			
Tripping delay		fixed approx. 200 ms	
Indication of operational states			
Output relay energized		R: yellow LED	
Output circuits		**13-14**	
Kind of output		1 n/o contact	
Operational principle[1)]		open-circuit principle[1)]	closed-circuit principle[1)]
Rated operational voltage U_e	(IEC/EN 60947-1)	250 V	
Minimum switching voltage / minimum switching current		- / -	
Maximum switching voltage		250 V	
Rated operational voltage U_e and rated operational current I_e	AC-12 (resistive) 230 V	4 A	
	AC-15 (inductive) 230 V	3 A	
	DC-12 (resistive) 24 V	4 A	
	DC-13 (inductive) 24 V	2 A	
AC rating (UL 508)	Utilization category (Control Circuit Rating Code)	B 300	
	max. rated operational voltage	300 V AC	
	max. continuous thermal current at B 300	5 A	
	max. making/breaking apparent power at B 300	3600/360 VA	
Mechanical lifetime		30 x 10^6 switching cycles	
Electrical lifetime (AC-12, 230 V, 4 A)		0.3 x 10^6 switching cycles	
Max. fuse rating to achieve short-circuit protection	n/c contact	-	
	n/o contact	10 A fast-acting	
General data			
Duty cycle		100 %	
Dimensions		see dimensional drawings	
Mounting		DIN rail (IEC/EN 60715)	
Mounting position		any	
Degree of protection	enclosure / terminals	IP50 / IP20	
Ambient temperature range	operation / storage	-20...+60 °C / -40...+85 °C	
Electrical connection			
Wire size	fine-strand with wire-end ferrule	2 x 0.75-1.5 mm² (2 x 18-16 AWG)	
	fine-strand without wire-end ferrule	2 x 1-1.5 mm² (2 x 18-16 AWG)	
	rigid	2 x 0.75-1.5 mm² (2 x 18-16 AWG)	
Stripping length		10 mm (0.39 inch)	
Tightening torque		0.6-0.8 Nm	

Liquid level monitoring relays

Technical data

Type			CM-ENE MIN	CM-ENE MAX
Standards / Directives				
Standard			IEC/EN 60947-5-1, EN 50178	
Low Voltage Directive			2014/35/EU	
EMC Directive			2014/35/EU	
RoHS Directive			2011/65/EU	
Electromagnetic compatibility				
Interference immunity to			EN 61000-6-2, EN 61000-6-4	
	Electrostatic discharge	IEC/EN 61000-4-2	level 3 (6 kV / 8 kV)	
	Radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)	
	Electrical fast transient / burst	IEC/EN 61000-4-4	level 3 (2 kV / 5 kHz)	
	Surge	IEC/EN 61000-4-5	level 4 (2 kV L-L)	
	Conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)	
Interference emission				
	high-frequency radiated	IEC/CISPR 22, EN 55022	class B	
	high-frequency conducted	IEC/CISPR 22, EN 55022	class B	
Environmental data				
Ambient temperature ranges		operation/storage	-20..+60 °C / -40...+85 °C	
Damp heat		IEC/EN 60068-2-30	40 °C, 93 % RH, 4 days	
Vibration withstand		IEC/EN 60068-2-6	10-57 Hz: 0.075 mm; 57-150 Hz: 1 g	
Isolation data				
Rat. insulation volt. betw. supply, measuring & output circuit			250 V	
Rated impulse withstand voltage U_{imp} between all isolated circuits			4 kV / 1.2-50 µs	
Pollution category			3	
Overvoltage category			III	

1) Open-circuit principle: Output relay energizes if the measured value exceeds/drops below the adjusted threshold.
Closed-circuit principle: Output relay de-energizes if the measured value exceeds/drops below the adjusted threshold.

Liquid level monitoring relays
Technical data

Type		**CM-ENS.1x**		**CM-ENS.2x**		**CM-ENS.31**	
Supply circuit							
Rated control supply voltage U_S	CM-ENS.11, CM-ENS.21, CM-ENS.31: A1-A2	24-240 V AC/DC					
	CM-ENS.13, CM-ENS.23: A1-A2	220-240 V AC					
	CM-ENS.13, CM-ENS.23: A3-A2	110-130 V AC					
Rated control supply voltage U_S tolerance		-15...+10 %					
Rated frequency		50-60 Hz					
Frequency range		47-63 Hz					
Typical current / power consumption	24 V AC	25 mA / 0.6 W		25 mA / 0.6 W		25 mA / 0.6 W	
	110-130 V AC	20 mA / 2.6 VA		20 mA / 2.6 VA		8 mA / 1.1 VA	
	220-240 V AC	8.5 mA / 2.1 VA		8.5 mA / 2.1 VA		10 mA / 2.4 VA	
	24-240 V AC/DC	11 mA / 2.6 VA		11 mA / 2.6 VA		11 mA / 2.6 VA	
Power failure buffering time	min.	20 ms					
Start-up time t_s	Range 5-100 kΩ	max. 1.3 s		-		-	
	Range 0.1-1 kΩ	-		max. 900 ms			
	Range 1-10 kΩ	-		max. 900 ms			
	Range 10-100 kΩ	-		max. 1.3 s			
	Range 100-1000 kΩ	-		max. 6.3 s			
Measuring circuit		**MAX-MIN-C**					
Sensor type		electrode					
Monitoring function		fill or drain		fill or drain, selectable			
Measuring principle		conductivity measurement					
Number of electrodes		3					
Response sensitivity		adjustable: 5-100 kΩ		adjustable: 0.1-1000 kΩ			
Maximum electrode voltage		6 V AC					
Maximum electrode current		1 mA		2 mA			
		max cable capacity	**max cable length**	**max cable capacity**	**max cable length**	**max cable capacity**	**max cable length**
Electrode supply line	Range 5-100 kΩ	10 nF	100 m	-	-	-	-
	Range 0.1-1 kΩ	-	-	200 nF	1000 m	200 nF	1000 m
	Range 1-10 kΩ	-	-	200 nF	1000 m	200 nF	1000 m
	Range 10-100 kΩ	-	-	20 nF	100 m	20 nF	100 m
	Range 100-1000 kΩ	-	-	4 nF	20 m	4 nF	20 m
Max. measuring cycle	Range 5-100 kΩ	1000 ms		-		-	
	Range 0.1-1 kΩ	-		700 ms			
	Range 1-10 kΩ	-		700 ms			
	Range 10-100 kΩ	-		1.1 s			
	Range 100-1000 kΩ	-		5 s			
Timing circuit							
Time delay		-				0.1-30 s, adjustable, ON- or OFF-delay	
Indication of operational states							
Control supply voltage		U: green LED					
Output relay energized		R: Yellow LED					

Liquid level monitoring relays

Technical data

Type		**CM-ENS.1x**	**CM-ENS.2x**	**CM-ENS.31**
Electrode / alarm status		MAX/MIN: Yellow LED		
Output circuits				
Kind of output	11_{15}-12_{16}/14_{18}	relay, 1 c/o (SPDT) contact		relay, 1st c/o (SPDT) contact
	21_{15}-22_{16}/24_{18}	-		relay, 2nd c/o (SPDT) contact
Operational principle		open-circuit principle	open- or closed-circuit principle (selectable)	
Contact material		AgNi alloy, Cd free		
Minimum switching voltage / minimum switching current		12 V / 10 mA		
Maximum switching voltage / Maximum switching current		see data sheets		
Rated operational voltage U_e and rated operational current I_e (IEC/EN 60947-5-1)	AC-12 (resistive) 230 V	4 A		
	AC-15 (inductive) 230 V	3 A		
	DC-12 (resistive) 24 V	4 A		
	DC-13 (inductive) 24 V	2 A		
AC rating (UL 508)	Utilization category (Control Circuit Rating Code)	B 300, pilot duty general purpose 250 V, 4 A, cos φ 0.75		
	max. rated operational voltage	300 V AC		
	max. continuous thermal current at B 300	5 A		
	max. making/breaking apparent power at B 300	3600/360 VA		
Mechanical lifetime		10 x 10^6 switching cycles		
Electrical lifetime (AC-12, 230 V, 4 A)		0.1 x 10^6 switching cycles		
Max. fuse rating to achieve short-circuit protection	n/c / n/o contact	6 A / 10 A fast-acting		10 A / 10 A fast-acting
Conventional thermal current I_{th}		4 A		

Liquid level monitoring relays

Technical data

Type		CM-ENS.1x	CM-ENS.2x	CM-ENS.31
General data				
MTBF		on request		
Duty cycle		100 %		
Dimensions		see dimensional drawings		
Weight		see ordering details		
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool		
Mounting position		any		
Minimum distance to other units		CM-ENS.x1: not necessary CM-ENS.x3: 10 mm if contact current > 2 A		
Degree of protection	housing / terminals	IP50 / IP20		
Material of housing		UL 94 V-0		
Electrical connection				
		Screw connection technology		**Easy Connect Technology (push-in)**
Wire size	fine-strand with(out) wire end ferrule	1 x 0.5-2.5 mm² (1 x 18-14 AWG) 2 x 0.5-1.5 mm² (2 x 18-16 AWG)		2 x 0.5-1.5 mm² (2 x 18-16 AWG)
	rigid	1 x 0.5-4 mm² (1 x 20-12 AWG) 2 x 0.5-2.5 mm² (2 x 20-14 AWG)		2 x 0.5-1.5 mm² (2 x 20-16 AWG)
Stripping length		8 mm (0.32 in)		
Tightening torque		0.6 - 0.8 Nm (7.08 lb.in)		-
Standards / Directives				
Standard		IEC/EN 60255-27, IEC/EN 60947-5-1		
Low Voltage Directive		2014/35/EU		
RoHS Directive		2014/30/EU		
EMC Directive		2011/65/EU		
Environmental data				
Ambient temperature ranges	operation	-25...+60 °C		
	storage	-40...+85 °C		
Damp heat, cyclic (IEC/EN 60068-2-30)		6 x 24 h cycle, 55 °C, 95 % RH		
Climatic category (IEC/EN 60721-3-3)		3K5 (no condensation, no ice formation)		
Vibration, sinusoidal (IEC/EN 60255-21-1)		class 2		
Shock (IEC/EN 60255-21-2)		class 2		
Isolation data				
Rated impulse withstand voltage U_{imp}	supply circuit / measuring circuit	4 kV		
	supply circuit / output circuits	4 kV		
	measuring circuit / output circuits	4 kV		
	output circuit 1 / output circuit 2	4 kV		
Pollution degree (IEC/EN 60664-1)		3		
Overvoltage category (IEC/EN 60664-1)		III		
Rated insulation voltage U_i	supply circuit / measuring circuit	300 V		
	supply circuit / output circuits	300 V		
	measuring circuit / output circuits	300 V		
	output circuit 1 / output circuit 2	300 V		
Basisc insulation	supply circuit / measuring circuit	250 V AC / 300 V DC		
	supply circuit / output circuits	250 V AC / 300 V DC		
	measuring circuit / output circuits	250 V AC / 300 V DC		
	output circuit 1 / output circuit 2	250 V AC / 300 V DC		


Liquid level monitoring relays

Technical data


Type		CM-ENS.1x	CM-ENS.2x	CM-ENS.31
Protective separation (IEC/EN 61140, EN 50178)	supply circuit / measuring circuit	250 V AC / 300 V DC		
	supply circuit / output circuits	250 V AC / 300 V DC		
	measuring circuit / output circuits	250 V AC / 300 V DC		
Pollution degree		3		
Overvoltage category		III		
Electromagnetic compatibility				
Interference immunity to		EN 61000-6-1, EN60255-26		
electrostatic discharge	IEC/EN 61000-4-2	level 3 (6 kV / 8 kV)		
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)		
electrical fast transient / burst	IEC/EN 61000-4-4	level 3, 2 KV / 5 kHz		
surge	IEC/EN 61000-4-5	level 3, installation class 3, supply circuit and measuring circuit 1 kV L-L, 2 kV L-earth		
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3, 10 V		
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	class 3		
Interference emission		IEC/EN 61000-6-3, IEC/EN 61000-6-4		
high-frequency radiated	IEC/CISPR 22, EN 55022	class B		
high-frequency conducted	IEC/CISPR 22, EN 55022	class B		

Liquid level monitoring relays
Function diagrams


CM-ENS




Drain: CM-ENS.1x, CM-ENS.2x



Fill: CM-ENS.2x




Drain: CM-ENS.31




Fill: CM-ENS.31

CM-ENE MIN



CM-ENE MAX




The liquid level relays CM-ENE MIN and CM-ENE MAX are used to monitor levels of conductive liquids, for example, in pump control systems for dry-running or overflow monitoring.
The measuring principle is based on the occurring resistance change when moistening single-pole electrodes. The single-pole electrodes (see also section Accessories) are connected to the terminals C and MIN or MAX.
If the supply voltage is applied to A1-A2 and the electrodes are wet, the output relay of the CM-ENE MIN is energized and the output relay of the CM-ENE MAX is de-energized. The output relay of the CM-ENE MIN de-energizes if the electrodes are no longer wet. The output relay of the CM-ENE MAX energizes if the electrodes are no longer wet.

Liquid level monitoring relays

Technical diagrams


Connection diagrams

CM-ENS.11x, CM-ENS.21x




A1–A2	Control supply voltage
11–12/14	1 c/o (SPDT) contact
C	Reference electrode
MAX	Maximum level electrode
MIN	Minimum level electrode

CM-ENS.13x, CM-ENS.23x




A1–A2	Control supply voltage 220-240 V AC
A3-A2	Control supply voltage 110-130 V AC
11–12/14	1 c/o (SPDT) contact
C	Reference electrode
MAX	Maximum level electrode
MIN	Minimum level electrode

CM-ENS.31x




A1–A2	Control supply voltage
11_{15}–12_{16}/14_{18}	1 c/o (SPDT) contact
21_{25}-22_{26}/24_{28}	2nd c/o (SPDT) contact
C	Reference electrode
MAX	Maximum level electrode
MIN	Minimum level electrode

CM-ENE MIN



A1-A2	Rated control supply voltage
C	Reference electrode
MIN	Minimum level
13-14	Output contact -open-circuit principle


CM-ENE MAX



A1-A2	Rated control supply voltage
C	Reference electrode
MIN	Maximum level
13-14	Output contact -open-circuit principle


Liquid level monitoring relays
Technical diagrams

CM-ENS.1x




Liquid level control - drain

CM-ENS.2x, CM-ENS.31x



Liquid level control - fill - selected function "↑" (UP)

CM-ENS.2x, CM-ENS.31x




Liquid level control - drain - selected function "↓" (Down)

Liquid level monitoring relays
Technical diagrams


Load limit curves

CM-S (22.5 mm), CM-E (22.5 mm)


AC load (resistive)




DC load (resistive)



Derating factor F for inductive AC load




Contact lifetime



Dimensional drawing

Dimension in mm and inches



CM-xxS
1SVR730xxxxxx, 1SVR740xxxxxx



Accessories
Table of contents

242 **Ordering details**

244 **Technical diagrams**

245 **Technical diagrams**

Accessories
Ordering details



Bar electrode



Suspension electrode

Ordering details

Accessories

Description	For type	Width in mm	for devices	Type	Order code	Pkg qty	Weight (1 pc) g (oz)
Adapter for screw mounting	CM-S CM-S.S/P	22.5		ADP.01	1SVR430029R0100	1	18.4 (0.65)
	CM-N CM-N.S/P	45		ADP.02	1SVR440029R0100	1	36.7 (1.30)
Marker label	CM-S, CM-N CM-S.S/P CM-N.S/P		without DIP switches	MAR.01	1SVR366017R0100	10	0.19 (0.007)
	CM-S, CM-N		with DIP switches	MAR.02	1SVR430043R0000	10	0.13 (0.005)
	CM-S.S/P CM-N.S/P		with DIP switches	MAR.12	1SVR730006R0000	10	0.152 (0.335)
Sealable transparent cover	CM-S	22.5		COV.01	1SVR430005R0100	1	5.2 (0.18)
	CM-N	45		COV.02	1SVR440005R0100	1	7.7 (0.27)
	CM-S.S/P	22.5		COV.11	1SVR730005R0100	1	4.0 (0.129)
	CM-N.S/P	45		COV.12	1SVR750005R0100	1	7 (0.247)

Bar electrodes

Description	Material no.	Type	Order code	Weight (1 pc) kg (lb)
Compact support for 3 bar electrodes	-	CM-KH-3	1SVR450056R6000	0.06 (0.132)
Distance plate for 3 bar electrodes		CM-AH-3	1SVR450056R7000	0.06 (0.132)
Counter nut for 1" thread		CM-GM-1	1SVR450056R8000	0.06 (0.132)
Length: 300 mm	1.4301	CM-SE-300	1SVR450056R0000	0.08 (0.176)
Length: 600 mm	1.4301	CM-SE-600	1SVR450056R0100	0.08 (0.176)
Length: 1000 mm	1.4301	CM-SE-1000	1SVR450056R0200	0.08 (0.176)

Suspension electrodes

Description	Connec-tion	Material no.	Type	Order code	Weight (1 pc) kg (lb)
CM-HE suspension electrode high-alloy steel, material no. 1.4104 (according to EN 10088-1)	Screw	1.4104	CM-HE	1SVR402902R0000	0.074 (0.163)
CM-HC suspension electrode high-alloy steel, material no. 1.4104 (according to EN 10088-1)	Crimp	1.4104	CM-HC	1SVR402902R1000	0.09 (0.198)
CM-HCT suspension electrode suitable for drink water high-alloy steel, material no. 1.4301 (according to EN 10088-1)	Crimp	1.4301	CM-HCT	1SVR402902R2000	0.09 (0.198)

Accessories

Ordering details



CM-CT



CM-CT
with mounted accessories



CM-CT-A
mounted on DIN rail

Plug-in current transformers CM-CT

- Without primary conductor though with foot angle, insulating protective cap and bar fastening screws
- Primary / rated current from 50 A to 600 A
- Secondary current of 1 A or 5 A
- Class 1

Ordering details

Rated primary current	Secondary current	Burden class	Type	Order code	Weight (1 pc) g (oz)
50 A	1 A	1 VA / 1	CM-CT 50/1	1SVR450116R1000	0.31 (0.683)
75 A		1.5 VA / 1	CM-CT 75/1	1SVR450116R1100	0.31 (0.683)
100 A		2.5 VA / 1	CM-CT 100/1	1SVR450116R1200	0.276 (0.608)
150 A		2.5 VA / 1	CM-CT 150/1	1SVR450116R1300	0.32 (0.705)
200 A		2.5 VA / 1	CM-CT 200/1	1SVR450116R1400	0.222 (0.489)
300 A		5 VA / 1	CM-CT 300/1	1SVR450117R1100	0.29 (0.639)
400 A		5 VA / 1	CM-CT 400/1	1SVR450117R1200	0.27 (0.595)
500 A		5 VA / 1	CM-CT 500/1	1SVR450117R1300	0.29 (0.639)
600 A		5 VA / 1	CM-CT 600/1	1SVR450117R1400	0.24 (0.529)
50 A	5 A	1 VA / 1	CM-CT 50/5	1SVR450116R5000	0.3 (0.661)
75 A		1.5 VA / 1	CM-CT 75/5	1SVR450116R5100	0.31 (0.683)
100 A		2.5 VA / 1	CM-CT 100/5	1SVR450116R5200	0.31 (0.683)
150 A		2.5 VA / 1	CM-CT 150/5	1SVR450116R5300	0.28 (0.617)
200 A		5 VA / 1	CM-CT 200/5	1SVR450116R5400	0.29 (0.639)
300 A		5 VA / 1	CM-CT 300/5	1SVR450117R5100	0.252 (0.556)
400 A		5 VA / 1	CM-CT 400/5	1SVR450117R5200	0.26 (0.573)
500 A		5 VA / 1	CM-CT 500/5	1SVR450117R5300	0.208 (0.459)
600 A		5 VA / 1	CM-CT 600/5	1SVR450117R5400	0.21 (0.463)

Accessories


Description	Type	Order code	Weight (1 pc) g (oz)
Snap-on fastener for DIN rail mounting of CM-CT	CM-CT A	1SVR450118R1000	0.009 (0.02)

Accessories

Technical diagrams


Operating principle / circuit diagram

CM-CT




Dimensional drawings


in **mm** and inches



Sealable cover
COV.11



Sealable cover
COV:12




MAR.01

Accessories

Technical diagrams


Dimensional drawings

in **mm** and inches




a	10,5 mm	0.41 inch
b	12,5 mm	0.49 inch
c	20,5 mm	0.81 inch
d	25,5 mm	1.00 inch
e	30,5 mm	1.20 inch

CM-CT



ADP.01



ADP.02


CP-D 12/0.83
CP-D 12/2.1
CP-E 5/3.0
CP-E 12/2.5
CP-E 24/0.75
CP-C.1 24/5.0
CP-C.1 24/10.0
CP-C.1 24/20.0
CP-T 24/10.0
INPUT 3x400-500 VAC

Power supplies
Table of contents

248	**Overview**
250	**Selection table**
253	**Power supplies for industrial applications**
255	CP-E range
275	CP-T range
289	CP-C.1 range
313	**Power supplies for building applications**
314	CP-D range
327	**CP-B range buffer modules**
339	**Redundancy units**
349	**Electronic protection devices EPD24**

Primary switch mode power supplies
Overview

Modern power supply units are a vital component in energy management and automation technology. As your global partner in these areas, ABB pays the utmost attention to the resulting requirements. Innovation is the key to ABB's power supply product program.

Power supplies for industrial applications



CP-E range: economy range
The CP-E range offers enhanced functionality while the number of different types has been considerably reduced. Now all power supply units can be operated at an ambient temperature of up to +70 °C. The CP-E range 24 V devices over 18 W offer an output/contact for monitoring of the output voltage and remote diagnosis. Optimized for worldwide applications, the CP-E power supplies can be supplied within a wide range of AC or DC voltages. The output voltage is continuously adjustable, ensuring optimal adaptation to the application, e.g. compensating the voltage drop caused by a long line length. For decoupling of parallel connected power supplies below or equal to 56 V, redundancy modules are available in order to achieve true redundancy.



CP-T range: three-phase range
The CP-T range of three-phase power supply units perfectly complements ABB's existing power supply offering in terms of design and functionality, giving you more advanced options for your three-phase applications. Solid state output for function monitoring and remote diagnostics is available. The range is to be used in 340 - 575 V AC or 480 - 820 V DC supply systems. Its continuously adjustable output voltage ensures optimal adaptation to the application, e.g. compensating the voltage drop caused by a long line length.



CP-C.1 range: high-performance range
The CP-C.1 power supplies are ABB's high-performance and most advanced range. With excellent efficiency, high reliability and innovative functionality, the CP-C.1 range is ready to take on the most demanding industrial applications. These power supplies have a 150 % integrated power reserve and operate at an efficiency of up to 94 %. They are equipped with overheat protection and active power factor correction. Combined with a broad AC and DC input range and extensive worldwide approvals, the CP-C.1 power supplies are the preferred choice for professional DC applications. Giving the power to control.

Primary switch mode power supplies
Overview

Power supplies for industrial applications



CP-B range: short time buffers
ABB offers an innovative and completely maintenance- free product range for buffering the 24 V DC supply in case of interrupted mains on the primary side of the switch mode power supply.

- Ultra cap based buffer modules for short time UPS systems
- Rated input voltage 24 V DC
- Rated currents 3 A, 10 A and 20 A
- Expandable with CP-B EXT.2 module
- LEDs for status indication
- Higher than 90% efficiency
- Signaling and status outputs
- Buffering times at 100 % load current from 13 s to 38 s (depending on device)

Power supplies for building applications



CP-D range: distribution panel design
The CP-D range of power supply units in MDRC design (modular DIN rail components) fits into all domestic installation and distribution panels. With their width of only 18 to 90 mm, the CP-D range switch mode power supplies are ideally suited for installation in distribution panels. The range is optimized for worldwide applications: The CP-D power supplies can be supplied with 90-264 V AC or 120-375 V DC. The continuously adjustable output voltage (CP-D > 10 W) ensures optimal adaption to the application, e.g. compensating the voltage drop caused by a long line length. An additional redundancy unit CP-RUD to establish true redundancy is available.

For certifications and approvals, please refer to the download section on the product web pages.

Primary switch mode power supplies
Selection table - Single-phase

		Order number	1SVR427041R1000	1SVR427043R1200	1SVR427041R0000	1SVR427043R0100	1SVR427044R0200	1SVR427045R0400	1SVR427033R3000	1SVR427032R1000	1SVR427035R1000	1SVR427030R0000	1SVR427031R0000	1SVR427032R0000	1SVR427034R0000	1SVR427035R0000	1SVR427036R0000	1SVR427030R2000	1SVR427031R2000	1SVR427034R0000	1SVR427035R2000	1SVR360563R1001	1SVR360663R1001	1SVR360763R1001	1SVR360563R2001	1SVR360663R2001	1SVR360763R2001	1SVR361563R1001	1SVR361663R1001	1SVR361763R1001
			Single-phase																										
			CP-D						CP-E													CP-C.1								
Rated output voltage	5 V DC								■																				
	12 V DC		■	■						■	■																			
	24 V DC				■	■	■	■				■	■	■	■	■	■					■	■	■	■	■	■	■	■	■
	48 V DC																	■	■	■	■									
Rated output current	0.42 A				■																									
	0.625 A																	■												
	0.75 A											■																		
	0.83 A	■																												
	1.25 A												■						■											
	1.3 A				■																									
	2.1 A		■																											
	2.5 A					■				■				■																
	3 A								■																					
	4.2 A						■																							
	5 A														■					■		■			■			■		
	10 A										■					■							■			■			■	
	20 A																■							■			■			■
Rated output power	10 W		■		■																									
	15 W								■																					
	18 W											■																		
	25 W		■																											
	30 W					■				■			■					■												
	60 W						■							■					■											
	100 W							■																						
	120 W										■				■							■			■			■		
	240 W															■					■					■			■	
	480 W																■				■			■			■			■
Rated input voltage	100-240 V AC		■	■	■	■	■	■	■	■		■	■	■				■	■			■	■	■	■	■	■	■	■	■
	115/230 V AC auto select										■				■	■					■									
	115-230 V AC																■				■									
DC input voltage range	90-300 V DC																					■	■	■	■	■	■	■	■	■
	90-375 V DC									■			■	■				■	■											
	120-375 V DC		■	■	■	■	■	■	■			■					■				■									
	210-375 V DC										■				■	■				■										
Features	Power reserve design																					■	■	■	■	■	■	■	■	■
	Adjustable output voltage		■		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	Integrated input fuse	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	Short-circuit stable	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	Fold-forward behavior (U/I)		■		■	■	■		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
	Fold-back behavior (hiccup)	■		■				■			■																			
	Power factor correction										pas				pas	pas	act			pas	act	act	act	act	act	act	act	act	act	act
	Signalling contact												■	■	■	■	■					■	■	■	■	■	■	■	■	■
	Extended temp. range	■	■	■	■	■	■		■	■		■	■	■	■	■	■	■	■	■				■	■	■				
	Parallel connection							■	■	3	■	■	■	3	3	3	■	■	3	3	5	5	5	5	5	5	5	5	5	5
	Serial connection	■	■	■	■	■	■	■	■	2	■	■	■	2	2	2	■	■	2	2	2	2	2	2	2	2	2	2	2	2
	Coated PCBA																								■	■	■			

pas = passive, act = active

Primary switch mode power supplies
Selection table - Three-phase

		Order number	1SVR427054R0000	1SVR427055R0000	1SVR427056R0000	1SVR427057R0000	1SVR427054R2000	1SVR427055R2000	1SVR427056R2000
			Three-phase						
			CP-T						
Rated output voltage		24 V DC	■	■	■	■			
		48 V DC					■	■	■
Rated output current		5 A	■				■		
		10 A		■				■	
		20 A			■				■
		40 A				■			
Rated output power		120 W	■						
		240 W		■			■		
		480 W			■			■	
		960 W				■			■
Rated input voltage		3 x 400-500 V AC	■	■	■	■	■	■	■
DC input voltage range		480-820 V DC	■	■	■	■	■	■	■
Features	Adjustable output voltage		■	■	■	■	■	■	■
	Integrated input fuse		■	■	■	■	■	■	■
	Short-circuit stable		■	■	■	■	■	■	■
	Fold forward behavior (U/I)		■	■	■		■	■	
	Fold back behavior (hiccup)		■	■	■	■	■	■	■
	Extended temp. range		■	■	■	■	■	■	■
	Signalling contact		■	■	■	■			
	Parallel connection			2	2	2	2	2	2
	Serial connection			2	2	2	2	2	2







Power supplies for industrial applications
Table of contents

255	CP-E range
275	CP-T range
289	CP-C.1 range


CP-E 24/20.0
CP-E 24/10.0
CP-E 24/5.0
CP-E 12/2.5
CP-E 24/0.75
CP-E 5/3.0
CP-E 45/1.25

CP-E range
Table of contents

256 Benefits and advantages

258 Operating controls

259 Applications

260 Ordering details

261 Technical data

271 Technical diagrams

CP-E range
Benefits and advantages



ABB's CP-E range offers enhanced functionality and a simpler, more rational selection process. All power supply units can be operated at an ambient temperature of up to +70 °C (158 °F).

Affordable range

Products with exactly the functions you require.
Designed for best possible price-performance ratio.

Global availability

The product can be used in any installations in the world. Giving you the confidence of worldwide sourcing – no matter where you build, install or operate your equipment.

Speed up your projects

Data available for common planning software: Less engineering time required.

CP-E range
Benefits and advantages

Characteristics
- Output voltages 5 V, 12 V, 24 V, 48 V DC
- Adjustable output voltages
- Output currents 0.625 A / 0.75 A / 1.25 A / 2.5 A / 3 A / 5 A / 10 A / 20 A
- Power range 15 W, 18 W, 30 W, 60 W, 120 W, 240 W, 480 W
- High efficiency, up to 90 %
- Low power dissipation and low heating
- Free convection cooling (no forced cooling with ventilators)
- Open-circuit, overload and short-circuit stable
- Integrated input fuse
- U/I characteristic curve on devices > 18 W (fold-forward behavior at overload – no switch-off)
- Redundancy units offering true redundancy
- LED(s) for status indication
- Signalling output/contact for output voltage OK
  - Transistor on 24 V devices > 18 W and < 120 W
  - Solid-state on 24 V devices ≥ 120 W
- Various approvals and marks

Main benefits


Signalling output / contact
The CP-E range 24 V devices > 18 W offer an output/contact for monitoring of the output voltage and remote diagnosis.

Wide range input
Optimized for worldwide applications: The CP-E power supplies can be supplied with a wide range of AC or DC voltages.

Adjustable output voltage
A continuously adjustable output voltage ensures optimal adaptation to the application, e.g. compensating the voltage drop caused by a long line length.

Redundancy units
For decoupling of parallelized power supply units ≤ 40 A. Thus, true redundancy can be achieved.









CP-E range
Operating controls

OUTPUT Adjust:
Potentiometer - adjustment of output voltage


Single/parallel:
Sliding switch - adjustment of single or parallel operation

OUTPUT
L+, L+, L-, L-:
Terminals - output 5 V / 12 V / 24 V / 48 V

13-14:
Terminals - signalling contact (or solid-state)

Circuit diagram

Indication of operational states:
OUTPUT OK:
green LED - output voltage OK
OUTPUT LOW:
red LED - output voltage too low



INPUT L, N, PE:
terminals - input
90-132 V AC, 180-265 V AC / 210-375 V DC
90-264 V AC / 120-375 V DC
85-264 V AC / 90-375 V DC

CP-E range
Applications

Tooling machines

Packaging industry

Food industry

Textile industry

Printing industry

Electro-mobility













CP-E range
Ordering details



2CDC 271 017 F0006

CP-E 5/0.75



2CDC 271 013 F0006

CP-E 12/2.5



2CDC 271 028 F0008

CP-E 48/5.0



2CDC 271 027 F0008

CP-E 24/20.0

Description

This range offers types with output voltages from 5 V DC to 48 V DC at output currents of 0.625 A to 20 A. With their high thermal efficiency of up to 90 %, these power supplies have very low power and heat dissipation and can be operated without forced cooling. The functionality has been enhanced while the number of different types has been considerably reduced.
Of course, all power supplies of the CP-E range are approved in accordance with all relevant international standards.

Ordering details - CP-E < 100 W

Input voltage range	Rated output voltage / current	Type	Order code	Weight (1 pc.) kg (lb)
90-264 V AC / 120-375 V DC	5 V DC / 3 A	CP-E 5/3.0	1SVR427033R3000	0.15 (0.33)
85-264 V AC / 90-375 V DC	12 V DC / 2.5 A	CP-E 12/2.5	1SVR427032R1000	0.29 (0.64)
90-132 V AC, 180-264 V AC / 210-375 V DC	12 V DC / 10 A	CP-E 12/10.0	1SVR427035R1000	1.00 (2.20)
90-264 V AC / 120-375 V DC	24 V DC / 0.75 A	CP-E 24/0.75	1SVR427030R0000	0.15 (0.33)
85-264 V AC / 90-375 V DC	24 V DC / 1.25 A	CP-E 24/1.25	1SVR427031R0000	0.29 (0.64)
85-264 V AC / 90-375 V DC	24 V DC / 2.5 A	CP-E 24/2.5	1SVR427032R0000	0.36 (0.79)

Ordering details - CP-E ≥ 120 W

Input voltage range	Rated output voltage / current	Type	Order code	Weight (1 pc.) kg (lb)
90-132 V AC, 180-264 V AC / 210-375 V DC	24 V DC / 5 A	CP-E 24/5.0	1SVR427034R0000	1.00 (2.20)
90-132 V AC, 180-264 V AC / 210-375 V DC	24 V DC / 10 A	CP-E 24/10.0	1SVR427035R0000	1.36 (3.01)
90-264 V AC / 120-375 V DC	24 V DC / 20 A	CP-E 24/20.0	1SVR427036R0000	1.90 (4.18)
85-264 V AC / 90-375 V DC	48 V DC / 0.625 A	CP-E 48/0.62	1SVR427030R2000	0.29 (0.64)
85-264 V AC / 90-375 V DC	48 V DC / 1.25 A	CP-E 48/1.25	1SVR427031R2000	0.36 (0.79)
90-132 V AC, 180-264 V AC / 210-375 V DC	48 V DC / 5 A	CP-E 48/5.0	1SVR427034R2000	1.36 (3.01)
90-264 V AC / 120-375 V DC	48 V DC / 10 A	CP-E 48/10.0	1SVR427035R2000	1.90 (4.19)

CP-E range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-E 5/3.0	CP-E 12/2.5	CP-E 12/10.0
Input circuit		**L, N**		
Rated input voltage U_{in}		100-240 V AC		115 / 230 V AC auto select
Input voltage range		90-264 V AC / 120-375 V DC	85-264 V AC / 90-375 V DC	90-132 V AC, 180-264 V AC / 210-375 V DC
Frequency range AC		47-63 Hz		
Typical input current	at 115 V AC	335 mA	560 mA	2.2 A
	at 230 V AC	210 mA	330 mA	0.83 A
Typical power consumption		19.8 W	35.9 W	143 W
Inrush current	at 115 V AC	15 A	20 A	24 A
	at 230 V AC	30 A	40 A	48 A
Discharge current	input / output	0.25 mA		
	input / PE	3.5 mA		
Power failure buffering time	at 115 V AC	min. 20 ms	min. 20 ms	min. 25 ms
	at 230 V AC	min. 75 ms	min. 30 ms	min. 30 ms
Internal input fuse		2 A slow-acting / 250 V AC		3.15 A slow-acting / 250 V AC
Power factor correction (PFC)		no		yes, passive, 0.7
Indication of operational states				
Output voltage	green LED	OK: ⎍: output voltage OK	OUTPUT OK: ⎍: output voltage OK	OUTPUT OK: ⎍: output voltage OK
	red LED	LOW: ⎍: output voltage too low	-	OUTPUT LOW: ⎍: output voltage too low
Output circuit		**L+,L-**	**L+, L+, L-, L-**	
Rated output voltage		5 V DC	12 V DC	
Tolerance of the output voltage		0...+1 %		
Adjustment range of the output voltage		4.5-5.75 V DC	12-14 V DC	11.4-14.5 V DC
Rated output power		15 W	30 W	120 W
Rated output current I_r	$T_a \leq 60$ °C	3.0 A	2.5 A	10 A
Derating of the output current	60 °C < $T_a \leq$ 70 °C	2.5 %/°C	2.5 %/°C	
Maximum deviation with	load change statical	±2 %	±0.5 %	±1 % (single mode) ±5 % (parallel mode)
	change of output voltage within the input voltage range	±1 %	±0.5 %	±0.5 %
Recovery time T_R		< 2 ms		
Starting time after applying the supply voltage	at I_r	max. 1 s		
	with 3500 µF	-	max. 2 s	-
	with 7000 µF	max. 1.5 s	-	max. 1.5 s
Rise time	at rated load	max. 150 ms		
	with 3500 µF	-	max. 500 ms	-
	with 7000 µF	max. 500 ms	-	max. 500 ms
Fall time		max. 150 ms		
Residual ripple and switching peaks	BW = 20 MHz	50 mV		
Parallel connection		yes, to enable redundancy		configurable, to increase power, up to 3 devices, min. 0.1 I_r - max. 0.9 I_r
Series connection		yes, to increase voltage		yes, to increase voltage, max. 2 devices
Resistance to reverse feed		1 s - max. 7.5 V DC	1 s - max.18 V DC	max. 18 V DC
Output circuit - No-load, overload and short-circuit behavior				
Characteristic curve of output		hiccup-mode	U/I characteristic curve	
Short-circuit protection		continuous short-circuit proof		
Short-circuit behavior		Hiccup-mode	continuation with output power limiting	
Overload protection		output power limiting		
No-load protection		continuous no-load stability		
Starting of capacitive loads		7000 µF	3500 µF	7000 µF

CP-E range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-E 5/3.0	CP-E 12/2.5	CP-E 12/10.0
General data				
Power loss		typ. 5 W	typ. 5.6 W	typ. 24 W
Efficiency		typ. 75 %	typ. 84 %	typ. 84 %
Duty cycle		100 %		
Dimensions		see “Dimensional drawings”		
Material of housing		plastic		metal
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool		
Mounting position		horizontal		
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)		
Degree of protection	housing / terminals	IP20 / IP20		
Protection class		I		
Electrical connection - input circuit / output circuit				
Connecting capacity	fine-strand with wire end ferrule	0.2-2.5 mm2 (24-14 AWG)		0.2-4 mm² (24-11 AWG)
	fine-strand without wire end ferrule			0.2-6 mm² (24-10 AWG)
	rigid			
Stripping length		6 mm (0.24 in)		8 mm (0.31 in)
Tightening torque	input / output	0.6 Nm (5 lb.in)		1.0 Nm (9 lb.in) / 0.62 Nm (5.5 lb.in)
Environmental data				
Ambient temperature range	operation	-20…+70 °C	-40…+70 °C	-35…+70 °C
	rated load	-20...+60 °C	-40...+60 °C	-35...+60 °C
	storage	-20…+85 °C	-40…+85 °C	-40…+85 °C
Damp heat (cyclic) (IEC/EN 60068-2-30)		95 RH, % without condensation		
Vibration (sinusoidal) (IEC/EN 60068-2-6)		10-500 Hz, 2 G, along X, Y, Z each axis, 60 min. for each axis		
Shock (half-sine) (IEC/EN 60068-2-27)		15 G, 11 ms, 3 axes, 6 faces, 3 times for each face		
Isolation data				
Rated insulation voltage U_i	input circuit / output circuit	3 kV AC		
	input / PE	1.5 kV AC		
	output / PE	0.5 kV AC; 0.71 kV DC		
Pollution degree		2		
Overvoltage category		II		
Standards / Directives				
Standards		IEC/EN 60950-1		
Low Voltage Directive		2014/35/EU		
EMC Directive		2014/30/EU		
RoHS Directive		2011/65/EU		
Protective low voltage		SELV (IEC/EN 60950-1)		
Electromagnetic compatibility				
Interference immunity to		IEC/EN 61000-6-2		
electrostatic discharge	IEC/EN 61000-4-2	level 4 (air discharge 15 kV / contact discharge 8 kV)		
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)		
electrical fast transient/burst	IEC/EN 61000-4-4	level 4 (4 kV / 2,5 kHz)	level 4 (4 kV / 5 kHz)	
surge	IEC/EN 61000-4-5	L-L level 3 (2 kV) / L-PE level 4 (4 kV)		
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)		
power frequency magnetic fields	IEC/EN 61000-4-8	level 4 (30 A/m)		
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	dip: >95 % 10 ms / >30 % 500 ms interruptions: >95 % 5000 ms		
Interference emission		IEC/EN 61000-6-3		
high-frequency radiated		class B		
high-frequency conducted		class B		
limits for harmonic current emissions	IEC/EN 61000-3-2	class D	class A	class D

CP-E range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-E 24/0.75	CP-E 24/1.25	CP-E 24/2.5
Input circuit		**L, N**		
Rated input voltage U_{in}		100-240 V AC		
Input voltage range		90-264 V AC / 120-375 V DC	85-264 V AC / 90-375 V DC	
Frequency range AC		47-63 Hz		
Typical input current	at 115 V AC	335 mA	560 mA	1060 mA
	at 230 V AC	210 mA	330 mA	590 mA
Typical power consumption		22.8 W	36.7 W	69.2 W
Inrush current	at 115 V AC	15 A	20 A (max. 3 ms)	30 A
	at 230 V AC	30 A	40 A (max. 3 ms)	60 A
Discharge current	input / output	0.25 mA		
	input / PE	3.5 mA		
Power failure buffering time	at 115 V AC	min. 20 ms	min. 20 ms	
	at 230 V AC	min. 75 ms	min. 30 ms	
Internal input fuse		2 A slow-acting / 250 V AC		
Power factor correction (PFC)		no		
Indication of operational states				
Output voltage	green LED	OK: ⎍: output voltage OK	OUTPUT OK: ⎍: output voltage OK	
	red LED	LOW: ⎍: output voltage too low	-	-
Output circuit		**L+,L-**	**L+, L+, L-, L-**	
Rated output voltage		24 V DC		
Tolerance of the output voltage		0 ... +1 %		
Adjustment range of the output voltage		21.6-28.8 V DC	24-28 V DC	
Rated output power		18 W	30 W	60 W
Rated output current I_r	$T_a \leq 60$ °C	0.75 A	1.25 A	2.5 A
Derating of the output current	60 °C < $T_a \leq$ 70 °C	2.5 %/°C		
Signalling output for output voltage OK	DC OK	-	transistor	
Maximum deviation with	load change statical	±2 %	±0.5 %	
	change of output voltage within the input voltage range	±1 %	±0.5 %	
Recovery time T_A		< 2 ms		
Starting time after applying the supply voltage	at I_r	max. 1 s		
	with 3500 µF	-	max. 2 s	-
	with 7000 µF	max. 1.5 s	-	max. 1.5 s
Rise time	at rated load	max. 150 ms		
	with 3500 µF	-	max. 500 ms	-
	with 7000 µF	max. 500 ms	-	max. 500 ms
Fall time		max. 150 ms		
Residual ripple and switching peaks	BW = 20 MHz	50 mV		
Parallel connection		yes, to enable redundancy		
Series connection		yes, to increase voltage		
Resistance to reverse feed		1 s - max. 35 V DC		
Output circuit - No-load, overload and short-circuit behavior				
Characteristic curve of output		hiccup-mode	U/I characteristic curve	
Short-circuit protection		continuous short-circuit proof		
Short-circuit behavior		hiccup-mode	continuation with output power limiting	
Overload protection		output power limiting		
No-load protection		continuous no-load stability		
Starting of capacitive loads		7000 µF	3500 µF	7000 µF

CP-E range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-E 24/0.75	CP-E 24/1.25	CP-E 24/2.5
General data				
Power loss		typ. 4.45 W	typ. 5.5 W	typ. 8.8 W
Efficiency		typ. 77 %	typ. 86 %	typ. 89 %
Duty cycle		100 %		
Dimensions		see “Dimensional drawings”		
Material of housing		plastic		
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool		
Mounting position		horizontal		
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)		
Degree of protection	housing / terminals	IP20 / IP20		
Protection class		I		
Electrical connection - input circuit / output circuit				
Connecting capacity	fine-strand with wire end ferrule	0.2-2.5 mm² (24-14 AWG)		
	fine-strand without wire end ferrule			
	rigid			
Stripping length		6 mm (0.24 in)		
Tightening torque	input / output	0.6 Nm (5 lb.in)		
Environmental data				
Ambient temperature range	operation	-20…+70 °C	-40…+70 °C	
	rated load	-20…+60 °C	-40…+60 °C	
	storage	-20…+85 °C	-40…+85 °C	
Damp heat (cyclic) (IEC/EN 60068-2-30)		95 % RH, without condensation		
Vibration (sinusoidal) (IEC/EN 60068-2-6)		10-500 Hz, 2 G, along X, Y, Z each axis, 60 min. for each axis		
Shock (half-sine) (IEC/EN 60068-2-27)		15 G, 11 ms, 3 axes, 6 faces, 3 times for each face		
Isolation data				
Rated insulation voltage U_i	input circuit / output circuit	3 kV AC		
	input / PE	1.5 kV AC		
	output / PE	0.5 kV AC; 0.71 kV DC		
Pollution degree		2		
Overvoltage category		II		
Standards / Directives				
Standards		IEC/EN 60950-1		
Low Voltage Directive		2014/35/EU		
EMC Directive		2014/30/EU		
RoHS Directive		2011/65/EU		
Protective low voltage		SELV (IEC/EN 60950-1)		
Electromagnetic compatibility				
Interference immunity to		IEC/EN 61000-6-2		
electrostatic discharge	IEC/EN 61000-4-2	level 4 (air discharge 15 kV / contact discharge 8 kV)		
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)		
electrical fast transient/burst	IEC/EN 61000-4-4	level 4 (4 kV / 2.5 kHz)	level 4 (4 kV / 5 kHz)	
surge	IEC/EN 61000-4-5	L-L level 3 (2 kV) / L-PE level 4 (4 kV)		
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)		
power frequency magnetic fields	IEC/EN 61000-4-8	level 4 (30 A/m)		
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	dip: >95 % 10 ms / >30 % 500 ms, interruptions: >95 % 5000 ms		
Interference emission		IEC/EN 61000-6-3		
high-frequency radiated		class B		
high-frequency conducted		class B		
limits for harmonic current emissions	IEC/EN 61000-3-2	class D	class A	

CP-E range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-E 24/5.0	CP-E 24/10.0	CP-E 24/20.0
Input circuit		**L, N**		
Rated input voltage U_{in}		115 / 230 V AC auto select		115-230 V AC
Input voltage range		90-132 V AC, 180-264 V AC / 210-375 V DC	90-132 V AC, 180-264 V AC / 210-375 V DC	90-264 V AC, 120-375 V DC
Frequency range AC		47-63 Hz		
Typical input current	at 115 V AC	2.2 A	4.0 A	4.9 A
	at 230 V AC	0.83 A	1.55 A	2.5 A
Typical power consumption		140 W	270 W	539 W
Inrush current	at 115 V AC	24 A (max. 5 ms)	30 A (max. 5 ms)	25 A (max. 5 ms)
	at 230 V AC	48 A (max. 5 ms)	60 A (max. 5 ms)	50 A (max. 5 ms)
Discharge current	input / output	0.25 mA		
	input / PE	3.5 mA		
Power failure buffering time	at 115 V AC	min. 25 ms		
	at 230 V AC	min. 30 ms		
Internal input fuse		3.15 A slow-acting / 250 V AC	6.3 A slow-acting / 250 V AC	10 A slow-acting / 250 V AC
Power factor correction (PFC)		yes, passive, 0.7	yes, passive, 0.75	yes, active 115 V AC: 0.99 230 V AC: 0.97
Indication of operational states				
Output voltage	green LED	OUTPUT OK: ⎍: output voltage OK		
	red LED	OUTPUT LOW: ⎍: output voltage too low		
Output circuit		**L+, L+, L-, L-**		
Rated output voltage		24 V DC		
Tolerance of the output voltage		0...+1 %		
Adjustment range of the output voltage		22.5-28.5 V DC		
Rated output power		120 W	240 W	480 W
Rated output current I_r	$T_a \leq 60$ °C	5 A	10 A	-
	$T_a \leq 55$ °C	-	-	20 A
Derating of the output current	60 °C < $T_a \leq 70$ °C	2.5 %/°C		-
	55 °C < $T_a \leq 70$ °C	-	-	2.5 %/°C
Signalling contact for output voltage OK	13-14	solid-state (max. 60 V DC, 0.3 A)		
Minimum fuse rating to achieve short-circuit protection	13-14	≥ 60 V DC, ≤ 0.3 A fast-acting		
Maximum deviation with	load change statical	±1 % (single mode), ±5 % (parallel mode)		
	change of output voltage within the input voltage range	±0.5 %		
Recovery time T_R		< 2 ms		
Starting time after applying the supply voltage	at I_r	max. 1 s	2.5 s (at -40 °C / 90 V AC starting time >2.5 s has to be expected)	max. 1 s
	with 3500 µF	max. 1.5 s	-	-
	with 7000 µF	-	2.5 s	max. 1.5 s
Rise time	at rated load	max. 150 ms		
	with 3500 µF	max. 500 ms	-	-
	with 7000 µF	-	max. 500 ms	
Fall time		max. 150 ms		
Residual ripple and switching peaks	BW = 20 MHz	50 mV	100 mV	
Parallel connection		configurable, to increase power, up to 3 devices, min. 0.1 I_r - max. 0.9 I_r		
Series connection		yes, to increase voltage, max. 2 devices		
Resistance to reverse feed		max. 35 V DC		

CP-E range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-E 24/5.0	CP-E 24/10.0	CP-E 24/20.0
Output circuit - No-load, overload and short-circuit behavior				
Characteristic curve of output		U/I characteristic curve		
Short-circuit protection		continuous short-circuit proof		
Short-circuit behavior		continuation with output power limiting		
Overload protection		output power limiting		
No-load protection		continuous no-load stability		
Starting of capacitive loads		3500 µF	7000 µF	
General data				
Power loss		typ. 20 W	typ. 35 W	typ. 63 W
Efficiency		typ. 86 %	typ. 89 %	typ. 89 %
Duty cycle		100 %		
Dimensions		see “Dimensional drawings”		
Material of housing		metal		
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool		
Mounting position		horizontal		
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)		
Degree of protection	housing / terminals	IP20 / IP20		
Protection class		I		
Electrical connection - input circuit / output circuit				
Connecting capacity	fine-strand with wire end ferrule	0.2-4 mm² (24-11 AWG)		
	fine-strand without wire end ferrule	0.2-6 mm² (24-10 AWG)		
	rigid			
Stripping length		8 mm (0.31 in)		
Tightening torque	input / output	1.0 Nm (9 lb.in) / 0.62 Nm (5.5 lb.in)		
Environmental data				
Ambient temperature range	operation	-35…+70 °C	-40…+70 °C	
	rated load	-35…+60 °C	-40…+60 °C	-40…+55 °C
	storage	-40…+85 °C	-40…+85 °C	
Damp heat (cyclic) (IEC/EN 60068-2-30)		95 % RH, without condensation		
Vibration (sinusoidal) (IEC/EN 60068-2-6)		10-500 Hz, 2 G, along X, Y, Z each axis, 60 min. for each axis		
Shock (half-sine) (IEC/EN 60068-2-27)		15 G, 11 ms, 3 axes, 6 faces, 3 times for each face		
Isolation data				
Rated insulation voltage U_i	input circuit / output circuit	3 kV AC		
	input / PE	1.5 kV AC		
	output / PE	0.5 kV AC; 0.71 kV DC		
	signalling contact / PE	0.5 kV DC		
Pollution degree		2		
Overvoltage category		II		
Standards / Directives				
Standards		IEC/EN 60950-1		
Low Voltage Directive		2014/35/EU		
EMC Directive		2014/30/EU		
RoHS Directive		2011/65/EU		
Protective low voltage		SELV (IEC/EN 60950-1)		

CP-E range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-E 24/5.0	CP-E 24/10.0	CP-E 24/20.0
Electromagnetic compatibility				
Interference immunity to		IEC/EN 61000-6-2		
electrostatic discharge	IEC/EN 61000-4-2	level 4 (air discharge 15 kV / contact discharge 8 kV)		
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)		
electrical fast transient/burst	IEC/EN 61000-4-4	level 4 (4 kV / 5 kHz)	level 4 (4 kV / 2.5 kHz)	
surge	IEC/EN 61000-4-5	L-L level 3 (2 kV) / L-PE level 4 (4 kV)		
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)		
power frequency magnetic fields	IEC/EN 61000-4-8	level 4 (30 A/m)		
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	dip: >95 % 10 ms / >30 % 500 ms interruptions: >95 % 5000 ms		
Interference emission		IEC/EN 61000-6-3		
high-frequency radiated		class B		
high-frequency conducted		class B		
limits for harmonic current emissions		class D		

CP-E range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		**CP-E 48/0.62**	**CP-E 48/1.25**	**CP-E 48/5.0**	**CP-E 48/10.0**
Input circuit		**L, N**			
Rated input voltage U_{in}		100-240 V AC		115 / 230 V AC auto select	115-230 V AC
Input voltage range		85-264 V AC / 90-375 V DC		90-132 V AC, 180-264 V AC / 210-375 V DC	90-264 V AC, 120-375 V DC
Frequency range AC		47-63 Hz			
Typical input current	at 115 V AC	560 mA	1060 mA	4.0 A	4.9 A
	at 230 V AC	330 mA	590 mA	1.55 A	2.5 A
Typical power consumption		35.7 W	69.0 W	267 W	528 W
Inrush current	at 115 V AC	20 A	30 A	30 A (max. 5 ms)	25 A (max. 5 ms)
	at 230 V AC	40 A	60 A	60 A (max. 5 ms)	50 A (max. 5 ms)
Discharge current	input / output	0.25 mA			
	input / PE	3.5 mA			
Power failure buffering time	at 115 V AC	min. 20 ms		min. 25 ms	min. 25 ms
	at 230 V AC	min. 30 ms			
Internal input fuse		2 A slow-acting / 250 V AC		6.3 A slow-acting / 250 V AC	10 A slow-acting / 250 V AC
Power factor correction (PFC)		no		yes, passive, 0.7	yes, active 115 V AC: 0.99 230 V AC: 0.97
Indication of operational states					
Output voltage	green LED	OUTPUT OK: ⎍: output voltage OK			
	red LED	-	-	OUTPUT LOW: ⎍: output voltage too low	
Output circuit		**L+, L+, L-, L-**			
Rated output voltage		48 V DC			
Tolerance of the output voltage		0...+1 %			
Adjustment range of the output voltage		48-55 V DC		47-56 V DC	
Rated output power		30 W	60 W	240 W	480 W
Rated output current I_r	$T_a \leq 60$ °C	0.625 A	1.25 A	5 A	-
	$T_a \leq 55$ °C	-	-	-	10 A
Derating of the output current	60 °C < $T_a \leq 70$ °C	2.5 %/°C			-
	55 °C < $T_a \leq 70$ °C	-	-	-	2.5 %/°C
Signalling output for output voltage OK	DC OK	-	-	-	-
Maximum deviation with	load change statical	±0.5 %		±1 % (single mode) ±5 % (parallel mode)	
	change of output voltage within the input voltage range	±0.5 %		±0.5 %	
Recovery time T_R		< 2 ms			
Starting time after applying the supply voltage	at I_r	max. 1 s			
	with 3500 µF	max. 2 s	-	-	-
	with 7000 µF	-	max. 1.5 s	max. 1.5 s	
Rise time	at rated load	max. 150 ms			
	with 3500 µF	max. 500 ms	-	-	-
	with 7000 µF	-	max. 500 ms	max. 500 ms	
Fall time		max. 150 ms			
Residual ripple and switching peaks	BW = 20 MHz	50 mV		100 mV	
Parallel connection		yes, to enable redundancy		configurable, to increase power, up to 3 devices, min. 0.1 I_r - max. 0.9 I_r	
Series connection		yes, to increase voltage		yes, to increase voltage, max. 2 devices	
Resistance to reverse feed		1 s - max. 63 V DC			

CP-E range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-E 48/0.62	CP-E 48/1.25	CP-E 48/5.0	CP-E 48/10.0
Output circuit - No-load, overload and short-circuit behavior					
Characteristic curve of output		U/I characteristic curve			
Short-circuit protection		continuous short-circuit proof			
Short-circuit behavior		continuation with output power limiting			
Overload protection		output power limiting			
No-load protection		continuous no-load stability			
Starting of capacitive loads		3500 µF	7000 µF	unlimited	7000 µF
General data					
Power loss		typ. 4.9 W	typ. 7.8 W	typ. 32 W	typ. 60 W
Efficiency		typ. 86 %	typ. 89 %	typ. 90 %	
Duty cycle		100 %			
Dimensions		see “Dimensional drawings”			
Material of housing		plastic		metal	
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool			
Mounting position		horizontal			
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)			
Degree of protection	housing / terminals	IP/20 / IP20			
Protection class		I			
Electrical connection - input circuit / output circuit					
Connecting capacity	fine-strand with wire end ferrule	0.2-2.5 mm² (24-14 AWG)		0.2-4 mm² (24-11 AWG)	
	fine-strand without wire end ferrule			0.2-6 mm² (24-10 AWG)	
	rigid				
Stripping length		6 mm (0.24 in)		8 mm (0.31 in)	
Tightening torque	input / output	0.6 Nm (5 lb.in)		1.0 Nm (9 lb.in) / 0.62 Nm (5.5 lb.in)	
Environmental data					
Ambient temperature range	operation	-40…+70 °C			
	rated load	-40…+60 °C			-40…+55 °C
	storage	-40…+85 °C			
Damp heat (cyclic) (IEC/EN 60068-2-30)		95 % RH, without condensation			
Vibration (sinusoidal) (IEC/EN 60068-2-6)		10-500 Hz, 2 G, along X, Y, Z each axis, 60 min. for each axis			
Shock (half-sine) (IEC/EN 60068-2-27)		15 G, 11 ms, 3 axes, 6 faces, 3 times for each face			
Isolation data					
Rated insulation voltage U_i	input circuit / output circuit	3 kV AC			
	input / PE	1.5 kV AC			
	output / PE	0.5 kV AC; 0.71 kV DC			
Pollution degree		2			
Overvoltage category		II			
Standards / Directives					
Standards		EN 61204-3			
Low Voltage Directive		2014/35/EU			
EMC Directive		2014/30/EU			
RoHS Directive		2011/65/EU			
Protective low voltage		SELV (IEC/EN 60950-1)			


CP-E range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated


Type		CP-E 48/0.62	CP-E 48/1.25	CP-E 48/5.0	CP-E 48/10.0
Electromagnetic compatibility					
Interference immunity to		IEC/EN 61000-6-2			
electrostatic discharge	IEC/EN 61000-4-2	level 4 (air discharge 15 kV / contact discharge 8 kV)			
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)			
electrical fast transient/burst	IEC/EN 61000-4-4	level 4 (4 kV / 5 kHz)		level 4 (4 kV / 2.5 kHz)	
surge	IEC/EN 61000-4-5	L-L level 3 (2 kV) / L-PE level 4 (4 kV)			
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V/m)			
power frequency magnetic fields	IEC/EN 61000-4-8	level 4 (30 A/m)			
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	dip: >95 % 10 ms / >30 % 500 ms, interruptions: >95 % 5000 ms			
Interference emission		IEC/EN 61000-6-3			
high-frequency radiated		class B			
high-frequency conducted		class B			
limits for harmonic current emissions		class A		class D	

CP-E range
Technical diagrams


Output curve at T_a = 25 °C




CP-E 12/2.5




CP-E 12/10.0




CP-E 24/1.25




CP-E 24/2.5




CP-E 24/5.0




CP-E 24/10.0




CP-E 24/20.0




CP-E 48/0.62



CP-E 48/1.25




CP-E 48/5.0




CP-E 48/10.0

CP-E range
Technical diagrams


Temperature behavior at T_a = 25 °C




CP-E 12/10.0, CP-E 24/5.0



CP-E 24/20.0, CP-E 48/10.0




CP-E 5/3.0, CP-E 24/0.75



CP-E 12/2.5, CP-E 24/1.25, CP-E 48/0.62,
CP-E 24/2.5, CP-E 48/1.25, CP-E 24/10.0, CP-E 48/5.0

CP-E range
Technical diagrams


Wiring instructions



CP-E 24/1.25, CP-E 24/2.5


Dimensional drawings

Dimensions in **mm**, inches



CP-E 5/3.0,
CP-E 24/0.75

CP-E 12/2.5,
CP-E 24/1.25,
CP-E 24/2.5,
CP-E 48/0.62,
CP-E 48/1.25



CP-E 12/10.0,
CP-E 24/5.0

CP-E 24/10.0,
CP-E 48/5.0

CP-E 24/20.0,
CP-E 48/10.0


ABB
CP-T 24/5.0
CP-T 24/10.0
CP-T 24/20.0
CP-T 48/5.0
CP-T 48/10.0
CP-T 48/20.0

CP-T range
Table of contents

276 Benefits and advantages

278 Operating controls

279 Applications

280 Ordering details

281 Technical data

285 Technical diagrams

CP-T range
Benefits and advantages



ABB's CP-T range of three-phase power supply units perfectly complements our existing power supply offering in terms of design and functionality, giving you more advanced options for your three-phase applications.

Affordable range

Products with exactly the functions you require. Designed for best price-performance ratio.

Global availability

The product can be used in any installation in the world. Giving you the confidence of world-wide sourcing – no matter where you build, install or operate your equipment.

Speed up your projects

Data available for common planning software: Less engineering time required

CP-T range
Benefits and advantages

Characteristics

- Rated output voltages 24 V, 48 V DC
- Output voltage adjustable via front-facing rotary potentiometer “OUTPUT Adjust”
- Rated output currents 5 A, 10 A, 20 A, 40 A
- Rated output powers 120 W, 240 W, 480 W, 960 W
- Three-phase operation (see derating note)
- Two-phase operation (25 % derating possible, see derating note)
- Supply range 3 x 400–500 V AC (3 x 340-575 V AC, 480-820 V DC)
- Typical efficiency of 93 %
- Low power dissipation and low heating
- Free convection cooling (no forced cooling with ventilators)
- Ambient temperature range during operation -40...+70 °C [1)]
- Open-circuit, overload and short-circuit stable
- Integrated input fuse
- Redundancy unit CP-C.1-A-RU (-C) offering true redundancy, available as accessory
- LEDs for status indication
- Signalling contact "13-14" (solid-state) for output voltage OK on 24 V devices
- Various approvals and marks

[1)] 480 W variants: -30...+70°C

Main benefits

Signalling output
Some devices of the CP-T series offer a solid-state output for function monitoring and remote diagnostics.

Wide input range
Optimized for worldwide applications: The CP-T power supplies can be used in 340 - 575 V AC or 480 - 820 V DC supply systems.

Adjustable output voltage
The CP-T range features a continuously adjustable output voltage. Thus, they can be optimally adapted to the applications, e.g. compensating the voltage drop caused by a long line length.







CP-T range
Operating controls

Indication of operational states
- OUTPUT OK: green LED - green LED - output voltage OK
- OUTPUT LOW: red LED - output voltage too low

Circuit diagram

INPUT L1, L2, L3, PE: Terminals - input
340-575 V AC /
480-820 V DC




OUTPUT Adjust:
Potentiometer - adjustment of output voltage 22.5...28.5V DC

Single/parallel:
Sliding switch - adjustment of single or parallel operation

OUTPUT L+, L+, L-, L-: Terminals - output
24 V DC, 48 V DC

13-14: Terminals - signalling contact
A solid-state output indicates the error-free operation of the output voltage


Tunnel drilling machines
Quality power management systems
Floor conveyors

CP-T range
Ordering details


2CDC 271 043 S0009

CP-T 24/5.0


2CDC 271 045 S0009

CP-T 24/10.0, CP-T 48/5.0


2CDC 271 047 S0009

CP-T 24/20.0, CP-T 48/10.0

Description

In terms of design and functionality, the CP-T range perfectly supplements the existing products and extends the range appropriately. The devices can be supplied with a three-phase voltage as well as with two-phase mains. Here, ABB offers power supply units with 24 V DC and 48 V DC outputs with 5 A, 10 A, 20 A and 40 A and efficiency of up to 93 %.

As in the case of all products, they are designed for an ambient temperature of up to 70 °C. All products can be supplied within an AC supply voltage range between 340 to 575 V AC and a DC supply voltage range between 480 to 820 V DC.

Ordering details

Input voltage range	Rated output voltage / current	Type	Order code	Weight (1 pc.) kg (lb)
340-575 V AC / 480-820 V DC	24 V DC / 5 A	CP-T 24/5.0	1SVR427054R0000	0.80 (1.77)
340-575 V AC / 480-820 V DC	24 V DC / 10 A	CP-T 24/10.0	1SVR427055R0000	1.05 (2.31)
340-575 V AC / 480-820 V DC	24 V DC / 20 A	CP-T 24/20.0	1SVR427056R0000	1.75 (3.86)
340-575 V AC / 480-820 V DC	24 V DC / 40 A	CP-T 24/40.0	1SVR427057R0000	3.20 (7.05)
340-575 V AC / 480-820 V DC	48 V DC / 5 A	CP-T 48/5.0	1SVR427054R2000	1.05 (2.31)
340-575 V AC / 480-820 V DC	48 V DC / 10 A	CP-T 48/10.0	1SVR427055R2000	1.75 (3.86)
340-575 V AC / 480-820 V DC	48 V DC / 20 A	CP-T 48/20.0	1SVR427056R2000	3.40 (7.50)

CP-T range
Technical data

Data at T_a = 25 °C, U_{in} = 3 x 400 V AC and rated values, unless otherwise indicated

Type		CP-T 24/5.0	CP-T 24/10.0	CP-T 24/20.0	CP-T 24/40.0
Input circuit		**L1, L2, L3**			
Rated input voltage U_{in}		3 x 400-500 V AC			
Input voltage range		340-575 V AC			
		480-820 V DC			
Frequency range AC		47-63 Hz			
Typical input current		0.36 A	0.65 A	1.1 A	1.72 A
Typical power consumption		135 W	270 W	538 W	1058 W
Inrush current	typ.	10 A	20 A		30 A
Power failure buffering time		min. 20 ms			min. 15 ms
Internal input fuse	per phase	2 A / 600 V AC		T 3.15 A / 500 V AC	T 5 A / 500 V AC
Recommended backup fuse		3 pole miniature circuit breaker ABB Type S203			
Power factor correction (PFC)		yes, passive			
Discharge current	towards PE	< 3.5 mA			
	input / output	< 0.25 mA			
Indication of operational states					
Output voltage	OUTPUT OK: green LED	output voltage OK when the output voltage > 75 % of the rated output voltage			
	OUTPUT LOW: red LED	output voltage too low when the output voltage < 70 % of the rated output voltage			
Output circuit		**L+, L+, L-, L-**			
Rated output voltage		24 V DC			
Tolerance of the output voltage		0...+1 %			
Adjustment range of the output voltage		22.5-28.5 V DC			
Rated output power		120 W	240 W	480 W	960 W
Rated output current I_r	$T_a \leq 60$ °C	5 A	10 A	20 A	40 A
Derating of the output current	60 °C < $T_a \leq$ 70 °C	2.5 %/°C			3.5 %/°C
Signalling contact for output voltage OK	13-14	solid-state (max. 60 V DC, 0.3 A)			
	Threshold	17.6-19.4 V			
	Insulation voltage	500 V DC			
Mininum fuse rating to achieve short-circuit protection	13-14	≥ 60 V DC, ≤ 0.3 A fast-acting			
Maximum deviation with	load change statical	±1 %	±1 % (single mode)		
		-	±5 % (parallel mode)		
	change of output voltage within the input voltage range	± 0.5 %			
Recovery time T_A	at nominal load	< 2 ms			
Starting time after applying the supply voltage	at I_r	max. 1 s			
	with 3500 µF	max. 1.5 s			
Rise time	at nominal load	max. 150 ms			
	with 3500 µF	max. 500 ms			
Fall time		max. 150 ms			
Residual ripple and switching peaks	BW = 20 MHz	100 mV			80 mV
Parallel connection		not supported	configurable, to increase power, up to 2 devices, min. 0.1 I_r - max 0.9 I_r		to increase power, up to 2 devices, min. 0.1 I_r - max. 0.9 I_r,use active current balancing
Series connection		not supported	yes, to increase voltage, max. 2 devices		
Resistance to reverse feed		approx. 35 V			
Output circuit - No-load, overload and short-circuit behavior					
Characteristic curve of output		combined U/I characteristic curve and hiccup mode		U/I- or hiccup-mode adjustable	hiccup / fold back behavior
Short-circuit protection		continuous short-circuit proof			
Short-circuit behavior		current limiting			
Overload protection		hiccup mode			
No-load protection		continuous no-load stability			
Overtemperature protection		yes, automatic recovery after temperature went down			
Starting of capacitive loads		3500 µF	7000 µF	7000 µF	7000 µF

CP-T range
Technical data

Data at T_a = 25 °C, U_{in} = 3 x 400 V AC and rated values, unless otherwise indicated

Type		CP-T 24/5.0	CP-T 24/10.0	CP-T 24/20.0	CP-T 24/40.0
General data					
Efficiency		typ. 89 %	typ. 90 %		typ. 92 %
Duty cycle		100 %			
Dimensions		see “Dimensional drawings”			
Material of housing		metal			
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool			
Mounting position		horizontal			
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)			
Degree of protection	housing / terminals	IP20 / IP20			
Protection class		I			
Electrical connection - input circuit / output circuit / signalling circuit					
Connecting capacity	fine-strand with wire end ferrule	0.2-4 mm² (24-11 AWG)			
	fine-strand without wire end ferrule	0.2-6 mm² (24-10 AWG)			
	rigid	0.2-6 mm² (24-10 AWG)			
Stripping length		8 mm (0.31 in)			
Tightening torque	input / output	1 Nm (9 lb.in) / 0.6 Nm (5.5 lb.in)			1 Nm (9 lb.in) / 1.8 Nm (15.6 lb.in)
Environmental data					
Ambient temperature range	operation	-40...+70 °C		-30...+70 °C	-40...+70 °C
	rated load	-40...+60 °C		-30...+60 °C	-40...+60 °C
	storage	-40...+85 °C			
Altitude during operation	IEC/EN 60068-2-13	max. 5000 m			
Damp heat (cyclic) (IEC/EN 60068-2-30)		95 % without condensation			
Vibration (sinusoidal) (IEC/EN 60068-2-6)		10-500 Hz, 2G, each along X, Y, Z axes 60 min / cycle			
Shock (half-sine) (IEC/EN 60068-2-27)		15 g, 11 ms, 3 axes, 6 faces, 3 times for each face			
Isolation data					
Rated insulation voltage U_i	input circuit / output circuit	3 kV AC			
	input / PE	1.5 kV AC			
	output / PE	0.5 kV AC; 0.71 kV DC			
	signalling output / PE	0.5 kV DC			
Pollution degree		2			
Standards / Directives					
Standards		IEC/EN 60950-1			
Low Voltage Directive		2014/35/EU			
EMC Directive		2014/30/EU			
RoHS Directive		2011/65/EU			
Protective low voltage		SELV (IEC/EN 60950-1)			
Electromagnetic compatibility					
Interference immunity to		IEC/EN 61000-6-2			
electrostatic discharge	IEC/EN 61000-4-2	level 4 (air discharge 15 kV / contact discharge 8 kV)			
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)			
electrical fast transient/burst	IEC/EN 61000-4-4	level 4 (4 kV / 2.5 kHz)	level 4 (4 kV / 5 kHz)		
surge	IEC/EN 61000-4-5	L-L level 3 (2 kV) / L-PE level 4 (4 kV)			
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)			
power frequency magnetic fields	IEC/EN 61000-4-8	level 4 (30 A/m)			
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	dips: >95 % 0.5 ms / >30 % 0.5 ms, interruptions: >95 % 250 ms			
Interference emission		IEC/EN 61000-6-3			
high-frequency radiated		class B			
high-frequency conducted		class B			
limits for harmonic current emissions	IEC/EN 61000-3-2	class A			

CP-T range
Technical data

Data at T_a = 25 °C, U_{in} = 3 x 400 V AC and rated values, unless otherwise indicated

Type		CP-T 48/5.0	CP-T 48/10.0	CP-T 48/20.0
Input circuit		**L1, L2, L3**		
Rated input voltage U_{in}		3 x 400-500 V AC		
Input voltage range		340-575 V AC		
		480-820 V DC		
Frequency range AC		47-63 Hz		
Typical input current		0.65 A	1.1 A	1.72 A
Typical power consumption		264 W	535 W	1050 W
Inrush current	typ.	20 A		30 A
Power failure buffering time		min. 20 ms		min. 15 ms
Internal input fuse	per phase	2 A / 600 V AC	T 3.15 A / 500 V AC	T 5 A / 500 V AC
Power factor correction (PFC)		yes, passive		
Discharge current	towards PE	< 3.5 mA		
	input / output	< 0.25 mA		
Indication of operational states				
Output voltage	OUTPUT OK: green LED	output voltage OK when the output voltage > 75 % of the rated output voltage		
	OUTPUT LOW: red LED	output voltage too low when the output voltage < 70 % of the rated output voltage		
Output circuit		**L+, L+, L-, L-**		
Rated output voltage		48 V DC		
Tolerance of the output voltage		0...+1 %		
Adjustment range of the output voltage		47-56 V DC		
Rated output power		240 W	480 W	960 W
Rated output current I_r	$T_a \leq 60$ °C	5 A	10 A	20 A
Derating of the output current	60 °C < $T_a \leq$ 70 °C	2.5 %/°C		3.5 %/°C
Maximum deviation with	load change statical	±1 % (single mode)		
		± 5 % (parallel mode)		
	change of output voltage within the input voltage range	±0.5 %		
Recovery time T_A	at rated load	< 2 ms		
Starting time after applying the supply voltage	at I_r	max. 1 s		
	with 7000 µF	max. 1.5 s		
Rise time	at rated load	max. 150 ms		
	with 7000 µF	max. 500 ms		
Fall time		max. 150 ms		
Residual ripple and switching peaks	BW = 20 MHz	100 mV		80 mV
Parallel connection		configurable, to increase power, up to 2 devices, min. 0.1 I_r - max 0.9 I_r		to increase power, up to 2 devices, min. 0.1 I_r - max. 0.9 I_r, use active current balancing
Series connection		yes, to increase voltage, max. 2 devices		
Resistance to reverse feed		approx. 35 V	approx. 63 V	approx. 63 V
Output circuit - No-load, overload and short-circuit behavior				
Characteristic curve of output		combined U/I and hiccup mode	U/I or hiccup mode, configurable	hiccup mode / fold back behavior
Short-circuit protection		continuous short-circuit proof		
Short-circuit behavior		current limiting		
Overload protection		hiccup mode		
No-load protection		continuous no-load stability		
Over temperature protection		yes, automatic recovery after temperature went down		
Starting of capacitive loads		7000 µF		


CP-T range
Technical data

Data at T_a = 25 °C, U_{in} = 3 x 400 V AC and rated values, unless otherwise indicated


Type		CP-T 48/5.0	CP-T 48/10.0	CP-T 48/20.0
General data				
Efficiency		typ. 91 %		typ. 93 %
Duty cycle		100%		
Dimensions		see “Dimensional drawings”		
Material of housing		Metal		
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool		
Mounting position		horizontal		
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)		
Degree of protection	housing / terminals	IP20 / IP20		
Protection class		I		
Electrical connection - input circuit / output circuit				
Connecting capacity	fine-strand with wire end ferrule	0.2-4 mm² (24-11 AWG)		0.2-4 mm² (24-11 AWG) / 0.5-10 mm² (20-8 AWG)
	fine-strand without wire end ferrule	0.2-6 mm² (24-10 AWG)		
	rigid			
Stripping length		8 mm (0.31 in)		
Tightening torque	input / output	1 Nm (9 lb.in) / 0.6 Nm (5.5 lb.in)		1 Nm (9 lb.in) / 1.8 Nm (15.6 lb.in)
Environmental data				
Ambient temperature range	operation	-40…+70 °C	-30…+70 °C	-40…+70 °C
	rated load	-40…+60 °C	-30…+60 °C	-40…+60 °C
	storage	-40…+85 °C	-40…+85 °C	-40…+85 °C
Altitude during operation	IEC/EN 60068-2-13	max. 5000 m		
Damp heat (cyclic) (IEC/EN 60068-2-30)		95 % without condensation		
Vibration (sinusoidal) (IEC/EN 60068-2-6)		10-500 Hz, 2G, each along X, Y, Z axes 6 min / cycle		
Shock (half-sine) (IEC/EN 60068-2-27)		15G, 11 ms, 3 axes, 6 Faces, 3 times for each face		
Isolation data				
Rated insulation voltage U_i	input circuit / output circuit	3 kV AC		
	input / PE	1.5 kV AC		
	output / PE	0.5 kV AC; 0.71 kV DC		
Pollution degree		2		
Standards / Directives				
Standards		IEC/EN 60950-1		
Low Voltage Directive		2014/35/EU		
EMC Directive		2014/30/EU		
RoHS Directive		2011/65/EU		
Protective low voltage		SELV (IEC/EN 60950-1)		
Electromagnetic compatibility				
Interference immunity to		IEC/EN 61000-6-2		
electrostatic discharge	IEC/EN 61000-4-2	level 4 (air discharge 15 kV / contact discharge 8 kV)		
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)		
electrical fast transient/burst	IEC/EN 61000-4-4	level 4 (4 kV / 5 kHz)		
surge	IEC/EN 61000-4-5	L-L level 3 (2 kV) / L-PE level 4 (4 kV)		
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)		
power frequency magnetic fields	IEC/EN 61000-4-8	level 4 (30 A/m)		
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	dips: >95 % 0.5 ms / >30 % 0.5 ms interruptions: >95 % 250 ms		
Interference emission		IEC/EN 61000-6-3		
high-frequency radiated		class B		
high-frequency conducted		class B		
limits for harmonic current emissions	IEC/EN 61000-3-2	class A		

CP-T range
Technical diagrams


Output curves at T_a = 25 °C




CP-T 24/5.0




CP-T 24/10.0




CP-T 24/20.0 U/I curve




CP-T 24/20.0 Hiccup mode




CP-T 24/40.0




CP-T 48/5.0



CP-T 48/10.0 U/I curve




CP-T 48/10.0 Hiccup mode




CP-T 48/20.0


Temperature curves at rated load



CP-T 24/40.0, CP-T 48/20.0




CP-T 24/20.0, CP-T 48/10.0




CP-T 24/5.0, CP-T 24/10.0, CP-T 48/5.0

CP-T range
Technical diagrams


Dimensional drawings
Dimensions in **mm**, inches




CP-T 24/5.0



CP-T 24/10.0, CP-T 48/5.0



CP-T 24/20.0, CP-T 48/10.0



CP-T 24/40.0, CP-T 48/20.0


CP-C.1 24/5.0
CP-C.1 24/10.0
CP-C.1 24/20.0
CP-C.1-A-RU
OUTPUT 24 V DC 5 A
OUTPUT 24 V DC 10 A
OUTPUT 24 V DC 20 A
INPUT 100-240 V AC
OUTPUT

CP-C.1 range
Table of contents

290 Benefits and advantages

292 Operating controls

293 Applications

294 Ordering details

295 Technical data

307 Technical diagrams

CP-C.1 range
Benefits and advantages




The high-performance CP-C.1 power supplies are ABB's most advanced range. With excellent efficiency, high reliability and innovative functionality, it is ready to take on the most demanding of industrial applications These power supplies have a 150 % integrated power reserve, operate at an efficiency of up to 94 % and are equipped with overheat protection and active power factor correction. Combined with a broad AC and DC input range and extensive worldwide approvals, CP-C.1 power supplies are the preferred choice for professional DC applications. ATEX and IECEx approvals are available for the use in hazardous areas.



Continuous operation

- Power reserve design to allow performance with up to 150 % more current
- Redundancy setup of the application possible to allow parallel operation
- Long lifetime
- High peak currents for switching on capacitive loads are supported



Project cost reduction

- Up to 94 % efficiency saves money for energy during operation
- Less need for external cooling in the cabinet
- Small size to reduce space needed in panel



Reliabel in harsh conditions

- Extended ambient temperature range during operation -40...+70 °C with coated PCBA version
- IECEx/ATEX approvals for hazardous locations available
- High MTBF values

CP-C.1 range
Benefits and advantages



Characteristics
- Rated output voltage 24 V DC
- Power reserve design delivers up to 150 % at $T_a \leq 40$ °C
- Output voltage adjustable via front-facing rotary potentiometer “OUTPUT Adjust”, 22.5-28.5 V
- High efficiency of up to 94 %
- Low power dissipation and low heating
- Free convection cooling (no forced cooling)
- Devices with coated PCBAs for harsh environments and with extended temperature range
- Open-circuit, overload and short-circuit stable
- Integrated input fuse
- OUTPUT OK - signaling output “13-14” (relay), Power reserve signaling output “$I > I_R$ (transistor)
- Redundancy unit offers true redundancy, available as accessory
- Various approvals and marks



Main benefits

The primary switch mode power supply CP-C.1 has a wide range of AC and DC input voltages. Furthermore, the CP-C.1 is equipped with capacitors that ensure a hold-up time of at least 50 ms. This enables worldwide usage and permits safe operation in fluctuating networks and battery-powered applications.

With their robust metallic housing and the reliable construction, CP-C.1 power supplies are suitable for applications in industrial environments. The CP-C.1-C units have coated PCBAs, which enables their use in harsh industrial environments. The power reserve of up to 150 % enables trouble-free starting of heavy loads eliminating the need for an oversized power supply.

Signaling output
To communicate the status of the power supply, the CP-C.1 is equipped with a relay output to signal OUTPUT OK as well as a transistor output $I > I_R$ to indicate when the power reserve is active. These signals can be used for communication with a higher level control system, e.g. a PLC.
Depending on the logic of the higher level control system, an appropriate action is initiated by forwarding the signal. The receptor of this signal could be a contactor, a signal tower, or an interface relay.

CP-C.1 range
Operating controls

13-14: Relay output to signal 'Output OK'

I > I_R: Power reserve transistor output to signal 'Power reserve is active'



OUTPUT L+, L-: Output terminals 24 V DC

Side mounting screw holes for DIN rail adapter / lateral mounting

Indication of operational states OUTPUT OK: Green LED POWER RESERVE I > I_R: Yellow LED


Circuit diagram

OUTPUT Adjust: Rotary potentiometer - Adjustment of output voltage 22.5-28.5 V DC

INPUT L(+), N(-), PE: Input terminals 85-264 V AC / 90 - 300 V DC


CP-C.1 range
Applications

Application
The primary switch mode power supply CP-C.1 has a wide range of AC and DC input voltages. Furthermore, the CP-C.1 is equipped with capacitors that ensure a hold-up time of at least 50 ms. This enables worldwide usage and permits safe operation in fluctuating networks and battery-powered applications. With their robust metallic housing and reliable construction, CP-C.1 power supplies are suitable for applications in industrial environments. The CP-C.1-C units have coated PCBAs, which enables their use in the harshest of industrial environments. usage in even harsh industrial environments. The power reserve of up to 150 % enables trouble-free starting of heavy loads eliminating the need for an oversized power supply.



Adjustable output voltage
The CP-C.1 range power supplies feature a continuously adjustable output voltage of 22.5 to 28.5 V DC. Thus, they can be optimally adapted to the applications, e.g. compensating the voltage drop caused by a long line length.

Signaling output
To communicate the status of the power supply, the CP-C.1 is equipped with a relay output to signal OUTPUT OK as well as a transistor output $I > I_R$ to indicate when the power reserve is active. These signals can be used for communication with a higher level control system,
e.g. a PLC.



Power reserve
The primary switch mode power supply CP-C.1 is equipped with a power reserve functionality to handle the start-up of particularly heavy loads (e.g. of a capacitive load or a motor). To ensure that heavy loads are started up, the CP-C.1 delivers additionally up to 150 % of the rated output current to secure the operation of the application. This status is displayed by the yellow LED labelled POWER RESERVE $I > I_R$.

CP-C.1 range
Ordering details



CP-C.1 24/5.0
CP-C.1 24/5.0-C



CP-C.1 24/10.0
CP-C.1 24/10.0-C



CP-C.1 24/20.0
CP-C.1 24/20.0-C



CP-C.1 24/5.0
light grey



CP-C.1 24/10.0
light grey

Description

High-performance CP-C.1 power supplies are ABB's most advanced range. With excellent efficiency, high reliability, and innovative functionality, it is ready to take on the most demanding industrial applications. These power supplies have up to 50 % integrated power reserve and operate at an efficiency of up to 94 %. They are equipped with overheat protection and active power factor correction. Combined with a broad AC and DC input range and extensive worldwide approvals, the CP-C.1 power supplies are the preferred choice for professional DC applications.

Ordering details - CP-C.1

Input voltage range	Rated output voltage / current	PCBA	Color	Type	Order code	Weight (1 pc.) kg (lb)
85-264 V AC, 90-300 V DC	24 V DC / 5 A	uncoated	dark grey	CP-C.1 24/5.0	1SVR360563R1001	0.87 (1.92)
	24 V DC / 10 A			CP-C.1 24/10.0	1SVR360663R1001	1.21 (2.67)
	24 V DC / 20 A			CP-C.1 24/20.0	1SVR360763R1001	1.70 (3.75)
	24 V DC / 5 A	coated		CP-C.1 24/5.0-C	1SVR360563R2001	0.87 (1.92)
	24 V DC / 10 A			CP-C.1 24/10.0-C	1SVR360663R2001	1.24 (2.73)
	24 V DC / 20 A			CP-C.1 24/20.0-C	1SVR360763R2001	1.72 (3.79)
	24 V DC / 5 A	uncoated	light grey	CP-C.1 24/5.0-L	1SVR361563R1001	0.87 (1.92)
	24 V DC / 10 A			CP-C.1 24/10.0-L	1SVR361663R1001	1.21 (2.67)
	24 V DC / 20 A			CP-C.1 24/20.0-L	1SVR361763R1001	1.70 (3.75)

CP-C.1 range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type			CP-C.1 24/5.0, CP-C.1 24/5.0-L	CP-C.1 24/5.0-C
Input circuit - Supply circuit				
			L (+), N (-)	
Rated input voltage U_{in}			100-240 V AC, 90-300 V DC	
Input voltage range		AC	85-264 V AC	
		DC	90-300 V DC	
Typical input current		at 115 V AC	1.1 A	
		at 230 V AC	0.6 A	
Typical power consumption		at 230 V AC	132 W	
Rated frequency			DC, 50/60 Hz	
Frequency range		AC	45-65 Hz	
Inrush current, cold state			< 8 A	
Let-through energy I^2t , cold state		at 230 V AC	< 1 A^2s	
Discharge current towards PE			< 3.5 mA	
Hold-up time		at 115 V AC	min. 50 ms	
		at 230 V AC	min. 50 ms	
Internal input fuse			T4.0 A, not exchangeable	
Recommended backup fuse for wire protection at 1.5 mm^2			1 pole miniature circuit breaker ABB type S 200	
		characteristic	B or C	
		max. rating	16 A	
Power factor correction (PFC)			yes, active	
Transient overvoltage protection			yes, varistor	
User interface				
Indication of operational states				
Output voltage	LED 'OUTPUT OK ' (green)	ON	92 % adjusted U_{out}	
		flashing	90 % adjusted U_{out}	
Power reserve	LED 'I > I_R' (yellow)	OFF	I ≤ I_R	
		ON	I > I_R	
Output circuit - Power output				
			L+, L-	
Rated output voltage			24 V DC	
Tolerance of the output voltage			± 1 %	
Adjustment range of the output voltage			22.5-28.5 V DC	
Rated output power			120 W	
Rated output current I_R		- 25 °C ≤ T_a ≤ 60 °C	5.0 A	-
		- 40 °C ≤ T_a ≤ 60 °C	-	5.0 A
Reserve output current		- 25 °C ≤ T_a ≤ 40 °C	7.5 A continuously	-
		- 40 °C ≤ T_a ≤ 40 °C	-	7.5 A continuously
Short-circuit current limiting			7.6 A	
Derating of the output current		60 °C < T_a ≤ 70 °C	2.5 %/°C	
Deviation width of output voltage		static output voltage deviaton 25-100 %	< 1%, class C	
		dynamical 0-100 %	< 2%, class A	
		change of input voltage within the rated input voltage	< 1 ms, class A	
Recovery time T_A			< 1 ms, class A	
Starting time after applying the supply voltage			< 500 ms, class C	
Rise time			< 10 ms	
Residual ripple and switching peaks		BW = 20 MHz	< 120 mV_{pp}, class A	
Parallel connection			yes, up to 5 devices, to enable redundancy and to increase power, current not symmetrical	
Series connection			yes, max. 2 devices to increase voltage	

CP-C.1 range
Technical data

Type		CP-C.1 24/5.0, CP-C.1 24/5.0-L	CP-C.1 24/5.0-C
No-load, overload and short-circuit behavior			
Characteristic curve of output		U/I characteristic curve with power reserve	
Short-circuit protection		continuous short-circuit stability	
Short-circuit behavior		current limiting	
Resistance to reverse feed		≤ 35 V DC	
Overload protection		constant current limitation	
Overtemperature protection		protection by switch off in case of overtemperature (thermal protection), automatic restart	
No-load protection		continuous no-load stability	
Starting of capacitive loads		yes	
Signaling outputs			
OUTPUT OK signaling output			
Type of output	13-14	relay, n/o contact	
ON (contact closed)		92 % adjusted U_{out}	
OFF (contact open)		90 % adjusted U_{out}	
Contact ratings	max. switching voltage / current	30 V AC - 0.5 A / 24 V DC - 1 A (resistive load)	
	min. switching voltage / current	5 V DC / 1 mA	
POWER RESERVE signaling output			
Type of output	I > I_R	transistor, short-circuit proof	
Active / ON (closed)		I > I_R	
Inactive / OFF (open)		I ≤ I_R	
Ratings	voltage/current	24 V DC / ≤ 20 mA	
General data			
Efficiency	at rated output power	up to 93 %	
Power loss	at rated output power	12 W	
	at 50% of rated output power	8 W	
	at no load	< 3.6 W	
Duty cycle		100 %	
MTBF	acc. to MIL 217 HDBK	on request	
Dimensions		see “Dimensional drawings”	
Material of housing	cover	zinc-coated sheet-steel	
	housing shell	aluminium	
	front	plastic, PA6, V-0	
Mounting		DIN rail (IEC/EN 60715), snap-on mounting	
Mounting position		see “Mounting positions” in the data sheet	
Minimum distance to other units	horizontal	25 mm (0.98 in)	
	vertical	25 mm (0.98 in)	
Degree of protection (IEC/EN 60529)	housing / terminals	IP20 / IP20	
Protection class (IEC/EN 61140)		I	
Electrical connection			
Input circuits (L(+), N(-), PE)			
Connecting capacity	rigid	0.5-4.0 mm² (20-10 AWG)	
	fine-strand with(out) wire end ferrule	0.5-2.5 mm² (20-12 AWG)	
Stripping length		8 mm (0.315 in)	
Tightening torque		0.5 Nm (4.4 lb.in)	
Recommended screw driver		PH1 / Ø 4.0 x 0.8 mm	
Output circuits (L+, L+, L-, L-)			
Connecting capacity	rigid	0.5-4.0 mm² (20-10 AWG)	
	fine-strand with(out) wire end ferrule	0.5-2.5 mm² (20-12 AWG)	
Stripping length		8 mm (0.315 in)	
Tightening torque		0.5 Nm (4.4 lb.in)	
Recommended screw driver		PH1 / Ø 4.0 x 0.8 mm	

CP-C.1 range
Technical data

Type		CP-C.1 24/5.0, CP-C.1 24/5.0-L	CP-C.1 24/5.0-C
Signaling output (13-14, I > IR)			
Connecting capacity	rigid	0.5-4.0 mm² (20-10 AWG)	
	fine-strand with(out) wire end ferrule	0.5-2.5 mm² (20-12 AWG)	
Stripping length		8 mm (0.315 in)	
Tightening torque		0.5 Nm (4.4 lb.in)	
Recommended screw driver		PH1 / Ø 4.0 x 0.8 mm	
Maximum cable length (applicable for I>IR)		30 m	
Environmental data			
Ambient temperature range	operation	-25…+70 °C (-13... +158 °F)	-40…+70 °C (-40...+158 °F)
	rated output power	-25...+60 °C (-13... +140 °F)	-40...+60 °C (-40...+140 °F)
	storage	-40…+85 °C (-40...+185 °F)	
	transportation	-40…+85 °C (-40...+185 °F)	
Climatic class (IEC/EN 60721-3-1)	storage	1K2 (-40...+85 °C / -40...+185 °F)	
Climatic class (IEC/EN 60721-3-2)	transportation	2K2 (-40…+85 °C / -40...+185 °F)	
Climatic class (IEC/EN 60721-3-3)	operation	3K3 (-25…+70 °C / -13...+158 °F)	3K3 (-40…+70 °C / -40...+158 °F)
Damp heat, cyclic (IEC/EN 60068-2-30)		test Db: 55 °C, 2 cycles	
Vibration (IEC/EN 60068-2-6)		test Fc: 10-58 Hz, amplitude ±0.15 mm, 58-150 Hz, 2 g, 10 sweep cycles each axis	
Shock, half-sine (IEC/EN 60068-2-27)		test Ea: 30 g, 6 ms, 3 pulses each axis; bump 20 g, 11 ms, 100 pulses each axis	
Coated PCBA		no	yes
Gaseous corrosive environment withstand test (IEC/EN 60068-2-60)		-	testing method: 4 testing period: 21 days ambient conditions: 25 °C, 75 % r.h. air/volume change rate per hour: 3-6 sample not energized during exposure gas concentrations acc. ISA-S71.04.2013 Harsh Group A, G3 IEC 60721-3.3 acc. 3C2/3C3 - H2S ≥ 100 ± 10 ppb - SO2/SO3 ≥ 300 ± 20 ppb - Cl2 ≥ 100 ± 10 ppb - NOx ≥ 1250 ± 20 ppb

Isolation data		
Rated impulse withstand voltage U_{imp} (EN 50178)	input circuit / output circuit	4 kV (1.2/50 µs)
	input circuit / PE	4 kV (1.2/50 µs)
	input circuit / relay contact	4 kV (1.2/50 µs)
	output circuit / relay contact	0.5 kV (1.2/50 µs)
	relay contact / PE	0.5 kV (1.2/50 µs)
	output circuit / PE	0.5 kV (1.2/50 µs)
Rated insulation voltage U_i (EN 50178)	input circuit / output circuit	300 V
	input circuit / PE	300 V
	input circuit / relay contact	300 V
	output circuit / relay contact	50 V
	relay contact / PE	50 V
	output circuit / PE	50 V
Overvoltage category (EN 50178)	< 2000 m	III
	2000…5000 m	II
Overvoltage category (IEC/EN 60950-1)	< 2000 m	II
	2000…5000 m	I
Pollution degree		2
Protective separation (IEC/EN 60950-1)	input circuit / output circuit	yes
	input circuit / relay contact	yes

CP-C.1 range
Technical data

Type		**CP-C.1 24/5.0, CP-C.1 24/5.0-L**	**CP-C.1 24/5.0-C**
Standards / Directives			
Standards		IEC/EN 61204	
Low Voltage Directive		2014/35/EU	
EMC Directive		2014/30/EU	
ATEX Directive		-	2014/34/EU
RoHS Directive		2011/65/EU	
Electrical safety		IEC/EN 60950-1	
Industrial control equipment		UL 508 / CSA 22.2 No 107.1	
Electronic equipment for use in power installations		EN 50178	
Protective extra low voltage		PELV (EN 50178)	
Safety extra low voltage		SELV (IEC/EN 60950-1)	
Limitation of harmonic line currents		IEC/EN 61000-3-2	
Electromagnetic compatibility			
Low-voltage power supplies, d.c. output – Part 3: Electromagnetic compatibility (EMC)		IEC/EN 61204-3	
Interference immunity to		IEC/EN 61000-6-2	
electrostatic discharge (ESD)	IEC/EN 61000-4-2	level 4, 8 kV / 15 kV (criterion A)	
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3, 10 V/m (criterion A)	
electrical fast transient / burst	IEC/EN 61000-4-4	level 4, 4 kV / 2 kV (criterion A)	
surge	IEC/EN 61000-4-5	level 4, L/N 2 kV (criterion A) level 4, L,N/PE 4 kV (criterion A)	
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3, 10 V (criterion A)	
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	class 3	
harmonics and interharmonics	IEC/EN 61000-4-13	class 3 (criterion A)	
conducted, common mode disturbances in the frequency range 0 Hz to 150 kHz	IEC/EN 61000-4-16	level 3, 10 V	
Interference emission		IEC/EN 61000-6-3	
limits for harmonic current emissions	IEC/EN 61000-3-2	class A	
limitation of voltage changes etc.	IEC/EN 61000-3-3	compliant	
Information technology equipment radio disturbance characteristics limits and methods of measurement	IEC/CISPR 22, EN 55022	class B	
Industrial scientific and medical (ISM) radio-frequency equipment electromagnetic disturbance characteristics limits and methods of measurement	IEC/CISPR 11, EN 55011	class B	
Voltage sags	SEMI F47	passed	
Federal Communications Commission	FCC15	compliant	

CP-C.1 range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type			CP-C.1 24/10.0, CP-C.1 24/10.0-L	CP-C.1 24/10.0-C
Input circuit - Supply circuit				
			L (+), N (-)	
Rated input voltage U_{in}			100-240 V AC, 90-300 V DC	
Input voltage range		AC	85-264 V AC	
		DC	90-300 V DC	
Typical input current		at 115 V AC	2.3 A	
		at 230 V AC	1.2 A	
Typical power consumption		at 230 V AC	256 W	
Rated frequency			DC, 50/60 Hz	
Frequency range		AC	45-65 Hz	
Inrush current, cold state			< 11 A	
Let-through energy I^2t , cold state		at 230 V AC	< 1,5 A^2s	
Discharge current towards PE			< 3.5 mA	
Hold-up time		at 115 V AC	min. 40 ms	
		at 230 V AC	min. 40 ms	
Internal input fuse			T6.3 A, not exchangeable	
Recommended backup fuse for wire protection at 1.5 mm^2			1 pole miniature circuit breaker ABB type S 200	
		characteristic	B or C	
		max. rating	16 A	
Power factor correction (PFC)			yes, active	
Transient overvoltage protection			yes, varistor	
User interface				
Indication of operational states				
Output voltage	LED 'OUTPUT OK ' (green)	ON	92 % adjusted U_{out}	
		flashing	90 % adjusted U_{out}	
Power reserve	LED 'I > I_R' (yellow)	OFF	I ≤ I_R	
		ON	I > I_R	
Output circuit - Power output				
			L+, L-	
Rated output voltage			24 V DC	
Tolerance of the output voltage			±1 %	
Adjustment range of the output voltage			22.5-28.5 V DC	
Rated output power			240 W	
Rated output current I_R		- 25 °C ≤ T_a ≤ 60 °C	10.0 A	-
		- 40 °C ≤ T_a ≤ 60 °C	-	10.0 A
Reserve output current		- 25 °C ≤ T_a ≤ 40 °C	15.0 A continuously	-
		- 40 °C ≤ T_a ≤ 60 °C	-	15.0 A continuously
Short-circuit current limiting			15.5 A	15.5 A
Derating of the output current		60 °C < T_a ≤ 70 °C	2.5 %/°C	2.5 %/°C
Deviation width of output voltage		static output voltage deviation 25-100 %	< 1%, class C	
		dynamic 0-100 %	< 5 %, class B	
		change of input voltage within the rated input voltage	< 1 ms, class A	
Recovery time T_A			< 1 ms, class A	
Starting time after applying the supply voltage			< 500 ms, class C	
Rise time			< 10 ms	
Residual ripple and switching peaks		BW = 20 MHz	< 120 mV_{pp}, class A	
Parallel connection			yes, up to 5 devices, to enable redundancy and to increase power, current not symmetrical	
Series connection			yes, max. 2 devices to increase voltage	

CP-C.1 range
Technical data

Type		CP-C.1 24/10.0, CP-C.1 24/10.0-L	CP-C.1 24/10.0-C
No-load, overload and short-circuit behavior			
Characteristic curve of output		U/I characteristic curve with power reserve	
Short-circuit protection		continuous short-circuit stability	
Short-circuit behavior		current limiting	
Resistance to reverse feed		≤ 35 V DC	
Overload protection		constant current limitation	
Overtemperature protection		protection by switch off in case of overtemperature (thermal protection), automatic restart	
No-load protection		continuous no-load stability	
Starting of capacitive loads		yes	
Signaling outputs			
OUTPUT OK signaling output			
Type of output	13-14	relay, n/o contact	
ON (contact closed)		92 % adjusted U_{out}	
OFF (contact open)		90 % adjusted U_{out}	
Contact ratings	max. switching voltage / current	30 V AC - 0.5 A / 24 V DC - 1 A (resistive load)	
	min. switching voltage / current	5 V DC / 1 mA	
POWER RESERVE signaling output			
Type of output	$I > I_R$	transistor, short-circuit proof	
Active / ON (closed)		$I > I_R$	
Inactive / OFF (open)		$I \leq I_R$	
Ratings	voltage/current	24 V DC / ≤ 20 mA	
General data			
Efficiency	at rated output power	up to 94 %	
Power loss	at rated output power	16 W	
	at 50% of rated output power	12 W	
	at no load	< 3.6 W	
Duty cycle		100 %	
MTBF	acc. to MIL 217 HDBK	on request	
Dimensions		see “Dimensional drawings”	
Material of housing	cover	zinc-coated sheet-steel	
	housing shell	aluminium	
	front	plastic, PA6, V-0	
Mounting		DIN rail (IEC/EN 60715), snap-on mounting	
Mounting position		see “Mounting positions” in the data sheet	
Minimum distance to other units	horizontal	25 mm (0.98 in)	
	vertical	25 mm (0.98 in)	
Degree of protection (IEC/EN 60529)	housing / terminals	IP20 / IP20	
Protection class (IEC/EN 61140)		I	
Electrical connection			
Input circuits (L(+), N(-), PE)			
Connecting capacity	rigid	0.5-4.0 mm² (20-10 AWG)	
	fine-strand with(out) wire end ferrule	0.5-2.5 mm² (20-12 AWG)	
Stripping length		8 mm (0.315 in)	
Tightening torque		0.5 Nm (4.4 lb.in)	
Recommended screw driver		PH1 / Ø 4.0 x 0.8 mm	
Output circuits (L+, L+, L-, L-)			
Connecting capacity	rigid	0.5-4.0 mm² (20-10 AWG)	
	fine-strand with(out) wire end ferrule	0.5-2.5 mm² (20-12 AWG)	
Stripping length		8 mm (0.315 in)	
Tightening torque		0.5 Nm (4.4 lb.in)	
Recommended screw driver		PH1 / Ø 4.0 x 0.8 mm	

CP-C.1 range
Technical data

Type			CP-C.1 24/10.0, CP-C.1 24/10.0-L	CP-C.1 24/10.0-C
Signaling output (13-14, I > IR)				
Connecting capacity		rigid	0.5-4.0 mm² (20-10 AWG)	
		fine-strand with(out) wire end ferrule	0.5-2.5 mm² (20-12 AWG)	
Stripping length			8 mm (0.315 in)	
Tightening torque			0.5 Nm (4.4 lb.in)	
Recommended screw driver			PH1 / Ø 4.0 x 0.8 mm	
Maximum cable length (applicable for $I>I_R$)			30 m	
Environmental data				
Ambient temperature range		operation	-25…+70 °C (-13...+158 °F)	-40…+70 °C (-40...+158 °F)
		rated output power	-25...+60 °C (-13...+140 °F)	-40...+60 °C (-40...+140 °F)
		storage	-40…+85 °C (-40...+185 °F)	
		transportation	-40…+85 °C (-40...+185 °F)	
Climatic class (IEC/EN 60721-3-1)		storage	1K2 (-40...+85 °C / -40...+185 °F)	
Climatic class (IEC/EN 60721-3-2)		transportation	2K2 (-40…+85 °C / -40...+185 °F)	
Climatic class (IEC/EN 60721-3-3)		operation	3K3 (-25…+70 °C / -13...+158 °F)	3K3 (-40…+70 °C / -40...+158 °F)
Damp heat, cyclic (IEC/EN 60068-2-30)			test Db: 55 °C, 2 cycles	
Vibration (IEC/EN 60068-2-6)			test Fc: 10-58 Hz, amplitude ±0.15 mm, 58-150 Hz, 2 g, 10 sweep cycles each axis	
Shock, half-sine (IEC/EN 60068-2-27)			test Ea: 30 g, 6 ms, 3 pulses each axis; bump 20 g, 11 ms, 100 pulses each axis	
Coated PCBA			no	yes
Gaseous corrosive environment withstand test (IEC/EN 60068-2-60)			-	testing method: 4 testing period: 21 days ambient conditions: 25 °C, 75 % r.h. air/volume change rate per hour: 3-6 sample not energized during exposure gas concentrations acc. ISA-S71.04.2013 Harsh Group A, G3 IEC 60721-3.3 acc. 3C2/3C3 - H2S ≥ 100 ± 10 ppb - SO2/SO3 ≥ 300 ± 20 ppb - Cl2 ≥ 100 ± 10 ppb - NOx ≥ 1250 ± 20 ppb
Isolation data				
Rated impulse withstand voltage U_{imp} (EN 50178)		input circuit / output circuit	4 kV (1.2/50 µs)	
		input circuit / PE	4 kV (1.2/50 µs)	
		input circuit / relay contact	4 kV (1.2/50 µs)	
		output circuit / relay contact	0.5 kV (1.2/50 µs)	
		relay contact / PE	0.5 kV (1.2/50 µs)	
		output circuit / PE	0.5 kV (1.2/50 µs)	
Rated insulation voltage U_i (EN 50178)		input circuit / output circuit	300 V	
		input circuit / PE	300 V	
		input circuit / relay contact	300 V	
		output circuit / relay contact	50 V	
		relay contact / PE	50 V	
		output circuit / PE	50 V	
Overvoltage category (EN 50178)		< 2000 m	III	
		2000…5000 m	II	
Overvoltage category (IEC/EN 60950-1)		< 2000 m	II	
		2000…5000 m	I	
Pollution degree			2	
Protective separation (IEC/EN 60950-1)		input circuit / output circuit	yes	
		input circuit / relay contact	yes	

CP-C.1 range
Technical data

Type		CP-C.1 24/10.0, CP-C.1 24/10.0-L	CP-C.1 24/10.0-C
Standards / Directives			
Standards		IEC/EN 61204	
Low Voltage Directive		2014/35/EU	
EMC Directive		2014/30/EU	
ATEX Directive		-	2014/34/EU
RoHS Directive		2011/65/EU	
Electrical safety		IEC/EN 60950-1	
Industrial control equipment / General Use Power Supplies		UL 508 / CSA 22.2 No 107.1	
Electronic equipment for use in power installations		EN 50178	
Protective extra low voltage		PELV (EN 50178)	
Safety extra low voltage		SELV (IEC/EN 60950-1)	
Limitation of harmonic line currents		IEC/EN 61000-3-2	
Electromagnetic compatibility			
Low-voltage power supplies, d.c. output – Part 3: Electromagnetic compatibility (EMC)		IEC/EN 61204-3	
Interference immunity to		IEC/EN 61000-6-2	
electrostatic discharge (ESD)	IEC/EN 61000-4-2	level 4, 8 kV / 15 kV (criterion A)	
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3, 10 V/m (criterion A)	
electrical fast transient / burst	IEC/EN 61000-4-4	level 4, 4 kV / 2 kV (criterion A)	
surge	IEC/EN 61000-4-5	level 4, L/N 2 kV (criterion A) level 4, L,N/PE 4 kV (criterion A)	
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3, 10 V (criterion A)	
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	class 3	
harmonics and interharmonics	IEC/EN 61000-4-13	class 3 (Criterion A)	
conducted, common mode disturbances in the frequency range 0 Hz to 150 kHz	IEC/EN 61000-4-16	level 3, 10 V	
Interference emission		IEC/EN 61000-6-3	
limits for harmonic current emissions	IEC/EN 61000-3-2	class A	
limitation of voltage changes etc.	IEC/EN 61000-3-3	compliant	
Information technology equipment radio disturbance characteristics limits and methods of measurement	IEC/CISPR 22, EN 55022	class B	
Industrial scientific and medical (ISM) radio-frequency equipment electromagnetic disturbance characteristics limits and methods of measurement	IEC/CISPR 11, EN 55011	class B	
Voltage sags	SEMI F47	passed	
Federal Communications Commission	FCC15	compliant	

CP-C.1 range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type			**CP-C.1 24/20.0, CP-C.1 24/20.0-L**	**CP-C.1 24/20.0-C**
Input circuit - Supply circuit				
			L (+), N (-)	
Rated input voltage U_{in}			100-240 V AC, 90-300 V DC	
Input voltage range		AC	85-264 V AC	
		DC	90-300 V DC	
Typical input current		at 115 V AC	4.6 A	
		at 230 V AC	2.3 A	
Typical power consumption		at 230 V AC	508 W	
Rated frequency			DC, 50/60 Hz	
Frequency range		AC	45-65 Hz	
Inrush current, cold state			< 11 A	
Let-through energy I^2t , cold state		at 230 V AC	< 3 A^2s	
Discharge current towards PE			< 3.5 mA	
Hold-up time		at 115 V AC	min. 40 ms	
		at 230 V AC	min. 40 ms	
Internal input fuse			T12 A, not exchangeable	
Recommended backup fuse for wire protection at 1.5 mm^2			1 pole miniature circuit breaker ABB type S 200	
		characteristic	B or C	
		max. rating	16 A	
Power factor correction (PFC)			yes, active	
Transient overvoltage protection			yes, varistor	
User interface				
Indication of operational states				
Output voltage	LED 'OUTPUT OK ' (green)	ON	92 % adjusted U_{out}	
		flashing	90 % adjusted U_{out}	
Power reserve	LED 'I > I_R' (yellow)	OFF	I ≤ I_R	
		ON	I > I_R	
Output circuit - Power output				
			L+, L-	
Rated output voltage			24 V DC	
Tolerance of the output voltage			± 1 %	
Adjustment range of the output voltage			22.5-28.5 V DC	
Rated output power			480 W	
Rated output current I_R		- 25 °C ≤ T_a ≤ 60 °C	20 A	-
		- 40 °C ≤ T_a ≤ 60 °C	-	20 A
Reserve output current		- 25 °C ≤ T_a ≤ 40 °C	26.0 A continuously	-
		- 40 °C ≤ T_a ≤ 60 °C	-	26.0 A continuously
Short-circuit current limiting			27.7 A	
Derating of the output current		60 °C < T_a ≤ 70 °C	2.5 %/°C	
Deviation width of output voltage	static output voltage deviaton 25-100 %		< 1 %, class C	
		dynamical 0-100 %	< 5 %, class B	
		change of input voltage within the rated input voltage	< 5 ms, class B	
Recovery time T_A			< 1 ms, class A	
Starting time after applying the supply voltage			< 500 ms, class C	
Rise time			< 10 ms	
Residual ripple and switching peaks		BW = 20 MHz	< 120 mV_{pp}, class A	
Parallel connection			yes, up to 5 devices, to enable redundancy and to increase power, current not symmetrical	
Series connection			yes, max. 2 devices to increase voltage	

CP-C.1 range
Technical data

Type		CP-C.1 24/20.0, CP-C.1 24/20.0-L	CP-C.1 24/20.0-C
No-load, overload and short-circuit behavior			
Characteristic curve of output		U/I characteristic curve with power reserve	
Short-circuit protection		continuous short-circuit stability	
Short-circuit behavior		current limiting	
Resistance to reverse feed		≤ 35 V DC	
Overload protection		constant current limitation	
Overtemperature protection		protection by switch off in case of overtemperature (thermal protection), automatic restart	
No-load protection		continuous no-load stability	
Starting of capacitive loads		yes	
Signaling outputs			
OUTPUT OK signaling output			
Type of output	13-14	relay, n/o contact	
ON (contact closed)		92 % adjusted U_{out}	
OFF (contact open)		90 % adjusted U_{out}	
Contact ratings	max. switching voltage / current	30 V AC - 0.5 A / 24 V DC - 1 A (resistive load)	
	min. switching voltage / current	5 V DC / 1 mA	
POWER RESERVE signaling output			
Type of output	$I > I_R$	transistor, short-circuit proof	
Active / ON (closed)		$I > I_R$	
Inactive / OFF (open)		$I \leq I_R$	
Ratings	voltage/current	24 V DC / ≤ 20 mA	
General data			
Efficiency	at rated output power	up to 94 %	
Power loss	at rated output power	28 W	
	at 50 % of rated output power	17 W	
	at no load	< 3.6 W	
Duty cycle		100 %	
MTBF	acc. to MIL 217 HDBK	on request	
Dimensions		see “Dimensional drawings”	
Material of housing	cover	zinc-coated sheet-steel	
	housing shell	aluminium	
	front	plastic, PA6, V-0	
Mounting		DIN rail (IEC/EN 60715), snap-on mounting	
Mounting position		see “Mounting positions” in the data sheet	
Minimum distance to other units	horizontal	25 mm (0.98 in)	
	vertical	25 mm (0.98 in)	
Degree of protection (IEC/EN 60529)	housing / terminals	IP20 / IP20	
Protection class (IEC/EN 61140)		I	
Electrical connection			
Input circuits (L(+), N(-), PE)			
Connecting capacity	rigid	0.5-4.0 mm² (20-10 AWG)	
	fine-strand with(out) wire end ferrule	0.5-2.5 mm² (20-12 AWG)	
Stripping length		8 mm (0.315 in)	
Tightening torque		0.5 Nm (4.4 lb.in)	
Recommended screw driver		PH1 / Ø 4.0 x 0.8 mm	

CP-C.1 range
Technical data


Type		CP-C.1 24/20.0, CP-C.1 24/20.0-L	CP-C.1 24/20.0-C
Output circuits (L+, L+, L-, L-)			
Connecting capacity	rigid	2.5-16.0 mm² (12-6 AWG)	
	fine-strand with(out) wire end ferrule	2.5-10 mm² (12-8 AWG)	
Stripping length		10 mm (0.394 in)	
Tightening torque		1.2 Nm (10.5 lb-in)	
Recommended screw driver		PH1 / Ø 4.0 x 0.8 mm	
Signaling output (13-14, I > IR)			
Connecting capacity	rigid	0.5-4.0 mm² (20-10 AWG)	
	fine-strand with(out) wire end ferrule	0.5-2.5 mm² (20-12 AWG)	
Stripping length		8 mm (0.315 in)	
Tightening torque		0.5 Nm (4.4 lb.in)	
Recommended screw driver		PH1 / Ø 4.0 x 0.8 mm	
Maximum cable length (applicable for $I>I_R$)		30 m	
Environmental data			
Ambient temperature range	operation	-25…+70 °C (-13...+158 °F)	-40…+70 °C (-40...+158 °F)
	rated output power	-25...+60 °C (-13...+140 °F)	-40...+60 °C (-40...+140 °F)
	storage	-40…+85 °C (-40...+185 °F)	
	transportation	-40…+85 °C (-40...+185 °F)	
Climatic class (IEC/EN 60721-3-1)	storage	1K2 (-40...+85 °C / -40...+185 °F)	
Climatic class (IEC/EN 60721-3-2)	transportation	2K2 (-40...+85 °C / -40...+185 °F)	
Climatic class (IEC/EN 60721-3-3)	operation	3K3 (-25…+70 °C / -13...+158 °F)	3K3 (-40…+70 °C / -40... +158 °F)
Damp heat, cyclic (IEC/EN 60068-2-30)		test Db: 55 °C, 2 cycles	
Vibration (IEC/EN 60068-2-6)		test Fc: 10-58 Hz, amplitude ±0.15 mm, 58-150 Hz, 2 g, 10 sweep cycles each axis	
Shock, half-sine (IEC/EN 60068-2-27)		test Ea: 30 g, 6 ms, 3 pulses each axis; bump 20 g, 11 ms, 100 pulses each axis	
Coated PCBA		no	yes
Gaseous corrosive environment withstand test (IEC/EN 60068-2-60)		-	testing method: 4 testing period: 21 days ambient conditions: 25 °C, 75 % r.h. air/volume change rate per hour: 3-6 sample not energized during exposure gas concentrations acc. ISA-S71.04.2013 Harsh Group A, G3 IEC 60721-3.3 acc. 3C2/3C3 - H2S ≥ 100 ± 10 ppb - SO2/SO3 ≥ 300 ± 20 ppb - Cl2 ≥ 100 ± 10 ppb - NOx ≥ 1250 ± 20 ppb

CP-C.1 range
Technical data


Type		**CP-C.1 24/20.0, CP-C.1 24/20.0-L**	**CP-C.1 24/20.0-C**
Isolation data			
Rated impulse withstand voltage U_{imp} (EN 50178)	input circuit / output circuit	4 kV (1.2/50 µs)	
	input circuit / PE	4 kV (1.2/50 µs)	
	input circuit / relay contact	4 kV (1.2/50 µs)	
	output circuit / relay contact	0.5 kV (1.2/50 µs)	
	relay contact / PE	0.5 kV (1.2/50 µs)	
	output circuit / PE	0.5 kV (1.2/50 µs)	
Rated insulation voltage U_i (EN 50178)	input circuit / output circuit	300 V	
	input circuit / PE	300 V	
	input circuit / relay contact	300 V	
	output circuit / relay contact	50 V	
	relay contact / PE	50 V	
	output circuit / PE	50 V	
Overvoltage category (EN 50178)	< 2000 m	III	
	2000…5000 m	II	
Overvoltage category (IEC/EN 60950-1)	< 2000 m	II	
	2000…5000 m	I	
Pollution degree		2	
Protective separation (IEC/EN 60950-1)	input circuit / output circuit	yes	
	input circuit / relay contact	yes	
Standards / Directives			
Standards		IEC/EN 61204	
Low Voltage Directive		2014/35/EU	
EMC Directive		2014/30/EU	
ATEX Directive		-	2014/34/EU
RoHS Directive		2011/65/EU	
Electrical safety		IEC/EN 60950-1	
Industrial control equipment / General Use Power Supplies		UL 508 / CSA 22.2 No 107.1	
Electronic equipment for use in power installations		EN 50178	
Protective extra low voltage		PELV (EN 50178)	
Safety extra low voltage		SELV (IEC/EN 60950-1)	
Limitation of harmonic line currents		IEC/EN 61000-3-2	
Electromagnetic compatibility			
Low-voltage power supplies, d.c. output – Part 3: Electromagnetic compatibility (EMC)		IEC/EN 61204-3	
Interference immunity to		IEC/EN 61000-6-2	
electrostatic discharge (ESD)	IEC/EN 61000-4-2	level 4, 8 kV / 15 kV (criterion A)	
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3, 10 V/m (criterion A)	
electrical fast transient / burst	IEC/EN 61000-4-4	level 4, 4 kV / 2 kV (criterion A)	
surge	IEC/EN 61000-4-5	level 4, L/N 2 kV (criterion A) level 4, L,N/PE 4 kV (criterion A)	
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3, 10 V (criterion A)	
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	class 3	
harmonics and interharmonics	IEC/EN 61000-4-13	class 3 (Criterion A)	
conducted, common mode disturbances in the frequency range 0 Hz to 150 kHz	IEC/EN 61000-4-16	level 3, 10 V	
Interference emission		IEC/EN 61000-6-3	
limits for harmonic current emissions	IEC/EN 61000-3-2	class A	
limitation of voltage changes etc.	IEC/EN 61000-3-3	compliant	
Information technology equipment radio disturbance characteristics limits and methods of measurement	IEC/CISPR 22, EN 55022	class B	
Industrial scientific and medical (ISM) radio-frequency equipment electromagnetic disturbance characteristics limits and methods of measurement	IEC/CISPR 11, EN 55011	class B	
Voltage sags	SEMI F47	passed	
Federal Communications Commission	FCC15	compliant	

CP-C.1 range
Technical diagrams


CP-C.1 24/5.0 , CP-C.1 24/5.0-L and CP-C.1 24/5.0-C




Typical efficiency over output current




Typical efficiency over AC input voltage



Typical efficiency over ambient temperature




Typical power loss over AC input voltage




Typical power loss over output current


CP-C.1 24/10.0, CP-C.1 24/10.0 -L and CP-C.1 24/10.0-C




Typical efficiency over output current




Typical efficiency over AC input voltage



Typical efficiency over ambient temperature




Typical power loss over AC input voltage




Typical power loss over output current

CP-C.1 range
Technical diagrams


CP-C.1 24/20.0, CP-C.1 24/20.0-L and CP-C.1 24/20.0-C




Typical efficiency over output current




Typical efficiency over AC input voltage



Typical efficiency over ambient temperature




Typical power loss over AC input voltage




Typical power loss over output current

CP-C.1 range
Technical diagrams


Characteristic curve of output at T_a = 25 °C



CP-C.1 24/5.0, CP-C.1 24/5.0-L
CP-C.1 24/5.0-C




CP-C.1 24/10.0, CP-C.1 24/10.0-L
CP-C.1 24/10.0-C




CP-C.1 24/20.0, CP-C.1 24/20.0-L
CP-C.1 24/20.0-C


Characteristic curve of temperature at U_{out} = 24 V




CP-C.1 24/5.0, CP-C.1 24/5.0-L




CP-C.1 24/10.0, CP-C.1 24/10.0-L




CP-C.1 24/20.0, CP-C.1 24/20.0-L



CP-C.1 24/5.0-C




CP-C.1 24/10.0-C



CP-C.1 24/20.0-C

CP-C.1 range
Technical diagrams

Dimensional drawings
Dimensions in **mm**, inches




OUTPUT ADJ.
DC LOW
DC ON
L N

Power supplies for building applications
Table of contents

314	CP-D range
314	Benefits and advantages
316	Operation controls
317	Applications
318	Ordering details
319	Technical data
323	Technical diagrams

CP-D range
Benefits and advantages



Thanks to its compact modular housing, the CP-D range is ideal for building applications and installation. For maximum flexibility in operation, six different versions are available, from 10 W up to 100 W. Their wide input voltage range allows their use in global applications.

Easy to install

The CP-D range is easy to adjust and ideally suited for installation in distribution panels due to its width being only 18 to 90 mm.

Global availability

The product can be used in any installation in the world. Giving you the confidence of worldwide sourcing – no matter where you build, install or operate your equipment.

Speed up your projects

Data available for common planning software: Less engineering time required.

CP-D range
Benefits and advantages


Characteristics
- Output voltages 12 V, 24 V DC
- Adjustable output voltages (devices > 10 W)
- Output currents 0.42 A / 0.83 A / 1.3 A / 2.1 A / 2.5 A / 4.2 A
- Power range 10 W, 25 W, 30 W, 60 W, 100 W
- Wide range input 100-240 V AC (90-264 V AC, 120-375 V DC)
- High efficiency of up to 89 %
- Low power dissipation and low heating
- Free convection cooling (no forced cooling with ventilators)
- Ambient temperature range during operation -40...+70 °C
- Open-circuit, overload and short-circuit stable
- Integrated input fuse
- LEDs for status indication
- Light-grey housing in RAL 7035
- Various approvals and marks

Main benefits

Adjustable output voltage
The CP-D range types > 10 W feature a continuously adjustable output voltage. Thus, they can be optimally adapted to the application, for example compensating the voltage drop caused by a long line length.

Wide range input
Optimized for world-wide applications: The CP-D power supplies can be supplied with 90-264 V AC or 120-375 V DC.

Width and structural form
With their width being only 18 to 90 mm, the CP-D range switch mode power supplies are ideally suited for installation in distribution panels.







CP-D range
Operation controls

OUTPUT Adjust:
potentiometer - adjustment of output voltage*)

OUTPUT ++/--:
terminals - output
12 V, 24 V



Indication of operational states
DC ON: green LED - output voltage applied
DC LOW: red LED - output voltage too low

Circuit diagram

INPUT L, N: terminals - input
90 ... 264 V AC
120 ... 375 V DC

*) only for devices > 10 W. 12 V version: 12...14 V DC, 24 V version: 24 ... 28 V DC.

CP-D range
Applications

Emergency lighting

Communication

Escalators

Elevators

LED lighting

Venetian blind drives













CP-D range
Ordering details



CP-D 12/0.83, CP-D 24/0.42



CP-D 12/2.1, CP-D 24/1.3



CP-D 24/2.5

Description

The CP-D range of modular power supply units in MDRC design (modular DIN rail components) is ideally suited for installation in distribution panels. This range offers devices with output voltages of 12 V DC and 24 V DC at output currents of 0.42 A to 4.2 A. Thanks to their high thermal efficiency, these power supplies have very low power and heat dissipation and can be operated without forced cooling. All power supply units in the CP-D range are approved according to all relevant international standards.

Ordering details

Input voltage range	Rated output voltage / current	Type	Order code	Weight (1 pc.) kg (lb)
90-264 V AC/ 120-375 V DC	12 V DC / 0.83 A	CP-D 12/0.83	1SVR427041R1000	0.06 (0.13)
90-264 V AC/ 120-375 V DC	12 V DC / 2.1 A	CP-D 12/2.1	1SVR427043R1200	0.19 (0.41)
90-264 V AC/ 120-375 V DC	24 V DC / 0.42 A	CP-D 24/0.42	1SVR427041R0000	0.06 (0.13)
90-264 V AC/ 120-375 V DC	24 V DC / 1.3 A	CP-D 24/1.3	1SVR427043R0100	0.19 (0.41)
90-264 V AC/ 120-375 V DC	24 V DC / 2.5 A	CP-D 24/2.5	1SVR427044R0200	0.25 (0.56)
90-264 V AC/ 120-375 V DC	24 V DC / 4.2 A	CP-D 24/4.2	1SVR427045R0400	0.32 (0.71)

CP-D range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-D 12/0.83	CP-D 12/2.1
Input circuit - supply circuit		**L, N**	
Rated input voltage U_{in}		100-240 V AC	
Input voltage range		90-264 V AC / 120-375 V DC	
Frequency range AC		47-63 Hz	
Typical input current / typical power consumption	at 115 V AC	200 mA / 12.68 W	502 mA / 31.14 W
	at 230 V AC	128.3 mA / 13.01 W	277 mA / 31.2 W
Inrush current	at 115 / 230 V AC	16 A / 32 A	25 A / 50 A
Power failure buffering time		min. 30 ms	
Internal input fuse		1 A slow-acting / 250 V AC	2 A slow-acting / 250 V AC
Power factor correction (PFC)		no	
Indication of operational states			
Output voltage	DC ON: green LED	⎍: output voltage applied	
	DC LOW: red LED	⎍: output voltage too low	
Output circuit		**+, -**	**++, --**
Rated output voltage		12 V DC	
Tolerance of the output voltage		±1 %	
Adjustment range of the output voltage		-	12-14 V DC
Rated output power		10 W	25 W
Rated output current I_r	$T_a \leq 60$ °C	0.83 A	2.1 A
Derating of the output current	60 °C < $T_a \leq$ 70 °C	2.5 %/°C	
Maximum deviation with	load change statical	max. 1 %	
	change of output voltage within the input voltage range	max. 1 %	
Recover time T_A		< 1 ms	
Starting time after applying the supply voltage	at I_r	1000 ms	
Rise time	at rated load	typ. 1 ms	
Residual ripple and switching peaks	BW = 20 MHz	50 mV	
Parallel connection		yes, using CP-D RU	
Series connection		yes, to increase voltage	
Resistance to reverse feed		18 V / 1 s	
Output circuit - No-load, overload and short-circuit behavior			
Characteristic curve of output		hiccup-mode	U/I characteristic curve
Short-circuit protection		continuous short-circuit stability	
Short-circuit behavior		continuation with output power limiting	
Current limiting at short circuit		typ. 1.4 A	typ. 5.9 A
Overload protection		output power limiting	
Overvoltage protection		15-16.5 V DC	
No-load protection		continuous no-load stability	
Starting of capacitive loads		unlimited	
General data			
Efficiency		typ. 78 %	typ. 82 %
Duty cycle		100 %	
Dimensions		see “Dimensional drawings”	
Material of housing		plastic	
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool	
Mounting position		horizontal	
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)	
Degree of protection	housing / terminals	IP20 / IP20	
Protection class		II	

CP-D range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-D 12/0.83	CP-D 12/2.1
Electrical connection - Input circuit / Output circuit			
Connecting capacity	fine-strand with wire end ferrule	0.2-1.5 mm² (24-16 AWG)	0.2-2.5 mm² (24-14 AWG)
	rigid	0.2-2.5 mm² (26-12 AWG)	0.2-2.5 mm² (24-12 AWG)
Stripping length		4-5 mm (0.16-0.2 in)	7 mm (0.28 in)
Tightening torque		0.6 Nm (5 lb.in)	0.7 Nm (6 lb.in)
Environmental data			
Ambient temperature range	operation	-40…+70 °C (-40...+158 °F)	
	rated load	-40…+60 °C (-40...+131 °F)	
	storage	-40…+85 °C (-40...+185 °F)	
Altitude during operation	IEC/EN 60068-2-13	max. 4850 m	
Damp heat (cyclic) (IEC/EN 60068-2-30)		4 x 24 cycles, 40 °C, 95 % RH	
Vibration (sinusoidal) (IEC/EN 60068-2-6)		50 m/s², 10 Hz - 2 kHz	
Shock (half-sine) (IEC/EN 60068-2-27)		40 m/s², 22 ms	
Isolation data			
Rated insulation voltage U_i	input circuit / output circuit	3 kV AC	
Pollution degree		2	
Overvoltage category		II	
Standards / Directives			
Standards		IEC/EN 60950-1	
Low Voltage Directive		2014/35/EU	
EMC Directive		2014/30/EU	
RoHS Directive		2011/65/EU	
Protective low voltage		SELV (IEC/EN 60950-1)	
Electromagnetic compatibility			
Interference immunity to		IEC/EN 61000-6-2	
electrostatic discharge	IEC/EN 61000-4-2	level 4 (4 kV / 8 kV)	level 4 (4 kV / 15 kV)
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)	
electrical fast transient/burst	IEC/EN 61000-4-4	level 4 (4 kV)	
surge	IEC/EN 61000-4-5	level 3 (2 kV L-L)	
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)	
Interference emission		IEC/EN 61000-6-3	
high-frequency radiated		class B	
high-frequency conducted		class B	

CP-D range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-D 24/0.42	CP-D 24/1.3	CP-D 24/2.5	CP-D 24/4.2
Input circuit - supply circuit		**L, N**			
Rated input voltage U_{in}		100-240 V AC			
Input voltage range		90-264 V AC /120-375 V DC			
Frequency range AC		47-63 Hz			
Typical input current / typical power consumption	at 115 V AC	184 mA / 11.62 W	600 mA / 37.92 W	1120 mA / 69.3 W	1800 mA / 117.3 W
	at 230 V AC	120.6 mA / 12 W	344 mA / 38.16 W	660 mA / 70.1 W	900 mA / 114.4 W
Inrush current	at 115 / 230 V AC	max. 16 A / 32 A	max. 25 A / 50 A	max. 30 A / 60 A	
Power failure buffering time		min. 30 ms		min. 60 ms	
Internal input fuse		1 A slow-acting / 250 V AC	2 A slow-acting / 250 V AC		3.15 A slow-acting / 250 V AC
Power factor correction (PFC)		no			
Indication of operational states					
Output voltage	DC ON: green LED	⎍: output voltage applied			
	DC LOW: red LED	⎍: output voltage too low			
Output circuit		**+, -**		**++, --**	
Rated output voltage		24 V DC			
Tolerance of the output voltage		±1 %			
Adjustment range of the output voltage		-	24-28 V DC		
Rated output power		10 W	30 W	60 W	100 W
Rated output current I_r		T_a ≤ 60 °C: 0.42 A	T_a ≤ 60 °C: 1.3 A	T_a ≤ 55 °C: 2.5 A	T_a ≤ 60 °C: 4.2 A
Derating of the output current		60 °C < T_a ≤ 70 °C: 2.5 %/°C	60 °C < T_a ≤ 70 °C: 2.5 %/°C	55 °C < T_a ≤ 70 °C: 2.5 %/°C	60 °C < T_a ≤ 70 °C: 2.5 %/°C
Maximum deviation with	load change statical	max. 1 %			
	change of output voltage within the input voltage range	max. 1 %			
Recover time T_A		< 1 ms			
Starting time after applying the supply voltage	at I_r	1000 ms			
Rise time	at rated load	typ. 1 ms			
Residual ripple and switching peaks	BW = 20 MHz	50 mV			
Parallel connection		yes, using CP-D RU			
Series connection		yes, to increase voltage			
Resistance to reverse feed		35 V / 1 s			
Output circuit - No-load, overload and short-circuit behavior					
Characteristic curve of output		hiccup-mode	U/I characteristic curve		
Short-circuit protection		continuous short-circuit stability			
Short-circuit behavior		continuation with output power limiting			
Current limiting at short circuit		typ. 0.78 A	typ. 4.2 A	typ. 6.05 A	typ. 11.5 A
Overload protection		output power limiting			
Overvoltage protection		30-33 V DC			
No-load protection		continuous no-load stability			
Starting of capacitive loads		unlimited			
General data					
Efficiency		typ. 80 %	typ. 83 %	typ. 86 %	typ. 89 %
Duty cycle		100 %			
Dimensions		see “Dimensional drawings”			
Material of housing		plastic			
Mounting		DIN rail (IEC/EN 60715), snap-on mounting without any tool			
Mounting position		horizontal			
Minimum distance to other units	horizontal / vertical	25 mm / 25 mm (0.98 in / 0.98 in)			
Degree of protection	housing / terminals	IP20 / IP20			
Protection class		II			


CP-D range
Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated


Type		CP-D 24/0.42	CP-D 24/1.3	CP-D 24/2.5	CP-D 24/4.2
Electrical connection - Input circuit / Output circuit					
Connecting capacity	fine-strand with wire end ferrule	0.2-1.5 mm² (24-16 AWG)	0.2-2.5 mm² (24-14 AWG)		
	rigid	0.2-2.5 mm² (26-12 AWG)	0.2-2.5 mm² (24-12 AWG)		
Stripping length		4-5 mm (0.16-0.2 in)		7 mm (0.28 in)	
Tightening torque		0.6 Nm (5 lb.in)		0.7 Nm (6 lb.in)	
Environmental data					
Ambient temperature range	operation	-40…+70 °C			
	rated load	-40…+60 °C		-40…+55 °C	-40…+60 °C
	storage	-40…+85 °C			
Altitude during operation	IEC/EN 60068-2-13	max. 4850 m			
Damp heat (cyclic) (IEC/EN 60068-2-30)		4 x 24 cycles, 40 °C, 95 % RH			
Vibration (sinusoidal) (IEC/EN 60068-2-6)		50 m/s², 10 Hz - 2 kHz			
Shock (half-sine) (IEC/EN 60068-2-27)		40 m/s², 22 ms			
Isolation data					
Rated insulation voltage U_i	input circuit / output circuit	3 kV AC		4 kV AC	3 kV AC
Pollution degree		2			
Overvoltage category		II			
Standards / Directives					
Standards		IEC/EN 60950-1			
Low Voltage Directive		2014/35/EU			
EMC Directive		2014/30/EU			
RoHS Directive		2011/65/EU			
Protective low voltage		SELV (IEC/EN 60950-1)			
Electromagnetic compatibility					
Interference immunity to		IEC/EN 61000-6-2			
electrostatic discharge	IEC/EN 61000-4-2	level 4 (4 kV / 8 kV)	level 4 (4 kV / 15 kV)		level 4 (4 kV / 8 kV)
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)			
electrical fast transient/burst	IEC/EN 61000-4-4	level 4 (4 kV)			
surge	IEC/EN 61000-4-5	level 3 (2 kV L-L)			
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)			
Interference emission		IEC/EN 61000-6-3			
high-frequency radiated		class B			
high-frequency conducted		class B			

CP-D range
Technical diagrams


Characteristic curve of output at T_a = 25 °C




CP-D 12/0.83




CP-D 12/2.1




CP-D 24/0.42



CP-D 24/1.3




CP-D 24/2.5




CP-D 24/4.2

Characteristic curve of temperature at rated output voltage




CP-D except CP-D 24/2.5




CP-D 24/2.5

CP-D range
Technical diagrams


Dimensional drawings
Dimensions in mm




CP-D 12/0.83, CP-D 24/0.42



CP-D 12/2.1, CP-D 24/1.3



CP-D 24/2.5



CP-D 24/4.2


CP-B EXT.2
CP-B 24/3.0
CP-B 24/10.0
CP-B 24/20.0

CP-B range
Table of contents

328 Benefits and advantages

330 Operation controls

331 Applications

332 Ordering details

333 Technical data

336 Technical diagrams

CP-B range
Benefits and advantages



ABB's ultra-capacitor based CP-B buffer modules serve to ensure a short-term uninterrupted power supply system with a voltage of 24 V DC by buffering the load in case of power loss.

The buffer modules feature a technology for storing energy: the use of ultra-capacitors obviates the need for maintenance and exempts deep discharge in comparison to batteries.

Energy storage can be expanded with additional extension modules for longer buffering times and is therefore extremely adaptable.

24/7
Continuous operation

- Buffering 24 V DC supply of up to 380 s
- Maintenance-free, ultra-capacitor technology
- Temperature resistant
- No deep charge
- Small footprint

CP-B range
Benefits and advantages

Power supply systems have to be highly reliable in most areas of energy management and automation technology. Often, batteries are used for supporting the supply system in case of mains failures. Batteries have limited lifetimes depending on environmental parameters and have to be maintained regularly, which causes extra work and costs.

Using the ultra-capacitor technology, ABB offers an innovative and completely maintenance-free new product for buffering the 24 V DC supply in case of interrupted mains on the primary side of the switch mode power supply.

The CP-B range is an ultra-capacitor buffer energy storage system for power supply units which ensures a short term uninterrupted power supply system. In case of power loss, the energy stored in the capacitor guarantees that the load is continually provided for up to several hundred seconds depending on the load current.



Characteristics
- 3 buffer modules for buffering 24 V DC:
  CP-B 24/3.0 (3 A / 1 kWs[1])
  CP-B 24/10.0 (10 A / 10 kWs[1])
  CP-B 24/20.0 (20 A / 8 kWs[1])
- CP-B 24/3.0 and CP-B 24/20.0 expandable with additional extension module(s)
  CP-B EXT.2 (2 kWs[1])
- LEDs for status indication
- Relay contacts for status messaging
- Very high backup times (e.g. with CP-B 24/10.0 up to 8 minutes at 1 A load current)
- Short charging times
- High efficiency, higher than 90 %
- Wide temperature range
- DIN rail mountable, compact housing
- Extended temperature range -40...60 °C


[1] internal energy buffer

		CP-B 24/3.0	CP-B 24/10.0	CP-B 24/20.0	CP-B EXT.2
Order code		1SVR427060R0300	1SVR427060R1000	1SVR427060R2000	1SVR427065R0000
Rated input voltage		24 V DC	24 V DC	24 V DC	–
Rated current		3 A DC	10 A DC	20 A DC	3 A DC
Energy storage (min.)		1.000 Ws	10.000 Ws	8.000 Ws	2.000 Ws
Typical charging time at load current	100 %	65 s	134 s	135 s	
	0 %	56 s	82 s	62 s	
Typical buffering time[1] at load current	100 %	13 s	38 s	15 s	
	50 %	28 s	76 s	30 s	
	25 %	66 s	140 s	60 s	
	10 %	148 s	380 s	150 s	

[1] buffering time $\approx \frac{\text{energy storage x 0.9}}{\text{current x output voltage}}$

CP-B range
Operation controls

Input terminals
SHUT-DOWN+,
SHUT-DOWN-:
Input signal terminals
INPUT OK,
BUFFER STATUS,
FAILURE:
Signalling contact – terminals
$L+_{IN}$, $L-_{IN}$: Input voltage terminals




Indication of operational states
OPERATION:
Buffer module in operation (standby or buffering)
INPUT OK:
Input voltage applied

Output terminals
$L+_{OUT}$, $L-_{OUT}$, $L-_{OUT}$:
Output voltage terminals

CP-B range
Applications

Example of application



CP-B range
Ordering details


2CDC 271 001 S0010

CP-B 24/3.0


2CDC 271 002 S0010

CP-B 24/10.0


2CDC 271 003 S0010

CP-B 24/20.0

Description

Ultra capacitor based buffer units of the CP-B range offer the highest reliability also in harsh environments. Thanks to their ultra-cap based technology, the units are maintenance free, there will be no deep discharge and these products offer a very wide operational ambient temperature range. CP-B range buffer units are an excellent solution for avoiding voltage drops in solar applications, for example.

Ordering details

Rated input voltage	Rated current	Type	Order code	Weight (1 pc.) kg (lb)
24 V DC	3 A DC	CP-B 24/3.0	1SVR427060R0300	0.59 (1.31)
	10 A DC	CP-B 24/10.0	1SVR427060R1000	2.10 (4.63)
	20 A DC	CP-B 24/20.0	1SVR427060R2000	2.20 (4.85)

Ordering details - Extension unit for CP-B 24/3.0 and CP-B 24/20.0

Rated voltage	Voltage range	Type	Order code	Weight (1 pc.) kg (lb)
24 V DC	0-26.4 V DC	CP-B EXT.2	1SVR427065R0000	1.04 (2.30)

CP-B range
Technical data

Type		CP-B 24/3.0	CP-B 24/10.0	CP-B 24/20.0
Input circuit - Supply circuit		**$L+_{IN}$ $L-_{IN}$**		
Rated input voltage U_{in}		24 V DC		
Input voltage range		23.7-26.4 V DC	23.9-27 V DC	23.4-29 V DC
Minimum charging potential		23.7 V DC	23.9 V DC	23.4 V DC
Rated input current		3 A DC	10 A DC	20 A DC
Inrush current limiting		50 A / 1 ms	35 A / 2 ms	35 A / 2 ms
Transient overvoltage protection		suppressor diode	varistor / suppressor diode	varistor / suppressor diode
Internal input fuse (apparatus protection, not accessible)		4 A slow acting	15 A (FK2)	30 A (FK2)
Internal fuse capacitors circuit (not accessible)			25 A (FK2)	
Kind of input	SHUT-DOWN	-	control input	control input
	rated voltage	-	24 V DC	24 V DC
	voltage range	-	6-45 V DC	6-45 V DC
Output circuit		**$L+_{OUT}$ $L-_{OUT}$ $L-_{OUT}$**		
Rated output power		69 W	240 W	480 W
Rated output voltage U_{out}		24 V DC		
Output voltage (buffer mode)		23.0 V DC	23.2 V DC	23.2 V DC
Tolerance of the output voltage		+2...-10 %		
Rated output current I_r	$T_a \leq 60$ °C	3 A DC	10 A DC	20 A DC
Peak output current (fully loaded capacitors required)	$T_a \leq 60$ °C	6 A DC (min. 1.5 s)	20 A DC (10 A power supply + 10 A CP-B, min. 1.5 s)	40 A DC (min. 1.5 s)
Control of limiting current		-	10.3 A DC ±0.1A	-
Shut-down if limiting current is exceeded		-	after 1.5 s	-
Short-circuit protection (only via external fuse)		no continuous short-circuit stability		
Internal output fuse (not accessible)		-	15 A (FK2)	-
Required external fuse		3.15 A slow acting	10 A slow acting	25 A slow acting
Current limiting at output circuit		-	1.05...1.2 x I_r	-
Breaking capacity of output circuit	t= 2.5 ms	-	24 V DC, 10 A	-
Power failure buffering time [1]		load-dependent, min. 13 s at 100 % load	load-dependent, min. 38 s at 100 % load	load-dependent, min. 15 s at 100 % load
Overload protection		thermal protection		
Kind of output	INPUT OK	n/o contact		
	BUFFER STATUS	-	n/o contact	
	FAILURE	-	c/o contact	
Contact material		Ag + Au-clad		
Minimum switching voltage / Minimum switching current		5 V DC / 1 mA		
Maximum switching voltage / Maximum switching current		50 V AC / 1.0 A, 30 V DC / 0.5 A		
Mechanical lifetime		5 x 10^6 switching cycles		
Electrical lifetime		0.1 x 10^6 switching cycles		
Maximum fuse rating to achieve short-circuit protection	n/o or n/c contact	1.0 A AC / 0.5 A DC		

CP-B range
Technical data

Type			CP-B 24/3.0	CP-B 24/10.0	CP-B 24/20.0
General data					
Maximum internal power consumption			7 W	20 W	40 W
Power consumption with unloaded output			0.75 W	3 W	1.6 W
Energy storage (min.)			1000 Ws	10000 Ws	8000 Ws
Typical charging time at load current		100 %	65 s	134 s	135 s
		0 %	56 s	82 s	62 s
Typical buffering time at load current[1)]		100 %	13 s	38 s	15 s
		50 %	28 s	76 s	30 s
		25 %	66 s	140 s	60 s
		10 %	148 s	380 s	150 s
Efficiency			> 90 %		
Dimensions			see “Dimensional drawings”		
Material		cover / housing shell	steel sheet powdered		
Mounting			DIN rail (IEC/EN 60715), snap-on mounting		
Mounting position			horizontal		
Minimum distance to other units		horizontal	not necessary		
		vertical	40 mm (1.58 in)		80 mm (3.15 in)
Pollution degree			2		
Degree of protection		housing / terminal	IP20		
Protection class (IEC/EN 61140)			III SELV / PELV (condition: power supply fulfills class III)		
Electrical connection - Input circuit / Output circuit			**pull spring terminals**	**pull spring terminals**	**pluggable screw type terminals**
Connecting capacity	fine-strand with(out) wire end ferrule		0.08-1.0 mm² (28-18 AWG)	0.08-1.5 mm² (28-18 AWG)	0.2-4.0 mm² (24-12 AWG)
		rigid	0.08-1.5 mm² (28-16 AWG)	0.08-4.0 mm² (28-16 AWG)	0.2-6.0 mm² (24-10 AWG)
Stripping length			6.0 mm (0.24 in)		7.0 mm (0.28 in)
Signaling circuit					
Connecting capacity	fine-strand with(out) wire end ferrule		0.08-1.0 mm² (28-18 AWG)		0.14-1.0 mm² (26-16 AWG)
		rigid	0.08-1.5 mm² (28-16 AWG)		0.14-1.5 mm² (28-16 AWG)
Stripping length			6.0 mm (0.24 in)		7.0 mm (0.28 in)
Environmental data					
Ambient temperature		operation	-40...+60 °C		
		storage	-40...+60 °C		
Standards / Directives					
Standards			EN 50178, IEC/EN 60950-1, IEC/EN 62040-2		
Low Voltage Directive			2014/35/EU		
EMC Directive			2014/30/EU		
RoHS Directive			2011/65/EC		
Electromagnetic compatibility					
Interference immunity to			IEC/EN 61000-6-2		
electrostatic discharge		IEC/EN 61000-4-2	level 3, 6 kV / 8 kV		
radiated, radio-frequency, electromagnetic field		IEC/EN 61000-4-3	level 3, 10 V/m (27-1000 MHz) / level 2, 3 V/m (1400-2700 MHz)		
electrical fast transient/burst		IEC/EN 61000-4-4	level 3, 2(1) kV / 5 kHz		
surge		IEC/EN 61000-4-5	level 1, 0.5 kV		
conducted disturbances, induced by radio-frequency fields		IEC/EN 61000-4-6	level 3, 10 V (150 kHz-80 MHz)		
voltage dips, short interruptions and voltage variations		IEC/EN 61000-4-11	buffered by ultra-capacitors		
Interference emission			EN 61000-6-4		
high-frequency radiated		DIN EN 55011	B/C1		
high-frequency conducted		DIN EN 55011	B/C1		

[1)] buffering time ≈ $\frac{\text{energy storage x 0.9}}{\text{current x output voltage}}$


CP-B range
Technical data

Data at T_a = 25 °C and rated values, unless otherwise indicated


Type		CP-B EXT 2.0
Extension circuit		**EXT+ EXT+ EXT- EXT-**
Rated voltage		24 V DC
Voltage range		0-26.4 V DC
Rated current		3 A DC
Internal input fuse (apparatus protection, not accessible)		4 A slow acting (PTC)
Short-circuit protection		via internal 3 A fuse
Overload protection		only in combination with CP-B 24/3.0 or CP-B 24/20.0
Indication of operational states		
		status information and fault messages of the buffer module apply
General data		
Power consumption without load		0.5 W
Energy storage (min.)		2000 Ws
Material	cover / housing shell	steel sheet powdered
Mounting		DIN rail (IEC/EN 60715), snap-on mounting
Mounting position		horizontal
Minimum distance to other units	horizontal	not necessary
	vertical	40 mm (1.58 in)
Pollution degree		2
Degree of protection	housing / terminal	IP20
Protection class (IEC/EN 61140)		III SELV / PELV (condition: power supply fulfills class III)
Electrical connection - Extension circuit		pull spring terminals
Connecting capacity	fine-strand with(out) wire end ferrule	0.08-1.0 mm² (28-18 AWG)
	rigid	0.08-1.5 mm² (28-16 AWG)
Stripping length		6.0 mm (0.24 in)
Environmental data		
Ambient temperature	operation	-40...+60 °C
	storage	-40...+60 °C
Vibration, sinusoidal	IEC/EN 60068-2-6	1.5 mm, 3-57.55 Hz; 2 g, 57.55-500 Hz, 10 cycles
Shock, half-sine	IEC/EN 60068-2-27	15 g, 11 ms, 3 axes, 6 faces, 3 times for each face
Standards / Directives		
Standards		EN 50178, IEC/EN 60950-1, IEC/EN 62040-2
Low Voltage Directive		2014/35/EU
EMC Directive		2014/30/EU
RoHS Directive		2011/65/EU
Electromagnetic compatibility		
Interference immunity to		IEC/EN 61000-6-2
electrostatic discharge	IEC/EN 61000-4-2	level 3, 6 kV / 8 kV
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3, 10 V/m (27-1000 MHz) / level 2, 3 V/m (1400-2700 MHz)
electrical fast transient/burst	IEC/EN 61000-4-4	level 3, 2(1) kV / 5 kHz
surge	IEC/EN 61000-4-5	level 1, 0.5 kV
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3, 10 V (150 kHz-80 MHz)
voltage dips, short interruptions and voltage variations	IEC/EN 61000-4-11	buffered by ultra-capacitors
Interference emission		EN 61000-6-4
high-frequency radiated	DIN EN 55011	B/C1
high-frequency conducted	DIN EN 55011	B/C1

CP-B range
Technical diagrams


Characteristic curve of the temperature at rated load



CP-B 24/3.0



CP-B 24/10.0




CP-B 24/20.0

A Normal application (up to 50 % buffer mode, 5 charging and discharging cycles in direct series)


B Continuous charging and discharging in direct series. As this is not typical of a real application, this should be considered as theoretical indication

Capacitors life span over temperature




CP-B range
Technical diagrams


Dimensional drawings
Dimensions in **mm**, inches




CP-B 24/3.0



CP-B EXT.2



CP-B 24/10.0



CP-B 24/20.0


INPUT 1
INPUT 2
CP-C.1-A-RU
OUTPUT
IN1
IN2
IN1 IN2
CP-D RU
OUT
U1+
U-
U2+
CP-RUD

Redundancy units
Table of contents

341 **Benefits and advantages**

342 **Ordering details**

343 **Technical data**

347 **Technical diagrams**

Establish true redundancy where it really matters with ABB's power supply redundancy units.



Redundancy units
Benefits and advantages



ABB's redundancy units are used to establish true redundancy, which increases the availability of electrical systems significantly. Three versions are available with different output currents and power supply housings:

- CP-D RU in MDRC housing
- CP-RUD for a true redundant setup of two 24 V DC power supplies with a max. output current of 2.5 A per channel
- CP-C.1-A-RU for a true redundant setup of two 24 V DC power supplies of the CP range

24/7

Continuous operation

Highest system reliability
- Redundancy setup of the application possible to allow parallel operation
- Long lifetime

Redundancy units
Ordering details



CP-C.1-A-RU



CP-C.1-A-RU-L



CP-D RU



CP-RUD

Description

Whenever the highest availability and reliability are key requirements, a true redundancy setup with two power supplies connected to a redundancy unit is the best solution. In case one power supply fails, the other one keeps supplying the load. Furthermore, even a short circuit in one power supply will not affect the other one, which keeps supplying the load. The CP-C.1-A-RU is also available with coated PCBA (CP-C.1-A-RU-C) for harsh environments.

Ordering details - CP-C.1-A-RU for decoupling of CP power supplies up to 20 A per input / channel

Input voltage range	Rated input current per channel	Rated output voltage / current		Type	Order code	Weight (1 pc.) kg (lb)
10 - 28.5 V DC	20 A	24 V DC / 2 x 20 A or 1 x 40 A	uncoated	CP-C.1-A-RU	1SVR360060R1001	1.04 (2.29)
			coated	CP-C.1-A-RU-C	1SVR360060R2001	1.04 (2.29)
			uncoated	CP-C.1-A-RU-L	1SVR361060R1001	1.04 (2.29)

Ordering details - CP-D RU for decoupling of two CP-D power supply units

Input voltage range	Rated input current	Rated output voltage / current	Type	Order code	Weight (1 pc.) kg (lb)
9-35 V DC	2 x 5 A	24 V DC / 1 x 10 A	CP-D RU	1SVR427049R0000	0.075 (0.165)

Ordering details - CP-RUD for decoupling of two CP-E power supply units ≤ 35 V and < 5 A

Input voltage range	Rated input current	Rated output voltage / current	Type	Order code	Weight (1 pc.) kg (lb)
5-35 V DC	0.5 - 2.5 A	24 V DC / 5 A	CP-RUD	1SVR423418R9000	0.088 (0.195)

Redundancy units

Technical data

Data at T_a = 25 °C, U_{in} = 230 V AC and rated values, unless otherwise indicated

Type		CP-C.1-A-RU, CP-C.1-A-RU-L	CP-C.1-A-RU-C
Input circuit - Supply circuit		**(+/+, -/-)**	
Rated input voltage U_{in}		24 V DC	
Input voltage range		10-28.5 V DC	
Rated input current I_{in} per channel	-25 °C ≤ T_a ≤ 60 °C	20 A	
Maximum input current per channel	-25 °C ≤ T_a ≤ 40 °C	30 A	
	-40 °C ≤ T_a ≤ 40 °C	-	30 A
Transient overvoltage protection		yes, varistor	
Output circuit		**(++/--)**	
Rated output voltage U_{out}		24 V DC	
Voltage drop input/output		typ. 0.6 V, max. 0.9 V	
Rated output current I_r	-25 °C ≤ T_a ≤ 60 °C	2 x 20 A or 1 x 40 A	
Max. output current (Power reserve)	-25 °C ≤ T_a ≤ 40 °C	2 x 30 A or 1 x 60 A	
	-40 °C ≤ T_a ≤ 40 °C	-	2 x 30 A or 1 x 60 A
Derating of the output current	60 °C < T_a ≤ 70 °C	2.5 % per Kelvin temperature increase	
Resistance to reverse feed		< 60 V	
General data			
Power loss	input 2 x 20 A	23.0 W	
	input 2 x 10 A	9.4 W	
	input 2 x 5 A	4.1 W	
MTBF	acc. to MIL 217 HDBK	on request	
Dimensions		see "Dimensional drawings"	
Material of housing	cover / housing shell / front	aluminium / zinc-coated sheet steel / plastic	
Mounting		DIN rail (IEC/EN 60715), snap-on mounting	
Mounting position		1 and 7	
Minimum distance to other units	horizontal / vertical	25 mm (0.98 in) / 25 mm (0.98 in)	
Degree of protection (IEC/EN 60529)	housing / terminals	IP20 / IP20	
Protection class (IEC/EN 61140)		III	
Electrical connection - Input circuit / Output circuit			
Connecting capacity	fine-strand with(out) wire end ferrule	2.5-10 mm² (12-8 AWG)	
	rigid	2.5-16 mm² (12-6 AWG)	
Stripping length		10 mm (0.39 in)	
Tightening torque		1.2 Nm (10.5 lb.in)	
Recommended screw driver		PH1 / Ø 4.0 x 0.8 mm (0.16 x 0.03 in)	

Redundancy units

Technical data

Type		CP-C.1-A-RU, CP-C.1-A-RU-L	CP-C.1-A-RU-C
Environmental data			
Ambient temperature range	operation	-25…+70 °C (-13… +158 °F)	-40…+70 °C (-40…+158 °F)
	rated load	-25…+60 °C (-13… +140 °F)	-40…+60 °C (-40…+140 °F)
	storage	-40…+85 °C (-40…+185 °F)	
	transportation	-40…+85 °C (-40…+185 °F)	
Climatic class (IEC/EN 60721-3-1)	storage	1K2 (-40…+85 °C / -40…+185 °F)	
Climatic class (IEC/EN 60721-3-2)	transportation	2K2 (-40…+85 °C / -40…+185 °F)	
Climatic class (IEC/EN 60721-3-3)	operation	3K3 (-25…+70 °C / -13…+158 °F)	3K3 (-40…+70 °C / -40…+158 °F)
Damp heat, cyclic (IEC/EN 60068-2-30)		test Db: 55 °C, 2 cycles	
Vibration (IEC/EN 60068-2-6)		test Fc: 10-58 Hz, amplitude ±0.15 mm, 58-150 Hz, 2 g, 10 sweep cycles each axis	
Shock, half-sine (IEC/EN 60068-2-27)		test Ea: 30 g, 6 ms, 3 pulses each axis; bump 20 g, 11 ms, 100 pulses each axis	
Coated PCBA		no	yes
Gaseous corrosive environment withstand test (IEC/EN 60068-2-60)		-	testing method: 4 testing period: 21 days ambient conditions: 25 °C, 75 % r.h. air/volume change rate per hour: 3-6 sample not energized during exposure gas concentrations acc. ISA-S71.04.2013 Harsh Group A, G3 IEC 60721-3.3 acc. 3C2/3C3 - H2S ≥ 100 ± 10 ppb - SO2/SO3 ≥ 300 ± 20 ppb - Cl2 ≥ 100 ± 10 ppb - NOx ≥ 1250 ± 20 ppb
Isolation data			
Rated impulse withstand voltage U_{imp} (EN 50178)	input / housing	1.5 kV (1.2/50 µs)	
	output / housing	1.5 kV (1.2/50 µs)	
Pollution degree		2	
Standards / Directives			
Standards		IEC/EN 61204	
EMC Directive		2014/30/EU	
ATEX Directive		-	2014/34/EU
RoHS Directive		2011/65/EU	
Electrical safety		IEC/EN 60950-1	
Industrial control equipment / General Use Power Supplies		UL 508 / CSA 22.2 No 107.1	
Electromagnetic compatibility			
Interference immunity to			
electrostatic discharge	IEC/EN 61000-4-2	Level 4, contact discharge ±8 kV, air discharge ±15 kV (criterion B)	
electrical fast transient / burst	IEC/EN 61000-4-4	Level 3, DC mains inputs and output ±2 kV (criterion B)	
surge	IEC/EN 61000-4-5	Level 1, DC mains inputs and output ±0.5 kV, input and output vs. PE ±1 kV (criterion B)	

Redundancy units
Technical data

Type		CP-D RU
Input circuit - Supply circuit		**IN 1 + + -, IN 2 + + -**
Rated input voltage U_{in}		24 V DC
Input voltage range		9-35 V DC
Rated input current I_{in} per channel		5 A
Maximum input current per channel		10 A for 300 s
Transient overvoltage protection		no
Output circuit		**OUT + + +, - - -**
Rated output voltage U_{out}		24 V DC
Voltage drop		typ. 0.5 V
Rated output current I_{out}		10 A
Resistance to reverse feed		< 35 V
General data		
MTBF		on request
Duty cycle		100 %
Dimensions		see “Dimensional drawings”
Material of housing		plastic
Mounting		DIN rail, snap-on mounting without any tool
Mounting position		1, 7
Minimum distance to other units	horizontal / vertical	25 mm (0.98 in) / 25 mm (0.98 in)
Electrical connection - Input circuit / Output circuit		
Connecting capacity	fine-strand with (out)wire end ferrule	0.2-2.5 mm² (24-14 AWG)
	rigid	0.2-2.5 mm² (24-12 AWG)
Stripping length		7.0 mm (0.28 in)
Tightening torque		0.67 Nm (6 lb.in)
Environmental data		
Ambient temperature range	operation	-40...+70 °C
	storage	-40...+85 °C
Relative humidity	RH at 40 °C	20-95 %, no condensation
Vibration (IEC/EN 60068-2-6)		mounting by rail: 10-500 Hz, 2 G, along X, Y, Z each axis, 60 min for each axis
Shock (IEC/EN 60068-2-27)		15 G, 11 ms, 3 axis, 6 faces, 3 times for each face
Standards / Directives		
Standards		IEC/EN 61204-3, IEC/EN 60950-1
RoHS Directive		2011/65/EU
Electromagnetic compatibility		
Interference immunity to		EN 55024
electrostatic discharge	IEC/EN 61000-4-2	level 3, air discharge 8 kV, contact discharge 4 kV
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3, 10 V/m
electrical fast transient/burst	IEC/EN 61000-4-4	level 3, 2 kV / 5 kHz
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3, 10 V
Interference emission		EN 55022
high-frequency radiated	IEC/CISPR 22 / EN 55022	class B
high-frequency conducted	IEC/CISPR 22 / EN 55022	class B


Redundancy units

Technical data


Type		CP-RUD
Input circuit - Supply circuit		**A: U1+/-U ; B: U2+/-U**
Rated input voltage U_{in}		24 V DC
Input voltage range		5-35 V DC
Rated input current I_{in} per channel		0.5-2.5 A
Maximum input current per channel		10 A for 300 s
Transient overvoltage protection		no
Output circuit		**L+, L+, L+, L-, L-, L-**
Rated output voltage U_{out}		24 V DC
Voltage drop		typ. 0.6 V, max. 0.7 V
Rated output current I_{out}		0.5-5 A
Peak output current		20 A for 150 s
Resistance to reverse feed		< 35 V
General data		
Dimensions		see “Dimensional drawings”
Minimum distance to other units	horizontal / vertical	10 mm / 10 mm (0.39 in / 0.39 in)
Degree of protection	housing / terminals	IP20 / IP20
Material of housing	housing shell / cover	plastic / plastic
Protection class		-
Mounting		DIN rail (IEC/EN 60715)
Mounting position		horizontal
Electrical connection - Input circuit / Output circuit		
Connecting capacity	fine-strand with wire end ferrule	2 x 0.75-2.5 mm² (2 x 18-14 AWG)
	fine-strand without wire end ferrule	
	rigid	2 x 0.5-4 mm² (2 x 20-12 AWG)
Stripping length		7 mm (0.28 in)
Tightening torque		0.6-0.8 Nm
Environmental data		
Ambient temperature range	operation	-20...+60 °C
	rated load	-20...+60 °C
	storage	-40...+85 °C
Damp heat (IEC/EN 60068-2-3)		93 % at 40 °C, no condensation
Isolation data		
Insulation voltage	input / output / housing	-
Pollution degree (EN 50178)		2
Standards / Directives		
Electrical safety		EN 50178
RoHS Directive		2011/65/EU
Electromagnetic compatibility		
Interference immunity to		IEC/EN 61000-6-2
electrostatic discharge	IEC/EN 61000-4-2	level 3 (air discharge ±8 kV, contact discharge ±6 kV)
radiated, radio-frequency, electromagnetic field	IEC/EN 61000-4-3	level 3 (10 V/m)
electrical fast transient/burst	IEC/EN 61000-4-4	level 3 (±2 kV)
surge	IEC/EN 61000-4-5	level 1 (±0.5 kV)
conducted disturbances, induced by radio-frequency fields	IEC/EN 61000-4-6	level 3 (10 V)
Interference emission		IEC/EN 61000-6-3
high-frequency radiated		class B
high-frequency conducted		class B

Redundancy units
Technical diagrams


Dimensional drawings
Dimensions in **mm**, inches




CP-C.1-A-RU, CP-C.1-A-RU-L
CP-C.1-A-RU-C



CP-D RU




CP-RUD


ABB
Elektronisches Schutzgerät
Electronic Protection Device
EPD24-TB-101-4A-24VDC
Made in Germany
1140
UL-2367
UL-1604
Class 1 Div2
GP 2.10
cULus
LINE+
LOAD+
DV
ok
on
off
reset
3A
3A
4A
6A
4A

Electronic protection devices EPD24
Table of contents

350 Benefits and advantages
351 Applications
352 Ordering details
353 Operating data
354 Technical data
355 Technical information
356 Technical diagrams
357 Approvals, Safety instructions
358 Installation guidelines

Electronic protection devices EPD24
Benefits and advantages



With its narrow width of only 12.5 mm, EPD24 can fit everywhere – it can even be mounted side-by-side.

Its adjustable and fixed current ratings, projectable protection through current limitation as well as a single trip curve for all types of loads allow for use in a wide field of applications.



Continuous operation

Highlights
- Safety and reliability
- Operational continuity
- Worldwide use thanks to relevant certifications
- Compact and effective

Electronic protection devices EPD24
Applications

Features
- Selective load protection, one electronic tripping characteristic.
- Active current limitation for safe connection of capacitive loads up to 20,000 µF and on overload/short circuit
- Current ratings 0.5...12 A
- Reliable overload disconnection with 1.1 x I_N
- Manual ON/OFF button
- Clear status and failure indication through LED and integrated auxiliary contact
- Integral fail-safe element adjusted to current rating
- Width per unit only 12.5 mm
- Rail mounting
- Ease of wiring through busbar LINE+ and 0 V as well as signal bars
- UL- and CSA-approvals allow international use of the devices

Applications
- Packaging machines
- Automation
- Automation & Process Control
- Automotive Manufacturing
- Chemical, Oil & Gas
- Medical Equipment
- Pharmaceutical & Food
- Power Engineering DC 24 V
- Renewable Energy
- Steel Production











Electronic protection devices EPD24

Ordering details



2CDC 051 001 S0010

EPD24-TB-101-3A

Description

The protection devices EPD24 extend the ABB product range of modular DIN rail components by electronic overcurrent protection modules for selective protection of 24 V DC load circuits. This protection is achieved by a combination of active electronic current limitation in the case of a short circuit and an overload deactivation from 1.1 x I_n upwards.
If a fault occurs in a load circuit, the protection device EPD24 will detect this rapidly and reliably, then disable the power output transistor and hence interrupt the current flow in the defective circuit. The maximum possible overcurrent is always limited to 1.3...1.8 times the selected rated current. An activation of capacitive loads up to 20,000 µF is possible, deactivation only occurring in the case of overloads or short circuits. Selective deactivation of the defective current circuit means undefined error states and a complete system stop are prevented.

Ordering details

Rated current IN A	bbn 40 16779 EAN	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
0.5	829960	EPD24-TB-101-0.5A	2CDE601101R2905	4	0.065 (1.433)
1	829984	EPD24-TB-101-1A	2CDE601101R2001	4	0.065 (1.433)
2	830003	EPD24-TB-101-2A	2CDE601101R2002	4	0.065 (1.433)
3	830027	EPD24-TB-101-3A	2CDE601101R2003	4	0.065 (1.433)
4	830041	EPD24-TB-101-4A	2CDE601101R2004	4	0.065 (1.433)
6	830065	EPD24-TB-101-6A	2CDE601101R2006	4	0.065 (1.433)
8	830089	EPD24-TB-101-8A	2CDE601101R2008	4	0.065 (1.433)
10	830102	EPD24-TB-101-10A	2CDE601101R2010	4	0.065 (1.433)
12	830126	EPD24-TB-101-12A	2CDE601101R2012	4	0.065 (1.433)

Description	bbn 40 16779 EAN	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
Busbars for LINE+ and 0 V, grey insulation, length 500 mm [1)]	830140	EPD-BB500	2CDE605100R0500	10	0.2 (0.441)
Signal bars for aux. contacts, grey insulation, length 21 mm	830164	EPD-SB21	2CDE605200R0021	10	0.4 (0.882)

[1)] Max. load with one line entry I_{max} = 50 A (recommended: mid line entry)
Max. load with two line entries I_{max} = 63 A

Electronic protection devices EPD24

Operating data

Operating data	
Operating voltage U_B	24 V DC (18...32 V)
Current rating I_N	fixed current ratings: 0.5, 1, 2, 3, 4, 6, 8, 10, 12 A
Closed current I_0	ON condition: typically 20...30 mA depending on signal output
Status indication by means of	Green: unit is ON load circuit / Power-MOSFET is switched on
	Orange: in the event of overload or short circuit until electronic disconnection
	Red: unit electronically disconnected load circuit/Power-MOSFET OFF undervoltage (U_B < 8 V) after switch-on till the end of the delay period
	OFF: manually switched off or device is dead
	potential-free auxiliary contact F
	ON/OFF/ condition of switch
Load circuit	
Load output	Power-MOSFET switching output (high slide switch)
Overload disconnection	typically 1.1 x I_N (1.05...1.35 x I_N)
Short-circuit current I_K	active current limitation
Trip time	see time/current characteristics
For electronic disconnection	typically 3 s at I_{Load} > 1.1 x I_N typically 100 ms...3 s at I_{Load} > 1.8 x I_N (or 1.5 x I_N/1.3 x I_N,)
Temperature disconnection	internal temperature monitoring with electronic disconnection
Low voltage monitoring load output	with hysteresis, no reset required: load »OFF« at U_B< 8 V
Starting delay t_{Start}	typically 0.5 sec after every switch-on and after applying U_B
Disconnection of load circuit	electronic disconnection
Free-wheeling circuit	suitable external free-wheeling circuit to be used with inductive load
Several load outputs must not be connected in parallel	
Signal output	
Electrical data	potential-free auxiliary contact max. 30 V DC/0.5 A, min. 10 V DC/10 mA
ON condition LED green	voltage U_B applied, switch is in ON position no overload, no short circuit
OFF condition LED off	device switched off (switch is in OFF position) no voltage U_B applied
Fault condition LED orange	overload condition > 1.1 x I_N up to electronic disconnection
Fault condition LED red	electronic disconnection upon overload or short circuit Device switched off with control signal (switch is in ON position)
Aux. contact	single signal, make contact contact open, terminal 13-14
Fault	signal output fault conditions no operating voltage U_B ON/OFF switch is in OFF position red LED lighted (electronic disconnection)

Electronic protection devices EPD24

Technical data

General data	
Fail-Safe element	backup fuse for EPD24 not required because of the integral redundant fail-safe element
Housing material	moulded
Mounting	symmetrical rail to EN 50022-35x7.5
Ambient temperature	0...+50 °C (without condensation, see EN 60204-1)
Storage temperature	-20...+70 °C
Humidity	96 hrs/95 % RH/40 °C to IEC 60068-2-78, test Cab. climate class 3K3 to EN 60721
Vibration	3 g, test to IEC 60068-2-6 test Fc
Degree of protection	housing: IP20 DIN 40050 terminals: IP20 DIN 40050
EMC (EMC directive, CE logo)	emission: EN 61000-6-3 susceptibility: EN 61000-6-2
Isolations coordination (IEC 60934)	0.5 kV/pollution degree 2 reinforced insulation in operating area
Dielectric strength	max. 32 V DC (load circuit)
Isolation resistance (OFF condition)	n/a, only electronic disconnection
Approvals/Declarations of conformity	UL 2367 Solid State Overcurrent Protectors UL 1604, (class I, division 2, groups A, B, C, D) UL 508 CSA C22.2 No. 213 (class I, division 2) CSA C22.2 No. 142 CE logo
Dimensions (B x H x T)	12.5 x 80 x 83 mm
Weight	approx. 65 g
Terminals	**Line+/LOAD+/0V**
Screw terminals	M4
Max. cable cross section flexible with wire end ferrule w/wo plastic sleeve	0.5 – 10 mm²
Multi-lead connection (2 identical cables) rigid/flexible	0.5 – 4 mm²
Flexible with wire end ferrule without plastic sleeve	0.5 – 2.5 mm²
Flexible with TWIN wire end ferrule with plastic sleeve	0.5 – 6 mm²
Wire stripping length	10 mm
Tightening torque (EN 60934)	1.5 – 1.8 Nm
Terminals	**aux. contacts**
Screw terminals	M3
Max. cable cross section flexible with wire end ferrule w/wo plastic sleeve	0.25 - 2.5 mm²
Wire stripping length	8 mm
Tightening torque (EN 60934)	0.5 Nm

Table 1: voltage drop, current limitation, max. load current

current rating	typically voltage drop	active current	max. load current at 100 % ON duty	
I_N	U_{ON} at I_N	limitation (typically)	$T_{ambient}$ = 40 °C	$T_{ambient}$ = 40 °C
0.5 A	70 mV	1.8 x I_N	0.5 A	0.5 A
1 A	80 mV	1.8 x I_N	1 A	1 A
2 A	130 mV	1.8 x I_N	2 A	2 A
3 A	80 mV	1.8 x I_N	3 A	3 A
4 A	100 mV	1.8 x I_N	4 A	4 A
6 A	130 mV	1.8 x I_N	6 A	5 A
8 A	120 mV	1.5 x I_N	8 A	7 A
10 A	150 mV	1.5 x I_N	10 A	9 A
12 A	180 mV	1.3 x I_N	12 A	10.8 A

Attention: when mounted side-by-side without convection, the ERD24 should carry no more than 80 % of its rated load with 100 % ON duty due to thermal effects.

Electronic protection devices EPD24

Technical information

Time/Current characteristic curve (Tambient = 25 °C)

The trip time is typically 3 s in the range between 1.1 and 1.8 x I_N [1)].
Electronic current limitation occurs at typically 1.8 x I_N [1)] which means that under all overload conditions (independent of the power supply and the resistance of the load circuit) the max. overload before disconnection will not exceed 1.8 x I_N [1)] times the current rating. Trip time is between 100 ms and 3 sec (depending on overload or at short circuit).
Without this current limitation a considerably higher overload current would flow in the event of an overload or short circuit.

Maximum cable lenghts

EPD24 reliably trips from 0 Ω up to max. circuit resistance R_{max}.

Calculation of R_{max}

Selected rating I_N (A)	3	6
Operating voltage U_S (V DC) (= 80 % of 24 V) [2)]	19.2	19.2
Trip current I_{ab} = 1.25 x I_N (A) (EPD24 trips after 3 s)	3.75	7.50
R_{max} (Ω) = (U_B/I_{ab}) -0.050	5.07	2.51

[2)] Voltage drop of EPD24 and tolerance of trip point (typically 1.1 x I_N = 1.05 ... 1.35 x I_N) have been taken into account

Selection table for the incoming cable lengths with different cable cross-sections


Cable cross section A (mm²)	**0.14**	**0.25**	**0.34**	**0.5**	**0.75**	**1.00**	**1.50**
Cable length L (m) (= single length)	**cable resistance (Ω) = (ρ_0 x 2 x L) / A [3)]**						
5	1.27	0.71	0.52	0.36	0.24	0.18	0.12
10	2.54	1.42	1.05	0.71	0.47	0.36	0.24
15	3.81	2.14	1.57	1.07	0.71	0.53	0.36
20	5.09	2.85	2.09	1.42	0.95	0.71	0.47
25	6.36	3.56	2.62	1.78	1.19	0.89	0.59
30	7.63	4.27	3.14	2.14	1.42	1.07	0.71
35	8.90	4.98	3.66	2.49	1.66	1.25	0.83
40	10.17	5.70	4.19	2.85	1.90	1.42	0.95
45	11.44	6.41	4.71	3.20	2.14	1.60	1.07
50	12.71	7.12	5.24	3.56	2.37	1.78	1.19
75	19.07	10.68	7.85	5.34	3.56	2.67	1.78
100	25.34	14.24	10.47	7.12	4.75	3.56	2.37
125	31.79	17.80	13.09	8.90	5.93	4.45	2.97
150	38.14	21.36	15.71	10.68	7.12	5.34	3.56
175	44.50	24.92	18.32	12.46	8.31	6.23	4.15
200	50.86	28.48	20.94	14.24	9.49	7.12	4.75
225	57.21	32.04	23.56	16.02	10.68	8.01	5.34
250	63.57	35.60	26.18	17.80	11.87	8.90	5.93

[3)] Resistivity of copper ρ_0 = 0.0178 (Ω x mm²)/m
Example 1: max. length for 1.5 mm² and 3 A: 214 m
Example 2: max. length for 1.5 mm² and 6 A: 106 m
Example 3: mixed wiring: (Control cabinet --- sensor/actuator level)
R1 = 40 m for 1.5 mm² and R2 = 5 m for 0.25 mm²:
R1 = 0.95 Ω, R2 = 0.71 Ω, total (R1 + R2) = 1.66 Ω

Electronic protection devices EPD24

Technical diagrams

Time/Current characteristic curve




1) Current limitation typically 1.8 x I_N at I_N = 0.5 A...6 A
Current limitation typically 1.5 x I_N at I_N = 8 A or 10 A
Current limitation typically 1.3 x I_N at I_N = 12 A

Wiring diagram

EPD24-TB-101
without signal input
with signal output F
(Single signal, N/O)

Operating condition: 13-14 closed
Fault condition: 13-14 open



Electronic protection devices EPD24

Approvals, Safety instructions

Please note

The user must ensure that the cable cross sections of the relevant load circuit are suitable for the current rating of the EPD24 used. Automatic start-up of machinery after shut down must be prevented (Machinery Directive 2006/42/EU and IEC/EN 60204-1). In the event of a short circuit or overload the load circuit will be disconnected electronically by the EPD24.

Information on UL approvals/CSA approvals

UL1604
UL File # E 339238

CSA C22.2 No. 213 (Class I, Division 2)
CSA File # 2305929

Operating Temperature Code T5

- This equipment is suitable for use in Class I, Division 2, Groups A, B, C and D or non-hazardous locations only

WARNING:

- Exposure to some chemicals may degrade the sealing properties of materials used in the following device: relay Sealant Material:
  - Generic Name: Modified diglycidyl ether of bisphenol A
  - Supplier: Fine Polymers Corporation
  - Type: Epi Fine 4616L-160PK
- Casing Material:
  - Generic Name: Liquid Crystal Polymer
  - Supplier: Sumitomo Chemical
  - Type: E4008, E4009, or E6008

RECOMMENDATION:

- Periodically inspect the device named above for any degradation of properties and replace if degradation is found

WARNING – EXPLOSION HAZARD:

- Do not disconnect equipment unless power has been removed or the area is known to be non-hazardous
- Substitution of any components may impair suitability for Class I, Division 2

UL2367
Non-hazardous use - UL File # E 339236

UL 508
Non-hazardous use - UL File # E 149922

CSA C22.2 No. 14
CSA C22.2 No. 142 - CSA File # E 2305929


Class 2
Meets requirement for Class 2 current limitation (EPD24 ... -0,5 A/1 A/2 A/3 A)

Electronic protection devices EPD24

Installation guidelines

The EPD24 features an integral power distribution system.
The following wiring modes are possible with various pluggable current and signal busbars:

- LINE+ (24 V DC)
- 0 V
  Caution: The electronic devices EPD24 require a 0 V connection
- Auxiliary contacts




Mounting procedure
Before wiring insert busbars into protector block. A maximum of 10 connection cycles are permissible using connecting busbars.

Recommendation
After 10 units the busbars should be interrupted and receive a new entry live.

Table of length for busbars
(Order code 2CDE605100R0500)

No. of units	2	3	4	5	6	7	8	9	10
Length of busbar (mm) ± 0.5 mm	22	34.5	47	59.5	72	84.5	97	109.5	122


ABB
CR-P012DC1
1SVR 405 600 R4000
12V DC
16A 250VAC RES.
1.5A 240VAC AC15
CR-U012DC2
1SVR 405 621 R4000
12VDC
24VDC
A2 COIL
A1
A2
S1
S2
24V
0925
250 VAC
6A

Interface relays and optocouplers
Table of contents

362 Offer overview

365 Applications

367 Pluggable interface relays and optocouplers

368 Selection tables

370 List of components

385 Benefits and advantages

386 Socket & terminal connection types

387 Relay components

389 Ordering details

410 Technical data

424 Technical diagrams

437 Boxed interface relays and optocouplers R600 range

438 Overview

440 Boxed interface relays R600 range

440 Selection table

442 Ordering details

444 Technical data

448 Technical diagrams

450 Boxed optocouplers R600 range

450 Selection table

451 Ordering details

453 Technical data

456 Technical diagrams

Interface relays and optocouplers
Offer overview

Relays are universally applicable and are utilized in a diverse array of applications. They are a significant element in contemporary industrial processes and are used in applications where galvanic isolation, signal separation, voltage coupling and signal amplification are required.

The ABB portfolio includes electromechanical relays and optocouplers. The electromechanical relays operate using an electromagnetic field whereas optocouplers use light. Optocouplers are predominantly used in applications where a high switching frequency is necessary. Furthermore, optocouplers do not contain any moving parts and are therefore bounce-free, immune to vibrations and possess a long electrical life.



CR-S range
The slim line of interface relays and optocouplers
The pluggable interface relays and optocouplers of the CR-S range are used for electrical isolation, amplification and signal matching between the electronic controlling, e.g. PLC, iPC or field bus systems and the sensor / actuator level. The CR-S range combines the flexibility of a modular system and the ability of switching high currents on a small footprint thus can be used in applications where space saving is essential. The CR-S range also includes complete versions consisting of a relay, socket and marker.



CR-P range
The pluggable pcb interface relays and optocouplers
The pluggable interface relays of the CR-P range are used for electrical isolation, amplification and signal matching between the electronic controlling, e.g. PLC, iPC or field bus systems and the sensor / actuator level. The CR-P range offers highest current switching in an IP67 rated relay housing. Furthermore, nine different coil voltages are available to suit world wide applications and even gold contact versions are available which is essential when it comes to switch sensitive signals. The CR-P range also includes complete versions consisting of a relay, socket, holder, marker and function module.

Interface relays and optocouplers
Offer overview



CR-M range
The pluggable miniature interface relays
The pluggable interface relays of the CR-M range are used for electrical isolation, amplification and signal matching between the electronic controlling, e.g. PLC, iPC or field bus systems and the sensor / actuator level. The CR-M range offers up to 4 contacts in one relay and a built in test button which makes a circuit check fast and easy. 12 different coil voltages are available to suit world wide applications and even gold contact versions are available which is essential when it comes to switch sensitive signals. The CR-M range also includes complete versions consisting of a relay, socket, holder, marker and where applicable a function module.



CR-U range
The pluggable universal interface relays
The pluggable interface relays of the CR-U range are used for electrical isolation, amplification and signal matching between the electronic controlling, e.g. PLC, iPC or field bus systems and the sensor / actuator level. The CR-U range offers up to 3 contacts in one relay and a built in test button which makes a circuit check fast and easy. 12 different coil voltages are available to suit world wide applications.



R600 range
Boxed interface relays and optocouplers
Boxed interface relays of the R600 range are used for electrical isolation, amplification and signal matching between the electronic controlling, e.g. PLC, iPC or field bus systems and the sensor / actuator level. The relay itself is built in thus the perfect solution because this design fulfills highest vibration requirements. The compact design and different connection terminal possibilities further optimize your panel installation.




ANCON TRADER





ABB


ABB


Applications of interface relays
A proven technology used worldwide

Relays are universally applicable and are utilized in a diverse array of applications. They are a significant element in contemporary industrial processes and are used in applications where galvanic isolation, signal separation, voltage coupling and signal amplification are required.




Circuit multiplication

A single voltage signal may be used to simultaneously perform up to four different switching operations. Each output contact can be used to switch load circuits with different voltage and current levels.



Galvanic isolation

Interface relays are excellently suited to ensure safe galvanic isolation, i.e. separation between control circuit and load circuit.





Voltage conversion

Interface relays allow for small voltage signals to switch much larger loads. For example: a 24 V DC 10 mA signal can be used to switch a 230 V AC 16 A load.

Billions

of relays operate and interface between control circuits and electrical loads.




ABB
CR-U012DC2
1SVR 405 621 R4000
12VDC
ABB
24VDC
ABB
CR-P012DC1
1SVR 405 600 R4000
12V DC
ABB
24VDC

Pluggable interface relays and optocouplers
Table of contents

368 Selection tables

370 List of components

385 Benefits and advantages

386 Socket & terminal connection types

387 Relay components

389 Ordering details

389 CR-S range

393 CR-P range

397 CR-M range

404 CR-P/M function modules

406 CR-U range

408 CR-U function modules

410 Technical data

410 CR-S interface relays

411 CR-S optocouplers

412 CR-S sockets

413 CR-S jumper bars

414 CR-P, CR-M, CR-U

418 CR-P optocouplers

419 CR-P and CR-M sockets

420 CR-P and CR-M jumper bars

421 CR-P and CR-M function modules

422 CR-U sockets

423 CR-U function modules

424 Technical diagrams

Pluggable interface relays
Selection table CR-S range



How to use the selection table
Choose the desired control supply voltage from the column “Control voltage”, e.g. "5 V DC".
Choose the desired kind of connection terminal from the column “Connection terminal”, e.g. "spring".
Choose the desired material of contact from the column “Contact Material” e.g. "gold plated".

Control voltage	Connection terminal	Contact material	Socket type	Socket order code	Relay type	Relay order code
5 V DC	screw	standard	CR-S006/024VDC1SS	1SVR405521R1100	CR-S005VDC1R	1SVR405501R1010
		gold plated	CR-S006/024VDC1SS	1SVR405521R1100	CR-S005VDC1RG	1SVR405501R1020
	spring	standard	CR-S006/024VDC1SZ	1SVR405521R1200	CR-S005VDC1R	1SVR405501R1010
		gold plated	**CR-S006/024VDC1SZ**	**1SVR405521R1200**	**CR-S005VDC1RG**	**1SVR405501R1020**
12 V AC	screw	standard	CR-S012/024VADC1SS	1SVR405521R3100	CR-S012VDC1R	1SVR405501R2010
		gold plated	CR-S012/024VADC1SS	1SVR405521R3100	CR-S012VDC1RG	1SVR405501R2020
	spring	standard	CR-S012/024VADC1SZ	1SVR405521R3200	CR-S012VDC1R	1SVR405501R2010
		gold plated	CR-S012/024VADC1SZ	1SVR405521R3200	CR-S012VDC1RG	1SVR405501R2020



Example

When you have chosen 5 V DC as control supply voltage, spring connection as connection terminal and gold plated as contact material the following order codes and type designators are valid:

Socket: CR-S006/024VDC1SZ, 1SVR405521R1200
Relay: CR-S005VDC1RG, 1SVR405501R1020

—

CR-S range relay assemblies

Control voltage	Connection terminal	Contact material	Socket type	Socket order code	Relay type	Relay order code
5 V DC	screw	standard	CR-S006/024VDC1SS	1SVR405521R1100	CR-S005VDC1R	1SVR405501R1010
		gold plated	CR-S006/024VDC1SS	1SVR405521R1100	CR-S005VDC1RG	1SVR405501R1020
	spring	standard	CR-S006/024VDC1SZ	1SVR405521R1200	CR-S005VDC1R	1SVR405501R1010
		gold plated	CR-S006/024VDC1SZ	1SVR405521R1200	CR-S005VDC1RG	1SVR405501R1020
12 V DC	screw	standard	CR-S006/024VDC1SS or CR-S012/024VADC1SS	1SVR405521R1100 or 1SVR405521R3100	CR-S012VDC1R	1SVR405501R2010
		gold plated	CR-S006/024VDC1SS or CR-S012/024VADC1SS	1SVR405521R1100 or 1SVR405521R3100	CR-S012VDC1RG	1SVR405501R2020
	spring	standard	CR-S006/024VDC1SZ or CR-S012/024VADC1SZ	1SVR405521R1200 or 1SVR405521R3200	CR-S012VDC1R	1SVR405501R2010
		gold plated	CR-S006/024VDC1SZ or CR-S012/024VADC1SZ	1SVR405521R1200 or 1SVR405521R3200	CR-S012VDC1RG	1SVR405501R2020
12 V AC	screw	standard	CR-S012/024VADC1SS	1SVR405521R3100	CR-S012VDC1R	1SVR405501R2010
		gold plated	CR-S012/024VADC1SS	1SVR405521R3100	CR-S012VDC1RG	1SVR405501R2020
	spring	standard	CR-S012/024VADC1SZ	1SVR405521R3200	CR-S012VDC1R	1SVR405501R2010
		gold plated	CR-S012/024VADC1SZ	1SVR405521R3200	CR-S012VDC1RG	1SVR405501R2020
24 V DC	screw	standard	CR-S006/024VDC1SS or CR-S012/024VADC1SS	1SVR405521R1100 or 1SVR405521R3100	CR-S024VDC1R	1SVR405501R3010
		gold plated	CR-S006/024VDC1SS or CR-S012/024VADC1SS	1SVR405521R1100 or 1SVR405521R3100	CR-S024VDC1RG	1SVR405501R3020
	spring	standard	CR-S006/024VDC1SZ or CR-S012/024VADC1SZ	1SVR405521R1200 or 1SVR405521R3200	CR-S024VDC1R	1SVR405501R3010
		gold plated	CR-S006/024VDC1SZ or CR-S012/024VADC1SZ	1SVR405521R1200 or 1SVR405521R3200	CR-S024VDC1RG	1SVR405501R3020
24 V AC	screw	standard	CR-S012/024VADC1SS	1SVR405521R3100	CR-S024VDC1R	1SVR405501R3010
		gold plated	CR-S012/024VADC1SS	1SVR405521R3100	CR-S024VDC1RG	1SVR405501R3020
	spring	standard	CR-S012/024VADC1SZ	1SVR405521R3200	CR-S024VDC1R	1SVR405501R3010
		gold plated	CR-S012/024VADC1SZ	1SVR405521R3200	CR-S024VDC1RG	1SVR405501R3020
48 V AC/DC	screw	standard	CR-S048/060VADC1SS	1SVR405521R5100	CR-S048VDC1R	1SVR405501R4010
		gold plated	CR-S048/060VADC1SS	1SVR405521R5100	CR-S048VDC1RG	1SVR405501R4020
	spring	standard	CR-S048/060VADC1SZ	1SVR405521R5200	CR-S048VDC1R	1SVR405501R4010
		gold plated	CR-S048/060VADC1SZ	1SVR405521R5200	CR-S048VDC1RG	1SVR405501R4020
60 V AC/DC	screw	standard	CR-S048/060VADC1SS	1SVR405521R5100	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S048/060VADC1SS	1SVR405521R5100	CR-S060VDC1RG	1SVR405501R5020
	spring	standard	CR-S048/060VADC1SZ	1SVR405521R5200	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S048/060VADC1SZ	1SVR405521R5200	CR-S060VDC1RG	1SVR405501R5020
110-125 V AC/DC	screw	standard	CR-S110/125VADC1SS	1SVR405521R6100	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S110/125VADC1SS	1SVR405521R6100	CR-S060VDC1RG	1SVR405501R5020
	spring	standard	CR-S110/125VADC1SZ	1SVR405521R6200	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S110/125VADC1SZ	1SVR405521R6200	CR-S060VDC1RG	1SVR405501R5020
220-240 V AC/DC	screw	standard	CR-S220/240VADC1SS	1SVR405521R7100	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S220/240VADC1SS	1SVR405521R7100	CR-S060VDC1RG	1SVR405501R5020
	spring	standard	CR-S220/240VADC1SZ	1SVR405521R7200	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S220/240VADC1SZ	1SVR405521R7200	CR-S060VDC1RG	1SVR405501R5020

—

CR-S optocoupler range relay assemblies

Control voltage	Connection terminal	Output characteristics	Socket type	Socket order code	Opto type	Opto order code
24 V DC	screw	Transistor 100 mA - 48 V DC	CR-S012/024VADC1SS	1SVR405521R3100	CR-S024VDC1TRA	1SVR405510R3050
	spring		CR-S012/024VADC1SZ	1SVR405521R3200	CR-S024VDC1TRA	1SVR405510R3050
	screw	MOS-FET 2 A - 24 V DC	CR-S012/024VADC1SS	1SVR405521R3100	CR-S024VDC1MOS	1SVR405510R3060
	spring		CR-S012/024VADC1SZ	1SVR405521R3200	CR-S024VDC1MOS	1SVR405510R3060
	screw	Triac 2 A - 240 V AC	CR-S012/024VADC1SS	1SVR405521R3100	CR-S024VDC1TRI	1SVR405510R3070
	spring		CR-S012/024VADC1SZ	1SVR405521R3200	CR-S024VDC1TRI	1SVR405510R3070

List of components
Selection table CR-S range complete versions

The complete versions of the CR-S range comprise of a pluggable interface relay, socket and marker.

—
CR-S complete versions

Complete versions			Relay				Socket					
		Order code	1SVR405501R3010	1SVR405501R3020	1SVR405501R5010	1SVR405501R5020	1SVR405521R3100	1SVR405521R3200	1SVR405521R6100	1SVR405521R6200	1SVR405521R7100	1SVR405521R7200
Order code	**Type**	**Type**	CR-S024VDC1R	CR-S024VDC1RG	CR-S060VDC1R	CR-S060VDC1RG	CR-S012/024VADC1SS	CR-S012/024VADC1SZ	CR-S110/125VADC1SS	CR-S110/125VADC1SZ	CR-S220/240VADC1SS	CR-S220/240VADC1SZ
1SVR405541R3110	CR-S024VADC1CRS		■				■					
1SVR405541R3120	CR-S024VADC1CRGS			■			■					
1SVR405541R3210	CR-S024VADC1CRZ		■					■				
1SVR405541R3220	CR-S024VADC1CRGZ			■				■				
1SVR405541R6110	CR-S110VADC1CRS				■				■			
1SVR405541R6120	CR-S110VADC1CRGS					■			■			
1SVR405541R6210	CR-S110VADC1CRZ				■					■		
1SVR405541R6220	CR-S110VADC1CRGZ					■				■		
1SVR405541R7110	CR-S230VADC1CRS				■						■	
1SVR405541R7120	CR-S230VADC1CRGS					■					■	
1SVR405541R7210	CR-S230VADC1CRZ				■							■
1SVR405541R7220	CR-S230VADC1CRGZ					■						■

Pluggable interface relays and optocouplers
Selection table CR-P range

CR-P pluggable relays

	Order code	1SVR405600R4000	1SVR405600R1000	1SVR405600R6000	1SVR405600R8000	1SVR405600R0000	1SVR405600R5000	1SVR405600R7000	1SVR405600R2000	1SVR405600R3000	1SVR405601R4000	1SVR405601R1000	1SVR405601R6000	1SVR405601R8000	1SVR405601R0200	1SVR405601R0000	1SVR405601R5000	1SVR405601R7000	1SVR405601R2000	1SVR405601R3000	1SVR405606R1000	1SVR405606R0000	1SVR405606R7000	1SVR405606R3000
	Type	CR-P012DC1	CR-P024DC1	CR-P048DC1	CR-P110DC1	CR-P024AC1	CR-P048AC1	CR-P110AC1	CR-P120AC1	CR-P230AC1	CR-P012DC2	CR-P024DC2	CR-P048DC2	CR-P110DC2	CR-P012AC2	CR-P024AC2	CR-P048AC2	CR-P110AC2	CR-P120AC2	CR-P230AC2	CR-P024DC2G	CR-P024AC2G	CR-P110AC2G	CR-P230AC2G
Input voltage																								
12 V DC		■									■													
24 V DC			■									■									■			
48 V DC				■									■											
110 V DC					■									■										
12 V AC															■									
24 V AC						■										■						■		
48 V AC							■										■							
110 V AC								■										■					■	
120 V AC									■										■					
230 V AC										■										■				■
Output rating																								
250 V 16 A		■	■	■	■	■	■	■	■	■														
250 V 8 A											■	■	■	■	■	■	■	■	■	■	■	■	■	■
Output contacts																								
c/o		1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2
Gold plated contacts																					■	■	■	■

Pluggable interface relays and optocouplers
Selection table CR-P range

CR-P range complete versions

	Order code	1SVR405600R4010	1SVR405600R1010	1SVR405600R1011	1SVR405600R1013	1SVR405600R8010	1SVR405600R0010	1SVR405600R2010	1SVR405600R3110	1SVR405600R3011	1SVR405600R3010	1SVR405601R4010	1SVR405601R1010	1SVR405601R1013	1SVR405601R1011	1SVR405601R1012	1SVR405606R1010	1SVR405606R1013	1SVR405606R1011	1SVR405601R8010	1SVR405601R0010	1SVR405601R2010	1SVR405601R3110	1SVR405601R3011	1SVR405601R3012	1SVR405606R3013	1SVR405606R3012	1SVR405606R3010
	Type	CR-P012DC1SS42V	CR-P024DC1SS42V	CR-P024DC1LC42V	CR-P024DC1LC62C	CR-P110DC1SS42CV	CR-P024AC1SS62CV	CR-P120AC1SS92CV	CR-P230AC1SS92CV	CR-P230AC1LS	CR-P230AC1LC92CV	CR-P012DC2SS42V	CR-P024DC2SS42V	CR-P024DC2LS42	CR-P024DC2LS42V	CR-P024DC2LC42	CR-P024DC2GLC42V	CR-P024DC2GLC62C	CR-P024DC2GLC62CV	CR-P110DC2SS42CV	CR-P024AC2SS62CV	CR-P120AC2SS92CV	CR-P230AC2SS92CV	CR-P230AC2LS92CV	CR-P230AC2LC92	CR-P230AC2GLC92	CR-P230AC2GLC92C	CR-P230AC2GLC92CV
Input voltage																												
12 V DC		■										■																
24 V DC			■	■	■								■	■	■	■	■	■	■									
48 V DC																												
110 V DC						■														■								
12 V AC																												
24 V AC							■														■							
48 V AC																												
110 V AC																												
120 V AC								■														■						
230 V AC									■	■	■												■	■	■	■	■	■
Output rating																												
250 V 16 A		■	■	■	■	■	■	■	■	■	■																	
250 V 8 A												■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Output contacts																												
c/o		1	1	1	1	1	1	1	1	1	1	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
Gold plated contacts																	■	■	■							■	■	■
Socket type																												
Standard socket		■	■			■	■	■	■			■	■							■	■	■	■					
Logical socket				■	■					■	■			■	■	■	■	■	■					■	■	■	■	■
Additional features																												
LED		■	■	■	■	■	■	■	■		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Free-wheeling diode		■	■	■		■						■	■	■	■	■	■			■					■	■		

List of components
Selection table CR-P range complete versions

The complete versions of the CR-P range comprise of a pluggable interface relay, socket, holder, marker and a function module.

CR-P complete versions

		Relay								Socket			Function module								Holder
	Order code	1SVR405601R4000	1SVR405601R1000	1SVR405606R1000	1SVR405601R8000	1SVR405601R0000	1SVR405601R2000	1SVR405601R3000	1SVR405606R3000	1SVR405650R1000	1SVR405650R0000	1SVR405650R0200	1SVR405652R0000	1SVR405652R1000	1SVR405652R9100	1SVR405655R0000	1SVR405655R1000	1SVR405654R0100	1SVR405655R0100	1SVR405655R1100	1SVR405659R0000
	Type	CR-P012DC2	CR-P024DC2	CR-P024DC2G	CR-P110DC2	CR-P024AC2	CR-P120AC2	CR-P230AC2	CR-P230AC2G	CR-PSS	CR-PLS	CR-PLC	CR-P/M 42	CR-P/M 42V	CR-P/M 42CV	CR-P/M 62C	CR-P/M 62CV	CR-P/M 92	CR-P/M 92C	CR-P/M 92CV	CR-PH
Complete versions																					
Order code	**Type**																				
1SVR405601R4010	CR-P012DC2SS42V	■								■				■							■
1SVR405601R1010	CR-P024DC2SS42V		■							■				■							■
1SVR405601R1013	CR-P024DC2LS42		■								■		■								■
1SVR405601R1011	CR-P024DC2LS42V		■								■			■							■
1SVR405601R1012	CR-P024DC2LC42		■									■	■								■
1SVR405606R1010	CR-P024DC2GLC42V			■								■		■							■
1SVR405606R1013	CR-P024DC2GLC62C			■								■				■					■
1SVR405606R1011	CR-P024DC2GLC62CV			■								■					■				■
1SVR405601R8010	CR-P110DC2SS42CV				■					■					■						■
1SVR405601R0010	CR-P024AC2SS62CV					■				■							■				■
1SVR405601R2010	CR-P120AC2SS92CV						■			■										■	■
1SVR405601R3110	CR-P230AC2SS92CV							■		■										■	■
1SVR405601R3011	CR-P230AC2LS92CV							■			■									■	■
1SVR405601R3012	CR-P230AC2LC92							■				■						■			■
1SVR405606R3013	CR-P230AC2GLC92								■			■						■			■
1SVR405606R3012	CR-P230AC2GLC92C								■			■							■		■
1SVR405606R3010	CR-P230AC2GLC92CV								■			■								■	■

Pluggable interface relays and optocouplers
Selection table CR-M range

CR-M pluggable relays without LED

	Order code	1SVR405611R4000	1SVR405611R1000	1SVR405611R6000	1SVR405611R4200	1SVR405611R8000	1SVR405611R8200	1SVR405611R9000	1SVR405611R0000	1SVR405611R5000	1SVR405611R7000	1SVR405611R2000	1SVR405611R3000	1SVR405612R4000	1SVR405612R1000	1SVR405612R6000	1SVR405612R4200	1SVR405612R8000	1SVR405612R8200	1SVR405612R9000	1SVR405612R0000	1SVR405612R5000	1SVR405612R5200	1SVR405612R7000	1SVR405612R2000	1SVR405612R3000	1SVR405613R4000	1SVR405613R1000	1SVR405613R6000	1SVR405613R4200	1SVR405613R8000	1SVR405613R8200	1SVR405613R9000	1SVR405613R0000	1SVR405613R5000	1SVR405613R7000	1SVR405613R2000	1SVR405613R3000
	Type	CR-M012DC2	CR-M024DC2	CR-M048DC2	CR-M060DC2	CR-M110DC2	CR-M125DC2	CR-M220DC2	CR-M024AC2	CR-M048AC2	CR-M110AC2	CR-M120AC2	CR-M230AC2	CR-M012DC3	CR-M024DC3	CR-M048DC3	CR-M060DC3	CR-M110DC3	CR-M125DC3	CR-M220DC3	CR-M024AC3	CR-M048AC3	CR-M060AC3	CR-M110AC3	CR-M120AC3	CR-M230AC3	CR-M012DC4	CR-M024DC4	CR-M048DC4	CR-M060DC4	CR-M110DC4	CR-M125DC4	CR-M220DC4	CR-M024AC4	CR-M048AC4	CR-M110AC4	CR-M120AC4	CR-M230AC4
Input voltage																																				
12 V DC		■											■													■											
24 V DC			■											■													■										
48 V DC				■											■													■									
60 V DC					■											■													■								
110 V DC						■											■													■							
125 V DC							■											■													■						
220 V DC								■											■													■					
24 V AC									■												■												■				
48 V AC										■												■												■			
60 V AC																							■														
110 V AC											■													■											■		
120 V AC												■													■											■	
230 V AC													■													■											■
Output rating																																				
250 V 6 A																										■	■	■	■	■	■	■	■	■	■	■	■
250 V 10 A													■	■	■	■	■	■	■	■	■	■	■	■	■												
250 V 12 A		■	■	■	■	■	■	■	■	■	■	■	■																							
Output contacts																																				
c/o		2	2	2	2	2	2	2	2	2	2	2	2	3	3	3	3	3	3	3	3	3	3	3	3	3	4	4	4	4	4	4	4	4	4	4	4
Gold plated contacts																																					
Additional features																																				
LED																																					
Free-wheeling diode																																					

Pluggable interface relays and optocouplers
Selection table CR-M range

CR-M pluggable relays with LED

	Order code	1SVR405611R4100	1SVR405611R4400	1SVR405611R1100	1SVR405611R1400	1SVR405611R6100	1SVR405611R6400	1SVR405611R4300	1SVR405611R8100	1SVR405611R8400	1SVR405611R8300	1SVR405611R8500	1SVR405611R9100	1SVR405611R9400	1SVR405611R0300	1SVR405611R0300	1SVR405611R5100	1SVR405611R7100	1SVR405611R2100	1SVR405611R3100
	Type	CR-M012DC2L	CR-M012DC2LD	CR-M024DC2L	CR-M024DC2LD	CR-M048DC2L	CR-M048DC2LD	CR-M060DC2L	CR-M110DC2L	CR-M110DC2LD	CR-M125DC2L	CR-M125DC2LD	CR-M220DC2L	CR-M220DC2LD	CR-M012AC2L	CR-M024AC2L	CR-M048AC2L	CR-M110AC2L	CR-M120AC2L	CR-M230AC2L
Input voltage																				
12 V DC		■	■																	
24 V DC				■	■															
48 V DC						■	■													
60 V DC								■												
110 V DC									■	■										
125 V DC											■	■								
220 V DC													■	■						
12 V AC															■					
24 V AC																■				
48 V AC																	■			
60 V AC																				
110 V AC																		■		
120 V AC																			■	
230 V AC																				■
Output rating																				
250 V 6 A																				
250 V 10 A																				
250 V 12 A		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Output contacts																				
c/o		2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	2
Gold plated contacts																				
Additional features																				
LED		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Free-wheeling diode			■		■		■			■		■		■						

Pluggable interface relays and optocouplers
Selection table CR-M range

CR-M pluggable relays with LED

	Order code	1SVR405612R4100	1SVR405612R4400	1SVR405612R1100	1SVR405612R1400	1SVR405612R6100	1SVR405612R6400	1SVR405612R4300	1SVR405612R8100	1SVR405612R8400	1SVR405612R8300	1SVR405612R8500	1SVR405612R9100	1SVR405612R9400	1SVR405612R0300	1SVR405612R0100	1SVR405612R5100	1SVR405612R7100	1SVR405612R2100	1SVR405612R3100
	Type	CR-M012DC3L	CR-M012DC3LD	CR-M024DC3L	CR-M024DC3LD	CR-M048DC3L	CR-M048DC3LD	CR-M060DC3L	CR-M110DC3L	CR-M110DC3LD	CR-M125DC3L	CR-M125DC3LD	CR-M220DC3L	CR-M220DC3LD	CR-M012AC3L	CR-M024AC3L	CR-M048AC3L	CR-M110AC3L	CR-M120AC3L	CR-M230AC3L
Input voltage																				
12 V DC		■	■																	
24 V DC				■	■															
48 V DC						■	■													
60 V DC								■												
110 V DC									■	■										
125 V DC											■	■								
220 V DC													■	■						
12 V AC															■					
24 V AC																■				
48 V AC																	■			
60 V AC																				
110 V AC																		■		
120 V AC																			■	
230 V AC																				■
Output rating																				
250 V 6 A																				
250 V 10 A		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
250 V 12 A																				
Output contacts																				
c/o		3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3	3
Gold plated contacts																				
Additional features																				
LED		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Free-wheeling diode			■		■		■			■		■		■						

Pluggable interface relays and optocouplers
Selection table CR-M range

CR-M pluggable relays with LED

	Order code	1SVR405613R4100	1SVR405613R4400	1SVR405613R1100	1SVR405614R1100	1SVR405613R6100	1SVR405613R6400	1SVR405613R4300	1SVR405613R8100	1SVR405613R8400	1SVR405613R8300	1SVR405613R8500	1SVR405613R9100	1SVR405613R9400	1SVR405613R0300	1SVR405613R0100	1SVR405613R5100	1SVR405613R7100	1SVR405613R2100	1SVR405613R3100
	Type	CR-M012DC4L	CR-M012DC4LD	CR-M024DC4L	CR-M024DC4LD	CR-M048DC4L	CR-M048DC4LD	CR-M060DC4L	CR-M110DC4L	CR-M110DC4LD	CR-M125DC4L	CR-M125DC4LD	CR-M220DC4L	CR-M220DC4LD	CR-M012AC4L	CR-M024AC4L	CR-M048AC4L	CR-M110AC4L	CR-M120AC4L	CR-M230AC4L
Input voltage																				
12 V DC		■	■																	
24 V DC				■	■															
48 V DC						■	■													
60 V DC								■												
110 V DC									■	■										
125 V DC											■	■								
220 V DC													■	■						
12 V AC															■					
24 V AC																■				
48 V AC																	■			
60 V AC																				
110 V AC																		■		
120 V AC																			■	
230 V AC																				■
Output rating																				
250 V 6 A		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
250 V 10 A																				
250 V 12 A																				
Output contacts																				
c/o		4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
Gold plated contacts																				
Additional features																				
LED		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Free-wheeling diode			■		■		■			■		■		■						

Pluggable interface relays and optocouplers
Selection table CR-M range

CR-M pluggable relays with Gold Plated Contacts

	Order code	1SVR405618R1000	1SVR405618R0000	1SVR405618R7000	1SVR405618R3000	1SVR405618R3000	1SVR405618R4100	1SVR405618R1100	1SVR405618R6100	1SVR405618R4300	1SVR405618R8100	1SVR405618R8300	1SVR405618R9100	1SVR405618R0100	1SVR405618R5100	1SVR405618R7100	1SVR405618R2100	1SVR405618R3100	1SVR405618R4400	1SVR405618R1400
	Type	CR-M024DC4G	CR-M024AC4G	CR-M110AC4G	CR-M230AC4G	CR-M230AC4G	CR-M012DC4LG	CR-M024DC4LG	CR-M048DC4LG	CR-M060DC4LG	CR-M110DC4LG	CR-M125DC4LG	CR-M220DC4LG	CR-M024AC4LG	CR-M048AC4LG	CR-M110AC4LG	CR-M120AC4LG	CR-M230AC4LG	CR-M012DC4LDG	CR-M024DC4LDG
Input voltage																				
12 V DC							■												■	
24 V DC	■							■												■
48 V DC									■											
60 V DC										■										
110 V DC											■									
125 V DC												■								
220 V DC													■							
24 V AC		■												■						
48 V AC															■					
60 V AC																				
110 V AC			■													■				
120 V AC																	■			
230 V AC				■	■													■		
Output rating																				
250 V 6 A	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
250 V 10 A																				
250 V 12 A																				
Output contacts																				
c/o	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
Gold plated contacts	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Additional features																				
LED							■	■	■	■	■	■	■	■	■	■	■	■	■	■
Free-wheeling diode																			■	■

Pluggable interface relays and optocouplers
Selection table CR-M range complete versions

CR-M range complete versions

	Order code	1SVR405618R4410	1SVR405613R1010	1SVR405613R1011	1SVR405613R1012	1SVR405618R1011	1SVR405618R1010	1SVR405618R1110	1SVR405618R1410	1SVR405613R0010	1SVR405613R3110	1SVR405613R3011	1SVR405613R3012	1SVR405618R3112	1SVR405618R3110	1SVR405618R3111
	Type	CR-M012DC4LDGSS	CR-M024DC4SS42V	CR-M024DC4LS42V	CR-M024DC4LC42	CR-M024DC4GSS42V	CR-M024DC4GLC62CV	CR-M024DC4LGLC22	CR-M024DC4LDGSS	CR-M024AC4LS62CV	CR-M230AC4SS92CV	CR-M230AC4LS92CV	CR-M230AC4LC92	CR-M230AC4GSS92CV	CR-M230AC4LGLC	CR-M230AC4LGSS
Input voltage																
12 V DC		■														
24 V DC			■	■	■	■	■	■	■							
48 V DC																
60 V DC																
110 V DC																
125 V DC																
220 V DC																
24 V AC										■						
48 V AC																
60 V AC																
110 V AC																
120 V AC																
230 V AC											■	■	■	■	■	■
Output rating																
250 V 6 A		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
250 V 10 A																
250 V 12 A																
Output contacts																
c/o		4	4	4	4	4	4	4	4	4	4	4	4	4	4	4
Gold plated contacts		■				■	■	■	■					■	■	■
Socket type																
Standard socket		■	■			■			■		■			■		■
Logical socket				■	■		■	■		■		■	■		■	
Additional features																
LED		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Free-wheeling diode		■	■	■	■	■		■	■					■		■

List of components
Selection table CR-M range complete versions

The complete versions of the CR-M range comprise of a pluggable interface relay, socket, holder, marker and where applicable a function module.

CR-M complete versions

		Relay									Socket			Function module							Holder
	Order code	1SVR405618R4400	1SVR405613R1000	1SVR405618R1000	1SVR405618R1100	1SVR405618R1400	1SVR405613R0000	1SVR405613R3000	1SVR405618R3000	1SVR405618R3100	1SVR405651R3000	1SVR405651R3100	1SVR405651R3200	1SVR405651R0000	1SVR405652R0000	1SVR405652R1000	1SVR405652R9100	1SVR405655R1000	1SVR405654R0100	1SVR405655R1100	1SVR405659R1000
	Type	CR-M012DC4LDG	CR-M024DC4	CR-M024DC4G	CR-M024DC4LG	CR-M024DC4LDG	CR-M024AC4	CR-M230AC4	CR-M230AC4G	CR-M230AC4LG	CR-M4SS	CR-M4LS	CR-M4LC	CR-P/M 22	CR-P/M 42	CR-P/M 42V	CR-P/M 42CV	CR-P/M 62CV	CR-P/M 92	CR-P/M 92CV	CR-MH
Complete versions																					
Order code	**Type**																				
1SVR405618R4410	CR-M012DC4LDGSS	■									■										■
1SVR405613R1010	CR-M024DC4SS42V		■								■					■					■
1SVR405613R1011	CR-M024DC4LS42V		■									■				■					■
1SVR405613R1012	CR-M024DC4LC42		■										■		■						■
1SVR405618R1011	CR-M024DC4GSS42V			■							■					■					■
1SVR405618R1010	CR-M024DC4GLC62CV			■									■					■			■
1SVR405618R1110	CR-M024DC4LGLC22				■								■	■							■
1SVR405618R1410	CR-M024DC4LDGSS					■					■										■
1SVR405613R0010	CR-M024AC4LS62CV						■					■						■			■
1SVR405613R3110	CR-M230AC4SS92CV							■			■									■	■
1SVR405613R3011	CR-M230AC4LS92CV							■				■								■	■
1SVR405613R3012	CR-M230AC4LC92							■					■						■		■
1SVR405618R3112	CR-M230AC4GSS92CV								■		■									■	■
1SVR405618R3110	CR-M230AC4LGLC									■			■								■
1SVR405618R3111	CR-M230AC4LGSS									■	■										■

Pluggable interface relays and optocouplers
Selection table CR-P/M function modules

CR-P/M function modules

	Order code	1SVR405651R0000	1SVR405652R0000	1SVR405652R1000	1SVR405652R4000	1SVR405652R4100	1SVR405652R9000	1SVR405652R9100	1SVR405653R0000	1SVR405653R4000	1SVR405653R1000	1SVR405654R0000	1SVR405654R1000	1SVR405654R4000	1SVR405654R4100	1SVR405654R0100	1SVR405654R1100	1SVR405655R0000	1SVR405655R1000	1SVR405655R4000	1SVR405655R4100	1SVR405655R0100	1SVR405655R1100	1SVR405656R0000	1SVR405656R1000	1SVR405656R2000
	Type	CR-P/M 22	CR-P/M 42	CR-P/M 42V	CR-P/M 42B	CR-P/M 42BV	CR-P/M 42C	CR-P/M 42CV	CR-P/M 52B	CR-P/M 52D	CR-P/M 52C	CR-P/M 62	CR-P/M 62V	CR-P/M 62E	CR-P/M 62EV	CR-P/M 92	CR-P/M 92V	CR-P/M 62C	CR-P/M 62CV	CR-P/M 62D	CR-P/M 62DV	CR-P/M 92C	CR-P/M 92CV	CR-P/M 72	CR-P/M 72A	CR-P/M 82
Related control supply voltage																										
6-220 V DC		■																								
6-24 V DC			■	■								■	■					■	■							
24-60 V DC				■	■	■								■	■					■	■						
110 V DC							■	■																		
110-230 V DC											■					■	■					■	■			
6-24 V AC									■			■	■					■	■							
24-60 V AC										■				■	■					■	■					
110-230 V AC											■					■	■					■	■			
24 V AC																								■		
115 V AC																									■	
230 V AC																										■
24-240 V AC/DC																										
Function																										
Diode - reverse polarity protection / free-wheeling diode		■																								
Diode and LED - reverse polarity protection / free-wheeling diode			■	■	■	■	■	■																		
RC element - spark quenching									■	■	■															
Diode and LED												■	■	■	■	■	■									
Varistor and LED - overvoltage protection																		■	■	■	■	■	■			
Varistor - overvoltage protection																								■	■	■
LED red			■		■		■					■		■		■		■		■		■				
LED green				■		■		■					■		■		■		■		■		■			

Pluggable interface relays and optocouplers
Selection table CR-U range

CR-U pluggable relays without LED

	Order code	1SVR405621R4000	1SVR405621R1000	1SVR405621R6000	1SVR405621R8000	1SVR405621R9000	1SVR405621R0000	1SVR405621R5000	1SVR405621R7000	1SVR405621R2000	1SVR405621R3000	1SVR405622R4000	1SVR405622R1000	1SVR405622R6000	1SVR405622R8000	1SVR405622R8200	1SVR405622R9000	1SVR405622R0000	1SVR405622R5000	1SVR405622R5200	1SVR405622R7000	1SVR405622R2000	1SVR405622R3000
	Type	CR-U012DC2	CR-U024DC2	CR-U048DC2	CR-U110DC2	CR-U220DC2	CR-U024AC2	CR-U048AC2	CR-U110AC2	CR-U120AC2	CR-U230AC2	CR-U012DC3	CR-U024DC3	CR-U048DC3	CR-U110DC3	CR-U125DC3	CR-U220DC3	CR-U024AC3	CR-U048AC3	CR-U060AC3	CR-U110AC3	CR-U120AC3	CR-U230AC3
Input voltage																							
12 V DC		■										■											
24 V DC			■										■										
48 V DC				■										■									
110 V DC					■										■								
125 V DC																■							
220 V DC						■											■						
12 V AC																							
24 V AC							■											■					
48 V AC								■											■				
60 V AC																				■			
110 V AC									■												■		
120 V AC										■												■	
230 V AC											■												■
Output rating																							
250 V 10 A		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Output contacts																							
c/o		2	2	2	2	2	2	2	2	2	2	3	3	3	3	3	3	3	3	3	3	3	3
Gold plated contacts																							

Pluggable interface relays and optocouplers
Selection table CR-U range

CR-U pluggable relays with LED


	Order code	1SVR405621R4100	1SVR405621R4400	1SVR405621R1100	1SVR405621R1400	1SVR405621R6100	1SVR405621R6400	1SVR405621R8100	1SVR405621R8400	1SVR405621R9100	1SVR405621R0300	1SVR405621R0100	1SVR405621R5100	1SVR405621R7100	1SVR405621R2100	1SVR405621R3100	1SVR405622R4100	1SVR405622R4400	1SVR405622R1100	1SVR405623R1100	1SVR405622R6100	1SVR405622R6400	1SVR405622R8100	1SVR405622R8400	1SVR405622R9100	1SVR405622R0300	1SVR405622R0100	1SVR405622R5100	1SVR405622R7100	1SVR405622R2100	1SVR405622R3100
	Type	CR-U012DC2L	CR-U012DC2LD	CR-U024DC2L	CR-U024DC2LD	CR-U048DC2L	CR-U048DC2LD	CR-U110DC2L	CR-U110DC2LD	CR-U220DC2L	CR-U012AC2L	CR-U024AC2L	CR-U048AC2L	CR-U110AC2L	CR-U120AC2L	CR-U230AC2L	CR-U012DC3L	CR-U012DC3LD	CR-U024DC3L	CR-U024DC3LD	CR-U048DC3L	CR-U048DC3LD	CR-U110DC3L	CR-U110DC3LD	CR-U220DC3L	CR-U012AC3L	CR-U024AC3L	CR-U048AC3L	CR-U110AC3L	CR-U120AC3L	CR-U230AC3L
Input voltage																														
12 V DC		■	■														■	■												
24 V DC				■	■														■	■										
48 V DC						■	■														■	■								
110 V DC								■	■														■							
125 V DC																								■						
220 V DC										■															■					
12 V AC											■															■				
24 V AC												■															■			
48 V AC													■															■		
60 V AC																														
110 V AC														■															■	
120 V AC															■															■	
230 V AC																■														■
Output rating																														
250 V 10 A		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Output contacts																														
c/o		2	2	2	2	2	2	2	2	2	2	2	2	2	2	2	3	3	3	3	3	3	3	3	3	3	3	3	3	3
Gold plated contacts																														
Additional features																														
LED		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
Free-wheeling diode			■		■		■		■									■		■		■		■							

Pluggable interface relays and optocouplers
Selection table CR-U function modules

CR-U function modules

	Order code	1SVR405661R0000	1SVR405662R0000	1SVR405662R1000	1SVR405662R4000	1SVR405662R4100	1SVR405662R9000	1SVR405662R9100	1SVR405663R0000	1SVR405663R4000	1SVR405663R1000	1SVR405664R0000	1SVR405664R1000	1SVR405664R4000	1SVR405664R4100	1SVR405664R0100	1SVR405664R1100	1SVR405665R0000	1SVR405665R1000	1SVR405665R4000	1SVR405665R4100	1SVR405665R0100	1SVR405665R1100	1SVR405666R0000	1SVR405666R1000	1SVR405666R2000	1SVR405677R0000
	Type	CR-U 21	CR-U 41	CR-U 41V	CR-U 41B	CR-U 41BV	CR-U 41C	CR-U 41CV	CR-U 51B	CR-U 51D	CR-U 51C	CR-U 61	CR-U 61V	CR-U 61E	CR-U 61EV	CR-U 91	CR-U 91V	CR-U 61C	CR-U 61CV	CR-U 61D	CR-U 61DV	CR-U 91C	CR-U 91CV	CR-U 71	CR-U 71A	CR-U 81	CR-U T
Related control supply voltage																											
6-220 V DC		■																									
6-24 V DC			■	■					■			■	■				■	■									
24-60 V DC					■	■				■				■	■				■	■							
110 V DC							■	■																			
110-230 V DC											■					■	■					■	■				
6-24 V AC									■			■	■				■	■									
24-60 V AC										■				■	■				■	■							
110-230 V AC											■					■	■					■	■				
24 V AC																							■				
115 V AC																								■			
230 V AC																									■		
24-240 V AC/DC																											■
Function																											
Diode - reverse polarity protection / free wheeling diode		■																									
Diode and LED - Reverse polarity protection / free-wheeling diode and LED to indicate energized coil			■	■	■	■	■	■																			
RC element - Spark quenching									■	■	■																
Diode and LED - LED to indicate energized coil												■	■	■	■	■	■										
Varistor and LED - Overvoltage protection and LED to indicate energized coil																		■	■	■	■	■	■				
Varistor - Overvoltage protection																								■	■	■	
Multi-function time module																											■
LED red			■		■		■					■		■		■		■		■		■					
LED green				■		■		■					■		■		■		■		■		■				■

Pluggable interface relays and optocouplers
Benefits and advantages



ABB’s interface relays and optocouplers ensure a reliable voltage conversion between process peripherals and higher level control systems. These relays ensure reliable signal switching and provide electrical isolation for sensitive electronics such as PLCs. The wide variety of pluggable interface relays with accompanied by standard or logic sockets may be used for switching AC or DC loads. Suitable for extreme environments, ABB's interface relays are offered across a wide spectrum of coil voltages, with a variety of optional function modules.



Continuous operation

The interface relay portfolio incorporates a large assortment of relays. It includes both electro-mechanical relays and optocouplers. Optocouplers allow for continuous operation without any mechanical wear-and -tear.



Easy to install

The interface relay includes both pluggable and non-pluggable relays. The plugggable relays allow for the easy and seamless exchange of relay modules.



Global availability


The ABB interface relays and optocouplers are approved for a large variety of applications, comply to the highest global approvals and are available world-wide.

Pluggable interface relays and optocouplers
Socket and terminal connection types

Standard sockets



01 Standard socket CR-P




02 Standard socket CR-M

Position of connection terminals:
Coil connection (A1-A2) on lower side of the socket, contact connections (n/o and n/c contacts) on the lower and upper side of the socket.

Logical sockets




03 Logical socket CR-P




04 Logical socket CR-M

Position of connection terminals:
Coil connection (A1-A2) on lower side of the socket, all contact connections (common contacts, n/o and n/c contacts) on the upper side of the socket.


Terminal connection types



05 Screw type



06 Spring type




07 Fork type


A variety of sockets are available for interface relays and optocouplers to meet the needs of different applications such as vibration- intensive environments.

Pluggable interface relays and optocouplers
Relay components

CR-S range




CR-P range




Pluggable interface relays and optocouplers
Relay components

CR-M range



CR-U range



Pluggable interface relays and optocouplers

Ordering details – CR-S range



CR-S relay

The slim pluggable interface relays and optocouplers of the CR-S range may be used for electrical isolation, amplification and signal matching. The CR-S relays are 6.2 mm wide and therefore allow for the switching high currents on a small footprint.

Ordering details - CR-S range pluggable interface relays

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
5 V DC	1 c/o (SPDT) standard contacts	250 V, 6 A	CR-S005VDC1R	1SVR405501R1010	10	0.005 (0.011)
12 V DC			CR-S012VDC1R	1SVR405501R2010		
24 V DC			CR-S024VDC1R	1SVR405501R3010		
48 V DC			CR-S048VDC1R	1SVR405501R4010		
60 V DC			CR-S060VDC1R	1SVR405501R5010		
5 V DC	1 c/o (SPDT) gold plated contacts	12 V, 250 mA (3W)[1]	CR-S005VDC1RG	1SVR405501R1020	10	0.005 (0.011)
12 V DC			CR-S012VDC1RG	1SVR405501R2020		
24 V DC			CR-S024VDC1RG	1SVR405501R3020		
48 V DC			CR-S048VDC1RG	1SVR405501R4020		
60 V DC			CR-S060VDC1RG	1SVR405501R5020		



CR-S optocoupler

Ordering details - CR-S range pluggable optocouplers

Rated control supply voltage	Outputs	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V DC	Transistor, 100 mA - 48 V DC	CR-S024VDC1TRA	1SVR405510R3050	10	0.004 (0.009)
	MOS-FET, 2 A - 24 V DC	CR-S024VDC1MOS	1SVR405510R3060		
	Triac, 2 A - 240 V AC	CR-S024VDC1TRI	1SVR405510R3070		



CR-S complete interface relay


Ordering details - CR-S range complete interface relays (relay + socket)

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V AC/DC	1 c/o (SPDT) standard contacts	250 V, 6 A	CR-S024VADC1CRS	1SVR405541R3110	10	0.03 (0.066)
			CR-S024VADC1CRZ	1SVR405541R3210		
110 V AC/DC			CR-S110VADC1CRS	1SVR405541R6110		
			CR-S110VADC1CRZ	1SVR405541R6210		
230 V AC/DC			CR-S230VADC1CRS	1SVR405541R7110		
			CR-S230VADC1CRZ	1SVR405541R7210		
24 V AC/DC	1 c/o (SPDT) gold plated contacts	12 V, 250 mA (3W)[1]	CR-S024VADC1CRGS	1SVR405541R3120	10	0.03 (0.066)
			CR-S024VADC1CRGZ	1SVR405541R3220		
110 V AC/DC			CR-S110VADC1CRGS	1SVR405541R6120		
			CR-S110VADC1CRGZ	1SVR405541R6220		
230 V AC/DC			CR-S230VADC1CRGS	1SVR405541R7120		
			CR-S230VADC1CRGZ	1SVR405541R7220		

[1] If specified maximum values exceeded, the gold plating is destroyed. The maximum values of the standard contacts are then valid.

Pluggable interface relays and optocouplers

Ordering details – CR-S range



CR-S socket

Ordering details - CR-S range sockets

Rated control supply voltage	Connection type	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-24 V DC	screw	CR-S006/024VDC1SS	1SVR405521R1100	10	0.025 (0.055)
	spring	CR-S006/024VDC1SZ	1SVR405521R1200		
12-24 V AC/DC	screw	CR-S012/024VADC1SS	1SVR405521R3100		
	spring	CR-S012/024VADC1SZ	1SVR405521R3200		
48-60 V AC/DC	screw	CR-S048/060VADC1SS	1SVR405521R5100		
	spring	CR-S048/060VADC1SZ	1SVR405521R5200		
110-125 V AC/DC	screw	CR-S110/125VADC1SS	1SVR405521R6100		
	spring	CR-S110/125VADC1SZ	1SVR405521R6200		
220-240 V AC/DC	screw	CR-S220/240VADC1SS	1SVR405521R7100		
	spring	CR-S220/240VADC1SZ	1SVR405521R7200		

Ordering details - CR-S range accessories

Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
Jumper bar 20 pole, blue color	CR-SJB20-BLUE	1SVR405598R0700	10	0.008 (0.018)
Jumper bar 20 pole, red color	CR-SJB20-RED	1SVR405598R0800		
Jumper bar 20 pole, black color	CR-SJB20-BLACK	1SVR405598R0900		
Separator	CR-SSEP	1SVR405599R0000	10	0.012 (0.026)

Pluggable interface relays and optocouplers

Ordering details – CR-S range

Relay assemblies

Control voltage	Connection terminal	Contact material	Socket type	Socket order code	Relay type	Relay order code
5 V DC	screw	standard	CR-S006/024VDC1SS	1SVR405521R1100	CR-S005VDC1R	1SVR405501R1010
		gold plated	CR-S006/024VDC1SS	1SVR405521R1100	CR-S005VDC1RG	1SVR405501R1020
	spring	standard	CR-S006/024VDC1SZ	1SVR405521R1200	CR-S005VDC1R	1SVR405501R1010
		gold plated	CR-S006/024VDC1SZ	1SVR405521R1200	CR-S005VDC1RG	1SVR405501R1020
12 V DC	screw	standard	CR-S006/024VDC1SS or CR-S012/024VADC1SS	1SVR405521R1100 or 1SVR405521R3100	CR-S012VDC1R	1SVR405501R2010
		gold plated	CR-S006/024VDC1SS or CR-S012/024VADC1SS	1SVR405521R1100 or 1SVR405521R3100	CR-S012VDC1RG	1SVR405501R2020
	spring	standard	CR-S006/024VDC1SZ or CR-S012/024VADC1SZ	1SVR405521R1200 or 1SVR405521R3200	CR-S012VDC1R	1SVR405501R2010
		gold plated	CR-S006/024VDC1SZ or CR-S012/024VADC1SZ	1SVR405521R1200 or 1SVR405521R3200	CR-S012VDC1RG	1SVR405501R2020
12 V AC	screw	standard	CR-S012/024VADC1SS	1SVR405521R3100	CR-S012VDC1R	1SVR405501R2010
		gold plated	CR-S012/024VADC1SS	1SVR405521R3100	CR-S012VDC1RG	1SVR405501R2020
	spring	standard	CR-S012/024VADC1SZ	1SVR405521R3200	CR-S012VDC1R	1SVR405501R2010
		gold plated	CR-S012/024VADC1SZ	1SVR405521R3200	CR-S012VDC1RG	1SVR405501R2020
24 V DC	screw	standard	CR-S006/024VDC1SS or CR-S012/024VADC1SS	1SVR405521R1100 or 1SVR405521R3100	CR-S024VDC1R	1SVR405501R3010
		gold plated	CR-S006/024VDC1SS or CR-S012/024VADC1SS	1SVR405521R1100 or 1SVR405521R3100	CR-S024VDC1RG	1SVR405501R3020
	spring	standard	CR-S006/024VDC1SZ or CR-S012/024VADC1SZ	1SVR405521R1200 or 1SVR405521R3200	CR-S024VDC1R	1SVR405501R3010
		gold plated	CR-S006/024VDC1SZ or CR-S012/024VADC1SZ	1SVR405521R1200 or 1SVR405521R3200	CR-S024VDC1RG	1SVR405501R3020
24 V AC	screw	standard	CR-S012/024VADC1SS	1SVR405521R3100	CR-S024VDC1R	1SVR405501R3010
		gold plated	CR-S012/024VADC1SS	1SVR405521R3100	CR-S024VDC1RG	1SVR405501R3020
	spring	standard	CR-S012/024VADC1SZ	1SVR405521R3200	CR-S024VDC1R	1SVR405501R3010
		gold plated	CR-S012/024VADC1SZ	1SVR405521R3200	CR-S024VDC1RG	1SVR405501R3020
48 V AC/DC	screw	standard	CR-S048/060VADC1SS	1SVR405521R5100	CR-S048VDC1R	1SVR405501R4010
		gold plated	CR-S048/060VADC1SS	1SVR405521R5100	CR-S048VDC1RG	1SVR405501R4020
	spring	standard	CR-S048/060VADC1SZ	1SVR405521R5200	CR-S048VDC1R	1SVR405501R4010
		gold plated	CR-S048/060VADC1SZ	1SVR405521R5200	CR-S048VDC1RG	1SVR405501R4020
60 V AC/DC	screw	standard	CR-S048/060VADC1SS	1SVR405521R5100	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S048/060VADC1SS	1SVR405521R5100	CR-S060VDC1RG	1SVR405501R5020
	spring	standard	CR-S048/060VADC1SZ	1SVR405521R5200	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S048/060VADC1SZ	1SVR405521R5200	CR-S060VDC1RG	1SVR405501R5020
110-125 V AC/DC	screw	standard	CR-S110/125VADC1SS	1SVR405521R6100	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S110/125VADC1SS	1SVR405521R6100	CR-S060VDC1RG	1SVR405501R5020
	spring	standard	CR-S110/125VADC1SZ	1SVR405521R6200	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S110/125VADC1SZ	1SVR405521R6200	CR-S060VDC1RG	1SVR405501R5020
220-240 V AC/DC	screw	standard	CR-S220/240VADC1SS	1SVR405521R7100	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S220/240VADC1SS	1SVR405521R7100	CR-S060VDC1RG	1SVR405501R5020
	spring	standard	CR-S220/240VADC1SZ	1SVR405521R7200	CR-S060VDC1R	1SVR405501R5010
		gold plated	CR-S220/240VADC1SZ	1SVR405521R7200	CR-S060VDC1RG	1SVR405501R5020

Pluggable interface relays and optocouplers

Ordering details – CR-S range

Optocoupler assemblies

Control voltage	Connection terminal	Output characteristics	Socket type	Socket order code	Opto type	Opto order code
24 V DC	screw	Transistor 100 mA - 48 V DC	CR-S012/024VADC1SS	1SVR405521R3100	CR-S024VDC1TRA	1SVR405510R3050
	spring		CR-S012/024VADC1SZ	1SVR405521R3200	CR-S024VDC1TRA	1SVR405510R3050
	screw	MOS-FET 2 A - 24 V DC	CR-S012/024VADC1SS	1SVR405521R3100	CR-S024VDC1MOS	1SVR405510R3060
	spring		CR-S012/024VADC1SZ	1SVR405521R3200	CR-S024VDC1MOS	1SVR405510R3060
	screw	Triac 2 A - 240 V AC	CR-S012/024VADC1SS	1SVR405521R3100	CR-S024VDC1TRI	1SVR405510R3070
	spring		CR-S012/024VADC1SZ	1SVR405521R3200	CR-S024VDC1TRI	1SVR405510R3070

Pluggable interface relays and optocouplers

Ordering details – CR-P range

The CR-P range offers the highest current switching in an IP67 rated relay housing. This range comprises of pluggable interface relays and optocouplers offered in 10 different control supply voltages. Additionally, gold plated contacts are available for applications where sensitive signals are to be switched. The CR-P range also includes complete versions consisting of a relay, socket, holder, marker and function module.


2CDC 291 045 F0004

CR-P relay

Ordering details - CR-P range relays

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	1 c/o (SPDT)	250 V, 16 A	CR-P012DC1	1SVR405600R4000	10	0.014 (0.031)
24 V DC			CR-P024DC1	1SVR405600R1000		
48 V DC			CR-P048DC1	1SVR405600R6000		
110 V DC			CR-P110DC1	1SVR405600R8000		
24 V AC			CR-P024AC1	1SVR405600R0000		
48 V AC			CR-P048AC1	1SVR405600R5000		
110 V AC			CR-P110AC1	1SVR405600R7000		
120 V AC			CR-P120AC1	1SVR405600R2000		
230 V AC			CR-P230AC1	1SVR405600R3000		
12 V DC	2 c/o (SPDT)	250 V, 8 A	CR-P012DC2	1SVR405601R4000	10	0.014 (0.031)
24 V DC			CR-P024DC2	1SVR405601R1000		
48 V DC			CR-P048DC2	1SVR405601R6000		
110 V DC			CR-P110DC2	1SVR405601R8000		
12 V AC			CR-P012AC2	1SVR405601R0200		
24 V AC			CR-P024AC2	1SVR405601R0000		
48 V AC			CR-P048AC2	1SVR405601R5000		
110 V AC			CR-P110AC2	1SVR405601R7000		
120 V AC			CR-P120AC2	1SVR405601R2000		
230 V AC			CR-P230AC2	1SVR405601R3000		

Ordering details - CR-P range relays with gold contacts

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V DC	2 c/o (SPDT) gold contact	250 V, 8 A	CR-P024DC2G	1SVR405606R1000	10	0.014 (0.031)
24 V AC			CR-P024AC2G	1SVR405606R0000		
110 V AC			CR-P110AC2G	1SVR405606R7000		
230 V AC			CR-P230AC2G	1SVR405606R3000		


2CDC 291 006 S0016

CR-P optocoupler

Ordering details - CR-P range pluggable optocouplers

Rated control supply voltage (Us)	Outputs	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
10-32 V DC	MOS-FET, 5 A - 35 V DC	CR-P024MOS1	1SVR405610R4060	10	0.011 (0.618)
	Triac, 3 A - 275 V AC	CR-P024TRI1	1SVR405610R4070		

Pluggable interface relays and optocouplers

Ordering details – CR-P range



CR-PLSX



CR-PSS

Standard and logical sockets for CR-P interface relays are suitable for snap-on mounting onto a DIN rail. Optional function modules for the CR-P range are plugged into both standard and logical sockets.

Ordering details - Sockets*

Version	Connection terminal	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
Logical socket with protective separation	screw	CR-PLS	1SVR405650R0000	10	0.045 (0.099)
Logical socket	screw	CR-PLSX	1SVR405650R0100		0.043 (0.095)
	spring	CR-PLC	1SVR405650R0200		0.042 (0.093)
Standard socket	screw	CR-PSS	1SVR405650R1000		0.038 (0.084)


*All CR-P socket packages include a set of markers.

Standard sockets

Position of connection terminals: coil connection (A1-A2) on lower side of the socket, contact connections (n/o and n/c contacts) on the lower and upper side of the socket.

Logical sockets

Position of connection terminals: coil connection (A1-A2) on lower side of the socket, all contact connections (common contacts, n/o and n/c contacts) on the upper side of the socket.



CR-PJ

Ordering details - Accessories

Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
Plastic holder for socket	CR-PH	1SVR405659R0000	10	0.002 (0.004)
Metal holder for socket	CR-PH1	1SVR405659R0100		0.4g
Jumper bar for sockets with screw connection	CR-PJ	1SVR405658R5000		0.018 (0.040)
Marker	CR-PM	1SVR405658R0000	10	0.0002 (0.0004)

Pluggable interface relays and optocouplers

Ordering details – CR-P range



2CDC291001F0019

CR-P complete version

Ordering details - CR-P range complete versions

Rated control supply voltage	Out-puts	Description	Socket type	Connection terminal	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	1 c/o	Reverse polarity protection and freewheeling diode, LED green, holder	standard	screw	CR-P012DC1SS42V	1SVR405600R4010	10	0.057 (0.126)
24 V DC	1 c/o	Reverse polarity protection and freewheeling diode, LED green, holder	standard	screw	CR-P024DC1SS42V	1SVR405600R1010	10	0.057 (0.126)
		Reverse polarity protection and freewheeling diode, LED green, holder	logical	spring	CR-P024DC1LC42V	1SVR405600R1011	10	0.057 (0.126)
		Varistor and LED red, holder	logical	spring	CR-P024DC1LC62C	1SVR405600R1013	10	0.057 (0.126)
110 V DC	1 c/o	Reverse polarity protection and freewheeling diode, LED green, holder	standard	screw	CR-P110DC1SS42CV	1SVR405600R8010	10	0.057 (0.126)
24 V AC	1 c/o	Varistor and LED green, holder	standard	screw	CR-P024AC1SS62CV	1SVR405600R0010	10	0.057 (0.126)
120 V AC	1 c/o	Varistor and LED green, holder	standard	screw	CR-P120AC1SS92CV	1SVR405600R2010	10	0.057 (0.126)
230 V AC	1 c/o	Reverse polarity protection and freewheeling diode, LED green, holder	standard	screw	CR-P230AC1SS92CV	1SVR405600R3110	10	0.057 (0.126)
		Holder	logical	screw	CR-P230AC1LS	1SVR405600R3011	10	0.057 (0.126)
		Varistor and LED green, holder	logical	spring	CR-P230AC1LC92CV	1SVR405600R3010	10	0.057 (0.126)

Pluggable interface relays and optocouplers

Ordering details – CR-P range



2CDC291001F0019

CR-P complete version

Ordering details - CR-P range complete versions

Rated control supply voltage	Out-puts	Description	Socket type	Connec-tion terminal	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	2 c/o	Reverse polarity protection and freewheeling diode, LED green, holder	standard	screw	CR-P012DC2SS42V	1SVR405601R4010	10	0.057 (0.126)
24 V DC	2 c/o	Reverse polarity protection and freewheeling diode, LED green, holder	standard	screw	CR-P024DC2SS42V	1SVR405601R1010	10	0.057 (0.126)
		Reverse polarity protection and freewheeling diode, LED red, holder	logical	screw	CR-P024DC2LS42	1SVR405601R1013	10	0.057 (0.126)
		Reverse polarity protection and freewheeling diode, LED green, holder	logical	screw	CR-P024DC2LS42V	1SVR405601R1011	10	0.057 (0.126)
		Reverse polarity protection and freewheeling diode, LED red, holder	logical	spring	CR-P024DC2LC42	1SVR405601R1012	10	0.057 (0.126)
24 V DC	2 c/o gold plated	Reverse polarity protection and freewheeling diode, LED green, holder	logical	spring	CR-P024DC2GLC42V	1SVR405606R1010	10	0.057 (0.126)
		Varistor and LED red, holder	logical	spring	CR-P024DC2GLC62C	1SVR405606R1013	10	0.057 (0.126)
		Varistor and LED green, holder	logical	spring	CR-P024DC2GLC62CV	1SVR405606R1011	10	0.057 (0.126)
110 V DC	2 c/o	Reverse polarity protection and freewheeling diode, LED green, holder	standard	screw	CR-P110DC2SS42CV	1SVR405601R8010	10	0.057 (0.126)
24 V AC	2 c/o	Varistor and LED green, holder	standard	screw	CR-P024AC2SS62CV	1SVR405601R0010	10	0.057 (0.126)
120 V AC	2 c/o	Varistor and LED green, holder	standard	screw	CR-P120AC2SS92CV	1SVR405601R2010	10	0.057 (0.126)
230 V AC	2 c/o	Reverse polarity protection and freewheeling diode, LED green, holder	standard	screw	CR-P230AC2SS92CV	1SVR405601R3110	10	0.057 (0.126)
		Varistor and LED green, holder	logical	screw	CR-P230AC2LS92CV	1SVR405601R3011	10	0.057 (0.126)
		Diode and LED red, holder	logical	spring	CR-P230AC2LC92	1SVR405601R3012	10	0.057 (0.126)
230 V AC	2 c/o gold plated	Diode and LED red, holder	logical	spring	CR-P230AC2GLC92	1SVR405606R3013	10	0.057 (0.126)
		Varistor and LED red, holder	logical	spring	CR-P230AC2GLC92C	1SVR405606R3012	10	0.057 (0.126)
		Varistor and LED green, holder	logical	spring	CR-P230AC2GLC92CV	1SVR405606R3010	10	0.057 (0.126)

Pluggable interface relays and optocouplers

Ordering details – CR-M range



CR-M

The CR-M range offers the possibility of switching up to 4 different circuits with a single relay. The integrated LED and test button* allow for easy testing and commissioning. This range of relays are available at a wide range of different coil voltages and are accompanied by a wide variety of function modules. The CR-M range also includes complete versions consisting of a relay, socket, holder, marker and where applicable, function module.

Ordering details - CR-M range without LED

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	2 c/o (SPDT)	250 V, 12 A	CR-M012DC2	1SVR405611R4000	10	0.033 (0.073)
24 V DC			CR-M024DC2	1SVR405611R1000		
48 V DC			CR-M048DC2	1SVR405611R6000		
60 V DC			CR-M060DC2	1SVR405611R4200		
110 V DC			CR-M110DC2	1SVR405611R8000		
125 V DC			CR-M125DC2	1SVR405611R8200		
220 V DC			CR-M220DC2	1SVR405611R9000		
24 V AC			CR-M024AC2	1SVR405611R0000		
48 V AC			CR-M048AC2	1SVR405611R5000		
110 V AC			CR-M110AC2	1SVR405611R7000		
120 V AC			CR-M120AC2	1SVR405611R2000		
230 V AC			CR-M230AC2	1SVR405611R3000		
12 V DC	3 c/o (SPDT)	250 V, 10 A	CR-M012DC3	1SVR405612R4000	10	0.033 (0.073)
24 V DC			CR-M024DC3	1SVR405612R1000		
48 V DC			CR-M048DC3	1SVR405612R6000		
60 V DC			CR-M060DC3	1SVR405612R4200		
110 V DC			CR-M110DC3	1SVR405612R8000		
125 V DC			CR-M125DC3	1SVR405612R8200		
220 V DC			CR-M220DC3	1SVR405612R9000		
24 V AC			CR-M024AC3	1SVR405612R0000		
48 V AC			CR-M048AC3	1SVR405612R5000		
60 V AC			CR-M060AC3	1SVR405612R5200		
110 V AC			CR-M110AC3	1SVR405612R7000		
120 V AC			CR-M120AC3	1SVR405612R2000		
230 V AC			CR-M230AC3	1SVR405612R3000		
12 V DC	4 c/o (SPDT)	250 V, 6 A	CR-M012DC4	1SVR405613R4000	10	0.033 (0.073)
24 V DC			CR-M024DC4	1SVR405613R1000		
48 V DC			CR-M048DC4	1SVR405613R6000		
60 V DC			CR-M060DC4	1SVR405613R4200		
110 V DC			CR-M110DC4	1SVR405613R8000		
125 V DC			CR-M125DC4	1SVR405613R8200		
220 V DC			CR-M220DC4	1SVR405613R9000		
24 V AC			CR-M024AC4	1SVR405613R0000		
48 V AC			CR-M048AC4	1SVR405613R5000		
110 V AC			CR-M110AC4	1SVR405613R7000		
120 V AC			CR-M120AC4	1SVR405613R2000		
230 V AC			CR-M230AC4	1SVR405613R3000		

* Note: During the operation of the relay, the temperature of the test button will increase. In order to manually operate the test button, the supply voltage should first be disconnected. The test button is only safe to operate once it has cooled down or by using protective gloves and insulated tools. During operation, the test button should be pressed smoothly and quickly. When the test button is depressed, the n/o contacts will close and remain closed. Once the button is released, the n/o contacts change status and open. A 90 degree rotation of the test button closes and holds the n/o contacts in a closed position. Reverse rotation of the test button will once again change the status of the n/o contacts to their default open position.

Pluggable interface relays and optocouplers

Ordering details – CR-M range



CR-M

Ordering details - CR-M range with LED

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	2 c/o (SPDT)	250 V, 12 A	CR-M012DC2L	1SVR405611R4100	10	0.033 (0.073)
24 V DC			CR-M024DC2L	1SVR405611R1100		
48 V DC			CR-M048DC2L	1SVR405611R6100		
60 V DC			CR-M060DC2L	1SVR405611R4300		
110 V DC			CR-M110DC2L	1SVR405611R8100		
125 V DC			CR-M125DC2L	1SVR405611R8300		
220 V DC			CR-M220DC2L	1SVR405611R9100		
12 V AC			CR-M012AC2L	1SVR405611R0300		
24 V AC			CR-M024AC2L	1SVR405611R0100		
48 V AC			CR-M048AC2L	1SVR405611R5100		
110 V AC			CR-M110AC2L	1SVR405611R7100		
120 V AC			CR-M120AC2L	1SVR405611R2100		
230 V AC			CR-M230AC2L	1SVR405611R3100		
12 V DC	3 c/o (SPDT)	250 V, 10 A	CR-M012DC3L	1SVR405612R4100	10	0.033 (0.073)
24 V DC			CR-M024DC3L	1SVR405612R1100		
48 V DC			CR-M048DC3L	1SVR405612R6100		
60 V DC			CR-M060DC3L	1SVR405612R4300		
110 V DC			CR-M110DC3L	1SVR405612R8100		
125 V DC			CR-M125DC3L	1SVR405612R8300		
220 V DC			CR-M220DC3L	1SVR405612R9100		
12 V AC			CR-M012AC3L	1SVR405612R0300		
24 V AC			CR-M024AC3L	1SVR405612R0100		
48 V AC			CR-M048AC3L	1SVR405612R5100		
110 V AC			CR-M110AC3L	1SVR405612R7100		
120 V AC			CR-M120AC3L	1SVR405612R2100		
230 V AC			CR-M230AC3L	1SVR405612R3100		
12 V DC	4 c/o (SPDT)	250 V, 6 A	CR-M012DC4L	1SVR405613R4100	10	0.033 (0.073)
24 V DC			CR-M024DC4L	1SVR405613R1100		
48 V DC			CR-M048DC4L	1SVR405613R6100		
60 V DC			CR-M060DC4L	1SVR405613R4300		
110 V DC			CR-M110DC4L	1SVR405613R8100		
125 V DC			CR-M125DC4L	1SVR405613R8300		
220 V DC			CR-M220DC4L	1SVR405613R9100		
12 V AC			CR-M012AC4L	1SVR405613R0300		
24 V AC			CR-M024AC4L	1SVR405613R0100		
48 V AC			CR-M048AC4L	1SVR405613R5100		
110 V AC			CR-M110AC4L	1SVR405613R7100		
120 V AC			CR-M120AC4L	1SVR405613R2100		
230 V AC			CR-M230AC4L	1SVR405613R3100		

Pluggable interface relays and optocouplers

Ordering details – CR-M range



CR-M

Ordering details - CR-M range with LED and free-wheeling diode

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	2 c/o (SPDT)	250 V, 6 A	CR-M012DC2LD	1SVR405611R4400	10	0.033 (0.073)
24 V DC			CR-M024DC2LD	1SVR405611R1400	10	0.033 (0.073)
48 V DC			CR-M048DC2LD	1SVR405611R6400	10	0.033 (0.073)
110 V DC			CR-M110DC2LD	1SVR405611R8400	10	0.033 (0.073)
125 V DC			CR-M125DC2LD	1SVR405611R8500	10	0.033 (0.073)
220 V DC			CR-M220DC2LD	1SVR405611R9400	10	0.033 (0.073)
12 V DC	3 c/o (SPDT)	250 V, 10 A	CR-M012DC3LD	1SVR405612R4400	10	0.033 (0.073)
24 V DC			CR-M024DC3LD	1SVR405612R1400	10	0.033 (0.073)
48 V DC			CR-M048DC3LD	1SVR405612R6400	10	0.033 (0.073)
110 V DC			CR-M110DC3LD	1SVR405612R8400	10	0.033 (0.073)
125 V DC			CR-M125DC3LD	1SVR405612R8500	10	0.033 (0.073)
220 V DC			CR-M220DC3LD	1SVR405612R9400	10	0.033 (0.073)
12 VDC	4 c/o (SPDT)	250 V, 6 A	CR-M012DC4LD	1SVR405613R4400	10	0.033 (0.073)
24 V DC			CR-M024DC4LD	1SVR405614R1100	10	0.033 (0.073)
48 V DC			CR-M048DC4LD	1SVR405613R6400	10	0.033 (0.073)
110 V DC			CR-M110DC4LD	1SVR405613R8400	10	0.033 (0.073)
125 V DC			CR-M125DC4LD	1SVR405613R8500	10	0.033 (0.073)
220 V DC			CR-M220DC4LD	1SVR405613R9400	10	0.033 (0.073)

Ordering details - CR-M range with gold contacts

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V DC	4 c/o (SPDT)	250 V, 6 A	CR-M024DC4G	1SVR405618R1000	10	0.033 (0.073)
24 V AC			CR-M024AC4G	1SVR405618R0000		
110 V AC			CR-M110AC4G	1SVR405618R7000		
230 V AC			CR-M230AC4G	1SVR405618R3000		

Pluggable interface relays and optocouplers

Ordering details – CR-M range



CR-M

Ordering details – CR-M range with gold contacts and LED

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	4 c/o (SPDT)	250 V / 6 A	CR-M012DC4LG	1SVR405618R4100	10	0.033 (0.073)
24 V DC			CR-M024DC4LG	1SVR405618R1100		
48 V DC			CR-M048DC4LG	1SVR405618R6100		
60 V DC			CR-M060DC4LG	1SVR405618R4300		
110 V DC			CR-M110DC4LG	1SVR405618R8100		
125 V DC			CR-M125DC4LG	1SVR405618R8300		
220 V DC			CR-M220DC4LG	1SVR405618R9100		
24 V AC			CR-M024AC4LG	1SVR405618R0100	10	0.033 (0.073)
48 V AC			CR-M048AC4LG	1SVR405618R5100		
110 V AC			CR-M110AC4LG	1SVR405618R7100		
120 V AC			CR-M120AC4LG	1SVR405618R2100		
230 V AC			CR-M230AC4LG	1SVR405618R3100		

Ordering details – CR-M range with gold contacts, LED and free-wheeling diode

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	4 c/o (SPDT)	250 V / 6 A	CR-M012DC4LDG	1SVR405618R4400	10	0.033 (0.073)
24 V DC			CR-M024DC4LDG	1SVR405618R1400		

Pluggable interface relays and optocouplers

Ordering details – CR-M range



CR-M complete version

Ordering details – CR-M range complete version

Rated control supply voltage	Out-puts	Description	Socket type	Connec-tion terminal	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	4 c/o gold-plated	LED red, holder	standard	screw	CR-M012DC4LDGSS	1SVR405618R4410	10	0.0109 (0.024)
24 V DC	4 c/o	Reverse polarity protection and free-wheeling diode, LED green, holder	standard	screw	CR-M024DC4SS42V	1SVR405613R1010	10	0.0109 (0.024)
		Reverse polarity protection and free-wheeling diode, LED green, holder	logical	screw	CR-M024DC4LS42V	1SVR405613R1011	10	0.0109 (0.024)
		Reverse polarity protection and free-wheeling diode, LED red, holder	logical	spring	CR-M024DC4LC42	1SVR405613R1012	10	0.0109 (0.024)
24 V DC	4 c/o gold-plated	Reverse polarity protection and free-wheeling diode, LED green, holder	standard	screw	CR-M024DC4GSS42V	1SVR405618R1011	10	0.0109 (0.024)
		Varistor, LED green, holder	logical	spring	CR-M024DC4GLC62CV	1SVR405618R1010	10	0.0109 (0.024)
		LED, free-wheeling diode, holder	logical	spring	CR-M024DC4LGLC22	1SVR405618R1110	10	0.0109 (0.024)
		LED red, free-wheeling diode, holder	standard	screw	CR-M024DC4LDGSS	1SVR405618R1410	10	0.0109 (0.024)
24 V AC	4 c/o	Varistor and LED green, holder	logical	screw	CR-M024AC4LS62CV	1SVR405613R0010	10	0.0109 (0.024)

Pluggable interface relays and optocouplers

Ordering details – CR-M range



CR-M complete version

Ordering details – CR-M range complete version


Rated control supply voltage	Out-puts	Description	Socket type	Connection terminal	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
230 V AC	4 c/o	Varistor, LED green, holder	standard	screw	CR-M230AC4SS92CV	1SVR405613R3110	10	0.0109 (0.024)
		Varistor, LED green, holder	logical	screw	CR-M230AC4LS92CV	1SVR405613R3011	10	0.0109 (0.024)
		Diode and LED red, holder	logical	spring	CR-M230AC4LC92	1SVR405613R3012	10	0.0109 (0.024)
230 V AC	4 c/o gold-pla-ted	Reverse polarity protection and free-wheeling diode, LED green, holder	standard	screw	CR-M230AC4GSS92CV	1SVR405618R3112	10	0.0109 (0.024)
		LED red, holder	logical	screw	CR-M230AC4LGLC	1SVR405618R3110	10	0.0109 (0.024)
		LED red, holder	standard	screw	CR-M230AC4LGSS	1SVR405618R3111	10	0.0109 (0.024)

Pluggable interface relays and optocouplers

Ordering details – CR-M range



CR-M2LS



CR-M4SS

Standard and logical sockets for CR-M interface relays are suitable for snap-on mounting onto a DIN rail. Optional function modules for the CR-M range are plugged into both standard and logical sockets.

Ordering details - Sockets*

Version	Connection terminal	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
Logical socket for 2 c/o	screw	CR-M2LS	1SVR405651R1100	10	0.055 (0.121)
Logical socket for 3 c/o		CR-M3LS	1SVR405651R2100		0.062 (0.137)
Logical socket for 2/4 c/o		CR-M4LS	1SVR405651R3100		0.066 (0.146)
Logical socket for 2 c/o	spring	CR-M2LC	1SVR405651R1200	10	0.065 (0.143)
Logical socket for 2/4 c/o		CR-M4LC	1SVR405651R3200		0.066 (0.146)
Standard socket for 2 c/o	screw	CR-M2SS	1SVR405651R1000	10	0.066 (0.146)
Standard socket for 3 c/o		CR-M3SS	1SVR405651R2000		0.068 (0.150)
Standard socket for 2/4 c/o		CR-M4SS	1SVR405651R3000		0.070 (0.154)
Standard socket for 2 c/o	fork type	CR-M2SF	1SVR405651R1300	10	0.040 (0.088)
Standard socket for 2/4 c/o		CR-M4SF	1SVR405651R3300		0.048 (0.106)


*All CR-M socket packages include a set of markers.

Standard sockets

Position of connection terminals: coil connection (A1-A2) on lower side of the socket, contact connections (n/o and n/c contacts) on the lower and upper side of the socket.

Logical sockets

Position of connection terminals: coil connection (A1-A2) on lower side of the socket, all contact connections (common contacts, n/o and n/c contacts) on upper side of the socket.



CR-MJ

Ordering details - Accessories

Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
Plastic holder for socket	CR-MH	1SVR405659R1000	10	0.003 (0.007)
Metal holder for socket	CR-MH1	1SVR405659R1100	10	0.0005 (0.001)
Jumper bar for sockets with screw connection	CR-MJ	1SVR405658R6000	10	0.029 (0.064)
Marker for CR-M standard sockets	CR-MM	1SVR405658R1000	10	0.0005 (0.001)
Plug for test button replacement	CR-MP	1SVR405658R2000	100	0.001 (0.002)

Pluggable interface relays and optocouplers

Ordering details – CR-P/M function modules



CR-P/M ...

Ordering details - Diode - Reverse polarity protection / free-wheeling diode

Rated control supply voltage U_s	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-220 V DC	**A1+, A2-**	**CR-P/M 22**	1SVR405651R0000	10	0.003 (0.007)

Ordering details - Diode and LED - Reverse polarity protection / free-wheeling diode and LED to indicate energized coil

Rated control supply voltage U_s	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-24 V DC	red, A1+, A2-	CR-P/M 42	1SVR405652R0000	10	0.003 (0.007)
6-24 V DC	green, A1+, A2-	CR-P/M 42 V	1SVR405652R1000		
24-60 V DC	red, A1+, A2-	CR-P/M 42 B	1SVR405652R4000		
24-60 V DC	green, A1+, A2-	CR-P/M 42 BV	1SVR405652R4100		
110 V DC	red, A1+, A2-	CR-P/M 42 C	1SVR405652R9000		
110 V DC	green, A1+, A2-	CR-P/M 42 CV	1SVR405652R9100		

Ordering details - RC element - Spark quenching

Rated control supply voltage U_s	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-24 V AC/DC		CR-P/M 52B	1SVR405653R0000	10	0.003 (0.007)
24-60 V AC/DC		CR-P/M 52D	1SVR405653R4000		
110-230 V AC/DC		CR-P/M 52C	1SVR405653R1000		

Ordering details - Diode and LED - LED to indicate energized coil

Rated control supply voltage U_s	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-24 V AC/DC	red, for DC: A1+, A2-	CR-P/M 62	1SVR405654R0000	10	0.003 (0.007)
6-24 V AC/DC	green, for DC: A1+, A2-	CR-P/M 62 V	1SVR405654R1000		
24-60 V AC/DC	red, for DC: A1+, A2-	CR-P/M 62 E	1SVR405654R4000		
24-60 V AC/DC	green, for DC: A1+, A2-	CR-P/M 62 EV	1SVR405654R4100		
110-230 V AC/DC	red, for DC: A1+, A2-	CR-P/M 92	1SVR405654R0100		
110-230 V AC/DC	green, for DC: A1+, A2-	CR-P/M 92 V	1SVR405654R1100		

Pluggable interface relays and optocouplers

Ordering details – CR-P/M function modules



2CDC291 005S0011

CR-P/M ...

Ordering details - Varistor and LED - Overvoltage protection and LED to indicate energized coil

Rated control supply voltage U_s	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-24 V AC/DC	red, for DC: A1+, A2-	CR-P/M 62 C	1SVR405655R0000	10	0.003 (0.007)
6-24 V AC/DC	green, for DC: A1+, A2-	CR-P/M 62 CV	1SVR405655R1000		
24-60 V AC/DC	red, for DC: A1+, A2-	CR-P/M 62 D	1SVR405655R4000		
24-60 V AC/DC	green, for DC: A1+, A2-	CR-P/M 62 DV	1SVR405655R4100		
110-230 V AC/DC	red, for DC: A1+, A2-	CR-P/M 92 C	1SVR405655R0100		
110-230 V AC/DC	green, for DC: A1+, A2-	CR-P/M 92 CV	1SVR405655R1100		

Ordering details - Varistor - Overvoltage protection

Rated control supply voltage U_s	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V AC		CR-P/M 72	1SVR405656R0000	10	0.002 (0.004)
115 V AC		CR-P/M 72 A	1SVR405656R1000		
230 V AC		CR-P/M 82	1SVR405656R2000		

Pluggable interface relays and optocouplers

Ordering details – CR-U range



2CDC 291 047 F0004

CR-U

The CR-U range offers up to 3 change over contacts in single relay. The integrated LED and test button* allow for easy testing and commissioning. This robust range of relays are available at a wide range of different coil voltages and are accompanied by a wide variety of function modules.

Ordering details - CR-U range without LED

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	2 c/o (SPDT)	250 V, 10 A	CR-U012DC2	1SVR405621R4000	10	0.083 (0.183)
24 V DC			CR-U024DC2	1SVR405621R1000		
48 V DC			CR-U048DC2	1SVR405621R6000		
110 V DC			CR-U110DC2	1SVR405621R8000		
220 V DC			CR-U220DC2	1SVR405621R9000		
24 V AC			CR-U024AC2	1SVR405621R0000		
48 V AC			CR-U048AC2	1SVR405621R5000		
110 V AC			CR-U110AC2	1SVR405621R7000		
120 V AC			CR-U120AC2	1SVR405621R2000		
230 V AC			CR-U230AC2	1SVR405621R3000		
12 V DC	3 c/o (SPDT)	250 V, 10 A	CR-U012DC3	1SVR405622R4000	10	0.083 (0.183)
24 V DC			CR-U024DC3	1SVR405622R1000		
48 V DC			CR-U048DC3	1SVR405622R6000		
110 V DC			CR-U110DC3	1SVR405622R8000		
125 V DC			CR-U125DC3	1SVR405622R8200		
220 V DC			CR-U220DC3	1SVR405622R9000		
24 V AC			CR-U024AC3	1SVR405622R0000		
48 V AC			CR-U048AC3	1SVR405622R5000		
60 V AC			CR-U060AC3	1SVR405622R5200		
110 V AC			CR-U110AC3	1SVR405622R7000		
120 V AC			CR-U120AC3	1SVR405622R2000		
230 V AC			CR-U230AC3	1SVR405622R3000		

* Note: During the operation of the relay, the temperature of the test button will increase. In order to manually operate the test botton, the supply voltage should first be disconnected. The test button is only safe to operate once it has cooled down or by using protective gloves and insulated tools. During operation, the test button should be pressed smoothly and quickly. When the test button is depressed, the n/o contacts will close and remain closed. Once the button is released, the n/o contacts change status and open. A 90 degree rotation of the test button closes and holds the n/o contacts in a closed position. Reverse rotation of the test button will once again change the status of the n/o contacts to their default open position.

Ordering details - CR-U range with LED

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	2 c/o (SPDT)	250 V, 10 A	CR-U012DC2L	1SVR405621R4100	10	0.083 (0.183)
24 V DC			CR-U024DC2L	1SVR405621R1100		
48 V DC			CR-U048DC2L	1SVR405621R6100		
110 V DC			CR-U110DC2L	1SVR405621R8100		
220 V DC			CR-U220DC2L	1SVR405621R9100		
12 V AC			CR-U012AC2L	1SVR405621R0300		
24 V AC			CR-U024AC2L	1SVR405621R0100		
48 V AC			CR-U048AC2L	1SVR405621R5100		
110 V AC			CR-U110AC2L	1SVR405621R7100		
120 V AC			CR-U120AC2L	1SVR405621R2100		
230 V AC			CR-U230AC2L	1SVR405621R3100		

Pluggable interface relays and optocouplers

Ordering details – CR-U range

Ordering details - CR-U range with LED

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	3 c/o (SPDT)	250 V, 10 A	CR-U012DC3L	1SVR405622R4100	10	0.083 (0.183)
24 V DC			CR-U024DC3L	1SVR405622R1100		
48 V DC			CR-U048DC3L	1SVR405622R6100		
110 V DC			CR-U110DC3L	1SVR405622R8100		
220 V DC			CR-U220DC3L	1SVR405622R9100		
12 V AC			CR-U012AC3L	1SVR405622R0300		
24 V AC			CR-U024AC3L	1SVR405622R0100		
48 V AC			CR-U048AC3L	1SVR405622R5100		
110 V AC			CR-U110AC3L	1SVR405622R7100		
120 V AC			CR-U120AC3L	1SVR405622R2100		
230 V AC			CR-U230AC3L	1SVR405622R3100		



2CDC 291 047 F0004

CR-U

Ordering details - CR-U range with LED and free-wheeling diode

Rated control supply voltage	Outputs	Contact ratings	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
12 V DC	2 c/o (SPDT)	250 V, 10 A	CR-U012DC2LD	1SVR405621R4400	10	0.033 (0.073)
24 V DC			CR-U024DC2LD	1SVR405621R1400	10	0.033 (0.073)
48 V DC			CR-U048DC2LD	1SVR405621R6400	10	0.033 (0.073)
110 V DC			CR-U110DC2LD	1SVR405621R8400	10	0.033 (0.073)
12 V DC	3 c/o (SPDT)		CR-U012DC3LD	1SVR405622R4400	10	0.033 (0.073)
24 V DC			CR-U024DC3LD	1SVR405623R1100	10	0.033 (0.073)
48 V DC			CR-U048DC3LD	1SVR405622R6400	10	0.033 (0.073)
110 V DC			CR-U110DC3LD	1SVR405622R8400	10	0.033 (0.073)

The sockets for CR-U interface relays have screw connection terminals and are suitable for snap-on mounting onto a DIN rail. Optional function modules for the CR-U range may only be plugged into compatible standard sockets.

Ordering details - Sockets and Accessories

Version	Type	Order code	Pkg qty	Weight (1 pc.) kg
Socket for 2 c/o and function module	CR-U2S	1SVR405670R0000	10	0.065
Socket for 3 c/o and function module	CR-U3S	1SVR405660R0000		0.065
Socket for 3 c/o	CR-U3E	1SVR405660R0100		0.065
Small socket for 2 c/o	CR-U2SM	1SVR405670R1100		0.054
Small socket for 3 c/o	CR-U3SM	1SVR405660R1100		0.058
Metal holder for socket	CR-UH	1SVR405669R0000		0.001



2CDC 291 007 S0011

CR-U2S

CR-U sockets
Position of connection terminals: coil connection (A1-A2) on lower side of socket, contact connections (n/o and n/c contacts) on the lower and upper side of socket.

Pluggable interface relays and optocouplers

Ordering details – CR-U function modules



CR-U...

CR-U function modules are compatible with the CR-U2S and CR-U3S sockets only.

Diode - Reverse polarity protection / free-wheeling diode

Rated control supply voltage	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-220 V DC	A1+, A2-	CR-U 21	1SVR405661R0000	10	0.007 (0.015)

Diode and LED - Reverse polarity protection / free-wheeling diode and LED to indicate energized coil

Rated control supply voltage	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-24 V DC	red, A1+, A2-	CR-U 41	1SVR405662R0000	10	0.007 (0.015)
6-24 V DC	green, A1+, A2-	CR-U 41V	1SVR405662R1000		
24-60 V DC	red, A1+, A2-	CR-U 41B	1SVR405662R4000		
24-60 V DC	green, A1+, A2-	CR-U 41BV	1SVR405662R4100		
110 V DC	red, A1+, A2-	CR-U 41C	1SVR405662R9000		
110 V DC	green, A1+, A2-	CR-U 41CV	1SVR405662R9100		

RC element - Spark quenching

Rated control supply voltage	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-24 V AC/DC		CR-U 51B	1SVR405663R0000	10	0.007 (0.015)
24-60 V AC/DC		CR-U 51D	1SVR405663R4000		
110 -230 V AC/DC		CR-U 51C	1SVR405663R1000		

Diode and LED - LED to indicate energized coil

Rated control supply voltage	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-24 V AC/DC	red, for DC A1+, A2-	CR-U 61	1SVR405664R0000	10	0.007 (0.015)
6-24 V AC/DC	green, for DC A1+, A2-	CR-U 61V	1SVR405664R1000		
24-60 V AC/DC	red, for DC A1+, A2-	CR-U 61E	1SVR405664R4000		
24-60 V AC/DC	green, for DC A1+, A2-	CR-U 61EV	1SVR405664R4100		
110-230 V AC/DC	red, for DC A1+, A2-	CR-U 91	1SVR405664R0100		
110-230 V AC/DC	green, for DC: A1+, A2-	CR-U 91V	1SVR405664R1100		

Pluggable interface relays and optocouplers

Ordering details – CR-U function modules



2CDC 291 004 S0011

CR-U...

Varistor and LED - Overvoltage protection and LED to indicate energized coil

Rated control supply voltage	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
6-24 V AC/DC	red, for DC A1+, A2-	CR-U 61C	1SVR405665R0000	10	0.007 (0.015)
6-24 V AC/DC	green, for DC A1+, A2-	CR-U 61CV	1SVR405665R1000		
24-60 V AC/DC	red, for DC A1+, A2-	CR-U 61D	1SVR405665R4000		
24-60 V AC/DC	green, for DC A1+, A2-	CR-U 61DV	1SVR405665R4100		
110-230 V AC/DC	red, for DC A1+, A2-	CR-U 91C	1SVR405665R0100		
110-230 V AC/DC	green, for DC A1+, A2-	CR-U 91CV	1SVR405665R1100		



2CDC 291 032 F0005

CR-U T

Varistor - Overvoltage protection

Rated control supply voltage	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V AC		CR-U 71	1SVR405666R0000	10	0.007 (0.015)
115 V AC		CR-U 71A	1SVR405666R1000		
230 V AC		CR-U 81	1SVR405666R2000		

Multi-function time module*

Rated control supply voltage	Version	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24-240 V AC/DC	green LED	CR-U T	1SVR405667R0000	10	0.014 (0.031)

* For more details, refer to the CR-U T datasheet.

Pluggable interface relays and optocouplers

Technical data - CR-S interface relays

Input circuit							
	Rated control supply voltage U_s	**Make voltage (at 23 °C)**	**Maximum voltage (at 55 °C)**	**Break voltage**	**Rated power**	**Coil resistance (at 23 °C)**	**Tolerance of coil resistance**
CR-S005VDC1R(G)	5 V DC	3.75 V DC	7.5 V DC	0.25 V DC	170 mW	147 Ω	± 10 %
CR-S012VDC1R(G)	12 V DC	9 V DC	18 V DC	0.6 V DC	170 mW	848 Ω	± 10 %
CR-S024VDC1R(G)	24 V DC	18 V DC	36 V DC	1.2 V DC	170 mW	3390 Ω	± 15 %
CR-S048VDC1R(G)	48 V DC	36 V DC	72 V DC	2.4 V DC	210 mW	10600 Ω	± 15 %
CR-S060VDC1R(G)	60 V DC	45 V DC	90 V DC	3 V DC	210 mW	16600 Ω	± 15 %

Output circuits			
Output circuit(s)			11-12/14
Kind of output			1 c/o (SPDT)
Contact material			$AgSnO_2$ or $AgSnO_2$/Au
Rated operational voltage U_e (IEC/EN 60947-1)			250 V AC
Minimum switching voltage			5 V at 100 mA ($AgSnO_2$) / 5 V at 12 mA ($AgSnO_2$/Au)
Maximum switching voltage			400 V AC / 250 V DC
Minimum switching current			10 mA at 10 V ($AgSnO_2$) / 3 mA at 20 V ($AgSnO_2$/Au)
Rated free air thermal current I_{th}			5 A
Rated operational current (IEC/EN 60947-5-1)	AC12 (resistive)	230 V	6 A
	AC15 (inductive)	230 V	1.5 A
	AC15 (inductive)	120 V	3 A
	DC12 (resistive)	24 V	6 A
	DC13 (inductive)	24 V	1 A
	DC13 (inductive)	120 V	0.22 A
	DC13 (inductive)	250 V	0.11 A
AC rating (UL 508; NEMA ICS-5)	utilization category (pilot duty) (contact rating code designation)		B300
DC rating (UL 508; NEMA ICS-5)	utilization category (pilot duty) (contact rating code designation)		R300
Maximum making (inrush) current			15 A, 240 V AC
Minimum switching power			100 mA/12 V ($AgSnO_2$) / 50 mW ($AgSnO_2$/Au)
Maximum switching (breaking) power	AC1 (resistive)		1500 VA, 250 V AC
Contact resistance			100 mΩ (at 1 A/ 6 V DC)
Maximum operating frequency	rated load AC1		360 switching cycles/h
	without load		18000 switching cycles/h
Mechanical lifetime			1 x 10^7 switching cycles
Electrical lifetime	AC1 (resistive)		(n/c) 3 x 10^4 switching cycles (at +85 °C) (n/o) 1 x 10^4 switching cycles (at +85 °C)
Response time			8 ms
Release time			4 ms
Isolation data			
Rated insulation voltage			250 V AC
Rated impulse withstand voltage U_{imp}	between coil and contacts		4000 V 1 min
	between open contacts		1000 V 1 min
Clearance	between coil and contacts		5.5 mm (0.217 in)
Creepage distance	between coil and contacts		8 mm (0.315 in)
Overvoltage category			III
Pollution degree			2
General data			
Dimensions			see 'Dimensional drawings'
Mounting			on socket
Mounting position			any
Degree of protection			RT II and RT III

Pluggable interface relays and optocouplers

Technical data - CR-S interface relays and CR-S optocouplers

Electrical connection		
Connection		by socket
Environmental data		
Ambient temperature range	operation	-40...+85 °C
	storage	-40...+85 °C
Vibration resistance (10-150 Hz)	n/o contact	10 Hz to 55 Hz 1 mm DA
	n/c contact	10 Hz to 55 Hz 1 mm DA
Shock resistance	n/o contact	function 49 m/s² / destructive 980 m/s²
	n/c contact	function 49 m/s² / destructive 980 m/s²
Standards/directives		
Standards		IEC/EN 61810-1
RoHS Directive		2011/65/EU

Technical data - CR-S optocouplers

Input circuit		**CR-S024VDC1TRA**	**CR-S024VDC1MOS**	**CR-S024VDC1TRI**
Input resistance		3400 Ohm		
Rated control voltage		24 V DC*		
Pull-in voltage		15 V DC		
Maximum input voltage		30 V DC		
Nominal input current		7 mA		
Input power		168 mW		
Typical switching-on time		< 40 ms	< 60 ms	< 1/2 cycle
Typical switch-off time		< 600 ms	< 600 ms	< 1/2 cycle
Output circuits				
Output circuit(s)		11 (13+) - 14	11 (13+) - 14	11 (13+) - 14
Kind of output		Transistor	MOS-FET	Triac
Rated operational voltage		48 V DC	24 V DC	240 V AC
Maximum switching voltage		48 V DC	24 V DC	275 V AC
Minimum switching current		50 mA	50 mA	22 mA
Maximum switching current continuously		100 mA	2 A	2 A
Leakage current at maximum switching voltage		<1 mA	<1 mA	< 1.5 mA
Voltage drop at rated current		< 120 mV DC	< 120 mV DC	< 1.6 V AC
Isolation data				
Rated insulation voltage	input/output	2.5 kV		
Insulation class		2		
Clearance	input/output	14 mm		
Creepage distance	input/output	14 mm		
Overvoltage category		III		
Pollution degree		2		
General data				
Dimensions		see 'Dimensional drawings'		
Weight		3.5 g (0.007 lb)		
Mounting		on socket		
Environmental data				
Ambient temperature	operation	-30…+80 °C		
	storage	-40…+100 °C		
Standards / Directives				
Standards		IEC/EN 62314		
EMC Directive		2014/30/EN		
RoHS Directive		2011/65/EN		

* The output circuit should not exceed 30 m.

Pluggable interface relays and optocouplers

Technical data - CR-S sockets

Input circuit		**CR-S 6-24 V**	**CR-S 12-24 V**	**CR-S 48-60 V**	**CR-S 110-125 V**	**CR-S 220-240 V**
Rated control supply voltage U_s		6-24 V DC	12-24 V AC/DC*	48-60 V AC/DC	110-125 V AC/DC	220-240 V AC/DC
Rated control supply voltage U_s tolerance		(0.8-1.2) U_n	(0.8-1.1) U_n			
Typical current		11-29 mA	11-16 mA	3.6-4.5 mA	3.6 mA	3.6 mA
Response time		8 ms				
Release time		4 ms				
Status device		green LED				
Protective circuit		yes				
Output circuits						
Output circuit(s)		11-12/14				
Number of poles		1				
Rated voltage		250 V AC				
Rated current		6 A				
General data for CR-S with screw connection terminal						
Dimensions		see 'Dimensional drawings'				
Degree of protection (EN 60529)		Degree of protection (EN 60529) IP20 (terminals)				
Temperature range	operation	-40...+70 °C			-40...+55 °C	
	storage	-40...+85 °C				
Connection type		Screw				
Maximum number of wires per connection terminal		2				
Connecting capacity	rigid	2 x 0.5 - 1.5 mm² (2 x 20 - 16 AWG)				
	fine-strand					
	with wire end ferule	2 x 0.5 - 1 mm² (2 x 20 - 18 AWG)				
Tightening torque		0.5 Nm (4.426 lb.in)				
Stripping length		7 mm (0.28 in)				
Minimum clamping force for fine-strand wire	with 0.2 mm²	10 N				
	with 1.5 mm²	40 N				
Mounting (IEC/EN 60715)		DIN rail				
Material	socket	PA6 +GF-V2				
	contacts	CuZn36				
	contact surface	3 µ Ni/Sn				
	terminals	CuZn40, 3 µ Ni				
	combi screw M3	Fe				
General data for CR-S with spring connection terminal						
Dimensions without holder (L x W x H)		see 'Dimensional drawings'				
Degree of protection (EN 60529)		Degree of protection (EN 60529) IP20 (terminals)				
Temperature range	operation	-40...+70 °C			-40...+55 °C	
	storage	-40...+85 °C				
Connection type		Spring				
Maximum number of wires per connection terminal		1				
Connecting capacity		0.75 - 2.5 mm² (20 - 14 AWG) rigid, fine-strand and with wire end ferrule				
Stripping length		7 mm (0.28 in)				
Mounting (IEC/EN 60715)		DIN rail				
Material	socket	PA6 +GF-V2				
	contacts	CuZn36				
	contact surface	3 µ Ni/Sn				
	spring terminals	SUS301				
Isolation data						
Isolation between coil and contacts		5000 V AC				
Resistance to shock coil to contact		1000 MΩ				
Clearance and creepage distance		IEC/EN 61984				
Standards / Directives						
Standard		IEC/EN 61984				
Low Voltage Directive		2014/35/EU				
RoHS Directive		2011/65/EU				

* In combination with optocouplers, only DC supply is allowed

Pluggable interface relays and optocouplers

Technical data - CR-S jumper bars

Rated operational voltage / current		CR-SJB20-BLUE	CR-SJB20-RED	CR-SJB20-BLACK
Rated operational voltage		250 V AC		
Rated operational current		36 A		
Electrical connection				
Jumper bar cross section		123.2 mm (4.850 in)		
Step distance		6.3 mm (0.248 in)		
Rail length	with isolation	16.7 mm (0.657 in)		
	without isolation	6.7 mm (0.264 in)		
Stripping length of a connection wire that is used in combination with a jumper bar		7 mm (0.276 in)		
Environmental data				
Ambient temperature range	operation	-40 ... +70 °C		
General data				
Material of rail		Cu		
Number of pins		20		
Flammability		V0		

Pluggable interface relays and optocouplers

Technical data – CR-P, CR-M, CR-U

Input circuit - coil data

CR-P range

	Rated control supply voltage U_s	Rated frequency	Make voltage (at 20 °C)	Maximum voltage (at 55 °C)	Break voltage	Rated power	Coil resistance (at 20 °C)	Tolerance of coil resistance
DC coils	12 V DC	-	8.4 V DC	30.6 V DC	≥ 0.1 U_s	0.4-0.48 W	360 Ω	± 10%
	24 V DC	-	16.8 V DC	61.2 V DC	≥ 0.1 U_s	0.4-0.48 W	1440 Ω	± 10%
	48 V DC	-	33.6 V DC	122.4 V DC	≥ 0.1 U_s	0.4-0.48 W	5700 Ω	± 10%
	110 V DC	-	77 V DC	280 V DC	≥ 0.1 U_s	0.4-0.48 W	25200 Ω	± 10%
AC coils	24 V AC	50 / 60 Hz	19.2 V AC	28.8 V AC	≥ 0.15 U_s	0.75 VA	400 Ω	± 10%
	48 V AC	50 / 60 Hz	38.4 V AC	57.6 V AC	≥ 0.15 U_s	0.75 VA	1550 Ω	± 10%
	110 V AC	50 / 60 Hz	88 V AC	132 V AC	≥ 0.15 U_s	0.75 VA	8900 Ω	± 10%
	120 V AC	50 / 60 Hz	96 V AC	144 V AC	≥ 0.15 U_s	0.75 VA	10200 Ω	± 10%
	230 V AC	50 / 60 Hz	184 V AC	276 V AC	≥ 0.15 U_s	0.75 VA	38500 Ω	± 10%

CR-P optocouplers range

Input circuit	CR-P024MOS1	CR-P024TRI1
Input resistance	2200 Ω	1950 Ω
Rated control voltage	24 V DC	24 V DC
Pull-in voltage	10 V DC	10 V DC
Maximum input voltage	32 V DC	32 V DC
Nominal input current	10 mA	12 mA
Input power	260 mW	295 mW
Typical switching-on time	50 ms	< 1/2 cycle
Typical switch-off time	250 ms	< 1/2 cycle

CR-M range

	Rated control supply voltage U_s	Rated frequency	Make voltage (at 20 °C)	Maximum voltage (at 55 °C)	Break voltage	Rated power	Coil resistance (at 20 °C)	Tolerance of coil resistance
DC coils	12 V DC	-	9.6 V DC	13.2 V DC	≥ 0.1 U_s	0.9 W	160 Ω	± 10%
	24 V DC	-	19.2 DC	26.4 V DC	≥ 0.1 U_s	0.9 W	640 Ω	± 10%
	48 V DC	-	38.4 V DC	52.8 V DC	≥ 0.1 U_s	0.9 W	2600 Ω	± 10%
	60 V DC	-	48 V DC	66 V DC	≥ 0.1 U_s	0.9 W	4000 Ω	± 10%
	110 V DC	-	88 V DC	121 V DC	≥ 0.1 U_s	0.9 W	13600 Ω	± 10%
	125 V DC	-	100 V DC	137.5 V DC	≥ 0.1 U_s	0.9 W	16000 Ω	± 10%
	220 V DC	-	176 V DC	242 V DC	≥ 0.1 U_s	0.9 W	54000 Ω	± 10%
AC coils	24 V AC	50 / 60 Hz	19.2 V AC	26.4 V AC	≥ 0.2 U_s	1.6 VA	158 Ω	± 10%
	48 V AC	50 / 60 Hz	38.4 V AC	52.8 V AC	≥ 0.2 U_s	1.6 VA	640 Ω	± 10%
	60 V AC	50 / 60 Hz	48 V AC	66 V AC	≥ 0.2 U_s	1.6 VA	930 Ω	± 10%
	110 V AC	50 / 60 Hz	88 V AC	121 V AC	≥ 0.2 U_s	1.6 VA	3450 Ω	± 10%
	120 V AC	50 / 60 Hz	96 V AC	132 V AC	≥ 0.2 U_s	1.6 VA	3770 Ω	± 10%
	230 V AC	50 / 60 Hz	184 V AC	253 V AC	≥ 0.2 U_s	1.6 VA	16100 Ω	± 10%

Pluggable interface relays and optocouplers

Technical data – CR-P, CR-M, CR-U

CR-U range

	**Rated control supply voltage U_s**	**Rated frequency**	**Make voltage (at 20 °C)**	**Maximum voltage (at 55 °C)**	**Break voltage**	**Rated power**	**Coil resistance (at 20 °C)**	**Tolerance of coil resistance**
DC coils	12 V DC	-	9.6 V DC	13.2 V DC	≥ 0.1 U_s	1.5 W	110 Ω	± 10 %
	24 V DC	-	19.2 V DC	26.4 V DC	≥ 0.1 U_s	1.5 W	430 Ω	± 10 %
	48 V DC	-	38.4 V DC	52.8 V DC	≥ 0.1 U_s	1.5 W	1750 Ω	± 10 %
	110 V DC	-	88.0 V DC	121.0 V DC	≥ 0.1 U_s	1.5 W	9200 Ω	±10 %
	125 V DC	-	100 V DC	137.5 V DC	≥ 0.1 U_s	1.5 W	11000 Ω	± 10 %
	220 V DC	-	176.0 V DC	242.0 V DC	≥ 0.1 U_s	1.5 W	37000 Ω	± 10 %
AC coils	24 V AC	50 / 60 Hz	19.2 V AC	26.4 V AC	≥ 0.15 U_s	2.8 VA (50 Hz) 2.5 VA (60 Hz)	75 Ω	± 10 %
	48 V AC	50 / 60 Hz	38.4 V AC	52.8 V AC	≥ 0.15 U_s	2.8 VA (50 Hz) 2.5 VA (60 Hz)	305 Ω	± 10 %
	60 V AC	50 / 60 Hz	48.0 V AC	66.0 V AC	≥ 0.15 U_s	2.8 VA (50 Hz) 2.5 VA (60 Hz)	475 Ω	± 10 %
	110 V AC	50 / 60 Hz	88.0 V AC	121.0 V AC	≥ 0.15 U_s	2.8 VA (50 Hz) 2.5 VA (60 Hz)	1700 Ω	± 10 %
	120 V AC	50 / 60 Hz	96.0 V AC	132.0 V AC	≥ 0.15 U_s	2.8 VA (50 Hz) 2.5 VA (60 Hz)	1910 Ω	± 10 %
	230 V AC	50 / 60 Hz	184.0 V AC	253.0 V AC	≥ 0.15 U_s	2.8 VA (50 Hz) 2.5 VA (60 Hz)	7080 Ω	± 10 %

Pluggable interface relays and optocouplers

Technical data – CR-P, CR-M, CR-U

Type		CR-P...1	CR-P...2	CR-M...2	CR-M...3	CR-M...4	CR-U...2	CR-U...3
Output circuit(s)		11-12/14	11-12/14 21-22/24	11-12/14 21-22/24	11-12/14 21-22/24 31-32/34	11-12/14 21-22/24 31-32/34 41-42/44	11-12/14 31-32/34	11-12/14 21-22/24 31-32/34
Kind of output		Relay, 1 c/o	Relay, 2 c/o	Relay, 2 c/o	Relay, 3 c/o	Relay, 4 c/o	Relay, 2 c/o	Relay, 3 c/o
Contact material		AgNi	AgNi AgNi/Au 5 µm	AgNi	AgNi	AgNi AgNi/Au 5 µm	AgNi	
Rated operational voltage U_e (VDE 0110, IEC 60947-1)		250 V						
Minimum switching voltage		5 V		10 V (AgNi); 5 V (AgNi/Au)			10 V	
Maximum switching voltage	DC	300 V DC		250 V DC				
	AC	440 V AC		250 V AC			440 V AC	
Minimum switching current		5 mA (AgNi), 2 mA (AgNi/Au)		5 mA (AgNi)	5 mA (AgNi)	2 mA (AgNi/Au)	5 mA	
Rated free air thermal current I_{th}		16 A	8 A	12 A	10 A	6 A	10 A	
Rated operational current (IEC 60947-5-1)	AC-12 (resistive) 230 V	16 A	8 A	12 A	10 A	6 A	10 A	
	AC-15 (inductive) 230 V	1.5 A	1.5 A	1.5 A	1.5 A	1 A	1.5 A	
	AC-15 (inductive) 120 V	3 A				1.5 A	3 A	
	DC-12 (resistive) 24 V	16 A	8 A	12 A	10 A	6 A	10 A	
	DC-13 (inductive) 24 V	2.5 A	2 A	2.5 A	2.5 A	2 A	2 A	
	DC-13 (inductive) 120 V	0.22 A						
	DC-13 (inductive) 250 V	0.1 A						
AC rating (UL 508)	utilization category (pilot duty) (contact rating code designation)	B300		B300			B300	
	max. rated operational voltage	300 V AC		300 V AC			300 V AC	
	max. continuous thermal current at utilization category	5 A		5 A	5 A	2.5 A	5 A	
	max. making / breaking apparent power at utilization category	3600 / 360 VA		3600 / 360 VA		1800 / 180 VA	3600/360 VA	
	utilization category (resistive) (CSA22.2 No.14....)	16 A, 250 V AC	8 A, 250 V AC	10 A, 250 V AC 12 A,150 V AC	6 A, 250 V AC 10 A, 150 V AC	5 A, 250 V AC 10 A, 150 V AC	10 A, 250 V AC (resistive + single-phase)	
DC rating * (UL 508; NEMA ICS-5)	utilization category (pilot duty) (contact rating code designation)	R300						
	max. rated operational voltage	300 V DC						
	max. continuous thermal current at utilization category	1 A						
	max. making / breaking apparent power at utilization category	28 VA						
	utilization category (resistive) (CSA22.2 No.14....)	-	10 A, 24 V DC	-			10 A, 28 V DC	
Maximum making (inrush) current		30 A	15 A	24 A	20 A	12 A	20 A	
Minimum switching power		0.3 W (AgNi), 0.05 W (AgNi/Au)		0.3 W (AgNi), 0.1 W (AgNi/Au)			0.3 W	
Maximum switching (breaking) power	AC1 (resistive)	4000 VA	2000 VA	3000 VA	2500 VA	1500 VA	2500 VA	
Contact resistance		≤ 100 mΩ						
Maximum operating frequency	rated load AC-1	600 switching cycles/h		1200 switching cycles/h				
	without load	72000 switching cycles/h		18000 switching cycles/h			12000 switching cycles/h	

Pluggable interface relays and optocouplers

Technical data – CR-P, CR-M, CR-U

Type		CR-P...1	CR-P...2	CR-M...2	CR-M...3	CR-M...4	CR-U...2	CR-U...3
Mechanical lifetime		> 3 x 10^7 switching cycles		> 2 x 10^7 switching cycles				
Electrical lifetime	electrical AC1 (resistive)	> 0.7 x 10^5 switching cycles (16 A, 250 V)	> 10^5 switching cycles (8 A, 250 V)	> 10^5 switching cycles			> 10^5 switching cycles (12 A, 250 V)	
				(12 A, 250 V)	(10 A, 250 V)	(6 A, 250 V)		
	cos ϕ	see reduction factor F						
Response time		typ. 7 ms		typ. 13 ms (DC), 10 ms (AC)			typ. 18 ms (DC), 12 ms (AC)	
Release time		typ. 3 ms		typ. 3 ms (DC), 8 ms (AC)			typ. 7 ms (DC), 10 ms (AC)	
Isolation data								
Rated insulation voltage		400 V AC		250 V AC				
Insulation class (In accordance to VDE 0110b)		C250 / B400		C250 / B250			C250	
Rated impulse withstand voltage U_{imp}	between coil and contacts	5 kV		2.5 kV				
	between open contacts	1 kV		1.5 kV				
	between c/o (SPDT) contacts	-	2.5 kV	2.5 kV		≥ 2 kV	2 kV	
Clearance between coil and contacts		≥ 10 mm		≥ 2.5 mm		≥ 1.6 mm	≥ 3 mm	
Creepage distance between coil and contacts		≥ 10 mm		≥ 4 mm		≥ 3.2 mm	≥ 4.2 mm	
Overvoltage category		III		III		II	III	
Pollution degree		3		3		2	3	
General data								
Dimensions		see 'Dimensional drawings'						
Mounting		on socket (see accessories)						
Mounting position		any						
Degree of protection		IP 67		IP 40				
Electrical connection								
Connection		by socket						
Environmental data								
Ambient temperature range	operation	DC: -40...+85 °; AC: -40...+70 °C		DC: -40...+70 °; AC: -40...+55 °C				
	storage	-40 ... +85 °C						
Vibration resistance 10-150 Hz	n/o contact	10 g		5 g			5 g	
	n/c contact	10 g	5 g	5 g			5 g	
Shock resistance	n/o contact	30 g	20 g	10 g			10 g	
	n/c contact	30 g	20 g	5 g			10 g	
Standards / Directives								
Standards		IEC/EN 61810-1						
Low Voltage Directive		-		2014/35/EU				
RoHS Directive		2011/65/EU						

* These ratings are based on different type tests which are not covered by the cULus or CSA approvals.

Pluggable interface relays and optocouplers

Technical data – CR-P optocouplers

Output circuits		**CR-P024MOS1**	**CR-P024TRI1**
Output circuit(s)		11 (13+) - 14	11 (13+) - 14
Kind of output		MOS-FET	Triac
Rated operational voltage		24 V DC	240 V AC
Maximum switching voltage		35 V DC	275 V AC
Minimum switching current		1 mA	50 mA
Maximum switching current continuously		5 A	3,5 A
Leakage current at maximum switching voltage		10 uA	1 mA
Voltage drop at rated current		300 mV	1.1 V
Isolation data			
Rated insulation voltage	input/output	2.5 kV	2.5 kV
Insulation class		2	2
Clearance	input/output	19 mm	19 mm
Creepage distance	input/output	19 mm	19 mm
Overvoltage category		III	III
Pollution degree		2	2
General data			
Dimensions		see 'Dimensional drawings'	
Weight		11 g (0.618 lbs)	11 g (0.618 lbs)
Mounting		on socket	on socket
Environmental data			
Ambient temperature	operational	-20...+80 °C	-20...+80 °C
	storage	-40...+100 °C	-40...+100 °C
Standards / Directives			
Standards		IEC/EN 62314	IEC/EN 62314
EMC Directive		2014/30/EU	2014/30/EU
RoHS Directive		2011/65/EU	2011/65/EU

Pluggable interface relays and optocouplers

Technical data - CR-P and CR-M sockets

Output circuits		**CR-PLS**	**CR-PLSx**	**CR-PSS**	**CR-PLC**	**CR-MxLS**	**CR-MxSS**	**CR-MxSF**	**CR-MxLC**
Output circuit(s)		11-12/14, 21-22/24				11-12/14, 21-22/24, ...			
Number of poles		2				2, 3 or 4		2 or 4	
Rated voltage		250 V AC/DC	300 V AC/DC	250 V AC/DC		250 V AC/DC			300 V AC/DC
Rated current		2 x 10 A[1)]	2 x 12 A[1)]	2 x 10 A[1)]		7 A			10 A
General data									
Dimensions without holder and module (L x W x H)		76 x 15.8 x 62 mm (2.992 x 0.622 x 2.441 in)	78.5 x 15.5 x 61 mm (3.011 x 0.610 x 2.402 in)	76 x 15.8 x 42.8 mm (2.992 x 0.622 x 1.685 in)	97.5 x 16.3 x 45.2 mm (3.839 x 0.642 x 1.780 in)	75 x 27.2 x 60.8 mm (2.952 x 1.071 x 2.394 in)	75.2 x 27.2 x 42.6 mm (2.961 x 1.071 x 1.677 in)	66.7 x 30.3 x 29 mm (2.626 x 1.193 x 1.142 in)	95 x 31 x 42.5 mm (3.74 x 1.22 x 1.67 in)
Degree of protection	terminals	IP 20 B (EN 60529)							
Temperature range	operation	-40...+70 °C	-40...+85 °C	-40...+70 °C		-40...+70 °C			-25...+85 °C
	storage	-40...+70 °C	-40...+85 °C	-40...+70 °C		-40...+70 °C			
Connection type		screw connection			spring connection	screw connection		fork type screw	spring connection
Maximum number of wires per connecting terminal		2			2 (one per connection point)	2		-	2 (one per connection point)
Connecting capacity	rigid	2 x 0.5 - 2.5 mm² (2 x 20 - 14 AWG)			2 x 0.2 - 1.5 mm² (2 x 24 - 16 AWG)	2 x 0.5 - 2.5 mm² (2 x 20 - 14 AWG)			2 x 0.5 - 1.5 mm² (2 x 20 - 16 AWG)
	fine-strand								
	with wire end ferrule	2 x 0.5 - 1.5 mm² (2 x 20 - 16 AWG)	2 x 1.5 mm² (2 x 16 AWG)	2 x 0.5 - 1.5 mm² (2 x 20 - 16 AWG)	2 x 1.5 mm² (2 x 16 AWG)	2 x 0.5 - 1.5 mm² (2 x 20 - 16 AWG)			2 x 1.5 mm² (2 x 16 AWG)
Stripping length		7 mm (0.28 in)			11 mm (0.43 in)	7 mm (0.28 in)			10 mm (0.39 in)
Tightening torque		0.6 Nm	0.8 Nm	0.6 Nm		0.6 Nm (5.31 lb.in)			
Maximum clamping force	with 0,2 mm²	-	-	-	10 N	-	-	-	10 N
	with 1,5 mm²	-	-	-	40 N	-	-	-	40 N
	with wire end ferrule	-				-	-	-	> 40 N
Mounting		DIN rail (IEC/EN 60715)							
Material	socket	PA 6+GF - V2				PA 6+GF - V2			
	contacts	CuZn33				CuZn33			
	contact surface	5 µ Ni	5 µ tinned	5 µ Ni		5 µ Ni		6 µ Ni	5 µ tinned
	terminals	8 µ Ni	8 µ galvanized	8 µ Ni	XCrNi Steel	8 µ Ni			CCSC
	combi screw M3	8.8 Steel, 5µ Ni			-	8.8 Steel, 5µ Ni			-
Isolation data									
Insulation voltage		> 5 kV	> 3 kV	> 5 kV		> 3 kV		> 4 kV	
Isolation between coil and contacts		IEC/EN 61984							
Clearance and creepage distance		IEC/EN 61984							
Standards / Directives									
Standards		IEC/EN 61984							
Low Voltage Directive		2014/35/EU							
RoHS Directive		2011/65/EU							

[1)] Loads >10 A (>12 A for CR-PLSx) require jumpering of terminal 11 with 21, 12 with 22, and 14 with 24

Pluggable interface relays and optocouplers

Technical data - CR-P and CR-M jumper bars

Rated operational voltage / Rated current		**CR-PJ**	**CR-MJ**
Rated operational voltage (VDE 0660 / part 500)		400 V	
Rated current (VDE 0660 / part 500)		25 A	
Electrical connection			
Bus bar diameter		6 mm² (0.0093 in²)	
Step distance		15.5 mm (0.610 in)	27.2 mm (1.071 in)
Rail length	with isolation	150 mm (5.906 in)	255 mm (10.039 in)
	without isolation	141.5 mm (5.571 in)	245 mm (9.646 in)
Stripping length of a connection wire that is used in combination with a jumper bar		6 mm (0.236 in)	
Environmental data			
Ambient temperature range	operation	-40... +55 °C	
Isolation data			
Rated impulse withstand voltage U_{imp} (VDE 0660 / part 500)		4 kV	
Overvoltage category (IEC/EN 60664)		III	
Polution degree (IEC/EN 60664)		2	
General data			
Material of rail		E-Cu-F25	
Type of rail		pin type	
Number of pins		10	
Number of phases		1	
Color of insulating material		RAL 7035	
Flammability (UL 94)		V0	

Pluggable interface relays and optocouplers

Technical data - CR-P and CR-M function modules

CR-P/M 22													
Type		CR-P/M 22											
Version		Diode											
Function		Reverse polarity protection											
Control supply voltage		6-220 V DC											
Component data	diode	1 A, 1000 V											
Polarized		yes (A1+, A2-)											
Material	enclosure / base	PA6 + GF V2											
CR-P/M 42													
Type		CR-P/M 42		CR-P/M 42V		CR-P/M 42B		CR-P/M 42BV		CR-P/M 42C		CR-P/M 42CV	
Version		Diode and LED											
Function		Reverse polarity protection, applied supply voltage indicated via LED											
Control supply voltage		6-24 V DC				24-60 V DC				110 V DC			
Component data	diode	1 A, 1000 V											
	LED	red		green		red		green		red		green	
	resistance	3 kΩ, 0.25 W				15 kΩ, 0.25 W				200 kΩ, 0.25 W			
Polarized		yes (A1+, A2-)											
Material	enclosure / base	PA6 + GF V2											
CR-P/M 52													
Type		CR-P/M 52B				CR-P/M 52D				CR-P/M 52C			
Version		RC element											
Function		Arc elimination											
Control supply voltage		6-24 V AC/DC				24-60 V AC/DC				110-230 V AC/DC			
Component data	capacitor	0.1 µF, 63 V DC				0.1 µF, 100 V DC				0.082 µF, 400 V DC			
	resistance	10 Ω, 0.25 W				47 Ω, 0.25 W				100 Ω, 0.25 W			
Polarized		no											
Material	enclosure / base	PA6 + GF V2											
CR-P/M 62													
Type		CR-P/M 62	CR-P/M 62V		CR-P/M 62E		CR-P/M 62EV		CR-P/M 62C		CR-P/M 62CV		CR-P/M 62D	CR-P/M 62DV
Version		Diode and LED							Varistor and LED					
Control supply voltage		6-24 V AC/DC			24-60 V AC/DC				6-24 V AC/DC				24-60 V AC/DC	
Component data	diode	1 A, 1000 V												
	LED	red	green		red		green		red		green		red	green
	varistor	25 V AC			75 V AC				25 V AC				75 V AC	
	resistance	3 kΩ, 0.25 W			15 kΩ, 0.25 W				3 kΩ, 0.25 W				15 kΩ, 0.25 W	
Polarized		AC: no, DC: yes (A1+, A2-)												
Material	enclosure / base	PA6 + GF V2												
CR-P/M 72, 82													
Type		CR-P/M 72				CR-P/M 72A			CR-P/M 82					
Version		Varistor												
Function		Overvoltage protection												
Control supply voltage		24 V AC				115 V AC			230 V AC					
Component data	varistor	25 V AC				115 V AC			275 V AC					
Polarized		no												
Material	enclosure / base	PA6 + GF V2												
CR-P/M 92													
Type		CR-P/M 92			CR-P/M 92V			CR-P/M 92C			CR-P/M 92CV		
Version		Diode and LED						Varistor and LED					
Control supply voltage		110-230 V AC / 110 V DC											
Component data	diode	1 A, 1000 V											
	LED	red			green			red			green		
	varistor	275 V AC											
	resistance	120 kΩ, 0.25 W											
Polarized		AC: no, DC: yes (A1+, A2-)											
Material	enclosure / base	PA6 + GF V2											
Standards / Directives													
Standards		IEC/EN 61984											
Low Voltage Directive		2014/35/EU											
RoHS Directive		2011/65/EU											

Pluggable interface relays and optocouplers

Technical data - CR-U sockets and function modules

Output circuits		**CR-U2S**	**CR-U3S**	**CR-U3E**	**CR-UxSM**
Output circuit(s)		11-12/14, 21-22/24,...			
Number of poles		2	3		2 or 3
Rated voltage		250 V AC		300 V AC	250 V
Rated current		10 A			
General data					
Dimensions		see 'Dimensional drawings'			
Degree of protection	terminals	IP 20 B (EN 60529)			
Temperature range	operation	-40...+70 °C		-40...+85 °C	-40...+70 °C
	storage	-40...+70 °C		-40...+85 °C	-40...+70 °C
Connecting capacity	rigid	2 x 2 x 0,5 - 2,5 mm² (2 x 20 - 14 AWG)			
	fine-strand				
	with wire end ferrule	2 x 0.5 - 1.5 mm² (2 x 20 - 16 AWG)		2 x 0.5 - 1.5 mm² (2 x 20 - 16 AWG)	2 x 0.5 - 1.5 mm² (2 x 20 - 16 AWG)
Stripping length		7 mm (0.28 in)			
Tightening torque		0.6 Nm		0.8 Nm	0.6 Nm
Mounting		DIN rail (IEC/EN 60715)			
Material	socket	PA 6+GF - V2			
	contacts	CuZn33			
	contact surface	6 µ Ni			3 µ Ni
	terminals	8 µ Ni		8 µ galvanized	10 µ Ni
	combi screw M3	8.8 steel, 5µ Ni			Steel, 8 µ Ni
Isolation data					
Insulation voltage		> 2 kV			
Isolation between coil and contacts		IEC/EN 61984			
Clearance and creepage distance		IEC/EN 61984			
Standards/Directives					
Standards		IEC/EN 61984			
Low Voltage Directive		2014/35/EU			
RoHS Directive		2011/65/EU			

Technical data - CR-U function modules

CR-U 21							
Type		CR-U 21					
Version		Diode					
Function		Reverse polarity protection and elimination of the converse current					
Control supply voltage		6-220 V DC					
Component data	Diode	1 A, 1000 V					
Polarized		yes (A1+, A2-)					
Material	Enclosure / Base	PA6 + GF V2					
CR-U 41							
Type		CR-U 41	CR-U 41V	CR-U 41B	CR-U 41BV	CR-U 41C	CR-U 41CV
Version		Diode and LED					
Function		Reverse polarity protection and elimination of the converse current. LED to indicate the energization of coil					
Control supply voltage		6-24 V DC		24-60 VDC		110 V DC	
Component data	Diode	1 A, 1000 V					
	LED	red	green	red	green	red	green
	Resistance	3 kΩ, 0.25 W		15 kΩ, 0.25 W		200 kΩ, 0.25 W	
Polarized		yes (A1+, A2-)					
Material	Enclosure / Base	PA6 + GF V2					


Pluggable interface relays and optocouplers

Technical data - CR-U function modules


CR-U 51									
Type		CR-U 51B		CR-U 51D		CR-U 51C			
Version		RC element							
Function		Arc elimination							
Control supply voltage		6-24 V AC/DC		24-60 V AC/DC		110-230 V AC/DC			
Component data	Capacitor	0.1 µF, 63 V DC		0.1 µF, 100 V DC		0.082 µF, 400 V DC			
	Resistance	10 Ω, 0.25 W		47 Ω, 0.25 W		100 Ω, 0.25 W			
Polarized		no							
Material	Enclosure / Base	PA6 + GF V2							
CR-U 61									
Type		CR-U 61	CR-U 61V	CR-U 61E	CR-U 61EV	CR-U 61C	CR-U 61CV	CR-U 61D	CR-U61DV
Version		Diode and LED				Varistor and LED			
Function		Reverse polarity protection and elimination of the converse current. LED to indicate the energization of coil.				Overvoltage protection, LED to indicate the energized of coil			
Control supply voltage		6-24 V AC/DC		24-60 V AC/DC		6-24 V AC/DC		24-60 V AC/DC	
Component data	Diode	1 A, 1000 V							
	LED	red	green	red	green	red	green	red	green
	Resistance	3 kΩ, 0.25 W		15 kΩ, 0.25 W		3 kΩ, 0.25 W		15 kΩ, 0.25 W	
Polarized		AC: no, DC: yes (A1+, A2-)							
Material	Enclosure / Base	PA6 + GF V2							
CR-U 71, 81									
Type		CR-U 71		CR-U 71A		CR-U 81			
Version		Varistor							
Function		Overvoltage protection							
Control supply voltage		24 V AC		115 V AC		230 V AC			
Component data	Varistor	25 V AC		115 V AC		275 V AC			
Polarized		no							
Material	Enclosure / Base	PA6 + GF V2							
CR-U 91									
Type		CR-U 91		CR-U 91V		CR-U 91C		CR-U 91CV	
Version		Diode and LED				Varistor and LED			
Function		Reverse polarity protection and elimination of the converse current. LED to indicate the energization of coil.				Overvoltage protection, LED to indicate the energized of coil			
Control supply voltage		110-230 V AC / 110 V DC							
Component data	Diode	1 A, 1000 V							
	LED	red		green		red		green	
	Resistance	120 kΩ, 0.25 W							
Polarized		AC: no, DC: yes (A1+, A2-)							
Material	Enclosure / Base	PA6 + GF V2							
Standards / Directives									
Standards		IEC/EN 61984							
Low Voltage Directive		2014/35/EU							
RoHS Directive		2011/65/EU							

Pluggable interface relays and optocouplers
Technical diagrams


Connection diagrams




CR-P/M 22




CR-P/M 42, CR-P/M 42B,
CR-P/M 42C, CR-P/M 42V,
CR-P/M 42BV, CR-P/M 42CV




CR-P/M 52B, CR-P/M 52C
CR-P/M 52D,




CR-P/M 62, CR-P/M 62E,
CR-P/M 92, CR-P/M 62V,
CR-P/M 62EV, CR-P/M 92V




CR-P/M 62C, CR-P/M 62D,
CR-P/M 92C, CR-P/M 62CV,
CR-P/M 62DV, CR-P/M 92CV




CR-P/M 72, CR-P/M 82
CR-P/M 72A,




CR-U 21




CR-U 41, CR-U 41B, CR-U 41C,
CR-U 41V, CR-U 41BV, CR-U 41CV




CR-U 51B, CR-U 51C CR-U 51D



CR-U 61, CR-U 61E, CR-U 91,
CR-U 61V, CR-U 61EV, CR-U 91V



CR-U 61C, CR-U 61CV, CR-U 61D,
CR-U 61DV, CR-U 91C, CR-U 91CV




CR-U 71, CR-U 71A , CR-U 81


Pluggable interface relays and optocouplers

Technical diagrams


Connection diagrams




CR-P with 1 c/o contact




CR-M with 2 c/o contacts




CR-M with 3 c/o contacts




CR-U with 2 c/o contacts




CR-P with 2 c/o contacts




CR-M with 4 c/o contacts




CR-S




CR-U with 3 c/o contacts



CR-S optocoupler with Transistor



CR-S optocoupler with MOSFET




CR-S optocoupler with Triac


Pluggable interface relays and optocouplers

Technical diagrams

CR-P: Operating range of coils




Operating range of DC coil




Operating range of AC coil

A	unloaded contacts, coil temperature = ambient temperature
B	continued with I_{th} (16 A at CR-P ... 1 and 8 A at CR-P ... 2) loaded contacts coil heated with 1,1 x U_s
1	at unloaded contacts
2	at 50 % rated load
3	at rated load


Electrical connection



CR-PLS



CR-PLSx, CR-PLC




CR-PSS

A1-A2	Supply voltage
11-12/14,	Relay outputs
21-22/24	Relay outputs


Pluggable interface relays and optocouplers

Technical diagrams

Mounting and removal of sockets




Mounting




Removal


Electrical connection




CR-M2LS




CR-M3LS



CR-M4LS



CR-M2LC




CR-M4LC

Pluggable interface relays and optocouplers


Technical diagrams

Electrical connection




CR-M2SS,
CR-M2SF

A1-A2	Supply voltage
11-12/14,	Relay outputs
41-42/44	Relay outputs



CR-M3SS

A1-A2	Supply voltage
11-12/14,	Relay outputs
21-22/24,	Relay outputs
31-32/34	Relay outputs




CR-M4SS,
CR-M4SF


A1-A2	Supply voltage
11-12/14,	Relay outputs
21-22/24	Relay outputs
31-32/34	Relay outputs
41-42/44	Relay outputs

Pluggable interface relays and optocouplers
Technical diagrams

Technical diagrams CR-S interface relays




Max. DC load breaking capacity




Endurance curve


Load limit curves CR-P, CR-M and CR-U - Electrical lifetime at resistive AC load




CR-P with 1 c/o contact




CR-P with 2 c/o contacts




CR-U with 2 and 3 c/o contacts



CR-M with 2 c/o contacts



CR-M with 3 c/o contacts




CR-M with 4 c/o contacts


Pluggable interface relays and optocouplers

Technical diagrams


Load limit curves CR-P, CR-M and CR-U - Maximum switching power at resistive DC load




CR-P with 1 c/o contact




CR-P with 2 c/o contacts




CR-U with 2 and 3 c/o contacts



CR-M with 2 c/o contacts




CR-M with 3 c/o contacts




CR-M with 4 c/o contacts


Reduction factor CR-P, CR-M and CR-U – F at inductive AC load



CR-P




CR-M




CR-U

Pluggable interface relays and optocouplers
Technical diagrams


Derating curves




Derating curve Transistor output CR-S




Derating curve MOS-FET output CR-S



Derating curve Triac output CR-S



MOS-FET output CR-P




Triac output CR-P

Pluggable interface relays and optocouplers


Technical diagrams

Dimensional drawings


in **mm** and inches




CR-S relay




CR-S optocoupler




CR-S socket - spring connection



CR-S socket - screw connection



CR-S separator




CR-SJB20 - blue, CR-SJB20 - red, CR-SJB20 - black jumper bar

Pluggable interface relays and optocouplers


Technical diagrams

Dimensional drawings


in **mm** and inches




CR-P relay




CR-P optocoupler




CR-PLS - screw connection




CR-PLSx - screw connection




CR-PSS - screw connection



CR-PLC - spring connection



CR- P/Mxx function module




CR-PJ jumper bar

Pluggable interface relays and optocouplers


Technical diagrams

Dimensional drawings


in **mm** and inches




CR-M relay with 2 c/o contacts




CR-M relay with 3 c/o contacts




CR-M relay with 4 c/o contacts




CR-M2LS - CR-M3LS - CR-M4LS - screw connection




CR-MxSF - screw connection



CR-M2LC , CR-M4LC - spring connection



CR-MJ jumper bar




CR-M2SS - CR-M3SS - CR-M4SS - screw connection

Pluggable interface relays and optocouplers


Technical diagrams

Dimensional drawings


in **mm** and inches




CR-U relay with 2 c/o contacts




CR-U relay with 3 c/o contacts




CR-U2S - CR-U3S - screw connection



CR-U3E - screw connection



CR-U2SM - CR-U3SM - screw connection



CR-Uxx function module


A2
ABB
A1
S1
24V
A1
24V
AC/DC
13
0925
A2
A1
A2
S1
250 VAC
6A
14
S2
13
14
S2
14
13

Boxed interface relays and optocouplers R600 range
Table of contents

438	**Overview**
440	**Boxed interface relays R600 range**
440	Selection table
442	Ordering details
444	Technical data
448	Technical diagrams
450	**Boxed optocouplers R600 range**
450	Selection table
451	Ordering details
453	Technical data
456	Technical diagrams

Boxed interface relays and optocouplers R600 range
Overview



ABB's R600 range may be used in applications where electrical isolation, amplification and signal matching are required. The slim, compact design, incorporated with the variety of terminal connections available allow for the optimization of space within a control panel. This broad portfolio allows for the flexibility of choice and includes both electromagnetic relays and optocouplers.

Continuous operation

The ABB boxed interface relays portfolio incorporates a large assortment of non-pluggable relays. It includes both electro-mechanical relays and optocouplers. The R600 Optocouplers allow for continuous operation without any mechanical wear-and -tear.


Space saving

The 6 mm slim housing of the R600 boxed interface relays provides the possibility of space saving within control cabinets . The 75 mm depth of these relays allows for the use in compact cabinets.

Global availability

The ABB boxed interface relays are approved for a large variety of applications and adhere to highest levels of global approvals (UL, CSA, VDE, CCC).


Boxed interface relays and optocouplers R600 range
Overview




Complete product line
1 n/o, 1 n/c, 1 c/o, 2 c/o output configuration. Standard contact material for switching high current signals as well as gold-plated contacts for reliable switching of low current signals.




Marine certification
The R600 range offers the LR approval, which allows usage of the boxed interface relays and optocouplers in many applications around the marine segment. The performance of the R600 range has been proven by successfully passing tests required for operating under harsh conditions.



Safe operation
High resistance to vibration and shock thanks to the relay soldered inside of the housing. Wrong relay replacement or relay lose not possible . Devices with immunity to leakage currents.



Longevity
Optocoupler with transistor, MOS-FET and Triac output ensure a longer lifetime, higher reliability and quiet operation.



Easy to mount
The R600 interface relays and optocouplers are easy to mount by snapping onto a DIN-rail according to IEC/EN 60715. Time saving wiring thanks to a jumper bar.

Boxed interface relays R600 range
Selection table

	Order number	1SNA645034R2300	1SNA645036R2500	1SNA645534R2500	1SNA645073R0000	1SNA645035R2400	1SNA645075R0000	1SNA645535R2600	1SNA645019R0400	1SNA645519R0600	1SNA645014R2700	1SNA645018R0300	1SNA645518R0500	1SNA645514R2100	1SNA645001R0300	1SNA645005R0700	1SNA645501R0500	1SNA645505R0100	1SNA645012R2500	1SNA645512R2700	1SNA645071R0000	1SNA645571R0000	1SNA645072R0000	1SNA645572R0000	1SNA645002R0400	1SNA645006R0000
	Type	RB121P-5VDC	RB121PG-5VDC	RBR121P-5VDC	RB121-12VDC	RB121P-12VDC	RB121G-12VDC	RBR121P-12VDC	RB101R-24VUC	RBR101R-24VUC	RB111-24VUC	RB111R-24VUC	RBR111R-24VUC	RBR111-24VUC	RB121-24VUC	RB121G-24VUC	RBR121-24VUC	RBR121G-24VUC	RB122G-24VUC	RBR122G-24VUC	RB121-24VDC	RBR121-24VDC	RB121G-24VDC	RBR121G-24VDC	RB121-48-60VUC	RB121G-48-60VUC
Input voltage																										
5 V DC		■	■	■																						
12 V DC					■	■	■	■																		
24 V DC									■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■		
48-60 V DC																									■	■
115 V DC																										
230 V DC																										
60-230 V DC																										
24 V AC									■	■	■	■	■	■	■	■	■	■	■	■						
48-60 V AC																									■	■
115 V AC																										
230 V AC																										
60-230 V AC																										
Output rating																										
10 mA - 6 A		■		■	■	■		■	■	■	■	■	■	■	■		■				■	■			■	
3 mA - 6 A			■				■									■		■					■	■		■
1 mA - 8 A																			■	■						
Output contacts																										
c/o		1	1	1	1	1	1	1							1	1	1	1	2	2	1	1	1	1	1	1
n/o											1	1	1	1												
n/c									1	1																
Gold plated contacts			■				■									■		■	■	■			■	■		■
Terminal type																										
Screw		■	■		■	■	■		■		■	■			■	■			■		■		■		■	■
Spring				■				■		■			■	■			■	■		■		■		■			

Boxed interface relays R600 range
Selection table

	Order number	1SNA645502R0600	1SNA645506R0200	1SNA645040R1500	1SNA645540R1700	1SNA645003R0500	1SNA645007R0100	1SNA645046R0700	1SNA645503R0700	1SNA645507R0300	1SNA645041R0200	1SNA645541R0400	1SNA645016R2100	1SNA645017R2200	1SNA645004R0400	1SNA645008R1200	1SNA645011R2400	1SNA645504R0000	1SNA645508R1400	1SNA645511R2600	1SNA645013R2600	1SNA645513R2000	1SNA645020R0100	1SNA645520R0300
	Type	RBR121-48-60VUC	RBR121G-48-60VUC	RB122G-48-60VUC	RBR122G-48-60VUC	RB121-115VUC	RB121G-115VUC	RB121R-115VUC	RBR121-115VUC	RBR121G-115VUC	RB122G-115VUC	RBR122G-115VUC	RB111-115VUC	RB111-230VUC	RB121-230VUC	RB121G-230VUC	RB121R-230VUC	RBR121-230VUC	RBR121G-230VUC	RBR121R-230VUC	RB122G-230VUC	RBR122G-230VUC	RB121-60-230VUC	RBR121-60-230VUC
Input voltage																								
5 V DC																								
12 V DC																								
24 V DC																								
48-60 V DC	■	■	■	■																				
115 V DC					■	■	■	■	■	■	■	■												
230 V DC													■	■	■	■	■	■	■	■	■			
60-230 V DC																						■	■	
24 V AC																								
48-60 V AC	■	■	■	■																				
115 V AC					■	■	■	■	■	■	■	■												
230 V AC													■	■	■	■	■	■	■	■	■			
60-230 V AC																						■	■	
Output rating																								
10 mA - 6 A	■				■		■	■				■	■	■		■	■		■			■	■	
3 mA - 6 A		■				■			■						■			■						
1 mA - 8 A			■	■						■	■									■	■			
Output contacts																								
c/o	1	1	2	2	1	1	1	1	1	2	2			1	1	1	1	1	1	2	2	1	1	
n/o												1	1											
n/c																								
Gold plated contacts		■	■	■		■			■	■	■				■			■		■	■			
Terminal type																								
Screw			■		■	■	■			■		■	■	■	■	■				■		■		
Spring	■	■		■				■	■		■						■	■	■		■		■	

Boxed interface relays R600 range
Ordering details



R600 - 6 mm

The R600 range comprises of boxed interface relays and optocouplers. In this range, the relay is soldered into device housing, fulfilling the highest vibration requirements. This compact range of relays are 6 mm wide and provide the possibility of switching AC and DC circuits with the same relay. All the sockets in this range are equipped with an indicator LED and available with screw or spring terminals.

Ordering details - 1 n/c contact: 250 V, 10 mA - 6 A, width 12 mm

Rated control supply voltage	Connection type	Particularities	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V AC/DC	screw	RC circuit parallel to output contact	RB101R-24VUC	1SNA645019R0400	5	0.04 (0.088)
	spring		RBR101R-24VUC	1SNA645519R0600		

Ordering details - 1 n/o contact: 250 V, 10 mA - 6 A, width 6 mm

Rated control supply voltage	Connection type	Particularities	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V AC/DC	screw		RB111-24VUC	1SNA645014R2700	10	0.02 (0.044)
115 V AC/DC	screw		RB111-115VUC	1SNA645016R2100		
230 V AC/DC	screw		RB111-230VUC	1SNA645017R2200		
24 V AC/DC	spring		RBR111-24VUC	1SNA645514R2100		

Ordering details - 1 n/o contact: 250 V, 10 mA - 6 A, width 12 mm

Rated control supply voltage	Connection type	Particularities	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V AC/DC	screw	RC circuit parallel to output contact	RB111R-24VUC	1SNA645018R0300	5	0.04 (0.088)
	spring		RBR111R-24VUC	1SNA645518R0500		

Ordering details - 1 c/o (SPDT) contact: 250 V, 10 mA - 6 A, width 6 mm

Rated control supply voltage	Connection type	Particularities	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
5 V DC	screw	A1-A2 polarized	RB121P-5VDC	1SNA645034R2300	10	0.02 (0.044)
12 V DC	screw	A1-A2 polarized	RB121P-12VDC	1SNA645035R2400		
12 V DC	screw		RB121-12VDC	1SNA645073R0000		
24 V DC	screw		RB121-24VDC	1SNA645071R0000		
24 V AC/DC	screw		RB121-24VUC	1SNA645001R0300		
48-60 V AC/DC	screw		RB121-48-60VUC	1SNA645002R0400		
115 V AC/DC	screw		RB121-115VUC	1SNA645003R0500		
230 V AC/DC	screw		RB121-230VUC	1SNA645004R0400		
5 V DC	spring	A1-A2 polarized	RBR121P-5VDC	1SNA645534R2500		
12 V DC	spring	A1-A2 polarized	RBR121P-12VDC	1SNA645535R2600		
24 V DC	spring		RBR121-24VDC	1SNA645571R0000		
24 V AC/DC	spring		RBR121-24VUC	1SNA645501R0500		
48-60 V AC/DC	spring		RBR121-48-60VUC	1SNA645502R0600		
115 V AC/DC	spring		RBR121-115VUC	1SNA645503R0700		
230 V AC/DC	spring		RBR121-230VUC	1SNA645504R0000		

Boxed interface relays R600 range

Ordering details

Ordering details - 1 c/o (SPDT) contact: 250 V, 3 mA - 6 A, gold-plated contacts, width 6 mm

Rated control supply voltage	Connection type	Particularities	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
5 V DC	screw	A1-A2 polarized	RB121PG-5VDC	1SNA645036R2500	10	0.02 (0.044)
12 V DC	screw		RB121G-12VDC	1SNA645075R0000		
24 V DC	screw		RB121G-24VDC	1SNA645072R0000		
24 V AC/DC	screw		RB121G-24VUC	1SNA645005R0700		
48-60 V AC/DC	screw		RB121G-48-60VUC	1SNA645006R0000		
115 V AC/DC	screw		RB121G-115VUC	1SNA645007R0100		
230 V AC/DC	screw		RB121G-230VUC	1SNA645008R1200		
24 V DC	spring		RBR121G-24VDC	1SNA645572R0000		
24 V AC/DC	spring		RBR121G-24VUC	1SNA645505R0100		
48-60 V AC/DC	spring		RBR121G-48-60VUC	1SNA645506R0200		
115 V AC/DC	spring		RBR121G-115VUC	1SNA645507R0300		
230 V AC/DC	spring		RBR121G-230VUC	1SNA645508R1400		



R600 - 12 mm

Ordering details - 1 c/o (SPDT) contact: 250 V, 10 mA - 6 A, width 12 mm

Rated control supply voltage	Connection type	Particularities	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
60-230 V AC/DC	screw		RB121-60-230VUC	1SNA645020R0100	5	0.04 (0.088)
115 V AC/DC	screw	Leakage current protection, RC circuit parallel to input	RB121R-115VUC	1SNA645046R0700		
230 V AC/DC	screw		RB121R-230VUC	1SNA645011R2400		
60-230 V AC/DC	spring		RBR121-60-230VUC	1SNA645520R0300		
230 V AC/DC	spring	Leakage current protection, RC circuit parallel to input	RBR121R-230VUC	1SNA645511R2600		

Ordering details - 2 c/o (SPDT) contacts: 250 V, 1 mA - 8 A, gold-plated contacts, width 12 mm

Rated control supply voltage	Connection type	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V AC/DC	screw	RB122G-24VUC	1SNA645012R2500	5	0.04 (0.088)
48-60 V AC/DC	screw	RB122G-48-60VUC	1SNA645040R1500		
115 V AC/DC	screw	RB122G-115VUC	1SNA645041R0200		
230 V AC/DC	screw	RB122G-230VUC	1SNA645013R2600		
24 V AC/DC	spring	RBR122G-24VUC	1SNA645512R2700		
48-60 V AC/DC	spring	RBR122G-48-60VUC	1SNA645540R1700		
115 V AC/DC	spring	RBR122G-115VUC	1SNA645541R0400		
230 V AC/DC	spring	RBR122G-230VUC	1SNA645513R2000		

Ordering details - Accessories

Description	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
Jumper bar, 10 poles * (replacement of BJ612-10 - 1SNA290488R0100)	RB-JB10	1SVR406570R0000	10	0.05 (0.11)
Jumper bar, 20 poles * (replacement of BJ612-20 - 1SNA206754R0000)	RB-JB20	1SVR406580R0000		0.10 (0.22)
Separator end section	SC612	1SNA290474R0200		0.05 (0.11)

* - Before the first and after the last jumpered R600 relay, a separator end section shall be used.
- The sum of the current for jumpered devices shall not exceed 6 A on 6 mm devices and 8 A on 12 mm devices.

Boxed interface relays R600 range

Technical data

			RB(R)101R-	RB(R)111R-
			24 V UC	**24 V UC**
Input circuit				
Rated control supply voltage U_s			24 V AC/DC	
Rated control supply voltage U_s tolerance		DC	-15 %, +20 %	
		AC	-/+ 10 %	
Rated frequency			50/60 Hz	
Typical power consumption			0.24 W	
Typical current			10 mA	
Drop-out voltage		at 20 °C	4.5 V	
Indication of operational states		green LED	⎍: control supply voltage applied	
Output circuit				
Kind of output		11-12	relay, 1 n/c contact	-
		13-14	-	relay, 1 n/o contact
Rated operational voltage U_e			250 V AC	
Minimum switching voltage			5 V	
Maximum switching voltage			250 V AC	
Minimum switching current			60 mA	
Rated free air thermal current I_{th}			6 A	
Rated operational current I_e		AC-12 (resistive) 230 V	6 A	
		AC-15 (inductive) 230 V	1.5 A	
		AC-15 (inductive) 120 V	3 A	
		DC-12 (resistive) 24 V	6 A	
		DC-13 (inductive) 24 V	1 A	
		DC-13 (inductive) 110 V	0.2 A	
		DC-13 (inductive) 220 V	0.1 A	
AC rating (UL 508; NEMA ICS-5)		utilization category (pilot duty)	B300	
DC rating (UL 508; NEMA ICS-5)		utilization category (pilot duty)	R300	
Minimum switching power			300 mW	
Mechanical lifetime			1 x 10^7 switching cycles	
Electrical lifetime		at AC-15	1 x 10^5 switching cycles	
Max. fuse rating to achieve short-circuit protection			6 A fast	
Response time			5 ms	
Release time			8 ms	

			RB(R)111-		
			24 V UC	**115 V UC**	**230 V UC**
Input circuit					
Rated control supply voltage U_s			24 V AC/DC	115 V AC/DC	230 V AC/DC
Rated control supply voltage U_s tolerance		DC	-15 %, +20 %		-15 %, +10 %
		AC	-/+ 10 %		
Rated frequency			50/60 Hz		
Typical power consumption			0.24 W	0.46 W	0.8 W
Typical current			10 mA	4 mA	3.5 mA
Drop-out voltage		at 20 °C	4.5 V	17 V	27 V
Indication of operational states		green LED	⎍: control supply voltage applied		
Output circuit					
Kind of output		13-14	relay, 1 n/o contact		
Rated operational voltage U_e			250 V AC		
Minimum switching voltage			12 V		
Maximum switching voltage			250 V AC		
Minimum switching current			10 mA		
Rated free air thermal current I_{th}			6 A		

Boxed interface relays R600 range

Technical data

		RB(R)111-		
		24 V UC	**115 V UC**	**230 V UC**
Rated operational current I_e	AC-12 (resistive) 230 V	6 A		
	AC-15 (inductive) 230 V	1.5 A		
	AC-15 (inductive) 120 V	3 A		
	DC-12 (resistive) 24 V	6 A		
	DC-13 (inductive) 24 V	1 A		
	DC-13 (inductive) 110 V	0.2 A		
	DC-13 (inductive) 220 V	0.1 A		
AC rating (UL 508; NEMA ICS-5)	utilization category (pilot duty)	B300		
DC rating (UL 508; NEMA ICS-5)	utilization category (pilot duty)	R300		
Minimum switching power		300 mW		
Mechanical lifetime		1 x 10^7 switching cycles		
Electrical lifetime	at AC-15	1 x 10^5 switching cycles		
Max. fuse rating to achieve short-circuit protection		6 A fast		
Response time		5 ms	6 ms	7 ms
Release time		8 ms	15 ms	15 ms

		RB(R)121(P)(G)-						
		5 V DC	**12 V DC**	**24 V DC**	**24 V UC**	**48-60 V UC**	**115 V UC**	**230 V UC**
Input circuit								
Rated control supply voltage U_s		5 V DC	12 V DC	24 V DC	24 V AC/DC	48 V AC/DC	60 V AC/DC	115 V AC/DC	230 V AC/DC
Rated control supply voltage U_s tolerance	DC	-15 %, +20 %						-15 %, +10 %
	AC	-			-/+ 10 %			
Rated frequency		-			50/60 Hz			
Typical power consumption		0.2 W	0.2 W	0.24 W		0.33 W	0.54 W	0.46 W	0.8 W
Typical current		40 mA	16 mA	10 mA		7 mA	9 mA	4 mA	3.5 mA
Drop-out voltage	at 20 °C	1.2 V	2.2 V	4.5 V		8 V	8 V	17 V	27 V
Indication of operational states	green LED	control supply voltage applied						
Output circuit								
Kind of output	11-12/14	relay, 1 c/o (SPDT) contact						
Rated operational voltage U_e		250 V AC						
Minimum switching voltage		5 V / gold-plated contacts: 5 V						
Maximum switching voltage		250 V AC						
Minimum switching current		60 mA / gold-plated contacts: 10 mA						
Rated free air thermal current I_{th}		6 A						
Rated operational current I_e	AC-12 (resistive) 230 V	6 A						
	AC-15 (inductive) 230 V	1.5 A						
	AC-15 (inductive) 120 V	3 A						
	DC-12 (resistive) 24 V	6 A						
	DC-13 (inductive) 24 V	1 A						
	DC-13 (inductive) 110 V	0.2 A						
	DC-13 (inductive) 220 V	0.1 A						
AC rating (UL 508; NEMA ICS-5)	utilization category (pilot duty)	B300						
DC rating (UL 508; NEMA ICS-5)	utilization category (pilot duty)	R300						
Minimum switching power		300 mW / gold-plated contacts: 50 mW						
Mechanical lifetime		1 x 10^7 switching cycles						
Electrical lifetime	at AC-15	1 x 10^5 switching cycles						
Max. fuse rating to achieve short-circuit protection		6 A fast						
Response time		5 ms	5 ms	5 ms		5 ms	5 ms	6 ms	7 ms
Release time		8 ms	8 ms	8 ms		8 ms	8 ms	15 ms	16 ms

Boxed interface relays R600 range

Technical data

			RB(R)121R-	
			115 V UC	**230 V UC**
Input circuit				
Rated control supply voltage U_s			115 V AC/DC	230 V AC/DC
Rated control supply voltage U_s tolerance		DC	-20%, +15%	-10%, +15%
		AC	-/+ 10 %	
Rated frequency			50/60 Hz	
Typical power consumption			2 W	2.8 W
Typical current			18 mA	12 mA
Drop-out voltage		at 20 °C	17 V	27 V
Indication of operational states		green LED	⎍: control supply voltage applied	
Output circuit				
Kind of output		11-12/14	relay, 1 c/o (SPDT) contact	
Rated operational voltage U_e			250 V AC	
Minimum switching voltage			5 V	
Maximum switching voltage			250 V AC	
Minimum switching current			60 mA	
Rated free air thermal current I_{th}			6 A	
Rated operational current I_e		AC-12 (resistive) 230 V	6 A	
		AC-15 (inductive) 230 V	1.5 A	
		AC-15 (inductive) 120 V	3 A	
		DC-12 (resistive) 24 V	6 A	
		DC-13 (inductive) 24 V	1 A	
		DC-13 (inductive) 110 V	0.2 A	
		DC-13 (inductive) 220 V	0.1 A	
AC rating (UL 508; NEMA ICS-5)		utilization category (pilot duty)	B300	
DC rating (UL 508; NEMA ICS-5)		utilization category (pilot duty)	R300	
Minimum switching power			300 mW	
Mechanical lifetime			1 x 10^7 switching cycles	
Electrical lifetime		at AC-15	1 x 10^5 switching cycles	
Max. fuse rating to achieve short-circuit protection			6 A fast	
Response time			6 ms	7 ms
Release time			15 ms	16 ms

Boxed interface relays R600 range

Technical data

		RB(R)122G				
		24 V UC	**48-60 V UC**		**115 V UC**	**230 V UC**
Input circuit						
Rated control supply voltage U_s		24 V AC/DC	48 V AC/DC	60 V AC/DC	115 V AC/DC	230 V AC/DC
Rated control supply voltage U_s tolerance	DC	-15 %, +20 %				-15 %, +10 %
	AC	-/+ 10 %				
Rated frequency		50/60 Hz				
Typical power consumption		0.48 W	0.62 W	0.96 W	0.58 W	1.15 W
Typical current		20 mA	13 mA	16 mA	5 mA	5 mA
Drop-out	at 20 °C	5.4 V	8.8 V	8.8 V V	20 V	10 V
Indication of operational states	green LED	⎍: control supply voltage applied				
Output circuit						
Kind of output	11-12/14	relay, 1st c/o (SPDT) contact				
	21-22/24	relay, 2nd c/o (SPDT) contact				
Rated operational voltage U_e		250 V AC				
Minimum switching voltage		5 V / gold-plated contacts: 5 V				
Maximum switching voltage		250 V				
Minimum switching current		60 mA / gold-plated contacts: 10 mA				
Rated free air thermal current I_{th}		8 A				
Rated operational current I_e	AC-12 (resistive) 230 V	8 A				
	AC-15 (inductive) 230 V	1.5 A				
	DC-12 (resistive) 24 V	8 A				
	DC-13 (inductive) 24 V	1 A				
	DC-13 (inductive) 110 V	0.2 A				
	DC-13 (inductive) 220 V	0.1 A				
Minimum switching power		300 mW / gold-plated contacts: 50 mW				
Mechanical lifetime		2 x 10^7 switching cycles				
Electrical lifetime	at AC-15	1 x 10^5 switching cycles				
Max. fuse rating to achieve short-circuit protection		10 A fast				
Response time		6 ms	10 ms	10 ms	6 ms	6 ms
Release time		10 ms	14 ms	14 ms	15 ms	15 ms

General technical data - Interface relays


		RB	RBR
General data			
Material of housing		UL 94 V0	
Mounting		DIN rail	
Degree of protection	housing / terminals	IP20 NEMA1	
Electrical connection		**Screw terminal**	**Spring-type terminal**
Connecting capacity	fine-strand	0.22-2.5 mm² (24-14 AWG)	
	rigid	0.2-4 mm² (24-12 AWG)	0.2-2.5 mm² (24-14 AWG)
Stripping length		9 mm (0.354 in)	
Tightening torque		0.4-0.6 Nm (3.5-5.3 lb.in)	n/a
Environmental data			
Ambient temperature ranges	storage	-40...+80 °C (-40...+176 °F)	
	operation	-20...+70 °C (-4...+158 °F) [1]	
Isolation data			
Rated insulation voltage Ui		250 V	
Rated impulse withstand voltage Uimp	input / output	4 kV	
	shock coil / output	4 kV	
	output / output	1 kV	
Overvoltage category		III	
Pollution degree		2	
Standards/Directives			
Standards		IEC/EN 60947-5-1	
Low Voltage Directive		2014/35/EC	
RoHS Directive		2011/65/EC	

[1] Over 55 °C, blocks have to be mounted on horizontal rail with 10 mm spacing between each block. For vertical rail mounting max. operation temperature is 15 °C lower.


Boxed interface relays R600 range

Technical diagrams

Load limit curves




Versions with 1 n/o, 1 n/c or 1 c/o contact




Versions with 2 c/o contacts

Dimensional drawings

in **mm** and inches



R600 - screw connection




R600 - spring connection


Boxed interface relays R600 range

Technical diagrams


Connection diagrams




RB(R)101R - 24VUC




RB(R)111-24VUC




RB111-115VUC/230VUC




RB(R)111R-24VUC




RB(R)121P(G)-5VDC/12VDC




RB(R)121-12VDC/24VDC




RB(R)121(G)-24VUC




RB(R)121(G)-48-60VUC/
115VUC/230VUC/60-230VUC



RB(R)121R-115VUC/230VUC



RB(R)122G-24VUC/48-60VUC



RB(R)122G-115VUC/230VUC

Boxed optocouplers R600 range

Selection table

	Order number	1SNA645047R0000	1SNA645547R0200	1SNA645021R2600	1SNA645521R2000	1SNA645049R1200	1SNA645549R1400	1SNA645022R2700	1SNA645522R2100	1SNA645050R1700	1SNA645550R1100	1SNA645051R0400	1SNA645025R2200	1SNA645024R2100	1SNA645551R0600	1SNA645525R2400	1SNA645524R2300	1SNA645053R0600	1SNA645553R0000	1SNA645054R0700	1SNA645058R1300	1SNA645026R2300	1SNA645526R2500	1SNA645559R1600	1SNA645027R2400	1SNA645029R0600	1SNA645527R2600	1SNA645529R0000	1SNA645062R0700	1SNA645028R0500
	Type	OBIC0100-5-12VDC	OBRIC0100-5-12VDC	OBIC0100-24VDC	OBRIC0100-24VDC	OBIC0100-48-60VUC	OBRIC0100-48-60VUC	OBIC0100-115-230	OBRIC0100-115-230	OBOC2000-5-12VDC	OBROC2000-5-12VDC	OBOC2000-24VDC	OBOC2000-24VUC	OBOC5000-24VDC	OBROC2000-24VDC	OBROC2000-24VUC	OBROC5000-24VDC	OBOC2000-48-60VUC	OBROC2000-48-60VUC	OBOC2000-115VUC	OBOC5000-115VUC	OBOC2000-230VUC	OBROC2000-230VUC	OBROC5000-230VUC	OBOA1000-24VDC	OBOA2000-24VDC	OBROA1000-24VDC	OBROA2000-24VDC	OBOA1000-115VUC	OBOA1000-230VUC
Input voltage																													
5-12 V DC		■	■							■	■																		
24 V DC				■	■							■	■	■	■	■	■								■	■	■	■		
48-60 V DC						■	■											■	■											
115-230 V DC								■	■																					
115 V DC																				■	■								■	
230 V DC								■	■													■	■	■						■
24 V AC													■			■														
48-60 V AC						■	■											■	■											
115-230 V AC								■	■																					
115 V AC																				■	■								■	
230 V AC																						■	■	■						■
Output rating																														
100 mA		■	■	■	■	■	■	■	■																					
1 A																									■		■		■	■
2 A										■	■	■	■		■	■		■	■	■		■	■			■		■		
5 A														■			■				■			■							
Output voltage																														
58 V DC		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■						
230 V AC																										■		■		
400 V AC																									■		■		■	■
Terminal type																														
Screw		■		■		■		■		■		■	■	■				■		■	■	■			■	■			■	■
Spring			■		■		■		■		■				■	■	■		■				■	■			■	■		
Kind of output																														
Transistor		■	■	■	■	■	■	■	■																					
MOS-FET										■	■	■	■	■	■	■	■	■	■	■	■	■	■	■						
Triac																									■	■	■	■	■	■

Boxed optocouplers R600 range

Ordering details



R600 - 6 mm

Ordering details - Transistor output, 58 V DC, 100 mA, width 6 mm

Rated control supply voltage	Connection type	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
5 - 12 V DC	screw	OBIC0100-5-12VDC	1SNA645047R0000	10	0.02 (0.044)
24 V DC	screw	OBIC0100-24VDC	1SNA645021R2600		
48 - 60 V AC/DC	screw	OBIC0100-48-60VUC	1SNA645049R1200		
115 - 230 V AC/DC	screw	OBIC0100-115-230	1SNA645022R2700		
5 - 12 V DC	spring	OBRIC0100-5-12VDC	1SNA645547R0200	10	0.02 (0.044)
24 V DC	spring	OBRIC0100-24VDC	1SNA645521R2000		
48 - 60 V AC/DC	spring	OBRIC0100-48-60VUC	1SNA645549R1400		
115 - 230 V AC/DC	spring	OBRIC0100-115-230	1SNA645522R2100		

Ordering details - MOS-FET output, 58 V DC, 2 A, width 6 mm

Rated control supply voltage	Connection type	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
5 - 12 V DC	screw	OBOC2000-5-12VDC	1SNA645050R1700	10	0.02 (0.044)
24 V DC	screw	OBOC2000-24VDC	1SNA645051R0400		
24 V AC/DC	screw	OBOC2000-24VUC	1SNA645025R2200		
48 - 60 V AC/DC	screw	OBOC2000-48-60VUC	1SNA645053R0600		
115 V AC/DC	screw	OBOC2000-115VUC	1SNA645054R0700		
230 V AC/DC	screw	OBOC2000-230VUC	1SNA645026R2300		
5 - 12 V DC	spring	OBROC2000-5-12VDC	1SNA645550R1100	10	0.02 (0.044)
24 V DC	spring	OBROC2000-24VDC	1SNA645551R0600		
24 V AC/DC	spring	OBROC2000-24VUC	1SNA645525R2400		
48 - 60 V AC/DC	spring	OBROC2000-48-60VUC	1SNA645553R0000		
230 V AC/DC	spring	OBROC2000-230VUC	1SNA645526R2500		

Ordering details - MOS-FET output, 58 V DC, 5 A, width 6 mm

Rated control supply voltage	Connection type	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V DC	screw	OBOC5000-24VDC	1SNA645024R2100	10	0.02 (0.044)
115 V AC/DC	screw	OBOC5000-115VUC	1SNA645058R1300		
24 V DC	spring	OBROC5000-24VDC	1SNA645524R2300	10	0.02 (0.044)
230 V AC/DC	spring	OBROC5000-230VUC	1SNA645559R1600		

Ordering details - Triac output, 400 V AC, 1 A, width 6 mm

Rated control supply voltage	Connection type	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V DC	screw	OBOA1000-24VDC	1SNA645027R2400	10	0.03 (0.066)
115 V AC/DC	screw	OBOA1000-115VUC	1SNA645062R0700		
230 V AC/DC	screw	OBOA1000-230VUC	1SNA645028R0500		
24 V DC	spring	OBROA1000-24VDC	1SNA645527R2600	10	

Boxed optocouplers R600 range

Ordering details



R600 - 12 mm

Ordering details - Triac output, 230 V AC, 2 A, width 12 mm

Rated control supply voltage	Connection type	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
24 V DC	screw	OBOA2000-24VDC	1SNA645029R0600	5	0.03 (0.066)
24 V DC	spring	OBROA2000-24VDC	1SNA645529R0000	5	

Ordering details - Accessories

Description	Type	Order code	Pkg qty	Weight (1 pc.) kg (lb)
Jumper bar, 10 poles * (replacement of BJ612-10 - 1SNA290488R0100)	RB-JB10	1SVR406570R0000	10	0.05 (0.11)
Jumper bar, 20 poles * (replacement of BJ612-20 - 1SNA206754R0000)	RB-JB20	1SVR406580R0000		0.10 (0.22)
Separator end section	SC612	1SNA290474R0200		0.05 (0.11)

* - Before the first and after the last jumpered R600 optocoupler, a separator end section shall be used.
- The sum of the current for jumpered devices shall not exceed 6 A on 6 mm devices and 8 A on 12 mm devices.

Boxed optocouplers R600 range

Technical data

	OB(R)IC0100-...						
	5-12 V DC		**24 V DC**	**48-60 V UC**		**115-230**	
Input circuit							
Input voltage	5 V DC	12 V DC	24 V DC	48 V AC/DC	60 V AC/DC	115 V AC/DC	230 V AC/DC
Frequency	-			50/60 Hz			
Input current	5 mA	9 mA	4 mA	4 mA	5 mA	7 mA (AC) 16 mA (DC)	11.5 mA (AC) 25 mA (DC)
Pull-in voltage	4 V		15 V	25 V		60 V AC / 70 V DC	
Typ. switch-on time	10 µs			5 ms			
Typ. switch-off time	500 µs			20 ms			
Operating frequency	1000 Hz				20 Hz		
Permissible leakage current	0.9 mA		1.0 mA	0.9 mA		1.6 mA	
Output circuit	11(13+)- 14						
Kind of output	Transistor						
Rated operational voltage	4.5-58 V DC						
Minimum switching current	1 mA						
Maximum switching current	100 mA						
Leakage current at max. switching voltage	< 50 µA						
Rated operational current I_e (IEC/EN 60947-5-1) DC-12 (resistive) 58 V	0.1 A						
Residual voltage typical	1 V						
maximum	1.3 V						
Max. fuse rating to achieve short-circuit protection	100 mA fast						
Isolation data							
Rated insulation voltage Ui	250 V						
Rated impulse withstand voltage Uimp	2.5 kV						
Overvoltage category	II						
Pollution degree	2						

	OB(R)OC2000-...							
	5-12 V DC		**24 V DC**	**24 V UC**	**48-60 V UC**		**115 V UC**	**230 V UC**
Input circuit								
Input voltage	5 V DC	12 V DC	24 V DC	24 V AC/DC	48 V AC/DC	60 V AC/DC	115 V AC/DC	230 V AC/DC
Frequency	-			50/60 Hz				
Input current	5 mA	9 mA	5.4 mA	6.3 mA	4 mA	5.1 mA	4.2 mA	4 mA
Pull-in voltage	4 V		12 V	15 V	27 V		50 V	80 V
Typ. switch-on time	15 µs		30 µs	1 ms	5 ms		500 µs	1 ms
Typ. switch-off time	250 µs		400 µs	7 ms	20 ms		10 ms	15 ms
Operating frequency	2000 Hz		1000 Hz	60 Hz	20 Hz		50 Hz	35 Hz
Permissible leakage current	1 mA		0.8 mA	0.9 mA	1 mA		0.3 mA	
Output circuit	11(13+)- 14							
Kind of output	MOS-FET							
Rated operational voltage	4.5-58 V DC							
Minimum switching current	1 mA							
Maximum switching current	2 A							
Leakage current at max. switching voltage	< 50 µA							
Rated operational current I_e DC-12 (resistive) 58 V	2 A							
Residual voltage typical	0.1 V							
maximum	0.5 V							
Max. fuse rating to achieve short-circuit protection	2 A ultra-fast							
Isolation data								
Rated insulation voltage U_i	250 V							
Rated impulse withstand voltage U_{imp}	2.5 kV							
Overvoltage category	II							
Pollution degree	2							

Boxed optocouplers R600 range

Technical data

		OB(R)OC5000-...		
		24 V DC	115 V UC	230 V UC
Input circuit				
Input voltage		24 V DC	115 V AC/DC	230 V AC/DC
Frequency		-	50/60 Hz	
Input current		5.4 mA	4.2 mA	4 mA
Pull-in voltage		12 V	50 V	80 V
Typ. switch-on time		30 µs	500 µs	1 ms
Typ. switch-off time		400 µs	10 ms	15 ms
Operating frequency		1000 Hz	50 Hz	35 Hz
Permissible leakage current		0.8 mA	0.3 mA	0.3 mA
Output circuit		11(13+)- 14		
Kind of output		MOS-FET		
Rated operational voltage		4.5-58 V DC		
Minimum switching current		1 mA		
Maximum switching current		5 A		
Leakage current at max. switching voltage		< 50 µA		
Rated operational current I_e	DC-12 (resistive) 58 V	5 A		
Residual voltage	typical	0.1 V		
	maximum	0.5 V		
Max. fuse rating to achieve short-circuit protection		6 A ultra-fast		
Isolation data				
Rated insulation voltage Ui		250 V		
Rated impulse withstand voltage Uimp		2.5 kV		
Overvoltage category		II		
Pollution degree		2		

		OB(R)OA1000-...			OB(R)OA2000-...
		24 V DC	**115 V UC**	**230 V UC**	**24 V DC**
Input circuit					
Input voltage		24 V DC	115 V AC/DC	230 V AC/DC	24 V DC
Frequency		-	50/60 Hz		-
Input current		3.6 mA	4.15 mA	4.6 mA	3.6 mA
Pull-in voltage		14 V	60 V	135 V	14 V
Typ. switch-on time		150 µs	2.2 ms	2.5 ms	150 µs
Typ. switch-off time		1 ms	18 ms	25 ms	1 ms
Operating frequency		500 Hz	25 Hz	20 Hz	500 Hz
Permissible leakage current		1 mA			1 mA
Output circuit		11(13+)- 14			
Kind of output		Triac			Triac
Rated operational voltage		24-400 V AC			10-230 V AC
Minimum switching current		25 mA			25 mA
Maximum switching current		1 A			2 A
Leakage current at max. switching voltage		< 500 µA			< 500 µA
Rated operational current I_e	AC-12 (resistive) 400 V	1 A			-
	AC-12 (resistive) 230 V	-			2A
Residual voltage	typical	1 V			1 V
	maximum	1.6 V			1.6 V
Max. fuse rating to achieve short-circuit protection		4 A ultra-fast			4 A ultra-fast
Isolation data					
Rated insulation voltage U_i		400 V			230 V
Rated impulse withstand voltage U_{imp}		4 kV			4 kV
Overvoltage category		II			II
Pollution degree		2			2

Boxed optocouplers R600 range

Technical data

General technical data - Optocouplers


		OB	OBR
General data			
Material of housing		UL 94 V0	
Mounting		DIN Rail	
Degree of protection	housing / terminals	IP20 NEMA1	
Electrical connection		**Screw terminal**	**Spring-type terminal**
Connecting capacity	fine-strand	0.22-2.5 mm² (24-14 AWG)	
	rigid	0.2-4 mm² (24-12 AWG)	0.2-2.5 mm² (24-14 AWG)
Stripping length		9 mm (0.354 in)	
Tightening torque		0.4-0.6 Nm (3.5-5.3 lb.in)	n/a
Environmental data			
Ambient temperature ranges	storage	-40...+80 °C (-40...+176 °F)	
	operation	-20...+70 °C (-4...+158 °F)	
Standards/Directives			
Standards		IEC/EN 60947-5-1	
Low Voltage Directive		2014/35/EU	
RoHS Directive		2011/65/EU	

Boxed optocouplers R600 range


Technical diagrams

Dimensional drawings

in **mm** and inches




R600 - screw connection




R600 - spring connection


Connection diagrams



OB(R)OC, OB(R)IC
except 5-12 V DC versions



OB(R)IC0100-5-12 V DC
OB(R)OC2000-5-12 V DC



OB(R)OA

Index
Product type

Type	Order code	Page
ADP.01	1SVR430029R0100	41
ADP.01	1SVR430029R0100	242
ADP.02	1SVR440029R0100	242
C011-100	GHC0110003R0004	191
C011-110	GHC0110003R0005	191
C011-120	GHC0110003R0006	191
C011-130	GHC0110003R0007	191
C011-140	GHC0110003R0011	191
C011-150	GHC0110003R0008	191
C011-160	GHC0110003R0009	191
C011-170	GHC0110003R0010	191
C011-3-150	GHC0110033R0008	191
C011-70	GHC0110003R0001	191
C011-80	GHC0110003R0002	191
C011-90	GHC0110003R0003	191
CM-AH-3	1SVR450056R7000	242
CM-CT 100/1	1SVR450116R1200	243
CM-CT 100/5	1SVR450116R5200	243
CM-CT 150/1	1SVR450116R1300	243
CM-CT 150/5	1SVR450116R5300	243
CM-CT 200/1	1SVR450116R1400	243
CM-CT 200/5	1SVR450116R5400	243
CM-CT 300/1	1SVR450117R1100	243
CM-CT 300/5	1SVR450117R5100	243
CM-CT 400/1	1SVR450117R1200	243
CM-CT 400/5	1SVR450117R5200	243
CM-CT 50/1	1SVR450116R1000	243
CM-CT 50/5	1SVR450116R5000	243
CM-CT 500/1	1SVR450117R1300	243
CM-CT 500/5	1SVR450117R5300	243
CM-CT 600/1	1SVR450117R1400	243
CM-CT 600/5	1SVR450117R5400	243
CM-CT 75/1	1SVR450116R1100	243
CM-CT 75/5	1SVR450116R5100	243
CM-CT A	1SVR450118R1000	243
CM-EFS.2P	1SVR740750R0400	89
CM-EFS.2S	1SVR730750R0400	89
CM-ENE MAX	1SVR550855R9400	229
CM-ENE MAX	1SVR550850R9400	229
CM-ENE MAX	1SVR550851R9400	229
CM-ENE MIN	1SVR550855R9500	229
CM-ENE MIN	1SVR550850R9500	229
CM-ENE MIN	1SVR550851R9500	229
CM-ENS.11P	1SVR730850R2100	229
CM-ENS.11S	1SVR730850R0100	229
CM-ENS.13P	1SVR740850R2100	229
CM-ENS.13S	1SVR740850R0100	229
CM-ENS.21P	1SVR740850R0200	229
CM-ENS.21S	1SVR730850R0200	229
CM-ENS.23P	1SVR740850R2200	229
CM-ENS.23S	1SVR730850R2200	229
CM-ENS.31P	1SVR740850R0300	229
CM-ENS.31S	1SVR730850R0300	229
CM-ESS.1P	1SVR740830R0300	89
CM-ESS.1P	1SVR740831R0300	89
CM-ESS.1P	1SVR740831R1300	89
CM-ESS.1S	1SVR730830R0300	89
CM-ESS.1S	1SVR730831R0300	89
CM-ESS.1S	1SVR730831R1300	89
CM-ESS.2P	1SVR740830R0400	89
CM-ESS.2P	1SVR740831R0400	89
CM-ESS.2P	1SVR740831R1400	89
CM-ESS.2S	1SVR730830R0400	89
CM-ESS.2S	1SVR730831R0400	89
CM-ESS.2S	1SVR730831R1400	89
CM-ESS.MP	1SVR740830R0500	89
CM-ESS.MS	1SVR730830R0500	89
CM-GM-1	1SVR450056R8000	242
CM-HC	1SVR402902R1000	242
CM-HCT	1SVR402902R2000	242
CM-HE	1SVR402902R0000	242
CM-IVN.P	1SVR760669R9400	161
CM-IVN.S	1SVR750669R9400	161
CM-IWM.10	1SVR470670R1000	161
CM-IWM.11	1SVR470670R1100	161
CM-IWN.1P	1SVR760660R0200	161
CM-IWN.1S	1SVR750660R0200	161
CM-IWS.1P	1SVR740660R0100	161
CM-IWS.1S	1SVR730660R0100	161
CM-IWS.2P	1SVR740670R0200	161
CM-IWS.2S	1SVR730670R0200	161
CM-KH-3	1SVR450056R6000	242
CM-MPN.52P	1SVR760487R8300	115
CM-MPN.52S	1SVR750487R8300	115
CM-MPN.62P	1SVR760488R8300	115
CM-MPN.62S	1SVR750488R8300	115
CM-MPN.72P	1SVR760489R8300	115
CM-MPN.72S	1SVR750489R8300	115
CM-MPS.11P	1SVR740885R1300	115
CM-MPS.11S	1SVR730885R1300	115
CM-MPS.21P	1SVR740885R3300	115
CM-MPS.21S	1SVR730885R3300	115
CM-MPS.23P	1SVR740885R4300	115
CM-MPS.23S	1SVR730885R4300	115
CM-MPS.31P	1SVR740884R1300	115
CM-MPS.31S	1SVR730884R1300	115
CM-MPS.41P	1SVR740884R3300	115
CM-MPS.41S	1SVR730884R3300	115
CM-MPS.43P	1SVR740884R4300	115
CM-MPS.43S	1SVR730884R4300	115
CM-MSE	1SVR550805R9300	190
CM-MSE	1SVR550800R9300	190

Index
Product type

Type	Order code	Page
CM-MSE	1SVR550801R9300	190
CM-MSS.11P	1SVR740720R1400	190
CM-MSS.11S	1SVR730720R1400	190
CM-MSS.12P	1SVR740700R0100	190
CM-MSS.12S	1SVR730700R0100	190
CM-MSS.13P	1SVR740700R2100	190
CM-MSS.13S	1SVR730700R2100	190
CM-MSS.21P	1SVR740722R1400	190
CM-MSS.21S	1SVR730722R1400	190
CM-MSS.22P	1SVR740700R0200	190
CM-MSS.22S	1SVR730700R0200	190
CM-MSS.23P	1SVR740700R2200	190
CM-MSS.23S	1SVR730700R2200	190
CM-MSS.31P	1SVR740712R1400	190
CM-MSS.31S	1SVR730712R1400	190
CM-MSS.32P	1SVR740712R0200	190
CM-MSS.32S	1SVR730712R0200	190
CM-MSS.33P	1SVR740712R2200	190
CM-MSS.33S	1SVR730712R2200	190
CM-MSS.41P	1SVR740712R1200	190
CM-MSS.41S	1SVR730712R1200	190
CM-MSS.51P	1SVR740712R1300	190
CM-MSS.51S	1SVR730712R1300	190
CM-PAS.31P	1SVR740774R1300	113
CM-PAS.31S	1SVR730774R1300	113
CM-PAS.41P	1SVR740774R3300	113
CM-PAS.41S	1SVR730774R3300	113
CM-PBE	1SVR550881R9400	113
CM-PBE	1SVR550882R9500	113
CM-PFE	1SVR550824R9100	113
CM-PFE.2	1SVR550826R9100	113
CM-PFS.P	1SVR740824R9300	113
CM-PFS.S	1SVR730824R9300	113
CM-PSS.31P	1SVR740784R2300	113
CM-PSS.31S	1SVR730784R2300	113
CM-PSS.41P	1SVR740784R3300	113
CM-PSS.41S	1SVR730784R3300	113
CM-PVE	1SVR550870R9400	113
CM-PVE	1SVR550871R9500	113
CM-PVS.31P	1SVR740794R1300	113
CM-PVS.31S	1SVR730794R1300	113
CM-PVS.41P	1SVR740794R3300	113
CM-PVS.41S	1SVR730794R3300	113
CM-PVS.81P	1SVR740794R2300	113
CM-PVS.81S	1SVR730794R2300	113
CM-SE-1000	1SVR450056R0200	242
CM-SE-300	1SVR450056R0000	242
CM-SE-600	1SVR450056R0100	242
CM-SFS.21P	1SVR740760R0400	87
CM-SFS.21S	1SVR730760R0400	87
CM-SFS.22S	1SVR730760R0500	87

Type	Order code	Page
CM-SRS.11P	1SVR740840R0200	87
CM-SRS.11P	1SVR740841R0200	87
CM-SRS.11P	1SVR740841R1200	87
CM-SRS.11S	1SVR730840R0200	87
CM-SRS.11S	1SVR730841R0200	87
CM-SRS.11S	1SVR730841R1200	87
CM-SRS.12S	1SVR730840R0300	87
CM-SRS.12S	1SVR730841R0300	87
CM-SRS.12S	1SVR730841R1300	87
CM-SRS.21P	1SVR740840R0400	87
CM-SRS.21P	1SVR740841R0400	87
CM-SRS.21P	1SVR740841R1400	87
CM-SRS.21S	1SVR730840R0400	87
CM-SRS.21S	1SVR730841R0400	87
CM-SRS.21S	1SVR730841R1400	87
CM-SRS.22S	1SVR730840R0500	87
CM-SRS.22S	1SVR730841R0500	87
CM-SRS.22S	1SVR730841R1500	87
CM-SRS.M1P	1SVR740840R0600	87
CM-SRS.M1S	1SVR730840R0600	87
CM-SRS.M2S	1SVR730840R0700	87
CM-TCS.11P	1SVR740740R0100	209
CM-TCS.11S	1SVR730740R0100	209
CM-TCS.12P	1SVR740740R0200	209
CM-TCS.12S	1SVR730740R0200	209
CM-TCS.13P	1SVR740740R0300	209
CM-TCS.13S	1SVR730740R0300	209
CM-TCS.21P	1SVR740740R9100	209
CM-TCS.21S	1SVR730740R9100	209
CM-TCS.22P	1SVR740740R9200	209
CM-TCS.22S	1SVR730740R9200	209
CM-TCS.23P	1SVR740740R9300	209
CM-TCS.23S	1SVR730740R9300	209
CM-UFD.M22M	1SVR560731R3700	145
CM-UFD.M31	1SVR560730R3401	145
CM-UFD.M31M	1SVR560731R3701	145
CM-UFD.M33	1SVR560730R3402	145
CM-UFD.M33M	1SVR560731R3702	145
CM-UFD.M34M	1SVR560731R3703	145
COV.01	1SVR430005R0100	242
COV.02	1SVR440005R0100	242
COV.11	1SVR730005R0100	41
COV.11	1SVR730005R0100	242
COV.12	1SVR750005R0100	242
CP-B 24/10.0	1SVR427060R1000	332
CP-B 24/20.0	1SVR427060R2000	332
CP-B 24/3.0	1SVR427060R0300	332
CP-B EXT.2	1SVR427065R0000	332
CP-C.1 24/10.0	1SVR360663R1001	294
CP-C.1 24/10.0-C	1SVR360663R2001	294
CP-C.1 24/10.0-L	1SVR361663R1001	294

Index
Product type

Type	Order code	Page
CP-C.1 24/20.0	1SVR360763R1001	294
CP-C.1 24/20.0-C	1SVR360763R2001	294
CP-C.1 24/20.0-L	1SVR361763R1001	294
CP-C.1 24/5.0	1SVR360563R1001	294
CP-C.1 24/5.0-C	1SVR360563R2001	294
CP-C.1 24/5.0-L	1SVR361563R1001	294
CP-C.1-A-RU	1SVR360060R1001	342
CP-C.1-A-RU-C	1SVR360060R2001	342
CP-C.1-A-RU-L	1SVR361060R1001	342
CP-D 12/0.83	1SVR427041R1000	318
CP-D 12/2.1	1SVR427043R1200	318
CP-D 24/0.42	1SVR427041R0000	318
CP-D 24/1.3	1SVR427043R0100	318
CP-D 24/2.5	1SVR427044R0200	318
CP-D 24/4.2	1SVR427045R0400	318
CP-D RU	1SVR427049R0000	342
CP-E 12/10.0	1SVR427035R1000	260
CP-E 12/2.5	1SVR427032R1000	260
CP-E 24/0.75	1SVR427030R0000	260
CP-E 24/1.25	1SVR427031R0000	260
CP-E 24/10.0	1SVR427035R0000	260
CP-E 24/2.5	1SVR427032R0000	260
CP-E 24/20.0	1SVR427036R0000	260
CP-E 24/5.0	1SVR427034R0000	260
CP-E 48/0.62	1SVR427030R2000	260
CP-E 48/1.25	1SVR427031R2000	260
CP-E 48/10.0	1SVR427035R2000	260
CP-E 48/5.0	1SVR427034R2000	260
CP-E 5/3.0	1SVR427033R3000	260
CP-RUD	1SVR423418R9000	342
CP-T 24/10.0	1SVR427055R0000	280
CP-T 24/20.0	1SVR427056R0000	280
CP-T 24/40.0	1SVR427057R0000	280
CP-T 24/5.0	1SVR427054R0000	280
CP-T 48/10.0	1SVR427055R2000	280
CP-T 48/20.0	1SVR427056R2000	280
CP-T 48/5.0	1SVR427054R2000	280
CR-M012AC2L	1SVR405611R0300	398
CR-M012AC3L	1SVR405612R0300	398
CR-M012AC4L	1SVR405613R0300	398
CR-M012DC2	1SVR405611R4000	397
CR-M012DC2L	1SVR405611R4100	398
CR-M012DC2LD	1SVR405611R4400	399
CR-M012DC3	1SVR405612R4000	397
CR-M012DC3L	1SVR405612R4100	398
CR-M012DC3LD	1SVR405612R4400	399
CR-M012DC4	1SVR405613R4000	397
CR-M012DC4L	1SVR405613R4100	398
CR-M012DC4LD	1SVR405613R4400	399
CR-M012DC4LDG	1SVR405618R4400	400
CR-M012DC4LDGSS	1SVR405618R4410	401
CR-M012DC4LG	1SVR405618R4100	400
CR-M024AC2	1SVR405611R0000	397
CR-M024AC2L	1SVR405611R0100	398
CR-M024AC3	1SVR405612R0000	397
CR-M024AC3L	1SVR405612R0100	398
CR-M024AC4	1SVR405613R0000	397
CR-M024AC4G	1SVR405618R0000	399
CR-M024AC4L	1SVR405613R0100	398
CR-M024AC4LG	1SVR405618R0100	400
CR-M024AC4LS62CV	1SVR405613R0010	401
CR-M024DC2	1SVR405611R1000	397
CR-M024DC2L	1SVR405611R1100	398
CR-M024DC2LD	1SVR405611R1400	399
CR-M024DC3	1SVR405612R1000	397
CR-M024DC3L	1SVR405612R1100	398
CR-M024DC3LD	1SVR405612R1400	399
CR-M024DC4	1SVR405613R1000	397
CR-M024DC4G	1SVR405618R1000	399
CR-M024DC4GLC62CV	1SVR405618R1010	401
CR-M024DC4GSS42V	1SVR405618R1011	401
CR-M024DC4L	1SVR405613R1100	398
CR-M024DC4LC42	1SVR405613R1012	401
CR-M024DC4LD	1SVR405614R1100	399
CR-M024DC4LDG	1SVR405618R1400	400
CR-M024DC4LDGSS	1SVR405618R1410	401
CR-M024DC4LG	1SVR405618R1100	400
CR-M024DC4LGLC22	1SVR405618R1110	401
CR-M024DC4LS42V	1SVR405613R1011	401
CR-M024DC4SS42V	1SVR405613R1010	401
CR-M048AC2	1SVR405611R5000	397
CR-M048AC2L	1SVR405611R5100	398
CR-M048AC3	1SVR405612R5000	397
CR-M048AC3L	1SVR405612R5100	398
CR-M048AC4	1SVR405613R5000	397
CR-M048AC4L	1SVR405613R5100	398
CR-M048AC4LG	1SVR405618R5100	400
CR-M048DC2	1SVR405611R6000	397
CR-M048DC2L	1SVR405611R6100	398
CR-M048DC2LD	1SVR405611R6400	399
CR-M048DC3	1SVR405612R6000	397
CR-M048DC3L	1SVR405612R6100	398
CR-M048DC3LD	1SVR405612R6400	399
CR-M048DC4	1SVR405613R6000	397
CR-M048DC4L	1SVR405613R6100	398
CR-M048DC4LD	1SVR405613R6400	399
CR-M048DC4LG	1SVR405618R6100	400
CR-M060AC3	1SVR405612R5200	397
CR-M060DC2	1SVR405611R4200	397
CR-M060DC2L	1SVR405611R4300	398
CR-M060DC3	1SVR405612R4200	397
CR-M060DC3L	1SVR405612R4300	398

Index
Product type

Type	Order code	Page
CR-M060DC4	1SVR405613R4200	397
CR-M060DC4L	1SVR405613R4300	398
CR-M060DC4LG	1SVR405618R4300	400
CR-M110AC2	1SVR405611R7000	397
CR-M110AC2L	1SVR405611R7100	398
CR-M110AC3	1SVR405612R7000	397
CR-M110AC3L	1SVR405612R7100	398
CR-M110AC4	1SVR405613R7000	397
CR-M110AC4G	1SVR405618R7000	399
CR-M110AC4L	1SVR405613R7100	398
CR-M110AC4LG	1SVR405618R7100	400
CR-M110DC2	1SVR405611R8000	397
CR-M110DC2L	1SVR405611R8100	398
CR-M110DC2LD	1SVR405611R8400	399
CR-M110DC3	1SVR405612R8000	397
CR-M110DC3L	1SVR405612R8100	398
CR-M110DC3LD	1SVR405612R8400	399
CR-M110DC4	1SVR405613R8000	397
CR-M110DC4L	1SVR405613R8100	398
CR-M110DC4LD	1SVR405613R8400	399
CR-M110DC4LG	1SVR405618R8100	400
CR-M120AC2	1SVR405611R2000	397
CR-M120AC2L	1SVR405611R2100	398
CR-M120AC3	1SVR405612R2000	397
CR-M120AC3L	1SVR405612R2100	398
CR-M120AC4	1SVR405613R2000	397
CR-M120AC4L	1SVR405613R2100	398
CR-M120AC4LG	1SVR405618R2100	400
CR-M125DC2	1SVR405611R8200	397
CR-M125DC2L	1SVR405611R8300	398
CR-M125DC2LD	1SVR405611R8500	399
CR-M125DC3	1SVR405612R8200	397
CR-M125DC3L	1SVR405612R8300	398
CR-M125DC3LD	1SVR405612R8500	399
CR-M125DC4	1SVR405613R8200	397
CR-M125DC4L	1SVR405613R8300	398
CR-M125DC4LD	1SVR405613R8500	399
CR-M125DC4LG	1SVR405618R8300	400
CR-M220DC2	1SVR405611R9000	397
CR-M220DC2L	1SVR405611R9100	398
CR-M220DC2LD	1SVR405611R9400	399
CR-M220DC3	1SVR405612R9000	397
CR-M220DC3L	1SVR405612R9100	398
CR-M220DC3LD	1SVR405612R9400	399
CR-M220DC4	1SVR405613R9000	397
CR-M220DC4L	1SVR405613R9100	398
CR-M220DC4LD	1SVR405613R9400	399
CR-M220DC4LG	1SVR405618R9100	400
CR-M230AC2	1SVR405611R3000	397
CR-M230AC2L	1SVR405611R3100	398
CR-M230AC3	1SVR405612R3000	397
CR-M230AC3L	1SVR405612R3100	398
CR-M230AC4	1SVR405613R3000	397
CR-M230AC4G	1SVR405618R3000	399
CR-M230AC4GSS92CV	1SVR405618R3112	402
CR-M230AC4L	1SVR405613R3100	398
CR-M230AC4LC92	1SVR405613R3012	402
CR-M230AC4LG	1SVR405618R3100	400
CR-M230AC4LGLC	1SVR405618R3110	402
CR-M230AC4LGSS	1SVR405618R3111	402
CR-M230AC4LS92CV	1SVR405613R3011	402
CR-M230AC4SS92CV	1SVR405613R3110	402
CR-M2LC	1SVR405651R1200	403
CR-M2LS	1SVR405651R1100	403
CR-M2SF	1SVR405651R1300	403
CR-M2SS	1SVR405651R1000	403
CR-M3LS	1SVR405651R2100	403
CR-M3SS	1SVR405651R2000	403
CR-M4LC	1SVR405651R3200	403
CR-M4LS	1SVR405651R3100	403
CR-M4SF	1SVR405651R3300	403
CR-M4SS	1SVR405651R3000	403
CR-MH	1SVR405659R1000	403
CR-MH1	1SVR405659R1100	403
CR-MJ	1SVR405658R6000	403
CR-MM	1SVR405658R1000	403
CR-MP	1SVR405658R2000	403
CR-P/M 22	1SVR405651R0000	404
CR-P/M 42	1SVR405652R0000	404
CR-P/M 42 B	1SVR405652R4000	404
CR-P/M 42 BV	1SVR405652R4100	404
CR-P/M 42 C	1SVR405652R9000	404
CR-P/M 42 CV	1SVR405652R9100	404
CR-P/M 42 V	1SVR405652R1000	404
CR-P/M 52B	1SVR405653R0000	404
CR-P/M 52C	1SVR405653R1000	404
CR-P/M 52D	1SVR405653R4000	404
CR-P/M 62	1SVR405654R0000	404
CR-P/M 62 C	1SVR405655R0000	405
CR-P/M 62 CV	1SVR405655R1000	405
CR-P/M 62 D	1SVR405655R4000	405
CR-P/M 62 DV	1SVR405655R4100	405
CR-P/M 62 E	1SVR405654R4000	404
CR-P/M 62 EV	1SVR405654R4100	404
CR-P/M 62 V	1SVR405654R1000	404
CR-P/M 72	1SVR405656R0000	405
CR-P/M 72 A	1SVR405656R1000	405
CR-P/M 82	1SVR405656R2000	405
CR-P/M 92	1SVR405654R0100	404
CR-P/M 92 C	1SVR405655R0100	405
CR-P/M 92 CV	1SVR405655R1100	405
CR-P/M 92 V	1SVR405654R1100	404

Index
Product type

Type	Order code	Page
CR-P012AC2	1SVR405601R0200	393
CR-P012DC1	1SVR405600R4000	393
CR-P012DC1SS42V	1SVR405600R4010	395
CR-P012DC2	1SVR405601R4000	393
CR-P012DC2SS42V	1SVR405601R4010	396
CR-P024AC1	1SVR405600R0000	393
CR-P024AC1SS62CV	1SVR405600R0010	395
CR-P024AC2	1SVR405601R0000	393
CR-P024AC2G	1SVR405606R0000	393
CR-P024AC2SS62CV	1SVR405601R0010	396
CR-P024DC1	1SVR405600R1000	393
CR-P024DC1LC42V	1SVR405600R1011	395
CR-P024DC1LC62C	1SVR405600R1013	395
CR-P024DC1SS42V	1SVR405600R1010	395
CR-P024DC2	1SVR405601R1000	393
CR-P024DC2G	1SVR405606R1000	393
CR-P024DC2GLC42V	1SVR405606R1010	396
CR-P024DC2GLC62C	1SVR405606R1013	396
CR-P024DC2GLC62CV	1SVR405606R1011	396
CR-P024DC2LC42	1SVR405601R1012	396
CR-P024DC2LS42	1SVR405601R1013	396
CR-P024DC2LS42V	1SVR405601R1011	396
CR-P024DC2SS42V	1SVR405601R1010	396
CR-P024MOS1	1SVR405610R4060	393
CR-P024TRI1	1SVR405610R4070	393
CR-P048AC1	1SVR405600R5000	393
CR-P048AC2	1SVR405601R5000	393
CR-P048DC1	1SVR405600R6000	393
CR-P048DC2	1SVR405601R6000	393
CR-P110AC1	1SVR405600R7000	393
CR-P110AC2	1SVR405601R7000	393
CR-P110AC2G	1SVR405606R7000	393
CR-P110DC1	1SVR405600R8000	393
CR-P110DC1SS42CV	1SVR405600R8010	395
CR-P110DC2	1SVR405601R8000	393
CR-P110DC2SS42CV	1SVR405601R8010	396
CR-P120AC1	1SVR405600R2000	393
CR-P120AC1SS92CV	1SVR405600R2010	395
CR-P120AC2	1SVR405601R2000	393
CR-P120AC2SS92CV	1SVR405601R2010	396
CR-P230AC1	1SVR405600R3000	393
CR-P230AC1LC92CV	1SVR405600R3010	395
CR-P230AC1LS	1SVR405600R3011	395
CR-P230AC1SS92CV	1SVR405600R3110	395
CR-P230AC2	1SVR405601R3000	393
CR-P230AC2G	1SVR405606R3000	393
CR-P230AC2GLC92	1SVR405606R3013	396
CR-P230AC2GLC92C	1SVR405606R3012	396
CR-P230AC2GLC92CV	1SVR405606R3010	396
CR-P230AC2LC92	1SVR405601R3012	396
CR-P230AC2LS92CV	1SVR405601R3011	396
CR-P230AC2SS92CV	1SVR405601R3110	396
CR-PH	1SVR405659R0000	394
CR-PH1	1SVR405659R0100	394
CR-PJ	1SVR405658R5000	394
CR-PLC	1SVR405650R0200	394
CR-PLS	1SVR405650R0000	394
CR-PLSX	1SVR405650R0100	394
CR-PM	1SVR405658R0000	394
CR-PSS	1SVR405650R1000	394
CR-S005VDC1R	1SVR405501R1010	389
CR-S005VDC1RG	1SVR405501R1020	389
CR-S006/024VDC1SS	1SVR405521R1100	390
CR-S006/024VDC1SZ	1SVR405521R1200	390
CR-S012/024VADC1SS	1SVR405521R3100	390
CR-S012/024VADC1SZ	1SVR405521R3200	390
CR-S012VDC1R	1SVR405501R2010	389
CR-S012VDC1RG	1SVR405501R2020	389
CR-S024VADC1CRGS	1SVR405541R3120	389
CR-S024VADC1CRGZ	1SVR405541R3220	389
CR-S024VADC1CRS	1SVR405541R3110	389
CR-S024VADC1CRZ	1SVR405541R3210	389
CR-S024VDC1MOS	1SVR405510R3060	389
CR-S024VDC1R	1SVR405501R3010	389
CR-S024VDC1RG	1SVR405501R3020	389
CR-S024VDC1TRA	1SVR405510R3050	389
CR-S024VDC1TRI	1SVR405510R3070	389
CR-S048/060VADC1SS	1SVR405521R5100	390
CR-S048/060VADC1SZ	1SVR405521R5200	390
CR-S048VDC1R	1SVR405501R4010	389
CR-S048VDC1RG	1SVR405501R4020	389
CR-S060VDC1R	1SVR405501R5010	389
CR-S060VDC1RG	1SVR405501R5020	389
CR-S110/125VADC1SS	1SVR405521R6100	390
CR-S110/125VADC1SZ	1SVR405521R6200	390
CR-S110VADC1CRGS	1SVR405541R6120	389
CR-S110VADC1CRGZ	1SVR405541R6220	389
CR-S110VADC1CRS	1SVR405541R6110	389
CR-S110VADC1CRZ	1SVR405541R6210	389
CR-S220/240VADC1SS	1SVR405521R7100	390
CR-S220/240VADC1SZ	1SVR405521R7200	390
CR-S230VADC1CRGS	1SVR405541R7120	389
CR-S230VADC1CRGZ	1SVR405541R7220	389
CR-S230VADC1CRS	1SVR405541R7110	389
CR-S230VADC1CRZ	1SVR405541R7210	389
CR-SJB20-BLACK	1SVR405598R0900	390
CR-SJB20-BLUE	1SVR405598R0700	390
CR-SJB20-RED	1SVR405598R0800	390
CR-SSEP	1SVR405599R0000	390
CR-U 21	1SVR405661R0000	408
CR-U 41	1SVR405662R0000	408
CR-U 41B	1SVR405662R4000	408

Index
Product type

Type	Order code	Page
CR-U 41BV	1SVR405662R4100	408
CR-U 41C	1SVR405662R9000	408
CR-U 41CV	1SVR405662R9100	408
CR-U 41V	1SVR405662R1000	408
CR-U 51B	1SVR405663R0000	408
CR-U 51C	1SVR405663R1000	408
CR-U 51D	1SVR405663R4000	408
CR-U 61	1SVR405664R0000	408
CR-U 61C	1SVR405665R0000	409
CR-U 61CV	1SVR405665R1000	409
CR-U 61D	1SVR405665R4000	409
CR-U 61DV	1SVR405665R4100	409
CR-U 61E	1SVR405664R4000	408
CR-U 61EV	1SVR405664R4100	408
CR-U 61V	1SVR405664R1000	408
CR-U 71	1SVR405666R0000	409
CR-U 71A	1SVR405666R1000	409
CR-U 81	1SVR405666R2000	409
CR-U 91	1SVR405664R0100	408
CR-U 91C	1SVR405665R0100	409
CR-U 91CV	1SVR405665R1100	409
CR-U 91V	1SVR405664R1100	408
CR-U T	1SVR405667R0000	409
CR-U012AC2L	1SVR405621R0300	406
CR-U012AC3L	1SVR405622R0300	407
CR-U012DC2	1SVR405621R4000	406
CR-U012DC2L	1SVR405621R4100	406
CR-U012DC2LD	1SVR405621R4400	407
CR-U012DC3	1SVR405622R4000	406
CR-U012DC3L	1SVR405622R4100	407
CR-U012DC3LD	1SVR405622R4400	407
CR-U024AC2	1SVR405621R0000	406
CR-U024AC2L	1SVR405621R0100	406
CR-U024AC3	1SVR405622R0000	406
CR-U024AC3L	1SVR405622R0100	407
CR-U024DC2	1SVR405621R1000	406
CR-U024DC2L	1SVR405621R1100	406
CR-U024DC2LD	1SVR405621R1400	407
CR-U024DC3	1SVR405622R1000	406
CR-U024DC3L	1SVR405622R1100	407
CR-U024DC3LD	1SVR405623R1100	407
CR-U048AC2	1SVR405621R5000	406
CR-U048AC2L	1SVR405621R5100	406
CR-U048AC3	1SVR405622R5000	406
CR-U048AC3L	1SVR405622R5100	407
CR-U048DC2	1SVR405621R6000	406
CR-U048DC2L	1SVR405621R6100	406
CR-U048DC2LD	1SVR405621R6400	407
CR-U048DC3	1SVR405622R6000	406
CR-U048DC3L	1SVR405622R6100	407
CR-U048DC3LD	1SVR405622R6400	407
CR-U060AC3	1SVR405622R5200	406
CR-U110AC2	1SVR405621R7000	406
CR-U110AC2L	1SVR405621R7100	406
CR-U110AC3	1SVR405622R7000	406
CR-U110AC3L	1SVR405622R7100	407
CR-U110DC2	1SVR405621R8000	406
CR-U110DC2L	1SVR405621R8100	406
CR-U110DC2LD	1SVR405621R8400	407
CR-U110DC3	1SVR405622R8000	406
CR-U110DC3L	1SVR405622R8100	407
CR-U110DC3LD	1SVR405622R8400	407
CR-U120AC2	1SVR405621R2000	406
CR-U120AC2L	1SVR405621R2100	406
CR-U120AC3	1SVR405622R2000	406
CR-U120AC3L	1SVR405622R2100	407
CR-U125DC3	1SVR405622R8200	406
CR-U220DC2	1SVR405621R9000	406
CR-U220DC2L	1SVR405621R9100	406
CR-U220DC3	1SVR405622R9000	406
CR-U220DC3L	1SVR405622R9100	407
CR-U230AC2	1SVR405621R3000	406
CR-U230AC2L	1SVR405621R3100	406
CR-U230AC3	1SVR405622R3000	406
CR-U230AC3L	1SVR405622R3100	407
CR-U2S	1SVR405670R0000	407
CR-U2SM	1SVR405670R1100	407
CR-U3E	1SVR405660R0100	407
CR-U3S	1SVR405660R0000	407
CR-U3SM	1SVR405660R1100	407
CR-UH	1SVR405669R0000	407
CT- MXS.22S	1SVR730030R3300	39
CT-AHC.12	1SVR508110R0000	25
CT-AHC.22	1SVR508110R0100	25
CT-AHD.12	1SVR500110R0000	57
CT-AHD.22	1SVR500110R0100	57
CT-AHS.22P	1SVR740110R3300	40
CT-AHS.22S	1SVR730110R3300	40
CT-APS.12P	1SVR740180R3100	40
CT-APS.12S	1SVR730180R3100	40
CT-APS.21P	1SVR740180R0300	40
CT-APS.21S	1SVR730180R0300	40
CT-APS.22P	1SVR740180R3300	40
CT-APS.22S	1SVR730180R3300	40
CT-ARC.12	1SVR508120R0000	25
CT-ARS.11P	1SVR740120R3100	40
CT-ARS.11S	1SVR730120R3100	40
CT-ARS.21P	1SVR740120R3300	40
CT-ARS.21S	1SVR730120R3300	40
CT-EBC.12	1SVR508150R0000	25
CT-EBD.12	1SVR500150R0000	57
CT-ERC.12	1SVR508100R0000	25

Index
Product type

Type	Order code	Page
CT-ERC.22	1SVR508100R0100	25
CT-ERD.12	1SVR500100R0000	57
CT-ERD.22	1SVR500100R0100	57
CT-ERS.12P	1SVR740100R3100	40
CT-ERS.12S	1SVR730100R3100	40
CT-ERS.21P	1SVR740100R0300	40
CT-ERS.21S	1SVR730100R0300	40
CT-ERS.22P	1SVR740100R3300	40
CT-ERS.22S	1SVR730100R3300	40
CT-MBS.22P	1SVR740010R3200	39
CT-MBS.22S	1SVR730010R3200	39
CT-MFC.12	1SVR508020R0000	25
CT-MFC.21	1SVR508020R1100	25
CT-MFD.12	1SVR500020R0000	57
CT-MFD.21	1SVR500020R1100	57
CT-MFS.21P	1SVR740010R0200	39
CT-MFS.21S	1SVR730010R0200	39
CT-MKC.31	1SVR508010R1300	25
CT-MVS.12P	1SVR740020R3100	39
CT-MVS.12S	1SVR730020R3100	39
CT-MVS.21P	1SVR740020R0200	39
CT-MVS.21S	1SVR730020R0200	39
CT-MVS.22P	1SVR740020R3300	39
CT-MVS.22S	1SVR730020R3300	39
CT-MVS.23P	1SVR740021R2300	39
CT-MVS.23S	1SVR730021R2300	39
CT-MXS.22P	1SVR740030R3300	39
CT-SAC.22	1SVR508210R0100	25
CT-SAD.22	1SVR500210R0100	57
CT-SDC.22	1SVR508211R0100	25
CT-SDD.22	1SVR500211R0100	57
CT-SDS.22P	1SVR740210R3300	40
CT-SDS.22S	1SVR730210R3300	40
CT-SDS.23P	1SVR740211R2300	40
CT-SDS.23S	1SVR730211R2300	40
CT-TGC.12	1SVR508160R0000	25
CT-TGC.22	1SVR508160R0100	25
CT-TGD.12	1SVR500160R0000	57
CT-TGD.22	1SVR500160R0100	57
CT-VWC.12	1SVR508130R0000	25
CT-VWD.12	1SVR500130R0000	57
CT-WBS.22P	1SVR740040R3300	39
CT-WBS.22S	1SVR730040R3300	39
EPD24-TB-101-0.5A	2CDE601101R2905	352
EPD24-TB-101-10A	2CDE601101R2010	352
EPD24-TB-101-12A	2CDE601101R2012	352
EPD24-TB-101-1A	2CDE601101R2001	352
EPD24-TB-101-2A	2CDE601101R2002	352
EPD24-TB-101-3A	2CDE601101R2003	352
EPD24-TB-101-4A	2CDE601101R2004	352
EPD24-TB-101-6A	2CDE601101R2006	352

Type	Order code	Page
EPD24-TB-101-8A	2CDE601101R2008	352
EPD-BB500	2CDE605100R0500	352
EPD-SB21	2CDE605200R0021	352
KA1-8029	1SFA616920R8029	41
KA1-8030	1SFA616920R8030	41
MA16-1060	1SFA611940R1060	41
MAR.01	1SVR366017R0100	41
MAR.01	1SVR366017R0100	242
MAR.02	1SVR430043R0000	242
MAR.12	1SVR730006R0000	41
MAR.12	1SVR730006R0000	242
MT-150B	1SFA611410R1506	41
MT-250B	1SFA611410R2506	41
MT-350B	1SFA611410R3506	41
OBIC0100-115-230	1SNA645022R2700	451
OBIC0100-24VDC	1SNA645021R2600	451
OBIC0100-48-60VUC	1SNA645049R1200	451
OBIC0100-5-12VDC	1SNA645047R0000	451
OBOA1000-115VUC	1SNA645062R0700	451
OBOA1000-230VUC	1SNA645028R0500	451
OBOA1000-24VDC	1SNA645027R2400	451
OBOA2000-24VDC	1SNA645029R0600	452
OBOC2000-115VUC	1SNA645054R0700	451
OBOC2000-230VUC	1SNA645026R2300	451
OBOC2000-24VDC	1SNA645051R0400	451
OBOC2000-24VUC	1SNA645025R2200	451
OBOC2000-48-60VUC	1SNA645053R0600	451
OBOC2000-5-12VDC	1SNA645050R1700	451
OBOC5000-115VUC	1SNA645058R1300	451
OBOC5000-24VDC	1SNA645024R2100	451
OBRIC0100-115-230	1SNA645522R2100	451
OBRIC0100-24VDC	1SNA645521R2000	451
OBRIC0100-48-60VUC	1SNA645549R1400	451
OBRIC0100-5-12VDC	1SNA645547R0200	451
OBROA1000-24VDC	1SNA645527R2600	451
OBROA2000-24VDC	1SNA645529R0000	452
OBROC2000-230VUC	1SNA645526R2500	451
OBROC2000-24VDC	1SNA645551R0600	451
OBROC2000-24VUC	1SNA645525R2400	451
OBROC2000-48-60VUC	1SNA645553R0000	451
OBROC2000-5-12VDC	1SNA645550R1100	451
OBROC5000-230VUC	1SNA645559R1600	451
OBROC5000-24VDC	1SNA645524R2300	451
RB101R-24VUC	1SNA645019R0400	442
RB111-115VUC	1SNA645016R2100	442
RB111-230VUC	1SNA645017R2200	442
RB111-24VUC	1SNA645014R2700	442
RB111R-24VUC	1SNA645018R0300	442
RB121-115VUC	1SNA645003R0500	442
RB121-12VDC	1SNA645073R0000	442
RB121-230VUC	1SNA645004R0400	442

Index
Product type

Type	Order code	Page
RB121-24VDC	1SNA645071R0000	442
RB121-24VUC	1SNA645001R0300	442
RB121-48-60VUC	1SNA645002R0400	442
RB121-60-230VUC	1SNA645020R0100	443
RB121G-115VUC	1SNA645007R0100	443
RB121G-12VDC	1SNA645075R0000	443
RB121G-230VUC	1SNA645008R1200	443
RB121G-24VDC	1SNA645072R0000	443
RB121G-24VUC	1SNA645005R0700	443
RB121G-48-60VUC	1SNA645006R0000	443
RB121P-12VDC	1SNA645035R2400	442
RB121P-5VDC	1SNA645034R2300	442
RB121PG-5VDC	1SNA645036R2500	443
RB121R-115VUC	1SNA645046R0700	443
RB121R-230VUC	1SNA645011R2400	443
RB122G-115VUC	1SNA645041R0200	443
RB122G-230VUC	1SNA645013R2600	443
RB122G-24VUC	1SNA645012R2500	443
RB122G-48-60VUC	1SNA645040R1500	443
RB-JB10	1SVR406570R0000	452
RB-JB20	1SVR406580R0000	452
RBR101R-24VUC	1SNA645519R0600	442
RBR111-24VUC	1SNA645514R2100	442
RBR111R-24VUC	1SNA645518R0500	442
RBR121-115VUC	1SNA645503R0700	442
RBR121-230VUC	1SNA645504R0000	442
RBR121-24VDC	1SNA645571R0000	442
RBR121-24VUC	1SNA645501R0500	442
RBR121-48-60VUC	1SNA645502R0600	442
RBR121-60-230VUC	1SNA645520R0300	443
RBR121G-115VUC	1SNA645507R0300	443
RBR121G-230VUC	1SNA645508R1400	443
RBR121G-24VDC	1SNA645572R0000	443
RBR121G-24VUC	1SNA645505R0100	443
RBR121G-48-60VUC	1SNA645506R0200	443
RBR121P-12VDC	1SNA645535R2600	442
RBR121P-5VDC	1SNA645534R2500	442
RBR121R-230VUC	1SNA645511R2600	443
RBR122G-115VUC	1SNA645541R0400	443
RBR122G-230VUC	1SNA645513R2000	443
RBR122G-24VUC	1SNA645512R2700	443
RBR122G-48-60VUC	1SNA645540R1700	443
SC612	1SNA290474R0200	443
SK 615 562-87	GJD6155620R0087	41
SK 615 562-88	GJD6155620R0088	41

Index
Order code

Type	Order code	Page
MT-150B	1SFA611410R1506	41
MT-250B	1SFA611410R2506	41
MT-350B	1SFA611410R3506	41
MA16-1060	1SFA611940R1060	41
KA1-8029	1SFA616920R8029	41
KA1-8030	1SFA616920R8030	41
SC612	1SNA290474R0200	443
RB121-24VUC	1SNA645001R0300	442
RB121-48-60VUC	1SNA645002R0400	442
RB121-115VUC	1SNA645003R0500	442
RB121-230VUC	1SNA645004R0400	442
RB121G-24VUC	1SNA645005R0700	443
RB121G-48-60VUC	1SNA645006R0000	443
RB121G-115VUC	1SNA645007R0100	443
RB121G-230VUC	1SNA645008R1200	443
RB121R-230VUC	1SNA645011R2400	443
RB122G-24VUC	1SNA645012R2500	443
RB122G-230VUC	1SNA645013R2600	443
RB111-24VUC	1SNA645014R2700	442
RB111-115VUC	1SNA645016R2100	442
RB111-230VUC	1SNA645017R2200	442
RB111R-24VUC	1SNA645018R0300	442
RB101R-24VUC	1SNA645019R0400	442
RB121-60-230VUC	1SNA645020R0100	443
OBIC0100-24VDC	1SNA645021R2600	451
OBIC0100-115-230	1SNA645022R2700	451
OBOC5000-24VDC	1SNA645024R2100	451
OBOC2000-24VUC	1SNA645025R2200	451
OBOC2000-230VUC	1SNA645026R2300	451
OBOA1000-24VDC	1SNA645027R2400	451
OBOA1000-230VUC	1SNA645028R0500	451
OBOA2000-24VDC	1SNA645029R0600	452
RB121P-5VDC	1SNA645034R2300	442
RB121P-12VDC	1SNA645035R2400	442
RB121PG-5VDC	1SNA645036R2500	443
RB122G-48-60VUC	1SNA645040R1500	443
RB122G-115VUC	1SNA645041R0200	443
RB121R-115VUC	1SNA645046R0700	443
OBIC0100-5-12VDC	1SNA645047R0000	451
OBIC0100-48-60VUC	1SNA645049R1200	451
OBOC2000-5-12VDC	1SNA645050R1700	451
OBOC2000-24VDC	1SNA645051R0400	451
OBOC2000-48-60VUC	1SNA645053R0600	451
OBOC2000-115VUC	1SNA645054R0700	451
OBOC5000-115VUC	1SNA645058R1300	451
OBOA1000-115VUC	1SNA645062R0700	451
RB121-24VDC	1SNA645071R0000	442
RB121G-24VDC	1SNA645072R0000	443
RB121-12VDC	1SNA645073R0000	442
RB121G-12VDC	1SNA645075R0000	443
RBR121-24VUC	1SNA645501R0500	442
RBR121-48-60VUC	1SNA645502R0600	442
RBR121-115VUC	1SNA645503R0700	442
RBR121-230VUC	1SNA645504R0000	442
RBR121G-24VUC	1SNA645505R0100	443
RBR121G-48-60VUC	1SNA645506R0200	443
RBR121G-115VUC	1SNA645507R0300	443
RBR121G-230VUC	1SNA645508R1400	443
RBR121R-230VUC	1SNA645511R2600	443
RBR122G-24VUC	1SNA645512R2700	443
RBR122G-230VUC	1SNA645513R2000	443
RBR111-24VUC	1SNA645514R2100	442
RBR111R-24VUC	1SNA645518R0500	442
RBR101R-24VUC	1SNA645519R0600	442
RBR121-60-230VUC	1SNA645520R0300	443
OBRIC0100-24VDC	1SNA645521R2000	451
OBRIC0100-115-230	1SNA645522R2100	451
OBROC5000-24VDC	1SNA645524R2300	451
OBROC2000-24VUC	1SNA645525R2400	451
OBROC2000-230VUC	1SNA645526R2500	451
OBROA1000-24VDC	1SNA645527R2600	451
OBROA2000-24VDC	1SNA645529R0000	452
RBR121P-5VDC	1SNA645534R2500	442
RBR121P-12VDC	1SNA645535R2600	442
RBR122G-48-60VUC	1SNA645540R1700	443
RBR122G-115VUC	1SNA645541R0400	443
OBRIC0100-5-12VDC	1SNA645547R0200	451
OBRIC0100-48-60VUC	1SNA645549R1400	451
OBROC2000-5-12VDC	1SNA645550R1100	451
OBROC2000-24VDC	1SNA645551R0600	451
OBROC2000-48-60VUC	1SNA645553R0000	451
OBROC5000-230VUC	1SNA645559R1600	451
RBR121-24VDC	1SNA645571R0000	442
RBR121G-24VDC	1SNA645572R0000	443
CP-C.1-A-RU	1SVR360060R1001	342
CP-C.1-A-RU-C	1SVR360060R2001	342
CP-C.1 24/5.0	1SVR360563R1001	294
CP-C.1 24/5.0-C	1SVR360563R2001	294
CP-C.1 24/10.0	1SVR360663R1001	294
CP-C.1 24/10.0-C	1SVR360663R2001	294
CP-C.1 24/20.0	1SVR360763R1001	294
CP-C.1 24/20.0-C	1SVR360763R2001	294
CP-C.1-A-RU-L	1SVR361060R1001	342
CP-C.1 24/5.0-L	1SVR361563R1001	294
CP-C.1 24/10.0-L	1SVR361663R1001	294
CP-C.1 24/20.0-L	1SVR361763R1001	294
MAR.01	1SVR366017R0100	41
MAR.01	1SVR366017R0100	242
CM-HE	1SVR402902R0000	242
CM-HC	1SVR402902R1000	242
CM-HCT	1SVR402902R2000	242
CR-S005VDC1R	1SVR405501R1010	389

Index
Order code

Type	Order code	Page
CR-S005VDC1RG	1SVR405501R1020	389
CR-S012VDC1R	1SVR405501R2010	389
CR-S012VDC1RG	1SVR405501R2020	389
CR-S024VDC1R	1SVR405501R3010	389
CR-S024VDC1RG	1SVR405501R3020	389
CR-S048VDC1R	1SVR405501R4010	389
CR-S048VDC1RG	1SVR405501R4020	389
CR-S060VDC1R	1SVR405501R5010	389
CR-S060VDC1RG	1SVR405501R5020	389
CR-S024VDC1TRA	1SVR405510R3050	389
CR-S024VDC1MOS	1SVR405510R3060	389
CR-S024VDC1TRI	1SVR405510R3070	389
CR-S006/024VDC1SS	1SVR405521R1100	390
CR-S006/024VDC1SZ	1SVR405521R1200	390
CR-S012/024VADC1SS	1SVR405521R3100	390
CR-S012/024VADC1SZ	1SVR405521R3200	390
CR-S048/060VADC1SS	1SVR405521R5100	390
CR-S048/060VADC1SZ	1SVR405521R5200	390
CR-S110/125VADC1SS	1SVR405521R6100	390
CR-S110/125VADC1SZ	1SVR405521R6200	390
CR-S220/240VADC1SS	1SVR405521R7100	390
CR-S220/240VADC1SZ	1SVR405521R7200	390
CR-S024VADC1CRS	1SVR405541R3110	389
CR-S024VADC1CRGS	1SVR405541R3120	389
CR-S024VADC1CRZ	1SVR405541R3210	389
CR-S024VADC1CRGZ	1SVR405541R3220	389
CR-S110VADC1CRS	1SVR405541R6110	389
CR-S110VADC1CRGS	1SVR405541R6120	389
CR-S110VADC1CRZ	1SVR405541R6210	389
CR-S110VADC1CRGZ	1SVR405541R6220	389
CR-S230VADC1CRS	1SVR405541R7110	389
CR-S230VADC1CRGS	1SVR405541R7120	389
CR-S230VADC1CRZ	1SVR405541R7210	389
CR-S230VADC1CRGZ	1SVR405541R7220	389
CR-SJB20-BLUE	1SVR405598R0700	390
CR-SJB20-RED	1SVR405598R0800	390
CR-SJB20-BLACK	1SVR405598R0900	390
CR-SSEP	1SVR405599R0000	390
CR-P024AC1	1SVR405600R0000	393
CR-P024AC1SS62CV	1SVR405600R0010	395
CR-P024DC1	1SVR405600R1000	393
CR-P024DC1SS42V	1SVR405600R1010	395
CR-P024DC1LC42V	1SVR405600R1011	395
CR-P024DC1LC62C	1SVR405600R1013	395
CR-P120AC1	1SVR405600R2000	393
CR-P120AC1SS92CV	1SVR405600R2010	395
CR-P230AC1	1SVR405600R3000	393
CR-P230AC1LC92CV	1SVR405600R3010	395
CR-P230AC1LS	1SVR405600R3011	395
CR-P230AC1SS92CV	1SVR405600R3110	395
CR-P012DC1	1SVR405600R4000	393
CR-P012DC1SS42V	1SVR405600R4010	395
CR-P048AC1	1SVR405600R5000	393
CR-P048DC1	1SVR405600R6000	393
CR-P110AC1	1SVR405600R7000	393
CR-P110DC1	1SVR405600R8000	393
CR-P110DC1SS42CV	1SVR405600R8010	395
CR-P024AC2	1SVR405601R0000	393
CR-P024AC2SS62CV	1SVR405601R0010	396
CR-P012AC2	1SVR405601R0200	393
CR-P024DC2	1SVR405601R1000	393
CR-P024DC2SS42V	1SVR405601R1010	396
CR-P024DC2LS42V	1SVR405601R1011	396
CR-P024DC2LC42	1SVR405601R1012	396
CR-P024DC2LS42	1SVR405601R1013	396
CR-P120AC2	1SVR405601R2000	393
CR-P120AC2SS92CV	1SVR405601R2010	396
CR-P230AC2	1SVR405601R3000	393
CR-P230AC2LS92CV	1SVR405601R3011	396
CR-P230AC2LC92	1SVR405601R3012	396
CR-P230AC2SS92CV	1SVR405601R3110	396
CR-P012DC2	1SVR405601R4000	393
CR-P012DC2SS42V	1SVR405601R4010	396
CR-P048AC2	1SVR405601R5000	393
CR-P048DC2	1SVR405601R6000	393
CR-P110AC2	1SVR405601R7000	393
CR-P110DC2	1SVR405601R8000	393
CR-P110DC2SS42CV	1SVR405601R8010	396
CR-P024AC2G	1SVR405606R0000	393
CR-P024DC2G	1SVR405606R1000	393
CR-P024DC2GLC42V	1SVR405606R1010	396
CR-P024DC2GLC62CV	1SVR405606R1011	396
CR-P024DC2GLC62C	1SVR405606R1013	396
CR-P230AC2G	1SVR405606R3000	393
CR-P230AC2GLC92CV	1SVR405606R3010	396
CR-P230AC2GLC92C	1SVR405606R3012	396
CR-P230AC2GLC92	1SVR405606R3013	396
CR-P110AC2G	1SVR405606R7000	393
CR-P024MOS1	1SVR405610R4060	393
CR-P024TRI1	1SVR405610R4070	393
CR-M024AC2	1SVR405611R0000	397
CR-M024AC2L	1SVR405611R0100	398
CR-M012AC2L	1SVR405611R0300	398
CR-M024DC2	1SVR405611R1000	397
CR-M024DC2L	1SVR405611R1100	398
CR-M024DC2LD	1SVR405611R1400	399
CR-M120AC2	1SVR405611R2000	397
CR-M120AC2L	1SVR405611R2100	398
CR-M230AC2	1SVR405611R3000	397
CR-M230AC2L	1SVR405611R3100	398
CR-M012DC2	1SVR405611R4000	397
CR-M012DC2L	1SVR405611R4100	398

Index
Order code

Type	Order code	Page
CR-M060DC2	1SVR405611R4200	397
CR-M060DC2L	1SVR405611R4300	398
CR-M012DC2LD	1SVR405611R4400	399
CR-M048AC2	1SVR405611R5000	397
CR-M048AC2L	1SVR405611R5100	398
CR-M048DC2	1SVR405611R6000	397
CR-M048DC2L	1SVR405611R6100	398
CR-M048DC2LD	1SVR405611R6400	399
CR-M110AC2	1SVR405611R7000	397
CR-M110AC2L	1SVR405611R7100	398
CR-M110DC2	1SVR405611R8000	397
CR-M110DC2L	1SVR405611R8100	398
CR-M125DC2	1SVR405611R8200	397
CR-M125DC2L	1SVR405611R8300	398
CR-M110DC2LD	1SVR405611R8400	399
CR-M125DC2LD	1SVR405611R8500	399
CR-M220DC2	1SVR405611R9000	397
CR-M220DC2L	1SVR405611R9100	398
CR-M220DC2LD	1SVR405611R9400	399
CR-M024AC3	1SVR405612R0000	397
CR-M024AC3L	1SVR405612R0100	398
CR-M012AC3L	1SVR405612R0300	398
CR-M024DC3	1SVR405612R1000	397
CR-M024DC3L	1SVR405612R1100	398
CR-M024DC3LD	1SVR405612R1400	399
CR-M120AC3	1SVR405612R2000	397
CR-M120AC3L	1SVR405612R2100	398
CR-M230AC3	1SVR405612R3000	397
CR-M230AC3L	1SVR405612R3100	398
CR-M012DC3	1SVR405612R4000	397
CR-M012DC3L	1SVR405612R4100	398
CR-M060DC3	1SVR405612R4200	397
CR-M060DC3L	1SVR405612R4300	398
CR-M012DC3LD	1SVR405612R4400	399
CR-M048AC3	1SVR405612R5000	397
CR-M048AC3L	1SVR405612R5100	398
CR-M060AC3	1SVR405612R5200	397
CR-M048DC3	1SVR405612R6000	397
CR-M048DC3L	1SVR405612R6100	398
CR-M048DC3LD	1SVR405612R6400	399
CR-M110AC3	1SVR405612R7000	397
CR-M110AC3L	1SVR405612R7100	398
CR-M110DC3	1SVR405612R8000	397
CR-M110DC3L	1SVR405612R8100	398
CR-M125DC3	1SVR405612R8200	397
CR-M125DC3L	1SVR405612R8300	398
CR-M110DC3LD	1SVR405612R8400	399
CR-M125DC3LD	1SVR405612R8500	399
CR-M220DC3	1SVR405612R9000	397
CR-M220DC3L	1SVR405612R9100	398
CR-M220DC3LD	1SVR405612R9400	399

Type	Order code	Page
CR-M024AC4	1SVR405613R0000	397
CR-M024AC4LS62CV	1SVR405613R0010	401
CR-M024AC4L	1SVR405613R0100	398
CR-M012AC4L	1SVR405613R0300	398
CR-M024DC4	1SVR405613R1000	397
CR-M024DC4SS42V	1SVR405613R1010	401
CR-M024DC4LS42V	1SVR405613R1011	401
CR-M024DC4LC42	1SVR405613R1012	401
CR-M024DC4L	1SVR405613R1100	398
CR-M120AC4	1SVR405613R2000	397
CR-M120AC4L	1SVR405613R2100	398
CR-M230AC4	1SVR405613R3000	397
CR-M230AC4LS92CV	1SVR405613R3011	402
CR-M230AC4LC92	1SVR405613R3012	402
CR-M230AC4L	1SVR405613R3100	398
CR-M230AC4SS92CV	1SVR405613R3110	402
CR-M012DC4	1SVR405613R4000	397
CR-M012DC4L	1SVR405613R4100	398
CR-M060DC4	1SVR405613R4200	397
CR-M060DC4L	1SVR405613R4300	398
CR-M012DC4LD	1SVR405613R4400	399
CR-M048AC4	1SVR405613R5000	397
CR-M048AC4L	1SVR405613R5100	398
CR-M048DC4	1SVR405613R6000	397
CR-M048DC4L	1SVR405613R6100	398
CR-M048DC4LD	1SVR405613R6400	399
CR-M110AC4	1SVR405613R7000	397
CR-M110AC4L	1SVR405613R7100	398
CR-M110DC4	1SVR405613R8000	397
CR-M110DC4L	1SVR405613R8100	398
CR-M125DC4	1SVR405613R8200	397
CR-M125DC4L	1SVR405613R8300	398
CR-M110DC4LD	1SVR405613R8400	399
CR-M125DC4LD	1SVR405613R8500	399
CR-M220DC4	1SVR405613R9000	397
CR-M220DC4L	1SVR405613R9100	398
CR-M220DC4LD	1SVR405613R9400	399
CR-M024DC4LD	1SVR405614R1100	399
CR-M024AC4G	1SVR405618R0000	399
CR-M024AC4LG	1SVR405618R0100	400
CR-M024DC4G	1SVR405618R1000	399
CR-M024DC4GLC62CV	1SVR405618R1010	401
CR-M024DC4GSS42V	1SVR405618R1011	401
CR-M024DC4LG	1SVR405618R1100	400
CR-M024DC4LGLC22	1SVR405618R1110	401
CR-M024DC4LDG	1SVR405618R1400	400
CR-M024DC4LDGSS	1SVR405618R1410	401
CR-M120AC4LG	1SVR405618R2100	400
CR-M230AC4G	1SVR405618R3000	399
CR-M230AC4LG	1SVR405618R3100	400
CR-M230AC4LGLC	1SVR405618R3110	402

Index
Order code

Type	Order code	Page
CR-M230AC4LGSS	1SVR405618R3111	402
CR-M230AC4GSS92CV	1SVR405618R3112	402
CR-M012DC4LG	1SVR405618R4100	400
CR-M060DC4LG	1SVR405618R4300	400
CR-M012DC4LDG	1SVR405618R4400	400
CR-M012DC4LDGSS	1SVR405618R4410	401
CR-M048AC4LG	1SVR405618R5100	400
CR-M048DC4LG	1SVR405618R6100	400
CR-M110AC4G	1SVR405618R7000	399
CR-M110AC4LG	1SVR405618R7100	400
CR-M110DC4LG	1SVR405618R8100	400
CR-M125DC4LG	1SVR405618R8300	400
CR-M220DC4LG	1SVR405618R9100	400
CR-U024AC2	1SVR405621R0000	406
CR-U024AC2L	1SVR405621R0100	406
CR-U012AC2L	1SVR405621R0300	406
CR-U024DC2	1SVR405621R1000	406
CR-U024DC2L	1SVR405621R1100	406
CR-U024DC2LD	1SVR405621R1400	407
CR-U120AC2	1SVR405621R2000	406
CR-U120AC2L	1SVR405621R2100	406
CR-U230AC2	1SVR405621R3000	406
CR-U230AC2L	1SVR405621R3100	406
CR-U012DC2	1SVR405621R4000	406
CR-U012DC2L	1SVR405621R4100	406
CR-U012DC2LD	1SVR405621R4400	407
CR-U048AC2	1SVR405621R5000	406
CR-U048AC2L	1SVR405621R5100	406
CR-U048DC2	1SVR405621R6000	406
CR-U048DC2L	1SVR405621R6100	406
CR-U048DC2LD	1SVR405621R6400	407
CR-U110AC2	1SVR405621R7000	406
CR-U110AC2L	1SVR405621R7100	406
CR-U110DC2	1SVR405621R8000	406
CR-U110DC2L	1SVR405621R8100	406
CR-U110DC2LD	1SVR405621R8400	407
CR-U220DC2	1SVR405621R9000	406
CR-U220DC2L	1SVR405621R9100	406
CR-U024AC3	1SVR405622R0000	406
CR-U024AC3L	1SVR405622R0100	407
CR-U012AC3L	1SVR405622R0300	407
CR-U024DC3	1SVR405622R1000	406
CR-U024DC3L	1SVR405622R1100	407
CR-U120AC3	1SVR405622R2000	406
CR-U120AC3L	1SVR405622R2100	407
CR-U230AC3	1SVR405622R3000	406
CR-U230AC3L	1SVR405622R3100	407
CR-U012DC3	1SVR405622R4000	406
CR-U012DC3L	1SVR405622R4100	407
CR-U012DC3LD	1SVR405622R4400	407
CR-U048AC3	1SVR405622R5000	406
CR-U048AC3L	1SVR405622R5100	407
CR-U060AC3	1SVR405622R5200	406
CR-U048DC3	1SVR405622R6000	406
CR-U048DC3L	1SVR405622R6100	407
CR-U048DC3LD	1SVR405622R6400	407
CR-U110AC3	1SVR405622R7000	406
CR-U110AC3L	1SVR405622R7100	407
CR-U110DC3	1SVR405622R8000	406
CR-U110DC3L	1SVR405622R8100	407
CR-U125DC3	1SVR405622R8200	406
CR-U110DC3LD	1SVR405622R8400	407
CR-U220DC3	1SVR405622R9000	406
CR-U220DC3L	1SVR405622R9100	407
CR-U024DC3LD	1SVR405623R1100	407
CR-PLS	1SVR405650R0000	394
CR-PLSX	1SVR405650R0100	394
CR-PLC	1SVR405650R0200	394
CR-PSS	1SVR405650R1000	394
CR-P/M 22	1SVR405651R0000	404
CR-M2SS	1SVR405651R1000	403
CR-M2LS	1SVR405651R1100	403
CR-M2LC	1SVR405651R1200	403
CR-M2SF	1SVR405651R1300	403
CR-M3SS	1SVR405651R2000	403
CR-M3LS	1SVR405651R2100	403
CR-M4SS	1SVR405651R3000	403
CR-M4LS	1SVR405651R3100	403
CR-M4LC	1SVR405651R3200	403
CR-M4SF	1SVR405651R3300	403
CR-P/M 42	1SVR405652R0000	404
CR-P/M 42 V	1SVR405652R1000	404
CR-P/M 42 B	1SVR405652R4000	404
CR-P/M 42 BV	1SVR405652R4100	404
CR-P/M 42 C	1SVR405652R9000	404
CR-P/M 42 CV	1SVR405652R9100	404
CR-P/M 52B	1SVR405653R0000	404
CR-P/M 52C	1SVR405653R1000	404
CR-P/M 52D	1SVR405653R4000	404
CR-P/M 62	1SVR405654R0000	404
CR-P/M 92	1SVR405654R0100	404
CR-P/M 62 V	1SVR405654R1000	404
CR-P/M 92 V	1SVR405654R1100	404
CR-P/M 62 E	1SVR405654R4000	404
CR-P/M 62 EV	1SVR405654R4100	404
CR-P/M 62 C	1SVR405655R0000	405
CR-P/M 92 C	1SVR405655R0100	405
CR-P/M 62 CV	1SVR405655R1000	405
CR-P/M 92 CV	1SVR405655R1100	405
CR-P/M 62 D	1SVR405655R4000	405
CR-P/M 62 DV	1SVR405655R4100	405
CR-P/M 72	1SVR405656R0000	405

Index
Order code

Type	Order code	Page
CR-P/M 72 A	1SVR405656R1000	405
CR-P/M 82	1SVR405656R2000	405
CR-PM	1SVR405658R0000	394
CR-MM	1SVR405658R1000	403
CR-MP	1SVR405658R2000	403
CR-PJ	1SVR405658R5000	394
CR-MJ	1SVR405658R6000	403
CR-PH	1SVR405659R0000	394
CR-PH1	1SVR405659R0100	394
CR-MH	1SVR405659R1000	403
CR-MH1	1SVR405659R1100	403
CR-U3S	1SVR405660R0000	407
CR-U3E	1SVR405660R0100	407
CR-U3SM	1SVR405660R1100	407
CR-U 21	1SVR405661R0000	408
CR-U 41	1SVR405662R0000	408
CR-U 41V	1SVR405662R1000	408
CR-U 41B	1SVR405662R4000	408
CR-U 41BV	1SVR405662R4100	408
CR-U 41C	1SVR405662R9000	408
CR-U 41CV	1SVR405662R9100	408
CR-U 51B	1SVR405663R0000	408
CR-U 51C	1SVR405663R1000	408
CR-U 51D	1SVR405663R4000	408
CR-U 61	1SVR405664R0000	408
CR-U 91	1SVR405664R0100	408
CR-U 61V	1SVR405664R1000	408
CR-U 91V	1SVR405664R1100	408
CR-U 61E	1SVR405664R4000	408
CR-U 61EV	1SVR405664R4100	408
CR-U 61C	1SVR405665R0000	409
CR-U 91C	1SVR405665R0100	409
CR-U 61CV	1SVR405665R1000	409
CR-U 91CV	1SVR405665R1100	409
CR-U 61D	1SVR405665R4000	409
CR-U 61DV	1SVR405665R4100	409
CR-U 71	1SVR405666R0000	409
CR-U 71A	1SVR405666R1000	409
CR-U 81	1SVR405666R2000	409
CR-U T	1SVR405667R0000	409
CR-UH	1SVR405669R0000	407
CR-U2S	1SVR405670R0000	407
CR-U2SM	1SVR405670R1100	407
RB-JB10	1SVR406570R0000	452
RB-JB20	1SVR406580R0000	452
CP-RUD	1SVR423418R9000	342
CP-E 24/0.75	1SVR427030R0000	260
CP-E 48/0.62	1SVR427030R2000	260
CP-E 24/1.25	1SVR427031R0000	260
CP-E 48/1.25	1SVR427031R2000	260
CP-E 24/2.5	1SVR427032R0000	260
CP-E 12/2.5	1SVR427032R1000	260
CP-E 5/3.0	1SVR427033R3000	260
CP-E 24/5.0	1SVR427034R0000	260
CP-E 48/5.0	1SVR427034R2000	260
CP-E 24/10.0	1SVR427035R0000	260
CP-E 12/10.0	1SVR427035R1000	260
CP-E 48/10.0	1SVR427035R2000	260
CP-E 24/20.0	1SVR427036R0000	260
CP-D 24/0.42	1SVR427041R0000	318
CP-D 12/0.83	1SVR427041R1000	318
CP-D 24/1.3	1SVR427043R0100	318
CP-D 12/2.1	1SVR427043R1200	318
CP-D 24/2.5	1SVR427044R0200	318
CP-D 24/4.2	1SVR427045R0400	318
CP-D RU	1SVR427049R0000	342
CP-T 24/5.0	1SVR427054R0000	280
CP-T 48/5.0	1SVR427054R2000	280
CP-T 24/10.0	1SVR427055R0000	280
CP-T 48/10.0	1SVR427055R2000	280
CP-T 24/20.0	1SVR427056R0000	280
CP-T 48/20.0	1SVR427056R2000	280
CP-T 24/40.0	1SVR427057R0000	280
CP-B 24/3.0	1SVR427060R0300	332
CP-B 24/10.0	1SVR427060R1000	332
CP-B 24/20.0	1SVR427060R2000	332
CP-B EXT.2	1SVR427065R0000	332
COV.01	1SVR430005R0100	242
ADP.01	1SVR430029R0100	41
ADP.01	1SVR430029R0100	242
MAR.02	1SVR430043R0000	242
COV.02	1SVR440005R0100	242
ADP.02	1SVR440029R0100	242
CM-SE-300	1SVR450056R0000	242
CM-SE-600	1SVR450056R0100	242
CM-SE-1000	1SVR450056R0200	242
CM-KH-3	1SVR450056R6000	242
CM-AH-3	1SVR450056R7000	242
CM-GM-1	1SVR450056R8000	242
CM-CT 50/1	1SVR450116R1000	243
CM-CT 75/1	1SVR450116R1100	243
CM-CT 100/1	1SVR450116R1200	243
CM-CT 150/1	1SVR450116R1300	243
CM-CT 200/1	1SVR450116R1400	243
CM-CT 50/5	1SVR450116R5000	243
CM-CT 75/5	1SVR450116R5100	243
CM-CT 100/5	1SVR450116R5200	243
CM-CT 150/5	1SVR450116R5300	243
CM-CT 200/5	1SVR450116R5400	243
CM-CT 300/1	1SVR450117R1100	243
CM-CT 400/1	1SVR450117R1200	243
CM-CT 500/1	1SVR450117R1300	243

Index
Order code

Type	Order code	Page
CM-CT 600/1	1SVR450117R1400	243
CM-CT 300/5	1SVR450117R5100	243
CM-CT 400/5	1SVR450117R5200	243
CM-CT 500/5	1SVR450117R5300	243
CM-CT 600/5	1SVR450117R5400	243
CM-CT A	1SVR450118R1000	243
CM-IWM.10	1SVR470670R1000	161
CM-IWM.11	1SVR470670R1100	161
CT-MFD.12	1SVR500020R0000	57
CT-MFD.21	1SVR500020R1100	57
CT-ERD.12	1SVR500100R0000	57
CT-ERD.22	1SVR500100R0100	57
CT-AHD.12	1SVR500110R0000	57
CT-AHD.22	1SVR500110R0100	57
CT-VWD.12	1SVR500130R0000	57
CT-EBD.12	1SVR500150R0000	57
CT-TGD.12	1SVR500160R0000	57
CT-TGD.22	1SVR500160R0100	57
CT-SAD.22	1SVR500210R0100	57
CT-SDD.22	1SVR500211R0100	57
CT-MKC.31	1SVR508010R1300	25
CT-MFC.12	1SVR508020R0000	25
CT-MFC.21	1SVR508020R1100	25
CT-ERC.12	1SVR508100R0000	25
CT-ERC.22	1SVR508100R0100	25
CT-AHC.12	1SVR508110R0000	25
CT-AHC.22	1SVR508110R0100	25
CT-ARC.12	1SVR508120R0000	25
CT-VWC.12	1SVR508130R0000	25
CT-EBC.12	1SVR508150R0000	25
CT-TGC.12	1SVR508160R0000	25
CT-TGC.22	1SVR508160R0100	25
CT-SAC.22	1SVR508210R0100	25
CT-SDC.22	1SVR508211R0100	25
CM-MSE	1SVR550800R9300	190
CM-MSE	1SVR550801R9300	190
CM-MSE	1SVR550805R9300	190
CM-PFE	1SVR550824R9100	113
CM-PFE.2	1SVR550826R9100	113
CM-ENE MAX	1SVR550850R9400	229
CM-ENE MIN	1SVR550850R9500	229
CM-ENE MAX	1SVR550851R9400	229
CM-ENE MIN	1SVR550851R9500	229
CM-ENE MAX	1SVR550855R9400	229
CM-ENE MIN	1SVR550855R9500	229
CM-PVE	1SVR550870R9400	113
CM-PVE	1SVR550871R9500	113
CM-PBE	1SVR550881R9400	113
CM-PBE	1SVR550882R9500	113
CM-UFD.M31	1SVR560730R3401	145
CM-UFD.M33	1SVR560730R3402	145
CM-UFD.M22M	1SVR560731R3700	145
CM-UFD.M31M	1SVR560731R3701	145
CM-UFD.M33M	1SVR560731R3702	145
CM-UFD.M34M	1SVR560731R3703	145
COV.11	1SVR730005R0100	41
COV.11	1SVR730005R0100	242
MAR.12	1SVR730006R0000	41
MAR.12	1SVR730006R0000	242
CT-MFS.21S	1SVR730010R0200	39
CT-MBS.22S	1SVR730010R3200	39
CT-MVS.21S	1SVR730020R0200	39
CT-MVS.12S	1SVR730020R3100	39
CT-MVS.22S	1SVR730020R3300	39
CT-MVS.23S	1SVR730021R2300	39
CT- MXS.22S	1SVR730030R3300	39
CT-WBS.22S	1SVR730040R3300	39
CT-ERS.21S	1SVR730100R0300	40
CT-ERS.12S	1SVR730100R3100	40
CT-ERS.22S	1SVR730100R3300	40
CT-AHS.22S	1SVR730110R3300	40
CT-ARS.11S	1SVR730120R3100	40
CT-ARS.21S	1SVR730120R3300	40
CT-APS.21S	1SVR730180R0300	40
CT-APS.12S	1SVR730180R3100	40
CT-APS.22S	1SVR730180R3300	40
CT-SDS.22S	1SVR730210R3300	40
CT-SDS.23S	1SVR730211R2300	40
CM-IWS.1S	1SVR730660R0100	161
CM-IWS.2S	1SVR730670R0200	161
CM-MSS.12S	1SVR730700R0100	190
CM-MSS.22S	1SVR730700R0200	190
CM-MSS.13S	1SVR730700R2100	190
CM-MSS.23S	1SVR730700R2200	190
CM-MSS.32S	1SVR730712R0200	190
CM-MSS.41S	1SVR730712R1200	190
CM-MSS.51S	1SVR730712R1300	190
CM-MSS.31S	1SVR730712R1400	190
CM-MSS.33S	1SVR730712R2200	190
CM-MSS.11S	1SVR730720R1400	190
CM-MSS.21S	1SVR730722R1400	190
CM-TCS.11S	1SVR730740R0100	209
CM-TCS.12S	1SVR730740R0200	209
CM-TCS.13S	1SVR730740R0300	209
CM-TCS.21S	1SVR730740R9100	209
CM-TCS.22S	1SVR730740R9200	209
CM-TCS.23S	1SVR730740R9300	209
CM-EFS.2S	1SVR730750R0400	89
CM-SFS.21S	1SVR730760R0400	87
CM-SFS.22S	1SVR730760R0500	87
CM-PAS.31S	1SVR730774R1300	113
CM-PAS.41S	1SVR730774R3300	113

Index
Order code

Type	Order code	Page
CM-PSS.31S	1SVR730784R2300	113
CM-PSS.41S	1SVR730784R3300	113
CM-PVS.31S	1SVR730794R1300	113
CM-PVS.81S	1SVR730794R2300	113
CM-PVS.41S	1SVR730794R3300	113
CM-PFS.S	1SVR730824R9300	113
CM-ESS.1S	1SVR730830R0300	89
CM-ESS.2S	1SVR730830R0400	89
CM-ESS.MS	1SVR730830R0500	89
CM-ESS.1S	1SVR730831R0300	89
CM-ESS.2S	1SVR730831R0400	89
CM-ESS.1S	1SVR730831R1300	89
CM-ESS.2S	1SVR730831R1400	89
CM-SRS.11S	1SVR730840R0200	87
CM-SRS.12S	1SVR730840R0300	87
CM-SRS.21S	1SVR730840R0400	87
CM-SRS.22S	1SVR730840R0500	87
CM-SRS.M1S	1SVR730840R0600	87
CM-SRS.M2S	1SVR730840R0700	87
CM-SRS.11S	1SVR730841R0200	87
CM-SRS.12S	1SVR730841R0300	87
CM-SRS.21S	1SVR730841R0400	87
CM-SRS.22S	1SVR730841R0500	87
CM-SRS.11S	1SVR730841R1200	87
CM-SRS.12S	1SVR730841R1300	87
CM-SRS.21S	1SVR730841R1400	87
CM-SRS.22S	1SVR730841R1500	87
CM-ENS.11S	1SVR730850R0100	229
CM-ENS.21S	1SVR730850R0200	229
CM-ENS.31S	1SVR730850R0300	229
CM-ENS.11P	1SVR730850R2100	229
CM-ENS.23S	1SVR730850R2200	229
CM-MPS.31S	1SVR730884R1300	115
CM-MPS.41S	1SVR730884R3300	115
CM-MPS.43S	1SVR730884R4300	115
CM-MPS.11S	1SVR730885R1300	115
CM-MPS.21S	1SVR730885R3300	115
CM-MPS.23S	1SVR730885R4300	115
CT-MFS.21P	1SVR740010R0200	39
CT-MBS.22P	1SVR740010R3200	39
CT-MVS.21P	1SVR740020R0200	39
CT-MVS.12P	1SVR740020R3100	39
CT-MVS.22P	1SVR740020R3300	39
CT-MVS.23P	1SVR740021R2300	39
CT-MXS.22P	1SVR740030R3300	39
CT-WBS.22P	1SVR740040R3300	39
CT-ERS.21P	1SVR740100R0300	40
CT-ERS.12P	1SVR740100R3100	40
CT-ERS.22P	1SVR740100R3300	40
CT-AHS.22P	1SVR740110R3300	40
CT-ARS.11P	1SVR740120R3100	40
CT-ARS.21P	1SVR740120R3300	40
CT-APS.21P	1SVR740180R0300	40
CT-APS.12P	1SVR740180R3100	40
CT-APS.22P	1SVR740180R3300	40
CT-SDS.22P	1SVR740210R3300	40
CT-SDS.23P	1SVR740211R2300	40
CM-IWS.1P	1SVR740660R0100	161
CM-IWS.2P	1SVR740670R0200	161
CM-MSS.12P	1SVR740700R0100	190
CM-MSS.22P	1SVR740700R0200	190
CM-MSS.13P	1SVR740700R2100	190
CM-MSS.23P	1SVR740700R2200	190
CM-MSS.32P	1SVR740712R0200	190
CM-MSS.41P	1SVR740712R1200	190
CM-MSS.51P	1SVR740712R1300	190
CM-MSS.31P	1SVR740712R1400	190
CM-MSS.33P	1SVR740712R2200	190
CM-MSS.11P	1SVR740720R1400	190
CM-MSS.21P	1SVR740722R1400	190
CM-TCS.11P	1SVR740740R0100	209
CM-TCS.12P	1SVR740740R0200	209
CM-TCS.13P	1SVR740740R0300	209
CM-TCS.21P	1SVR740740R9100	209
CM-TCS.22P	1SVR740740R9200	209
CM-TCS.23P	1SVR740740R9300	209
CM-EFS.2P	1SVR740750R0400	89
CM-SFS.21P	1SVR740760R0400	87
CM-PAS.31P	1SVR740774R1300	113
CM-PAS.41P	1SVR740774R3300	113
CM-PSS.31P	1SVR740784R2300	113
CM-PSS.41P	1SVR740784R3300	113
CM-PVS.31P	1SVR740794R1300	113
CM-PVS.81P	1SVR740794R2300	113
CM-PVS.41P	1SVR740794R3300	113
CM-PFS.P	1SVR740824R9300	113
CM-ESS.1P	1SVR740830R0300	89
CM-ESS.2P	1SVR740830R0400	89
CM-ESS.MP	1SVR740830R0500	89
CM-ESS.1P	1SVR740831R0300	89
CM-ESS.2P	1SVR740831R0400	89
CM-ESS.1P	1SVR740831R1300	89
CM-ESS.2P	1SVR740831R1400	89
CM-SRS.11P	1SVR740840R0200	87
CM-SRS.21P	1SVR740840R0400	87
CM-SRS.M1P	1SVR740840R0600	87
CM-SRS.11P	1SVR740841R0200	87
CM-SRS.21P	1SVR740841R0400	87
CM-SRS.11P	1SVR740841R1200	87
CM-SRS.21P	1SVR740841R1400	87
CM-ENS.13S	1SVR740850R0100	229
CM-ENS.21P	1SVR740850R0200	229

Index
Order code

Type	Order code	Page
CM-ENS.31P	1SVR740850R0300	229
CM-ENS.13P	1SVR740850R2100	229
CM-ENS.23P	1SVR740850R2200	229
CM-MPS.31P	1SVR740884R1300	115
CM-MPS.41P	1SVR740884R3300	115
CM-MPS.43P	1SVR740884R4300	115
CM-MPS.11P	1SVR740885R1300	115
CM-MPS.21P	1SVR740885R3300	115
CM-MPS.23P	1SVR740885R4300	115
COV.12	1SVR750005R0100	242
CM-MPN.52S	1SVR750487R8300	115
CM-MPN.62S	1SVR750488R8300	115
CM-MPN.72S	1SVR750489R8300	115
CM-IWN.1S	1SVR750660R0200	161
CM-IVN.S	1SVR750669R9400	161
CM-MPN.52P	1SVR760487R8300	115
CM-MPN.62P	1SVR760488R8300	115
CM-MPN.72P	1SVR760489R8300	115
CM-IWN.1P	1SVR760660R0200	161
CM-IVN.P	1SVR760669R9400	161
EPD24-TB-101-1A	2CDE601101R2001	352
EPD24-TB-101-2A	2CDE601101R2002	352
EPD24-TB-101-3A	2CDE601101R2003	352
EPD24-TB-101-4A	2CDE601101R2004	352
EPD24-TB-101-6A	2CDE601101R2006	352
EPD24-TB-101-8A	2CDE601101R2008	352
EPD24-TB-101-10A	2CDE601101R2010	352
EPD24-TB-101-12A	2CDE601101R2012	352
EPD24-TB-101-0.5A	2CDE601101R2905	352
EPD-BB500	2CDE605100R0500	352
EPD-SB21	2CDE605200R0021	352
C011-70	GHC0110003R0001	191
C011-80	GHC0110003R0002	191
C011-90	GHC0110003R0003	191
C011-100	GHC0110003R0004	191
C011-110	GHC0110003R0005	191
C011-120	GHC0110003R0006	191
C011-130	GHC0110003R0007	191
C011-150	GHC0110003R0008	191
C011-160	GHC0110003R0009	191
C011-170	GHC0110003R0010	191
C011-140	GHC0110003R0011	191
C011-3-150	GHC0110033R0008	191
SK 615 562-87	GJD6155620R0087	41
SK 615 562-88	GJD6155620R0088	41

ABB STOTZ-KONTAKT GmbH
Eppelheimer Strasse 82
69123 Heidelberg
Germany

You can find the address of your local sales organization on the ABB homepage

abb.com/lowvoltage



We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB AG does not accept any responsibility whatsoever for potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB AG Copyright© 2021 ABB AG
All rights reserved

2CDC110004C0210 Rev. E (01/2020)