

LOW VOLTAGE AC DRIVES

# **ABB** general purpose drives

ACS550, 0.75 to 355 kW/1 to 500 hp



\_

All your energy saving needs covered from the start. ACS550 drives.

### **Table of contents**

<b>04</b> -05 Introduction to ACS5	550	ACS:	to A	luction	Introd	<b>04</b> -05
------------------------------------	-----	------	------	---------	--------	---------------

06 Ratings, types, voltages and construction

07 Technical data

**08**–09 **Dimensions and weights** 

10 Electromagnetic compatibility

11 Assistant control panel

**12**–15 **Options** 

16 Cooling

17 Fuses

**18**–19 **Control connections** 

**20**–22 **Drives service** 

### **Introduction to ACS550**

#### ABB general purpose drives

ABB general purpose drives are simple to buy, install, configure and use, saving considerable time. They are widely available through ABB channel partners. The drives have common user and process interfaces with fieldbuses, common software tools for sizing, commissioning, maintenance and common spare parts.

#### **Applications**

ABB general purpose drives can be used in a wide range of industries. Typical applications include pump, fan and constant torque use, such as conveyors. ABB general purpose drives are ideal in those situations where there is a need for simplicity to install, commission and use and where customizing or special product engineering is not required.

#### Highlights

- FlashDrop tool
- Intuitive use with assistant control panel
- Swinging choke for superior harmonic reduction
- Vector control
- Coated boards for harsh environments
- Built-in category C2 EMC filter (1st environment) as standard
- Flexible fieldbus system with built-in Modbus and numerous internally mountable fieldbus adapters
- UL, cUL, CE, C-Tick and GOST R approved
- RoHS compliant








Feature	Advantage	Benefit		
Energy efficiency counters	Several counters to illustrate saved energy (kWh), carbondioxide emissions (CO <sub>2</sub> ) and cost in local currency.	Shows direct impact on energy bill and helps control operational expenditure (OPEX).		
Load analyzer	Load analyzer saves process data, such as current and torque values, which can be used to analyze the process and dimensioning of the drive and motor.	Optimized dimensioning of the drive, motor and proc		
FlashDrop tool	Faster and easier drive setup and commissioning.	Patented, fast, safe and trouble-free parametrization method without electricity.		
Assistant control panel	Two soft-keys, function of which changes according to the state of the panel. Built-in help function via dedicated button. Real-time clock, allows timed tracing of faults and setting of parameters to activate at various times of day. Changed parameters -menu.	Easy commissioning.  Fast setup. Easier configuration. Rapid fault diagnosis. Quick access to recent parameter changes.		
Commissioning assistants	PID controller, real-time clock, serial communications assistant, drive optimizer, startup assistant.	Easy setup of parameters.		
Maintenance assistant	Monitors consumed energy (kWh), running hours or motor rotation.	Takes care of preventative maintenance of drive, the motor or run application.		
Intuitive features	Noise optimization. Increases switching frequency of drive when drive temperature is reduced. Controlled cooling fan: the drive is cooled only when necessary.	Considerable motor noise reduction.  Reduces inverter noise and improves energy efficiency.		
Choke  Patented swinging choke – matches the right induc to the right load, thereby suppressing and reducing harmonics.		Reduces total harmonic distortion (THD) emissions up to 25%.		
Vector control	Improved motor control performance.	Enables wider range of applications.		
Built-in EMC filter	Category C2 (1st environment) and category C3 (2nd environment) RFI filters as standard.	No need for additional external filtering.		
Brake chopper	Built-in up to 11 kW.	Reduced cost.		
Connectivity	Built-in Modbus using EIA-485. Simple to install: Easy connection of cables Easy connection to external fieldbus systems through multiple I/Os and plug-in options	Reduced cost. Reduced installation time. Secure cable connections.		
Mounting template	Supplied separately with unit.	Quick and easy to mark mounting screw holes on installation surface.		
RoHS compliant	ACS550 drives comply with EU Directive RoHS 2002/95/CE restricting the use of certaing hazardous substances.	Environmentally friendly product.		

### Selecting and ordering your drive

Build up your own ordering code using the type code key below or contact your local ABB drives sales office and let them know what you want.



### Ratings, types, voltages and construction

		Ratir	nae			Type designation	Frame
No	rmal use	Nacii		y-duty u	150	Type designation	size
P <sub>N</sub> (kW)	P <sub>N</sub> (hp)	/ <sub>2N</sub> (A)	P <sub>hd</sub> (kW)	P <sub>hd</sub> (hp)	I <sub>2hd</sub> (A)		
1.1	1.5	3.3	0.75	1	2.4	ACS550-01-03A3-4	R1
1.5	2	4.1	1.1	1.5	3.3	ACS550-01-04A1-4	R
2.2	3	5.4	1.5	2	4.1	ACS550-01-05A4-4	R
3	4	6.9	2.2	3	5.4	ACS550-01-06A9-4	R:
4	5.4	8.8	3	4	6.9	ACS550-01-08A8-4	R:
5.5	7.5	11.9	4	5.4	8.8	ACS550-01-012A-4	R:
7.5	10	15.4	5.5	7.5	11.9	ACS550-01-015A-4	R2
11	15	23	7.5	10	15.4	ACS550-01-023A-4	R
15	20	31	11	15	23	ACS550-01-031A-4	R3
18.5	25	38	15	20	31	ACS550-01-038A-4	R3
22	30	45	18.5	25	38	ACS550-01-045A-4	R3
30	40	59	22	30	45	ACS550-01-059A-4	R4
37	50	72	30	40	59	ACS550-01-072A-4	R4
45	60	87	37	60	72	ACS550-01-087A-4	R4
55	100	125	45	75	96	ACS550-01-125A-4	R:
75	125	157	55	100	125	ACS550-01-157A-4	R
90	150	180	75	125	156	ACS550-01-180A-4	R
110	150	205	90	125	162	ACS550-01-195A-4	R
132	200	246	110	150	192	ACS550-01-246A-4	R
160	200	290	132	200	246	ACS550-01-290A-4	Re
ree-star	nding unit	s					
200	300	368	160	250	302	ACS550-02-368A-4	R
250	400	486	200	350	414	ACS550-02-486A-4	R
280	450	526	250	400	477	ACS550-02-526A-4	R
315	500	602	280	450	515	ACS550-02-602A-4	R
355	500	645	315	500	590	ACS550-02-645A-4	R
-	supply vo	_	08 to 240	O V			
0.75	1.0	4.6	0.75	0.8	3.5	ACS550-01-04A6-2	R
1.1	1.5	6.6	0.75	1.0	4.6	ACS550-01-06A6-2	R
1.5	2.0	7.5	1.1	1.5	6.6	ACS550-01-07A5-2	R
2.2	3.0	11.8	1.5	2.0	7.5	ACS550-01-012A-2	R
4.0	5.0	16.7	3.0	3.0	11.8	ACS550-01-017A-2	R
5.5	7.5	24.2	4.0	5.0	16.7	ACS550-01-024A-2	R
7.5	10.0	30.8	5.5	7.5	24.2	ACS550-01-031A-2	R
11.0	15.0	46.2	7.5	10.0	30.8	ACS550-01-046A-2	R
15.0	20.0	59.4	11.0	15.0	46.2	ACS550-01-059A-2	R
18.5	25.0	74.8	15.0	20.0	59.4	ACS550-01-075A-2	R
22.0	30.0	88.0	18.5	25.0	74.8	ACS550-01-088A-2	R
30.0	40.0	114	22.0	30.0	88.0	ACS550-01-114A-2	R
37.0	50.0	143	30.0	40	114	ACS550-01-143A-2	R
45.0	60.0	178	37.0	50	150	ACS550-01-178A-2	R
55.0	75.0	221	45.0	60	178	ACS550-01-221A-2	R
75.0	100	248	55.0	75	192	ACS550-01-248A-2	R

#### Type designation

Drive's type designation (shown on the previous page and in column 7 of the tables on the left side) identifies your drive by construction, current rating and voltage range. Once you have selected the type designation, the frame size (column 8) can be used to determine the drives dimensions, shown on the page 8.

#### **Voltages**

ACS550 is available in two voltage ranges:

**4** = 380 to 480 V

2 = 208 to 240 V

Insert either "4" or "2", depending on your chosen voltage, into the type designation shown on the previous page.

#### Construction

"01" within the type designation varies depending on the drive mounting arrangement, and power rating.

**01** = wall-mounted **02** = free-standing

Normal use vs heavy-duty use. For the majority of pump, fan and conveyor applications, select "Normal use" figures. For high overload requirements, select "Heavy-duty use" figures. If in doubt contact your local ABB sales office or your drives distributor.

 $\begin{array}{lll} P_{\rm N} \ {\rm for} \ {\rm kW} & = \ {\rm Typical} \ {\rm motor} \ {\rm power} \ {\rm in} \ 400 \ {\rm V} \ {\rm at} \ {\rm normal} \ {\rm use} \\ P_{\rm N} \ {\rm for} \ {\rm ho} & = \ {\rm Typical} \ {\rm motor} \ {\rm power} \ {\rm in} \ 460 \ {\rm V} \ {\rm at} \ {\rm heavy-duty} \ {\rm use} \\ P_{\rm hd} \ {\rm for} \ {\rm kW} & = \ {\rm Typical} \ {\rm motor} \ {\rm power} \ {\rm in} \ 460 \ {\rm V} \ {\rm at} \ {\rm heavy-duty} \ {\rm use} \\ I_{\rm 2N} \ {\rm for} \ {\rm A} & = \ {\rm Continuous} \ {\rm rms} \ {\rm current.} \ 10\% \ {\rm overload} \ {\rm is} \\ {\rm allowed} \ {\rm for} \ {\rm one} \ {\rm minute} \ {\rm in} \ {\rm tenminutes}. \\ I_{\rm 2hd} \ {\rm for} \ {\rm A} & = \ {\rm Continuous} \ {\rm rms} \ {\rm current.} \ 50\% \ {\rm overload} \ {\rm is} \\ {\rm allowed} \ {\rm for} \ {\rm one} \ {\rm minute} \ {\rm in} \ {\rm tenminutes}. \\ \end{array}$ 

### **Technical data**

Mains connection	
Voltage and power range	3-phase, 380 to 480 V, +10/ -15%, 0.75 to 355 kW 3-phase, 208 to 240 V, +10/ -15%, 0.75 to 75 kW Auto-identification of input line
Frequency	48 to 63 Hz
Power factor	0.98
Motor connection	
Voltage	3-phase, from 0 to $U_{\text{supply}}$
Frequency	0 to 500 Hz
Continuous loading capability (constant torque at a max ambient temperature of 40 °C)	Rated output current $I_{\rm 2N}$
Overload capacity (at a max. ambient temperature of 40 °C)	At normal use $1.1 \times I_{2N}$ for 1 minute every 10 minutes At heavy-duty use $1.5 \times I_{2hd}$ for 1 minute every 10 minutes Always $1.8 \times I_{2hd}$ for 2 seconds every 60 seconds
Switching frequency Selectable	Default 4 kHz 1 kHz, 2 kHz, 4 kHz, 8 kHz, 12 kHz
Acceleration time	0.1 to 1800 s
Deceleration time	0.1 to 1800 s
Speed control Open loop Closed loop Open loop Closed loop	20% of motor nominal slip 0.1% of motor nominal speed < 1% s with 100% torque step 0.5% s with 100% torque step
Torque control Open loop Closed loop Open loop Closed loop	< 10 ms with nominal torque < 10 ms with nominal torque ± 5% with nominal torque ± 2% with nominal torque
Environmental limits	·
Ambient temperature -15 to 50 °C	No frost allowed. From 40 to 50 °C with derating.
Altitude Output current	Rated current available at 0 to 1000 m. In altitudes from 1000 to 4000 m (3300 to 13,200 ft) above sea level, the derating is 1% for every 100 m (330 ft). If the installation site is higher than 2000 m (6600 ft) above sea level, please contact your local ABB distributor or office for further information.
Relative humidity	5 to 95%, no condensation allowed
Degree of protection	IP21 or IP54 (≤ 160 kW)
Enclosure colour	NCS 1502-Y, RAL 9002, PMS 420 C
Contamination levels  Transportation	IEC 721-3-3 No conductive dust allowed Class 1C2 (chemical gases),
Storage	Class 1S2 (solid particles) Class 2C2 (chemical gases), Class 2S2 (solid particles)
Operation	Class 3C2 (chemical gases), Class 3S2 (solid particles)

to 10 V, $R_{\rm in}$ > 312 k $\Omega$ single-ended to 20 mA, $R_{\rm in}$ = 100 $\Omega$ single-ended to 2% max. 10 mA, $R$ < 10 k $\Omega$ 32 ms
to 20 mA, $R_{\rm in} = 100 \Omega$ single-ended 2% max. 10 mA, $R < 10 \text{ k}\Omega$
: 2% max. 1 <sup>™</sup> 0 mA, <i>R</i> < 10 kΩ 32 ms
32 ms
o 20 mA, load < 500 Ω
o 20 mA, load < 500 Ω
o 20 mA, load < 500 Ω
OC ± 10%, max. 250 mA
24 V DC with internal or external supply, nd NPN
Ω
± 1 ms
AC/30 V DC
0 V DC; 1500 V A/230 V AC
าร
us protocol
95/EC
9001
1001

UL, cUL, CE, C-Tick and GOST R approvals

RoHS compliant

# **Dimensions and weights**

Wall-mou	Vall-mounted units								
Frame		IP21	/ UL type	1			IP54 / UL	type 12 <sup>2)</sup>	
size	H1 (mm)	H2 (mm)	W (mm)	D (mm)	Weight (kg)	H (mm)	W (mm)	D (mm)	Weight (kg)
R1	369	330	125	212	6.5	461	213	234	8
R2	469	430	125	222	9	561	213	245	11
R3	583	490	203	231	16	629	257	254	17
R4	689	596	203	262	24	760	257	284	26
R5	736	602	265	286	34	775	369	309	42
R6	8881)	700	302	400	69	924 <sup>3)</sup>	410	423	86



H2 = Height without cable connection box


W = Width


D = Depth

<sup>&</sup>lt;sup>3)</sup> ACS550-01-290A-4: 1119 mm

Free-standing units								
Frame		/ UL type	1					
size	H1	H2	W	D	Weight			
	(mm)	(mm)	(mm)	(mm)	(kg)			
R8	2024	n/a	347 1)	617 1)	230			

n/a = not applicablez





<sup>&</sup>lt;sup>1)</sup> ACS550-01-246A-4 and ACS550-01-290A-4: 981 mm <sup>2)</sup> UL Type 12 not available for ACS550-01-290A-4

 $<sup>^{\</sup>mbox{\tiny 1)}}$  The dimensions apply to bookshelf mounting. In flat type mounting the width and depth change places.

DIMENSIONS AND WEIGHTS



## **Electromagnetic compatibility**

The EMC product standard (EN 61800-3:2004 + Amendment A1:2012) covers the specific EMC requirements stated for drives (tested with motor and cable) within the EU. EMC standards such as EN 55011, or EN 61000-6-3/4, apply to industrial and household equipment and systems including drive component inside. Drive units complying with requirements of EN 61800-3

are always complient with comparable categories in EN 55011 and EN 61000-6-3/4, but not necessarily vice versa. EN 55011 and EN 61000-6-3/4 do not specify cable length nor require a motor to be connected as a load. The emission limits are comparable according to the following table, EMC standards.

#### EMC according to EN61800-3

1st environment restricted distribution for frame sizes R3, R4 with 75 m motor cables and for rame sizes R1, R2, R5, R6 with 100 m motor cables as standard with default switching frequency.

R1, R2, R5, R6 with 100 m motor cables as standard with default switching frequency.

 $2^{nd}$  environment unrestricted distribution for frame sizes R1 to R4 with 300 m motor cables and for frame sizes R5 to R8 with 100 m motor cables as standard with default switching frequency.

These cable lengths are for EMC purposes only. Operational cable lengths are available in the output choke selection table on page 11. For longer motor cable lengths, external EMC filters are available on request.

EMC standards in general		
EN 61800-3/A11 (2000), product standard	EN 61800-3 (2004) + A1:2012 product standard	EN 55011, product family standard for industrial, scientific and medical (ISM) equipment
1 <sup>st</sup> environment, unrestricted distribution	Category C1	Group 1 Class B
1 <sup>st</sup> environment, restricted distribution	Category C2	Group 1 Class A
2 <sup>nd</sup> environment, unrestricted distribution	Category C3	Group 2 Class A
2 <sup>nd</sup> environment, restricted distribution	Category C4	Not applicable

## **Assistant control panel**

The assistant control panel, which is delivered as standard, features a multilingual alphanumeric display for easy drive programming. The control panel has various assistants and a built-in help function to guide the user. It includes a real time clock, which can be used during fault logging and in controlling the drive, such as start/stop. The control panel can be used for copying parameters for back up or for downloading them to another drive. A graphical display and soft keys make it extremely easy to navigate.





### **Options**

## Control interfaces

#### Panel mounting kits

To attach the control panel to the outside of a larger enclosure, two panel mounting kits are available. A simple and costefficient installation is possible with the ACS/H-CP-EXT kit, while the OPMP-01 kit provides a more user-friendly solution, including a panel platform that enables the panel to be removed in the same way as a drive-mounted panel. The panel mounting kits include all hardware required, including 3 m extension cables and installation instructions.



#### How to select options

The options shown in the table are available within the ACS550 range. Most of them have an associated 4-figure option code, which is shown in the table. It is this code that replaces B055 in the type code above. External options require a separate order line and material or type code number.

#### **Basic control panel**

The basic control panel features a single line numeric display. The panel can be used to control the drive, set the parameter values or copy them from one drive to another.


Availab	le options	
Protect	tion class	
B055	IP54	
Contro	l panel	
0J400	If no control panel is required	
J404	Basic control panel	ACS-CP-C
_1)	Panel mounting kit	ACS/H-CP-EXT
_1)	Panel holder mounting kit	OPMP-01
_1)	Panel mounting kit IP66	ACS/H-CP-EXT-IP66
I/O opt	ions <sup>2)</sup>	
L511	Relay output extension	OREL-01
Contro	ol option <sup>2)</sup>	
_1)	Encoder	OTAC-01
Fieldbu	IS <sup>3)</sup>	
K451	DeviceNet™	RDNA-01
K452	LonWorks®	RLON-01
K454	PROFIBUS DP	RPBA-01
K457	CANopen®	RCAN-01
K462	ControlNet	RCNA-01
K466	Modbus TCP	RETA-01
K466	EtherNet/IP™	RETA-01
K467	Modbus TCP	RETA-02
K467	PROFINET IO	RETA-02
_1)	POWERLINK	REPL-02
_1)	EtherCAT®	RECA-01
Tools		
_1)	FlashDrop	MFDT-01
_ 1)	DriveWindow Light and	DriveWindow Light
	USB serial adapters	
Remote	monitoring	
<b>-</b> 1)	Ethernet adapter	SREA-01

- 1) Ordering with a separate material code number.
- 2) One slot available for relay or encoder.
- <sup>3)</sup> One slot available for fi eldbus adapter. Modbus built-in as standard.



### **Options**

# Plug-in options



#### FlashDrop tool

ACS550 drives have an interface for a FlashDrop tool. FlashDrop is a powerful palm sized tool for fast and easy parameter selection and setting of an unpowered drive. The user can hide each parameter/group from the drive's display, which protects the drive and connected machinery. For more information on the FlashDrop tool, please see page 14.

#### Relay output extension option module

This plug-in option offers three additional relay outputs. They can be used, for example, in pump and fan control or many supervisory functions. All the relays can be programmed to on/off by using the assistant control panel's clock. Alternatively, fieldbus can be used to control any external components in the system.

#### Encoder feedback option module

The general purpose drives can accommodate an encoder module. Using an encoder for speed feedback is a straight forward way to increase motor control in many applications.

#### Plug-in fieldbus module

The plug-in fieldbus options bring connectivity to major automation systems. A single twisted pair avoids large amounts of conventional cabling, thereby reducing cost and increasing system reliability.

ACS550 supports the following fieldbus options:

- DeviceNetTM
- LonWorks®
- PROFIBUS DP
- CANopen®
- ControlNet
- Modbus TCP
- EtherNet/IPTM
- PROFINET IO
- POWERLINK
- EtherCAT®

For type codes see page 12.

### **Options**

### External options

01 FlashDrop tool

02 SREA-01 Ethernet adapter

03 DriveWindow Light

#### FlashDrop tool

FlashDrop is a powerful palm sized tool for fast and easy parameter selecting and setting. It gives the possibility to hide selected parameters to protect the machine. Only the parameters needed in the application are shown. The tool can copy parameters between two drives or between a PC and a drive. All the above can be done without a power connection to the drive. The interface for FlashDrop is available in all wallmounted units.

#### **DrivePM**

DrivePM (drive parameter manager) is a tool to create, edit and copy parameter sets for the FlashDrop tool. For each parameter/group the user has a possibility to hide it, which means that the drive user does not see the parameter/group at all.

#### FlashDrop package includes

- FlashDrop tool
- · DrivePM software
- User's manual (hardcopy and PDF)
- RS232 cable for connection between PC and the FlashDrop tool
- Battery charger

#### **SREA-01 Ethernet adapter**

SREA-01 Ethernet adapter with remote monitoring access can send process data, data logs and event messages independently, without a PLC or a dedicated on-site computer. It has an internal web server for configuration and drive access.

#### **DriveWindow Light**

DriveWindow Light is an easy-to-use startup and maintenance tool for ACS550 drives. It can be used in an offline mode, which enables parameter setting at the office even before going to the actual site. The parameter browser enables viewing, editing and saving of parameters. The parameter comparison feature makes it possible to compare parameter values between the drive and the file. With the parameter subset you can create your own parameter sets. Controlling of the drive is naturally one of the features in DriveWindow Light. With this software tool, you can monitor up to four signals simultaneously. This can be done in both graphical and numerical format. Any signal can be set to stop the monitoring from a predefined level.

#### Startup wizards

Startup wizards make the setting of parameters easy. Simply launch the wizard, select an appropriate assistant eg, for setting analog outputs, and all parameters related to this function are shown together with help pictures.

#### **Highlights**

- Editing, saving and downloading parameters
- Graphical and numerical signal monitoring
- · Drive control
- · Startup wizards






EXTERNAL OPTIONS 15

#### Brake units and choppers

Frame sizes R1 to R2 are delivered with integrated brake choppers as standard. Other units can use the compact-sized brake units which include brake chopper and resistor. For more information please refer to the ACS-BRK brake units installation and startup guide.

Brake units technical data								
Frequency converter input voltage	Resistor (ohm)	Continuous output (W)	Max. output 20 s (W)	Brake unit type code				
200 to 240 V AC	32	2000	4500	ACS-BRK-C				
380 to 480 V AC			12000					
200 to 240 V AC	10.5	7000	14000	ACS-BRK-D				
380 to 480 V AC			42000					



#### **Output chokes**

Output chokes are used when motor cables above normal length are required. Cable can be roughly 1.5 times standard cable length, see below.

Dimensions				
Width = W (mm)	Height = H (mm)	Depth = D (mm)	Weight (kg)	Brake unit type code
150	500	347	7.5	ACS-BRK-C
270	600	450	20.5	ACS-BRK-D

Type designation	Frame size	Nominal current I <sub>2N</sub> (A)	Output choke type code 1)	Choke thermal current <i>I</i> (A)	Max. cable length without choke <sup>2)</sup> (m)	Max. cable length with choke <sup>3)</sup> (m)
U <sub>N</sub> = 380 to 480 V (380	, 400, 415, 440,	460, 480 V)				
ACS550-01-03A3-4	R1	3.3	NOCH-0016-6X	19	100	150
ACS550-01-04A1-4	R1	4.1	NOCH-0016-6X	19	100	150
ACS550-01-05A4-4	R1	5.4	NOCH-0016-6X	19	100	150
ACS550-01-06A9-4	R1	6.9	NOCH-0016-6X	19	100	150
ACS550-01-08A8-4	R1	8.8	NOCH-0016-6X	19	100	150
ACS550-01-012A-4	R1	11.9	NOCH-0016-6X	19	100	150
ACS550-01-015A-4	R2	15.4	NOCH-0016-6X	19	200	250
ACS550-01-023A-4	R2	23	NOCH-0030-6X	41	200	250
ACS550-01-031A-4	R3	31	NOCH-0030-6X	41	200	250
ACS550-01-038A-4	R3	38	NOCH-0030-6X	41	200	250
ACS550-01-045A-4	R3	45	NOCH-0070-6X	112	200	300
ACS550-01-059A-4	R4	59	NOCH-0070-6X	112	200	300
ACS550-01-072A-4	R4	72	NOCH-0070-6X	112	200	300
ACS550-01-087A-4	R4	87	NOCH-0070-6X	112	300	300
ACS550-01-125A-4	R5	125	NOCH-0120-6X	157	300	300
ACS550-01-157A-4	R6	157	FOCH-0260-70	289	300	300
ACS550-01-180A-4	R6	180	FOCH-0260-70	289	300	300
ACS550-01-195A-4	R6	205	FOCH-0260-70	289	300	300
ACS550-01-246A-4	R6	246	FOCH-0260-70	289	300	300
ACS550-01-290A-4	R6	290	FOCH-0320-50	445	300	300
ACS550-02-368A-4	R8	368	FOCH-0320-50	445	300	300
ACS550-02-486A-4	R8	486	FOCH-0610-70	720	300	300
ACS550-02-526A-4	R8	526	FOCH-0610-70	720	300	300
ACS550-02-602A-4	R8	602	FOCH-0610-70	720	300	300
ACS550-02-645A-4	R8	645	FOCH-0610-70	720	300	300

 $<sup>^{1)}</sup>$  The last digit of the output choke type defi nes the degree of protection; X stands for 2 = IP22 or 5 = IP54, 0 = IP00.

Note: An output choke does not improve the EMC performance of the drive. To fulfil local EMC requirements use sufficient RFI filtering. For more information refer to the ACS550 User's manual/Technical reference.

 $<sup>^{\</sup>mbox{\tiny 2)}}$  Cable lengths according to 4 kHz switching frequency.

<sup>3)</sup> Maximum switching frequency to be used with du/dt fi lter is 4 kHz.

# Cooling

Cooling air flow 380 to 480 V units						
Type designation	Frame	Heat dissipation		Air flow		
	size	(W)	(BTU/Hr)	(m³/h)	(ft³/min)	
ACS550-01-03A3-4	R1	40	137	44	26	
ACS550-01-04A1-4	R1	52	178	44	26	
ACS550-01-05A4-4	R1	73	249	44	26	
ACS550-01-06A9-4	R1	97	331	44	26	
ACS550-01-08A8-4	R1	127	434	44	26	
ACS550-01-012A-4	R1	172	587	44	26	
ACS550-01-015A-4	R2	232	792	88	52	
ACS550-01-023A-4	R2	337	1151	88	52	
ACS550-01-031A-4	R3	457	1561	134	79	
ACS550-01-038A-4	R3	562	1919	134	79	
ACS550-01-045A-4	R3	667	2278	134	79	
ACS550-01-059A-4	R4	907	3098	280	165	
ACS550-01-072A-4	R4	1120	3825	280	165	
ACS550-01-087A-4	R4	1440	4918	280	165	
ACS550-01-125A-4	R5	1940	6625	350	205	
ACS550-01-157A-4	R6	2310	7889	405	238	
ACS550-01-180A-4	R6	2810	9597	405	238	
ACS550-01-195A-4	R6	3050	10416	405	238	
ACS550-01-246A-4	R6	3260	11134	405	238	
ACS550-01-290A-4	R6	3850	13125	405	238	
ACS550-02-368A-4	R8	6850	23394	1220	718	
ACS550-02-486A-4	R8	7850	26809	1220	718	
ACS550-02-526A-4	R8	7600	25955	1220	718	
ACS550-02-602A-4	R8	8100	27663	1220	718	
ACS550-02-645A-4	R8	9100	31078	1220	718	

Type designation	Frame size	Heat dissipation		Air flow	
		(W)	(BTU/Hr)	(m³/h)	(ft³/min)
ACS550-01-04A6-2	R1	55	189	44	26
ACS550-01-06A6-2	R1	73	249	44	26
ACS550-01-07A5-2	R1	81	276	44	26
ACS550-01-012A-2	R1	118	404	44	26
ACS550-01-017A-2	R1	161	551	44	26
ACS550-01-024A-2	R2	227	776	88	52
ACS550-01-031A-2	R2	285	973	88	52
ACS550-01-046A-2	R3	420	1434	134	79
ACS550-01-059A-2	R3	536	1829	134	79
ACS550-01-075A-2	R4	671	2290	280	165
ACS550-01-088A-2	R4	786	2685	280	165
ACS550-01-114A-2	R4	1014	3463	280	165
ACS550-01-143A-2	R6	1268	4331	405	238
ACS550-01-178A-2	R6	1575	5379	405	238
ACS550-01-221A-2	R6	1952	6666	405	238
ACS550-01-248A-2	R6	2189	7474	405	238

#### Cooling

ACS550 is fitted with cooling air fans. The cooling air must be free from corrosive materials and not above the maximum ambient temperature of 40  $^{\circ}$ C (50  $^{\circ}$ C with derating). For more specific environmental limits see page 7.

Free space requirements							
Enclosure type	Space above (mm)	Space below (mm)	Space on left/right (mm)				
Wall mounted	200	200	0				
Free standing	200	0	0				

### **Fuses**

Recommended input protection fuses for 380 to 480 V units						
Type designation			C fuses	UL fuses		
	size	(A)	Fuse type*)	(A)	Fuse type	
ACS550-01-03A3-4	R1	10	gG	10	UL Class T	
ACS550-01-04A1-4	R1	10	gG	10	UL Class T	
ACS550-01-05A4-4	R1	10	gG	10	UL Class T	
ACS550-01-06A9-4	R1	10	gG	10	UL Class T	
ACS550-01-08A8-4	R1	10	gG	15	UL Class T	
ACS550-01-012A-4	R1	16	gG	15	UL Class T	
ACS550-01-015A-4	R2	16	gG	20	UL Class T	
ACS550-01-023A-4	R2	25	gG	30	UL Class T	
ACS550-01-031A-4	R3	35	gG	40	UL Class T	
ACS550-01-038A-4	R3	50	gG	50	UL Class T	
ACS550-01-045A-4	R3	50	gG	60	UL Class T	
ACS550-01-059A-4	R4	63	gG	80	UL Class T	
ACS550-01-072A-4	R4	80	gG	90	UL Class T	
ACS550-01-087A-4	R4	125	gG	125	UL Class T	
ACS550-01-125A-4	R5	160	gG	175	UL Class T	
ACS550-01-157A-4	R6	200	gG	200	UL Class T	
ACS550-01-180A-4	R6	250	gG	250	UL Class T	
ACS550-01-195A-4	R6	250	gG	250	UL Class T	
ACS550-01-246A-4	R6	250	gG	250	UL Class T	
ACS550-01-290A-4	R6	315	gG	315	UL Class T	
ACS550-02-368A-4	R8	400	gG	400	UL Class T	
ACS550-02-486A-4	R8	500	gG	500	UL Class T	
ACS550-02-526A-4	R8	630	gG	630	UL Class T	
ACS550-02-602A-4	R8	630	gG	630	UL Class T	
ACS550-02-645A-4	R8	800	gG	800	UL Class T	

<sup>\*)</sup> According to IEC-60269 standard

Type designation	Frame	IE	IEC fuses		UL fuses	
	size (	(A)	Fuse type *)	(A)	Fuse type	
ACS550-01-04A6-2	R1	10	gG	10	UL Class T	
ACS550-01-06A6-2	R1	10	gG	10	UL Class T	
ACS550-01-07A5-2	R1	10	gG	10	UL Class T	
ACS550-01-012A-2	R1	16	gG	15	UL Class T	
ACS550-01-017A-2	R1	25	gG	25	UL Class T	
ACS550-01-024A-2	R2	25	gG	30	UL Class T	
ACS550-01-031A-2	R2	40	gG	40	UL Class T	
ACS550-01-046A-2	R3	63	gG	60	UL Class T	
ACS550-01-059A-2	R3	63	gG	80	UL Class T	
ACS550-01-075A-2	R4	80	gG	100	UL Class T	
ACS550-01-088A-2	R4	100	gG	110	UL Class T	
ACS550-01-114A-2	R4	125	gG	150	UL Class T	
ACS550-01-143A-2	R6	200	gG	200	UL Class T	
ACS550-01-178A-2	R6	250	gG	250	UL Class T	
ACS550-01-221A-2	R6	315	gG	300	UL Class T	
ACS550-01-248A-2	R6	315	gG	350	UL Class T	


<sup>\*)</sup> According to IEC-60269 standard

#### **Fuse connections**

Standard fuses can be used with ABB general purpose drives. For input fuse connections see tables.

### **Control connections**

These connections are shown as examples only. Please refer to the ACS550 User's manual, chapter Installations, for more detailed information.





### Services to match your needs

Your service needs depend on your operation, life cycle of your equipment and business priorities. We have identified our customers' four most common needs and defined service options to satisfy them. What is your choice to keep your drives at peak performance?

### Is uptime your priority?

Keep your drives running with precisely planned and executed maintenance.

#### Example services include:

- ABB Ability Life Cycle Assessment
- Installation and Commissioning
- Spare Parts
- · Preventive Maintenance
- Reconditioning
- ABB Drive Care agreement
- Drive Exchange

# Is rapid response a key consideration?

If your drives require immediate action, our global network is at your service.

#### Example services include:


- · Technical Support
- On-site Repair
- ABB Ability Remote Assistance
- Response time agreements
- Training



#### Rapid response



Operational efficiency



### **Drives service**

### Your choice, your future

### The future of your drives depends on the service you choose.

Whatever you choose, it should be a well-informed decision. No guesswork. We have the expertise and experience to help you find and implement the right service for your drive equipment. You can start by asking yourself these two critical questions:

- Why should my drive be serviced?
- What would my optimal service options be?

From here, you have our guidance and full support along the course you take, throughout the entire lifetime of your drives.

#### Your choice, your business efficiency

ABB Drive Care agreement lets you focus on your core business. A selection of predefined service options matching your needs provides optimal, more reliable performance, extended drive lifetime and improved cost control. So you can reduce the risk of unplanned downtime and find it easier to budget for maintenance.

# Need to extend your assets' lifetime?

Maximize your drive's lifetime with our services.

#### Example services include:

- · ABB Ability Life Cycle Assessment
- · Upgrades, Retrofits and Modernization
- Replacement, Disposal and Recycling



### Life cycle management

# Is performance most critical to your operation?

Get optimal performance out of your machinery and systems.

#### Example services include:

- ABB Ability Remote Services
- Engineering and Consulting
- Inspection and Diagnostics
- Upgrades, Retrofits and Modernization
- Workshop Repair
- · Tailored services



Performance improvement

#### \_\_\_\_

### A lifetime of peak performance

You're in control of every life cycle phase of your drives. At the heart of drive services is a four-phase product life cycle management model. This model defines the services recommended and available throughout drives lifespan.

Now it's easy for you to see the exact service and maintenance available for your drives.

#### ABB drives life cycle phases explained: **Active** Classic Limited Obsolete Full range of life cycle services and support Limited range of life cycle Replacement and services and support end-of-life services Product is in Serial production has Product is no Product is no longer active sales and ceased. Product may be available. longer manufacturing available for plant available. extensions, as a spare phase. part or for installed Full range of life cycle Full range of life cycle Limited range of life Replacement and

#### **Keeping you informed**

services is available.

We notify you every step of the way using life cycle status statements and announcements.

services is available.

through upgrade and

may be available

Your benefit is clear information about your drives' status and precise services available. It helps you plan the preferred service actions ahead of time and make sure that continuous support is always available.

#### Step 1

Spare parts availability

is limited to available

cycle services is

available.

stock.

#### **Life Cycle Status Announcement**

Provides early information about the upcoming life cycle phase change and how it affects the availability of services.

end-of-life services

are available.

#### Step 2

#### Life Cycle Status Statement

Provides information about the drive's current life cycle status, availability of product and services, life cycle plan and recommended actions.

#### Additional information

We reserve the right to make technical changes or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB cloes not accept any responsibility whatsoever fo potential errors or possible lack of information in this document.

We reserve all rights in this document and in the subject matter and illustrations contained therein. Any reproduction, disclosure to third parties or utilization of its contents – in whole or in parts – is forbidden without prior written consent of ABB.



For more information, please contact your local ABB representative or visit

abb.com/drives abb.com/drivespartners