
DATA SHEET

Freelance - Device Type Managers

Integrated HART Devices





DATA SHEET

Freelance - Device Type Managers

Integrated HART Devices

Introduction

This document consists summary of released device types and detail information for HART Protocol in ABB System Freelance.

Notice

This document contains information about one or more ABB products and may include a description of or a reference to one or more standards that may be generally relevant to the ABB products. The presence of any such description of a standard or reference to a standard is not a representation that all of the ABB products referenced in this document support all of the features of the described or referenced standard. In order to determine the specific features supported by a particular ABB product, the reader should consult the product specifications for the particular ABB product.

ABB may have one or more patents or pending patent applications protecting the intellectual property in the ABB products described in this document.

The information in this document is subject to change without notice and should not be construed as a commitment by ABB. ABB assumes no responsibility for any errors that may appear in this document.

Products described or referenced in this document are designed to be connected and to communicate information and data through network interfaces, which should be connected to a secure network. It is the sole responsibility of the system/product owner to provide and continuously ensure a secure connection between the product and the system network and/or any other networks that may be connected.

The system/product owners must establish and maintain appropriate measures, including, but not limited to, the installation of firewalls, application of authentication measures, encryption of data, installation of antivirus programs, and so on, to protect these products, the network, its system, and interfaces against security breaches, unauthorized access, interference, intrusion, leakage, and/or theft of data or information.

ABB performs functionality testing on the products and updates that we release. However, system/product owners are ultimately responsible for ensuring that any product updates or other major system updates (to include but not limited to code changes, configuration file changes, third-party software updates or patches, hardware change out, and so on) are compatible with the security measures implemented. The system/product owners must verify that the system and associated products function as expected in the environment in which they are deployed.

In no event shall ABB be liable for direct, indirect, special, incidental or consequential damages of any nature or kind arising from the use of this document, nor shall ABB be liable for incidental or consequential damages arising from use of any software or hardware described in this document.

This document and parts thereof must not be reproduced or copied without written permission from ABB, and the contents thereof must not be imparted to a third party nor used for any unauthorized purpose.

The software or hardware described in this document is furnished under a license and may be used, copied, or disclosed only in accordance with the terms of such license.

This product meets the requirements specified in EMC Directive 2014/30/EU and in Low Voltage Directive 2014/35/EU.



The crossed-out wheeled bin symbol on the product and accompanying documents means that used electrical and electronic equipment (WEEE) should not be mixed with general household waste. If you wish to discard electrical and electronic equipment (EEE), please contact your dealer or supplier for further information.

Disposing of this product correctly will help save valuable resources and prevent any potential negative effects on human health and the environment, which could otherwise arise from inappropriate waste handling.

Trademarks and copyright

All rights to copyrights, registered trademarks, and trademarks reside with their respective owners.

Copyright © 2004 - 2024 ABB. All rights reserved.

Release: September 2024

Document ID: 3BDD011926

Revision: DL

Integrated device List:

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version					
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1
Analytical	ABB	AZ20-AZ30 HART	05.00.03	0x22	0	x	x	x	x	x	x
		APA592-PH HART Endura pH	05.00.03	0x030	1	x	x	x	x	x	x
		ACA592-XX HART Endura	05.00.03	0x03x	1	x	x	x	x	x	x
	Berthold Technologies	LB491	V2*	0x007d	2	x	x	x	x	x	x
	Detector Electronics	Eclipse	V1*	0x007f	1	x	x	x	x	x	x
		X3301	V1*	0x007c	1	x	x	x	x	x	x
	Drager Safety	polytron2 IR	V1*	0x00ed	1	x	x	x	x	x	x
	Draeger	Pulsar 7x00	V0.5.0.391	0x52EF	2			x	x	x	x
	Endress+ Hauser	Liquiline Cond CM42	V2.02.01-0010	0x11A0	2	x	x	x	x	x	x
			V13.04.07	0x90	14	x		x	x	x	x
			V13.05.xx	0x90	15	x		x	x	x	x
		Liquiline M / CM44x	V1.02.zz	0x000011	1	x		x	x	x	x
		Liquiline M DO / CM 42	V20.02.07	0x9B	21	x		x	x	x	x
			V20.03.xx	0x9B	22	x		x	x	x	x
		Liquiline M pH-ORP / CM42	V10.04.07	0x8F	11	x		x	x	x	x
			V10.05.xx	0x8F	12	x		x	x	x	x
		Mycom S cond.C / CLM 153/ V1.20	V1.20	0x99	1	x		x	x	x	x
	Knick	2211 Cond	V2*	0x00ea	2	x	x	x	x	x	x

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version						
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1	
Analytical (Continued)	Knick (Continued)	2211pH	V2*	0x00eb	2	x	x	x	x	x	x	
		2212 Condl	V2*	0x00e8	2	x	x	x	x	x	x	
	Mettler Toledo	Condl7100	V2*	0x007a	2	x	x	x	x	x	x	
			V2*	0x00078	2	x	x	x	x	x	x	
		O2 4100	V1*	0x00079	1	x	x	x	x	x	x	
		pH 2100	V2*	0x007b	2	x	x	x	x	x	x	
	Rosemount	54eC	V1*	0x0051	1	x	x	x	x	x	x	
	Simtronics AS	GD10P	V0.0*	0xE0F7	0			x	x	x	x	
	Yokogawa	ISC202	V1*	0x0014	1	x	x	x	x	x	x	
		PH202	V1*	0x0015	1	x	x	x	x	x	x	
		SC202	V1*	0x0016	1	x	x	x	x	x	x	
		ZR402	V1*	0x000c	1	x	x	x	x	x	x	
	Flow	ABB	FAM5400-HART	01.01.04	0x1B	0	x	x	x	x	x	x
			FCM2000-HART	1.04.02	0x13	0	x	x	x	x	x	x
FCXxxx			07.02.03	0x1AA0	2			x	x	x	x	
FEX100 HART WaterMaster			05.00.05	0x1F	0	x	x	x	x	x	x	
FEX300/500-HART			05.01.03	0x1E	1	x	x	x	x	x	x	
FEW5xx/FEX6xx HART			05.00.01	0x1AA4	1	x	x	x	x	x	x	
			07.01.00		1			x	x	x	x	
FMT500-HART			01.01.00	0x1C	1	x	x	x	x	x	x	
FMT4xx FMT2xx			07.01.01	0x1A27	1			x	x	x	x	
FSM4000-HART			01.01.16	0x1D	0	x	x	x	x	x	x	
FSX400 HART(1AA3)			05.01.01	0xA3	1			x	x	x	x	

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version						
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1	
Flow (Continued)	ABB (Continued)	FSX400 HART(1A9F)	05.00.01	0x9F	1		x	x	x	x	x	
		FVS4000-HART	01.01.01	0x1A	3	x	x	x	x	x	x	
		FXE4000-HART	01.01.04	0x08	0	x	x	x	x	x	x	
	Boop + Reuther Messtechnik	ES	V2*	0x00ec	2	x	x	x	x	x	x	
	Endress+ Hauser	Promag / 50		V2.02.xx	0x41	7	x		x	x	x	x
			Promag / 51	V2.02.xx	0x43	7	x		x	x	x	x
				V2.04.zz	0x43	9	x		x	x	x	x
		Promag / 53		V2.02.xx	0x42	7	x		x	x	x	x
				V2.03.zz	0x42	8	x		x	x	x	x
				V2.07.zz	0x0042	9	x		x	x	x	x
		Promag / 55		V1.01.xx	0x44	2	x		x	x	x	x
				V1.02.xx	0x44	3	x		x	x	x	x
				V1.03.zz	0x44	4	x		x	x	x	x
		Promag 100/5x1B/HART/FW 1.01.zz/Dev.Rev.2	V1.01.zz	0x003A	2	x	x	x	x	x	x	
		Promag 200/HART/FW 1.01.zz/Dev.Rev.2	V1.01.zz	0x0048	2	x	x	x	x	x	x	
		Promag 300/500		V01.00.zz	0x113C	1	x	x	x	x	x	x
				V1.01.zz	0x113C	2	x	x	x	x	x	x
				V01.05.zz	0x113C	6			x	x	x	x
		Promag 400/5x4C/HART/FW 1.05.zz/Dev.Rev.6	V1.05.zz	0x0067	6	x	x	x	x	x	x	
		Promag 400	V2.00.01	0x1169	8	x	x	x	x	x	x	

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version					
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1
Flow (Continued)	Endress+ Hauser (Continued)	Promass / 80	V2.02.0x	0x50	8	x		x	x	x	x
			V3.01.0x	0x50	9	x		x	x	x	x
		Promass / 83	V3.01.0x	0x51	9	x		x	x	x	x
			V3.07.zz	0x0051	10	x		x	x	x	x
		Promass 200/HART/FW 01.04.zz/Dev.Rev.1	V01.04.zz	0x0054	1	x	x	x	x	x	x
		Promass 300/500	V01.00.zz	0x113B	1	x	x	x	x	x	x
			V1.01.zz	0x113B	2	x	x	x	x	x	x
		Prosonic Flow / 90	V2.01.0x	0x58	5	x		x	x	x	x
		Prosonic Flow / 92	V1.00.xx	0x61	1	x		x	x	x	x
		Prosonic Flow / 93	V2.01.0x	0x59	6	x		x	x	x	x
			V2.02.0x	0x59	7	x		x	x	x	x
		Prosonic Flow / 100	V1.00.zz	0x115C	1	x	x	x	x	x	x
		Prosonic Flow B 200/ 9B2BXX/HART/FW 1.01.ZZ/Dev.Rev.1	V1.00.00	0x5A	1	x	x	x	x	x	x
		Prosonic Flow B 200 /9B2BXX/HART/FW/1.01.ZZ/Dev. Rev.2	V1.01.zz	0x5A	2	x	x	x	x	x	x
		Prosonic Flow B 200 /HART/FW 1.02.zz/Dev.Rev.3	V1.02.zz	0x005A	3	x	x	x	x	x	x
		Prowirl / 72	V1.03.xx	0x56	4	x		x	x	x	x
			V1.04.xx	0x56	5	x		x	x	x	x
			V1.05.00	0x56	6	x		x	x	x	x

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version					
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1
Flow (Continued)	Endress+ Hauser (Continued)	Prowirl /72/HART/FW 1.06.zz/Dev. Rev. 7	V1.06.zz	0x56	7	x		x	x	x	x
		Prowirl /73/HART/FW 1.06.zz/Dev. Rev. 7	V1.06.zz	0x57	7	x		x	x	x	x
		Prowirl 200/HART/FW 1.03.zz / Dev.Rev.4	V1.03.zz	0x1138	4	x		x	x	x	x
		T-mass / 65	V1.01.xx	0x65	1	x		x	x	x	x
		t-mass 150/6xABxx/HART/FW 1.00.ZZ/Dev.Rev.1	V1.01.zz	0x0066	1	x	x	x	x	x	x
		t-mass50L T 150/6xAB/HART.FW 1.00.zz/dev.rev.1	V1.01.zz	0x0068	1	x	x	x	x	x	x
Foxboro	CFT50	V2*	0x34	2	x	x	x	x	x	x	
	IMT25	V1*	0x29	1	x	x	x	x	x	x	
	TVORTEX / 183 Vortex IT	V1*	0x33	1	x	x	x	x	x	x	
Krohne	H250 ESK II HART	1.1.5	0x00f2	1	x	x	x	x	x	x	
	IFC 300	V1.0.1	0x00e3	1	x	x	x	x	x	x	
	IFC 040	V1.00.0006	0x00e9	2	x	x	x	x	x	x	
	UFC 030	V1.0.1	0x00e7	2	x	x	x	x	x	x	
	VFM 31	V1*	0x00ed	1	x	x	x	x	x	x	
Magnetrol	TA2	V2*	0x00e9	2	x	x	x	x	x	x	
Micro Motion	2700IS V07.04	V07.04	0x1F26	7	x	x	x	x	x	x	
Panametrics	XMT 868	V1*	0x00d7	1	x	x	x	x	x	x	
Rosemount	3095 MV	V2*	0x16	2	x	x	x	x	x	x	
	8712	V7*	0x003c	2	x	x	x	x	x	x	

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version					
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1
Flow (Continued)	Yokogawa	ADMAG_SE	V2*	0x08	2	x	x	x	x	x	x
		AXFA11	V1*	0x50	1	x	x	x	x	x	x
		AXFA14	V1*	0x52	1	x	x	x	x	x	x
		DYF	V2*	0x000b	2	x	x	x	x	x	x
		RAMC	V1*	0x41	1	x	x	x	x	x	x
		RCCT_F3	V1*	0x42	1	x	x	x	x	x	x
Level	ABB	AT100/AT100S/200	05.00.00	0x507x	1	x	x	x	x	x	x
		LWT Guided Wave Radar	07.01.04	0x1A9E	1			x	x	x	x
	Berthold Technologies	LB490	V3*	0x7f	3	x	x	x	x	x	x
	Endress+ Hauser	LevelflexMint / FMP 4x I	V1.08	0x20	8	x		x	x	x	x
		Levelflex / FMP 5x	V1.01.zz	0x22	2	x	x	x	x	x	x
		Levelflex/FMP5x/HART/FW1.01.z z/Dev.Rev3	V1.01.zz	0x0022	3	x	x	x	x	x	x
		LiquicapM / FMI 5x	V1.03.xx	0x1D	3	x		x	x	x	x
		Micropilot M / FMR 2xx HART	V2.0	0x0F	2	x		x	x	x	x
		Micropilot / FMR20	V1.00.zz	0x112C	1			x	x	x	x
		Micropilot /FMR5x / HART/FW/1.00.zz/Dev.Rev.1	V1.00.00	0x28	1	x	x	x	x	x	x
		Micropilot/FMR5x/HART/ FW 1.01.zz/Dev.Rev.2	V1.01.zz	0x0028	2	x	x	x	x	x	x
		Micropilot/FMR6x/HART/ FW 01.00.zz/Dev.Rev.1	V01.00.zz	0x112B	1	x	x	x	x	x	x
	Micropilot S /FMR53x	V2.00	0x10	2	x		x	x	x	x	

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version					
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1
Level (Continued)	Endress+ Hauser (Continued)	Micropilot S /FMR540	V1.01.xx	0x1F	1	x		x	x	x	x
		Prosonic S / FMU 90	V2.00.xx	0x1B	2	x		x	x	x	x
	Krohne	M8E	V1.0.0	0xE6	1	x	x	x	x	x	x
		M10	V1.00.0006	0xEA	2	x	x	x	x	x	x
	Magnetrol	704	V1*	0x00e7	1	x	x	x	x	x	x
		805	V1*	0x00ed	1	x	x	x	x	x	x
		Digital ES II	V2*	0xEF	2	x	x	x	x	x	x
	Mobrey	MLT 100	V1.3*	0x29	1	x	x	x	x	x	x
	Robertshaw Industrial	Excalibur 7000	V1*	0x00c8	1	x	x	x	x	x	x
	Rosemount	3100 V05.07	V1.4.181.1	0x50	5			x	x	x	x
	Vega	VEGAFLEX60 Series Guided Microwave DTM	2.0.0.12	0xE7	1	x	x	x	x	x	x
		VEGAPULS60 Series Radar DTM	2.0.0.12	0x00D6	5	x	x	x	x	x	x
		VEGACAL 60 Series Capacitive DTM	2.0.0.12	0xE3	1	x	x	x	x	x	x
		VEGASON 60 Series Ultrasonic DTM	2.0.0.12	0xE6	1	x	x	x	x	x	x
		VEGAWELL72	2.0.0.12	0xEB	1	x	x	x	x	x	x
		VEGAPULS31	2.0.0.12	0x62BC	2			x	x	x	x
VEGAPULS69		2.0.0.12	0x62c1	1	x	x	x	x	x	x	
Positioner	ABB	CONTRAC HART	4.02.04	0x87	1	x	x	x	x	x	x
		EDP300	05.00.03	0x1A8D	2	x	x	x	x	x	x
		TZIDC HART	05.01.04	0x41	1	x	x	x	x	x	x

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version					
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1
Positioner (Continued)	Dresser Masoneilan	SVI II AP HART 5	2.00.0	0xCA	2	x	x	x	x	x	x
	Fisher	DVC 2000	13.5	0x1305	1			x	x	x	x
		DVC 6000	V1*	0x03	1	x	x	x	x	x	x
	Flowserve	Logix 3820	1.0.0.11	0x000a	60	x	x	x	x	x	x
		Valvesight D3x	1.1.5.2	0xD3	1	x	x	x	x	x	x
		Valvesight Logix 3200MD	V1.0.0.7	0x3005	2			x	x	x	x
	Foxboro-Eckardt	SRD_960	V2	0x06	1	x	x	x	x	x	x
		SRD_991	V1*	0x01	1	x	x	x	x	x	x
	Metso	ND820	5.02	0xEF	7	x	x	x	x	x	x
		ND800/T	5.02	0xEE	7	x	x	x	x	x	x
		ND9000H	V3	0xE5	1	x	x	x	x	x	x
	Samson	3730-3 HART	1.0.22	0x00ef	5	x	x	x	x	x	x
		3780-HART	1.0.32	0x00f9	2	x	x	x	x	x	x
	SMC	IP8101	V1*	0x7E	1			x	x	x	x
	Westlock Controls Corporation	D-EPIC	V1*	0x04	1	x	x	x	x	x	x
		ICOT	V5*	0x01	5	x	x	x	x	x	x
Pressure	ABB	Pxx100 HART	07.01.02	0x1A91	1			x	x	x	x
		ST2600-HART (261)	01.01.00	0x8C	1	x	x	x	x	x	x
		2600T-264 HART	05.00.05	0x04	2	x	x	x	x	x	x
		2600T(266xxx)-PdP	07.02.00	0x1A07	2			x	x	x	x
		266-MV HART	05.00.03	0x8E	1	x	x	x	x	x	x
		2600T-266-PdP HART	05.00.07	0x07	2	x	x	x	x	x	x

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version					
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1
Pressure (Continued)	ABB (Continued)	364-HART	01.00.02	0x05	1	x	x	x	x	x	x
		HI2600-HART	02.00.02	0x04	2	x	x	x	x	x	x
		MV2600-HART	01.02.05	0x8A	2	x	x	x	x	x	x
		ST2600-HART	1.00.00	0x8C	1	x	x	x	x	x	x
		TO-2600-HART	01.02.05	0x89	2	x	x	x	x	x	x
	Anderson Instrument Co.	ANDRSN1	V1*	0x00c8	1	x	x	x	x	x	x
	Bourdon-Haenni	FlexBar 816x	V1*	0xEE	1	x	x	x	x	x	x
	Dynisco Instruments	IPX I Series	V1*	0x00e0	1	x	x	x	x	x	x
		IPX II Series	V1*	0x00df	1	x	x	x	x	x	x
	Druck	RTX 1000H Gauge	V1*	0x00e9	1	x	x	x	x	x	x
	Endress+ Hauser	Cerebar M / PMx5x	V1.00.xx	0x19	1	x		x	x	x	x
		Deltabar FMD 7x	V1.00.xx	0x27	1	x		x	x	x	x
		Deltabar M 5x / PMD55	V1.00.xx	0x21	1	x		x	x	x	x
		Waterpilot 2x / FMX21	V1.00.xx	0x24	1	x		x	x	x	x
	Foxboro	I/A Series Pressure	V1*	0x002e	1	x	x	x	x	x	x
			V3*	0x142E	3			x	x	x	x
	Fuji	FCX-A2/C2	V2*	0x02	2	x	x	x	x	x	x
	GP:50 New York Ltd.	430RHAA	V1*	0x007c	1	x	x	x	x	x	x
	Honeywell	ST 3000	V2*	0x01	2	x	x	x	x	x	x
	Omega	PX2088	V3*	0x23	3	x	x	x	x	x	x

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version						
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1	
Pressure (Continued)	Paper Machine Components	SMT-EL	V1*	0xE0	1	x	x	x	x	x	x	
	Rosemount	1151s	V6*	0x03	6	x	x	x	x	x	x	
		2051	V10.02	0x2655	10			x	x	x	x	
		2088	V3*	0x23	3	x	x	x	x	x	x	
		2090	V3*	0x27	3	x	x	x	x	x	x	
		3051C		V3*	0x06	3	x	x	x	x	x	x
				V7*	0x06	7	x	x	x	x	x	x
		3051S Diag	V03.01	0x4A	3			x	x	x	x	
	Satron Instruments	PSMART	V2*	0x007f	2	x	x	x	x	x	x	
	Siemens	SITRANS P DS	V3*	0x000b	3	x	x	x	x	x	x	
		SITRANS P MS	V1*	0x000d	1	x	x	x	x	x	x	
	Smar	LD301	V3*	0x01	3	x	x	x	x	x	x	
			V4*	0x01	4	x	x	x	x	x	x	
	Vega	VEGABAR 50 and 60 Series Pressure DTM	2.0.0.12	0xE2	1			x	x	x	x	
	Viatran	970	V2*	0x01	2	x	x	x	x	x	x	
	Yamatake Corporation	DST J3000	V1*	0x02	1	x	x	x	x	x	x	
		PTG	V1*	0x05	1	x	x	x	x	x	x	
	Yokogawa	EJA Series	V2*	0x04	2	x	x	x	x	x	x	
	Temperature	ABB	THx02-HART	1.00.11	0x08	1	x	x	x	x	x	x
			TTX200-HART	05.00.03	0x0D	2	x	x	x	x	x	x
TTX300-HART			05.00.15	0x0B	2	x	x	x	x	x	x	

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version					
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1
Temperature (Continued)	Accutech	AI1500	V1*	0x00ef	1	x	x	x	x	x	x
	Bourdon-Haenni	FlexTop 2221	V2*	0x00ef	2	x	x	x	x	x	x
	Endress+ Hauser	iTemp/TMT 122	V1.1	0xC9	1	x		x	x	x	x
		iTemp/TMT 162	V1.03.00	0xCA	2	x		x	x	x	x
		iTEMP/TMT82/HART/FW 1.01.zz/Dev.Rev 2	V1.01.zz	0x00CC	2	x	x	x	x	x	x
		iTEMP/TMT82/HART/FW 1.02.zz/Dev.Rev 3	V1.02.zz	0x11CC	3		x	x	x	x	x
		Foxboro	RTT15	V1*	0x38	1	x	x	x	x	x
		RTT20	V1*	0x03	1	x	x	x	x	x	x
	Fuji	FRC	V1*	0x81	1	x	x	x	x	x	x
	Honeywell	STT17H	V1*	0x07	1	x	x	x	x	x	x
		STT25H	V1*	0x04	1	x	x	x	x	x	x
		STT25T	V1*	0x02	1	x	x	x	x	x	x
	Inor Process AB	MESO	V1*	0x00ef	1	x	x	x	x	x	x
	Krohne	TT50C/R	V1*	0x00db	1	x	x	x	x	x	x
	M-Systems Co., Ltd.	B6U	V1*	0x01	1	x	x	x	x	x	x
	PR electronics	Pretop 5335	V1*	0x00ef	1	x	x	x	x	x	x
		Pretrans 6335	V1*	0x00ee	1	x	x	x	x	x	x
	Pyromatic Inc.,	Series442	V21*	0x007f	1	x	x	x	x	x	x

Category	Manufacturer	Device Name	DTM Version	Device Type ID (Hex)	Device Revision	Supported Engineering Version					
						2013 SP1	2016	2016 SP1	2019	2019 SP1	2019 SP1 FP1
Temperature (Continued)	Rosemount	248	V1*	0x003b	1	x	x	x	x	x	x
		3144P	V3*	0x19	3	x	x	x	x	x	x
		3144	V4*	0x19	4	x	x	x	x	x	x
		644	V6*	0x18	6	x	x	x	x	x	x
			V7*	0x18	7	x	x	x	x	x	x
			V09.01	0x18	9			x	x	x	x
	Siemens	SITRANS TK-H	V2*	0x13	2	x	x	x	x	x	x
	Smar	TT301	V3*	0x02	2	x	x	x	x	x	x
	Status Instruments	SEM300	V1*	0x00ef	2	x	x	x	x	x	x
	WIKA	T32	V2*	0x00ef	2	x	x	x	x	x	x
Yamatake Corporation	ATT60	V1*	0x04	1	x	x	x	x	x	x	
Yokogawa	YTA Series	V2*	0x09	2	x	x	x	x	x	x	
Various	Metso	VG800	V3.0	0xEB	1.1	x	x	x	x	x	x

Note

- 1.(VX*) - This version refers to ABB 3rd Party DTM Library. For more details about the device specific DTM version, refer to the 'ABB 3rd Party HART DTM Library' release notes with document ID 2PAA107705RXX inside ABB Library.
- 2.Due to size constraint, Endress + Hauser HART DTM Library is published in .zip format inside ABB Library with document ID 2PAA107704SXX.



Visit us

solutions.abb/controlsystems